

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P147707

Luminaire Tested: **VXS-F03-LED-E1-5WQ-7060**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P147707  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: VXS-F03-LED-E1-5WQ-7060  
Description: VISION SITE SMALL LED LUMINAIRE  
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE  
Light Source: (21) 5700K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8090.8 lumens  
Efficiency: N/A  
Efficacy: 103.3 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type V - Short - Semi-Cutoff  
BUG Rating: B3 - U0 - G2


Input Watts (W): 78.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P147707  
 CATALOG NUMBER: VXS-F03-LED-E1-5WQ-7060

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.9 fc  
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P147707  
CATALOG NUMBER: VXS-F03-LED-E1-5WQ-7060

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P147707

CATALOG NUMBER: VXS-F03-LED-E1-5WQ-7060


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	4045.4	0.0	4045.4
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	4045.4	0.0	4045.4
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	8090.8	0.0	8090.8
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.2	0.5
10°-20°	149.0	1.8
20°-30°	301.7	3.7
30°-40°	505.8	6.3
40°-50°	892.1	11.0
50°-60°	1573.2	19.4
60°-70°	2401.8	29.7
70°-80°	2007.0	24.8
80°-90°	218.1	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8090.8	100.0
0°-180°	8090.8	100.0



REPORT NUMBER: P147707


CATALOG NUMBER: VXS-F03-LED-E1-5WQ-7060

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	246.4	3.0			
FM	(30°-60°)	1485.5	18.4			
FH	(60°-80°)	2204.4	27.2			G2/5000
FVH	(80°-90°)	109.0	1.3			G2/225
BL	(0°-30°)	246.4	3.0	B1/500		
BM	(30°-60°)	1485.5	18.4	B2/2500		
BH	(60°-80°)	2204.4	27.2	B3/2500		G2/5000
BVH	(80°-90°)	109.0	1.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G2**

Type V Short





REPORT NUMBER: P147707

CATALOG NUMBER: VXS-F03-LED-E1-5WQ-7060

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	420.1	420.1	420.1	420.1	420.1	420.1	420.1	420.1	420.1	420.1	420.1
2.5°	423.5	424.4	423.5	423.5	423.5	423.5	423.5	422.7	422.7	422.7	423.5
5°	432.0	432.8	432.0	432.8	432.8	432.8	432.8	432.0	432.0	432.0	432.0
7.5°	445.6	445.6	445.6	446.4	445.6	445.6	446.4	445.6	445.6	445.6	445.6
10°	465.1	464.2	464.2	464.2	464.2	464.2	465.1	465.1	465.1	464.2	464.2
12.5°	488.8	487.9	488.8	488.8	489.6	489.6	489.6	489.6	489.6	489.6	488.8
15°	517.5	517.5	517.5	518.4	520.1	520.1	519.3	520.1	520.1	520.1	520.1
17.5°	549.7	551.4	549.7	550.6	551.4	550.6	552.3	553.2	554.0	553.2	550.6
20°	582.8	583.6	583.6	583.6	583.6	585.3	586.2	586.2	588.7	587.9	587.0
22.5°	614.1	615.9	615.9	616.7	616.7	619.2	619.2	619.2	620.9	622.6	620.9
25°	647.2	646.3	646.3	648.0	648.8	652.2	652.2	654.0	656.5	657.3	655.6
27.5°	676.8	676.0	676.0	678.5	679.4	683.6	683.6	686.9	688.7	689.5	687.9
30°	708.2	708.2	707.4	709.8	712.4	715.8	717.5	720.8	723.4	724.2	722.6
32.5°	745.4	743.7	744.6	746.3	748.0	751.4	753.9	758.1	761.6	762.4	760.7
35°	787.8	785.3	786.1	787.8	790.4	795.4	799.7	802.2	807.3	808.9	805.6
37.5°	834.4	835.2	834.4	838.7	842.8	848.8	853.9	857.2	862.3	864.9	862.3
40°	900.4	897.9	900.4	904.7	911.5	919.1	929.2	931.8	936.9	942.0	936.1
42.5°	986.0	984.4	990.3	993.6	1001.2	1009.7	1022.4	1029.2	1036.8	1040.2	1035.1
45°	1097.8	1097.8	1104.6	1105.4	1117.3	1128.3	1146.1	1154.6	1169.0	1169.0	1169.0
47.5°	1221.5	1226.5	1230.8	1239.3	1247.8	1268.1	1285.9	1304.5	1318.0	1319.8	1317.2
50°	1349.4	1354.5	1367.2	1379.1	1397.7	1423.1	1442.6	1467.2	1479.0	1489.1	1485.8
52.5°	1490.9	1491.7	1506.9	1522.2	1549.3	1577.3	1608.6	1634.0	1655.2	1664.5	1656.9
55°	1645.9	1647.6	1661.1	1677.2	1707.7	1739.9	1778.9	1805.1	1832.2	1849.1	1836.5
57.5°	1813.6	1814.4	1828.0	1847.5	1883.9	1916.1	1953.4	1990.7	2016.1	2031.3	2022.8
60°	1999.1	2003.3	2013.5	2038.0	2072.7	2106.6	2143.9	2177.0	2206.6	2222.7	2214.3
62.5°	2197.3	2201.6	2216.0	2235.4	2265.9	2303.2	2338.8	2381.1	2405.7	2423.5	2410.8
65°	2330.3	2337.9	2360.8	2387.0	2431.9	2480.2	2521.8	2579.4	2609.0	2630.2	2618.3
67.5°	2338.8	2343.0	2371.0	2410.8	2470.9	2543.7	2628.5	2718.2	2776.7	2804.7	2784.4
69°	2281.1	2287.2	2314.2	2359.1	2426.0	2510.8	2611.5	2723.3	2813.2	2854.6	2835.1
70°	2216.0	2228.7	2258.3	2307.5	2372.6	2461.6	2565.8	2685.2	2790.3	2847.0	2832.6
72.5°	2078.8	2082.1	2101.6	2140.5	2190.6	2264.2	2362.5	2475.1	2575.1	2656.5	2668.3
75°	1845.0	1856.0	1870.4	1896.6	1922.0	1975.3	2041.5	2118.5	2177.0	2239.7	2242.2
77.5°	1394.3	1427.4	1438.3	1444.2	1455.2	1497.6	1555.2	1622.2	1670.5	1680.6	1678.9
80°	626.0	670.1	680.2	728.5	758.1	828.4	916.6	1019.1	1087.7	1095.2	1076.7
82.5°	122.8	131.3	153.4	191.4	260.9	302.4	360.0	432.0	498.0	536.2	513.4
85°	40.6	43.2	49.9	55.0	63.5	72.0	87.3	108.4	134.7	149.1	133.0
87.5°	16.1	16.1	18.7	20.3	22.1	22.1	22.1	20.3	19.5	16.1	14.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147707

CATALOG NUMBER: VXS-F03-LED-E1-5WQ-7060

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	420.1	420.1	420.1	420.1	420.1	420.1	420.1	420.1
2.5°	422.7	422.7	422.7	422.7	422.7	422.7	422.7	422.7
5°	432.0	431.2	431.2	430.4	430.4	430.4	430.4	430.4
7.5°	444.7	443.8	443.0	443.8	443.0	443.0	443.0	443.0
10°	464.2	462.5	461.7	460.8	460.8	460.8	460.0	460.0
12.5°	487.0	487.0	486.2	485.4	483.7	484.6	483.7	482.0
15°	518.4	516.7	515.9	515.0	513.4	513.4	513.4	512.4
17.5°	549.7	548.1	548.1	545.5	544.7	544.7	544.7	545.5
20°	584.5	582.0	580.2	578.5	576.9	577.7	576.1	577.7
22.5°	619.2	615.9	614.1	611.6	609.0	609.0	608.2	606.5
25°	653.1	648.8	647.2	644.7	641.2	641.2	639.6	637.8
27.5°	685.3	681.0	679.4	674.3	670.9	670.1	668.4	667.5
30°	720.8	715.8	713.3	708.2	703.1	702.2	699.7	699.7
32.5°	758.1	753.1	751.4	743.7	739.5	739.5	737.8	736.1
35°	804.8	797.1	795.4	787.8	781.9	781.9	780.2	781.0
37.5°	859.8	853.9	847.9	842.0	835.2	834.4	832.6	831.0
40°	933.5	926.7	919.9	911.5	905.5	903.8	901.2	900.4
42.5°	1031.7	1025.0	1011.4	1004.7	998.7	993.6	992.7	991.9
45°	1157.1	1148.6	1139.3	1126.6	1119.0	1108.0	1106.3	1102.1
47.5°	1307.9	1291.8	1275.6	1264.7	1252.8	1240.1	1237.6	1230.8
50°	1468.0	1455.2	1428.2	1410.4	1391.7	1379.1	1370.6	1368.0
52.5°	1639.9	1616.3	1589.1	1565.4	1538.2	1521.3	1506.1	1501.9
55°	1819.5	1785.6	1751.7	1723.8	1696.7	1676.4	1662.0	1655.2
57.5°	1999.1	1961.9	1924.6	1894.1	1871.2	1845.0	1830.6	1827.2
60°	2186.3	2150.7	2112.6	2082.1	2054.2	2031.3	2022.8	2006.7
62.5°	2384.6	2347.3	2311.7	2282.1	2246.4	2230.4	2216.0	2206.6
65°	2579.4	2536.2	2491.3	2459.9	2424.4	2401.5	2383.6	2371.0
67.5°	2730.2	2664.9	2604.8	2552.2	2503.9	2468.4	2445.5	2433.7
69°	2772.4	2691.2	2614.1	2545.5	2488.7	2448.9	2423.5	2411.6
70°	2767.4	2677.6	2592.8	2517.5	2455.6	2413.4	2388.7	2366.7
72.5°	2610.7	2528.5	2434.5	2352.3	2296.4	2255.8	2231.2	2219.4
75°	2227.8	2172.7	2105.0	2041.5	2000.8	1977.1	1946.5	1947.5
77.5°	1622.2	1623.8	1578.1	1512.8	1467.2	1458.7	1445.1	1431.6
80°	1006.3	925.8	873.4	803.0	751.4	706.4	686.9	644.7
82.5°	464.2	362.6	281.2	212.6	163.5	127.9	111.8	91.5
85°	103.3	78.8	65.2	52.5	44.9	41.6	33.9	31.3
87.5°	14.4	12.7	11.8	11.0	9.3	6.7	5.1	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)