

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P155447

Luminaire Tested: **VXS-F04-LED-E1-T3-7060**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P155447
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F04-LED-E1-T3-7060
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 3
Light Source: (28) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10449.3 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G3

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P155447

CATALOG NUMBER: VXS-F04-LED-E1-T3-7060

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 2.8 fc
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P155447

CATALOG NUMBER: VXS-F04-LED-E1-T3-7060

Luminous Intensity Polar Plot



— Vertical Plane Through 67.5-Deg Lateral - - - Horizontal Cone Through 66-Deg Vertical

REPORT NUMBER: P155447

CATALOG NUMBER: VXS-F04-LED-E1-T3-7060

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3608.5	0.0	3608.5
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	6840.8	0.0	6840.8
	% Fixture	65.5	0.0	65.5
Total	Lumens	10449.3	0.0	10449.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.9	1.0
10°-20°	318.3	3.0
20°-30°	547.0	5.2
30°-40°	888.2	8.5
40°-50°	1482.9	14.2
50°-60°	2335.1	22.3
60°-70°	3184.1	30.5
70°-80°	1378.4	13.2
80°-90°	207.3	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10449.3	100.0
0°-180°	10449.3	100.0

Coefficient of Utilization



REPORT NUMBER: P155447


CATALOG NUMBER: VXS-F04-LED-E1-T3-7060

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	488.8	4.7			
FM	(30°-60°)	2918.1	27.9			
FH	(60°-80°)	3263.7	31.2			G2/5000
FVH	(80°-90°)	170.2	1.6			G2/225
BL	(0°-30°)	484.4	4.6	B1/500		
BM	(30°-60°)	1788.1	17.1	B2/2500		
BH	(60°-80°)	1298.9	12.4	B3/2500		G3/2500
BVH	(80°-90°)	37.1	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type III Short





REPORT NUMBER: P155447

CATALOG NUMBER: VXS-F04-LED-E1-T3-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0
2.5°	1130.6	1135.1	1130.6	1131.7	1132.8	1131.7	1130.6	1130.6	1127.2	1129.4	1131.7
5°	1126.0	1129.4	1128.3	1129.4	1130.6	1129.4	1128.3	1129.4	1127.2	1128.3	1131.7
7.5°	1120.4	1119.3	1120.4	1122.7	1124.9	1124.9	1124.9	1126.0	1124.9	1124.9	1128.3
10°	1103.4	1104.6	1106.8	1110.3	1111.4	1114.7	1114.7	1118.1	1119.3	1121.6	1126.0
12.5°	1082.0	1083.1	1085.4	1087.7	1093.3	1099.0	1099.0	1106.8	1110.3	1115.9	1123.8
15°	1066.2	1067.4	1069.5	1071.8	1076.4	1082.0	1085.4	1094.4	1100.1	1110.3	1121.6
17.5°	1075.2	1074.1	1076.4	1077.5	1077.5	1082.0	1082.0	1088.8	1095.5	1104.6	1119.3
20°	1101.2	1101.2	1103.4	1103.4	1102.3	1104.6	1100.1	1100.1	1101.2	1105.7	1115.9
22.5°	1127.2	1126.0	1130.6	1132.8	1134.0	1137.3	1132.8	1131.7	1126.0	1122.7	1126.0
25°	1152.0	1150.9	1156.6	1159.9	1165.6	1169.0	1169.0	1169.0	1164.5	1158.8	1155.4
27.5°	1190.5	1190.5	1196.1	1199.5	1203.9	1210.8	1214.1	1214.1	1215.2	1207.4	1201.8
30°	1254.8	1256.0	1257.1	1261.6	1266.1	1268.4	1272.8	1276.3	1279.7	1275.1	1266.1
32.5°	1331.6	1324.9	1324.9	1331.6	1337.2	1344.0	1346.3	1350.8	1357.6	1354.2	1353.1
35°	1423.1	1420.8	1418.5	1420.8	1427.6	1435.5	1444.6	1452.4	1448.0	1454.7	1451.3
37.5°	1558.7	1560.8	1562.0	1562.0	1560.8	1563.1	1567.7	1575.5	1573.3	1575.5	1580.1
40°	1782.3	1774.3	1766.4	1767.6	1756.3	1758.5	1740.4	1748.4	1749.5	1741.6	1745.0
42.5°	2005.9	2010.4	2013.8	2022.8	2014.9	2010.4	1993.5	1993.5	1984.5	1976.5	1974.3
45°	2247.6	2256.6	2257.7	2275.9	2269.0	2283.7	2296.2	2292.7	2278.0	2276.9	2261.1
47.5°	2440.7	2455.4	2471.2	2492.6	2509.6	2542.4	2580.7	2600.0	2611.3	2620.3	2602.2
50°	2585.3	2592.0	2632.7	2666.6	2703.8	2758.0	2811.2	2880.1	2935.4	2961.3	2986.2
52.5°	2663.2	2680.1	2724.1	2777.3	2842.8	2924.1	3009.9	3119.5	3214.4	3277.6	3334.1
55°	2680.1	2697.1	2746.7	2814.5	2903.7	3013.4	3136.5	3285.5	3427.9	3549.8	3668.4
57.5°	2632.7	2651.9	2705.0	2782.9	2888.0	3021.2	3176.0	3371.4	3567.9	3765.5	3940.6
60°	2545.7	2569.4	2618.0	2694.8	2811.2	2961.3	3146.6	3391.7	3667.3	3969.9	4305.4
62.5°	2402.3	2427.2	2472.3	2557.0	2676.8	2842.8	3057.4	3362.3	3752.0	4228.6	4823.8
65°	2171.9	2183.2	2238.5	2324.4	2430.6	2613.5	2849.5	3217.7	3724.9	4387.9	5207.8
66°	2068.0	2087.2	2121.0	2189.9	2291.6	2463.3	2700.5	3074.3	3622.1	4332.5	5197.6
67.5°	1905.4	1920.0	1942.6	1988.9	2051.1	2177.5	2402.3	2755.9	3308.1	4052.4	4982.0
70°	1540.5	1547.4	1577.8	1593.7	1615.1	1656.9	1738.2	1941.5	2371.8	3070.9	4020.8
72.5°	1050.4	1069.5	1102.3	1147.5	1206.2	1262.7	1301.1	1327.0	1419.7	1831.9	2679.1
75°	770.3	790.6	832.4	892.2	995.0	1112.5	1234.5	1291.0	1252.5	1199.5	1492.0
77.5°	447.3	474.4	509.3	566.9	661.9	817.7	1026.6	1211.9	1337.2	1345.2	1277.4
80°	188.6	192.0	213.5	242.8	301.6	411.1	573.8	840.3	1118.1	1305.6	1349.6
82.5°	42.9	53.1	67.8	80.2	98.2	135.5	201.0	334.3	604.2	947.6	1235.6
85°	15.9	15.9	21.5	31.6	36.2	40.6	53.1	84.7	144.6	266.5	555.6
87.5°	0.0	1.1	2.3	2.3	4.6	5.6	9.0	12.4	11.3	10.2	33.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155447

CATALOG NUMBER: VXS-F04-LED-E1-T3-7060

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0
2.5°	1129.4	1128.3	1126.0	1126.0	1126.0	1126.0	1123.8	1124.9	1122.7	1123.8	1123.8
5°	1128.3	1128.3	1127.2	1124.9	1126.0	1126.0	1127.2	1124.9	1124.9	1126.0	1124.9
7.5°	1128.3	1127.2	1127.2	1127.2	1128.3	1127.2	1128.3	1128.3	1128.3	1129.4	1129.4
10°	1128.3	1128.3	1130.6	1131.7	1131.7	1132.8	1136.2	1136.2	1137.3	1138.4	1140.7
12.5°	1129.4	1134.0	1137.3	1140.7	1141.9	1144.1	1149.7	1149.7	1152.0	1155.4	1156.6
15°	1130.6	1137.3	1144.1	1146.4	1148.6	1153.2	1158.8	1161.0	1164.5	1167.9	1170.1
17.5°	1129.4	1138.4	1146.4	1149.7	1153.2	1158.8	1165.6	1167.9	1172.3	1176.9	1181.3
20°	1128.3	1140.7	1153.2	1157.7	1162.2	1170.1	1179.2	1184.8	1189.3	1196.1	1200.6
22.5°	1135.1	1149.7	1166.7	1173.5	1181.3	1191.5	1203.9	1210.8	1216.4	1223.2	1226.5
25°	1156.6	1167.9	1188.2	1199.5	1209.6	1226.5	1243.5	1251.4	1258.2	1263.8	1265.0
27.5°	1192.6	1196.1	1220.9	1235.6	1250.3	1277.4	1297.7	1303.3	1315.8	1320.3	1319.2
30°	1251.4	1245.8	1266.1	1288.7	1310.2	1347.5	1372.2	1386.9	1398.2	1398.2	1389.2
32.5°	1336.2	1327.0	1332.7	1358.8	1383.5	1437.7	1467.2	1486.3	1494.2	1492.0	1472.7
35°	1446.8	1441.1	1437.7	1458.1	1497.6	1560.8	1599.3	1609.4	1621.9	1619.6	1594.7
37.5°	1577.8	1573.3	1573.3	1597.0	1635.4	1729.1	1771.0	1777.7	1776.6	1758.5	1712.2
40°	1732.5	1730.3	1720.1	1733.7	1766.4	1888.4	1944.9	1953.9	1941.5	1912.1	1857.9
42.5°	1955.0	1941.5	1909.8	1917.8	1942.6	2061.2	2134.6	2159.5	2147.0	2117.7	2029.6
45°	2245.3	2230.7	2177.5	2170.8	2184.4	2288.2	2383.1	2388.7	2386.5	2349.2	2245.3
47.5°	2586.4	2563.8	2507.4	2489.2	2484.8	2580.7	2672.2	2681.2	2675.6	2620.3	2481.3
50°	2955.8	2923.0	2885.7	2873.3	2855.2	2924.1	3016.7	3017.8	2995.2	2918.4	2788.6
52.5°	3349.9	3338.7	3331.8	3319.4	3311.5	3371.4	3427.9	3394.0	3360.1	3279.9	3166.9
55°	3747.5	3793.8	3841.2	3845.7	3859.3	3923.6	3922.5	3829.9	3805.1	3761.0	3649.2
57.5°	4169.8	4341.6	4490.7	4536.9	4582.1	4701.9	4690.6	4599.1	4567.5	4513.3	4420.6
60°	4744.8	5207.8	5638.1	5740.9	5812.0	5955.5	5942.0	5800.7	5866.3	5861.8	5742.1
62.5°	5550.1	6320.3	6965.2	7123.3	7173.1	7188.8	7103.0	6950.6	7014.9	7087.2	6719.0
65°	6095.5	7001.3	7663.2	7785.2	7791.9	7603.3	7412.4	7232.8	7217.1	7154.9	6628.6
66°	6108.0	7035.2	7699.4	7817.9	7776.2	7518.7	7277.0	7096.3	7018.3	6881.7	6336.2
67.5°	5888.9	6824.0	7539.0	7664.4	7572.8	7208.1	6874.8	6642.2	6489.7	6268.4	5787.3
70°	4945.8	5873.1	6754.0	6987.8	7017.2	6472.7	6010.9	5737.5	5531.9	5228.2	4813.7
72.5°	3677.4	4515.4	5292.5	5516.2	5630.3	5195.4	4805.7	4597.9	4316.7	3997.1	3702.3
75°	2305.2	2897.0	3417.6	3574.6	3467.4	3130.8	2897.0	2810.1	2533.4	2342.5	2208.1
77.5°	1318.0	1503.3	1545.1	1485.2	1358.8	1040.2	739.8	547.8	475.4	526.3	580.5
80°	1286.4	1179.2	939.7	826.7	748.8	515.0	302.7	207.8	172.8	177.3	192.0
82.5°	1393.7	1495.3	1231.1	1004.0	842.6	569.2	314.0	167.2	113.0	133.3	150.3
85°	905.8	1260.4	1135.1	956.6	774.8	486.7	258.7	86.9	57.6	75.6	103.9
87.5°	91.5	100.5	85.8	116.4	86.9	40.6	20.3	12.4	11.3	13.6	20.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155447

CATALOG NUMBER: VXS-F04-LED-E1-T3-7060

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0	1126.0
2.5°	1124.9	1124.9	1126.0	1127.2	1128.3	1129.4	1129.4	1129.4	1129.4	1131.7	1130.6
5°	1127.2	1129.4	1131.7	1132.8	1135.1	1135.1	1138.4	1137.3	1137.3	1140.7	1141.9
7.5°	1131.7	1135.1	1139.6	1138.4	1143.0	1141.9	1144.1	1144.1	1140.7	1141.9	1139.6
10°	1141.9	1146.4	1148.6	1145.3	1146.4	1141.9	1140.7	1135.1	1128.3	1124.9	1120.4
12.5°	1158.8	1163.3	1163.3	1157.7	1150.9	1140.7	1132.8	1120.4	1110.3	1104.6	1099.0
15°	1173.5	1178.0	1176.9	1167.9	1157.7	1141.9	1130.6	1115.9	1101.2	1092.1	1086.5
17.5°	1184.8	1187.0	1183.6	1171.2	1159.9	1145.3	1134.0	1118.1	1101.2	1089.9	1079.7
20°	1201.8	1199.5	1191.5	1175.8	1163.3	1149.7	1140.7	1127.2	1108.0	1093.3	1078.7
22.5°	1226.5	1217.5	1202.8	1185.9	1173.5	1161.0	1152.0	1137.3	1118.1	1100.1	1083.1
25°	1259.3	1241.2	1220.9	1202.8	1191.5	1178.0	1167.9	1152.0	1131.7	1111.4	1091.0
27.5°	1306.7	1275.1	1249.1	1233.4	1220.9	1203.9	1191.5	1171.2	1149.7	1126.0	1103.4
30°	1359.8	1316.9	1292.1	1279.7	1266.1	1248.0	1228.8	1202.8	1178.0	1152.0	1124.9
32.5°	1428.7	1376.8	1353.1	1340.6	1322.6	1300.0	1277.4	1248.0	1213.1	1179.2	1146.4
35°	1519.1	1466.0	1441.1	1422.0	1397.1	1367.8	1335.0	1295.4	1248.0	1202.8	1161.0
37.5°	1616.3	1558.7	1534.9	1514.6	1477.3	1438.9	1392.6	1335.0	1270.6	1210.8	1158.8
40°	1739.4	1686.2	1655.8	1620.7	1576.7	1510.1	1437.7	1354.2	1271.7	1198.3	1137.3
42.5°	1895.2	1842.1	1796.9	1741.6	1664.8	1562.0	1459.3	1350.8	1251.4	1167.9	1102.3
45°	2101.9	2037.5	1959.6	1862.5	1738.2	1594.7	1460.3	1329.3	1213.1	1120.4	1050.4
47.5°	2354.8	2256.6	2129.0	1965.2	1786.7	1603.8	1442.3	1286.4	1153.2	1052.6	974.7
50°	2655.3	2500.5	2290.5	2049.9	1811.6	1590.3	1397.1	1222.1	1068.4	961.1	868.5
52.5°	2998.7	2745.7	2436.2	2110.9	1810.5	1545.1	1320.3	1124.9	957.7	838.0	749.9
55°	3401.9	3025.8	2586.4	2156.1	1778.9	1461.5	1202.8	988.3	821.1	710.4	629.1
57.5°	3992.5	3479.8	2848.4	2226.1	1715.6	1332.7	1043.6	824.5	677.6	572.6	503.7
60°	5072.3	4237.6	3320.5	2367.3	1618.4	1144.1	857.2	649.4	526.3	441.7	395.3
62.5°	5885.5	4823.8	3575.8	2335.6	1423.1	911.5	635.9	473.3	387.4	329.8	300.4
65°	5769.1	4642.0	3303.6	2011.5	1115.9	642.7	422.4	321.9	266.5	239.5	222.5
66°	5506.0	4404.8	3067.6	1810.5	964.6	534.2	347.9	269.9	229.3	210.1	198.8
67.5°	5006.7	3964.4	2645.2	1484.0	740.9	387.4	262.1	213.5	186.3	178.4	170.6
70°	4162.0	3161.2	1856.8	864.0	378.3	215.8	166.0	149.1	142.3	141.1	139.0
72.5°	3189.5	2237.4	1093.3	408.8	196.5	143.4	128.7	123.1	120.8	120.8	122.0
75°	1955.0	1257.1	483.4	199.9	137.8	120.8	114.1	111.8	110.7	111.8	110.7
77.5°	652.8	399.8	206.7	151.3	125.4	111.8	107.3	105.1	105.1	105.1	105.1
80°	199.9	173.9	158.1	140.0	118.5	106.2	99.4	98.2	99.4	100.5	97.1
82.5°	150.3	142.3	133.3	124.2	107.3	94.9	92.6	92.6	92.6	89.2	84.7
85°	110.7	109.5	90.4	84.7	79.1	79.1	79.1	79.1	75.6	70.1	65.5
87.5°	20.3	19.2	20.3	21.5	31.6	33.9	33.9	36.2	39.5	37.3	37.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155447

CATALOG NUMBER: VXS-F04-LED-E1-T3-7060

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	1126.0	1126.0	1126.0	1126.0	1126.0
2.5°	1130.6	1129.4	1132.8	1130.6	1131.7
5°	1140.7	1139.6	1141.9	1139.6	1143.0
7.5°	1137.3	1135.1	1134.0	1135.1	1136.2
10°	1113.6	1111.4	1110.3	1109.1	1110.3
12.5°	1093.3	1088.8	1088.8	1086.5	1087.7
15°	1078.7	1075.2	1074.1	1071.8	1073.0
17.5°	1071.8	1066.2	1063.9	1061.7	1061.7
20°	1067.4	1060.5	1057.2	1054.9	1053.8
22.5°	1067.4	1057.2	1052.6	1050.4	1049.2
25°	1071.8	1059.4	1052.6	1049.2	1048.1
27.5°	1080.8	1065.1	1057.2	1052.6	1052.6
30°	1096.7	1076.4	1065.1	1059.4	1058.2
32.5°	1112.5	1085.4	1069.5	1062.8	1060.5
35°	1120.4	1085.4	1066.2	1054.9	1052.6
37.5°	1111.4	1070.7	1046.9	1030.1	1026.6
40°	1083.1	1040.2	1014.2	998.4	996.2
42.5°	1045.9	1004.0	973.6	962.3	958.9
45°	995.0	945.3	914.8	899.1	900.2
47.5°	908.1	857.2	830.2	815.4	817.7
50°	805.3	755.5	731.9	716.1	719.5
52.5°	692.3	647.2	624.6	616.7	614.4
55°	573.8	538.8	522.9	513.9	510.5
57.5°	465.3	440.5	429.2	417.9	419.1
60°	367.0	354.6	351.3	338.9	337.7
62.5°	289.1	281.2	277.8	268.8	269.9
65°	219.1	216.9	219.1	213.5	215.8
66°	197.6	198.8	198.8	195.4	197.6
67.5°	170.6	172.8	176.2	172.8	175.0
70°	141.1	143.4	145.7	145.7	145.7
72.5°	123.1	125.4	126.5	126.5	126.5
75°	113.0	114.1	115.2	113.0	113.0
77.5°	106.2	106.2	103.9	102.8	101.7
80°	96.0	94.9	91.5	89.2	89.2
82.5°	80.2	77.9	75.6	72.3	72.3
85°	61.0	58.8	56.5	51.9	49.7
87.5°	31.6	32.7	31.6	26.0	22.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)