

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P148213

Luminaire Tested: **VXS-F02-LED-E1-5XQ-8030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P148213
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F02-LED-E1-5XQ-8030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (14) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4431.8 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B3 - U0 - G2

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P148213

CATALOG NUMBER: VXS-F02-LED-E1-5XQ-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.2 fc
Type V - Short - Non-Cutoff

REPORT NUMBER: P148213

CATALOG NUMBER: VXS-F02-LED-E1-5XQ-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P148213

CATALOG NUMBER: VXS-F02-LED-E1-5XQ-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2215.9	0.0	2215.9
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2215.9	0.0	2215.9
	% Fixture	50.0	0.0	50.0
Total	Lumens	4431.8	0.0	4431.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.0	0.9
10°-20°	118.4	2.7
20°-30°	198.2	4.5
30°-40°	302.2	6.8
40°-50°	482.5	10.9
50°-60°	741.9	16.7
60°-70°	1080.3	24.4
70°-80°	1216.9	27.5
80°-90°	251.2	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4431.8	100.0
0°-180°	4431.8	100.0

Coefficient of Utilization



REPORT NUMBER: P148213


CATALOG NUMBER: VXS-F02-LED-E1-5XQ-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	178.3	4.0			
FM	(30°-60°)	763.3	17.2			
FH	(60°-80°)	1148.6	25.9			G1/1800
FVH	(80°-90°)	125.6	2.8			G2/225
BL	(0°-30°)	178.3	4.0	B1/500		
BM	(30°-60°)	763.3	17.2	B1/1000		
BH	(60°-80°)	1148.6	25.9	B3/2500		G1/1800
BVH	(80°-90°)	125.6	2.8			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short



REPORT NUMBER: P148213

CATALOG NUMBER: VXS-F02-LED-E1-5XQ-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	419.9	419.9	419.9	419.9	419.9	419.9	419.9	419.9	419.9	419.9	419.9
2.5°	420.5	420.8	420.7	420.5	420.6	420.5	420.2	420.1	419.3	419.8	420.5
5°	420.6	420.3	420.2	420.1	420.1	420.5	420.1	419.8	419.7	419.9	419.6
7.5°	420.3	419.9	419.7	419.5	419.7	419.8	419.5	419.0	419.3	419.0	418.5
10°	419.7	419.3	419.5	419.0	419.1	419.0	418.5	418.1	418.4	418.0	417.4
12.5°	419.9	419.3	419.2	419.0	418.9	418.8	418.1	417.6	417.7	417.4	416.9
15°	419.9	419.6	419.5	419.0	418.9	418.7	417.9	417.7	417.7	417.3	416.7
17.5°	420.1	419.9	419.9	419.3	419.1	419.0	418.1	417.8	418.1	417.4	417.0
20°	420.8	420.6	420.7	420.3	419.9	419.9	419.3	419.1	419.2	419.2	417.8
22.5°	422.2	422.3	422.5	422.4	422.3	422.4	421.9	421.9	422.0	422.0	420.9
25°	426.1	426.1	426.3	426.3	426.4	427.2	426.9	426.7	427.4	427.4	426.3
27.5°	433.6	433.4	433.6	433.8	434.4	435.4	435.2	435.6	436.5	436.3	435.3
30°	442.3	442.0	442.5	443.2	443.7	445.4	444.7	446.4	447.3	447.9	447.2
32.5°	454.7	454.7	455.8	456.3	457.3	458.9	459.2	460.5	461.6	462.8	462.0
35°	471.5	471.2	472.0	472.8	474.2	475.6	476.3	478.1	479.7	480.5	479.0
37.5°	497.0	495.8	497.2	497.7	498.8	499.1	500.7	503.0	504.8	504.6	503.5
40°	531.6	531.4	530.8	530.2	531.7	532.3	532.3	535.4	538.2	537.7	537.6
42.5°	572.0	571.0	570.4	570.3	571.2	571.4	575.0	577.4	579.3	579.8	579.3
45°	615.5	614.4	614.6	614.1	614.5	616.1	618.1	622.4	626.1	626.2	624.2
47.5°	662.2	658.9	661.5	657.8	660.1	661.1	666.4	672.7	679.2	680.4	678.7
50°	709.4	709.2	708.9	708.2	709.3	711.8	718.2	728.1	734.3	738.5	735.8
52.5°	761.3	759.6	758.8	757.5	758.7	763.6	772.6	781.1	792.4	797.1	793.4
55°	811.7	811.1	808.1	808.0	810.2	818.0	827.7	838.2	850.5	855.9	854.4
57.5°	863.5	860.1	859.2	857.8	862.2	869.5	881.5	900.5	913.2	919.3	915.8
60°	914.2	911.5	909.6	909.1	912.1	922.4	939.5	962.5	978.1	986.0	980.4
62.5°	968.5	966.8	964.6	961.9	968.3	981.3	1002.7	1028.0	1051.2	1060.8	1052.4
65°	1036.1	1032.6	1030.2	1026.7	1032.0	1048.5	1075.2	1111.0	1142.0	1153.4	1147.4
67.5°	1107.4	1104.2	1104.5	1102.4	1111.6	1134.5	1169.1	1217.5	1259.1	1278.4	1267.2
70°	1169.5	1171.4	1171.8	1180.3	1196.3	1231.1	1288.7	1364.6	1427.6	1457.2	1445.0
71°	1151.3	1155.0	1161.0	1169.8	1197.5	1238.7	1317.3	1409.1	1484.4	1534.5	1517.7
72.5°	1099.3	1101.6	1104.6	1118.0	1149.2	1203.8	1284.8	1389.7	1486.4	1551.4	1531.9
75°	1024.0	1026.2	1027.2	1036.7	1065.1	1112.6	1186.7	1279.9	1365.2	1420.5	1415.1
77.5°	910.4	910.8	918.9	933.4	965.3	1019.8	1097.8	1194.4	1274.7	1317.6	1290.4
80°	653.7	649.3	657.7	676.4	715.9	778.3	858.2	968.6	1057.6	1097.8	1055.5
82.5°	248.7	262.2	283.4	314.3	327.7	397.1	471.7	536.5	611.5	695.3	674.3
85°	26.7	30.1	37.7	46.8	59.1	81.8	113.0	154.2	190.1	223.4	198.3
87.5°	9.9	10.2	11.4	13.2	13.4	13.9	14.8	17.3	16.2	13.9	11.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P148213

CATALOG NUMBER: VXS-F02-LED-E1-5XQ-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	419.9	419.9	419.9	419.9	419.9	419.9	419.9	419.9
2.5°	419.9	420.0	419.9	420.0	420.1	419.6	419.7	419.5
5°	419.8	419.5	419.5	419.7	419.5	419.8	419.5	419.7
7.5°	419.2	418.4	418.8	418.8	418.5	418.9	418.7	418.5
10°	418.0	417.1	417.6	417.4	417.3	417.4	417.4	417.4
12.5°	417.0	416.4	416.6	416.4	416.3	416.7	416.6	416.6
15°	416.8	415.9	415.8	415.5	415.5	415.9	415.9	416.2
17.5°	416.6	415.3	415.2	415.0	415.1	415.6	415.8	415.5
20°	417.2	416.4	416.1	415.9	415.8	416.4	416.2	416.2
22.5°	420.5	419.4	419.2	418.2	417.9	418.2	418.0	418.0
25°	425.7	424.4	423.8	422.6	421.7	421.7	421.2	421.0
27.5°	435.1	433.1	432.5	431.5	430.3	430.5	429.7	429.6
30°	446.0	444.1	442.5	441.0	439.5	439.0	438.1	438.0
32.5°	460.3	458.2	456.3	454.4	452.3	451.5	450.1	449.4
35°	477.8	475.0	472.7	471.5	469.3	468.3	467.4	468.4
37.5°	502.4	499.0	497.8	496.3	494.9	493.3	493.7	493.3
40°	536.3	533.3	532.0	529.4	529.1	527.3	528.4	527.2
42.5°	578.2	572.6	571.8	569.6	569.0	568.0	568.5	567.7
45°	623.8	618.9	617.8	614.5	614.6	612.2	613.2	613.2
47.5°	675.1	669.9	665.6	663.2	662.3	660.7	661.6	661.5
50°	728.1	721.0	716.3	711.5	709.4	709.9	708.4	711.1
52.5°	785.0	774.4	767.7	763.1	759.2	760.0	760.3	761.0
55°	843.8	830.4	820.6	814.7	811.1	811.3	812.4	813.3
57.5°	903.1	886.2	873.1	864.2	861.9	862.9	862.9	862.8
60°	964.6	944.2	927.3	917.2	915.1	914.6	919.2	917.5
62.5°	1030.5	1006.2	988.6	975.8	972.7	974.8	978.9	978.0
65°	1117.9	1084.4	1061.6	1048.9	1043.8	1045.9	1051.4	1051.2
67.5°	1230.7	1183.7	1153.7	1137.4	1133.7	1136.3	1139.3	1142.2
70°	1399.3	1332.2	1289.3	1254.1	1239.0	1236.2	1239.2	1239.3
71°	1458.7	1381.7	1313.3	1270.3	1245.5	1235.0	1235.9	1230.7
72.5°	1456.2	1361.3	1281.2	1236.4	1202.0	1193.7	1189.5	1183.2
75°	1358.0	1272.5	1203.1	1154.1	1121.0	1111.2	1103.9	1103.6
77.5°	1231.6	1168.5	1092.0	1040.1	999.8	983.4	976.2	976.0
80°	990.1	895.6	839.7	808.4	759.8	745.8	730.9	725.3
82.5°	598.8	467.9	380.4	338.0	314.6	259.1	232.5	219.9
85°	139.5	99.1	68.3	44.9	32.3	25.7	19.7	17.4
87.5°	9.4	7.5	6.6	5.4	4.0	3.9	2.5	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)