

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P147723

Luminaire Tested: **VXS-F05-LED-E1-5WQ-8030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P147723
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F05-LED-E1-5WQ-8030
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (35) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11091.3 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B4 - U0 - G2

Input Watts (W): 133.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P147723

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 1.7 fc
Type V - Short - Semi-Cutoff

REPORT NUMBER: P147723

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P147723

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5545.7	0.0	5545.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5545.7	0.0	5545.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	11091.3	0.0	11091.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.8	0.5
10°-20°	204.2	1.8
20°-30°	413.5	3.7
30°-40°	693.3	6.3
40°-50°	1223.0	11.0
50°-60°	2156.6	19.4
60°-70°	3292.6	29.7
70°-80°	2751.3	24.8
80°-90°	299.0	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11091.3	100.0
0°-180°	11091.3	100.0

Coefficient of Utilization



REPORT NUMBER: P147723


CATALOG NUMBER: VXS-F05-LED-E1-5WQ-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	337.8	3.0			
FM	(30°-60°)	2036.5	18.4			
FH	(60°-80°)	3021.9	27.2			G2/5000
FVH	(80°-90°)	149.5	1.3			G2/225
BL	(0°-30°)	337.8	3.0	B1/500		
BM	(30°-60°)	2036.5	18.4	B2/2500		
BH	(60°-80°)	3021.9	27.2	B4/5000		G2/5000
BVH	(80°-90°)	149.5	1.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short



REPORT NUMBER: P147723

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.0	576.0	576.0	576.0	576.0	576.0	576.0	576.0	576.0	576.0	576.0
2.5°	580.6	581.8	580.6	580.6	580.6	580.6	580.6	579.5	579.5	579.5	580.6
5°	592.2	593.4	592.2	593.4	593.4	593.4	593.4	592.2	592.2	592.2	592.2
7.5°	610.8	610.8	610.8	611.9	610.8	610.8	611.9	610.8	610.8	610.8	610.8
10°	637.5	636.4	636.4	636.4	636.4	636.4	637.5	637.5	637.5	636.4	636.4
12.5°	670.1	668.9	670.1	670.1	671.2	671.2	671.2	671.2	671.2	671.2	670.1
15°	709.5	709.5	709.5	710.7	713.0	713.0	711.8	713.0	713.0	713.0	713.0
17.5°	753.7	756.0	753.7	754.8	756.0	754.8	757.1	758.2	759.5	758.2	754.8
20°	799.0	800.1	800.1	800.1	800.1	802.4	803.5	803.5	807.0	805.9	804.8
22.5°	841.9	844.2	844.2	845.4	845.4	848.8	848.8	848.8	851.2	853.5	851.2
25°	887.2	886.0	886.0	888.3	889.5	894.1	894.1	896.5	900.0	901.1	898.8
27.5°	927.8	926.6	926.6	930.2	931.3	937.1	937.1	941.8	944.0	945.3	942.9
30°	970.8	970.8	969.6	973.1	976.6	981.2	983.5	988.2	991.7	992.8	990.6
32.5°	1021.9	1019.6	1020.7	1023.0	1025.4	1030.1	1033.5	1039.3	1043.9	1045.1	1042.8
35°	1079.9	1076.5	1077.6	1079.9	1083.4	1090.4	1096.2	1099.7	1106.6	1109.0	1104.4
37.5°	1143.8	1145.0	1143.8	1149.6	1155.4	1163.5	1170.5	1175.1	1182.2	1185.6	1182.2
40°	1234.4	1230.9	1234.4	1240.2	1249.4	1259.9	1273.9	1277.3	1284.4	1291.3	1283.1
42.5°	1351.7	1349.3	1357.5	1362.1	1372.5	1384.1	1401.6	1410.9	1421.3	1426.0	1419.1
45°	1505.0	1505.0	1514.2	1515.4	1531.6	1546.7	1571.1	1582.8	1602.5	1602.5	1602.5
47.5°	1674.5	1681.5	1687.3	1698.9	1710.5	1738.3	1762.7	1788.3	1806.8	1809.2	1805.7
50°	1849.8	1856.8	1874.2	1890.5	1916.1	1950.9	1977.6	2011.2	2027.5	2041.5	2036.8
52.5°	2043.7	2044.9	2065.8	2086.7	2123.8	2162.2	2205.2	2240.0	2269.0	2281.8	2271.4
55°	2256.3	2258.5	2277.2	2299.3	2341.0	2385.2	2438.5	2474.6	2511.7	2534.9	2517.5
57.5°	2486.2	2487.4	2505.9	2532.6	2582.6	2626.7	2677.8	2728.9	2763.7	2784.7	2773.1
60°	2740.5	2746.3	2760.2	2793.9	2841.6	2888.0	2939.1	2984.4	3025.0	3047.0	3035.4
62.5°	3012.2	3018.0	3037.7	3064.5	3106.3	3157.4	3206.1	3264.2	3297.9	3322.3	3304.9
65°	3194.5	3205.0	3236.4	3272.3	3333.9	3400.1	3457.0	3536.0	3576.6	3605.6	3589.3
67.5°	3206.1	3211.9	3250.3	3304.9	3387.3	3487.2	3603.3	3726.4	3806.5	3844.9	3817.0
69°	3127.2	3135.3	3172.4	3234.0	3325.7	3441.9	3580.1	3733.4	3856.5	3913.4	3886.6
70°	3037.7	3055.2	3095.9	3163.2	3252.6	3374.5	3517.3	3681.0	3825.1	3902.9	3883.1
72.5°	2849.6	2854.3	2881.0	2934.4	3002.9	3103.9	3238.7	3393.1	3530.2	3641.6	3657.8
75°	2529.1	2544.2	2563.9	2600.0	2634.8	2708.0	2798.5	2904.2	2984.4	3070.3	3073.8
77.5°	1911.4	1956.7	1971.7	1979.9	1995.0	2053.1	2132.0	2223.7	2289.9	2303.8	2301.6
80°	858.1	918.5	932.4	998.7	1039.3	1135.6	1256.5	1397.0	1491.0	1501.5	1476.0
82.5°	168.4	180.0	210.2	262.5	357.6	414.5	493.5	592.2	682.8	735.0	703.7
85°	55.8	59.2	68.5	75.4	87.0	98.7	119.6	148.6	184.7	204.4	182.3
87.5°	22.1	22.1	25.6	27.9	30.2	30.2	30.2	27.9	26.7	22.1	19.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P147723

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	576.0	576.0	576.0	576.0	576.0	576.0	576.0	576.0
2.5°	579.5	579.5	579.5	579.5	579.5	579.5	579.5	579.5
5°	592.2	591.1	591.1	589.9	589.9	589.9	589.9	589.9
7.5°	609.6	608.5	607.4	608.5	607.4	607.4	607.4	607.4
10°	636.4	634.0	632.8	631.7	631.7	631.7	630.6	630.6
12.5°	667.7	667.7	666.5	665.4	663.1	664.2	663.1	660.7
15°	710.7	708.4	707.2	706.0	703.7	703.7	703.7	702.6
17.5°	753.7	751.3	751.3	747.9	746.6	746.6	746.6	747.9
20°	801.2	797.7	795.4	793.2	790.8	791.9	789.6	791.9
22.5°	848.8	844.2	841.9	838.4	834.9	834.9	833.8	831.4
25°	895.3	889.5	887.2	883.7	879.1	879.1	876.7	874.4
27.5°	939.5	933.6	931.3	924.4	919.7	918.5	916.2	915.0
30°	988.2	981.2	977.7	970.8	963.8	962.7	959.2	959.2
32.5°	1039.3	1032.3	1030.1	1019.6	1013.8	1013.8	1011.4	1009.1
35°	1103.2	1092.7	1090.4	1079.9	1071.8	1071.8	1069.5	1070.7
37.5°	1178.7	1170.5	1162.4	1154.3	1145.0	1143.8	1141.5	1139.2
40°	1279.7	1270.4	1261.1	1249.4	1241.3	1239.1	1235.5	1234.4
42.5°	1414.4	1405.1	1386.5	1377.2	1369.1	1362.1	1360.9	1359.8
45°	1586.2	1574.6	1561.9	1544.5	1534.0	1518.9	1516.6	1510.8
47.5°	1793.0	1770.9	1748.8	1733.7	1717.4	1700.0	1696.6	1687.3
50°	2012.4	1995.0	1957.8	1933.5	1907.9	1890.5	1878.9	1875.3
52.5°	2248.1	2215.6	2178.4	2145.9	2108.8	2085.6	2064.7	2058.9
55°	2494.3	2447.9	2401.5	2363.1	2325.9	2298.0	2278.3	2269.0
57.5°	2740.5	2689.4	2638.3	2596.5	2565.2	2529.1	2509.4	2504.8
60°	2997.1	2948.4	2896.1	2854.3	2816.0	2784.7	2773.1	2751.0
62.5°	3268.8	3217.7	3169.0	3128.4	3079.6	3057.5	3037.7	3025.0
65°	3536.0	3476.7	3415.1	3372.2	3323.4	3292.1	3267.7	3250.3
67.5°	3742.6	3653.3	3570.8	3498.8	3432.5	3383.8	3352.4	3336.2
69°	3800.7	3689.2	3583.5	3489.5	3411.7	3357.1	3322.3	3306.0
70°	3793.7	3670.7	3554.5	3451.2	3366.4	3308.3	3274.6	3244.5
72.5°	3578.9	3466.2	3337.4	3224.8	3148.1	3092.3	3058.7	3042.4
75°	3054.0	2978.5	2885.6	2798.5	2742.8	2710.3	2668.5	2669.6
77.5°	2223.7	2226.1	2163.3	2074.0	2011.2	1999.6	1981.0	1962.5
80°	1379.6	1269.2	1197.2	1100.8	1030.1	968.5	941.8	883.7
82.5°	636.4	497.0	385.5	291.5	224.1	175.3	153.3	125.4
85°	141.7	108.0	89.4	72.0	61.6	56.9	46.4	43.0
87.5°	19.7	17.4	16.3	15.1	12.7	9.3	6.9	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)