

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P152183

Luminaire Tested: **VXS-F05-LED-E1-SL4-8030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P152183
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F05-LED-E1-SL4-8030
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (35) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10291.2 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 133.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P152183

CATALOG NUMBER: VXS-F05-LED-E1-SL4-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 --- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 5.5 fc
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152183

CATALOG NUMBER: VXS-F05-LED-E1-SL4-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P152183

CATALOG NUMBER: VXS-F05-LED-E1-SL4-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2136.3	0.0	2136.3
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	8154.8	0.0	8154.8
	% Fixture	79.2	0.0	79.2
Total	Lumens	10291.2	0.0	10291.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.1	2.0
10°-20°	561.6	5.5
20°-30°	831.3	8.1
30°-40°	1050.6	10.2
40°-50°	1188.2	11.5
50°-60°	1690.8	16.4
60°-70°	3149.0	30.6
70°-80°	1443.2	14.0
80°-90°	171.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10291.2	100.0
0°-180°	10291.2	100.0

Coefficient of Utilization



REPORT NUMBER: P152183


CATALOG NUMBER: VXS-F05-LED-E1-SL4-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	937.1	9.1			
FM	(30°-60°)	3015.0	29.3			
FH	(60°-80°)	4075.7	39.6			G2/5000
FVH	(80°-90°)	127.1	1.2			G2/225
BL	(0°-30°)	661.0	6.4	B2/1000		
BM	(30°-60°)	914.6	8.9	B1/1000		
BH	(60°-80°)	516.5	5.0	B2/1000		G2/1000
BVH	(80°-90°)	44.2	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short



REPORT NUMBER: P152183

CATALOG NUMBER: VXS-F05-LED-E1-SL4-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9
2.5°	2229.5	2235.3	2228.4	2227.3	2227.3	2226.1	2219.1	2217.9	2208.6	2209.8	2212.1
5°	2245.8	2248.1	2243.5	2242.3	2240.0	2235.3	2229.5	2222.6	2215.6	2208.6	2202.8
7.5°	2262.1	2259.8	2256.3	2256.3	2252.7	2245.8	2234.2	2224.9	2209.8	2201.7	2191.2
10°	2285.3	2281.8	2277.2	2274.8	2269.0	2258.5	2242.3	2229.5	2211.0	2194.7	2177.3
12.5°	2307.4	2306.2	2299.3	2295.8	2286.4	2276.0	2256.3	2236.5	2212.1	2186.6	2163.3
15°	2346.8	2342.2	2335.2	2328.3	2313.2	2299.3	2269.0	2245.8	2211.0	2177.3	2141.3
17.5°	2415.3	2407.3	2400.2	2385.2	2366.5	2342.2	2298.0	2258.5	2211.0	2162.2	2121.6
20°	2540.7	2523.3	2514.1	2494.3	2461.8	2417.7	2349.1	2285.3	2214.5	2151.7	2097.2
22.5°	2682.4	2670.8	2658.0	2645.3	2594.2	2530.4	2437.4	2342.2	2235.3	2147.2	2077.4
25°	2841.6	2826.4	2819.5	2797.4	2749.7	2676.6	2550.1	2417.7	2283.0	2165.7	2077.4
27.5°	2983.2	2978.5	2977.4	2951.8	2906.5	2820.6	2670.8	2511.7	2348.0	2204.0	2094.8
30°	3112.1	3107.5	3105.1	3091.2	3039.0	2936.8	2774.2	2595.3	2418.9	2257.4	2127.4
32.5°	3249.1	3234.0	3227.0	3200.3	3141.1	3021.6	2835.8	2649.9	2474.6	2309.6	2163.3
35°	3360.6	3347.8	3333.9	3295.5	3211.9	3070.3	2862.4	2668.5	2496.7	2338.8	2182.0
37.5°	3441.9	3429.1	3409.3	3360.6	3257.2	3086.5	2861.2	2662.7	2488.5	2334.1	2185.4
40°	3477.8	3465.1	3444.1	3382.7	3265.4	3077.2	2839.2	2636.0	2464.1	2309.6	2171.5
42.5°	3463.9	3454.6	3428.0	3368.7	3239.8	3035.4	2795.0	2586.0	2417.7	2270.2	2140.1
45°	3410.6	3403.5	3378.0	3315.3	3181.8	2968.1	2730.1	2523.3	2362.0	2221.5	2098.3
47.5°	3330.4	3328.1	3302.5	3240.9	3108.6	2900.7	2662.7	2461.8	2306.2	2173.8	2063.5
50°	3242.2	3230.6	3217.7	3160.8	3040.1	2842.7	2613.9	2423.5	2274.8	2156.4	2048.4
52.5°	3186.4	3182.9	3171.3	3120.2	3004.0	2809.0	2591.8	2409.5	2272.5	2153.0	2040.3
55°	3681.0	3689.2	3582.4	3360.6	3165.5	2901.9	2658.0	2480.4	2329.4	2208.6	2126.2
57.5°	5445.0	5409.0	5225.5	4785.4	4288.4	3632.3	3159.7	2872.8	2685.9	2706.8	2748.6
60°	6343.7	6336.8	6303.1	6132.4	5801.5	5302.2	4748.3	4113.1	3911.0	3933.1	3949.3
62.5°	6745.6	6756.1	6781.6	6717.7	6630.6	6485.5	6209.1	5953.6	5683.0	5582.0	5311.4
65°	6931.4	6949.9	7008.0	7044.0	7077.7	7103.2	7212.3	7512.0	7709.4	7340.1	6480.8
67.5°	6546.9	6636.4	6828.0	7014.9	7182.2	7420.2	7789.5	8485.1	8969.3	8515.2	7269.2
70°	4772.6	4894.6	5114.0	5692.3	6310.1	6850.1	7565.4	8624.5	9354.8	9004.1	7464.4
72.5°	2992.4	3026.1	3123.7	3336.2	3794.9	4488.2	5738.8	7327.4	8170.4	7890.6	6308.9
75°	1898.7	1910.3	1906.7	1955.5	2033.3	2184.2	2679.0	4327.9	5597.1	5160.5	3516.2
77.5°	1131.0	1148.5	1155.4	1170.5	1207.7	1261.1	1301.8	1472.4	2346.8	2278.3	1276.2
80°	947.6	961.5	949.8	946.4	923.2	906.9	926.6	906.9	841.9	810.6	746.6
82.5°	501.7	500.5	497.0	530.7	599.2	652.6	693.3	683.9	619.0	527.2	447.0
85°	275.2	284.5	284.5	296.1	285.7	286.8	296.1	312.3	289.1	241.6	197.4
87.5°	23.2	36.0	29.0	36.0	48.8	34.8	33.7	33.7	29.0	20.9	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152183

CATALOG NUMBER: VXS-F05-LED-E1-SL4-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9
2.5°	2206.3	2204.0	2199.4	2195.9	2195.9	2190.1	2186.6	2184.2	2183.1	2178.4	2178.4
5°	2199.4	2191.2	2183.1	2177.3	2173.8	2168.0	2158.8	2154.1	2148.3	2143.6	2141.3
7.5°	2184.2	2169.1	2156.4	2147.2	2135.5	2126.2	2114.6	2104.1	2093.7	2089.0	2086.7
10°	2161.0	2141.3	2121.6	2104.1	2087.9	2071.6	2056.6	2041.5	2028.7	2019.4	2010.1
12.5°	2139.0	2108.8	2083.2	2057.7	2032.1	2012.4	1991.5	1969.4	1950.9	1933.5	1928.8
15°	2108.8	2074.0	2041.5	2010.1	1978.8	1946.2	1920.6	1896.3	1866.1	1846.3	1831.3
17.5°	2080.9	2039.1	1999.6	1962.5	1924.1	1890.5	1852.1	1819.7	1789.4	1759.3	1737.2
20°	2050.7	2005.4	1963.6	1921.9	1880.0	1837.1	1793.0	1751.1	1714.0	1677.9	1642.0
22.5°	2024.0	1977.6	1936.9	1891.6	1845.2	1796.4	1745.3	1693.1	1650.1	1603.6	1561.9
25°	2007.8	1956.7	1914.8	1870.8	1819.7	1766.2	1708.2	1646.6	1594.4	1540.9	1491.0
27.5°	2007.8	1941.6	1898.7	1854.5	1802.2	1745.3	1681.5	1614.1	1554.9	1495.6	1434.1
30°	2025.2	1943.9	1885.8	1839.4	1786.0	1724.5	1653.6	1582.8	1517.7	1448.1	1388.8
32.5°	2041.5	1948.5	1876.6	1817.3	1755.8	1695.4	1623.4	1547.9	1476.0	1409.7	1347.0
35°	2051.9	1948.5	1859.2	1783.6	1714.0	1654.7	1583.9	1508.4	1435.2	1370.3	1312.2
37.5°	2053.1	1939.3	1831.3	1745.3	1672.1	1610.6	1543.3	1472.4	1402.8	1342.4	1293.6
40°	2041.5	1920.6	1803.4	1704.7	1628.1	1565.3	1503.8	1439.9	1377.2	1327.3	1285.5
42.5°	2020.5	1900.9	1776.7	1672.1	1592.0	1527.0	1470.2	1415.5	1360.9	1318.0	1283.1
45°	1989.2	1874.2	1752.3	1652.4	1573.5	1505.0	1449.2	1403.9	1357.5	1321.5	1286.6
47.5°	1961.3	1865.0	1760.4	1665.2	1582.8	1511.9	1455.0	1416.7	1380.7	1356.3	1308.7
50°	1955.5	1860.3	1763.9	1675.6	1592.0	1520.0	1470.2	1450.4	1439.9	1424.9	1351.7
52.5°	1939.3	1859.2	1789.4	1740.7	1687.3	1653.6	1601.3	1619.9	1608.3	1554.9	1422.5
55°	2109.9	2133.2	2198.2	2291.1	2377.0	2396.8	2391.0	2368.9	2251.6	1936.9	1593.2
57.5°	2900.7	3031.9	3155.0	3209.6	3202.7	3141.1	3097.0	3007.6	2838.0	2454.8	1929.9
60°	3999.3	4020.2	3955.1	3858.8	3696.2	3560.3	3415.1	3248.0	3001.8	2626.7	2136.7
62.5°	5010.7	4729.6	4440.5	4168.8	3921.5	3705.5	3503.4	3270.1	2949.5	2558.1	2109.9
65°	5724.9	5130.3	4673.9	4283.7	3934.2	3632.3	3380.3	3077.2	2716.1	2363.1	1955.5
67.5°	6093.0	5181.3	4481.1	3937.7	3441.9	3023.8	2688.2	2393.3	2125.1	1970.6	1711.6
70°	5681.9	4397.5	3422.2	2807.9	2214.5	1775.5	1402.8	1177.5	1099.7	1246.0	1296.0
72.5°	4233.8	2862.4	2035.6	1574.6	1206.5	961.5	737.4	579.5	471.5	494.7	642.2
75°	2002.0	1235.5	873.3	664.2	528.4	437.8	357.6	327.5	274.1	227.6	213.7
77.5°	779.2	567.9	469.1	343.7	243.8	196.3	167.3	161.5	164.9	160.2	157.9
80°	593.4	401.8	252.0	184.7	159.1	140.5	124.2	119.6	122.0	127.8	133.6
82.5°	331.0	206.7	153.3	133.6	119.6	102.2	92.8	85.9	87.0	94.1	106.8
85°	127.8	99.9	91.7	88.3	82.5	66.2	56.9	58.0	66.2	79.0	79.0
87.5°	13.9	13.9	18.5	13.9	13.9	13.9	12.7	15.1	16.3	20.9	24.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152183

CATALOG NUMBER: VXS-F05-LED-E1-SL4-8030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9	2195.9
2.5°	2176.2	2176.2	2176.2	2173.8	2175.0	2170.4	2170.4	2166.8	2172.6	2169.1	2168.0
5°	2142.5	2141.3	2136.7	2136.7	2136.7	2136.7	2140.1	2130.9	2137.8	2137.8	2134.3
7.5°	2085.6	2085.6	2072.7	2079.8	2077.4	2080.9	2085.6	2080.9	2087.9	2092.5	2089.0
10°	2006.6	2006.6	1996.2	2004.2	2000.8	2008.9	2017.1	2012.4	2017.1	2024.0	2026.3
12.5°	1919.5	1914.8	1905.6	1909.0	1909.0	1913.7	1917.2	1923.0	1928.8	1938.1	1942.7
15°	1818.4	1811.5	1799.9	1799.9	1793.0	1795.2	1802.2	1804.6	1816.2	1828.9	1844.0
17.5°	1715.1	1697.7	1685.0	1669.8	1658.2	1667.6	1675.6	1681.5	1690.8	1710.5	1720.9
20°	1617.6	1582.8	1558.3	1538.7	1525.8	1531.6	1542.1	1549.1	1557.2	1561.9	1565.3
22.5°	1521.2	1481.8	1448.1	1423.6	1402.8	1408.6	1403.9	1400.4	1406.2	1391.2	1389.9
25°	1437.6	1391.2	1345.9	1316.8	1291.3	1283.1	1258.8	1253.0	1236.7	1223.9	1214.6
27.5°	1377.2	1316.8	1266.9	1233.3	1192.5	1162.4	1131.0	1099.7	1082.3	1061.3	1050.9
30°	1329.6	1265.7	1206.5	1149.6	1096.2	1049.7	1008.0	967.3	939.5	909.2	889.5
32.5°	1285.5	1226.2	1154.3	1076.5	1004.5	952.2	897.6	851.2	807.0	767.6	738.5
35°	1255.3	1189.1	1097.4	1002.2	920.8	859.3	801.2	735.0	681.7	630.6	599.2
37.5°	1239.1	1157.7	1045.1	939.5	848.8	779.2	707.2	630.6	565.5	517.9	470.3
40°	1226.2	1126.4	998.7	883.7	788.5	704.9	621.2	530.7	458.7	408.7	371.6
42.5°	1212.3	1091.5	958.0	839.6	733.9	636.4	535.3	439.0	370.5	335.5	319.4
45°	1197.2	1061.3	919.7	797.7	680.5	562.1	445.9	356.5	315.9	304.2	304.2
47.5°	1193.8	1041.7	891.8	757.1	620.1	476.1	363.4	307.8	296.1	298.4	303.1
50°	1207.7	1035.9	867.5	709.5	540.0	385.5	307.8	289.1	291.5	298.4	305.4
52.5°	1241.3	1040.4	841.9	643.3	444.8	318.1	284.5	283.3	290.3	300.7	307.8
55°	1298.2	1040.4	793.2	544.7	355.3	285.7	276.4	281.0	290.3	299.6	305.4
57.5°	1420.2	1030.1	707.2	435.4	297.3	274.1	274.1	279.9	288.0	297.3	302.0
60°	1565.3	1016.1	586.4	336.8	268.3	264.8	272.8	279.9	286.8	294.9	299.6
62.5°	1574.6	980.1	464.5	278.7	253.2	259.0	271.7	281.0	283.3	289.1	294.9
65°	1446.8	854.6	369.2	249.6	246.2	255.4	268.3	275.2	276.4	278.7	284.5
67.5°	1266.9	696.7	298.4	235.8	239.2	249.6	256.6	262.5	265.9	271.7	272.8
70°	1040.4	559.7	255.4	221.8	225.3	236.9	242.7	248.5	255.4	262.5	259.0
72.5°	737.4	435.4	224.1	206.7	211.3	221.8	228.8	233.4	239.2	246.2	241.6
75°	313.6	304.2	193.9	186.9	193.9	200.9	207.9	214.8	220.6	224.1	224.1
77.5°	160.2	178.9	167.3	167.3	171.8	178.9	184.7	191.6	195.1	198.5	203.2
80°	135.9	138.1	140.5	145.2	149.8	156.8	162.6	168.4	169.5	170.7	173.1
82.5°	112.6	117.3	119.6	126.5	130.1	132.3	135.9	135.9	138.1	138.1	134.7
85°	81.2	87.0	90.6	91.7	90.6	91.7	92.8	95.2	101.0	101.0	96.4
87.5°	23.2	22.1	27.9	29.0	31.4	36.0	40.6	48.8	51.1	53.4	53.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152183

CATALOG NUMBER: VXS-F05-LED-E1-SL4-8030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2195.9	2195.9	2195.9	2195.9
2.5°	2166.8	2169.1	2164.6	2165.7
5°	2134.3	2139.0	2133.2	2140.1
7.5°	2092.5	2099.5	2098.3	2097.2
10°	2032.1	2041.5	2041.5	2044.9
12.5°	1955.5	1961.3	1965.9	1968.3
15°	1852.1	1862.6	1868.4	1868.4
17.5°	1727.9	1734.9	1738.3	1733.7
20°	1569.9	1567.7	1568.8	1557.2
22.5°	1387.7	1391.2	1380.7	1383.0
25°	1208.8	1203.0	1207.7	1200.7
27.5°	1035.9	1037.0	1024.2	1030.1
30°	870.9	865.1	848.8	857.0
32.5°	711.8	696.7	679.3	668.9
35°	562.1	538.9	530.7	527.2
37.5°	441.2	415.8	407.6	398.3
40°	350.7	341.5	337.9	340.2
42.5°	314.7	314.7	317.0	318.1
45°	305.4	308.9	312.3	313.6
47.5°	306.5	310.1	314.7	315.9
50°	308.9	312.3	315.9	317.0
52.5°	310.1	310.1	312.3	313.6
55°	307.8	306.5	307.8	308.9
57.5°	303.1	300.7	302.0	305.4
60°	300.7	297.3	299.6	302.0
62.5°	294.9	293.8	296.1	297.3
65°	282.2	283.3	286.8	286.8
67.5°	270.6	271.7	272.8	274.1
70°	256.6	257.8	260.1	261.2
72.5°	240.4	245.0	248.5	253.2
75°	227.6	232.2	239.2	243.8
77.5°	205.5	209.0	217.1	223.0
80°	174.2	173.1	174.2	177.6
82.5°	133.6	133.6	132.3	131.2
85°	94.1	92.8	89.4	89.4
87.5°	51.1	49.9	48.8	46.4
90°	0.0	0.0	0.0	0.0

(END OF REPORT)