

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P152753

Luminaire Tested: **VXS-F05-LED-E1-SLL-8030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P152753
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33681)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F05-LED-E1-SLL-8030
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - 90° SPILL LIGHT ELIMINATOR LEFT
Light Source: (35) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9693.2 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type IV - Short - Non-Cutoff
BUG Rating: B2 - U0 - G3

Input Watts (W): 133.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P152753

CATALOG NUMBER: VXS-F05-LED-E1-SLL-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 24.1 fc
 Type IV - Short - Non-Cutoff

REPORT NUMBER: P152753

CATALOG NUMBER: VXS-F05-LED-E1-SLL-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P152753

CATALOG NUMBER: VXS-F05-LED-E1-SLL-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2101.9	0.0	2101.9
	% Fixture	21.7	0.0	21.7
Street Side	Lumens	7591.2	0.0	7591.2
	% Fixture	78.3	0.0	78.3
Total	Lumens	9693.2	0.0	9693.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.6	1.2
10°-20°	369.3	3.8
20°-30°	656.1	6.8
30°-40°	1033.2	10.7
40°-50°	1520.5	15.7
50°-60°	2019.7	20.8
60°-70°	2224.7	23.0
70°-80°	1395.7	14.4
80°-90°	355.5	3.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9693.2	100.0
0°-180°	9693.2	100.0

Coefficient of Utilization



REPORT NUMBER: P152753


CATALOG NUMBER: VXS-F05-LED-E1-SLL-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	620.7	6.4			
FM	(30°-60°)	3522.7	36.3			
FH	(60°-80°)	3135.9	32.4			G2/5000
FVH	(80°-90°)	312.0	3.2			G3/500
BL	(0°-30°)	523.3	5.4	B2/1000		
BM	(30°-60°)	1050.6	10.8	B2/2500		
BH	(60°-80°)	484.5	5.0	B1/500		G1/500
BVH	(80°-90°)	43.5	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P152753

CATALOG NUMBER: VXS-F05-LED-E1-SLL-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1
2.5°	1201.9	1204.1	1204.1	1203.0	1203.0	1205.4	1204.1	1203.0	1199.6	1204.1	1204.1
5°	1192.5	1194.9	1194.9	1197.2	1199.6	1201.9	1201.9	1204.1	1203.0	1207.7	1211.2
7.5°	1204.1	1206.5	1211.2	1217.0	1220.4	1228.6	1228.6	1234.4	1236.7	1240.2	1239.1
10°	1219.3	1225.1	1235.5	1244.9	1251.8	1261.1	1268.1	1276.2	1276.2	1279.7	1282.0
12.5°	1246.0	1251.8	1263.4	1275.0	1285.5	1297.1	1307.6	1315.6	1323.8	1326.1	1330.8
15°	1290.2	1297.1	1314.5	1330.8	1343.5	1358.7	1372.5	1388.8	1403.9	1407.4	1409.7
17.5°	1356.3	1370.3	1383.0	1412.0	1430.7	1450.4	1472.4	1495.6	1500.3	1524.7	1530.5
20°	1450.4	1467.8	1479.4	1515.4	1546.7	1572.3	1604.8	1631.5	1642.0	1665.2	1688.4
22.5°	1613.0	1609.4	1626.8	1662.9	1686.1	1737.2	1765.1	1793.0	1806.8	1841.7	1860.3
25°	1831.3	1849.8	1888.2	1891.6	1913.7	1973.0	2008.9	2036.8	2037.9	2048.4	2068.2
27.5°	2046.1	2122.7	2183.1	2215.6	2274.8	2329.4	2327.0	2366.5	2305.1	2317.8	2336.4
30°	2306.2	2433.9	2547.8	2624.4	2684.8	2748.6	2780.0	2802.1	2775.3	2763.7	2741.7
32.5°	2550.1	2728.9	2904.2	3040.1	3152.7	3258.4	3328.1	3359.4	3396.6	3490.7	3524.4
35°	2717.3	2970.5	3188.7	3385.0	3573.1	3741.5	3863.4	3933.1	3906.3	3893.6	3886.6
37.5°	2817.1	3126.0	3398.9	3676.5	3892.4	4144.5	4333.7	4517.2	4559.0	4485.8	4449.8
40°	2879.8	3245.6	3596.3	3923.7	4203.6	4528.8	4763.3	5038.5	5247.6	5275.4	5189.5
42.5°	2910.1	3325.7	3734.5	4105.0	4483.5	4881.8	5179.1	5512.3	5824.7	6039.6	5986.1
45°	2914.7	3378.0	3835.5	4268.7	4719.2	5191.8	5575.0	5944.4	6362.4	6730.5	6740.9
47.5°	2914.7	3417.5	3905.2	4387.2	4930.6	5461.2	5879.3	6316.0	6828.0	7263.4	7397.0
50°	2917.0	3444.1	3970.3	4480.0	5092.0	5688.8	6161.5	6677.1	7215.9	7689.6	7947.5
52.5°	2927.5	3463.9	4021.3	4546.2	5196.5	5849.1	6380.9	6975.4	7512.0	7998.5	8331.8
55°	2950.7	3491.8	4058.4	4586.8	5266.1	5953.6	6540.0	7179.9	7703.5	8197.1	8662.7
57.5°	3015.8	3540.6	4103.7	4622.8	5304.5	6022.1	6651.5	7268.1	7776.7	8291.2	8838.1
60°	3145.8	3643.9	4181.6	4694.8	5368.4	6148.7	6704.9	7208.9	7723.3	8263.3	8877.6
62.5°	3353.6	3805.4	4289.5	4816.8	5550.7	6345.0	6664.2	7032.4	7513.2	8101.9	8737.1
63°	3425.6	3840.2	4314.0	4843.5	5600.6	6380.9	6646.8	6980.1	7470.2	8050.8	8687.2
65°	3626.5	3994.6	4430.1	4978.1	5806.1	6416.9	6511.0	6708.4	7172.8	7759.3	8392.2
67.5°	4001.6	4369.7	4679.7	5205.8	5979.2	6275.2	6089.4	6113.9	6599.3	7206.5	7775.5
70°	4238.4	4677.4	4838.9	5234.8	5947.8	6065.1	5543.7	5220.8	5609.8	6302.0	6800.1
72.5°	4176.9	4680.9	4663.5	4848.1	5320.7	5429.8	4889.9	4381.3	4612.4	5129.1	5451.9
75°	3577.7	4180.4	4052.6	4015.5	4181.6	4253.6	3848.3	3770.5	4062.0	4348.8	4353.5
77.5°	2575.6	3238.7	3088.9	2874.0	2862.4	3028.5	3083.0	3592.8	4023.6	4250.1	4150.3
80°	1640.8	2359.6	2204.0	1828.9	1823.1	2039.1	2518.7	3211.9	3668.3	3794.9	3534.8
82.5°	857.0	1544.5	1603.6	1372.5	1571.1	1928.8	2396.8	2588.4	2761.3	2778.9	2472.2
85°	534.2	949.8	1117.1	1153.1	1419.1	1710.5	1707.0	1639.7	1563.0	1337.7	1209.9
87.5°	60.4	119.6	181.1	171.8	231.1	323.9	404.1	236.9	166.0	60.4	83.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152753

CATALOG NUMBER: VXS-F05-LED-E1-SLL-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1
2.5°	1206.5	1207.7	1208.8	1208.8	1214.6	1213.5	1214.6	1217.0	1220.4	1222.8	1225.1
5°	1215.9	1215.9	1220.4	1223.9	1230.9	1235.5	1237.8	1244.9	1253.0	1250.7	1257.6
7.5°	1246.0	1244.9	1249.4	1251.8	1257.6	1265.7	1264.6	1270.4	1277.3	1279.7	1285.5
10°	1286.6	1283.1	1283.1	1280.8	1282.0	1279.7	1279.7	1279.7	1284.4	1283.1	1287.8
12.5°	1328.4	1327.3	1325.0	1318.0	1318.0	1308.7	1304.0	1298.2	1297.1	1288.9	1290.2
15°	1414.4	1414.4	1409.7	1395.8	1384.1	1376.1	1364.5	1356.3	1344.7	1329.6	1321.5
17.5°	1539.8	1523.5	1517.7	1515.4	1496.8	1489.8	1464.4	1437.6	1424.9	1403.9	1392.3
20°	1693.1	1689.5	1666.3	1654.7	1631.5	1599.0	1566.5	1531.6	1510.8	1485.2	1471.3
22.5°	1866.1	1840.5	1828.9	1811.5	1775.5	1738.3	1689.5	1643.1	1610.6	1593.2	1582.8
25°	2068.2	2042.6	2031.0	2007.8	1963.6	1924.1	1863.7	1809.2	1780.2	1751.1	1734.9
27.5°	2336.4	2312.0	2298.0	2237.7	2222.6	2157.5	2083.2	2008.9	1970.6	1927.7	1899.8
30°	2737.0	2738.1	2666.2	2593.1	2517.5	2404.9	2327.0	2243.5	2180.8	2119.3	2057.7
32.5°	3414.0	3240.9	3107.5	2950.7	2786.9	2667.4	2571.0	2471.1	2384.0	2294.6	2192.4
35°	3827.4	3743.8	3570.8	3283.9	3119.1	2973.9	2867.0	2746.3	2639.5	2481.6	2325.9
37.5°	4294.2	4100.3	3890.2	3731.0	3544.0	3375.6	3196.9	3059.8	2875.2	2662.7	2442.1
40°	4975.9	4698.3	4445.2	4231.5	3989.9	3813.5	3613.8	3415.1	3170.2	2862.4	2559.4
42.5°	5687.7	5400.8	5066.4	4788.9	4504.4	4297.7	4050.4	3771.7	3411.7	3030.8	2660.4
45°	6434.4	6051.2	5650.6	5311.4	5015.3	4758.7	4452.1	4082.9	3643.9	3181.8	2754.4
47.5°	7170.6	6730.5	6253.2	5888.6	5503.0	5189.5	4813.3	4346.4	3825.1	3324.6	2848.5
50°	7819.7	7395.9	6821.0	6357.7	5967.6	5580.8	5111.7	4549.6	3967.9	3447.7	2933.3
52.5°	8379.4	8014.8	7409.7	6824.6	6375.1	5940.8	5352.1	4713.4	4111.9	3561.5	3002.9
55°	8790.5	8547.8	7990.4	7264.7	6734.0	6216.1	5555.3	4871.3	4247.8	3652.0	3048.2
57.5°	9100.5	8965.8	8487.4	7679.2	7063.7	6483.1	5765.5	5060.6	4382.5	3729.8	3069.1
60°	9270.1	9307.3	8863.6	8041.5	7355.2	6706.1	5975.6	5222.1	4482.4	3775.1	3057.5
62.5°	9253.8	9481.5	9145.8	8264.5	7524.8	6838.4	6117.3	5297.5	4468.4	3703.1	2951.8
63°	9222.5	9487.3	9177.2	8279.6	7535.2	6843.1	6120.8	5287.0	4439.4	3668.3	2910.1
65°	8951.9	9353.7	9150.5	8211.0	7442.3	6756.1	6047.7	5136.1	4235.0	3481.3	2695.2
67.5°	8227.3	8730.1	8672.0	7726.8	7002.2	6396.1	5673.8	4649.5	3729.8	3021.6	2284.1
70°	7030.1	7502.7	7513.2	6720.0	6115.0	5520.5	4920.1	3783.3	2956.5	2342.2	1703.5
72.5°	5388.1	5692.3	5798.0	5275.4	4870.2	4452.1	3913.4	2746.3	2107.7	1593.2	1109.0
75°	4172.3	4088.7	4087.6	3866.8	3702.0	3497.6	2905.4	1853.4	1384.1	1035.9	678.1
77.5°	3750.8	3379.2	3019.2	2754.4	2622.1	2553.6	1905.6	1117.1	816.4	595.8	390.2
80°	3093.5	2545.4	2056.6	1770.9	1657.1	1736.1	1062.5	603.8	447.0	339.1	253.2
82.5°	2133.2	1770.9	1345.9	1114.8	956.9	1000.9	543.4	308.9	206.7	189.3	156.8
85°	1111.3	974.3	822.2	706.0	623.6	548.1	282.2	147.5	85.9	75.4	68.5
87.5°	0.0	1.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152753

CATALOG NUMBER: VXS-F05-LED-E1-SLL-8030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1
2.5°	1228.6	1227.5	1229.7	1230.9	1234.4	1236.7	1237.8	1235.5	1239.1	1242.5	1240.2
5°	1261.1	1269.2	1270.4	1273.9	1273.9	1280.8	1280.8	1280.8	1279.7	1280.8	1278.5
7.5°	1288.9	1299.4	1300.6	1305.2	1306.4	1314.5	1311.0	1313.4	1313.4	1307.6	1305.2
10°	1292.4	1302.9	1308.7	1314.5	1322.6	1333.1	1333.1	1338.9	1338.9	1334.2	1333.1
12.5°	1293.6	1301.8	1307.6	1315.6	1327.3	1342.4	1350.5	1358.7	1362.1	1360.9	1357.5
15°	1318.0	1318.0	1319.2	1326.1	1334.2	1352.8	1364.5	1373.7	1379.6	1377.2	1371.4
17.5°	1381.9	1372.5	1365.6	1354.0	1356.3	1365.6	1372.5	1380.7	1381.9	1379.6	1370.3
20°	1456.2	1444.6	1427.2	1408.6	1399.3	1392.3	1387.7	1387.7	1384.1	1372.5	1357.5
22.5°	1561.9	1546.7	1522.4	1494.5	1476.0	1453.9	1427.2	1401.6	1373.7	1345.9	1313.4
25°	1708.2	1687.3	1661.8	1618.8	1579.3	1532.8	1478.2	1421.3	1355.1	1297.1	1249.4
27.5°	1855.6	1809.2	1743.0	1683.7	1610.6	1540.9	1463.1	1393.5	1308.7	1239.1	1186.7
30°	1977.6	1889.3	1794.1	1700.0	1603.6	1509.6	1416.7	1333.1	1240.2	1169.3	1118.2
32.5°	2071.6	1949.7	1817.3	1694.2	1575.8	1460.8	1354.0	1261.1	1167.0	1093.9	1039.3
35°	2158.8	1989.2	1820.8	1668.7	1522.4	1402.8	1282.0	1180.9	1081.1	1004.5	945.3
37.5°	2223.7	2007.8	1799.9	1621.0	1452.6	1319.2	1196.1	1092.7	990.6	906.9	839.6
40°	2265.6	1996.2	1754.6	1552.5	1370.3	1229.7	1104.4	997.5	898.8	807.0	725.8
42.5°	2299.3	1981.0	1709.3	1489.8	1305.2	1151.9	1023.0	908.1	808.2	708.4	619.0
45°	2349.1	1992.6	1689.5	1445.7	1247.2	1085.7	944.0	824.5	720.0	622.4	536.5
47.5°	2397.9	1998.4	1660.5	1391.2	1174.0	1017.2	873.3	757.1	650.3	560.8	481.9
50°	2442.1	1995.0	1615.2	1321.5	1103.2	948.7	809.3	693.3	587.6	505.2	430.8
52.5°	2463.0	1975.2	1559.5	1254.1	1046.2	888.3	746.6	634.0	529.5	451.7	383.2
55°	2460.6	1924.1	1486.3	1190.3	983.5	824.5	685.1	573.7	479.6	407.6	348.4
57.5°	2425.8	1845.2	1408.6	1119.4	901.1	745.5	613.2	505.2	426.2	365.8	315.9
60°	2352.6	1744.1	1306.4	1016.1	797.7	648.0	523.7	430.8	366.9	320.5	288.0
62.5°	2215.6	1599.0	1178.7	872.1	658.4	521.3	413.4	353.1	305.4	277.5	262.5
63°	2175.0	1559.5	1124.0	837.2	625.9	492.3	390.2	327.5	292.6	268.3	254.3
65°	1973.0	1365.6	940.6	675.9	486.5	379.7	313.6	265.9	245.0	234.6	233.4
67.5°	1597.8	1074.1	665.4	463.3	331.0	274.1	240.4	220.6	211.3	209.0	211.3
70°	1121.8	678.1	422.7	307.8	245.0	220.6	205.5	197.4	191.6	192.7	195.1
72.5°	715.3	406.4	290.3	233.4	206.7	193.9	186.9	184.7	183.5	182.3	182.3
75°	407.6	270.6	223.0	202.1	188.1	177.6	171.8	169.5	170.7	171.8	169.5
77.5°	269.4	223.0	198.5	184.7	171.8	160.2	156.8	155.6	157.9	160.2	160.2
80°	212.5	198.5	184.7	170.7	149.8	141.7	144.0	145.2	144.0	145.2	141.7
82.5°	149.8	147.5	151.0	145.2	124.2	117.3	114.9	116.2	113.8	113.8	111.5
85°	69.6	69.6	73.2	73.2	70.9	72.0	77.8	84.8	88.3	84.8	80.1
87.5°	0.0	0.0	0.0	0.0	0.0	10.5	20.9	30.2	32.5	40.6	39.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152753

CATALOG NUMBER: VXS-F05-LED-E1-SLL-8030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1
2.5°	1236.7	1239.1	1237.8	1236.7	1239.1	1236.7	1237.8	1236.7	1236.7	1235.5	1235.5
5°	1276.2	1279.7	1272.7	1271.5	1269.2	1263.4	1263.4	1261.1	1261.1	1256.5	1253.0
7.5°	1301.8	1302.9	1297.1	1296.0	1290.2	1284.4	1279.7	1275.0	1273.9	1270.4	1263.4
10°	1326.1	1323.8	1319.2	1313.4	1307.6	1299.4	1293.6	1287.8	1286.6	1280.8	1272.7
12.5°	1347.0	1345.9	1336.6	1330.8	1321.5	1313.4	1306.4	1299.4	1296.0	1288.9	1277.3
15°	1360.9	1354.0	1342.4	1331.9	1321.5	1312.2	1304.0	1296.0	1292.4	1284.4	1272.7
17.5°	1355.1	1342.4	1327.3	1314.5	1300.6	1288.9	1282.0	1273.9	1268.1	1263.4	1247.2
20°	1334.2	1315.6	1292.4	1277.3	1258.8	1243.6	1239.1	1230.9	1226.2	1208.8	1188.0
22.5°	1279.7	1253.0	1223.9	1201.9	1180.9	1165.9	1154.3	1146.1	1134.5	1124.0	1091.5
25°	1211.2	1180.9	1150.8	1124.0	1096.2	1073.0	1052.0	1032.3	1026.5	1004.5	973.1
27.5°	1145.0	1111.3	1081.1	1049.7	1013.8	984.8	948.7	920.8	902.3	879.1	850.1
30°	1074.1	1040.4	999.8	958.0	916.2	884.9	844.2	810.6	787.4	762.9	736.2
32.5°	984.8	944.0	895.3	848.8	810.6	773.4	732.7	700.2	677.0	654.9	629.4
35°	882.5	829.1	776.9	725.8	685.1	653.8	617.8	593.4	577.1	557.4	530.7
37.5°	765.3	704.9	649.1	609.6	573.7	543.4	517.9	502.8	485.4	474.9	458.7
40°	646.8	587.6	533.0	497.0	466.8	449.4	435.4	432.0	420.4	406.4	396.0
42.5°	542.3	485.4	432.0	402.9	383.2	378.5	371.6	371.6	365.8	355.3	348.4
45°	471.5	412.2	365.8	344.9	334.4	333.3	329.7	329.7	328.6	323.9	315.9
47.5°	420.4	366.9	331.0	318.1	315.9	313.6	310.1	308.9	307.8	304.2	299.6
50°	373.9	328.6	305.4	299.6	300.7	297.3	293.8	290.3	289.1	285.7	281.0
52.5°	331.0	298.4	283.3	279.9	279.9	279.9	277.5	277.5	275.2	274.1	269.4
55°	306.5	282.2	274.1	272.8	271.7	270.6	268.3	268.3	265.9	264.8	259.0
57.5°	285.7	270.6	265.9	263.6	262.5	260.1	259.0	259.0	259.0	259.0	252.0
60°	269.4	262.5	261.2	259.0	257.8	253.2	250.8	249.6	250.8	252.0	245.0
62.5°	252.0	250.8	249.6	247.4	246.2	241.6	238.0	235.8	238.0	240.4	239.2
63°	247.4	246.2	246.2	245.0	243.8	238.0	234.6	232.2	234.6	236.9	236.9
65°	231.1	232.2	232.2	231.1	229.9	226.4	221.8	219.5	220.6	224.1	225.3
67.5°	213.7	214.8	213.7	214.8	213.7	211.3	207.9	205.5	204.4	205.5	206.7
70°	197.4	199.7	198.5	197.4	196.3	196.3	193.9	190.5	189.3	188.1	188.1
72.5°	183.5	183.5	181.1	181.1	180.0	180.0	177.6	174.2	173.1	173.1	170.7
75°	168.4	168.4	164.9	164.9	162.6	163.7	161.5	157.9	156.8	156.8	155.6
77.5°	159.1	155.6	149.8	148.6	147.5	147.5	146.3	142.8	141.7	141.7	140.5
80°	140.5	133.6	127.8	126.5	127.8	130.1	130.1	127.8	127.8	127.8	127.8
82.5°	109.1	106.8	103.3	101.0	101.0	104.6	109.1	111.5	113.8	116.2	116.2
85°	80.1	81.2	80.1	76.7	75.4	79.0	83.6	88.3	89.4	94.1	92.8
87.5°	43.0	44.1	40.6	39.5	43.0	45.3	49.9	51.1	53.4	54.6	55.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152753

CATALOG NUMBER: VXS-F05-LED-E1-SLL-8030

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1
2.5°	1234.4	1233.3	1234.4	1232.0	1232.0	1229.7	1227.5	1226.2	1223.9	1222.8	1220.4
5°	1255.3	1251.8	1248.3	1247.2	1242.5	1237.8	1234.4	1228.6	1223.9	1215.9	1213.5
7.5°	1269.2	1261.1	1256.5	1255.3	1248.3	1244.9	1236.7	1229.7	1222.8	1212.3	1208.8
10°	1275.0	1266.9	1258.8	1255.3	1247.2	1241.3	1233.3	1222.8	1217.0	1206.5	1204.1
12.5°	1282.0	1266.9	1254.1	1244.9	1233.3	1220.4	1212.3	1206.5	1198.3	1192.5	1190.3
15°	1269.2	1249.4	1229.7	1212.3	1193.8	1179.8	1171.7	1162.4	1153.1	1149.6	1149.6
17.5°	1234.4	1208.8	1175.1	1153.1	1133.4	1118.2	1107.8	1098.5	1097.4	1092.7	1095.0
20°	1162.4	1128.7	1096.2	1079.9	1068.3	1059.1	1048.6	1043.9	1040.4	1033.5	1031.2
22.5°	1062.5	1034.6	1011.4	999.8	990.6	979.0	969.6	955.6	952.2	945.3	941.8
25°	952.2	930.2	910.4	902.3	896.5	880.2	874.4	855.9	843.0	834.9	839.6
27.5°	841.9	825.6	807.0	796.6	793.2	778.0	772.2	751.3	740.8	740.8	729.2
30°	728.1	713.0	701.3	689.7	687.5	668.9	653.8	645.6	634.0	629.4	621.2
32.5°	621.2	606.1	596.9	591.1	581.8	566.6	551.6	537.6	519.1	512.1	508.6
35°	522.6	511.0	499.4	494.7	481.9	465.7	447.0	435.4	413.4	405.3	401.8
37.5°	447.0	433.2	425.0	412.2	399.5	382.1	368.1	357.6	349.5	346.0	346.0
40°	386.7	376.3	366.9	356.5	346.0	336.8	329.7	327.5	326.3	326.3	328.6
42.5°	341.5	332.1	327.5	321.7	318.1	318.1	317.0	318.1	319.4	320.5	323.9
45°	311.2	305.4	303.1	302.0	304.2	306.5	307.8	310.1	314.7	317.0	318.1
47.5°	294.9	290.3	289.1	290.3	293.8	298.4	303.1	306.5	310.1	311.2	312.3
50°	278.7	272.8	270.6	272.8	277.5	284.5	288.0	293.8	296.1	298.4	296.1
52.5°	264.8	260.1	259.0	259.0	263.6	268.3	272.8	277.5	278.7	278.7	277.5
55°	253.2	249.6	246.2	248.5	252.0	256.6	263.6	267.0	269.4	270.6	270.6
57.5°	243.8	240.4	236.9	239.2	242.7	247.4	254.3	257.8	260.1	263.6	264.8
60°	236.9	232.2	228.8	232.2	235.8	242.7	248.5	252.0	257.8	259.0	259.0
62.5°	229.9	225.3	219.5	223.0	223.0	226.4	232.2	236.9	242.7	245.0	245.0
63°	228.8	224.1	218.3	220.6	220.6	223.0	227.6	232.2	239.2	241.6	240.4
65°	219.5	218.3	212.5	212.5	210.2	212.5	216.0	220.6	224.1	227.6	227.6
67.5°	204.4	203.2	202.1	202.1	202.1	204.4	206.7	210.2	213.7	216.0	214.8
70°	186.9	186.9	186.9	188.1	188.1	190.5	191.6	190.5	193.9	196.3	195.1
72.5°	171.8	170.7	169.5	171.8	170.7	170.7	173.1	171.8	175.3	175.3	176.5
75°	155.6	154.4	154.4	155.6	153.3	151.0	152.1	152.1	153.3	153.3	155.6
77.5°	141.7	141.7	141.7	140.5	138.1	137.0	135.9	135.9	135.9	135.9	137.0
80°	128.9	128.9	128.9	127.8	125.4	123.1	120.7	119.6	118.4	112.6	112.6
82.5°	116.2	116.2	116.2	116.2	114.9	112.6	109.1	99.9	95.2	90.6	91.7
85°	91.7	94.1	96.4	99.9	98.7	98.7	91.7	80.1	73.2	68.5	69.6
87.5°	59.2	52.2	52.2	51.1	48.8	46.4	46.4	39.5	32.5	29.0	30.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152753
CATALOG NUMBER: VXS-F05-LED-E1-SLL-8030

REPORT N
CATALOG

CANDELA DISTRIBUTION (continued):

CANDELA

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°	
0°	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	0°
2.5°	1220.4	1218.1	1215.9	1215.9	1212.3	1212.3	1209.9	1214.6	1209.9	1206.5	1206.5	2.5°
5°	1211.2	1208.8	1201.9	1200.7	1196.1	1196.1	1196.1	1193.8	1193.8	1191.4	1190.3	5°
7.5°	1205.4	1199.6	1193.8	1190.3	1190.3	1188.0	1192.5	1190.3	1191.4	1191.4	1192.5	7.5°
10°	1200.7	1196.1	1193.8	1192.5	1192.5	1196.1	1199.6	1200.7	1199.6	1200.7	1200.7	10°
12.5°	1189.1	1191.4	1192.5	1197.2	1203.0	1209.9	1218.1	1219.3	1221.7	1221.7	1223.9	12.5°
15°	1151.9	1157.7	1164.7	1176.4	1191.4	1206.5	1221.7	1234.4	1246.0	1251.8	1256.5	15°
17.5°	1099.7	1105.5	1118.2	1131.0	1150.8	1172.8	1198.3	1220.4	1244.9	1266.9	1288.9	17.5°
20°	1028.8	1038.1	1041.7	1064.9	1088.1	1118.2	1148.5	1183.3	1225.1	1266.9	1309.8	20°
22.5°	937.1	947.6	963.8	982.4	1006.7	1043.9	1079.9	1134.5	1190.3	1249.4	1316.8	22.5°
25°	834.9	846.5	860.5	880.2	904.6	944.0	996.4	1054.4	1122.9	1200.7	1284.4	25°
27.5°	729.2	740.8	752.4	766.4	794.3	836.1	897.6	958.0	1033.5	1118.2	1215.9	27.5°
30°	623.6	624.8	631.7	649.1	678.1	732.7	778.0	853.5	932.4	1021.9	1134.5	30°
32.5°	507.5	506.3	514.4	529.5	557.4	609.6	665.4	738.5	816.4	929.0	1045.1	32.5°
35°	404.1	404.1	419.2	434.3	465.7	502.8	551.6	616.6	708.4	812.8	929.0	35°
37.5°	349.5	357.6	366.9	382.1	406.4	435.4	478.4	535.3	607.4	707.2	814.0	37.5°
40°	332.1	336.8	344.9	358.9	379.7	406.4	437.8	480.7	536.5	616.6	714.2	40°
42.5°	325.2	326.3	331.0	341.5	360.0	386.7	419.2	457.5	499.4	556.3	641.0	42.5°
45°	318.1	317.0	319.4	327.5	342.6	372.7	409.9	451.7	493.5	541.1	610.8	45°
47.5°	312.3	312.3	312.3	315.9	329.7	360.0	402.9	451.7	501.7	555.0	623.6	47.5°
50°	296.1	294.9	294.9	297.3	307.8	340.2	391.3	450.6	515.5	585.3	663.1	50°
52.5°	277.5	277.5	278.7	279.9	289.1	321.7	378.5	450.6	531.8	624.8	722.3	52.5°
55°	271.7	272.8	274.1	272.8	279.9	307.8	364.7	443.6	538.9	656.1	786.1	55°
57.5°	267.0	269.4	269.4	268.3	272.8	296.1	350.7	429.6	533.0	667.7	831.4	57.5°
60°	260.1	260.1	260.1	256.6	259.0	279.9	329.7	407.6	514.4	657.2	838.4	60°
62.5°	245.0	245.0	242.7	241.6	240.4	256.6	302.0	375.0	480.7	629.4	821.0	62.5°
63°	241.6	240.4	240.4	236.9	236.9	252.0	296.1	370.5	471.5	622.4	814.0	63°
65°	228.8	228.8	228.8	226.4	225.3	236.9	272.8	337.9	435.4	589.9	779.2	65°
67.5°	214.8	216.0	213.7	212.5	211.3	218.3	246.2	297.3	379.7	521.3	714.2	67.5°
70°	195.1	196.3	196.3	195.1	193.9	198.5	216.0	255.4	314.7	434.3	608.5	70°
72.5°	177.6	180.0	180.0	182.3	182.3	185.8	192.7	212.5	252.0	339.1	478.4	72.5°
75°	159.1	160.2	162.6	164.9	162.6	161.5	162.6	177.6	197.4	250.8	341.5	75°
77.5°	142.8	146.3	146.3	145.2	141.7	139.4	139.4	146.3	162.6	190.5	243.8	77.5°
80°	118.4	124.2	125.4	122.0	118.4	118.4	120.7	125.4	135.9	156.8	184.7	80°
82.5°	95.2	101.0	102.2	103.3	102.2	105.7	105.7	106.8	112.6	128.9	151.0	82.5°
85°	73.2	77.8	81.2	82.5	83.6	84.8	83.6	77.8	81.2	91.7	102.2	85°
87.5°	32.5	33.7	31.4	32.5	31.4	32.5	33.7	27.9	26.7	36.0	37.2	87.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	90°

NUMBER: P152753

NUMBER: VXS-F05-LED-E1-SLL-8030

DISTRIBUTION (continued):

330°	335°	340°	345°	350°	355°	360°
1218.1	1218.1	1218.1	1218.1	1218.1	1218.1	1218.1
1205.4	1205.4	1206.5	1204.1	1204.1	1205.4	1201.9
1186.7	1191.4	1191.4	1191.4	1189.1	1191.4	1192.5
1191.4	1194.9	1197.2	1197.2	1196.1	1200.7	1204.1
1197.2	1203.0	1205.4	1205.4	1205.4	1211.2	1219.3
1219.3	1223.9	1227.5	1227.5	1229.7	1236.7	1246.0
1259.9	1265.7	1265.7	1264.6	1271.5	1279.7	1290.2
1305.2	1321.5	1329.6	1328.4	1334.2	1344.7	1356.3
1348.2	1393.5	1413.2	1427.2	1433.0	1446.8	1450.4
1384.1	1459.7	1514.2	1560.7	1582.8	1596.7	1613.0
1371.4	1473.6	1571.1	1666.3	1733.7	1802.2	1831.3
1319.2	1446.8	1574.6	1714.0	1835.9	1957.8	2046.1
1255.3	1408.6	1580.4	1777.8	1970.6	2157.5	2306.2
1182.2	1372.5	1593.2	1837.1	2090.2	2335.2	2550.1
1090.4	1304.0	1561.9	1842.9	2141.3	2438.5	2717.3
974.3	1211.2	1488.7	1801.0	2143.6	2483.8	2817.1
858.1	1093.9	1395.8	1740.7	2113.5	2494.3	2879.8
776.9	989.3	1301.8	1664.0	2064.7	2478.0	2910.1
721.1	913.9	1218.1	1594.4	2012.4	2449.0	2914.7
716.5	881.3	1163.5	1543.3	1970.6	2423.5	2914.7
756.0	898.8	1145.0	1517.7	1953.2	2415.3	2917.0
830.3	968.5	1178.7	1537.5	1967.2	2425.8	2927.5
919.7	1074.1	1269.2	1606.0	2026.3	2460.6	2950.7
1000.9	1196.1	1423.6	1738.3	2134.3	2548.9	3015.8
1048.6	1300.6	1587.4	1924.1	2319.0	2724.2	3145.8
1054.4	1358.7	1732.5	2126.2	2543.1	2925.1	3353.6
1049.7	1363.3	1751.1	2164.6	2590.7	2975.0	3425.6
1024.2	1364.5	1803.4	2299.3	2755.5	3185.3	3626.5
959.2	1327.3	1822.0	2404.9	2963.4	3461.7	4001.6
846.5	1221.7	1767.4	2407.3	3043.5	3616.1	4238.4
680.5	1020.7	1531.6	2190.1	2832.2	3463.9	4176.9
498.1	750.2	1157.7	1696.6	2310.9	2883.3	3577.7
331.0	485.4	780.3	1208.8	1657.1	2075.1	2575.6
227.6	300.7	456.4	726.9	1013.8	1217.0	1640.8
167.3	198.5	253.2	371.6	487.7	600.3	857.0
104.6	113.8	126.5	183.5	262.5	354.2	534.2
27.9	29.0	26.7	36.0	56.9	54.6	60.4
0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)