

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P880499

Luminaire Tested: **EMM2-HSN-VA4-830-U-CQ**

Issue Date: 10/01/2024



Test Information

Test Method: LM-79-08
Report Number: P880499
Test Lab: INNOVATION CENTER(G3)
Issue Date: 10/01/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: EMM2-HSN-VA4-830-U-CQ
Description: EPIC MODERN SHORT HOUSING 4W 80CRI 3000K VISUAL COMFORT FIXTURE w/
TYPE V CONCENTRATED DISTRIBUTION OPTIC
Light Source: (1) 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4446.6 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type V - Short
BUG Rating: B2 - U0 - G1

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 9%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P880499
 CATALOG NUMBER: EMM2-HSN-VA4-830-U-CQ

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 4.5 fc
 Type V - Short - N/A

REPORT NUMBER: P880499
CATALOG NUMBER: EMM2-HSN-VA4-830-U-CQ

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P880499
 CATALOG NUMBER: EMM2-HSN-VA4-830-U-CQ

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 2223.3 | 0.0 | 2223.3 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 2223.3 | 0.0 | 2223.3 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 4446.6 | 0.0 | 4446.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 95.8 | 2.2 |
| 10°-20° | 281.7 | 6.3 |
| 20°-30° | 453.2 | 10.2 |
| 30°-40° | 611.9 | 13.8 |
| 40°-50° | 769.2 | 17.3 |
| 50°-60° | 864.7 | 19.4 |
| 60°-70° | 787.4 | 17.7 |
| 70°-80° | 475.5 | 10.7 |
| 80°-90° | 107.2 | 2.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4446.6 | 100.0 |
| 0°-180° | 4446.6 | 100.0 |



REPORT NUMBER: P880499


CATALOG NUMBER: EMM2-HSN-VA4-830-U-CQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 415.4 | 9.3 | | | |
| FM (30°-60°) | 1122.9 | 25.3 | | | |
| FH (60°-80°) | 631.4 | 14.2 | | | G0/660 |
| FVH (80°-90°) | 53.6 | 1.2 | | | G1/100 |
| BL (0°-30°) | 415.4 | 9.3 | B1/500 | | |
| BM (30°-60°) | 1122.9 | 25.3 | B2/2500 | | |
| BH (60°-80°) | 631.4 | 14.2 | B2/1000 | | G0/660 |
| BVH (80°-90°) | 53.6 | 1.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G1

Type V Short





REPORT NUMBER: P880499

CATALOG NUMBER: EMM2-HSN-VA4-830-U-CQ

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 |
| 2.5° | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 | 1005.4 |
| 5° | 1003.7 | 1003.7 | 1003.7 | 1003.7 | 1003.7 | 1003.7 | 1003.7 | 1003.7 | 1003.7 | 1003.7 | 1005.4 |
| 7.5° | 1001.9 | 1003.7 | 1003.7 | 1001.9 | 1003.7 | 1003.7 | 1003.7 | 1003.7 | 1003.7 | 1003.7 | 1003.7 |
| 10° | 1000.2 | 1000.2 | 1001.9 | 1001.9 | 1001.9 | 1001.9 | 1001.9 | 1001.9 | 1001.9 | 1001.9 | 1000.2 |
| 12.5° | 996.7 | 998.4 | 998.4 | 998.4 | 998.4 | 998.4 | 998.4 | 998.4 | 998.4 | 998.4 | 998.4 |
| 15° | 994.9 | 994.9 | 994.9 | 994.9 | 994.9 | 994.9 | 994.9 | 994.9 | 993.2 | 993.2 | 994.9 |
| 17.5° | 989.7 | 989.7 | 991.5 | 991.5 | 991.5 | 991.5 | 991.5 | 991.5 | 989.7 | 989.7 | 989.7 |
| 20° | 986.2 | 986.2 | 988.0 | 988.0 | 988.0 | 989.7 | 988.0 | 986.2 | 986.2 | 986.2 | 986.2 |
| 22.5° | 982.7 | 982.7 | 984.5 | 984.5 | 986.2 | 986.2 | 984.5 | 984.5 | 982.7 | 982.7 | 982.7 |
| 25° | 979.2 | 979.2 | 979.2 | 981.0 | 982.7 | 981.0 | 981.0 | 979.2 | 977.5 | 975.7 | 975.7 |
| 27.5° | 974.0 | 974.0 | 974.0 | 977.5 | 977.5 | 979.2 | 977.5 | 975.7 | 972.3 | 970.5 | 970.5 |
| 30° | 968.8 | 968.8 | 970.5 | 974.0 | 975.7 | 975.7 | 974.0 | 970.5 | 967.0 | 965.3 | 965.3 |
| 32.5° | 963.5 | 965.3 | 967.0 | 972.3 | 974.0 | 975.7 | 972.3 | 968.8 | 963.5 | 960.0 | 960.0 |
| 35° | 963.5 | 963.5 | 968.8 | 974.0 | 979.2 | 981.0 | 977.5 | 970.5 | 963.5 | 958.3 | 958.3 |
| 37.5° | 965.3 | 967.0 | 974.0 | 981.0 | 988.0 | 991.5 | 986.2 | 977.5 | 967.0 | 960.0 | 960.0 |
| 40° | 972.3 | 972.3 | 981.0 | 993.2 | 1001.9 | 1003.7 | 998.4 | 986.2 | 972.3 | 963.5 | 961.8 |
| 42.5° | 975.7 | 977.5 | 986.2 | 1000.2 | 1010.7 | 1014.1 | 1007.2 | 993.2 | 975.7 | 963.5 | 961.8 |
| 45° | 975.7 | 977.5 | 988.0 | 1003.7 | 1017.6 | 1021.1 | 1014.1 | 996.7 | 977.5 | 965.3 | 961.8 |
| 47.5° | 970.5 | 972.3 | 986.2 | 1005.4 | 1021.1 | 1024.6 | 1015.9 | 998.4 | 975.7 | 961.8 | 958.3 |
| 50° | 963.5 | 965.3 | 979.2 | 1003.7 | 1022.9 | 1029.9 | 1019.4 | 996.7 | 970.5 | 954.8 | 951.3 |
| 52.5° | 949.6 | 951.3 | 970.5 | 996.7 | 1021.1 | 1028.1 | 1015.9 | 991.5 | 960.0 | 942.6 | 939.1 |
| 55° | 928.6 | 932.1 | 951.3 | 982.7 | 1010.7 | 1019.4 | 1005.4 | 977.5 | 944.3 | 923.4 | 919.9 |
| 57.5° | 900.7 | 902.4 | 925.1 | 960.0 | 989.7 | 998.4 | 984.5 | 954.8 | 918.1 | 895.5 | 893.7 |
| 60° | 860.5 | 864.0 | 890.2 | 925.1 | 956.5 | 965.3 | 951.3 | 919.9 | 881.5 | 857.1 | 855.3 |
| 62.5° | 811.7 | 815.2 | 839.6 | 879.7 | 911.2 | 919.9 | 905.9 | 872.8 | 834.4 | 808.2 | 806.4 |
| 65° | 750.6 | 754.1 | 778.5 | 816.9 | 850.1 | 858.8 | 846.6 | 811.7 | 773.3 | 748.8 | 745.3 |
| 67.5° | 682.5 | 686.0 | 708.7 | 741.8 | 771.5 | 783.7 | 771.5 | 741.8 | 705.2 | 675.5 | 672.0 |
| 70° | 600.5 | 600.5 | 623.2 | 656.3 | 684.2 | 700.0 | 684.2 | 654.6 | 617.9 | 593.5 | 593.5 |
| 72.5° | 514.9 | 511.4 | 532.4 | 563.8 | 586.5 | 593.5 | 590.0 | 563.8 | 528.9 | 506.2 | 502.7 |
| 75° | 411.9 | 418.9 | 434.6 | 457.3 | 481.8 | 492.2 | 480.0 | 457.3 | 432.9 | 413.7 | 411.9 |
| 77.5° | 319.4 | 324.7 | 338.6 | 357.8 | 371.8 | 378.8 | 375.3 | 357.8 | 331.6 | 322.9 | 319.4 |
| 80° | 225.2 | 228.7 | 240.9 | 254.8 | 265.3 | 272.3 | 267.1 | 253.1 | 239.1 | 230.4 | 226.9 |
| 82.5° | 146.6 | 144.9 | 155.4 | 164.1 | 172.8 | 171.1 | 169.3 | 158.8 | 153.6 | 146.6 | 144.9 |
| 85° | 75.1 | 76.8 | 76.8 | 85.5 | 87.3 | 90.8 | 89.0 | 85.5 | 76.8 | 73.3 | 75.1 |
| 87.5° | 24.4 | 24.4 | 26.2 | 26.2 | 29.7 | 29.7 | 31.4 | 27.9 | 26.2 | 22.7 | 22.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-7

Test Date: 09/27/2024

Luminaire Tested: MEM2-HTN-VA-30-830-U-WQ

Data in this report applies to families of products including MEM2-HTN-VA-30-830-U-WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-176-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 09/27/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Streetworks
 Catalog Number: **MEM2-HTN-VA-30-830-U-WQ**
 Description: EPIC MODERN VISUAL COMFORT 30W WAVESTREAM WIDE

Spectral Parameters

CCT (K): 2984
 CIE u': 0.2500
 CIE v': 0.5264
 Duv: 0.0033
 CIE x: 0.4431
 CIE y: 0.4147
 CIE z: 0.1422
 Peak Wavelength (nm): 601
 Dominant Wavelength (nm): 581
 Purity: 57.4798
 Rf: 85.8
 Rg: 94.1

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 81.8 | | |
| R1: | 79.4 | R9: | -1.1 |
| R2: | 89.9 | R10: | 78.4 |
| R3: | 96.6 | R11: | 80.8 |
| R4: | 80.6 | R12: | 72.8 |
| R5: | 80.1 | R13: | 81.7 |
| R6: | 88.9 | R14: | 98.5 |
| R7: | 82.6 | R15: | 70.2 |
| R8: | 56.0 | | |



Test Conditions

Stabilization Time: 29M
 Operation Time: 1H 29M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-176-7

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-176-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 2984K
 CIE x = 0.4431
 CIE y = 0.4147
 Duv = 0.0033

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 260 | NR | 620 | 905 | NR | 750 | 22 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 312 | NR | 625 | 856 | NR | 755 | 19 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 362 | NR | 630 | 801 | NR | 760 | 17 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 399 | NR | 635 | 742 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 425 | NR | 640 | 677 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 446 | NR | 645 | 613 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 459 | NR | 650 | 549 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 0 | NR | 525 | 473 | NR | 655 | 485 | NR | 785 | 7 | NR | 915 | 0 | NR |
| 400 | 1 | NR | 530 | 490 | NR | 660 | 425 | NR | 790 | 6 | NR | 920 | 0 | NR |
| 405 | 2 | NR | 535 | 511 | NR | 665 | 371 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 535 | NR | 670 | 321 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 11 | NR | 545 | 565 | NR | 675 | 276 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 24 | NR | 550 | 595 | NR | 680 | 238 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 47 | NR | 555 | 631 | NR | 685 | 203 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 86 | NR | 560 | 672 | NR | 690 | 174 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 144 | NR | 565 | 715 | NR | 695 | 148 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 224 | NR | 570 | 763 | NR | 700 | 124 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 342 | NR | 575 | 814 | NR | 705 | 105 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 446 | NR | 580 | 866 | NR | 710 | 88 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 357 | NR | 585 | 912 | NR | 715 | 73 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 237 | NR | 590 | 954 | NR | 720 | 59 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 202 | NR | 595 | 981 | NR | 725 | 48 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 172 | NR | 600 | 996 | NR | 730 | 40 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 152 | NR | 605 | 996 | NR | 735 | 34 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 171 | NR | 610 | 980 | NR | 740 | 29 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 210 | NR | 615 | 947 | NR | 745 | 25 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-176-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.32

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 260 | NR | 620 | 905 | NR | 750 | 22 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 312 | NR | 625 | 856 | NR | 755 | 19 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 362 | NR | 630 | 801 | NR | 760 | 17 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 399 | NR | 635 | 742 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 425 | NR | 640 | 677 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 446 | NR | 645 | 613 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 459 | NR | 650 | 549 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 0 | NR | 525 | 473 | NR | 655 | 485 | NR | 785 | 7 | NR | 915 | 0 | NR |
| 400 | 1 | NR | 530 | 490 | NR | 660 | 425 | NR | 790 | 6 | NR | 920 | 0 | NR |
| 405 | 2 | NR | 535 | 511 | NR | 665 | 371 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 535 | NR | 670 | 321 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 11 | NR | 545 | 565 | NR | 675 | 276 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 24 | NR | 550 | 595 | NR | 680 | 238 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 47 | NR | 555 | 631 | NR | 685 | 203 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 86 | NR | 560 | 672 | NR | 690 | 174 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 144 | NR | 565 | 715 | NR | 695 | 148 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 224 | NR | 570 | 763 | NR | 700 | 124 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 342 | NR | 575 | 814 | NR | 705 | 105 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 446 | NR | 580 | 866 | NR | 710 | 88 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 357 | NR | 585 | 912 | NR | 715 | 73 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 237 | NR | 590 | 954 | NR | 720 | 59 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 202 | NR | 595 | 981 | NR | 725 | 48 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 172 | NR | 600 | 996 | NR | 730 | 40 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 152 | NR | 605 | 996 | NR | 735 | 34 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 171 | NR | 610 | 980 | NR | 740 | 29 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 210 | NR | 615 | 947 | NR | 745 | 25 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-176-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.51

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 260 | NR | 620 | 905 | NR | 750 | 22 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 312 | NR | 625 | 856 | NR | 755 | 19 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 362 | NR | 630 | 801 | NR | 760 | 17 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 399 | NR | 635 | 742 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 425 | NR | 640 | 677 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 446 | NR | 645 | 613 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 459 | NR | 650 | 549 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 0 | NR | 525 | 473 | NR | 655 | 485 | NR | 785 | 7 | NR | 915 | 0 | NR |
| 400 | 1 | NR | 530 | 490 | NR | 660 | 425 | NR | 790 | 6 | NR | 920 | 0 | NR |
| 405 | 2 | NR | 535 | 511 | NR | 665 | 371 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 535 | NR | 670 | 321 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 11 | NR | 545 | 565 | NR | 675 | 276 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 24 | NR | 550 | 595 | NR | 680 | 238 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 47 | NR | 555 | 631 | NR | 685 | 203 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 86 | NR | 560 | 672 | NR | 690 | 174 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 144 | NR | 565 | 715 | NR | 695 | 148 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 224 | NR | 570 | 763 | NR | 700 | 124 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 342 | NR | 575 | 814 | NR | 705 | 105 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 446 | NR | 580 | 866 | NR | 710 | 88 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 357 | NR | 585 | 912 | NR | 715 | 73 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 237 | NR | 590 | 954 | NR | 720 | 59 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 202 | NR | 595 | 981 | NR | 725 | 48 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 172 | NR | 600 | 996 | NR | 730 | 40 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 152 | NR | 605 | 996 | NR | 735 | 34 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 171 | NR | 610 | 980 | NR | 740 | 29 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 210 | NR | 615 | 947 | NR | 745 | 25 | NR | 875 | 0 | NR | | | |

Summary

$R_f = 85.8$
 $R_g = 94.1$
 $CIE R_a = 81.8$
 $R_g = -1.1$




Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 86 | CES51 = 95 | CES76 = 84 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 86 |
| CES03 = 31 | CES28 = 95 | CES53 = 90 | CES78 = 83 |
| CES04 = 70 | CES29 = 89 | CES54 = 91 | CES79 = 90 |
| CES05 = 50 | CES30 = 95 | CES55 = 91 | CES80 = 90 |
| CES06 = 51 | CES31 = 91 | CES56 = 87 | CES81 = 70 |
| CES07 = 42 | CES32 = 85 | CES57 = 86 | CES82 = 96 |
| CES08 = 41 | CES33 = 93 | CES58 = 87 | CES83 = 94 |
| CES09 = 29 | CES34 = 94 | CES59 = 92 | CES84 = 92 |
| CES10 = 76 | CES35 = 97 | CES60 = 94 | CES85 = 77 |
| CES11 = 59 | CES36 = 90 | CES61 = 90 | CES86 = 66 |
| CES12 = 65 | CES37 = 97 | CES62 = 94 | CES87 = 84 |
| CES13 = 43 | CES38 = 97 | CES63 = 88 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 84 | CES89 = 75 |
| CES15 = 72 | CES40 = 95 | CES65 = 80 | CES90 = 88 |
| CES16 = 47 | CES41 = 97 | CES66 = 83 | CES91 = 81 |
| CES17 = 50 | CES42 = 99 | CES67 = 82 | CES92 = 64 |
| CES18 = 56 | CES43 = 93 | CES68 = 84 | CES93 = 79 |
| CES19 = 72 | CES44 = 99 | CES69 = 89 | CES94 = 60 |
| CES20 = 67 | CES45 = 94 | CES70 = 82 | CES95 = 74 |
| CES21 = 87 | CES46 = 90 | CES71 = 81 | CES96 = 83 |
| CES22 = 79 | CES47 = 93 | CES72 = 93 | CES97 = 89 |
| CES23 = 92 | CES48 = 83 | CES73 = 77 | CES98 = 84 |
| CES24 = 91 | CES49 = 92 | CES74 = 92 | CES99 = 75 |
| CES25 = 72 | CES50 = 95 | CES75 = 83 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)