

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P680431

Luminaire Tested: **CCP-SA-2-AMB-U-SLL**

Issue Date: 04/26/2023



Test Information

Test Method: LM-79-08
Report Number: P680431
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/26/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2-AMB-U-SLL
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @500mA w/ SLL distribution lens
Light Source: (16) 1620 CCT, 0 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1619.3 lumens
Efficiency: N/A
Efficacy: 40.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B0 - U0 - G1

Input Watts (W): 40.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 2.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P680431
CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	301.3	0.0	301.3
	% Fixture	18.6	0.0	18.6
Street Side	Lumens	1318.0	0.0	1318.0
	% Fixture	81.4	0.0	81.4
Total	Lumens	1619.3	0.0	1619.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.8	2.5
10°-20°	75.9	4.7
20°-30°	109.8	6.8
30°-40°	159.5	9.9
40°-50°	218.4	13.5
50°-60°	329.1	20.3
60°-70°	416.8	25.7
70°-80°	212.1	13.1
80°-90°	57.9	3.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	1619.3	100.0
0°-180°	1619.3	100.0



REPORT NUMBER: P680431


CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	157.4	9.7			
FM (30°-60°)	574.3	35.5			
FH (60°-80°)	536.9	33.2			G0/660
FVH (80°-90°)	49.5	3.1			G1/100
BL (0°-30°)	68.2	4.2	B0/110		
BM (30°-60°)	132.7	8.2	B0/220		
BH (60°-80°)	92.0	5.7	B0/110		G0/110
BVH (80°-90°)	8.4	0.5			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type IV Short





REPORT NUMBER: P680431

CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	596.5	596.5	595.4	601.0	607.8	613.4	619.1	621.3	623.6	624.7	627.0
5°	556.9	566.0	573.9	586.3	598.7	610.0	622.5	631.5	639.4	648.5	656.4
7.5°	493.7	503.8	512.9	528.7	544.5	560.3	576.2	588.6	601.0	612.3	624.7
10°	430.4	446.2	460.9	475.6	489.2	503.8	517.4	532.1	546.8	560.3	575.0
12.5°	401.0	419.1	437.2	449.6	462.1	473.3	485.8	497.1	507.2	518.5	528.7
15°	401.0	416.9	431.5	442.8	454.1	464.3	475.6	482.4	490.3	497.1	503.8
17.5°	430.4	448.5	466.6	472.2	476.7	482.4	486.9	486.9	486.9	486.9	486.9
20°	464.3	486.9	509.5	511.8	512.9	515.1	516.3	505.0	492.6	481.3	468.8
22.5°	521.9	541.1	560.3	554.7	547.9	542.3	535.5	519.7	503.8	488.0	472.2
25°	579.5	589.7	599.9	592.0	585.2	577.3	569.4	549.0	527.6	507.2	485.8
27.5°	663.1	662.0	659.7	647.3	633.8	621.3	607.8	584.1	559.2	535.5	510.6
30°	703.8	689.1	673.3	663.1	653.0	642.8	632.6	604.4	577.3	549.0	520.8
32.5°	751.3	726.4	700.4	691.4	683.5	674.4	665.4	636.0	607.8	578.4	549.0
35°	782.9	755.8	728.7	719.6	709.5	700.4	690.3	659.7	629.2	598.7	568.2
37.5°	791.9	769.3	746.7	734.3	720.8	708.3	694.8	668.8	641.7	615.7	588.6
40°	826.9	803.2	779.5	761.4	744.5	726.4	708.3	681.2	654.1	627.0	599.9
42.5°	854.1	831.5	808.9	785.1	760.3	736.6	711.7	689.1	667.7	645.1	622.5
45°	890.2	849.5	808.9	778.4	747.9	717.4	686.9	677.8	668.8	658.6	649.6
47.5°	933.1	866.5	798.7	767.1	735.4	703.8	672.2	672.2	673.3	673.3	673.3
50°	950.1	884.6	819.0	781.8	745.6	708.3	671.0	689.1	706.1	724.1	741.1
52.5°	986.2	921.8	856.3	823.6	790.8	758.0	725.3	747.9	769.3	791.9	813.4
55°	1051.8	986.2	920.7	893.6	865.4	838.2	810.0	839.4	868.7	897.0	926.4
57.5°	1182.8	1100.3	1017.9	989.6	962.5	935.4	908.3	945.6	982.8	1020.1	1057.4
60°	1296.9	1234.8	1171.5	1135.4	1100.3	1064.2	1028.0	1074.4	1119.5	1165.9	1211.0
62.5°	1312.7	1283.3	1254.0	1226.9	1199.7	1173.8	1146.7	1180.5	1213.3	1247.2	1280.0
65°	1276.6	1261.9	1247.2	1241.5	1235.9	1230.3	1224.6	1230.3	1235.9	1241.5	1247.2
67.5°	1132.0	1151.2	1169.2	1185.1	1200.9	1215.6	1231.4	1190.7	1151.2	1110.5	1069.8
70°	913.9	956.9	998.7	1026.9	1055.1	1083.4	1111.6	1051.8	990.8	930.9	869.9
72.5°	698.2	726.4	754.6	794.2	833.7	873.3	912.8	848.4	784.0	718.5	654.1
75°	467.7	499.3	531.0	579.5	628.1	675.6	724.1	664.3	603.3	543.4	482.4
77.5°	311.8	332.1	351.3	405.6	459.8	514.0	568.2	517.4	466.6	414.6	363.8
80°	224.8	240.6	255.3	291.5	327.6	362.6	398.8	371.7	344.6	316.3	289.2
82.5°	136.7	152.5	168.3	192.1	215.8	238.4	262.1	251.9	241.8	230.5	220.3
85°	62.1	81.3	99.4	122.0	144.6	167.2	189.8	180.8	170.6	161.5	151.4
87.5°	9.0	14.7	19.2	47.4	76.8	105.1	133.3	122.0	110.7	98.3	87.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431

CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	630.4	633.8	637.2	640.5	640.5	641.7	641.7	641.7	642.8	643.9	643.9
5°	659.7	663.1	666.5	669.9	673.3	676.7	679.0	682.3	681.2	680.1	677.8
7.5°	633.8	641.7	650.7	658.6	665.4	671.0	677.8	683.5	675.6	668.8	660.9
10°	588.6	603.3	616.8	630.4	631.5	633.8	634.9	636.0	632.6	630.4	627.0
12.5°	538.9	549.0	558.1	568.2	571.6	575.0	578.4	581.8	582.9	584.1	585.2
15°	507.2	510.6	514.0	517.4	520.8	523.1	526.4	528.7	531.0	533.2	535.5
17.5°	484.6	483.5	481.3	479.0	481.3	483.5	484.6	486.9	490.3	492.6	495.9
20°	466.6	463.2	460.9	457.5	457.5	457.5	456.4	456.4	460.9	465.4	468.8
22.5°	463.2	455.3	446.2	437.2	437.2	436.1	436.1	434.9	440.6	446.2	451.9
25°	473.3	462.1	449.6	437.2	437.2	436.1	436.1	434.9	441.7	449.6	456.4
27.5°	494.8	477.9	462.1	445.1	444.0	441.7	440.6	438.3	447.4	455.3	464.3
30°	505.0	489.2	473.3	457.5	454.1	450.8	446.2	442.8	453.0	464.3	474.5
32.5°	528.7	509.5	489.2	468.8	463.2	457.5	451.9	446.2	459.8	473.3	486.9
35°	545.6	524.2	501.6	479.0	474.5	468.8	464.3	458.7	471.1	484.6	497.1
37.5°	568.2	546.8	526.4	505.0	499.3	493.7	486.9	481.3	497.1	511.8	527.6
40°	581.8	563.7	545.6	527.6	526.4	525.3	523.1	521.9	536.6	550.2	564.9
42.5°	610.0	598.7	586.3	573.9	576.2	578.4	579.5	581.8	592.0	602.1	612.3
45°	648.5	646.2	645.1	642.8	647.3	650.7	655.2	658.6	666.5	675.6	683.5
47.5°	686.9	699.3	712.8	725.3	735.4	745.6	754.6	764.8	764.8	765.9	765.9
50°	761.4	781.8	801.0	821.3	836.0	849.5	864.2	877.8	878.9	880.0	881.2
52.5°	848.4	882.3	917.3	951.2	970.4	989.6	1008.8	1028.0	1022.4	1016.7	1010.0
55°	974.9	1024.6	1073.2	1121.8	1139.9	1158.0	1176.0	1194.1	1178.3	1163.6	1147.8
57.5°	1113.9	1169.2	1225.7	1282.2	1298.0	1315.0	1331.9	1348.9	1334.2	1319.5	1304.8
60°	1272.1	1331.9	1392.9	1452.8	1465.2	1477.7	1490.1	1502.5	1490.1	1477.7	1465.2
62.5°	1342.1	1403.1	1465.2	1527.4	1544.3	1562.4	1580.5	1598.5	1583.8	1568.0	1553.3
65°	1293.5	1341.0	1387.3	1433.6	1450.5	1467.5	1484.4	1501.4	1496.9	1493.5	1489.0
67.5°	1092.4	1115.0	1137.6	1160.2	1187.3	1214.4	1240.4	1267.5	1256.2	1246.1	1234.8
70°	865.4	860.8	855.2	850.7	869.9	888.0	907.2	925.2	920.7	917.3	912.8
72.5°	632.6	611.2	589.7	568.2	581.8	594.2	607.8	620.2	616.8	614.6	611.2
75°	467.7	453.0	438.3	423.6	422.5	421.4	420.3	419.1	422.5	424.8	428.2
77.5°	358.1	352.5	345.7	340.0	338.9	337.8	335.5	334.4	338.9	343.4	346.8
80°	293.7	298.2	302.8	307.3	305.0	303.9	301.6	299.4	303.9	307.3	311.8
82.5°	232.7	245.1	256.4	268.9	267.7	266.6	265.5	264.4	266.6	267.7	270.0
85°	158.2	166.1	172.8	179.6	177.4	175.1	172.8	170.6	176.2	183.0	188.7
87.5°	81.3	76.8	71.2	65.5	57.6	49.7	40.7	32.8	44.1	55.4	66.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431

CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	645.1	640.5	634.9	630.4	624.7	621.3	617.9	613.4	610.0	605.5	602.1
5°	676.7	671.0	665.4	659.7	654.1	641.7	630.4	617.9	605.5	597.6	588.6
7.5°	653.0	643.9	633.8	624.7	614.6	604.4	594.2	582.9	572.8	561.5	550.2
10°	623.6	613.4	604.4	594.2	584.1	573.9	562.6	552.4	541.1	528.7	515.1
12.5°	586.3	579.5	571.6	564.9	556.9	545.6	533.2	521.9	509.5	499.3	489.2
15°	537.7	534.4	531.0	526.4	523.1	519.7	516.3	511.8	508.4	498.2	489.2
17.5°	498.2	499.3	500.5	501.6	502.7	509.5	516.3	523.1	529.8	525.3	519.7
20°	473.3	481.3	489.2	497.1	505.0	515.1	526.4	536.6	546.8	546.8	546.8
22.5°	457.5	468.8	480.1	490.3	501.6	517.4	534.4	550.2	566.0	572.8	578.4
25°	463.2	479.0	494.8	509.5	525.3	542.3	560.3	577.3	594.2	603.3	612.3
27.5°	472.2	490.3	507.2	525.3	542.3	564.9	587.4	610.0	632.6	647.3	662.0
30°	484.6	502.7	519.7	537.7	554.7	577.3	599.9	622.5	645.1	663.1	680.1
32.5°	500.5	520.8	540.0	560.3	579.5	602.1	625.9	648.5	671.0	684.6	697.0
35°	509.5	529.8	551.3	571.6	592.0	617.9	642.8	668.8	693.6	706.1	718.5
37.5°	542.3	561.5	580.7	598.7	617.9	640.5	663.1	685.7	708.3	724.1	741.1
40°	578.4	596.5	614.6	632.6	650.7	671.0	692.5	712.8	733.2	755.8	778.4
42.5°	622.5	636.0	650.7	664.3	677.8	702.7	727.5	751.3	776.1	799.8	822.4
45°	691.4	697.0	701.5	707.2	711.7	730.9	749.0	768.2	786.3	815.6	845.0
47.5°	765.9	761.4	756.9	751.3	746.7	750.1	752.4	755.8	758.0	794.2	831.5
50°	882.3	860.8	839.4	817.9	796.4	787.4	777.2	768.2	758.0	797.6	837.1
52.5°	1004.3	962.5	920.7	878.9	837.1	823.6	811.1	797.6	784.0	823.6	863.1
55°	1132.0	1083.4	1034.8	985.1	936.5	908.3	881.2	852.9	824.7	876.7	927.5
57.5°	1290.1	1225.7	1162.5	1098.1	1034.8	1005.4	977.2	947.8	919.6	968.2	1017.9
60°	1452.8	1376.0	1298.0	1221.2	1143.3	1117.3	1091.3	1065.3	1039.3	1092.4	1144.4
62.5°	1537.5	1460.7	1383.9	1307.1	1230.3	1208.8	1187.3	1165.9	1144.4	1194.1	1243.8
65°	1484.4	1428.0	1371.5	1315.0	1258.5	1257.4	1257.4	1256.2	1255.1	1280.0	1304.8
67.5°	1223.5	1194.1	1165.9	1136.5	1107.1	1143.3	1179.4	1214.4	1250.6	1259.6	1268.7
70°	908.3	903.8	900.4	895.9	891.3	947.8	1005.4	1061.9	1118.4	1120.7	1121.8
72.5°	607.8	625.9	642.8	660.9	677.8	742.2	805.5	869.9	933.1	915.1	897.0
75°	430.4	449.6	468.8	488.0	507.2	563.7	619.1	675.6	730.9	704.9	679.0
77.5°	351.3	358.1	364.9	370.5	377.3	427.0	476.7	525.3	575.0	538.9	501.6
80°	315.2	310.7	305.0	300.5	294.9	320.8	345.7	371.7	396.5	375.1	354.7
82.5°	271.1	261.0	251.9	241.8	231.6	247.4	263.2	277.9	293.7	276.8	259.8
85°	194.3	188.7	181.9	176.2	169.5	185.3	201.1	216.9	232.7	206.7	180.8
87.5°	77.9	83.6	88.1	93.8	98.3	115.2	133.3	150.3	167.2	131.0	94.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431

CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	597.6	593.1	589.7	594.2	585.2	589.7	581.8	573.9	566.0	558.1	556.9
5°	580.7	571.6	562.6	549.0	541.1	535.5	526.4	517.4	508.4	499.3	491.4
7.5°	537.7	526.4	514.0	505.0	493.7	484.6	472.2	459.8	446.2	433.8	421.4
10°	502.7	489.2	473.3	456.4	440.6	430.4	416.9	403.3	389.7	376.2	366.0
12.5°	479.0	468.8	451.9	432.7	419.1	401.0	387.5	373.9	359.2	345.7	337.8
15°	479.0	468.8	451.9	434.9	421.4	402.2	385.2	367.2	350.2	332.1	320.8
17.5°	515.1	509.5	488.0	467.7	444.0	419.1	395.4	370.5	346.8	322.0	307.3
20°	546.8	546.8	519.7	494.8	470.0	439.5	407.8	376.2	345.7	314.1	293.7
22.5°	585.2	590.8	567.1	542.3	506.1	463.2	423.6	385.2	346.8	307.3	281.3
25°	620.2	629.2	619.1	602.1	561.5	515.1	463.2	410.1	358.1	306.2	272.3
27.5°	676.7	691.4	684.6	666.5	628.1	575.0	509.5	444.0	379.6	314.1	273.4
30°	698.2	715.1	709.5	711.7	681.2	630.4	549.0	468.8	388.6	307.3	262.1
32.5°	710.6	723.0	737.7	752.4	723.0	669.9	578.4	485.8	394.3	302.8	255.3
35°	729.8	742.2	763.7	796.4	761.4	712.8	607.8	502.7	397.7	292.6	247.4
37.5°	756.9	772.7	803.2	823.6	787.4	734.3	619.1	502.7	387.5	272.3	233.8
40°	801.0	823.6	845.0	869.9	833.7	764.8	639.4	515.1	390.9	265.5	228.2
42.5°	846.2	868.7	897.0	926.4	863.1	788.5	656.4	524.2	392.0	259.8	223.7
45°	873.3	902.6	935.4	964.8	892.5	808.9	674.4	541.1	407.8	273.4	233.8
47.5°	867.6	903.8	954.6	988.5	934.3	854.1	715.1	576.2	438.3	299.4	253.1
50°	875.5	915.1	970.4	1024.6	985.1	908.3	763.7	619.1	474.5	329.9	275.6
52.5°	902.6	942.2	1013.3	1082.3	1035.9	962.5	814.5	667.7	520.8	372.8	307.3
55°	979.5	1030.3	1087.9	1144.4	1117.3	1056.3	893.6	732.1	570.5	407.8	333.3
57.5°	1066.4	1116.2	1177.2	1229.1	1176.0	1099.2	936.5	772.7	610.0	447.4	361.5
60°	1197.5	1249.5	1291.3	1304.8	1231.4	1145.5	977.2	810.0	642.8	474.5	380.7
62.5°	1293.5	1343.2	1348.9	1333.1	1233.6	1109.4	949.0	788.5	628.1	467.7	375.1
65°	1329.7	1354.5	1334.2	1294.6	1183.9	1066.4	908.3	750.1	593.1	434.9	351.3
67.5°	1276.6	1285.6	1248.3	1196.4	1075.5	947.8	805.5	662.0	519.7	377.3	310.7
70°	1124.1	1125.2	1071.0	1006.6	895.9	772.7	663.1	553.6	444.0	334.4	280.2
72.5°	878.9	860.8	811.1	742.2	645.1	566.0	494.8	423.6	353.6	282.4	240.6
75°	651.8	625.9	561.5	495.9	438.3	390.9	349.1	307.3	265.5	223.7	195.4
77.5°	465.4	428.2	380.7	331.0	302.8	275.6	247.4	219.2	189.8	161.5	142.3
80°	333.3	311.8	281.3	254.2	227.1	202.2	178.5	153.6	129.9	105.1	93.8
82.5°	242.9	225.9	189.8	169.5	151.4	141.2	123.1	105.1	85.9	67.8	59.9
85°	154.8	128.8	101.7	80.2	81.3	80.2	70.0	61.0	50.8	40.7	35.0
87.5°	57.6	21.5	15.8	12.4	14.7	19.2	19.2	20.3	20.3	20.3	16.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	555.8	553.6	552.4	546.8	541.1	535.5	529.8	524.2	519.7	514.0	508.4
5°	484.6	476.7	468.8	459.8	451.9	442.8	434.9	425.9	418.0	409.0	399.9
7.5°	407.8	395.4	381.8	375.1	368.3	361.5	354.7	346.8	338.9	331.0	323.1
10°	355.9	344.6	334.4	328.7	323.1	317.4	311.8	306.2	299.4	293.7	286.9
12.5°	328.7	320.8	311.8	305.0	298.2	290.3	283.6	275.6	267.7	258.7	250.8
15°	309.5	298.2	286.9	277.9	270.0	261.0	253.1	241.8	231.6	221.4	210.1
17.5°	291.5	276.8	261.0	248.5	236.1	223.7	211.3	198.8	187.5	176.2	163.8
20°	273.4	251.9	231.6	216.9	201.1	186.4	171.7	159.3	148.0	135.6	123.1
22.5°	255.3	229.3	203.3	186.4	170.6	153.6	137.8	127.7	118.6	108.5	98.3
25°	238.4	204.5	170.6	154.8	139.0	124.3	108.5	103.9	98.3	93.8	88.1
27.5°	231.6	190.9	149.1	136.7	123.1	110.7	98.3	94.9	92.6	89.2	85.9
30°	215.8	170.6	124.3	117.5	109.6	102.8	94.9	92.6	89.2	87.0	83.6
32.5°	209.0	161.5	114.1	107.3	100.5	92.6	85.9	83.6	80.2	77.9	74.6
35°	203.3	158.2	113.0	105.1	97.2	89.2	81.3	79.1	75.7	73.4	70.0
37.5°	195.4	155.9	117.5	107.3	97.2	88.1	77.9	75.7	72.3	70.0	66.7
40°	192.1	154.8	117.5	107.3	97.2	87.0	76.8	73.4	70.0	66.7	63.3
42.5°	188.7	152.5	116.4	106.2	94.9	84.7	74.6	71.2	68.9	65.5	62.1
45°	194.3	153.6	114.1	102.8	91.5	81.3	70.0	67.8	66.7	64.4	62.1
47.5°	205.6	159.3	111.8	100.5	89.2	77.9	66.7	65.5	63.3	62.1	59.9
50°	220.3	166.1	110.7	98.3	87.0	74.6	63.3	62.1	61.0	59.9	58.7
52.5°	240.6	175.1	108.5	96.0	84.7	72.3	61.0	59.9	59.9	58.7	57.6
55°	257.6	183.0	107.3	94.9	82.5	71.2	58.7	57.6	55.4	54.2	52.0
57.5°	274.5	188.7	102.8	91.5	80.2	68.9	57.6	55.4	53.1	50.8	49.7
60°	285.8	192.1	97.2	87.0	75.7	65.5	55.4	53.1	50.8	48.6	46.3
62.5°	281.3	188.7	96.0	84.7	73.4	63.3	52.0	49.7	48.6	46.3	44.1
65°	268.9	185.3	101.7	88.1	74.6	62.1	48.6	47.4	45.2	44.1	41.8
67.5°	244.0	176.2	109.6	93.8	77.9	62.1	46.3	45.2	42.9	41.8	39.5
70°	225.9	170.6	116.4	98.3	80.2	63.3	45.2	42.9	41.8	39.5	37.3
72.5°	200.0	158.2	116.4	98.3	80.2	62.1	44.1	41.8	38.4	36.2	32.8
75°	166.1	137.8	108.5	91.5	74.6	57.6	40.7	38.4	36.2	32.8	30.5
77.5°	123.1	103.9	84.7	72.3	58.7	46.3	33.9	31.6	30.5	28.2	26.0
80°	81.3	70.0	57.6	49.7	41.8	33.9	26.0	24.9	23.7	22.6	21.5
82.5°	50.8	42.9	33.9	30.5	27.1	22.6	19.2	19.2	18.1	18.1	16.9
85°	30.5	24.9	19.2	18.1	16.9	14.7	13.6	12.4	12.4	11.3	10.2
87.5°	14.7	11.3	7.9	7.9	7.9	6.8	6.8	5.6	5.6	4.5	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	506.1	502.7	500.5	497.1	493.7	490.3	485.8	482.4	482.4	481.3	481.3
5°	394.3	388.6	381.8	376.2	370.5	364.9	359.2	353.6	351.3	349.1	346.8
7.5°	318.6	312.9	308.4	302.8	297.1	290.3	284.7	277.9	273.4	268.9	264.4
10°	282.4	276.8	272.3	266.6	261.0	256.4	250.8	245.1	239.5	233.8	227.1
12.5°	245.1	239.5	232.7	227.1	220.3	213.5	206.7	200.0	193.2	186.4	179.6
15°	201.1	190.9	181.9	171.7	166.1	160.4	153.6	148.0	142.3	136.7	131.0
17.5°	154.8	146.9	137.8	128.8	123.1	117.5	111.8	106.2	103.9	101.7	98.3
20°	117.5	110.7	105.1	98.3	96.0	94.9	92.6	90.4	89.2	88.1	87.0
22.5°	96.0	92.6	90.4	87.0	85.9	84.7	83.6	82.5	81.3	80.2	79.1
25°	85.9	84.7	82.5	80.2	79.1	77.9	76.8	75.7	75.7	74.6	74.6
27.5°	83.6	81.3	79.1	76.8	75.7	74.6	72.3	71.2	71.2	70.0	70.0
30°	82.5	81.3	79.1	77.9	76.8	75.7	73.4	72.3	71.2	70.0	68.9
32.5°	74.6	73.4	73.4	72.3	72.3	72.3	72.3	72.3	71.2	70.0	68.9
35°	68.9	67.8	65.5	64.4	63.3	62.1	59.9	58.7	58.7	57.6	57.6
37.5°	65.5	64.4	63.3	62.1	61.0	59.9	57.6	56.5	55.4	55.4	54.2
40°	62.1	61.0	59.9	58.7	57.6	56.5	55.4	54.2	53.1	53.1	52.0
42.5°	61.0	59.9	58.7	57.6	56.5	55.4	53.1	52.0	52.0	50.8	50.8
45°	61.0	59.9	57.6	56.5	55.4	54.2	53.1	52.0	50.8	49.7	48.6
47.5°	58.7	58.7	57.6	56.5	55.4	54.2	52.0	50.8	49.7	48.6	47.4
50°	58.7	59.9	59.9	59.9	57.6	55.4	53.1	50.8	49.7	48.6	46.3
52.5°	58.7	58.7	59.9	59.9	57.6	55.4	53.1	50.8	49.7	47.4	46.3
55°	54.2	55.4	57.6	58.7	56.5	54.2	52.0	49.7	48.6	46.3	45.2
57.5°	50.8	52.0	53.1	54.2	53.1	52.0	50.8	49.7	47.4	46.3	44.1
60°	46.3	47.4	47.4	47.4	48.6	49.7	50.8	52.0	49.7	46.3	44.1
62.5°	44.1	44.1	44.1	45.2	47.4	49.7	52.0	55.4	50.8	47.4	44.1
65°	41.8	42.9	42.9	42.9	44.1	45.2	46.3	47.4	45.2	44.1	41.8
67.5°	39.5	40.7	40.7	40.7	40.7	41.8	41.8	41.8	40.7	39.5	38.4
70°	37.3	38.4	38.4	38.4	38.4	38.4	38.4	38.4	37.3	37.3	36.2
72.5°	33.9	33.9	35.0	35.0	35.0	36.2	36.2	36.2	35.0	35.0	33.9
75°	31.6	31.6	32.8	32.8	32.8	33.9	33.9	33.9	32.8	32.8	31.6
77.5°	27.1	28.2	28.2	29.4	29.4	30.5	30.5	30.5	30.5	29.4	29.4
80°	22.6	22.6	23.7	23.7	24.9	24.9	26.0	26.0	26.0	24.9	24.9
82.5°	16.9	18.1	18.1	18.1	19.2	19.2	20.3	20.3	20.3	19.2	19.2
85°	11.3	11.3	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
87.5°	4.5	4.5	5.6	5.6	5.6	5.6	4.5	4.5	4.5	5.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	480.1	476.7	473.3	470.0	466.6	468.8	471.1	466.6	463.2	462.1	462.1
5°	344.6	341.2	336.7	332.1	328.7	328.7	328.7	329.9	331.0	331.0	329.9
7.5°	259.8	257.6	255.3	253.1	250.8	248.5	245.1	242.9	240.6	239.5	238.4
10°	221.4	216.9	212.4	206.7	202.2	201.1	198.8	192.1	186.4	185.3	183.0
12.5°	172.8	168.3	164.9	160.4	155.9	153.6	150.3	149.1	146.9	145.7	144.6
15°	125.4	123.1	119.7	117.5	114.1	113.0	111.8	111.8	110.7	109.6	109.6
17.5°	96.0	94.9	93.8	92.6	91.5	91.5	90.4	90.4	89.2	89.2	89.2
20°	85.9	85.9	84.7	84.7	83.6	83.6	82.5	81.3	80.2	80.2	80.2
22.5°	77.9	77.9	77.9	76.8	76.8	76.8	75.7	75.7	74.6	74.6	74.6
25°	73.4	73.4	72.3	72.3	71.2	71.2	71.2	72.3	72.3	72.3	71.2
27.5°	68.9	68.9	68.9	68.9	68.9	68.9	68.9	68.9	68.9	68.9	70.0
30°	67.8	67.8	67.8	67.8	67.8	67.8	67.8	67.8	67.8	67.8	67.8
32.5°	67.8	67.8	67.8	67.8	67.8	67.8	66.7	66.7	66.7	66.7	66.7
35°	56.5	56.5	56.5	55.4	55.4	56.5	57.6	57.6	57.6	57.6	57.6
37.5°	53.1	53.1	53.1	52.0	52.0	52.0	52.0	52.0	50.8	50.8	50.8
40°	50.8	50.8	49.7	49.7	48.6	48.6	47.4	47.4	47.4	47.4	47.4
42.5°	49.7	48.6	48.6	47.4	46.3	46.3	46.3	46.3	45.2	45.2	45.2
45°	47.4	47.4	46.3	46.3	45.2	45.2	44.1	44.1	42.9	42.9	42.9
47.5°	46.3	45.2	45.2	44.1	42.9	42.9	41.8	41.8	40.7	40.7	40.7
50°	45.2	44.1	42.9	41.8	40.7	40.7	39.5	39.5	39.5	39.5	38.4
52.5°	44.1	42.9	41.8	40.7	39.5	39.5	38.4	38.4	37.3	37.3	37.3
55°	42.9	41.8	40.7	38.4	37.3	37.3	37.3	37.3	36.2	36.2	36.2
57.5°	41.8	40.7	39.5	38.4	37.3	36.2	36.2	35.0	35.0	33.9	33.9
60°	40.7	39.5	38.4	36.2	35.0	35.0	33.9	33.9	32.8	32.8	32.8
62.5°	40.7	39.5	38.4	36.2	35.0	33.9	32.8	32.8	31.6	31.6	31.6
65°	39.5	38.4	37.3	35.0	33.9	32.8	31.6	31.6	30.5	30.5	30.5
67.5°	37.3	36.2	35.0	33.9	32.8	31.6	30.5	30.5	29.4	29.4	29.4
70°	35.0	33.9	33.9	32.8	31.6	30.5	29.4	29.4	28.2	28.2	28.2
72.5°	32.8	31.6	31.6	30.5	29.4	28.2	27.1	27.1	26.0	26.0	26.0
75°	30.5	29.4	28.2	27.1	26.0	26.0	24.9	24.9	23.7	23.7	23.7
77.5°	28.2	27.1	26.0	23.7	22.6	22.6	21.5	21.5	20.3	20.3	20.3
80°	23.7	22.6	21.5	19.2	18.1	18.1	16.9	16.9	16.9	16.9	15.8
82.5°	18.1	16.9	15.8	13.6	12.4	11.3	10.2	11.3	11.3	11.3	11.3
85°	12.4	11.3	9.0	7.9	5.6	5.6	4.5	5.6	5.6	5.6	6.8
87.5°	5.6	4.5	3.4	2.3	1.1	1.1	1.1	1.1	1.1	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	460.9	459.8	460.9	463.2	464.3	465.4	466.6	466.6	467.7	467.7	465.4
5°	329.9	328.7	331.0	332.1	334.4	335.5	338.9	342.3	344.6	347.9	350.2
7.5°	236.1	235.0	233.8	233.8	232.7	231.6	233.8	236.1	238.4	240.6	241.8
10°	181.9	179.6	177.4	176.2	174.0	171.7	171.7	171.7	170.6	170.6	170.6
12.5°	143.5	142.3	140.1	137.8	134.4	132.2	131.0	128.8	127.7	125.4	125.4
15°	108.5	107.3	107.3	107.3	107.3	107.3	106.2	103.9	102.8	100.5	101.7
17.5°	89.2	89.2	89.2	90.4	90.4	90.4	89.2	89.2	88.1	87.0	87.0
20°	80.2	80.2	80.2	80.2	79.1	79.1	79.1	80.2	80.2	80.2	80.2
22.5°	74.6	74.6	74.6	74.6	74.6	74.6	74.6	75.7	75.7	75.7	75.7
25°	71.2	70.0	70.0	70.0	68.9	68.9	68.9	70.0	70.0	70.0	70.0
27.5°	70.0	70.0	70.0	68.9	68.9	67.8	67.8	67.8	66.7	66.7	66.7
30°	66.7	66.7	66.7	65.5	65.5	64.4	64.4	64.4	63.3	63.3	63.3
32.5°	65.5	65.5	64.4	64.4	63.3	62.1	61.0	61.0	59.9	58.7	58.7
35°	57.6	57.6	57.6	56.5	56.5	55.4	55.4	55.4	55.4	55.4	55.4
37.5°	49.7	49.7	49.7	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8
40°	46.3	46.3	46.3	46.3	45.2	45.2	46.3	47.4	47.4	48.6	48.6
42.5°	44.1	44.1	44.1	44.1	42.9	42.9	44.1	44.1	45.2	45.2	45.2
45°	41.8	41.8	41.8	41.8	41.8	41.8	41.8	42.9	42.9	42.9	44.1
47.5°	40.7	40.7	40.7	40.7	39.5	39.5	39.5	40.7	40.7	40.7	40.7
50°	38.4	37.3	37.3	37.3	37.3	37.3	37.3	38.4	38.4	38.4	38.4
52.5°	36.2	36.2	36.2	36.2	36.2	36.2	36.2	36.2	36.2	36.2	36.2
55°	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0
57.5°	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.9
60°	31.6	31.6	31.6	31.6	31.6	31.6	31.6	32.8	32.8	32.8	32.8
62.5°	30.5	30.5	30.5	30.5	30.5	30.5	30.5	30.5	30.5	31.6	31.6
65°	29.4	29.4	29.4	29.4	28.2	28.2	28.2	28.2	28.2	28.2	28.2
67.5°	28.2	28.2	28.2	28.2	27.1	27.1	27.1	27.1	26.0	26.0	26.0
70°	27.1	27.1	27.1	26.0	26.0	24.9	24.9	24.9	23.7	23.7	23.7
72.5°	24.9	24.9	24.9	23.7	23.7	22.6	22.6	21.5	21.5	20.3	20.3
75°	22.6	22.6	21.5	21.5	20.3	19.2	19.2	19.2	18.1	18.1	18.1
77.5°	19.2	19.2	18.1	18.1	16.9	15.8	15.8	15.8	14.7	14.7	14.7
80°	15.8	14.7	14.7	13.6	13.6	12.4	12.4	12.4	11.3	11.3	11.3
82.5°	11.3	11.3	11.3	10.2	10.2	9.0	9.0	9.0	9.0	9.0	9.0
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	5.6	5.6	5.6
87.5°	3.4	3.4	3.4	3.4	2.3	2.3	2.3	2.3	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	463.2	460.9	458.7	459.8	460.9	460.9	462.1	465.4	470.0	473.3	476.7
5°	353.6	355.9	358.1	357.0	354.7	353.6	351.3	353.6	355.9	357.0	359.2
7.5°	244.0	245.1	246.3	247.4	247.4	248.5	248.5	250.8	253.1	254.2	256.4
10°	170.6	170.6	170.6	172.8	174.0	176.2	177.4	178.5	179.6	180.8	181.9
12.5°	126.5	126.5	126.5	128.8	129.9	132.2	133.3	134.4	135.6	135.6	136.7
15°	101.7	102.8	102.8	103.9	105.1	105.1	106.2	107.3	108.5	108.5	109.6
17.5°	88.1	88.1	88.1	88.1	89.2	89.2	89.2	89.2	90.4	90.4	90.4
20°	81.3	81.3	81.3	81.3	81.3	80.2	80.2	80.2	80.2	80.2	80.2
22.5°	75.7	74.6	74.6	74.6	74.6	74.6	74.6	74.6	74.6	73.4	73.4
25°	70.0	70.0	70.0	70.0	70.0	70.0	70.0	70.0	68.9	68.9	67.8
27.5°	66.7	66.7	66.7	66.7	66.7	65.5	65.5	65.5	65.5	64.4	64.4
30°	63.3	62.1	62.1	62.1	62.1	61.0	61.0	62.1	62.1	63.3	63.3
32.5°	58.7	57.6	57.6	57.6	57.6	57.6	57.6	57.6	58.7	58.7	58.7
35°	55.4	55.4	55.4	55.4	54.2	54.2	53.1	53.1	54.2	54.2	54.2
37.5°	50.8	50.8	50.8	50.8	50.8	49.7	49.7	49.7	49.7	48.6	48.6
40°	49.7	49.7	49.7	49.7	49.7	48.6	48.6	47.4	47.4	46.3	45.2
42.5°	46.3	46.3	46.3	46.3	45.2	45.2	44.1	44.1	44.1	42.9	42.9
45°	44.1	45.2	45.2	44.1	44.1	42.9	41.8	41.8	41.8	40.7	40.7
47.5°	41.8	41.8	41.8	41.8	40.7	40.7	39.5	39.5	39.5	38.4	38.4
50°	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4	37.3	37.3	36.2
52.5°	37.3	37.3	37.3	37.3	37.3	36.2	36.2	36.2	36.2	35.0	35.0
55°	36.2	36.2	36.2	36.2	36.2	35.0	35.0	35.0	35.0	33.9	33.9
57.5°	35.0	35.0	36.2	35.0	35.0	35.0	35.0	33.9	33.9	33.9	33.9
60°	33.9	33.9	33.9	33.9	32.8	32.8	31.6	31.6	31.6	31.6	31.6
62.5°	31.6	31.6	31.6	30.5	30.5	30.5	30.5	30.5	30.5	30.5	30.5
65°	29.4	29.4	29.4	29.4	29.4	28.2	28.2	28.2	28.2	28.2	28.2
67.5°	26.0	26.0	26.0	26.0	26.0	26.0	26.0	26.0	27.1	27.1	27.1
70°	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7	24.9	24.9	24.9
72.5°	21.5	21.5	21.5	21.5	21.5	20.3	20.3	20.3	21.5	21.5	21.5
75°	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1
77.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	15.8	15.8	15.8
80°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	12.4	12.4	12.4
82.5°	9.0	7.9	7.9	7.9	9.0	9.0	9.0	9.0	9.0	9.0	9.0
85°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6
87.5°	2.3	1.1	1.1	1.1	2.3	2.3	2.3	2.3	2.3	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	476.7	477.9	477.9	477.9	477.9	476.7	476.7	475.6	476.7	477.9	483.5
5°	359.2	359.2	359.2	359.2	361.5	362.6	364.9	366.0	368.3	369.4	369.4
7.5°	256.4	256.4	256.4	256.4	258.7	259.8	262.1	263.2	261.0	258.7	262.1
10°	184.1	187.5	189.8	192.1	193.2	195.4	196.6	197.7	202.2	207.9	210.1
12.5°	140.1	143.5	145.7	149.1	151.4	153.6	155.9	158.2	161.5	166.1	168.3
15°	110.7	110.7	111.8	111.8	113.0	115.2	116.4	117.5	118.6	119.7	122.0
17.5°	90.4	90.4	89.2	89.2	89.2	89.2	88.1	88.1	89.2	89.2	90.4
20°	80.2	79.1	79.1	77.9	77.9	77.9	77.9	77.9	79.1	79.1	80.2
22.5°	73.4	73.4	72.3	72.3	72.3	73.4	73.4	73.4	73.4	73.4	73.4
25°	67.8	67.8	67.8	67.8	67.8	67.8	67.8	67.8	67.8	66.7	67.8
27.5°	64.4	65.5	65.5	65.5	65.5	65.5	65.5	65.5	65.5	64.4	64.4
30°	63.3	63.3	63.3	63.3	64.4	64.4	65.5	65.5	64.4	63.3	63.3
32.5°	59.9	59.9	61.0	61.0	61.0	62.1	62.1	62.1	62.1	62.1	63.3
35°	54.2	54.2	53.1	53.1	53.1	53.1	53.1	53.1	53.1	53.1	52.0
37.5°	48.6	47.4	47.4	46.3	46.3	47.4	47.4	47.4	47.4	47.4	47.4
40°	45.2	45.2	45.2	45.2	45.2	45.2	45.2	45.2	45.2	45.2	45.2
42.5°	42.9	42.9	41.8	41.8	41.8	41.8	41.8	41.8	41.8	41.8	42.9
45°	40.7	40.7	40.7	40.7	40.7	40.7	40.7	40.7	40.7	40.7	41.8
47.5°	38.4	38.4	38.4	38.4	38.4	39.5	39.5	39.5	39.5	39.5	39.5
50°	36.2	37.3	37.3	37.3	37.3	37.3	37.3	37.3	38.4	38.4	38.4
52.5°	35.0	36.2	36.2	36.2	36.2	36.2	36.2	36.2	37.3	37.3	37.3
55°	33.9	35.0	35.0	35.0	35.0	35.0	35.0	35.0	36.2	36.2	37.3
57.5°	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.9	35.0	35.0	35.0
60°	31.6	31.6	31.6	31.6	31.6	32.8	32.8	32.8	33.9	33.9	35.0
62.5°	30.5	30.5	30.5	30.5	30.5	30.5	30.5	31.6	31.6	32.8	32.8
65°	28.2	29.4	29.4	29.4	29.4	30.5	30.5	30.5	31.6	31.6	32.8
67.5°	27.1	27.1	27.1	27.1	27.1	28.2	28.2	28.2	29.4	30.5	31.6
70°	24.9	26.0	26.0	26.0	27.1	27.1	28.2	28.2	29.4	29.4	30.5
72.5°	22.6	22.6	23.7	23.7	23.7	24.9	24.9	24.9	26.0	26.0	27.1
75°	19.2	19.2	20.3	20.3	21.5	21.5	22.6	22.6	23.7	23.7	24.9
77.5°	15.8	16.9	16.9	16.9	18.1	18.1	19.2	19.2	20.3	20.3	21.5
80°	12.4	13.6	13.6	13.6	14.7	14.7	15.8	15.8	16.9	16.9	18.1
82.5°	9.0	10.2	10.2	10.2	10.2	11.3	11.3	11.3	11.3	10.2	11.3
85°	5.6	5.6	5.6	5.6	5.6	5.6	4.5	4.5	4.5	3.4	4.5
87.5°	1.1	1.1	1.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	490.3	491.4	493.7	494.8	495.9	498.2	500.5	501.6	503.8	506.1	508.4
5°	369.4	372.8	376.2	379.6	383.0	384.1	385.2	386.4	387.5	392.0	396.5
7.5°	266.6	270.0	274.5	277.9	281.3	284.7	289.2	292.6	296.0	298.2	301.6
10°	213.5	218.0	222.6	227.1	231.6	237.2	241.8	247.4	251.9	256.4	262.1
12.5°	171.7	177.4	183.0	188.7	194.3	200.0	205.6	210.1	215.8	220.3	225.9
15°	123.1	127.7	132.2	136.7	141.2	146.9	152.5	158.2	163.8	170.6	178.5
17.5°	90.4	92.6	94.9	96.0	98.3	102.8	106.2	110.7	114.1	120.9	128.8
20°	80.2	81.3	81.3	82.5	82.5	84.7	85.9	88.1	89.2	92.6	96.0
22.5°	73.4	73.4	74.6	74.6	74.6	75.7	77.9	79.1	80.2	81.3	83.6
25°	68.9	68.9	70.0	70.0	70.0	71.2	71.2	72.3	72.3	74.6	75.7
27.5°	64.4	64.4	65.5	65.5	65.5	66.7	66.7	67.8	67.8	68.9	71.2
30°	63.3	64.4	64.4	65.5	65.5	66.7	67.8	67.8	68.9	71.2	72.3
32.5°	64.4	64.4	65.5	65.5	65.5	65.5	65.5	65.5	65.5	65.5	66.7
35°	50.8	50.8	52.0	52.0	52.0	53.1	53.1	54.2	54.2	55.4	56.5
37.5°	47.4	48.6	48.6	49.7	49.7	49.7	50.8	50.8	50.8	52.0	54.2
40°	45.2	46.3	46.3	47.4	47.4	47.4	48.6	48.6	49.7	49.7	50.8
42.5°	42.9	44.1	44.1	45.2	45.2	46.3	46.3	47.4	47.4	48.6	49.7
45°	41.8	41.8	42.9	42.9	42.9	44.1	45.2	45.2	46.3	47.4	48.6
47.5°	39.5	40.7	40.7	41.8	41.8	42.9	44.1	44.1	45.2	46.3	47.4
50°	38.4	39.5	40.7	40.7	41.8	42.9	44.1	44.1	45.2	47.4	49.7
52.5°	37.3	38.4	39.5	39.5	40.7	41.8	44.1	45.2	46.3	48.6	52.0
55°	37.3	38.4	39.5	39.5	40.7	41.8	44.1	45.2	46.3	48.6	50.8
57.5°	36.2	36.2	37.3	38.4	39.5	41.8	44.1	45.2	47.4	48.6	50.8
60°	35.0	36.2	37.3	38.4	39.5	41.8	45.2	47.4	49.7	48.6	48.6
62.5°	33.9	35.0	36.2	37.3	38.4	41.8	45.2	48.6	53.1	49.7	47.4
65°	32.8	33.9	36.2	37.3	38.4	40.7	42.9	44.1	46.3	45.2	42.9
67.5°	31.6	32.8	33.9	35.0	36.2	37.3	38.4	38.4	39.5	39.5	38.4
70°	30.5	31.6	32.8	33.9	35.0	36.2	36.2	37.3	37.3	37.3	36.2
72.5°	28.2	29.4	30.5	31.6	32.8	32.8	33.9	33.9	33.9	33.9	33.9
75°	26.0	27.1	28.2	28.2	29.4	29.4	30.5	30.5	30.5	30.5	30.5
77.5°	21.5	22.6	23.7	24.9	26.0	26.0	27.1	27.1	27.1	27.1	26.0
80°	18.1	19.2	20.3	20.3	21.5	21.5	21.5	21.5	21.5	21.5	20.3
82.5°	12.4	13.6	14.7	14.7	15.8	15.8	15.8	15.8	15.8	15.8	14.7
85°	4.5	5.6	6.8	6.8	7.9	7.9	7.9	6.8	6.8	6.8	6.8
87.5°	0.0	1.1	1.1	2.3	2.3	2.3	2.3	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	510.6	512.9	516.3	519.7	521.9	525.3	531.0	535.5	541.1	545.6	549.0
5°	399.9	404.4	411.2	419.1	425.9	432.7	438.3	444.0	449.6	455.3	463.2
7.5°	303.9	306.2	311.8	318.6	324.2	329.9	337.8	345.7	352.5	360.4	367.2
10°	266.6	271.1	276.8	281.3	286.9	291.5	293.7	297.1	299.4	301.6	306.2
12.5°	230.5	235.0	239.5	244.0	247.4	251.9	257.6	262.1	267.7	272.3	276.8
15°	185.3	192.1	198.8	205.6	212.4	219.2	225.9	232.7	239.5	246.3	253.1
17.5°	135.6	142.3	152.5	162.7	172.8	183.0	192.1	201.1	210.1	219.2	228.2
20°	98.3	101.7	111.8	120.9	131.0	140.1	151.4	162.7	174.0	185.3	197.7
22.5°	84.7	85.9	90.4	94.9	99.4	103.9	117.5	131.0	143.5	157.0	170.6
25°	77.9	79.1	81.3	84.7	87.0	89.2	97.2	106.2	114.1	122.0	139.0
27.5°	72.3	73.4	75.7	79.1	81.3	83.6	88.1	93.8	98.3	102.8	119.7
30°	74.6	75.7	77.9	79.1	81.3	82.5	85.9	89.2	92.6	96.0	107.3
32.5°	66.7	66.7	67.8	68.9	70.0	71.2	74.6	79.1	82.5	85.9	96.0
35°	57.6	58.7	61.0	62.1	64.4	65.5	70.0	74.6	77.9	82.5	92.6
37.5°	55.4	56.5	57.6	58.7	59.9	61.0	65.5	71.2	75.7	80.2	92.6
40°	53.1	54.2	55.4	56.5	56.5	57.6	62.1	67.8	72.3	76.8	90.4
42.5°	49.7	50.8	52.0	54.2	55.4	56.5	61.0	65.5	68.9	73.4	88.1
45°	49.7	50.8	53.1	54.2	56.5	57.6	61.0	64.4	66.7	70.0	84.7
47.5°	48.6	49.7	50.8	53.1	54.2	55.4	58.7	61.0	64.4	66.7	81.3
50°	52.0	54.2	54.2	54.2	54.2	54.2	56.5	58.7	59.9	62.1	76.8
52.5°	54.2	56.5	55.4	55.4	54.2	53.1	55.4	56.5	58.7	59.9	74.6
55°	52.0	54.2	53.1	52.0	50.8	49.7	52.0	53.1	55.4	56.5	71.2
57.5°	52.0	53.1	52.0	49.7	47.4	46.3	47.4	49.7	52.0	54.2	66.7
60°	47.4	46.3	46.3	45.2	45.2	44.1	46.3	48.6	49.7	52.0	64.4
62.5°	44.1	41.8	41.8	41.8	41.8	42.9	44.1	46.3	47.4	49.7	61.0
65°	41.8	39.5	39.5	39.5	39.5	39.5	41.8	42.9	45.2	46.3	59.9
67.5°	38.4	37.3	37.3	37.3	37.3	37.3	39.5	41.8	42.9	45.2	58.7
70°	36.2	35.0	35.0	35.0	33.9	33.9	36.2	38.4	40.7	42.9	56.5
72.5°	32.8	32.8	32.8	31.6	31.6	30.5	32.8	36.2	38.4	40.7	55.4
75°	29.4	29.4	28.2	28.2	27.1	26.0	29.4	31.6	35.0	37.3	52.0
77.5°	26.0	24.9	24.9	23.7	23.7	22.6	24.9	27.1	29.4	31.6	42.9
80°	20.3	19.2	19.2	18.1	18.1	16.9	19.2	20.3	22.6	23.7	31.6
82.5°	14.7	13.6	13.6	12.4	12.4	11.3	12.4	14.7	15.8	16.9	20.3
85°	6.8	6.8	6.8	6.8	6.8	6.8	7.9	9.0	9.0	10.2	12.4
87.5°	1.1	1.1	1.1	1.1	1.1	1.1	2.3	3.4	3.4	4.5	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3	560.3
2.5°	552.4	555.8	559.2	562.6	566.0	570.5	573.9	576.2	578.4	579.5	581.8
5°	470.0	477.9	485.8	493.7	500.5	508.4	515.1	524.2	532.1	541.1	549.0
7.5°	372.8	379.6	385.2	394.3	403.3	413.5	422.5	436.1	448.5	462.1	474.5
10°	310.7	315.2	319.7	327.6	335.5	343.4	351.3	366.0	380.7	394.3	409.0
12.5°	281.3	286.9	291.5	297.1	302.8	308.4	314.1	327.6	342.3	355.9	369.4
15°	259.8	267.7	274.5	282.4	290.3	298.2	306.2	322.0	336.7	352.5	367.2
17.5°	236.1	245.1	254.2	267.7	281.3	294.9	308.4	329.9	350.2	371.7	392.0
20°	210.1	222.6	235.0	253.1	270.0	288.1	306.2	335.5	364.9	393.1	422.5
22.5°	183.0	196.6	209.0	233.8	257.6	282.4	307.3	342.3	378.5	413.5	448.5
25°	155.9	172.8	189.8	223.7	257.6	291.5	325.4	370.5	415.7	460.9	506.1
27.5°	136.7	153.6	170.6	213.5	256.4	299.4	342.3	402.2	462.1	521.9	581.8
30°	118.6	131.0	142.3	196.6	250.8	305.0	359.2	429.3	498.2	568.2	637.2
32.5°	105.1	115.2	125.4	186.4	247.4	308.4	369.4	447.4	525.3	602.1	680.1
35°	102.8	114.1	124.3	186.4	247.4	309.5	370.5	456.4	542.3	628.1	714.0
37.5°	103.9	116.4	127.7	185.3	242.9	300.5	358.1	449.6	542.3	633.8	725.3
40°	102.8	116.4	129.9	180.8	231.6	283.6	334.4	436.1	537.7	639.4	741.1
42.5°	101.7	116.4	129.9	176.2	221.4	267.7	314.1	420.3	525.3	631.5	736.6
45°	98.3	113.0	126.5	172.8	218.0	264.4	310.7	423.6	537.7	650.7	763.7
47.5°	94.9	109.6	123.1	171.7	220.3	268.9	317.4	446.2	575.0	702.7	831.5
50°	91.5	107.3	122.0	179.6	236.1	293.7	351.3	485.8	621.3	755.8	890.2
52.5°	88.1	102.8	117.5	187.5	257.6	327.6	397.7	535.5	673.3	810.0	947.8
55°	84.7	99.4	113.0	193.2	273.4	354.7	434.9	581.8	729.8	876.7	1023.5
57.5°	79.1	92.6	105.1	197.7	290.3	383.0	476.7	637.2	797.6	958.0	1118.4
60°	76.8	89.2	101.7	200.0	297.1	395.4	492.6	665.4	838.2	1010.0	1182.8
62.5°	72.3	84.7	96.0	192.1	286.9	383.0	479.0	646.2	814.5	982.8	1151.2
65°	72.3	85.9	98.3	180.8	263.2	345.7	428.2	579.5	730.9	881.2	1032.6
67.5°	71.2	84.7	97.2	162.7	228.2	294.9	360.4	489.2	617.9	746.7	875.5
70°	70.0	83.6	97.2	151.4	205.6	259.8	314.1	412.3	510.6	607.8	706.1
72.5°	70.0	85.9	100.5	142.3	183.0	224.8	265.5	324.2	381.8	440.6	498.2
75°	65.5	80.2	93.8	124.3	153.6	184.1	213.5	248.5	283.6	318.6	353.6
77.5°	54.2	66.7	77.9	98.3	117.5	137.8	157.0	178.5	200.0	221.4	242.9
80°	38.4	46.3	53.1	63.3	73.4	84.7	94.9	114.1	133.3	152.5	171.7
82.5°	23.7	28.2	31.6	38.4	44.1	50.8	57.6	73.4	88.1	103.9	118.6
85°	13.6	15.8	18.1	22.6	26.0	30.5	35.0	45.2	54.2	64.4	73.4
87.5°	5.6	6.8	6.8	10.2	12.4	15.8	18.1	18.1	19.2	19.2	19.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P680431
 CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	560.3	560.3
2.5°	589.7	596.5
5°	553.6	556.9
7.5°	484.6	493.7
10°	420.3	430.4
12.5°	385.2	401.0
15°	384.1	401.0
17.5°	411.2	430.4
20°	444.0	464.3
22.5°	485.8	521.9
25°	543.4	579.5
27.5°	622.5	663.1
30°	671.0	703.8
32.5°	716.2	751.3
35°	749.0	782.9
37.5°	759.2	791.9
40°	784.0	826.9
42.5°	795.3	854.1
45°	826.9	890.2
47.5°	882.3	933.1
50°	920.7	950.1
52.5°	967.0	986.2
55°	1038.2	1051.8
57.5°	1150.0	1182.8
60°	1240.4	1296.9
62.5°	1231.4	1312.7
65°	1154.6	1276.6
67.5°	1004.3	1132.0
70°	810.0	913.9
72.5°	598.7	698.2
75°	411.2	467.7
77.5°	277.9	311.8
80°	198.8	224.8
82.5°	127.7	136.7
85°	67.8	62.1
87.5°	14.7	9.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P680431
CATALOG NUMBER: CCP-SA-2-AMB-U-SLL

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)