

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671785

Luminaire Tested: **CCP-SA-2B-722-U-SLR**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P671785  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2B-722-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR distribution lens  
Light Source: (32) 2200K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4221.7 lumens  
Efficiency: N/A  
Efficacy: 91.8 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2

Input Watts (W): 46  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 6 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671785  
CATALOG NUMBER: CCP-SA-2B-722-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	868.6	0.0	868.6
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	3353.0	0.0	3353.0
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	4221.7	0.0	4221.7
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.8	2.5
10°-20°	221.2	5.2
20°-30°	323.6	7.7
30°-40°	455.9	10.8
40°-50°	626.4	14.8
50°-60°	853.8	20.2
60°-70°	934.5	22.1
70°-80°	539.7	12.8
80°-90°	161.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4221.7	100.0
0°-180°	4221.7	100.0



REPORT NUMBER: P671785


CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	433.6	10.3			
FM (30°-60°)	1540.6	36.5			
FH (60°-80°)	1241.4	29.4			G1/1800
FVH (80°-90°)	137.4	3.3			G2/225
BL (0°-30°)	215.9	5.1	B1/500		
BM (30°-60°)	395.5	9.4	B1/1000		
BH (60°-80°)	232.8	5.5	B1/500		G1/500
BVH (80°-90°)	24.4	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**

Type IV Short





REPORT NUMBER: P671785

CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1391.2	1383.7	1378.1	1372.5	1365.0	1359.4	1351.9	1344.4	1335.0	1327.5	1318.2
5°	1310.7	1288.2	1265.7	1252.6	1237.7	1224.6	1209.6	1192.7	1175.9	1157.1	1140.3
7.5°	1222.7	1194.6	1166.5	1144.0	1119.7	1097.2	1072.9	1052.3	1031.7	1011.1	990.5
10°	1140.3	1114.1	1087.9	1059.8	1029.8	1001.7	971.8	943.7	915.6	887.5	859.4
12.5°	1086.0	1054.2	1024.2	992.4	962.4	930.6	898.8	872.5	846.3	818.2	792.0
15°	1061.7	1031.7	1003.6	971.8	939.9	908.1	876.3	846.3	818.2	788.3	758.3
17.5°	1119.7	1076.6	1033.6	992.4	951.2	910.0	868.8	831.3	793.9	756.5	719.0
20°	1194.6	1140.3	1087.9	1037.3	984.9	934.3	881.9	829.5	777.0	724.6	672.2
22.5°	1290.1	1228.3	1168.4	1102.8	1035.4	969.9	902.5	837.0	771.4	704.0	638.5
25°	1460.5	1387.5	1314.4	1220.8	1125.3	1031.7	936.2	850.1	765.8	679.7	593.6
27.5°	1606.5	1507.3	1409.9	1297.6	1185.2	1072.9	960.5	861.3	763.9	664.7	565.5
30°	1692.7	1595.3	1497.9	1361.2	1226.4	1089.7	953.1	842.6	734.0	623.5	513.0
32.5°	1771.3	1662.7	1554.1	1404.3	1252.6	1102.8	951.2	829.5	709.6	587.9	466.2
35°	1879.9	1760.1	1642.1	1468.0	1293.8	1119.7	945.6	820.1	692.8	567.3	440.0
37.5°	1996.0	1848.1	1702.0	1509.2	1316.3	1123.4	930.6	807.0	683.4	559.9	436.3
40°	2123.3	1943.6	1765.7	1552.2	1340.6	1127.2	913.7	790.2	666.6	541.1	417.5
42.5°	2205.7	2011.0	1816.2	1585.9	1357.5	1127.2	896.9	775.2	653.5	529.9	408.2
45°	2252.5	2063.4	1876.2	1627.1	1378.1	1129.1	880.0	760.2	640.4	518.7	398.8
47.5°	2273.1	2097.1	1921.1	1659.0	1398.7	1136.6	874.4	752.7	629.1	507.4	383.8
50°	2327.4	2172.0	2016.6	1735.7	1456.7	1175.9	895.0	763.9	634.7	503.7	372.6
52.5°	2359.2	2226.3	2093.4	1805.0	1516.7	1228.3	939.9	793.9	647.9	501.8	355.8
55°	2475.3	2348.0	2220.7	1913.6	1604.7	1297.6	988.6	827.6	666.6	503.7	342.7
57.5°	2623.2	2488.4	2355.5	2024.1	1692.7	1361.2	1029.8	857.6	683.4	511.2	337.0
60°	2726.2	2595.2	2466.0	2113.9	1760.1	1408.1	1054.2	874.4	694.7	513.0	333.3
62.5°	2737.5	2568.9	2402.3	2059.6	1717.0	1372.5	1029.8	855.7	681.6	505.6	331.4
65°	2666.3	2469.7	2273.1	1945.4	1617.8	1290.1	962.4	803.3	644.1	483.1	323.9
67.5°	2524.0	2293.7	2063.4	1763.8	1464.2	1164.6	865.1	728.4	593.6	456.9	320.2
70°	2192.6	1990.4	1790.0	1529.8	1271.4	1011.1	750.8	638.5	528.0	415.7	303.3
72.5°	1840.6	1651.5	1464.2	1252.6	1042.9	831.3	619.8	535.5	451.3	365.1	280.9
75°	1409.9	1267.6	1127.2	969.9	812.6	653.5	496.2	434.4	372.6	310.8	249.0
77.5°	990.5	913.7	838.8	720.9	602.9	485.0	367.0	325.8	284.6	243.4	202.2
80°	672.2	629.1	587.9	503.7	419.4	333.3	249.0	222.8	194.7	168.5	140.4
82.5°	417.5	415.7	411.9	353.9	295.8	237.8	179.8	157.3	136.7	114.2	91.7
85°	191.0	222.8	252.8	220.9	189.1	157.3	125.5	110.5	95.5	78.6	63.7
87.5°	59.9	73.0	84.3	80.5	74.9	71.2	65.5	56.2	46.8	37.4	28.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1310.7	1305.1	1297.6	1290.1	1280.7	1273.2	1263.9	1254.5	1252.6	1248.9	1247.0
5°	1129.1	1117.8	1104.7	1093.5	1082.3	1069.1	1057.9	1044.8	1035.4	1024.2	1014.8
7.5°	969.9	951.2	930.6	910.0	891.3	872.5	851.9	833.2	823.9	814.5	805.1
10°	842.6	823.9	807.0	788.3	775.2	763.9	750.8	737.7	726.5	715.3	704.0
12.5°	778.9	765.8	752.7	739.6	724.6	711.5	696.5	681.6	668.4	657.2	644.1
15°	739.6	720.9	700.3	681.6	661.0	642.2	621.6	601.0	586.1	573.0	558.0
17.5°	692.8	664.7	638.5	610.4	587.9	565.5	541.1	518.7	501.8	483.1	466.2
20°	640.4	608.5	574.8	543.0	516.8	492.4	466.2	440.0	421.3	400.7	382.0
22.5°	595.4	554.2	511.2	468.1	440.0	411.9	382.0	353.9	337.0	318.3	301.5
25°	546.7	501.8	455.0	408.2	380.1	350.1	322.1	292.1	279.0	267.8	254.6
27.5°	520.5	475.6	428.8	383.8	357.6	329.5	303.3	275.2	265.9	254.6	245.3
30°	468.1	425.0	380.1	335.2	316.4	299.6	280.9	262.1	258.4	256.5	252.8
32.5°	421.3	376.4	331.4	286.5	269.6	252.8	235.9	219.1	217.2	213.5	211.6
35°	397.0	353.9	308.9	265.9	250.9	234.1	219.1	202.2	198.5	192.9	189.1
37.5°	391.3	346.4	299.6	254.6	239.7	224.7	207.8	192.9	189.1	185.4	181.6
40°	376.4	333.3	292.1	249.0	234.1	219.1	202.2	187.2	183.5	179.8	176.0
42.5°	365.1	323.9	280.9	237.8	224.7	211.6	196.6	183.5	179.8	176.0	170.4
45°	355.8	312.7	267.8	224.7	215.3	206.0	194.7	185.4	181.6	176.0	172.3
47.5°	340.8	299.6	256.5	213.5	204.1	196.6	187.2	177.9	174.1	170.4	166.6
50°	329.5	286.5	243.4	200.3	192.9	185.4	177.9	170.4	170.4	172.3	172.3
52.5°	314.6	273.4	232.2	191.0	183.5	176.0	168.5	161.0	162.9	164.8	166.6
55°	301.5	262.1	220.9	179.8	172.3	164.8	155.4	147.9	149.8	151.7	153.5
57.5°	295.8	254.6	213.5	172.3	164.8	155.4	147.9	138.6	138.6	138.6	138.6
60°	292.1	249.0	207.8	164.8	155.4	147.9	138.6	129.2	127.3	127.3	125.5
62.5°	290.2	247.2	206.0	162.9	151.7	142.3	131.1	119.8	118.0	116.1	114.2
65°	282.7	243.4	202.2	161.0	147.9	136.7	123.6	110.5	108.6	108.6	106.7
67.5°	280.9	239.7	200.3	159.2	146.0	131.1	118.0	103.0	101.1	99.2	97.4
70°	265.9	230.3	192.9	155.4	140.4	127.3	112.3	97.4	95.5	91.7	89.9
72.5°	247.2	215.3	181.6	147.9	132.9	118.0	103.0	88.0	86.1	84.3	80.5
75°	219.1	189.1	159.2	129.2	116.1	104.9	91.7	78.6	76.8	74.9	71.2
77.5°	179.8	155.4	132.9	108.6	99.2	89.9	80.5	71.2	69.3	67.4	63.7
80°	127.3	112.3	99.2	84.3	78.6	71.2	65.5	58.0	58.0	56.2	56.2
82.5°	84.3	76.8	69.3	61.8	58.0	54.3	50.6	46.8	46.8	44.9	44.9
85°	59.9	56.2	50.6	46.8	44.9	41.2	39.3	35.6	35.6	35.6	35.6
87.5°	28.1	28.1	26.2	26.2	24.3	24.3	22.5	20.6	20.6	20.6	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785

CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1243.3	1237.7	1232.0	1224.6	1218.9	1211.4	1202.1	1194.6	1185.2	1185.2	1183.4
5°	1003.6	998.0	992.4	984.9	979.3	971.8	966.2	958.7	951.2	951.2	949.3
7.5°	795.8	784.5	773.3	760.2	749.0	741.5	734.0	724.6	717.1	711.5	705.9
10°	692.8	681.6	668.4	657.2	644.1	634.7	625.4	614.2	604.8	597.3	589.8
12.5°	631.0	617.9	604.8	591.7	578.6	565.5	554.2	541.1	528.0	518.7	509.3
15°	543.0	529.9	516.8	503.7	490.6	475.6	460.6	443.8	428.8	421.3	415.7
17.5°	447.5	434.4	419.4	406.3	391.3	380.1	368.9	357.6	346.4	338.9	333.3
20°	361.4	346.4	331.4	316.4	301.5	294.0	286.5	279.0	271.5	265.9	262.1
22.5°	282.7	273.4	265.9	256.5	247.2	241.5	237.8	232.2	226.6	226.6	226.6
25°	241.5	235.9	232.2	226.6	220.9	219.1	217.2	213.5	211.6	209.7	209.7
27.5°	234.1	228.4	222.8	217.2	211.6	209.7	207.8	204.1	202.2	202.2	202.2
30°	249.0	247.2	245.3	243.4	241.5	237.8	232.2	228.4	222.8	219.1	215.3
32.5°	207.8	206.0	206.0	204.1	202.2	206.0	207.8	211.6	213.5	215.3	217.2
35°	183.5	179.8	176.0	172.3	168.5	166.6	164.8	162.9	161.0	161.0	159.2
37.5°	177.9	174.1	170.4	166.6	162.9	161.0	159.2	157.3	155.4	155.4	153.5
40°	172.3	168.5	166.6	162.9	159.2	157.3	155.4	151.7	149.8	147.9	147.9
42.5°	166.6	164.8	161.0	159.2	155.4	153.5	151.7	147.9	146.0	144.2	142.3
45°	166.6	162.9	159.2	155.4	151.7	149.8	146.0	144.2	140.4	140.4	138.6
47.5°	162.9	159.2	155.4	151.7	147.9	146.0	142.3	140.4	136.7	134.8	132.9
50°	172.3	166.6	159.2	153.5	146.0	144.2	140.4	138.6	134.8	132.9	131.1
52.5°	168.5	162.9	155.4	149.8	142.3	138.6	136.7	132.9	129.2	127.3	125.5
55°	155.4	149.8	146.0	140.4	134.8	131.1	127.3	123.6	119.8	118.0	118.0
57.5°	138.6	136.7	134.8	132.9	131.1	127.3	123.6	118.0	114.2	112.3	110.5
60°	123.6	125.5	127.3	129.2	131.1	125.5	119.8	114.2	108.6	106.7	104.9
62.5°	112.3	116.1	119.8	121.7	125.5	119.8	114.2	108.6	103.0	101.1	99.2
65°	104.9	106.7	106.7	108.6	108.6	104.9	103.0	99.2	95.5	93.6	93.6
67.5°	95.5	95.5	95.5	93.6	93.6	91.7	91.7	89.9	88.0	86.1	86.1
70°	86.1	86.1	86.1	84.3	84.3	82.4	82.4	80.5	78.6	78.6	76.8
72.5°	78.6	78.6	76.8	76.8	74.9	74.9	74.9	73.0	73.0	71.2	71.2
75°	69.3	69.3	67.4	67.4	65.5	65.5	65.5	63.7	63.7	63.7	61.8
77.5°	61.8	61.8	59.9	59.9	58.0	58.0	58.0	56.2	56.2	54.3	54.3
80°	54.3	54.3	52.4	52.4	50.6	50.6	48.7	48.7	46.8	46.8	44.9
82.5°	43.1	43.1	43.1	43.1	43.1	41.2	41.2	39.3	37.4	37.4	35.6
85°	35.6	35.6	35.6	33.7	33.7	33.7	31.8	31.8	30.0	28.1	28.1
87.5°	20.6	20.6	20.6	18.7	18.7	18.7	18.7	18.7	18.7	18.7	16.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1183.4	1181.5	1174.0	1166.5	1174.0	1181.5	1181.5	1181.5	1179.6	1179.6	1179.6
5°	949.3	947.4	943.7	939.9	939.9	938.1	941.8	945.6	949.3	953.1	956.8
7.5°	698.4	692.8	687.2	681.6	685.3	687.2	692.8	696.5	702.2	705.9	715.3
10°	582.3	574.8	569.2	563.6	559.9	556.1	552.4	550.5	546.7	543.0	546.7
12.5°	498.1	488.7	479.3	468.1	466.2	464.4	460.6	456.9	453.1	449.4	447.5
15°	408.2	400.7	397.0	391.3	383.8	376.4	372.6	370.7	367.0	363.2	361.4
17.5°	325.8	318.3	312.7	307.1	305.2	301.5	301.5	301.5	301.5	301.5	301.5
20°	256.5	250.9	250.9	249.0	249.0	247.2	249.0	250.9	250.9	252.8	254.6
22.5°	224.7	224.7	222.8	220.9	222.8	222.8	224.7	226.6	228.4	230.3	232.2
25°	207.8	206.0	207.8	209.7	209.7	209.7	211.6	211.6	213.5	213.5	213.5
27.5°	200.3	200.3	202.2	202.2	204.1	204.1	204.1	202.2	202.2	200.3	200.3
30°	211.6	207.8	207.8	207.8	206.0	204.1	202.2	202.2	200.3	198.5	196.6
32.5°	219.1	220.9	219.1	215.3	213.5	209.7	207.8	204.1	202.2	198.5	194.7
35°	159.2	157.3	161.0	162.9	164.8	166.6	168.5	170.4	170.4	172.3	172.3
37.5°	153.5	151.7	151.7	149.8	149.8	149.8	149.8	149.8	147.9	147.9	149.8
40°	146.0	144.2	144.2	142.3	142.3	140.4	140.4	140.4	140.4	140.4	140.4
42.5°	140.4	138.6	138.6	138.6	138.6	136.7	136.7	134.8	134.8	132.9	132.9
45°	138.6	136.7	134.8	132.9	132.9	131.1	131.1	131.1	129.2	129.2	129.2
47.5°	131.1	129.2	129.2	127.3	127.3	125.5	125.5	125.5	123.6	123.6	123.6
50°	127.3	125.5	125.5	123.6	123.6	121.7	121.7	121.7	119.8	119.8	119.8
52.5°	121.7	119.8	119.8	119.8	118.0	116.1	116.1	116.1	114.2	114.2	114.2
55°	116.1	114.2	114.2	114.2	112.3	110.5	110.5	110.5	108.6	108.6	108.6
57.5°	108.6	106.7	106.7	104.9	104.9	104.9	104.9	104.9	103.0	103.0	103.0
60°	103.0	101.1	101.1	99.2	99.2	97.4	97.4	97.4	97.4	97.4	97.4
62.5°	97.4	95.5	93.6	91.7	93.6	93.6	93.6	93.6	91.7	91.7	91.7
65°	91.7	89.9	88.0	86.1	86.1	86.1	86.1	86.1	86.1	86.1	86.1
67.5°	84.3	82.4	80.5	78.6	80.5	80.5	80.5	80.5	80.5	80.5	80.5
70°	76.8	74.9	74.9	73.0	73.0	71.2	71.2	73.0	73.0	73.0	73.0
72.5°	69.3	67.4	67.4	65.5	65.5	65.5	65.5	65.5	65.5	65.5	65.5
75°	61.8	59.9	59.9	58.0	58.0	58.0	58.0	58.0	58.0	58.0	58.0
77.5°	52.4	50.6	50.6	50.6	50.6	50.6	50.6	52.4	52.4	52.4	52.4
80°	44.9	43.1	43.1	43.1	43.1	43.1	43.1	43.1	43.1	43.1	43.1
82.5°	35.6	33.7	33.7	33.7	33.7	33.7	33.7	33.7	33.7	33.7	33.7
85°	26.2	24.3	24.3	24.3	26.2	26.2	26.2	26.2	26.2	26.2	26.2
87.5°	16.9	15.0	15.0	15.0	16.9	16.9	16.9	16.9	15.0	15.0	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1179.6	1179.6	1179.6	1177.7	1175.9	1174.0	1172.1	1177.7	1181.5	1187.1	1190.9
5°	958.7	962.4	964.3	969.9	975.5	981.1	986.8	990.5	994.2	996.1	999.9
7.5°	722.7	732.1	739.6	747.1	754.6	760.2	767.7	773.3	778.9	784.5	790.2
10°	548.6	552.4	554.2	561.7	567.3	574.8	580.4	586.1	591.7	595.4	601.0
12.5°	445.6	441.9	440.0	440.0	440.0	440.0	440.0	443.8	447.5	451.3	455.0
15°	359.5	357.6	355.8	353.9	352.0	348.3	346.4	350.1	353.9	357.6	361.4
17.5°	301.5	301.5	301.5	299.6	297.7	295.8	294.0	295.8	297.7	297.7	299.6
20°	258.4	260.3	262.1	264.0	264.0	265.9	265.9	267.8	269.6	269.6	271.5
22.5°	232.2	234.1	234.1	234.1	235.9	235.9	235.9	237.8	239.7	241.5	243.4
25°	211.6	211.6	209.7	209.7	211.6	211.6	211.6	211.6	213.5	213.5	213.5
27.5°	200.3	198.5	198.5	198.5	198.5	196.6	196.6	196.6	196.6	196.6	196.6
30°	194.7	192.9	191.0	189.1	189.1	187.2	185.4	185.4	185.4	185.4	185.4
32.5°	192.9	189.1	185.4	183.5	183.5	181.6	179.8	177.9	177.9	176.0	174.1
35°	172.3	170.4	170.4	168.5	166.6	164.8	162.9	162.9	162.9	161.0	161.0
37.5°	149.8	151.7	151.7	151.7	153.5	153.5	153.5	153.5	155.4	155.4	155.4
40°	140.4	140.4	140.4	142.3	144.2	144.2	146.0	146.0	147.9	147.9	147.9
42.5°	132.9	131.1	131.1	132.9	132.9	134.8	134.8	136.7	138.6	138.6	140.4
45°	129.2	127.3	127.3	127.3	127.3	125.5	125.5	127.3	129.2	131.1	132.9
47.5°	121.7	121.7	119.8	119.8	119.8	119.8	119.8	119.8	121.7	121.7	121.7
50°	118.0	118.0	116.1	116.1	116.1	116.1	116.1	116.1	116.1	116.1	116.1
52.5°	114.2	112.3	112.3	112.3	112.3	110.5	110.5	110.5	110.5	110.5	110.5
55°	108.6	106.7	106.7	106.7	106.7	106.7	106.7	106.7	108.6	108.6	108.6
57.5°	103.0	101.1	101.1	101.1	103.0	103.0	103.0	103.0	104.9	104.9	104.9
60°	97.4	97.4	97.4	97.4	97.4	97.4	97.4	99.2	99.2	101.1	101.1
62.5°	91.7	91.7	91.7	91.7	93.6	93.6	93.6	93.6	95.5	95.5	95.5
65°	86.1	86.1	86.1	86.1	88.0	88.0	88.0	88.0	88.0	88.0	88.0
67.5°	80.5	80.5	80.5	80.5	80.5	80.5	80.5	82.4	82.4	84.3	84.3
70°	73.0	71.2	71.2	73.0	73.0	74.9	74.9	76.8	76.8	78.6	78.6
72.5°	65.5	65.5	65.5	65.5	65.5	65.5	65.5	67.4	69.3	69.3	71.2
75°	58.0	58.0	58.0	58.0	59.9	59.9	59.9	61.8	61.8	63.7	63.7
77.5°	52.4	50.6	50.6	50.6	52.4	52.4	52.4	54.3	54.3	56.2	56.2
80°	43.1	43.1	43.1	43.1	44.9	44.9	44.9	44.9	46.8	46.8	46.8
82.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	37.4	37.4	37.4
85°	26.2	26.2	26.2	26.2	28.1	28.1	28.1	28.1	28.1	28.1	28.1
87.5°	16.9	16.9	16.9	16.9	16.9	16.9	16.9	16.9	18.7	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671785

CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1190.9	1190.9	1190.9	1190.9	1194.6	1196.5	1200.2	1202.1	1200.2	1198.3	1194.6
5°	1001.7	1003.6	1003.6	1005.5	1005.5	1005.5	1005.5	1005.5	1009.2	1013.0	1016.7
7.5°	792.0	793.9	795.8	797.6	797.6	797.6	795.8	795.8	797.6	797.6	799.5
10°	606.7	614.2	619.8	625.4	621.6	616.0	612.3	606.7	606.7	606.7	604.8
12.5°	458.7	460.6	464.4	466.2	464.4	464.4	462.5	460.6	462.5	466.2	468.1
15°	363.2	363.2	365.1	365.1	367.0	368.9	368.9	370.7	374.5	376.4	380.1
17.5°	301.5	303.3	303.3	305.2	305.2	307.1	307.1	307.1	310.8	314.6	320.2
20°	271.5	271.5	271.5	271.5	271.5	269.6	269.6	267.8	269.6	273.4	275.2
22.5°	243.4	245.3	245.3	245.3	243.4	241.5	237.8	235.9	235.9	237.8	237.8
25°	213.5	211.6	211.6	209.7	209.7	211.6	211.6	211.6	213.5	213.5	215.3
27.5°	196.6	194.7	194.7	192.9	192.9	194.7	194.7	194.7	194.7	194.7	194.7
30°	183.5	183.5	181.6	179.8	181.6	181.6	183.5	183.5	185.4	185.4	187.2
32.5°	174.1	172.3	172.3	170.4	172.3	172.3	174.1	174.1	176.0	177.9	177.9
35°	161.0	161.0	161.0	161.0	161.0	161.0	159.2	159.2	159.2	159.2	159.2
37.5°	153.5	153.5	151.7	149.8	149.8	149.8	149.8	149.8	147.9	146.0	144.2
40°	147.9	146.0	146.0	144.2	142.3	142.3	140.4	138.6	138.6	136.7	136.7
42.5°	140.4	138.6	138.6	136.7	134.8	134.8	132.9	131.1	131.1	131.1	129.2
45°	131.1	131.1	129.2	127.3	127.3	127.3	125.5	125.5	125.5	125.5	123.6
47.5°	121.7	121.7	119.8	119.8	119.8	119.8	118.0	118.0	118.0	118.0	118.0
50°	116.1	116.1	116.1	116.1	116.1	116.1	114.2	114.2	114.2	114.2	114.2
52.5°	110.5	110.5	110.5	110.5	110.5	110.5	110.5	110.5	110.5	110.5	110.5
55°	108.6	108.6	108.6	108.6	108.6	108.6	106.7	106.7	106.7	108.6	108.6
57.5°	104.9	104.9	103.0	103.0	103.0	103.0	103.0	103.0	103.0	103.0	103.0
60°	101.1	101.1	101.1	101.1	101.1	101.1	101.1	101.1	101.1	101.1	101.1
62.5°	95.5	95.5	95.5	95.5	95.5	97.4	97.4	97.4	97.4	97.4	95.5
65°	88.0	89.9	89.9	89.9	89.9	89.9	89.9	89.9	89.9	89.9	89.9
67.5°	84.3	84.3	84.3	84.3	84.3	84.3	84.3	84.3	84.3	84.3	84.3
70°	78.6	78.6	76.8	76.8	76.8	78.6	78.6	78.6	78.6	78.6	78.6
72.5°	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	73.0	73.0
75°	63.7	63.7	63.7	63.7	63.7	63.7	63.7	63.7	63.7	63.7	63.7
77.5°	56.2	56.2	54.3	54.3	54.3	56.2	56.2	56.2	56.2	58.0	58.0
80°	46.8	46.8	46.8	46.8	46.8	46.8	46.8	46.8	46.8	48.7	48.7
82.5°	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	39.3	39.3
85°	28.1	30.0	30.0	30.0	30.0	30.0	30.0	30.0	30.0	31.8	31.8
87.5°	18.7	18.7	18.7	18.7	18.7	18.7	16.9	16.9	16.9	16.9	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785

CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1192.7	1194.6	1196.5	1196.5	1198.3	1200.2	1200.2	1207.7	1215.2	1218.9	1222.7
5°	1020.5	1018.6	1018.6	1016.7	1014.8	1020.5	1026.1	1037.3	1048.5	1050.4	1054.2
7.5°	799.5	801.4	803.3	803.3	805.1	799.5	792.0	793.9	795.8	805.1	812.6
10°	604.8	606.7	608.5	608.5	610.4	608.5	604.8	610.4	616.0	623.5	632.9
12.5°	470.0	475.6	481.2	485.0	490.6	494.3	496.2	503.7	509.3	518.7	528.0
15°	383.8	387.6	391.3	395.1	398.8	402.6	406.3	413.8	421.3	432.5	443.8
17.5°	323.9	323.9	325.8	325.8	325.8	329.5	333.3	337.0	338.9	350.1	361.4
20°	277.1	275.2	273.4	271.5	269.6	273.4	275.2	277.1	279.0	286.5	292.1
22.5°	237.8	237.8	239.7	239.7	239.7	237.8	234.1	235.9	235.9	239.7	245.3
25°	215.3	215.3	215.3	213.5	213.5	215.3	217.2	217.2	215.3	217.2	219.1
27.5°	194.7	196.6	196.6	198.5	198.5	200.3	200.3	200.3	200.3	202.2	204.1
30°	187.2	187.2	189.1	189.1	189.1	191.0	192.9	192.9	192.9	194.7	198.5
32.5°	179.8	181.6	183.5	185.4	187.2	189.1	189.1	191.0	191.0	192.9	194.7
35°	159.2	157.3	157.3	155.4	153.5	153.5	153.5	153.5	151.7	153.5	153.5
37.5°	142.3	142.3	142.3	140.4	140.4	142.3	142.3	142.3	142.3	144.2	144.2
40°	134.8	134.8	134.8	134.8	134.8	134.8	134.8	136.7	136.7	138.6	140.4
42.5°	129.2	129.2	129.2	129.2	129.2	131.1	131.1	131.1	131.1	132.9	132.9
45°	123.6	123.6	123.6	123.6	123.6	123.6	123.6	125.5	125.5	127.3	129.2
47.5°	118.0	118.0	118.0	118.0	118.0	119.8	121.7	121.7	121.7	123.6	123.6
50°	114.2	114.2	114.2	114.2	114.2	116.1	116.1	118.0	118.0	119.8	121.7
52.5°	110.5	110.5	110.5	110.5	110.5	112.3	112.3	114.2	114.2	116.1	118.0
55°	108.6	108.6	108.6	106.7	106.7	108.6	108.6	110.5	110.5	112.3	112.3
57.5°	103.0	103.0	103.0	103.0	103.0	103.0	103.0	104.9	104.9	106.7	108.6
60°	101.1	101.1	99.2	99.2	97.4	99.2	99.2	101.1	101.1	103.0	103.0
62.5°	95.5	95.5	95.5	93.6	93.6	95.5	95.5	95.5	95.5	97.4	99.2
65°	89.9	89.9	89.9	88.0	88.0	89.9	89.9	89.9	89.9	91.7	93.6
67.5°	84.3	84.3	84.3	82.4	82.4	82.4	82.4	84.3	84.3	86.1	88.0
70°	78.6	78.6	78.6	76.8	76.8	76.8	74.9	76.8	78.6	80.5	80.5
72.5°	73.0	73.0	73.0	71.2	71.2	71.2	69.3	71.2	71.2	73.0	73.0
75°	63.7	63.7	63.7	63.7	63.7	63.7	61.8	61.8	61.8	63.7	63.7
77.5°	58.0	58.0	58.0	56.2	56.2	56.2	54.3	54.3	54.3	56.2	56.2
80°	48.7	48.7	48.7	46.8	46.8	46.8	44.9	44.9	44.9	46.8	46.8
82.5°	39.3	39.3	39.3	37.4	37.4	37.4	35.6	35.6	35.6	37.4	37.4
85°	31.8	31.8	31.8	31.8	31.8	31.8	30.0	30.0	30.0	31.8	33.7
87.5°	15.0	15.0	16.9	16.9	16.9	16.9	15.0	15.0	13.1	13.1	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1226.4	1230.2	1239.5	1247.0	1256.4	1263.9	1269.5	1277.0	1282.6	1288.2	1292.0
5°	1056.0	1057.9	1067.3	1076.6	1084.1	1093.5	1106.6	1119.7	1132.8	1145.9	1155.3
7.5°	822.0	829.5	840.7	853.8	865.1	876.3	889.4	904.4	917.5	930.6	943.7
10°	640.4	647.9	659.1	670.3	679.7	690.9	705.9	720.9	735.9	750.8	765.8
12.5°	537.4	546.7	559.9	573.0	584.2	597.3	616.0	632.9	651.6	668.4	687.2
15°	453.1	464.4	481.2	499.9	516.8	533.6	552.4	571.1	587.9	606.7	625.4
17.5°	372.6	383.8	398.8	415.7	430.7	445.6	468.1	488.7	511.2	531.8	552.4
20°	299.6	305.2	320.2	335.2	350.1	365.1	382.0	398.8	415.7	432.5	458.7
22.5°	249.0	252.8	260.3	265.9	273.4	279.0	295.8	312.7	327.7	344.5	368.9
25°	219.1	220.9	226.6	230.3	235.9	239.7	250.9	260.3	271.5	280.9	303.3
27.5°	204.1	206.0	207.8	209.7	211.6	213.5	220.9	228.4	234.1	241.5	262.1
30°	200.3	202.2	207.8	211.6	217.2	220.9	224.7	228.4	232.2	235.9	249.0
32.5°	196.6	198.5	198.5	196.6	196.6	194.7	198.5	200.3	204.1	206.0	217.2
35°	155.4	155.4	157.3	159.2	161.0	162.9	168.5	172.3	177.9	181.6	191.0
37.5°	146.0	146.0	147.9	151.7	153.5	155.4	159.2	162.9	166.6	170.4	179.8
40°	140.4	142.3	144.2	146.0	147.9	149.8	153.5	155.4	159.2	161.0	168.5
42.5°	134.8	134.8	136.7	140.4	142.3	144.2	147.9	149.8	153.5	155.4	162.9
45°	131.1	132.9	134.8	136.7	136.7	138.6	142.3	146.0	147.9	151.7	159.2
47.5°	125.5	125.5	129.2	131.1	134.8	136.7	140.4	142.3	146.0	147.9	155.4
50°	121.7	123.6	127.3	129.2	132.9	134.8	140.4	144.2	149.8	153.5	157.3
52.5°	118.0	119.8	123.6	125.5	129.2	131.1	138.6	146.0	151.7	159.2	159.2
55°	114.2	114.2	118.0	123.6	127.3	131.1	134.8	140.4	144.2	147.9	147.9
57.5°	108.6	110.5	114.2	119.8	123.6	127.3	131.1	134.8	136.7	140.4	138.6
60°	104.9	104.9	110.5	116.1	121.7	127.3	127.3	127.3	125.5	125.5	125.5
62.5°	99.2	101.1	108.6	118.0	125.5	132.9	127.3	121.7	116.1	110.5	112.3
65°	95.5	97.4	101.1	106.7	110.5	114.2	110.5	108.6	104.9	101.1	103.0
67.5°	88.0	89.9	91.7	91.7	93.6	93.6	93.6	93.6	93.6	93.6	95.5
70°	82.4	82.4	82.4	84.3	84.3	84.3	84.3	84.3	84.3	84.3	86.1
72.5°	74.9	74.9	74.9	74.9	74.9	74.9	74.9	74.9	74.9	74.9	76.8
75°	65.5	65.5	65.5	65.5	65.5	65.5	65.5	65.5	65.5	65.5	67.4
77.5°	58.0	58.0	58.0	58.0	58.0	58.0	58.0	58.0	56.2	56.2	58.0
80°	48.7	48.7	48.7	48.7	46.8	46.8	46.8	46.8	46.8	46.8	48.7
82.5°	39.3	39.3	39.3	39.3	37.4	37.4	37.4	37.4	35.6	35.6	37.4
85°	35.6	37.4	37.4	39.3	39.3	39.3	37.4	35.6	33.7	31.8	31.8
87.5°	15.0	15.0	15.0	15.0	13.1	13.1	13.1	13.1	13.1	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785

CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1297.6	1301.3	1305.1	1310.7	1318.2	1323.8	1329.4	1340.6	1353.8	1365.0	1376.2
5°	1164.6	1174.0	1183.4	1194.6	1205.8	1215.2	1226.4	1248.9	1271.4	1292.0	1314.4
7.5°	954.9	968.0	979.3	998.0	1014.8	1033.6	1050.4	1078.5	1104.7	1132.8	1159.0
10°	780.8	795.8	810.8	835.1	861.3	885.6	910.0	932.5	956.8	979.3	1001.7
12.5°	705.9	722.7	741.5	756.5	773.3	788.3	803.3	829.5	855.7	881.9	908.1
15°	644.1	662.8	681.6	700.3	717.1	735.9	752.7	775.2	799.5	822.0	844.5
17.5°	573.0	591.7	612.3	632.9	653.5	674.1	694.7	726.5	758.3	788.3	820.1
20°	483.1	509.3	533.6	561.7	589.8	617.9	646.0	679.7	713.4	745.2	778.9
22.5°	393.2	417.5	441.9	475.6	509.3	541.1	574.8	619.8	662.8	707.8	750.8
25°	327.7	350.1	372.6	410.1	445.6	483.1	518.7	573.0	625.4	679.7	732.1
27.5°	282.7	303.3	323.9	363.2	402.6	440.0	479.3	539.3	597.3	657.2	715.3
30°	262.1	275.2	288.4	325.8	363.2	398.8	436.3	494.3	552.4	610.4	668.4
32.5°	228.4	239.7	250.9	284.6	318.3	350.1	383.8	443.8	501.8	561.7	619.8
35°	202.2	211.6	220.9	252.8	282.7	314.6	344.5	404.4	464.4	524.3	584.2
37.5°	187.2	196.6	204.1	232.2	262.1	290.2	318.3	378.2	436.3	496.2	554.2
40°	176.0	181.6	189.1	217.2	243.4	271.5	297.7	352.0	408.2	462.5	516.8
42.5°	168.5	176.0	181.6	206.0	232.2	256.5	280.9	333.3	385.7	436.3	488.7
45°	166.6	174.1	181.6	202.2	222.8	241.5	262.1	312.7	363.2	413.8	464.4
47.5°	162.9	168.5	176.0	192.9	207.8	224.7	239.7	290.2	340.8	389.5	440.0
50°	161.0	162.9	166.6	181.6	196.6	211.6	226.6	277.1	327.7	378.2	428.8
52.5°	159.2	159.2	159.2	172.3	185.4	196.6	209.7	260.3	312.7	363.2	413.8
55°	147.9	146.0	146.0	159.2	170.4	183.5	194.7	245.3	295.8	344.5	395.1
57.5°	136.7	134.8	132.9	144.2	155.4	166.6	177.9	228.4	280.9	331.4	382.0
60°	125.5	123.6	123.6	134.8	144.2	155.4	164.8	217.2	267.8	320.2	370.7
62.5°	112.3	114.2	114.2	123.6	134.8	144.2	153.5	206.0	260.3	312.7	365.1
65°	103.0	104.9	104.9	116.1	127.3	138.6	149.8	200.3	252.8	303.3	353.9
67.5°	95.5	97.4	97.4	110.5	121.7	134.8	146.0	191.0	237.8	282.7	327.7
70°	88.0	88.0	89.9	103.0	116.1	129.2	142.3	181.6	220.9	258.4	297.7
72.5°	78.6	80.5	82.4	95.5	106.7	119.8	131.1	166.6	202.2	237.8	273.4
75°	69.3	71.2	73.0	84.3	95.5	106.7	118.0	151.7	183.5	217.2	249.0
77.5°	61.8	63.7	65.5	74.9	84.3	93.6	103.0	127.3	153.5	177.9	202.2
80°	50.6	50.6	52.4	59.9	67.4	73.0	80.5	97.4	114.2	129.2	146.0
82.5°	37.4	39.3	39.3	44.9	48.7	54.3	58.0	67.4	74.9	84.3	91.7
85°	31.8	30.0	30.0	33.7	35.6	39.3	41.2	46.8	50.6	56.2	59.9
87.5°	13.1	11.2	11.2	13.1	16.9	18.7	20.6	20.6	22.5	22.5	22.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671785

CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1381.8	1385.6	1391.2	1394.9	1404.3	1411.8	1421.2	1428.6	1434.3	1443.6	1439.9
5°	1331.3	1348.1	1365.0	1381.8	1394.9	1408.1	1419.3	1432.4	1447.4	1475.5	1482.9
7.5°	1181.5	1204.0	1224.6	1247.0	1273.2	1299.5	1325.7	1351.9	1376.2	1411.8	1434.3
10°	1033.6	1065.4	1095.4	1127.2	1151.5	1175.9	1198.3	1222.7	1256.4	1292.0	1333.2
12.5°	939.9	971.8	1003.6	1035.4	1071.0	1104.7	1140.3	1174.0	1205.8	1233.9	1280.7
15°	878.2	913.7	947.4	981.1	1024.2	1065.4	1108.5	1149.7	1196.5	1233.9	1265.7
17.5°	863.2	906.2	947.4	990.5	1035.4	1080.4	1125.3	1170.3	1217.1	1273.2	1314.4
20°	837.0	895.0	953.1	1011.1	1069.1	1125.3	1183.4	1239.5	1301.3	1368.7	1387.5
22.5°	822.0	891.3	962.4	1031.7	1110.3	1190.9	1269.5	1348.1	1413.7	1464.2	1520.4
25°	820.1	906.2	994.2	1080.4	1179.6	1277.0	1376.2	1473.6	1557.8	1608.4	1653.3
27.5°	818.2	923.1	1026.1	1129.1	1250.8	1370.6	1492.3	1612.1	1690.8	1763.8	1801.3
30°	795.8	921.2	1048.5	1174.0	1310.7	1447.4	1584.1	1720.7	1801.3	1851.8	1870.5
32.5°	767.7	915.6	1063.5	1211.4	1366.9	1522.3	1675.8	1831.2	1894.9	1937.9	1923.0
35°	745.2	908.1	1069.1	1230.2	1394.9	1561.6	1726.4	1891.1	1982.9	2042.8	2018.5
37.5°	724.6	895.0	1065.4	1235.8	1428.6	1621.5	1814.4	2007.2	2095.2	2158.9	2130.8
40°	700.3	881.9	1065.4	1247.0	1468.0	1687.0	1908.0	2127.1	2241.3	2295.6	2252.5
42.5°	679.7	868.8	1059.8	1248.9	1484.8	1720.7	1956.7	2192.6	2319.9	2396.7	2342.4
45°	653.5	842.6	1029.8	1218.9	1479.2	1739.5	1997.9	2258.1	2406.0	2466.0	2391.1
47.5°	625.4	812.6	998.0	1183.4	1460.5	1737.6	2014.7	2291.8	2428.5	2499.7	2430.4
50°	616.0	803.3	988.6	1175.9	1475.5	1776.9	2076.5	2376.1	2475.3	2533.4	2441.6
52.5°	614.2	812.6	1013.0	1211.4	1512.9	1812.5	2113.9	2413.5	2494.0	2555.8	2473.5
55°	608.5	823.9	1037.3	1250.8	1565.3	1881.8	2196.3	2510.9	2591.4	2636.4	2574.6
57.5°	614.2	846.3	1076.6	1308.8	1632.7	1956.7	2280.6	2604.5	2701.9	2733.7	2720.6
60°	617.9	865.1	1110.3	1357.5	1673.9	1990.4	2306.8	2623.2	2724.4	2803.0	2818.0
62.5°	608.5	851.9	1093.5	1336.9	1623.4	1909.9	2196.3	2482.8	2649.5	2765.5	2833.0
65°	580.4	805.1	1031.7	1256.4	1520.4	1786.3	2050.3	2314.3	2490.3	2662.6	2716.9
67.5°	518.7	709.6	900.6	1091.6	1321.9	1552.2	1780.7	2011.0	2231.9	2398.6	2473.5
70°	449.4	599.2	750.8	900.6	1110.3	1320.0	1529.8	1739.5	1934.2	2117.7	2188.8
72.5°	391.3	507.4	625.4	741.5	891.3	1039.2	1189.0	1336.9	1567.2	1750.7	1820.0
75°	333.3	417.5	499.9	584.2	687.2	790.2	891.3	994.2	1157.1	1321.9	1391.2
77.5°	256.5	312.7	367.0	421.3	492.4	561.7	632.9	702.2	816.4	939.9	975.5
80°	177.9	209.7	239.7	271.5	327.7	383.8	440.0	496.2	571.1	640.4	694.7
82.5°	110.5	131.1	149.8	168.5	213.5	258.4	301.5	346.4	376.4	380.1	434.4
85°	71.2	84.3	95.5	106.7	132.9	161.0	187.2	213.5	191.0	177.9	211.6
87.5°	28.1	35.6	41.2	46.8	44.9	43.1	41.2	39.3	33.7	30.0	37.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785

CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1443.6	1449.2	1454.9	1458.6	1464.2	1466.1	1468.0	1468.0	1469.8	1471.7	1475.5
5°	1512.9	1524.1	1535.4	1544.7	1556.0	1565.3	1572.8	1582.2	1589.7	1589.7	1587.8
7.5°	1454.9	1482.9	1511.0	1539.1	1567.2	1587.8	1606.5	1627.1	1645.8	1649.6	1653.3
10°	1378.1	1408.1	1436.1	1466.1	1494.2	1526.0	1556.0	1585.9	1617.8	1623.4	1630.9
12.5°	1306.9	1342.5	1378.1	1411.8	1447.4	1469.8	1492.3	1512.9	1535.4	1550.4	1565.3
15°	1305.1	1335.0	1365.0	1393.1	1423.0	1436.1	1449.2	1460.5	1473.6	1473.6	1475.5
17.5°	1348.1	1366.9	1385.6	1402.4	1421.2	1423.0	1426.8	1428.6	1430.5	1424.9	1419.3
20°	1432.4	1439.9	1447.4	1454.9	1462.4	1449.2	1438.0	1424.9	1411.8	1396.8	1383.7
22.5°	1556.0	1539.1	1522.3	1505.4	1488.6	1466.1	1441.8	1419.3	1394.9	1376.2	1357.5
25°	1672.1	1651.5	1630.9	1610.3	1589.7	1541.0	1492.3	1441.8	1393.1	1372.5	1351.9
27.5°	1827.5	1795.6	1763.8	1732.0	1700.1	1634.6	1569.1	1503.5	1438.0	1402.4	1368.7
30°	1864.9	1829.3	1793.8	1756.3	1720.7	1657.1	1595.3	1531.6	1468.0	1426.8	1387.5
32.5°	1919.2	1878.0	1836.8	1795.6	1754.4	1692.7	1630.9	1567.2	1505.4	1468.0	1428.6
35°	2009.1	1962.3	1915.5	1866.8	1820.0	1756.3	1694.5	1630.9	1567.2	1524.1	1482.9
37.5°	2085.9	2031.6	1977.3	1923.0	1868.7	1812.5	1754.4	1698.3	1640.2	1597.2	1556.0
40°	2172.0	2112.1	2052.2	1994.1	1934.2	1881.8	1829.3	1775.0	1722.6	1688.9	1655.2
42.5°	2246.9	2173.9	2102.7	2031.6	1958.5	1923.0	1889.3	1853.7	1818.1	1801.3	1782.5
45°	2299.3	2231.9	2162.6	2095.2	2027.8	2001.6	1975.4	1949.2	1923.0	1939.8	1956.7
47.5°	2321.8	2267.5	2215.1	2162.6	2108.3	2117.7	2127.1	2134.5	2143.9	2166.4	2190.7
50°	2342.4	2312.4	2280.6	2250.6	2218.8	2254.4	2288.1	2323.7	2359.2	2406.0	2452.9
52.5°	2383.6	2366.7	2351.7	2334.9	2318.0	2379.8	2441.6	2503.4	2565.2	2617.6	2670.1
55°	2507.2	2494.0	2480.9	2466.0	2452.9	2540.9	2627.0	2715.0	2803.0	2857.3	2911.6
57.5°	2677.5	2670.1	2660.7	2653.2	2643.8	2730.0	2814.2	2898.5	2984.6	3037.0	3091.3
60°	2806.7	2808.6	2808.6	2810.5	2810.5	2876.0	2941.6	3009.0	3074.5	3119.4	3166.2
62.5°	2876.0	2872.3	2868.5	2864.8	2861.0	2915.3	2969.6	3023.9	3078.2	3111.9	3145.6
65°	2801.1	2821.7	2842.3	2862.9	2883.5	2891.0	2896.6	2904.1	2909.7	2930.3	2950.9
67.5°	2550.2	2591.4	2630.7	2671.9	2711.2	2683.2	2656.9	2628.9	2600.8	2606.4	2610.1
70°	2271.2	2318.0	2366.7	2413.5	2460.3	2394.8	2329.3	2261.9	2196.3	2173.9	2151.4
72.5°	1915.5	1956.7	1999.7	2040.9	2082.1	2001.6	1923.0	1842.5	1761.9	1722.6	1683.3
75°	1464.2	1512.9	1563.5	1612.1	1660.8	1571.0	1479.2	1389.3	1297.6	1271.4	1247.0
77.5°	1067.3	1125.3	1183.4	1241.4	1299.5	1218.9	1138.4	1056.0	975.5	960.5	945.6
80°	777.0	822.0	865.1	910.0	953.1	906.2	859.4	812.6	765.8	763.9	762.1
82.5°	524.3	563.6	601.0	640.4	677.8	659.1	642.2	623.5	604.8	623.5	644.1
85°	269.6	323.9	380.1	434.4	488.7	483.1	479.3	473.7	468.1	492.4	514.9
87.5°	54.3	101.1	147.9	192.9	239.7	228.4	217.2	204.1	192.9	200.3	206.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785

CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1477.3	1479.2	1479.2	1479.2	1479.2	1479.2	1475.5	1473.6	1469.8	1466.1	1460.5
5°	1587.8	1585.9	1578.4	1571.0	1561.6	1554.1	1548.5	1541.0	1535.4	1527.9	1516.7
7.5°	1657.1	1660.8	1647.7	1636.5	1623.4	1610.3	1597.2	1584.1	1571.0	1557.8	1531.6
10°	1636.5	1642.1	1634.6	1627.1	1617.8	1610.3	1595.3	1578.4	1563.5	1546.6	1514.8
12.5°	1578.4	1593.4	1589.7	1585.9	1582.2	1578.4	1569.1	1557.8	1548.5	1537.2	1501.7
15°	1475.5	1475.5	1477.3	1479.2	1479.2	1481.1	1482.9	1484.8	1486.7	1488.6	1468.0
17.5°	1413.7	1408.1	1408.1	1408.1	1408.1	1408.1	1415.5	1424.9	1432.4	1439.9	1434.3
20°	1368.7	1355.6	1353.8	1353.8	1351.9	1350.0	1363.1	1378.1	1391.2	1404.3	1411.8
22.5°	1338.8	1320.0	1318.2	1316.3	1314.4	1312.6	1329.4	1346.3	1363.1	1380.0	1406.2
25°	1331.3	1310.7	1312.6	1314.4	1314.4	1316.3	1329.4	1342.5	1355.6	1368.7	1413.7
27.5°	1333.2	1299.5	1301.3	1303.2	1303.2	1305.1	1325.7	1344.4	1365.0	1383.7	1439.9
30°	1346.3	1306.9	1303.2	1299.5	1295.7	1292.0	1320.0	1348.1	1376.2	1404.3	1447.4
32.5°	1391.2	1353.8	1344.4	1335.0	1325.7	1316.3	1350.0	1381.8	1415.5	1447.4	1482.9
35°	1439.9	1398.7	1394.9	1391.2	1385.6	1381.8	1411.8	1443.6	1473.6	1503.5	1535.4
37.5°	1512.9	1471.7	1468.0	1462.4	1458.6	1453.0	1486.7	1518.5	1552.2	1584.1	1612.1
40°	1621.5	1587.8	1585.9	1585.9	1584.1	1582.2	1608.4	1636.5	1662.7	1688.9	1707.6
42.5°	1765.7	1748.8	1754.4	1761.9	1767.6	1773.2	1793.8	1816.2	1836.8	1857.4	1851.8
45°	1973.5	1990.4	1992.2	1994.1	1996.0	1997.9	2003.5	2011.0	2016.6	2022.2	1999.7
47.5°	2213.2	2235.7	2246.9	2258.1	2267.5	2278.7	2271.2	2261.9	2254.4	2245.0	2188.8
50°	2497.8	2544.6	2542.7	2540.9	2537.1	2535.2	2520.3	2505.3	2488.4	2473.5	2391.1
52.5°	2722.5	2774.9	2784.3	2793.6	2803.0	2812.4	2784.3	2756.2	2726.2	2698.1	2595.2
55°	2964.0	3018.3	3020.2	3022.1	3022.1	3023.9	2984.6	2945.3	2904.1	2864.8	2758.1
57.5°	3143.8	3196.2	3190.6	3186.8	3181.2	3175.6	3128.8	3082.0	3035.2	2988.4	2881.6
60°	3211.2	3256.1	3244.9	3233.7	3220.5	3209.3	3173.7	3138.2	3100.7	3065.1	2962.2
62.5°	3179.4	3213.1	3196.2	3181.2	3164.4	3147.5	3102.6	3055.8	3010.8	2964.0	2889.1
65°	2969.6	2990.2	2967.8	2947.2	2926.6	2904.1	2866.7	2829.2	2789.9	2752.4	2701.9
67.5°	2615.8	2619.5	2617.6	2615.8	2613.9	2612.0	2557.7	2503.4	2447.2	2392.9	2389.2
70°	2130.8	2108.3	2112.1	2117.7	2121.4	2125.2	2084.0	2044.7	2003.5	1962.3	1981.0
72.5°	1644.0	1604.7	1614.0	1625.3	1634.6	1644.0	1610.3	1578.4	1544.7	1511.0	1537.2
75°	1220.8	1196.5	1205.8	1217.1	1226.4	1235.8	1222.7	1209.6	1194.6	1181.5	1205.8
77.5°	930.6	915.6	917.5	917.5	919.4	919.4	921.2	925.0	926.8	928.7	954.9
80°	758.3	756.5	754.6	752.7	749.0	747.1	765.8	784.5	803.3	822.0	835.1
82.5°	662.8	681.6	670.3	661.0	649.7	638.5	655.3	672.2	689.0	705.9	700.3
85°	539.3	561.7	541.1	520.5	498.1	477.5	492.4	505.6	520.5	533.6	526.1
87.5°	213.5	219.1	185.4	153.5	119.8	86.1	136.7	185.4	235.9	284.6	292.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785

CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1	1348.1
2.5°	1454.9	1447.4	1441.8	1439.9	1436.1	1434.3	1430.5	1426.8	1421.2	1417.4	1411.8
5°	1503.5	1492.3	1479.2	1460.5	1443.6	1424.9	1406.2	1389.3	1372.5	1353.8	1336.9
7.5°	1505.4	1479.2	1453.0	1428.6	1402.4	1378.1	1351.9	1329.4	1305.1	1280.7	1258.3
10°	1484.8	1453.0	1421.2	1389.3	1359.4	1327.5	1295.7	1269.5	1241.4	1213.3	1187.1
12.5°	1468.0	1432.4	1396.8	1359.4	1323.8	1286.3	1248.9	1222.7	1196.5	1170.3	1144.0
15°	1447.4	1424.9	1404.3	1370.6	1336.9	1303.2	1269.5	1233.9	1200.2	1164.6	1129.1
17.5°	1430.5	1424.9	1419.3	1396.8	1374.3	1350.0	1327.5	1292.0	1256.4	1218.9	1183.4
20°	1421.2	1428.6	1436.1	1424.9	1413.7	1400.6	1389.3	1363.1	1336.9	1308.8	1282.6
22.5°	1432.4	1460.5	1486.7	1488.6	1492.3	1494.2	1496.1	1471.7	1447.4	1421.2	1396.8
25°	1458.6	1503.5	1548.5	1572.8	1597.2	1623.4	1647.7	1632.7	1617.8	1602.8	1587.8
27.5°	1494.2	1550.4	1606.5	1642.1	1675.8	1711.4	1747.0	1745.1	1743.2	1739.5	1737.6
30°	1488.6	1531.6	1574.7	1617.8	1660.8	1703.9	1747.0	1769.4	1790.0	1812.5	1835.0
32.5°	1520.4	1556.0	1593.4	1638.4	1683.3	1730.1	1775.0	1821.9	1866.8	1913.6	1960.4
35°	1569.1	1600.9	1634.6	1683.3	1733.9	1782.5	1833.1	1889.3	1947.3	2005.3	2061.5
37.5°	1642.1	1670.2	1700.1	1741.3	1784.4	1825.6	1868.7	1951.1	2033.4	2117.7	2200.1
40°	1726.4	1745.1	1763.8	1803.1	1842.5	1881.8	1921.1	2024.1	2127.1	2230.0	2333.0
42.5°	1848.1	1842.5	1836.8	1868.7	1902.4	1934.2	1967.9	2061.5	2155.1	2248.8	2342.4
45°	1977.3	1954.8	1932.3	1947.3	1964.2	1979.1	1996.0	2091.5	2187.0	2284.3	2379.8
47.5°	2132.7	2076.5	2020.3	2007.2	1994.1	1979.1	1966.0	2069.0	2172.0	2276.8	2379.8
50°	2308.7	2224.4	2142.0	2108.3	2072.8	2039.1	2003.5	2087.7	2173.9	2260.0	2344.3
52.5°	2492.2	2387.3	2284.3	2231.9	2179.5	2125.2	2072.8	2143.9	2216.9	2290.0	2361.1
55°	2649.5	2542.7	2434.1	2372.3	2310.6	2248.8	2187.0	2258.1	2329.3	2400.4	2471.6
57.5°	2774.9	2668.2	2561.5	2503.4	2443.5	2385.4	2325.5	2392.9	2462.2	2531.5	2598.9
60°	2861.0	2758.1	2655.1	2598.9	2542.7	2486.6	2430.4	2510.9	2591.4	2673.8	2754.3
62.5°	2816.1	2741.2	2666.3	2642.0	2617.6	2591.4	2567.1	2643.8	2718.7	2795.5	2872.3
65°	2651.3	2600.8	2550.2	2574.6	2600.8	2625.1	2651.3	2701.9	2752.4	2804.9	2855.4
67.5°	2383.6	2379.8	2374.2	2428.5	2482.8	2539.0	2593.3	2627.0	2658.8	2692.5	2726.2
70°	1999.7	2020.3	2039.1	2132.7	2226.3	2319.9	2413.5	2426.6	2439.7	2452.9	2466.0
72.5°	1565.3	1591.5	1619.6	1743.2	1864.9	1988.5	2112.1	2104.6	2097.1	2087.7	2080.2
75°	1232.0	1256.4	1282.6	1396.8	1511.0	1625.3	1739.5	1707.6	1677.7	1645.8	1614.0
77.5°	983.0	1009.2	1037.3	1144.0	1250.8	1359.4	1466.1	1389.3	1312.6	1235.8	1159.0
80°	846.3	859.4	870.7	943.7	1014.8	1087.9	1160.9	1082.3	1001.7	921.2	842.6
82.5°	694.7	687.2	681.6	724.6	767.7	810.8	853.8	778.9	704.0	627.3	552.4
85°	518.7	511.2	503.7	526.1	548.6	573.0	595.4	509.3	423.2	335.2	249.0
87.5°	301.5	308.9	316.4	340.8	365.1	391.3	415.7	327.7	239.7	149.8	61.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671785  
 CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	1348.1	1348.1
2.5°	1400.6	1391.2
5°	1323.8	1310.7
7.5°	1239.5	1222.7
10°	1162.8	1140.3
12.5°	1114.1	1086.0
15°	1095.4	1061.7
17.5°	1151.5	1119.7
20°	1237.7	1194.6
22.5°	1342.5	1290.1
25°	1524.1	1460.5
27.5°	1672.1	1606.5
30°	1763.8	1692.7
32.5°	1864.9	1771.3
35°	1969.8	1879.9
37.5°	2097.1	1996.0
40°	2228.2	2123.3
42.5°	2273.1	2205.7
45°	2316.2	2252.5
47.5°	2325.5	2273.1
50°	2334.9	2327.4
52.5°	2361.1	2359.2
55°	2473.5	2475.3
57.5°	2612.0	2623.2
60°	2739.3	2726.2
62.5°	2804.9	2737.5
65°	2759.9	2666.3
67.5°	2625.1	2524.0
70°	2329.3	2192.6
72.5°	1960.4	1840.6
75°	1511.0	1409.9
77.5°	1074.8	990.5
80°	756.5	672.2
82.5°	485.0	417.5
85°	219.1	191.0
87.5°	61.8	59.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671785  
CATALOG NUMBER: CCP-SA-2B-722-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)