

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671807

Luminaire Tested: **CCP-SA-2B-730-U-SLR**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P671807  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2B-730-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR distribution lens  
Light Source: (32) 3000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5218.9 lumens  
Efficiency: N/A  
Efficacy: 113.5 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2


Input Watts (W): 46  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 7.4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671807  
CATALOG NUMBER: CCP-SA-2B-730-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral      - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671807

CATALOG NUMBER: CCP-SA-2B-730-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1073.8	0.0	1073.8
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	4145.1	0.0	4145.1
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	5218.9	0.0	5218.9
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.5	2.5
10°-20°	273.4	5.2
20°-30°	400.0	7.7
30°-40°	563.6	10.8
40°-50°	774.4	14.8
50°-60°	1055.5	20.2
60°-70°	1155.3	22.1
70°-80°	667.2	12.8
80°-90°	200.0	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5218.9	100.0
0°-180°	5218.9	100.0




REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	536.0	10.3			
FM (30°-60°)	1904.5	36.5			
FH (60°-80°)	1534.7	29.4			G1/1800
FVH (80°-90°)	169.9	3.3			G2/225
BL (0°-30°)	267.0	5.1	B1/500		
BM (30°-60°)	489.0	9.4	B1/1000		
BH (60°-80°)	287.8	5.5	B1/500		G1/500
BVH (80°-90°)	30.1	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**

Type IV Short





REPORT NUMBER: P671807

CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1719.8	1710.6	1703.6	1696.7	1687.4	1680.5	1671.2	1662.0	1650.4	1641.1	1629.6
5°	1620.3	1592.5	1564.7	1548.5	1530.0	1513.8	1495.3	1474.5	1453.6	1430.5	1409.7
7.5°	1511.5	1476.8	1442.1	1414.3	1384.2	1356.4	1326.3	1300.9	1275.4	1249.9	1224.5
10°	1409.7	1377.3	1344.8	1310.1	1273.1	1238.4	1201.3	1166.6	1131.9	1097.2	1062.5
12.5°	1342.5	1303.2	1266.1	1226.8	1189.8	1150.4	1111.1	1078.7	1046.2	1011.5	979.1
15°	1312.4	1275.4	1240.7	1201.3	1162.0	1122.6	1083.3	1046.2	1011.5	974.5	937.5
17.5°	1384.2	1331.0	1277.7	1226.8	1175.9	1124.9	1074.0	1027.7	981.4	935.1	888.8
20°	1476.8	1409.7	1344.8	1282.3	1217.5	1155.0	1090.2	1025.4	960.6	895.8	831.0
22.5°	1594.8	1518.4	1444.4	1363.4	1280.0	1199.0	1115.7	1034.7	953.7	870.3	789.3
25°	1805.5	1715.2	1624.9	1509.2	1391.1	1275.4	1157.4	1050.9	946.7	840.2	733.8
27.5°	1986.0	1863.3	1743.0	1604.1	1465.2	1326.3	1187.4	1064.8	944.4	821.7	699.0
30°	2092.5	1972.1	1851.8	1682.8	1516.1	1347.2	1178.2	1041.6	907.4	770.8	634.2
32.5°	2189.7	2055.5	1921.2	1736.0	1548.5	1363.4	1175.9	1025.4	877.3	726.8	576.4
35°	2324.0	2175.8	2030.0	1814.7	1599.5	1384.2	1168.9	1013.8	856.4	701.4	544.0
37.5°	2467.5	2284.6	2104.1	1865.7	1627.2	1388.8	1150.4	997.6	844.9	692.1	539.3
40°	2624.9	2402.7	2182.8	1918.9	1657.3	1393.5	1129.6	976.8	824.0	669.0	516.2
42.5°	2726.7	2486.0	2245.3	1960.6	1678.2	1393.5	1108.7	958.3	807.8	655.1	504.6
45°	2784.6	2550.8	2319.3	2011.5	1703.6	1395.8	1087.9	939.8	791.6	641.2	493.0
47.5°	2810.1	2592.5	2374.9	2050.8	1729.1	1405.0	1081.0	930.5	777.7	627.3	474.5
50°	2877.2	2685.1	2492.9	2145.7	1800.8	1453.6	1106.4	944.4	784.7	622.7	460.6
52.5°	2916.5	2752.2	2587.8	2231.4	1874.9	1518.4	1162.0	981.4	800.9	620.3	439.8
55°	3060.0	2902.6	2745.2	2365.6	1983.7	1604.1	1222.2	1023.1	824.0	622.7	423.6
57.5°	3242.9	3076.2	2911.9	2502.2	2092.5	1682.8	1273.1	1060.1	844.9	631.9	416.6
60°	3370.2	3208.2	3048.5	2613.3	2175.8	1740.7	1303.2	1081.0	858.8	634.2	412.0
62.5°	3384.1	3175.8	2969.8	2546.2	2122.6	1696.7	1273.1	1057.8	842.6	625.0	409.7
65°	3296.1	3053.1	2810.1	2405.0	1999.9	1594.8	1189.8	993.0	796.3	597.2	400.4
67.5°	3120.2	2835.5	2550.8	2180.5	1810.1	1439.7	1069.4	900.4	733.8	564.8	395.8
70°	2710.5	2460.5	2212.9	1891.1	1571.7	1249.9	928.2	789.3	652.7	513.9	375.0
72.5°	2275.4	2041.6	1810.1	1548.5	1289.3	1027.7	766.2	662.0	557.8	451.4	347.2
75°	1743.0	1567.1	1393.5	1199.0	1004.6	807.8	613.4	537.0	460.6	384.2	307.9
77.5°	1224.5	1129.6	1037.0	891.2	745.3	599.5	453.7	402.8	351.8	300.9	250.0
80°	831.0	777.7	726.8	622.7	518.5	412.0	307.9	275.5	240.7	208.3	173.6
82.5°	516.2	513.9	509.2	437.5	365.7	294.0	222.2	194.4	169.0	141.2	113.4
85°	236.1	275.5	312.5	273.1	233.8	194.4	155.1	136.6	118.1	97.2	78.7
87.5°	74.1	90.3	104.2	99.5	92.6	88.0	81.0	69.4	57.9	46.3	34.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671807

CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1620.3	1613.4	1604.1	1594.8	1583.3	1574.0	1562.4	1550.9	1548.5	1543.9	1541.6
5°	1395.8	1381.9	1365.7	1351.8	1337.9	1321.7	1307.8	1291.6	1280.0	1266.1	1254.6
7.5°	1199.0	1175.9	1150.4	1124.9	1101.8	1078.7	1053.2	1030.0	1018.5	1006.9	995.3
10°	1041.6	1018.5	997.6	974.5	958.3	944.4	928.2	912.0	898.1	884.2	870.3
12.5°	962.9	946.7	930.5	914.3	895.8	879.6	861.1	842.6	826.4	812.5	796.3
15°	914.3	891.2	865.7	842.6	817.1	793.9	768.5	743.0	724.5	708.3	689.8
17.5°	856.4	821.7	789.3	754.6	726.8	699.0	669.0	641.2	620.3	597.2	576.4
20°	791.6	752.3	710.6	671.3	638.9	608.8	576.4	544.0	520.8	495.3	472.2
22.5°	736.1	685.2	631.9	578.7	544.0	509.2	472.2	437.5	416.6	393.5	372.7
25°	675.9	620.3	562.5	504.6	469.9	432.9	398.1	361.1	344.9	331.0	314.8
27.5°	643.5	587.9	530.1	474.5	442.1	407.4	375.0	340.3	328.7	314.8	303.2
30°	578.7	525.4	469.9	414.3	391.2	370.4	347.2	324.1	319.4	317.1	312.5
32.5°	520.8	465.3	409.7	354.2	333.3	312.5	291.7	270.8	268.5	263.9	261.6
35°	490.7	437.5	381.9	328.7	310.2	289.3	270.8	250.0	245.4	238.4	233.8
37.5°	483.8	428.2	370.4	314.8	296.3	277.8	256.9	238.4	233.8	229.2	224.5
40°	465.3	412.0	361.1	307.9	289.3	270.8	250.0	231.5	226.8	222.2	217.6
42.5°	451.4	400.4	347.2	294.0	277.8	261.6	243.0	226.8	222.2	217.6	210.6
45°	439.8	386.6	331.0	277.8	266.2	254.6	240.7	229.2	224.5	217.6	213.0
47.5°	421.3	370.4	317.1	263.9	252.3	243.0	231.5	219.9	215.3	210.6	206.0
50°	407.4	354.2	300.9	247.7	238.4	229.2	219.9	210.6	210.6	210.6	213.0
52.5°	388.9	337.9	287.0	236.1	226.8	217.6	208.3	199.1	201.4	203.7	206.0
55°	372.7	324.1	273.1	222.2	213.0	203.7	192.1	182.9	185.2	187.5	189.8
57.5°	365.7	314.8	263.9	213.0	203.7	192.1	182.9	171.3	171.3	171.3	171.3
60°	361.1	307.9	256.9	203.7	192.1	182.9	171.3	159.7	157.4	157.4	155.1
62.5°	358.8	305.5	254.6	201.4	187.5	175.9	162.0	148.1	145.8	143.5	141.2
65°	349.5	300.9	250.0	199.1	182.9	169.0	152.8	136.6	134.3	134.3	131.9
67.5°	347.2	296.3	247.7	196.8	180.5	162.0	145.8	127.3	125.0	122.7	120.4
70°	328.7	284.7	238.4	192.1	173.6	157.4	138.9	120.4	118.1	113.4	111.1
72.5°	305.5	266.2	224.5	182.9	164.3	145.8	127.3	108.8	106.5	104.2	99.5
75°	270.8	233.8	196.8	159.7	143.5	129.6	113.4	97.2	94.9	92.6	88.0
77.5°	222.2	192.1	164.3	134.3	122.7	111.1	99.5	88.0	85.6	83.3	78.7
80°	157.4	138.9	122.7	104.2	97.2	88.0	81.0	71.8	71.8	69.4	69.4
82.5°	104.2	94.9	85.6	76.4	71.8	67.1	62.5	57.9	57.9	55.6	55.6
85°	74.1	69.4	62.5	57.9	55.6	50.9	48.6	44.0	44.0	44.0	44.0
87.5°	34.7	34.7	32.4	32.4	30.1	30.1	27.8	25.5	25.5	25.5	25.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1537.0	1530.0	1523.1	1513.8	1506.9	1497.6	1486.0	1476.8	1465.2	1465.2	1462.9
5°	1240.7	1233.7	1226.8	1217.5	1210.6	1201.3	1194.4	1185.1	1175.9	1175.9	1173.6
7.5°	983.8	969.9	956.0	939.8	925.9	916.6	907.4	895.8	886.5	879.6	872.6
10°	856.4	842.6	826.4	812.5	796.3	784.7	773.1	759.2	747.7	738.4	729.1
12.5°	780.1	763.9	747.7	731.4	715.2	699.0	685.2	669.0	652.7	641.2	629.6
15°	671.3	655.1	638.9	622.7	606.5	587.9	569.4	548.6	530.1	520.8	513.9
17.5°	553.2	537.0	518.5	502.3	483.8	469.9	456.0	442.1	428.2	419.0	412.0
20°	446.7	428.2	409.7	391.2	372.7	363.4	354.2	344.9	335.6	328.7	324.1
22.5°	349.5	337.9	328.7	317.1	305.5	298.6	294.0	287.0	280.1	280.1	280.1
25°	298.6	291.7	287.0	280.1	273.1	270.8	268.5	263.9	261.6	259.2	259.2
27.5°	289.3	282.4	275.5	268.5	261.6	259.2	256.9	252.3	250.0	250.0	250.0
30°	307.9	305.5	303.2	300.9	298.6	294.0	287.0	282.4	275.5	270.8	266.2
32.5°	256.9	254.6	254.6	252.3	250.0	254.6	256.9	261.6	263.9	266.2	268.5
35°	226.8	222.2	217.6	213.0	208.3	206.0	203.7	201.4	199.1	199.1	196.8
37.5°	219.9	215.3	210.6	206.0	201.4	199.1	196.8	194.4	192.1	192.1	189.8
40°	213.0	208.3	206.0	201.4	196.8	194.4	192.1	187.5	185.2	182.9	182.9
42.5°	206.0	203.7	199.1	196.8	192.1	189.8	187.5	182.9	180.5	178.2	175.9
45°	206.0	201.4	196.8	192.1	187.5	185.2	180.5	178.2	173.6	173.6	171.3
47.5°	201.4	196.8	192.1	187.5	182.9	180.5	175.9	173.6	169.0	166.7	164.3
50°	213.0	206.0	196.8	189.8	180.5	178.2	173.6	171.3	166.7	164.3	162.0
52.5°	208.3	201.4	192.1	185.2	175.9	171.3	169.0	164.3	159.7	157.4	155.1
55°	192.1	185.2	180.5	173.6	166.7	162.0	157.4	152.8	148.1	145.8	145.8
57.5°	171.3	169.0	166.7	164.3	162.0	157.4	152.8	145.8	141.2	138.9	136.6
60°	152.8	155.1	157.4	159.7	162.0	155.1	148.1	141.2	134.3	131.9	129.6
62.5°	138.9	143.5	148.1	150.5	155.1	148.1	141.2	134.3	127.3	125.0	122.7
65°	129.6	131.9	131.9	134.3	134.3	129.6	127.3	122.7	118.1	115.7	115.7
67.5°	118.1	118.1	118.1	115.7	115.7	113.4	113.4	111.1	108.8	106.5	106.5
70°	106.5	106.5	106.5	104.2	104.2	101.8	101.8	99.5	97.2	97.2	94.9
72.5°	97.2	97.2	94.9	94.9	92.6	92.6	92.6	90.3	90.3	88.0	88.0
75°	85.6	85.6	83.3	83.3	81.0	81.0	81.0	78.7	78.7	78.7	76.4
77.5°	76.4	76.4	74.1	74.1	71.8	71.8	71.8	69.4	69.4	67.1	67.1
80°	67.1	67.1	64.8	64.8	62.5	62.5	60.2	60.2	57.9	57.9	55.6
82.5°	53.2	53.2	53.2	53.2	53.2	50.9	50.9	48.6	46.3	46.3	44.0
85°	44.0	44.0	44.0	41.7	41.7	41.7	39.4	39.4	37.0	34.7	34.7
87.5°	25.5	25.5	25.5	23.1	23.1	23.1	23.1	23.1	23.1	23.1	20.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1462.9	1460.6	1451.3	1442.1	1451.3	1460.6	1460.6	1460.6	1458.3	1458.3	1458.3
5°	1173.6	1171.2	1166.6	1162.0	1162.0	1159.7	1164.3	1168.9	1173.6	1178.2	1182.8
7.5°	863.4	856.4	849.5	842.6	847.2	849.5	856.4	861.1	868.0	872.6	884.2
10°	719.9	710.6	703.7	696.7	692.1	687.5	682.8	680.5	675.9	671.3	675.9
12.5°	615.7	604.1	592.6	578.7	576.4	574.0	569.4	564.8	560.2	555.5	553.2
15°	504.6	495.3	490.7	483.8	474.5	465.3	460.6	458.3	453.7	449.1	446.7
17.5°	402.8	393.5	386.6	379.6	377.3	372.7	372.7	372.7	372.7	372.7	372.7
20°	317.1	310.2	310.2	307.9	307.9	305.5	307.9	310.2	310.2	312.5	314.8
22.5°	277.8	277.8	275.5	273.1	275.5	275.5	277.8	280.1	282.4	284.7	287.0
25°	256.9	254.6	256.9	259.2	259.2	259.2	261.6	261.6	263.9	263.9	263.9
27.5°	247.7	247.7	250.0	250.0	252.3	252.3	252.3	250.0	250.0	247.7	247.7
30°	261.6	256.9	256.9	256.9	254.6	252.3	250.0	250.0	247.7	245.4	243.0
32.5°	270.8	273.1	270.8	266.2	263.9	259.2	256.9	252.3	250.0	245.4	240.7
35°	196.8	194.4	199.1	201.4	203.7	206.0	208.3	210.6	210.6	213.0	213.0
37.5°	189.8	187.5	187.5	185.2	185.2	185.2	185.2	185.2	182.9	182.9	185.2
40°	180.5	178.2	178.2	175.9	175.9	173.6	173.6	173.6	173.6	173.6	173.6
42.5°	173.6	171.3	171.3	171.3	171.3	169.0	169.0	166.7	166.7	164.3	164.3
45°	171.3	169.0	166.7	164.3	164.3	162.0	162.0	162.0	159.7	159.7	159.7
47.5°	162.0	159.7	159.7	157.4	157.4	155.1	155.1	155.1	152.8	152.8	152.8
50°	157.4	155.1	155.1	152.8	152.8	150.5	150.5	150.5	148.1	148.1	148.1
52.5°	150.5	148.1	148.1	148.1	145.8	143.5	143.5	143.5	141.2	141.2	141.2
55°	143.5	141.2	141.2	141.2	138.9	136.6	136.6	136.6	134.3	134.3	134.3
57.5°	134.3	131.9	131.9	129.6	129.6	129.6	129.6	129.6	127.3	127.3	127.3
60°	127.3	125.0	125.0	122.7	122.7	120.4	120.4	120.4	120.4	120.4	120.4
62.5°	120.4	118.1	115.7	113.4	115.7	115.7	115.7	115.7	113.4	113.4	113.4
65°	113.4	111.1	108.8	106.5	106.5	106.5	106.5	106.5	106.5	106.5	106.5
67.5°	104.2	101.8	99.5	97.2	99.5	99.5	99.5	99.5	99.5	99.5	99.5
70°	94.9	92.6	92.6	90.3	90.3	88.0	88.0	90.3	90.3	90.3	90.3
72.5°	85.6	83.3	83.3	81.0	81.0	81.0	81.0	81.0	81.0	81.0	81.0
75°	76.4	74.1	74.1	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8
77.5°	64.8	62.5	62.5	62.5	62.5	62.5	62.5	64.8	64.8	64.8	64.8
80°	55.6	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2
82.5°	44.0	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7
85°	32.4	30.1	30.1	30.1	32.4	32.4	32.4	32.4	32.4	32.4	32.4
87.5°	20.8	18.5	18.5	18.5	20.8	20.8	20.8	20.8	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1458.3	1458.3	1458.3	1456.0	1453.6	1451.3	1449.0	1456.0	1460.6	1467.5	1472.2
5°	1185.1	1189.8	1192.1	1199.0	1206.0	1212.9	1219.9	1224.5	1229.1	1231.4	1236.1
7.5°	893.5	905.1	914.3	923.6	932.8	939.8	949.0	956.0	962.9	969.9	976.8
10°	678.2	682.8	685.2	694.4	701.4	710.6	717.6	724.5	731.4	736.1	743.0
12.5°	550.9	546.3	544.0	544.0	544.0	544.0	544.0	548.6	553.2	557.8	562.5
15°	444.4	442.1	439.8	437.5	435.2	430.5	428.2	432.9	437.5	442.1	446.7
17.5°	372.7	372.7	372.7	370.4	368.0	365.7	363.4	365.7	368.0	368.0	370.4
20°	319.4	321.7	324.1	326.4	326.4	328.7	328.7	331.0	333.3	333.3	335.6
22.5°	287.0	289.3	289.3	289.3	291.7	291.7	291.7	294.0	296.3	298.6	300.9
25°	261.6	261.6	259.2	259.2	261.6	261.6	261.6	261.6	263.9	263.9	263.9
27.5°	247.7	245.4	245.4	245.4	245.4	243.0	243.0	243.0	243.0	243.0	243.0
30°	240.7	238.4	236.1	233.8	233.8	231.5	229.2	229.2	229.2	229.2	229.2
32.5°	238.4	233.8	229.2	226.8	226.8	224.5	222.2	219.9	219.9	217.6	215.3
35°	213.0	210.6	210.6	208.3	206.0	203.7	201.4	201.4	201.4	199.1	199.1
37.5°	185.2	187.5	187.5	187.5	189.8	189.8	189.8	189.8	192.1	192.1	192.1
40°	173.6	173.6	173.6	175.9	178.2	178.2	180.5	180.5	182.9	182.9	182.9
42.5°	164.3	162.0	162.0	164.3	164.3	166.7	166.7	169.0	171.3	171.3	173.6
45°	159.7	157.4	157.4	157.4	157.4	155.1	155.1	157.4	159.7	162.0	164.3
47.5°	150.5	150.5	148.1	148.1	148.1	148.1	148.1	148.1	150.5	150.5	150.5
50°	145.8	145.8	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5
52.5°	141.2	138.9	138.9	138.9	138.9	136.6	136.6	136.6	136.6	136.6	136.6
55°	134.3	131.9	131.9	131.9	131.9	131.9	131.9	131.9	134.3	134.3	134.3
57.5°	127.3	125.0	125.0	125.0	127.3	127.3	127.3	127.3	129.6	129.6	129.6
60°	120.4	120.4	120.4	120.4	120.4	120.4	120.4	122.7	122.7	125.0	125.0
62.5°	113.4	113.4	113.4	113.4	115.7	115.7	115.7	115.7	118.1	118.1	118.1
65°	106.5	106.5	106.5	106.5	108.8	108.8	108.8	108.8	108.8	108.8	108.8
67.5°	99.5	99.5	99.5	99.5	99.5	99.5	99.5	101.8	101.8	104.2	104.2
70°	90.3	88.0	88.0	90.3	90.3	92.6	92.6	94.9	94.9	97.2	97.2
72.5°	81.0	81.0	81.0	81.0	81.0	81.0	81.0	83.3	85.6	85.6	88.0
75°	71.8	71.8	71.8	71.8	74.1	74.1	74.1	76.4	76.4	78.7	78.7
77.5°	64.8	62.5	62.5	62.5	64.8	64.8	64.8	67.1	67.1	69.4	69.4
80°	53.2	53.2	53.2	53.2	55.6	55.6	55.6	55.6	57.9	57.9	57.9
82.5°	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0	46.3	46.3	46.3
85°	32.4	32.4	32.4	32.4	34.7	34.7	34.7	34.7	34.7	34.7	34.7
87.5°	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	23.1	23.1	23.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671807

CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1472.2	1472.2	1472.2	1472.2	1476.8	1479.1	1483.7	1486.0	1483.7	1481.4	1476.8
5°	1238.4	1240.7	1240.7	1243.0	1243.0	1243.0	1243.0	1243.0	1247.6	1252.3	1256.9
7.5°	979.1	981.4	983.8	986.1	986.1	986.1	983.8	983.8	986.1	986.1	988.4
10°	750.0	759.2	766.2	773.1	768.5	761.5	756.9	750.0	750.0	750.0	747.7
12.5°	567.1	569.4	574.0	576.4	574.0	574.0	571.7	569.4	571.7	576.4	578.7
15°	449.1	449.1	451.4	451.4	453.7	456.0	456.0	458.3	462.9	465.3	469.9
17.5°	372.7	375.0	375.0	377.3	377.3	379.6	379.6	379.6	384.2	388.9	395.8
20°	335.6	335.6	335.6	335.6	335.6	333.3	333.3	331.0	333.3	337.9	340.3
22.5°	300.9	303.2	303.2	303.2	300.9	298.6	294.0	291.7	291.7	294.0	294.0
25°	263.9	261.6	261.6	259.2	259.2	261.6	261.6	261.6	263.9	263.9	266.2
27.5°	243.0	240.7	240.7	238.4	238.4	240.7	240.7	240.7	240.7	240.7	240.7
30°	226.8	226.8	224.5	222.2	224.5	224.5	226.8	226.8	229.2	229.2	231.5
32.5°	215.3	213.0	213.0	210.6	213.0	213.0	215.3	215.3	217.6	219.9	219.9
35°	199.1	199.1	199.1	199.1	199.1	199.1	196.8	196.8	196.8	196.8	196.8
37.5°	189.8	189.8	187.5	185.2	185.2	185.2	185.2	185.2	182.9	180.5	178.2
40°	182.9	180.5	180.5	178.2	175.9	175.9	173.6	171.3	171.3	169.0	169.0
42.5°	173.6	171.3	171.3	169.0	166.7	166.7	164.3	162.0	162.0	162.0	159.7
45°	162.0	162.0	159.7	157.4	157.4	157.4	155.1	155.1	155.1	155.1	152.8
47.5°	150.5	150.5	148.1	148.1	148.1	148.1	145.8	145.8	145.8	145.8	145.8
50°	143.5	143.5	143.5	143.5	143.5	143.5	141.2	141.2	141.2	141.2	141.2
52.5°	136.6	136.6	136.6	136.6	136.6	136.6	136.6	136.6	136.6	136.6	136.6
55°	134.3	134.3	134.3	134.3	134.3	134.3	131.9	131.9	131.9	134.3	134.3
57.5°	129.6	129.6	127.3	127.3	127.3	127.3	127.3	127.3	127.3	127.3	127.3
60°	125.0	125.0	125.0	125.0	125.0	125.0	125.0	125.0	125.0	125.0	125.0
62.5°	118.1	118.1	118.1	118.1	118.1	120.4	120.4	120.4	120.4	120.4	118.1
65°	108.8	111.1	111.1	111.1	111.1	111.1	111.1	111.1	111.1	111.1	111.1
67.5°	104.2	104.2	104.2	104.2	104.2	104.2	104.2	104.2	104.2	104.2	104.2
70°	97.2	97.2	94.9	94.9	94.9	97.2	97.2	97.2	97.2	97.2	97.2
72.5°	88.0	88.0	88.0	88.0	88.0	88.0	88.0	88.0	88.0	90.3	90.3
75°	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.7
77.5°	69.4	69.4	67.1	67.1	67.1	69.4	69.4	69.4	69.4	71.8	71.8
80°	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	60.2	60.2
82.5°	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	48.6	48.6
85°	34.7	37.0	37.0	37.0	37.0	37.0	37.0	37.0	37.0	39.4	39.4
87.5°	23.1	23.1	23.1	23.1	23.1	23.1	20.8	20.8	20.8	20.8	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1474.5	1476.8	1479.1	1479.1	1481.4	1483.7	1483.7	1493.0	1502.2	1506.9	1511.5
5°	1261.5	1259.2	1259.2	1256.9	1254.6	1261.5	1268.5	1282.3	1296.2	1298.6	1303.2
7.5°	988.4	990.7	993.0	993.0	995.3	988.4	979.1	981.4	983.8	995.3	1004.6
10°	747.7	750.0	752.3	752.3	754.6	752.3	747.7	754.6	761.5	770.8	782.4
12.5°	581.0	587.9	594.9	599.5	606.5	611.1	613.4	622.7	629.6	641.2	652.7
15°	474.5	479.1	483.8	488.4	493.0	497.7	502.3	511.6	520.8	534.7	548.6
17.5°	400.4	400.4	402.8	402.8	402.8	407.4	412.0	416.6	419.0	432.9	446.7
20°	342.6	340.3	337.9	335.6	333.3	337.9	340.3	342.6	344.9	354.2	361.1
22.5°	294.0	294.0	296.3	296.3	296.3	294.0	289.3	291.7	291.7	296.3	303.2
25°	266.2	266.2	266.2	263.9	263.9	266.2	268.5	268.5	266.2	268.5	270.8
27.5°	240.7	243.0	243.0	245.4	245.4	247.7	247.7	247.7	247.7	250.0	252.3
30°	231.5	231.5	233.8	233.8	233.8	236.1	238.4	238.4	238.4	240.7	245.4
32.5°	222.2	224.5	226.8	229.2	231.5	233.8	233.8	236.1	236.1	238.4	240.7
35°	196.8	194.4	194.4	192.1	189.8	189.8	189.8	189.8	187.5	189.8	189.8
37.5°	175.9	175.9	175.9	173.6	173.6	175.9	175.9	175.9	175.9	178.2	178.2
40°	166.7	166.7	166.7	166.7	166.7	166.7	166.7	169.0	169.0	171.3	173.6
42.5°	159.7	159.7	159.7	159.7	159.7	162.0	162.0	162.0	162.0	164.3	164.3
45°	152.8	152.8	152.8	152.8	152.8	152.8	152.8	155.1	155.1	157.4	159.7
47.5°	145.8	145.8	145.8	145.8	145.8	148.1	150.5	150.5	150.5	152.8	152.8
50°	141.2	141.2	141.2	141.2	141.2	143.5	143.5	145.8	145.8	148.1	150.5
52.5°	136.6	136.6	136.6	136.6	136.6	138.9	138.9	141.2	141.2	143.5	145.8
55°	134.3	134.3	134.3	131.9	131.9	134.3	134.3	136.6	136.6	138.9	138.9
57.5°	127.3	127.3	127.3	127.3	127.3	127.3	127.3	129.6	129.6	131.9	134.3
60°	125.0	125.0	122.7	122.7	120.4	122.7	122.7	125.0	125.0	127.3	127.3
62.5°	118.1	118.1	118.1	115.7	115.7	118.1	118.1	118.1	118.1	120.4	122.7
65°	111.1	111.1	111.1	108.8	108.8	111.1	111.1	111.1	111.1	113.4	115.7
67.5°	104.2	104.2	104.2	101.8	101.8	101.8	101.8	104.2	104.2	106.5	108.8
70°	97.2	97.2	97.2	94.9	94.9	94.9	92.6	94.9	97.2	99.5	99.5
72.5°	90.3	90.3	90.3	88.0	88.0	88.0	85.6	88.0	88.0	90.3	90.3
75°	78.7	78.7	78.7	78.7	78.7	78.7	76.4	76.4	76.4	78.7	78.7
77.5°	71.8	71.8	71.8	69.4	69.4	69.4	67.1	67.1	67.1	69.4	69.4
80°	60.2	60.2	60.2	57.9	57.9	57.9	55.6	55.6	55.6	57.9	57.9
82.5°	48.6	48.6	48.6	46.3	46.3	46.3	44.0	44.0	44.0	46.3	46.3
85°	39.4	39.4	39.4	39.4	39.4	39.4	37.0	37.0	37.0	39.4	41.7
87.5°	18.5	18.5	20.8	20.8	20.8	20.8	18.5	18.5	16.2	16.2	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807

CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1516.1	1520.8	1532.3	1541.6	1553.2	1562.4	1569.4	1578.6	1585.6	1592.5	1597.2
5°	1305.5	1307.8	1319.4	1331.0	1340.2	1351.8	1368.0	1384.2	1400.4	1416.6	1428.2
7.5°	1016.2	1025.4	1039.3	1055.5	1069.4	1083.3	1099.5	1118.0	1134.2	1150.4	1166.6
10°	791.6	800.9	814.8	828.7	840.2	854.1	872.6	891.2	909.7	928.2	946.7
12.5°	664.3	675.9	692.1	708.3	722.2	738.4	761.5	782.4	805.5	826.4	849.5
15°	560.2	574.0	594.9	618.0	638.9	659.7	682.8	706.0	726.8	750.0	773.1
17.5°	460.6	474.5	493.0	513.9	532.4	550.9	578.7	604.1	631.9	657.4	682.8
20°	370.4	377.3	395.8	414.3	432.9	451.4	472.2	493.0	513.9	534.7	567.1
22.5°	307.9	312.5	321.7	328.7	337.9	344.9	365.7	386.6	405.1	425.9	456.0
25°	270.8	273.1	280.1	284.7	291.7	296.3	310.2	321.7	335.6	347.2	375.0
27.5°	252.3	254.6	256.9	259.2	261.6	263.9	273.1	282.4	289.3	298.6	324.1
30°	247.7	250.0	256.9	261.6	268.5	273.1	277.8	282.4	287.0	291.7	307.9
32.5°	243.0	245.4	245.4	243.0	243.0	240.7	245.4	247.7	252.3	254.6	268.5
35°	192.1	192.1	194.4	196.8	199.1	201.4	208.3	213.0	219.9	224.5	236.1
37.5°	180.5	180.5	182.9	187.5	189.8	192.1	196.8	201.4	206.0	210.6	222.2
40°	173.6	175.9	178.2	180.5	182.9	185.2	189.8	192.1	196.8	199.1	208.3
42.5°	166.7	166.7	169.0	173.6	175.9	178.2	182.9	185.2	189.8	192.1	201.4
45°	162.0	164.3	166.7	169.0	169.0	171.3	175.9	180.5	182.9	187.5	196.8
47.5°	155.1	155.1	159.7	162.0	166.7	169.0	173.6	175.9	180.5	182.9	192.1
50°	150.5	152.8	157.4	159.7	164.3	166.7	173.6	178.2	185.2	189.8	194.4
52.5°	145.8	148.1	152.8	155.1	159.7	162.0	171.3	180.5	187.5	196.8	196.8
55°	141.2	141.2	145.8	152.8	157.4	162.0	166.7	173.6	178.2	182.9	182.9
57.5°	134.3	136.6	141.2	148.1	152.8	157.4	162.0	166.7	169.0	173.6	171.3
60°	129.6	129.6	136.6	143.5	150.5	157.4	157.4	157.4	155.1	155.1	155.1
62.5°	122.7	125.0	134.3	145.8	155.1	164.3	157.4	150.5	143.5	136.6	138.9
65°	118.1	120.4	125.0	131.9	136.6	141.2	136.6	134.3	129.6	125.0	127.3
67.5°	108.8	111.1	113.4	113.4	115.7	115.7	115.7	115.7	115.7	115.7	118.1
70°	101.8	101.8	101.8	104.2	104.2	104.2	104.2	104.2	104.2	104.2	106.5
72.5°	92.6	92.6	92.6	92.6	92.6	92.6	92.6	92.6	92.6	92.6	94.9
75°	81.0	81.0	81.0	81.0	81.0	81.0	81.0	81.0	81.0	81.0	83.3
77.5°	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8	69.4	69.4	71.8
80°	60.2	60.2	60.2	60.2	57.9	57.9	57.9	57.9	57.9	57.9	60.2
82.5°	48.6	48.6	48.6	48.6	46.3	46.3	46.3	46.3	44.0	44.0	46.3
85°	44.0	46.3	46.3	48.6	48.6	48.6	46.3	44.0	41.7	39.4	39.4
87.5°	18.5	18.5	18.5	18.5	16.2	16.2	16.2	16.2	16.2	16.2	16.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807

CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1604.1	1608.7	1613.4	1620.3	1629.6	1636.5	1643.4	1657.3	1673.5	1687.4	1701.3
5°	1439.7	1451.3	1462.9	1476.8	1490.7	1502.2	1516.1	1543.9	1571.7	1597.2	1624.9
7.5°	1180.5	1196.7	1210.6	1233.7	1254.6	1277.7	1298.6	1333.3	1365.7	1400.4	1432.8
10°	965.2	983.8	1002.3	1032.4	1064.8	1094.9	1124.9	1152.7	1182.8	1210.6	1238.4
12.5°	872.6	893.5	916.6	935.1	956.0	974.5	993.0	1025.4	1057.8	1090.2	1122.6
15°	796.3	819.4	842.6	865.7	886.5	909.7	930.5	958.3	988.4	1016.2	1043.9
17.5°	708.3	731.4	756.9	782.4	807.8	833.3	858.8	898.1	937.5	974.5	1013.8
20°	597.2	629.6	659.7	694.4	729.1	763.9	798.6	840.2	881.9	921.3	962.9
22.5°	486.1	516.2	546.3	587.9	629.6	669.0	710.6	766.2	819.4	875.0	928.2
25°	405.1	432.9	460.6	506.9	550.9	597.2	641.2	708.3	773.1	840.2	905.1
27.5°	349.5	375.0	400.4	449.1	497.7	544.0	592.6	666.6	738.4	812.5	884.2
30°	324.1	340.3	356.5	402.8	449.1	493.0	539.3	611.1	682.8	754.6	826.4
32.5°	282.4	296.3	310.2	351.8	393.5	432.9	474.5	548.6	620.3	694.4	766.2
35°	250.0	261.6	273.1	312.5	349.5	388.9	425.9	500.0	574.0	648.1	722.2
37.5°	231.5	243.0	252.3	287.0	324.1	358.8	393.5	467.6	539.3	613.4	685.2
40°	217.6	224.5	233.8	268.5	300.9	335.6	368.0	435.2	504.6	571.7	638.9
42.5°	208.3	217.6	224.5	254.6	287.0	317.1	347.2	412.0	476.8	539.3	604.1
45°	206.0	215.3	224.5	250.0	275.5	298.6	324.1	386.6	449.1	511.6	574.0
47.5°	201.4	208.3	217.6	238.4	256.9	277.8	296.3	358.8	421.3	481.5	544.0
50°	199.1	201.4	206.0	224.5	243.0	261.6	280.1	342.6	405.1	467.6	530.1
52.5°	196.8	196.8	196.8	213.0	229.2	243.0	259.2	321.7	386.6	449.1	511.6
55°	182.9	180.5	180.5	196.8	210.6	226.8	240.7	303.2	365.7	425.9	488.4
57.5°	169.0	166.7	164.3	178.2	192.1	206.0	219.9	282.4	347.2	409.7	472.2
60°	155.1	152.8	152.8	166.7	178.2	192.1	203.7	268.5	331.0	395.8	458.3
62.5°	138.9	141.2	141.2	152.8	166.7	178.2	189.8	254.6	321.7	386.6	451.4
65°	127.3	129.6	129.6	143.5	157.4	171.3	185.2	247.7	312.5	375.0	437.5
67.5°	118.1	120.4	120.4	136.6	150.5	166.7	180.5	236.1	294.0	349.5	405.1
70°	108.8	108.8	111.1	127.3	143.5	159.7	175.9	224.5	273.1	319.4	368.0
72.5°	97.2	99.5	101.8	118.1	131.9	148.1	162.0	206.0	250.0	294.0	337.9
75°	85.6	88.0	90.3	104.2	118.1	131.9	145.8	187.5	226.8	268.5	307.9
77.5°	76.4	78.7	81.0	92.6	104.2	115.7	127.3	157.4	189.8	219.9	250.0
80°	62.5	62.5	64.8	74.1	83.3	90.3	99.5	120.4	141.2	159.7	180.5
82.5°	46.3	48.6	48.6	55.6	60.2	67.1	71.8	83.3	92.6	104.2	113.4
85°	39.4	37.0	37.0	41.7	44.0	48.6	50.9	57.9	62.5	69.4	74.1
87.5°	16.2	13.9	13.9	16.2	20.8	23.1	25.5	25.5	27.8	27.8	27.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1708.3	1712.9	1719.8	1724.5	1736.0	1745.3	1756.9	1766.1	1773.1	1784.6	1780.0
5°	1645.8	1666.6	1687.4	1708.3	1724.5	1740.7	1754.6	1770.8	1789.3	1824.0	1833.3
7.5°	1460.6	1488.4	1513.8	1541.6	1574.0	1606.4	1638.8	1671.2	1701.3	1745.3	1773.1
10°	1277.7	1317.1	1354.1	1393.5	1423.5	1453.6	1481.4	1511.5	1553.2	1597.2	1648.1
12.5°	1162.0	1201.3	1240.7	1280.0	1324.0	1365.7	1409.7	1451.3	1490.7	1525.4	1583.3
15°	1085.6	1129.6	1171.2	1212.9	1266.1	1317.1	1370.3	1421.2	1479.1	1525.4	1564.7
17.5°	1067.1	1120.3	1171.2	1224.5	1280.0	1335.6	1391.1	1446.7	1504.6	1574.0	1624.9
20°	1034.7	1106.4	1178.2	1249.9	1321.7	1391.1	1462.9	1532.3	1608.7	1692.1	1715.2
22.5°	1016.2	1101.8	1189.8	1275.4	1372.6	1472.2	1569.4	1666.6	1747.6	1810.1	1879.5
25°	1013.8	1120.3	1229.1	1335.6	1458.3	1578.6	1701.3	1821.7	1925.8	1988.3	2043.9
27.5°	1011.5	1141.2	1268.5	1395.8	1546.2	1694.4	1844.8	1993.0	2090.2	2180.5	2226.8
30°	983.8	1138.8	1296.2	1451.3	1620.3	1789.3	1958.2	2127.2	2226.8	2289.2	2312.4
32.5°	949.0	1131.9	1314.8	1497.6	1689.7	1881.9	2071.7	2263.8	2342.5	2395.7	2377.2
35°	921.3	1122.6	1321.7	1520.8	1724.5	1930.5	2134.2	2337.9	2451.3	2525.3	2495.3
37.5°	895.8	1106.4	1317.1	1527.7	1766.1	2004.5	2243.0	2481.4	2590.2	2668.9	2634.1
40°	865.7	1090.2	1317.1	1541.6	1814.7	2085.6	2358.7	2629.5	2770.7	2837.8	2784.6
42.5°	840.2	1074.0	1310.1	1543.9	1835.6	2127.2	2418.9	2710.5	2867.9	2962.8	2895.7
45°	807.8	1041.6	1273.1	1506.9	1828.6	2150.4	2469.8	2791.5	2974.4	3048.5	2955.9
47.5°	773.1	1004.6	1233.7	1462.9	1805.5	2148.1	2490.6	2833.2	3002.2	3090.1	3004.5
50°	761.5	993.0	1222.2	1453.6	1824.0	2196.7	2567.0	2937.4	3060.0	3131.8	3018.4
52.5°	759.2	1004.6	1252.3	1497.6	1870.3	2240.6	2613.3	2983.7	3083.2	3159.6	3057.7
55°	752.3	1018.5	1282.3	1546.2	1935.1	2326.3	2715.2	3104.0	3203.6	3259.1	3182.7
57.5°	759.2	1046.2	1331.0	1618.0	2018.4	2418.9	2819.3	3219.8	3340.1	3379.5	3363.3
60°	763.9	1069.4	1372.6	1678.2	2069.4	2460.5	2851.7	3242.9	3367.9	3465.1	3483.6
62.5°	752.3	1053.2	1351.8	1652.7	2006.9	2361.0	2715.2	3069.3	3275.3	3418.8	3502.2
65°	717.6	995.3	1275.4	1553.2	1879.5	2208.2	2534.6	2861.0	3078.6	3291.5	3358.6
67.5°	641.2	877.3	1113.4	1349.5	1634.2	1918.9	2201.3	2486.0	2759.1	2965.1	3057.7
70°	555.5	740.7	928.2	1113.4	1372.6	1631.9	1891.1	2150.4	2391.1	2617.9	2705.9
72.5°	483.8	627.3	773.1	916.6	1101.8	1284.7	1469.8	1652.7	1937.4	2164.3	2249.9
75°	412.0	516.2	618.0	722.2	849.5	976.8	1101.8	1229.1	1430.5	1634.2	1719.8
77.5°	317.1	386.6	453.7	520.8	608.8	694.4	782.4	868.0	1009.2	1162.0	1206.0
80°	219.9	259.2	296.3	335.6	405.1	474.5	544.0	613.4	706.0	791.6	858.8
82.5°	136.6	162.0	185.2	208.3	263.9	319.4	372.7	428.2	465.3	469.9	537.0
85°	88.0	104.2	118.1	131.9	164.3	199.1	231.5	263.9	236.1	219.9	261.6
87.5°	34.7	44.0	50.9	57.9	55.6	53.2	50.9	48.6	41.7	37.0	46.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807

CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1784.6	1791.6	1798.5	1803.2	1810.1	1812.4	1814.7	1814.7	1817.0	1819.4	1824.0
5°	1870.3	1884.2	1898.1	1909.6	1923.5	1935.1	1944.4	1955.9	1965.2	1965.2	1962.9
7.5°	1798.5	1833.3	1868.0	1902.7	1937.4	1962.9	1986.0	2011.5	2034.6	2039.3	2043.9
10°	1703.6	1740.7	1775.4	1812.4	1847.1	1886.5	1923.5	1960.6	1999.9	2006.9	2016.1
12.5°	1615.7	1659.6	1703.6	1745.3	1789.3	1817.0	1844.8	1870.3	1898.1	1916.6	1935.1
15°	1613.4	1650.4	1687.4	1722.1	1759.2	1775.4	1791.6	1805.5	1821.7	1821.7	1824.0
17.5°	1666.6	1689.7	1712.9	1733.7	1756.9	1759.2	1763.8	1766.1	1768.4	1761.5	1754.6
20°	1770.8	1780.0	1789.3	1798.5	1807.8	1791.6	1777.7	1761.5	1745.3	1726.8	1710.6
22.5°	1923.5	1902.7	1881.9	1861.0	1840.2	1812.4	1782.3	1754.6	1724.5	1701.3	1678.2
25°	2067.0	2041.6	2016.1	1990.7	1965.2	1905.0	1844.8	1782.3	1722.1	1696.7	1671.2
27.5°	2259.2	2219.8	2180.5	2141.1	2101.8	2020.7	1939.7	1858.7	1777.7	1733.7	1692.1
30°	2305.5	2261.5	2217.5	2171.2	2127.2	2048.5	1972.1	1893.4	1814.7	1763.8	1715.2
32.5°	2372.6	2321.7	2270.7	2219.8	2168.9	2092.5	2016.1	1937.4	1861.0	1814.7	1766.1
35°	2483.7	2425.8	2367.9	2307.8	2249.9	2171.2	2094.8	2016.1	1937.4	1884.2	1833.3
37.5°	2578.6	2511.5	2444.3	2377.2	2310.1	2240.6	2168.9	2099.4	2027.7	1974.4	1923.5
40°	2685.1	2611.0	2536.9	2465.2	2391.1	2326.3	2261.5	2194.3	2129.5	2087.9	2046.2
42.5°	2777.7	2687.4	2599.4	2511.5	2421.2	2377.2	2335.5	2291.6	2247.6	2226.8	2203.6
45°	2842.5	2759.1	2673.5	2590.2	2506.8	2474.4	2442.0	2409.6	2377.2	2398.0	2418.9
47.5°	2870.2	2803.1	2738.3	2673.5	2606.4	2617.9	2629.5	2638.8	2650.3	2678.1	2708.2
50°	2895.7	2858.7	2819.3	2782.3	2742.9	2786.9	2828.6	2872.6	2916.5	2974.4	3032.3
52.5°	2946.6	2925.8	2907.3	2886.4	2865.6	2942.0	3018.4	3094.8	3171.2	3236.0	3300.8
55°	3099.4	3083.2	3067.0	3048.5	3032.3	3141.1	3247.5	3356.3	3465.1	3532.2	3599.4
57.5°	3310.0	3300.8	3289.2	3279.9	3268.4	3374.8	3479.0	3583.2	3689.6	3754.5	3821.6
60°	3469.8	3472.1	3472.1	3474.4	3474.4	3555.4	3636.4	3719.7	3800.8	3856.3	3914.2
62.5°	3555.4	3550.8	3546.1	3541.5	3536.9	3604.0	3671.1	3738.3	3805.4	3847.0	3888.7
65°	3462.8	3488.3	3513.7	3539.2	3564.7	3573.9	3580.9	3590.1	3597.1	3622.5	3648.0
67.5°	3152.6	3203.6	3252.2	3303.1	3351.7	3317.0	3284.6	3249.9	3215.1	3222.1	3226.7
70°	2807.7	2865.6	2925.8	2983.7	3041.5	2960.5	2879.5	2796.2	2715.2	2687.4	2659.6
72.5°	2367.9	2418.9	2472.1	2523.0	2574.0	2474.4	2377.2	2277.7	2178.1	2129.5	2080.9
75°	1810.1	1870.3	1932.8	1993.0	2053.1	1942.0	1828.6	1717.5	1604.1	1571.7	1541.6
77.5°	1319.4	1391.1	1462.9	1534.7	1606.4	1506.9	1407.3	1305.5	1206.0	1187.4	1168.9
80°	960.6	1016.2	1069.4	1124.9	1178.2	1120.3	1062.5	1004.6	946.7	944.4	942.1
82.5°	648.1	696.7	743.0	791.6	837.9	814.8	793.9	770.8	747.7	770.8	796.3
85°	333.3	400.4	469.9	537.0	604.1	597.2	592.6	585.6	578.7	608.8	636.5
87.5°	67.1	125.0	182.9	238.4	296.3	282.4	268.5	252.3	238.4	247.7	254.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807

CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1826.3	1828.6	1828.6	1828.6	1828.6	1828.6	1824.0	1821.7	1817.0	1812.4	1805.5
5°	1962.9	1960.6	1951.3	1942.0	1930.5	1921.2	1914.3	1905.0	1898.1	1888.8	1874.9
7.5°	2048.5	2053.1	2036.9	2023.1	2006.9	1990.7	1974.4	1958.2	1942.0	1925.8	1893.4
10°	2023.1	2030.0	2020.7	2011.5	1999.9	1990.7	1972.1	1951.3	1932.8	1912.0	1872.6
12.5°	1951.3	1969.8	1965.2	1960.6	1955.9	1951.3	1939.7	1925.8	1914.3	1900.4	1856.4
15°	1824.0	1824.0	1826.3	1828.6	1828.6	1830.9	1833.3	1835.6	1837.9	1840.2	1814.7
17.5°	1747.6	1740.7	1740.7	1740.7	1740.7	1740.7	1749.9	1761.5	1770.8	1780.0	1773.1
20°	1692.1	1675.9	1673.5	1673.5	1671.2	1668.9	1685.1	1703.6	1719.8	1736.0	1745.3
22.5°	1655.0	1631.9	1629.6	1627.2	1624.9	1622.6	1643.4	1664.3	1685.1	1705.9	1738.3
25°	1645.8	1620.3	1622.6	1624.9	1624.9	1627.2	1643.4	1659.6	1675.9	1692.1	1747.6
27.5°	1648.1	1606.4	1608.7	1611.0	1611.0	1613.4	1638.8	1662.0	1687.4	1710.6	1780.0
30°	1664.3	1615.7	1611.0	1606.4	1601.8	1597.2	1631.9	1666.6	1701.3	1736.0	1789.3
32.5°	1719.8	1673.5	1662.0	1650.4	1638.8	1627.2	1668.9	1708.3	1749.9	1789.3	1833.3
35°	1780.0	1729.1	1724.5	1719.8	1712.9	1708.3	1745.3	1784.6	1821.7	1858.7	1898.1
37.5°	1870.3	1819.4	1814.7	1807.8	1803.2	1796.2	1837.9	1877.2	1918.9	1958.2	1993.0
40°	2004.5	1962.9	1960.6	1960.6	1958.2	1955.9	1988.3	2023.1	2055.5	2087.9	2111.0
42.5°	2182.8	2161.9	2168.9	2178.1	2185.1	2192.0	2217.5	2245.3	2270.7	2296.2	2289.2
45°	2439.7	2460.5	2462.9	2465.2	2467.5	2469.8	2476.7	2486.0	2492.9	2499.9	2472.1
47.5°	2736.0	2763.8	2777.7	2791.5	2803.1	2817.0	2807.7	2796.2	2786.9	2775.3	2705.9
50°	3087.8	3145.7	3143.4	3141.1	3136.4	3134.1	3115.6	3097.1	3076.2	3057.7	2955.9
52.5°	3365.6	3430.4	3442.0	3453.5	3465.1	3476.7	3442.0	3407.3	3370.2	3335.5	3208.2
55°	3664.2	3731.3	3733.6	3735.9	3735.9	3738.3	3689.6	3641.0	3590.1	3541.5	3409.6
57.5°	3886.4	3951.2	3944.3	3939.6	3932.7	3925.7	3867.9	3810.0	3752.1	3694.3	3562.3
60°	3969.7	4025.3	4011.4	3997.5	3981.3	3967.4	3923.4	3879.5	3833.2	3789.2	3661.9
62.5°	3930.4	3972.0	3951.2	3932.7	3911.9	3891.0	3835.5	3777.6	3722.1	3664.2	3571.6
65°	3671.1	3696.6	3668.8	3643.4	3617.9	3590.1	3543.8	3497.5	3448.9	3402.6	3340.1
67.5°	3233.7	3238.3	3236.0	3233.7	3231.3	3229.0	3161.9	3094.8	3025.3	2958.2	2953.6
70°	2634.1	2606.4	2611.0	2617.9	2622.6	2627.2	2576.3	2527.7	2476.7	2425.8	2449.0
72.5°	2032.3	1983.7	1995.3	2009.2	2020.7	2032.3	1990.7	1951.3	1909.6	1868.0	1900.4
75°	1509.2	1479.1	1490.7	1504.6	1516.1	1527.7	1511.5	1495.3	1476.8	1460.6	1490.7
77.5°	1150.4	1131.9	1134.2	1134.2	1136.5	1136.5	1138.8	1143.5	1145.8	1148.1	1180.5
80°	937.5	935.1	932.8	930.5	925.9	923.6	946.7	969.9	993.0	1016.2	1032.4
82.5°	819.4	842.6	828.7	817.1	803.2	789.3	810.1	831.0	851.8	872.6	865.7
85°	666.6	694.4	669.0	643.5	615.7	590.3	608.8	625.0	643.5	659.7	650.4
87.5°	263.9	270.8	229.2	189.8	148.1	106.5	169.0	229.2	291.7	351.8	361.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807

CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6	1666.6
2.5°	1798.5	1789.3	1782.3	1780.0	1775.4	1773.1	1768.4	1763.8	1756.9	1752.2	1745.3
5°	1858.7	1844.8	1828.6	1805.5	1784.6	1761.5	1738.3	1717.5	1696.7	1673.5	1652.7
7.5°	1861.0	1828.6	1796.2	1766.1	1733.7	1703.6	1671.2	1643.4	1613.4	1583.3	1555.5
10°	1835.6	1796.2	1756.9	1717.5	1680.5	1641.1	1601.8	1569.4	1534.7	1499.9	1467.5
12.5°	1814.7	1770.8	1726.8	1680.5	1636.5	1590.2	1543.9	1511.5	1479.1	1446.7	1414.3
15°	1789.3	1761.5	1736.0	1694.4	1652.7	1611.0	1569.4	1525.4	1483.7	1439.7	1395.8
17.5°	1768.4	1761.5	1754.6	1726.8	1699.0	1668.9	1641.1	1597.2	1553.2	1506.9	1462.9
20°	1756.9	1766.1	1775.4	1761.5	1747.6	1731.4	1717.5	1685.1	1652.7	1618.0	1585.6
22.5°	1770.8	1805.5	1837.9	1840.2	1844.8	1847.1	1849.5	1819.4	1789.3	1756.9	1726.8
25°	1803.2	1858.7	1914.3	1944.4	1974.4	2006.9	2036.9	2018.4	1999.9	1981.4	1962.9
27.5°	1847.1	1916.6	1986.0	2030.0	2071.7	2115.6	2159.6	2157.3	2155.0	2150.4	2148.1
30°	1840.2	1893.4	1946.7	1999.9	2053.1	2106.4	2159.6	2187.4	2212.9	2240.6	2268.4
32.5°	1879.5	1923.5	1969.8	2025.4	2080.9	2138.8	2194.3	2252.2	2307.8	2365.6	2423.5
35°	1939.7	1979.1	2020.7	2080.9	2143.4	2203.6	2266.1	2335.5	2407.3	2479.1	2548.5
37.5°	2030.0	2064.7	2101.8	2152.7	2205.9	2256.8	2310.1	2411.9	2513.8	2617.9	2719.8
40°	2134.2	2157.3	2180.5	2229.1	2277.7	2326.3	2374.9	2502.2	2629.5	2756.8	2884.1
42.5°	2284.6	2277.7	2270.7	2310.1	2351.7	2391.1	2432.8	2548.5	2664.2	2780.0	2895.7
45°	2444.3	2416.6	2388.8	2407.3	2428.1	2446.6	2467.5	2585.5	2703.6	2823.9	2942.0
47.5°	2636.5	2567.0	2497.6	2481.4	2465.2	2446.6	2430.4	2557.8	2685.1	2814.7	2942.0
50°	2854.0	2749.9	2648.0	2606.4	2562.4	2520.7	2476.7	2580.9	2687.4	2793.9	2898.0
52.5°	3080.9	2951.3	2823.9	2759.1	2694.3	2627.2	2562.4	2650.3	2740.6	2830.9	2918.8
55°	3275.3	3143.4	3009.1	2932.7	2856.4	2780.0	2703.6	2791.5	2879.5	2967.5	3055.4
57.5°	3430.4	3298.5	3166.5	3094.8	3020.7	2948.9	2874.9	2958.2	3043.8	3129.5	3212.8
60°	3536.9	3409.6	3282.3	3212.8	3143.4	3073.9	3004.5	3104.0	3203.6	3305.4	3404.9
62.5°	3481.3	3388.7	3296.1	3266.1	3236.0	3203.6	3173.5	3268.4	3361.0	3455.9	3550.8
65°	3277.6	3215.1	3152.6	3182.7	3215.1	3245.2	3277.6	3340.1	3402.6	3467.4	3529.9
67.5°	2946.6	2942.0	2935.1	3002.2	3069.3	3138.7	3205.9	3247.5	3286.9	3328.6	3370.2
70°	2472.1	2497.6	2520.7	2636.5	2752.2	2867.9	2983.7	2999.9	3016.1	3032.3	3048.5
72.5°	1935.1	1967.5	2002.2	2155.0	2305.5	2458.2	2611.0	2601.7	2592.5	2580.9	2571.6
75°	1523.1	1553.2	1585.6	1726.8	1868.0	2009.2	2150.4	2111.0	2074.0	2034.6	1995.3
77.5°	1215.2	1247.6	1282.3	1414.3	1546.2	1680.5	1812.4	1717.5	1622.6	1527.7	1432.8
80°	1046.2	1062.5	1076.3	1166.6	1254.6	1344.8	1435.1	1337.9	1238.4	1138.8	1041.6
82.5°	858.8	849.5	842.6	895.8	949.0	1002.3	1055.5	962.9	870.3	775.4	682.8
85°	641.2	631.9	622.7	650.4	678.2	708.3	736.1	629.6	523.1	414.3	307.9
87.5°	372.7	381.9	391.2	421.3	451.4	483.8	513.9	405.1	296.3	185.2	76.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671807  
 CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	1666.6	1666.6
2.5°	1731.4	1719.8
5°	1636.5	1620.3
7.5°	1532.3	1511.5
10°	1437.4	1409.7
12.5°	1377.3	1342.5
15°	1354.1	1312.4
17.5°	1423.5	1384.2
20°	1530.0	1476.8
22.5°	1659.6	1594.8
25°	1884.2	1805.5
27.5°	2067.0	1986.0
30°	2180.5	2092.5
32.5°	2305.5	2189.7
35°	2435.1	2324.0
37.5°	2592.5	2467.5
40°	2754.5	2624.9
42.5°	2810.1	2726.7
45°	2863.3	2784.6
47.5°	2874.9	2810.1
50°	2886.4	2877.2
52.5°	2918.8	2916.5
55°	3057.7	3060.0
57.5°	3229.0	3242.9
60°	3386.4	3370.2
62.5°	3467.4	3384.1
65°	3411.9	3296.1
67.5°	3245.2	3120.2
70°	2879.5	2710.5
72.5°	2423.5	2275.4
75°	1868.0	1743.0
77.5°	1328.6	1224.5
80°	935.1	831.0
82.5°	599.5	516.2
85°	270.8	236.1
87.5°	76.4	74.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671807  
CATALOG NUMBER: CCP-SA-2B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)