

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671828

Luminaire Tested: **CCP-SA-2A-740-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671828
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2A-740-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @350mA w/ SLR distribution lens
Light Source: (32) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4540.8 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 6.4 fc
 Type IV - Short - N/A

REPORT NUMBER: P671828
CATALOG NUMBER: CCP-SA-2A-740-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671828

CATALOG NUMBER: CCP-SA-2A-740-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	934.3	0.0	934.3
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3606.5	0.0	3606.5
	% Fixture	79.4	0.0	79.4
Total	Lumens	4540.8	0.0	4540.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.7	2.5
10°-20°	237.9	5.2
20°-30°	348.0	7.7
30°-40°	490.3	10.8
40°-50°	673.8	14.8
50°-60°	918.4	20.2
60°-70°	1005.2	22.1
70°-80°	580.5	12.8
80°-90°	174.0	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4540.8	100.0
0°-180°	4540.8	100.0



REPORT NUMBER: P671828


CATALOG NUMBER: CCP-SA-2A-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	466.3	10.3			
FM (30°-60°)	1657.1	36.5			
FH (60°-80°)	1335.3	29.4			G1/1800
FVH (80°-90°)	147.8	3.3			G2/225
BL (0°-30°)	232.3	5.1	B1/500		
BM (30°-60°)	425.4	9.4	B1/1000		
BH (60°-80°)	250.4	5.5	B1/500		G1/500
BVH (80°-90°)	26.2	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P671828

CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1496.4	1488.3	1482.3	1476.2	1468.2	1462.1	1454.1	1446.0	1435.9	1427.9	1417.8
5°	1409.8	1385.6	1361.4	1347.3	1331.2	1317.1	1301.0	1282.9	1264.8	1244.6	1226.5
7.5°	1315.1	1284.9	1254.7	1230.5	1204.3	1180.2	1154.0	1131.8	1109.7	1087.5	1065.4
10°	1226.5	1198.3	1170.1	1139.9	1107.7	1077.5	1045.2	1015.0	984.8	954.6	924.4
12.5°	1168.1	1133.8	1101.6	1067.4	1035.2	1000.9	966.7	938.5	910.3	880.1	851.9
15°	1141.9	1109.7	1079.5	1045.2	1011.0	976.8	942.5	910.3	880.1	847.9	815.6
17.5°	1204.3	1158.0	1111.7	1067.4	1023.1	978.8	934.5	894.2	853.9	813.6	773.4
20°	1284.9	1226.5	1170.1	1115.7	1059.3	1005.0	948.6	892.2	835.8	779.4	723.0
22.5°	1387.6	1321.1	1256.7	1186.2	1113.7	1043.2	970.7	900.2	829.7	757.2	686.8
25°	1570.9	1492.3	1413.8	1313.1	1210.4	1109.7	1007.0	914.3	823.7	731.1	638.4
27.5°	1728.0	1621.2	1516.5	1395.7	1274.8	1154.0	1033.2	926.4	821.7	714.9	608.2
30°	1820.6	1715.9	1611.2	1464.1	1319.1	1172.1	1025.1	906.3	789.5	670.6	551.8
32.5°	1905.2	1788.4	1671.6	1510.5	1347.3	1186.2	1023.1	892.2	763.3	632.4	501.5
35°	2022.0	1893.1	1766.2	1578.9	1391.6	1204.3	1017.0	882.1	745.2	610.2	473.3
37.5°	2146.9	1987.8	1830.7	1623.2	1415.8	1208.4	1000.9	868.0	735.1	602.2	469.2
40°	2283.8	2090.5	1899.1	1669.6	1442.0	1212.4	982.8	849.9	717.0	582.0	449.1
42.5°	2372.4	2163.0	1953.5	1705.8	1460.1	1212.4	964.7	833.8	702.9	569.9	439.0
45°	2422.8	2219.4	2018.0	1750.1	1482.3	1214.4	946.6	817.7	688.8	557.9	429.0
47.5°	2444.9	2255.6	2066.3	1784.3	1504.4	1222.5	940.5	809.6	676.7	545.8	412.9
50°	2503.3	2336.2	2169.0	1866.9	1566.8	1264.8	962.7	821.7	682.7	541.7	400.8
52.5°	2537.6	2394.6	2251.6	1941.4	1631.3	1321.1	1011.0	853.9	696.8	539.7	382.6
55°	2662.4	2525.5	2388.5	2058.2	1725.9	1395.7	1063.4	890.2	717.0	541.7	368.6
57.5°	2821.5	2676.5	2533.5	2177.1	1820.6	1464.1	1107.7	922.4	735.1	549.8	362.5
60°	2932.3	2791.3	2652.4	2273.7	1893.1	1514.5	1133.8	940.5	747.2	551.8	358.5
62.5°	2944.4	2763.1	2583.9	2215.3	1846.8	1476.2	1107.7	920.4	733.1	543.8	356.5
65°	2867.8	2656.4	2444.9	2092.5	1740.0	1387.6	1035.2	864.0	692.8	519.6	348.4
67.5°	2714.8	2467.1	2219.4	1897.1	1574.9	1252.7	930.4	783.4	638.4	491.4	344.4
70°	2358.3	2140.8	1925.3	1645.4	1367.5	1087.5	807.6	686.8	567.9	447.1	326.3
72.5°	1979.7	1776.3	1574.9	1347.3	1121.8	894.2	666.6	576.0	485.4	392.7	302.1
75°	1516.5	1363.4	1212.4	1043.2	874.0	702.9	533.7	467.2	400.8	334.3	267.9
77.5°	1065.4	982.8	902.2	775.4	648.5	521.6	394.7	350.4	306.1	261.8	217.5
80°	723.0	676.7	632.4	541.7	451.1	358.5	267.9	239.7	209.4	181.3	151.0
82.5°	449.1	447.1	443.1	380.6	318.2	255.8	193.3	169.2	147.0	122.9	98.7
85°	205.4	239.7	271.9	237.6	203.4	169.2	134.9	118.8	102.7	84.6	68.5
87.5°	64.4	78.5	90.6	86.6	80.6	76.5	70.5	60.4	50.3	40.3	30.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1409.8	1403.7	1395.7	1387.6	1377.5	1369.5	1359.4	1349.3	1347.3	1343.3	1341.3
5°	1214.4	1202.3	1188.2	1176.1	1164.1	1150.0	1137.9	1123.8	1113.7	1101.6	1091.6
7.5°	1043.2	1023.1	1000.9	978.8	958.6	938.5	916.3	896.2	886.1	876.1	866.0
10°	906.3	886.1	868.0	847.9	833.8	821.7	807.6	793.5	781.4	769.3	757.2
12.5°	837.8	823.7	809.6	795.5	779.4	765.3	749.2	733.1	719.0	706.9	692.8
15°	795.5	775.4	753.2	733.1	710.9	690.8	668.6	646.5	630.4	616.3	600.2
17.5°	745.2	714.9	686.8	656.5	632.4	608.2	582.0	557.9	539.7	519.6	501.5
20°	688.8	654.5	618.3	584.0	555.8	529.7	501.5	473.3	453.1	431.0	410.8
22.5°	640.4	596.1	549.8	503.5	473.3	443.1	410.8	380.6	362.5	342.4	324.2
25°	588.1	539.7	489.4	439.0	408.8	376.6	346.4	314.2	300.1	288.0	273.9
27.5°	559.9	511.5	461.2	412.9	384.7	354.5	326.3	296.0	286.0	273.9	263.8
30°	503.5	457.2	408.8	360.5	340.4	322.2	302.1	282.0	277.9	275.9	271.9
32.5°	453.1	404.8	356.5	308.1	290.0	271.9	253.8	235.6	233.6	229.6	227.6
35°	427.0	380.6	332.3	286.0	269.9	251.7	235.6	217.5	213.5	207.4	203.4
37.5°	420.9	372.6	322.2	273.9	257.8	241.7	223.5	207.4	203.4	199.4	195.4
40°	404.8	358.5	314.2	267.9	251.7	235.6	217.5	201.4	197.4	193.3	189.3
42.5°	392.7	348.4	302.1	255.8	241.7	227.6	211.5	197.4	193.3	189.3	183.3
45°	382.6	336.3	288.0	241.7	231.6	221.5	209.4	199.4	195.4	189.3	185.3
47.5°	366.5	322.2	275.9	229.6	219.5	211.5	201.4	191.3	187.3	183.3	179.2
50°	354.5	308.1	261.8	215.5	207.4	199.4	191.3	183.3	183.3	185.3	185.3
52.5°	338.3	294.0	249.7	205.4	197.4	189.3	181.3	173.2	175.2	177.2	179.2
55°	324.2	282.0	237.6	193.3	185.3	177.2	167.2	159.1	161.1	163.1	165.1
57.5°	318.2	273.9	229.6	185.3	177.2	167.2	159.1	149.0	149.0	149.0	149.0
60°	314.2	267.9	223.5	177.2	167.2	159.1	149.0	139.0	136.9	136.9	134.9
62.5°	312.2	265.8	221.5	175.2	163.1	153.1	141.0	128.9	126.9	124.9	122.9
65°	304.1	261.8	217.5	173.2	159.1	147.0	132.9	118.8	116.8	116.8	114.8
67.5°	302.1	257.8	215.5	171.2	157.1	141.0	126.9	110.8	108.8	106.7	104.7
70°	286.0	247.7	207.4	167.2	151.0	136.9	120.8	104.7	102.7	98.7	96.7
72.5°	265.8	231.6	195.4	159.1	143.0	126.9	110.8	94.7	92.6	90.6	86.6
75°	235.6	203.4	171.2	139.0	124.9	112.8	98.7	84.6	82.6	80.6	76.5
77.5°	193.3	167.2	143.0	116.8	106.7	96.7	86.6	76.5	74.5	72.5	68.5
80°	136.9	120.8	106.7	90.6	84.6	76.5	70.5	62.4	62.4	60.4	60.4
82.5°	90.6	82.6	74.5	66.5	62.4	58.4	54.4	50.3	50.3	48.3	48.3
85°	64.4	60.4	54.4	50.3	48.3	44.3	42.3	38.3	38.3	38.3	38.3
87.5°	30.2	30.2	28.2	28.2	26.2	26.2	24.2	22.2	22.2	22.2	22.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1337.3	1331.2	1325.2	1317.1	1311.1	1303.0	1292.9	1284.9	1274.8	1274.8	1272.8
5°	1079.5	1073.4	1067.4	1059.3	1053.3	1045.2	1039.2	1031.1	1023.1	1023.1	1021.1
7.5°	855.9	843.8	831.8	817.7	805.6	797.5	789.5	779.4	771.3	765.3	759.3
10°	745.2	733.1	719.0	706.9	692.8	682.7	672.7	660.6	650.5	642.4	634.4
12.5°	678.7	664.6	650.5	636.4	622.3	608.2	596.1	582.0	567.9	557.9	547.8
15°	584.0	569.9	555.8	541.7	527.7	511.5	495.4	477.3	461.2	453.1	447.1
17.5°	481.3	467.2	451.1	437.0	420.9	408.8	396.7	384.7	372.6	364.5	358.5
20°	388.7	372.6	356.5	340.4	324.2	316.2	308.1	300.1	292.0	286.0	282.0
22.5°	304.1	294.0	286.0	275.9	265.8	259.8	255.8	249.7	243.7	243.7	243.7
25°	259.8	253.8	249.7	243.7	237.6	235.6	233.6	229.6	227.6	225.6	225.6
27.5°	251.7	245.7	239.7	233.6	227.6	225.6	223.5	219.5	217.5	217.5	217.5
30°	267.9	265.8	263.8	261.8	259.8	255.8	249.7	245.7	239.7	235.6	231.6
32.5°	223.5	221.5	221.5	219.5	217.5	221.5	223.5	227.6	229.6	231.6	233.6
35°	197.4	193.3	189.3	185.3	181.3	179.2	177.2	175.2	173.2	173.2	171.2
37.5°	191.3	187.3	183.3	179.2	175.2	173.2	171.2	169.2	167.2	167.2	165.1
40°	185.3	181.3	179.2	175.2	171.2	169.2	167.2	163.1	161.1	159.1	159.1
42.5°	179.2	177.2	173.2	171.2	167.2	165.1	163.1	159.1	157.1	155.1	153.1
45°	179.2	175.2	171.2	167.2	163.1	161.1	157.1	155.1	151.0	151.0	149.0
47.5°	175.2	171.2	167.2	163.1	159.1	157.1	153.1	151.0	147.0	145.0	143.0
50°	185.3	179.2	171.2	165.1	157.1	155.1	151.0	149.0	145.0	143.0	141.0
52.5°	181.3	175.2	167.2	161.1	153.1	149.0	147.0	143.0	139.0	136.9	134.9
55°	167.2	161.1	157.1	151.0	145.0	141.0	136.9	132.9	128.9	126.9	126.9
57.5°	149.0	147.0	145.0	143.0	141.0	136.9	132.9	126.9	122.9	120.8	118.8
60°	132.9	134.9	136.9	139.0	141.0	134.9	128.9	122.9	116.8	114.8	112.8
62.5°	120.8	124.9	128.9	130.9	134.9	128.9	122.9	116.8	110.8	108.8	106.7
65°	112.8	114.8	114.8	116.8	116.8	112.8	110.8	106.7	102.7	100.7	100.7
67.5°	102.7	102.7	102.7	100.7	100.7	98.7	98.7	96.7	94.7	92.6	92.6
70°	92.6	92.6	92.6	90.6	90.6	88.6	88.6	86.6	84.6	84.6	82.6
72.5°	84.6	84.6	82.6	82.6	80.6	80.6	80.6	78.5	78.5	76.5	76.5
75°	74.5	74.5	72.5	72.5	70.5	70.5	70.5	68.5	68.5	68.5	66.5
77.5°	66.5	66.5	64.4	64.4	62.4	62.4	62.4	60.4	60.4	58.4	58.4
80°	58.4	58.4	56.4	56.4	54.4	54.4	52.4	52.4	50.3	50.3	48.3
82.5°	46.3	46.3	46.3	46.3	46.3	44.3	44.3	42.3	40.3	40.3	38.3
85°	38.3	38.3	38.3	36.3	36.3	36.3	34.2	34.2	32.2	30.2	30.2
87.5°	22.2	22.2	22.2	20.1	20.1	20.1	20.1	20.1	20.1	20.1	18.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1272.8	1270.8	1262.7	1254.7	1262.7	1270.8	1270.8	1270.8	1268.8	1268.8	1268.8
5°	1021.1	1019.1	1015.0	1011.0	1011.0	1009.0	1013.0	1017.0	1021.1	1025.1	1029.1
7.5°	751.2	745.2	739.1	733.1	737.1	739.1	745.2	749.2	755.2	759.3	769.3
10°	626.3	618.3	612.2	606.2	602.2	598.1	594.1	592.1	588.1	584.0	588.1
12.5°	535.7	525.6	515.6	503.5	501.5	499.5	495.4	491.4	487.4	483.3	481.3
15°	439.0	431.0	427.0	420.9	412.9	404.8	400.8	398.8	394.7	390.7	388.7
17.5°	350.4	342.4	336.3	330.3	328.3	324.2	324.2	324.2	324.2	324.2	324.2
20°	275.9	269.9	269.9	267.9	267.9	265.8	267.9	269.9	269.9	271.9	273.9
22.5°	241.7	241.7	239.7	237.6	239.7	239.7	241.7	243.7	245.7	247.7	249.7
25°	223.5	221.5	223.5	225.6	225.6	225.6	227.6	227.6	229.6	229.6	229.6
27.5°	215.5	215.5	217.5	217.5	219.5	219.5	219.5	217.5	217.5	215.5	215.5
30°	227.6	223.5	223.5	223.5	221.5	219.5	217.5	217.5	215.5	213.5	211.5
32.5°	235.6	237.6	235.6	231.6	229.6	225.6	223.5	219.5	217.5	213.5	209.4
35°	171.2	169.2	173.2	175.2	177.2	179.2	181.3	183.3	183.3	185.3	185.3
37.5°	165.1	163.1	163.1	161.1	161.1	161.1	161.1	161.1	159.1	159.1	161.1
40°	157.1	155.1	155.1	153.1	153.1	151.0	151.0	151.0	151.0	151.0	151.0
42.5°	151.0	149.0	149.0	149.0	149.0	147.0	147.0	145.0	145.0	143.0	143.0
45°	149.0	147.0	145.0	143.0	143.0	141.0	141.0	141.0	139.0	139.0	139.0
47.5°	141.0	139.0	139.0	136.9	136.9	134.9	134.9	134.9	132.9	132.9	132.9
50°	136.9	134.9	134.9	132.9	132.9	130.9	130.9	130.9	128.9	128.9	128.9
52.5°	130.9	128.9	128.9	128.9	126.9	124.9	124.9	124.9	122.9	122.9	122.9
55°	124.9	122.9	122.9	122.9	120.8	118.8	118.8	118.8	116.8	116.8	116.8
57.5°	116.8	114.8	114.8	112.8	112.8	112.8	112.8	112.8	110.8	110.8	110.8
60°	110.8	108.8	108.8	106.7	106.7	104.7	104.7	104.7	104.7	104.7	104.7
62.5°	104.7	102.7	100.7	98.7	100.7	100.7	100.7	100.7	98.7	98.7	98.7
65°	98.7	96.7	94.7	92.6	92.6	92.6	92.6	92.6	92.6	92.6	92.6
67.5°	90.6	88.6	86.6	84.6	86.6	86.6	86.6	86.6	86.6	86.6	86.6
70°	82.6	80.6	80.6	78.5	78.5	76.5	76.5	78.5	78.5	78.5	78.5
72.5°	74.5	72.5	72.5	70.5	70.5	70.5	70.5	70.5	70.5	70.5	70.5
75°	66.5	64.4	64.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4
77.5°	56.4	54.4	54.4	54.4	54.4	54.4	54.4	56.4	56.4	56.4	56.4
80°	48.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3
82.5°	38.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3
85°	28.2	26.2	26.2	26.2	28.2	28.2	28.2	28.2	28.2	28.2	28.2
87.5°	18.1	16.1	16.1	16.1	18.1	18.1	18.1	18.1	16.1	16.1	16.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1268.8	1268.8	1268.8	1266.8	1264.8	1262.7	1260.7	1266.8	1270.8	1276.8	1280.9
5°	1031.1	1035.2	1037.2	1043.2	1049.3	1055.3	1061.3	1065.4	1069.4	1071.4	1075.4
7.5°	777.4	787.5	795.5	803.6	811.6	817.7	825.7	831.8	837.8	843.8	849.9
10°	590.1	594.1	596.1	604.2	610.2	618.3	624.3	630.4	636.4	640.4	646.5
12.5°	479.3	475.3	473.3	473.3	473.3	473.3	473.3	477.3	481.3	485.4	489.4
15°	386.7	384.7	382.6	380.6	378.6	374.6	372.6	376.6	380.6	384.7	388.7
17.5°	324.2	324.2	324.2	322.2	320.2	318.2	316.2	318.2	320.2	320.2	322.2
20°	277.9	279.9	282.0	284.0	284.0	286.0	286.0	288.0	290.0	290.0	292.0
22.5°	249.7	251.7	251.7	251.7	253.8	253.8	253.8	255.8	257.8	259.8	261.8
25°	227.6	227.6	225.6	225.6	227.6	227.6	227.6	227.6	229.6	229.6	229.6
27.5°	215.5	213.5	213.5	213.5	213.5	211.5	211.5	211.5	211.5	211.5	211.5
30°	209.4	207.4	205.4	203.4	203.4	201.4	199.4	199.4	199.4	199.4	199.4
32.5°	207.4	203.4	199.4	197.4	197.4	195.4	193.3	191.3	191.3	189.3	187.3
35°	185.3	183.3	183.3	181.3	179.2	177.2	175.2	175.2	175.2	173.2	173.2
37.5°	161.1	163.1	163.1	163.1	165.1	165.1	165.1	165.1	167.2	167.2	167.2
40°	151.0	151.0	151.0	153.1	155.1	155.1	157.1	157.1	159.1	159.1	159.1
42.5°	143.0	141.0	141.0	143.0	143.0	145.0	145.0	147.0	149.0	149.0	151.0
45°	139.0	136.9	136.9	136.9	136.9	134.9	134.9	136.9	139.0	141.0	143.0
47.5°	130.9	130.9	128.9	128.9	128.9	128.9	128.9	128.9	130.9	130.9	130.9
50°	126.9	126.9	124.9	124.9	124.9	124.9	124.9	124.9	124.9	124.9	124.9
52.5°	122.9	120.8	120.8	120.8	120.8	118.8	118.8	118.8	118.8	118.8	118.8
55°	116.8	114.8	114.8	114.8	114.8	114.8	114.8	114.8	116.8	116.8	116.8
57.5°	110.8	108.8	108.8	108.8	110.8	110.8	110.8	110.8	112.8	112.8	112.8
60°	104.7	104.7	104.7	104.7	104.7	104.7	104.7	106.7	106.7	108.8	108.8
62.5°	98.7	98.7	98.7	98.7	100.7	100.7	100.7	100.7	102.7	102.7	102.7
65°	92.6	92.6	92.6	92.6	94.7	94.7	94.7	94.7	94.7	94.7	94.7
67.5°	86.6	86.6	86.6	86.6	86.6	86.6	86.6	88.6	88.6	90.6	90.6
70°	78.5	76.5	76.5	78.5	78.5	80.6	80.6	82.6	82.6	84.6	84.6
72.5°	70.5	70.5	70.5	70.5	70.5	70.5	70.5	72.5	74.5	74.5	76.5
75°	62.4	62.4	62.4	62.4	64.4	64.4	64.4	66.5	66.5	68.5	68.5
77.5°	56.4	54.4	54.4	54.4	56.4	56.4	56.4	58.4	58.4	60.4	60.4
80°	46.3	46.3	46.3	46.3	48.3	48.3	48.3	48.3	50.3	50.3	50.3
82.5°	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	40.3	40.3	40.3
85°	28.2	28.2	28.2	28.2	30.2	30.2	30.2	30.2	30.2	30.2	30.2
87.5°	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	20.1	20.1	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1280.9	1280.9	1280.9	1280.9	1284.9	1286.9	1290.9	1292.9	1290.9	1288.9	1284.9
5°	1077.5	1079.5	1079.5	1081.5	1081.5	1081.5	1081.5	1081.5	1085.5	1089.5	1093.6
7.5°	851.9	853.9	855.9	857.9	857.9	857.9	855.9	855.9	857.9	857.9	860.0
10°	652.5	660.6	666.6	672.7	668.6	662.6	658.6	652.5	652.5	652.5	650.5
12.5°	493.4	495.4	499.5	501.5	499.5	499.5	497.4	495.4	497.4	501.5	503.5
15°	390.7	390.7	392.7	392.7	394.7	396.7	396.7	398.8	402.8	404.8	408.8
17.5°	324.2	326.3	326.3	328.3	328.3	330.3	330.3	330.3	334.3	338.3	344.4
20°	292.0	292.0	292.0	292.0	292.0	290.0	290.0	288.0	290.0	294.0	296.0
22.5°	261.8	263.8	263.8	263.8	261.8	259.8	255.8	253.8	253.8	255.8	255.8
25°	229.6	227.6	227.6	225.6	225.6	227.6	227.6	227.6	229.6	229.6	231.6
27.5°	211.5	209.4	209.4	207.4	207.4	209.4	209.4	209.4	209.4	209.4	209.4
30°	197.4	197.4	195.4	193.3	195.4	195.4	197.4	197.4	199.4	199.4	201.4
32.5°	187.3	185.3	185.3	183.3	185.3	185.3	187.3	187.3	189.3	191.3	191.3
35°	173.2	173.2	173.2	173.2	173.2	173.2	171.2	171.2	171.2	171.2	171.2
37.5°	165.1	165.1	163.1	161.1	161.1	161.1	161.1	161.1	159.1	157.1	155.1
40°	159.1	157.1	157.1	155.1	153.1	153.1	151.0	149.0	149.0	147.0	147.0
42.5°	151.0	149.0	149.0	147.0	145.0	145.0	143.0	141.0	141.0	141.0	139.0
45°	141.0	141.0	139.0	136.9	136.9	136.9	134.9	134.9	134.9	134.9	132.9
47.5°	130.9	130.9	128.9	128.9	128.9	128.9	126.9	126.9	126.9	126.9	126.9
50°	124.9	124.9	124.9	124.9	124.9	124.9	122.9	122.9	122.9	122.9	122.9
52.5°	118.8	118.8	118.8	118.8	118.8	118.8	118.8	118.8	118.8	118.8	118.8
55°	116.8	116.8	116.8	116.8	116.8	116.8	114.8	114.8	114.8	116.8	116.8
57.5°	112.8	112.8	110.8	110.8	110.8	110.8	110.8	110.8	110.8	110.8	110.8
60°	108.8	108.8	108.8	108.8	108.8	108.8	108.8	108.8	108.8	108.8	108.8
62.5°	102.7	102.7	102.7	102.7	102.7	104.7	104.7	104.7	104.7	104.7	102.7
65°	94.7	96.7	96.7	96.7	96.7	96.7	96.7	96.7	96.7	96.7	96.7
67.5°	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6
70°	84.6	84.6	82.6	82.6	82.6	84.6	84.6	84.6	84.6	84.6	84.6
72.5°	76.5	76.5	76.5	76.5	76.5	76.5	76.5	76.5	76.5	78.5	78.5
75°	68.5	68.5	68.5	68.5	68.5	68.5	68.5	68.5	68.5	68.5	68.5
77.5°	60.4	60.4	58.4	58.4	58.4	60.4	60.4	60.4	60.4	62.4	62.4
80°	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3	52.4	52.4
82.5°	40.3	40.3	40.3	40.3	40.3	40.3	40.3	40.3	40.3	42.3	42.3
85°	30.2	32.2	32.2	32.2	32.2	32.2	32.2	32.2	32.2	34.2	34.2
87.5°	20.1	20.1	20.1	20.1	20.1	20.1	18.1	18.1	18.1	18.1	16.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1282.9	1284.9	1286.9	1286.9	1288.9	1290.9	1290.9	1299.0	1307.0	1311.1	1315.1
5°	1097.6	1095.6	1095.6	1093.6	1091.6	1097.6	1103.6	1115.7	1127.8	1129.8	1133.8
7.5°	860.0	862.0	864.0	864.0	866.0	860.0	851.9	853.9	855.9	866.0	874.0
10°	650.5	652.5	654.5	654.5	656.5	654.5	650.5	656.5	662.6	670.6	680.7
12.5°	505.5	511.5	517.6	521.6	527.7	531.7	533.7	541.7	547.8	557.9	567.9
15°	412.9	416.9	420.9	424.9	429.0	433.0	437.0	445.1	453.1	465.2	477.3
17.5°	348.4	348.4	350.4	350.4	350.4	354.5	358.5	362.5	364.5	376.6	388.7
20°	298.1	296.0	294.0	292.0	290.0	294.0	296.0	298.1	300.1	308.1	314.2
22.5°	255.8	255.8	257.8	257.8	257.8	255.8	251.7	253.8	253.8	257.8	263.8
25°	231.6	231.6	231.6	229.6	229.6	231.6	233.6	233.6	231.6	233.6	235.6
27.5°	209.4	211.5	211.5	213.5	213.5	215.5	215.5	215.5	215.5	217.5	219.5
30°	201.4	201.4	203.4	203.4	203.4	205.4	207.4	207.4	207.4	209.4	213.5
32.5°	193.3	195.4	197.4	199.4	201.4	203.4	203.4	205.4	205.4	207.4	209.4
35°	171.2	169.2	169.2	167.2	165.1	165.1	165.1	165.1	163.1	165.1	165.1
37.5°	153.1	153.1	153.1	151.0	151.0	153.1	153.1	153.1	153.1	155.1	155.1
40°	145.0	145.0	145.0	145.0	145.0	145.0	145.0	147.0	147.0	149.0	151.0
42.5°	139.0	139.0	139.0	139.0	139.0	141.0	141.0	141.0	141.0	143.0	143.0
45°	132.9	132.9	132.9	132.9	132.9	132.9	132.9	134.9	134.9	136.9	139.0
47.5°	126.9	126.9	126.9	126.9	126.9	128.9	130.9	130.9	130.9	132.9	132.9
50°	122.9	122.9	122.9	122.9	122.9	124.9	124.9	126.9	126.9	128.9	130.9
52.5°	118.8	118.8	118.8	118.8	118.8	120.8	120.8	122.9	122.9	124.9	126.9
55°	116.8	116.8	116.8	114.8	114.8	116.8	116.8	118.8	118.8	120.8	120.8
57.5°	110.8	110.8	110.8	110.8	110.8	110.8	110.8	112.8	112.8	114.8	116.8
60°	108.8	108.8	106.7	106.7	104.7	106.7	106.7	108.8	108.8	110.8	110.8
62.5°	102.7	102.7	102.7	100.7	100.7	102.7	102.7	102.7	102.7	104.7	106.7
65°	96.7	96.7	96.7	94.7	94.7	96.7	96.7	96.7	96.7	98.7	100.7
67.5°	90.6	90.6	90.6	88.6	88.6	88.6	88.6	90.6	90.6	92.6	94.7
70°	84.6	84.6	84.6	82.6	82.6	82.6	80.6	82.6	84.6	86.6	86.6
72.5°	78.5	78.5	78.5	76.5	76.5	76.5	74.5	76.5	76.5	78.5	78.5
75°	68.5	68.5	68.5	68.5	68.5	68.5	66.5	66.5	66.5	68.5	68.5
77.5°	62.4	62.4	62.4	60.4	60.4	60.4	58.4	58.4	58.4	60.4	60.4
80°	52.4	52.4	52.4	50.3	50.3	50.3	48.3	48.3	48.3	50.3	50.3
82.5°	42.3	42.3	42.3	40.3	40.3	40.3	38.3	38.3	38.3	40.3	40.3
85°	34.2	34.2	34.2	34.2	34.2	34.2	32.2	32.2	32.2	34.2	36.3
87.5°	16.1	16.1	18.1	18.1	18.1	18.1	16.1	16.1	14.1	14.1	16.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1319.1	1323.2	1333.2	1341.3	1351.4	1359.4	1365.5	1373.5	1379.5	1385.6	1389.6
5°	1135.9	1137.9	1147.9	1158.0	1166.1	1176.1	1190.2	1204.3	1218.4	1232.5	1242.6
7.5°	884.1	892.2	904.3	918.4	930.4	942.5	956.6	972.7	986.8	1000.9	1015.0
10°	688.8	696.8	708.9	721.0	731.1	743.1	759.3	775.4	791.5	807.6	823.7
12.5°	578.0	588.1	602.2	616.3	628.3	642.4	662.6	680.7	700.9	719.0	739.1
15°	487.4	499.5	517.6	537.7	555.8	574.0	594.1	614.3	632.4	652.5	672.7
17.5°	400.8	412.9	429.0	447.1	463.2	479.3	503.5	525.6	549.8	572.0	594.1
20°	322.2	328.3	344.4	360.5	376.6	392.7	410.8	429.0	447.1	465.2	493.4
22.5°	267.9	271.9	279.9	286.0	294.0	300.1	318.2	336.3	352.4	370.6	396.7
25°	235.6	237.6	243.7	247.7	253.8	257.8	269.9	279.9	292.0	302.1	326.3
27.5°	219.5	221.5	223.5	225.6	227.6	229.6	237.6	245.7	251.7	259.8	282.0
30°	215.5	217.5	223.5	227.6	233.6	237.6	241.7	245.7	249.7	253.8	267.9
32.5°	211.5	213.5	213.5	211.5	211.5	209.4	213.5	215.5	219.5	221.5	233.6
35°	167.2	167.2	169.2	171.2	173.2	175.2	181.3	185.3	191.3	195.4	205.4
37.5°	157.1	157.1	159.1	163.1	165.1	167.2	171.2	175.2	179.2	183.3	193.3
40°	151.0	153.1	155.1	157.1	159.1	161.1	165.1	167.2	171.2	173.2	181.3
42.5°	145.0	145.0	147.0	151.0	153.1	155.1	159.1	161.1	165.1	167.2	175.2
45°	141.0	143.0	145.0	147.0	147.0	149.0	153.1	157.1	159.1	163.1	171.2
47.5°	134.9	134.9	139.0	141.0	145.0	147.0	151.0	153.1	157.1	159.1	167.2
50°	130.9	132.9	136.9	139.0	143.0	145.0	151.0	155.1	161.1	165.1	169.2
52.5°	126.9	128.9	132.9	134.9	139.0	141.0	149.0	157.1	163.1	171.2	171.2
55°	122.9	122.9	126.9	132.9	136.9	141.0	145.0	151.0	155.1	159.1	159.1
57.5°	116.8	118.8	122.9	128.9	132.9	136.9	141.0	145.0	147.0	151.0	149.0
60°	112.8	112.8	118.8	124.9	130.9	136.9	136.9	136.9	134.9	134.9	134.9
62.5°	106.7	108.8	116.8	126.9	134.9	143.0	136.9	130.9	124.9	118.8	120.8
65°	102.7	104.7	108.8	114.8	118.8	122.9	118.8	116.8	112.8	108.8	110.8
67.5°	94.7	96.7	98.7	98.7	100.7	100.7	100.7	100.7	100.7	100.7	102.7
70°	88.6	88.6	88.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6	92.6
72.5°	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.6	82.6
75°	70.5	70.5	70.5	70.5	70.5	70.5	70.5	70.5	70.5	70.5	72.5
77.5°	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4	60.4	60.4	62.4
80°	52.4	52.4	52.4	52.4	50.3	50.3	50.3	50.3	50.3	50.3	52.4
82.5°	42.3	42.3	42.3	42.3	40.3	40.3	40.3	40.3	38.3	38.3	40.3
85°	38.3	40.3	40.3	42.3	42.3	42.3	40.3	38.3	36.3	34.2	34.2
87.5°	16.1	16.1	16.1	16.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828

CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1395.7	1399.7	1403.7	1409.8	1417.8	1423.9	1429.9	1442.0	1456.1	1468.2	1480.2
5°	1252.7	1262.7	1272.8	1284.9	1297.0	1307.0	1319.1	1343.3	1367.5	1389.6	1413.8
7.5°	1027.1	1041.2	1053.3	1073.4	1091.6	1111.7	1129.8	1160.0	1188.2	1218.4	1246.6
10°	839.8	855.9	872.0	898.2	926.4	952.6	978.8	1002.9	1029.1	1053.3	1077.5
12.5°	759.3	777.4	797.5	813.6	831.8	847.9	864.0	892.2	920.4	948.6	976.8
15°	692.8	712.9	733.1	753.2	771.3	791.5	809.6	833.8	860.0	884.1	908.3
17.5°	616.3	636.4	658.6	680.7	702.9	725.0	747.2	781.4	815.6	847.9	882.1
20°	519.6	547.8	574.0	604.2	634.4	664.6	694.8	731.1	767.3	801.5	837.8
22.5°	422.9	449.1	475.3	511.5	547.8	582.0	618.3	666.6	712.9	761.3	807.6
25°	352.4	376.6	400.8	441.1	479.3	519.6	557.9	616.3	672.7	731.1	787.5
27.5°	304.1	326.3	348.4	390.7	433.0	473.3	515.6	580.0	642.4	706.9	769.3
30°	282.0	296.0	310.1	350.4	390.7	429.0	469.2	531.7	594.1	656.5	719.0
32.5°	245.7	257.8	269.9	306.1	342.4	376.6	412.9	477.3	539.7	604.2	666.6
35°	217.5	227.6	237.6	271.9	304.1	338.3	370.6	435.0	499.5	563.9	628.3
37.5°	201.4	211.5	219.5	249.7	282.0	312.2	342.4	406.8	469.2	533.7	596.1
40°	189.3	195.4	203.4	233.6	261.8	292.0	320.2	378.6	439.0	497.4	555.8
42.5°	181.3	189.3	195.4	221.5	249.7	275.9	302.1	358.5	414.9	469.2	525.6
45°	179.2	187.3	195.4	217.5	239.7	259.8	282.0	336.3	390.7	445.1	499.5
47.5°	175.2	181.3	189.3	207.4	223.5	241.7	257.8	312.2	366.5	418.9	473.3
50°	173.2	175.2	179.2	195.4	211.5	227.6	243.7	298.1	352.4	406.8	461.2
52.5°	171.2	171.2	171.2	185.3	199.4	211.5	225.6	279.9	336.3	390.7	445.1
55°	159.1	157.1	157.1	171.2	183.3	197.4	209.4	263.8	318.2	370.6	424.9
57.5°	147.0	145.0	143.0	155.1	167.2	179.2	191.3	245.7	302.1	356.5	410.8
60°	134.9	132.9	132.9	145.0	155.1	167.2	177.2	233.6	288.0	344.4	398.8
62.5°	120.8	122.9	122.9	132.9	145.0	155.1	165.1	221.5	279.9	336.3	392.7
65°	110.8	112.8	112.8	124.9	136.9	149.0	161.1	215.5	271.9	326.3	380.6
67.5°	102.7	104.7	104.7	118.8	130.9	145.0	157.1	205.4	255.8	304.1	352.4
70°	94.7	94.7	96.7	110.8	124.9	139.0	153.1	195.4	237.6	277.9	320.2
72.5°	84.6	86.6	88.6	102.7	114.8	128.9	141.0	179.2	217.5	255.8	294.0
75°	74.5	76.5	78.5	90.6	102.7	114.8	126.9	163.1	197.4	233.6	267.9
77.5°	66.5	68.5	70.5	80.6	90.6	100.7	110.8	136.9	165.1	191.3	217.5
80°	54.4	54.4	56.4	64.4	72.5	78.5	86.6	104.7	122.9	139.0	157.1
82.5°	40.3	42.3	42.3	48.3	52.4	58.4	62.4	72.5	80.6	90.6	98.7
85°	34.2	32.2	32.2	36.3	38.3	42.3	44.3	50.3	54.4	60.4	64.4
87.5°	14.1	12.1	12.1	14.1	18.1	20.1	22.2	22.2	24.2	24.2	24.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828

CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1486.3	1490.3	1496.4	1500.4	1510.5	1518.5	1528.6	1536.6	1542.7	1552.7	1548.7
5°	1431.9	1450.0	1468.2	1486.3	1500.4	1514.5	1526.6	1540.7	1556.8	1587.0	1595.0
7.5°	1270.8	1295.0	1317.1	1341.3	1369.5	1397.7	1425.9	1454.1	1480.2	1518.5	1542.7
10°	1111.7	1145.9	1178.2	1212.4	1238.6	1264.8	1288.9	1315.1	1351.4	1389.6	1433.9
12.5°	1011.0	1045.2	1079.5	1113.7	1152.0	1188.2	1226.5	1262.7	1297.0	1327.2	1377.5
15°	944.5	982.8	1019.1	1055.3	1101.6	1145.9	1192.3	1236.6	1286.9	1327.2	1361.4
17.5°	928.4	974.7	1019.1	1065.4	1113.7	1162.0	1210.4	1258.7	1309.1	1369.5	1413.8
20°	900.2	962.7	1025.1	1087.5	1150.0	1210.4	1272.8	1333.2	1399.7	1472.2	1492.3
22.5°	884.1	958.6	1035.2	1109.7	1194.3	1280.9	1365.5	1450.0	1520.5	1574.9	1635.3
25°	882.1	974.7	1069.4	1162.0	1268.8	1373.5	1480.2	1585.0	1675.6	1730.0	1778.3
27.5°	880.1	992.9	1103.6	1214.4	1345.3	1474.2	1605.1	1734.0	1818.6	1897.1	1937.4
30°	855.9	990.9	1127.8	1262.7	1409.8	1556.8	1703.8	1850.8	1937.4	1991.8	2011.9
32.5°	825.7	984.8	1143.9	1303.0	1470.2	1637.3	1802.5	1969.6	2038.1	2084.4	2068.3
35°	801.5	976.8	1150.0	1323.2	1500.4	1679.6	1856.9	2034.1	2132.8	2197.2	2171.0
37.5°	779.4	962.7	1145.9	1329.2	1536.6	1744.1	1951.5	2158.9	2253.6	2322.1	2291.9
40°	753.2	948.6	1145.9	1341.3	1578.9	1814.6	2052.2	2287.8	2410.7	2469.1	2422.8
42.5°	731.1	934.5	1139.9	1343.3	1597.1	1850.8	2104.6	2358.3	2495.3	2577.8	2519.4
45°	702.9	906.3	1107.7	1311.1	1591.0	1870.9	2148.9	2428.8	2587.9	2652.4	2571.8
47.5°	672.7	874.0	1073.4	1272.8	1570.9	1868.9	2167.0	2465.1	2612.1	2688.6	2614.1
50°	662.6	864.0	1063.4	1264.8	1587.0	1911.2	2233.5	2555.7	2662.4	2724.9	2626.2
52.5°	660.6	874.0	1089.5	1303.0	1627.3	1949.5	2273.7	2596.0	2682.6	2749.0	2660.4
55°	654.5	886.1	1115.7	1345.3	1683.7	2024.0	2362.4	2700.7	2787.3	2835.6	2769.2
57.5°	660.6	910.3	1158.0	1407.7	1756.2	2104.6	2453.0	2801.4	2906.1	2940.4	2926.3
60°	664.6	930.4	1194.3	1460.1	1800.5	2140.8	2481.2	2821.5	2930.3	3014.9	3031.0
62.5°	654.5	916.3	1176.1	1438.0	1746.1	2054.2	2362.4	2670.5	2849.7	2974.6	3047.1
65°	624.3	866.0	1109.7	1351.4	1635.3	1921.3	2205.3	2489.2	2678.5	2863.8	2922.2
67.5°	557.9	763.3	968.7	1174.1	1421.8	1669.6	1915.3	2163.0	2400.6	2579.9	2660.4
70°	483.3	644.5	807.6	968.7	1194.3	1419.8	1645.4	1870.9	2080.4	2277.8	2354.3
72.5°	420.9	545.8	672.7	797.5	958.6	1117.7	1278.9	1438.0	1685.7	1883.0	1957.5
75°	358.5	449.1	537.7	628.3	739.1	849.9	958.6	1069.4	1244.6	1421.8	1496.4
77.5°	275.9	336.3	394.7	453.1	529.7	604.2	680.7	755.2	878.1	1011.0	1049.3
80°	191.3	225.6	257.8	292.0	352.4	412.9	473.3	533.7	614.3	688.8	747.2
82.5°	118.8	141.0	161.1	181.3	229.6	277.9	324.2	372.6	404.8	408.8	467.2
85°	76.5	90.6	102.7	114.8	143.0	173.2	201.4	229.6	205.4	191.3	227.6
87.5°	30.2	38.3	44.3	50.3	48.3	46.3	44.3	42.3	36.3	32.2	40.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828

CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1552.7	1558.8	1564.8	1568.9	1574.9	1576.9	1578.9	1578.9	1580.9	1583.0	1587.0
5°	1627.3	1639.3	1651.4	1661.5	1673.6	1683.7	1691.7	1701.8	1709.8	1709.8	1707.8
7.5°	1564.8	1595.0	1625.2	1655.5	1685.7	1707.8	1728.0	1750.1	1770.3	1774.3	1778.3
10°	1482.3	1514.5	1544.7	1576.9	1607.1	1641.4	1673.6	1705.8	1740.0	1746.1	1754.1
12.5°	1405.7	1444.0	1482.3	1518.5	1556.8	1580.9	1605.1	1627.3	1651.4	1667.5	1683.7
15°	1403.7	1435.9	1468.2	1498.4	1530.6	1544.7	1558.8	1570.9	1585.0	1585.0	1587.0
17.5°	1450.0	1470.2	1490.3	1508.4	1528.6	1530.6	1534.6	1536.6	1538.6	1532.6	1526.6
20°	1540.7	1548.7	1556.8	1564.8	1572.9	1558.8	1546.7	1532.6	1518.5	1502.4	1488.3
22.5°	1673.6	1655.5	1637.3	1619.2	1601.1	1576.9	1550.7	1526.6	1500.4	1480.2	1460.1
25°	1798.4	1776.3	1754.1	1732.0	1709.8	1657.5	1605.1	1550.7	1498.4	1476.2	1454.1
27.5°	1965.6	1931.4	1897.1	1862.9	1828.7	1758.2	1687.7	1617.2	1546.7	1508.4	1472.2
30°	2005.9	1967.6	1929.4	1889.1	1850.8	1782.3	1715.9	1647.4	1578.9	1534.6	1492.3
32.5°	2064.3	2020.0	1975.7	1931.4	1887.1	1820.6	1754.1	1685.7	1619.2	1578.9	1536.6
35°	2161.0	2110.6	2060.3	2007.9	1957.5	1889.1	1822.6	1754.1	1685.7	1639.3	1595.0
37.5°	2243.5	2185.1	2126.7	2068.3	2009.9	1949.5	1887.1	1826.6	1764.2	1717.9	1673.6
40°	2336.2	2271.7	2207.3	2144.8	2080.4	2024.0	1967.6	1909.2	1852.8	1816.6	1780.3
42.5°	2416.7	2338.2	2261.7	2185.1	2106.6	2068.3	2032.1	1993.8	1955.5	1937.4	1917.3
45°	2473.1	2400.6	2326.1	2253.6	2181.1	2152.9	2124.7	2096.5	2068.3	2086.4	2104.6
47.5°	2497.3	2438.9	2382.5	2326.1	2267.7	2277.8	2287.8	2295.9	2306.0	2330.1	2356.3
50°	2519.4	2487.2	2453.0	2420.8	2386.5	2424.8	2461.0	2499.3	2537.6	2587.9	2638.3
52.5°	2563.7	2545.6	2529.5	2511.4	2493.3	2559.7	2626.2	2692.6	2759.1	2815.5	2871.9
55°	2696.7	2682.6	2668.5	2652.4	2638.3	2732.9	2825.6	2920.2	3014.9	3073.3	3131.7
57.5°	2879.9	2871.9	2861.8	2853.8	2843.7	2936.3	3027.0	3117.6	3210.2	3266.6	3325.0
60°	3018.9	3020.9	3020.9	3022.9	3022.9	3093.4	3163.9	3236.4	3306.9	3355.2	3405.6
62.5°	3093.4	3089.4	3085.4	3081.3	3077.3	3135.7	3194.1	3252.5	3310.9	3347.2	3383.4
65°	3012.9	3035.0	3057.2	3079.3	3101.5	3109.5	3115.6	3123.6	3129.7	3151.8	3174.0
67.5°	2743.0	2787.3	2829.6	2873.9	2916.2	2886.0	2857.8	2827.6	2797.4	2803.4	2807.4
70°	2442.9	2493.3	2545.6	2596.0	2646.3	2575.8	2505.3	2432.8	2362.4	2338.2	2314.0
72.5°	2060.3	2104.6	2150.9	2195.2	2239.5	2152.9	2068.3	1981.7	1895.1	1852.8	1810.5
75°	1574.9	1627.3	1681.6	1734.0	1786.4	1689.7	1591.0	1494.3	1395.7	1367.5	1341.3
77.5°	1147.9	1210.4	1272.8	1335.2	1397.7	1311.1	1224.5	1135.9	1049.3	1033.2	1017.0
80°	835.8	884.1	930.4	978.8	1025.1	974.7	924.4	874.0	823.7	821.7	819.7
82.5°	563.9	606.2	646.5	688.8	729.0	708.9	690.8	670.6	650.5	670.6	692.8
85°	290.0	348.4	408.8	467.2	525.6	519.6	515.6	509.5	503.5	529.7	553.8
87.5°	58.4	108.8	159.1	207.4	257.8	245.7	233.6	219.5	207.4	215.5	221.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828

CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1589.0	1591.0	1591.0	1591.0	1591.0	1591.0	1587.0	1585.0	1580.9	1576.9	1570.9
5°	1707.8	1705.8	1697.8	1689.7	1679.6	1671.6	1665.5	1657.5	1651.4	1643.4	1631.3
7.5°	1782.3	1786.4	1772.3	1760.2	1746.1	1732.0	1717.9	1703.8	1689.7	1675.6	1647.4
10°	1760.2	1766.2	1758.2	1750.1	1740.0	1732.0	1715.9	1697.8	1681.6	1663.5	1629.3
12.5°	1697.8	1713.9	1709.8	1705.8	1701.8	1697.8	1687.7	1675.6	1665.5	1653.4	1615.2
15°	1587.0	1587.0	1589.0	1591.0	1591.0	1593.0	1595.0	1597.1	1599.1	1601.1	1578.9
17.5°	1520.5	1514.5	1514.5	1514.5	1514.5	1514.5	1522.5	1532.6	1540.7	1548.7	1542.7
20°	1472.2	1458.1	1456.1	1456.1	1454.1	1452.1	1466.1	1482.3	1496.4	1510.5	1518.5
22.5°	1440.0	1419.8	1417.8	1415.8	1413.8	1411.8	1429.9	1448.0	1466.1	1484.3	1512.5
25°	1431.9	1409.8	1411.8	1413.8	1413.8	1415.8	1429.9	1444.0	1458.1	1472.2	1520.5
27.5°	1433.9	1397.7	1399.7	1401.7	1401.7	1403.7	1425.9	1446.0	1468.2	1488.3	1548.7
30°	1448.0	1405.7	1401.7	1397.7	1393.6	1389.6	1419.8	1450.0	1480.2	1510.5	1556.8
32.5°	1496.4	1456.1	1446.0	1435.9	1425.9	1415.8	1452.1	1486.3	1522.5	1556.8	1595.0
35°	1548.7	1504.4	1500.4	1496.4	1490.3	1486.3	1518.5	1552.7	1585.0	1617.2	1651.4
37.5°	1627.3	1583.0	1578.9	1572.9	1568.9	1562.8	1599.1	1633.3	1669.6	1703.8	1734.0
40°	1744.1	1707.8	1705.8	1705.8	1703.8	1701.8	1730.0	1760.2	1788.4	1816.6	1836.7
42.5°	1899.1	1881.0	1887.1	1895.1	1901.2	1907.2	1929.4	1953.5	1975.7	1997.8	1991.8
45°	2122.7	2140.8	2142.8	2144.8	2146.9	2148.9	2154.9	2163.0	2169.0	2175.1	2150.9
47.5°	2380.5	2404.6	2416.7	2428.8	2438.9	2451.0	2442.9	2432.8	2424.8	2414.7	2354.3
50°	2686.6	2736.9	2734.9	2732.9	2728.9	2726.9	2710.8	2694.7	2676.5	2660.4	2571.8
52.5°	2928.3	2984.7	2994.7	3004.8	3014.9	3024.9	2994.7	2964.5	2932.3	2902.1	2791.3
55°	3188.1	3246.5	3248.5	3250.5	3250.5	3252.5	3210.2	3167.9	3123.6	3081.3	2966.5
57.5°	3381.4	3437.8	3431.8	3427.7	3421.7	3415.6	3365.3	3314.9	3264.6	3214.2	3099.5
60°	3453.9	3502.2	3490.2	3478.1	3464.0	3451.9	3413.6	3375.4	3335.1	3296.8	3186.1
62.5°	3419.7	3455.9	3437.8	3421.7	3403.6	3385.4	3337.1	3286.7	3238.4	3188.1	3107.5
65°	3194.1	3216.3	3192.1	3169.9	3147.8	3123.6	3083.3	3043.1	3000.8	2960.5	2906.1
67.5°	2813.5	2817.5	2815.5	2813.5	2811.5	2809.4	2751.0	2692.6	2632.2	2573.8	2569.8
70°	2291.9	2267.7	2271.7	2277.8	2281.8	2285.8	2241.5	2199.2	2154.9	2110.6	2130.7
72.5°	1768.2	1725.9	1736.0	1748.1	1758.2	1768.2	1732.0	1697.8	1661.5	1625.2	1653.4
75°	1313.1	1286.9	1297.0	1309.1	1319.1	1329.2	1315.1	1301.0	1284.9	1270.8	1297.0
77.5°	1000.9	984.8	986.8	986.8	988.8	988.8	990.9	994.9	996.9	998.9	1027.1
80°	815.6	813.6	811.6	809.6	805.6	803.6	823.7	843.8	864.0	884.1	898.2
82.5°	712.9	733.1	721.0	710.9	698.8	686.8	704.9	723.0	741.1	759.3	753.2
85°	580.0	604.2	582.0	559.9	535.7	513.6	529.7	543.8	559.9	574.0	565.9
87.5°	229.6	235.6	199.4	165.1	128.9	92.6	147.0	199.4	253.8	306.1	314.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828

CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0	1450.0
2.5°	1564.8	1556.8	1550.7	1548.7	1544.7	1542.7	1538.6	1534.6	1528.6	1524.6	1518.5
5°	1617.2	1605.1	1591.0	1570.9	1552.7	1532.6	1512.5	1494.3	1476.2	1456.1	1438.0
7.5°	1619.2	1591.0	1562.8	1536.6	1508.4	1482.3	1454.1	1429.9	1403.7	1377.5	1353.4
10°	1597.1	1562.8	1528.6	1494.3	1462.1	1427.9	1393.6	1365.5	1335.2	1305.0	1276.8
12.5°	1578.9	1540.7	1502.4	1462.1	1423.9	1383.6	1343.3	1315.1	1286.9	1258.7	1230.5
15°	1556.8	1532.6	1510.5	1474.2	1438.0	1401.7	1365.5	1327.2	1290.9	1252.7	1214.4
17.5°	1538.6	1532.6	1526.6	1502.4	1478.2	1452.1	1427.9	1389.6	1351.4	1311.1	1272.8
20°	1528.6	1536.6	1544.7	1532.6	1520.5	1506.4	1494.3	1466.1	1438.0	1407.7	1379.5
22.5°	1540.7	1570.9	1599.1	1601.1	1605.1	1607.1	1609.1	1583.0	1556.8	1528.6	1502.4
25°	1568.9	1617.2	1665.5	1691.7	1717.9	1746.1	1772.3	1756.2	1740.0	1723.9	1707.8
27.5°	1607.1	1667.5	1728.0	1766.2	1802.5	1840.7	1879.0	1877.0	1875.0	1870.9	1868.9
30°	1601.1	1647.4	1693.7	1740.0	1786.4	1832.7	1879.0	1903.2	1925.3	1949.5	1973.7
32.5°	1635.3	1673.6	1713.9	1762.2	1810.5	1860.9	1909.2	1959.6	2007.9	2058.2	2108.6
35°	1687.7	1721.9	1758.2	1810.5	1864.9	1917.3	1971.6	2032.1	2094.5	2156.9	2217.3
37.5°	1766.2	1796.4	1828.7	1873.0	1919.3	1963.6	2009.9	2098.5	2187.1	2277.8	2366.4
40°	1856.9	1877.0	1897.1	1939.4	1981.7	2024.0	2066.3	2177.1	2287.8	2398.6	2509.4
42.5°	1987.8	1981.7	1975.7	2009.9	2046.2	2080.4	2116.6	2217.3	2318.0	2418.7	2519.4
45°	2126.7	2102.6	2078.4	2094.5	2112.6	2128.7	2146.9	2249.6	2352.3	2457.0	2559.7
47.5°	2293.9	2233.5	2173.0	2158.9	2144.8	2128.7	2114.6	2225.4	2336.2	2448.9	2559.7
50°	2483.2	2392.6	2303.9	2267.7	2229.4	2193.2	2154.9	2245.5	2338.2	2430.8	2521.5
52.5°	2680.6	2567.8	2457.0	2400.6	2344.2	2285.8	2229.4	2306.0	2384.5	2463.0	2539.6
55°	2849.7	2734.9	2618.1	2551.7	2485.2	2418.7	2352.3	2428.8	2505.3	2581.9	2658.4
57.5°	2984.7	2869.9	2755.1	2692.6	2628.2	2565.8	2501.3	2573.8	2648.3	2722.8	2795.3
60°	3077.3	2966.5	2855.8	2795.3	2734.9	2674.5	2614.1	2700.7	2787.3	2875.9	2962.5
62.5°	3029.0	2948.4	2867.8	2841.7	2815.5	2787.3	2761.1	2843.7	2924.2	3006.8	3089.4
65°	2851.7	2797.4	2743.0	2769.2	2797.4	2823.5	2851.7	2906.1	2960.5	3016.9	3071.3
67.5°	2563.7	2559.7	2553.7	2612.1	2670.5	2730.9	2789.3	2825.6	2859.8	2896.0	2932.3
70°	2150.9	2173.0	2193.2	2293.9	2394.6	2495.3	2596.0	2610.1	2624.2	2638.3	2652.4
72.5°	1683.7	1711.8	1742.1	1875.0	2005.9	2138.8	2271.7	2263.7	2255.6	2245.5	2237.5
75°	1325.2	1351.4	1379.5	1502.4	1625.2	1748.1	1870.9	1836.7	1804.5	1770.3	1736.0
77.5°	1057.3	1085.5	1115.7	1230.5	1345.3	1462.1	1576.9	1494.3	1411.8	1329.2	1246.6
80°	910.3	924.4	936.5	1015.0	1091.6	1170.1	1248.6	1164.1	1077.5	990.9	906.3
82.5°	747.2	739.1	733.1	779.4	825.7	872.0	918.4	837.8	757.2	674.7	594.1
85°	557.9	549.8	541.7	565.9	590.1	616.3	640.4	547.8	455.2	360.5	267.9
87.5°	324.2	332.3	340.4	366.5	392.7	420.9	447.1	352.4	257.8	161.1	66.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671828
 CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1450.0	1450.0
2.5°	1506.4	1496.4
5°	1423.9	1409.8
7.5°	1333.2	1315.1
10°	1250.7	1226.5
12.5°	1198.3	1168.1
15°	1178.2	1141.9
17.5°	1238.6	1204.3
20°	1331.2	1284.9
22.5°	1444.0	1387.6
25°	1639.3	1570.9
27.5°	1798.4	1728.0
30°	1897.1	1820.6
32.5°	2005.9	1905.2
35°	2118.7	2022.0
37.5°	2255.6	2146.9
40°	2396.6	2283.8
42.5°	2444.9	2372.4
45°	2491.2	2422.8
47.5°	2501.3	2444.9
50°	2511.4	2503.3
52.5°	2539.6	2537.6
55°	2660.4	2662.4
57.5°	2809.4	2821.5
60°	2946.4	2932.3
62.5°	3016.9	2944.4
65°	2968.5	2867.8
67.5°	2823.5	2714.8
70°	2505.3	2358.3
72.5°	2108.6	1979.7
75°	1625.2	1516.5
77.5°	1156.0	1065.4
80°	813.6	723.0
82.5°	521.6	449.1
85°	235.6	205.4
87.5°	66.5	64.4
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671828
CATALOG NUMBER: CCP-SA-2A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)