

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671832

Luminaire Tested: **CCP-SA-2E-740-U-SLR**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P671832  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2E-740-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/ SLR distribution lens  
Light Source: (32) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11346.9 lumens  
Efficiency: N/A  
Efficacy: 106.4 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G3

Input Watts (W): 106.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 16.1 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671832  
CATALOG NUMBER: CCP-SA-2E-740-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral      - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2334.7	0.0	2334.7
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	9012.2	0.0	9012.2
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	11346.9	0.0	11346.9
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	281.6	2.5
10°-20°	594.5	5.2
20°-30°	869.7	7.7
30°-40°	1225.3	10.8
40°-50°	1683.7	14.8
50°-60°	2294.9	20.2
60°-70°	2511.8	22.1
70°-80°	1450.6	12.8
80°-90°	434.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11346.9	100.0
0°-180°	11346.9	100.0



REPORT NUMBER: P671832


CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1165.4	10.3			
FM (30°-60°)	4140.8	36.5			
FH (60°-80°)	3336.7	29.4			G2/5000
FVH (80°-90°)	369.3	3.3			G3/500
BL (0°-30°)	580.4	5.1	B2/1000		
BM (30°-60°)	1063.1	9.4	B2/2500		
BH (60°-80°)	625.7	5.5	B2/1000		G2/1000
BVH (80°-90°)	65.5	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G3**

Type IV Short





REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3739.2	3719.1	3704.0	3688.9	3668.8	3653.7	3633.6	3613.4	3588.3	3568.1	3543.0
5°	3522.8	3462.5	3402.1	3366.8	3326.6	3291.3	3251.1	3205.8	3160.5	3110.2	3064.9
7.5°	3286.3	3210.8	3135.3	3074.9	3009.5	2949.1	2883.7	2828.3	2773.0	2717.6	2662.3
10°	3064.9	2994.4	2924.0	2848.5	2767.9	2692.5	2611.9	2536.4	2461.0	2385.5	2310.0
12.5°	2918.9	2833.4	2752.9	2667.3	2586.8	2501.2	2415.7	2345.2	2274.8	2199.3	2128.8
15°	2853.5	2773.0	2697.5	2611.9	2526.4	2440.8	2355.3	2274.8	2199.3	2118.7	2038.2
17.5°	3009.5	2893.8	2778.0	2667.3	2556.6	2445.9	2335.1	2234.5	2133.8	2033.2	1932.5
20°	3210.8	3064.9	2924.0	2788.1	2647.2	2511.3	2370.4	2229.5	2088.5	1947.6	1806.7
22.5°	3467.5	3301.4	3140.4	2964.2	2783.0	2606.9	2425.7	2249.6	2073.4	1892.3	1716.1
25°	3925.5	3729.2	3532.9	3281.3	3024.6	2773.0	2516.3	2284.8	2058.3	1826.8	1595.3
27.5°	4318.0	4051.3	3789.6	3487.6	3185.7	2883.7	2581.7	2315.0	2053.3	1786.6	1519.9
30°	4549.5	4287.8	4026.1	3658.7	3296.4	2929.0	2561.6	2264.7	1972.8	1675.9	1378.9
32.5°	4760.9	4469.0	4177.1	3774.5	3366.8	2964.2	2556.6	2229.5	1907.4	1580.2	1253.1
35°	5052.8	4730.7	4413.6	3945.6	3477.5	3009.5	2541.5	2204.3	1862.1	1524.9	1182.7
37.5°	5364.8	4967.2	4574.7	4056.3	3537.9	3019.6	2501.2	2169.1	1836.9	1504.8	1172.6
40°	5707.0	5223.9	4745.8	4172.1	3603.4	3029.6	2455.9	2123.8	1791.6	1454.4	1122.3
42.5°	5928.4	5405.0	4881.7	4262.6	3648.7	3029.6	2410.6	2083.5	1756.4	1424.2	1097.1
45°	6054.3	5546.0	5042.7	4373.4	3704.0	3034.7	2365.3	2043.2	1721.2	1394.0	1072.0
47.5°	6109.6	5636.5	5163.5	4458.9	3759.4	3054.8	2350.2	2023.1	1691.0	1363.8	1031.7
50°	6255.6	5837.9	5420.1	4665.3	3915.4	3160.5	2405.6	2053.3	1706.1	1353.8	1001.5
52.5°	6341.1	5983.8	5626.5	4851.5	4076.4	3301.4	2526.4	2133.8	1741.3	1348.7	956.2
55°	6653.1	6310.9	5968.7	5143.4	4313.0	3487.6	2657.2	2224.4	1791.6	1353.8	921.0
57.5°	7050.7	6688.4	6331.1	5440.3	4549.5	3658.7	2767.9	2304.9	1836.9	1373.9	905.9
60°	7327.5	6975.2	6628.0	5681.8	4730.7	3784.5	2833.4	2350.2	1867.1	1378.9	895.8
62.5°	7357.7	6904.8	6456.9	5535.9	4614.9	3688.9	2767.9	2299.9	1831.9	1358.8	890.8
65°	7166.5	6638.0	6109.6	5228.9	4348.2	3467.5	2586.8	2159.0	1731.2	1298.4	870.6
67.5°	6784.0	6165.0	5546.0	4740.7	3935.5	3130.3	2325.1	1957.7	1595.3	1228.0	860.6
70°	5893.2	5349.7	4811.2	4111.7	3417.2	2717.6	2018.1	1716.1	1419.2	1117.2	815.3
72.5°	4947.1	4438.8	3935.5	3366.8	2803.2	2234.5	1665.8	1439.3	1212.9	981.4	754.9
75°	3789.6	3407.1	3029.6	2606.9	2184.2	1756.4	1333.6	1167.6	1001.5	835.4	669.3
77.5°	2662.3	2455.9	2254.6	1937.6	1620.5	1303.5	986.4	875.7	765.0	654.2	543.5
80°	1806.7	1691.0	1580.2	1353.8	1127.3	895.8	669.3	598.9	523.4	452.9	377.4
82.5°	1122.3	1117.2	1107.2	951.2	795.2	639.1	483.1	422.7	367.4	307.0	246.6
85°	513.3	598.9	679.4	593.9	508.3	422.7	337.2	296.9	256.7	211.4	171.1
87.5°	161.0	196.3	226.5	216.4	201.3	191.2	176.1	151.0	125.8	100.7	75.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3522.8	3507.7	3487.6	3467.5	3442.3	3422.2	3397.0	3371.9	3366.8	3356.8	3351.7
5°	3034.7	3004.5	2969.3	2939.1	2908.9	2873.6	2843.4	2808.2	2783.0	2752.9	2727.7
7.5°	2606.9	2556.6	2501.2	2445.9	2395.5	2345.2	2289.8	2239.5	2214.4	2189.2	2164.0
10°	2264.7	2214.4	2169.1	2118.7	2083.5	2053.3	2018.1	1982.9	1952.7	1922.5	1892.3
12.5°	2093.6	2058.3	2023.1	1987.9	1947.6	1912.4	1872.1	1831.9	1796.7	1766.5	1731.2
15°	1987.9	1937.6	1882.2	1831.9	1776.5	1726.2	1670.8	1615.5	1575.2	1540.0	1499.7
17.5°	1862.1	1786.6	1716.1	1640.6	1580.2	1519.9	1454.4	1394.0	1348.7	1298.4	1253.1
20°	1721.2	1635.6	1545.0	1459.5	1389.0	1323.6	1253.1	1182.7	1132.3	1077.0	1026.7
22.5°	1600.4	1489.7	1373.9	1258.2	1182.7	1107.2	1026.7	951.2	905.9	855.5	810.3
25°	1469.5	1348.7	1222.9	1097.1	1021.6	941.1	865.6	785.1	749.9	719.7	684.4
27.5°	1399.1	1278.3	1152.5	1031.7	961.2	885.7	815.3	739.8	714.6	684.4	659.3
30°	1258.2	1142.4	1021.6	900.8	850.5	805.2	754.9	704.6	694.5	689.5	679.4
32.5°	1132.3	1011.6	890.8	770.0	724.7	679.4	634.1	588.8	583.8	573.7	568.7
35°	1066.9	951.2	830.4	714.6	674.4	629.1	588.8	543.5	533.5	518.4	508.3
37.5°	1051.8	931.0	805.2	684.4	644.2	603.9	558.6	518.4	508.3	498.2	488.2
40°	1011.6	895.8	785.1	669.3	629.1	588.8	543.5	503.3	493.2	483.1	473.1
42.5°	981.4	870.6	754.9	639.1	603.9	568.7	528.4	493.2	483.1	473.1	458.0
45°	956.2	840.4	719.7	603.9	578.8	553.6	523.4	498.2	488.2	473.1	463.0
47.5°	915.9	805.2	689.5	573.7	548.6	528.4	503.3	478.1	468.0	458.0	447.9
50°	885.7	770.0	654.2	538.5	518.4	498.2	478.1	458.0	458.0	463.0	463.0
52.5°	845.5	734.8	624.0	513.3	493.2	473.1	452.9	432.8	437.8	442.9	447.9
55°	810.3	704.6	593.9	483.1	463.0	442.9	417.7	397.6	402.6	407.6	412.7
57.5°	795.2	684.4	573.7	463.0	442.9	417.7	397.6	372.4	372.4	372.4	372.4
60°	785.1	669.3	558.6	442.9	417.7	397.6	372.4	347.3	342.2	342.2	337.2
62.5°	780.1	664.3	553.6	437.8	407.6	382.5	352.3	322.1	317.1	312.0	307.0
65°	759.9	654.2	543.5	432.8	397.6	367.4	332.2	296.9	291.9	291.9	286.9
67.5°	754.9	644.2	538.5	427.8	392.5	352.3	317.1	276.8	271.8	266.7	261.7
70°	714.6	619.0	518.4	417.7	377.4	342.2	302.0	261.7	256.7	246.6	241.6
72.5°	664.3	578.8	488.2	397.6	357.3	317.1	276.8	236.5	231.5	226.5	216.4
75°	588.8	508.3	427.8	347.3	312.0	281.8	246.6	211.4	206.3	201.3	191.2
77.5°	483.1	417.7	357.3	291.9	266.7	241.6	216.4	191.2	186.2	181.2	171.1
80°	342.2	302.0	266.7	226.5	211.4	191.2	176.1	156.0	156.0	151.0	151.0
82.5°	226.5	206.3	186.2	166.1	156.0	145.9	135.9	125.8	125.8	120.8	120.8
85°	161.0	151.0	135.9	125.8	120.8	110.7	105.7	95.6	95.6	95.6	95.6
87.5°	75.5	75.5	70.5	70.5	65.4	65.4	60.4	55.4	55.4	55.4	55.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3341.7	3326.6	3311.5	3291.3	3276.2	3256.1	3231.0	3210.8	3185.7	3185.7	3180.6
5°	2697.5	2682.4	2667.3	2647.2	2632.1	2611.9	2596.8	2576.7	2556.6	2556.6	2551.5
7.5°	2138.9	2108.7	2078.5	2043.2	2013.1	1992.9	1972.8	1947.6	1927.5	1912.4	1897.3
10°	1862.1	1831.9	1796.7	1766.5	1731.2	1706.1	1680.9	1650.7	1625.5	1605.4	1585.3
12.5°	1696.0	1660.8	1625.5	1590.3	1555.1	1519.9	1489.7	1454.4	1419.2	1394.0	1368.9
15°	1459.5	1424.2	1389.0	1353.8	1318.6	1278.3	1238.0	1192.7	1152.5	1132.3	1117.2
17.5°	1202.8	1167.6	1127.3	1092.1	1051.8	1021.6	991.4	961.2	931.0	910.9	895.8
20°	971.3	931.0	890.8	850.5	810.3	790.1	770.0	749.9	729.7	714.6	704.6
22.5°	759.9	734.8	714.6	689.5	664.3	649.2	639.1	624.0	608.9	608.9	608.9
25°	649.2	634.1	624.0	608.9	593.9	588.8	583.8	573.7	568.7	563.7	563.7
27.5°	629.1	614.0	598.9	583.8	568.7	563.7	558.6	548.6	543.5	543.5	543.5
30°	669.3	664.3	659.3	654.2	649.2	639.1	624.0	614.0	598.9	588.8	578.8
32.5°	558.6	553.6	553.6	548.6	543.5	553.6	558.6	568.7	573.7	578.8	583.8
35°	493.2	483.1	473.1	463.0	452.9	447.9	442.9	437.8	432.8	432.8	427.8
37.5°	478.1	468.0	458.0	447.9	437.8	432.8	427.8	422.7	417.7	417.7	412.7
40°	463.0	452.9	447.9	437.8	427.8	422.7	417.7	407.6	402.6	397.6	397.6
42.5°	447.9	442.9	432.8	427.8	417.7	412.7	407.6	397.6	392.5	387.5	382.5
45°	447.9	437.8	427.8	417.7	407.6	402.6	392.5	387.5	377.4	377.4	372.4
47.5°	437.8	427.8	417.7	407.6	397.6	392.5	382.5	377.4	367.4	362.3	357.3
50°	463.0	447.9	427.8	412.7	392.5	387.5	377.4	372.4	362.3	357.3	352.3
52.5°	452.9	437.8	417.7	402.6	382.5	372.4	367.4	357.3	347.3	342.2	337.2
55°	417.7	402.6	392.5	377.4	362.3	352.3	342.2	332.2	322.1	317.1	317.1
57.5°	372.4	367.4	362.3	357.3	352.3	342.2	332.2	317.1	307.0	302.0	296.9
60°	332.2	337.2	342.2	347.3	352.3	337.2	322.1	307.0	291.9	286.9	281.8
62.5°	302.0	312.0	322.1	327.1	337.2	322.1	307.0	291.9	276.8	271.8	266.7
65°	281.8	286.9	286.9	291.9	291.9	281.8	276.8	266.7	256.7	251.6	251.6
67.5°	256.7	256.7	256.7	251.6	251.6	246.6	246.6	241.6	236.5	231.5	231.5
70°	231.5	231.5	231.5	226.5	226.5	221.4	221.4	216.4	211.4	211.4	206.3
72.5°	211.4	211.4	206.3	206.3	201.3	201.3	201.3	196.3	196.3	191.2	191.2
75°	186.2	186.2	181.2	181.2	176.1	176.1	176.1	171.1	171.1	171.1	166.1
77.5°	166.1	166.1	161.0	161.0	156.0	156.0	156.0	151.0	151.0	145.9	145.9
80°	145.9	145.9	140.9	140.9	135.9	135.9	130.8	130.8	125.8	125.8	120.8
82.5°	115.8	115.8	115.8	115.8	115.8	110.7	110.7	105.7	100.7	100.7	95.6
85°	95.6	95.6	95.6	90.6	90.6	90.6	85.6	85.6	80.5	75.5	75.5
87.5°	55.4	55.4	55.4	50.3	50.3	50.3	50.3	50.3	50.3	50.3	45.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3180.6	3175.6	3155.5	3135.3	3155.5	3175.6	3175.6	3175.6	3170.6	3170.6	3170.6
5°	2551.5	2546.5	2536.4	2526.4	2526.4	2521.3	2531.4	2541.5	2551.5	2561.6	2571.7
7.5°	1877.2	1862.1	1847.0	1831.9	1841.9	1847.0	1862.1	1872.1	1887.2	1897.3	1922.5
10°	1565.1	1545.0	1529.9	1514.8	1504.8	1494.7	1484.6	1479.6	1469.5	1459.5	1469.5
12.5°	1338.7	1313.5	1288.4	1258.2	1253.1	1248.1	1238.0	1228.0	1217.9	1207.8	1202.8
15°	1097.1	1077.0	1066.9	1051.8	1031.7	1011.6	1001.5	996.5	986.4	976.3	971.3
17.5°	875.7	855.5	840.4	825.4	820.3	810.3	810.3	810.3	810.3	810.3	810.3
20°	689.5	674.4	674.4	669.3	669.3	664.3	669.3	674.4	674.4	679.4	684.4
22.5°	603.9	603.9	598.9	593.9	598.9	598.9	603.9	608.9	614.0	619.0	624.0
25°	558.6	553.6	558.6	563.7	563.7	563.7	568.7	568.7	573.7	573.7	573.7
27.5°	538.5	538.5	543.5	543.5	548.6	548.6	548.6	543.5	543.5	538.5	538.5
30°	568.7	558.6	558.6	558.6	553.6	548.6	543.5	543.5	538.5	533.5	528.4
32.5°	588.8	593.9	588.8	578.8	573.7	563.7	558.6	548.6	543.5	533.5	523.4
35°	427.8	422.7	432.8	437.8	442.9	447.9	452.9	458.0	458.0	463.0	463.0
37.5°	412.7	407.6	407.6	402.6	402.6	402.6	402.6	402.6	397.6	397.6	402.6
40°	392.5	387.5	387.5	382.5	382.5	377.4	377.4	377.4	377.4	377.4	377.4
42.5°	377.4	372.4	372.4	372.4	372.4	367.4	367.4	362.3	362.3	357.3	357.3
45°	372.4	367.4	362.3	357.3	357.3	352.3	352.3	352.3	347.3	347.3	347.3
47.5°	352.3	347.3	347.3	342.2	342.2	337.2	337.2	337.2	332.2	332.2	332.2
50°	342.2	337.2	337.2	332.2	332.2	327.1	327.1	327.1	322.1	322.1	322.1
52.5°	327.1	322.1	322.1	322.1	317.1	312.0	312.0	312.0	307.0	307.0	307.0
55°	312.0	307.0	307.0	307.0	302.0	296.9	296.9	296.9	291.9	291.9	291.9
57.5°	291.9	286.9	286.9	281.8	281.8	281.8	281.8	281.8	276.8	276.8	276.8
60°	276.8	271.8	271.8	266.7	266.7	261.7	261.7	261.7	261.7	261.7	261.7
62.5°	261.7	256.7	251.6	246.6	251.6	251.6	251.6	251.6	246.6	246.6	246.6
65°	246.6	241.6	236.5	231.5	231.5	231.5	231.5	231.5	231.5	231.5	231.5
67.5°	226.5	221.4	216.4	211.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4
70°	206.3	201.3	201.3	196.3	196.3	191.2	191.2	196.3	196.3	196.3	196.3
72.5°	186.2	181.2	181.2	176.1	176.1	176.1	176.1	176.1	176.1	176.1	176.1
75°	166.1	161.0	161.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0
77.5°	140.9	135.9	135.9	135.9	135.9	135.9	135.9	140.9	140.9	140.9	140.9
80°	120.8	115.8	115.8	115.8	115.8	115.8	115.8	115.8	115.8	115.8	115.8
82.5°	95.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6
85°	70.5	65.4	65.4	65.4	70.5	70.5	70.5	70.5	70.5	70.5	70.5
87.5°	45.3	40.3	40.3	40.3	45.3	45.3	45.3	45.3	40.3	40.3	40.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3170.6	3170.6	3170.6	3165.5	3160.5	3155.5	3150.4	3165.5	3175.6	3190.7	3200.8
5°	2576.7	2586.8	2591.8	2606.9	2622.0	2637.1	2652.2	2662.3	2672.3	2677.4	2687.4
7.5°	1942.6	1967.8	1987.9	2008.0	2028.2	2043.2	2063.4	2078.5	2093.6	2108.7	2123.8
10°	1474.6	1484.6	1489.7	1509.8	1524.9	1545.0	1560.1	1575.2	1590.3	1600.4	1615.5
12.5°	1197.8	1187.7	1182.7	1182.7	1182.7	1182.7	1182.7	1192.7	1202.8	1212.9	1222.9
15°	966.3	961.2	956.2	951.2	946.1	936.1	931.0	941.1	951.2	961.2	971.3
17.5°	810.3	810.3	810.3	805.2	800.2	795.2	790.1	795.2	800.2	800.2	805.2
20°	694.5	699.5	704.6	709.6	709.6	714.6	714.6	719.7	724.7	724.7	729.7
22.5°	624.0	629.1	629.1	629.1	634.1	634.1	634.1	639.1	644.2	649.2	654.2
25°	568.7	568.7	563.7	563.7	568.7	568.7	568.7	568.7	573.7	573.7	573.7
27.5°	538.5	533.5	533.5	533.5	533.5	528.4	528.4	528.4	528.4	528.4	528.4
30°	523.4	518.4	513.3	508.3	508.3	503.3	498.2	498.2	498.2	498.2	498.2
32.5°	518.4	508.3	498.2	493.2	493.2	488.2	483.1	478.1	478.1	473.1	468.0
35°	463.0	458.0	458.0	452.9	447.9	442.9	437.8	437.8	437.8	432.8	432.8
37.5°	402.6	407.6	407.6	407.6	412.7	412.7	412.7	412.7	417.7	417.7	417.7
40°	377.4	377.4	377.4	382.5	387.5	387.5	392.5	392.5	397.6	397.6	397.6
42.5°	357.3	352.3	352.3	357.3	357.3	362.3	362.3	367.4	372.4	372.4	377.4
45°	347.3	342.2	342.2	342.2	342.2	337.2	337.2	342.2	347.3	352.3	357.3
47.5°	327.1	327.1	322.1	322.1	322.1	322.1	322.1	322.1	327.1	327.1	327.1
50°	317.1	317.1	312.0	312.0	312.0	312.0	312.0	312.0	312.0	312.0	312.0
52.5°	307.0	302.0	302.0	302.0	302.0	296.9	296.9	296.9	296.9	296.9	296.9
55°	291.9	286.9	286.9	286.9	286.9	286.9	286.9	286.9	291.9	291.9	291.9
57.5°	276.8	271.8	271.8	271.8	276.8	276.8	276.8	276.8	281.8	281.8	281.8
60°	261.7	261.7	261.7	261.7	261.7	261.7	261.7	266.7	266.7	271.8	271.8
62.5°	246.6	246.6	246.6	246.6	251.6	251.6	251.6	251.6	256.7	256.7	256.7
65°	231.5	231.5	231.5	231.5	236.5	236.5	236.5	236.5	236.5	236.5	236.5
67.5°	216.4	216.4	216.4	216.4	216.4	216.4	216.4	221.4	221.4	226.5	226.5
70°	196.3	191.2	191.2	196.3	196.3	201.3	201.3	206.3	206.3	211.4	211.4
72.5°	176.1	176.1	176.1	176.1	176.1	176.1	176.1	181.2	186.2	186.2	191.2
75°	156.0	156.0	156.0	156.0	161.0	161.0	161.0	166.1	166.1	171.1	171.1
77.5°	140.9	135.9	135.9	135.9	140.9	140.9	140.9	145.9	145.9	151.0	151.0
80°	115.8	115.8	115.8	115.8	120.8	120.8	120.8	120.8	125.8	125.8	125.8
82.5°	95.6	95.6	95.6	95.6	95.6	95.6	95.6	95.6	100.7	100.7	100.7
85°	70.5	70.5	70.5	70.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5
87.5°	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3	50.3	50.3	50.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3200.8	3200.8	3200.8	3200.8	3210.8	3215.9	3225.9	3231.0	3225.9	3220.9	3210.8
5°	2692.5	2697.5	2697.5	2702.5	2702.5	2702.5	2702.5	2702.5	2712.6	2722.7	2732.7
7.5°	2128.8	2133.8	2138.9	2143.9	2143.9	2143.9	2138.9	2138.9	2143.9	2143.9	2148.9
10°	1630.6	1650.7	1665.8	1680.9	1670.8	1655.7	1645.7	1630.6	1630.6	1630.6	1625.5
12.5°	1233.0	1238.0	1248.1	1253.1	1248.1	1248.1	1243.1	1238.0	1243.1	1253.1	1258.2
15°	976.3	976.3	981.4	981.4	986.4	991.4	991.4	996.5	1006.5	1011.6	1021.6
17.5°	810.3	815.3	815.3	820.3	820.3	825.4	825.4	825.4	835.4	845.5	860.6
20°	729.7	729.7	729.7	729.7	729.7	724.7	724.7	719.7	724.7	734.8	739.8
22.5°	654.2	659.3	659.3	659.3	654.2	649.2	639.1	634.1	634.1	639.1	639.1
25°	573.7	568.7	568.7	563.7	563.7	568.7	568.7	568.7	573.7	573.7	578.8
27.5°	528.4	523.4	523.4	518.4	518.4	523.4	523.4	523.4	523.4	523.4	523.4
30°	493.2	493.2	488.2	483.1	488.2	488.2	493.2	493.2	498.2	498.2	503.3
32.5°	468.0	463.0	463.0	458.0	463.0	463.0	468.0	468.0	473.1	478.1	478.1
35°	432.8	432.8	432.8	432.8	432.8	432.8	427.8	427.8	427.8	427.8	427.8
37.5°	412.7	412.7	407.6	402.6	402.6	402.6	402.6	402.6	397.6	392.5	387.5
40°	397.6	392.5	392.5	387.5	382.5	382.5	377.4	372.4	372.4	367.4	367.4
42.5°	377.4	372.4	372.4	367.4	362.3	362.3	357.3	352.3	352.3	352.3	347.3
45°	352.3	352.3	347.3	342.2	342.2	342.2	337.2	337.2	337.2	337.2	332.2
47.5°	327.1	327.1	322.1	322.1	322.1	322.1	317.1	317.1	317.1	317.1	317.1
50°	312.0	312.0	312.0	312.0	312.0	312.0	307.0	307.0	307.0	307.0	307.0
52.5°	296.9	296.9	296.9	296.9	296.9	296.9	296.9	296.9	296.9	296.9	296.9
55°	291.9	291.9	291.9	291.9	291.9	291.9	286.9	286.9	286.9	291.9	291.9
57.5°	281.8	281.8	276.8	276.8	276.8	276.8	276.8	276.8	276.8	276.8	276.8
60°	271.8	271.8	271.8	271.8	271.8	271.8	271.8	271.8	271.8	271.8	271.8
62.5°	256.7	256.7	256.7	256.7	256.7	261.7	261.7	261.7	261.7	261.7	256.7
65°	236.5	241.6	241.6	241.6	241.6	241.6	241.6	241.6	241.6	241.6	241.6
67.5°	226.5	226.5	226.5	226.5	226.5	226.5	226.5	226.5	226.5	226.5	226.5
70°	211.4	211.4	206.3	206.3	206.3	211.4	211.4	211.4	211.4	211.4	211.4
72.5°	191.2	191.2	191.2	191.2	191.2	191.2	191.2	191.2	191.2	196.3	196.3
75°	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1
77.5°	151.0	151.0	145.9	145.9	145.9	151.0	151.0	151.0	151.0	156.0	156.0
80°	125.8	125.8	125.8	125.8	125.8	125.8	125.8	125.8	125.8	130.8	130.8
82.5°	100.7	100.7	100.7	100.7	100.7	100.7	100.7	100.7	100.7	105.7	105.7
85°	75.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5	85.6	85.6
87.5°	50.3	50.3	50.3	50.3	50.3	50.3	45.3	45.3	45.3	45.3	40.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3205.8	3210.8	3215.9	3215.9	3220.9	3225.9	3225.9	3246.0	3266.2	3276.2	3286.3
5°	2742.8	2737.8	2737.8	2732.7	2727.7	2742.8	2757.9	2788.1	2818.3	2823.3	2833.4
7.5°	2148.9	2154.0	2159.0	2159.0	2164.0	2148.9	2128.8	2133.8	2138.9	2164.0	2184.2
10°	1625.5	1630.6	1635.6	1635.6	1640.6	1635.6	1625.5	1640.6	1655.7	1675.9	1701.0
12.5°	1263.2	1278.3	1293.4	1303.5	1318.6	1328.6	1333.6	1353.8	1368.9	1394.0	1419.2
15°	1031.7	1041.8	1051.8	1061.9	1072.0	1082.0	1092.1	1112.2	1132.3	1162.5	1192.7
17.5°	870.6	870.6	875.7	875.7	875.7	885.7	895.8	905.9	910.9	941.1	971.3
20°	744.8	739.8	734.8	729.7	724.7	734.8	739.8	744.8	749.9	770.0	785.1
22.5°	639.1	639.1	644.2	644.2	644.2	639.1	629.1	634.1	634.1	644.2	659.3
25°	578.8	578.8	578.8	573.7	573.7	578.8	583.8	583.8	578.8	583.8	588.8
27.5°	523.4	528.4	528.4	533.5	533.5	538.5	538.5	538.5	538.5	543.5	548.6
30°	503.3	503.3	508.3	508.3	508.3	513.3	518.4	518.4	518.4	523.4	533.5
32.5°	483.1	488.2	493.2	498.2	503.3	508.3	508.3	513.3	513.3	518.4	523.4
35°	427.8	422.7	422.7	417.7	412.7	412.7	412.7	412.7	407.6	412.7	412.7
37.5°	382.5	382.5	382.5	377.4	377.4	382.5	382.5	382.5	382.5	387.5	387.5
40°	362.3	362.3	362.3	362.3	362.3	362.3	362.3	367.4	367.4	372.4	377.4
42.5°	347.3	347.3	347.3	347.3	347.3	352.3	352.3	352.3	352.3	357.3	357.3
45°	332.2	332.2	332.2	332.2	332.2	332.2	332.2	337.2	337.2	342.2	347.3
47.5°	317.1	317.1	317.1	317.1	317.1	322.1	327.1	327.1	327.1	332.2	332.2
50°	307.0	307.0	307.0	307.0	307.0	312.0	312.0	317.1	317.1	322.1	327.1
52.5°	296.9	296.9	296.9	296.9	296.9	302.0	302.0	307.0	307.0	312.0	317.1
55°	291.9	291.9	291.9	286.9	286.9	291.9	291.9	296.9	296.9	302.0	302.0
57.5°	276.8	276.8	276.8	276.8	276.8	276.8	276.8	281.8	281.8	286.9	291.9
60°	271.8	271.8	266.7	266.7	261.7	266.7	266.7	271.8	271.8	276.8	276.8
62.5°	256.7	256.7	256.7	251.6	251.6	256.7	256.7	256.7	256.7	261.7	266.7
65°	241.6	241.6	241.6	236.5	236.5	241.6	241.6	241.6	241.6	246.6	251.6
67.5°	226.5	226.5	226.5	221.4	221.4	221.4	221.4	226.5	226.5	231.5	236.5
70°	211.4	211.4	211.4	206.3	206.3	206.3	201.3	206.3	211.4	216.4	216.4
72.5°	196.3	196.3	196.3	191.2	191.2	191.2	186.2	191.2	191.2	196.3	196.3
75°	171.1	171.1	171.1	171.1	171.1	171.1	166.1	166.1	166.1	171.1	171.1
77.5°	156.0	156.0	156.0	151.0	151.0	151.0	145.9	145.9	145.9	151.0	151.0
80°	130.8	130.8	130.8	125.8	125.8	125.8	120.8	120.8	120.8	125.8	125.8
82.5°	105.7	105.7	105.7	100.7	100.7	100.7	95.6	95.6	95.6	100.7	100.7
85°	85.6	85.6	85.6	85.6	85.6	85.6	80.5	80.5	80.5	85.6	90.6
87.5°	40.3	40.3	45.3	45.3	45.3	45.3	40.3	40.3	35.2	35.2	40.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3296.4	3306.4	3331.6	3351.7	3376.9	3397.0	3412.1	3432.3	3447.4	3462.5	3472.5
5°	2838.4	2843.4	2868.6	2893.8	2913.9	2939.1	2974.3	3009.5	3044.7	3080.0	3105.1
7.5°	2209.3	2229.5	2259.7	2294.9	2325.1	2355.3	2390.5	2430.8	2466.0	2501.2	2536.4
10°	1721.2	1741.3	1771.5	1801.7	1826.8	1857.0	1897.3	1937.6	1977.8	2018.1	2058.3
12.5°	1444.4	1469.5	1504.8	1540.0	1570.2	1605.4	1655.7	1701.0	1751.4	1796.7	1847.0
15°	1217.9	1248.1	1293.4	1343.7	1389.0	1434.3	1484.6	1535.0	1580.2	1630.6	1680.9
17.5°	1001.5	1031.7	1072.0	1117.2	1157.5	1197.8	1258.2	1313.5	1373.9	1429.3	1484.6
20°	805.2	820.3	860.6	900.8	941.1	981.4	1026.7	1072.0	1117.2	1162.5	1233.0
22.5°	669.3	679.4	699.5	714.6	734.8	749.9	795.2	840.4	880.7	926.0	991.4
25°	588.8	593.9	608.9	619.0	634.1	644.2	674.4	699.5	729.7	754.9	815.3
27.5°	548.6	553.6	558.6	563.7	568.7	573.7	593.9	614.0	629.1	649.2	704.6
30°	538.5	543.5	558.6	568.7	583.8	593.9	603.9	614.0	624.0	634.1	669.3
32.5°	528.4	533.5	533.5	528.4	528.4	523.4	533.5	538.5	548.6	553.6	583.8
35°	417.7	417.7	422.7	427.8	432.8	437.8	452.9	463.0	478.1	488.2	513.3
37.5°	392.5	392.5	397.6	407.6	412.7	417.7	427.8	437.8	447.9	458.0	483.1
40°	377.4	382.5	387.5	392.5	397.6	402.6	412.7	417.7	427.8	432.8	452.9
42.5°	362.3	362.3	367.4	377.4	382.5	387.5	397.6	402.6	412.7	417.7	437.8
45°	352.3	357.3	362.3	367.4	367.4	372.4	382.5	392.5	397.6	407.6	427.8
47.5°	337.2	337.2	347.3	352.3	362.3	367.4	377.4	382.5	392.5	397.6	417.7
50°	327.1	332.2	342.2	347.3	357.3	362.3	377.4	387.5	402.6	412.7	422.7
52.5°	317.1	322.1	332.2	337.2	347.3	352.3	372.4	392.5	407.6	427.8	427.8
55°	307.0	307.0	317.1	332.2	342.2	352.3	362.3	377.4	387.5	397.6	397.6
57.5°	291.9	296.9	307.0	322.1	332.2	342.2	352.3	362.3	367.4	377.4	372.4
60°	281.8	281.8	296.9	312.0	327.1	342.2	342.2	342.2	337.2	337.2	337.2
62.5°	266.7	271.8	291.9	317.1	337.2	357.3	342.2	327.1	312.0	296.9	302.0
65°	256.7	261.7	271.8	286.9	296.9	307.0	296.9	291.9	281.8	271.8	276.8
67.5°	236.5	241.6	246.6	246.6	251.6	251.6	251.6	251.6	251.6	251.6	256.7
70°	221.4	221.4	221.4	226.5	226.5	226.5	226.5	226.5	226.5	226.5	231.5
72.5°	201.3	201.3	201.3	201.3	201.3	201.3	201.3	201.3	201.3	201.3	206.3
75°	176.1	176.1	176.1	176.1	176.1	176.1	176.1	176.1	176.1	176.1	181.2
77.5°	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	151.0	151.0	156.0
80°	130.8	130.8	130.8	130.8	125.8	125.8	125.8	125.8	125.8	125.8	130.8
82.5°	105.7	105.7	105.7	105.7	100.7	100.7	100.7	100.7	95.6	95.6	100.7
85°	95.6	100.7	100.7	105.7	105.7	105.7	100.7	95.6	90.6	85.6	85.6
87.5°	40.3	40.3	40.3	40.3	35.2	35.2	35.2	35.2	35.2	35.2	35.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3487.6	3497.7	3507.7	3522.8	3543.0	3558.1	3573.2	3603.4	3638.6	3668.8	3699.0
5°	3130.3	3155.5	3180.6	3210.8	3241.0	3266.2	3296.4	3356.8	3417.2	3472.5	3532.9
7.5°	2566.6	2601.9	2632.1	2682.4	2727.7	2778.0	2823.3	2898.8	2969.3	3044.7	3115.2
10°	2098.6	2138.9	2179.1	2244.6	2315.0	2380.4	2445.9	2506.3	2571.7	2632.1	2692.5
12.5°	1897.3	1942.6	1992.9	2033.2	2078.5	2118.7	2159.0	2229.5	2299.9	2370.4	2440.8
15°	1731.2	1781.6	1831.9	1882.2	1927.5	1977.8	2023.1	2083.5	2148.9	2209.3	2269.7
17.5°	1540.0	1590.3	1645.7	1701.0	1756.4	1811.7	1867.1	1952.7	2038.2	2118.7	2204.3
20°	1298.4	1368.9	1434.3	1509.8	1585.3	1660.8	1736.3	1826.8	1917.4	2003.0	2093.6
22.5°	1056.9	1122.3	1187.7	1278.3	1368.9	1454.4	1545.0	1665.8	1781.6	1902.3	2018.1
25°	880.7	941.1	1001.5	1102.1	1197.8	1298.4	1394.0	1540.0	1680.9	1826.8	1967.8
27.5°	759.9	815.3	870.6	976.3	1082.0	1182.7	1288.4	1449.4	1605.4	1766.5	1922.5
30°	704.6	739.8	775.0	875.7	976.3	1072.0	1172.6	1328.6	1484.6	1640.6	1796.7
32.5°	614.0	644.2	674.4	765.0	855.5	941.1	1031.7	1192.7	1348.7	1509.8	1665.8
35°	543.5	568.7	593.9	679.4	759.9	845.5	926.0	1087.0	1248.1	1409.1	1570.2
37.5°	503.3	528.4	548.6	624.0	704.6	780.1	855.5	1016.6	1172.6	1333.6	1489.7
40°	473.1	488.2	508.3	583.8	654.2	729.7	800.2	946.1	1097.1	1243.1	1389.0
42.5°	452.9	473.1	488.2	553.6	624.0	689.5	754.9	895.8	1036.7	1172.6	1313.5
45°	447.9	468.0	488.2	543.5	598.9	649.2	704.6	840.4	976.3	1112.2	1248.1
47.5°	437.8	452.9	473.1	518.4	558.6	603.9	644.2	780.1	915.9	1046.8	1182.7
50°	432.8	437.8	447.9	488.2	528.4	568.7	608.9	744.8	880.7	1016.6	1152.5
52.5°	427.8	427.8	427.8	463.0	498.2	528.4	563.7	699.5	840.4	976.3	1112.2
55°	397.6	392.5	392.5	427.8	458.0	493.2	523.4	659.3	795.2	926.0	1061.9
57.5°	367.4	362.3	357.3	387.5	417.7	447.9	478.1	614.0	754.9	890.8	1026.7
60°	337.2	332.2	332.2	362.3	387.5	417.7	442.9	583.8	719.7	860.6	996.5
62.5°	302.0	307.0	307.0	332.2	362.3	387.5	412.7	553.6	699.5	840.4	981.4
65°	276.8	281.8	281.8	312.0	342.2	372.4	402.6	538.5	679.4	815.3	951.2
67.5°	256.7	261.7	261.7	296.9	327.1	362.3	392.5	513.3	639.1	759.9	880.7
70°	236.5	236.5	241.6	276.8	312.0	347.3	382.5	488.2	593.9	694.5	800.2
72.5°	211.4	216.4	221.4	256.7	286.9	322.1	352.3	447.9	543.5	639.1	734.8
75°	186.2	191.2	196.3	226.5	256.7	286.9	317.1	407.6	493.2	583.8	669.3
77.5°	166.1	171.1	176.1	201.3	226.5	251.6	276.8	342.2	412.7	478.1	543.5
80°	135.9	135.9	140.9	161.0	181.2	196.3	216.4	261.7	307.0	347.3	392.5
82.5°	100.7	105.7	105.7	120.8	130.8	145.9	156.0	181.2	201.3	226.5	246.6
85°	85.6	80.5	80.5	90.6	95.6	105.7	110.7	125.8	135.9	151.0	161.0
87.5°	35.2	30.2	30.2	35.2	45.3	50.3	55.4	55.4	60.4	60.4	60.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3714.1	3724.1	3739.2	3749.3	3774.5	3794.6	3819.8	3839.9	3855.0	3880.2	3870.1
5°	3578.2	3623.5	3668.8	3714.1	3749.3	3784.5	3814.7	3850.0	3890.2	3965.7	3985.8
7.5°	3175.6	3236.0	3291.3	3351.7	3422.2	3492.6	3563.1	3633.6	3699.0	3794.6	3855.0
10°	2778.0	2863.6	2944.1	3029.6	3095.1	3160.5	3220.9	3286.3	3376.9	3472.5	3583.2
12.5°	2526.4	2611.9	2697.5	2783.0	2878.7	2969.3	3064.9	3155.5	3241.0	3316.5	3442.3
15°	2360.3	2455.9	2546.5	2637.1	2752.9	2863.6	2979.3	3090.0	3215.9	3316.5	3402.1
17.5°	2320.0	2435.8	2546.5	2662.3	2783.0	2903.8	3024.6	3145.4	3271.2	3422.2	3532.9
20°	2249.6	2405.6	2561.6	2717.6	2873.6	3024.6	3180.6	3331.6	3497.7	3678.9	3729.2
22.5°	2209.3	2395.5	2586.8	2773.0	2984.4	3200.8	3412.1	3623.5	3799.6	3935.5	4086.5
25°	2204.3	2435.8	2672.3	2903.8	3170.6	3432.3	3699.0	3960.7	4187.2	4323.0	4443.8
27.5°	2199.3	2481.1	2757.9	3034.7	3361.8	3683.9	4011.0	4333.1	4544.5	4740.7	4841.4
30°	2138.9	2476.1	2818.3	3155.5	3522.8	3890.2	4257.6	4625.0	4841.4	4977.3	5027.6
32.5°	2063.4	2461.0	2858.5	3256.1	3673.8	4091.5	4504.2	4921.9	5093.0	5208.8	5168.5
35°	2003.0	2440.8	2873.6	3306.4	3749.3	4197.2	4640.1	5083.0	5329.6	5490.6	5425.2
37.5°	1947.6	2405.6	2863.6	3321.5	3839.9	4358.3	4876.6	5395.0	5631.5	5802.6	5727.1
40°	1882.2	2370.4	2863.6	3351.7	3945.6	4534.4	5128.3	5717.1	6024.1	6170.0	6054.3
42.5°	1826.8	2335.1	2848.5	3356.8	3990.9	4625.0	5259.1	5893.2	6235.4	6441.8	6295.8
45°	1756.4	2264.7	2767.9	3276.2	3975.8	4675.3	5369.8	6069.4	6466.9	6628.0	6426.7
47.5°	1680.9	2184.2	2682.4	3180.6	3925.5	4670.3	5415.1	6159.9	6527.3	6718.6	6532.4
50°	1655.7	2159.0	2657.2	3160.5	3965.7	4776.0	5581.2	6386.4	6653.1	6809.2	6562.6
52.5°	1650.7	2184.2	2722.7	3256.1	4066.4	4871.6	5681.8	6487.1	6703.5	6869.5	6648.1
55°	1635.6	2214.4	2788.1	3361.8	4207.3	5057.8	5903.3	6748.8	6965.2	7085.9	6919.9
57.5°	1650.7	2274.8	2893.8	3517.8	4388.5	5259.1	6129.7	7000.4	7262.1	7347.6	7312.4
60°	1660.8	2325.1	2984.4	3648.7	4499.2	5349.7	6200.2	7050.7	7322.5	7533.9	7574.1
62.5°	1635.6	2289.8	2939.1	3593.3	4363.3	5133.3	5903.3	6673.3	7121.2	7433.2	7614.4
65°	1560.1	2164.0	2773.0	3376.9	4086.5	4801.1	5510.7	6220.3	6693.4	7156.4	7302.4
67.5°	1394.0	1907.4	2420.7	2934.0	3553.0	4172.1	4786.0	5405.0	5998.9	6446.8	6648.1
70°	1207.8	1610.4	2018.1	2420.7	2984.4	3548.0	4111.7	4675.3	5198.7	5691.9	5883.1
72.5°	1051.8	1363.8	1680.9	1992.9	2395.5	2793.1	3195.7	3593.3	4212.3	4705.5	4891.7
75°	895.8	1122.3	1343.7	1570.2	1847.0	2123.8	2395.5	2672.3	3110.2	3553.0	3739.2
77.5°	689.5	840.4	986.4	1132.3	1323.6	1509.8	1701.0	1887.2	2194.2	2526.4	2622.0
80°	478.1	563.7	644.2	729.7	880.7	1031.7	1182.7	1333.6	1535.0	1721.2	1867.1
82.5°	296.9	352.3	402.6	452.9	573.7	694.5	810.3	931.0	1011.6	1021.6	1167.6
85°	191.2	226.5	256.7	286.9	357.3	432.8	503.3	573.7	513.3	478.1	568.7
87.5°	75.5	95.6	110.7	125.8	120.8	115.8	110.7	105.7	90.6	80.5	100.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3880.2	3895.3	3910.4	3920.4	3935.5	3940.6	3945.6	3945.6	3950.6	3955.7	3965.7
5°	4066.4	4096.6	4126.8	4151.9	4182.1	4207.3	4227.4	4252.6	4272.7	4272.7	4267.7
7.5°	3910.4	3985.8	4061.3	4136.8	4212.3	4267.7	4318.0	4373.4	4423.7	4433.8	4443.8
10°	3704.0	3784.5	3860.0	3940.6	4016.0	4101.6	4182.1	4262.6	4348.2	4363.3	4383.4
12.5°	3512.8	3608.4	3704.0	3794.6	3890.2	3950.6	4011.0	4066.4	4126.8	4167.0	4207.3
15°	3507.7	3588.3	3668.8	3744.3	3824.8	3860.0	3895.3	3925.5	3960.7	3960.7	3965.7
17.5°	3623.5	3673.8	3724.1	3769.4	3819.8	3824.8	3834.9	3839.9	3844.9	3829.8	3814.7
20°	3850.0	3870.1	3890.2	3910.4	3930.5	3895.3	3865.1	3829.8	3794.6	3754.3	3719.1
22.5°	4182.1	4136.8	4091.5	4046.2	4000.9	3940.6	3875.1	3814.7	3749.3	3699.0	3648.7
25°	4494.1	4438.8	4383.4	4328.1	4272.7	4141.9	4011.0	3875.1	3744.3	3688.9	3633.6
27.5°	4911.9	4826.3	4740.7	4655.2	4569.6	4393.5	4217.3	4041.2	3865.1	3769.4	3678.9
30°	5012.5	4916.9	4821.3	4720.6	4625.0	4453.9	4287.8	4116.7	3945.6	3834.9	3729.2
32.5°	5158.4	5047.7	4937.0	4826.3	4715.6	4549.5	4383.4	4212.3	4046.2	3945.6	3839.9
35°	5400.0	5274.2	5148.4	5017.5	4891.7	4720.6	4554.5	4383.4	4212.3	4096.6	3985.8
37.5°	5606.4	5460.4	5314.5	5168.5	5022.6	4871.6	4715.6	4564.6	4408.6	4292.8	4182.1
40°	5837.9	5676.8	5515.8	5359.8	5198.7	5057.8	4916.9	4770.9	4630.0	4539.4	4448.8
42.5°	6039.2	5842.9	5651.6	5460.4	5264.1	5168.5	5077.9	4982.3	4886.7	4841.4	4791.1
45°	6180.1	5998.9	5812.7	5631.5	5450.3	5379.9	5309.4	5239.0	5168.5	5213.8	5259.1
47.5°	6240.5	6094.5	5953.6	5812.7	5666.7	5691.9	5717.1	5737.2	5762.4	5822.8	5888.2
50°	6295.8	6215.3	6129.7	6049.2	5963.7	6059.3	6149.9	6245.5	6341.1	6466.9	6592.8
52.5°	6406.5	6361.2	6321.0	6275.7	6230.4	6396.5	6562.6	6728.6	6894.7	7035.6	7176.5
55°	6738.7	6703.5	6668.2	6628.0	6592.8	6829.3	7060.8	7297.3	7533.9	7679.8	7825.7
57.5°	7196.7	7176.5	7151.4	7131.2	7106.1	7337.6	7564.0	7790.5	8022.0	8162.9	8308.9
60°	7543.9	7549.0	7549.0	7554.0	7554.0	7730.1	7906.3	8087.4	8263.6	8384.4	8510.2
62.5°	7730.1	7720.1	7710.0	7699.9	7689.9	7835.8	7981.8	8127.7	8273.6	8364.2	8454.8
65°	7528.8	7584.2	7639.5	7694.9	7750.3	7770.4	7785.5	7805.6	7820.7	7876.1	7931.4
67.5°	6854.4	6965.2	7070.9	7181.6	7287.3	7211.8	7141.3	7065.8	6990.3	7005.4	7015.5
70°	6104.6	6230.4	6361.2	6487.1	6612.9	6436.7	6260.6	6079.4	5903.3	5842.9	5782.5
72.5°	5148.4	5259.1	5374.9	5485.6	5596.3	5379.9	5168.5	4952.1	4735.7	4630.0	4524.3
75°	3935.5	4066.4	4202.2	4333.1	4463.9	4222.4	3975.8	3734.2	3487.6	3417.2	3351.7
77.5°	2868.6	3024.6	3180.6	3336.6	3492.6	3276.2	3059.8	2838.4	2622.0	2581.7	2541.5
80°	2088.5	2209.3	2325.1	2445.9	2561.6	2435.8	2310.0	2184.2	2058.3	2053.3	2048.3
82.5°	1409.1	1514.8	1615.5	1721.2	1821.8	1771.5	1726.2	1675.9	1625.5	1675.9	1731.2
85°	724.7	870.6	1021.6	1167.6	1313.5	1298.4	1288.4	1273.3	1258.2	1323.6	1384.0
87.5°	145.9	271.8	397.6	518.4	644.2	614.0	583.8	548.6	518.4	538.5	553.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3970.7	3975.8	3975.8	3975.8	3975.8	3975.8	3965.7	3960.7	3950.6	3940.6	3925.5
5°	4267.7	4262.6	4242.5	4222.4	4197.2	4177.1	4162.0	4141.9	4126.8	4106.6	4076.4
7.5°	4453.9	4463.9	4428.7	4398.5	4363.3	4328.1	4292.8	4257.6	4222.4	4187.2	4116.7
10°	4398.5	4413.6	4393.5	4373.4	4348.2	4328.1	4287.8	4242.5	4202.2	4157.0	4071.4
12.5°	4242.5	4282.8	4272.7	4262.6	4252.6	4242.5	4217.3	4187.2	4162.0	4131.8	4036.2
15°	3965.7	3965.7	3970.7	3975.8	3975.8	3980.8	3985.8	3990.9	3995.9	4000.9	3945.6
17.5°	3799.6	3784.5	3784.5	3784.5	3784.5	3784.5	3804.7	3829.8	3850.0	3870.1	3855.0
20°	3678.9	3643.6	3638.6	3638.6	3633.6	3628.5	3663.8	3704.0	3739.2	3774.5	3794.6
22.5°	3598.3	3548.0	3543.0	3537.9	3532.9	3527.9	3573.2	3618.5	3663.8	3709.1	3779.5
25°	3578.2	3522.8	3527.9	3532.9	3532.9	3537.9	3573.2	3608.4	3643.6	3678.9	3799.6
27.5°	3583.2	3492.6	3497.7	3502.7	3502.7	3507.7	3563.1	3613.4	3668.8	3719.1	3870.1
30°	3618.5	3512.8	3502.7	3492.6	3482.6	3472.5	3548.0	3623.5	3699.0	3774.5	3890.2
32.5°	3739.2	3638.6	3613.4	3588.3	3563.1	3537.9	3628.5	3714.1	3804.7	3890.2	3985.8
35°	3870.1	3759.4	3749.3	3739.2	3724.1	3714.1	3794.6	3880.2	3960.7	4041.2	4126.8
37.5°	4066.4	3955.7	3945.6	3930.5	3920.4	3905.3	3995.9	4081.5	4172.1	4257.6	4333.1
40°	4358.3	4267.7	4262.6	4262.6	4257.6	4252.6	4323.0	4398.5	4469.0	4539.4	4589.8
42.5°	4745.8	4700.5	4715.6	4735.7	4750.8	4765.9	4821.3	4881.7	4937.0	4992.4	4977.3
45°	5304.4	5349.7	5354.7	5359.8	5364.8	5369.8	5384.9	5405.0	5420.1	5435.2	5374.9
47.5°	5948.6	6009.0	6039.2	6069.4	6094.5	6124.7	6104.6	6079.4	6059.3	6034.1	5883.1
50°	6713.5	6839.3	6834.3	6829.3	6819.2	6814.2	6773.9	6733.7	6688.4	6648.1	6426.7
52.5°	7317.4	7458.4	7483.5	7508.7	7533.9	7559.0	7483.5	7408.0	7327.5	7252.0	6975.2
55°	7966.7	8112.6	8117.6	8122.7	8122.7	8127.7	8022.0	7916.3	7805.6	7699.9	7413.1
57.5°	8449.8	8590.7	8575.6	8565.5	8550.4	8535.3	8409.5	8283.7	8157.9	8032.1	7745.2
60°	8631.0	8751.7	8721.6	8691.4	8656.1	8625.9	8530.3	8434.7	8334.0	8238.4	7961.6
62.5°	8545.4	8636.0	8590.7	8550.4	8505.2	8459.9	8339.1	8213.3	8092.5	7966.7	7765.4
65°	7981.8	8037.1	7976.7	7921.4	7866.0	7805.6	7705.0	7604.3	7498.6	7398.0	7262.1
67.5°	7030.6	7040.7	7035.6	7030.6	7025.6	7020.5	6874.6	6728.6	6577.7	6431.7	6421.6
70°	5727.1	5666.7	5676.8	5691.9	5702.0	5712.0	5601.3	5495.6	5384.9	5274.2	5324.5
72.5°	4418.7	4313.0	4338.1	4368.3	4393.5	4418.7	4328.1	4242.5	4151.9	4061.3	4131.8
75°	3281.3	3215.9	3241.0	3271.2	3296.4	3321.5	3286.3	3251.1	3210.8	3175.6	3241.0
77.5°	2501.2	2461.0	2466.0	2466.0	2471.0	2471.0	2476.1	2486.1	2491.2	2496.2	2566.6
80°	2038.2	2033.2	2028.2	2023.1	2013.1	2008.0	2058.3	2108.7	2159.0	2209.3	2244.6
82.5°	1781.6	1831.9	1801.7	1776.5	1746.3	1716.1	1761.4	1806.7	1852.0	1897.3	1882.2
85°	1449.4	1509.8	1454.4	1399.1	1338.7	1283.3	1323.6	1358.8	1399.1	1434.3	1414.2
87.5°	573.7	588.8	498.2	412.7	322.1	231.5	367.4	498.2	634.1	765.0	785.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832

CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5	3623.5
2.5°	3910.4	3890.2	3875.1	3870.1	3860.0	3855.0	3844.9	3834.9	3819.8	3809.7	3794.6
5°	4041.2	4011.0	3975.8	3925.5	3880.2	3829.8	3779.5	3734.2	3688.9	3638.6	3593.3
7.5°	4046.2	3975.8	3905.3	3839.9	3769.4	3704.0	3633.6	3573.2	3507.7	3442.3	3381.9
10°	3990.9	3905.3	3819.8	3734.2	3653.7	3568.1	3482.6	3412.1	3336.6	3261.1	3190.7
12.5°	3945.6	3850.0	3754.3	3653.7	3558.1	3457.4	3356.8	3286.3	3215.9	3145.4	3074.9
15°	3890.2	3829.8	3774.5	3683.9	3593.3	3502.7	3412.1	3316.5	3225.9	3130.3	3034.7
17.5°	3844.9	3829.8	3814.7	3754.3	3694.0	3628.5	3568.1	3472.5	3376.9	3276.2	3180.6
20°	3819.8	3839.9	3860.0	3829.8	3799.6	3764.4	3734.2	3663.8	3593.3	3517.8	3447.4
22.5°	3850.0	3925.5	3995.9	4000.9	4011.0	4016.0	4021.1	3955.7	3890.2	3819.8	3754.3
25°	3920.4	4041.2	4162.0	4227.4	4292.8	4363.3	4428.7	4388.5	4348.2	4307.9	4267.7
27.5°	4016.0	4167.0	4318.0	4413.6	4504.2	4599.8	4695.4	4690.4	4685.4	4675.3	4670.3
30°	4000.9	4116.7	4232.4	4348.2	4463.9	4579.7	4695.4	4755.8	4811.2	4871.6	4932.0
32.5°	4086.5	4182.1	4282.8	4403.6	4524.3	4650.2	4770.9	4896.8	5017.5	5143.4	5269.2
35°	4217.3	4302.9	4393.5	4524.3	4660.2	4791.1	4926.9	5077.9	5233.9	5390.0	5540.9
37.5°	4413.6	4489.1	4569.6	4680.3	4796.1	4906.8	5022.6	5244.0	5465.4	5691.9	5913.3
40°	4640.1	4690.4	4740.7	4846.4	4952.1	5057.8	5163.5	5440.3	5717.1	5993.9	6270.7
42.5°	4967.2	4952.1	4937.0	5022.6	5113.2	5198.7	5289.3	5540.9	5792.6	6044.2	6295.8
45°	5314.5	5254.1	5193.7	5233.9	5279.2	5319.5	5364.8	5621.5	5878.1	6139.8	6396.5
47.5°	5732.2	5581.2	5430.2	5395.0	5359.8	5319.5	5284.3	5561.1	5837.9	6119.7	6396.5
50°	6205.2	5978.8	5757.3	5666.7	5571.1	5480.5	5384.9	5611.4	5842.9	6074.4	6300.9
52.5°	6698.4	6416.6	6139.8	5998.9	5858.0	5712.0	5571.1	5762.4	5958.6	6154.9	6346.2
55°	7121.2	6834.3	6542.4	6376.3	6210.3	6044.2	5878.1	6069.4	6260.6	6451.8	6643.1
57.5°	7458.4	7171.5	6884.6	6728.6	6567.6	6411.6	6250.5	6431.7	6617.9	6804.1	6985.3
60°	7689.9	7413.1	7136.3	6985.3	6834.3	6683.3	6532.4	6748.8	6965.2	7186.6	7403.0
62.5°	7569.1	7367.8	7166.5	7101.0	7035.6	6965.2	6899.7	7106.1	7307.4	7513.7	7720.1
65°	7126.2	6990.3	6854.4	6919.9	6990.3	7055.8	7126.2	7262.1	7398.0	7538.9	7674.8
67.5°	6406.5	6396.5	6381.4	6527.3	6673.3	6824.3	6970.2	7060.8	7146.3	7236.9	7327.5
70°	5374.9	5430.2	5480.5	5732.2	5983.8	6235.4	6487.1	6522.3	6557.5	6592.8	6628.0
72.5°	4207.3	4277.7	4353.2	4685.4	5012.5	5344.7	5676.8	5656.7	5636.5	5611.4	5591.3
75°	3311.5	3376.9	3447.4	3754.3	4061.3	4368.3	4675.3	4589.8	4509.2	4423.7	4338.1
77.5°	2642.1	2712.6	2788.1	3074.9	3361.8	3653.7	3940.6	3734.2	3527.9	3321.5	3115.2
80°	2274.8	2310.0	2340.2	2536.4	2727.7	2924.0	3120.2	2908.9	2692.5	2476.1	2264.7
82.5°	1867.1	1847.0	1831.9	1947.6	2063.4	2179.1	2294.9	2093.6	1892.3	1685.9	1484.6
85°	1394.0	1373.9	1353.8	1414.2	1474.6	1540.0	1600.4	1368.9	1137.4	900.8	669.3
87.5°	810.3	830.4	850.5	915.9	981.4	1051.8	1117.2	880.7	644.2	402.6	166.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671832  
 CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671832  
CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	3623.5	3623.5
2.5°	3764.4	3739.2
5°	3558.1	3522.8
7.5°	3331.6	3286.3
10°	3125.3	3064.9
12.5°	2994.4	2918.9
15°	2944.1	2853.5
17.5°	3095.1	3009.5
20°	3326.6	3210.8
22.5°	3608.4	3467.5
25°	4096.6	3925.5
27.5°	4494.1	4318.0
30°	4740.7	4549.5
32.5°	5012.5	4760.9
35°	5294.3	5052.8
37.5°	5636.5	5364.8
40°	5988.8	5707.0
42.5°	6109.6	5928.4
45°	6225.4	6054.3
47.5°	6250.5	6109.6
50°	6275.7	6255.6
52.5°	6346.2	6341.1
55°	6648.1	6653.1
57.5°	7020.5	7050.7
60°	7362.7	7327.5
62.5°	7538.9	7357.7
65°	7418.1	7166.5
67.5°	7055.8	6784.0
70°	6260.6	5893.2
72.5°	5269.2	4947.1
75°	4061.3	3789.6
77.5°	2888.7	2662.3
80°	2033.2	1806.7
82.5°	1303.5	1122.3
85°	588.8	513.3
87.5°	166.1	161.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671832  
CATALOG NUMBER: CCP-SA-2E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)