

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671788

Luminaire Tested: **CCP-SA-2E-722-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671788
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2E-722-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/ SLR distribution lens
Light Source: (32) 2200K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8358.1 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3

Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 11.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P671788
CATALOG NUMBER: CCP-SA-2E-722-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1719.7	0.0	1719.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	6638.4	0.0	6638.4
	% Fixture	79.4	0.0	79.4
Total	Lumens	8358.1	0.0	8358.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.4	2.5
10°-20°	437.9	5.2
20°-30°	640.6	7.7
30°-40°	902.6	10.8
40°-50°	1240.2	14.8
50°-60°	1690.4	20.2
60°-70°	1850.2	22.1
70°-80°	1068.5	12.8
80°-90°	320.3	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8358.1	100.0
0°-180°	8358.1	100.0



REPORT NUMBER: P671788


CATALOG NUMBER: CCP-SA-2E-722-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	858.4	10.3			
FM (30°-60°)	3050.1	36.5			
FH (60°-80°)	2457.8	29.4			G2/5000
FVH (80°-90°)	272.1	3.3			G3/500
BL (0°-30°)	427.5	5.1	B1/500		
BM (30°-60°)	783.1	9.4	B1/1000		
BH (60°-80°)	460.9	5.5	B1/500		G1/500
BVH (80°-90°)	48.2	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short





REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2754.3	2739.5	2728.4	2717.3	2702.4	2691.3	2676.5	2661.7	2643.1	2628.3	2609.8
5°	2594.9	2550.4	2506.0	2480.0	2450.4	2424.4	2394.7	2361.4	2328.0	2290.9	2257.6
7.5°	2420.7	2365.1	2309.5	2265.0	2216.8	2172.3	2124.1	2083.4	2042.6	2001.8	1961.0
10°	2257.6	2205.7	2153.8	2098.2	2038.9	1983.3	1924.0	1868.3	1812.7	1757.1	1701.5
12.5°	2150.1	2087.1	2027.7	1964.7	1905.4	1842.4	1779.4	1727.5	1675.6	1620.0	1568.1
15°	2101.9	2042.6	1987.0	1924.0	1860.9	1797.9	1734.9	1675.6	1620.0	1560.7	1501.4
17.5°	2216.8	2131.5	2046.3	1964.7	1883.2	1801.6	1720.1	1645.9	1571.8	1497.6	1423.5
20°	2365.1	2257.6	2153.8	2053.7	1949.9	1849.8	1746.0	1642.2	1538.4	1434.6	1330.8
22.5°	2554.1	2431.8	2313.2	2183.4	2050.0	1920.2	1786.8	1657.0	1527.3	1393.8	1264.1
25°	2891.5	2746.9	2602.3	2417.0	2227.9	2042.6	1853.5	1683.0	1516.2	1345.7	1175.1
27.5°	3180.6	2984.2	2791.4	2569.0	2346.6	2124.1	1901.7	1705.2	1512.5	1316.0	1119.5
30°	3351.2	3158.4	2965.6	2695.0	2428.1	2157.5	1886.9	1668.2	1453.2	1234.4	1015.7
32.5°	3506.9	3291.8	3076.8	2780.3	2480.0	2183.4	1883.2	1642.2	1405.0	1164.0	923.1
35°	3721.9	3484.6	3251.1	2906.3	2561.6	2216.8	1872.1	1623.7	1371.6	1123.2	871.2
37.5°	3951.7	3658.8	3369.7	2987.9	2606.0	2224.2	1842.4	1597.7	1353.1	1108.4	863.7
40°	4203.8	3847.9	3495.7	3073.1	2654.2	2231.6	1809.0	1564.4	1319.7	1071.3	826.7
42.5°	4366.9	3981.4	3595.8	3139.9	2687.6	2231.6	1775.7	1534.7	1293.8	1049.1	808.1
45°	4459.6	4085.2	3714.5	3221.4	2728.4	2235.3	1742.3	1505.1	1267.8	1026.8	789.6
47.5°	4500.3	4151.9	3803.4	3284.4	2769.2	2250.2	1731.2	1490.2	1245.6	1004.6	759.9
50°	4607.8	4300.2	3992.5	3436.4	2884.1	2328.0	1772.0	1512.5	1256.7	997.2	737.7
52.5°	4670.9	4407.7	4144.5	3573.6	3002.7	2431.8	1860.9	1571.8	1282.6	993.5	704.3
55°	4900.7	4648.6	4396.5	3788.6	3176.9	2569.0	1957.3	1638.5	1319.7	997.2	678.4
57.5°	5193.6	4926.7	4663.5	4007.3	3351.2	2695.0	2038.9	1697.8	1353.1	1012.0	667.3
60°	5397.4	5138.0	4882.2	4185.2	3484.6	2787.7	2087.1	1731.2	1375.3	1015.7	659.9
62.5°	5419.7	5086.1	4756.1	4077.7	3399.4	2717.3	2038.9	1694.1	1349.4	1000.9	656.1
65°	5278.8	4889.6	4500.3	3851.6	3202.9	2554.1	1905.4	1590.3	1275.2	956.4	641.3
67.5°	4997.1	4541.1	4085.2	3492.0	2898.9	2305.8	1712.7	1442.0	1175.1	904.5	633.9
70°	4340.9	3940.6	3543.9	3028.7	2517.1	2001.8	1486.5	1264.1	1045.4	823.0	600.5
72.5°	3644.0	3269.6	2898.9	2480.0	2064.8	1645.9	1227.0	1060.2	893.4	722.9	556.1
75°	2791.4	2509.7	2231.6	1920.2	1608.9	1293.8	982.4	860.0	737.7	615.4	493.0
77.5°	1961.0	1809.0	1660.8	1427.2	1193.7	960.1	726.6	645.0	563.5	481.9	400.4
80°	1330.8	1245.6	1164.0	997.2	830.4	659.9	493.0	441.1	385.5	333.6	278.0
82.5°	826.7	823.0	815.5	700.6	585.7	470.8	355.9	311.4	270.6	226.1	181.6
85°	378.1	441.1	500.5	437.4	374.4	311.4	248.4	218.7	189.1	155.7	126.0
87.5°	118.6	144.6	166.8	159.4	148.3	140.9	129.7	111.2	92.7	74.1	55.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2594.9	2583.8	2569.0	2554.1	2535.6	2520.8	2502.3	2483.7	2480.0	2472.6	2468.9
5°	2235.3	2213.1	2187.2	2164.9	2142.7	2116.7	2094.5	2068.5	2050.0	2027.7	2009.2
7.5°	1920.2	1883.2	1842.4	1801.6	1764.6	1727.5	1686.7	1649.6	1631.1	1612.6	1594.0
10°	1668.2	1631.1	1597.7	1560.7	1534.7	1512.5	1486.5	1460.6	1438.3	1416.1	1393.8
12.5°	1542.1	1516.2	1490.2	1464.3	1434.6	1408.7	1379.0	1349.4	1323.4	1301.2	1275.2
15°	1464.3	1427.2	1386.4	1349.4	1308.6	1271.5	1230.7	1190.0	1160.3	1134.4	1104.7
17.5°	1371.6	1316.0	1264.1	1208.5	1164.0	1119.5	1071.3	1026.8	993.5	956.4	923.1
20°	1267.8	1204.8	1138.1	1075.0	1023.1	975.0	923.1	871.2	834.1	793.3	756.2
22.5°	1178.8	1097.3	1012.0	926.8	871.2	815.5	756.2	700.6	667.3	630.2	596.8
25°	1082.5	993.5	900.8	808.1	752.5	693.2	637.6	578.3	552.3	530.1	504.2
27.5°	1030.6	941.6	848.9	759.9	708.0	652.4	600.5	544.9	526.4	504.2	485.6
30°	926.8	841.5	752.5	663.6	626.5	593.1	556.1	519.0	511.6	507.9	500.5
32.5°	834.1	745.1	656.1	567.2	533.8	500.5	467.1	433.7	430.0	422.6	418.9
35°	785.9	700.6	611.7	526.4	496.7	463.4	433.7	400.4	392.9	381.8	374.4
37.5°	774.8	685.8	593.1	504.2	474.5	444.8	411.5	381.8	374.4	367.0	359.6
40°	745.1	659.9	578.3	493.0	463.4	433.7	400.4	370.7	363.3	355.9	348.5
42.5°	722.9	641.3	556.1	470.8	444.8	418.9	389.2	363.3	355.9	348.5	337.3
45°	704.3	619.1	530.1	444.8	426.3	407.8	385.5	367.0	359.6	348.5	341.0
47.5°	674.7	593.1	507.9	422.6	404.1	389.2	370.7	352.2	344.8	337.3	329.9
50°	652.4	567.2	481.9	396.7	381.8	367.0	352.2	337.3	337.3	341.0	341.0
52.5°	622.8	541.2	459.7	378.1	363.3	348.5	333.6	318.8	322.5	326.2	329.9
55°	596.8	519.0	437.4	355.9	341.0	326.2	307.7	292.9	296.6	300.3	304.0
57.5°	585.7	504.2	422.6	341.0	326.2	307.7	292.9	274.3	274.3	274.3	274.3
60°	578.3	493.0	411.5	326.2	307.7	292.9	274.3	255.8	252.1	252.1	248.4
62.5°	574.6	489.3	407.8	322.5	300.3	281.7	259.5	237.3	233.5	229.8	226.1
65°	559.8	481.9	400.4	318.8	292.9	270.6	244.7	218.7	215.0	215.0	211.3
67.5°	556.1	474.5	396.7	315.1	289.1	259.5	233.5	203.9	200.2	196.5	192.8
70°	526.4	456.0	381.8	307.7	278.0	252.1	222.4	192.8	189.1	181.6	177.9
72.5°	489.3	426.3	359.6	292.9	263.2	233.5	203.9	174.2	170.5	166.8	159.4
75°	433.7	374.4	315.1	255.8	229.8	207.6	181.6	155.7	152.0	148.3	140.9
77.5°	355.9	307.7	263.2	215.0	196.5	177.9	159.4	140.9	137.2	133.5	126.0
80°	252.1	222.4	196.5	166.8	155.7	140.9	129.7	114.9	114.9	111.2	111.2
82.5°	166.8	152.0	137.2	122.3	114.9	107.5	100.1	92.7	92.7	89.0	89.0
85°	118.6	111.2	100.1	92.7	89.0	81.6	77.8	70.4	70.4	70.4	70.4
87.5°	55.6	55.6	51.9	51.9	48.2	48.2	44.5	40.8	40.8	40.8	40.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2461.5	2450.4	2439.2	2424.4	2413.3	2398.5	2379.9	2365.1	2346.6	2346.6	2342.8
5°	1987.0	1975.9	1964.7	1949.9	1938.8	1924.0	1912.8	1898.0	1883.2	1883.2	1879.5
7.5°	1575.5	1553.2	1531.0	1505.1	1482.8	1468.0	1453.2	1434.6	1419.8	1408.7	1397.6
10°	1371.6	1349.4	1323.4	1301.2	1275.2	1256.7	1238.2	1215.9	1197.4	1182.5	1167.7
12.5°	1249.3	1223.3	1197.4	1171.4	1145.5	1119.5	1097.3	1071.3	1045.4	1026.8	1008.3
15°	1075.0	1049.1	1023.1	997.2	971.2	941.6	911.9	878.6	848.9	834.1	823.0
17.5°	886.0	860.0	830.4	804.4	774.8	752.5	730.3	708.0	685.8	671.0	659.9
20°	715.5	685.8	656.1	626.5	596.8	582.0	567.2	552.3	537.5	526.4	519.0
22.5°	559.8	541.2	526.4	507.9	489.3	478.2	470.8	459.7	448.6	448.6	448.6
25°	478.2	467.1	459.7	448.6	437.4	433.7	430.0	422.6	418.9	415.2	415.2
27.5°	463.4	452.3	441.1	430.0	418.9	415.2	411.5	404.1	400.4	400.4	400.4
30°	493.0	489.3	485.6	481.9	478.2	470.8	459.7	452.3	441.1	433.7	426.3
32.5°	411.5	407.8	407.8	404.1	400.4	407.8	411.5	418.9	422.6	426.3	430.0
35°	363.3	355.9	348.5	341.0	333.6	329.9	326.2	322.5	318.8	318.8	315.1
37.5°	352.2	344.8	337.3	329.9	322.5	318.8	315.1	311.4	307.7	307.7	304.0
40°	341.0	333.6	329.9	322.5	315.1	311.4	307.7	300.3	296.6	292.9	292.9
42.5°	329.9	326.2	318.8	315.1	307.7	304.0	300.3	292.9	289.1	285.4	281.7
45°	329.9	322.5	315.1	307.7	300.3	296.6	289.1	285.4	278.0	278.0	274.3
47.5°	322.5	315.1	307.7	300.3	292.9	289.1	281.7	278.0	270.6	266.9	263.2
50°	341.0	329.9	315.1	304.0	289.1	285.4	278.0	274.3	266.9	263.2	259.5
52.5°	333.6	322.5	307.7	296.6	281.7	274.3	270.6	263.2	255.8	252.1	248.4
55°	307.7	296.6	289.1	278.0	266.9	259.5	252.1	244.7	237.3	233.5	233.5
57.5°	274.3	270.6	266.9	263.2	259.5	252.1	244.7	233.5	226.1	222.4	218.7
60°	244.7	248.4	252.1	255.8	259.5	248.4	237.3	226.1	215.0	211.3	207.6
62.5°	222.4	229.8	237.3	241.0	248.4	237.3	226.1	215.0	203.9	200.2	196.5
65°	207.6	211.3	211.3	215.0	215.0	207.6	203.9	196.5	189.1	185.4	185.4
67.5°	189.1	189.1	189.1	185.4	185.4	181.6	181.6	177.9	174.2	170.5	170.5
70°	170.5	170.5	170.5	166.8	166.8	163.1	163.1	159.4	155.7	155.7	152.0
72.5°	155.7	155.7	152.0	152.0	148.3	148.3	148.3	144.6	144.6	140.9	140.9
75°	137.2	137.2	133.5	133.5	129.7	129.7	129.7	126.0	126.0	126.0	122.3
77.5°	122.3	122.3	118.6	118.6	114.9	114.9	114.9	111.2	111.2	107.5	107.5
80°	107.5	107.5	103.8	103.8	100.1	100.1	96.4	96.4	92.7	92.7	89.0
82.5°	85.3	85.3	85.3	85.3	85.3	81.6	81.6	77.8	74.1	74.1	70.4
85°	70.4	70.4	70.4	66.7	66.7	66.7	63.0	63.0	59.3	55.6	55.6
87.5°	40.8	40.8	40.8	37.1	37.1	37.1	37.1	37.1	37.1	37.1	33.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2342.8	2339.1	2324.3	2309.5	2324.3	2339.1	2339.1	2339.1	2335.4	2335.4	2335.4
5°	1879.5	1875.8	1868.3	1860.9	1860.9	1857.2	1864.6	1872.1	1879.5	1886.9	1894.3
7.5°	1382.7	1371.6	1360.5	1349.4	1356.8	1360.5	1371.6	1379.0	1390.1	1397.6	1416.1
10°	1152.9	1138.1	1126.9	1115.8	1108.4	1101.0	1093.6	1089.9	1082.5	1075.0	1082.5
12.5°	986.1	967.5	949.0	926.8	923.1	919.3	911.9	904.5	897.1	889.7	886.0
15°	808.1	793.3	785.9	774.8	759.9	745.1	737.7	734.0	726.6	719.2	715.5
17.5°	645.0	630.2	619.1	608.0	604.2	596.8	596.8	596.8	596.8	596.8	596.8
20°	507.9	496.7	496.7	493.0	493.0	489.3	493.0	496.7	496.7	500.5	504.2
22.5°	444.8	444.8	441.1	437.4	441.1	441.1	444.8	448.6	452.3	456.0	459.7
25°	411.5	407.8	411.5	415.2	415.2	415.2	418.9	418.9	422.6	422.6	422.6
27.5°	396.7	396.7	400.4	400.4	404.1	404.1	404.1	400.4	400.4	396.7	396.7
30°	418.9	411.5	411.5	411.5	407.8	404.1	400.4	400.4	396.7	392.9	389.2
32.5°	433.7	437.4	433.7	426.3	422.6	415.2	411.5	404.1	400.4	392.9	385.5
35°	315.1	311.4	318.8	322.5	326.2	329.9	333.6	337.3	337.3	341.0	341.0
37.5°	304.0	300.3	300.3	296.6	296.6	296.6	296.6	296.6	292.9	292.9	296.6
40°	289.1	285.4	285.4	281.7	281.7	278.0	278.0	278.0	278.0	278.0	278.0
42.5°	278.0	274.3	274.3	274.3	274.3	270.6	270.6	266.9	266.9	263.2	263.2
45°	274.3	270.6	266.9	263.2	263.2	259.5	259.5	259.5	255.8	255.8	255.8
47.5°	259.5	255.8	255.8	252.1	252.1	248.4	248.4	248.4	244.7	244.7	244.7
50°	252.1	248.4	248.4	244.7	244.7	241.0	241.0	241.0	237.3	237.3	237.3
52.5°	241.0	237.3	237.3	237.3	233.5	229.8	229.8	229.8	226.1	226.1	226.1
55°	229.8	226.1	226.1	226.1	222.4	218.7	218.7	218.7	215.0	215.0	215.0
57.5°	215.0	211.3	211.3	207.6	207.6	207.6	207.6	207.6	203.9	203.9	203.9
60°	203.9	200.2	200.2	196.5	196.5	192.8	192.8	192.8	192.8	192.8	192.8
62.5°	192.8	189.1	185.4	181.6	185.4	185.4	185.4	185.4	181.6	181.6	181.6
65°	181.6	177.9	174.2	170.5	170.5	170.5	170.5	170.5	170.5	170.5	170.5
67.5°	166.8	163.1	159.4	155.7	159.4	159.4	159.4	159.4	159.4	159.4	159.4
70°	152.0	148.3	148.3	144.6	144.6	140.9	140.9	144.6	144.6	144.6	144.6
72.5°	137.2	133.5	133.5	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7
75°	122.3	118.6	118.6	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.9
77.5°	103.8	100.1	100.1	100.1	100.1	100.1	100.1	103.8	103.8	103.8	103.8
80°	89.0	85.3	85.3	85.3	85.3	85.3	85.3	85.3	85.3	85.3	85.3
82.5°	70.4	66.7	66.7	66.7	66.7	66.7	66.7	66.7	66.7	66.7	66.7
85°	51.9	48.2	48.2	48.2	51.9	51.9	51.9	51.9	51.9	51.9	51.9
87.5°	33.4	29.7	29.7	29.7	33.4	33.4	33.4	33.4	29.7	29.7	29.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2335.4	2335.4	2335.4	2331.7	2328.0	2324.3	2320.6	2331.7	2339.1	2350.3	2357.7
5°	1898.0	1905.4	1909.1	1920.2	1931.4	1942.5	1953.6	1961.0	1968.4	1972.1	1979.6
7.5°	1430.9	1449.5	1464.3	1479.1	1493.9	1505.1	1519.9	1531.0	1542.1	1553.2	1564.4
10°	1086.2	1093.6	1097.3	1112.1	1123.2	1138.1	1149.2	1160.3	1171.4	1178.8	1190.0
12.5°	882.3	874.9	871.2	871.2	871.2	871.2	871.2	878.6	886.0	893.4	900.8
15°	711.8	708.0	704.3	700.6	696.9	689.5	685.8	693.2	700.6	708.0	715.5
17.5°	596.8	596.8	596.8	593.1	589.4	585.7	582.0	585.7	589.4	589.4	593.1
20°	511.6	515.3	519.0	522.7	522.7	526.4	526.4	530.1	533.8	533.8	537.5
22.5°	459.7	463.4	463.4	463.4	467.1	467.1	467.1	470.8	474.5	478.2	481.9
25°	418.9	418.9	415.2	415.2	418.9	418.9	418.9	418.9	422.6	422.6	422.6
27.5°	396.7	392.9	392.9	392.9	392.9	389.2	389.2	389.2	389.2	389.2	389.2
30°	385.5	381.8	378.1	374.4	374.4	370.7	367.0	367.0	367.0	367.0	367.0
32.5°	381.8	374.4	367.0	363.3	363.3	359.6	355.9	352.2	352.2	348.5	344.8
35°	341.0	337.3	337.3	333.6	329.9	326.2	322.5	322.5	322.5	318.8	318.8
37.5°	296.6	300.3	300.3	300.3	304.0	304.0	304.0	304.0	307.7	307.7	307.7
40°	278.0	278.0	278.0	281.7	285.4	285.4	289.1	289.1	292.9	292.9	292.9
42.5°	263.2	259.5	259.5	263.2	263.2	266.9	266.9	270.6	274.3	274.3	278.0
45°	255.8	252.1	252.1	252.1	252.1	248.4	248.4	252.1	255.8	259.5	263.2
47.5°	241.0	241.0	237.3	237.3	237.3	237.3	237.3	237.3	241.0	241.0	241.0
50°	233.5	233.5	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8
52.5°	226.1	222.4	222.4	222.4	222.4	218.7	218.7	218.7	218.7	218.7	218.7
55°	215.0	211.3	211.3	211.3	211.3	211.3	211.3	211.3	215.0	215.0	215.0
57.5°	203.9	200.2	200.2	200.2	203.9	203.9	203.9	203.9	207.6	207.6	207.6
60°	192.8	192.8	192.8	192.8	192.8	192.8	192.8	196.5	196.5	200.2	200.2
62.5°	181.6	181.6	181.6	181.6	185.4	185.4	185.4	185.4	189.1	189.1	189.1
65°	170.5	170.5	170.5	170.5	174.2	174.2	174.2	174.2	174.2	174.2	174.2
67.5°	159.4	159.4	159.4	159.4	159.4	159.4	159.4	163.1	163.1	166.8	166.8
70°	144.6	140.9	140.9	144.6	144.6	148.3	148.3	152.0	152.0	155.7	155.7
72.5°	129.7	129.7	129.7	129.7	129.7	129.7	129.7	133.5	137.2	137.2	140.9
75°	114.9	114.9	114.9	114.9	118.6	118.6	118.6	122.3	122.3	126.0	126.0
77.5°	103.8	100.1	100.1	100.1	103.8	103.8	103.8	107.5	107.5	111.2	111.2
80°	85.3	85.3	85.3	85.3	89.0	89.0	89.0	89.0	92.7	92.7	92.7
82.5°	70.4	70.4	70.4	70.4	70.4	70.4	70.4	70.4	74.1	74.1	74.1
85°	51.9	51.9	51.9	51.9	55.6	55.6	55.6	55.6	55.6	55.6	55.6
87.5°	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	37.1	37.1	37.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2357.7	2357.7	2357.7	2357.7	2365.1	2368.8	2376.2	2379.9	2376.2	2372.5	2365.1
5°	1983.3	1987.0	1987.0	1990.7	1990.7	1990.7	1990.7	1990.7	1998.1	2005.5	2012.9
7.5°	1568.1	1571.8	1575.5	1579.2	1579.2	1579.2	1575.5	1575.5	1579.2	1579.2	1582.9
10°	1201.1	1215.9	1227.0	1238.2	1230.7	1219.6	1212.2	1201.1	1201.1	1201.1	1197.4
12.5°	908.2	911.9	919.3	923.1	919.3	919.3	915.6	911.9	915.6	923.1	926.8
15°	719.2	719.2	722.9	722.9	726.6	730.3	730.3	734.0	741.4	745.1	752.5
17.5°	596.8	600.5	600.5	604.2	604.2	608.0	608.0	608.0	615.4	622.8	633.9
20°	537.5	537.5	537.5	537.5	537.5	533.8	533.8	530.1	533.8	541.2	544.9
22.5°	481.9	485.6	485.6	485.6	481.9	478.2	470.8	467.1	467.1	470.8	470.8
25°	422.6	418.9	418.9	415.2	415.2	418.9	418.9	418.9	422.6	422.6	426.3
27.5°	389.2	385.5	385.5	381.8	381.8	385.5	385.5	385.5	385.5	385.5	385.5
30°	363.3	363.3	359.6	355.9	359.6	359.6	363.3	363.3	367.0	367.0	370.7
32.5°	344.8	341.0	341.0	337.3	341.0	341.0	344.8	344.8	348.5	352.2	352.2
35°	318.8	318.8	318.8	318.8	318.8	318.8	315.1	315.1	315.1	315.1	315.1
37.5°	304.0	304.0	300.3	296.6	296.6	296.6	296.6	296.6	292.9	289.1	285.4
40°	292.9	289.1	289.1	285.4	281.7	281.7	278.0	274.3	274.3	270.6	270.6
42.5°	278.0	274.3	274.3	270.6	266.9	266.9	263.2	259.5	259.5	259.5	255.8
45°	259.5	259.5	255.8	252.1	252.1	252.1	248.4	248.4	248.4	248.4	244.7
47.5°	241.0	241.0	237.3	237.3	237.3	237.3	233.5	233.5	233.5	233.5	233.5
50°	229.8	229.8	229.8	229.8	229.8	229.8	226.1	226.1	226.1	226.1	226.1
52.5°	218.7	218.7	218.7	218.7	218.7	218.7	218.7	218.7	218.7	218.7	218.7
55°	215.0	215.0	215.0	215.0	215.0	215.0	211.3	211.3	211.3	215.0	215.0
57.5°	207.6	207.6	203.9	203.9	203.9	203.9	203.9	203.9	203.9	203.9	203.9
60°	200.2	200.2	200.2	200.2	200.2	200.2	200.2	200.2	200.2	200.2	200.2
62.5°	189.1	189.1	189.1	189.1	189.1	192.8	192.8	192.8	192.8	192.8	189.1
65°	174.2	177.9	177.9	177.9	177.9	177.9	177.9	177.9	177.9	177.9	177.9
67.5°	166.8	166.8	166.8	166.8	166.8	166.8	166.8	166.8	166.8	166.8	166.8
70°	155.7	155.7	152.0	152.0	152.0	155.7	155.7	155.7	155.7	155.7	155.7
72.5°	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9	144.6	144.6
75°	126.0	126.0	126.0	126.0	126.0	126.0	126.0	126.0	126.0	126.0	126.0
77.5°	111.2	111.2	107.5	107.5	107.5	111.2	111.2	111.2	111.2	114.9	114.9
80°	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	96.4	96.4
82.5°	74.1	74.1	74.1	74.1	74.1	74.1	74.1	74.1	74.1	77.8	77.8
85°	55.6	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	63.0	63.0
87.5°	37.1	37.1	37.1	37.1	37.1	37.1	33.4	33.4	33.4	33.4	29.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2361.4	2365.1	2368.8	2368.8	2372.5	2376.2	2376.2	2391.0	2405.9	2413.3	2420.7
5°	2020.3	2016.6	2016.6	2012.9	2009.2	2020.3	2031.5	2053.7	2075.9	2079.6	2087.1
7.5°	1582.9	1586.6	1590.3	1590.3	1594.0	1582.9	1568.1	1571.8	1575.5	1594.0	1608.9
10°	1197.4	1201.1	1204.8	1204.8	1208.5	1204.8	1197.4	1208.5	1219.6	1234.4	1253.0
12.5°	930.5	941.6	952.7	960.1	971.2	978.7	982.4	997.2	1008.3	1026.8	1045.4
15°	759.9	767.4	774.8	782.2	789.6	797.0	804.4	819.3	834.1	856.3	878.6
17.5°	641.3	641.3	645.0	645.0	645.0	652.4	659.9	667.3	671.0	693.2	715.5
20°	548.6	544.9	541.2	537.5	533.8	541.2	544.9	548.6	552.3	567.2	578.3
22.5°	470.8	470.8	474.5	474.5	474.5	470.8	463.4	467.1	467.1	474.5	485.6
25°	426.3	426.3	426.3	422.6	422.6	426.3	430.0	430.0	426.3	430.0	433.7
27.5°	385.5	389.2	389.2	392.9	392.9	396.7	396.7	396.7	396.7	400.4	404.1
30°	370.7	370.7	374.4	374.4	374.4	378.1	381.8	381.8	381.8	385.5	392.9
32.5°	355.9	359.6	363.3	367.0	370.7	374.4	374.4	378.1	378.1	381.8	385.5
35°	315.1	311.4	311.4	307.7	304.0	304.0	304.0	304.0	300.3	304.0	304.0
37.5°	281.7	281.7	281.7	278.0	278.0	281.7	281.7	281.7	281.7	285.4	285.4
40°	266.9	266.9	266.9	266.9	266.9	266.9	266.9	270.6	270.6	274.3	278.0
42.5°	255.8	255.8	255.8	255.8	255.8	259.5	259.5	259.5	259.5	263.2	263.2
45°	244.7	244.7	244.7	244.7	244.7	244.7	244.7	248.4	248.4	252.1	255.8
47.5°	233.5	233.5	233.5	233.5	233.5	237.3	241.0	241.0	241.0	244.7	244.7
50°	226.1	226.1	226.1	226.1	226.1	229.8	229.8	233.5	233.5	237.3	241.0
52.5°	218.7	218.7	218.7	218.7	218.7	222.4	222.4	226.1	226.1	229.8	233.5
55°	215.0	215.0	215.0	211.3	211.3	215.0	215.0	218.7	218.7	222.4	222.4
57.5°	203.9	203.9	203.9	203.9	203.9	203.9	203.9	207.6	207.6	211.3	215.0
60°	200.2	200.2	196.5	196.5	192.8	196.5	196.5	200.2	200.2	203.9	203.9
62.5°	189.1	189.1	189.1	185.4	185.4	189.1	189.1	189.1	189.1	192.8	196.5
65°	177.9	177.9	177.9	174.2	174.2	177.9	177.9	177.9	177.9	181.6	185.4
67.5°	166.8	166.8	166.8	163.1	163.1	163.1	163.1	166.8	166.8	170.5	174.2
70°	155.7	155.7	155.7	152.0	152.0	152.0	148.3	152.0	155.7	159.4	159.4
72.5°	144.6	144.6	144.6	140.9	140.9	140.9	137.2	140.9	140.9	144.6	144.6
75°	126.0	126.0	126.0	126.0	126.0	126.0	122.3	122.3	122.3	126.0	126.0
77.5°	114.9	114.9	114.9	111.2	111.2	111.2	107.5	107.5	107.5	111.2	111.2
80°	96.4	96.4	96.4	92.7	92.7	92.7	89.0	89.0	89.0	92.7	92.7
82.5°	77.8	77.8	77.8	74.1	74.1	74.1	70.4	70.4	70.4	74.1	74.1
85°	63.0	63.0	63.0	63.0	63.0	63.0	59.3	59.3	59.3	63.0	66.7
87.5°	29.7	29.7	33.4	33.4	33.4	33.4	29.7	29.7	25.9	25.9	29.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2428.1	2435.5	2454.1	2468.9	2487.4	2502.3	2513.4	2528.2	2539.3	2550.4	2557.9
5°	2090.8	2094.5	2113.0	2131.5	2146.4	2164.9	2190.9	2216.8	2242.8	2268.7	2287.2
7.5°	1627.4	1642.2	1664.5	1690.4	1712.7	1734.9	1760.8	1790.5	1816.4	1842.4	1868.3
10°	1267.8	1282.6	1304.9	1327.1	1345.7	1367.9	1397.6	1427.2	1456.9	1486.5	1516.2
12.5°	1063.9	1082.5	1108.4	1134.4	1156.6	1182.5	1219.6	1253.0	1290.0	1323.4	1360.5
15°	897.1	919.3	952.7	989.8	1023.1	1056.5	1093.6	1130.6	1164.0	1201.1	1238.2
17.5°	737.7	759.9	789.6	823.0	852.6	882.3	926.8	967.5	1012.0	1052.8	1093.6
20°	593.1	604.2	633.9	663.6	693.2	722.9	756.2	789.6	823.0	856.3	908.2
22.5°	493.0	500.5	515.3	526.4	541.2	552.3	585.7	619.1	648.7	682.1	730.3
25°	433.7	437.4	448.6	456.0	467.1	474.5	496.7	515.3	537.5	556.1	600.5
27.5°	404.1	407.8	411.5	415.2	418.9	422.6	437.4	452.3	463.4	478.2	519.0
30°	396.7	400.4	411.5	418.9	430.0	437.4	444.8	452.3	459.7	467.1	493.0
32.5°	389.2	392.9	392.9	389.2	389.2	385.5	392.9	396.7	404.1	407.8	430.0
35°	307.7	307.7	311.4	315.1	318.8	322.5	333.6	341.0	352.2	359.6	378.1
37.5°	289.1	289.1	292.9	300.3	304.0	307.7	315.1	322.5	329.9	337.3	355.9
40°	278.0	281.7	285.4	289.1	292.9	296.6	304.0	307.7	315.1	318.8	333.6
42.5°	266.9	266.9	270.6	278.0	281.7	285.4	292.9	296.6	304.0	307.7	322.5
45°	259.5	263.2	266.9	270.6	270.6	274.3	281.7	289.1	292.9	300.3	315.1
47.5°	248.4	248.4	255.8	259.5	266.9	270.6	278.0	281.7	289.1	292.9	307.7
50°	241.0	244.7	252.1	255.8	263.2	266.9	278.0	285.4	296.6	304.0	311.4
52.5°	233.5	237.3	244.7	248.4	255.8	259.5	274.3	289.1	300.3	315.1	315.1
55°	226.1	226.1	233.5	244.7	252.1	259.5	266.9	278.0	285.4	292.9	292.9
57.5°	215.0	218.7	226.1	237.3	244.7	252.1	259.5	266.9	270.6	278.0	274.3
60°	207.6	207.6	218.7	229.8	241.0	252.1	252.1	252.1	248.4	248.4	248.4
62.5°	196.5	200.2	215.0	233.5	248.4	263.2	252.1	241.0	229.8	218.7	222.4
65°	189.1	192.8	200.2	211.3	218.7	226.1	218.7	215.0	207.6	200.2	203.9
67.5°	174.2	177.9	181.6	181.6	185.4	185.4	185.4	185.4	185.4	185.4	189.1
70°	163.1	163.1	163.1	166.8	166.8	166.8	166.8	166.8	166.8	166.8	170.5
72.5°	148.3	148.3	148.3	148.3	148.3	148.3	148.3	148.3	148.3	148.3	152.0
75°	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7	133.5
77.5°	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.9	111.2	111.2	114.9
80°	96.4	96.4	96.4	96.4	92.7	92.7	92.7	92.7	92.7	92.7	96.4
82.5°	77.8	77.8	77.8	77.8	74.1	74.1	74.1	74.1	70.4	70.4	74.1
85°	70.4	74.1	74.1	77.8	77.8	77.8	74.1	70.4	66.7	63.0	63.0
87.5°	29.7	29.7	29.7	29.7	25.9	25.9	25.9	25.9	25.9	25.9	25.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2569.0	2576.4	2583.8	2594.9	2609.8	2620.9	2632.0	2654.2	2680.2	2702.4	2724.7
5°	2305.8	2324.3	2342.8	2365.1	2387.3	2405.9	2428.1	2472.6	2517.1	2557.9	2602.3
7.5°	1890.6	1916.5	1938.8	1975.9	2009.2	2046.3	2079.6	2135.3	2187.2	2242.8	2294.7
10°	1545.8	1575.5	1605.1	1653.3	1705.2	1753.4	1801.6	1846.1	1894.3	1938.8	1983.3
12.5°	1397.6	1430.9	1468.0	1497.6	1531.0	1560.7	1590.3	1642.2	1694.1	1746.0	1797.9
15°	1275.2	1312.3	1349.4	1386.4	1419.8	1456.9	1490.2	1534.7	1582.9	1627.4	1671.9
17.5°	1134.4	1171.4	1212.2	1253.0	1293.8	1334.5	1375.3	1438.3	1501.4	1560.7	1623.7
20°	956.4	1008.3	1056.5	1112.1	1167.7	1223.3	1278.9	1345.7	1412.4	1475.4	1542.1
22.5°	778.5	826.7	874.9	941.6	1008.3	1071.3	1138.1	1227.0	1312.3	1401.3	1486.5
25°	648.7	693.2	737.7	811.8	882.3	956.4	1026.8	1134.4	1238.2	1345.7	1449.5
27.5°	559.8	600.5	641.3	719.2	797.0	871.2	949.0	1067.6	1182.5	1301.2	1416.1
30°	519.0	544.9	570.9	645.0	719.2	789.6	863.7	978.7	1093.6	1208.5	1323.4
32.5°	452.3	474.5	496.7	563.5	630.2	693.2	759.9	878.6	993.5	1112.1	1227.0
35°	400.4	418.9	437.4	500.5	559.8	622.8	682.1	800.7	919.3	1038.0	1156.6
37.5°	370.7	389.2	404.1	459.7	519.0	574.6	630.2	748.8	863.7	982.4	1097.3
40°	348.5	359.6	374.4	430.0	481.9	537.5	589.4	696.9	808.1	915.6	1023.1
42.5°	333.6	348.5	359.6	407.8	459.7	507.9	556.1	659.9	763.6	863.7	967.5
45°	329.9	344.8	359.6	400.4	441.1	478.2	519.0	619.1	719.2	819.3	919.3
47.5°	322.5	333.6	348.5	381.8	411.5	444.8	474.5	574.6	674.7	771.1	871.2
50°	318.8	322.5	329.9	359.6	389.2	418.9	448.6	548.6	648.7	748.8	848.9
52.5°	315.1	315.1	315.1	341.0	367.0	389.2	415.2	515.3	619.1	719.2	819.3
55°	292.9	289.1	289.1	315.1	337.3	363.3	385.5	485.6	585.7	682.1	782.2
57.5°	270.6	266.9	263.2	285.4	307.7	329.9	352.2	452.3	556.1	656.1	756.2
60°	248.4	244.7	244.7	266.9	285.4	307.7	326.2	430.0	530.1	633.9	734.0
62.5°	222.4	226.1	226.1	244.7	266.9	285.4	304.0	407.8	515.3	619.1	722.9
65°	203.9	207.6	207.6	229.8	252.1	274.3	296.6	396.7	500.5	600.5	700.6
67.5°	189.1	192.8	192.8	218.7	241.0	266.9	289.1	378.1	470.8	559.8	648.7
70°	174.2	174.2	177.9	203.9	229.8	255.8	281.7	359.6	437.4	511.6	589.4
72.5°	155.7	159.4	163.1	189.1	211.3	237.3	259.5	329.9	400.4	470.8	541.2
75°	137.2	140.9	144.6	166.8	189.1	211.3	233.5	300.3	363.3	430.0	493.0
77.5°	122.3	126.0	129.7	148.3	166.8	185.4	203.9	252.1	304.0	352.2	400.4
80°	100.1	100.1	103.8	118.6	133.5	144.6	159.4	192.8	226.1	255.8	289.1
82.5°	74.1	77.8	77.8	89.0	96.4	107.5	114.9	133.5	148.3	166.8	181.6
85°	63.0	59.3	59.3	66.7	70.4	77.8	81.6	92.7	100.1	111.2	118.6
87.5°	25.9	22.2	22.2	25.9	33.4	37.1	40.8	40.8	44.5	44.5	44.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2735.8	2743.2	2754.3	2761.7	2780.3	2795.1	2813.6	2828.5	2839.6	2858.1	2850.7
5°	2635.7	2669.1	2702.4	2735.8	2761.7	2787.7	2809.9	2835.9	2865.5	2921.1	2936.0
7.5°	2339.1	2383.6	2424.4	2468.9	2520.8	2572.7	2624.6	2676.5	2724.7	2795.1	2839.6
10°	2046.3	2109.3	2168.6	2231.6	2279.8	2328.0	2372.5	2420.7	2487.4	2557.9	2639.4
12.5°	1860.9	1924.0	1987.0	2050.0	2120.4	2187.2	2257.6	2324.3	2387.3	2442.9	2535.6
15°	1738.6	1809.0	1875.8	1942.5	2027.7	2109.3	2194.6	2276.1	2368.8	2442.9	2506.0
17.5°	1708.9	1794.2	1875.8	1961.0	2050.0	2139.0	2227.9	2316.9	2409.6	2520.8	2602.3
20°	1657.0	1772.0	1886.9	2001.8	2116.7	2227.9	2342.8	2454.1	2576.4	2709.8	2746.9
22.5°	1627.4	1764.6	1905.4	2042.6	2198.3	2357.7	2513.4	2669.1	2798.8	2898.9	3010.1
25°	1623.7	1794.2	1968.4	2139.0	2335.4	2528.2	2724.7	2917.4	3084.3	3184.3	3273.3
27.5°	1620.0	1827.6	2031.5	2235.3	2476.3	2713.6	2954.5	3191.8	3347.5	3492.0	3566.2
30°	1575.5	1823.9	2075.9	2324.3	2594.9	2865.5	3136.2	3406.8	3566.2	3666.3	3703.3
32.5°	1519.9	1812.7	2105.6	2398.5	2706.1	3013.8	3317.8	3625.5	3751.5	3836.8	3807.1
35°	1475.4	1797.9	2116.7	2435.5	2761.7	3091.7	3417.9	3744.1	3925.8	4044.4	3996.2
37.5°	1434.6	1772.0	2109.3	2446.6	2828.5	3210.3	3592.1	3973.9	4148.2	4274.2	4218.6
40°	1386.4	1746.0	2109.3	2468.9	2906.3	3340.0	3777.5	4211.2	4437.3	4544.8	4459.6
42.5°	1345.7	1720.1	2098.2	2472.6	2939.7	3406.8	3873.9	4340.9	4593.0	4745.0	4637.5
45°	1293.8	1668.2	2038.9	2413.3	2928.6	3443.8	3955.4	4470.7	4763.5	4882.2	4733.9
47.5°	1238.2	1608.9	1975.9	2342.8	2891.5	3440.1	3988.8	4537.4	4808.0	4948.9	4811.7
50°	1219.6	1590.3	1957.3	2328.0	2921.1	3518.0	4111.1	4704.2	4900.7	5015.6	4834.0
52.5°	1215.9	1608.9	2005.5	2398.5	2995.3	3588.4	4185.2	4778.4	4937.8	5060.1	4897.0
55°	1204.8	1631.1	2053.7	2476.3	3099.1	3725.6	4348.4	4971.1	5130.5	5219.5	5097.2
57.5°	1215.9	1675.6	2131.5	2591.2	3232.5	3873.9	4515.2	5156.5	5349.3	5412.3	5386.3
60°	1223.3	1712.7	2198.3	2687.6	3314.1	3940.6	4567.1	5193.6	5393.7	5549.4	5579.1
62.5°	1204.8	1686.7	2164.9	2646.8	3214.0	3781.2	4348.4	4915.5	5245.5	5475.3	5608.7
65°	1149.2	1594.0	2042.6	2487.4	3010.1	3536.5	4059.2	4581.9	4930.4	5271.4	5378.9
67.5°	1026.8	1405.0	1783.1	2161.2	2617.2	3073.1	3525.4	3981.4	4418.8	4748.7	4897.0
70°	889.7	1186.3	1486.5	1783.1	2198.3	2613.5	3028.7	3443.8	3829.4	4192.7	4333.5
72.5°	774.8	1004.6	1238.2	1468.0	1764.6	2057.4	2354.0	2646.8	3102.8	3466.1	3603.2
75°	659.9	826.7	989.8	1156.6	1360.5	1564.4	1764.6	1968.4	2290.9	2617.2	2754.3
77.5°	507.9	619.1	726.6	834.1	975.0	1112.1	1253.0	1390.1	1616.3	1860.9	1931.4
80°	352.2	415.2	474.5	537.5	648.7	759.9	871.2	982.4	1130.6	1267.8	1375.3
82.5°	218.7	259.5	296.6	333.6	422.6	511.6	596.8	685.8	745.1	752.5	860.0
85°	140.9	166.8	189.1	211.3	263.2	318.8	370.7	422.6	378.1	352.2	418.9
87.5°	55.6	70.4	81.6	92.7	89.0	85.3	81.6	77.8	66.7	59.3	74.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2858.1	2869.2	2880.4	2887.8	2898.9	2902.6	2906.3	2906.3	2910.0	2913.7	2921.1
5°	2995.3	3017.5	3039.8	3058.3	3080.5	3099.1	3113.9	3132.4	3147.3	3147.3	3143.6
7.5°	2880.4	2936.0	2991.6	3047.2	3102.8	3143.6	3180.6	3221.4	3258.5	3265.9	3273.3
10°	2728.4	2787.7	2843.3	2902.6	2958.2	3021.2	3080.5	3139.9	3202.9	3214.0	3228.8
12.5°	2587.5	2657.9	2728.4	2795.1	2865.5	2910.0	2954.5	2995.3	3039.8	3069.4	3099.1
15°	2583.8	2643.1	2702.4	2758.0	2817.3	2843.3	2869.2	2891.5	2917.4	2917.4	2921.1
17.5°	2669.1	2706.1	2743.2	2776.6	2813.6	2817.3	2824.8	2828.5	2832.2	2821.1	2809.9
20°	2835.9	2850.7	2865.5	2880.4	2895.2	2869.2	2847.0	2821.1	2795.1	2765.5	2739.5
22.5°	3080.5	3047.2	3013.8	2980.5	2947.1	2902.6	2854.4	2809.9	2761.7	2724.7	2687.6
25°	3310.4	3269.6	3228.8	3188.1	3147.3	3050.9	2954.5	2854.4	2758.0	2717.3	2676.5
27.5°	3618.1	3555.0	3492.0	3429.0	3366.0	3236.2	3106.5	2976.8	2847.0	2776.6	2709.8
30°	3692.2	3621.8	3551.3	3477.2	3406.8	3280.7	3158.4	3032.4	2906.3	2824.8	2746.9
32.5°	3799.7	3718.2	3636.6	3555.0	3473.5	3351.2	3228.8	3102.8	2980.5	2906.3	2828.5
35°	3977.7	3885.0	3792.3	3695.9	3603.2	3477.2	3354.9	3228.8	3102.8	3017.5	2936.0
37.5°	4129.6	4022.1	3914.6	3807.1	3699.6	3588.4	3473.5	3362.3	3247.4	3162.1	3080.5
40°	4300.2	4181.5	4062.9	3948.0	3829.4	3725.6	3621.8	3514.3	3410.5	3343.7	3277.0
42.5°	4448.4	4303.9	4163.0	4022.1	3877.6	3807.1	3740.4	3670.0	3599.5	3566.2	3529.1
45°	4552.2	4418.8	4281.6	4148.2	4014.7	3962.8	3910.9	3859.0	3807.1	3840.5	3873.9
47.5°	4596.7	4489.2	4385.4	4281.6	4174.1	4192.7	4211.2	4226.0	4244.6	4289.0	4337.2
50°	4637.5	4578.2	4515.2	4455.9	4392.8	4463.3	4530.0	4600.4	4670.9	4763.5	4856.2
52.5°	4719.1	4685.7	4656.0	4622.7	4589.3	4711.6	4834.0	4956.3	5078.6	5182.4	5286.2
55°	4963.7	4937.8	4911.8	4882.2	4856.2	5030.5	5201.0	5375.2	5549.4	5656.9	5764.4
57.5°	5301.1	5286.2	5267.7	5252.9	5234.3	5404.9	5571.7	5738.5	5909.0	6012.8	6120.3
60°	5556.8	5560.6	5560.6	5564.3	5564.3	5694.0	5823.8	5957.2	6087.0	6175.9	6268.6
62.5°	5694.0	5686.6	5679.2	5671.8	5664.4	5771.9	5879.4	5986.9	6094.4	6161.1	6227.8
65°	5545.7	5586.5	5627.3	5668.1	5708.8	5723.7	5734.8	5749.6	5760.7	5801.5	5842.3
67.5°	5049.0	5130.5	5208.4	5289.9	5367.8	5312.2	5260.3	5204.7	5149.1	5160.2	5167.6
70°	4496.6	4589.3	4685.7	4778.4	4871.0	4741.3	4611.6	4478.1	4348.4	4303.9	4259.4
72.5°	3792.3	3873.9	3959.1	4040.7	4122.2	3962.8	3807.1	3647.7	3488.3	3410.5	3332.6
75°	2898.9	2995.3	3095.4	3191.8	3288.1	3110.2	2928.6	2750.6	2569.0	2517.1	2468.9
77.5°	2113.0	2227.9	2342.8	2457.8	2572.7	2413.3	2253.9	2090.8	1931.4	1901.7	1872.1
80°	1538.4	1627.4	1712.7	1801.6	1886.9	1794.2	1701.5	1608.9	1516.2	1512.5	1508.8
82.5°	1038.0	1115.8	1190.0	1267.8	1341.9	1304.9	1271.5	1234.4	1197.4	1234.4	1275.2
85°	533.8	641.3	752.5	860.0	967.5	956.4	949.0	937.9	926.8	975.0	1019.4
87.5°	107.5	200.2	292.9	381.8	474.5	452.3	430.0	404.1	381.8	396.7	407.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2924.9	2928.6	2928.6	2928.6	2928.6	2928.6	2921.1	2917.4	2910.0	2902.6	2891.5
5°	3143.6	3139.9	3125.0	3110.2	3091.7	3076.8	3065.7	3050.9	3039.8	3024.9	3002.7
7.5°	3280.7	3288.1	3262.2	3240.0	3214.0	3188.1	3162.1	3136.2	3110.2	3084.3	3032.4
10°	3240.0	3251.1	3236.2	3221.4	3202.9	3188.1	3158.4	3125.0	3095.4	3062.0	2999.0
12.5°	3125.0	3154.7	3147.3	3139.9	3132.4	3125.0	3106.5	3084.3	3065.7	3043.5	2973.0
15°	2921.1	2921.1	2924.9	2928.6	2928.6	2932.3	2936.0	2939.7	2943.4	2947.1	2906.3
17.5°	2798.8	2787.7	2787.7	2787.7	2787.7	2787.7	2802.5	2821.1	2835.9	2850.7	2839.6
20°	2709.8	2683.9	2680.2	2680.2	2676.5	2672.8	2698.7	2728.4	2754.3	2780.3	2795.1
22.5°	2650.5	2613.5	2609.8	2606.0	2602.3	2598.6	2632.0	2665.4	2698.7	2732.1	2784.0
25°	2635.7	2594.9	2598.6	2602.3	2602.3	2606.0	2632.0	2657.9	2683.9	2709.8	2798.8
27.5°	2639.4	2572.7	2576.4	2580.1	2580.1	2583.8	2624.6	2661.7	2702.4	2739.5	2850.7
30°	2665.4	2587.5	2580.1	2572.7	2565.3	2557.9	2613.5	2669.1	2724.7	2780.3	2865.5
32.5°	2754.3	2680.2	2661.7	2643.1	2624.6	2606.0	2672.8	2735.8	2802.5	2865.5	2936.0
35°	2850.7	2769.2	2761.7	2754.3	2743.2	2735.8	2795.1	2858.1	2917.4	2976.8	3039.8
37.5°	2995.3	2913.7	2906.3	2895.2	2887.8	2876.7	2943.4	3006.4	3073.1	3136.2	3191.8
40°	3210.3	3143.6	3139.9	3139.9	3136.2	3132.4	3184.3	3240.0	3291.8	3343.7	3380.8
42.5°	3495.7	3462.4	3473.5	3488.3	3499.4	3510.6	3551.3	3595.8	3636.6	3677.4	3666.3
45°	3907.2	3940.6	3944.3	3948.0	3951.7	3955.4	3966.5	3981.4	3992.5	4003.6	3959.1
47.5°	4381.7	4426.2	4448.4	4470.7	4489.2	4511.5	4496.6	4478.1	4463.3	4444.7	4333.5
50°	4945.2	5037.9	5034.2	5030.5	5023.0	5019.3	4989.7	4960.0	4926.7	4897.0	4733.9
52.5°	5390.0	5493.8	5512.4	5530.9	5549.4	5568.0	5512.4	5456.8	5397.4	5341.8	5138.0
55°	5868.2	5975.7	5979.5	5983.2	5983.2	5986.9	5909.0	5831.2	5749.6	5671.8	5460.5
57.5°	6224.1	6327.9	6316.8	6309.4	6298.3	6287.1	6194.5	6101.8	6009.1	5916.4	5705.1
60°	6357.6	6446.5	6424.3	6402.1	6376.1	6353.9	6283.4	6213.0	6138.9	6068.4	5864.5
62.5°	6294.6	6361.3	6327.9	6298.3	6264.9	6231.5	6142.6	6049.9	5960.9	5868.2	5720.0
65°	5879.4	5920.1	5875.7	5834.9	5794.1	5749.6	5675.5	5601.3	5523.5	5449.3	5349.3
67.5°	5178.7	5186.1	5182.4	5178.7	5175.0	5171.3	5063.8	4956.3	4845.1	4737.6	4730.2
70°	4218.6	4174.1	4181.5	4192.7	4200.1	4207.5	4125.9	4048.1	3966.5	3885.0	3922.0
72.5°	3254.8	3176.9	3195.5	3217.7	3236.2	3254.8	3188.1	3125.0	3058.3	2991.6	3043.5
75°	2417.0	2368.8	2387.3	2409.6	2428.1	2446.6	2420.7	2394.7	2365.1	2339.1	2387.3
77.5°	1842.4	1812.7	1816.4	1816.4	1820.2	1820.2	1823.9	1831.3	1835.0	1838.7	1890.6
80°	1501.4	1497.6	1493.9	1490.2	1482.8	1479.1	1516.2	1553.2	1590.3	1627.4	1653.3
82.5°	1312.3	1349.4	1327.1	1308.6	1286.3	1264.1	1297.5	1330.8	1364.2	1397.6	1386.4
85°	1067.6	1112.1	1071.3	1030.6	986.1	945.3	975.0	1000.9	1030.6	1056.5	1041.7
87.5°	422.6	433.7	367.0	304.0	237.3	170.5	270.6	367.0	467.1	563.5	578.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788

CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1	2669.1
2.5°	2880.4	2865.5	2854.4	2850.7	2843.3	2839.6	2832.2	2824.8	2813.6	2806.2	2795.1
5°	2976.8	2954.5	2928.6	2891.5	2858.1	2821.1	2784.0	2750.6	2717.3	2680.2	2646.8
7.5°	2980.5	2928.6	2876.7	2828.5	2776.6	2728.4	2676.5	2632.0	2583.8	2535.6	2491.1
10°	2939.7	2876.7	2813.6	2750.6	2691.3	2628.3	2565.3	2513.4	2457.8	2402.2	2350.3
12.5°	2906.3	2835.9	2765.5	2691.3	2620.9	2546.7	2472.6	2420.7	2368.8	2316.9	2265.0
15°	2865.5	2821.1	2780.3	2713.6	2646.8	2580.1	2513.4	2442.9	2376.2	2305.8	2235.3
17.5°	2832.2	2821.1	2809.9	2765.5	2721.0	2672.8	2628.3	2557.9	2487.4	2413.3	2342.8
20°	2813.6	2828.5	2843.3	2821.1	2798.8	2772.9	2750.6	2698.7	2646.8	2591.2	2539.3
22.5°	2835.9	2891.5	2943.4	2947.1	2954.5	2958.2	2961.9	2913.7	2865.5	2813.6	2765.5
25°	2887.8	2976.8	3065.7	3113.9	3162.1	3214.0	3262.2	3232.5	3202.9	3173.2	3143.6
27.5°	2958.2	3069.4	3180.6	3251.1	3317.8	3388.2	3458.7	3455.0	3451.3	3443.8	3440.1
30°	2947.1	3032.4	3117.6	3202.9	3288.1	3373.4	3458.7	3503.2	3543.9	3588.4	3632.9
32.5°	3010.1	3080.5	3154.7	3243.7	3332.6	3425.3	3514.3	3606.9	3695.9	3788.6	3881.3
35°	3106.5	3169.5	3236.2	3332.6	3432.7	3529.1	3629.2	3740.4	3855.3	3970.2	4081.4
37.5°	3251.1	3306.7	3366.0	3447.5	3532.8	3614.4	3699.6	3862.7	4025.8	4192.7	4355.8
40°	3417.9	3455.0	3492.0	3569.9	3647.7	3725.6	3803.4	4007.3	4211.2	4415.1	4619.0
42.5°	3658.8	3647.7	3636.6	3699.6	3766.4	3829.4	3896.1	4081.4	4266.8	4452.2	4637.5
45°	3914.6	3870.1	3825.7	3855.3	3888.7	3918.3	3951.7	4140.8	4329.8	4522.6	4711.6
47.5°	4222.3	4111.1	3999.9	3973.9	3948.0	3918.3	3892.4	4096.3	4300.2	4507.8	4711.6
50°	4570.8	4404.0	4240.9	4174.1	4103.7	4037.0	3966.5	4133.3	4303.9	4474.4	4641.2
52.5°	4934.1	4726.5	4522.6	4418.8	4315.0	4207.5	4103.7	4244.6	4389.1	4533.7	4674.6
55°	5245.5	5034.2	4819.1	4696.8	4574.5	4452.2	4329.8	4470.7	4611.6	4752.4	4893.3
57.5°	5493.8	5282.5	5071.2	4956.3	4837.7	4722.8	4604.1	4737.6	4874.8	5011.9	5145.4
60°	5664.4	5460.5	5256.6	5145.4	5034.2	4922.9	4811.7	4971.1	5130.5	5293.7	5453.1
62.5°	5575.4	5427.1	5278.8	5230.6	5182.4	5130.5	5082.3	5234.3	5382.6	5534.6	5686.6
65°	5249.2	5149.1	5049.0	5097.2	5149.1	5197.3	5249.2	5349.3	5449.3	5553.1	5653.2
67.5°	4719.1	4711.6	4700.5	4808.0	4915.5	5026.7	5134.2	5201.0	5264.0	5330.7	5397.4
70°	3959.1	3999.9	4037.0	4222.3	4407.7	4593.0	4778.4	4804.3	4830.3	4856.2	4882.2
72.5°	3099.1	3151.0	3206.6	3451.3	3692.2	3936.9	4181.5	4166.7	4151.9	4133.3	4118.5
75°	2439.2	2487.4	2539.3	2765.5	2991.6	3217.7	3443.8	3380.8	3321.5	3258.5	3195.5
77.5°	1946.2	1998.1	2053.7	2265.0	2476.3	2691.3	2902.6	2750.6	2598.6	2446.6	2294.7
80°	1675.6	1701.5	1723.8	1868.3	2009.2	2153.8	2298.4	2142.7	1983.3	1823.9	1668.2
82.5°	1375.3	1360.5	1349.4	1434.6	1519.9	1605.1	1690.4	1542.1	1393.8	1241.9	1093.6
85°	1026.8	1012.0	997.2	1041.7	1086.2	1134.4	1178.8	1008.3	837.8	663.6	493.0
87.5°	596.8	611.7	626.5	674.7	722.9	774.8	823.0	648.7	474.5	296.6	122.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671788
 CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2669.1	2669.1
2.5°	2772.9	2754.3
5°	2620.9	2594.9
7.5°	2454.1	2420.7
10°	2302.1	2257.6
12.5°	2205.7	2150.1
15°	2168.6	2101.9
17.5°	2279.8	2216.8
20°	2450.4	2365.1
22.5°	2657.9	2554.1
25°	3017.5	2891.5
27.5°	3310.4	3180.6
30°	3492.0	3351.2
32.5°	3692.2	3506.9
35°	3899.8	3721.9
37.5°	4151.9	3951.7
40°	4411.4	4203.8
42.5°	4500.3	4366.9
45°	4585.6	4459.6
47.5°	4604.1	4500.3
50°	4622.7	4607.8
52.5°	4674.6	4670.9
55°	4897.0	4900.7
57.5°	5171.3	5193.6
60°	5423.4	5397.4
62.5°	5553.1	5419.7
65°	5464.2	5278.8
67.5°	5197.3	4997.1
70°	4611.6	4340.9
72.5°	3881.3	3644.0
75°	2991.6	2791.4
77.5°	2127.8	1961.0
80°	1497.6	1330.8
82.5°	960.1	826.7
85°	433.7	378.1
87.5°	122.3	118.6
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671788
CATALOG NUMBER: CCP-SA-2E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)