

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671894

Luminaire Tested: **CCP-SA-2A-840-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671894
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2A-840-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @350mA w/ SLR distribution lens
Light Source: (32) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3871.4 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 5.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P671894
CATALOG NUMBER: CCP-SA-2A-840-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671894

CATALOG NUMBER: CCP-SA-2A-840-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	796.6	0.0	796.6
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3074.9	0.0	3074.9
	% Fixture	79.4	0.0	79.4
Total	Lumens	3871.4	0.0	3871.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.1	2.5
10°-20°	202.8	5.2
20°-30°	296.7	7.7
30°-40°	418.1	10.8
40°-50°	574.5	14.8
50°-60°	783.0	20.2
60°-70°	857.0	22.1
70°-80°	494.9	12.8
80°-90°	148.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3871.4	100.0
0°-180°	3871.4	100.0



REPORT NUMBER: P671894


CATALOG NUMBER: CCP-SA-2A-840-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	397.6	10.3			
FM (30°-60°)	1412.8	36.5			
FH (60°-80°)	1138.4	29.4			G1/1800
FVH (80°-90°)	126.0	3.3			G2/225
BL (0°-30°)	198.0	5.1	B1/500		
BM (30°-60°)	362.7	9.4	B1/1000		
BH (60°-80°)	213.5	5.5	B1/500		G1/500
BVH (80°-90°)	22.3	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P671894

CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1275.8	1268.9	1263.8	1258.6	1251.8	1246.6	1239.7	1232.9	1224.3	1217.4	1208.8
5°	1202.0	1181.4	1160.7	1148.7	1135.0	1123.0	1109.2	1093.8	1078.3	1061.2	1045.7
7.5°	1121.3	1095.5	1069.7	1049.1	1026.8	1006.2	983.9	965.0	946.1	927.2	908.3
10°	1045.7	1021.7	997.6	971.9	944.4	918.6	891.2	865.4	839.7	813.9	788.1
12.5°	995.9	966.7	939.2	910.1	882.6	853.4	824.2	800.2	776.1	750.4	726.3
15°	973.6	946.1	920.4	891.2	862.0	832.8	803.6	776.1	750.4	722.9	695.4
17.5°	1026.8	987.3	947.8	910.1	872.3	834.5	796.7	762.4	728.0	693.7	659.4
20°	1095.5	1045.7	997.6	951.3	903.2	856.8	808.7	760.7	712.6	664.5	616.4
22.5°	1183.1	1126.4	1071.5	1011.4	949.5	889.4	827.6	767.5	707.4	645.6	585.5
25°	1339.3	1272.4	1205.4	1119.5	1032.0	946.1	858.5	779.6	702.3	623.3	544.3
27.5°	1473.3	1382.3	1293.0	1189.9	1086.9	983.9	880.9	789.9	700.6	609.6	518.6
30°	1552.2	1463.0	1373.7	1248.3	1124.7	999.3	874.0	772.7	673.1	571.8	470.5
32.5°	1624.4	1524.8	1425.2	1287.8	1148.7	1011.4	872.3	760.7	650.8	539.2	427.6
35°	1724.0	1614.1	1505.9	1346.2	1186.5	1026.8	867.1	752.1	635.3	520.3	403.5
37.5°	1830.4	1694.8	1560.8	1384.0	1207.1	1030.3	853.4	740.1	626.7	513.4	400.1
40°	1947.2	1782.3	1619.2	1423.5	1229.4	1033.7	837.9	724.6	611.3	496.2	382.9
42.5°	2022.7	1844.1	1665.6	1454.4	1244.9	1033.7	822.5	710.9	599.3	485.9	374.3
45°	2065.7	1892.2	1720.5	1492.1	1263.8	1035.4	807.0	697.1	587.2	475.6	365.7
47.5°	2084.5	1923.1	1761.7	1521.3	1282.7	1042.3	801.9	690.3	576.9	465.3	352.0
50°	2134.3	1991.8	1849.3	1591.7	1335.9	1078.3	820.8	700.6	582.1	461.9	341.7
52.5°	2163.5	2041.6	1919.7	1655.3	1390.8	1126.4	862.0	728.0	594.1	460.2	326.2
55°	2270.0	2153.2	2036.5	1754.9	1471.5	1189.9	906.6	759.0	611.3	461.9	314.2
57.5°	2405.6	2282.0	2160.1	1856.2	1552.2	1248.3	944.4	786.4	626.7	468.8	309.1
60°	2500.1	2379.9	2261.4	1938.6	1614.1	1291.2	966.7	801.9	637.0	470.5	305.6
62.5°	2510.4	2355.8	2203.0	1888.8	1574.6	1258.6	944.4	784.7	625.0	463.6	303.9
65°	2445.1	2264.8	2084.5	1784.1	1483.6	1183.1	882.6	736.6	590.7	443.0	297.1
67.5°	2314.6	2103.4	1892.2	1617.5	1342.8	1068.0	793.3	667.9	544.3	419.0	293.6
70°	2010.7	1825.3	1641.5	1402.9	1165.9	927.2	688.6	585.5	484.2	381.2	278.2
72.5°	1687.9	1514.5	1342.8	1148.7	956.4	762.4	568.4	491.1	413.8	334.8	257.6
75°	1293.0	1162.5	1033.7	889.4	745.2	599.3	455.0	398.4	341.7	285.0	228.4
77.5°	908.3	837.9	769.3	661.1	552.9	444.7	336.5	298.8	261.0	223.2	185.4
80°	616.4	576.9	539.2	461.9	384.6	305.6	228.4	204.3	178.6	154.5	128.8
82.5°	382.9	381.2	377.8	324.5	271.3	218.1	164.8	144.2	125.3	104.7	84.1
85°	175.1	204.3	231.8	202.6	173.4	144.2	115.0	101.3	87.6	72.1	58.4
87.5°	54.9	67.0	77.3	73.8	68.7	65.2	60.1	51.5	42.9	34.3	25.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894

CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1202.0	1196.8	1189.9	1183.1	1174.5	1167.6	1159.0	1150.4	1148.7	1145.3	1143.6
5°	1035.4	1025.1	1013.1	1002.8	992.5	980.5	970.2	958.1	949.5	939.2	930.7
7.5°	889.4	872.3	853.4	834.5	817.3	800.2	781.3	764.1	755.5	746.9	738.3
10°	772.7	755.5	740.1	722.9	710.9	700.6	688.6	676.5	666.2	655.9	645.6
12.5°	714.3	702.3	690.3	678.2	664.5	652.5	638.8	625.0	613.0	602.7	590.7
15°	678.2	661.1	642.2	625.0	606.1	589.0	570.1	551.2	537.4	525.4	511.7
17.5°	635.3	609.6	585.5	559.8	539.2	518.6	496.2	475.6	460.2	443.0	427.6
20°	587.2	558.1	527.1	498.0	473.9	451.6	427.6	403.5	386.3	367.5	350.3
22.5°	546.0	508.3	468.8	429.3	403.5	377.8	350.3	324.5	309.1	291.9	276.5
25°	501.4	460.2	417.3	374.3	348.6	321.1	295.3	267.9	255.8	245.5	233.5
27.5°	477.3	436.1	393.2	352.0	328.0	302.2	278.2	252.4	243.8	233.5	224.9
30°	429.3	389.8	348.6	307.4	290.2	274.7	257.6	240.4	237.0	235.2	231.8
32.5°	386.3	345.1	303.9	262.7	247.3	231.8	216.4	200.9	199.2	195.7	194.0
35°	364.0	324.5	283.3	243.8	230.1	214.6	200.9	185.4	182.0	176.9	173.4
37.5°	358.9	317.7	274.7	233.5	219.8	206.1	190.6	176.9	173.4	170.0	166.6
40°	345.1	305.6	267.9	228.4	214.6	200.9	185.4	171.7	168.3	164.8	161.4
42.5°	334.8	297.1	257.6	218.1	206.1	194.0	180.3	168.3	164.8	161.4	156.3
45°	326.2	286.8	245.5	206.1	197.5	188.9	178.6	170.0	166.6	161.4	158.0
47.5°	312.5	274.7	235.2	195.7	187.2	180.3	171.7	163.1	159.7	156.3	152.8
50°	302.2	262.7	223.2	183.7	176.9	170.0	163.1	156.3	156.3	158.0	158.0
52.5°	288.5	250.7	212.9	175.1	168.3	161.4	154.5	147.7	149.4	151.1	152.8
55°	276.5	240.4	202.6	164.8	158.0	151.1	142.5	135.6	137.4	139.1	140.8
57.5°	271.3	233.5	195.7	158.0	151.1	142.5	135.6	127.1	127.1	127.1	127.1
60°	267.9	228.4	190.6	151.1	142.5	135.6	127.1	118.5	116.8	116.8	115.0
62.5°	266.1	226.7	188.9	149.4	139.1	130.5	120.2	109.9	108.2	106.5	104.7
65°	259.3	223.2	185.4	147.7	135.6	125.3	113.3	101.3	99.6	99.6	97.9
67.5°	257.6	219.8	183.7	146.0	133.9	120.2	108.2	94.4	92.7	91.0	89.3
70°	243.8	211.2	176.9	142.5	128.8	116.8	103.0	89.3	87.6	84.1	82.4
72.5°	226.7	197.5	166.6	135.6	121.9	108.2	94.4	80.7	79.0	77.3	73.8
75°	200.9	173.4	146.0	118.5	106.5	96.2	84.1	72.1	70.4	68.7	65.2
77.5°	164.8	142.5	121.9	99.6	91.0	82.4	73.8	65.2	63.5	61.8	58.4
80°	116.8	103.0	91.0	77.3	72.1	65.2	60.1	53.2	53.2	51.5	51.5
82.5°	77.3	70.4	63.5	56.7	53.2	49.8	46.4	42.9	42.9	41.2	41.2
85°	54.9	51.5	46.4	42.9	41.2	37.8	36.1	32.6	32.6	32.6	32.6
87.5°	25.8	25.8	24.0	24.0	22.3	22.3	20.6	18.9	18.9	18.9	18.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1140.1	1135.0	1129.8	1123.0	1117.8	1111.0	1102.4	1095.5	1086.9	1086.9	1085.2
5°	920.4	915.2	910.1	903.2	898.0	891.2	886.0	879.1	872.3	872.3	870.6
7.5°	729.8	719.5	709.2	697.1	686.8	680.0	673.1	664.5	657.6	652.5	647.3
10°	635.3	625.0	613.0	602.7	590.7	582.1	573.5	563.2	554.6	547.7	540.9
12.5°	578.7	566.6	554.6	542.6	530.6	518.6	508.3	496.2	484.2	475.6	467.0
15°	498.0	485.9	473.9	461.9	449.9	436.1	422.4	406.9	393.2	386.3	381.2
17.5°	410.4	398.4	384.6	372.6	358.9	348.6	338.3	328.0	317.7	310.8	305.6
20°	331.4	317.7	303.9	290.2	276.5	269.6	262.7	255.8	249.0	243.8	240.4
22.5°	259.3	250.7	243.8	235.2	226.7	221.5	218.1	212.9	207.8	207.8	207.8
25°	221.5	216.4	212.9	207.8	202.6	200.9	199.2	195.7	194.0	192.3	192.3
27.5°	214.6	209.5	204.3	199.2	194.0	192.3	190.6	187.2	185.4	185.4	185.4
30°	228.4	226.7	224.9	223.2	221.5	218.1	212.9	209.5	204.3	200.9	197.5
32.5°	190.6	188.9	188.9	187.2	185.4	188.9	190.6	194.0	195.7	197.5	199.2
35°	168.3	164.8	161.4	158.0	154.5	152.8	151.1	149.4	147.7	147.7	146.0
37.5°	163.1	159.7	156.3	152.8	149.4	147.7	146.0	144.2	142.5	142.5	140.8
40°	158.0	154.5	152.8	149.4	146.0	144.2	142.5	139.1	137.4	135.6	135.6
42.5°	152.8	151.1	147.7	146.0	142.5	140.8	139.1	135.6	133.9	132.2	130.5
45°	152.8	149.4	146.0	142.5	139.1	137.4	133.9	132.2	128.8	128.8	127.1
47.5°	149.4	146.0	142.5	139.1	135.6	133.9	130.5	128.8	125.3	123.6	121.9
50°	158.0	152.8	146.0	140.8	133.9	132.2	128.8	127.1	123.6	121.9	120.2
52.5°	154.5	149.4	142.5	137.4	130.5	127.1	125.3	121.9	118.5	116.8	115.0
55°	142.5	137.4	133.9	128.8	123.6	120.2	116.8	113.3	109.9	108.2	108.2
57.5°	127.1	125.3	123.6	121.9	120.2	116.8	113.3	108.2	104.7	103.0	101.3
60°	113.3	115.0	116.8	118.5	120.2	115.0	109.9	104.7	99.6	97.9	96.2
62.5°	103.0	106.5	109.9	111.6	115.0	109.9	104.7	99.6	94.4	92.7	91.0
65°	96.2	97.9	97.9	99.6	99.6	96.2	94.4	91.0	87.6	85.9	85.9
67.5°	87.6	87.6	87.6	85.9	85.9	84.1	84.1	82.4	80.7	79.0	79.0
70°	79.0	79.0	79.0	77.3	77.3	75.6	75.6	73.8	72.1	72.1	70.4
72.5°	72.1	72.1	70.4	70.4	68.7	68.7	68.7	67.0	67.0	65.2	65.2
75°	63.5	63.5	61.8	61.8	60.1	60.1	60.1	58.4	58.4	58.4	56.7
77.5°	56.7	56.7	54.9	54.9	53.2	53.2	53.2	51.5	51.5	49.8	49.8
80°	49.8	49.8	48.1	48.1	46.4	46.4	44.6	44.6	42.9	42.9	41.2
82.5°	39.5	39.5	39.5	39.5	39.5	37.8	37.8	36.1	34.3	34.3	32.6
85°	32.6	32.6	32.6	30.9	30.9	30.9	29.2	29.2	27.5	25.8	25.8
87.5°	18.9	18.9	18.9	17.2	17.2	17.2	17.2	17.2	17.2	17.2	15.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1085.2	1083.5	1076.6	1069.7	1076.6	1083.5	1083.5	1083.5	1081.8	1081.8	1081.8
5°	870.6	868.8	865.4	862.0	862.0	860.3	863.7	867.1	870.6	874.0	877.4
7.5°	640.5	635.3	630.2	625.0	628.5	630.2	635.3	638.8	643.9	647.3	655.9
10°	534.0	527.1	522.0	516.8	513.4	510.0	506.5	504.8	501.4	498.0	501.4
12.5°	456.7	448.2	439.6	429.3	427.6	425.8	422.4	419.0	415.5	412.1	410.4
15°	374.3	367.5	364.0	358.9	352.0	345.1	341.7	340.0	336.5	333.1	331.4
17.5°	298.8	291.9	286.8	281.6	279.9	276.5	276.5	276.5	276.5	276.5	276.5
20°	235.2	230.1	230.1	228.4	228.4	226.7	228.4	230.1	230.1	231.8	233.5
22.5°	206.1	206.1	204.3	202.6	204.3	204.3	206.1	207.8	209.5	211.2	212.9
25°	190.6	188.9	190.6	192.3	192.3	192.3	194.0	194.0	195.7	195.7	195.7
27.5°	183.7	183.7	185.4	185.4	187.2	187.2	187.2	185.4	185.4	183.7	183.7
30°	194.0	190.6	190.6	190.6	188.9	187.2	185.4	185.4	183.7	182.0	180.3
32.5°	200.9	202.6	200.9	197.5	195.7	192.3	190.6	187.2	185.4	182.0	178.6
35°	146.0	144.2	147.7	149.4	151.1	152.8	154.5	156.3	156.3	158.0	158.0
37.5°	140.8	139.1	139.1	137.4	137.4	137.4	137.4	137.4	135.6	135.6	137.4
40°	133.9	132.2	132.2	130.5	130.5	128.8	128.8	128.8	128.8	128.8	128.8
42.5°	128.8	127.1	127.1	127.1	127.1	125.3	125.3	123.6	123.6	121.9	121.9
45°	127.1	125.3	123.6	121.9	121.9	120.2	120.2	120.2	118.5	118.5	118.5
47.5°	120.2	118.5	118.5	116.8	116.8	115.0	115.0	115.0	113.3	113.3	113.3
50°	116.8	115.0	115.0	113.3	113.3	111.6	111.6	111.6	109.9	109.9	109.9
52.5°	111.6	109.9	109.9	109.9	108.2	106.5	106.5	106.5	104.7	104.7	104.7
55°	106.5	104.7	104.7	104.7	103.0	101.3	101.3	101.3	99.6	99.6	99.6
57.5°	99.6	97.9	97.9	96.2	96.2	96.2	96.2	96.2	94.4	94.4	94.4
60°	94.4	92.7	92.7	91.0	91.0	89.3	89.3	89.3	89.3	89.3	89.3
62.5°	89.3	87.6	85.9	84.1	85.9	85.9	85.9	85.9	84.1	84.1	84.1
65°	84.1	82.4	80.7	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0
67.5°	77.3	75.6	73.8	72.1	73.8	73.8	73.8	73.8	73.8	73.8	73.8
70°	70.4	68.7	68.7	67.0	67.0	65.2	65.2	67.0	67.0	67.0	67.0
72.5°	63.5	61.8	61.8	60.1	60.1	60.1	60.1	60.1	60.1	60.1	60.1
75°	56.7	54.9	54.9	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2
77.5°	48.1	46.4	46.4	46.4	46.4	46.4	46.4	48.1	48.1	48.1	48.1
80°	41.2	39.5	39.5	39.5	39.5	39.5	39.5	39.5	39.5	39.5	39.5
82.5°	32.6	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9
85°	24.0	22.3	22.3	22.3	24.0	24.0	24.0	24.0	24.0	24.0	24.0
87.5°	15.5	13.7	13.7	13.7	15.5	15.5	15.5	15.5	13.7	13.7	13.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1081.8	1081.8	1081.8	1080.0	1078.3	1076.6	1074.9	1080.0	1083.5	1088.6	1092.1
5°	879.1	882.6	884.3	889.4	894.6	899.8	904.9	908.3	911.8	913.5	916.9
7.5°	662.8	671.4	678.2	685.1	692.0	697.1	704.0	709.2	714.3	719.5	724.6
10°	503.1	506.5	508.3	515.1	520.3	527.1	532.3	537.4	542.6	546.0	551.2
12.5°	408.7	405.2	403.5	403.5	403.5	403.5	403.5	406.9	410.4	413.8	417.3
15°	329.7	328.0	326.2	324.5	322.8	319.4	317.7	321.1	324.5	328.0	331.4
17.5°	276.5	276.5	276.5	274.7	273.0	271.3	269.6	271.3	273.0	273.0	274.7
20°	237.0	238.7	240.4	242.1	242.1	243.8	243.8	245.5	247.3	247.3	249.0
22.5°	212.9	214.6	214.6	214.6	216.4	216.4	216.4	218.1	219.8	221.5	223.2
25°	194.0	194.0	192.3	192.3	194.0	194.0	194.0	194.0	195.7	195.7	195.7
27.5°	183.7	182.0	182.0	182.0	182.0	180.3	180.3	180.3	180.3	180.3	180.3
30°	178.6	176.9	175.1	173.4	173.4	171.7	170.0	170.0	170.0	170.0	170.0
32.5°	176.9	173.4	170.0	168.3	168.3	166.6	164.8	163.1	163.1	161.4	159.7
35°	158.0	156.3	156.3	154.5	152.8	151.1	149.4	149.4	149.4	147.7	147.7
37.5°	137.4	139.1	139.1	139.1	140.8	140.8	140.8	140.8	142.5	142.5	142.5
40°	128.8	128.8	128.8	130.5	132.2	132.2	133.9	133.9	135.6	135.6	135.6
42.5°	121.9	120.2	120.2	121.9	121.9	123.6	123.6	125.3	127.1	127.1	128.8
45°	118.5	116.8	116.8	116.8	116.8	115.0	115.0	116.8	118.5	120.2	121.9
47.5°	111.6	111.6	109.9	109.9	109.9	109.9	109.9	109.9	111.6	111.6	111.6
50°	108.2	108.2	106.5	106.5	106.5	106.5	106.5	106.5	106.5	106.5	106.5
52.5°	104.7	103.0	103.0	103.0	103.0	101.3	101.3	101.3	101.3	101.3	101.3
55°	99.6	97.9	97.9	97.9	97.9	97.9	97.9	97.9	99.6	99.6	99.6
57.5°	94.4	92.7	92.7	92.7	94.4	94.4	94.4	94.4	96.2	96.2	96.2
60°	89.3	89.3	89.3	89.3	89.3	89.3	89.3	91.0	91.0	92.7	92.7
62.5°	84.1	84.1	84.1	84.1	85.9	85.9	85.9	85.9	87.6	87.6	87.6
65°	79.0	79.0	79.0	79.0	80.7	80.7	80.7	80.7	80.7	80.7	80.7
67.5°	73.8	73.8	73.8	73.8	73.8	73.8	73.8	75.6	75.6	77.3	77.3
70°	67.0	65.2	65.2	67.0	67.0	68.7	68.7	70.4	70.4	72.1	72.1
72.5°	60.1	60.1	60.1	60.1	60.1	60.1	60.1	61.8	63.5	63.5	65.2
75°	53.2	53.2	53.2	53.2	54.9	54.9	54.9	56.7	56.7	58.4	58.4
77.5°	48.1	46.4	46.4	46.4	48.1	48.1	48.1	49.8	49.8	51.5	51.5
80°	39.5	39.5	39.5	39.5	41.2	41.2	41.2	41.2	42.9	42.9	42.9
82.5°	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	34.3	34.3	34.3
85°	24.0	24.0	24.0	24.0	25.8	25.8	25.8	25.8	25.8	25.8	25.8
87.5°	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5	17.2	17.2	17.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1092.1	1092.1	1092.1	1092.1	1095.5	1097.2	1100.7	1102.4	1100.7	1098.9	1095.5
5°	918.6	920.4	920.4	922.1	922.1	922.1	922.1	922.1	925.5	928.9	932.4
7.5°	726.3	728.0	729.8	731.5	731.5	731.5	729.8	729.8	731.5	731.5	733.2
10°	556.3	563.2	568.4	573.5	570.1	564.9	561.5	556.3	556.3	556.3	554.6
12.5°	420.7	422.4	425.8	427.6	425.8	425.8	424.1	422.4	424.1	427.6	429.3
15°	333.1	333.1	334.8	334.8	336.5	338.3	338.3	340.0	343.4	345.1	348.6
17.5°	276.5	278.2	278.2	279.9	279.9	281.6	281.6	281.6	285.0	288.5	293.6
20°	249.0	249.0	249.0	249.0	249.0	247.3	247.3	245.5	247.3	250.7	252.4
22.5°	223.2	224.9	224.9	224.9	223.2	221.5	218.1	216.4	216.4	218.1	218.1
25°	195.7	194.0	194.0	192.3	192.3	194.0	194.0	194.0	195.7	195.7	197.5
27.5°	180.3	178.6	178.6	176.9	176.9	178.6	178.6	178.6	178.6	178.6	178.6
30°	168.3	168.3	166.6	164.8	166.6	166.6	168.3	168.3	170.0	170.0	171.7
32.5°	159.7	158.0	158.0	156.3	158.0	158.0	159.7	159.7	161.4	163.1	163.1
35°	147.7	147.7	147.7	147.7	147.7	147.7	146.0	146.0	146.0	146.0	146.0
37.5°	140.8	140.8	139.1	137.4	137.4	137.4	137.4	137.4	135.6	133.9	132.2
40°	135.6	133.9	133.9	132.2	130.5	130.5	128.8	127.1	127.1	125.3	125.3
42.5°	128.8	127.1	127.1	125.3	123.6	123.6	121.9	120.2	120.2	120.2	118.5
45°	120.2	120.2	118.5	116.8	116.8	116.8	115.0	115.0	115.0	115.0	113.3
47.5°	111.6	111.6	109.9	109.9	109.9	109.9	108.2	108.2	108.2	108.2	108.2
50°	106.5	106.5	106.5	106.5	106.5	106.5	104.7	104.7	104.7	104.7	104.7
52.5°	101.3	101.3	101.3	101.3	101.3	101.3	101.3	101.3	101.3	101.3	101.3
55°	99.6	99.6	99.6	99.6	99.6	99.6	97.9	97.9	97.9	99.6	99.6
57.5°	96.2	96.2	94.4	94.4	94.4	94.4	94.4	94.4	94.4	94.4	94.4
60°	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7
62.5°	87.6	87.6	87.6	87.6	87.6	89.3	89.3	89.3	89.3	89.3	87.6
65°	80.7	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4
67.5°	77.3	77.3	77.3	77.3	77.3	77.3	77.3	77.3	77.3	77.3	77.3
70°	72.1	72.1	70.4	70.4	70.4	72.1	72.1	72.1	72.1	72.1	72.1
72.5°	65.2	65.2	65.2	65.2	65.2	65.2	65.2	65.2	65.2	67.0	67.0
75°	58.4	58.4	58.4	58.4	58.4	58.4	58.4	58.4	58.4	58.4	58.4
77.5°	51.5	51.5	49.8	49.8	49.8	51.5	51.5	51.5	51.5	53.2	53.2
80°	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9	44.6	44.6
82.5°	34.3	34.3	34.3	34.3	34.3	34.3	34.3	34.3	34.3	36.1	36.1
85°	25.8	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5	29.2	29.2
87.5°	17.2	17.2	17.2	17.2	17.2	17.2	15.5	15.5	15.5	15.5	13.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894

CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1093.8	1095.5	1097.2	1097.2	1098.9	1100.7	1100.7	1107.5	1114.4	1117.8	1121.3
5°	935.8	934.1	934.1	932.4	930.7	935.8	941.0	951.3	961.6	963.3	966.7
7.5°	733.2	734.9	736.6	736.6	738.3	733.2	726.3	728.0	729.8	738.3	745.2
10°	554.6	556.3	558.1	558.1	559.8	558.1	554.6	559.8	564.9	571.8	580.4
12.5°	431.0	436.1	441.3	444.7	449.9	453.3	455.0	461.9	467.0	475.6	484.2
15°	352.0	355.4	358.9	362.3	365.7	369.2	372.6	379.5	386.3	396.6	406.9
17.5°	297.1	297.1	298.8	298.8	298.8	302.2	305.6	309.1	310.8	321.1	331.4
20°	254.1	252.4	250.7	249.0	247.3	250.7	252.4	254.1	255.8	262.7	267.9
22.5°	218.1	218.1	219.8	219.8	219.8	218.1	214.6	216.4	216.4	219.8	224.9
25°	197.5	197.5	197.5	195.7	195.7	197.5	199.2	199.2	197.5	199.2	200.9
27.5°	178.6	180.3	180.3	182.0	182.0	183.7	183.7	183.7	183.7	185.4	187.2
30°	171.7	171.7	173.4	173.4	173.4	175.1	176.9	176.9	176.9	178.6	182.0
32.5°	164.8	166.6	168.3	170.0	171.7	173.4	173.4	175.1	175.1	176.9	178.6
35°	146.0	144.2	144.2	142.5	140.8	140.8	140.8	140.8	139.1	140.8	140.8
37.5°	130.5	130.5	130.5	128.8	128.8	130.5	130.5	130.5	130.5	132.2	132.2
40°	123.6	123.6	123.6	123.6	123.6	123.6	123.6	125.3	125.3	127.1	128.8
42.5°	118.5	118.5	118.5	118.5	118.5	120.2	120.2	120.2	120.2	121.9	121.9
45°	113.3	113.3	113.3	113.3	113.3	113.3	113.3	115.0	115.0	116.8	118.5
47.5°	108.2	108.2	108.2	108.2	108.2	109.9	111.6	111.6	111.6	113.3	113.3
50°	104.7	104.7	104.7	104.7	104.7	106.5	106.5	108.2	108.2	109.9	111.6
52.5°	101.3	101.3	101.3	101.3	101.3	103.0	103.0	104.7	104.7	106.5	108.2
55°	99.6	99.6	99.6	97.9	97.9	99.6	99.6	101.3	101.3	103.0	103.0
57.5°	94.4	94.4	94.4	94.4	94.4	94.4	94.4	96.2	96.2	97.9	99.6
60°	92.7	92.7	91.0	91.0	89.3	91.0	91.0	92.7	92.7	94.4	94.4
62.5°	87.6	87.6	87.6	85.9	85.9	87.6	87.6	87.6	87.6	89.3	91.0
65°	82.4	82.4	82.4	80.7	80.7	82.4	82.4	82.4	82.4	84.1	85.9
67.5°	77.3	77.3	77.3	75.6	75.6	75.6	75.6	77.3	77.3	79.0	80.7
70°	72.1	72.1	72.1	70.4	70.4	70.4	68.7	70.4	72.1	73.8	73.8
72.5°	67.0	67.0	67.0	65.2	65.2	65.2	63.5	65.2	65.2	67.0	67.0
75°	58.4	58.4	58.4	58.4	58.4	58.4	56.7	56.7	56.7	58.4	58.4
77.5°	53.2	53.2	53.2	51.5	51.5	51.5	49.8	49.8	49.8	51.5	51.5
80°	44.6	44.6	44.6	42.9	42.9	42.9	41.2	41.2	41.2	42.9	42.9
82.5°	36.1	36.1	36.1	34.3	34.3	34.3	32.6	32.6	32.6	34.3	34.3
85°	29.2	29.2	29.2	29.2	29.2	29.2	27.5	27.5	27.5	29.2	30.9
87.5°	13.7	13.7	15.5	15.5	15.5	15.5	13.7	13.7	12.0	12.0	13.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1124.7	1128.1	1136.7	1143.6	1152.2	1159.0	1164.2	1171.1	1176.2	1181.4	1184.8
5°	968.4	970.2	978.7	987.3	994.2	1002.8	1014.8	1026.8	1038.8	1050.9	1059.4
7.5°	753.8	760.7	771.0	783.0	793.3	803.6	815.6	829.4	841.4	853.4	865.4
10°	587.2	594.1	604.4	614.7	623.3	633.6	647.3	661.1	674.8	688.6	702.3
12.5°	492.8	501.4	513.4	525.4	535.7	547.7	564.9	580.4	597.5	613.0	630.2
15°	415.5	425.8	441.3	458.5	473.9	489.4	506.5	523.7	539.2	556.3	573.5
17.5°	341.7	352.0	365.7	381.2	394.9	408.7	429.3	448.2	468.8	487.7	506.5
20°	274.7	279.9	293.6	307.4	321.1	334.8	350.3	365.7	381.2	396.6	420.7
22.5°	228.4	231.8	238.7	243.8	250.7	255.8	271.3	286.8	300.5	315.9	338.3
25°	200.9	202.6	207.8	211.2	216.4	219.8	230.1	238.7	249.0	257.6	278.2
27.5°	187.2	188.9	190.6	192.3	194.0	195.7	202.6	209.5	214.6	221.5	240.4
30°	183.7	185.4	190.6	194.0	199.2	202.6	206.1	209.5	212.9	216.4	228.4
32.5°	180.3	182.0	182.0	180.3	180.3	178.6	182.0	183.7	187.2	188.9	199.2
35°	142.5	142.5	144.2	146.0	147.7	149.4	154.5	158.0	163.1	166.6	175.1
37.5°	133.9	133.9	135.6	139.1	140.8	142.5	146.0	149.4	152.8	156.3	164.8
40°	128.8	130.5	132.2	133.9	135.6	137.4	140.8	142.5	146.0	147.7	154.5
42.5°	123.6	123.6	125.3	128.8	130.5	132.2	135.6	137.4	140.8	142.5	149.4
45°	120.2	121.9	123.6	125.3	125.3	127.1	130.5	133.9	135.6	139.1	146.0
47.5°	115.0	115.0	118.5	120.2	123.6	125.3	128.8	130.5	133.9	135.6	142.5
50°	111.6	113.3	116.8	118.5	121.9	123.6	128.8	132.2	137.4	140.8	144.2
52.5°	108.2	109.9	113.3	115.0	118.5	120.2	127.1	133.9	139.1	146.0	146.0
55°	104.7	104.7	108.2	113.3	116.8	120.2	123.6	128.8	132.2	135.6	135.6
57.5°	99.6	101.3	104.7	109.9	113.3	116.8	120.2	123.6	125.3	128.8	127.1
60°	96.2	96.2	101.3	106.5	111.6	116.8	116.8	116.8	115.0	115.0	115.0
62.5°	91.0	92.7	99.6	108.2	115.0	121.9	116.8	111.6	106.5	101.3	103.0
65°	87.6	89.3	92.7	97.9	101.3	104.7	101.3	99.6	96.2	92.7	94.4
67.5°	80.7	82.4	84.1	84.1	85.9	85.9	85.9	85.9	85.9	85.9	87.6
70°	75.6	75.6	75.6	77.3	77.3	77.3	77.3	77.3	77.3	77.3	79.0
72.5°	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.7	70.4
75°	60.1	60.1	60.1	60.1	60.1	60.1	60.1	60.1	60.1	60.1	61.8
77.5°	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2	51.5	51.5	53.2
80°	44.6	44.6	44.6	44.6	42.9	42.9	42.9	42.9	42.9	42.9	44.6
82.5°	36.1	36.1	36.1	36.1	34.3	34.3	34.3	34.3	32.6	32.6	34.3
85°	32.6	34.3	34.3	36.1	36.1	36.1	34.3	32.6	30.9	29.2	29.2
87.5°	13.7	13.7	13.7	13.7	12.0	12.0	12.0	12.0	12.0	12.0	12.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894

CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1189.9	1193.4	1196.8	1202.0	1208.8	1214.0	1219.1	1229.4	1241.5	1251.8	1262.1
5°	1068.0	1076.6	1085.2	1095.5	1105.8	1114.4	1124.7	1145.3	1165.9	1184.8	1205.4
7.5°	875.7	887.7	898.0	915.2	930.7	947.8	963.3	989.0	1013.1	1038.8	1062.9
10°	716.0	729.8	743.5	765.8	789.9	812.2	834.5	855.1	877.4	898.0	918.6
12.5°	647.3	662.8	680.0	693.7	709.2	722.9	736.6	760.7	784.7	808.7	832.8
15°	590.7	607.8	625.0	642.2	657.6	674.8	690.3	710.9	733.2	753.8	774.4
17.5°	525.4	542.6	561.5	580.4	599.3	618.2	637.0	666.2	695.4	722.9	752.1
20°	443.0	467.0	489.4	515.1	540.9	566.6	592.4	623.3	654.2	683.4	714.3
22.5°	360.6	382.9	405.2	436.1	467.0	496.2	527.1	568.4	607.8	649.1	688.6
25°	300.5	321.1	341.7	376.0	408.7	443.0	475.6	525.4	573.5	623.3	671.4
27.5°	259.3	278.2	297.1	333.1	369.2	403.5	439.6	494.5	547.7	602.7	655.9
30°	240.4	252.4	264.4	298.8	333.1	365.7	400.1	453.3	506.5	559.8	613.0
32.5°	209.5	219.8	230.1	261.0	291.9	321.1	352.0	406.9	460.2	515.1	568.4
35°	185.4	194.0	202.6	231.8	259.3	288.5	315.9	370.9	425.8	480.8	535.7
37.5°	171.7	180.3	187.2	212.9	240.4	266.1	291.9	346.9	400.1	455.0	508.3
40°	161.4	166.6	173.4	199.2	223.2	249.0	273.0	322.8	374.3	424.1	473.9
42.5°	154.5	161.4	166.6	188.9	212.9	235.2	257.6	305.6	353.7	400.1	448.2
45°	152.8	159.7	166.6	185.4	204.3	221.5	240.4	286.8	333.1	379.5	425.8
47.5°	149.4	154.5	161.4	176.9	190.6	206.1	219.8	266.1	312.5	357.2	403.5
50°	147.7	149.4	152.8	166.6	180.3	194.0	207.8	254.1	300.5	346.9	393.2
52.5°	146.0	146.0	146.0	158.0	170.0	180.3	192.3	238.7	286.8	333.1	379.5
55°	135.6	133.9	133.9	146.0	156.3	168.3	178.6	224.9	271.3	315.9	362.3
57.5°	125.3	123.6	121.9	132.2	142.5	152.8	163.1	209.5	257.6	303.9	350.3
60°	115.0	113.3	113.3	123.6	132.2	142.5	151.1	199.2	245.5	293.6	340.0
62.5°	103.0	104.7	104.7	113.3	123.6	132.2	140.8	188.9	238.7	286.8	334.8
65°	94.4	96.2	96.2	106.5	116.8	127.1	137.4	183.7	231.8	278.2	324.5
67.5°	87.6	89.3	89.3	101.3	111.6	123.6	133.9	175.1	218.1	259.3	300.5
70°	80.7	80.7	82.4	94.4	106.5	118.5	130.5	166.6	202.6	237.0	273.0
72.5°	72.1	73.8	75.6	87.6	97.9	109.9	120.2	152.8	185.4	218.1	250.7
75°	63.5	65.2	67.0	77.3	87.6	97.9	108.2	139.1	168.3	199.2	228.4
77.5°	56.7	58.4	60.1	68.7	77.3	85.9	94.4	116.8	140.8	163.1	185.4
80°	46.4	46.4	48.1	54.9	61.8	67.0	73.8	89.3	104.7	118.5	133.9
82.5°	34.3	36.1	36.1	41.2	44.6	49.8	53.2	61.8	68.7	77.3	84.1
85°	29.2	27.5	27.5	30.9	32.6	36.1	37.8	42.9	46.4	51.5	54.9
87.5°	12.0	10.3	10.3	12.0	15.5	17.2	18.9	18.9	20.6	20.6	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894

CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1267.2	1270.6	1275.8	1279.2	1287.8	1294.7	1303.3	1310.1	1315.3	1323.9	1320.4
5°	1220.8	1236.3	1251.8	1267.2	1279.2	1291.2	1301.5	1313.6	1327.3	1353.1	1359.9
7.5°	1083.5	1104.1	1123.0	1143.6	1167.6	1191.7	1215.7	1239.7	1262.1	1294.7	1315.3
10°	947.8	977.0	1004.5	1033.7	1056.0	1078.3	1098.9	1121.3	1152.2	1184.8	1222.6
12.5°	862.0	891.2	920.4	949.5	982.2	1013.1	1045.7	1076.6	1105.8	1131.6	1174.5
15°	805.3	837.9	868.8	899.8	939.2	977.0	1016.5	1054.3	1097.2	1131.6	1160.7
17.5°	791.6	831.1	868.8	908.3	949.5	990.8	1032.0	1073.2	1116.1	1167.6	1205.4
20°	767.5	820.8	874.0	927.2	980.5	1032.0	1085.2	1136.7	1193.4	1255.2	1272.4
22.5°	753.8	817.3	882.6	946.1	1018.2	1092.1	1164.2	1236.3	1296.4	1342.8	1394.3
25°	752.1	831.1	911.8	990.8	1081.8	1171.1	1262.1	1351.3	1428.6	1475.0	1516.2
27.5°	750.4	846.5	941.0	1035.4	1147.0	1256.9	1368.5	1478.4	1550.5	1617.5	1651.8
30°	729.8	844.8	961.6	1076.6	1202.0	1327.3	1452.7	1578.0	1651.8	1698.2	1715.4
32.5°	704.0	839.7	975.3	1111.0	1253.5	1396.0	1536.8	1679.3	1737.7	1777.2	1763.4
35°	683.4	832.8	980.5	1128.1	1279.2	1432.0	1583.2	1734.3	1818.4	1873.3	1851.0
37.5°	664.5	820.8	977.0	1133.3	1310.1	1487.0	1663.9	1840.7	1921.4	1979.8	1954.0
40°	642.2	808.7	977.0	1143.6	1346.2	1547.1	1749.7	1950.6	2055.4	2105.1	2065.7
42.5°	623.3	796.7	971.9	1145.3	1361.6	1578.0	1794.4	2010.7	2127.5	2197.9	2148.1
45°	599.3	772.7	944.4	1117.8	1356.5	1595.2	1832.1	2070.8	2206.5	2261.4	2192.7
47.5°	573.5	745.2	915.2	1085.2	1339.3	1593.5	1847.6	2101.7	2227.1	2292.3	2228.8
50°	564.9	736.6	906.6	1078.3	1353.1	1629.5	1904.2	2179.0	2270.0	2323.2	2239.1
52.5°	563.2	745.2	928.9	1111.0	1387.4	1662.1	1938.6	2213.3	2287.2	2343.8	2268.3
55°	558.1	755.5	951.3	1147.0	1435.5	1725.7	2014.1	2302.6	2376.4	2417.7	2361.0
57.5°	563.2	776.1	987.3	1200.2	1497.3	1794.4	2091.4	2388.5	2477.8	2506.9	2494.9
60°	566.6	793.3	1018.2	1244.9	1535.1	1825.3	2115.4	2405.6	2498.4	2570.5	2584.2
62.5°	558.1	781.3	1002.8	1226.0	1488.7	1751.4	2014.1	2276.9	2429.7	2536.1	2597.9
65°	532.3	738.3	946.1	1152.2	1394.3	1638.1	1880.2	2122.3	2283.7	2441.7	2491.5
67.5°	475.6	650.8	825.9	1001.1	1212.3	1423.5	1632.9	1844.1	2046.8	2199.6	2268.3
70°	412.1	549.5	688.6	825.9	1018.2	1210.5	1402.9	1595.2	1773.7	1942.0	2007.3
72.5°	358.9	465.3	573.5	680.0	817.3	953.0	1090.3	1226.0	1437.2	1605.5	1669.0
75°	305.6	382.9	458.5	535.7	630.2	724.6	817.3	911.8	1061.2	1212.3	1275.8
77.5°	235.2	286.8	336.5	386.3	451.6	515.1	580.4	643.9	748.6	862.0	894.6
80°	163.1	192.3	219.8	249.0	300.5	352.0	403.5	455.0	523.7	587.2	637.0
82.5°	101.3	120.2	137.4	154.5	195.7	237.0	276.5	317.7	345.1	348.6	398.4
85°	65.2	77.3	87.6	97.9	121.9	147.7	171.7	195.7	175.1	163.1	194.0
87.5°	25.8	32.6	37.8	42.9	41.2	39.5	37.8	36.1	30.9	27.5	34.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894

CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1323.9	1329.0	1334.2	1337.6	1342.8	1344.5	1346.2	1346.2	1347.9	1349.6	1353.1
5°	1387.4	1397.7	1408.0	1416.6	1426.9	1435.5	1442.4	1450.9	1457.8	1457.8	1456.1
7.5°	1334.2	1359.9	1385.7	1411.4	1437.2	1456.1	1473.3	1492.1	1509.3	1512.8	1516.2
10°	1263.8	1291.2	1317.0	1344.5	1370.2	1399.4	1426.9	1454.4	1483.6	1488.7	1495.6
12.5°	1198.5	1231.1	1263.8	1294.7	1327.3	1347.9	1368.5	1387.4	1408.0	1421.7	1435.5
15°	1196.8	1224.3	1251.8	1277.5	1305.0	1317.0	1329.0	1339.3	1351.3	1351.3	1353.1
17.5°	1236.3	1253.5	1270.6	1286.1	1303.3	1305.0	1308.4	1310.1	1311.9	1306.7	1301.5
20°	1313.6	1320.4	1327.3	1334.2	1341.0	1329.0	1318.7	1306.7	1294.7	1280.9	1268.9
22.5°	1426.9	1411.4	1396.0	1380.5	1365.1	1344.5	1322.2	1301.5	1279.2	1262.1	1244.9
25°	1533.4	1514.5	1495.6	1476.7	1457.8	1413.2	1368.5	1322.2	1277.5	1258.6	1239.7
27.5°	1675.9	1646.7	1617.5	1588.3	1559.1	1499.0	1438.9	1378.8	1318.7	1286.1	1255.2
30°	1710.2	1677.6	1645.0	1610.6	1578.0	1519.6	1463.0	1404.6	1346.2	1308.4	1272.4
32.5°	1760.0	1722.2	1684.5	1646.7	1608.9	1552.2	1495.6	1437.2	1380.5	1346.2	1310.1
35°	1842.4	1799.5	1756.6	1711.9	1669.0	1610.6	1554.0	1495.6	1437.2	1397.7	1359.9
37.5°	1912.8	1863.0	1813.2	1763.4	1713.7	1662.1	1608.9	1557.4	1504.2	1464.7	1426.9
40°	1991.8	1936.9	1881.9	1828.7	1773.7	1725.7	1677.6	1627.8	1579.7	1548.8	1517.9
42.5°	2060.5	1993.5	1928.3	1863.0	1796.1	1763.4	1732.5	1699.9	1667.3	1651.8	1634.7
45°	2108.6	2046.8	1983.2	1921.4	1859.6	1835.6	1811.5	1787.5	1763.4	1778.9	1794.4
47.5°	2129.2	2079.4	2031.3	1983.2	1933.4	1942.0	1950.6	1957.5	1966.1	1986.7	2009.0
50°	2148.1	2120.6	2091.4	2063.9	2034.7	2067.4	2098.3	2130.9	2163.5	2206.5	2249.4
52.5°	2185.8	2170.4	2156.7	2141.2	2125.8	2182.4	2239.1	2295.7	2352.4	2400.5	2448.6
55°	2299.2	2287.2	2275.1	2261.4	2249.4	2330.1	2409.1	2489.8	2570.5	2620.3	2670.1
57.5°	2455.4	2448.6	2440.0	2433.1	2424.5	2503.5	2580.8	2658.0	2737.0	2785.1	2834.9
60°	2573.9	2575.6	2575.6	2577.3	2577.3	2637.4	2697.5	2759.4	2819.5	2860.7	2903.6
62.5°	2637.4	2634.0	2630.6	2627.1	2623.7	2673.5	2723.3	2773.1	2822.9	2853.8	2884.7
65°	2568.8	2587.6	2606.5	2625.4	2644.3	2651.2	2656.3	2663.2	2668.3	2687.2	2706.1
67.5°	2338.7	2376.4	2412.5	2450.3	2486.3	2460.6	2436.5	2410.8	2385.0	2390.2	2393.6
70°	2082.8	2125.8	2170.4	2213.3	2256.2	2196.2	2136.1	2074.2	2014.1	1993.5	1972.9
72.5°	1756.6	1794.4	1833.8	1871.6	1909.4	1835.6	1763.4	1689.6	1615.8	1579.7	1543.7
75°	1342.8	1387.4	1433.8	1478.4	1523.1	1440.6	1356.5	1274.1	1189.9	1165.9	1143.6
77.5°	978.7	1032.0	1085.2	1138.4	1191.7	1117.8	1044.0	968.4	894.6	880.9	867.1
80°	712.6	753.8	793.3	834.5	874.0	831.1	788.1	745.2	702.3	700.6	698.9
82.5°	480.8	516.8	551.2	587.2	621.6	604.4	589.0	571.8	554.6	571.8	590.7
85°	247.3	297.1	348.6	398.4	448.2	443.0	439.6	434.4	429.3	451.6	472.2
87.5°	49.8	92.7	135.6	176.9	219.8	209.5	199.2	187.2	176.9	183.7	188.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894

CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1354.8	1356.5	1356.5	1356.5	1356.5	1356.5	1353.1	1351.3	1347.9	1344.5	1339.3
5°	1456.1	1454.4	1447.5	1440.6	1432.0	1425.2	1420.0	1413.2	1408.0	1401.1	1390.8
7.5°	1519.6	1523.1	1511.0	1500.7	1488.7	1476.7	1464.7	1452.7	1440.6	1428.6	1404.6
10°	1500.7	1505.9	1499.0	1492.1	1483.6	1476.7	1463.0	1447.5	1433.8	1418.3	1389.1
12.5°	1447.5	1461.2	1457.8	1454.4	1450.9	1447.5	1438.9	1428.6	1420.0	1409.7	1377.1
15°	1353.1	1353.1	1354.8	1356.5	1356.5	1358.2	1359.9	1361.6	1363.4	1365.1	1346.2
17.5°	1296.4	1291.2	1291.2	1291.2	1291.2	1291.2	1298.1	1306.7	1313.6	1320.4	1315.3
20°	1255.2	1243.2	1241.5	1241.5	1239.7	1238.0	1250.0	1263.8	1275.8	1287.8	1294.7
22.5°	1227.7	1210.5	1208.8	1207.1	1205.4	1203.7	1219.1	1234.6	1250.0	1265.5	1289.5
25°	1220.8	1202.0	1203.7	1205.4	1205.4	1207.1	1219.1	1231.1	1243.2	1255.2	1296.4
27.5°	1222.6	1191.7	1193.4	1195.1	1195.1	1196.8	1215.7	1232.9	1251.8	1268.9	1320.4
30°	1234.6	1198.5	1195.1	1191.7	1188.2	1184.8	1210.5	1236.3	1262.1	1287.8	1327.3
32.5°	1275.8	1241.5	1232.9	1224.3	1215.7	1207.1	1238.0	1267.2	1298.1	1327.3	1359.9
35°	1320.4	1282.7	1279.2	1275.8	1270.6	1267.2	1294.7	1323.9	1351.3	1378.8	1408.0
37.5°	1387.4	1349.6	1346.2	1341.0	1337.6	1332.5	1363.4	1392.6	1423.5	1452.7	1478.4
40°	1487.0	1456.1	1454.4	1454.4	1452.7	1450.9	1475.0	1500.7	1524.8	1548.8	1566.0
42.5°	1619.2	1603.8	1608.9	1615.8	1620.9	1626.1	1645.0	1665.6	1684.5	1703.3	1698.2
45°	1809.8	1825.3	1827.0	1828.7	1830.4	1832.1	1837.3	1844.1	1849.3	1854.5	1833.8
47.5°	2029.6	2050.2	2060.5	2070.8	2079.4	2089.7	2082.8	2074.2	2067.4	2058.8	2007.3
50°	2290.6	2333.5	2331.8	2330.1	2326.6	2324.9	2311.2	2297.5	2282.0	2268.3	2192.7
52.5°	2496.6	2544.7	2553.3	2561.9	2570.5	2579.1	2553.3	2527.5	2500.1	2474.3	2379.9
55°	2718.1	2767.9	2769.7	2771.4	2771.4	2773.1	2737.0	2701.0	2663.2	2627.1	2529.3
57.5°	2883.0	2931.1	2925.9	2922.5	2917.3	2912.2	2869.2	2826.3	2783.4	2740.5	2642.6
60°	2944.8	2986.0	2975.7	2965.4	2953.4	2943.1	2910.5	2877.8	2843.5	2810.9	2716.4
62.5°	2915.6	2946.5	2931.1	2917.3	2901.9	2886.4	2845.2	2802.3	2761.1	2718.1	2649.5
65°	2723.3	2742.2	2721.6	2702.7	2683.8	2663.2	2628.9	2594.5	2558.5	2524.1	2477.8
67.5°	2398.8	2402.2	2400.5	2398.8	2397.0	2395.3	2345.5	2295.7	2244.2	2194.4	2191.0
70°	1954.0	1933.4	1936.9	1942.0	1945.5	1948.9	1911.1	1875.1	1837.3	1799.5	1816.7
72.5°	1507.6	1471.5	1480.1	1490.4	1499.0	1507.6	1476.7	1447.5	1416.6	1385.7	1409.7
75°	1119.5	1097.2	1105.8	1116.1	1124.7	1133.3	1121.3	1109.2	1095.5	1083.5	1105.8
77.5°	853.4	839.7	841.4	841.4	843.1	843.1	844.8	848.2	850.0	851.7	875.7
80°	695.4	693.7	692.0	690.3	686.8	685.1	702.3	719.5	736.6	753.8	765.8
82.5°	607.8	625.0	614.7	606.1	595.8	585.5	601.0	616.4	631.9	647.3	642.2
85°	494.5	515.1	496.2	477.3	456.7	437.9	451.6	463.6	477.3	489.4	482.5
87.5°	195.7	200.9	170.0	140.8	109.9	79.0	125.3	170.0	216.4	261.0	267.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894

CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3	1236.3
2.5°	1334.2	1327.3	1322.2	1320.4	1317.0	1315.3	1311.9	1308.4	1303.3	1299.8	1294.7
5°	1378.8	1368.5	1356.5	1339.3	1323.9	1306.7	1289.5	1274.1	1258.6	1241.5	1226.0
7.5°	1380.5	1356.5	1332.5	1310.1	1286.1	1263.8	1239.7	1219.1	1196.8	1174.5	1153.9
10°	1361.6	1332.5	1303.3	1274.1	1246.6	1217.4	1188.2	1164.2	1138.4	1112.7	1088.6
12.5°	1346.2	1313.6	1280.9	1246.6	1214.0	1179.6	1145.3	1121.3	1097.2	1073.2	1049.1
15°	1327.3	1306.7	1287.8	1256.9	1226.0	1195.1	1164.2	1131.6	1100.7	1068.0	1035.4
17.5°	1311.9	1306.7	1301.5	1280.9	1260.3	1238.0	1217.4	1184.8	1152.2	1117.8	1085.2
20°	1303.3	1310.1	1317.0	1306.7	1296.4	1284.4	1274.1	1250.0	1226.0	1200.2	1176.2
22.5°	1313.6	1339.3	1363.4	1365.1	1368.5	1370.2	1372.0	1349.6	1327.3	1303.3	1280.9
25°	1337.6	1378.8	1420.0	1442.4	1464.7	1488.7	1511.0	1497.3	1483.6	1469.8	1456.1
27.5°	1370.2	1421.7	1473.3	1505.9	1536.8	1569.4	1602.0	1600.3	1598.6	1595.2	1593.5
30°	1365.1	1404.6	1444.1	1483.6	1523.1	1562.5	1602.0	1622.6	1641.5	1662.1	1682.7
32.5°	1394.3	1426.9	1461.2	1502.4	1543.7	1586.6	1627.8	1670.7	1711.9	1754.9	1797.8
35°	1438.9	1468.1	1499.0	1543.7	1590.0	1634.7	1681.0	1732.5	1785.8	1839.0	1890.5
37.5°	1505.9	1531.6	1559.1	1596.9	1636.4	1674.2	1713.7	1789.2	1864.8	1942.0	2017.6
40°	1583.2	1600.3	1617.5	1653.6	1689.6	1725.7	1761.7	1856.2	1950.6	2045.0	2139.5
42.5°	1694.8	1689.6	1684.5	1713.7	1744.6	1773.7	1804.7	1890.5	1976.4	2062.2	2148.1
45°	1813.2	1792.6	1772.0	1785.8	1801.2	1815.0	1830.4	1918.0	2005.6	2094.8	2182.4
47.5°	1955.8	1904.2	1852.7	1840.7	1828.7	1815.0	1802.9	1897.4	1991.8	2088.0	2182.4
50°	2117.2	2039.9	1964.3	1933.4	1900.8	1869.9	1837.3	1914.5	1993.5	2072.5	2149.8
52.5°	2285.4	2189.3	2094.8	2046.8	1998.7	1948.9	1900.8	1966.1	2033.0	2100.0	2165.2
55°	2429.7	2331.8	2232.2	2175.5	2118.9	2062.2	2005.6	2070.8	2136.1	2201.3	2266.6
57.5°	2544.7	2446.8	2349.0	2295.7	2240.8	2187.6	2132.6	2194.4	2258.0	2321.5	2383.3
60°	2623.7	2529.3	2434.8	2383.3	2331.8	2280.3	2228.8	2302.6	2376.4	2452.0	2525.8
62.5°	2582.5	2513.8	2445.1	2422.8	2400.5	2376.4	2354.1	2424.5	2493.2	2563.6	2634.0
65°	2431.4	2385.0	2338.7	2361.0	2385.0	2407.4	2431.4	2477.8	2524.1	2572.2	2618.6
67.5°	2185.8	2182.4	2177.3	2227.1	2276.9	2328.4	2378.2	2409.1	2438.3	2469.2	2500.1
70°	1833.8	1852.7	1869.9	1955.8	2041.6	2127.5	2213.3	2225.3	2237.4	2249.4	2261.4
72.5°	1435.5	1459.5	1485.3	1598.6	1710.2	1823.5	1936.9	1930.0	1923.1	1914.5	1907.7
75°	1129.8	1152.2	1176.2	1280.9	1385.7	1490.4	1595.2	1566.0	1538.5	1509.3	1480.1
77.5°	901.5	925.5	951.3	1049.1	1147.0	1246.6	1344.5	1274.1	1203.7	1133.3	1062.9
80°	776.1	788.1	798.4	865.4	930.7	997.6	1064.6	992.5	918.6	844.8	772.7
82.5°	637.0	630.2	625.0	664.5	704.0	743.5	783.0	714.3	645.6	575.2	506.5
85°	475.6	468.8	461.9	482.5	503.1	525.4	546.0	467.0	388.1	307.4	228.4
87.5°	276.5	283.3	290.2	312.5	334.8	358.9	381.2	300.5	219.8	137.4	56.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671894
 CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1236.3	1236.3
2.5°	1284.4	1275.8
5°	1214.0	1202.0
7.5°	1136.7	1121.3
10°	1066.3	1045.7
12.5°	1021.7	995.9
15°	1004.5	973.6
17.5°	1056.0	1026.8
20°	1135.0	1095.5
22.5°	1231.1	1183.1
25°	1397.7	1339.3
27.5°	1533.4	1473.3
30°	1617.5	1552.2
32.5°	1710.2	1624.4
35°	1806.4	1724.0
37.5°	1923.1	1830.4
40°	2043.3	1947.2
42.5°	2084.5	2022.7
45°	2124.0	2065.7
47.5°	2132.6	2084.5
50°	2141.2	2134.3
52.5°	2165.2	2163.5
55°	2268.3	2270.0
57.5°	2395.3	2405.6
60°	2512.1	2500.1
62.5°	2572.2	2510.4
65°	2531.0	2445.1
67.5°	2407.4	2314.6
70°	2136.1	2010.7
72.5°	1797.8	1687.9
75°	1385.7	1293.0
77.5°	985.6	908.3
80°	693.7	616.4
82.5°	444.7	382.9
85°	200.9	175.1
87.5°	56.7	54.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671894
CATALOG NUMBER: CCP-SA-2A-840-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)