

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671798

Luminaire Tested: **CCP-SA-2D-727-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671798
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2D-727-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @800mA w/ SLR distribution lens
Light Source: (32) 2700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7740.3 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3


Input Watts (W): 80.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 11 fc
 Type IV - Short - N/A

REPORT NUMBER: P671798
CATALOG NUMBER: CCP-SA-2D-727-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1592.6	0.0	1592.6
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	6147.7	0.0	6147.7
	% Fixture	79.4	0.0	79.4
Total	Lumens	7740.3	0.0	7740.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.1	2.5
10°-20°	405.5	5.2
20°-30°	593.3	7.7
30°-40°	835.8	10.8
40°-50°	1148.5	14.8
50°-60°	1565.5	20.2
60°-70°	1713.4	22.1
70°-80°	989.5	12.8
80°-90°	296.6	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7740.3	100.0
0°-180°	7740.3	100.0



REPORT NUMBER: P671798


CATALOG NUMBER: CCP-SA-2D-727-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	794.9	10.3			
FM (30°-60°)	2824.7	36.5			
FH (60°-80°)	2276.1	29.4			G2/5000
FVH (80°-90°)	251.9	3.3			G3/500
BL (0°-30°)	395.9	5.1	B1/500		
BM (30°-60°)	725.2	9.4	B1/1000		
BH (60°-80°)	426.8	5.5	B1/500		G1/500
BVH (80°-90°)	44.7	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short





REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2550.7	2537.0	2526.7	2516.4	2502.7	2492.4	2478.6	2464.9	2447.7	2434.0	2416.8
5°	2403.1	2361.9	2320.7	2296.7	2269.2	2245.2	2217.7	2186.8	2155.9	2121.6	2090.7
7.5°	2241.8	2190.3	2138.8	2097.6	2052.9	2011.7	1967.1	1929.4	1891.6	1853.8	1816.1
10°	2090.7	2042.6	1994.6	1943.1	1888.2	1836.7	1781.7	1730.2	1678.7	1627.2	1575.8
12.5°	1991.1	1932.8	1877.9	1819.5	1764.6	1706.2	1647.8	1599.8	1551.7	1500.2	1452.2
15°	1946.5	1891.6	1840.1	1781.7	1723.4	1665.0	1606.6	1551.7	1500.2	1445.3	1390.4
17.5°	2052.9	1974.0	1895.0	1819.5	1744.0	1668.4	1592.9	1524.3	1455.6	1386.9	1318.3
20°	2190.3	2090.7	1994.6	1901.9	1805.8	1713.1	1616.9	1520.8	1424.7	1328.6	1232.5
22.5°	2365.3	2252.1	2142.2	2022.0	1898.5	1778.3	1654.7	1534.6	1414.4	1290.8	1170.7
25°	2677.7	2543.9	2410.0	2238.3	2063.2	1891.6	1716.5	1558.6	1404.1	1246.2	1088.3
27.5°	2945.5	2763.6	2585.1	2379.1	2173.1	1967.1	1761.1	1579.2	1400.7	1218.7	1036.8
30°	3103.4	2924.9	2746.4	2495.8	2248.6	1998.0	1747.4	1544.9	1345.7	1143.2	940.6
32.5°	3247.6	3048.5	2849.4	2574.8	2296.7	2022.0	1744.0	1520.8	1301.1	1078.0	854.8
35°	3446.7	3227.0	3010.7	2691.5	2372.2	2052.9	1733.7	1503.7	1270.2	1040.2	806.8
37.5°	3659.6	3388.4	3120.6	2767.0	2413.4	2059.8	1706.2	1479.6	1253.0	1026.5	799.9
40°	3893.0	3563.5	3237.3	2846.0	2458.0	2066.7	1675.3	1448.7	1222.2	992.1	765.6
42.5°	4044.1	3687.1	3330.0	2907.8	2488.9	2066.7	1644.4	1421.3	1198.1	971.5	748.4
45°	4129.9	3783.2	3439.9	2983.3	2526.7	2070.1	1613.5	1393.8	1174.1	950.9	731.2
47.5°	4167.7	3845.0	3522.3	3041.6	2564.5	2083.8	1603.2	1380.1	1153.5	930.3	703.8
50°	4267.2	3982.3	3697.4	3182.4	2670.9	2155.9	1641.0	1400.7	1163.8	923.5	683.2
52.5°	4325.6	4081.8	3838.1	3309.4	2780.7	2252.1	1723.4	1455.6	1187.8	920.0	652.3
55°	4538.4	4305.0	4071.5	3508.5	2942.1	2379.1	1812.6	1517.4	1222.2	923.5	628.2
57.5°	4809.6	4562.5	4318.7	3711.1	3103.4	2495.8	1888.2	1572.3	1253.0	937.2	617.9
60°	4998.5	4758.2	4521.3	3875.9	3227.0	2581.6	1932.8	1603.2	1273.6	940.6	611.1
62.5°	5019.1	4710.1	4404.6	3776.3	3148.1	2516.4	1888.2	1568.9	1249.6	926.9	607.6
65°	4888.6	4528.1	4167.7	3566.9	2966.1	2365.3	1764.6	1472.8	1181.0	885.7	593.9
67.5°	4627.7	4205.4	3783.2	3233.9	2684.6	2135.3	1586.1	1335.4	1088.3	837.7	587.0
70°	4020.1	3649.3	3282.0	2804.8	2331.0	1853.8	1376.6	1170.7	968.1	762.1	556.1
72.5°	3374.6	3027.9	2684.6	2296.7	1912.2	1524.3	1136.3	981.8	827.4	669.4	515.0
75°	2585.1	2324.1	2066.7	1778.3	1489.9	1198.1	909.7	796.5	683.2	569.9	456.6
77.5°	1816.1	1675.3	1538.0	1321.7	1105.4	889.1	672.9	597.3	521.8	446.3	370.8
80°	1232.5	1153.5	1078.0	923.5	769.0	611.1	456.6	408.5	357.0	309.0	257.5
82.5°	765.6	762.1	755.3	648.8	542.4	436.0	329.6	288.4	250.6	209.4	168.2
85°	350.2	408.5	463.5	405.1	346.7	288.4	230.0	202.5	175.1	144.2	116.7
87.5°	109.9	133.9	154.5	147.6	137.3	130.5	120.2	103.0	85.8	68.7	51.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2403.1	2392.8	2379.1	2365.3	2348.2	2334.4	2317.3	2300.1	2296.7	2289.8	2286.4
5°	2070.1	2049.5	2025.5	2004.9	1984.3	1960.2	1939.6	1915.6	1898.5	1877.9	1860.7
7.5°	1778.3	1744.0	1706.2	1668.4	1634.1	1599.8	1562.0	1527.7	1510.5	1493.4	1476.2
10°	1544.9	1510.5	1479.6	1445.3	1421.3	1400.7	1376.6	1352.6	1332.0	1311.4	1290.8
12.5°	1428.1	1404.1	1380.1	1356.0	1328.6	1304.5	1277.1	1249.6	1225.6	1205.0	1181.0
15°	1356.0	1321.7	1283.9	1249.6	1211.9	1177.5	1139.8	1102.0	1074.5	1050.5	1023.0
17.5°	1270.2	1218.7	1170.7	1119.2	1078.0	1036.8	992.1	950.9	920.0	885.7	854.8
20°	1174.1	1115.7	1053.9	995.6	947.5	902.9	854.8	806.8	772.4	734.7	700.3
22.5°	1091.7	1016.2	937.2	858.3	806.8	755.3	700.3	648.8	617.9	583.6	552.7
25°	1002.4	920.0	834.2	748.4	696.9	642.0	590.5	535.5	511.5	490.9	466.9
27.5°	954.4	872.0	786.2	703.8	655.7	604.2	556.1	504.7	487.5	466.9	449.7
30°	858.3	779.3	696.9	614.5	580.2	549.3	515.0	480.6	473.8	470.3	463.5
32.5°	772.4	690.0	607.6	525.3	494.4	463.5	432.6	401.7	398.2	391.4	387.9
35°	727.8	648.8	566.4	487.5	460.0	429.1	401.7	370.8	363.9	353.6	346.7
37.5°	717.5	635.1	549.3	466.9	439.4	412.0	381.1	353.6	346.7	339.9	333.0
40°	690.0	611.1	535.5	456.6	429.1	401.7	370.8	343.3	336.4	329.6	322.7
42.5°	669.4	593.9	515.0	436.0	412.0	387.9	360.5	336.4	329.6	322.7	312.4
45°	652.3	573.3	490.9	412.0	394.8	377.6	357.0	339.9	333.0	322.7	315.8
47.5°	624.8	549.3	470.3	391.4	374.2	360.5	343.3	326.1	319.3	312.4	305.5
50°	604.2	525.3	446.3	367.3	353.6	339.9	326.1	312.4	312.4	315.8	315.8
52.5°	576.7	501.2	425.7	350.2	336.4	322.7	309.0	295.2	298.7	302.1	305.5
55°	552.7	480.6	405.1	329.6	315.8	302.1	284.9	271.2	274.6	278.1	281.5
57.5°	542.4	466.9	391.4	315.8	302.1	284.9	271.2	254.0	254.0	254.0	254.0
60°	535.5	456.6	381.1	302.1	284.9	271.2	254.0	236.9	233.4	233.4	230.0
62.5°	532.1	453.2	377.6	298.7	278.1	260.9	240.3	219.7	216.3	212.8	209.4
65°	518.4	446.3	370.8	295.2	271.2	250.6	226.6	202.5	199.1	199.1	195.7
67.5°	515.0	439.4	367.3	291.8	267.8	240.3	216.3	188.8	185.4	181.9	178.5
70°	487.5	422.3	353.6	284.9	257.5	233.4	206.0	178.5	175.1	168.2	164.8
72.5°	453.2	394.8	333.0	271.2	243.7	216.3	188.8	161.4	157.9	154.5	147.6
75°	401.7	346.7	291.8	236.9	212.8	192.2	168.2	144.2	140.8	137.3	130.5
77.5°	329.6	284.9	243.7	199.1	181.9	164.8	147.6	130.5	127.0	123.6	116.7
80°	233.4	206.0	181.9	154.5	144.2	130.5	120.2	106.4	106.4	103.0	103.0
82.5°	154.5	140.8	127.0	113.3	106.4	99.6	92.7	85.8	85.8	82.4	82.4
85°	109.9	103.0	92.7	85.8	82.4	75.5	72.1	65.2	65.2	65.2	65.2
87.5°	51.5	51.5	48.1	48.1	44.6	44.6	41.2	37.8	37.8	37.8	37.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2279.5	2269.2	2258.9	2245.2	2234.9	2221.2	2204.0	2190.3	2173.1	2173.1	2169.7
5°	1840.1	1829.8	1819.5	1805.8	1795.5	1781.7	1771.4	1757.7	1744.0	1744.0	1740.5
7.5°	1459.0	1438.4	1417.8	1393.8	1373.2	1359.5	1345.7	1328.6	1314.8	1304.5	1294.2
10°	1270.2	1249.6	1225.6	1205.0	1181.0	1163.8	1146.6	1126.0	1108.9	1095.1	1081.4
12.5°	1156.9	1132.9	1108.9	1084.8	1060.8	1036.8	1016.2	992.1	968.1	950.9	933.8
15°	995.6	971.5	947.5	923.5	899.4	872.0	844.5	813.6	786.2	772.4	762.1
17.5°	820.5	796.5	769.0	745.0	717.5	696.9	676.3	655.7	635.1	621.4	611.1
20°	662.6	635.1	607.6	580.2	552.7	539.0	525.3	511.5	497.8	487.5	480.6
22.5°	518.4	501.2	487.5	470.3	453.2	442.9	436.0	425.7	415.4	415.4	415.4
25°	442.9	432.6	425.7	415.4	405.1	401.7	398.2	391.4	387.9	384.5	384.5
27.5°	429.1	418.8	408.5	398.2	387.9	384.5	381.1	374.2	370.8	370.8	370.8
30°	456.6	453.2	449.7	446.3	442.9	436.0	425.7	418.8	408.5	401.7	394.8
32.5°	381.1	377.6	377.6	374.2	370.8	377.6	381.1	387.9	391.4	394.8	398.2
35°	336.4	329.6	322.7	315.8	309.0	305.5	302.1	298.7	295.2	295.2	291.8
37.5°	326.1	319.3	312.4	305.5	298.7	295.2	291.8	288.4	284.9	284.9	281.5
40°	315.8	309.0	305.5	298.7	291.8	288.4	284.9	278.1	274.6	271.2	271.2
42.5°	305.5	302.1	295.2	291.8	284.9	281.5	278.1	271.2	267.8	264.3	260.9
45°	305.5	298.7	291.8	284.9	278.1	274.6	267.8	264.3	257.5	257.5	254.0
47.5°	298.7	291.8	284.9	278.1	271.2	267.8	260.9	257.5	250.6	247.2	243.7
50°	315.8	305.5	291.8	281.5	267.8	264.3	257.5	254.0	247.2	243.7	240.3
52.5°	309.0	298.7	284.9	274.6	260.9	254.0	250.6	243.7	236.9	233.4	230.0
55°	284.9	274.6	267.8	257.5	247.2	240.3	233.4	226.6	219.7	216.3	216.3
57.5°	254.0	250.6	247.2	243.7	240.3	233.4	226.6	216.3	209.4	206.0	202.5
60°	226.6	230.0	233.4	236.9	240.3	230.0	219.7	209.4	199.1	195.7	192.2
62.5°	206.0	212.8	219.7	223.1	230.0	219.7	209.4	199.1	188.8	185.4	181.9
65°	192.2	195.7	195.7	199.1	199.1	192.2	188.8	181.9	175.1	171.7	171.7
67.5°	175.1	175.1	175.1	171.7	171.7	168.2	168.2	164.8	161.4	157.9	157.9
70°	157.9	157.9	157.9	154.5	154.5	151.1	151.1	147.6	144.2	144.2	140.8
72.5°	144.2	144.2	140.8	140.8	137.3	137.3	137.3	133.9	133.9	130.5	130.5
75°	127.0	127.0	123.6	123.6	120.2	120.2	120.2	116.7	116.7	116.7	113.3
77.5°	113.3	113.3	109.9	109.9	106.4	106.4	106.4	103.0	103.0	99.6	99.6
80°	99.6	99.6	96.1	96.1	92.7	92.7	89.3	89.3	85.8	85.8	82.4
82.5°	79.0	79.0	79.0	79.0	79.0	75.5	75.5	72.1	68.7	68.7	65.2
85°	65.2	65.2	65.2	61.8	61.8	61.8	58.4	58.4	54.9	51.5	51.5
87.5°	37.8	37.8	37.8	34.3	34.3	34.3	34.3	34.3	34.3	34.3	30.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2169.7	2166.2	2152.5	2138.8	2152.5	2166.2	2166.2	2166.2	2162.8	2162.8	2162.8
5°	1740.5	1737.1	1730.2	1723.4	1723.4	1719.9	1726.8	1733.7	1740.5	1747.4	1754.3
7.5°	1280.5	1270.2	1259.9	1249.6	1256.5	1259.9	1270.2	1277.1	1287.4	1294.2	1311.4
10°	1067.7	1053.9	1043.6	1033.3	1026.5	1019.6	1012.7	1009.3	1002.4	995.6	1002.4
12.5°	913.2	896.0	878.9	858.3	854.8	851.4	844.5	837.7	830.8	823.9	820.5
15°	748.4	734.7	727.8	717.5	703.8	690.0	683.2	679.7	672.9	666.0	662.6
17.5°	597.3	583.6	573.3	563.0	559.6	552.7	552.7	552.7	552.7	552.7	552.7
20°	470.3	460.0	460.0	456.6	456.6	453.2	456.6	460.0	460.0	463.5	466.9
22.5°	412.0	412.0	408.5	405.1	408.5	408.5	412.0	415.4	418.8	422.3	425.7
25°	381.1	377.6	381.1	384.5	384.5	384.5	387.9	387.9	391.4	391.4	391.4
27.5°	367.3	367.3	370.8	370.8	374.2	374.2	374.2	370.8	370.8	367.3	367.3
30°	387.9	381.1	381.1	381.1	377.6	374.2	370.8	370.8	367.3	363.9	360.5
32.5°	401.7	405.1	401.7	394.8	391.4	384.5	381.1	374.2	370.8	363.9	357.0
35°	291.8	288.4	295.2	298.7	302.1	305.5	309.0	312.4	312.4	315.8	315.8
37.5°	281.5	278.1	278.1	274.6	274.6	274.6	274.6	274.6	271.2	271.2	274.6
40°	267.8	264.3	264.3	260.9	260.9	257.5	257.5	257.5	257.5	257.5	257.5
42.5°	257.5	254.0	254.0	254.0	254.0	250.6	250.6	247.2	247.2	243.7	243.7
45°	254.0	250.6	247.2	243.7	243.7	240.3	240.3	240.3	236.9	236.9	236.9
47.5°	240.3	236.9	236.9	233.4	233.4	230.0	230.0	230.0	226.6	226.6	226.6
50°	233.4	230.0	230.0	226.6	226.6	223.1	223.1	223.1	219.7	219.7	219.7
52.5°	223.1	219.7	219.7	219.7	216.3	212.8	212.8	212.8	209.4	209.4	209.4
55°	212.8	209.4	209.4	209.4	206.0	202.5	202.5	202.5	199.1	199.1	199.1
57.5°	199.1	195.7	195.7	192.2	192.2	192.2	192.2	192.2	188.8	188.8	188.8
60°	188.8	185.4	185.4	181.9	181.9	178.5	178.5	178.5	178.5	178.5	178.5
62.5°	178.5	175.1	171.7	168.2	171.7	171.7	171.7	171.7	168.2	168.2	168.2
65°	168.2	164.8	161.4	157.9	157.9	157.9	157.9	157.9	157.9	157.9	157.9
67.5°	154.5	151.1	147.6	144.2	147.6	147.6	147.6	147.6	147.6	147.6	147.6
70°	140.8	137.3	137.3	133.9	133.9	130.5	130.5	133.9	133.9	133.9	133.9
72.5°	127.0	123.6	123.6	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2
75°	113.3	109.9	109.9	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4
77.5°	96.1	92.7	92.7	92.7	92.7	92.7	92.7	96.1	96.1	96.1	96.1
80°	82.4	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0
82.5°	65.2	61.8	61.8	61.8	61.8	61.8	61.8	61.8	61.8	61.8	61.8
85°	48.1	44.6	44.6	44.6	48.1	48.1	48.1	48.1	48.1	48.1	48.1
87.5°	30.9	27.5	27.5	27.5	30.9	30.9	30.9	30.9	27.5	27.5	27.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2162.8	2162.8	2162.8	2159.4	2155.9	2152.5	2149.1	2159.4	2166.2	2176.5	2183.4
5°	1757.7	1764.6	1768.0	1778.3	1788.6	1798.9	1809.2	1816.1	1822.9	1826.4	1833.2
7.5°	1325.1	1342.3	1356.0	1369.8	1383.5	1393.8	1407.5	1417.8	1428.1	1438.4	1448.7
10°	1005.9	1012.7	1016.2	1029.9	1040.2	1053.9	1064.2	1074.5	1084.8	1091.7	1102.0
12.5°	817.1	810.2	806.8	806.8	806.8	806.8	806.8	813.6	820.5	827.4	834.2
15°	659.1	655.7	652.3	648.8	645.4	638.5	635.1	642.0	648.8	655.7	662.6
17.5°	552.7	552.7	552.7	549.3	545.8	542.4	539.0	542.4	545.8	545.8	549.3
20°	473.8	477.2	480.6	484.1	484.1	487.5	487.5	490.9	494.4	494.4	497.8
22.5°	425.7	429.1	429.1	429.1	432.6	432.6	432.6	436.0	439.4	442.9	446.3
25°	387.9	387.9	384.5	384.5	387.9	387.9	387.9	387.9	391.4	391.4	391.4
27.5°	367.3	363.9	363.9	363.9	363.9	360.5	360.5	360.5	360.5	360.5	360.5
30°	357.0	353.6	350.2	346.7	346.7	343.3	339.9	339.9	339.9	339.9	339.9
32.5°	353.6	346.7	339.9	336.4	336.4	333.0	329.6	326.1	326.1	322.7	319.3
35°	315.8	312.4	312.4	309.0	305.5	302.1	298.7	298.7	298.7	295.2	295.2
37.5°	274.6	278.1	278.1	278.1	281.5	281.5	281.5	281.5	284.9	284.9	284.9
40°	257.5	257.5	257.5	260.9	264.3	264.3	267.8	267.8	271.2	271.2	271.2
42.5°	243.7	240.3	240.3	243.7	243.7	247.2	247.2	250.6	254.0	254.0	257.5
45°	236.9	233.4	233.4	233.4	233.4	230.0	230.0	233.4	236.9	240.3	243.7
47.5°	223.1	223.1	219.7	219.7	219.7	219.7	219.7	219.7	223.1	223.1	223.1
50°	216.3	216.3	212.8	212.8	212.8	212.8	212.8	212.8	212.8	212.8	212.8
52.5°	209.4	206.0	206.0	206.0	206.0	202.5	202.5	202.5	202.5	202.5	202.5
55°	199.1	195.7	195.7	195.7	195.7	195.7	195.7	195.7	199.1	199.1	199.1
57.5°	188.8	185.4	185.4	185.4	188.8	188.8	188.8	188.8	192.2	192.2	192.2
60°	178.5	178.5	178.5	178.5	178.5	178.5	178.5	181.9	181.9	185.4	185.4
62.5°	168.2	168.2	168.2	168.2	171.7	171.7	171.7	171.7	175.1	175.1	175.1
65°	157.9	157.9	157.9	157.9	161.4	161.4	161.4	161.4	161.4	161.4	161.4
67.5°	147.6	147.6	147.6	147.6	147.6	147.6	147.6	151.1	151.1	154.5	154.5
70°	133.9	130.5	130.5	133.9	133.9	137.3	137.3	140.8	140.8	144.2	144.2
72.5°	120.2	120.2	120.2	120.2	120.2	120.2	120.2	123.6	127.0	127.0	130.5
75°	106.4	106.4	106.4	106.4	109.9	109.9	109.9	113.3	113.3	116.7	116.7
77.5°	96.1	92.7	92.7	92.7	96.1	96.1	96.1	99.6	99.6	103.0	103.0
80°	79.0	79.0	79.0	79.0	82.4	82.4	82.4	82.4	85.8	85.8	85.8
82.5°	65.2	65.2	65.2	65.2	65.2	65.2	65.2	65.2	68.7	68.7	68.7
85°	48.1	48.1	48.1	48.1	51.5	51.5	51.5	51.5	51.5	51.5	51.5
87.5°	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9	34.3	34.3	34.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2183.4	2183.4	2183.4	2183.4	2190.3	2193.7	2200.6	2204.0	2200.6	2197.1	2190.3
5°	1836.7	1840.1	1840.1	1843.5	1843.5	1843.5	1843.5	1843.5	1850.4	1857.3	1864.1
7.5°	1452.2	1455.6	1459.0	1462.5	1462.5	1462.5	1459.0	1459.0	1462.5	1462.5	1465.9
10°	1112.3	1126.0	1136.3	1146.6	1139.8	1129.5	1122.6	1112.3	1112.3	1112.3	1108.9
12.5°	841.1	844.5	851.4	854.8	851.4	851.4	848.0	844.5	848.0	854.8	858.3
15°	666.0	666.0	669.4	669.4	672.9	676.3	676.3	679.7	686.6	690.0	696.9
17.5°	552.7	556.1	556.1	559.6	559.6	563.0	563.0	563.0	569.9	576.7	587.0
20°	497.8	497.8	497.8	497.8	497.8	494.4	494.4	490.9	494.4	501.2	504.7
22.5°	446.3	449.7	449.7	449.7	446.3	442.9	436.0	432.6	432.6	436.0	436.0
25°	391.4	387.9	387.9	384.5	384.5	387.9	387.9	387.9	391.4	391.4	394.8
27.5°	360.5	357.0	357.0	353.6	353.6	357.0	357.0	357.0	357.0	357.0	357.0
30°	336.4	336.4	333.0	329.6	333.0	333.0	336.4	336.4	339.9	339.9	343.3
32.5°	319.3	315.8	315.8	312.4	315.8	315.8	319.3	319.3	322.7	326.1	326.1
35°	295.2	295.2	295.2	295.2	295.2	295.2	291.8	291.8	291.8	291.8	291.8
37.5°	281.5	281.5	278.1	274.6	274.6	274.6	274.6	274.6	271.2	267.8	264.3
40°	271.2	267.8	267.8	264.3	260.9	260.9	257.5	254.0	254.0	250.6	250.6
42.5°	257.5	254.0	254.0	250.6	247.2	247.2	243.7	240.3	240.3	240.3	236.9
45°	240.3	240.3	236.9	233.4	233.4	233.4	230.0	230.0	230.0	230.0	226.6
47.5°	223.1	223.1	219.7	219.7	219.7	219.7	216.3	216.3	216.3	216.3	216.3
50°	212.8	212.8	212.8	212.8	212.8	212.8	209.4	209.4	209.4	209.4	209.4
52.5°	202.5	202.5	202.5	202.5	202.5	202.5	202.5	202.5	202.5	202.5	202.5
55°	199.1	199.1	199.1	199.1	199.1	199.1	195.7	195.7	195.7	199.1	199.1
57.5°	192.2	192.2	188.8	188.8	188.8	188.8	188.8	188.8	188.8	188.8	188.8
60°	185.4	185.4	185.4	185.4	185.4	185.4	185.4	185.4	185.4	185.4	185.4
62.5°	175.1	175.1	175.1	175.1	175.1	178.5	178.5	178.5	178.5	178.5	175.1
65°	161.4	164.8	164.8	164.8	164.8	164.8	164.8	164.8	164.8	164.8	164.8
67.5°	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5
70°	144.2	144.2	140.8	140.8	140.8	144.2	144.2	144.2	144.2	144.2	144.2
72.5°	130.5	130.5	130.5	130.5	130.5	130.5	130.5	130.5	130.5	133.9	133.9
75°	116.7	116.7	116.7	116.7	116.7	116.7	116.7	116.7	116.7	116.7	116.7
77.5°	103.0	103.0	99.6	99.6	99.6	103.0	103.0	103.0	103.0	106.4	106.4
80°	85.8	85.8	85.8	85.8	85.8	85.8	85.8	85.8	85.8	89.3	89.3
82.5°	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.7	72.1	72.1
85°	51.5	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	58.4	58.4
87.5°	34.3	34.3	34.3	34.3	34.3	34.3	30.9	30.9	30.9	30.9	27.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2186.8	2190.3	2193.7	2193.7	2197.1	2200.6	2200.6	2214.3	2228.0	2234.9	2241.8
5°	1871.0	1867.6	1867.6	1864.1	1860.7	1871.0	1881.3	1901.9	1922.5	1925.9	1932.8
7.5°	1465.9	1469.3	1472.8	1472.8	1476.2	1465.9	1452.2	1455.6	1459.0	1476.2	1489.9
10°	1108.9	1112.3	1115.7	1115.7	1119.2	1115.7	1108.9	1119.2	1129.5	1143.2	1160.4
12.5°	861.7	872.0	882.3	889.1	899.4	906.3	909.7	923.5	933.8	950.9	968.1
15°	703.8	710.6	717.5	724.4	731.2	738.1	745.0	758.7	772.4	793.0	813.6
17.5°	593.9	593.9	597.3	597.3	597.3	604.2	611.1	617.9	621.4	642.0	662.6
20°	508.1	504.7	501.2	497.8	494.4	501.2	504.7	508.1	511.5	525.3	535.5
22.5°	436.0	436.0	439.4	439.4	439.4	436.0	429.1	432.6	432.6	439.4	449.7
25°	394.8	394.8	394.8	391.4	391.4	394.8	398.2	398.2	394.8	398.2	401.7
27.5°	357.0	360.5	360.5	363.9	363.9	367.3	367.3	367.3	367.3	370.8	374.2
30°	343.3	343.3	346.7	346.7	346.7	350.2	353.6	353.6	353.6	357.0	363.9
32.5°	329.6	333.0	336.4	339.9	343.3	346.7	346.7	350.2	350.2	353.6	357.0
35°	291.8	288.4	288.4	284.9	281.5	281.5	281.5	281.5	278.1	281.5	281.5
37.5°	260.9	260.9	260.9	257.5	257.5	260.9	260.9	260.9	260.9	264.3	264.3
40°	247.2	247.2	247.2	247.2	247.2	247.2	247.2	250.6	250.6	254.0	257.5
42.5°	236.9	236.9	236.9	236.9	236.9	240.3	240.3	240.3	240.3	243.7	243.7
45°	226.6	226.6	226.6	226.6	226.6	226.6	226.6	230.0	230.0	233.4	236.9
47.5°	216.3	216.3	216.3	216.3	216.3	219.7	223.1	223.1	223.1	226.6	226.6
50°	209.4	209.4	209.4	209.4	209.4	212.8	212.8	216.3	216.3	219.7	223.1
52.5°	202.5	202.5	202.5	202.5	202.5	206.0	206.0	209.4	209.4	212.8	216.3
55°	199.1	199.1	199.1	195.7	195.7	199.1	199.1	202.5	202.5	206.0	206.0
57.5°	188.8	188.8	188.8	188.8	188.8	188.8	188.8	192.2	192.2	195.7	199.1
60°	185.4	185.4	181.9	181.9	178.5	181.9	181.9	185.4	185.4	188.8	188.8
62.5°	175.1	175.1	175.1	171.7	171.7	175.1	175.1	175.1	175.1	178.5	181.9
65°	164.8	164.8	164.8	161.4	161.4	164.8	164.8	164.8	164.8	168.2	171.7
67.5°	154.5	154.5	154.5	151.1	151.1	151.1	151.1	154.5	154.5	157.9	161.4
70°	144.2	144.2	144.2	140.8	140.8	140.8	137.3	140.8	144.2	147.6	147.6
72.5°	133.9	133.9	133.9	130.5	130.5	130.5	127.0	130.5	130.5	133.9	133.9
75°	116.7	116.7	116.7	116.7	116.7	116.7	113.3	113.3	113.3	116.7	116.7
77.5°	106.4	106.4	106.4	103.0	103.0	103.0	99.6	99.6	99.6	103.0	103.0
80°	89.3	89.3	89.3	85.8	85.8	85.8	82.4	82.4	82.4	85.8	85.8
82.5°	72.1	72.1	72.1	68.7	68.7	68.7	65.2	65.2	65.2	68.7	68.7
85°	58.4	58.4	58.4	58.4	58.4	58.4	54.9	54.9	54.9	58.4	61.8
87.5°	27.5	27.5	30.9	30.9	30.9	30.9	27.5	27.5	24.0	24.0	27.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2248.6	2255.5	2272.7	2286.4	2303.5	2317.3	2327.6	2341.3	2351.6	2361.9	2368.8
5°	1936.2	1939.6	1956.8	1974.0	1987.7	2004.9	2028.9	2052.9	2077.0	2101.0	2118.2
7.5°	1507.1	1520.8	1541.4	1565.5	1586.1	1606.6	1630.7	1658.1	1682.2	1706.2	1730.2
10°	1174.1	1187.8	1208.4	1229.0	1246.2	1266.8	1294.2	1321.7	1349.2	1376.6	1404.1
12.5°	985.3	1002.4	1026.5	1050.5	1071.1	1095.1	1129.5	1160.4	1194.7	1225.6	1259.9
15°	830.8	851.4	882.3	916.6	947.5	978.4	1012.7	1047.1	1078.0	1112.3	1146.6
17.5°	683.2	703.8	731.2	762.1	789.6	817.1	858.3	896.0	937.2	975.0	1012.7
20°	549.3	559.6	587.0	614.5	642.0	669.4	700.3	731.2	762.1	793.0	841.1
22.5°	456.6	463.5	477.2	487.5	501.2	511.5	542.4	573.3	600.8	631.7	676.3
25°	401.7	405.1	415.4	422.3	432.6	439.4	460.0	477.2	497.8	515.0	556.1
27.5°	374.2	377.6	381.1	384.5	387.9	391.4	405.1	418.8	429.1	442.9	480.6
30°	367.3	370.8	381.1	387.9	398.2	405.1	412.0	418.8	425.7	432.6	456.6
32.5°	360.5	363.9	363.9	360.5	360.5	357.0	363.9	367.3	374.2	377.6	398.2
35°	284.9	284.9	288.4	291.8	295.2	298.7	309.0	315.8	326.1	333.0	350.2
37.5°	267.8	267.8	271.2	278.1	281.5	284.9	291.8	298.7	305.5	312.4	329.6
40°	257.5	260.9	264.3	267.8	271.2	274.6	281.5	284.9	291.8	295.2	309.0
42.5°	247.2	247.2	250.6	257.5	260.9	264.3	271.2	274.6	281.5	284.9	298.7
45°	240.3	243.7	247.2	250.6	250.6	254.0	260.9	267.8	271.2	278.1	291.8
47.5°	230.0	230.0	236.9	240.3	247.2	250.6	257.5	260.9	267.8	271.2	284.9
50°	223.1	226.6	233.4	236.9	243.7	247.2	257.5	264.3	274.6	281.5	288.4
52.5°	216.3	219.7	226.6	230.0	236.9	240.3	254.0	267.8	278.1	291.8	291.8
55°	209.4	209.4	216.3	226.6	233.4	240.3	247.2	257.5	264.3	271.2	271.2
57.5°	199.1	202.5	209.4	219.7	226.6	233.4	240.3	247.2	250.6	257.5	254.0
60°	192.2	192.2	202.5	212.8	223.1	233.4	233.4	233.4	230.0	230.0	230.0
62.5°	181.9	185.4	199.1	216.3	230.0	243.7	233.4	223.1	212.8	202.5	206.0
65°	175.1	178.5	185.4	195.7	202.5	209.4	202.5	199.1	192.2	185.4	188.8
67.5°	161.4	164.8	168.2	168.2	171.7	171.7	171.7	171.7	171.7	171.7	175.1
70°	151.1	151.1	151.1	154.5	154.5	154.5	154.5	154.5	154.5	154.5	157.9
72.5°	137.3	137.3	137.3	137.3	137.3	137.3	137.3	137.3	137.3	137.3	140.8
75°	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2	123.6
77.5°	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4	103.0	103.0	106.4
80°	89.3	89.3	89.3	89.3	85.8	85.8	85.8	85.8	85.8	85.8	89.3
82.5°	72.1	72.1	72.1	72.1	68.7	68.7	68.7	68.7	65.2	65.2	68.7
85°	65.2	68.7	68.7	72.1	72.1	72.1	68.7	65.2	61.8	58.4	58.4
87.5°	27.5	27.5	27.5	27.5	24.0	24.0	24.0	24.0	24.0	24.0	24.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2379.1	2385.9	2392.8	2403.1	2416.8	2427.1	2437.4	2458.0	2482.1	2502.7	2523.3
5°	2135.3	2152.5	2169.7	2190.3	2210.9	2228.0	2248.6	2289.8	2331.0	2368.8	2410.0
7.5°	1750.8	1774.9	1795.5	1829.8	1860.7	1895.0	1925.9	1977.4	2025.5	2077.0	2125.0
10°	1431.6	1459.0	1486.5	1531.1	1579.2	1623.8	1668.4	1709.6	1754.3	1795.5	1836.7
12.5°	1294.2	1325.1	1359.5	1386.9	1417.8	1445.3	1472.8	1520.8	1568.9	1616.9	1665.0
15°	1181.0	1215.3	1249.6	1283.9	1314.8	1349.2	1380.1	1421.3	1465.9	1507.1	1548.3
17.5°	1050.5	1084.8	1122.6	1160.4	1198.1	1235.9	1273.6	1332.0	1390.4	1445.3	1503.7
20°	885.7	933.8	978.4	1029.9	1081.4	1132.9	1184.4	1246.2	1308.0	1366.3	1428.1
22.5°	720.9	765.6	810.2	872.0	933.8	992.1	1053.9	1136.3	1215.3	1297.7	1376.6
25°	600.8	642.0	683.2	751.8	817.1	885.7	950.9	1050.5	1146.6	1246.2	1342.3
27.5°	518.4	556.1	593.9	666.0	738.1	806.8	878.9	988.7	1095.1	1205.0	1311.4
30°	480.6	504.7	528.7	597.3	666.0	731.2	799.9	906.3	1012.7	1119.2	1225.6
32.5°	418.8	439.4	460.0	521.8	583.6	642.0	703.8	813.6	920.0	1029.9	1136.3
35°	370.8	387.9	405.1	463.5	518.4	576.7	631.7	741.5	851.4	961.2	1071.1
37.5°	343.3	360.5	374.2	425.7	480.6	532.1	583.6	693.5	799.9	909.7	1016.2
40°	322.7	333.0	346.7	398.2	446.3	497.8	545.8	645.4	748.4	848.0	947.5
42.5°	309.0	322.7	333.0	377.6	425.7	470.3	515.0	611.1	707.2	799.9	896.0
45°	305.5	319.3	333.0	370.8	408.5	442.9	480.6	573.3	666.0	758.7	851.4
47.5°	298.7	309.0	322.7	353.6	381.1	412.0	439.4	532.1	624.8	714.1	806.8
50°	295.2	298.7	305.5	333.0	360.5	387.9	415.4	508.1	600.8	693.5	786.2
52.5°	291.8	291.8	291.8	315.8	339.9	360.5	384.5	477.2	573.3	666.0	758.7
55°	271.2	267.8	267.8	291.8	312.4	336.4	357.0	449.7	542.4	631.7	724.4
57.5°	250.6	247.2	243.7	264.3	284.9	305.5	326.1	418.8	515.0	607.6	700.3
60°	230.0	226.6	226.6	247.2	264.3	284.9	302.1	398.2	490.9	587.0	679.7
62.5°	206.0	209.4	209.4	226.6	247.2	264.3	281.5	377.6	477.2	573.3	669.4
65°	188.8	192.2	192.2	212.8	233.4	254.0	274.6	367.3	463.5	556.1	648.8
67.5°	175.1	178.5	178.5	202.5	223.1	247.2	267.8	350.2	436.0	518.4	600.8
70°	161.4	161.4	164.8	188.8	212.8	236.9	260.9	333.0	405.1	473.8	545.8
72.5°	144.2	147.6	151.1	175.1	195.7	219.7	240.3	305.5	370.8	436.0	501.2
75°	127.0	130.5	133.9	154.5	175.1	195.7	216.3	278.1	336.4	398.2	456.6
77.5°	113.3	116.7	120.2	137.3	154.5	171.7	188.8	233.4	281.5	326.1	370.8
80°	92.7	92.7	96.1	109.9	123.6	133.9	147.6	178.5	209.4	236.9	267.8
82.5°	68.7	72.1	72.1	82.4	89.3	99.6	106.4	123.6	137.3	154.5	168.2
85°	58.4	54.9	54.9	61.8	65.2	72.1	75.5	85.8	92.7	103.0	109.9
87.5°	24.0	20.6	20.6	24.0	30.9	34.3	37.8	37.8	41.2	41.2	41.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2533.6	2540.4	2550.7	2557.6	2574.8	2588.5	2605.7	2619.4	2629.7	2646.8	2640.0
5°	2440.9	2471.8	2502.7	2533.6	2557.6	2581.6	2602.2	2626.3	2653.7	2705.2	2718.9
7.5°	2166.2	2207.4	2245.2	2286.4	2334.4	2382.5	2430.6	2478.6	2523.3	2588.5	2629.7
10°	1895.0	1953.4	2008.3	2066.7	2111.3	2155.9	2197.1	2241.8	2303.5	2368.8	2444.3
12.5°	1723.4	1781.7	1840.1	1898.5	1963.7	2025.5	2090.7	2152.5	2210.9	2262.4	2348.2
15°	1610.1	1675.3	1737.1	1798.9	1877.9	1953.4	2032.3	2107.9	2193.7	2262.4	2320.7
17.5°	1582.6	1661.6	1737.1	1816.1	1898.5	1980.8	2063.2	2145.6	2231.5	2334.4	2410.0
20°	1534.6	1641.0	1747.4	1853.8	1960.2	2063.2	2169.7	2272.7	2385.9	2509.5	2543.9
22.5°	1507.1	1634.1	1764.6	1891.6	2035.8	2183.4	2327.6	2471.8	2591.9	2684.6	2787.6
25°	1503.7	1661.6	1822.9	1980.8	2162.8	2341.3	2523.3	2701.8	2856.3	2949.0	3031.3
27.5°	1500.2	1692.5	1881.3	2070.1	2293.2	2513.0	2736.1	2955.8	3100.0	3233.9	3302.6
30°	1459.0	1689.0	1922.5	2152.5	2403.1	2653.7	2904.3	3154.9	3302.6	3395.2	3429.6
32.5°	1407.5	1678.7	1949.9	2221.2	2506.1	2791.0	3072.5	3357.5	3474.2	3553.2	3525.7
35°	1366.3	1665.0	1960.2	2255.5	2557.6	2863.1	3165.2	3467.3	3635.6	3745.4	3700.8
37.5°	1328.6	1641.0	1953.4	2265.8	2619.4	2973.0	3326.6	3680.2	3841.5	3958.3	3906.8
40°	1283.9	1616.9	1953.4	2286.4	2691.5	3093.1	3498.2	3899.9	4109.3	4208.9	4129.9
42.5°	1246.2	1592.9	1943.1	2289.8	2722.4	3154.9	3587.5	4020.1	4253.5	4394.3	4294.7
45°	1198.1	1544.9	1888.2	2234.9	2712.1	3189.3	3663.0	4140.2	4411.4	4521.3	4384.0
47.5°	1146.6	1489.9	1829.8	2169.7	2677.7	3185.8	3693.9	4202.0	4452.6	4583.1	4456.0
50°	1129.5	1472.8	1812.6	2155.9	2705.2	3257.9	3807.2	4356.5	4538.4	4644.9	4476.6
52.5°	1126.0	1489.9	1857.3	2221.2	2773.9	3323.2	3875.9	4425.1	4572.8	4686.1	4535.0
55°	1115.7	1510.5	1901.9	2293.2	2870.0	3450.2	4026.9	4603.7	4751.3	4833.7	4720.4
57.5°	1126.0	1551.7	1974.0	2399.7	2993.6	3587.5	4181.4	4775.3	4953.8	5012.2	4988.2
60°	1132.9	1586.1	2035.8	2488.9	3069.1	3649.3	4229.5	4809.6	4995.0	5139.2	5166.7
62.5°	1115.7	1562.0	2004.9	2451.2	2976.4	3501.7	4026.9	4552.2	4857.7	5070.6	5194.1
65°	1064.2	1476.2	1891.6	2303.5	2787.6	3275.1	3759.1	4243.2	4565.9	4881.7	4981.3
67.5°	950.9	1301.1	1651.3	2001.4	2423.7	2846.0	3264.8	3687.1	4092.1	4397.7	4535.0
70°	823.9	1098.6	1376.6	1651.3	2035.8	2420.3	2804.8	3189.3	3546.3	3882.7	4013.2
72.5°	717.5	930.3	1146.6	1359.5	1634.1	1905.3	2180.0	2451.2	2873.4	3209.9	3336.9
75°	611.1	765.6	916.6	1071.1	1259.9	1448.7	1634.1	1822.9	2121.6	2423.7	2550.7
77.5°	470.3	573.3	672.9	772.4	902.9	1029.9	1160.4	1287.4	1496.8	1723.4	1788.6
80°	326.1	384.5	439.4	497.8	600.8	703.8	806.8	909.7	1047.1	1174.1	1273.6
82.5°	202.5	240.3	274.6	309.0	391.4	473.8	552.7	635.1	690.0	696.9	796.5
85°	130.5	154.5	175.1	195.7	243.7	295.2	343.3	391.4	350.2	326.1	387.9
87.5°	51.5	65.2	75.5	85.8	82.4	79.0	75.5	72.1	61.8	54.9	68.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2646.8	2657.1	2667.4	2674.3	2684.6	2688.0	2691.5	2691.5	2694.9	2698.3	2705.2
5°	2773.9	2794.5	2815.1	2832.2	2852.8	2870.0	2883.7	2900.9	2914.6	2914.6	2911.2
7.5°	2667.4	2718.9	2770.4	2821.9	2873.4	2911.2	2945.5	2983.3	3017.6	3024.5	3031.3
10°	2526.7	2581.6	2633.1	2688.0	2739.5	2797.9	2852.8	2907.8	2966.1	2976.4	2990.2
12.5°	2396.2	2461.5	2526.7	2588.5	2653.7	2694.9	2736.1	2773.9	2815.1	2842.5	2870.0
15°	2392.8	2447.7	2502.7	2554.2	2609.1	2633.1	2657.1	2677.7	2701.8	2701.8	2705.2
17.5°	2471.8	2506.1	2540.4	2571.3	2605.7	2609.1	2616.0	2619.4	2622.8	2612.5	2602.2
20°	2626.3	2640.0	2653.7	2667.4	2681.2	2657.1	2636.6	2612.5	2588.5	2561.0	2537.0
22.5°	2852.8	2821.9	2791.0	2760.1	2729.2	2688.0	2643.4	2602.2	2557.6	2523.3	2488.9
25°	3065.7	3027.9	2990.2	2952.4	2914.6	2825.4	2736.1	2643.4	2554.2	2516.4	2478.6
27.5°	3350.6	3292.3	3233.9	3175.5	3117.2	2997.0	2876.9	2756.7	2636.6	2571.3	2509.5
30°	3419.3	3354.0	3288.8	3220.2	3154.9	3038.2	2924.9	2808.2	2691.5	2616.0	2543.9
32.5°	3518.8	3443.3	3367.8	3292.3	3216.7	3103.4	2990.2	2873.4	2760.1	2691.5	2619.4
35°	3683.6	3597.8	3512.0	3422.7	3336.9	3220.2	3106.9	2990.2	2873.4	2794.5	2718.9
37.5°	3824.4	3724.8	3625.3	3525.7	3426.1	3323.2	3216.7	3113.7	3007.3	2928.4	2852.8
40°	3982.3	3872.4	3762.6	3656.2	3546.3	3450.2	3354.0	3254.5	3158.4	3096.6	3034.8
42.5°	4119.6	3985.7	3855.3	3724.8	3590.9	3525.7	3463.9	3398.7	3333.5	3302.6	3268.2
45°	4215.7	4092.1	3965.1	3841.5	3717.9	3669.9	3621.8	3573.8	3525.7	3556.6	3587.5
47.5°	4256.9	4157.4	4061.2	3965.1	3865.6	3882.7	3899.9	3913.6	3930.8	3972.0	4016.6
50°	4294.7	4239.8	4181.4	4126.5	4068.1	4133.3	4195.1	4260.4	4325.6	4411.4	4497.2
52.5°	4370.2	4339.3	4311.9	4281.0	4250.1	4363.4	4476.6	4589.9	4703.2	4799.3	4895.5
55°	4596.8	4572.8	4548.7	4521.3	4497.2	4658.6	4816.5	4977.9	5139.2	5238.8	5338.3
57.5°	4909.2	4895.5	4878.3	4864.6	4847.4	5005.3	5159.8	5314.3	5472.2	5568.3	5667.9
60°	5146.1	5149.5	5149.5	5152.9	5152.9	5273.1	5393.3	5516.8	5637.0	5719.4	5805.2
62.5°	5273.1	5266.2	5259.4	5252.5	5245.6	5345.2	5444.8	5544.3	5643.9	5705.7	5767.5
65°	5135.8	5173.5	5211.3	5249.1	5286.8	5300.6	5310.9	5324.6	5334.9	5372.7	5410.4
67.5°	4675.8	4751.3	4823.4	4898.9	4971.0	4919.5	4871.4	4819.9	4768.4	4778.7	4785.6
70°	4164.2	4250.1	4339.3	4425.1	4511.0	4390.8	4270.7	4147.1	4026.9	3985.7	3944.5
72.5°	3512.0	3587.5	3666.5	3742.0	3817.5	3669.9	3525.7	3378.1	3230.5	3158.4	3086.3
75°	2684.6	2773.9	2866.6	2955.8	3045.1	2880.3	2712.1	2547.3	2379.1	2331.0	2286.4
77.5°	1956.8	2063.2	2169.7	2276.1	2382.5	2234.9	2087.3	1936.2	1788.6	1761.1	1733.7
80°	1424.7	1507.1	1586.1	1668.4	1747.4	1661.6	1575.8	1489.9	1404.1	1400.7	1397.2
82.5°	961.2	1033.3	1102.0	1174.1	1242.7	1208.4	1177.5	1143.2	1108.9	1143.2	1181.0
85°	494.4	593.9	696.9	796.5	896.0	885.7	878.9	868.6	858.3	902.9	944.1
87.5°	99.6	185.4	271.2	353.6	439.4	418.8	398.2	374.2	353.6	367.3	377.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2708.6	2712.1	2712.1	2712.1	2712.1	2712.1	2705.2	2701.8	2694.9	2688.0	2677.7
5°	2911.2	2907.8	2894.0	2880.3	2863.1	2849.4	2839.1	2825.4	2815.1	2801.3	2780.7
7.5°	3038.2	3045.1	3021.0	3000.4	2976.4	2952.4	2928.4	2904.3	2880.3	2856.3	2808.2
10°	3000.4	3010.7	2997.0	2983.3	2966.1	2952.4	2924.9	2894.0	2866.6	2835.7	2777.3
12.5°	2894.0	2921.5	2914.6	2907.8	2900.9	2894.0	2876.9	2856.3	2839.1	2818.5	2753.3
15°	2705.2	2705.2	2708.6	2712.1	2712.1	2715.5	2718.9	2722.4	2725.8	2729.2	2691.5
17.5°	2591.9	2581.6	2581.6	2581.6	2581.6	2581.6	2595.4	2612.5	2626.3	2640.0	2629.7
20°	2509.5	2485.5	2482.1	2482.1	2478.6	2475.2	2499.2	2526.7	2550.7	2574.8	2588.5
22.5°	2454.6	2420.3	2416.8	2413.4	2410.0	2406.5	2437.4	2468.3	2499.2	2530.1	2578.2
25°	2440.9	2403.1	2406.5	2410.0	2410.0	2413.4	2437.4	2461.5	2485.5	2509.5	2591.9
27.5°	2444.3	2382.5	2385.9	2389.4	2389.4	2392.8	2430.6	2464.9	2502.7	2537.0	2640.0
30°	2468.3	2396.2	2389.4	2382.5	2375.6	2368.8	2420.3	2471.8	2523.3	2574.8	2653.7
32.5°	2550.7	2482.1	2464.9	2447.7	2430.6	2413.4	2475.2	2533.6	2595.4	2653.7	2718.9
35°	2640.0	2564.5	2557.6	2550.7	2540.4	2533.6	2588.5	2646.8	2701.8	2756.7	2815.1
37.5°	2773.9	2698.3	2691.5	2681.2	2674.3	2664.0	2725.8	2784.2	2846.0	2904.3	2955.8
40°	2973.0	2911.2	2907.8	2907.8	2904.3	2900.9	2949.0	3000.4	3048.5	3096.6	3130.9
42.5°	3237.3	3206.4	3216.7	3230.5	3240.8	3251.1	3288.8	3330.0	3367.8	3405.5	3395.2
45°	3618.4	3649.3	3652.7	3656.2	3659.6	3663.0	3673.3	3687.1	3697.4	3707.6	3666.5
47.5°	4057.8	4099.0	4119.6	4140.2	4157.4	4178.0	4164.2	4147.1	4133.3	4116.2	4013.2
50°	4579.6	4665.5	4662.0	4658.6	4651.7	4648.3	4620.8	4593.4	4562.5	4535.0	4384.0
52.5°	4991.6	5087.7	5104.9	5122.0	5139.2	5156.4	5104.9	5053.4	4998.5	4947.0	4758.2
55°	5434.5	5534.0	5537.4	5540.9	5540.9	5544.3	5472.2	5400.1	5324.6	5252.5	5056.8
57.5°	5764.0	5860.1	5849.8	5843.0	5832.7	5822.4	5736.6	5650.7	5564.9	5479.1	5283.4
60°	5887.6	5970.0	5949.4	5928.8	5904.8	5884.2	5818.9	5753.7	5685.1	5619.8	5431.0
62.5°	5829.2	5891.0	5860.1	5832.7	5801.8	5770.9	5688.5	5602.7	5520.3	5434.5	5297.1
65°	5444.8	5482.5	5441.3	5403.6	5365.8	5324.6	5255.9	5187.3	5115.2	5046.5	4953.8
67.5°	4795.9	4802.8	4799.3	4795.9	4792.5	4789.0	4689.5	4589.9	4486.9	4387.4	4380.5
70°	3906.8	3865.6	3872.4	3882.7	3889.6	3896.5	3820.9	3748.8	3673.3	3597.8	3632.1
72.5°	3014.2	2942.1	2959.3	2979.9	2997.0	3014.2	2952.4	2894.0	2832.2	2770.4	2818.5
75°	2238.3	2193.7	2210.9	2231.5	2248.6	2265.8	2241.8	2217.7	2190.3	2166.2	2210.9
77.5°	1706.2	1678.7	1682.2	1682.2	1685.6	1685.6	1689.0	1695.9	1699.3	1702.8	1750.8
80°	1390.4	1386.9	1383.5	1380.1	1373.2	1369.8	1404.1	1438.4	1472.8	1507.1	1531.1
82.5°	1215.3	1249.6	1229.0	1211.9	1191.3	1170.7	1201.6	1232.5	1263.3	1294.2	1283.9
85°	988.7	1029.9	992.1	954.4	913.2	875.4	902.9	926.9	954.4	978.4	964.7
87.5°	391.4	401.7	339.9	281.5	219.7	157.9	250.6	339.9	432.6	521.8	535.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798

CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8	2471.8
2.5°	2667.4	2653.7	2643.4	2640.0	2633.1	2629.7	2622.8	2616.0	2605.7	2598.8	2588.5
5°	2756.7	2736.1	2712.1	2677.7	2646.8	2612.5	2578.2	2547.3	2516.4	2482.1	2451.2
7.5°	2760.1	2712.1	2664.0	2619.4	2571.3	2526.7	2478.6	2437.4	2392.8	2348.2	2307.0
10°	2722.4	2664.0	2605.7	2547.3	2492.4	2434.0	2375.6	2327.6	2276.1	2224.6	2176.5
12.5°	2691.5	2626.3	2561.0	2492.4	2427.1	2358.5	2289.8	2241.8	2193.7	2145.6	2097.6
15°	2653.7	2612.5	2574.8	2513.0	2451.2	2389.4	2327.6	2262.4	2200.6	2135.3	2070.1
17.5°	2622.8	2612.5	2602.2	2561.0	2519.8	2475.2	2434.0	2368.8	2303.5	2234.9	2169.7
20°	2605.7	2619.4	2633.1	2612.5	2591.9	2567.9	2547.3	2499.2	2451.2	2399.7	2351.6
22.5°	2626.3	2677.7	2725.8	2729.2	2736.1	2739.5	2743.0	2698.3	2653.7	2605.7	2561.0
25°	2674.3	2756.7	2839.1	2883.7	2928.4	2976.4	3021.0	2993.6	2966.1	2938.7	2911.2
27.5°	2739.5	2842.5	2945.5	3010.7	3072.5	3137.8	3203.0	3199.6	3196.1	3189.3	3185.8
30°	2729.2	2808.2	2887.2	2966.1	3045.1	3124.0	3203.0	3244.2	3282.0	3323.2	3364.3
32.5°	2787.6	2852.8	2921.5	3003.9	3086.3	3172.1	3254.5	3340.3	3422.7	3508.5	3594.4
35°	2876.9	2935.2	2997.0	3086.3	3179.0	3268.2	3360.9	3463.9	3570.3	3676.8	3779.7
37.5°	3010.7	3062.2	3117.2	3192.7	3271.7	3347.2	3426.1	3577.2	3728.2	3882.7	4033.8
40°	3165.2	3199.6	3233.9	3306.0	3378.1	3450.2	3522.3	3711.1	3899.9	4088.7	4277.5
42.5°	3388.4	3378.1	3367.8	3426.1	3487.9	3546.3	3608.1	3779.7	3951.4	4123.0	4294.7
45°	3625.3	3584.1	3542.9	3570.3	3601.2	3628.7	3659.6	3834.7	4009.8	4188.3	4363.4
47.5°	3910.2	3807.2	3704.2	3680.2	3656.2	3628.7	3604.7	3793.5	3982.3	4174.5	4363.4
50°	4232.9	4078.4	3927.4	3865.6	3800.3	3738.5	3673.3	3827.8	3985.7	4143.6	4298.1
52.5°	4569.3	4377.1	4188.3	4092.1	3996.0	3896.5	3800.3	3930.8	4064.7	4198.6	4329.0
55°	4857.7	4662.0	4462.9	4349.6	4236.3	4123.0	4009.8	4140.2	4270.7	4401.1	4531.6
57.5°	5087.7	4892.0	4696.4	4589.9	4480.1	4373.7	4263.8	4387.4	4514.4	4641.4	4765.0
60°	5245.6	5056.8	4868.0	4765.0	4662.0	4559.0	4456.0	4603.7	4751.3	4902.3	5050.0
62.5°	5163.2	5025.9	4888.6	4844.0	4799.3	4751.3	4706.7	4847.4	4984.7	5125.5	5266.2
65°	4861.1	4768.4	4675.8	4720.4	4768.4	4813.1	4861.1	4953.8	5046.5	5142.6	5235.3
67.5°	4370.2	4363.4	4353.1	4452.6	4552.2	4655.2	4754.7	4816.5	4874.9	4936.7	4998.5
70°	3666.5	3704.2	3738.5	3910.2	4081.8	4253.5	4425.1	4449.2	4473.2	4497.2	4521.3
72.5°	2870.0	2918.1	2969.6	3196.1	3419.3	3645.9	3872.4	3858.7	3845.0	3827.8	3814.1
75°	2258.9	2303.5	2351.6	2561.0	2770.4	2979.9	3189.3	3130.9	3076.0	3017.6	2959.3
77.5°	1802.3	1850.4	1901.9	2097.6	2293.2	2492.4	2688.0	2547.3	2406.5	2265.8	2125.0
80°	1551.7	1575.8	1596.3	1730.2	1860.7	1994.6	2128.5	1984.3	1836.7	1689.0	1544.9
82.5°	1273.6	1259.9	1249.6	1328.6	1407.5	1486.5	1565.5	1428.1	1290.8	1150.1	1012.7
85°	950.9	937.2	923.5	964.7	1005.9	1050.5	1091.7	933.8	775.9	614.5	456.6
87.5°	552.7	566.4	580.2	624.8	669.4	717.5	762.1	600.8	439.4	274.6	113.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
 CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671798
CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2471.8	2471.8
2.5°	2567.9	2550.7
5°	2427.1	2403.1
7.5°	2272.7	2241.8
10°	2131.9	2090.7
12.5°	2042.6	1991.1
15°	2008.3	1946.5
17.5°	2111.3	2052.9
20°	2269.2	2190.3
22.5°	2461.5	2365.3
25°	2794.5	2677.7
27.5°	3065.7	2945.5
30°	3233.9	3103.4
32.5°	3419.3	3247.6
35°	3611.5	3446.7
37.5°	3845.0	3659.6
40°	4085.3	3893.0
42.5°	4167.7	4044.1
45°	4246.6	4129.9
47.5°	4263.8	4167.7
50°	4281.0	4267.2
52.5°	4329.0	4325.6
55°	4535.0	4538.4
57.5°	4789.0	4809.6
60°	5022.5	4998.5
62.5°	5142.6	5019.1
65°	5060.3	4888.6
67.5°	4813.1	4627.7
70°	4270.7	4020.1
72.5°	3594.4	3374.6
75°	2770.4	2585.1
77.5°	1970.5	1816.1
80°	1386.9	1232.5
82.5°	889.1	765.6
85°	401.7	350.2
87.5°	113.3	109.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671798
CATALOG NUMBER: CCP-SA-2D-727-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)