

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671809

Luminaire Tested: **CCP-SA-2D-730-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671809
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2D-730-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @800mA w/ SLR distribution lens
Light Source: (32) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8427.9 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3


Input Watts (W): 80.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 12 fc
 Type IV - Short - N/A

REPORT NUMBER: P671809
CATALOG NUMBER: CCP-SA-2D-730-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1734.1	0.0	1734.1
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	6693.8	0.0	6693.8
	% Fixture	79.4	0.0	79.4
Total	Lumens	8427.9	0.0	8427.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.1	2.5
10°-20°	441.5	5.2
20°-30°	646.0	7.7
30°-40°	910.1	10.8
40°-50°	1250.6	14.8
50°-60°	1704.6	20.2
60°-70°	1865.6	22.1
70°-80°	1077.4	12.8
80°-90°	323.0	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8427.9	100.0
0°-180°	8427.9	100.0



REPORT NUMBER: P671809


CATALOG NUMBER: CCP-SA-2D-730-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	865.6	10.3			
FM (30°-60°)	3075.6	36.5			
FH (60°-80°)	2478.3	29.4			G2/5000
FVH (80°-90°)	274.3	3.3			G3/500
BL (0°-30°)	431.1	5.1	B1/500		
BM (30°-60°)	789.6	9.4	B1/1000		
BH (60°-80°)	464.7	5.5	B1/500		G1/500
BVH (80°-90°)	48.6	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short





REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2777.3	2762.4	2751.2	2740.0	2725.0	2713.8	2698.8	2683.9	2665.2	2650.2	2631.6
5°	2616.6	2571.8	2526.9	2500.7	2470.8	2444.7	2414.8	2381.1	2347.5	2310.1	2276.4
7.5°	2440.9	2384.9	2328.8	2283.9	2235.3	2190.5	2141.9	2100.8	2059.6	2018.5	1977.4
10°	2276.4	2224.1	2171.8	2115.7	2055.9	1999.8	1940.0	1884.0	1827.9	1771.8	1715.7
12.5°	2168.0	2104.5	2044.7	1981.1	1921.3	1857.8	1794.2	1741.9	1689.6	1633.5	1581.2
15°	2119.5	2059.6	2003.6	1940.0	1876.5	1812.9	1749.4	1689.6	1633.5	1573.7	1513.9
17.5°	2235.3	2149.4	2063.4	1981.1	1898.9	1816.7	1734.4	1659.7	1584.9	1510.2	1435.4
20°	2384.9	2276.4	2171.8	2070.9	1966.2	1865.3	1760.6	1655.9	1551.3	1446.6	1341.9
22.5°	2575.5	2452.1	2332.5	2201.7	2067.1	1936.3	1801.7	1670.9	1540.1	1405.5	1274.7
25°	2915.6	2769.9	2624.1	2437.2	2246.5	2059.6	1869.0	1697.1	1528.8	1356.9	1184.9
27.5°	3207.2	3009.1	2814.7	2590.4	2366.2	2141.9	1917.6	1719.5	1525.1	1327.0	1128.9
30°	3379.2	3184.8	2990.4	2717.5	2448.4	2175.5	1902.6	1682.1	1465.3	1244.8	1024.2
32.5°	3536.2	3319.4	3102.5	2803.5	2500.7	2201.7	1898.9	1655.9	1416.7	1173.7	930.8
35°	3753.0	3513.7	3278.2	2930.6	2583.0	2235.3	1887.7	1637.2	1383.1	1132.6	878.4
37.5°	3984.7	3689.4	3397.9	3012.8	2627.8	2242.8	1857.8	1611.1	1364.4	1117.7	871.0
40°	4238.9	3880.1	3524.9	3098.8	2676.4	2250.3	1824.1	1577.4	1330.7	1080.3	833.6
42.5°	4403.4	4014.6	3625.9	3166.1	2710.1	2250.3	1790.5	1547.5	1304.6	1057.9	814.9
45°	4496.8	4119.3	3745.5	3248.3	2751.2	2254.0	1756.9	1517.6	1278.4	1035.4	796.2
47.5°	4537.9	4186.6	3835.2	3311.9	2792.3	2269.0	1745.7	1502.7	1256.0	1013.0	766.3
50°	4646.3	4336.1	4025.8	3465.1	2908.2	2347.5	1786.8	1525.1	1267.2	1005.5	743.9
52.5°	4709.9	4444.5	4179.1	3603.4	3027.8	2452.1	1876.5	1584.9	1293.4	1001.8	710.2
55°	4941.6	4687.5	4433.3	3820.2	3203.5	2590.4	1973.7	1652.2	1330.7	1005.5	684.1
57.5°	5237.0	4967.8	4702.4	4040.8	3379.2	2717.5	2055.9	1712.0	1364.4	1020.5	672.8
60°	5442.5	5180.9	4923.0	4220.2	3513.7	2811.0	2104.5	1745.7	1386.8	1024.2	665.4
62.5°	5465.0	5128.5	4795.9	4111.8	3427.8	2740.0	2055.9	1708.3	1360.6	1009.3	661.6
65°	5322.9	4930.4	4537.9	3883.8	3229.6	2575.5	1921.3	1603.6	1285.9	964.4	646.7
67.5°	5038.8	4579.1	4119.3	3521.2	2923.1	2325.0	1727.0	1454.1	1184.9	912.1	639.2
70°	4377.2	3973.5	3573.5	3054.0	2538.1	2018.5	1498.9	1274.7	1054.1	829.8	605.6
72.5°	3674.5	3296.9	2923.1	2500.7	2082.1	1659.7	1237.3	1069.1	900.9	728.9	560.7
75°	2814.7	2530.6	2250.3	1936.3	1622.3	1304.6	990.6	867.2	743.9	620.5	497.2
77.5°	1977.4	1824.1	1674.6	1439.1	1203.6	968.1	732.6	650.4	568.2	485.9	403.7
80°	1341.9	1256.0	1173.7	1005.5	837.3	665.4	497.2	444.8	388.8	336.4	280.4
82.5°	833.6	829.8	822.4	706.5	590.6	474.7	358.8	314.0	272.9	228.0	183.2
85°	381.3	444.8	504.6	441.1	377.5	314.0	250.4	220.5	190.6	157.0	127.1
87.5°	119.6	145.8	168.2	160.7	149.5	142.0	130.8	112.1	93.5	74.8	56.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2616.6	2605.4	2590.4	2575.5	2556.8	2541.8	2523.2	2504.5	2500.7	2493.3	2489.5
5°	2254.0	2231.6	2205.4	2183.0	2160.6	2134.4	2112.0	2085.8	2067.1	2044.7	2026.0
7.5°	1936.3	1898.9	1857.8	1816.7	1779.3	1741.9	1700.8	1663.4	1644.7	1626.0	1607.3
10°	1682.1	1644.7	1611.1	1573.7	1547.5	1525.1	1498.9	1472.8	1450.3	1427.9	1405.5
12.5°	1555.0	1528.8	1502.7	1476.5	1446.6	1420.4	1390.5	1360.6	1334.5	1312.0	1285.9
15°	1476.5	1439.1	1398.0	1360.6	1319.5	1282.1	1241.0	1199.9	1170.0	1143.8	1113.9
17.5°	1383.1	1327.0	1274.7	1218.6	1173.7	1128.9	1080.3	1035.4	1001.8	964.4	930.8
20°	1278.4	1214.9	1147.6	1084.0	1031.7	983.1	930.8	878.4	841.1	799.9	762.6
22.5°	1188.7	1106.5	1020.5	934.5	878.4	822.4	762.6	706.5	672.8	635.5	601.8
25°	1091.5	1001.8	908.3	814.9	758.8	699.0	642.9	583.1	557.0	534.5	508.4
27.5°	1039.2	949.5	856.0	766.3	714.0	657.9	605.6	549.5	530.8	508.4	489.7
30°	934.5	848.5	758.8	669.1	631.7	598.1	560.7	523.3	515.8	512.1	504.6
32.5°	841.1	751.3	661.6	571.9	538.3	504.6	471.0	437.3	433.6	426.1	422.4
35°	792.5	706.5	616.8	530.8	500.9	467.3	437.3	403.7	396.2	385.0	377.5
37.5°	781.2	691.5	598.1	508.4	478.5	448.6	414.9	385.0	377.5	370.1	362.6
40°	751.3	665.4	583.1	497.2	467.3	437.3	403.7	373.8	366.3	358.8	351.4
42.5°	728.9	646.7	560.7	474.7	448.6	422.4	392.5	366.3	358.8	351.4	340.2
45°	710.2	624.2	534.5	448.6	429.9	411.2	388.8	370.1	362.6	351.4	343.9
47.5°	680.3	598.1	512.1	426.1	407.4	392.5	373.8	355.1	347.6	340.2	332.7
50°	657.9	571.9	485.9	400.0	385.0	370.1	355.1	340.2	340.2	343.9	343.9
52.5°	628.0	545.7	463.5	381.3	366.3	351.4	336.4	321.5	325.2	328.9	332.7
55°	601.8	523.3	441.1	358.8	343.9	328.9	310.3	295.3	299.0	302.8	306.5
57.5°	590.6	508.4	426.1	343.9	328.9	310.3	295.3	276.6	276.6	276.6	276.6
60°	583.1	497.2	414.9	328.9	310.3	295.3	276.6	257.9	254.2	254.2	250.4
62.5°	579.4	493.4	411.2	325.2	302.8	284.1	261.7	239.2	235.5	231.8	228.0
65°	564.4	485.9	403.7	321.5	295.3	272.9	246.7	220.5	216.8	216.8	213.1
67.5°	560.7	478.5	400.0	317.7	291.6	261.7	235.5	205.6	201.9	198.1	194.4
70°	530.8	459.8	385.0	310.3	280.4	254.2	224.3	194.4	190.6	183.2	179.4
72.5°	493.4	429.9	362.6	295.3	265.4	235.5	205.6	175.7	171.9	168.2	160.7
75°	437.3	377.5	317.7	257.9	231.8	209.3	183.2	157.0	153.3	149.5	142.0
77.5°	358.8	310.3	265.4	216.8	198.1	179.4	160.7	142.0	138.3	134.6	127.1
80°	254.2	224.3	198.1	168.2	157.0	142.0	130.8	115.9	115.9	112.1	112.1
82.5°	168.2	153.3	138.3	123.4	115.9	108.4	100.9	93.5	93.5	89.7	89.7
85°	119.6	112.1	100.9	93.5	89.7	82.2	78.5	71.0	71.0	71.0	71.0
87.5°	56.1	56.1	52.3	52.3	48.6	48.6	44.9	41.1	41.1	41.1	41.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2482.0	2470.8	2459.6	2444.7	2433.4	2418.5	2399.8	2384.9	2366.2	2366.2	2362.4
5°	2003.6	1992.4	1981.1	1966.2	1955.0	1940.0	1928.8	1913.9	1898.9	1898.9	1895.2
7.5°	1588.7	1566.2	1543.8	1517.6	1495.2	1480.3	1465.3	1446.6	1431.7	1420.4	1409.2
10°	1383.1	1360.6	1334.5	1312.0	1285.9	1267.2	1248.5	1226.1	1207.4	1192.4	1177.5
12.5°	1259.7	1233.5	1207.4	1181.2	1155.0	1128.9	1106.5	1080.3	1054.1	1035.4	1016.7
15°	1084.0	1057.9	1031.7	1005.5	979.4	949.5	919.6	885.9	856.0	841.1	829.8
17.5°	893.4	867.2	837.3	811.1	781.2	758.8	736.4	714.0	691.5	676.6	665.4
20°	721.4	691.5	661.6	631.7	601.8	586.9	571.9	557.0	542.0	530.8	523.3
22.5°	564.4	545.7	530.8	512.1	493.4	482.2	474.7	463.5	452.3	452.3	452.3
25°	482.2	471.0	463.5	452.3	441.1	437.3	433.6	426.1	422.4	418.7	418.7
27.5°	467.3	456.0	444.8	433.6	422.4	418.7	414.9	407.4	403.7	403.7	403.7
30°	497.2	493.4	489.7	485.9	482.2	474.7	463.5	456.0	444.8	437.3	429.9
32.5°	414.9	411.2	411.2	407.4	403.7	411.2	414.9	422.4	426.1	429.9	433.6
35°	366.3	358.8	351.4	343.9	336.4	332.7	328.9	325.2	321.5	321.5	317.7
37.5°	355.1	347.6	340.2	332.7	325.2	321.5	317.7	314.0	310.3	310.3	306.5
40°	343.9	336.4	332.7	325.2	317.7	314.0	310.3	302.8	299.0	295.3	295.3
42.5°	332.7	328.9	321.5	317.7	310.3	306.5	302.8	295.3	291.6	287.8	284.1
45°	332.7	325.2	317.7	310.3	302.8	299.0	291.6	287.8	280.4	280.4	276.6
47.5°	325.2	317.7	310.3	302.8	295.3	291.6	284.1	280.4	272.9	269.1	265.4
50°	343.9	332.7	317.7	306.5	291.6	287.8	280.4	276.6	269.1	265.4	261.7
52.5°	336.4	325.2	310.3	299.0	284.1	276.6	272.9	265.4	257.9	254.2	250.4
55°	310.3	299.0	291.6	280.4	269.1	261.7	254.2	246.7	239.2	235.5	235.5
57.5°	276.6	272.9	269.1	265.4	261.7	254.2	246.7	235.5	228.0	224.3	220.5
60°	246.7	250.4	254.2	257.9	261.7	250.4	239.2	228.0	216.8	213.1	209.3
62.5°	224.3	231.8	239.2	243.0	250.4	239.2	228.0	216.8	205.6	201.9	198.1
65°	209.3	213.1	213.1	216.8	216.8	209.3	205.6	198.1	190.6	186.9	186.9
67.5°	190.6	190.6	190.6	186.9	186.9	183.2	183.2	179.4	175.7	171.9	171.9
70°	171.9	171.9	171.9	168.2	168.2	164.5	164.5	160.7	157.0	157.0	153.3
72.5°	157.0	157.0	153.3	153.3	149.5	149.5	149.5	145.8	145.8	142.0	142.0
75°	138.3	138.3	134.6	134.6	130.8	130.8	130.8	127.1	127.1	127.1	123.4
77.5°	123.4	123.4	119.6	119.6	115.9	115.9	115.9	112.1	112.1	108.4	108.4
80°	108.4	108.4	104.7	104.7	100.9	100.9	97.2	97.2	93.5	93.5	89.7
82.5°	86.0	86.0	86.0	86.0	86.0	82.2	82.2	78.5	74.8	74.8	71.0
85°	71.0	71.0	71.0	67.3	67.3	67.3	63.5	63.5	59.8	56.1	56.1
87.5°	41.1	41.1	41.1	37.4	37.4	37.4	37.4	37.4	37.4	37.4	33.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2362.4	2358.7	2343.7	2328.8	2343.7	2358.7	2358.7	2358.7	2354.9	2354.9	2354.9
5°	1895.2	1891.4	1884.0	1876.5	1876.5	1872.7	1880.2	1887.7	1895.2	1902.6	1910.1
7.5°	1394.3	1383.1	1371.8	1360.6	1368.1	1371.8	1383.1	1390.5	1401.8	1409.2	1427.9
10°	1162.5	1147.6	1136.4	1125.1	1117.7	1110.2	1102.7	1099.0	1091.5	1084.0	1091.5
12.5°	994.3	975.6	956.9	934.5	930.8	927.0	919.6	912.1	904.6	897.1	893.4
15°	814.9	799.9	792.5	781.2	766.3	751.3	743.9	740.1	732.6	725.2	721.4
17.5°	650.4	635.5	624.2	613.0	609.3	601.8	601.8	601.8	601.8	601.8	601.8
20°	512.1	500.9	500.9	497.2	497.2	493.4	497.2	500.9	500.9	504.6	508.4
22.5°	448.6	448.6	444.8	441.1	444.8	444.8	448.6	452.3	456.0	459.8	463.5
25°	414.9	411.2	414.9	418.7	418.7	418.7	422.4	422.4	426.1	426.1	426.1
27.5°	400.0	400.0	403.7	403.7	407.4	407.4	407.4	403.7	403.7	400.0	400.0
30°	422.4	414.9	414.9	414.9	411.2	407.4	403.7	403.7	400.0	396.2	392.5
32.5°	437.3	441.1	437.3	429.9	426.1	418.7	414.9	407.4	403.7	396.2	388.8
35°	317.7	314.0	321.5	325.2	328.9	332.7	336.4	340.2	340.2	343.9	343.9
37.5°	306.5	302.8	302.8	299.0	299.0	299.0	299.0	299.0	295.3	295.3	299.0
40°	291.6	287.8	287.8	284.1	284.1	280.4	280.4	280.4	280.4	280.4	280.4
42.5°	280.4	276.6	276.6	276.6	276.6	272.9	272.9	269.1	269.1	265.4	265.4
45°	276.6	272.9	269.1	265.4	265.4	261.7	261.7	261.7	257.9	257.9	257.9
47.5°	261.7	257.9	257.9	254.2	254.2	250.4	250.4	250.4	246.7	246.7	246.7
50°	254.2	250.4	250.4	246.7	246.7	243.0	243.0	243.0	239.2	239.2	239.2
52.5°	243.0	239.2	239.2	239.2	235.5	231.8	231.8	231.8	228.0	228.0	228.0
55°	231.8	228.0	228.0	228.0	224.3	220.5	220.5	220.5	216.8	216.8	216.8
57.5°	216.8	213.1	213.1	209.3	209.3	209.3	209.3	209.3	205.6	205.6	205.6
60°	205.6	201.9	201.9	198.1	198.1	194.4	194.4	194.4	194.4	194.4	194.4
62.5°	194.4	190.6	186.9	183.2	186.9	186.9	186.9	186.9	183.2	183.2	183.2
65°	183.2	179.4	175.7	171.9	171.9	171.9	171.9	171.9	171.9	171.9	171.9
67.5°	168.2	164.5	160.7	157.0	160.7	160.7	160.7	160.7	160.7	160.7	160.7
70°	153.3	149.5	149.5	145.8	145.8	142.0	142.0	145.8	145.8	145.8	145.8
72.5°	138.3	134.6	134.6	130.8	130.8	130.8	130.8	130.8	130.8	130.8	130.8
75°	123.4	119.6	119.6	115.9	115.9	115.9	115.9	115.9	115.9	115.9	115.9
77.5°	104.7	100.9	100.9	100.9	100.9	100.9	100.9	104.7	104.7	104.7	104.7
80°	89.7	86.0	86.0	86.0	86.0	86.0	86.0	86.0	86.0	86.0	86.0
82.5°	71.0	67.3	67.3	67.3	67.3	67.3	67.3	67.3	67.3	67.3	67.3
85°	52.3	48.6	48.6	48.6	52.3	52.3	52.3	52.3	52.3	52.3	52.3
87.5°	33.6	29.9	29.9	29.9	33.6	33.6	33.6	33.6	29.9	29.9	29.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2354.9	2354.9	2354.9	2351.2	2347.5	2343.7	2340.0	2351.2	2358.7	2369.9	2377.4
5°	1913.9	1921.3	1925.1	1936.3	1947.5	1958.7	1969.9	1977.4	1984.9	1988.6	1996.1
7.5°	1442.9	1461.6	1476.5	1491.5	1506.4	1517.6	1532.6	1543.8	1555.0	1566.2	1577.4
10°	1095.2	1102.7	1106.5	1121.4	1132.6	1147.6	1158.8	1170.0	1181.2	1188.7	1199.9
12.5°	889.6	882.2	878.4	878.4	878.4	878.4	878.4	885.9	893.4	900.9	908.3
15°	717.7	714.0	710.2	706.5	702.7	695.3	691.5	699.0	706.5	714.0	721.4
17.5°	601.8	601.8	601.8	598.1	594.3	590.6	586.9	590.6	594.3	594.3	598.1
20°	515.8	519.6	523.3	527.1	527.1	530.8	530.8	534.5	538.3	538.3	542.0
22.5°	463.5	467.3	467.3	467.3	471.0	471.0	471.0	474.7	478.5	482.2	485.9
25°	422.4	422.4	418.7	418.7	422.4	422.4	422.4	422.4	426.1	426.1	426.1
27.5°	400.0	396.2	396.2	396.2	396.2	392.5	392.5	392.5	392.5	392.5	392.5
30°	388.8	385.0	381.3	377.5	377.5	373.8	370.1	370.1	370.1	370.1	370.1
32.5°	385.0	377.5	370.1	366.3	366.3	362.6	358.8	355.1	355.1	351.4	347.6
35°	343.9	340.2	340.2	336.4	332.7	328.9	325.2	325.2	325.2	321.5	321.5
37.5°	299.0	302.8	302.8	302.8	306.5	306.5	306.5	306.5	310.3	310.3	310.3
40°	280.4	280.4	280.4	284.1	287.8	287.8	291.6	291.6	295.3	295.3	295.3
42.5°	265.4	261.7	261.7	265.4	265.4	269.1	269.1	272.9	276.6	276.6	280.4
45°	257.9	254.2	254.2	254.2	254.2	250.4	250.4	254.2	257.9	261.7	265.4
47.5°	243.0	243.0	239.2	239.2	239.2	239.2	239.2	239.2	243.0	243.0	243.0
50°	235.5	235.5	231.8	231.8	231.8	231.8	231.8	231.8	231.8	231.8	231.8
52.5°	228.0	224.3	224.3	224.3	224.3	220.5	220.5	220.5	220.5	220.5	220.5
55°	216.8	213.1	213.1	213.1	213.1	213.1	213.1	213.1	216.8	216.8	216.8
57.5°	205.6	201.9	201.9	201.9	205.6	205.6	205.6	205.6	209.3	209.3	209.3
60°	194.4	194.4	194.4	194.4	194.4	194.4	194.4	198.1	198.1	201.9	201.9
62.5°	183.2	183.2	183.2	183.2	186.9	186.9	186.9	186.9	190.6	190.6	190.6
65°	171.9	171.9	171.9	171.9	175.7	175.7	175.7	175.7	175.7	175.7	175.7
67.5°	160.7	160.7	160.7	160.7	160.7	160.7	160.7	164.5	164.5	168.2	168.2
70°	145.8	142.0	142.0	145.8	145.8	149.5	149.5	153.3	153.3	157.0	157.0
72.5°	130.8	130.8	130.8	130.8	130.8	130.8	130.8	134.6	138.3	138.3	142.0
75°	115.9	115.9	115.9	115.9	119.6	119.6	119.6	123.4	123.4	127.1	127.1
77.5°	104.7	100.9	100.9	100.9	104.7	104.7	104.7	108.4	108.4	112.1	112.1
80°	86.0	86.0	86.0	86.0	89.7	89.7	89.7	89.7	93.5	93.5	93.5
82.5°	71.0	71.0	71.0	71.0	71.0	71.0	71.0	71.0	74.8	74.8	74.8
85°	52.3	52.3	52.3	52.3	56.1	56.1	56.1	56.1	56.1	56.1	56.1
87.5°	33.6	33.6	33.6	33.6	33.6	33.6	33.6	33.6	37.4	37.4	37.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2377.4	2377.4	2377.4	2377.4	2384.9	2388.6	2396.1	2399.8	2396.1	2392.3	2384.9
5°	1999.8	2003.6	2003.6	2007.3	2007.3	2007.3	2007.3	2007.3	2014.8	2022.3	2029.7
7.5°	1581.2	1584.9	1588.7	1592.4	1592.4	1592.4	1588.7	1588.7	1592.4	1592.4	1596.1
10°	1211.1	1226.1	1237.3	1248.5	1241.0	1229.8	1222.3	1211.1	1211.1	1211.1	1207.4
12.5°	915.8	919.6	927.0	930.8	927.0	927.0	923.3	919.6	923.3	930.8	934.5
15°	725.2	725.2	728.9	728.9	732.6	736.4	736.4	740.1	747.6	751.3	758.8
17.5°	601.8	605.6	605.6	609.3	609.3	613.0	613.0	613.0	620.5	628.0	639.2
20°	542.0	542.0	542.0	542.0	542.0	538.3	538.3	534.5	538.3	545.7	549.5
22.5°	485.9	489.7	489.7	489.7	485.9	482.2	474.7	471.0	471.0	474.7	474.7
25°	426.1	422.4	422.4	418.7	418.7	422.4	422.4	422.4	426.1	426.1	429.9
27.5°	392.5	388.8	388.8	385.0	385.0	388.8	388.8	388.8	388.8	388.8	388.8
30°	366.3	366.3	362.6	358.8	362.6	362.6	366.3	366.3	370.1	370.1	373.8
32.5°	347.6	343.9	343.9	340.2	343.9	343.9	347.6	347.6	351.4	355.1	355.1
35°	321.5	321.5	321.5	321.5	321.5	321.5	317.7	317.7	317.7	317.7	317.7
37.5°	306.5	306.5	302.8	299.0	299.0	299.0	299.0	299.0	295.3	291.6	287.8
40°	295.3	291.6	291.6	287.8	284.1	284.1	280.4	276.6	276.6	272.9	272.9
42.5°	280.4	276.6	276.6	272.9	269.1	269.1	265.4	261.7	261.7	261.7	257.9
45°	261.7	261.7	257.9	254.2	254.2	254.2	250.4	250.4	250.4	250.4	246.7
47.5°	243.0	243.0	239.2	239.2	239.2	239.2	235.5	235.5	235.5	235.5	235.5
50°	231.8	231.8	231.8	231.8	231.8	231.8	228.0	228.0	228.0	228.0	228.0
52.5°	220.5	220.5	220.5	220.5	220.5	220.5	220.5	220.5	220.5	220.5	220.5
55°	216.8	216.8	216.8	216.8	216.8	216.8	213.1	213.1	213.1	216.8	216.8
57.5°	209.3	209.3	205.6	205.6	205.6	205.6	205.6	205.6	205.6	205.6	205.6
60°	201.9	201.9	201.9	201.9	201.9	201.9	201.9	201.9	201.9	201.9	201.9
62.5°	190.6	190.6	190.6	190.6	190.6	194.4	194.4	194.4	194.4	194.4	190.6
65°	175.7	179.4	179.4	179.4	179.4	179.4	179.4	179.4	179.4	179.4	179.4
67.5°	168.2	168.2	168.2	168.2	168.2	168.2	168.2	168.2	168.2	168.2	168.2
70°	157.0	157.0	153.3	153.3	153.3	157.0	157.0	157.0	157.0	157.0	157.0
72.5°	142.0	142.0	142.0	142.0	142.0	142.0	142.0	142.0	142.0	145.8	145.8
75°	127.1	127.1	127.1	127.1	127.1	127.1	127.1	127.1	127.1	127.1	127.1
77.5°	112.1	112.1	108.4	108.4	108.4	112.1	112.1	112.1	112.1	115.9	115.9
80°	93.5	93.5	93.5	93.5	93.5	93.5	93.5	93.5	93.5	97.2	97.2
82.5°	74.8	74.8	74.8	74.8	74.8	74.8	74.8	74.8	74.8	78.5	78.5
85°	56.1	59.8	59.8	59.8	59.8	59.8	59.8	59.8	59.8	63.5	63.5
87.5°	37.4	37.4	37.4	37.4	37.4	37.4	33.6	33.6	33.6	33.6	29.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2381.1	2384.9	2388.6	2388.6	2392.3	2396.1	2396.1	2411.0	2426.0	2433.4	2440.9
5°	2037.2	2033.5	2033.5	2029.7	2026.0	2037.2	2048.4	2070.9	2093.3	2097.0	2104.5
7.5°	1596.1	1599.9	1603.6	1603.6	1607.3	1596.1	1581.2	1584.9	1588.7	1607.3	1622.3
10°	1207.4	1211.1	1214.9	1214.9	1218.6	1214.9	1207.4	1218.6	1229.8	1244.8	1263.4
12.5°	938.2	949.5	960.7	968.1	979.4	986.8	990.6	1005.5	1016.7	1035.4	1054.1
15°	766.3	773.8	781.2	788.7	796.2	803.7	811.1	826.1	841.1	863.5	885.9
17.5°	646.7	646.7	650.4	650.4	650.4	657.9	665.4	672.8	676.6	699.0	721.4
20°	553.2	549.5	545.7	542.0	538.3	545.7	549.5	553.2	557.0	571.9	583.1
22.5°	474.7	474.7	478.5	478.5	478.5	474.7	467.3	471.0	471.0	478.5	489.7
25°	429.9	429.9	429.9	426.1	426.1	429.9	433.6	433.6	429.9	433.6	437.3
27.5°	388.8	392.5	392.5	396.2	396.2	400.0	400.0	400.0	400.0	403.7	407.4
30°	373.8	373.8	377.5	377.5	377.5	381.3	385.0	385.0	385.0	388.8	396.2
32.5°	358.8	362.6	366.3	370.1	373.8	377.5	377.5	381.3	381.3	385.0	388.8
35°	317.7	314.0	314.0	310.3	306.5	306.5	306.5	306.5	302.8	306.5	306.5
37.5°	284.1	284.1	284.1	280.4	280.4	284.1	284.1	284.1	284.1	287.8	287.8
40°	269.1	269.1	269.1	269.1	269.1	269.1	269.1	272.9	272.9	276.6	280.4
42.5°	257.9	257.9	257.9	257.9	257.9	261.7	261.7	261.7	261.7	265.4	265.4
45°	246.7	246.7	246.7	246.7	246.7	246.7	246.7	250.4	250.4	254.2	257.9
47.5°	235.5	235.5	235.5	235.5	235.5	239.2	243.0	243.0	243.0	246.7	246.7
50°	228.0	228.0	228.0	228.0	228.0	231.8	231.8	235.5	235.5	239.2	243.0
52.5°	220.5	220.5	220.5	220.5	220.5	224.3	224.3	228.0	228.0	231.8	235.5
55°	216.8	216.8	216.8	213.1	213.1	216.8	216.8	220.5	220.5	224.3	224.3
57.5°	205.6	205.6	205.6	205.6	205.6	205.6	205.6	209.3	209.3	213.1	216.8
60°	201.9	201.9	198.1	198.1	194.4	198.1	198.1	201.9	201.9	205.6	205.6
62.5°	190.6	190.6	190.6	186.9	186.9	190.6	190.6	190.6	190.6	194.4	198.1
65°	179.4	179.4	179.4	175.7	175.7	179.4	179.4	179.4	179.4	183.2	186.9
67.5°	168.2	168.2	168.2	164.5	164.5	164.5	164.5	168.2	168.2	171.9	175.7
70°	157.0	157.0	157.0	153.3	153.3	153.3	149.5	153.3	157.0	160.7	160.7
72.5°	145.8	145.8	145.8	142.0	142.0	142.0	138.3	142.0	142.0	145.8	145.8
75°	127.1	127.1	127.1	127.1	127.1	127.1	123.4	123.4	123.4	127.1	127.1
77.5°	115.9	115.9	115.9	112.1	112.1	112.1	108.4	108.4	108.4	112.1	112.1
80°	97.2	97.2	97.2	93.5	93.5	93.5	89.7	89.7	89.7	93.5	93.5
82.5°	78.5	78.5	78.5	74.8	74.8	74.8	71.0	71.0	71.0	74.8	74.8
85°	63.5	63.5	63.5	63.5	63.5	63.5	59.8	59.8	59.8	63.5	67.3
87.5°	29.9	29.9	33.6	33.6	33.6	33.6	29.9	29.9	26.2	26.2	29.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2448.4	2455.9	2474.6	2489.5	2508.2	2523.2	2534.4	2549.3	2560.5	2571.8	2579.2
5°	2108.2	2112.0	2130.7	2149.4	2164.3	2183.0	2209.2	2235.3	2261.5	2287.7	2306.4
7.5°	1641.0	1655.9	1678.4	1704.5	1727.0	1749.4	1775.6	1805.5	1831.6	1857.8	1884.0
10°	1278.4	1293.4	1315.8	1338.2	1356.9	1379.3	1409.2	1439.1	1469.0	1498.9	1528.8
12.5°	1072.8	1091.5	1117.7	1143.8	1166.3	1192.4	1229.8	1263.4	1300.8	1334.5	1371.8
15°	904.6	927.0	960.7	998.0	1031.7	1065.3	1102.7	1140.1	1173.7	1211.1	1248.5
17.5°	743.9	766.3	796.2	829.8	859.7	889.6	934.5	975.6	1020.5	1061.6	1102.7
20°	598.1	609.3	639.2	669.1	699.0	728.9	762.6	796.2	829.8	863.5	915.8
22.5°	497.2	504.6	519.6	530.8	545.7	557.0	590.6	624.2	654.2	687.8	736.4
25°	437.3	441.1	452.3	459.8	471.0	478.5	500.9	519.6	542.0	560.7	605.6
27.5°	407.4	411.2	414.9	418.7	422.4	426.1	441.1	456.0	467.3	482.2	523.3
30°	400.0	403.7	414.9	422.4	433.6	441.1	448.6	456.0	463.5	471.0	497.2
32.5°	392.5	396.2	396.2	392.5	392.5	388.8	396.2	400.0	407.4	411.2	433.6
35°	310.3	310.3	314.0	317.7	321.5	325.2	336.4	343.9	355.1	362.6	381.3
37.5°	291.6	291.6	295.3	302.8	306.5	310.3	317.7	325.2	332.7	340.2	358.8
40°	280.4	284.1	287.8	291.6	295.3	299.0	306.5	310.3	317.7	321.5	336.4
42.5°	269.1	269.1	272.9	280.4	284.1	287.8	295.3	299.0	306.5	310.3	325.2
45°	261.7	265.4	269.1	272.9	272.9	276.6	284.1	291.6	295.3	302.8	317.7
47.5°	250.4	250.4	257.9	261.7	269.1	272.9	280.4	284.1	291.6	295.3	310.3
50°	243.0	246.7	254.2	257.9	265.4	269.1	280.4	287.8	299.0	306.5	314.0
52.5°	235.5	239.2	246.7	250.4	257.9	261.7	276.6	291.6	302.8	317.7	317.7
55°	228.0	228.0	235.5	246.7	254.2	261.7	269.1	280.4	287.8	295.3	295.3
57.5°	216.8	220.5	228.0	239.2	246.7	254.2	261.7	269.1	272.9	280.4	276.6
60°	209.3	209.3	220.5	231.8	243.0	254.2	254.2	254.2	250.4	250.4	250.4
62.5°	198.1	201.9	216.8	235.5	250.4	265.4	254.2	243.0	231.8	220.5	224.3
65°	190.6	194.4	201.9	213.1	220.5	228.0	220.5	216.8	209.3	201.9	205.6
67.5°	175.7	179.4	183.2	183.2	186.9	186.9	186.9	186.9	186.9	186.9	190.6
70°	164.5	164.5	164.5	168.2	168.2	168.2	168.2	168.2	168.2	168.2	171.9
72.5°	149.5	149.5	149.5	149.5	149.5	149.5	149.5	149.5	149.5	149.5	153.3
75°	130.8	130.8	130.8	130.8	130.8	130.8	130.8	130.8	130.8	130.8	134.6
77.5°	115.9	115.9	115.9	115.9	115.9	115.9	115.9	115.9	112.1	112.1	115.9
80°	97.2	97.2	97.2	97.2	93.5	93.5	93.5	93.5	93.5	93.5	97.2
82.5°	78.5	78.5	78.5	78.5	74.8	74.8	74.8	74.8	71.0	71.0	74.8
85°	71.0	74.8	74.8	78.5	78.5	78.5	74.8	71.0	67.3	63.5	63.5
87.5°	29.9	29.9	29.9	29.9	26.2	26.2	26.2	26.2	26.2	26.2	26.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2590.4	2597.9	2605.4	2616.6	2631.6	2642.8	2654.0	2676.4	2702.6	2725.0	2747.4
5°	2325.0	2343.7	2362.4	2384.9	2407.3	2426.0	2448.4	2493.3	2538.1	2579.2	2624.1
7.5°	1906.4	1932.6	1955.0	1992.4	2026.0	2063.4	2097.0	2153.1	2205.4	2261.5	2313.8
10°	1558.8	1588.7	1618.6	1667.2	1719.5	1768.1	1816.7	1861.5	1910.1	1955.0	1999.8
12.5°	1409.2	1442.9	1480.3	1510.2	1543.8	1573.7	1603.6	1655.9	1708.3	1760.6	1812.9
15°	1285.9	1323.3	1360.6	1398.0	1431.7	1469.0	1502.7	1547.5	1596.1	1641.0	1685.8
17.5°	1143.8	1181.2	1222.3	1263.4	1304.6	1345.7	1386.8	1450.3	1513.9	1573.7	1637.2
20°	964.4	1016.7	1065.3	1121.4	1177.5	1233.5	1289.6	1356.9	1424.2	1487.7	1555.0
22.5°	785.0	833.6	882.2	949.5	1016.7	1080.3	1147.6	1237.3	1323.3	1413.0	1498.9
25°	654.2	699.0	743.9	818.6	889.6	964.4	1035.4	1143.8	1248.5	1356.9	1461.6
27.5°	564.4	605.6	646.7	725.2	803.7	878.4	956.9	1076.5	1192.4	1312.0	1427.9
30°	523.3	549.5	575.7	650.4	725.2	796.2	871.0	986.8	1102.7	1218.6	1334.5
32.5°	456.0	478.5	500.9	568.2	635.5	699.0	766.3	885.9	1001.8	1121.4	1237.3
35°	403.7	422.4	441.1	504.6	564.4	628.0	687.8	807.4	927.0	1046.6	1166.3
37.5°	373.8	392.5	407.4	463.5	523.3	579.4	635.5	755.1	871.0	990.6	1106.5
40°	351.4	362.6	377.5	433.6	485.9	542.0	594.3	702.7	814.9	923.3	1031.7
42.5°	336.4	351.4	362.6	411.2	463.5	512.1	560.7	665.4	770.0	871.0	975.6
45°	332.7	347.6	362.6	403.7	444.8	482.2	523.3	624.2	725.2	826.1	927.0
47.5°	325.2	336.4	351.4	385.0	414.9	448.6	478.5	579.4	680.3	777.5	878.4
50°	321.5	325.2	332.7	362.6	392.5	422.4	452.3	553.2	654.2	755.1	856.0
52.5°	317.7	317.7	317.7	343.9	370.1	392.5	418.7	519.6	624.2	725.2	826.1
55°	295.3	291.6	291.6	317.7	340.2	366.3	388.8	489.7	590.6	687.8	788.7
57.5°	272.9	269.1	265.4	287.8	310.3	332.7	355.1	456.0	560.7	661.6	762.6
60°	250.4	246.7	246.7	269.1	287.8	310.3	328.9	433.6	534.5	639.2	740.1
62.5°	224.3	228.0	228.0	246.7	269.1	287.8	306.5	411.2	519.6	624.2	728.9
65°	205.6	209.3	209.3	231.8	254.2	276.6	299.0	400.0	504.6	605.6	706.5
67.5°	190.6	194.4	194.4	220.5	243.0	269.1	291.6	381.3	474.7	564.4	654.2
70°	175.7	175.7	179.4	205.6	231.8	257.9	284.1	362.6	441.1	515.8	594.3
72.5°	157.0	160.7	164.5	190.6	213.1	239.2	261.7	332.7	403.7	474.7	545.7
75°	138.3	142.0	145.8	168.2	190.6	213.1	235.5	302.8	366.3	433.6	497.2
77.5°	123.4	127.1	130.8	149.5	168.2	186.9	205.6	254.2	306.5	355.1	403.7
80°	100.9	100.9	104.7	119.6	134.6	145.8	160.7	194.4	228.0	257.9	291.6
82.5°	74.8	78.5	78.5	89.7	97.2	108.4	115.9	134.6	149.5	168.2	183.2
85°	63.5	59.8	59.8	67.3	71.0	78.5	82.2	93.5	100.9	112.1	119.6
87.5°	26.2	22.4	22.4	26.2	33.6	37.4	41.1	41.1	44.9	44.9	44.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2758.7	2766.1	2777.3	2784.8	2803.5	2818.5	2837.1	2852.1	2863.3	2882.0	2874.5
5°	2657.7	2691.4	2725.0	2758.7	2784.8	2811.0	2833.4	2859.6	2889.5	2945.6	2960.5
7.5°	2358.7	2403.5	2444.7	2489.5	2541.8	2594.2	2646.5	2698.8	2747.4	2818.5	2863.3
10°	2063.4	2126.9	2186.7	2250.3	2298.9	2347.5	2392.3	2440.9	2508.2	2579.2	2661.5
12.5°	1876.5	1940.0	2003.6	2067.1	2138.1	2205.4	2276.4	2343.7	2407.3	2463.3	2556.8
15°	1753.1	1824.1	1891.4	1958.7	2044.7	2126.9	2212.9	2295.1	2388.6	2463.3	2526.9
17.5°	1723.2	1809.2	1891.4	1977.4	2067.1	2156.8	2246.5	2336.3	2429.7	2541.8	2624.1
20°	1670.9	1786.8	1902.6	2018.5	2134.4	2246.5	2362.4	2474.6	2597.9	2732.5	2769.9
22.5°	1641.0	1779.3	1921.3	2059.6	2216.6	2377.4	2534.4	2691.4	2822.2	2923.1	3035.3
25°	1637.2	1809.2	1984.9	2156.8	2354.9	2549.3	2747.4	2941.8	3110.0	3211.0	3300.7
27.5°	1633.5	1842.8	2048.4	2254.0	2497.0	2736.2	2979.2	3218.4	3375.4	3521.2	3596.0
30°	1588.7	1839.1	2093.3	2343.7	2616.6	2889.5	3162.4	3435.2	3596.0	3696.9	3734.3
32.5°	1532.6	1827.9	2123.2	2418.5	2728.7	3039.0	3345.5	3655.8	3782.9	3868.8	3838.9
35°	1487.7	1812.9	2134.4	2455.9	2784.8	3117.5	3446.4	3775.4	3958.6	4078.2	4029.6
37.5°	1446.6	1786.8	2126.9	2467.1	2852.1	3237.1	3622.1	4007.1	4182.8	4309.9	4253.9
40°	1398.0	1760.6	2126.9	2489.5	2930.6	3367.9	3809.0	4246.4	4474.4	4582.8	4496.8
42.5°	1356.9	1734.4	2115.7	2493.3	2964.2	3435.2	3906.2	4377.2	4631.4	4784.7	4676.3
45°	1304.6	1682.1	2055.9	2433.4	2953.0	3472.6	3988.5	4508.0	4803.3	4923.0	4773.4
47.5°	1248.5	1622.3	1992.4	2362.4	2915.6	3468.9	4022.1	4575.3	4848.2	4990.2	4851.9
50°	1229.8	1603.6	1973.7	2347.5	2945.6	3547.4	4145.5	4743.5	4941.6	5057.5	4874.4
52.5°	1226.1	1622.3	2022.3	2418.5	3020.3	3618.4	4220.2	4818.3	4979.0	5102.4	4937.9
55°	1214.9	1644.7	2070.9	2497.0	3125.0	3756.7	4384.7	5012.7	5173.4	5263.1	5139.8
57.5°	1226.1	1689.6	2149.4	2612.9	3259.5	3906.2	4552.9	5199.6	5393.9	5457.5	5431.3
60°	1233.5	1727.0	2216.6	2710.1	3341.8	3973.5	4605.2	5237.0	5438.8	5595.8	5625.7
62.5°	1214.9	1700.8	2183.0	2668.9	3240.9	3812.8	4384.7	4956.6	5289.3	5521.0	5655.6
65°	1158.8	1607.3	2059.6	2508.2	3035.3	3566.1	4093.1	4620.2	4971.6	5315.5	5423.9
67.5°	1035.4	1416.7	1798.0	2179.3	2639.0	3098.8	3554.8	4014.6	4455.7	4788.4	4937.9
70°	897.1	1196.2	1498.9	1798.0	2216.6	2635.3	3054.0	3472.6	3861.4	4227.7	4369.7
72.5°	781.2	1013.0	1248.5	1480.3	1779.3	2074.6	2373.6	2668.9	3128.7	3495.0	3633.3
75°	665.4	833.6	998.0	1166.3	1371.8	1577.4	1779.3	1984.9	2310.1	2639.0	2777.3
77.5°	512.1	624.2	732.6	841.1	983.1	1121.4	1263.4	1401.8	1629.8	1876.5	1947.5
80°	355.1	418.7	478.5	542.0	654.2	766.3	878.4	990.6	1140.1	1278.4	1386.8
82.5°	220.5	261.7	299.0	336.4	426.1	515.8	601.8	691.5	751.3	758.8	867.2
85°	142.0	168.2	190.6	213.1	265.4	321.5	373.8	426.1	381.3	355.1	422.4
87.5°	56.1	71.0	82.2	93.5	89.7	86.0	82.2	78.5	67.3	59.8	74.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2882.0	2893.2	2904.4	2911.9	2923.1	2926.9	2930.6	2930.6	2934.3	2938.1	2945.6
5°	3020.3	3042.7	3065.2	3083.9	3106.3	3125.0	3139.9	3158.6	3173.6	3173.6	3169.8
7.5°	2904.4	2960.5	3016.6	3072.6	3128.7	3169.8	3207.2	3248.3	3285.7	3293.2	3300.7
10°	2751.2	2811.0	2867.1	2926.9	2982.9	3046.5	3106.3	3166.1	3229.6	3240.9	3255.8
12.5°	2609.1	2680.2	2751.2	2818.5	2889.5	2934.3	2979.2	3020.3	3065.2	3095.1	3125.0
15°	2605.4	2665.2	2725.0	2781.1	2840.9	2867.1	2893.2	2915.6	2941.8	2941.8	2945.6
17.5°	2691.4	2728.7	2766.1	2799.8	2837.1	2840.9	2848.4	2852.1	2855.8	2844.6	2833.4
20°	2859.6	2874.5	2889.5	2904.4	2919.4	2893.2	2870.8	2844.6	2818.5	2788.6	2762.4
22.5°	3106.3	3072.6	3039.0	3005.4	2971.7	2926.9	2878.3	2833.4	2784.8	2747.4	2710.1
25°	3338.0	3296.9	3255.8	3214.7	3173.6	3076.4	2979.2	2878.3	2781.1	2740.0	2698.8
27.5°	3648.3	3584.8	3521.2	3457.7	3394.1	3263.3	3132.5	3001.6	2870.8	2799.8	2732.5
30°	3723.1	3652.0	3581.0	3506.3	3435.2	3308.1	3184.8	3057.7	2930.6	2848.4	2769.9
32.5°	3831.5	3749.2	3667.0	3584.8	3502.5	3379.2	3255.8	3128.7	3005.4	2930.6	2852.1
35°	4010.9	3917.4	3824.0	3726.8	3633.3	3506.3	3382.9	3255.8	3128.7	3042.7	2960.5
37.5°	4164.1	4055.7	3947.3	3838.9	3730.5	3618.4	3502.5	3390.4	3274.5	3188.5	3106.3
40°	4336.1	4216.5	4096.9	3981.0	3861.4	3756.7	3652.0	3543.6	3439.0	3371.7	3304.4
42.5°	4485.6	4339.8	4197.8	4055.7	3910.0	3838.9	3771.7	3700.6	3629.6	3596.0	3558.6
45°	4590.3	4455.7	4317.4	4182.8	4048.3	3995.9	3943.6	3891.3	3838.9	3872.6	3906.2
47.5°	4635.1	4526.7	4422.1	4317.4	4209.0	4227.7	4246.4	4261.3	4280.0	4324.9	4373.5
50°	4676.3	4616.4	4552.9	4493.1	4429.5	4500.6	4567.8	4638.9	4709.9	4803.3	4896.8
52.5°	4758.5	4724.8	4694.9	4661.3	4627.7	4751.0	4874.4	4997.7	5121.1	5225.7	5330.4
55°	5005.2	4979.0	4952.9	4923.0	4896.8	5072.5	5244.4	5420.1	5595.8	5704.2	5812.6
57.5°	5345.4	5330.4	5311.7	5296.8	5278.1	5450.0	5618.2	5786.4	5958.4	6063.1	6171.5
60°	5603.3	5607.0	5607.0	5610.8	5610.8	5741.6	5872.4	6007.0	6137.8	6227.5	6321.0
62.5°	5741.6	5734.1	5726.6	5719.2	5711.7	5820.1	5928.5	6036.9	6145.3	6212.6	6279.9
65°	5592.1	5633.2	5674.3	5715.4	5756.5	5771.5	5782.7	5797.7	5808.9	5850.0	5891.1
67.5°	5091.2	5173.4	5251.9	5334.1	5412.6	5356.6	5304.2	5248.2	5192.1	5203.3	5210.8
70°	4534.2	4627.7	4724.8	4818.3	4911.7	4780.9	4650.1	4515.5	4384.7	4339.8	4295.0
72.5°	3824.0	3906.2	3992.2	4074.4	4156.7	3995.9	3838.9	3678.2	3517.5	3439.0	3360.5
75°	2923.1	3020.3	3121.2	3218.4	3315.6	3136.2	2953.0	2773.6	2590.4	2538.1	2489.5
77.5°	2130.7	2246.5	2362.4	2478.3	2594.2	2433.4	2272.7	2108.2	1947.5	1917.6	1887.7
80°	1551.3	1641.0	1727.0	1816.7	1902.6	1809.2	1715.7	1622.3	1528.8	1525.1	1521.4
82.5°	1046.6	1125.1	1199.9	1278.4	1353.2	1315.8	1282.1	1244.8	1207.4	1244.8	1285.9
85°	538.3	646.7	758.8	867.2	975.6	964.4	956.9	945.7	934.5	983.1	1028.0
87.5°	108.4	201.9	295.3	385.0	478.5	456.0	433.6	407.4	385.0	400.0	411.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2949.3	2953.0	2953.0	2953.0	2953.0	2953.0	2945.6	2941.8	2934.3	2926.9	2915.6
5°	3169.8	3166.1	3151.1	3136.2	3117.5	3102.5	3091.3	3076.4	3065.2	3050.2	3027.8
7.5°	3308.1	3315.6	3289.4	3267.0	3240.9	3214.7	3188.5	3162.4	3136.2	3110.0	3057.7
10°	3267.0	3278.2	3263.3	3248.3	3229.6	3214.7	3184.8	3151.1	3121.2	3087.6	3024.1
12.5°	3151.1	3181.0	3173.6	3166.1	3158.6	3151.1	3132.5	3110.0	3091.3	3068.9	2997.9
15°	2945.6	2945.6	2949.3	2953.0	2953.0	2956.8	2960.5	2964.2	2968.0	2971.7	2930.6
17.5°	2822.2	2811.0	2811.0	2811.0	2811.0	2811.0	2825.9	2844.6	2859.6	2874.5	2863.3
20°	2732.5	2706.3	2702.6	2702.6	2698.8	2695.1	2721.3	2751.2	2777.3	2803.5	2818.5
22.5°	2672.7	2635.3	2631.6	2627.8	2624.1	2620.3	2654.0	2687.6	2721.3	2754.9	2807.2
25°	2657.7	2616.6	2620.3	2624.1	2624.1	2627.8	2654.0	2680.2	2706.3	2732.5	2822.2
27.5°	2661.5	2594.2	2597.9	2601.7	2601.7	2605.4	2646.5	2683.9	2725.0	2762.4	2874.5
30°	2687.6	2609.1	2601.7	2594.2	2586.7	2579.2	2635.3	2691.4	2747.4	2803.5	2889.5
32.5°	2777.3	2702.6	2683.9	2665.2	2646.5	2627.8	2695.1	2758.7	2825.9	2889.5	2960.5
35°	2874.5	2792.3	2784.8	2777.3	2766.1	2758.7	2818.5	2882.0	2941.8	3001.6	3065.2
37.5°	3020.3	2938.1	2930.6	2919.4	2911.9	2900.7	2968.0	3031.5	3098.8	3162.4	3218.4
40°	3237.1	3169.8	3166.1	3166.1	3162.4	3158.6	3211.0	3267.0	3319.4	3371.7	3409.1
42.5°	3524.9	3491.3	3502.5	3517.5	3528.7	3539.9	3581.0	3625.9	3667.0	3708.1	3696.9
45°	3939.9	3973.5	3977.2	3981.0	3984.7	3988.5	3999.7	4014.6	4025.8	4037.1	3992.2
47.5°	4418.3	4463.2	4485.6	4508.0	4526.7	4549.2	4534.2	4515.5	4500.6	4481.9	4369.7
50°	4986.5	5080.0	5076.2	5072.5	5065.0	5061.3	5031.4	5001.5	4967.8	4937.9	4773.4
52.5°	5435.1	5539.7	5558.4	5577.1	5595.8	5614.5	5558.4	5502.4	5442.5	5386.5	5180.9
55°	5917.3	6025.7	6029.4	6033.1	6033.1	6036.9	5958.4	5879.9	5797.7	5719.2	5506.1
57.5°	6276.1	6380.8	6369.6	6362.1	6350.9	6339.7	6246.2	6152.8	6059.3	5965.9	5752.8
60°	6410.7	6500.4	6478.0	6455.5	6429.4	6406.9	6335.9	6264.9	6190.1	6119.1	5913.5
62.5°	6347.1	6414.4	6380.8	6350.9	6317.2	6283.6	6193.9	6100.4	6010.7	5917.3	5767.7
65°	5928.5	5969.6	5924.7	5883.6	5842.5	5797.7	5722.9	5648.1	5569.6	5494.9	5393.9
67.5°	5222.0	5229.5	5225.7	5222.0	5218.3	5214.5	5106.1	4997.7	4885.6	4777.2	4769.7
70°	4253.9	4209.0	4216.5	4227.7	4235.2	4242.6	4160.4	4081.9	3999.7	3917.4	3954.8
72.5°	3282.0	3203.5	3222.2	3244.6	3263.3	3282.0	3214.7	3151.1	3083.9	3016.6	3068.9
75°	2437.2	2388.6	2407.3	2429.7	2448.4	2467.1	2440.9	2414.8	2384.9	2358.7	2407.3
77.5°	1857.8	1827.9	1831.6	1831.6	1835.4	1835.4	1839.1	1846.6	1850.3	1854.1	1906.4
80°	1513.9	1510.2	1506.4	1502.7	1495.2	1491.5	1528.8	1566.2	1603.6	1641.0	1667.2
82.5°	1323.3	1360.6	1338.2	1319.5	1297.1	1274.7	1308.3	1341.9	1375.6	1409.2	1398.0
85°	1076.5	1121.4	1080.3	1039.2	994.3	953.2	983.1	1009.3	1039.2	1065.3	1050.4
87.5°	426.1	437.3	370.1	306.5	239.2	171.9	272.9	370.1	471.0	568.2	583.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809

CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4	2691.4
2.5°	2904.4	2889.5	2878.3	2874.5	2867.1	2863.3	2855.8	2848.4	2837.1	2829.7	2818.5
5°	3001.6	2979.2	2953.0	2915.6	2882.0	2844.6	2807.2	2773.6	2740.0	2702.6	2668.9
7.5°	3005.4	2953.0	2900.7	2852.1	2799.8	2751.2	2698.8	2654.0	2605.4	2556.8	2511.9
10°	2964.2	2900.7	2837.1	2773.6	2713.8	2650.2	2586.7	2534.4	2478.3	2422.2	2369.9
12.5°	2930.6	2859.6	2788.6	2713.8	2642.8	2568.0	2493.3	2440.9	2388.6	2336.3	2283.9
15°	2889.5	2844.6	2803.5	2736.2	2668.9	2601.7	2534.4	2463.3	2396.1	2325.0	2254.0
17.5°	2855.8	2844.6	2833.4	2788.6	2743.7	2695.1	2650.2	2579.2	2508.2	2433.4	2362.4
20°	2837.1	2852.1	2867.1	2844.6	2822.2	2796.0	2773.6	2721.3	2668.9	2612.9	2560.5
22.5°	2859.6	2915.6	2968.0	2971.7	2979.2	2982.9	2986.7	2938.1	2889.5	2837.1	2788.6
25°	2911.9	3001.6	3091.3	3139.9	3188.5	3240.9	3289.4	3259.5	3229.6	3199.7	3169.8
27.5°	2982.9	3095.1	3207.2	3278.2	3345.5	3416.5	3487.6	3483.8	3480.1	3472.6	3468.9
30°	2971.7	3057.7	3143.7	3229.6	3315.6	3401.6	3487.6	3532.4	3573.5	3618.4	3663.2
32.5°	3035.3	3106.3	3181.0	3270.8	3360.5	3453.9	3543.6	3637.1	3726.8	3820.2	3913.7
35°	3132.5	3196.0	3263.3	3360.5	3461.4	3558.6	3659.5	3771.7	3887.5	4003.4	4115.5
37.5°	3278.2	3334.3	3394.1	3476.3	3562.3	3644.6	3730.5	3895.0	4059.5	4227.7	4392.2
40°	3446.4	3483.8	3521.2	3599.7	3678.2	3756.7	3835.2	4040.8	4246.4	4452.0	4657.6
42.5°	3689.4	3678.2	3667.0	3730.5	3797.8	3861.4	3928.6	4115.5	4302.4	4489.3	4676.3
45°	3947.3	3902.5	3857.6	3887.5	3921.2	3951.1	3984.7	4175.4	4366.0	4560.4	4751.0
47.5°	4257.6	4145.5	4033.3	4007.1	3981.0	3951.1	3924.9	4130.5	4336.1	4545.4	4751.0
50°	4609.0	4440.8	4276.3	4209.0	4138.0	4070.7	3999.7	4167.9	4339.8	4511.8	4680.0
52.5°	4975.3	4766.0	4560.4	4455.7	4351.0	4242.6	4138.0	4280.0	4425.8	4571.6	4713.6
55°	5289.3	5076.2	4859.4	4736.1	4612.7	4489.3	4366.0	4508.0	4650.1	4792.1	4934.2
57.5°	5539.7	5326.7	5113.6	4997.7	4878.1	4762.2	4642.6	4777.2	4915.5	5053.8	5188.4
60°	5711.7	5506.1	5300.5	5188.4	5076.2	4964.1	4851.9	5012.7	5173.4	5337.9	5498.6
62.5°	5622.0	5472.4	5322.9	5274.3	5225.7	5173.4	5124.8	5278.1	5427.6	5580.8	5734.1
65°	5293.0	5192.1	5091.2	5139.8	5192.1	5240.7	5293.0	5393.9	5494.9	5599.5	5700.5
67.5°	4758.5	4751.0	4739.8	4848.2	4956.6	5068.7	5177.1	5244.4	5308.0	5375.3	5442.5
70°	3992.2	4033.3	4070.7	4257.6	4444.5	4631.4	4818.3	4844.5	4870.6	4896.8	4923.0
72.5°	3125.0	3177.3	3233.4	3480.1	3723.1	3969.8	4216.5	4201.5	4186.6	4167.9	4152.9
75°	2459.6	2508.2	2560.5	2788.6	3016.6	3244.6	3472.6	3409.1	3349.3	3285.7	3222.2
77.5°	1962.5	2014.8	2070.9	2283.9	2497.0	2713.8	2926.9	2773.6	2620.3	2467.1	2313.8
80°	1689.6	1715.7	1738.2	1884.0	2026.0	2171.8	2317.6	2160.6	1999.8	1839.1	1682.1
82.5°	1386.8	1371.8	1360.6	1446.6	1532.6	1618.6	1704.5	1555.0	1405.5	1252.2	1102.7
85°	1035.4	1020.5	1005.5	1050.4	1095.2	1143.8	1188.7	1016.7	844.8	669.1	497.2
87.5°	601.8	616.8	631.7	680.3	728.9	781.2	829.8	654.2	478.5	299.0	123.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671809
 CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2691.4	2691.4
2.5°	2796.0	2777.3
5°	2642.8	2616.6
7.5°	2474.6	2440.9
10°	2321.3	2276.4
12.5°	2224.1	2168.0
15°	2186.7	2119.5
17.5°	2298.9	2235.3
20°	2470.8	2384.9
22.5°	2680.2	2575.5
25°	3042.7	2915.6
27.5°	3338.0	3207.2
30°	3521.2	3379.2
32.5°	3723.1	3536.2
35°	3932.4	3753.0
37.5°	4186.6	3984.7
40°	4448.2	4238.9
42.5°	4537.9	4403.4
45°	4623.9	4496.8
47.5°	4642.6	4537.9
50°	4661.3	4646.3
52.5°	4713.6	4709.9
55°	4937.9	4941.6
57.5°	5214.5	5237.0
60°	5468.7	5442.5
62.5°	5599.5	5465.0
65°	5509.8	5322.9
67.5°	5240.7	5038.8
70°	4650.1	4377.2
72.5°	3913.7	3674.5
75°	3016.6	2814.7
77.5°	2145.6	1977.4
80°	1510.2	1341.9
82.5°	968.1	833.6
85°	437.3	381.3
87.5°	123.4	119.6
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671809
CATALOG NUMBER: CCP-SA-2D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)