

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671818

Luminaire Tested: **CCP-SA-2B-735-U-SLR**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P671818  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2B-735-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR distribution lens  
Light Source: (32) 3500K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5652.7 lumens  
Efficiency: N/A  
Efficacy: 122.9 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2


Input Watts (W): 46  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 8 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671818  
CATALOG NUMBER: CCP-SA-2B-735-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1163.1	0.0	1163.1
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	4489.7	0.0	4489.7
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	5652.7	0.0	5652.7
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.3	2.5
10°-20°	296.1	5.2
20°-30°	433.3	7.7
30°-40°	610.4	10.8
40°-50°	838.8	14.8
50°-60°	1143.3	20.2
60°-70°	1251.3	22.1
70°-80°	722.6	12.8
80°-90°	216.6	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5652.7	100.0
0°-180°	5652.7	100.0



REPORT NUMBER: P671818


CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	580.6	10.3			
FM (30°-60°)	2062.9	36.5			
FH (60°-80°)	1662.2	29.4			G1/1800
FVH (80°-90°)	184.0	3.3			G2/225
BL (0°-30°)	289.1	5.1	B1/500		
BM (30°-60°)	529.6	9.4	B1/1000		
BH (60°-80°)	311.7	5.5	B1/500		G1/500
BVH (80°-90°)	32.6	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**

Type IV Short





REPORT NUMBER: P671818

CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1862.8	1852.8	1845.3	1837.7	1827.7	1820.2	1810.2	1800.1	1787.6	1777.6	1765.0
5°	1755.0	1724.9	1694.8	1677.3	1657.2	1639.7	1619.6	1597.0	1574.5	1549.4	1526.8
7.5°	1637.2	1599.6	1561.9	1531.9	1499.3	1469.2	1436.6	1409.0	1381.4	1353.9	1326.3
10°	1526.8	1491.7	1456.6	1419.0	1378.9	1341.3	1301.2	1263.6	1226.0	1188.4	1150.8
12.5°	1454.1	1411.5	1371.4	1328.8	1288.7	1246.0	1203.4	1168.3	1133.2	1095.6	1060.5
15°	1421.5	1381.4	1343.8	1301.2	1258.6	1216.0	1173.3	1133.2	1095.6	1055.5	1015.4
17.5°	1499.3	1441.6	1383.9	1328.8	1273.6	1218.5	1163.3	1113.2	1063.0	1012.9	962.7
20°	1599.6	1526.8	1456.6	1389.0	1318.8	1251.1	1180.9	1110.7	1040.5	970.3	900.1
22.5°	1727.4	1644.7	1564.5	1476.7	1386.4	1298.7	1208.4	1120.7	1032.9	942.7	854.9
25°	1955.6	1857.8	1760.0	1634.7	1506.8	1381.4	1253.6	1138.2	1025.4	910.1	794.8
27.5°	2151.1	2018.2	1887.9	1737.4	1587.0	1436.6	1286.2	1153.3	1022.9	890.0	757.2
30°	2266.5	2136.1	2005.7	1822.7	1642.2	1459.2	1276.1	1128.2	982.8	834.9	687.0
32.5°	2371.8	2226.3	2080.9	1880.4	1677.3	1476.7	1273.6	1110.7	950.2	787.2	624.3
35°	2517.2	2356.7	2198.8	1965.6	1732.4	1499.3	1266.1	1098.1	927.6	759.7	589.2
37.5°	2672.6	2474.5	2279.0	2020.8	1762.5	1504.3	1246.0	1080.6	915.1	749.6	584.2
40°	2843.1	2602.4	2364.2	2078.4	1795.1	1509.3	1223.5	1058.0	892.5	724.6	559.1
42.5°	2953.4	2692.7	2431.9	2123.5	1817.7	1509.3	1200.9	1038.0	875.0	709.5	546.6
45°	3016.1	2762.9	2512.2	2178.7	1845.3	1511.8	1178.4	1017.9	857.4	694.5	534.0
47.5°	3043.7	2808.0	2572.3	2221.3	1872.8	1521.8	1170.8	1007.9	842.4	679.4	514.0
50°	3116.4	2908.3	2700.2	2324.1	1950.6	1574.5	1198.4	1022.9	849.9	674.4	498.9
52.5°	3159.0	2981.0	2803.0	2416.9	2030.8	1644.7	1258.6	1063.0	867.5	671.9	476.4
55°	3314.4	3143.9	2973.5	2562.3	2148.6	1737.4	1323.8	1108.2	892.5	674.4	458.8
57.5°	3512.5	3332.0	3154.0	2710.2	2266.5	1822.7	1378.9	1148.3	915.1	684.4	451.3
60°	3650.4	3474.9	3301.9	2830.6	2356.7	1885.4	1411.5	1170.8	930.1	687.0	446.3
62.5°	3665.4	3439.8	3216.7	2757.9	2299.0	1837.7	1378.9	1145.8	912.6	676.9	443.8
65°	3570.2	3306.9	3043.7	2604.9	2166.2	1727.4	1288.7	1075.6	862.5	646.8	433.7
67.5°	3379.6	3071.2	2762.9	2361.7	1960.6	1559.4	1158.3	975.3	794.8	611.7	428.7
70°	2935.9	2665.1	2396.8	2048.3	1702.3	1353.9	1005.4	854.9	707.0	556.6	406.2
72.5°	2464.5	2211.3	1960.6	1677.3	1396.5	1113.2	829.9	717.0	604.2	488.9	376.1
75°	1887.9	1697.3	1509.3	1298.7	1088.1	875.0	664.4	581.7	498.9	416.2	333.4
77.5°	1326.3	1223.5	1123.2	965.2	807.3	649.3	491.4	436.2	381.1	325.9	270.8
80°	900.1	842.4	787.2	674.4	561.6	446.3	333.4	298.3	260.7	225.6	188.0
82.5°	559.1	556.6	551.6	473.8	396.1	318.4	240.7	210.6	183.0	152.9	122.8
85°	255.7	298.3	338.5	295.8	253.2	210.6	168.0	147.9	127.9	105.3	85.2
87.5°	80.2	97.8	112.8	107.8	100.3	95.3	87.7	75.2	62.7	50.1	37.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671818

CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1755.0	1747.5	1737.4	1727.4	1714.9	1704.9	1692.3	1679.8	1677.3	1672.3	1669.8
5°	1511.8	1496.8	1479.2	1464.2	1449.1	1431.6	1416.5	1399.0	1386.4	1371.4	1358.9
7.5°	1298.7	1273.6	1246.0	1218.5	1193.4	1168.3	1140.7	1115.7	1103.1	1090.6	1078.1
10°	1128.2	1103.1	1080.6	1055.5	1038.0	1022.9	1005.4	987.8	972.8	957.7	942.7
12.5°	1043.0	1025.4	1007.9	990.3	970.3	952.7	932.7	912.6	895.0	880.0	862.5
15°	990.3	965.2	937.7	912.6	885.0	859.9	832.4	804.8	784.7	767.2	747.1
17.5°	927.6	890.0	854.9	817.3	787.2	757.2	724.6	694.5	671.9	646.8	624.3
20°	857.4	814.8	769.7	727.1	692.0	659.4	624.3	589.2	564.1	536.5	511.5
22.5°	797.3	742.1	684.4	626.8	589.2	551.6	511.5	473.8	451.3	426.2	403.6
25°	732.1	671.9	609.2	546.6	508.9	468.8	431.2	391.1	373.6	358.5	341.0
27.5°	697.0	636.8	574.1	514.0	478.9	441.3	406.2	368.5	356.0	341.0	328.4
30°	626.8	569.1	508.9	448.8	423.7	401.1	376.1	351.0	346.0	343.5	338.5
32.5°	564.1	503.9	443.8	383.6	361.0	338.5	315.9	293.3	290.8	285.8	283.3
35°	531.5	473.8	413.7	356.0	336.0	313.4	293.3	270.8	265.8	258.2	253.2
37.5°	524.0	463.8	401.1	341.0	320.9	300.9	278.3	258.2	253.2	248.2	243.2
40°	503.9	446.3	391.1	333.4	313.4	293.3	270.8	250.7	245.7	240.7	235.7
42.5°	488.9	433.7	376.1	318.4	300.9	283.3	263.2	245.7	240.7	235.7	228.1
45°	476.4	418.7	358.5	300.9	288.3	275.8	260.7	248.2	243.2	235.7	230.7
47.5°	456.3	401.1	343.5	285.8	273.3	263.2	250.7	238.2	233.2	228.1	223.1
50°	441.3	383.6	325.9	268.3	258.2	248.2	238.2	228.1	228.1	230.7	230.7
52.5°	421.2	366.0	310.9	255.7	245.7	235.7	225.6	215.6	218.1	220.6	223.1
55°	403.6	351.0	295.8	240.7	230.7	220.6	208.1	198.1	200.6	203.1	205.6
57.5°	396.1	341.0	285.8	230.7	220.6	208.1	198.1	185.5	185.5	185.5	185.5
60°	391.1	333.4	278.3	220.6	208.1	198.1	185.5	173.0	170.5	170.5	168.0
62.5°	388.6	330.9	275.8	218.1	203.1	190.5	175.5	160.5	157.9	155.4	152.9
65°	378.6	325.9	270.8	215.6	198.1	183.0	165.5	147.9	145.4	145.4	142.9
67.5°	376.1	320.9	268.3	213.1	195.6	175.5	157.9	137.9	135.4	132.9	130.4
70°	356.0	308.4	258.2	208.1	188.0	170.5	150.4	130.4	127.9	122.8	120.3
72.5°	330.9	288.3	243.2	198.1	178.0	157.9	137.9	117.8	115.3	112.8	107.8
75°	293.3	253.2	213.1	173.0	155.4	140.4	122.8	105.3	102.8	100.3	95.3
77.5°	240.7	208.1	178.0	145.4	132.9	120.3	107.8	95.3	92.8	90.3	85.2
80°	170.5	150.4	132.9	112.8	105.3	95.3	87.7	77.7	77.7	75.2	75.2
82.5°	112.8	102.8	92.8	82.7	77.7	72.7	67.7	62.7	62.7	60.2	60.2
85°	80.2	75.2	67.7	62.7	60.2	55.2	52.6	47.6	47.6	47.6	47.6
87.5°	37.6	37.6	35.1	35.1	32.6	32.6	30.1	27.6	27.6	27.6	27.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818

CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1664.7	1657.2	1649.7	1639.7	1632.1	1622.1	1609.6	1599.6	1587.0	1587.0	1584.5
5°	1343.8	1336.3	1328.8	1318.8	1311.2	1301.2	1293.7	1283.7	1273.6	1273.6	1271.1
7.5°	1065.5	1050.5	1035.4	1017.9	1002.9	992.8	982.8	970.3	960.2	952.7	945.2
10°	927.6	912.6	895.0	880.0	862.5	849.9	837.4	822.3	809.8	799.8	789.7
12.5°	844.9	827.4	809.8	792.3	774.7	757.2	742.1	724.6	707.0	694.5	681.9
15°	727.1	709.5	692.0	674.4	656.9	636.8	616.8	594.2	574.1	564.1	556.6
17.5°	599.2	581.7	561.6	544.0	524.0	508.9	493.9	478.9	463.8	453.8	446.3
20°	483.9	463.8	443.8	423.7	403.6	393.6	383.6	373.6	363.5	356.0	351.0
22.5°	378.6	366.0	356.0	343.5	330.9	323.4	318.4	310.9	303.4	303.4	303.4
25°	323.4	315.9	310.9	303.4	295.8	293.3	290.8	285.8	283.3	280.8	280.8
27.5°	313.4	305.9	298.3	290.8	283.3	280.8	278.3	273.3	270.8	270.8	270.8
30°	333.4	330.9	328.4	325.9	323.4	318.4	310.9	305.9	298.3	293.3	288.3
32.5°	278.3	275.8	275.8	273.3	270.8	275.8	278.3	283.3	285.8	288.3	290.8
35°	245.7	240.7	235.7	230.7	225.6	223.1	220.6	218.1	215.6	215.6	213.1
37.5°	238.2	233.2	228.1	223.1	218.1	215.6	213.1	210.6	208.1	208.1	205.6
40°	230.7	225.6	223.1	218.1	213.1	210.6	208.1	203.1	200.6	198.1	198.1
42.5°	223.1	220.6	215.6	213.1	208.1	205.6	203.1	198.1	195.6	193.0	190.5
45°	223.1	218.1	213.1	208.1	203.1	200.6	195.6	193.0	188.0	188.0	185.5
47.5°	218.1	213.1	208.1	203.1	198.1	195.6	190.5	188.0	183.0	180.5	178.0
50°	230.7	223.1	213.1	205.6	195.6	193.0	188.0	185.5	180.5	178.0	175.5
52.5°	225.6	218.1	208.1	200.6	190.5	185.5	183.0	178.0	173.0	170.5	168.0
55°	208.1	200.6	195.6	188.0	180.5	175.5	170.5	165.5	160.5	157.9	157.9
57.5°	185.5	183.0	180.5	178.0	175.5	170.5	165.5	157.9	152.9	150.4	147.9
60°	165.5	168.0	170.5	173.0	175.5	168.0	160.5	152.9	145.4	142.9	140.4
62.5°	150.4	155.4	160.5	163.0	168.0	160.5	152.9	145.4	137.9	135.4	132.9
65°	140.4	142.9	142.9	145.4	145.4	140.4	137.9	132.9	127.9	125.4	125.4
67.5°	127.9	127.9	127.9	125.4	125.4	122.8	122.8	120.3	117.8	115.3	115.3
70°	115.3	115.3	115.3	112.8	112.8	110.3	110.3	107.8	105.3	105.3	102.8
72.5°	105.3	105.3	102.8	102.8	100.3	100.3	100.3	97.8	97.8	95.3	95.3
75°	92.8	92.8	90.3	90.3	87.7	87.7	87.7	85.2	85.2	85.2	82.7
77.5°	82.7	82.7	80.2	80.2	77.7	77.7	77.7	75.2	75.2	72.7	72.7
80°	72.7	72.7	70.2	70.2	67.7	67.7	65.2	65.2	62.7	62.7	60.2
82.5°	57.7	57.7	57.7	57.7	57.7	55.2	55.2	52.6	50.1	50.1	47.6
85°	47.6	47.6	47.6	45.1	45.1	45.1	42.6	42.6	40.1	37.6	37.6
87.5°	27.6	27.6	27.6	25.1	25.1	25.1	25.1	25.1	25.1	25.1	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1584.5	1582.0	1572.0	1561.9	1572.0	1582.0	1582.0	1582.0	1579.5	1579.5	1579.5
5°	1271.1	1268.6	1263.6	1258.6	1258.6	1256.1	1261.1	1266.1	1271.1	1276.1	1281.1
7.5°	935.2	927.6	920.1	912.6	917.6	920.1	927.6	932.7	940.2	945.2	957.7
10°	779.7	769.7	762.2	754.6	749.6	744.6	739.6	737.1	732.1	727.1	732.1
12.5°	666.9	654.4	641.8	626.8	624.3	621.8	616.8	611.7	606.7	601.7	599.2
15°	546.6	536.5	531.5	524.0	514.0	503.9	498.9	496.4	491.4	486.4	483.9
17.5°	436.2	426.2	418.7	411.2	408.7	403.6	403.6	403.6	403.6	403.6	403.6
20°	343.5	336.0	336.0	333.4	333.4	330.9	333.4	336.0	336.0	338.5	341.0
22.5°	300.9	300.9	298.3	295.8	298.3	298.3	300.9	303.4	305.9	308.4	310.9
25°	278.3	275.8	278.3	280.8	280.8	280.8	283.3	283.3	285.8	285.8	285.8
27.5°	268.3	268.3	270.8	270.8	273.3	273.3	273.3	270.8	270.8	268.3	268.3
30°	283.3	278.3	278.3	278.3	275.8	273.3	270.8	270.8	268.3	265.8	263.2
32.5°	293.3	295.8	293.3	288.3	285.8	280.8	278.3	273.3	270.8	265.8	260.7
35°	213.1	210.6	215.6	218.1	220.6	223.1	225.6	228.1	228.1	230.7	230.7
37.5°	205.6	203.1	203.1	200.6	200.6	200.6	200.6	200.6	198.1	198.1	200.6
40°	195.6	193.0	193.0	190.5	190.5	188.0	188.0	188.0	188.0	188.0	188.0
42.5°	188.0	185.5	185.5	185.5	185.5	183.0	183.0	180.5	180.5	178.0	178.0
45°	185.5	183.0	180.5	178.0	178.0	175.5	175.5	175.5	173.0	173.0	173.0
47.5°	175.5	173.0	173.0	170.5	170.5	168.0	168.0	168.0	165.5	165.5	165.5
50°	170.5	168.0	168.0	165.5	165.5	163.0	163.0	163.0	160.5	160.5	160.5
52.5°	163.0	160.5	160.5	160.5	157.9	155.4	155.4	155.4	152.9	152.9	152.9
55°	155.4	152.9	152.9	152.9	150.4	147.9	147.9	147.9	145.4	145.4	145.4
57.5°	145.4	142.9	142.9	140.4	140.4	140.4	140.4	140.4	137.9	137.9	137.9
60°	137.9	135.4	135.4	132.9	132.9	130.4	130.4	130.4	130.4	130.4	130.4
62.5°	130.4	127.9	125.4	122.8	125.4	125.4	125.4	125.4	122.8	122.8	122.8
65°	122.8	120.3	117.8	115.3	115.3	115.3	115.3	115.3	115.3	115.3	115.3
67.5°	112.8	110.3	107.8	105.3	107.8	107.8	107.8	107.8	107.8	107.8	107.8
70°	102.8	100.3	100.3	97.8	97.8	95.3	95.3	97.8	97.8	97.8	97.8
72.5°	92.8	90.3	90.3	87.7	87.7	87.7	87.7	87.7	87.7	87.7	87.7
75°	82.7	80.2	80.2	77.7	77.7	77.7	77.7	77.7	77.7	77.7	77.7
77.5°	70.2	67.7	67.7	67.7	67.7	67.7	67.7	70.2	70.2	70.2	70.2
80°	60.2	57.7	57.7	57.7	57.7	57.7	57.7	57.7	57.7	57.7	57.7
82.5°	47.6	45.1	45.1	45.1	45.1	45.1	45.1	45.1	45.1	45.1	45.1
85°	35.1	32.6	32.6	32.6	35.1	35.1	35.1	35.1	35.1	35.1	35.1
87.5°	22.6	20.1	20.1	20.1	22.6	22.6	22.6	22.6	20.1	20.1	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818

CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1579.5	1579.5	1579.5	1577.0	1574.5	1572.0	1569.5	1577.0	1582.0	1589.5	1594.5
5°	1283.7	1288.7	1291.2	1298.7	1306.2	1313.7	1321.3	1326.3	1331.3	1333.8	1338.8
7.5°	967.8	980.3	990.3	1000.3	1010.4	1017.9	1027.9	1035.4	1043.0	1050.5	1058.0
10°	734.6	739.6	742.1	752.1	759.7	769.7	777.2	784.7	792.3	797.3	804.8
12.5°	596.7	591.7	589.2	589.2	589.2	589.2	589.2	594.2	599.2	604.2	609.2
15°	481.4	478.9	476.4	473.8	471.3	466.3	463.8	468.8	473.8	478.9	483.9
17.5°	403.6	403.6	403.6	401.1	398.6	396.1	393.6	396.1	398.6	398.6	401.1
20°	346.0	348.5	351.0	353.5	353.5	356.0	356.0	358.5	361.0	361.0	363.5
22.5°	310.9	313.4	313.4	313.4	315.9	315.9	315.9	318.4	320.9	323.4	325.9
25°	283.3	283.3	280.8	280.8	283.3	283.3	283.3	283.3	285.8	285.8	285.8
27.5°	268.3	265.8	265.8	265.8	265.8	263.2	263.2	263.2	263.2	263.2	263.2
30°	260.7	258.2	255.7	253.2	253.2	250.7	248.2	248.2	248.2	248.2	248.2
32.5°	258.2	253.2	248.2	245.7	245.7	243.2	240.7	238.2	238.2	235.7	233.2
35°	230.7	228.1	228.1	225.6	223.1	220.6	218.1	218.1	218.1	215.6	215.6
37.5°	200.6	203.1	203.1	203.1	205.6	205.6	205.6	205.6	208.1	208.1	208.1
40°	188.0	188.0	188.0	190.5	193.0	193.0	195.6	195.6	198.1	198.1	198.1
42.5°	178.0	175.5	175.5	178.0	178.0	180.5	180.5	183.0	185.5	185.5	188.0
45°	173.0	170.5	170.5	170.5	170.5	168.0	168.0	170.5	173.0	175.5	178.0
47.5°	163.0	163.0	160.5	160.5	160.5	160.5	160.5	160.5	163.0	163.0	163.0
50°	157.9	157.9	155.4	155.4	155.4	155.4	155.4	155.4	155.4	155.4	155.4
52.5°	152.9	150.4	150.4	150.4	150.4	147.9	147.9	147.9	147.9	147.9	147.9
55°	145.4	142.9	142.9	142.9	142.9	142.9	142.9	142.9	145.4	145.4	145.4
57.5°	137.9	135.4	135.4	135.4	137.9	137.9	137.9	137.9	140.4	140.4	140.4
60°	130.4	130.4	130.4	130.4	130.4	130.4	130.4	132.9	132.9	135.4	135.4
62.5°	122.8	122.8	122.8	122.8	125.4	125.4	125.4	125.4	127.9	127.9	127.9
65°	115.3	115.3	115.3	115.3	117.8	117.8	117.8	117.8	117.8	117.8	117.8
67.5°	107.8	107.8	107.8	107.8	107.8	107.8	107.8	110.3	110.3	112.8	112.8
70°	97.8	95.3	95.3	97.8	97.8	100.3	100.3	102.8	102.8	105.3	105.3
72.5°	87.7	87.7	87.7	87.7	87.7	87.7	87.7	90.3	92.8	92.8	95.3
75°	77.7	77.7	77.7	77.7	80.2	80.2	80.2	82.7	82.7	85.2	85.2
77.5°	70.2	67.7	67.7	67.7	70.2	70.2	70.2	72.7	72.7	75.2	75.2
80°	57.7	57.7	57.7	57.7	60.2	60.2	60.2	60.2	62.7	62.7	62.7
82.5°	47.6	47.6	47.6	47.6	47.6	47.6	47.6	47.6	50.1	50.1	50.1
85°	35.1	35.1	35.1	35.1	37.6	37.6	37.6	37.6	37.6	37.6	37.6
87.5°	22.6	22.6	22.6	22.6	22.6	22.6	22.6	22.6	25.1	25.1	25.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1594.5	1594.5	1594.5	1594.5	1599.6	1602.1	1607.1	1609.6	1607.1	1604.6	1599.6
5°	1341.3	1343.8	1343.8	1346.3	1346.3	1346.3	1346.3	1346.3	1351.3	1356.4	1361.4
7.5°	1060.5	1063.0	1065.5	1068.0	1068.0	1068.0	1065.5	1065.5	1068.0	1068.0	1070.5
10°	812.3	822.3	829.9	837.4	832.4	824.8	819.8	812.3	812.3	812.3	809.8
12.5°	614.2	616.8	621.8	624.3	621.8	621.8	619.3	616.8	619.3	624.3	626.8
15°	486.4	486.4	488.9	488.9	491.4	493.9	493.9	496.4	501.4	503.9	508.9
17.5°	403.6	406.2	406.2	408.7	408.7	411.2	411.2	411.2	416.2	421.2	428.7
20°	363.5	363.5	363.5	363.5	363.5	361.0	361.0	358.5	361.0	366.0	368.5
22.5°	325.9	328.4	328.4	328.4	325.9	323.4	318.4	315.9	315.9	318.4	318.4
25°	285.8	283.3	283.3	280.8	280.8	283.3	283.3	283.3	285.8	285.8	288.3
27.5°	263.2	260.7	260.7	258.2	258.2	260.7	260.7	260.7	260.7	260.7	260.7
30°	245.7	245.7	243.2	240.7	243.2	243.2	245.7	245.7	248.2	248.2	250.7
32.5°	233.2	230.7	230.7	228.1	230.7	230.7	233.2	233.2	235.7	238.2	238.2
35°	215.6	215.6	215.6	215.6	215.6	215.6	213.1	213.1	213.1	213.1	213.1
37.5°	205.6	205.6	203.1	200.6	200.6	200.6	200.6	200.6	198.1	195.6	193.0
40°	198.1	195.6	195.6	193.0	190.5	190.5	188.0	185.5	185.5	183.0	183.0
42.5°	188.0	185.5	185.5	183.0	180.5	180.5	178.0	175.5	175.5	175.5	173.0
45°	175.5	175.5	173.0	170.5	170.5	170.5	168.0	168.0	168.0	168.0	165.5
47.5°	163.0	163.0	160.5	160.5	160.5	160.5	157.9	157.9	157.9	157.9	157.9
50°	155.4	155.4	155.4	155.4	155.4	155.4	152.9	152.9	152.9	152.9	152.9
52.5°	147.9	147.9	147.9	147.9	147.9	147.9	147.9	147.9	147.9	147.9	147.9
55°	145.4	145.4	145.4	145.4	145.4	145.4	142.9	142.9	142.9	145.4	145.4
57.5°	140.4	140.4	137.9	137.9	137.9	137.9	137.9	137.9	137.9	137.9	137.9
60°	135.4	135.4	135.4	135.4	135.4	135.4	135.4	135.4	135.4	135.4	135.4
62.5°	127.9	127.9	127.9	127.9	127.9	130.4	130.4	130.4	130.4	130.4	127.9
65°	117.8	120.3	120.3	120.3	120.3	120.3	120.3	120.3	120.3	120.3	120.3
67.5°	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8
70°	105.3	105.3	102.8	102.8	102.8	105.3	105.3	105.3	105.3	105.3	105.3
72.5°	95.3	95.3	95.3	95.3	95.3	95.3	95.3	95.3	95.3	97.8	97.8
75°	85.2	85.2	85.2	85.2	85.2	85.2	85.2	85.2	85.2	85.2	85.2
77.5°	75.2	75.2	72.7	72.7	72.7	75.2	75.2	75.2	75.2	77.7	77.7
80°	62.7	62.7	62.7	62.7	62.7	62.7	62.7	62.7	62.7	65.2	65.2
82.5°	50.1	50.1	50.1	50.1	50.1	50.1	50.1	50.1	50.1	52.6	52.6
85°	37.6	40.1	40.1	40.1	40.1	40.1	40.1	40.1	40.1	42.6	42.6
87.5°	25.1	25.1	25.1	25.1	25.1	25.1	22.6	22.6	22.6	22.6	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818

CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1597.0	1599.6	1602.1	1602.1	1604.6	1607.1	1607.1	1617.1	1627.1	1632.1	1637.2
5°	1366.4	1363.9	1363.9	1361.4	1358.9	1366.4	1373.9	1389.0	1404.0	1406.5	1411.5
7.5°	1070.5	1073.1	1075.6	1075.6	1078.1	1070.5	1060.5	1063.0	1065.5	1078.1	1088.1
10°	809.8	812.3	814.8	814.8	817.3	814.8	809.8	817.3	824.8	834.9	847.4
12.5°	629.3	636.8	644.3	649.3	656.9	661.9	664.4	674.4	681.9	694.5	707.0
15°	514.0	519.0	524.0	529.0	534.0	539.0	544.0	554.1	564.1	579.1	594.2
17.5°	433.7	433.7	436.2	436.2	436.2	441.3	446.3	451.3	453.8	468.8	483.9
20°	371.1	368.5	366.0	363.5	361.0	366.0	368.5	371.1	373.6	383.6	391.1
22.5°	318.4	318.4	320.9	320.9	320.9	318.4	313.4	315.9	315.9	320.9	328.4
25°	288.3	288.3	288.3	285.8	285.8	288.3	290.8	290.8	288.3	290.8	293.3
27.5°	260.7	263.2	263.2	265.8	265.8	268.3	268.3	268.3	268.3	270.8	273.3
30°	250.7	250.7	253.2	253.2	253.2	255.7	258.2	258.2	258.2	260.7	265.8
32.5°	240.7	243.2	245.7	248.2	250.7	253.2	253.2	255.7	255.7	258.2	260.7
35°	213.1	210.6	210.6	208.1	205.6	205.6	205.6	205.6	203.1	205.6	205.6
37.5°	190.5	190.5	190.5	188.0	188.0	190.5	190.5	190.5	190.5	193.0	193.0
40°	180.5	180.5	180.5	180.5	180.5	180.5	180.5	183.0	183.0	185.5	188.0
42.5°	173.0	173.0	173.0	173.0	173.0	175.5	175.5	175.5	175.5	178.0	178.0
45°	165.5	165.5	165.5	165.5	165.5	165.5	165.5	168.0	168.0	170.5	173.0
47.5°	157.9	157.9	157.9	157.9	157.9	160.5	163.0	163.0	163.0	165.5	165.5
50°	152.9	152.9	152.9	152.9	152.9	155.4	155.4	157.9	157.9	160.5	163.0
52.5°	147.9	147.9	147.9	147.9	147.9	150.4	150.4	152.9	152.9	155.4	157.9
55°	145.4	145.4	145.4	142.9	142.9	145.4	145.4	147.9	147.9	150.4	150.4
57.5°	137.9	137.9	137.9	137.9	137.9	137.9	137.9	140.4	140.4	142.9	145.4
60°	135.4	135.4	132.9	132.9	130.4	132.9	132.9	135.4	135.4	137.9	137.9
62.5°	127.9	127.9	127.9	125.4	125.4	127.9	127.9	127.9	127.9	130.4	132.9
65°	120.3	120.3	120.3	117.8	117.8	120.3	120.3	120.3	120.3	122.8	125.4
67.5°	112.8	112.8	112.8	110.3	110.3	110.3	110.3	112.8	112.8	115.3	117.8
70°	105.3	105.3	105.3	102.8	102.8	102.8	100.3	102.8	105.3	107.8	107.8
72.5°	97.8	97.8	97.8	95.3	95.3	95.3	92.8	95.3	95.3	97.8	97.8
75°	85.2	85.2	85.2	85.2	85.2	85.2	82.7	82.7	82.7	85.2	85.2
77.5°	77.7	77.7	77.7	75.2	75.2	75.2	72.7	72.7	72.7	75.2	75.2
80°	65.2	65.2	65.2	62.7	62.7	62.7	60.2	60.2	60.2	62.7	62.7
82.5°	52.6	52.6	52.6	50.1	50.1	50.1	47.6	47.6	47.6	50.1	50.1
85°	42.6	42.6	42.6	42.6	42.6	42.6	40.1	40.1	40.1	42.6	45.1
87.5°	20.1	20.1	22.6	22.6	22.6	22.6	20.1	20.1	17.5	17.5	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818

CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1642.2	1647.2	1659.7	1669.8	1682.3	1692.3	1699.8	1709.9	1717.4	1724.9	1729.9
5°	1414.0	1416.5	1429.1	1441.6	1451.6	1464.2	1481.7	1499.3	1516.8	1534.4	1546.9
7.5°	1100.6	1110.7	1125.7	1143.3	1158.3	1173.3	1190.9	1210.9	1228.5	1246.0	1263.6
10°	857.4	867.5	882.5	897.6	910.1	925.1	945.2	965.2	985.3	1005.4	1025.4
12.5°	719.5	732.1	749.6	767.2	782.2	799.8	824.8	847.4	872.5	895.0	920.1
15°	606.7	621.8	644.3	669.4	692.0	714.5	739.6	764.7	787.2	812.3	837.4
17.5°	498.9	514.0	534.0	556.6	576.6	596.7	626.8	654.4	684.4	712.0	739.6
20°	401.1	408.7	428.7	448.8	468.8	488.9	511.5	534.0	556.6	579.1	614.2
22.5°	333.4	338.5	348.5	356.0	366.0	373.6	396.1	418.7	438.7	461.3	493.9
25°	293.3	295.8	303.4	308.4	315.9	320.9	336.0	348.5	363.5	376.1	406.2
27.5°	273.3	275.8	278.3	280.8	283.3	285.8	295.8	305.9	313.4	323.4	351.0
30°	268.3	270.8	278.3	283.3	290.8	295.8	300.9	305.9	310.9	315.9	333.4
32.5°	263.2	265.8	265.8	263.2	263.2	260.7	265.8	268.3	273.3	275.8	290.8
35°	208.1	208.1	210.6	213.1	215.6	218.1	225.6	230.7	238.2	243.2	255.7
37.5°	195.6	195.6	198.1	203.1	205.6	208.1	213.1	218.1	223.1	228.1	240.7
40°	188.0	190.5	193.0	195.6	198.1	200.6	205.6	208.1	213.1	215.6	225.6
42.5°	180.5	180.5	183.0	188.0	190.5	193.0	198.1	200.6	205.6	208.1	218.1
45°	175.5	178.0	180.5	183.0	183.0	185.5	190.5	195.6	198.1	203.1	213.1
47.5°	168.0	168.0	173.0	175.5	180.5	183.0	188.0	190.5	195.6	198.1	208.1
50°	163.0	165.5	170.5	173.0	178.0	180.5	188.0	193.0	200.6	205.6	210.6
52.5°	157.9	160.5	165.5	168.0	173.0	175.5	185.5	195.6	203.1	213.1	213.1
55°	152.9	152.9	157.9	165.5	170.5	175.5	180.5	188.0	193.0	198.1	198.1
57.5°	145.4	147.9	152.9	160.5	165.5	170.5	175.5	180.5	183.0	188.0	185.5
60°	140.4	140.4	147.9	155.4	163.0	170.5	170.5	170.5	168.0	168.0	168.0
62.5°	132.9	135.4	145.4	157.9	168.0	178.0	170.5	163.0	155.4	147.9	150.4
65°	127.9	130.4	135.4	142.9	147.9	152.9	147.9	145.4	140.4	135.4	137.9
67.5°	117.8	120.3	122.8	122.8	125.4	125.4	125.4	125.4	125.4	125.4	127.9
70°	110.3	110.3	110.3	112.8	112.8	112.8	112.8	112.8	112.8	112.8	115.3
72.5°	100.3	100.3	100.3	100.3	100.3	100.3	100.3	100.3	100.3	100.3	102.8
75°	87.7	87.7	87.7	87.7	87.7	87.7	87.7	87.7	87.7	87.7	90.3
77.5°	77.7	77.7	77.7	77.7	77.7	77.7	77.7	77.7	75.2	75.2	77.7
80°	65.2	65.2	65.2	65.2	62.7	62.7	62.7	62.7	62.7	62.7	65.2
82.5°	52.6	52.6	52.6	52.6	50.1	50.1	50.1	50.1	47.6	47.6	50.1
85°	47.6	50.1	50.1	52.6	52.6	52.6	50.1	47.6	45.1	42.6	42.6
87.5°	20.1	20.1	20.1	20.1	17.5	17.5	17.5	17.5	17.5	17.5	17.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1737.4	1742.5	1747.5	1755.0	1765.0	1772.5	1780.1	1795.1	1812.7	1827.7	1842.7
5°	1559.4	1572.0	1584.5	1599.6	1614.6	1627.1	1642.2	1672.3	1702.3	1729.9	1760.0
7.5°	1278.6	1296.2	1311.2	1336.3	1358.9	1383.9	1406.5	1444.1	1479.2	1516.8	1551.9
10°	1045.5	1065.5	1085.6	1118.2	1153.3	1185.9	1218.5	1248.6	1281.1	1311.2	1341.3
12.5°	945.2	967.8	992.8	1012.9	1035.4	1055.5	1075.6	1110.7	1145.8	1180.9	1216.0
15°	862.5	887.5	912.6	937.7	960.2	985.3	1007.9	1038.0	1070.5	1100.6	1130.7
17.5°	767.2	792.3	819.8	847.4	875.0	902.6	930.1	972.8	1015.4	1055.5	1098.1
20°	646.8	681.9	714.5	752.1	789.7	827.4	865.0	910.1	955.2	997.8	1043.0
22.5°	526.5	559.1	591.7	636.8	681.9	724.6	769.7	829.9	887.5	947.7	1005.4
25°	438.7	468.8	498.9	549.1	596.7	646.8	694.5	767.2	837.4	910.1	980.3
27.5°	378.6	406.2	433.7	486.4	539.0	589.2	641.8	722.1	799.8	880.0	957.7
30°	351.0	368.5	386.1	436.2	486.4	534.0	584.2	661.9	739.6	817.3	895.0
32.5°	305.9	320.9	336.0	381.1	426.2	468.8	514.0	594.2	671.9	752.1	829.9
35°	270.8	283.3	295.8	338.5	378.6	421.2	461.3	541.5	621.8	702.0	782.2
37.5°	250.7	263.2	273.3	310.9	351.0	388.6	426.2	506.4	584.2	664.4	742.1
40°	235.7	243.2	253.2	290.8	325.9	363.5	398.6	471.3	546.6	619.3	692.0
42.5°	225.6	235.7	243.2	275.8	310.9	343.5	376.1	446.3	516.5	584.2	654.4
45°	223.1	233.2	243.2	270.8	298.3	323.4	351.0	418.7	486.4	554.1	621.8
47.5°	218.1	225.6	235.7	258.2	278.3	300.9	320.9	388.6	456.3	521.5	589.2
50°	215.6	218.1	223.1	243.2	263.2	283.3	303.4	371.1	438.7	506.4	574.1
52.5°	213.1	213.1	213.1	230.7	248.2	263.2	280.8	348.5	418.7	486.4	554.1
55°	198.1	195.6	195.6	213.1	228.1	245.7	260.7	328.4	396.1	461.3	529.0
57.5°	183.0	180.5	178.0	193.0	208.1	223.1	238.2	305.9	376.1	443.8	511.5
60°	168.0	165.5	165.5	180.5	193.0	208.1	220.6	290.8	358.5	428.7	496.4
62.5°	150.4	152.9	152.9	165.5	180.5	193.0	205.6	275.8	348.5	418.7	488.9
65°	137.9	140.4	140.4	155.4	170.5	185.5	200.6	268.3	338.5	406.2	473.8
67.5°	127.9	130.4	130.4	147.9	163.0	180.5	195.6	255.7	318.4	378.6	438.7
70°	117.8	117.8	120.3	137.9	155.4	173.0	190.5	243.2	295.8	346.0	398.6
72.5°	105.3	107.8	110.3	127.9	142.9	160.5	175.5	223.1	270.8	318.4	366.0
75°	92.8	95.3	97.8	112.8	127.9	142.9	157.9	203.1	245.7	290.8	333.4
77.5°	82.7	85.2	87.7	100.3	112.8	125.4	137.9	170.5	205.6	238.2	270.8
80°	67.7	67.7	70.2	80.2	90.3	97.8	107.8	130.4	152.9	173.0	195.6
82.5°	50.1	52.6	52.6	60.2	65.2	72.7	77.7	90.3	100.3	112.8	122.8
85°	42.6	40.1	40.1	45.1	47.6	52.6	55.2	62.7	67.7	75.2	80.2
87.5°	17.5	15.0	15.0	17.5	22.6	25.1	27.6	27.6	30.1	30.1	30.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671818

CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1850.3	1855.3	1862.8	1867.8	1880.4	1890.4	1902.9	1912.9	1920.5	1933.0	1928.0
5°	1782.6	1805.1	1827.7	1850.3	1867.8	1885.4	1900.4	1918.0	1938.0	1975.6	1985.7
7.5°	1582.0	1612.1	1639.7	1669.8	1704.9	1740.0	1775.1	1810.2	1842.7	1890.4	1920.5
10°	1383.9	1426.6	1466.7	1509.3	1541.9	1574.5	1604.6	1637.2	1682.3	1729.9	1785.1
12.5°	1258.6	1301.2	1343.8	1386.4	1434.1	1479.2	1526.8	1572.0	1614.6	1652.2	1714.9
15°	1175.8	1223.5	1268.6	1313.7	1371.4	1426.6	1484.2	1539.4	1602.1	1652.2	1694.8
17.5°	1155.8	1213.5	1268.6	1326.3	1386.4	1446.6	1506.8	1567.0	1629.6	1704.9	1760.0
20°	1120.7	1198.4	1276.1	1353.9	1431.6	1506.8	1584.5	1659.7	1742.5	1832.7	1857.8
22.5°	1100.6	1193.4	1288.7	1381.4	1486.7	1594.5	1699.8	1805.1	1892.9	1960.6	2035.8
25°	1098.1	1213.5	1331.3	1446.6	1579.5	1709.9	1842.7	1973.1	2085.9	2153.6	2213.8
27.5°	1095.6	1236.0	1373.9	1511.8	1674.8	1835.2	1998.2	2158.6	2263.9	2361.7	2411.9
30°	1065.5	1233.5	1404.0	1572.0	1755.0	1938.0	2121.0	2304.1	2411.9	2479.6	2504.6
32.5°	1027.9	1226.0	1424.1	1622.1	1830.2	2038.3	2243.9	2452.0	2537.2	2594.9	2574.8
35°	997.8	1216.0	1431.6	1647.2	1867.8	2091.0	2311.6	2532.2	2655.1	2735.3	2702.7
37.5°	970.3	1198.4	1426.6	1654.7	1912.9	2171.2	2429.4	2687.7	2805.5	2890.7	2853.1
40°	937.7	1180.9	1426.6	1669.8	1965.6	2258.9	2554.8	2848.1	3001.0	3073.7	3016.1
42.5°	910.1	1163.3	1419.0	1672.3	1988.2	2304.1	2620.0	2935.9	3106.3	3209.1	3136.4
45°	875.0	1128.2	1378.9	1632.1	1980.6	2329.1	2675.1	3023.6	3221.7	3301.9	3201.6
47.5°	837.4	1088.1	1336.3	1584.5	1955.6	2326.6	2697.7	3068.7	3251.8	3347.0	3254.3
50°	824.8	1075.6	1323.8	1574.5	1975.6	2379.3	2780.4	3181.6	3314.4	3392.2	3269.3
52.5°	822.3	1088.1	1356.4	1622.1	2025.8	2426.9	2830.6	3231.7	3339.5	3422.2	3311.9
55°	814.8	1103.1	1389.0	1674.8	2096.0	2519.7	2940.9	3362.1	3469.9	3530.0	3447.3
57.5°	822.3	1133.2	1441.6	1752.5	2186.2	2620.0	3053.7	3487.4	3617.8	3660.4	3642.9
60°	827.4	1158.3	1486.7	1817.7	2241.4	2665.1	3088.8	3512.5	3647.9	3753.2	3773.2
62.5°	814.8	1140.7	1464.2	1790.1	2173.7	2557.3	2940.9	3324.5	3547.6	3703.0	3793.3
65°	777.2	1078.1	1381.4	1682.3	2035.8	2391.8	2745.3	3098.8	3334.5	3565.1	3637.9
67.5°	694.5	950.2	1205.9	1461.7	1770.0	2078.4	2384.3	2692.7	2988.5	3211.6	3311.9
70°	601.7	802.3	1005.4	1205.9	1486.7	1767.5	2048.3	2329.1	2589.9	2835.6	2930.8
72.5°	524.0	679.4	837.4	992.8	1193.4	1391.5	1592.0	1790.1	2098.5	2344.2	2436.9
75°	446.3	559.1	669.4	782.2	920.1	1058.0	1193.4	1331.3	1549.4	1770.0	1862.8
77.5°	343.5	418.7	491.4	564.1	659.4	752.1	847.4	940.2	1093.1	1258.6	1306.2
80°	238.2	280.8	320.9	363.5	438.7	514.0	589.2	664.4	764.7	857.4	930.1
82.5°	147.9	175.5	200.6	225.6	285.8	346.0	403.6	463.8	503.9	508.9	581.7
85°	95.3	112.8	127.9	142.9	178.0	215.6	250.7	285.8	255.7	238.2	283.3
87.5°	37.6	47.6	55.2	62.7	60.2	57.7	55.2	52.6	45.1	40.1	50.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818

CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1933.0	1940.5	1948.0	1953.1	1960.6	1963.1	1965.6	1965.6	1968.1	1970.6	1975.6
5°	2025.8	2040.8	2055.9	2068.4	2083.4	2096.0	2106.0	2118.5	2128.6	2128.6	2126.1
7.5°	1948.0	1985.7	2023.3	2060.9	2098.5	2126.1	2151.1	2178.7	2203.8	2208.8	2213.8
10°	1845.3	1885.4	1923.0	1963.1	2000.7	2043.3	2083.4	2123.5	2166.2	2173.7	2183.7
12.5°	1750.0	1797.6	1845.3	1890.4	1938.0	1968.1	1998.2	2025.8	2055.9	2075.9	2096.0
15°	1747.5	1787.6	1827.7	1865.3	1905.4	1923.0	1940.5	1955.6	1973.1	1973.1	1975.6
17.5°	1805.1	1830.2	1855.3	1877.8	1902.9	1905.4	1910.4	1912.9	1915.5	1907.9	1900.4
20°	1918.0	1928.0	1938.0	1948.0	1958.1	1940.5	1925.5	1907.9	1890.4	1870.3	1852.8
22.5°	2083.4	2060.9	2038.3	2015.7	1993.2	1963.1	1930.5	1900.4	1867.8	1842.7	1817.7
25°	2238.9	2211.3	2183.7	2156.1	2128.6	2063.4	1998.2	1930.5	1865.3	1837.7	1810.2
27.5°	2447.0	2404.3	2361.7	2319.1	2276.5	2188.7	2101.0	2013.2	1925.5	1877.8	1832.7
30°	2497.1	2449.5	2401.8	2351.7	2304.1	2218.8	2136.1	2050.8	1965.6	1910.4	1857.8
32.5°	2569.8	2514.7	2459.5	2404.3	2349.2	2266.5	2183.7	2098.5	2015.7	1965.6	1912.9
35°	2690.2	2627.5	2564.8	2499.6	2436.9	2351.7	2269.0	2183.7	2098.5	2040.8	1985.7
37.5°	2793.0	2720.2	2647.5	2574.8	2502.1	2426.9	2349.2	2274.0	2196.3	2138.6	2083.4
40°	2908.3	2828.1	2747.8	2670.1	2589.9	2519.7	2449.5	2376.8	2306.6	2261.4	2216.3
42.5°	3008.6	2910.8	2815.5	2720.2	2622.5	2574.8	2529.7	2482.1	2434.4	2411.9	2386.8
45°	3078.8	2988.5	2895.7	2805.5	2715.2	2680.1	2645.0	2609.9	2574.8	2597.4	2620.0
47.5°	3108.8	3036.1	2965.9	2895.7	2823.0	2835.6	2848.1	2858.1	2870.7	2900.8	2933.3
50°	3136.4	3096.3	3053.7	3013.6	2971.0	3018.6	3063.7	3111.4	3159.0	3221.7	3284.3
52.5°	3191.6	3169.0	3149.0	3126.4	3103.8	3186.6	3269.3	3352.0	3434.8	3505.0	3575.2
55°	3357.1	3339.5	3322.0	3301.9	3284.3	3402.2	3517.5	3635.3	3753.2	3825.9	3898.6
57.5°	3585.2	3575.2	3562.6	3552.6	3540.1	3655.4	3768.2	3881.0	3996.4	4066.6	4139.3
60°	3758.2	3760.7	3760.7	3763.2	3763.2	3851.0	3938.7	4029.0	4116.7	4176.9	4239.6
62.5°	3851.0	3845.9	3840.9	3835.9	3830.9	3903.6	3976.3	4049.0	4121.7	4166.9	4212.0
65°	3750.7	3778.3	3805.8	3833.4	3861.0	3871.0	3878.5	3888.6	3896.1	3923.7	3951.2
67.5°	3414.7	3469.9	3522.5	3577.7	3630.3	3592.7	3557.6	3520.0	3482.4	3489.9	3494.9
70°	3041.2	3103.8	3169.0	3231.7	3294.4	3206.6	3118.9	3028.6	2940.9	2910.8	2880.7
72.5°	2564.8	2620.0	2677.6	2732.8	2787.9	2680.1	2574.8	2467.0	2359.2	2306.6	2253.9
75°	1960.6	2025.8	2093.5	2158.6	2223.8	2103.5	1980.6	1860.3	1737.4	1702.3	1669.8
77.5°	1429.1	1506.8	1584.5	1662.2	1740.0	1632.1	1524.3	1414.0	1306.2	1286.2	1266.1
80°	1040.5	1100.6	1158.3	1218.5	1276.1	1213.5	1150.8	1088.1	1025.4	1022.9	1020.4
82.5°	702.0	754.6	804.8	857.4	907.6	882.5	859.9	834.9	809.8	834.9	862.5
85°	361.0	433.7	508.9	581.7	654.4	646.8	641.8	634.3	626.8	659.4	689.5
87.5°	72.7	135.4	198.1	258.2	320.9	305.9	290.8	273.3	258.2	268.3	275.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818

CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1978.1	1980.6	1980.6	1980.6	1980.6	1980.6	1975.6	1973.1	1968.1	1963.1	1955.6
5°	2126.1	2123.5	2113.5	2103.5	2091.0	2080.9	2073.4	2063.4	2055.9	2045.8	2030.8
7.5°	2218.8	2223.8	2206.3	2191.2	2173.7	2156.1	2138.6	2121.0	2103.5	2085.9	2050.8
10°	2191.2	2198.8	2188.7	2178.7	2166.2	2156.1	2136.1	2113.5	2093.5	2070.9	2028.3
12.5°	2113.5	2133.6	2128.6	2123.5	2118.5	2113.5	2101.0	2085.9	2073.4	2058.4	2010.7
15°	1975.6	1975.6	1978.1	1980.6	1980.6	1983.1	1985.7	1988.2	1990.7	1993.2	1965.6
17.5°	1892.9	1885.4	1885.4	1885.4	1885.4	1885.4	1895.4	1907.9	1918.0	1928.0	1920.5
20°	1832.7	1815.2	1812.7	1812.7	1810.2	1807.6	1825.2	1845.3	1862.8	1880.4	1890.4
22.5°	1792.6	1767.5	1765.0	1762.5	1760.0	1757.5	1780.1	1802.6	1825.2	1847.8	1882.9
25°	1782.6	1755.0	1757.5	1760.0	1760.0	1762.5	1780.1	1797.6	1815.2	1832.7	1892.9
27.5°	1785.1	1740.0	1742.5	1745.0	1745.0	1747.5	1775.1	1800.1	1827.7	1852.8	1928.0
30°	1802.6	1750.0	1745.0	1740.0	1734.9	1729.9	1767.5	1805.1	1842.7	1880.4	1938.0
32.5°	1862.8	1812.7	1800.1	1787.6	1775.1	1762.5	1807.6	1850.3	1895.4	1938.0	1985.7
35°	1928.0	1872.8	1867.8	1862.8	1855.3	1850.3	1890.4	1933.0	1973.1	2013.2	2055.9
37.5°	2025.8	1970.6	1965.6	1958.1	1953.1	1945.5	1990.7	2033.3	2078.4	2121.0	2158.6
40°	2171.2	2126.1	2123.5	2123.5	2121.0	2118.5	2153.6	2191.2	2226.3	2261.4	2286.5
42.5°	2364.2	2341.7	2349.2	2359.2	2366.7	2374.3	2401.8	2431.9	2459.5	2487.1	2479.6
45°	2642.5	2665.1	2667.6	2670.1	2672.6	2675.1	2682.6	2692.7	2700.2	2707.7	2677.6
47.5°	2963.4	2993.5	3008.6	3023.6	3036.1	3051.2	3041.2	3028.6	3018.6	3006.1	2930.8
50°	3344.5	3407.2	3404.7	3402.2	3397.2	3394.7	3374.6	3354.5	3332.0	3311.9	3201.6
52.5°	3645.4	3715.6	3728.1	3740.6	3753.2	3765.7	3728.1	3690.5	3650.4	3612.8	3474.9
55°	3968.8	4041.5	4044.0	4046.5	4046.5	4049.0	3996.4	3943.7	3888.6	3835.9	3693.0
57.5°	4209.5	4279.7	4272.2	4267.1	4259.6	4252.1	4189.4	4126.7	4064.1	4001.4	3858.5
60°	4299.7	4359.9	4344.9	4329.8	4312.3	4297.2	4249.6	4202.0	4151.8	4104.2	3966.3
62.5°	4257.1	4302.2	4279.7	4259.6	4237.1	4214.5	4154.3	4091.6	4031.5	3968.8	3868.5
65°	3976.3	4003.9	3973.8	3946.2	3918.7	3888.6	3838.4	3788.3	3735.6	3685.5	3617.8
67.5°	3502.5	3507.5	3505.0	3502.5	3500.0	3497.5	3424.7	3352.0	3276.8	3204.1	3199.1
70°	2853.1	2823.0	2828.1	2835.6	2840.6	2845.6	2790.4	2737.8	2682.6	2627.5	2652.6
72.5°	2201.3	2148.6	2161.2	2176.2	2188.7	2201.3	2156.1	2113.5	2068.4	2023.3	2058.4
75°	1634.7	1602.1	1614.6	1629.6	1642.2	1654.7	1637.2	1619.6	1599.6	1582.0	1614.6
77.5°	1246.0	1226.0	1228.5	1228.5	1231.0	1231.0	1233.5	1238.5	1241.0	1243.5	1278.6
80°	1015.4	1012.9	1010.4	1007.9	1002.9	1000.3	1025.4	1050.5	1075.6	1100.6	1118.2
82.5°	887.5	912.6	897.6	885.0	870.0	854.9	877.5	900.1	922.6	945.2	937.7
85°	722.1	752.1	724.6	697.0	666.9	639.3	659.4	676.9	697.0	714.5	704.5
87.5°	285.8	293.3	248.2	205.6	160.5	115.3	183.0	248.2	315.9	381.1	391.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818

CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1	1805.1
2.5°	1948.0	1938.0	1930.5	1928.0	1923.0	1920.5	1915.5	1910.4	1902.9	1897.9	1890.4
5°	2013.2	1998.2	1980.6	1955.6	1933.0	1907.9	1882.9	1860.3	1837.7	1812.7	1790.1
7.5°	2015.7	1980.6	1945.5	1912.9	1877.8	1845.3	1810.2	1780.1	1747.5	1714.9	1684.8
10°	1988.2	1945.5	1902.9	1860.3	1820.2	1777.6	1734.9	1699.8	1662.2	1624.6	1589.5
12.5°	1965.6	1918.0	1870.3	1820.2	1772.5	1722.4	1672.3	1637.2	1602.1	1567.0	1531.9
15°	1938.0	1907.9	1880.4	1835.2	1790.1	1745.0	1699.8	1652.2	1607.1	1559.4	1511.8
17.5°	1915.5	1907.9	1900.4	1870.3	1840.2	1807.6	1777.6	1729.9	1682.3	1632.1	1584.5
20°	1902.9	1912.9	1923.0	1907.9	1892.9	1875.3	1860.3	1825.2	1790.1	1752.5	1717.4
22.5°	1918.0	1955.6	1990.7	1993.2	1998.2	2000.7	2003.2	1970.6	1938.0	1902.9	1870.3
25°	1953.1	2013.2	2073.4	2106.0	2138.6	2173.7	2206.3	2186.2	2166.2	2146.1	2126.1
27.5°	2000.7	2075.9	2151.1	2198.8	2243.9	2291.5	2339.2	2336.7	2334.1	2329.1	2326.6
30°	1993.2	2050.8	2108.5	2166.2	2223.8	2281.5	2339.2	2369.2	2396.8	2426.9	2457.0
32.5°	2035.8	2083.4	2133.6	2193.7	2253.9	2316.6	2376.8	2439.4	2499.6	2562.3	2625.0
35°	2101.0	2143.6	2188.7	2253.9	2321.6	2386.8	2454.5	2529.7	2607.4	2685.1	2760.4
37.5°	2198.8	2236.4	2276.5	2331.6	2389.3	2444.5	2502.1	2612.4	2722.8	2835.6	2945.9
40°	2311.6	2336.7	2361.7	2414.4	2467.0	2519.7	2572.3	2710.2	2848.1	2986.0	3123.9
42.5°	2474.5	2467.0	2459.5	2502.1	2547.3	2589.9	2635.0	2760.4	2885.7	3011.1	3136.4
45°	2647.5	2617.5	2587.4	2607.4	2630.0	2650.0	2672.6	2800.5	2928.3	3058.7	3186.6
47.5°	2855.6	2780.4	2705.2	2687.7	2670.1	2650.0	2632.5	2770.4	2908.3	3048.7	3186.6
50°	3091.3	2978.5	2868.2	2823.0	2775.4	2730.3	2682.6	2795.5	2910.8	3026.1	3138.9
52.5°	3337.0	3196.6	3058.7	2988.5	2918.3	2845.6	2775.4	2870.7	2968.4	3066.2	3161.5
55°	3547.6	3404.7	3259.3	3176.5	3093.8	3011.1	2928.3	3023.6	3118.9	3214.1	3309.4
57.5°	3715.6	3572.7	3429.8	3352.0	3271.8	3194.1	3113.9	3204.1	3296.9	3389.6	3479.9
60°	3830.9	3693.0	3555.1	3479.9	3404.7	3329.5	3254.3	3362.1	3469.9	3580.2	3688.0
62.5°	3770.7	3670.4	3570.2	3537.6	3505.0	3469.9	3437.3	3540.1	3640.4	3743.2	3845.9
65°	3550.1	3482.4	3414.7	3447.3	3482.4	3515.0	3550.1	3617.8	3685.5	3755.7	3823.4
67.5°	3191.6	3186.6	3179.0	3251.8	3324.5	3399.7	3472.4	3517.5	3560.1	3605.3	3650.4
70°	2677.6	2705.2	2730.3	2855.6	2981.0	3106.3	3231.7	3249.2	3266.8	3284.3	3301.9
72.5°	2096.0	2131.1	2168.7	2334.1	2497.1	2662.6	2828.1	2818.0	2808.0	2795.5	2785.4
75°	1649.7	1682.3	1717.4	1870.3	2023.3	2176.2	2329.1	2286.5	2246.4	2203.8	2161.2
77.5°	1316.2	1351.3	1389.0	1531.9	1674.8	1820.2	1963.1	1860.3	1757.5	1654.7	1551.9
80°	1133.2	1150.8	1165.8	1263.6	1358.9	1456.6	1554.4	1449.1	1341.3	1233.5	1128.2
82.5°	930.1	920.1	912.6	970.3	1027.9	1085.6	1143.3	1043.0	942.7	839.9	739.6
85°	694.5	684.4	674.4	704.5	734.6	767.2	797.3	681.9	566.6	448.8	333.4
87.5°	403.6	413.7	423.7	456.3	488.9	524.0	556.6	438.7	320.9	200.6	82.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671818  
 CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671818  
CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	1805.1	1805.1
2.5°	1875.3	1862.8
5°	1772.5	1755.0
7.5°	1659.7	1637.2
10°	1556.9	1526.8
12.5°	1491.7	1454.1
15°	1466.7	1421.5
17.5°	1541.9	1499.3
20°	1657.2	1599.6
22.5°	1797.6	1727.4
25°	2040.8	1955.6
27.5°	2238.9	2151.1
30°	2361.7	2266.5
32.5°	2497.1	2371.8
35°	2637.5	2517.2
37.5°	2808.0	2672.6
40°	2983.5	2843.1
42.5°	3043.7	2953.4
45°	3101.3	3016.1
47.5°	3113.9	3043.7
50°	3126.4	3116.4
52.5°	3161.5	3159.0
55°	3311.9	3314.4
57.5°	3497.5	3512.5
60°	3667.9	3650.4
62.5°	3755.7	3665.4
65°	3695.5	3570.2
67.5°	3515.0	3379.6
70°	3118.9	2935.9
72.5°	2625.0	2464.5
75°	2023.3	1887.9
77.5°	1439.1	1326.3
80°	1012.9	900.1
82.5°	649.3	559.1
85°	293.3	255.7
87.5°	82.7	80.2
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671818  
CATALOG NUMBER: CCP-SA-2B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)