

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671819

Luminaire Tested: **CCP-SA-2C-735-U-SLR**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P671819  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2C-735-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @615mA w/ SLR distribution lens  
Light Source: (32) 3500K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7400.5 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G3

Input Watts (W): 62.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 10.5 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671819  
CATALOG NUMBER: CCP-SA-2C-735-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1522.7   | 0.0    | 1522.7 |
|                    | % Fixture | 20.6     | 0.0    | 20.6   |
| <b>Street Side</b> | Lumens    | 5877.8   | 0.0    | 5877.8 |
|                    | % Fixture | 79.4     | 0.0    | 79.4   |
| <b>Total</b>       | Lumens    | 7400.5   | 0.0    | 7400.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 183.6  | 2.5       |
| 10°-20°   | 387.7  | 5.2       |
| 20°-30°   | 567.2  | 7.7       |
| 30°-40°   | 799.1  | 10.8      |
| 40°-50°   | 1098.1 | 14.8      |
| 50°-60°   | 1496.8 | 20.2      |
| 60°-70°   | 1638.2 | 22.1      |
| 70°-80°   | 946.1  | 12.8      |
| 80°-90°   | 283.6  | 3.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 7400.5 | 100.0     |
| 0°-180°   | 7400.5 | 100.0     |



REPORT NUMBER: P671819


CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 760.1  | 10.3      |                         |      |         |
| FM   | (30°-60°)   | 2700.7 | 36.5      |                         |      |         |
| FH   | (60°-80°)   | 2176.2 | 29.4      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 240.9  | 3.3       |                         |      | G3/500  |
| BL   | (0°-30°)    | 378.5  | 5.1       | B1/500                  |      |         |
| BM   | (30°-60°)   | 693.4  | 9.4       | B1/1000                 |      |         |
| BH   | (60°-80°)   | 408.1  | 5.5       | B1/500                  |      | G1/500  |
| BVH  | (80°-90°)   | 42.7   | 0.6       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G3**

Type IV Short





REPORT NUMBER: P671819

CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2438.8 | 2425.6 | 2415.8 | 2405.9 | 2392.8 | 2383.0 | 2369.8 | 2356.7 | 2340.3 | 2327.2 | 2310.7 |
| 5°     | 2297.6 | 2258.2 | 2218.8 | 2195.9 | 2169.6 | 2146.6 | 2120.4 | 2090.8 | 2061.3 | 2028.5 | 1998.9 |
| 7.5°   | 2143.4 | 2094.1 | 2044.9 | 2005.5 | 1962.8 | 1923.4 | 1880.8 | 1844.7 | 1808.6 | 1772.4 | 1736.3 |
| 10°    | 1998.9 | 1953.0 | 1907.0 | 1857.8 | 1805.3 | 1756.0 | 1703.5 | 1654.3 | 1605.1 | 1555.8 | 1506.6 |
| 12.5°  | 1903.7 | 1847.9 | 1795.4 | 1739.6 | 1687.1 | 1631.3 | 1575.5 | 1529.6 | 1483.6 | 1434.4 | 1388.4 |
| 15°    | 1861.1 | 1808.6 | 1759.3 | 1703.5 | 1647.7 | 1591.9 | 1536.1 | 1483.6 | 1434.4 | 1381.9 | 1329.3 |
| 17.5°  | 1962.8 | 1887.3 | 1811.8 | 1739.6 | 1667.4 | 1595.2 | 1523.0 | 1457.3 | 1391.7 | 1326.1 | 1260.4 |
| 20°    | 2094.1 | 1998.9 | 1907.0 | 1818.4 | 1726.5 | 1637.9 | 1546.0 | 1454.1 | 1362.2 | 1270.3 | 1178.4 |
| 22.5°  | 2261.5 | 2153.2 | 2048.2 | 1933.3 | 1815.1 | 1700.2 | 1582.1 | 1467.2 | 1352.3 | 1234.2 | 1119.3 |
| 25°    | 2560.2 | 2432.2 | 2304.2 | 2140.1 | 1972.7 | 1808.6 | 1641.2 | 1490.2 | 1342.5 | 1191.5 | 1040.5 |
| 27.5°  | 2816.2 | 2642.3 | 2471.6 | 2274.6 | 2077.7 | 1880.8 | 1683.8 | 1509.9 | 1339.2 | 1165.2 | 991.3  |
| 30°    | 2967.2 | 2796.5 | 2625.9 | 2386.2 | 2149.9 | 1910.3 | 1670.7 | 1477.0 | 1286.7 | 1093.0 | 899.4  |
| 32.5°  | 3105.1 | 2914.7 | 2724.3 | 2461.7 | 2195.9 | 1933.3 | 1667.4 | 1454.1 | 1244.0 | 1030.6 | 817.3  |
| 35°    | 3295.4 | 3085.4 | 2878.6 | 2573.3 | 2268.1 | 1962.8 | 1657.6 | 1437.7 | 1214.5 | 994.5  | 771.3  |
| 37.5°  | 3498.9 | 3239.6 | 2983.6 | 2645.5 | 2307.5 | 1969.4 | 1631.3 | 1414.7 | 1198.0 | 981.4  | 764.8  |
| 40°    | 3722.1 | 3407.0 | 3095.2 | 2721.0 | 2350.1 | 1976.0 | 1601.8 | 1385.1 | 1168.5 | 948.6  | 732.0  |
| 42.5°  | 3866.6 | 3525.2 | 3183.8 | 2780.1 | 2379.7 | 1976.0 | 1572.2 | 1358.9 | 1145.5 | 928.9  | 715.5  |
| 45°    | 3948.6 | 3617.1 | 3288.9 | 2852.3 | 2415.8 | 1979.2 | 1542.7 | 1332.6 | 1122.6 | 909.2  | 699.1  |
| 47.5°  | 3984.7 | 3676.2 | 3367.7 | 2908.1 | 2451.9 | 1992.4 | 1532.8 | 1319.5 | 1102.9 | 889.5  | 672.9  |
| 50°    | 4079.9 | 3807.5 | 3535.1 | 3042.7 | 2553.6 | 2061.3 | 1568.9 | 1339.2 | 1112.7 | 882.9  | 653.2  |
| 52.5°  | 4135.7 | 3902.7 | 3669.6 | 3164.2 | 2658.7 | 2153.2 | 1647.7 | 1391.7 | 1135.7 | 879.7  | 623.6  |
| 55°    | 4339.2 | 4116.0 | 3892.8 | 3354.5 | 2812.9 | 2274.6 | 1733.1 | 1450.8 | 1168.5 | 882.9  | 600.7  |
| 57.5°  | 4598.5 | 4362.2 | 4129.2 | 3548.2 | 2967.2 | 2386.2 | 1805.3 | 1503.3 | 1198.0 | 896.1  | 590.8  |
| 60°    | 4779.1 | 4549.3 | 4322.8 | 3705.7 | 3085.4 | 2468.3 | 1847.9 | 1532.8 | 1217.7 | 899.4  | 584.3  |
| 62.5°  | 4798.7 | 4503.3 | 4211.2 | 3610.5 | 3009.9 | 2405.9 | 1805.3 | 1500.0 | 1194.8 | 886.2  | 581.0  |
| 65°    | 4674.0 | 4329.4 | 3984.7 | 3410.3 | 2835.9 | 2261.5 | 1687.1 | 1408.1 | 1129.1 | 846.8  | 567.8  |
| 67.5°  | 4424.6 | 4020.8 | 3617.1 | 3091.9 | 2566.8 | 2041.6 | 1516.4 | 1276.8 | 1040.5 | 800.9  | 561.3  |
| 70°    | 3843.6 | 3489.1 | 3137.9 | 2681.7 | 2228.7 | 1772.4 | 1316.2 | 1119.3 | 925.6  | 728.7  | 531.7  |
| 72.5°  | 3226.5 | 2895.0 | 2566.8 | 2195.9 | 1828.2 | 1457.3 | 1086.4 | 938.7  | 791.0  | 640.1  | 492.3  |
| 75°    | 2471.6 | 2222.1 | 1976.0 | 1700.2 | 1424.5 | 1145.5 | 869.8  | 761.5  | 653.2  | 544.9  | 436.5  |
| 77.5°  | 1736.3 | 1601.8 | 1470.5 | 1263.7 | 1056.9 | 850.1  | 643.3  | 571.1  | 498.9  | 426.7  | 354.5  |
| 80°    | 1178.4 | 1102.9 | 1030.6 | 882.9  | 735.2  | 584.3  | 436.5  | 390.6  | 341.4  | 295.4  | 246.2  |
| 82.5°  | 732.0  | 728.7  | 722.1  | 620.4  | 518.6  | 416.9  | 315.1  | 275.7  | 239.6  | 200.2  | 160.8  |
| 85°    | 334.8  | 390.6  | 443.1  | 387.3  | 331.5  | 275.7  | 219.9  | 193.7  | 167.4  | 137.9  | 111.6  |
| 87.5°  | 105.0  | 128.0  | 147.7  | 141.1  | 131.3  | 124.7  | 114.9  | 98.5   | 82.1   | 65.6   | 49.2   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |





REPORT NUMBER: P671819

CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2297.6 | 2287.8 | 2274.6 | 2261.5 | 2245.1 | 2232.0 | 2215.6 | 2199.2 | 2195.9 | 2189.3 | 2186.0 |
| 5°     | 1979.2 | 1959.5 | 1936.6 | 1916.9 | 1897.2 | 1874.2 | 1854.5 | 1831.5 | 1815.1 | 1795.4 | 1779.0 |
| 7.5°   | 1700.2 | 1667.4 | 1631.3 | 1595.2 | 1562.4 | 1529.6 | 1493.5 | 1460.6 | 1444.2 | 1427.8 | 1411.4 |
| 10°    | 1477.0 | 1444.2 | 1414.7 | 1381.9 | 1358.9 | 1339.2 | 1316.2 | 1293.2 | 1273.5 | 1253.8 | 1234.2 |
| 12.5°  | 1365.4 | 1342.5 | 1319.5 | 1296.5 | 1270.3 | 1247.3 | 1221.0 | 1194.8 | 1171.8 | 1152.1 | 1129.1 |
| 15°    | 1296.5 | 1263.7 | 1227.6 | 1194.8 | 1158.7 | 1125.8 | 1089.7 | 1053.6 | 1027.4 | 1004.4 | 978.1  |
| 17.5°  | 1214.5 | 1165.2 | 1119.3 | 1070.0 | 1030.6 | 991.3  | 948.6  | 909.2  | 879.7  | 846.8  | 817.3  |
| 20°    | 1122.6 | 1066.8 | 1007.7 | 951.9  | 905.9  | 863.2  | 817.3  | 771.3  | 738.5  | 702.4  | 669.6  |
| 22.5°  | 1043.8 | 971.6  | 896.1  | 820.6  | 771.3  | 722.1  | 669.6  | 620.4  | 590.8  | 558.0  | 528.5  |
| 25°    | 958.4  | 879.7  | 797.6  | 715.5  | 666.3  | 613.8  | 564.6  | 512.0  | 489.1  | 469.4  | 446.4  |
| 27.5°  | 912.5  | 833.7  | 751.7  | 672.9  | 626.9  | 577.7  | 531.7  | 482.5  | 466.1  | 446.4  | 430.0  |
| 30°    | 820.6  | 745.1  | 666.3  | 587.5  | 554.7  | 525.2  | 492.3  | 459.5  | 453.0  | 449.7  | 443.1  |
| 32.5°  | 738.5  | 659.7  | 581.0  | 502.2  | 472.7  | 443.1  | 413.6  | 384.0  | 380.7  | 374.2  | 370.9  |
| 35°    | 695.9  | 620.4  | 541.6  | 466.1  | 439.8  | 410.3  | 384.0  | 354.5  | 347.9  | 338.1  | 331.5  |
| 37.5°  | 686.0  | 607.2  | 525.2  | 446.4  | 420.1  | 393.9  | 364.3  | 338.1  | 331.5  | 324.9  | 318.4  |
| 40°    | 659.7  | 584.3  | 512.0  | 436.5  | 410.3  | 384.0  | 354.5  | 328.2  | 321.7  | 315.1  | 308.5  |
| 42.5°  | 640.1  | 567.8  | 492.3  | 416.9  | 393.9  | 370.9  | 344.6  | 321.7  | 315.1  | 308.5  | 298.7  |
| 45°    | 623.6  | 548.1  | 469.4  | 393.9  | 377.5  | 361.1  | 341.4  | 324.9  | 318.4  | 308.5  | 302.0  |
| 47.5°  | 597.4  | 525.2  | 449.7  | 374.2  | 357.8  | 344.6  | 328.2  | 311.8  | 305.3  | 298.7  | 292.1  |
| 50°    | 577.7  | 502.2  | 426.7  | 351.2  | 338.1  | 324.9  | 311.8  | 298.7  | 298.7  | 302.0  | 302.0  |
| 52.5°  | 551.4  | 479.2  | 407.0  | 334.8  | 321.7  | 308.5  | 295.4  | 282.3  | 285.6  | 288.8  | 292.1  |
| 55°    | 528.5  | 459.5  | 387.3  | 315.1  | 302.0  | 288.8  | 272.4  | 259.3  | 262.6  | 265.9  | 269.1  |
| 57.5°  | 518.6  | 446.4  | 374.2  | 302.0  | 288.8  | 272.4  | 259.3  | 242.9  | 242.9  | 242.9  | 242.9  |
| 60°    | 512.0  | 436.5  | 364.3  | 288.8  | 272.4  | 259.3  | 242.9  | 226.5  | 223.2  | 223.2  | 219.9  |
| 62.5°  | 508.8  | 433.3  | 361.1  | 285.6  | 265.9  | 249.5  | 229.8  | 210.1  | 206.8  | 203.5  | 200.2  |
| 65°    | 495.6  | 426.7  | 354.5  | 282.3  | 259.3  | 239.6  | 216.6  | 193.7  | 190.4  | 190.4  | 187.1  |
| 67.5°  | 492.3  | 420.1  | 351.2  | 279.0  | 256.0  | 229.8  | 206.8  | 180.5  | 177.2  | 174.0  | 170.7  |
| 70°    | 466.1  | 403.7  | 338.1  | 272.4  | 246.2  | 223.2  | 196.9  | 170.7  | 167.4  | 160.8  | 157.6  |
| 72.5°  | 433.3  | 377.5  | 318.4  | 259.3  | 233.0  | 206.8  | 180.5  | 154.3  | 151.0  | 147.7  | 141.1  |
| 75°    | 384.0  | 331.5  | 279.0  | 226.5  | 203.5  | 183.8  | 160.8  | 137.9  | 134.6  | 131.3  | 124.7  |
| 77.5°  | 315.1  | 272.4  | 233.0  | 190.4  | 174.0  | 157.6  | 141.1  | 124.7  | 121.4  | 118.2  | 111.6  |
| 80°    | 223.2  | 196.9  | 174.0  | 147.7  | 137.9  | 124.7  | 114.9  | 101.8  | 101.8  | 98.5   | 98.5   |
| 82.5°  | 147.7  | 134.6  | 121.4  | 108.3  | 101.8  | 95.2   | 88.6   | 82.1   | 82.1   | 78.8   | 78.8   |
| 85°    | 105.0  | 98.5   | 88.6   | 82.1   | 78.8   | 72.2   | 68.9   | 62.4   | 62.4   | 62.4   | 62.4   |
| 87.5°  | 49.2   | 49.2   | 46.0   | 46.0   | 42.7   | 42.7   | 39.4   | 36.1   | 36.1   | 36.1   | 36.1   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55°    | 57.5°  | 60°    | 62.5°  | 65°    | 67.5°  | 70°    | 72.5°  | 75°    | 77.5°  | 80°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2179.5 | 2169.6 | 2159.8 | 2146.6 | 2136.8 | 2123.7 | 2107.2 | 2094.1 | 2077.7 | 2077.7 | 2074.4 |
| 5°     | 1759.3 | 1749.5 | 1739.6 | 1726.5 | 1716.7 | 1703.5 | 1693.7 | 1680.5 | 1667.4 | 1667.4 | 1664.1 |
| 7.5°   | 1395.0 | 1375.3 | 1355.6 | 1332.6 | 1312.9 | 1299.8 | 1286.7 | 1270.3 | 1257.1 | 1247.3 | 1237.4 |
| 10°    | 1214.5 | 1194.8 | 1171.8 | 1152.1 | 1129.1 | 1112.7 | 1096.3 | 1076.6 | 1060.2 | 1047.1 | 1033.9 |
| 12.5°  | 1106.1 | 1083.2 | 1060.2 | 1037.2 | 1014.2 | 991.3  | 971.6  | 948.6  | 925.6  | 909.2  | 892.8  |
| 15°    | 951.9  | 928.9  | 905.9  | 882.9  | 860.0  | 833.7  | 807.4  | 777.9  | 751.7  | 738.5  | 728.7  |
| 17.5°  | 784.5  | 761.5  | 735.2  | 712.3  | 686.0  | 666.3  | 646.6  | 626.9  | 607.2  | 594.1  | 584.3  |
| 20°    | 633.5  | 607.2  | 581.0  | 554.7  | 528.5  | 515.3  | 502.2  | 489.1  | 475.9  | 466.1  | 459.5  |
| 22.5°  | 495.6  | 479.2  | 466.1  | 449.7  | 433.3  | 423.4  | 416.9  | 407.0  | 397.2  | 397.2  | 397.2  |
| 25°    | 423.4  | 413.6  | 407.0  | 397.2  | 387.3  | 384.0  | 380.7  | 374.2  | 370.9  | 367.6  | 367.6  |
| 27.5°  | 410.3  | 400.4  | 390.6  | 380.7  | 370.9  | 367.6  | 364.3  | 357.8  | 354.5  | 354.5  | 354.5  |
| 30°    | 436.5  | 433.3  | 430.0  | 426.7  | 423.4  | 416.9  | 407.0  | 400.4  | 390.6  | 384.0  | 377.5  |
| 32.5°  | 364.3  | 361.1  | 361.1  | 357.8  | 354.5  | 361.1  | 364.3  | 370.9  | 374.2  | 377.5  | 380.7  |
| 35°    | 321.7  | 315.1  | 308.5  | 302.0  | 295.4  | 292.1  | 288.8  | 285.6  | 282.3  | 282.3  | 279.0  |
| 37.5°  | 311.8  | 305.3  | 298.7  | 292.1  | 285.6  | 282.3  | 279.0  | 275.7  | 272.4  | 272.4  | 269.1  |
| 40°    | 302.0  | 295.4  | 292.1  | 285.6  | 279.0  | 275.7  | 272.4  | 265.9  | 262.6  | 259.3  | 259.3  |
| 42.5°  | 292.1  | 288.8  | 282.3  | 279.0  | 272.4  | 269.1  | 265.9  | 259.3  | 256.0  | 252.7  | 249.5  |
| 45°    | 292.1  | 285.6  | 279.0  | 272.4  | 265.9  | 262.6  | 256.0  | 252.7  | 246.2  | 246.2  | 242.9  |
| 47.5°  | 285.6  | 279.0  | 272.4  | 265.9  | 259.3  | 256.0  | 249.5  | 246.2  | 239.6  | 236.3  | 233.0  |
| 50°    | 302.0  | 292.1  | 279.0  | 269.1  | 256.0  | 252.7  | 246.2  | 242.9  | 236.3  | 233.0  | 229.8  |
| 52.5°  | 295.4  | 285.6  | 272.4  | 262.6  | 249.5  | 242.9  | 239.6  | 233.0  | 226.5  | 223.2  | 219.9  |
| 55°    | 272.4  | 262.6  | 256.0  | 246.2  | 236.3  | 229.8  | 223.2  | 216.6  | 210.1  | 206.8  | 206.8  |
| 57.5°  | 242.9  | 239.6  | 236.3  | 233.0  | 229.8  | 223.2  | 216.6  | 206.8  | 200.2  | 196.9  | 193.7  |
| 60°    | 216.6  | 219.9  | 223.2  | 226.5  | 229.8  | 219.9  | 210.1  | 200.2  | 190.4  | 187.1  | 183.8  |
| 62.5°  | 196.9  | 203.5  | 210.1  | 213.4  | 219.9  | 210.1  | 200.2  | 190.4  | 180.5  | 177.2  | 174.0  |
| 65°    | 183.8  | 187.1  | 187.1  | 190.4  | 190.4  | 183.8  | 180.5  | 174.0  | 167.4  | 164.1  | 164.1  |
| 67.5°  | 167.4  | 167.4  | 167.4  | 164.1  | 164.1  | 160.8  | 160.8  | 157.6  | 154.3  | 151.0  | 151.0  |
| 70°    | 151.0  | 151.0  | 151.0  | 147.7  | 147.7  | 144.4  | 144.4  | 141.1  | 137.9  | 137.9  | 134.6  |
| 72.5°  | 137.9  | 137.9  | 134.6  | 134.6  | 131.3  | 131.3  | 131.3  | 128.0  | 128.0  | 124.7  | 124.7  |
| 75°    | 121.4  | 121.4  | 118.2  | 118.2  | 114.9  | 114.9  | 114.9  | 111.6  | 111.6  | 111.6  | 108.3  |
| 77.5°  | 108.3  | 108.3  | 105.0  | 105.0  | 101.8  | 101.8  | 101.8  | 98.5   | 98.5   | 95.2   | 95.2   |
| 80°    | 95.2   | 95.2   | 91.9   | 91.9   | 88.6   | 88.6   | 85.3   | 85.3   | 82.1   | 82.1   | 78.8   |
| 82.5°  | 75.5   | 75.5   | 75.5   | 75.5   | 75.5   | 72.2   | 72.2   | 68.9   | 65.6   | 65.6   | 62.4   |
| 85°    | 62.4   | 62.4   | 62.4   | 59.1   | 59.1   | 59.1   | 55.8   | 55.8   | 52.5   | 49.2   | 49.2   |
| 87.5°  | 36.1   | 36.1   | 36.1   | 32.8   | 32.8   | 32.8   | 32.8   | 32.8   | 32.8   | 32.8   | 29.5   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P671819

CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5°  | 85°    | 87.5°  | 90°    | 92.5°  | 95°    | 97.5°  | 100°   | 102.5° | 105°   | 107.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2074.4 | 2071.1 | 2058.0 | 2044.9 | 2058.0 | 2071.1 | 2071.1 | 2071.1 | 2067.9 | 2067.9 | 2067.9 |
| 5°     | 1664.1 | 1660.9 | 1654.3 | 1647.7 | 1647.7 | 1644.4 | 1651.0 | 1657.6 | 1664.1 | 1670.7 | 1677.3 |
| 7.5°   | 1224.3 | 1214.5 | 1204.6 | 1194.8 | 1201.3 | 1204.6 | 1214.5 | 1221.0 | 1230.9 | 1237.4 | 1253.8 |
| 10°    | 1020.8 | 1007.7 | 997.8  | 988.0  | 981.4  | 974.8  | 968.3  | 965.0  | 958.4  | 951.9  | 958.4  |
| 12.5°  | 873.1  | 856.7  | 840.3  | 820.6  | 817.3  | 814.0  | 807.4  | 800.9  | 794.3  | 787.8  | 784.5  |
| 15°    | 715.5  | 702.4  | 695.9  | 686.0  | 672.9  | 659.7  | 653.2  | 649.9  | 643.3  | 636.8  | 633.5  |
| 17.5°  | 571.1  | 558.0  | 548.1  | 538.3  | 535.0  | 528.5  | 528.5  | 528.5  | 528.5  | 528.5  | 528.5  |
| 20°    | 449.7  | 439.8  | 439.8  | 436.5  | 436.5  | 433.3  | 436.5  | 439.8  | 439.8  | 443.1  | 446.4  |
| 22.5°  | 393.9  | 393.9  | 390.6  | 387.3  | 390.6  | 390.6  | 393.9  | 397.2  | 400.4  | 403.7  | 407.0  |
| 25°    | 364.3  | 361.1  | 364.3  | 367.6  | 367.6  | 367.6  | 370.9  | 370.9  | 374.2  | 374.2  | 374.2  |
| 27.5°  | 351.2  | 351.2  | 354.5  | 354.5  | 357.8  | 357.8  | 357.8  | 354.5  | 354.5  | 351.2  | 351.2  |
| 30°    | 370.9  | 364.3  | 364.3  | 364.3  | 361.1  | 357.8  | 354.5  | 354.5  | 351.2  | 347.9  | 344.6  |
| 32.5°  | 384.0  | 387.3  | 384.0  | 377.5  | 374.2  | 367.6  | 364.3  | 357.8  | 354.5  | 347.9  | 341.4  |
| 35°    | 279.0  | 275.7  | 282.3  | 285.6  | 288.8  | 292.1  | 295.4  | 298.7  | 298.7  | 302.0  | 302.0  |
| 37.5°  | 269.1  | 265.9  | 265.9  | 262.6  | 262.6  | 262.6  | 262.6  | 262.6  | 259.3  | 259.3  | 262.6  |
| 40°    | 256.0  | 252.7  | 252.7  | 249.5  | 249.5  | 246.2  | 246.2  | 246.2  | 246.2  | 246.2  | 246.2  |
| 42.5°  | 246.2  | 242.9  | 242.9  | 242.9  | 242.9  | 239.6  | 239.6  | 236.3  | 236.3  | 233.0  | 233.0  |
| 45°    | 242.9  | 239.6  | 236.3  | 233.0  | 233.0  | 229.8  | 229.8  | 229.8  | 226.5  | 226.5  | 226.5  |
| 47.5°  | 229.8  | 226.5  | 226.5  | 223.2  | 223.2  | 219.9  | 219.9  | 219.9  | 216.6  | 216.6  | 216.6  |
| 50°    | 223.2  | 219.9  | 219.9  | 216.6  | 216.6  | 213.4  | 213.4  | 213.4  | 210.1  | 210.1  | 210.1  |
| 52.5°  | 213.4  | 210.1  | 210.1  | 210.1  | 206.8  | 203.5  | 203.5  | 203.5  | 200.2  | 200.2  | 200.2  |
| 55°    | 203.5  | 200.2  | 200.2  | 200.2  | 196.9  | 193.7  | 193.7  | 193.7  | 190.4  | 190.4  | 190.4  |
| 57.5°  | 190.4  | 187.1  | 187.1  | 183.8  | 183.8  | 183.8  | 183.8  | 183.8  | 180.5  | 180.5  | 180.5  |
| 60°    | 180.5  | 177.2  | 177.2  | 174.0  | 174.0  | 170.7  | 170.7  | 170.7  | 170.7  | 170.7  | 170.7  |
| 62.5°  | 170.7  | 167.4  | 164.1  | 160.8  | 164.1  | 164.1  | 164.1  | 164.1  | 160.8  | 160.8  | 160.8  |
| 65°    | 160.8  | 157.6  | 154.3  | 151.0  | 151.0  | 151.0  | 151.0  | 151.0  | 151.0  | 151.0  | 151.0  |
| 67.5°  | 147.7  | 144.4  | 141.1  | 137.9  | 141.1  | 141.1  | 141.1  | 141.1  | 141.1  | 141.1  | 141.1  |
| 70°    | 134.6  | 131.3  | 131.3  | 128.0  | 128.0  | 124.7  | 124.7  | 128.0  | 128.0  | 128.0  | 128.0  |
| 72.5°  | 121.4  | 118.2  | 118.2  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  |
| 75°    | 108.3  | 105.0  | 105.0  | 101.8  | 101.8  | 101.8  | 101.8  | 101.8  | 101.8  | 101.8  | 101.8  |
| 77.5°  | 91.9   | 88.6   | 88.6   | 88.6   | 88.6   | 88.6   | 88.6   | 91.9   | 91.9   | 91.9   | 91.9   |
| 80°    | 78.8   | 75.5   | 75.5   | 75.5   | 75.5   | 75.5   | 75.5   | 75.5   | 75.5   | 75.5   | 75.5   |
| 82.5°  | 62.4   | 59.1   | 59.1   | 59.1   | 59.1   | 59.1   | 59.1   | 59.1   | 59.1   | 59.1   | 59.1   |
| 85°    | 46.0   | 42.7   | 42.7   | 42.7   | 46.0   | 46.0   | 46.0   | 46.0   | 46.0   | 46.0   | 46.0   |
| 87.5°  | 29.5   | 26.3   | 26.3   | 26.3   | 29.5   | 29.5   | 29.5   | 29.5   | 26.3   | 26.3   | 26.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110°   | 112.5° | 115°   | 117.5° | 120°   | 122.5° | 125°   | 127.5° | 130°   | 132.5° | 135°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2067.9 | 2067.9 | 2067.9 | 2064.6 | 2061.3 | 2058.0 | 2054.7 | 2064.6 | 2071.1 | 2081.0 | 2087.6 |
| 5°     | 1680.5 | 1687.1 | 1690.4 | 1700.2 | 1710.1 | 1719.9 | 1729.8 | 1736.3 | 1742.9 | 1746.2 | 1752.8 |
| 7.5°   | 1267.0 | 1283.4 | 1296.5 | 1309.6 | 1322.8 | 1332.6 | 1345.7 | 1355.6 | 1365.4 | 1375.3 | 1385.1 |
| 10°    | 961.7  | 968.3  | 971.6  | 984.7  | 994.5  | 1007.7 | 1017.5 | 1027.4 | 1037.2 | 1043.8 | 1053.6 |
| 12.5°  | 781.2  | 774.6  | 771.3  | 771.3  | 771.3  | 771.3  | 771.3  | 777.9  | 784.5  | 791.0  | 797.6  |
| 15°    | 630.2  | 626.9  | 623.6  | 620.4  | 617.1  | 610.5  | 607.2  | 613.8  | 620.4  | 626.9  | 633.5  |
| 17.5°  | 528.5  | 528.5  | 528.5  | 525.2  | 521.9  | 518.6  | 515.3  | 518.6  | 521.9  | 521.9  | 525.2  |
| 20°    | 453.0  | 456.2  | 459.5  | 462.8  | 462.8  | 466.1  | 466.1  | 469.4  | 472.7  | 472.7  | 475.9  |
| 22.5°  | 407.0  | 410.3  | 410.3  | 410.3  | 413.6  | 413.6  | 413.6  | 416.9  | 420.1  | 423.4  | 426.7  |
| 25°    | 370.9  | 370.9  | 367.6  | 367.6  | 370.9  | 370.9  | 370.9  | 370.9  | 374.2  | 374.2  | 374.2  |
| 27.5°  | 351.2  | 347.9  | 347.9  | 347.9  | 347.9  | 344.6  | 344.6  | 344.6  | 344.6  | 344.6  | 344.6  |
| 30°    | 341.4  | 338.1  | 334.8  | 331.5  | 331.5  | 328.2  | 324.9  | 324.9  | 324.9  | 324.9  | 324.9  |
| 32.5°  | 338.1  | 331.5  | 324.9  | 321.7  | 321.7  | 318.4  | 315.1  | 311.8  | 311.8  | 308.5  | 305.3  |
| 35°    | 302.0  | 298.7  | 298.7  | 295.4  | 292.1  | 288.8  | 285.6  | 285.6  | 285.6  | 282.3  | 282.3  |
| 37.5°  | 262.6  | 265.9  | 265.9  | 265.9  | 269.1  | 269.1  | 269.1  | 269.1  | 272.4  | 272.4  | 272.4  |
| 40°    | 246.2  | 246.2  | 246.2  | 249.5  | 252.7  | 252.7  | 256.0  | 256.0  | 259.3  | 259.3  | 259.3  |
| 42.5°  | 233.0  | 229.8  | 229.8  | 233.0  | 233.0  | 236.3  | 236.3  | 239.6  | 242.9  | 242.9  | 246.2  |
| 45°    | 226.5  | 223.2  | 223.2  | 223.2  | 223.2  | 219.9  | 219.9  | 223.2  | 226.5  | 229.8  | 233.0  |
| 47.5°  | 213.4  | 213.4  | 210.1  | 210.1  | 210.1  | 210.1  | 210.1  | 210.1  | 213.4  | 213.4  | 213.4  |
| 50°    | 206.8  | 206.8  | 203.5  | 203.5  | 203.5  | 203.5  | 203.5  | 203.5  | 203.5  | 203.5  | 203.5  |
| 52.5°  | 200.2  | 196.9  | 196.9  | 196.9  | 196.9  | 193.7  | 193.7  | 193.7  | 193.7  | 193.7  | 193.7  |
| 55°    | 190.4  | 187.1  | 187.1  | 187.1  | 187.1  | 187.1  | 187.1  | 187.1  | 190.4  | 190.4  | 190.4  |
| 57.5°  | 180.5  | 177.2  | 177.2  | 177.2  | 180.5  | 180.5  | 180.5  | 180.5  | 183.8  | 183.8  | 183.8  |
| 60°    | 170.7  | 170.7  | 170.7  | 170.7  | 170.7  | 170.7  | 170.7  | 174.0  | 174.0  | 177.2  | 177.2  |
| 62.5°  | 160.8  | 160.8  | 160.8  | 160.8  | 164.1  | 164.1  | 164.1  | 164.1  | 167.4  | 167.4  | 167.4  |
| 65°    | 151.0  | 151.0  | 151.0  | 151.0  | 154.3  | 154.3  | 154.3  | 154.3  | 154.3  | 154.3  | 154.3  |
| 67.5°  | 141.1  | 141.1  | 141.1  | 141.1  | 141.1  | 141.1  | 141.1  | 144.4  | 144.4  | 147.7  | 147.7  |
| 70°    | 128.0  | 124.7  | 124.7  | 128.0  | 128.0  | 131.3  | 131.3  | 134.6  | 134.6  | 137.9  | 137.9  |
| 72.5°  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 118.2  | 121.4  | 121.4  | 124.7  |
| 75°    | 101.8  | 101.8  | 101.8  | 101.8  | 105.0  | 105.0  | 105.0  | 108.3  | 108.3  | 111.6  | 111.6  |
| 77.5°  | 91.9   | 88.6   | 88.6   | 88.6   | 91.9   | 91.9   | 91.9   | 95.2   | 95.2   | 98.5   | 98.5   |
| 80°    | 75.5   | 75.5   | 75.5   | 75.5   | 78.8   | 78.8   | 78.8   | 78.8   | 82.1   | 82.1   | 82.1   |
| 82.5°  | 62.4   | 62.4   | 62.4   | 62.4   | 62.4   | 62.4   | 62.4   | 62.4   | 65.6   | 65.6   | 65.6   |
| 85°    | 46.0   | 46.0   | 46.0   | 46.0   | 49.2   | 49.2   | 49.2   | 49.2   | 49.2   | 49.2   | 49.2   |
| 87.5°  | 29.5   | 29.5   | 29.5   | 29.5   | 29.5   | 29.5   | 29.5   | 29.5   | 32.8   | 32.8   | 32.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P671819

CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°   | 142.5° | 145°   | 147.5° | 150°   | 152.5° | 155°   | 157.5° | 160°   | 162.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2087.6 | 2087.6 | 2087.6 | 2087.6 | 2094.1 | 2097.4 | 2104.0 | 2107.2 | 2104.0 | 2100.7 | 2094.1 |
| 5°     | 1756.0 | 1759.3 | 1759.3 | 1762.6 | 1762.6 | 1762.6 | 1762.6 | 1762.6 | 1769.2 | 1775.7 | 1782.3 |
| 7.5°   | 1388.4 | 1391.7 | 1395.0 | 1398.3 | 1398.3 | 1398.3 | 1395.0 | 1395.0 | 1398.3 | 1398.3 | 1401.5 |
| 10°    | 1063.5 | 1076.6 | 1086.4 | 1096.3 | 1089.7 | 1079.9 | 1073.3 | 1063.5 | 1063.5 | 1063.5 | 1060.2 |
| 12.5°  | 804.2  | 807.4  | 814.0  | 817.3  | 814.0  | 814.0  | 810.7  | 807.4  | 810.7  | 817.3  | 820.6  |
| 15°    | 636.8  | 636.8  | 640.1  | 640.1  | 643.3  | 646.6  | 646.6  | 649.9  | 656.5  | 659.7  | 666.3  |
| 17.5°  | 528.5  | 531.7  | 531.7  | 535.0  | 535.0  | 538.3  | 538.3  | 538.3  | 544.9  | 551.4  | 561.3  |
| 20°    | 475.9  | 475.9  | 475.9  | 475.9  | 475.9  | 472.7  | 472.7  | 469.4  | 472.7  | 479.2  | 482.5  |
| 22.5°  | 426.7  | 430.0  | 430.0  | 430.0  | 426.7  | 423.4  | 416.9  | 413.6  | 413.6  | 416.9  | 416.9  |
| 25°    | 374.2  | 370.9  | 370.9  | 367.6  | 367.6  | 370.9  | 370.9  | 370.9  | 374.2  | 374.2  | 377.5  |
| 27.5°  | 344.6  | 341.4  | 341.4  | 338.1  | 338.1  | 341.4  | 341.4  | 341.4  | 341.4  | 341.4  | 341.4  |
| 30°    | 321.7  | 321.7  | 318.4  | 315.1  | 318.4  | 318.4  | 321.7  | 321.7  | 324.9  | 324.9  | 328.2  |
| 32.5°  | 305.3  | 302.0  | 302.0  | 298.7  | 302.0  | 302.0  | 305.3  | 305.3  | 308.5  | 311.8  | 311.8  |
| 35°    | 282.3  | 282.3  | 282.3  | 282.3  | 282.3  | 282.3  | 279.0  | 279.0  | 279.0  | 279.0  | 279.0  |
| 37.5°  | 269.1  | 269.1  | 265.9  | 262.6  | 262.6  | 262.6  | 262.6  | 262.6  | 259.3  | 256.0  | 252.7  |
| 40°    | 259.3  | 256.0  | 256.0  | 252.7  | 249.5  | 249.5  | 246.2  | 242.9  | 242.9  | 239.6  | 239.6  |
| 42.5°  | 246.2  | 242.9  | 242.9  | 239.6  | 236.3  | 236.3  | 233.0  | 229.8  | 229.8  | 229.8  | 226.5  |
| 45°    | 229.8  | 229.8  | 226.5  | 223.2  | 223.2  | 223.2  | 219.9  | 219.9  | 219.9  | 219.9  | 216.6  |
| 47.5°  | 213.4  | 213.4  | 210.1  | 210.1  | 210.1  | 210.1  | 206.8  | 206.8  | 206.8  | 206.8  | 206.8  |
| 50°    | 203.5  | 203.5  | 203.5  | 203.5  | 203.5  | 203.5  | 200.2  | 200.2  | 200.2  | 200.2  | 200.2  |
| 52.5°  | 193.7  | 193.7  | 193.7  | 193.7  | 193.7  | 193.7  | 193.7  | 193.7  | 193.7  | 193.7  | 193.7  |
| 55°    | 190.4  | 190.4  | 190.4  | 190.4  | 190.4  | 190.4  | 187.1  | 187.1  | 187.1  | 190.4  | 190.4  |
| 57.5°  | 183.8  | 183.8  | 180.5  | 180.5  | 180.5  | 180.5  | 180.5  | 180.5  | 180.5  | 180.5  | 180.5  |
| 60°    | 177.2  | 177.2  | 177.2  | 177.2  | 177.2  | 177.2  | 177.2  | 177.2  | 177.2  | 177.2  | 177.2  |
| 62.5°  | 167.4  | 167.4  | 167.4  | 167.4  | 167.4  | 170.7  | 170.7  | 170.7  | 170.7  | 170.7  | 167.4  |
| 65°    | 154.3  | 157.6  | 157.6  | 157.6  | 157.6  | 157.6  | 157.6  | 157.6  | 157.6  | 157.6  | 157.6  |
| 67.5°  | 147.7  | 147.7  | 147.7  | 147.7  | 147.7  | 147.7  | 147.7  | 147.7  | 147.7  | 147.7  | 147.7  |
| 70°    | 137.9  | 137.9  | 134.6  | 134.6  | 134.6  | 137.9  | 137.9  | 137.9  | 137.9  | 137.9  | 137.9  |
| 72.5°  | 124.7  | 124.7  | 124.7  | 124.7  | 124.7  | 124.7  | 124.7  | 124.7  | 124.7  | 128.0  | 128.0  |
| 75°    | 111.6  | 111.6  | 111.6  | 111.6  | 111.6  | 111.6  | 111.6  | 111.6  | 111.6  | 111.6  | 111.6  |
| 77.5°  | 98.5   | 98.5   | 95.2   | 95.2   | 95.2   | 98.5   | 98.5   | 98.5   | 98.5   | 101.8  | 101.8  |
| 80°    | 82.1   | 82.1   | 82.1   | 82.1   | 82.1   | 82.1   | 82.1   | 82.1   | 82.1   | 85.3   | 85.3   |
| 82.5°  | 65.6   | 65.6   | 65.6   | 65.6   | 65.6   | 65.6   | 65.6   | 65.6   | 65.6   | 68.9   | 68.9   |
| 85°    | 49.2   | 52.5   | 52.5   | 52.5   | 52.5   | 52.5   | 52.5   | 52.5   | 52.5   | 55.8   | 55.8   |
| 87.5°  | 32.8   | 32.8   | 32.8   | 32.8   | 32.8   | 32.8   | 29.5   | 29.5   | 29.5   | 29.5   | 26.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671819

CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165°   | 167.5° | 170°   | 172.5° | 175°   | 177.5° | 180°   | 182.5° | 185°   | 187.5° | 190°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2090.8 | 2094.1 | 2097.4 | 2097.4 | 2100.7 | 2104.0 | 2104.0 | 2117.1 | 2130.2 | 2136.8 | 2143.4 |
| 5°     | 1788.9 | 1785.6 | 1785.6 | 1782.3 | 1779.0 | 1788.9 | 1798.7 | 1818.4 | 1838.1 | 1841.4 | 1847.9 |
| 7.5°   | 1401.5 | 1404.8 | 1408.1 | 1408.1 | 1411.4 | 1401.5 | 1388.4 | 1391.7 | 1395.0 | 1411.4 | 1424.5 |
| 10°    | 1060.2 | 1063.5 | 1066.8 | 1066.8 | 1070.0 | 1066.8 | 1060.2 | 1070.0 | 1079.9 | 1093.0 | 1109.4 |
| 12.5°  | 823.9  | 833.7  | 843.6  | 850.1  | 860.0  | 866.5  | 869.8  | 882.9  | 892.8  | 909.2  | 925.6  |
| 15°    | 672.9  | 679.4  | 686.0  | 692.6  | 699.1  | 705.7  | 712.3  | 725.4  | 738.5  | 758.2  | 777.9  |
| 17.5°  | 567.8  | 567.8  | 571.1  | 571.1  | 571.1  | 577.7  | 584.3  | 590.8  | 594.1  | 613.8  | 633.5  |
| 20°    | 485.8  | 482.5  | 479.2  | 475.9  | 472.7  | 479.2  | 482.5  | 485.8  | 489.1  | 502.2  | 512.0  |
| 22.5°  | 416.9  | 416.9  | 420.1  | 420.1  | 420.1  | 416.9  | 410.3  | 413.6  | 413.6  | 420.1  | 430.0  |
| 25°    | 377.5  | 377.5  | 377.5  | 374.2  | 374.2  | 377.5  | 380.7  | 380.7  | 377.5  | 380.7  | 384.0  |
| 27.5°  | 341.4  | 344.6  | 344.6  | 347.9  | 347.9  | 351.2  | 351.2  | 351.2  | 351.2  | 354.5  | 357.8  |
| 30°    | 328.2  | 328.2  | 331.5  | 331.5  | 331.5  | 334.8  | 338.1  | 338.1  | 338.1  | 341.4  | 347.9  |
| 32.5°  | 315.1  | 318.4  | 321.7  | 324.9  | 328.2  | 331.5  | 331.5  | 334.8  | 334.8  | 338.1  | 341.4  |
| 35°    | 279.0  | 275.7  | 275.7  | 272.4  | 269.1  | 269.1  | 269.1  | 269.1  | 265.9  | 269.1  | 269.1  |
| 37.5°  | 249.5  | 249.5  | 249.5  | 246.2  | 246.2  | 249.5  | 249.5  | 249.5  | 249.5  | 252.7  | 252.7  |
| 40°    | 236.3  | 236.3  | 236.3  | 236.3  | 236.3  | 236.3  | 236.3  | 239.6  | 239.6  | 242.9  | 246.2  |
| 42.5°  | 226.5  | 226.5  | 226.5  | 226.5  | 226.5  | 229.8  | 229.8  | 229.8  | 229.8  | 233.0  | 233.0  |
| 45°    | 216.6  | 216.6  | 216.6  | 216.6  | 216.6  | 216.6  | 216.6  | 219.9  | 219.9  | 223.2  | 226.5  |
| 47.5°  | 206.8  | 206.8  | 206.8  | 206.8  | 206.8  | 210.1  | 213.4  | 213.4  | 213.4  | 216.6  | 216.6  |
| 50°    | 200.2  | 200.2  | 200.2  | 200.2  | 200.2  | 203.5  | 203.5  | 206.8  | 206.8  | 210.1  | 213.4  |
| 52.5°  | 193.7  | 193.7  | 193.7  | 193.7  | 193.7  | 196.9  | 196.9  | 200.2  | 200.2  | 203.5  | 206.8  |
| 55°    | 190.4  | 190.4  | 190.4  | 187.1  | 187.1  | 190.4  | 190.4  | 193.7  | 193.7  | 196.9  | 196.9  |
| 57.5°  | 180.5  | 180.5  | 180.5  | 180.5  | 180.5  | 180.5  | 180.5  | 183.8  | 183.8  | 187.1  | 190.4  |
| 60°    | 177.2  | 177.2  | 174.0  | 174.0  | 170.7  | 174.0  | 174.0  | 177.2  | 177.2  | 180.5  | 180.5  |
| 62.5°  | 167.4  | 167.4  | 167.4  | 164.1  | 164.1  | 167.4  | 167.4  | 167.4  | 167.4  | 170.7  | 174.0  |
| 65°    | 157.6  | 157.6  | 157.6  | 154.3  | 154.3  | 157.6  | 157.6  | 157.6  | 157.6  | 160.8  | 164.1  |
| 67.5°  | 147.7  | 147.7  | 147.7  | 144.4  | 144.4  | 144.4  | 144.4  | 147.7  | 147.7  | 151.0  | 154.3  |
| 70°    | 137.9  | 137.9  | 137.9  | 134.6  | 134.6  | 134.6  | 131.3  | 134.6  | 137.9  | 141.1  | 141.1  |
| 72.5°  | 128.0  | 128.0  | 128.0  | 124.7  | 124.7  | 124.7  | 121.4  | 124.7  | 124.7  | 128.0  | 128.0  |
| 75°    | 111.6  | 111.6  | 111.6  | 111.6  | 111.6  | 111.6  | 108.3  | 108.3  | 108.3  | 111.6  | 111.6  |
| 77.5°  | 101.8  | 101.8  | 101.8  | 98.5   | 98.5   | 98.5   | 95.2   | 95.2   | 95.2   | 98.5   | 98.5   |
| 80°    | 85.3   | 85.3   | 85.3   | 82.1   | 82.1   | 82.1   | 78.8   | 78.8   | 78.8   | 82.1   | 82.1   |
| 82.5°  | 68.9   | 68.9   | 68.9   | 65.6   | 65.6   | 65.6   | 62.4   | 62.4   | 62.4   | 65.6   | 65.6   |
| 85°    | 55.8   | 55.8   | 55.8   | 55.8   | 55.8   | 55.8   | 52.5   | 52.5   | 52.5   | 55.8   | 59.1   |
| 87.5°  | 26.3   | 26.3   | 29.5   | 29.5   | 29.5   | 29.5   | 26.3   | 26.3   | 23.0   | 23.0   | 26.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671819

CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°   | 197.5° | 200°   | 202.5° | 205°   | 207.5° | 210°   | 212.5° | 215°   | 217.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2149.9 | 2156.5 | 2172.9 | 2186.0 | 2202.4 | 2215.6 | 2225.4 | 2238.5 | 2248.4 | 2258.2 | 2264.8 |
| 5°     | 1851.2 | 1854.5 | 1870.9 | 1887.3 | 1900.5 | 1916.9 | 1939.8 | 1962.8 | 1985.8 | 2008.8 | 2025.2 |
| 7.5°   | 1440.9 | 1454.1 | 1473.8 | 1496.7 | 1516.4 | 1536.1 | 1559.1 | 1585.4 | 1608.3 | 1631.3 | 1654.3 |
| 10°    | 1122.6 | 1135.7 | 1155.4 | 1175.1 | 1191.5 | 1211.2 | 1237.4 | 1263.7 | 1289.9 | 1316.2 | 1342.5 |
| 12.5°  | 942.0  | 958.4  | 981.4  | 1004.4 | 1024.1 | 1047.1 | 1079.9 | 1109.4 | 1142.2 | 1171.8 | 1204.6 |
| 15°    | 794.3  | 814.0  | 843.6  | 876.4  | 905.9  | 935.5  | 968.3  | 1001.1 | 1030.6 | 1063.5 | 1096.3 |
| 17.5°  | 653.2  | 672.9  | 699.1  | 728.7  | 754.9  | 781.2  | 820.6  | 856.7  | 896.1  | 932.2  | 968.3  |
| 20°    | 525.2  | 535.0  | 561.3  | 587.5  | 613.8  | 640.1  | 669.6  | 699.1  | 728.7  | 758.2  | 804.2  |
| 22.5°  | 436.5  | 443.1  | 456.2  | 466.1  | 479.2  | 489.1  | 518.6  | 548.1  | 574.4  | 603.9  | 646.6  |
| 25°    | 384.0  | 387.3  | 397.2  | 403.7  | 413.6  | 420.1  | 439.8  | 456.2  | 475.9  | 492.3  | 531.7  |
| 27.5°  | 357.8  | 361.1  | 364.3  | 367.6  | 370.9  | 374.2  | 387.3  | 400.4  | 410.3  | 423.4  | 459.5  |
| 30°    | 351.2  | 354.5  | 364.3  | 370.9  | 380.7  | 387.3  | 393.9  | 400.4  | 407.0  | 413.6  | 436.5  |
| 32.5°  | 344.6  | 347.9  | 347.9  | 344.6  | 344.6  | 341.4  | 347.9  | 351.2  | 357.8  | 361.1  | 380.7  |
| 35°    | 272.4  | 272.4  | 275.7  | 279.0  | 282.3  | 285.6  | 295.4  | 302.0  | 311.8  | 318.4  | 334.8  |
| 37.5°  | 256.0  | 256.0  | 259.3  | 265.9  | 269.1  | 272.4  | 279.0  | 285.6  | 292.1  | 298.7  | 315.1  |
| 40°    | 246.2  | 249.5  | 252.7  | 256.0  | 259.3  | 262.6  | 269.1  | 272.4  | 279.0  | 282.3  | 295.4  |
| 42.5°  | 236.3  | 236.3  | 239.6  | 246.2  | 249.5  | 252.7  | 259.3  | 262.6  | 269.1  | 272.4  | 285.6  |
| 45°    | 229.8  | 233.0  | 236.3  | 239.6  | 239.6  | 242.9  | 249.5  | 256.0  | 259.3  | 265.9  | 279.0  |
| 47.5°  | 219.9  | 219.9  | 226.5  | 229.8  | 236.3  | 239.6  | 246.2  | 249.5  | 256.0  | 259.3  | 272.4  |
| 50°    | 213.4  | 216.6  | 223.2  | 226.5  | 233.0  | 236.3  | 246.2  | 252.7  | 262.6  | 269.1  | 275.7  |
| 52.5°  | 206.8  | 210.1  | 216.6  | 219.9  | 226.5  | 229.8  | 242.9  | 256.0  | 265.9  | 279.0  | 279.0  |
| 55°    | 200.2  | 200.2  | 206.8  | 216.6  | 223.2  | 229.8  | 236.3  | 246.2  | 252.7  | 259.3  | 259.3  |
| 57.5°  | 190.4  | 193.7  | 200.2  | 210.1  | 216.6  | 223.2  | 229.8  | 236.3  | 239.6  | 246.2  | 242.9  |
| 60°    | 183.8  | 183.8  | 193.7  | 203.5  | 213.4  | 223.2  | 223.2  | 223.2  | 219.9  | 219.9  | 219.9  |
| 62.5°  | 174.0  | 177.2  | 190.4  | 206.8  | 219.9  | 233.0  | 223.2  | 213.4  | 203.5  | 193.7  | 196.9  |
| 65°    | 167.4  | 170.7  | 177.2  | 187.1  | 193.7  | 200.2  | 193.7  | 190.4  | 183.8  | 177.2  | 180.5  |
| 67.5°  | 154.3  | 157.6  | 160.8  | 160.8  | 164.1  | 164.1  | 164.1  | 164.1  | 164.1  | 164.1  | 167.4  |
| 70°    | 144.4  | 144.4  | 144.4  | 147.7  | 147.7  | 147.7  | 147.7  | 147.7  | 147.7  | 147.7  | 151.0  |
| 72.5°  | 131.3  | 131.3  | 131.3  | 131.3  | 131.3  | 131.3  | 131.3  | 131.3  | 131.3  | 131.3  | 134.6  |
| 75°    | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 114.9  | 118.2  |
| 77.5°  | 101.8  | 101.8  | 101.8  | 101.8  | 101.8  | 101.8  | 101.8  | 101.8  | 98.5   | 98.5   | 101.8  |
| 80°    | 85.3   | 85.3   | 85.3   | 85.3   | 82.1   | 82.1   | 82.1   | 82.1   | 82.1   | 82.1   | 85.3   |
| 82.5°  | 68.9   | 68.9   | 68.9   | 68.9   | 65.6   | 65.6   | 65.6   | 65.6   | 62.4   | 62.4   | 65.6   |
| 85°    | 62.4   | 65.6   | 65.6   | 68.9   | 68.9   | 68.9   | 65.6   | 62.4   | 59.1   | 55.8   | 55.8   |
| 87.5°  | 26.3   | 26.3   | 26.3   | 26.3   | 23.0   | 23.0   | 23.0   | 23.0   | 23.0   | 23.0   | 23.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220°   | 222.5° | 225°   | 227.5° | 230°   | 232.5° | 235°   | 237.5° | 240°   | 242.5° | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2274.6 | 2281.2 | 2287.8 | 2297.6 | 2310.7 | 2320.6 | 2330.4 | 2350.1 | 2373.1 | 2392.8 | 2412.5 |
| 5°     | 2041.6 | 2058.0 | 2074.4 | 2094.1 | 2113.8 | 2130.2 | 2149.9 | 2189.3 | 2228.7 | 2264.8 | 2304.2 |
| 7.5°   | 1674.0 | 1697.0 | 1716.7 | 1749.5 | 1779.0 | 1811.8 | 1841.4 | 1890.6 | 1936.6 | 1985.8 | 2031.8 |
| 10°    | 1368.7 | 1395.0 | 1421.2 | 1463.9 | 1509.9 | 1552.5 | 1595.2 | 1634.6 | 1677.3 | 1716.7 | 1756.0 |
| 12.5°  | 1237.4 | 1267.0 | 1299.8 | 1326.1 | 1355.6 | 1381.9 | 1408.1 | 1454.1 | 1500.0 | 1546.0 | 1591.9 |
| 15°    | 1129.1 | 1161.9 | 1194.8 | 1227.6 | 1257.1 | 1289.9 | 1319.5 | 1358.9 | 1401.5 | 1440.9 | 1480.3 |
| 17.5°  | 1004.4 | 1037.2 | 1073.3 | 1109.4 | 1145.5 | 1181.6 | 1217.7 | 1273.5 | 1329.3 | 1381.9 | 1437.7 |
| 20°    | 846.8  | 892.8  | 935.5  | 984.7  | 1033.9 | 1083.2 | 1132.4 | 1191.5 | 1250.6 | 1306.4 | 1365.4 |
| 22.5°  | 689.3  | 732.0  | 774.6  | 833.7  | 892.8  | 948.6  | 1007.7 | 1086.4 | 1161.9 | 1240.7 | 1316.2 |
| 25°    | 574.4  | 613.8  | 653.2  | 718.8  | 781.2  | 846.8  | 909.2  | 1004.4 | 1096.3 | 1191.5 | 1283.4 |
| 27.5°  | 495.6  | 531.7  | 567.8  | 636.8  | 705.7  | 771.3  | 840.3  | 945.3  | 1047.1 | 1152.1 | 1253.8 |
| 30°    | 459.5  | 482.5  | 505.5  | 571.1  | 636.8  | 699.1  | 764.8  | 866.5  | 968.3  | 1070.0 | 1171.8 |
| 32.5°  | 400.4  | 420.1  | 439.8  | 498.9  | 558.0  | 613.8  | 672.9  | 777.9  | 879.7  | 984.7  | 1086.4 |
| 35°    | 354.5  | 370.9  | 387.3  | 443.1  | 495.6  | 551.4  | 603.9  | 709.0  | 814.0  | 919.0  | 1024.1 |
| 37.5°  | 328.2  | 344.6  | 357.8  | 407.0  | 459.5  | 508.8  | 558.0  | 663.0  | 764.8  | 869.8  | 971.6  |
| 40°    | 308.5  | 318.4  | 331.5  | 380.7  | 426.7  | 475.9  | 521.9  | 617.1  | 715.5  | 810.7  | 905.9  |
| 42.5°  | 295.4  | 308.5  | 318.4  | 361.1  | 407.0  | 449.7  | 492.3  | 584.3  | 676.2  | 764.8  | 856.7  |
| 45°    | 292.1  | 305.3  | 318.4  | 354.5  | 390.6  | 423.4  | 459.5  | 548.1  | 636.8  | 725.4  | 814.0  |
| 47.5°  | 285.6  | 295.4  | 308.5  | 338.1  | 364.3  | 393.9  | 420.1  | 508.8  | 597.4  | 682.7  | 771.3  |
| 50°    | 282.3  | 285.6  | 292.1  | 318.4  | 344.6  | 370.9  | 397.2  | 485.8  | 574.4  | 663.0  | 751.7  |
| 52.5°  | 279.0  | 279.0  | 279.0  | 302.0  | 324.9  | 344.6  | 367.6  | 456.2  | 548.1  | 636.8  | 725.4  |
| 55°    | 259.3  | 256.0  | 256.0  | 279.0  | 298.7  | 321.7  | 341.4  | 430.0  | 518.6  | 603.9  | 692.6  |
| 57.5°  | 239.6  | 236.3  | 233.0  | 252.7  | 272.4  | 292.1  | 311.8  | 400.4  | 492.3  | 581.0  | 669.6  |
| 60°    | 219.9  | 216.6  | 216.6  | 236.3  | 252.7  | 272.4  | 288.8  | 380.7  | 469.4  | 561.3  | 649.9  |
| 62.5°  | 196.9  | 200.2  | 200.2  | 216.6  | 236.3  | 252.7  | 269.1  | 361.1  | 456.2  | 548.1  | 640.1  |
| 65°    | 180.5  | 183.8  | 183.8  | 203.5  | 223.2  | 242.9  | 262.6  | 351.2  | 443.1  | 531.7  | 620.4  |
| 67.5°  | 167.4  | 170.7  | 170.7  | 193.7  | 213.4  | 236.3  | 256.0  | 334.8  | 416.9  | 495.6  | 574.4  |
| 70°    | 154.3  | 154.3  | 157.6  | 180.5  | 203.5  | 226.5  | 249.5  | 318.4  | 387.3  | 453.0  | 521.9  |
| 72.5°  | 137.9  | 141.1  | 144.4  | 167.4  | 187.1  | 210.1  | 229.8  | 292.1  | 354.5  | 416.9  | 479.2  |
| 75°    | 121.4  | 124.7  | 128.0  | 147.7  | 167.4  | 187.1  | 206.8  | 265.9  | 321.7  | 380.7  | 436.5  |
| 77.5°  | 108.3  | 111.6  | 114.9  | 131.3  | 147.7  | 164.1  | 180.5  | 223.2  | 269.1  | 311.8  | 354.5  |
| 80°    | 88.6   | 88.6   | 91.9   | 105.0  | 118.2  | 128.0  | 141.1  | 170.7  | 200.2  | 226.5  | 256.0  |
| 82.5°  | 65.6   | 68.9   | 68.9   | 78.8   | 85.3   | 95.2   | 101.8  | 118.2  | 131.3  | 147.7  | 160.8  |
| 85°    | 55.8   | 52.5   | 52.5   | 59.1   | 62.4   | 68.9   | 72.2   | 82.1   | 88.6   | 98.5   | 105.0  |
| 87.5°  | 23.0   | 19.7   | 19.7   | 23.0   | 29.5   | 32.8   | 36.1   | 36.1   | 39.4   | 39.4   | 39.4   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P671819

CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 252.5° | 255°   | 257.5° | 260°   | 262.5° | 265°   | 267.5° | 270°   | 272.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2422.3 | 2428.9 | 2438.8 | 2445.3 | 2461.7 | 2474.9 | 2491.3 | 2504.4 | 2514.3 | 2530.7 | 2524.1 |
| 5°     | 2333.7 | 2363.3 | 2392.8 | 2422.3 | 2445.3 | 2468.3 | 2488.0 | 2511.0 | 2537.2 | 2586.5 | 2599.6 |
| 7.5°   | 2071.1 | 2110.5 | 2146.6 | 2186.0 | 2232.0 | 2277.9 | 2323.9 | 2369.8 | 2412.5 | 2474.9 | 2514.3 |
| 10°    | 1811.8 | 1867.6 | 1920.2 | 1976.0 | 2018.6 | 2061.3 | 2100.7 | 2143.4 | 2202.4 | 2264.8 | 2337.0 |
| 12.5°  | 1647.7 | 1703.5 | 1759.3 | 1815.1 | 1877.5 | 1936.6 | 1998.9 | 2058.0 | 2113.8 | 2163.0 | 2245.1 |
| 15°    | 1539.4 | 1601.8 | 1660.9 | 1719.9 | 1795.4 | 1867.6 | 1943.1 | 2015.3 | 2097.4 | 2163.0 | 2218.8 |
| 17.5°  | 1513.1 | 1588.6 | 1660.9 | 1736.3 | 1815.1 | 1893.9 | 1972.7 | 2051.4 | 2133.5 | 2232.0 | 2304.2 |
| 20°    | 1467.2 | 1568.9 | 1670.7 | 1772.4 | 1874.2 | 1972.7 | 2074.4 | 2172.9 | 2281.2 | 2399.4 | 2432.2 |
| 22.5°  | 1440.9 | 1562.4 | 1687.1 | 1808.6 | 1946.4 | 2087.6 | 2225.4 | 2363.3 | 2478.1 | 2566.8 | 2665.2 |
| 25°    | 1437.7 | 1588.6 | 1742.9 | 1893.9 | 2067.9 | 2238.5 | 2412.5 | 2583.2 | 2730.9 | 2819.5 | 2898.3 |
| 27.5°  | 1434.4 | 1618.2 | 1798.7 | 1979.2 | 2192.6 | 2402.7 | 2616.0 | 2826.1 | 2963.9 | 3091.9 | 3157.6 |
| 30°    | 1395.0 | 1614.9 | 1838.1 | 2058.0 | 2297.6 | 2537.2 | 2776.8 | 3016.4 | 3157.6 | 3246.2 | 3279.0 |
| 32.5°  | 1345.7 | 1605.1 | 1864.4 | 2123.7 | 2396.1 | 2668.5 | 2937.7 | 3210.1 | 3321.7 | 3397.2 | 3370.9 |
| 35°    | 1306.4 | 1591.9 | 1874.2 | 2156.5 | 2445.3 | 2737.5 | 3026.3 | 3315.1 | 3476.0 | 3581.0 | 3538.3 |
| 37.5°  | 1270.3 | 1568.9 | 1867.6 | 2166.3 | 2504.4 | 2842.5 | 3180.6 | 3518.6 | 3672.9 | 3784.5 | 3735.3 |
| 40°    | 1227.6 | 1546.0 | 1867.6 | 2186.0 | 2573.3 | 2957.4 | 3344.7 | 3728.7 | 3928.9 | 4024.1 | 3948.6 |
| 42.5°  | 1191.5 | 1523.0 | 1857.8 | 2189.3 | 2602.9 | 3016.4 | 3430.0 | 3843.6 | 4066.8 | 4201.4 | 4106.2 |
| 45°    | 1145.5 | 1477.0 | 1805.3 | 2136.8 | 2593.0 | 3049.3 | 3502.2 | 3958.5 | 4217.8 | 4322.8 | 4191.5 |
| 47.5°  | 1096.3 | 1424.5 | 1749.5 | 2074.4 | 2560.2 | 3046.0 | 3531.8 | 4017.6 | 4257.2 | 4381.9 | 4260.4 |
| 50°    | 1079.9 | 1408.1 | 1733.1 | 2061.3 | 2586.5 | 3114.9 | 3640.1 | 4165.3 | 4339.2 | 4441.0 | 4280.1 |
| 52.5°  | 1076.6 | 1424.5 | 1775.7 | 2123.7 | 2652.1 | 3177.3 | 3705.7 | 4230.9 | 4372.0 | 4480.4 | 4335.9 |
| 55°    | 1066.8 | 1444.2 | 1818.4 | 2192.6 | 2744.0 | 3298.7 | 3850.2 | 4401.6 | 4542.7 | 4621.5 | 4513.2 |
| 57.5°  | 1076.6 | 1483.6 | 1887.3 | 2294.3 | 2862.2 | 3430.0 | 3997.9 | 4565.7 | 4736.4 | 4792.2 | 4769.2 |
| 60°    | 1083.2 | 1516.4 | 1946.4 | 2379.7 | 2934.4 | 3489.1 | 4043.8 | 4598.5 | 4775.8 | 4913.6 | 4939.9 |
| 62.5°  | 1066.8 | 1493.5 | 1916.9 | 2343.6 | 2845.8 | 3348.0 | 3850.2 | 4352.3 | 4644.5 | 4848.0 | 4966.1 |
| 65°    | 1017.5 | 1411.4 | 1808.6 | 2202.4 | 2665.2 | 3131.3 | 3594.1 | 4056.9 | 4365.5 | 4667.5 | 4762.6 |
| 67.5°  | 909.2  | 1244.0 | 1578.8 | 1913.6 | 2317.3 | 2721.0 | 3121.5 | 3525.2 | 3912.5 | 4204.6 | 4335.9 |
| 70°    | 787.8  | 1050.3 | 1316.2 | 1578.8 | 1946.4 | 2314.0 | 2681.7 | 3049.3 | 3390.6 | 3712.3 | 3837.0 |
| 72.5°  | 686.0  | 889.5  | 1096.3 | 1299.8 | 1562.4 | 1821.7 | 2084.3 | 2343.6 | 2747.3 | 3069.0 | 3190.4 |
| 75°    | 584.3  | 732.0  | 876.4  | 1024.1 | 1204.6 | 1385.1 | 1562.4 | 1742.9 | 2028.5 | 2317.3 | 2438.8 |
| 77.5°  | 449.7  | 548.1  | 643.3  | 738.5  | 863.2  | 984.7  | 1109.4 | 1230.9 | 1431.1 | 1647.7 | 1710.1 |
| 80°    | 311.8  | 367.6  | 420.1  | 475.9  | 574.4  | 672.9  | 771.3  | 869.8  | 1001.1 | 1122.6 | 1217.7 |
| 82.5°  | 193.7  | 229.8  | 262.6  | 295.4  | 374.2  | 453.0  | 528.5  | 607.2  | 659.7  | 666.3  | 761.5  |
| 85°    | 124.7  | 147.7  | 167.4  | 187.1  | 233.0  | 282.3  | 328.2  | 374.2  | 334.8  | 311.8  | 370.9  |
| 87.5°  | 49.2   | 62.4   | 72.2   | 82.1   | 78.8   | 75.5   | 72.2   | 68.9   | 59.1   | 52.5   | 65.6   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671819

CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2530.7 | 2540.5 | 2550.4 | 2556.9 | 2566.8 | 2570.1 | 2573.3 | 2573.3 | 2576.6 | 2579.9 | 2586.5 |
| 5°     | 2652.1 | 2671.8 | 2691.5 | 2707.9 | 2727.6 | 2744.0 | 2757.1 | 2773.6 | 2786.7 | 2786.7 | 2783.4 |
| 7.5°   | 2550.4 | 2599.6 | 2648.8 | 2698.1 | 2747.3 | 2783.4 | 2816.2 | 2852.3 | 2885.2 | 2891.7 | 2898.3 |
| 10°    | 2415.8 | 2468.3 | 2517.5 | 2570.1 | 2619.3 | 2675.1 | 2727.6 | 2780.1 | 2835.9 | 2845.8 | 2858.9 |
| 12.5°  | 2291.1 | 2353.4 | 2415.8 | 2474.9 | 2537.2 | 2576.6 | 2616.0 | 2652.1 | 2691.5 | 2717.8 | 2744.0 |
| 15°    | 2287.8 | 2340.3 | 2392.8 | 2442.0 | 2494.6 | 2517.5 | 2540.5 | 2560.2 | 2583.2 | 2583.2 | 2586.5 |
| 17.5°  | 2363.3 | 2396.1 | 2428.9 | 2458.5 | 2491.3 | 2494.6 | 2501.1 | 2504.4 | 2507.7 | 2497.8 | 2488.0 |
| 20°    | 2511.0 | 2524.1 | 2537.2 | 2550.4 | 2563.5 | 2540.5 | 2520.8 | 2497.8 | 2474.9 | 2448.6 | 2425.6 |
| 22.5°  | 2727.6 | 2698.1 | 2668.5 | 2639.0 | 2609.4 | 2570.1 | 2527.4 | 2488.0 | 2445.3 | 2412.5 | 2379.7 |
| 25°    | 2931.1 | 2895.0 | 2858.9 | 2822.8 | 2786.7 | 2701.3 | 2616.0 | 2527.4 | 2442.0 | 2405.9 | 2369.8 |
| 27.5°  | 3203.5 | 3147.7 | 3091.9 | 3036.1 | 2980.3 | 2865.5 | 2750.6 | 2635.7 | 2520.8 | 2458.5 | 2399.4 |
| 30°    | 3269.2 | 3206.8 | 3144.5 | 3078.8 | 3016.4 | 2904.8 | 2796.5 | 2684.9 | 2573.3 | 2501.1 | 2432.2 |
| 32.5°  | 3364.4 | 3292.2 | 3220.0 | 3147.7 | 3075.5 | 2967.2 | 2858.9 | 2747.3 | 2639.0 | 2573.3 | 2504.4 |
| 35°    | 3521.9 | 3439.9 | 3357.8 | 3272.5 | 3190.4 | 3078.8 | 2970.5 | 2858.9 | 2747.3 | 2671.8 | 2599.6 |
| 37.5°  | 3656.5 | 3561.3 | 3466.1 | 3370.9 | 3275.8 | 3177.3 | 3075.5 | 2977.1 | 2875.3 | 2799.8 | 2727.6 |
| 40°    | 3807.5 | 3702.5 | 3597.4 | 3495.7 | 3390.6 | 3298.7 | 3206.8 | 3111.6 | 3019.7 | 2960.6 | 2901.6 |
| 42.5°  | 3938.8 | 3810.8 | 3686.0 | 3561.3 | 3433.3 | 3370.9 | 3311.9 | 3249.5 | 3187.1 | 3157.6 | 3124.8 |
| 45°    | 4030.7 | 3912.5 | 3791.1 | 3672.9 | 3554.7 | 3508.8 | 3462.8 | 3416.9 | 3370.9 | 3400.5 | 3430.0 |
| 47.5°  | 4070.1 | 3974.9 | 3883.0 | 3791.1 | 3695.9 | 3712.3 | 3728.7 | 3741.8 | 3758.3 | 3797.6 | 3840.3 |
| 50°    | 4106.2 | 4053.7 | 3997.9 | 3945.3 | 3889.5 | 3951.9 | 4011.0 | 4073.4 | 4135.7 | 4217.8 | 4299.8 |
| 52.5°  | 4178.4 | 4148.8 | 4122.6 | 4093.0 | 4063.5 | 4171.8 | 4280.1 | 4388.5 | 4496.8 | 4588.7 | 4680.6 |
| 55°    | 4395.0 | 4372.0 | 4349.1 | 4322.8 | 4299.8 | 4454.1 | 4605.1 | 4759.4 | 4913.6 | 5008.8 | 5104.0 |
| 57.5°  | 4693.7 | 4680.6 | 4664.2 | 4651.0 | 4634.6 | 4785.6 | 4933.3 | 5081.0 | 5232.0 | 5323.9 | 5419.1 |
| 60°    | 4920.2 | 4923.5 | 4923.5 | 4926.8 | 4926.8 | 5041.6 | 5156.5 | 5274.7 | 5389.6 | 5468.3 | 5550.4 |
| 62.5°  | 5041.6 | 5035.1 | 5028.5 | 5021.9 | 5015.4 | 5110.6 | 5205.8 | 5300.9 | 5396.1 | 5455.2 | 5514.3 |
| 65°    | 4910.3 | 4946.4 | 4982.6 | 5018.7 | 5054.8 | 5067.9 | 5077.7 | 5090.9 | 5100.7 | 5136.8 | 5172.9 |
| 67.5°  | 4470.5 | 4542.7 | 4611.7 | 4683.9 | 4752.8 | 4703.6 | 4657.6 | 4608.4 | 4559.1 | 4569.0 | 4575.5 |
| 70°    | 3981.4 | 4063.5 | 4148.8 | 4230.9 | 4313.0 | 4198.1 | 4083.2 | 3965.0 | 3850.2 | 3810.8 | 3771.4 |
| 72.5°  | 3357.8 | 3430.0 | 3505.5 | 3577.7 | 3649.9 | 3508.8 | 3370.9 | 3229.8 | 3088.7 | 3019.7 | 2950.8 |
| 75°    | 2566.8 | 2652.1 | 2740.7 | 2826.1 | 2911.4 | 2753.9 | 2593.0 | 2435.5 | 2274.6 | 2228.7 | 2186.0 |
| 77.5°  | 1870.9 | 1972.7 | 2074.4 | 2176.2 | 2277.9 | 2136.8 | 1995.6 | 1851.2 | 1710.1 | 1683.8 | 1657.6 |
| 80°    | 1362.2 | 1440.9 | 1516.4 | 1595.2 | 1670.7 | 1588.6 | 1506.6 | 1424.5 | 1342.5 | 1339.2 | 1335.9 |
| 82.5°  | 919.0  | 988.0  | 1053.6 | 1122.6 | 1188.2 | 1155.4 | 1125.8 | 1093.0 | 1060.2 | 1093.0 | 1129.1 |
| 85°    | 472.7  | 567.8  | 666.3  | 761.5  | 856.7  | 846.8  | 840.3  | 830.4  | 820.6  | 863.2  | 902.6  |
| 87.5°  | 95.2   | 177.2  | 259.3  | 338.1  | 420.1  | 400.4  | 380.7  | 357.8  | 338.1  | 351.2  | 361.1  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671819

CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2589.7 | 2593.0 | 2593.0 | 2593.0 | 2593.0 | 2593.0 | 2586.5 | 2583.2 | 2576.6 | 2570.1 | 2560.2 |
| 5°     | 2783.4 | 2780.1 | 2767.0 | 2753.9 | 2737.5 | 2724.3 | 2714.5 | 2701.3 | 2691.5 | 2678.4 | 2658.7 |
| 7.5°   | 2904.8 | 2911.4 | 2888.4 | 2868.7 | 2845.8 | 2822.8 | 2799.8 | 2776.8 | 2753.9 | 2730.9 | 2684.9 |
| 10°    | 2868.7 | 2878.6 | 2865.5 | 2852.3 | 2835.9 | 2822.8 | 2796.5 | 2767.0 | 2740.7 | 2711.2 | 2655.4 |
| 12.5°  | 2767.0 | 2793.2 | 2786.7 | 2780.1 | 2773.6 | 2767.0 | 2750.6 | 2730.9 | 2714.5 | 2694.8 | 2632.4 |
| 15°    | 2586.5 | 2586.5 | 2589.7 | 2593.0 | 2593.0 | 2596.3 | 2599.6 | 2602.9 | 2606.2 | 2609.4 | 2573.3 |
| 17.5°  | 2478.1 | 2468.3 | 2468.3 | 2468.3 | 2468.3 | 2468.3 | 2481.4 | 2497.8 | 2511.0 | 2524.1 | 2514.3 |
| 20°    | 2399.4 | 2376.4 | 2373.1 | 2373.1 | 2369.8 | 2366.5 | 2389.5 | 2415.8 | 2438.8 | 2461.7 | 2474.9 |
| 22.5°  | 2346.9 | 2314.0 | 2310.7 | 2307.5 | 2304.2 | 2300.9 | 2330.4 | 2360.0 | 2389.5 | 2419.1 | 2465.0 |
| 25°    | 2333.7 | 2297.6 | 2300.9 | 2304.2 | 2304.2 | 2307.5 | 2330.4 | 2353.4 | 2376.4 | 2399.4 | 2478.1 |
| 27.5°  | 2337.0 | 2277.9 | 2281.2 | 2284.5 | 2284.5 | 2287.8 | 2323.9 | 2356.7 | 2392.8 | 2425.6 | 2524.1 |
| 30°    | 2360.0 | 2291.1 | 2284.5 | 2277.9 | 2271.4 | 2264.8 | 2314.0 | 2363.3 | 2412.5 | 2461.7 | 2537.2 |
| 32.5°  | 2438.8 | 2373.1 | 2356.7 | 2340.3 | 2323.9 | 2307.5 | 2366.5 | 2422.3 | 2481.4 | 2537.2 | 2599.6 |
| 35°    | 2524.1 | 2451.9 | 2445.3 | 2438.8 | 2428.9 | 2422.3 | 2474.9 | 2530.7 | 2583.2 | 2635.7 | 2691.5 |
| 37.5°  | 2652.1 | 2579.9 | 2573.3 | 2563.5 | 2556.9 | 2547.1 | 2606.2 | 2662.0 | 2721.0 | 2776.8 | 2826.1 |
| 40°    | 2842.5 | 2783.4 | 2780.1 | 2780.1 | 2776.8 | 2773.6 | 2819.5 | 2868.7 | 2914.7 | 2960.6 | 2993.5 |
| 42.5°  | 3095.2 | 3065.7 | 3075.5 | 3088.7 | 3098.5 | 3108.4 | 3144.5 | 3183.8 | 3220.0 | 3256.1 | 3246.2 |
| 45°    | 3459.6 | 3489.1 | 3492.4 | 3495.7 | 3498.9 | 3502.2 | 3512.1 | 3525.2 | 3535.1 | 3544.9 | 3505.5 |
| 47.5°  | 3879.7 | 3919.1 | 3938.8 | 3958.5 | 3974.9 | 3994.6 | 3981.4 | 3965.0 | 3951.9 | 3935.5 | 3837.0 |
| 50°    | 4378.6 | 4460.7 | 4457.4 | 4454.1 | 4447.5 | 4444.3 | 4418.0 | 4391.7 | 4362.2 | 4335.9 | 4191.5 |
| 52.5°  | 4772.5 | 4864.4 | 4880.8 | 4897.2 | 4913.6 | 4930.0 | 4880.8 | 4831.6 | 4779.1 | 4729.8 | 4549.3 |
| 55°    | 5195.9 | 5291.1 | 5294.4 | 5297.7 | 5297.7 | 5300.9 | 5232.0 | 5163.1 | 5090.9 | 5021.9 | 4834.8 |
| 57.5°  | 5511.0 | 5602.9 | 5593.1 | 5586.5 | 5576.7 | 5566.8 | 5484.7 | 5402.7 | 5320.6 | 5238.6 | 5051.5 |
| 60°    | 5629.2 | 5707.9 | 5688.3 | 5668.6 | 5645.6 | 5625.9 | 5563.5 | 5501.2 | 5435.5 | 5373.1 | 5192.6 |
| 62.5°  | 5573.4 | 5632.5 | 5602.9 | 5576.7 | 5547.1 | 5517.6 | 5438.8 | 5356.7 | 5278.0 | 5195.9 | 5064.6 |
| 65°    | 5205.8 | 5241.9 | 5202.5 | 5166.4 | 5130.3 | 5090.9 | 5025.2 | 4959.6 | 4890.6 | 4825.0 | 4736.4 |
| 67.5°  | 4585.4 | 4592.0 | 4588.7 | 4585.4 | 4582.1 | 4578.8 | 4483.6 | 4388.5 | 4290.0 | 4194.8 | 4188.2 |
| 70°    | 3735.3 | 3695.9 | 3702.5 | 3712.3 | 3718.9 | 3725.4 | 3653.2 | 3584.3 | 3512.1 | 3439.9 | 3472.7 |
| 72.5°  | 2881.9 | 2812.9 | 2829.4 | 2849.0 | 2865.5 | 2881.9 | 2822.8 | 2767.0 | 2707.9 | 2648.8 | 2694.8 |
| 75°    | 2140.1 | 2097.4 | 2113.8 | 2133.5 | 2149.9 | 2166.3 | 2143.4 | 2120.4 | 2094.1 | 2071.1 | 2113.8 |
| 77.5°  | 1631.3 | 1605.1 | 1608.3 | 1608.3 | 1611.6 | 1611.6 | 1614.9 | 1621.5 | 1624.7 | 1628.0 | 1674.0 |
| 80°    | 1329.3 | 1326.1 | 1322.8 | 1319.5 | 1312.9 | 1309.6 | 1342.5 | 1375.3 | 1408.1 | 1440.9 | 1463.9 |
| 82.5°  | 1161.9 | 1194.8 | 1175.1 | 1158.7 | 1139.0 | 1119.3 | 1148.8 | 1178.4 | 1207.9 | 1237.4 | 1227.6 |
| 85°    | 945.3  | 984.7  | 948.6  | 912.5  | 873.1  | 837.0  | 863.2  | 886.2  | 912.5  | 935.5  | 922.3  |
| 87.5°  | 374.2  | 384.0  | 324.9  | 269.1  | 210.1  | 151.0  | 239.6  | 324.9  | 413.6  | 498.9  | 512.0  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671819

CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°   | 2550.4 | 2537.2 | 2527.4 | 2524.1 | 2517.5 | 2514.3 | 2507.7 | 2501.1 | 2491.3 | 2484.7 | 2474.9 |
| 5°     | 2635.7 | 2616.0 | 2593.0 | 2560.2 | 2530.7 | 2497.8 | 2465.0 | 2435.5 | 2405.9 | 2373.1 | 2343.6 |
| 7.5°   | 2639.0 | 2593.0 | 2547.1 | 2504.4 | 2458.5 | 2415.8 | 2369.8 | 2330.4 | 2287.8 | 2245.1 | 2205.7 |
| 10°    | 2602.9 | 2547.1 | 2491.3 | 2435.5 | 2383.0 | 2327.2 | 2271.4 | 2225.4 | 2176.2 | 2126.9 | 2081.0 |
| 12.5°  | 2573.3 | 2511.0 | 2448.6 | 2383.0 | 2320.6 | 2255.0 | 2189.3 | 2143.4 | 2097.4 | 2051.4 | 2005.5 |
| 15°    | 2537.2 | 2497.8 | 2461.7 | 2402.7 | 2343.6 | 2284.5 | 2225.4 | 2163.0 | 2104.0 | 2041.6 | 1979.2 |
| 17.5°  | 2507.7 | 2497.8 | 2488.0 | 2448.6 | 2409.2 | 2366.5 | 2327.2 | 2264.8 | 2202.4 | 2136.8 | 2074.4 |
| 20°    | 2491.3 | 2504.4 | 2517.5 | 2497.8 | 2478.1 | 2455.2 | 2435.5 | 2389.5 | 2343.6 | 2294.3 | 2248.4 |
| 22.5°  | 2511.0 | 2560.2 | 2606.2 | 2609.4 | 2616.0 | 2619.3 | 2622.6 | 2579.9 | 2537.2 | 2491.3 | 2448.6 |
| 25°    | 2556.9 | 2635.7 | 2714.5 | 2757.1 | 2799.8 | 2845.8 | 2888.4 | 2862.2 | 2835.9 | 2809.7 | 2783.4 |
| 27.5°  | 2619.3 | 2717.8 | 2816.2 | 2878.6 | 2937.7 | 3000.0 | 3062.4 | 3059.1 | 3055.8 | 3049.3 | 3046.0 |
| 30°    | 2609.4 | 2684.9 | 2760.4 | 2835.9 | 2911.4 | 2986.9 | 3062.4 | 3101.8 | 3137.9 | 3177.3 | 3216.7 |
| 32.5°  | 2665.2 | 2727.6 | 2793.2 | 2872.0 | 2950.8 | 3032.9 | 3111.6 | 3193.7 | 3272.5 | 3354.5 | 3436.6 |
| 35°    | 2750.6 | 2806.4 | 2865.5 | 2950.8 | 3039.4 | 3124.8 | 3213.4 | 3311.9 | 3413.6 | 3515.4 | 3613.8 |
| 37.5°  | 2878.6 | 2927.8 | 2980.3 | 3052.6 | 3128.0 | 3200.3 | 3275.8 | 3420.2 | 3564.6 | 3712.3 | 3856.7 |
| 40°    | 3026.3 | 3059.1 | 3091.9 | 3160.9 | 3229.8 | 3298.7 | 3367.7 | 3548.2 | 3728.7 | 3909.2 | 4089.8 |
| 42.5°  | 3239.6 | 3229.8 | 3220.0 | 3275.8 | 3334.8 | 3390.6 | 3449.7 | 3613.8 | 3777.9 | 3942.1 | 4106.2 |
| 45°    | 3466.1 | 3426.7 | 3387.3 | 3413.6 | 3443.1 | 3469.4 | 3498.9 | 3666.3 | 3833.7 | 4004.4 | 4171.8 |
| 47.5°  | 3738.6 | 3640.1 | 3541.6 | 3518.6 | 3495.7 | 3469.4 | 3446.4 | 3627.0 | 3807.5 | 3991.3 | 4171.8 |
| 50°    | 4047.1 | 3899.4 | 3755.0 | 3695.9 | 3633.5 | 3574.4 | 3512.1 | 3659.8 | 3810.8 | 3961.8 | 4109.5 |
| 52.5°  | 4368.8 | 4185.0 | 4004.4 | 3912.5 | 3820.6 | 3725.4 | 3633.5 | 3758.3 | 3886.3 | 4014.3 | 4139.0 |
| 55°    | 4644.5 | 4457.4 | 4267.0 | 4158.7 | 4050.4 | 3942.1 | 3833.7 | 3958.5 | 4083.2 | 4207.9 | 4332.7 |
| 57.5°  | 4864.4 | 4677.3 | 4490.2 | 4388.5 | 4283.4 | 4181.7 | 4076.6 | 4194.8 | 4316.2 | 4437.7 | 4555.9 |
| 60°    | 5015.4 | 4834.8 | 4654.3 | 4555.9 | 4457.4 | 4358.9 | 4260.4 | 4401.6 | 4542.7 | 4687.1 | 4828.3 |
| 62.5°  | 4936.6 | 4805.3 | 4674.0 | 4631.3 | 4588.7 | 4542.7 | 4500.1 | 4634.6 | 4765.9 | 4900.5 | 5035.1 |
| 65°    | 4647.8 | 4559.1 | 4470.5 | 4513.2 | 4559.1 | 4601.8 | 4647.8 | 4736.4 | 4825.0 | 4916.9 | 5005.5 |
| 67.5°  | 4178.4 | 4171.8 | 4162.0 | 4257.2 | 4352.3 | 4450.8 | 4546.0 | 4605.1 | 4660.9 | 4720.0 | 4779.1 |
| 70°    | 3505.5 | 3541.6 | 3574.4 | 3738.6 | 3902.7 | 4066.8 | 4230.9 | 4253.9 | 4276.9 | 4299.8 | 4322.8 |
| 72.5°  | 2744.0 | 2790.0 | 2839.2 | 3055.8 | 3269.2 | 3485.8 | 3702.5 | 3689.3 | 3676.2 | 3659.8 | 3646.7 |
| 75°    | 2159.8 | 2202.4 | 2248.4 | 2448.6 | 2648.8 | 2849.0 | 3049.3 | 2993.5 | 2941.0 | 2885.2 | 2829.4 |
| 77.5°  | 1723.2 | 1769.2 | 1818.4 | 2005.5 | 2192.6 | 2383.0 | 2570.1 | 2435.5 | 2300.9 | 2166.3 | 2031.8 |
| 80°    | 1483.6 | 1506.6 | 1526.3 | 1654.3 | 1779.0 | 1907.0 | 2035.0 | 1897.2 | 1756.0 | 1614.9 | 1477.0 |
| 82.5°  | 1217.7 | 1204.6 | 1194.8 | 1270.3 | 1345.7 | 1421.2 | 1496.7 | 1365.4 | 1234.2 | 1099.6 | 968.3  |
| 85°    | 909.2  | 896.1  | 882.9  | 922.3  | 961.7  | 1004.4 | 1043.8 | 892.8  | 741.8  | 587.5  | 436.5  |
| 87.5°  | 528.5  | 541.6  | 554.7  | 597.4  | 640.1  | 686.0  | 728.7  | 574.4  | 420.1  | 262.6  | 108.3  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P671819  
 CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 2363.3 | 2363.3 |
| 2.5°   | 2455.2 | 2438.8 |
| 5°     | 2320.6 | 2297.6 |
| 7.5°   | 2172.9 | 2143.4 |
| 10°    | 2038.3 | 1998.9 |
| 12.5°  | 1953.0 | 1903.7 |
| 15°    | 1920.2 | 1861.1 |
| 17.5°  | 2018.6 | 1962.8 |
| 20°    | 2169.6 | 2094.1 |
| 22.5°  | 2353.4 | 2261.5 |
| 25°    | 2671.8 | 2560.2 |
| 27.5°  | 2931.1 | 2816.2 |
| 30°    | 3091.9 | 2967.2 |
| 32.5°  | 3269.2 | 3105.1 |
| 35°    | 3453.0 | 3295.4 |
| 37.5°  | 3676.2 | 3498.9 |
| 40°    | 3906.0 | 3722.1 |
| 42.5°  | 3984.7 | 3866.6 |
| 45°    | 4060.2 | 3948.6 |
| 47.5°  | 4076.6 | 3984.7 |
| 50°    | 4093.0 | 4079.9 |
| 52.5°  | 4139.0 | 4135.7 |
| 55°    | 4335.9 | 4339.2 |
| 57.5°  | 4578.8 | 4598.5 |
| 60°    | 4802.0 | 4779.1 |
| 62.5°  | 4916.9 | 4798.7 |
| 65°    | 4838.1 | 4674.0 |
| 67.5°  | 4601.8 | 4424.6 |
| 70°    | 4083.2 | 3843.6 |
| 72.5°  | 3436.6 | 3226.5 |
| 75°    | 2648.8 | 2471.6 |
| 77.5°  | 1884.0 | 1736.3 |
| 80°    | 1326.1 | 1178.4 |
| 82.5°  | 850.1  | 732.0  |
| 85°    | 384.0  | 334.8  |
| 87.5°  | 108.3  | 105.0  |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |



REPORT NUMBER: P671819  
CATALOG NUMBER: CCP-SA-2C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

(END OF REPORT)