

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671820

Luminaire Tested: **CCP-SA-2D-735-U-SLR**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P671820  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2D-735-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @800mA w/ SLR distribution lens  
Light Source: (32) 3500K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9128.6 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G3

Input Watts (W): 80.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 13 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671820  
CATALOG NUMBER: CCP-SA-2D-735-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral      - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1878.3	0.0	1878.3
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	7250.3	0.0	7250.3
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	9128.6	0.0	9128.6
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	226.5	2.5
10°-20°	478.2	5.2
20°-30°	699.7	7.7
30°-40°	985.8	10.8
40°-50°	1354.6	14.8
50°-60°	1846.3	20.2
60°-70°	2020.7	22.1
70°-80°	1167.0	12.8
80°-90°	349.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9128.6	100.0
0°-180°	9128.6	100.0



REPORT NUMBER: P671820


CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	937.5	10.3			
FM (30°-60°)	3331.3	36.5			
FH (60°-80°)	2684.4	29.4			G2/5000
FVH (80°-90°)	297.1	3.3			G3/500
BL (0°-30°)	466.9	5.1	B1/500		
BM (30°-60°)	855.3	9.4	B1/1000		
BH (60°-80°)	503.4	5.5	B2/1000		G2/1000
BVH (80°-90°)	52.7	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G3**

Type IV Short





REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	3008.2	2992.0	2979.9	2967.7	2951.5	2939.4	2923.2	2907.0	2886.8	2870.6	2850.3
5°	2834.1	2785.5	2737.0	2708.6	2676.2	2647.9	2615.5	2579.1	2542.6	2502.1	2465.7
7.5°	2643.8	2583.1	2522.4	2473.8	2421.2	2372.6	2319.9	2275.4	2230.9	2186.3	2141.8
10°	2465.7	2409.0	2352.3	2291.6	2226.8	2166.1	2101.3	2040.6	1979.8	1919.1	1858.4
12.5°	2348.3	2279.5	2214.7	2145.8	2081.1	2012.2	1943.4	1886.7	1830.0	1769.3	1712.6
15°	2295.6	2230.9	2170.1	2101.3	2032.5	1963.6	1894.8	1830.0	1769.3	1704.5	1639.7
17.5°	2421.2	2328.0	2234.9	2145.8	2056.8	1967.7	1878.6	1797.6	1716.7	1635.7	1554.7
20°	2583.1	2465.7	2352.3	2243.0	2129.6	2020.3	1907.0	1793.6	1680.2	1566.9	1453.5
22.5°	2789.6	2656.0	2526.4	2384.7	2239.0	2097.3	1951.5	1809.8	1668.1	1522.3	1380.6
25°	3158.0	3000.1	2842.2	2639.8	2433.3	2230.9	2024.4	1838.1	1655.9	1469.7	1283.5
27.5°	3473.8	3259.3	3048.7	2805.8	2562.9	2319.9	2077.0	1862.4	1651.9	1437.3	1222.7
30°	3660.1	3449.5	3239.0	2943.4	2651.9	2356.4	2060.8	1821.9	1587.1	1348.2	1109.4
32.5°	3830.1	3595.3	3360.5	3036.6	2708.6	2384.7	2056.8	1793.6	1534.5	1271.3	1008.1
35°	4065.0	3805.8	3550.8	3174.2	2797.7	2421.2	2044.6	1773.4	1498.0	1226.8	951.5
37.5°	4316.0	3996.1	3680.3	3263.3	2846.3	2429.3	2012.2	1745.0	1477.8	1210.6	943.4
40°	4591.3	4202.6	3818.0	3356.4	2898.9	2437.4	1975.8	1708.6	1441.4	1170.1	902.9
42.5°	4769.4	4348.4	3927.3	3429.3	2935.3	2437.4	1939.4	1676.2	1413.0	1145.8	882.6
45°	4870.7	4461.7	4056.9	3518.4	2979.9	2441.4	1902.9	1643.8	1384.7	1121.5	862.4
47.5°	4915.2	4534.6	4154.0	3587.2	3024.4	2457.6	1890.8	1627.6	1360.4	1097.2	830.0
50°	5032.6	4696.6	4360.5	3753.2	3149.9	2542.6	1935.3	1651.9	1372.5	1089.1	805.7
52.5°	5101.4	4814.0	4526.5	3903.0	3279.5	2656.0	2032.5	1716.7	1400.9	1085.1	769.3
55°	5352.5	5077.1	4801.8	4137.8	3469.8	2805.8	2137.7	1789.6	1441.4	1089.1	740.9
57.5°	5672.3	5380.8	5093.3	4376.7	3660.1	2943.4	2226.8	1854.3	1477.8	1105.3	728.8
60°	5895.0	5611.6	5332.2	4571.0	3805.8	3044.7	2279.5	1890.8	1502.1	1109.4	720.7
62.5°	5919.3	5554.9	5194.6	4453.6	3712.7	2967.7	2226.8	1850.3	1473.7	1093.2	716.6
65°	5765.4	5340.3	4915.2	4206.7	3498.1	2789.6	2081.1	1736.9	1392.8	1044.6	700.4
67.5°	5457.7	4959.7	4461.7	3813.9	3166.1	2518.3	1870.5	1575.0	1283.5	987.9	692.3
70°	4741.1	4303.8	3870.6	3307.8	2749.1	2186.3	1623.6	1380.6	1141.7	898.8	655.9
72.5°	3979.9	3571.0	3166.1	2708.6	2255.2	1797.6	1340.1	1157.9	975.8	789.5	607.3
75°	3048.7	2741.0	2437.4	2097.3	1757.2	1413.0	1072.9	939.3	805.7	672.1	538.5
77.5°	2141.8	1975.8	1813.8	1558.8	1303.7	1048.6	793.6	704.5	615.4	526.3	437.3
80°	1453.5	1360.4	1271.3	1089.1	906.9	720.7	538.5	481.8	421.1	364.4	303.7
82.5°	902.9	898.8	890.7	765.2	639.7	514.2	388.7	340.1	295.6	247.0	198.4
85°	413.0	481.8	546.6	477.8	408.9	340.1	271.3	238.9	206.5	170.0	137.7
87.5°	129.6	157.9	182.2	174.1	162.0	153.9	141.7	121.5	101.2	81.0	60.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	2834.1	2822.0	2805.8	2789.6	2769.4	2753.2	2732.9	2712.7	2708.6	2700.5	2696.5
5°	2441.4	2417.1	2388.8	2364.5	2340.2	2311.8	2287.5	2259.2	2239.0	2214.7	2194.4
7.5°	2097.3	2056.8	2012.2	1967.7	1927.2	1886.7	1842.2	1801.7	1781.5	1761.2	1741.0
10°	1821.9	1781.5	1745.0	1704.5	1676.2	1651.9	1623.6	1595.2	1570.9	1546.6	1522.3
12.5°	1684.3	1655.9	1627.6	1599.3	1566.9	1538.5	1506.1	1473.7	1445.4	1421.1	1392.8
15°	1599.3	1558.8	1514.2	1473.7	1429.2	1388.7	1344.2	1299.7	1267.3	1238.9	1206.5
17.5°	1498.0	1437.3	1380.6	1319.9	1271.3	1222.7	1170.1	1121.5	1085.1	1044.6	1008.1
20°	1384.7	1315.8	1243.0	1174.1	1117.5	1064.8	1008.1	951.5	911.0	866.4	825.9
22.5°	1287.5	1198.4	1105.3	1012.2	951.5	890.7	825.9	765.2	728.8	688.3	651.9
25°	1182.2	1085.1	983.8	882.6	821.9	757.1	696.4	631.6	603.3	579.0	550.6
27.5°	1125.6	1028.4	927.2	830.0	773.3	712.6	655.9	595.2	574.9	550.6	530.4
30°	1012.2	919.1	821.9	724.7	684.2	647.8	607.3	566.8	558.7	554.7	546.6
32.5°	911.0	813.8	716.6	619.5	583.0	546.6	510.1	473.7	469.7	461.6	457.5
35°	858.3	765.2	668.0	574.9	542.5	506.1	473.7	437.3	429.2	417.0	408.9
37.5°	846.2	749.0	647.8	550.6	518.2	485.9	449.4	417.0	408.9	400.8	392.7
40°	813.8	720.7	631.6	538.5	506.1	473.7	437.3	404.9	396.8	388.7	380.6
42.5°	789.5	700.4	607.3	514.2	485.9	457.5	425.1	396.8	388.7	380.6	368.4
45°	769.3	676.1	579.0	485.9	465.6	445.4	421.1	400.8	392.7	380.6	372.5
47.5°	736.9	647.8	554.7	461.6	441.3	425.1	404.9	384.6	376.5	368.4	360.3
50°	712.6	619.5	526.3	433.2	417.0	400.8	384.6	368.4	368.4	372.5	372.5
52.5°	680.2	591.1	502.0	413.0	396.8	380.6	364.4	348.2	352.2	356.3	360.3
55°	651.9	566.8	477.8	388.7	372.5	356.3	336.0	319.9	323.9	327.9	332.0
57.5°	639.7	550.6	461.6	372.5	356.3	336.0	319.9	299.6	299.6	299.6	299.6
60°	631.6	538.5	449.4	356.3	336.0	319.9	299.6	279.4	275.3	275.3	271.3
62.5°	627.6	534.4	445.4	352.2	327.9	307.7	283.4	259.1	255.1	251.0	247.0
65°	611.4	526.3	437.3	348.2	319.9	295.6	267.2	238.9	234.8	234.8	230.8
67.5°	607.3	518.2	433.2	344.1	315.8	283.4	255.1	222.7	218.6	214.6	210.5
70°	574.9	498.0	417.0	336.0	303.7	275.3	242.9	210.5	206.5	198.4	194.3
72.5°	534.4	465.6	392.7	319.9	287.5	255.1	222.7	190.3	186.2	182.2	174.1
75°	473.7	408.9	344.1	279.4	251.0	226.7	198.4	170.0	166.0	162.0	153.9
77.5°	388.7	336.0	287.5	234.8	214.6	194.3	174.1	153.9	149.8	145.8	137.7
80°	275.3	242.9	214.6	182.2	170.0	153.9	141.7	125.5	125.5	121.5	121.5
82.5°	182.2	166.0	149.8	133.6	125.5	117.4	109.3	101.2	101.2	97.2	97.2
85°	129.6	121.5	109.3	101.2	97.2	89.1	85.0	76.9	76.9	76.9	76.9
87.5°	60.7	60.7	56.7	56.7	52.6	52.6	48.6	44.5	44.5	44.5	44.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	2688.4	2676.2	2664.1	2647.9	2635.7	2619.5	2599.3	2583.1	2562.9	2562.9	2558.8
5°	2170.1	2158.0	2145.8	2129.6	2117.5	2101.3	2089.2	2073.0	2056.8	2056.8	2052.7
7.5°	1720.7	1696.4	1672.1	1643.8	1619.5	1603.3	1587.1	1566.9	1550.7	1538.5	1526.4
10°	1498.0	1473.7	1445.4	1421.1	1392.8	1372.5	1352.3	1328.0	1307.7	1291.6	1275.4
12.5°	1364.4	1336.1	1307.7	1279.4	1251.1	1222.7	1198.4	1170.1	1141.7	1121.5	1101.3
15°	1174.1	1145.8	1117.5	1089.1	1060.8	1028.4	996.0	959.6	927.2	911.0	898.8
17.5°	967.7	939.3	906.9	878.6	846.2	821.9	797.6	773.3	749.0	732.8	720.7
20°	781.4	749.0	716.6	684.2	651.9	635.7	619.5	603.3	587.1	574.9	566.8
22.5°	611.4	591.1	574.9	554.7	534.4	522.3	514.2	502.0	489.9	489.9	489.9
25°	522.3	510.1	502.0	489.9	477.8	473.7	469.7	461.6	457.5	453.5	453.5
27.5°	506.1	493.9	481.8	469.7	457.5	453.5	449.4	441.3	437.3	437.3	437.3
30°	538.5	534.4	530.4	526.3	522.3	514.2	502.0	493.9	481.8	473.7	465.6
32.5°	449.4	445.4	445.4	441.3	437.3	445.4	449.4	457.5	461.6	465.6	469.7
35°	396.8	388.7	380.6	372.5	364.4	360.3	356.3	352.2	348.2	348.2	344.1
37.5°	384.6	376.5	368.4	360.3	352.2	348.2	344.1	340.1	336.0	336.0	332.0
40°	372.5	364.4	360.3	352.2	344.1	340.1	336.0	327.9	323.9	319.9	319.9
42.5°	360.3	356.3	348.2	344.1	336.0	332.0	327.9	319.9	315.8	311.8	307.7
45°	360.3	352.2	344.1	336.0	327.9	323.9	315.8	311.8	303.7	303.7	299.6
47.5°	352.2	344.1	336.0	327.9	319.9	315.8	307.7	303.7	295.6	291.5	287.5
50°	372.5	360.3	344.1	332.0	315.8	311.8	303.7	299.6	291.5	287.5	283.4
52.5°	364.4	352.2	336.0	323.9	307.7	299.6	295.6	287.5	279.4	275.3	271.3
55°	336.0	323.9	315.8	303.7	291.5	283.4	275.3	267.2	259.1	255.1	255.1
57.5°	299.6	295.6	291.5	287.5	283.4	275.3	267.2	255.1	247.0	242.9	238.9
60°	267.2	271.3	275.3	279.4	283.4	271.3	259.1	247.0	234.8	230.8	226.7
62.5°	242.9	251.0	259.1	263.2	271.3	259.1	247.0	234.8	222.7	218.6	214.6
65°	226.7	230.8	230.8	234.8	234.8	226.7	222.7	214.6	206.5	202.4	202.4
67.5°	206.5	206.5	206.5	202.4	202.4	198.4	198.4	194.3	190.3	186.2	186.2
70°	186.2	186.2	186.2	182.2	182.2	178.1	178.1	174.1	170.0	170.0	166.0
72.5°	170.0	170.0	166.0	166.0	162.0	162.0	162.0	157.9	157.9	153.9	153.9
75°	149.8	149.8	145.8	145.8	141.7	141.7	141.7	137.7	137.7	137.7	133.6
77.5°	133.6	133.6	129.6	129.6	125.5	125.5	125.5	121.5	121.5	117.4	117.4
80°	117.4	117.4	113.4	113.4	109.3	109.3	105.3	105.3	101.2	101.2	97.2
82.5°	93.1	93.1	93.1	93.1	93.1	89.1	89.1	85.0	81.0	81.0	76.9
85°	76.9	76.9	76.9	72.9	72.9	72.9	68.8	68.8	64.8	60.7	60.7
87.5°	44.5	44.5	44.5	40.5	40.5	40.5	40.5	40.5	40.5	40.5	36.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	2558.8	2554.8	2538.6	2522.4	2538.6	2554.8	2554.8	2554.8	2550.7	2550.7	2550.7
5°	2052.7	2048.7	2040.6	2032.5	2032.5	2028.4	2036.5	2044.6	2052.7	2060.8	2068.9
7.5°	1510.2	1498.0	1485.9	1473.7	1481.8	1485.9	1498.0	1506.1	1518.3	1526.4	1546.6
10°	1259.2	1243.0	1230.8	1218.7	1210.6	1202.5	1194.4	1190.3	1182.2	1174.1	1182.2
12.5°	1077.0	1056.7	1036.5	1012.2	1008.1	1004.1	996.0	987.9	979.8	971.7	967.7
15°	882.6	866.4	858.3	846.2	830.0	813.8	805.7	801.7	793.6	785.5	781.4
17.5°	704.5	688.3	676.1	664.0	659.9	651.9	651.9	651.9	651.9	651.9	651.9
20°	554.7	542.5	542.5	538.5	538.5	534.4	538.5	542.5	542.5	546.6	550.6
22.5°	485.9	485.9	481.8	477.8	481.8	481.8	485.9	489.9	493.9	498.0	502.0
25°	449.4	445.4	449.4	453.5	453.5	453.5	457.5	457.5	461.6	461.6	461.6
27.5°	433.2	433.2	437.3	437.3	441.3	441.3	441.3	437.3	437.3	433.2	433.2
30°	457.5	449.4	449.4	449.4	445.4	441.3	437.3	437.3	433.2	429.2	425.1
32.5°	473.7	477.8	473.7	465.6	461.6	453.5	449.4	441.3	437.3	429.2	421.1
35°	344.1	340.1	348.2	352.2	356.3	360.3	364.4	368.4	368.4	372.5	372.5
37.5°	332.0	327.9	327.9	323.9	323.9	323.9	323.9	323.9	319.9	319.9	323.9
40°	315.8	311.8	311.8	307.7	307.7	303.7	303.7	303.7	303.7	303.7	303.7
42.5°	303.7	299.6	299.6	299.6	299.6	295.6	295.6	291.5	291.5	287.5	287.5
45°	299.6	295.6	291.5	287.5	287.5	283.4	283.4	283.4	279.4	279.4	279.4
47.5°	283.4	279.4	279.4	275.3	275.3	271.3	271.3	271.3	267.2	267.2	267.2
50°	275.3	271.3	271.3	267.2	267.2	263.2	263.2	263.2	259.1	259.1	259.1
52.5°	263.2	259.1	259.1	259.1	255.1	251.0	251.0	251.0	247.0	247.0	247.0
55°	251.0	247.0	247.0	247.0	242.9	238.9	238.9	238.9	234.8	234.8	234.8
57.5°	234.8	230.8	230.8	226.7	226.7	226.7	226.7	226.7	222.7	222.7	222.7
60°	222.7	218.6	218.6	214.6	214.6	210.5	210.5	210.5	210.5	210.5	210.5
62.5°	210.5	206.5	202.4	198.4	202.4	202.4	202.4	202.4	198.4	198.4	198.4
65°	198.4	194.3	190.3	186.2	186.2	186.2	186.2	186.2	186.2	186.2	186.2
67.5°	182.2	178.1	174.1	170.0	174.1	174.1	174.1	174.1	174.1	174.1	174.1
70°	166.0	162.0	162.0	157.9	157.9	153.9	153.9	157.9	157.9	157.9	157.9
72.5°	149.8	145.8	145.8	141.7	141.7	141.7	141.7	141.7	141.7	141.7	141.7
75°	133.6	129.6	129.6	125.5	125.5	125.5	125.5	125.5	125.5	125.5	125.5
77.5°	113.4	109.3	109.3	109.3	109.3	109.3	109.3	113.4	113.4	113.4	113.4
80°	97.2	93.1	93.1	93.1	93.1	93.1	93.1	93.1	93.1	93.1	93.1
82.5°	76.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9
85°	56.7	52.6	52.6	52.6	56.7	56.7	56.7	56.7	56.7	56.7	56.7
87.5°	36.4	32.4	32.4	32.4	36.4	36.4	36.4	36.4	32.4	32.4	32.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	2550.7	2550.7	2550.7	2546.7	2542.6	2538.6	2534.5	2546.7	2554.8	2566.9	2575.0
5°	2073.0	2081.1	2085.1	2097.3	2109.4	2121.5	2133.7	2141.8	2149.9	2153.9	2162.0
7.5°	1562.8	1583.1	1599.3	1615.5	1631.6	1643.8	1660.0	1672.1	1684.3	1696.4	1708.6
10°	1186.3	1194.4	1198.4	1214.6	1226.8	1243.0	1255.1	1267.3	1279.4	1287.5	1299.7
12.5°	963.6	955.5	951.5	951.5	951.5	951.5	951.5	959.6	967.7	975.8	983.8
15°	777.4	773.3	769.3	765.2	761.2	753.1	749.0	757.1	765.2	773.3	781.4
17.5°	651.9	651.9	651.9	647.8	643.8	639.7	635.7	639.7	643.8	643.8	647.8
20°	558.7	562.8	566.8	570.9	570.9	574.9	574.9	579.0	583.0	583.0	587.1
22.5°	502.0	506.1	506.1	506.1	510.1	510.1	510.1	514.2	518.2	522.3	526.3
25°	457.5	457.5	453.5	453.5	457.5	457.5	457.5	457.5	461.6	461.6	461.6
27.5°	433.2	429.2	429.2	429.2	429.2	425.1	425.1	425.1	425.1	425.1	425.1
30°	421.1	417.0	413.0	408.9	408.9	404.9	400.8	400.8	400.8	400.8	400.8
32.5°	417.0	408.9	400.8	396.8	396.8	392.7	388.7	384.6	384.6	380.6	376.5
35°	372.5	368.4	368.4	364.4	360.3	356.3	352.2	352.2	352.2	348.2	348.2
37.5°	323.9	327.9	327.9	327.9	332.0	332.0	332.0	332.0	336.0	336.0	336.0
40°	303.7	303.7	303.7	307.7	311.8	311.8	315.8	315.8	319.9	319.9	319.9
42.5°	287.5	283.4	283.4	287.5	287.5	291.5	291.5	295.6	299.6	299.6	303.7
45°	279.4	275.3	275.3	275.3	275.3	271.3	271.3	275.3	279.4	283.4	287.5
47.5°	263.2	263.2	259.1	259.1	259.1	259.1	259.1	259.1	263.2	263.2	263.2
50°	255.1	255.1	251.0	251.0	251.0	251.0	251.0	251.0	251.0	251.0	251.0
52.5°	247.0	242.9	242.9	242.9	242.9	238.9	238.9	238.9	238.9	238.9	238.9
55°	234.8	230.8	230.8	230.8	230.8	230.8	230.8	230.8	234.8	234.8	234.8
57.5°	222.7	218.6	218.6	218.6	222.7	222.7	222.7	222.7	226.7	226.7	226.7
60°	210.5	210.5	210.5	210.5	210.5	210.5	210.5	214.6	214.6	218.6	218.6
62.5°	198.4	198.4	198.4	198.4	202.4	202.4	202.4	202.4	206.5	206.5	206.5
65°	186.2	186.2	186.2	186.2	190.3	190.3	190.3	190.3	190.3	190.3	190.3
67.5°	174.1	174.1	174.1	174.1	174.1	174.1	174.1	178.1	178.1	182.2	182.2
70°	157.9	153.9	153.9	157.9	157.9	162.0	162.0	166.0	166.0	170.0	170.0
72.5°	141.7	141.7	141.7	141.7	141.7	141.7	141.7	145.8	149.8	149.8	153.9
75°	125.5	125.5	125.5	125.5	129.6	129.6	129.6	133.6	133.6	137.7	137.7
77.5°	113.4	109.3	109.3	109.3	113.4	113.4	113.4	117.4	117.4	121.5	121.5
80°	93.1	93.1	93.1	93.1	97.2	97.2	97.2	97.2	101.2	101.2	101.2
82.5°	76.9	76.9	76.9	76.9	76.9	76.9	76.9	76.9	81.0	81.0	81.0
85°	56.7	56.7	56.7	56.7	60.7	60.7	60.7	60.7	60.7	60.7	60.7
87.5°	36.4	36.4	36.4	36.4	36.4	36.4	36.4	36.4	40.5	40.5	40.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	2575.0	2575.0	2575.0	2575.0	2583.1	2587.2	2595.3	2599.3	2595.3	2591.2	2583.1
5°	2166.1	2170.1	2170.1	2174.2	2174.2	2174.2	2174.2	2174.2	2182.3	2190.4	2198.5
7.5°	1712.6	1716.7	1720.7	1724.8	1724.8	1724.8	1720.7	1720.7	1724.8	1724.8	1728.8
10°	1311.8	1328.0	1340.1	1352.3	1344.2	1332.0	1323.9	1311.8	1311.8	1311.8	1307.7
12.5°	991.9	996.0	1004.1	1008.1	1004.1	1004.1	1000.0	996.0	1000.0	1008.1	1012.2
15°	785.5	785.5	789.5	789.5	793.6	797.6	797.6	801.7	809.8	813.8	821.9
17.5°	651.9	655.9	655.9	659.9	659.9	664.0	664.0	664.0	672.1	680.2	692.3
20°	587.1	587.1	587.1	587.1	587.1	583.0	583.0	579.0	583.0	591.1	595.2
22.5°	526.3	530.4	530.4	530.4	526.3	522.3	514.2	510.1	510.1	514.2	514.2
25°	461.6	457.5	457.5	453.5	453.5	457.5	457.5	457.5	461.6	461.6	465.6
27.5°	425.1	421.1	421.1	417.0	417.0	421.1	421.1	421.1	421.1	421.1	421.1
30°	396.8	396.8	392.7	388.7	392.7	392.7	396.8	396.8	400.8	400.8	404.9
32.5°	376.5	372.5	372.5	368.4	372.5	372.5	376.5	376.5	380.6	384.6	384.6
35°	348.2	348.2	348.2	348.2	348.2	348.2	344.1	344.1	344.1	344.1	344.1
37.5°	332.0	332.0	327.9	323.9	323.9	323.9	323.9	323.9	319.9	315.8	311.8
40°	319.9	315.8	315.8	311.8	307.7	307.7	303.7	299.6	299.6	295.6	295.6
42.5°	303.7	299.6	299.6	295.6	291.5	291.5	287.5	283.4	283.4	283.4	279.4
45°	283.4	283.4	279.4	275.3	275.3	275.3	271.3	271.3	271.3	271.3	267.2
47.5°	263.2	263.2	259.1	259.1	259.1	259.1	255.1	255.1	255.1	255.1	255.1
50°	251.0	251.0	251.0	251.0	251.0	251.0	247.0	247.0	247.0	247.0	247.0
52.5°	238.9	238.9	238.9	238.9	238.9	238.9	238.9	238.9	238.9	238.9	238.9
55°	234.8	234.8	234.8	234.8	234.8	234.8	230.8	230.8	230.8	234.8	234.8
57.5°	226.7	226.7	222.7	222.7	222.7	222.7	222.7	222.7	222.7	222.7	222.7
60°	218.6	218.6	218.6	218.6	218.6	218.6	218.6	218.6	218.6	218.6	218.6
62.5°	206.5	206.5	206.5	206.5	206.5	210.5	210.5	210.5	210.5	210.5	206.5
65°	190.3	194.3	194.3	194.3	194.3	194.3	194.3	194.3	194.3	194.3	194.3
67.5°	182.2	182.2	182.2	182.2	182.2	182.2	182.2	182.2	182.2	182.2	182.2
70°	170.0	170.0	166.0	166.0	166.0	170.0	170.0	170.0	170.0	170.0	170.0
72.5°	153.9	153.9	153.9	153.9	153.9	153.9	153.9	153.9	153.9	157.9	157.9
75°	137.7	137.7	137.7	137.7	137.7	137.7	137.7	137.7	137.7	137.7	137.7
77.5°	121.5	121.5	117.4	117.4	117.4	121.5	121.5	121.5	121.5	125.5	125.5
80°	101.2	101.2	101.2	101.2	101.2	101.2	101.2	101.2	101.2	105.3	105.3
82.5°	81.0	81.0	81.0	81.0	81.0	81.0	81.0	81.0	81.0	85.0	85.0
85°	60.7	64.8	64.8	64.8	64.8	64.8	64.8	64.8	64.8	68.8	68.8
87.5°	40.5	40.5	40.5	40.5	40.5	40.5	36.4	36.4	36.4	36.4	32.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	2579.1	2583.1	2587.2	2587.2	2591.2	2595.3	2595.3	2611.4	2627.6	2635.7	2643.8
5°	2206.6	2202.5	2202.5	2198.5	2194.4	2206.6	2218.7	2243.0	2267.3	2271.4	2279.5
7.5°	1728.8	1732.9	1736.9	1736.9	1741.0	1728.8	1712.6	1716.7	1720.7	1741.0	1757.2
10°	1307.7	1311.8	1315.8	1315.8	1319.9	1315.8	1307.7	1319.9	1332.0	1348.2	1368.5
12.5°	1016.2	1028.4	1040.5	1048.6	1060.8	1068.9	1072.9	1089.1	1101.3	1121.5	1141.7
15°	830.0	838.1	846.2	854.3	862.4	870.5	878.6	894.8	911.0	935.3	959.6
17.5°	700.4	700.4	704.5	704.5	704.5	712.6	720.7	728.8	732.8	757.1	781.4
20°	599.2	595.2	591.1	587.1	583.0	591.1	595.2	599.2	603.3	619.5	631.6
22.5°	514.2	514.2	518.2	518.2	518.2	514.2	506.1	510.1	510.1	518.2	530.4
25°	465.6	465.6	465.6	461.6	461.6	465.6	469.7	469.7	465.6	469.7	473.7
27.5°	421.1	425.1	425.1	429.2	429.2	433.2	433.2	433.2	433.2	437.3	441.3
30°	404.9	404.9	408.9	408.9	408.9	413.0	417.0	417.0	417.0	421.1	429.2
32.5°	388.7	392.7	396.8	400.8	404.9	408.9	408.9	413.0	413.0	417.0	421.1
35°	344.1	340.1	340.1	336.0	332.0	332.0	332.0	332.0	327.9	332.0	332.0
37.5°	307.7	307.7	307.7	303.7	303.7	307.7	307.7	307.7	307.7	311.8	311.8
40°	291.5	291.5	291.5	291.5	291.5	291.5	291.5	295.6	295.6	299.6	303.7
42.5°	279.4	279.4	279.4	279.4	279.4	283.4	283.4	283.4	283.4	287.5	287.5
45°	267.2	267.2	267.2	267.2	267.2	267.2	267.2	271.3	271.3	275.3	279.4
47.5°	255.1	255.1	255.1	255.1	255.1	259.1	263.2	263.2	263.2	267.2	267.2
50°	247.0	247.0	247.0	247.0	247.0	251.0	251.0	255.1	255.1	259.1	263.2
52.5°	238.9	238.9	238.9	238.9	238.9	242.9	242.9	247.0	247.0	251.0	255.1
55°	234.8	234.8	234.8	230.8	230.8	234.8	234.8	238.9	238.9	242.9	242.9
57.5°	222.7	222.7	222.7	222.7	222.7	222.7	222.7	226.7	226.7	230.8	234.8
60°	218.6	218.6	214.6	214.6	210.5	214.6	214.6	218.6	218.6	222.7	222.7
62.5°	206.5	206.5	206.5	202.4	202.4	206.5	206.5	206.5	206.5	210.5	214.6
65°	194.3	194.3	194.3	190.3	190.3	194.3	194.3	194.3	194.3	198.4	202.4
67.5°	182.2	182.2	182.2	178.1	178.1	178.1	178.1	182.2	182.2	186.2	190.3
70°	170.0	170.0	170.0	166.0	166.0	166.0	162.0	166.0	170.0	174.1	174.1
72.5°	157.9	157.9	157.9	153.9	153.9	153.9	149.8	153.9	153.9	157.9	157.9
75°	137.7	137.7	137.7	137.7	137.7	137.7	133.6	133.6	133.6	137.7	137.7
77.5°	125.5	125.5	125.5	121.5	121.5	121.5	117.4	117.4	117.4	121.5	121.5
80°	105.3	105.3	105.3	101.2	101.2	101.2	97.2	97.2	97.2	101.2	101.2
82.5°	85.0	85.0	85.0	81.0	81.0	81.0	76.9	76.9	76.9	81.0	81.0
85°	68.8	68.8	68.8	68.8	68.8	68.8	64.8	64.8	64.8	68.8	72.9
87.5°	32.4	32.4	36.4	36.4	36.4	36.4	32.4	32.4	28.3	28.3	32.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	2651.9	2660.0	2680.3	2696.5	2716.7	2732.9	2745.1	2761.3	2773.4	2785.5	2793.6
5°	2283.5	2287.5	2307.8	2328.0	2344.2	2364.5	2392.8	2421.2	2449.5	2477.8	2498.1
7.5°	1777.4	1793.6	1817.9	1846.2	1870.5	1894.8	1923.2	1955.6	1983.9	2012.2	2040.6
10°	1384.7	1400.9	1425.2	1449.5	1469.7	1494.0	1526.4	1558.8	1591.2	1623.6	1655.9
12.5°	1162.0	1182.2	1210.6	1238.9	1263.2	1291.6	1332.0	1368.5	1409.0	1445.4	1485.9
15°	979.8	1004.1	1040.5	1081.0	1117.5	1153.9	1194.4	1234.9	1271.3	1311.8	1352.3
17.5°	805.7	830.0	862.4	898.8	931.2	963.6	1012.2	1056.7	1105.3	1149.8	1194.4
20°	647.8	659.9	692.3	724.7	757.1	789.5	825.9	862.4	898.8	935.3	991.9
22.5°	538.5	546.6	562.8	574.9	591.1	603.3	639.7	676.1	708.5	745.0	797.6
25°	473.7	477.8	489.9	498.0	510.1	518.2	542.5	562.8	587.1	607.3	655.9
27.5°	441.3	445.4	449.4	453.5	457.5	461.6	477.8	493.9	506.1	522.3	566.8
30°	433.2	437.3	449.4	457.5	469.7	477.8	485.9	493.9	502.0	510.1	538.5
32.5°	425.1	429.2	429.2	425.1	425.1	421.1	429.2	433.2	441.3	445.4	469.7
35°	336.0	336.0	340.1	344.1	348.2	352.2	364.4	372.5	384.6	392.7	413.0
37.5°	315.8	315.8	319.9	327.9	332.0	336.0	344.1	352.2	360.3	368.4	388.7
40°	303.7	307.7	311.8	315.8	319.9	323.9	332.0	336.0	344.1	348.2	364.4
42.5°	291.5	291.5	295.6	303.7	307.7	311.8	319.9	323.9	332.0	336.0	352.2
45°	283.4	287.5	291.5	295.6	295.6	299.6	307.7	315.8	319.9	327.9	344.1
47.5°	271.3	271.3	279.4	283.4	291.5	295.6	303.7	307.7	315.8	319.9	336.0
50°	263.2	267.2	275.3	279.4	287.5	291.5	303.7	311.8	323.9	332.0	340.1
52.5°	255.1	259.1	267.2	271.3	279.4	283.4	299.6	315.8	327.9	344.1	344.1
55°	247.0	247.0	255.1	267.2	275.3	283.4	291.5	303.7	311.8	319.9	319.9
57.5°	234.8	238.9	247.0	259.1	267.2	275.3	283.4	291.5	295.6	303.7	299.6
60°	226.7	226.7	238.9	251.0	263.2	275.3	275.3	275.3	271.3	271.3	271.3
62.5°	214.6	218.6	234.8	255.1	271.3	287.5	275.3	263.2	251.0	238.9	242.9
65°	206.5	210.5	218.6	230.8	238.9	247.0	238.9	234.8	226.7	218.6	222.7
67.5°	190.3	194.3	198.4	198.4	202.4	202.4	202.4	202.4	202.4	202.4	206.5
70°	178.1	178.1	178.1	182.2	182.2	182.2	182.2	182.2	182.2	182.2	186.2
72.5°	162.0	162.0	162.0	162.0	162.0	162.0	162.0	162.0	162.0	162.0	166.0
75°	141.7	141.7	141.7	141.7	141.7	141.7	141.7	141.7	141.7	141.7	145.8
77.5°	125.5	125.5	125.5	125.5	125.5	125.5	125.5	125.5	121.5	121.5	125.5
80°	105.3	105.3	105.3	105.3	101.2	101.2	101.2	101.2	101.2	101.2	105.3
82.5°	85.0	85.0	85.0	85.0	81.0	81.0	81.0	81.0	76.9	76.9	81.0
85°	76.9	81.0	81.0	85.0	85.0	85.0	81.0	76.9	72.9	68.8	68.8
87.5°	32.4	32.4	32.4	32.4	28.3	28.3	28.3	28.3	28.3	28.3	28.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	2805.8	2813.9	2822.0	2834.1	2850.3	2862.5	2874.6	2898.9	2927.3	2951.5	2975.8
5°	2518.3	2538.6	2558.8	2583.1	2607.4	2627.6	2651.9	2700.5	2749.1	2793.6	2842.2
7.5°	2064.9	2093.2	2117.5	2158.0	2194.4	2234.9	2271.4	2332.1	2388.8	2449.5	2506.2
10°	1688.3	1720.7	1753.1	1805.7	1862.4	1915.1	1967.7	2016.3	2068.9	2117.5	2166.1
12.5°	1526.4	1562.8	1603.3	1635.7	1672.1	1704.5	1736.9	1793.6	1850.3	1907.0	1963.6
15°	1392.8	1433.3	1473.7	1514.2	1550.7	1591.2	1627.6	1676.2	1728.8	1777.4	1826.0
17.5°	1238.9	1279.4	1323.9	1368.5	1413.0	1457.6	1502.1	1570.9	1639.7	1704.5	1773.4
20°	1044.6	1101.3	1153.9	1214.6	1275.4	1336.1	1396.8	1469.7	1542.6	1611.4	1684.3
22.5°	850.2	902.9	955.5	1028.4	1101.3	1170.1	1243.0	1340.1	1433.3	1530.4	1623.6
25°	708.5	757.1	805.7	886.7	963.6	1044.6	1121.5	1238.9	1352.3	1469.7	1583.1
27.5°	611.4	655.9	700.4	785.5	870.5	951.5	1036.5	1166.0	1291.6	1421.1	1546.6
30°	566.8	595.2	623.5	704.5	785.5	862.4	943.4	1068.9	1194.4	1319.9	1445.4
32.5°	493.9	518.2	542.5	615.4	688.3	757.1	830.0	959.6	1085.1	1214.6	1340.1
35°	437.3	457.5	477.8	546.6	611.4	680.2	745.0	874.5	1004.1	1133.7	1263.2
37.5°	404.9	425.1	441.3	502.0	566.8	627.6	688.3	817.8	943.4	1072.9	1198.4
40°	380.6	392.7	408.9	469.7	526.3	587.1	643.8	761.2	882.6	1000.0	1117.5
42.5°	364.4	380.6	392.7	445.4	502.0	554.7	607.3	720.7	834.0	943.4	1056.7
45°	360.3	376.5	392.7	437.3	481.8	522.3	566.8	676.1	785.5	894.8	1004.1
47.5°	352.2	364.4	380.6	417.0	449.4	485.9	518.2	627.6	736.9	842.1	951.5
50°	348.2	352.2	360.3	392.7	425.1	457.5	489.9	599.2	708.5	817.8	927.2
52.5°	344.1	344.1	344.1	372.5	400.8	425.1	453.5	562.8	676.1	785.5	894.8
55°	319.9	315.8	315.8	344.1	368.4	396.8	421.1	530.4	639.7	745.0	854.3
57.5°	295.6	291.5	287.5	311.8	336.0	360.3	384.6	493.9	607.3	716.6	825.9
60°	271.3	267.2	267.2	291.5	311.8	336.0	356.3	469.7	579.0	692.3	801.7
62.5°	242.9	247.0	247.0	267.2	291.5	311.8	332.0	445.4	562.8	676.1	789.5
65°	222.7	226.7	226.7	251.0	275.3	299.6	323.9	433.2	546.6	655.9	765.2
67.5°	206.5	210.5	210.5	238.9	263.2	291.5	315.8	413.0	514.2	611.4	708.5
70°	190.3	190.3	194.3	222.7	251.0	279.4	307.7	392.7	477.8	558.7	643.8
72.5°	170.0	174.1	178.1	206.5	230.8	259.1	283.4	360.3	437.3	514.2	591.1
75°	149.8	153.9	157.9	182.2	206.5	230.8	255.1	327.9	396.8	469.7	538.5
77.5°	133.6	137.7	141.7	162.0	182.2	202.4	222.7	275.3	332.0	384.6	437.3
80°	109.3	109.3	113.4	129.6	145.8	157.9	174.1	210.5	247.0	279.4	315.8
82.5°	81.0	85.0	85.0	97.2	105.3	117.4	125.5	145.8	162.0	182.2	198.4
85°	68.8	64.8	64.8	72.9	76.9	85.0	89.1	101.2	109.3	121.5	129.6
87.5°	28.3	24.3	24.3	28.3	36.4	40.5	44.5	44.5	48.6	48.6	48.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	2988.0	2996.1	3008.2	3016.3	3036.6	3052.8	3073.0	3089.2	3101.3	3121.6	3113.5
5°	2878.7	2915.1	2951.5	2988.0	3016.3	3044.7	3069.0	3097.3	3129.7	3190.4	3206.6
7.5°	2554.8	2603.4	2647.9	2696.5	2753.2	2809.8	2866.5	2923.2	2975.8	3052.8	3101.3
10°	2234.9	2303.7	2368.5	2437.4	2490.0	2542.6	2591.2	2643.8	2716.7	2793.6	2882.7
12.5°	2032.5	2101.3	2170.1	2239.0	2315.9	2388.8	2465.7	2538.6	2607.4	2668.1	2769.4
15°	1898.9	1975.8	2048.7	2121.5	2214.7	2303.7	2396.9	2485.9	2587.2	2668.1	2737.0
17.5°	1866.5	1959.6	2048.7	2141.8	2239.0	2336.1	2433.3	2530.5	2631.7	2753.2	2842.2
20°	1809.8	1935.3	2060.8	2186.3	2311.8	2433.3	2558.8	2680.3	2813.9	2959.6	3000.1
22.5°	1777.4	1927.2	2081.1	2230.9	2400.9	2575.0	2745.1	2915.1	3056.8	3166.1	3287.6
25°	1773.4	1959.6	2149.9	2336.1	2550.7	2761.3	2975.8	3186.4	3368.6	3477.9	3575.1
27.5°	1769.3	1996.0	2218.7	2441.4	2704.6	2963.7	3226.9	3486.0	3656.0	3813.9	3894.9
30°	1720.7	1992.0	2267.3	2538.6	2834.1	3129.7	3425.2	3720.8	3894.9	4004.2	4044.7
32.5°	1660.0	1979.8	2299.7	2619.5	2955.6	3291.6	3623.6	3959.7	4097.3	4190.5	4158.1
35°	1611.4	1963.6	2311.8	2660.0	3016.3	3376.7	3733.0	4089.2	4287.6	4417.2	4364.6
37.5°	1566.9	1935.3	2303.7	2672.2	3089.2	3506.2	3923.2	4340.3	4530.6	4668.2	4607.5
40°	1514.2	1907.0	2303.7	2696.5	3174.2	3647.9	4125.7	4599.4	4846.4	4963.8	4870.7
42.5°	1469.7	1878.6	2291.6	2700.5	3210.7	3720.8	4231.0	4741.1	5016.4	5182.4	5065.0
45°	1413.0	1821.9	2226.8	2635.7	3198.5	3761.3	4320.0	4882.8	5202.7	5332.2	5170.3
47.5°	1352.3	1757.2	2158.0	2558.8	3158.0	3757.2	4356.5	4955.7	5251.2	5405.1	5255.3
50°	1332.0	1736.9	2137.7	2542.6	3190.4	3842.3	4490.1	5137.9	5352.5	5478.0	5279.6
52.5°	1328.0	1757.2	2190.4	2619.5	3271.4	3919.2	4571.0	5218.8	5392.9	5526.6	5348.4
55°	1315.8	1781.5	2243.0	2704.6	3384.8	4069.0	4749.2	5429.4	5603.5	5700.7	5567.0
57.5°	1328.0	1830.0	2328.0	2830.1	3530.5	4231.0	4931.4	5631.8	5842.4	5911.2	5882.8
60°	1336.1	1870.5	2400.9	2935.3	3619.6	4303.8	4988.1	5672.3	5890.9	6061.0	6093.4
62.5°	1315.8	1842.2	2364.5	2890.8	3510.3	4129.7	4749.2	5368.7	5729.0	5980.0	6125.8
65°	1255.1	1741.0	2230.9	2716.7	3287.6	3862.5	4433.4	5004.3	5384.8	5757.3	5874.7
67.5°	1121.5	1534.5	1947.5	2360.4	2858.4	3356.4	3850.4	4348.4	4826.1	5186.5	5348.4
70°	971.7	1295.6	1623.6	1947.5	2400.9	2854.4	3307.8	3761.3	4182.4	4579.1	4733.0
72.5°	846.2	1097.2	1352.3	1603.3	1927.2	2247.1	2571.0	2890.8	3388.8	3785.6	3935.4
75°	720.7	902.9	1081.0	1263.2	1485.9	1708.6	1927.2	2149.9	2502.1	2858.4	3008.2
77.5°	554.7	676.1	793.6	911.0	1064.8	1214.6	1368.5	1518.3	1765.3	2032.5	2109.4
80°	384.6	453.5	518.2	587.1	708.5	830.0	951.5	1072.9	1234.9	1384.7	1502.1
82.5°	238.9	283.4	323.9	364.4	461.6	558.7	651.9	749.0	813.8	821.9	939.3
85°	153.9	182.2	206.5	230.8	287.5	348.2	404.9	461.6	413.0	384.6	457.5
87.5°	60.7	76.9	89.1	101.2	97.2	93.1	89.1	85.0	72.9	64.8	81.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	3121.6	3133.7	3145.9	3154.0	3166.1	3170.2	3174.2	3174.2	3178.3	3182.3	3190.4
5°	3271.4	3295.7	3320.0	3340.2	3364.5	3384.8	3401.0	3421.2	3437.4	3437.4	3433.3
7.5°	3145.9	3206.6	3267.3	3328.1	3388.8	3433.3	3473.8	3518.4	3558.9	3567.0	3575.1
10°	2979.9	3044.7	3105.4	3170.2	3230.9	3299.7	3364.5	3429.3	3498.1	3510.3	3526.5
12.5°	2826.0	2903.0	2979.9	3052.8	3129.7	3178.3	3226.9	3271.4	3320.0	3352.4	3384.8
15°	2822.0	2886.8	2951.5	3012.3	3077.1	3105.4	3133.7	3158.0	3186.4	3186.4	3190.4
17.5°	2915.1	2955.6	2996.1	3032.5	3073.0	3077.1	3085.2	3089.2	3093.3	3081.1	3069.0
20°	3097.3	3113.5	3129.7	3145.9	3162.1	3133.7	3109.4	3081.1	3052.8	3020.4	2992.0
22.5°	3364.5	3328.1	3291.6	3255.2	3218.8	3170.2	3117.5	3069.0	3016.3	2975.8	2935.3
25°	3615.5	3571.0	3526.5	3481.9	3437.4	3332.1	3226.9	3117.5	3012.3	2967.7	2923.2
27.5°	3951.6	3882.8	3813.9	3745.1	3676.3	3534.6	3392.9	3251.2	3109.4	3032.5	2959.6
30°	4032.6	3955.6	3878.7	3797.7	3720.8	3583.2	3449.5	3311.9	3174.2	3085.2	3000.1
32.5°	4150.0	4060.9	3971.8	3882.8	3793.7	3660.1	3526.5	3388.8	3255.2	3174.2	3089.2
35°	4344.3	4243.1	4141.9	4036.6	3935.4	3797.7	3664.1	3526.5	3388.8	3295.7	3206.6
37.5°	4510.3	4392.9	4275.5	4158.1	4040.7	3919.2	3793.7	3672.2	3546.7	3453.6	3364.5
40°	4696.6	4567.0	4437.4	4311.9	4182.4	4069.0	3955.6	3838.2	3724.9	3652.0	3579.1
42.5°	4858.5	4700.6	4546.8	4392.9	4235.0	4158.1	4085.2	4008.3	3931.3	3894.9	3854.4
45°	4971.9	4826.1	4676.3	4530.6	4384.8	4328.1	4271.4	4214.8	4158.1	4194.5	4231.0
47.5°	5020.5	4903.0	4789.7	4676.3	4558.9	4579.1	4599.4	4615.6	4635.8	4684.4	4737.0
50°	5065.0	5000.2	4931.4	4866.6	4797.8	4874.7	4947.6	5024.5	5101.4	5202.7	5303.9
52.5°	5154.1	5117.6	5085.2	5048.8	5012.4	5146.0	5279.6	5413.2	5546.8	5660.2	5773.5
55°	5421.3	5392.9	5364.6	5332.2	5303.9	5494.2	5680.4	5870.7	6061.0	6178.4	6295.8
57.5°	5789.7	5773.5	5753.3	5737.1	5716.8	5903.1	6085.3	6267.5	6453.7	6567.1	6684.5
60°	6069.1	6073.1	6073.1	6077.2	6077.2	6218.9	6360.6	6506.4	6648.1	6745.2	6846.5
62.5°	6218.9	6210.8	6202.7	6194.6	6186.5	6303.9	6421.3	6538.7	6656.2	6729.0	6801.9
65°	6056.9	6101.5	6146.0	6190.6	6235.1	6251.3	6263.4	6279.6	6291.8	6336.3	6380.8
67.5°	5514.4	5603.5	5688.5	5777.6	5862.6	5801.9	5745.2	5684.5	5623.7	5635.9	5644.0
70°	4911.1	5012.4	5117.6	5218.8	5320.1	5178.4	5036.7	4890.9	4749.2	4700.6	4652.0
72.5°	4141.9	4231.0	4324.1	4413.1	4502.2	4328.1	4158.1	3984.0	3809.9	3724.9	3639.8
75°	3166.1	3271.4	3380.7	3486.0	3591.2	3396.9	3198.5	3004.2	2805.8	2749.1	2696.5
77.5°	2307.8	2433.3	2558.8	2684.3	2809.8	2635.7	2461.6	2283.5	2109.4	2077.0	2044.6
80°	1680.2	1777.4	1870.5	1967.7	2060.8	1959.6	1858.4	1757.2	1655.9	1651.9	1647.8
82.5°	1133.7	1218.7	1299.7	1384.7	1465.7	1425.2	1388.7	1348.2	1307.7	1348.2	1392.8
85°	583.0	700.4	821.9	939.3	1056.7	1044.6	1036.5	1024.3	1012.2	1064.8	1113.4
87.5°	117.4	218.6	319.9	417.0	518.2	493.9	469.7	441.3	417.0	433.2	445.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	3194.5	3198.5	3198.5	3198.5	3198.5	3198.5	3190.4	3186.4	3178.3	3170.2	3158.0
5°	3433.3	3429.3	3413.1	3396.9	3376.7	3360.5	3348.3	3332.1	3320.0	3303.8	3279.5
7.5°	3583.2	3591.2	3562.9	3538.6	3510.3	3481.9	3453.6	3425.2	3396.9	3368.6	3311.9
10°	3538.6	3550.8	3534.6	3518.4	3498.1	3481.9	3449.5	3413.1	3380.7	3344.3	3275.4
12.5°	3413.1	3445.5	3437.4	3429.3	3421.2	3413.1	3392.9	3368.6	3348.3	3324.0	3247.1
15°	3190.4	3190.4	3194.5	3198.5	3198.5	3202.6	3206.6	3210.7	3214.7	3218.8	3174.2
17.5°	3056.8	3044.7	3044.7	3044.7	3044.7	3044.7	3060.9	3081.1	3097.3	3113.5	3101.3
20°	2959.6	2931.3	2927.3	2927.3	2923.2	2919.2	2947.5	2979.9	3008.2	3036.6	3052.8
22.5°	2894.9	2854.4	2850.3	2846.3	2842.2	2838.2	2874.6	2911.1	2947.5	2983.9	3040.6
25°	2878.7	2834.1	2838.2	2842.2	2842.2	2846.3	2874.6	2903.0	2931.3	2959.6	3056.8
27.5°	2882.7	2809.8	2813.9	2817.9	2817.9	2822.0	2866.5	2907.0	2951.5	2992.0	3113.5
30°	2911.1	2826.0	2817.9	2809.8	2801.7	2793.6	2854.4	2915.1	2975.8	3036.6	3129.7
32.5°	3008.2	2927.3	2907.0	2886.8	2866.5	2846.3	2919.2	2988.0	3060.9	3129.7	3206.6
35°	3113.5	3024.4	3016.3	3008.2	2996.1	2988.0	3052.8	3121.6	3186.4	3251.2	3320.0
37.5°	3271.4	3182.3	3174.2	3162.1	3154.0	3141.8	3214.7	3283.5	3356.4	3425.2	3486.0
40°	3506.2	3433.3	3429.3	3429.3	3425.2	3421.2	3477.9	3538.6	3595.3	3652.0	3692.5
42.5°	3818.0	3781.5	3793.7	3809.9	3822.0	3834.2	3878.7	3927.3	3971.8	4016.4	4004.2
45°	4267.4	4303.8	4307.9	4311.9	4316.0	4320.0	4332.2	4348.4	4360.5	4372.7	4324.1
47.5°	4785.6	4834.2	4858.5	4882.8	4903.0	4927.3	4911.1	4890.9	4874.7	4854.5	4733.0
50°	5401.0	5502.3	5498.2	5494.2	5486.1	5482.0	5449.6	5417.2	5380.8	5348.4	5170.3
52.5°	5886.9	6000.3	6020.5	6040.7	6061.0	6081.2	6020.5	5959.8	5895.0	5834.3	5611.6
55°	6409.2	6526.6	6530.6	6534.7	6534.7	6538.7	6453.7	6368.7	6279.6	6194.6	5963.8
57.5°	6797.9	6911.2	6899.1	6891.0	6878.8	6866.7	6765.5	6664.3	6563.0	6461.8	6231.0
60°	6943.6	7040.8	7016.5	6992.2	6963.9	6939.6	6862.6	6785.7	6704.7	6627.8	6405.1
62.5°	6874.8	6947.7	6911.2	6878.8	6842.4	6806.0	6708.8	6607.6	6510.4	6409.2	6247.2
65°	6421.3	6465.9	6417.3	6372.7	6328.2	6279.6	6198.6	6117.7	6032.6	5951.7	5842.4
67.5°	5656.1	5664.2	5660.2	5656.1	5652.1	5648.0	5530.6	5413.2	5291.7	5174.3	5166.2
70°	4607.5	4558.9	4567.0	4579.1	4587.2	4595.3	4506.3	4421.2	4332.2	4243.1	4283.6
72.5°	3554.8	3469.8	3490.0	3514.3	3534.6	3554.8	3481.9	3413.1	3340.2	3267.3	3324.0
75°	2639.8	2587.2	2607.4	2631.7	2651.9	2672.2	2643.8	2615.5	2583.1	2554.8	2607.4
77.5°	2012.2	1979.8	1983.9	1983.9	1987.9	1987.9	1992.0	2000.1	2004.1	2008.2	2064.9
80°	1639.7	1635.7	1631.6	1627.6	1619.5	1615.5	1655.9	1696.4	1736.9	1777.4	1805.7
82.5°	1433.3	1473.7	1449.5	1429.2	1404.9	1380.6	1417.1	1453.5	1489.9	1526.4	1514.2
85°	1166.0	1214.6	1170.1	1125.6	1077.0	1032.4	1064.8	1093.2	1125.6	1153.9	1137.7
87.5°	461.6	473.7	400.8	332.0	259.1	186.2	295.6	400.8	510.1	615.4	631.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820

CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1	2915.1
2.5°	3145.9	3129.7	3117.5	3113.5	3105.4	3101.3	3093.3	3085.2	3073.0	3064.9	3052.8
5°	3251.2	3226.9	3198.5	3158.0	3121.6	3081.1	3040.6	3004.2	2967.7	2927.3	2890.8
7.5°	3255.2	3198.5	3141.8	3089.2	3032.5	2979.9	2923.2	2874.6	2822.0	2769.4	2720.8
10°	3210.7	3141.8	3073.0	3004.2	2939.4	2870.6	2801.7	2745.1	2684.3	2623.6	2566.9
12.5°	3174.2	3097.3	3020.4	2939.4	2862.5	2781.5	2700.5	2643.8	2587.2	2530.5	2473.8
15°	3129.7	3081.1	3036.6	2963.7	2890.8	2817.9	2745.1	2668.1	2595.3	2518.3	2441.4
17.5°	3093.3	3081.1	3069.0	3020.4	2971.8	2919.2	2870.6	2793.6	2716.7	2635.7	2558.8
20°	3073.0	3089.2	3105.4	3081.1	3056.8	3028.5	3004.2	2947.5	2890.8	2830.1	2773.4
22.5°	3097.3	3158.0	3214.7	3218.8	3226.9	3230.9	3235.0	3182.3	3129.7	3073.0	3020.4
25°	3154.0	3251.2	3348.3	3401.0	3453.6	3510.3	3562.9	3530.5	3498.1	3465.7	3433.3
27.5°	3230.9	3352.4	3473.8	3550.8	3623.6	3700.6	3777.5	3773.4	3769.4	3761.3	3757.2
30°	3218.8	3311.9	3405.0	3498.1	3591.2	3684.4	3777.5	3826.1	3870.6	3919.2	3967.8
32.5°	3287.6	3364.5	3445.5	3542.7	3639.8	3741.1	3838.2	3939.4	4036.6	4137.8	4239.0
35°	3392.9	3461.7	3534.6	3639.8	3749.2	3854.4	3963.7	4085.2	4210.7	4336.2	4457.7
37.5°	3550.8	3611.5	3676.3	3765.3	3858.5	3947.5	4040.7	4218.8	4397.0	4579.1	4757.3
40°	3733.0	3773.4	3813.9	3899.0	3984.0	4069.0	4154.0	4376.7	4599.4	4822.1	5044.8
42.5°	3996.1	3984.0	3971.8	4040.7	4113.5	4182.4	4255.2	4457.7	4660.1	4862.6	5065.0
45°	4275.5	4226.9	4178.3	4210.7	4247.1	4279.5	4316.0	4522.5	4728.9	4939.5	5146.0
47.5°	4611.5	4490.1	4368.6	4340.3	4311.9	4279.5	4251.2	4473.9	4696.6	4923.3	5146.0
50°	4992.1	4809.9	4631.8	4558.9	4482.0	4409.1	4332.2	4514.4	4700.6	4886.9	5069.0
52.5°	5388.9	5162.2	4939.5	4826.1	4712.8	4595.3	4482.0	4635.8	4793.7	4951.6	5105.5
55°	5729.0	5498.2	5263.4	5129.8	4996.2	4862.6	4728.9	4882.8	5036.7	5190.5	5344.4
57.5°	6000.3	5769.5	5538.7	5413.2	5283.6	5158.1	5028.6	5174.3	5324.1	5473.9	5619.7
60°	6186.5	5963.8	5741.1	5619.7	5498.2	5376.8	5255.3	5429.4	5603.5	5781.6	5955.7
62.5°	6089.3	5927.4	5765.4	5712.8	5660.2	5603.5	5550.8	5716.8	5878.8	6044.8	6210.8
65°	5733.0	5623.7	5514.4	5567.0	5623.7	5676.4	5733.0	5842.4	5951.7	6065.0	6174.4
67.5°	5154.1	5146.0	5133.8	5251.2	5368.7	5490.1	5607.5	5680.4	5749.2	5822.1	5895.0
70°	4324.1	4368.6	4409.1	4611.5	4814.0	5016.4	5218.8	5247.2	5275.5	5303.9	5332.2
72.5°	3384.8	3441.4	3502.2	3769.4	4032.6	4299.8	4567.0	4550.8	4534.6	4514.4	4498.2
75°	2664.1	2716.7	2773.4	3020.4	3267.3	3514.3	3761.3	3692.5	3627.7	3558.9	3490.0
77.5°	2125.6	2182.3	2243.0	2473.8	2704.6	2939.4	3170.2	3004.2	2838.2	2672.2	2506.2
80°	1830.0	1858.4	1882.7	2040.6	2194.4	2352.3	2510.2	2340.2	2166.1	1992.0	1821.9
82.5°	1502.1	1485.9	1473.7	1566.9	1660.0	1753.1	1846.2	1684.3	1522.3	1356.3	1194.4
85°	1121.5	1105.3	1089.1	1137.7	1186.3	1238.9	1287.5	1101.3	915.0	724.7	538.5
87.5°	651.9	668.0	684.2	736.9	789.5	846.2	898.8	708.5	518.2	323.9	133.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671820  
 CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671820  
CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	2915.1	2915.1
2.5°	3028.5	3008.2
5°	2862.5	2834.1
7.5°	2680.3	2643.8
10°	2514.3	2465.7
12.5°	2409.0	2348.3
15°	2368.5	2295.6
17.5°	2490.0	2421.2
20°	2676.2	2583.1
22.5°	2903.0	2789.6
25°	3295.7	3158.0
27.5°	3615.5	3473.8
30°	3813.9	3660.1
32.5°	4032.6	3830.1
35°	4259.3	4065.0
37.5°	4534.6	4316.0
40°	4818.0	4591.3
42.5°	4915.2	4769.4
45°	5008.3	4870.7
47.5°	5028.6	4915.2
50°	5048.8	5032.6
52.5°	5105.5	5101.4
55°	5348.4	5352.5
57.5°	5648.0	5672.3
60°	5923.3	5895.0
62.5°	6065.0	5919.3
65°	5967.9	5765.4
67.5°	5676.4	5457.7
70°	5036.7	4741.1
72.5°	4239.0	3979.9
75°	3267.3	3048.7
77.5°	2324.0	2141.8
80°	1635.7	1453.5
82.5°	1048.6	902.9
85°	473.7	413.0
87.5°	133.6	129.6
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671820  
CATALOG NUMBER: CCP-SA-2D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)