

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671908

Luminaire Tested: **CCP-SA-2D-850-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671908
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2D-850-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @800mA w/ SLR distribution lens
Light Source: (32) 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8076.3 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3

Input Watts (W): 80.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 11.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P671908
CATALOG NUMBER: CCP-SA-2D-850-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1661.7	0.0	1661.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	6414.5	0.0	6414.5
	% Fixture	79.4	0.0	79.4
Total	Lumens	8076.3	0.0	8076.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.4	2.5
10°-20°	423.1	5.2
20°-30°	619.0	7.7
30°-40°	872.1	10.8
40°-50°	1198.4	14.8
50°-60°	1633.4	20.2
60°-70°	1787.8	22.1
70°-80°	1032.5	12.8
80°-90°	309.5	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8076.3	100.0
0°-180°	8076.3	100.0



REPORT NUMBER: P671908


CATALOG NUMBER: CCP-SA-2D-850-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	829.5	10.3			
FM (30°-60°)	2947.3	36.5			
FH (60°-80°)	2374.9	29.4			G2/5000
FVH (80°-90°)	262.9	3.3			G3/500
BL (0°-30°)	413.1	5.1	B1/500		
BM (30°-60°)	756.7	9.4	B1/1000		
BH (60°-80°)	445.3	5.5	B1/500		G1/500
BVH (80°-90°)	46.6	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short





REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2661.4	2647.1	2636.4	2625.6	2611.3	2600.5	2586.2	2571.9	2554.0	2539.7	2521.7
5°	2507.4	2464.4	2421.4	2396.4	2367.7	2342.6	2314.0	2281.7	2249.5	2213.7	2181.5
7.5°	2339.1	2285.3	2231.6	2188.6	2142.0	2099.1	2052.5	2013.1	1973.7	1934.3	1894.9
10°	2181.5	2131.3	2081.2	2027.4	1970.1	1916.4	1859.1	1805.3	1751.6	1697.9	1644.1
12.5°	2077.6	2016.7	1959.4	1898.5	1841.2	1780.3	1719.4	1669.2	1619.1	1565.3	1515.2
15°	2031.0	1973.7	1920.0	1859.1	1798.2	1737.3	1676.4	1619.1	1565.3	1508.0	1450.7
17.5°	2142.0	2059.7	1977.3	1898.5	1819.7	1740.9	1662.1	1590.4	1518.8	1447.1	1375.5
20°	2285.3	2181.5	2081.2	1984.4	1884.1	1787.4	1687.1	1586.8	1486.5	1386.2	1285.9
22.5°	2468.0	2349.8	2235.2	2109.8	1980.9	1855.5	1726.5	1601.2	1475.8	1346.8	1221.5
25°	2794.0	2654.3	2514.6	2335.5	2152.8	1973.7	1791.0	1626.2	1465.0	1300.3	1135.5
27.5°	3073.4	2883.5	2697.3	2482.3	2267.4	2052.5	1837.6	1647.7	1461.5	1271.6	1081.8
30°	3238.1	3051.9	2865.6	2604.1	2346.2	2084.7	1823.2	1611.9	1404.2	1192.8	981.5
32.5°	3388.6	3180.8	2973.1	2686.5	2396.4	2109.8	1819.7	1586.8	1357.6	1124.8	891.9
35°	3596.3	3367.1	3141.4	2808.3	2475.2	2142.0	1808.9	1568.9	1325.3	1085.4	841.8
37.5°	3818.4	3535.5	3256.1	2887.1	2518.2	2149.2	1780.3	1543.9	1307.4	1071.0	834.6
40°	4062.0	3718.1	3377.8	2969.5	2564.7	2156.4	1748.0	1511.6	1275.2	1035.2	798.8
42.5°	4219.6	3847.1	3474.6	3034.0	2597.0	2156.4	1715.8	1483.0	1250.1	1013.7	780.9
45°	4309.2	3947.4	3589.2	3112.8	2636.4	2160.0	1683.5	1454.3	1225.1	992.2	763.0
47.5°	4348.6	4011.9	3675.2	3173.7	2675.8	2174.3	1672.8	1440.0	1203.6	970.7	734.3
50°	4452.5	4155.1	3857.8	3320.5	2786.8	2249.5	1712.2	1461.5	1214.3	963.6	712.8
52.5°	4513.3	4259.0	4004.7	3453.1	2901.4	2349.8	1798.2	1518.8	1239.4	960.0	680.6
55°	4735.4	4491.9	4248.3	3660.8	3069.8	2482.3	1891.3	1583.3	1275.2	963.6	655.5
57.5°	5018.4	4760.5	4506.2	3872.2	3238.1	2604.1	1970.1	1640.6	1307.4	977.9	644.8
60°	5215.4	4964.7	4717.5	4044.1	3367.1	2693.7	2016.7	1672.8	1328.9	981.5	637.6
62.5°	5236.9	4914.5	4595.7	3940.2	3284.7	2625.6	1970.1	1637.0	1303.9	967.1	634.0
65°	5100.8	4724.7	4348.6	3721.7	3094.9	2468.0	1841.2	1536.7	1232.2	924.2	619.7
67.5°	4828.6	4388.0	3947.4	3374.3	2801.1	2228.0	1654.9	1393.4	1135.5	874.0	612.5
70°	4194.5	3807.7	3424.4	2926.5	2432.2	1934.3	1436.4	1221.5	1010.1	795.2	580.3
72.5°	3521.1	3159.3	2801.1	2396.4	1995.2	1590.4	1185.6	1024.5	863.3	698.5	537.3
75°	2697.3	2425.0	2156.4	1855.5	1554.6	1250.1	949.2	831.0	712.8	594.6	476.4
77.5°	1894.9	1748.0	1604.7	1379.1	1153.4	927.7	702.1	623.3	544.5	465.7	386.9
80°	1285.9	1203.6	1124.8	963.6	802.4	637.6	476.4	426.3	372.5	322.4	268.7
82.5°	798.8	795.2	788.0	677.0	566.0	454.9	343.9	300.9	261.5	218.5	175.5
85°	365.4	426.3	483.6	422.7	361.8	300.9	240.0	211.3	182.7	150.4	121.8
87.5°	114.6	139.7	161.2	154.0	143.3	136.1	125.4	107.5	89.6	71.6	53.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2507.4	2496.7	2482.3	2468.0	2450.1	2435.8	2417.9	2400.0	2396.4	2389.2	2385.6
5°	2160.0	2138.5	2113.4	2091.9	2070.4	2045.3	2023.8	1998.8	1980.9	1959.4	1941.5
7.5°	1855.5	1819.7	1780.3	1740.9	1705.0	1669.2	1629.8	1594.0	1576.1	1558.2	1540.3
10°	1611.9	1576.1	1543.9	1508.0	1483.0	1461.5	1436.4	1411.3	1389.8	1368.3	1346.8
12.5°	1490.1	1465.0	1440.0	1414.9	1386.2	1361.2	1332.5	1303.9	1278.8	1257.3	1232.2
15°	1414.9	1379.1	1339.7	1303.9	1264.5	1228.6	1189.2	1149.8	1121.2	1096.1	1067.4
17.5°	1325.3	1271.6	1221.5	1167.7	1124.8	1081.8	1035.2	992.2	960.0	924.2	891.9
20°	1225.1	1164.2	1099.7	1038.8	988.6	942.1	891.9	841.8	806.0	766.6	730.7
22.5°	1139.1	1060.3	977.9	895.5	841.8	788.0	730.7	677.0	644.8	608.9	576.7
25°	1045.9	960.0	870.4	780.9	727.2	669.8	616.1	558.8	533.7	512.2	487.2
27.5°	995.8	909.8	820.3	734.3	684.2	630.4	580.3	526.6	508.6	487.2	469.2
30°	895.5	813.1	727.2	641.2	605.4	573.1	537.3	501.5	494.3	490.7	483.6
32.5°	806.0	720.0	634.0	548.0	515.8	483.6	451.3	419.1	415.5	408.4	404.8
35°	759.4	677.0	591.0	508.6	480.0	447.8	419.1	386.9	379.7	368.9	361.8
37.5°	748.6	662.7	573.1	487.2	458.5	429.8	397.6	368.9	361.8	354.6	347.5
40°	720.0	637.6	558.8	476.4	447.8	419.1	386.9	358.2	351.0	343.9	336.7
42.5°	698.5	619.7	537.3	454.9	429.8	404.8	376.1	351.0	343.9	336.7	326.0
45°	680.6	598.2	512.2	429.8	411.9	394.0	372.5	354.6	347.5	336.7	329.5
47.5°	651.9	573.1	490.7	408.4	390.4	376.1	358.2	340.3	333.1	326.0	318.8
50°	630.4	548.0	465.7	383.3	368.9	354.6	340.3	326.0	326.0	329.5	329.5
52.5°	601.8	523.0	444.2	365.4	351.0	336.7	322.4	308.1	311.6	315.2	318.8
55°	576.7	501.5	422.7	343.9	329.5	315.2	297.3	283.0	286.6	290.1	293.7
57.5°	566.0	487.2	408.4	329.5	315.2	297.3	283.0	265.1	265.1	265.1	265.1
60°	558.8	476.4	397.6	315.2	297.3	283.0	265.1	247.2	243.6	243.6	240.0
62.5°	555.2	472.8	394.0	311.6	290.1	272.2	250.7	229.2	225.7	222.1	218.5
65°	540.9	465.7	386.9	308.1	283.0	261.5	236.4	211.3	207.8	207.8	204.2
67.5°	537.3	458.5	383.3	304.5	279.4	250.7	225.7	197.0	193.4	189.8	186.3
70°	508.6	440.6	368.9	297.3	268.7	243.6	214.9	186.3	182.7	175.5	171.9
72.5°	472.8	411.9	347.5	283.0	254.3	225.7	197.0	168.4	164.8	161.2	154.0
75°	419.1	361.8	304.5	247.2	222.1	200.6	175.5	150.4	146.9	143.3	136.1
77.5°	343.9	297.3	254.3	207.8	189.8	171.9	154.0	136.1	132.5	129.0	121.8
80°	243.6	214.9	189.8	161.2	150.4	136.1	125.4	111.0	111.0	107.5	107.5
82.5°	161.2	146.9	132.5	118.2	111.0	103.9	96.7	89.6	89.6	86.0	86.0
85°	114.6	107.5	96.7	89.6	86.0	78.8	75.2	68.1	68.1	68.1	68.1
87.5°	53.7	53.7	50.1	50.1	46.6	46.6	43.0	39.4	39.4	39.4	39.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2378.5	2367.7	2357.0	2342.6	2331.9	2317.6	2299.7	2285.3	2267.4	2267.4	2263.8
5°	1920.0	1909.2	1898.5	1884.1	1873.4	1859.1	1848.3	1834.0	1819.7	1819.7	1816.1
7.5°	1522.4	1500.9	1479.4	1454.3	1432.8	1418.5	1404.2	1386.2	1371.9	1361.2	1350.4
10°	1325.3	1303.9	1278.8	1257.3	1232.2	1214.3	1196.4	1174.9	1157.0	1142.7	1128.3
12.5°	1207.1	1182.1	1157.0	1131.9	1106.8	1081.8	1060.3	1035.2	1010.1	992.2	974.3
15°	1038.8	1013.7	988.6	963.6	938.5	909.8	881.2	848.9	820.3	806.0	795.2
17.5°	856.1	831.0	802.4	777.3	748.6	727.2	705.7	684.2	662.7	648.3	637.6
20°	691.3	662.7	634.0	605.4	576.7	562.4	548.0	533.7	519.4	508.6	501.5
22.5°	540.9	523.0	508.6	490.7	472.8	462.1	454.9	444.2	433.4	433.4	433.4
25°	462.1	451.3	444.2	433.4	422.7	419.1	415.5	408.4	404.8	401.2	401.2
27.5°	447.8	437.0	426.3	415.5	404.8	401.2	397.6	390.4	386.9	386.9	386.9
30°	476.4	472.8	469.2	465.7	462.1	454.9	444.2	437.0	426.3	419.1	411.9
32.5°	397.6	394.0	394.0	390.4	386.9	394.0	397.6	404.8	408.4	411.9	415.5
35°	351.0	343.9	336.7	329.5	322.4	318.8	315.2	311.6	308.1	308.1	304.5
37.5°	340.3	333.1	326.0	318.8	311.6	308.1	304.5	300.9	297.3	297.3	293.7
40°	329.5	322.4	318.8	311.6	304.5	300.9	297.3	290.1	286.6	283.0	283.0
42.5°	318.8	315.2	308.1	304.5	297.3	293.7	290.1	283.0	279.4	275.8	272.2
45°	318.8	311.6	304.5	297.3	290.1	286.6	279.4	275.8	268.7	268.7	265.1
47.5°	311.6	304.5	297.3	290.1	283.0	279.4	272.2	268.7	261.5	257.9	254.3
50°	329.5	318.8	304.5	293.7	279.4	275.8	268.7	265.1	257.9	254.3	250.7
52.5°	322.4	311.6	297.3	286.6	272.2	265.1	261.5	254.3	247.2	243.6	240.0
55°	297.3	286.6	279.4	268.7	257.9	250.7	243.6	236.4	229.2	225.7	225.7
57.5°	265.1	261.5	257.9	254.3	250.7	243.6	236.4	225.7	218.5	214.9	211.3
60°	236.4	240.0	243.6	247.2	250.7	240.0	229.2	218.5	207.8	204.2	200.6
62.5°	214.9	222.1	229.2	232.8	240.0	229.2	218.5	207.8	197.0	193.4	189.8
65°	200.6	204.2	204.2	207.8	207.8	200.6	197.0	189.8	182.7	179.1	179.1
67.5°	182.7	182.7	182.7	179.1	179.1	175.5	175.5	171.9	168.4	164.8	164.8
70°	164.8	164.8	164.8	161.2	161.2	157.6	157.6	154.0	150.4	150.4	146.9
72.5°	150.4	150.4	146.9	146.9	143.3	143.3	143.3	139.7	139.7	136.1	136.1
75°	132.5	132.5	129.0	129.0	125.4	125.4	125.4	121.8	121.8	121.8	118.2
77.5°	118.2	118.2	114.6	114.6	111.0	111.0	111.0	107.5	107.5	103.9	103.9
80°	103.9	103.9	100.3	100.3	96.7	96.7	93.1	93.1	89.6	89.6	86.0
82.5°	82.4	82.4	82.4	82.4	82.4	78.8	78.8	75.2	71.6	71.6	68.1
85°	68.1	68.1	68.1	64.5	64.5	64.5	60.9	60.9	57.3	53.7	53.7
87.5°	39.4	39.4	39.4	35.8	35.8	35.8	35.8	35.8	35.8	35.8	32.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2263.8	2260.3	2245.9	2231.6	2245.9	2260.3	2260.3	2260.3	2256.7	2256.7	2256.7
5°	1816.1	1812.5	1805.3	1798.2	1798.2	1794.6	1801.8	1808.9	1816.1	1823.2	1830.4
7.5°	1336.1	1325.3	1314.6	1303.9	1311.0	1314.6	1325.3	1332.5	1343.3	1350.4	1368.3
10°	1114.0	1099.7	1088.9	1078.2	1071.0	1063.9	1056.7	1053.1	1045.9	1038.8	1045.9
12.5°	952.8	934.9	917.0	895.5	891.9	888.3	881.2	874.0	866.8	859.7	856.1
15°	780.9	766.6	759.4	748.6	734.3	720.0	712.8	709.2	702.1	694.9	691.3
17.5°	623.3	608.9	598.2	587.5	583.9	576.7	576.7	576.7	576.7	576.7	576.7
20°	490.7	480.0	480.0	476.4	476.4	472.8	476.4	480.0	480.0	483.6	487.2
22.5°	429.8	429.8	426.3	422.7	426.3	426.3	429.8	433.4	437.0	440.6	444.2
25°	397.6	394.0	397.6	401.2	401.2	401.2	404.8	404.8	408.4	408.4	408.4
27.5°	383.3	383.3	386.9	386.9	390.4	390.4	390.4	386.9	386.9	383.3	383.3
30°	404.8	397.6	397.6	397.6	394.0	390.4	386.9	386.9	383.3	379.7	376.1
32.5°	419.1	422.7	419.1	411.9	408.4	401.2	397.6	390.4	386.9	379.7	372.5
35°	304.5	300.9	308.1	311.6	315.2	318.8	322.4	326.0	326.0	329.5	329.5
37.5°	293.7	290.1	290.1	286.6	286.6	286.6	286.6	286.6	283.0	283.0	286.6
40°	279.4	275.8	275.8	272.2	272.2	268.7	268.7	268.7	268.7	268.7	268.7
42.5°	268.7	265.1	265.1	265.1	265.1	261.5	261.5	257.9	257.9	254.3	254.3
45°	265.1	261.5	257.9	254.3	254.3	250.7	250.7	250.7	247.2	247.2	247.2
47.5°	250.7	247.2	247.2	243.6	243.6	240.0	240.0	240.0	236.4	236.4	236.4
50°	243.6	240.0	240.0	236.4	236.4	232.8	232.8	232.8	229.2	229.2	229.2
52.5°	232.8	229.2	229.2	229.2	225.7	222.1	222.1	222.1	218.5	218.5	218.5
55°	222.1	218.5	218.5	218.5	214.9	211.3	211.3	211.3	207.8	207.8	207.8
57.5°	207.8	204.2	204.2	200.6	200.6	200.6	200.6	200.6	197.0	197.0	197.0
60°	197.0	193.4	193.4	189.8	189.8	186.3	186.3	186.3	186.3	186.3	186.3
62.5°	186.3	182.7	179.1	175.5	179.1	179.1	179.1	179.1	175.5	175.5	175.5
65°	175.5	171.9	168.4	164.8	164.8	164.8	164.8	164.8	164.8	164.8	164.8
67.5°	161.2	157.6	154.0	150.4	154.0	154.0	154.0	154.0	154.0	154.0	154.0
70°	146.9	143.3	143.3	139.7	139.7	136.1	136.1	139.7	139.7	139.7	139.7
72.5°	132.5	129.0	129.0	125.4	125.4	125.4	125.4	125.4	125.4	125.4	125.4
75°	118.2	114.6	114.6	111.0	111.0	111.0	111.0	111.0	111.0	111.0	111.0
77.5°	100.3	96.7	96.7	96.7	96.7	96.7	96.7	100.3	100.3	100.3	100.3
80°	86.0	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4
82.5°	68.1	64.5	64.5	64.5	64.5	64.5	64.5	64.5	64.5	64.5	64.5
85°	50.1	46.6	46.6	46.6	50.1	50.1	50.1	50.1	50.1	50.1	50.1
87.5°	32.2	28.7	28.7	28.7	32.2	32.2	32.2	32.2	28.7	28.7	28.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2256.7	2256.7	2256.7	2253.1	2249.5	2245.9	2242.3	2253.1	2260.3	2271.0	2278.2
5°	1834.0	1841.2	1844.7	1855.5	1866.2	1877.0	1887.7	1894.9	1902.1	1905.6	1912.8
7.5°	1382.7	1400.6	1414.9	1429.2	1443.6	1454.3	1468.6	1479.4	1490.1	1500.9	1511.6
10°	1049.5	1056.7	1060.3	1074.6	1085.4	1099.7	1110.4	1121.2	1131.9	1139.1	1149.8
12.5°	852.5	845.4	841.8	841.8	841.8	841.8	841.8	848.9	856.1	863.3	870.4
15°	687.7	684.2	680.6	677.0	673.4	666.3	662.7	669.8	677.0	684.2	691.3
17.5°	576.7	576.7	576.7	573.1	569.5	566.0	562.4	566.0	569.5	569.5	573.1
20°	494.3	497.9	501.5	505.1	505.1	508.6	508.6	512.2	515.8	515.8	519.4
22.5°	444.2	447.8	447.8	447.8	451.3	451.3	451.3	454.9	458.5	462.1	465.7
25°	404.8	404.8	401.2	401.2	404.8	404.8	404.8	404.8	408.4	408.4	408.4
27.5°	383.3	379.7	379.7	379.7	379.7	376.1	376.1	376.1	376.1	376.1	376.1
30°	372.5	368.9	365.4	361.8	361.8	358.2	354.6	354.6	354.6	354.6	354.6
32.5°	368.9	361.8	354.6	351.0	351.0	347.5	343.9	340.3	340.3	336.7	333.1
35°	329.5	326.0	326.0	322.4	318.8	315.2	311.6	311.6	311.6	308.1	308.1
37.5°	286.6	290.1	290.1	290.1	293.7	293.7	293.7	293.7	297.3	297.3	297.3
40°	268.7	268.7	268.7	272.2	275.8	275.8	279.4	279.4	283.0	283.0	283.0
42.5°	254.3	250.7	250.7	254.3	254.3	257.9	257.9	261.5	265.1	265.1	268.7
45°	247.2	243.6	243.6	243.6	243.6	240.0	240.0	243.6	247.2	250.7	254.3
47.5°	232.8	232.8	229.2	229.2	229.2	229.2	229.2	229.2	232.8	232.8	232.8
50°	225.7	225.7	222.1	222.1	222.1	222.1	222.1	222.1	222.1	222.1	222.1
52.5°	218.5	214.9	214.9	214.9	214.9	211.3	211.3	211.3	211.3	211.3	211.3
55°	207.8	204.2	204.2	204.2	204.2	204.2	204.2	204.2	207.8	207.8	207.8
57.5°	197.0	193.4	193.4	193.4	197.0	197.0	197.0	197.0	200.6	200.6	200.6
60°	186.3	186.3	186.3	186.3	186.3	186.3	186.3	189.8	189.8	193.4	193.4
62.5°	175.5	175.5	175.5	175.5	179.1	179.1	179.1	179.1	182.7	182.7	182.7
65°	164.8	164.8	164.8	164.8	168.4	168.4	168.4	168.4	168.4	168.4	168.4
67.5°	154.0	154.0	154.0	154.0	154.0	154.0	154.0	157.6	157.6	161.2	161.2
70°	139.7	136.1	136.1	139.7	139.7	143.3	143.3	146.9	146.9	150.4	150.4
72.5°	125.4	125.4	125.4	125.4	125.4	125.4	125.4	129.0	132.5	132.5	136.1
75°	111.0	111.0	111.0	111.0	114.6	114.6	114.6	118.2	118.2	121.8	121.8
77.5°	100.3	96.7	96.7	96.7	100.3	100.3	100.3	103.9	103.9	107.5	107.5
80°	82.4	82.4	82.4	82.4	86.0	86.0	86.0	86.0	89.6	89.6	89.6
82.5°	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1	71.6	71.6	71.6
85°	50.1	50.1	50.1	50.1	53.7	53.7	53.7	53.7	53.7	53.7	53.7
87.5°	32.2	32.2	32.2	32.2	32.2	32.2	32.2	32.2	35.8	35.8	35.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2278.2	2278.2	2278.2	2278.2	2285.3	2288.9	2296.1	2299.7	2296.1	2292.5	2285.3
5°	1916.4	1920.0	1920.0	1923.5	1923.5	1923.5	1923.5	1923.5	1930.7	1937.9	1945.0
7.5°	1515.2	1518.8	1522.4	1525.9	1525.9	1525.9	1522.4	1522.4	1525.9	1525.9	1529.5
10°	1160.6	1174.9	1185.6	1196.4	1189.2	1178.5	1171.3	1160.6	1160.6	1160.6	1157.0
12.5°	877.6	881.2	888.3	891.9	888.3	888.3	884.8	881.2	884.8	891.9	895.5
15°	694.9	694.9	698.5	698.5	702.1	705.7	705.7	709.2	716.4	720.0	727.2
17.5°	576.7	580.3	580.3	583.9	583.9	587.5	587.5	587.5	594.6	601.8	612.5
20°	519.4	519.4	519.4	519.4	519.4	515.8	515.8	512.2	515.8	523.0	526.6
22.5°	465.7	469.2	469.2	469.2	465.7	462.1	454.9	451.3	451.3	454.9	454.9
25°	408.4	404.8	404.8	401.2	401.2	404.8	404.8	404.8	408.4	408.4	411.9
27.5°	376.1	372.5	372.5	368.9	368.9	372.5	372.5	372.5	372.5	372.5	372.5
30°	351.0	351.0	347.5	343.9	347.5	347.5	351.0	351.0	354.6	354.6	358.2
32.5°	333.1	329.5	329.5	326.0	329.5	329.5	333.1	333.1	336.7	340.3	340.3
35°	308.1	308.1	308.1	308.1	308.1	308.1	304.5	304.5	304.5	304.5	304.5
37.5°	293.7	293.7	290.1	286.6	286.6	286.6	286.6	286.6	283.0	279.4	275.8
40°	283.0	279.4	279.4	275.8	272.2	272.2	268.7	265.1	265.1	261.5	261.5
42.5°	268.7	265.1	265.1	261.5	257.9	257.9	254.3	250.7	250.7	250.7	247.2
45°	250.7	250.7	247.2	243.6	243.6	243.6	240.0	240.0	240.0	240.0	236.4
47.5°	232.8	232.8	229.2	229.2	229.2	229.2	225.7	225.7	225.7	225.7	225.7
50°	222.1	222.1	222.1	222.1	222.1	222.1	218.5	218.5	218.5	218.5	218.5
52.5°	211.3	211.3	211.3	211.3	211.3	211.3	211.3	211.3	211.3	211.3	211.3
55°	207.8	207.8	207.8	207.8	207.8	207.8	204.2	204.2	204.2	207.8	207.8
57.5°	200.6	200.6	197.0	197.0	197.0	197.0	197.0	197.0	197.0	197.0	197.0
60°	193.4	193.4	193.4	193.4	193.4	193.4	193.4	193.4	193.4	193.4	193.4
62.5°	182.7	182.7	182.7	182.7	182.7	186.3	186.3	186.3	186.3	186.3	182.7
65°	168.4	171.9	171.9	171.9	171.9	171.9	171.9	171.9	171.9	171.9	171.9
67.5°	161.2	161.2	161.2	161.2	161.2	161.2	161.2	161.2	161.2	161.2	161.2
70°	150.4	150.4	146.9	146.9	146.9	150.4	150.4	150.4	150.4	150.4	150.4
72.5°	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1	139.7	139.7
75°	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8
77.5°	107.5	107.5	103.9	103.9	103.9	107.5	107.5	107.5	107.5	111.0	111.0
80°	89.6	89.6	89.6	89.6	89.6	89.6	89.6	89.6	89.6	93.1	93.1
82.5°	71.6	71.6	71.6	71.6	71.6	71.6	71.6	71.6	71.6	75.2	75.2
85°	53.7	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	60.9	60.9
87.5°	35.8	35.8	35.8	35.8	35.8	35.8	32.2	32.2	32.2	32.2	28.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2281.7	2285.3	2288.9	2288.9	2292.5	2296.1	2296.1	2310.4	2324.7	2331.9	2339.1
5°	1952.2	1948.6	1948.6	1945.0	1941.5	1952.2	1962.9	1984.4	2005.9	2009.5	2016.7
7.5°	1529.5	1533.1	1536.7	1536.7	1540.3	1529.5	1515.2	1518.8	1522.4	1540.3	1554.6
10°	1157.0	1160.6	1164.2	1164.2	1167.7	1164.2	1157.0	1167.7	1178.5	1192.8	1210.7
12.5°	899.1	909.8	920.6	927.7	938.5	945.7	949.2	963.6	974.3	992.2	1010.1
15°	734.3	741.5	748.6	755.8	763.0	770.1	777.3	791.6	806.0	827.4	848.9
17.5°	619.7	619.7	623.3	623.3	623.3	630.4	637.6	644.8	648.3	669.8	691.3
20°	530.1	526.6	523.0	519.4	515.8	523.0	526.6	530.1	533.7	548.0	558.8
22.5°	454.9	454.9	458.5	458.5	458.5	454.9	447.8	451.3	451.3	458.5	469.2
25°	411.9	411.9	411.9	408.4	408.4	411.9	415.5	415.5	411.9	415.5	419.1
27.5°	372.5	376.1	376.1	379.7	379.7	383.3	383.3	383.3	383.3	386.9	390.4
30°	358.2	358.2	361.8	361.8	361.8	365.4	368.9	368.9	368.9	372.5	379.7
32.5°	343.9	347.5	351.0	354.6	358.2	361.8	361.8	365.4	365.4	368.9	372.5
35°	304.5	300.9	300.9	297.3	293.7	293.7	293.7	293.7	290.1	293.7	293.7
37.5°	272.2	272.2	272.2	268.7	268.7	272.2	272.2	272.2	272.2	275.8	275.8
40°	257.9	257.9	257.9	257.9	257.9	257.9	257.9	261.5	261.5	265.1	268.7
42.5°	247.2	247.2	247.2	247.2	247.2	250.7	250.7	250.7	250.7	254.3	254.3
45°	236.4	236.4	236.4	236.4	236.4	236.4	236.4	240.0	240.0	243.6	247.2
47.5°	225.7	225.7	225.7	225.7	225.7	229.2	232.8	232.8	232.8	236.4	236.4
50°	218.5	218.5	218.5	218.5	218.5	222.1	222.1	225.7	225.7	229.2	232.8
52.5°	211.3	211.3	211.3	211.3	211.3	214.9	214.9	218.5	218.5	222.1	225.7
55°	207.8	207.8	207.8	204.2	204.2	207.8	207.8	211.3	211.3	214.9	214.9
57.5°	197.0	197.0	197.0	197.0	197.0	197.0	197.0	200.6	200.6	204.2	207.8
60°	193.4	193.4	189.8	189.8	186.3	189.8	189.8	193.4	193.4	197.0	197.0
62.5°	182.7	182.7	182.7	179.1	179.1	182.7	182.7	182.7	182.7	186.3	189.8
65°	171.9	171.9	171.9	168.4	168.4	171.9	171.9	171.9	171.9	175.5	179.1
67.5°	161.2	161.2	161.2	157.6	157.6	157.6	157.6	161.2	161.2	164.8	168.4
70°	150.4	150.4	150.4	146.9	146.9	146.9	143.3	146.9	150.4	154.0	154.0
72.5°	139.7	139.7	139.7	136.1	136.1	136.1	132.5	136.1	136.1	139.7	139.7
75°	121.8	121.8	121.8	121.8	121.8	121.8	118.2	118.2	118.2	121.8	121.8
77.5°	111.0	111.0	111.0	107.5	107.5	107.5	103.9	103.9	103.9	107.5	107.5
80°	93.1	93.1	93.1	89.6	89.6	89.6	86.0	86.0	86.0	89.6	89.6
82.5°	75.2	75.2	75.2	71.6	71.6	71.6	68.1	68.1	68.1	71.6	71.6
85°	60.9	60.9	60.9	60.9	60.9	60.9	57.3	57.3	57.3	60.9	64.5
87.5°	28.7	28.7	32.2	32.2	32.2	32.2	28.7	28.7	25.1	25.1	28.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2346.2	2353.4	2371.3	2385.6	2403.5	2417.9	2428.6	2442.9	2453.7	2464.4	2471.6
5°	2020.3	2023.8	2041.8	2059.7	2074.0	2091.9	2117.0	2142.0	2167.1	2192.2	2210.1
7.5°	1572.5	1586.8	1608.3	1633.4	1654.9	1676.4	1701.5	1730.1	1755.2	1780.3	1805.3
10°	1225.1	1239.4	1260.9	1282.4	1300.3	1321.8	1350.4	1379.1	1407.7	1436.4	1465.0
12.5°	1028.0	1045.9	1071.0	1096.1	1117.6	1142.7	1178.5	1210.7	1246.5	1278.8	1314.6
15°	866.8	888.3	920.6	956.4	988.6	1020.9	1056.7	1092.5	1124.8	1160.6	1196.4
17.5°	712.8	734.3	763.0	795.2	823.9	852.5	895.5	934.9	977.9	1017.3	1056.7
20°	573.1	583.9	612.5	641.2	669.8	698.5	730.7	763.0	795.2	827.4	877.6
22.5°	476.4	483.6	497.9	508.6	523.0	533.7	566.0	598.2	626.9	659.1	705.7
25°	419.1	422.7	433.4	440.6	451.3	458.5	480.0	497.9	519.4	537.3	580.3
27.5°	390.4	394.0	397.6	401.2	404.8	408.4	422.7	437.0	447.8	462.1	501.5
30°	383.3	386.9	397.6	404.8	415.5	422.7	429.8	437.0	444.2	451.3	476.4
32.5°	376.1	379.7	379.7	376.1	376.1	372.5	379.7	383.3	390.4	394.0	415.5
35°	297.3	297.3	300.9	304.5	308.1	311.6	322.4	329.5	340.3	347.5	365.4
37.5°	279.4	279.4	283.0	290.1	293.7	297.3	304.5	311.6	318.8	326.0	343.9
40°	268.7	272.2	275.8	279.4	283.0	286.6	293.7	297.3	304.5	308.1	322.4
42.5°	257.9	257.9	261.5	268.7	272.2	275.8	283.0	286.6	293.7	297.3	311.6
45°	250.7	254.3	257.9	261.5	261.5	265.1	272.2	279.4	283.0	290.1	304.5
47.5°	240.0	240.0	247.2	250.7	257.9	261.5	268.7	272.2	279.4	283.0	297.3
50°	232.8	236.4	243.6	247.2	254.3	257.9	268.7	275.8	286.6	293.7	300.9
52.5°	225.7	229.2	236.4	240.0	247.2	250.7	265.1	279.4	290.1	304.5	304.5
55°	218.5	218.5	225.7	236.4	243.6	250.7	257.9	268.7	275.8	283.0	283.0
57.5°	207.8	211.3	218.5	229.2	236.4	243.6	250.7	257.9	261.5	268.7	265.1
60°	200.6	200.6	211.3	222.1	232.8	243.6	243.6	243.6	240.0	240.0	240.0
62.5°	189.8	193.4	207.8	225.7	240.0	254.3	243.6	232.8	222.1	211.3	214.9
65°	182.7	186.3	193.4	204.2	211.3	218.5	211.3	207.8	200.6	193.4	197.0
67.5°	168.4	171.9	175.5	175.5	179.1	179.1	179.1	179.1	179.1	179.1	182.7
70°	157.6	157.6	157.6	161.2	161.2	161.2	161.2	161.2	161.2	161.2	164.8
72.5°	143.3	143.3	143.3	143.3	143.3	143.3	143.3	143.3	143.3	143.3	146.9
75°	125.4	125.4	125.4	125.4	125.4	125.4	125.4	125.4	125.4	125.4	129.0
77.5°	111.0	111.0	111.0	111.0	111.0	111.0	111.0	111.0	107.5	107.5	111.0
80°	93.1	93.1	93.1	93.1	89.6	89.6	89.6	89.6	89.6	89.6	93.1
82.5°	75.2	75.2	75.2	75.2	71.6	71.6	71.6	71.6	68.1	68.1	71.6
85°	68.1	71.6	71.6	75.2	75.2	75.2	71.6	68.1	64.5	60.9	60.9
87.5°	28.7	28.7	28.7	28.7	25.1	25.1	25.1	25.1	25.1	25.1	25.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2482.3	2489.5	2496.7	2507.4	2521.7	2532.5	2543.2	2564.7	2589.8	2611.3	2632.8
5°	2228.0	2245.9	2263.8	2285.3	2306.8	2324.7	2346.2	2389.2	2432.2	2471.6	2514.6
7.5°	1826.8	1851.9	1873.4	1909.2	1941.5	1977.3	2009.5	2063.2	2113.4	2167.1	2217.3
10°	1493.7	1522.4	1551.0	1597.6	1647.7	1694.3	1740.9	1783.8	1830.4	1873.4	1916.4
12.5°	1350.4	1382.7	1418.5	1447.1	1479.4	1508.0	1536.7	1586.8	1637.0	1687.1	1737.3
15°	1232.2	1268.0	1303.9	1339.7	1371.9	1407.7	1440.0	1483.0	1529.5	1572.5	1615.5
17.5°	1096.1	1131.9	1171.3	1210.7	1250.1	1289.5	1328.9	1389.8	1450.7	1508.0	1568.9
20°	924.2	974.3	1020.9	1074.6	1128.3	1182.1	1235.8	1300.3	1364.7	1425.6	1490.1
22.5°	752.2	798.8	845.4	909.8	974.3	1035.2	1099.7	1185.6	1268.0	1354.0	1436.4
25°	626.9	669.8	712.8	784.5	852.5	924.2	992.2	1096.1	1196.4	1300.3	1400.6
27.5°	540.9	580.3	619.7	694.9	770.1	841.8	917.0	1031.6	1142.7	1257.3	1368.3
30°	501.5	526.6	551.6	623.3	694.9	763.0	834.6	945.7	1056.7	1167.7	1278.8
32.5°	437.0	458.5	480.0	544.5	608.9	669.8	734.3	848.9	960.0	1074.6	1185.6
35°	386.9	404.8	422.7	483.6	540.9	601.8	659.1	773.7	888.3	1003.0	1117.6
37.5°	358.2	376.1	390.4	444.2	501.5	555.2	608.9	723.6	834.6	949.2	1060.3
40°	336.7	347.5	361.8	415.5	465.7	519.4	569.5	673.4	780.9	884.8	988.6
42.5°	322.4	336.7	347.5	394.0	444.2	490.7	537.3	637.6	737.9	834.6	934.9
45°	318.8	333.1	347.5	386.9	426.3	462.1	501.5	598.2	694.9	791.6	888.3
47.5°	311.6	322.4	336.7	368.9	397.6	429.8	458.5	555.2	651.9	745.1	841.8
50°	308.1	311.6	318.8	347.5	376.1	404.8	433.4	530.1	626.9	723.6	820.3
52.5°	304.5	304.5	304.5	329.5	354.6	376.1	401.2	497.9	598.2	694.9	791.6
55°	283.0	279.4	279.4	304.5	326.0	351.0	372.5	469.2	566.0	659.1	755.8
57.5°	261.5	257.9	254.3	275.8	297.3	318.8	340.3	437.0	537.3	634.0	730.7
60°	240.0	236.4	236.4	257.9	275.8	297.3	315.2	415.5	512.2	612.5	709.2
62.5°	214.9	218.5	218.5	236.4	257.9	275.8	293.7	394.0	497.9	598.2	698.5
65°	197.0	200.6	200.6	222.1	243.6	265.1	286.6	383.3	483.6	580.3	677.0
67.5°	182.7	186.3	186.3	211.3	232.8	257.9	279.4	365.4	454.9	540.9	626.9
70°	168.4	168.4	171.9	197.0	222.1	247.2	272.2	347.5	422.7	494.3	569.5
72.5°	150.4	154.0	157.6	182.7	204.2	229.2	250.7	318.8	386.9	454.9	523.0
75°	132.5	136.1	139.7	161.2	182.7	204.2	225.7	290.1	351.0	415.5	476.4
77.5°	118.2	121.8	125.4	143.3	161.2	179.1	197.0	243.6	293.7	340.3	386.9
80°	96.7	96.7	100.3	114.6	129.0	139.7	154.0	186.3	218.5	247.2	279.4
82.5°	71.6	75.2	75.2	86.0	93.1	103.9	111.0	129.0	143.3	161.2	175.5
85°	60.9	57.3	57.3	64.5	68.1	75.2	78.8	89.6	96.7	107.5	114.6
87.5°	25.1	21.5	21.5	25.1	32.2	35.8	39.4	39.4	43.0	43.0	43.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2643.5	2650.7	2661.4	2668.6	2686.5	2700.8	2718.8	2733.1	2743.8	2761.7	2754.6
5°	2546.8	2579.1	2611.3	2643.5	2668.6	2693.7	2715.2	2740.2	2768.9	2822.6	2837.0
7.5°	2260.3	2303.2	2342.6	2385.6	2435.8	2485.9	2536.1	2586.2	2632.8	2700.8	2743.8
10°	1977.3	2038.2	2095.5	2156.4	2202.9	2249.5	2292.5	2339.1	2403.5	2471.6	2550.4
12.5°	1798.2	1859.1	1920.0	1980.9	2048.9	2113.4	2181.5	2245.9	2306.8	2360.6	2450.1
15°	1680.0	1748.0	1812.5	1877.0	1959.4	2038.2	2120.6	2199.4	2288.9	2360.6	2421.4
17.5°	1651.3	1733.7	1812.5	1894.9	1980.9	2066.8	2152.8	2238.8	2328.3	2435.8	2514.6
20°	1601.2	1712.2	1823.2	1934.3	2045.3	2152.8	2263.8	2371.3	2489.5	2618.5	2654.3
22.5°	1572.5	1705.0	1841.2	1973.7	2124.1	2278.2	2428.6	2579.1	2704.4	2801.1	2908.6
25°	1568.9	1733.7	1902.1	2066.8	2256.7	2442.9	2632.8	2819.0	2980.2	3077.0	3162.9
27.5°	1565.3	1765.9	1962.9	2160.0	2392.8	2622.0	2854.9	3084.1	3234.6	3374.3	3445.9
30°	1522.4	1762.4	2005.9	2245.9	2507.4	2768.9	3030.4	3291.9	3445.9	3542.6	3578.4
32.5°	1468.6	1751.6	2034.6	2317.6	2614.9	2912.2	3205.9	3503.2	3625.0	3707.4	3678.7
35°	1425.6	1737.3	2045.3	2353.4	2668.6	2987.4	3302.6	3617.8	3793.4	3908.0	3861.4
37.5°	1386.2	1712.2	2038.2	2364.1	2733.1	3102.0	3471.0	3839.9	4008.3	4130.1	4076.3
40°	1339.7	1687.1	2038.2	2385.6	2808.3	3227.4	3650.1	4069.2	4287.7	4391.6	4309.2
42.5°	1300.3	1662.1	2027.4	2389.2	2840.5	3291.9	3743.2	4194.5	4438.1	4585.0	4481.1
45°	1250.1	1611.9	1970.1	2331.9	2829.8	3327.7	3822.0	4319.9	4602.9	4717.5	4574.2
47.5°	1196.4	1554.6	1909.2	2263.8	2794.0	3324.1	3854.3	4384.4	4645.9	4782.0	4649.5
50°	1178.5	1536.7	1891.3	2249.5	2822.6	3399.3	3972.5	4545.6	4735.4	4846.5	4671.0
52.5°	1174.9	1554.6	1937.9	2317.6	2894.3	3467.4	4044.1	4617.2	4771.3	4889.5	4731.8
55°	1164.2	1576.1	1984.4	2392.8	2994.6	3599.9	4201.7	4803.5	4957.5	5043.5	4925.3
57.5°	1174.9	1619.1	2059.7	2503.8	3123.5	3743.2	4362.9	4982.6	5168.9	5229.7	5204.7
60°	1182.1	1654.9	2124.1	2597.0	3202.3	3807.7	4413.0	5018.4	5211.8	5362.3	5390.9
62.5°	1164.2	1629.8	2091.9	2557.6	3105.6	3653.7	4201.7	4749.8	5068.6	5290.6	5419.6
65°	1110.4	1540.3	1973.7	2403.5	2908.6	3417.2	3922.3	4427.4	4764.1	5093.6	5197.5
67.5°	992.2	1357.6	1723.0	2088.3	2528.9	2969.5	3406.5	3847.1	4269.8	4588.6	4731.8
70°	859.7	1146.2	1436.4	1723.0	2124.1	2525.3	2926.5	3327.7	3700.2	4051.3	4187.4
72.5°	748.6	970.7	1196.4	1418.5	1705.0	1988.0	2274.6	2557.6	2998.2	3349.2	3481.7
75°	637.6	798.8	956.4	1117.6	1314.6	1511.6	1705.0	1902.1	2213.7	2528.9	2661.4
77.5°	490.7	598.2	702.1	806.0	942.1	1074.6	1210.7	1343.3	1561.8	1798.2	1866.2
80°	340.3	401.2	458.5	519.4	626.9	734.3	841.8	949.2	1092.5	1225.1	1328.9
82.5°	211.3	250.7	286.6	322.4	408.4	494.3	576.7	662.7	720.0	727.2	831.0
85°	136.1	161.2	182.7	204.2	254.3	308.1	358.2	408.4	365.4	340.3	404.8
87.5°	53.7	68.1	78.8	89.6	86.0	82.4	78.8	75.2	64.5	57.3	71.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2761.7	2772.5	2783.2	2790.4	2801.1	2804.7	2808.3	2808.3	2811.9	2815.5	2822.6
5°	2894.3	2915.8	2937.3	2955.2	2976.7	2994.6	3008.9	3026.8	3041.1	3041.1	3037.6
7.5°	2783.2	2837.0	2890.7	2944.4	2998.2	3037.6	3073.4	3112.8	3148.6	3155.8	3162.9
10°	2636.4	2693.7	2747.4	2804.7	2858.5	2919.3	2976.7	3034.0	3094.9	3105.6	3119.9
12.5°	2500.3	2568.3	2636.4	2700.8	2768.9	2811.9	2854.9	2894.3	2937.3	2965.9	2994.6
15°	2496.7	2554.0	2611.3	2665.0	2722.3	2747.4	2772.5	2794.0	2819.0	2819.0	2822.6
17.5°	2579.1	2614.9	2650.7	2682.9	2718.8	2722.3	2729.5	2733.1	2736.7	2725.9	2715.2
20°	2740.2	2754.6	2768.9	2783.2	2797.6	2772.5	2751.0	2725.9	2700.8	2672.2	2647.1
22.5°	2976.7	2944.4	2912.2	2879.9	2847.7	2804.7	2758.2	2715.2	2668.6	2632.8	2597.0
25°	3198.7	3159.3	3119.9	3080.5	3041.1	2948.0	2854.9	2758.2	2665.0	2625.6	2586.2
27.5°	3496.1	3435.2	3374.3	3313.4	3252.5	3127.1	3001.7	2876.4	2751.0	2682.9	2618.5
30°	3567.7	3499.6	3431.6	3359.9	3291.9	3170.1	3051.9	2930.1	2808.3	2729.5	2654.3
32.5°	3671.6	3592.8	3514.0	3435.2	3356.4	3238.1	3119.9	2998.2	2879.9	2808.3	2733.1
35°	3843.5	3754.0	3664.4	3571.3	3481.7	3359.9	3241.7	3119.9	2998.2	2915.8	2837.0
37.5°	3990.4	3886.5	3782.6	3678.7	3574.9	3467.4	3356.4	3248.9	3137.8	3055.5	2976.7
40°	4155.1	4040.5	3925.9	3814.9	3700.2	3599.9	3499.6	3395.8	3295.5	3231.0	3166.5
42.5°	4298.4	4158.7	4022.6	3886.5	3746.8	3678.7	3614.3	3546.2	3478.1	3445.9	3410.1
45°	4398.7	4269.8	4137.2	4008.3	3879.3	3829.2	3779.0	3728.9	3678.7	3711.0	3743.2
47.5°	4441.7	4337.8	4237.5	4137.2	4033.4	4051.3	4069.2	4083.5	4101.4	4144.4	4191.0
50°	4481.1	4423.8	4362.9	4305.6	4244.7	4312.8	4377.2	4445.3	4513.3	4602.9	4692.4
52.5°	4559.9	4527.7	4499.0	4466.8	4434.5	4552.7	4671.0	4789.2	4907.4	5007.7	5108.0
55°	4796.3	4771.3	4746.2	4717.5	4692.4	4860.8	5025.6	5193.9	5362.3	5466.2	5570.0
57.5°	5122.3	5108.0	5090.1	5075.7	5057.8	5222.6	5383.8	5545.0	5709.7	5810.0	5913.9
60°	5369.4	5373.0	5373.0	5376.6	5376.6	5502.0	5627.4	5756.3	5881.7	5967.6	6057.2
62.5°	5502.0	5494.8	5487.7	5480.5	5473.3	5577.2	5681.1	5785.0	5888.8	5953.3	6017.8
65°	5358.7	5398.1	5437.5	5476.9	5516.3	5530.6	5541.4	5555.7	5566.5	5605.9	5645.3
67.5°	4878.7	4957.5	5032.7	5111.5	5186.8	5133.0	5082.9	5029.2	4975.4	4986.2	4993.3
70°	4345.0	4434.5	4527.7	4617.2	4706.8	4581.4	4456.0	4327.1	4201.7	4158.7	4115.7
72.5°	3664.4	3743.2	3825.6	3904.4	3983.2	3829.2	3678.7	3524.7	3370.7	3295.5	3220.2
75°	2801.1	2894.3	2991.0	3084.1	3177.3	3005.3	2829.8	2657.9	2482.3	2432.2	2385.6
77.5°	2041.8	2152.8	2263.8	2374.9	2485.9	2331.9	2177.9	2020.3	1866.2	1837.6	1808.9
80°	1486.5	1572.5	1654.9	1740.9	1823.2	1733.7	1644.1	1554.6	1465.0	1461.5	1457.9
82.5°	1003.0	1078.2	1149.8	1225.1	1296.7	1260.9	1228.6	1192.8	1157.0	1192.8	1232.2
85°	515.8	619.7	727.2	831.0	934.9	924.2	917.0	906.3	895.5	942.1	985.1
87.5°	103.9	193.4	283.0	368.9	458.5	437.0	415.5	390.4	368.9	383.3	394.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2826.2	2829.8	2829.8	2829.8	2829.8	2829.8	2822.6	2819.0	2811.9	2804.7	2794.0
5°	3037.6	3034.0	3019.6	3005.3	2987.4	2973.1	2962.3	2948.0	2937.3	2922.9	2901.4
7.5°	3170.1	3177.3	3152.2	3130.7	3105.6	3080.5	3055.5	3030.4	3005.3	2980.2	2930.1
10°	3130.7	3141.4	3127.1	3112.8	3094.9	3080.5	3051.9	3019.6	2991.0	2958.7	2897.9
12.5°	3019.6	3048.3	3041.1	3034.0	3026.8	3019.6	3001.7	2980.2	2962.3	2940.8	2872.8
15°	2822.6	2822.6	2826.2	2829.8	2829.8	2833.4	2837.0	2840.5	2844.1	2847.7	2808.3
17.5°	2704.4	2693.7	2693.7	2693.7	2693.7	2693.7	2708.0	2725.9	2740.2	2754.6	2743.8
20°	2618.5	2593.4	2589.8	2589.8	2586.2	2582.6	2607.7	2636.4	2661.4	2686.5	2700.8
22.5°	2561.1	2525.3	2521.7	2518.2	2514.6	2511.0	2543.2	2575.5	2607.7	2639.9	2690.1
25°	2546.8	2507.4	2511.0	2514.6	2514.6	2518.2	2543.2	2568.3	2593.4	2618.5	2704.4
27.5°	2550.4	2485.9	2489.5	2493.1	2493.1	2496.7	2536.1	2571.9	2611.3	2647.1	2754.6
30°	2575.5	2500.3	2493.1	2485.9	2478.8	2471.6	2525.3	2579.1	2632.8	2686.5	2768.9
32.5°	2661.4	2589.8	2571.9	2554.0	2536.1	2518.2	2582.6	2643.5	2708.0	2768.9	2837.0
35°	2754.6	2675.8	2668.6	2661.4	2650.7	2643.5	2700.8	2761.7	2819.0	2876.4	2937.3
37.5°	2894.3	2815.5	2808.3	2797.6	2790.4	2779.6	2844.1	2905.0	2969.5	3030.4	3084.1
40°	3102.0	3037.6	3034.0	3034.0	3030.4	3026.8	3077.0	3130.7	3180.8	3231.0	3266.8
42.5°	3377.8	3345.6	3356.4	3370.7	3381.4	3392.2	3431.6	3474.6	3514.0	3553.4	3542.6
45°	3775.4	3807.7	3811.3	3814.9	3818.4	3822.0	3832.8	3847.1	3857.8	3868.6	3825.6
47.5°	4233.9	4276.9	4298.4	4319.9	4337.8	4359.3	4345.0	4327.1	4312.8	4294.8	4187.4
50°	4778.4	4868.0	4864.4	4860.8	4853.6	4850.1	4821.4	4792.7	4760.5	4731.8	4574.2
52.5°	5208.3	5308.6	5326.5	5344.4	5362.3	5380.2	5326.5	5272.7	5215.4	5161.7	4964.7
55°	5670.3	5774.2	5777.8	5781.4	5781.4	5785.0	5709.7	5634.5	5555.7	5480.5	5276.3
57.5°	6014.2	6114.5	6103.8	6096.6	6085.9	6075.1	5985.6	5896.0	5806.5	5716.9	5512.7
60°	6143.2	6229.1	6207.6	6186.1	6161.1	6139.6	6071.5	6003.5	5931.8	5863.8	5666.8
62.5°	6082.3	6146.7	6114.5	6085.9	6053.6	6021.4	5935.4	5845.9	5759.9	5670.3	5527.1
65°	5681.1	5720.5	5677.5	5638.1	5598.7	5555.7	5484.1	5412.4	5337.2	5265.6	5168.9
67.5°	5004.1	5011.2	5007.7	5004.1	5000.5	4996.9	4893.0	4789.2	4681.7	4577.8	4570.7
70°	4076.3	4033.4	4040.5	4051.3	4058.4	4065.6	3986.8	3911.6	3832.8	3754.0	3789.8
72.5°	3145.0	3069.8	3087.7	3109.2	3127.1	3145.0	3080.5	3019.6	2955.2	2890.7	2940.8
75°	2335.5	2288.9	2306.8	2328.3	2346.2	2364.1	2339.1	2314.0	2285.3	2260.3	2306.8
77.5°	1780.3	1751.6	1755.2	1755.2	1758.8	1758.8	1762.4	1769.5	1773.1	1776.7	1826.8
80°	1450.7	1447.1	1443.6	1440.0	1432.8	1429.2	1465.0	1500.9	1536.7	1572.5	1597.6
82.5°	1268.0	1303.9	1282.4	1264.5	1243.0	1221.5	1253.7	1285.9	1318.2	1350.4	1339.7
85°	1031.6	1074.6	1035.2	995.8	952.8	913.4	942.1	967.1	995.8	1020.9	1006.5
87.5°	408.4	419.1	354.6	293.7	229.2	164.8	261.5	354.6	451.3	544.5	558.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908

CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1	2579.1
2.5°	2783.2	2768.9	2758.2	2754.6	2747.4	2743.8	2736.7	2729.5	2718.8	2711.6	2700.8
5°	2876.4	2854.9	2829.8	2794.0	2761.7	2725.9	2690.1	2657.9	2625.6	2589.8	2557.6
7.5°	2879.9	2829.8	2779.6	2733.1	2682.9	2636.4	2586.2	2543.2	2496.7	2450.1	2407.1
10°	2840.5	2779.6	2718.8	2657.9	2600.5	2539.7	2478.8	2428.6	2374.9	2321.1	2271.0
12.5°	2808.3	2740.2	2672.2	2600.5	2532.5	2460.8	2389.2	2339.1	2288.9	2238.8	2188.6
15°	2768.9	2725.9	2686.5	2622.0	2557.6	2493.1	2428.6	2360.6	2296.1	2228.0	2160.0
17.5°	2736.7	2725.9	2715.2	2672.2	2629.2	2582.6	2539.7	2471.6	2403.5	2331.9	2263.8
20°	2718.8	2733.1	2747.4	2725.9	2704.4	2679.4	2657.9	2607.7	2557.6	2503.8	2453.7
22.5°	2740.2	2794.0	2844.1	2847.7	2854.9	2858.5	2862.0	2815.5	2768.9	2718.8	2672.2
25°	2790.4	2876.4	2962.3	3008.9	3055.5	3105.6	3152.2	3123.5	3094.9	3066.2	3037.6
27.5°	2858.5	2965.9	3073.4	3141.4	3205.9	3274.0	3342.0	3338.4	3334.9	3327.7	3324.1
30°	2847.7	2930.1	3012.5	3094.9	3177.3	3259.6	3342.0	3385.0	3424.4	3467.4	3510.4
32.5°	2908.6	2976.7	3048.3	3134.3	3220.2	3309.8	3395.8	3485.3	3571.3	3660.8	3750.4
35°	3001.7	3062.6	3127.1	3220.2	3317.0	3410.1	3506.8	3614.3	3725.3	3836.3	3943.8
37.5°	3141.4	3195.2	3252.5	3331.3	3413.7	3492.5	3574.9	3732.5	3890.1	4051.3	4208.9
40°	3302.6	3338.4	3374.3	3449.5	3524.7	3599.9	3675.2	3872.2	4069.2	4266.2	4463.2
42.5°	3535.5	3524.7	3514.0	3574.9	3639.3	3700.2	3764.7	3943.8	4122.9	4302.0	4481.1
45°	3782.6	3739.6	3696.6	3725.3	3757.5	3786.2	3818.4	4001.1	4183.8	4370.1	4552.7
47.5°	4079.9	3972.5	3865.0	3839.9	3814.9	3786.2	3761.1	3958.1	4155.1	4355.7	4552.7
50°	4416.6	4255.4	4097.8	4033.4	3965.3	3900.8	3832.8	3994.0	4158.7	4323.5	4484.7
52.5°	4767.7	4567.1	4370.1	4269.8	4169.5	4065.6	3965.3	4101.4	4241.1	4380.8	4516.9
55°	5068.6	4864.4	4656.6	4538.4	4420.2	4302.0	4183.8	4319.9	4456.0	4592.1	4728.3
57.5°	5308.6	5104.4	4900.2	4789.2	4674.5	4563.5	4448.9	4577.8	4710.4	4842.9	4971.8
60°	5473.3	5276.3	5079.3	4971.8	4864.4	4756.9	4649.5	4803.5	4957.5	5115.1	5269.2
62.5°	5387.4	5244.1	5100.8	5054.2	5007.7	4957.5	4910.9	5057.8	5201.1	5348.0	5494.8
65°	5072.1	4975.4	4878.7	4925.3	4975.4	5022.0	5072.1	5168.9	5265.6	5365.9	5462.6
67.5°	4559.9	4552.7	4542.0	4645.9	4749.8	4857.2	4961.1	5025.6	5086.5	5150.9	5215.4
70°	3825.6	3865.0	3900.8	4079.9	4259.0	4438.1	4617.2	4642.3	4667.4	4692.4	4717.5
72.5°	2994.6	3044.7	3098.4	3334.9	3567.7	3804.1	4040.5	4026.2	4011.9	3994.0	3979.6
75°	2357.0	2403.5	2453.7	2672.2	2890.7	3109.2	3327.7	3266.8	3209.5	3148.6	3087.7
77.5°	1880.6	1930.7	1984.4	2188.6	2392.8	2600.5	2804.7	2657.9	2511.0	2364.1	2217.3
80°	1619.1	1644.1	1665.6	1805.3	1941.5	2081.2	2220.9	2070.4	1916.4	1762.4	1611.9
82.5°	1328.9	1314.6	1303.9	1386.2	1468.6	1551.0	1633.4	1490.1	1346.8	1200.0	1056.7
85°	992.2	977.9	963.6	1006.5	1049.5	1096.1	1139.1	974.3	809.5	641.2	476.4
87.5°	576.7	591.0	605.4	651.9	698.5	748.6	795.2	626.9	458.5	286.6	118.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671908
 CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2579.1	2579.1
2.5°	2679.4	2661.4
5°	2532.5	2507.4
7.5°	2371.3	2339.1
10°	2224.4	2181.5
12.5°	2131.3	2077.6
15°	2095.5	2031.0
17.5°	2202.9	2142.0
20°	2367.7	2285.3
22.5°	2568.3	2468.0
25°	2915.8	2794.0
27.5°	3198.7	3073.4
30°	3374.3	3238.1
32.5°	3567.7	3388.6
35°	3768.3	3596.3
37.5°	4011.9	3818.4
40°	4262.6	4062.0
42.5°	4348.6	4219.6
45°	4431.0	4309.2
47.5°	4448.9	4348.6
50°	4466.8	4452.5
52.5°	4516.9	4513.3
55°	4731.8	4735.4
57.5°	4996.9	5018.4
60°	5240.5	5215.4
62.5°	5365.9	5236.9
65°	5279.9	5100.8
67.5°	5022.0	4828.6
70°	4456.0	4194.5
72.5°	3750.4	3521.1
75°	2890.7	2697.3
77.5°	2056.1	1894.9
80°	1447.1	1285.9
82.5°	927.7	798.8
85°	419.1	365.4
87.5°	118.2	114.6
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671908
CATALOG NUMBER: CCP-SA-2D-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)