

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P675961

Luminaire Tested: **CCW-SA-2C-727-U-SLR**

Issue Date: 04/25/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P675961  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/25/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCW-SA-2C-727-U-SLR  
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/  
SLR distribution lens  
Light Source: (32) 2700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6275 lumens  
Efficiency: N/A  
Efficacy: 101.0 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2

Input Watts (W): 62.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 8.9 fc  
 Type IV - Short - N/A

REPORT NUMBER: P675961  
CATALOG NUMBER: CCW-SA-2C-727-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral      - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1291.1	0.0	1291.1
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	4983.9	0.0	4983.9
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	6275.0	0.0	6275.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.7	2.5
10°-20°	328.7	5.2
20°-30°	481.0	7.7
30°-40°	677.6	10.8
40°-50°	931.1	14.8
50°-60°	1269.1	20.2
60°-70°	1389.1	22.1
70°-80°	802.2	12.8
80°-90°	240.5	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6275.0	100.0
0°-180°	6275.0	100.0




REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	644.5	10.3			
FM (30°-60°)	2289.9	36.5			
FH (60°-80°)	1845.2	29.4			G2/5000
FVH (80°-90°)	204.2	3.3			G2/225
BL (0°-30°)	321.0	5.1	B1/500		
BM (30°-60°)	587.9	9.4	B1/1000		
BH (60°-80°)	346.0	5.5	B1/500		G1/500
BVH (80°-90°)	36.2	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**  
 Type IV Short





REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	2067.9	2056.7	2048.4	2040.0	2028.9	2020.6	2009.4	1998.3	1984.4	1973.2	1959.3
5°	1948.2	1914.8	1881.4	1861.9	1839.6	1820.2	1797.9	1772.9	1747.8	1720.0	1694.9
7.5°	1817.4	1775.6	1733.9	1700.5	1664.3	1630.9	1594.7	1564.1	1533.5	1502.9	1472.3
10°	1694.9	1656.0	1617.0	1575.3	1530.7	1489.0	1444.4	1402.7	1360.9	1319.2	1277.5
12.5°	1614.2	1566.9	1522.4	1475.1	1430.5	1383.2	1335.9	1296.9	1258.0	1216.2	1177.3
15°	1578.0	1533.5	1491.8	1444.4	1397.1	1349.8	1302.5	1258.0	1216.2	1171.7	1127.2
17.5°	1664.3	1600.3	1536.3	1475.1	1413.8	1352.6	1291.4	1235.7	1180.0	1124.4	1068.7
20°	1775.6	1694.9	1617.0	1541.9	1463.9	1388.8	1310.9	1232.9	1155.0	1077.1	999.1
22.5°	1917.6	1825.7	1736.7	1639.3	1539.1	1441.7	1341.5	1244.1	1146.6	1046.5	949.0
25°	2170.8	2062.3	1953.8	1814.6	1672.7	1533.5	1391.6	1263.5	1138.3	1010.3	882.3
27.5°	2387.9	2240.4	2095.7	1928.7	1761.7	1594.7	1427.7	1280.2	1135.5	988.0	840.5
30°	2515.9	2371.2	2226.5	2023.3	1822.9	1619.8	1416.6	1252.4	1091.0	926.8	762.6
32.5°	2632.8	2471.4	2310.0	2087.3	1861.9	1639.3	1413.8	1232.9	1054.8	873.9	693.0
35°	2794.3	2616.1	2440.8	2182.0	1923.1	1664.3	1405.5	1219.0	1029.8	843.3	654.0
37.5°	2966.8	2746.9	2529.9	2243.2	1956.5	1669.9	1383.2	1199.5	1015.8	832.2	648.5
40°	3156.1	2888.9	2624.5	2307.2	1992.7	1675.4	1358.2	1174.5	990.8	804.3	620.6
42.5°	3278.5	2989.1	2699.6	2357.3	2017.8	1675.4	1333.1	1152.2	971.3	787.6	606.7
45°	3348.1	3067.0	2788.7	2418.5	2048.4	1678.2	1308.1	1130.0	951.8	770.9	592.8
47.5°	3378.7	3117.1	2855.5	2465.9	2079.0	1689.4	1299.7	1118.8	935.1	754.2	570.5
50°	3459.4	3228.4	2997.4	2580.0	2165.3	1747.8	1330.3	1135.5	943.5	748.7	553.8
52.5°	3506.7	3309.1	3111.5	2682.9	2254.3	1825.7	1397.1	1180.0	963.0	745.9	528.8
55°	3679.3	3490.0	3300.8	2844.4	2385.1	1928.7	1469.5	1230.1	990.8	748.7	509.3
57.5°	3899.2	3698.8	3501.2	3008.6	2515.9	2023.3	1530.7	1274.7	1015.8	759.8	501.0
60°	4052.2	3857.4	3665.4	3142.2	2616.1	2092.9	1566.9	1299.7	1032.5	762.6	495.4
62.5°	4068.9	3818.5	3570.8	3061.4	2552.1	2040.0	1530.7	1271.9	1013.1	751.4	492.6
65°	3963.2	3670.9	3378.7	2891.7	2404.6	1917.6	1430.5	1194.0	957.4	718.0	481.5
67.5°	3751.7	3409.3	3067.0	2621.7	2176.4	1731.1	1285.8	1082.6	882.3	679.1	475.9
70°	3259.0	2958.5	2660.7	2273.8	1889.7	1502.9	1116.0	949.0	784.8	617.9	450.9
72.5°	2735.8	2454.7	2176.4	1861.9	1550.2	1235.7	921.2	796.0	670.7	542.7	417.5
75°	2095.7	1884.2	1675.4	1441.7	1207.9	971.3	737.5	645.7	553.8	462.0	370.2
77.5°	1472.3	1358.2	1246.8	1071.5	896.2	720.8	545.5	484.3	423.0	361.8	300.6
80°	999.1	935.1	873.9	748.7	623.4	495.4	370.2	331.2	289.4	250.5	208.7
82.5°	620.6	617.9	612.3	526.0	439.7	353.5	267.2	233.8	203.2	169.8	136.4
85°	283.9	331.2	375.7	328.4	281.1	233.8	186.5	164.2	141.9	116.9	94.6
87.5°	89.1	108.5	125.2	119.7	111.3	105.8	97.4	83.5	69.6	55.7	41.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	1948.2	1939.8	1928.7	1917.6	1903.7	1892.5	1878.6	1864.7	1861.9	1856.3	1853.6
5°	1678.2	1661.5	1642.0	1625.3	1608.6	1589.2	1572.5	1553.0	1539.1	1522.4	1508.5
7.5°	1441.7	1413.8	1383.2	1352.6	1324.8	1296.9	1266.3	1238.5	1224.6	1210.7	1196.7
10°	1252.4	1224.6	1199.5	1171.7	1152.2	1135.5	1116.0	1096.6	1079.9	1063.2	1046.5
12.5°	1157.8	1138.3	1118.8	1099.3	1077.1	1057.6	1035.3	1013.1	993.6	976.9	957.4
15°	1099.3	1071.5	1040.9	1013.1	982.4	954.6	924.0	893.4	871.1	851.6	829.4
17.5°	1029.8	988.0	949.0	907.3	873.9	840.5	804.3	770.9	745.9	718.0	693.0
20°	951.8	904.5	854.4	807.1	768.1	732.0	693.0	654.0	626.2	595.6	567.8
22.5°	885.0	823.8	759.8	695.8	654.0	612.3	567.8	526.0	501.0	473.1	448.1
25°	812.7	745.9	676.3	606.7	565.0	520.4	478.7	434.2	414.7	398.0	378.5
27.5°	773.7	706.9	637.3	570.5	531.6	489.8	450.9	409.1	395.2	378.5	364.6
30°	695.8	631.8	565.0	498.2	470.3	445.3	417.5	389.6	384.1	381.3	375.7
32.5°	626.2	559.4	492.6	425.8	400.8	375.7	350.7	325.6	322.8	317.3	314.5
35°	590.0	526.0	459.2	395.2	372.9	347.9	325.6	300.6	295.0	286.7	281.1
37.5°	581.7	514.9	445.3	378.5	356.2	334.0	308.9	286.7	281.1	275.5	270.0
40°	559.4	495.4	434.2	370.2	347.9	325.6	300.6	278.3	272.7	267.2	261.6
42.5°	542.7	481.5	417.5	353.5	334.0	314.5	292.2	272.7	267.2	261.6	253.3
45°	528.8	464.8	398.0	334.0	320.1	306.1	289.4	275.5	270.0	261.6	256.0
47.5°	506.5	445.3	381.3	317.3	303.4	292.2	278.3	264.4	258.8	253.3	247.7
50°	489.8	425.8	361.8	297.8	286.7	275.5	264.4	253.3	253.3	256.0	256.0
52.5°	467.6	406.3	345.1	283.9	272.7	261.6	250.5	239.3	242.1	244.9	247.7
55°	448.1	389.6	328.4	267.2	256.0	244.9	231.0	219.9	222.7	225.4	228.2
57.5°	439.7	378.5	317.3	256.0	244.9	231.0	219.9	206.0	206.0	206.0	206.0
60°	434.2	370.2	308.9	244.9	231.0	219.9	206.0	192.0	189.3	189.3	186.5
62.5°	431.4	367.4	306.1	242.1	225.4	211.5	194.8	178.1	175.3	172.6	169.8
65°	420.3	361.8	300.6	239.3	219.9	203.2	183.7	164.2	161.4	161.4	158.6
67.5°	417.5	356.2	297.8	236.6	217.1	194.8	175.3	153.1	150.3	147.5	144.7
70°	395.2	342.3	286.7	231.0	208.7	189.3	167.0	144.7	141.9	136.4	133.6
72.5°	367.4	320.1	270.0	219.9	197.6	175.3	153.1	130.8	128.0	125.2	119.7
75°	325.6	281.1	236.6	192.0	172.6	155.9	136.4	116.9	114.1	111.3	105.8
77.5°	267.2	231.0	197.6	161.4	147.5	133.6	119.7	105.8	103.0	100.2	94.6
80°	189.3	167.0	147.5	125.2	116.9	105.8	97.4	86.3	86.3	83.5	83.5
82.5°	125.2	114.1	103.0	91.8	86.3	80.7	75.1	69.6	69.6	66.8	66.8
85°	89.1	83.5	75.1	69.6	66.8	61.2	58.4	52.9	52.9	52.9	52.9
87.5°	41.7	41.7	39.0	39.0	36.2	36.2	33.4	30.6	30.6	30.6	30.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	1848.0	1839.6	1831.3	1820.2	1811.8	1800.7	1786.8	1775.6	1761.7	1761.7	1758.9
5°	1491.8	1483.4	1475.1	1463.9	1455.6	1444.4	1436.1	1425.0	1413.8	1413.8	1411.0
7.5°	1182.8	1166.1	1149.4	1130.0	1113.3	1102.1	1091.0	1077.1	1065.9	1057.6	1049.2
10°	1029.8	1013.1	993.6	976.9	957.4	943.5	929.6	912.9	899.0	887.8	876.7
12.5°	937.9	918.4	899.0	879.5	860.0	840.5	823.8	804.3	784.8	770.9	757.0
15°	807.1	787.6	768.1	748.7	729.2	706.9	684.6	659.6	637.3	626.2	617.9
17.5°	665.2	645.7	623.4	603.9	581.7	565.0	548.3	531.6	514.9	503.7	495.4
20°	537.1	514.9	492.6	470.3	448.1	437.0	425.8	414.7	403.6	395.2	389.6
22.5°	420.3	406.3	395.2	381.3	367.4	359.0	353.5	345.1	336.8	336.8	336.8
25°	359.0	350.7	345.1	336.8	328.4	325.6	322.8	317.3	314.5	311.7	311.7
27.5°	347.9	339.5	331.2	322.8	314.5	311.7	308.9	303.4	300.6	300.6	300.6
30°	370.2	367.4	364.6	361.8	359.0	353.5	345.1	339.5	331.2	325.6	320.1
32.5°	308.9	306.1	306.1	303.4	300.6	306.1	308.9	314.5	317.3	320.1	322.8
35°	272.7	267.2	261.6	256.0	250.5	247.7	244.9	242.1	239.3	239.3	236.6
37.5°	264.4	258.8	253.3	247.7	242.1	239.3	236.6	233.8	231.0	231.0	228.2
40°	256.0	250.5	247.7	242.1	236.6	233.8	231.0	225.4	222.7	219.9	219.9
42.5°	247.7	244.9	239.3	236.6	231.0	228.2	225.4	219.9	217.1	214.3	211.5
45°	247.7	242.1	236.6	231.0	225.4	222.7	217.1	214.3	208.7	208.7	206.0
47.5°	242.1	236.6	231.0	225.4	219.9	217.1	211.5	208.7	203.2	200.4	197.6
50°	256.0	247.7	236.6	228.2	217.1	214.3	208.7	206.0	200.4	197.6	194.8
52.5°	250.5	242.1	231.0	222.7	211.5	206.0	203.2	197.6	192.0	189.3	186.5
55°	231.0	222.7	217.1	208.7	200.4	194.8	189.3	183.7	178.1	175.3	175.3
57.5°	206.0	203.2	200.4	197.6	194.8	189.3	183.7	175.3	169.8	167.0	164.2
60°	183.7	186.5	189.3	192.0	194.8	186.5	178.1	169.8	161.4	158.6	155.9
62.5°	167.0	172.6	178.1	180.9	186.5	178.1	169.8	161.4	153.1	150.3	147.5
65°	155.9	158.6	158.6	161.4	161.4	155.9	153.1	147.5	141.9	139.2	139.2
67.5°	141.9	141.9	141.9	139.2	139.2	136.4	136.4	133.6	130.8	128.0	128.0
70°	128.0	128.0	128.0	125.2	125.2	122.5	122.5	119.7	116.9	116.9	114.1
72.5°	116.9	116.9	114.1	114.1	111.3	111.3	111.3	108.5	108.5	105.8	105.8
75°	103.0	103.0	100.2	100.2	97.4	97.4	97.4	94.6	94.6	94.6	91.8
77.5°	91.8	91.8	89.1	89.1	86.3	86.3	86.3	83.5	83.5	80.7	80.7
80°	80.7	80.7	77.9	77.9	75.1	75.1	72.4	72.4	69.6	69.6	66.8
82.5°	64.0	64.0	64.0	64.0	64.0	61.2	61.2	58.4	55.7	55.7	52.9
85°	52.9	52.9	52.9	50.1	50.1	50.1	47.3	47.3	44.5	41.7	41.7
87.5°	30.6	30.6	30.6	27.8	27.8	27.8	27.8	27.8	27.8	27.8	25.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	1758.9	1756.2	1745.0	1733.9	1745.0	1756.2	1756.2	1756.2	1753.4	1753.4	1753.4
5°	1411.0	1408.3	1402.7	1397.1	1397.1	1394.3	1399.9	1405.5	1411.0	1416.6	1422.2
7.5°	1038.1	1029.8	1021.4	1013.1	1018.6	1021.4	1029.8	1035.3	1043.7	1049.2	1063.2
10°	865.6	854.4	846.1	837.7	832.2	826.6	821.0	818.2	812.7	807.1	812.7
12.5°	740.3	726.4	712.5	695.8	693.0	690.2	684.6	679.1	673.5	668.0	665.2
15°	606.7	595.6	590.0	581.7	570.5	559.4	553.8	551.1	545.5	539.9	537.1
17.5°	484.3	473.1	464.8	456.4	453.6	448.1	448.1	448.1	448.1	448.1	448.1
20°	381.3	372.9	372.9	370.2	370.2	367.4	370.2	372.9	372.9	375.7	378.5
22.5°	334.0	334.0	331.2	328.4	331.2	331.2	334.0	336.8	339.5	342.3	345.1
25°	308.9	306.1	308.9	311.7	311.7	311.7	314.5	314.5	317.3	317.3	317.3
27.5°	297.8	297.8	300.6	300.6	303.4	303.4	303.4	300.6	300.6	297.8	297.8
30°	314.5	308.9	308.9	308.9	306.1	303.4	300.6	300.6	297.8	295.0	292.2
32.5°	325.6	328.4	325.6	320.1	317.3	311.7	308.9	303.4	300.6	295.0	289.4
35°	236.6	233.8	239.3	242.1	244.9	247.7	250.5	253.3	253.3	256.0	256.0
37.5°	228.2	225.4	225.4	222.7	222.7	222.7	222.7	222.7	219.9	219.9	222.7
40°	217.1	214.3	214.3	211.5	211.5	208.7	208.7	208.7	208.7	208.7	208.7
42.5°	208.7	206.0	206.0	206.0	206.0	203.2	203.2	200.4	200.4	197.6	197.6
45°	206.0	203.2	200.4	197.6	197.6	194.8	194.8	194.8	192.0	192.0	192.0
47.5°	194.8	192.0	192.0	189.3	189.3	186.5	186.5	186.5	183.7	183.7	183.7
50°	189.3	186.5	186.5	183.7	183.7	180.9	180.9	180.9	178.1	178.1	178.1
52.5°	180.9	178.1	178.1	178.1	175.3	172.6	172.6	172.6	169.8	169.8	169.8
55°	172.6	169.8	169.8	169.8	167.0	164.2	164.2	164.2	161.4	161.4	161.4
57.5°	161.4	158.6	158.6	155.9	155.9	155.9	155.9	155.9	153.1	153.1	153.1
60°	153.1	150.3	150.3	147.5	147.5	144.7	144.7	144.7	144.7	144.7	144.7
62.5°	144.7	141.9	139.2	136.4	139.2	139.2	139.2	139.2	136.4	136.4	136.4
65°	136.4	133.6	130.8	128.0	128.0	128.0	128.0	128.0	128.0	128.0	128.0
67.5°	125.2	122.5	119.7	116.9	119.7	119.7	119.7	119.7	119.7	119.7	119.7
70°	114.1	111.3	111.3	108.5	108.5	105.8	105.8	108.5	108.5	108.5	108.5
72.5°	103.0	100.2	100.2	97.4	97.4	97.4	97.4	97.4	97.4	97.4	97.4
75°	91.8	89.1	89.1	86.3	86.3	86.3	86.3	86.3	86.3	86.3	86.3
77.5°	77.9	75.1	75.1	75.1	75.1	75.1	75.1	77.9	77.9	77.9	77.9
80°	66.8	64.0	64.0	64.0	64.0	64.0	64.0	64.0	64.0	64.0	64.0
82.5°	52.9	50.1	50.1	50.1	50.1	50.1	50.1	50.1	50.1	50.1	50.1
85°	39.0	36.2	36.2	36.2	39.0	39.0	39.0	39.0	39.0	39.0	39.0
87.5°	25.0	22.3	22.3	22.3	25.0	25.0	25.0	25.0	22.3	22.3	22.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	1753.4	1753.4	1753.4	1750.6	1747.8	1745.0	1742.2	1750.6	1756.2	1764.5	1770.1
5°	1425.0	1430.5	1433.3	1441.7	1450.0	1458.4	1466.7	1472.3	1477.8	1480.6	1486.2
7.5°	1074.3	1088.2	1099.3	1110.5	1121.6	1130.0	1141.1	1149.4	1157.8	1166.1	1174.5
10°	815.5	821.0	823.8	834.9	843.3	854.4	862.8	871.1	879.5	885.0	893.4
12.5°	662.4	656.8	654.0	654.0	654.0	654.0	654.0	659.6	665.2	670.7	676.3
15°	534.4	531.6	528.8	526.0	523.2	517.7	514.9	520.4	526.0	531.6	537.1
17.5°	448.1	448.1	448.1	445.3	442.5	439.7	437.0	439.7	442.5	442.5	445.3
20°	384.1	386.9	389.6	392.4	392.4	395.2	395.2	398.0	400.8	400.8	403.6
22.5°	345.1	347.9	347.9	347.9	350.7	350.7	350.7	353.5	356.2	359.0	361.8
25°	314.5	314.5	311.7	311.7	314.5	314.5	314.5	314.5	317.3	317.3	317.3
27.5°	297.8	295.0	295.0	295.0	295.0	292.2	292.2	292.2	292.2	292.2	292.2
30°	289.4	286.7	283.9	281.1	281.1	278.3	275.5	275.5	275.5	275.5	275.5
32.5°	286.7	281.1	275.5	272.7	272.7	270.0	267.2	264.4	264.4	261.6	258.8
35°	256.0	253.3	253.3	250.5	247.7	244.9	242.1	242.1	242.1	239.3	239.3
37.5°	222.7	225.4	225.4	225.4	228.2	228.2	228.2	228.2	231.0	231.0	231.0
40°	208.7	208.7	208.7	211.5	214.3	214.3	217.1	217.1	219.9	219.9	219.9
42.5°	197.6	194.8	194.8	197.6	197.6	200.4	200.4	203.2	206.0	206.0	208.7
45°	192.0	189.3	189.3	189.3	189.3	186.5	186.5	189.3	192.0	194.8	197.6
47.5°	180.9	180.9	178.1	178.1	178.1	178.1	178.1	178.1	180.9	180.9	180.9
50°	175.3	175.3	172.6	172.6	172.6	172.6	172.6	172.6	172.6	172.6	172.6
52.5°	169.8	167.0	167.0	167.0	167.0	164.2	164.2	164.2	164.2	164.2	164.2
55°	161.4	158.6	158.6	158.6	158.6	158.6	158.6	158.6	161.4	161.4	161.4
57.5°	153.1	150.3	150.3	150.3	153.1	153.1	153.1	153.1	155.9	155.9	155.9
60°	144.7	144.7	144.7	144.7	144.7	144.7	144.7	147.5	147.5	150.3	150.3
62.5°	136.4	136.4	136.4	136.4	139.2	139.2	139.2	139.2	141.9	141.9	141.9
65°	128.0	128.0	128.0	128.0	130.8	130.8	130.8	130.8	130.8	130.8	130.8
67.5°	119.7	119.7	119.7	119.7	119.7	119.7	119.7	122.5	122.5	125.2	125.2
70°	108.5	105.8	105.8	108.5	108.5	111.3	111.3	114.1	114.1	116.9	116.9
72.5°	97.4	97.4	97.4	97.4	97.4	97.4	97.4	100.2	103.0	103.0	105.8
75°	86.3	86.3	86.3	86.3	89.1	89.1	89.1	91.8	91.8	94.6	94.6
77.5°	77.9	75.1	75.1	75.1	77.9	77.9	77.9	80.7	80.7	83.5	83.5
80°	64.0	64.0	64.0	64.0	66.8	66.8	66.8	66.8	69.6	69.6	69.6
82.5°	52.9	52.9	52.9	52.9	52.9	52.9	52.9	52.9	55.7	55.7	55.7
85°	39.0	39.0	39.0	39.0	41.7	41.7	41.7	41.7	41.7	41.7	41.7
87.5°	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	27.8	27.8	27.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	1770.1	1770.1	1770.1	1770.1	1775.6	1778.4	1784.0	1786.8	1784.0	1781.2	1775.6
5°	1489.0	1491.8	1491.8	1494.5	1494.5	1494.5	1494.5	1494.5	1500.1	1505.7	1511.2
7.5°	1177.3	1180.0	1182.8	1185.6	1185.6	1185.6	1182.8	1182.8	1185.6	1185.6	1188.4
10°	901.7	912.9	921.2	929.6	924.0	915.6	910.1	901.7	901.7	901.7	899.0
12.5°	681.9	684.6	690.2	693.0	690.2	690.2	687.4	684.6	687.4	693.0	695.8
15°	539.9	539.9	542.7	542.7	545.5	548.3	548.3	551.1	556.6	559.4	565.0
17.5°	448.1	450.9	450.9	453.6	453.6	456.4	456.4	456.4	462.0	467.6	475.9
20°	403.6	403.6	403.6	403.6	403.6	400.8	400.8	398.0	400.8	406.3	409.1
22.5°	361.8	364.6	364.6	364.6	361.8	359.0	353.5	350.7	350.7	353.5	353.5
25°	317.3	314.5	314.5	311.7	311.7	314.5	314.5	314.5	317.3	317.3	320.1
27.5°	292.2	289.4	289.4	286.7	286.7	289.4	289.4	289.4	289.4	289.4	289.4
30°	272.7	272.7	270.0	267.2	270.0	270.0	272.7	272.7	275.5	275.5	278.3
32.5°	258.8	256.0	256.0	253.3	256.0	256.0	258.8	258.8	261.6	264.4	264.4
35°	239.3	239.3	239.3	239.3	239.3	239.3	236.6	236.6	236.6	236.6	236.6
37.5°	228.2	228.2	225.4	222.7	222.7	222.7	222.7	222.7	219.9	217.1	214.3
40°	219.9	217.1	217.1	214.3	211.5	211.5	208.7	206.0	206.0	203.2	203.2
42.5°	208.7	206.0	206.0	203.2	200.4	200.4	197.6	194.8	194.8	194.8	192.0
45°	194.8	194.8	192.0	189.3	189.3	189.3	186.5	186.5	186.5	186.5	183.7
47.5°	180.9	180.9	178.1	178.1	178.1	178.1	175.3	175.3	175.3	175.3	175.3
50°	172.6	172.6	172.6	172.6	172.6	172.6	169.8	169.8	169.8	169.8	169.8
52.5°	164.2	164.2	164.2	164.2	164.2	164.2	164.2	164.2	164.2	164.2	164.2
55°	161.4	161.4	161.4	161.4	161.4	161.4	158.6	158.6	158.6	161.4	161.4
57.5°	155.9	155.9	153.1	153.1	153.1	153.1	153.1	153.1	153.1	153.1	153.1
60°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3
62.5°	141.9	141.9	141.9	141.9	141.9	144.7	144.7	144.7	144.7	144.7	141.9
65°	130.8	133.6	133.6	133.6	133.6	133.6	133.6	133.6	133.6	133.6	133.6
67.5°	125.2	125.2	125.2	125.2	125.2	125.2	125.2	125.2	125.2	125.2	125.2
70°	116.9	116.9	114.1	114.1	114.1	116.9	116.9	116.9	116.9	116.9	116.9
72.5°	105.8	105.8	105.8	105.8	105.8	105.8	105.8	105.8	105.8	108.5	108.5
75°	94.6	94.6	94.6	94.6	94.6	94.6	94.6	94.6	94.6	94.6	94.6
77.5°	83.5	83.5	80.7	80.7	80.7	83.5	83.5	83.5	83.5	86.3	86.3
80°	69.6	69.6	69.6	69.6	69.6	69.6	69.6	69.6	69.6	72.4	72.4
82.5°	55.7	55.7	55.7	55.7	55.7	55.7	55.7	55.7	55.7	58.4	58.4
85°	41.7	44.5	44.5	44.5	44.5	44.5	44.5	44.5	44.5	47.3	47.3
87.5°	27.8	27.8	27.8	27.8	27.8	27.8	25.0	25.0	25.0	25.0	22.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	1772.9	1775.6	1778.4	1778.4	1781.2	1784.0	1784.0	1795.1	1806.3	1811.8	1817.4
5°	1516.8	1514.0	1514.0	1511.2	1508.5	1516.8	1525.2	1541.9	1558.6	1561.3	1566.9
7.5°	1188.4	1191.2	1194.0	1194.0	1196.7	1188.4	1177.3	1180.0	1182.8	1196.7	1207.9
10°	899.0	901.7	904.5	904.5	907.3	904.5	899.0	907.3	915.6	926.8	940.7
12.5°	698.6	706.9	715.3	720.8	729.2	734.7	737.5	748.7	757.0	770.9	784.8
15°	570.5	576.1	581.7	587.2	592.8	598.4	603.9	615.1	626.2	642.9	659.6
17.5°	481.5	481.5	484.3	484.3	484.3	489.8	495.4	501.0	503.7	520.4	537.1
20°	411.9	409.1	406.3	403.6	400.8	406.3	409.1	411.9	414.7	425.8	434.2
22.5°	353.5	353.5	356.2	356.2	356.2	353.5	347.9	350.7	350.7	356.2	364.6
25°	320.1	320.1	320.1	317.3	317.3	320.1	322.8	322.8	320.1	322.8	325.6
27.5°	289.4	292.2	292.2	295.0	295.0	297.8	297.8	297.8	297.8	300.6	303.4
30°	278.3	278.3	281.1	281.1	281.1	283.9	286.7	286.7	286.7	289.4	295.0
32.5°	267.2	270.0	272.7	275.5	278.3	281.1	281.1	283.9	283.9	286.7	289.4
35°	236.6	233.8	233.8	231.0	228.2	228.2	228.2	228.2	225.4	228.2	228.2
37.5°	211.5	211.5	211.5	208.7	208.7	211.5	211.5	211.5	211.5	214.3	214.3
40°	200.4	200.4	200.4	200.4	200.4	200.4	200.4	203.2	203.2	206.0	208.7
42.5°	192.0	192.0	192.0	192.0	192.0	194.8	194.8	194.8	194.8	197.6	197.6
45°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	186.5	186.5	189.3	192.0
47.5°	175.3	175.3	175.3	175.3	175.3	178.1	180.9	180.9	180.9	183.7	183.7
50°	169.8	169.8	169.8	169.8	169.8	172.6	172.6	175.3	175.3	178.1	180.9
52.5°	164.2	164.2	164.2	164.2	164.2	167.0	167.0	169.8	169.8	172.6	175.3
55°	161.4	161.4	161.4	158.6	158.6	161.4	161.4	164.2	164.2	167.0	167.0
57.5°	153.1	153.1	153.1	153.1	153.1	153.1	153.1	155.9	155.9	158.6	161.4
60°	150.3	150.3	147.5	147.5	144.7	147.5	147.5	150.3	150.3	153.1	153.1
62.5°	141.9	141.9	141.9	139.2	139.2	141.9	141.9	141.9	141.9	144.7	147.5
65°	133.6	133.6	133.6	130.8	130.8	133.6	133.6	133.6	133.6	136.4	139.2
67.5°	125.2	125.2	125.2	122.5	122.5	122.5	122.5	125.2	125.2	128.0	130.8
70°	116.9	116.9	116.9	114.1	114.1	114.1	111.3	114.1	116.9	119.7	119.7
72.5°	108.5	108.5	108.5	105.8	105.8	105.8	103.0	105.8	105.8	108.5	108.5
75°	94.6	94.6	94.6	94.6	94.6	94.6	91.8	91.8	91.8	94.6	94.6
77.5°	86.3	86.3	86.3	83.5	83.5	83.5	80.7	80.7	80.7	83.5	83.5
80°	72.4	72.4	72.4	69.6	69.6	69.6	66.8	66.8	66.8	69.6	69.6
82.5°	58.4	58.4	58.4	55.7	55.7	55.7	52.9	52.9	52.9	55.7	55.7
85°	47.3	47.3	47.3	47.3	47.3	47.3	44.5	44.5	44.5	47.3	50.1
87.5°	22.3	22.3	25.0	25.0	25.0	25.0	22.3	22.3	19.5	19.5	22.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	1822.9	1828.5	1842.4	1853.6	1867.5	1878.6	1887.0	1898.1	1906.4	1914.8	1920.4
5°	1569.7	1572.5	1586.4	1600.3	1611.4	1625.3	1644.8	1664.3	1683.8	1703.3	1717.2
7.5°	1221.8	1232.9	1249.6	1269.1	1285.8	1302.5	1322.0	1344.3	1363.7	1383.2	1402.7
10°	951.8	963.0	979.7	996.4	1010.3	1027.0	1049.2	1071.5	1093.8	1116.0	1138.3
12.5°	798.8	812.7	832.2	851.6	868.3	887.8	915.6	940.7	968.5	993.6	1021.4
15°	673.5	690.2	715.3	743.1	768.1	793.2	821.0	848.9	873.9	901.7	929.6
17.5°	553.8	570.5	592.8	617.9	640.1	662.4	695.8	726.4	759.8	790.4	821.0
20°	445.3	453.6	475.9	498.2	520.4	542.7	567.8	592.8	617.9	642.9	681.9
22.5°	370.2	375.7	386.9	395.2	406.3	414.7	439.7	464.8	487.0	512.1	548.3
25°	325.6	328.4	336.8	342.3	350.7	356.2	372.9	386.9	403.6	417.5	450.9
27.5°	303.4	306.1	308.9	311.7	314.5	317.3	328.4	339.5	347.9	359.0	389.6
30°	297.8	300.6	308.9	314.5	322.8	328.4	334.0	339.5	345.1	350.7	370.2
32.5°	292.2	295.0	295.0	292.2	292.2	289.4	295.0	297.8	303.4	306.1	322.8
35°	231.0	231.0	233.8	236.6	239.3	242.1	250.5	256.0	264.4	270.0	283.9
37.5°	217.1	217.1	219.9	225.4	228.2	231.0	236.6	242.1	247.7	253.3	267.2
40°	208.7	211.5	214.3	217.1	219.9	222.7	228.2	231.0	236.6	239.3	250.5
42.5°	200.4	200.4	203.2	208.7	211.5	214.3	219.9	222.7	228.2	231.0	242.1
45°	194.8	197.6	200.4	203.2	203.2	206.0	211.5	217.1	219.9	225.4	236.6
47.5°	186.5	186.5	192.0	194.8	200.4	203.2	208.7	211.5	217.1	219.9	231.0
50°	180.9	183.7	189.3	192.0	197.6	200.4	208.7	214.3	222.7	228.2	233.8
52.5°	175.3	178.1	183.7	186.5	192.0	194.8	206.0	217.1	225.4	236.6	236.6
55°	169.8	169.8	175.3	183.7	189.3	194.8	200.4	208.7	214.3	219.9	219.9
57.5°	161.4	164.2	169.8	178.1	183.7	189.3	194.8	200.4	203.2	208.7	206.0
60°	155.9	155.9	164.2	172.6	180.9	189.3	189.3	189.3	186.5	186.5	186.5
62.5°	147.5	150.3	161.4	175.3	186.5	197.6	189.3	180.9	172.6	164.2	167.0
65°	141.9	144.7	150.3	158.6	164.2	169.8	164.2	161.4	155.9	150.3	153.1
67.5°	130.8	133.6	136.4	136.4	139.2	139.2	139.2	139.2	139.2	139.2	141.9
70°	122.5	122.5	122.5	125.2	125.2	125.2	125.2	125.2	125.2	125.2	128.0
72.5°	111.3	111.3	111.3	111.3	111.3	111.3	111.3	111.3	111.3	111.3	114.1
75°	97.4	97.4	97.4	97.4	97.4	97.4	97.4	97.4	97.4	97.4	100.2
77.5°	86.3	86.3	86.3	86.3	86.3	86.3	86.3	86.3	83.5	83.5	86.3
80°	72.4	72.4	72.4	72.4	69.6	69.6	69.6	69.6	69.6	69.6	72.4
82.5°	58.4	58.4	58.4	58.4	55.7	55.7	55.7	55.7	52.9	52.9	55.7
85°	52.9	55.7	55.7	58.4	58.4	58.4	55.7	52.9	50.1	47.3	47.3
87.5°	22.3	22.3	22.3	22.3	19.5	19.5	19.5	19.5	19.5	19.5	19.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	1928.7	1934.3	1939.8	1948.2	1959.3	1967.7	1976.0	1992.7	2012.2	2028.9	2045.6
5°	1731.1	1745.0	1758.9	1775.6	1792.3	1806.3	1822.9	1856.3	1889.7	1920.4	1953.8
7.5°	1419.4	1438.9	1455.6	1483.4	1508.5	1536.3	1561.3	1603.1	1642.0	1683.8	1722.8
10°	1160.6	1182.8	1205.1	1241.3	1280.2	1316.4	1352.6	1386.0	1422.2	1455.6	1489.0
12.5°	1049.2	1074.3	1102.1	1124.4	1149.4	1171.7	1194.0	1232.9	1271.9	1310.9	1349.8
15°	957.4	985.2	1013.1	1040.9	1065.9	1093.8	1118.8	1152.2	1188.4	1221.8	1255.2
17.5°	851.6	879.5	910.1	940.7	971.3	1001.9	1032.5	1079.9	1127.2	1171.7	1219.0
20°	718.0	757.0	793.2	834.9	876.7	918.4	960.2	1010.3	1060.4	1107.7	1157.8
22.5°	584.5	620.6	656.8	706.9	757.0	804.3	854.4	921.2	985.2	1052.0	1116.0
25°	487.0	520.4	553.8	609.5	662.4	718.0	770.9	851.6	929.6	1010.3	1088.2
27.5°	420.3	450.9	481.5	539.9	598.4	654.0	712.5	801.5	887.8	976.9	1063.2
30°	389.6	409.1	428.6	484.3	539.9	592.8	648.5	734.7	821.0	907.3	993.6
32.5°	339.5	356.2	372.9	423.0	473.1	520.4	570.5	659.6	745.9	834.9	921.2
35°	300.6	314.5	328.4	375.7	420.3	467.6	512.1	601.2	690.2	779.3	868.3
37.5°	278.3	292.2	303.4	345.1	389.6	431.4	473.1	562.2	648.5	737.5	823.8
40°	261.6	270.0	281.1	322.8	361.8	403.6	442.5	523.2	606.7	687.4	768.1
42.5°	250.5	261.6	270.0	306.1	345.1	381.3	417.5	495.4	573.3	648.5	726.4
45°	247.7	258.8	270.0	300.6	331.2	359.0	389.6	464.8	539.9	615.1	690.2
47.5°	242.1	250.5	261.6	286.7	308.9	334.0	356.2	431.4	506.5	578.9	654.0
50°	239.3	242.1	247.7	270.0	292.2	314.5	336.8	411.9	487.0	562.2	637.3
52.5°	236.6	236.6	236.6	256.0	275.5	292.2	311.7	386.9	464.8	539.9	615.1
55°	219.9	217.1	217.1	236.6	253.3	272.7	289.4	364.6	439.7	512.1	587.2
57.5°	203.2	200.4	197.6	214.3	231.0	247.7	264.4	339.5	417.5	492.6	567.8
60°	186.5	183.7	183.7	200.4	214.3	231.0	244.9	322.8	398.0	475.9	551.1
62.5°	167.0	169.8	169.8	183.7	200.4	214.3	228.2	306.1	386.9	464.8	542.7
65°	153.1	155.9	155.9	172.6	189.3	206.0	222.7	297.8	375.7	450.9	526.0
67.5°	141.9	144.7	144.7	164.2	180.9	200.4	217.1	283.9	353.5	420.3	487.0
70°	130.8	130.8	133.6	153.1	172.6	192.0	211.5	270.0	328.4	384.1	442.5
72.5°	116.9	119.7	122.5	141.9	158.6	178.1	194.8	247.7	300.6	353.5	406.3
75°	103.0	105.8	108.5	125.2	141.9	158.6	175.3	225.4	272.7	322.8	370.2
77.5°	91.8	94.6	97.4	111.3	125.2	139.2	153.1	189.3	228.2	264.4	300.6
80°	75.1	75.1	77.9	89.1	100.2	108.5	119.7	144.7	169.8	192.0	217.1
82.5°	55.7	58.4	58.4	66.8	72.4	80.7	86.3	100.2	111.3	125.2	136.4
85°	47.3	44.5	44.5	50.1	52.9	58.4	61.2	69.6	75.1	83.5	89.1
87.5°	19.5	16.7	16.7	19.5	25.0	27.8	30.6	30.6	33.4	33.4	33.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	2053.9	2059.5	2067.9	2073.4	2087.3	2098.5	2112.4	2123.5	2131.9	2145.8	2140.2
5°	1978.8	2003.9	2028.9	2053.9	2073.4	2092.9	2109.6	2129.1	2151.4	2193.1	2204.2
7.5°	1756.2	1789.6	1820.2	1853.6	1892.5	1931.5	1970.5	2009.4	2045.6	2098.5	2131.9
10°	1536.3	1583.6	1628.1	1675.4	1711.6	1747.8	1781.2	1817.4	1867.5	1920.4	1981.6
12.5°	1397.1	1444.4	1491.8	1539.1	1591.9	1642.0	1694.9	1745.0	1792.3	1834.1	1903.7
15°	1305.3	1358.2	1408.3	1458.4	1522.4	1583.6	1647.6	1708.8	1778.4	1834.1	1881.4
17.5°	1283.0	1347.0	1408.3	1472.3	1539.1	1605.9	1672.7	1739.5	1809.0	1892.5	1953.8
20°	1244.1	1330.3	1416.6	1502.9	1589.2	1672.7	1758.9	1842.4	1934.3	2034.5	2062.3
22.5°	1221.8	1324.8	1430.5	1533.5	1650.4	1770.1	1887.0	2003.9	2101.3	2176.4	2259.9
25°	1219.0	1347.0	1477.8	1605.9	1753.4	1898.1	2045.6	2190.3	2315.6	2390.7	2457.5
27.5°	1216.2	1372.1	1525.2	1678.2	1859.1	2037.3	2218.2	2396.3	2513.2	2621.7	2677.4
30°	1182.8	1369.3	1558.6	1745.0	1948.2	2151.4	2354.5	2557.7	2677.4	2752.5	2780.3
32.5°	1141.1	1360.9	1580.8	1800.7	2031.7	2262.7	2490.9	2721.9	2816.5	2880.5	2858.3
35°	1107.7	1349.8	1589.2	1828.5	2073.4	2321.1	2566.0	2811.0	2947.3	3036.4	3000.2
37.5°	1077.1	1330.3	1583.6	1836.9	2123.5	2410.2	2696.9	2983.5	3114.3	3208.9	3167.2
40°	1040.9	1310.9	1583.6	1853.6	2182.0	2507.6	2836.0	3161.6	3331.4	3412.1	3348.1
42.5°	1010.3	1291.4	1575.3	1856.3	2207.0	2557.7	2908.4	3259.0	3448.3	3562.4	3481.7
45°	971.3	1252.4	1530.7	1811.8	2198.7	2585.5	2969.6	3356.5	3576.3	3665.4	3554.1
47.5°	929.6	1207.9	1483.4	1758.9	2170.8	2582.7	2994.6	3406.5	3609.7	3715.5	3612.5
50°	915.6	1194.0	1469.5	1747.8	2193.1	2641.2	3086.5	3531.8	3679.3	3765.6	3629.2
52.5°	912.9	1207.9	1505.7	1800.7	2248.8	2694.1	3142.2	3587.5	3707.1	3799.0	3676.5
55°	904.5	1224.6	1541.9	1859.1	2326.7	2797.0	3264.6	3732.2	3851.8	3918.6	3826.8
57.5°	912.9	1258.0	1600.3	1945.4	2426.9	2908.4	3389.9	3871.3	4016.1	4063.4	4043.9
60°	918.4	1285.8	1650.4	2017.8	2488.1	2958.5	3428.8	3899.2	4049.5	4166.3	4188.6
62.5°	904.5	1266.3	1625.3	1987.2	2413.0	2838.8	3264.6	3690.4	3938.1	4110.7	4210.9
65°	862.8	1196.7	1533.5	1867.5	2259.9	2655.1	3047.5	3439.9	3701.6	3957.6	4038.3
67.5°	770.9	1054.8	1338.7	1622.6	1964.9	2307.2	2646.8	2989.1	3317.5	3565.2	3676.5
70°	668.0	890.6	1116.0	1338.7	1650.4	1962.1	2273.8	2585.5	2875.0	3147.7	3253.5
72.5°	581.7	754.2	929.6	1102.1	1324.8	1544.6	1767.3	1987.2	2329.5	2602.2	2705.2
75°	495.4	620.6	743.1	868.3	1021.4	1174.5	1324.8	1477.8	1720.0	1964.9	2067.9
77.5°	381.3	464.8	545.5	626.2	732.0	834.9	940.7	1043.7	1213.4	1397.1	1450.0
80°	264.4	311.7	356.2	403.6	487.0	570.5	654.0	737.5	848.9	951.8	1032.5
82.5°	164.2	194.8	222.7	250.5	317.3	384.1	448.1	514.9	559.4	565.0	645.7
85°	105.8	125.2	141.9	158.6	197.6	239.3	278.3	317.3	283.9	264.4	314.5
87.5°	41.7	52.9	61.2	69.6	66.8	64.0	61.2	58.4	50.1	44.5	55.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	2145.8	2154.1	2162.5	2168.1	2176.4	2179.2	2182.0	2182.0	2184.8	2187.5	2193.1
5°	2248.8	2265.5	2282.2	2296.1	2312.8	2326.7	2337.8	2351.7	2362.9	2362.9	2360.1
7.5°	2162.5	2204.2	2246.0	2287.7	2329.5	2360.1	2387.9	2418.5	2446.4	2451.9	2457.5
10°	2048.4	2092.9	2134.7	2179.2	2220.9	2268.2	2312.8	2357.3	2404.6	2413.0	2424.1
12.5°	1942.6	1995.5	2048.4	2098.5	2151.4	2184.8	2218.2	2248.8	2282.2	2304.4	2326.7
15°	1939.8	1984.4	2028.9	2070.6	2115.2	2134.7	2154.1	2170.8	2190.3	2190.3	2193.1
17.5°	2003.9	2031.7	2059.5	2084.6	2112.4	2115.2	2120.7	2123.5	2126.3	2118.0	2109.6
20°	2129.1	2140.2	2151.4	2162.5	2173.6	2154.1	2137.4	2118.0	2098.5	2076.2	2056.7
22.5°	2312.8	2287.7	2262.7	2237.6	2212.6	2179.2	2143.0	2109.6	2073.4	2045.6	2017.8
25°	2485.3	2454.7	2424.1	2393.5	2362.9	2290.5	2218.2	2143.0	2070.6	2040.0	2009.4
27.5°	2716.3	2669.0	2621.7	2574.4	2527.1	2429.7	2332.3	2234.9	2137.4	2084.6	2034.5
30°	2772.0	2719.1	2666.2	2610.6	2557.7	2463.1	2371.2	2276.6	2182.0	2120.7	2062.3
32.5°	2852.7	2791.5	2730.2	2669.0	2607.8	2515.9	2424.1	2329.5	2237.6	2182.0	2123.5
35°	2986.3	2916.7	2847.1	2774.8	2705.2	2610.6	2518.7	2424.1	2329.5	2265.5	2204.2
37.5°	3100.4	3019.7	2939.0	2858.3	2777.6	2694.1	2607.8	2524.3	2438.0	2374.0	2312.8
40°	3228.4	3139.4	3050.3	2964.0	2875.0	2797.0	2719.1	2638.4	2560.5	2510.4	2460.3
42.5°	3339.8	3231.2	3125.5	3019.7	2911.2	2858.3	2808.2	2755.3	2702.4	2677.4	2649.5
45°	3417.7	3317.5	3214.5	3114.3	3014.1	2975.2	2936.2	2897.2	2858.3	2883.3	2908.4
47.5°	3451.1	3370.4	3292.4	3214.5	3133.8	3147.7	3161.6	3172.8	3186.7	3220.1	3256.3
50°	3481.7	3437.2	3389.9	3345.3	3298.0	3350.9	3401.0	3453.9	3506.7	3576.3	3645.9
52.5°	3542.9	3517.9	3495.6	3470.6	3445.5	3537.4	3629.2	3721.0	3812.9	3890.8	3968.7
55°	3726.6	3707.1	3687.6	3665.4	3645.9	3776.7	3904.7	4035.5	4166.3	4247.1	4327.8
57.5°	3979.9	3968.7	3954.8	3943.7	3929.8	4057.8	4183.0	4308.3	4436.3	4514.2	4594.9
60°	4171.9	4174.7	4174.7	4177.5	4177.5	4274.9	4372.3	4472.5	4569.9	4636.7	4706.3
62.5°	4274.9	4269.3	4263.8	4258.2	4252.6	4333.3	4414.0	4494.8	4575.5	4625.6	4675.7
65°	4163.6	4194.2	4224.8	4255.4	4286.0	4297.2	4305.5	4316.6	4325.0	4355.6	4386.2
67.5°	3790.6	3851.8	3910.3	3971.5	4030.0	3988.2	3949.3	3907.5	3865.8	3874.1	3879.7
70°	3375.9	3445.5	3517.9	3587.5	3657.0	3559.6	3462.2	3362.0	3264.6	3231.2	3197.8
72.5°	2847.1	2908.4	2972.4	3033.6	3094.8	2975.2	2858.3	2738.6	2618.9	2560.5	2502.0
75°	2176.4	2248.8	2323.9	2396.3	2468.6	2335.0	2198.7	2065.1	1928.7	1889.7	1853.6
77.5°	1586.4	1672.7	1758.9	1845.2	1931.5	1811.8	1692.1	1569.7	1450.0	1427.7	1405.5
80°	1155.0	1221.8	1285.8	1352.6	1416.6	1347.0	1277.5	1207.9	1138.3	1135.5	1132.7
82.5°	779.3	837.7	893.4	951.8	1007.5	979.7	954.6	926.8	899.0	926.8	957.4
85°	400.8	481.5	565.0	645.7	726.4	718.0	712.5	704.1	695.8	732.0	765.4
87.5°	80.7	150.3	219.9	286.7	356.2	339.5	322.8	303.4	286.7	297.8	306.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	2195.9	2198.7	2198.7	2198.7	2198.7	2198.7	2193.1	2190.3	2184.8	2179.2	2170.8
5°	2360.1	2357.3	2346.2	2335.0	2321.1	2310.0	2301.6	2290.5	2282.2	2271.0	2254.3
7.5°	2463.1	2468.6	2449.2	2432.5	2413.0	2393.5	2374.0	2354.5	2335.0	2315.6	2276.6
10°	2432.5	2440.8	2429.7	2418.5	2404.6	2393.5	2371.2	2346.2	2323.9	2298.9	2251.6
12.5°	2346.2	2368.4	2362.9	2357.3	2351.7	2346.2	2332.3	2315.6	2301.6	2284.9	2232.1
15°	2193.1	2193.1	2195.9	2198.7	2198.7	2201.5	2204.2	2207.0	2209.8	2212.6	2182.0
17.5°	2101.3	2092.9	2092.9	2092.9	2092.9	2092.9	2104.0	2118.0	2129.1	2140.2	2131.9
20°	2034.5	2015.0	2012.2	2012.2	2009.4	2006.6	2026.1	2048.4	2067.9	2087.3	2098.5
22.5°	1989.9	1962.1	1959.3	1956.5	1953.8	1951.0	1976.0	2001.1	2026.1	2051.2	2090.1
25°	1978.8	1948.2	1951.0	1953.8	1953.8	1956.5	1976.0	1995.5	2015.0	2034.5	2101.3
27.5°	1981.6	1931.5	1934.3	1937.1	1937.1	1939.8	1970.5	1998.3	2028.9	2056.7	2140.2
30°	2001.1	1942.6	1937.1	1931.5	1925.9	1920.4	1962.1	2003.9	2045.6	2087.3	2151.4
32.5°	2067.9	2012.2	1998.3	1984.4	1970.5	1956.5	2006.6	2053.9	2104.0	2151.4	2204.2
35°	2140.2	2079.0	2073.4	2067.9	2059.5	2053.9	2098.5	2145.8	2190.3	2234.9	2282.2
37.5°	2248.8	2187.5	2182.0	2173.6	2168.1	2159.7	2209.8	2257.1	2307.2	2354.5	2396.3
40°	2410.2	2360.1	2357.3	2357.3	2354.5	2351.7	2390.7	2432.5	2471.4	2510.4	2538.2
42.5°	2624.5	2599.4	2607.8	2618.9	2627.3	2635.6	2666.2	2699.6	2730.2	2760.9	2752.5
45°	2933.4	2958.5	2961.2	2964.0	2966.8	2969.6	2977.9	2989.1	2997.4	3005.8	2972.4
47.5°	3289.7	3323.1	3339.8	3356.5	3370.4	3387.1	3375.9	3362.0	3350.9	3337.0	3253.5
50°	3712.7	3782.3	3779.5	3776.7	3771.1	3768.4	3746.1	3723.8	3698.8	3676.5	3554.1
52.5°	4046.7	4124.6	4138.5	4152.4	4166.3	4180.3	4138.5	4096.8	4052.2	4010.5	3857.4
55°	4405.7	4486.4	4489.2	4492.0	4492.0	4494.8	4436.3	4377.9	4316.6	4258.2	4099.5
57.5°	4672.9	4750.8	4742.5	4736.9	4728.5	4720.2	4650.6	4581.0	4511.5	4441.9	4283.2
60°	4773.1	4839.9	4823.2	4806.5	4787.0	4770.3	4717.4	4664.5	4608.9	4556.0	4402.9
62.5°	4725.8	4775.8	4750.8	4728.5	4703.5	4678.4	4611.6	4542.1	4475.3	4405.7	4294.4
65°	4414.0	4444.7	4411.3	4380.6	4350.0	4316.6	4261.0	4205.3	4146.9	4091.2	4016.1
67.5°	3888.0	3893.6	3890.8	3888.0	3885.2	3882.5	3801.8	3721.0	3637.5	3556.8	3551.3
70°	3167.2	3133.8	3139.4	3147.7	3153.3	3158.9	3097.6	3039.2	2977.9	2916.7	2944.6
72.5°	2443.6	2385.1	2399.1	2415.8	2429.7	2443.6	2393.5	2346.2	2296.1	2246.0	2284.9
75°	1814.6	1778.4	1792.3	1809.0	1822.9	1836.9	1817.4	1797.9	1775.6	1756.2	1792.3
77.5°	1383.2	1360.9	1363.7	1363.7	1366.5	1366.5	1369.3	1374.9	1377.6	1380.4	1419.4
80°	1127.2	1124.4	1121.6	1118.8	1113.3	1110.5	1138.3	1166.1	1194.0	1221.8	1241.3
82.5°	985.2	1013.1	996.4	982.4	965.7	949.0	974.1	999.1	1024.2	1049.2	1040.9
85°	801.5	834.9	804.3	773.7	740.3	709.7	732.0	751.4	773.7	793.2	782.1
87.5°	317.3	325.6	275.5	228.2	178.1	128.0	203.2	275.5	350.7	423.0	434.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961

CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9	2003.9
2.5°	2162.5	2151.4	2143.0	2140.2	2134.7	2131.9	2126.3	2120.7	2112.4	2106.8	2098.5
5°	2234.9	2218.2	2198.7	2170.8	2145.8	2118.0	2090.1	2065.1	2040.0	2012.2	1987.2
7.5°	2237.6	2198.7	2159.7	2123.5	2084.6	2048.4	2009.4	1976.0	1939.8	1903.7	1870.3
10°	2207.0	2159.7	2112.4	2065.1	2020.6	1973.2	1925.9	1887.0	1845.2	1803.5	1764.5
12.5°	2182.0	2129.1	2076.2	2020.6	1967.7	1912.0	1856.3	1817.4	1778.4	1739.5	1700.5
15°	2151.4	2118.0	2087.3	2037.3	1987.2	1937.1	1887.0	1834.1	1784.0	1731.1	1678.2
17.5°	2126.3	2118.0	2109.6	2076.2	2042.8	2006.6	1973.2	1920.4	1867.5	1811.8	1758.9
20°	2112.4	2123.5	2134.7	2118.0	2101.3	2081.8	2065.1	2026.1	1987.2	1945.4	1906.4
22.5°	2129.1	2170.8	2209.8	2212.6	2218.2	2220.9	2223.7	2187.5	2151.4	2112.4	2076.2
25°	2168.1	2234.9	2301.6	2337.8	2374.0	2413.0	2449.2	2426.9	2404.6	2382.4	2360.1
27.5°	2220.9	2304.4	2387.9	2440.8	2490.9	2543.8	2596.7	2593.9	2591.1	2585.5	2582.7
30°	2212.6	2276.6	2340.6	2404.6	2468.6	2532.6	2596.7	2630.1	2660.7	2694.1	2727.5
32.5°	2259.9	2312.8	2368.4	2435.2	2502.0	2571.6	2638.4	2708.0	2774.8	2844.4	2913.9
35°	2332.3	2379.6	2429.7	2502.0	2577.2	2649.5	2724.7	2808.2	2894.5	2980.7	3064.2
37.5°	2440.8	2482.6	2527.1	2588.3	2652.3	2713.6	2777.6	2900.0	3022.5	3147.7	3270.2
40°	2566.0	2593.9	2621.7	2680.2	2738.6	2797.0	2855.5	3008.6	3161.6	3314.7	3467.8
42.5°	2746.9	2738.6	2730.2	2777.6	2827.7	2875.0	2925.1	3064.2	3203.4	3342.5	3481.7
45°	2939.0	2905.6	2872.2	2894.5	2919.5	2941.8	2966.8	3108.8	3250.7	3395.4	3537.4
47.5°	3170.0	3086.5	3003.0	2983.5	2964.0	2941.8	2922.3	3075.4	3228.4	3384.3	3537.4
50°	3431.6	3306.4	3183.9	3133.8	3080.9	3030.8	2977.9	3103.2	3231.2	3359.2	3484.5
52.5°	3704.3	3548.5	3395.4	3317.5	3239.6	3158.9	3080.9	3186.7	3295.2	3403.8	3509.5
55°	3938.1	3779.5	3618.1	3526.2	3434.4	3342.5	3250.7	3356.5	3462.2	3568.0	3673.7
57.5°	4124.6	3966.0	3807.3	3721.0	3632.0	3545.7	3456.6	3556.8	3659.8	3762.8	3863.0
60°	4252.6	4099.5	3946.5	3863.0	3779.5	3696.0	3612.5	3732.2	3851.8	3974.3	4094.0
62.5°	4185.8	4074.5	3963.2	3927.0	3890.8	3851.8	3815.7	3929.8	4041.1	4155.2	4269.3
65°	3940.9	3865.8	3790.6	3826.8	3865.8	3901.9	3940.9	4016.1	4091.2	4169.1	4244.3
67.5°	3542.9	3537.4	3529.0	3609.7	3690.4	3773.9	3854.6	3904.7	3952.0	4002.1	4052.2
70°	2972.4	3003.0	3030.8	3170.0	3309.1	3448.3	3587.5	3606.9	3626.4	3645.9	3665.4
72.5°	2326.7	2365.7	2407.4	2591.1	2772.0	2955.7	3139.4	3128.2	3117.1	3103.2	3092.1
75°	1831.3	1867.5	1906.4	2076.2	2246.0	2415.8	2585.5	2538.2	2493.7	2446.4	2399.1
77.5°	1461.1	1500.1	1541.9	1700.5	1859.1	2020.6	2179.2	2065.1	1951.0	1836.9	1722.8
80°	1258.0	1277.5	1294.2	1402.7	1508.5	1617.0	1725.5	1608.6	1489.0	1369.3	1252.4
82.5°	1032.5	1021.4	1013.1	1077.1	1141.1	1205.1	1269.1	1157.8	1046.5	932.3	821.0
85°	770.9	759.8	748.7	782.1	815.5	851.6	885.0	757.0	629.0	498.2	370.2
87.5°	448.1	459.2	470.3	506.5	542.7	581.7	617.9	487.0	356.2	222.7	91.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675961  
 CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P675961  
CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	2003.9	2003.9
2.5°	2081.8	2067.9
5°	1967.7	1948.2
7.5°	1842.4	1817.4
10°	1728.3	1694.9
12.5°	1656.0	1614.2
15°	1628.1	1578.0
17.5°	1711.6	1664.3
20°	1839.6	1775.6
22.5°	1995.5	1917.6
25°	2265.5	2170.8
27.5°	2485.3	2387.9
30°	2621.7	2515.9
32.5°	2772.0	2632.8
35°	2927.9	2794.3
37.5°	3117.1	2966.8
40°	3311.9	3156.1
42.5°	3378.7	3278.5
45°	3442.7	3348.1
47.5°	3456.6	3378.7
50°	3470.6	3459.4
52.5°	3509.5	3506.7
55°	3676.5	3679.3
57.5°	3882.5	3899.2
60°	4071.7	4052.2
62.5°	4169.1	4068.9
65°	4102.3	3963.2
67.5°	3901.9	3751.7
70°	3462.2	3259.0
72.5°	2913.9	2735.8
75°	2246.0	2095.7
77.5°	1597.5	1472.3
80°	1124.4	999.1
82.5°	720.8	620.6
85°	325.6	283.9
87.5°	91.8	89.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675961  
CATALOG NUMBER: CCW-SA-2C-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)