

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675963

Luminaire Tested: **CCW-SA-2E-727-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P675963
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2E-727-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/
SLR distribution lens
Light Source: (32) 2700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9489.4 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G3


Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 13.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P675963
CATALOG NUMBER: CCW-SA-2E-727-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1952.5	0.0	1952.5
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	7536.9	0.0	7536.9
	% Fixture	79.4	0.0	79.4
Total	Lumens	9489.4	0.0	9489.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.5	2.5
10°-20°	497.2	5.2
20°-30°	727.4	7.7
30°-40°	1024.7	10.8
40°-50°	1408.1	14.8
50°-60°	1919.3	20.2
60°-70°	2100.6	22.1
70°-80°	1213.1	12.8
80°-90°	363.6	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9489.4	100.0
0°-180°	9489.4	100.0




REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	974.6	10.3			
FM (30°-60°)	3463.0	36.5			
FH (60°-80°)	2790.5	29.4			G2/5000
FVH (80°-90°)	308.9	3.3			G3/500
BL (0°-30°)	485.4	5.1	B1/500		
BM (30°-60°)	889.1	9.4	B1/1000		
BH (60°-80°)	523.3	5.5	B2/1000		G2/1000
BVH (80°-90°)	54.8	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short





REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	3127.1	3110.3	3097.7	3085.0	3068.2	3055.6	3038.7	3021.9	3000.9	2984.0	2963.0
5°	2946.2	2895.6	2845.1	2815.7	2782.0	2752.5	2718.9	2681.0	2643.1	2601.0	2563.2
7.5°	2748.3	2685.2	2622.1	2571.6	2516.9	2466.4	2411.6	2365.3	2319.0	2272.7	2226.5
10°	2563.2	2504.2	2445.3	2382.2	2314.8	2251.7	2184.4	2121.2	2058.1	1995.0	1931.8
12.5°	2441.1	2369.5	2302.2	2230.7	2163.3	2091.8	2020.2	1961.3	1902.4	1839.2	1780.3
15°	2386.4	2319.0	2255.9	2184.4	2112.8	2041.3	1969.7	1902.4	1839.2	1771.9	1704.6
17.5°	2516.9	2420.1	2323.3	2230.7	2138.1	2045.5	1952.9	1868.7	1784.5	1700.4	1616.2
20°	2685.2	2563.2	2445.3	2331.7	2213.8	2100.2	1982.3	1864.5	1746.6	1628.8	1511.0
22.5°	2899.9	2761.0	2626.3	2479.0	2327.5	2180.2	2028.6	1881.3	1734.0	1582.5	1435.2
25°	3282.9	3118.7	2954.6	2744.1	2529.5	2319.0	2104.4	1910.8	1721.4	1527.8	1334.2
27.5°	3611.1	3388.1	3169.2	2916.7	2664.2	2411.6	2159.1	1936.0	1717.2	1494.1	1271.1
30°	3804.7	3585.9	3367.0	3059.8	2756.8	2449.5	2142.3	1894.0	1649.8	1401.5	1153.2
32.5°	3981.5	3737.4	3493.3	3156.6	2815.7	2479.0	2138.1	1864.5	1595.1	1321.6	1048.0
35°	4225.6	3956.3	3691.1	3299.7	2908.3	2516.9	2125.4	1843.5	1557.3	1275.3	989.1
37.5°	4486.6	4154.1	3825.8	3392.3	2958.8	2525.3	2091.8	1814.0	1536.2	1258.4	980.6
40°	4772.8	4368.7	3968.9	3489.1	3013.5	2533.7	2053.9	1776.1	1498.3	1216.3	938.6
42.5°	4958.0	4520.2	4082.5	3564.8	3051.4	2533.7	2016.0	1742.4	1468.9	1191.1	917.5
45°	5063.2	4638.1	4217.2	3657.4	3097.7	2537.9	1978.1	1708.8	1439.4	1165.8	896.5
47.5°	5109.5	4713.8	4318.2	3729.0	3144.0	2554.7	1965.5	1691.9	1414.2	1140.6	862.8
50°	5231.5	4882.2	4532.9	3901.5	3274.4	2643.1	2011.8	1717.2	1426.8	1132.2	837.5
52.5°	5303.1	5004.3	4705.4	4057.3	3409.1	2761.0	2112.8	1784.5	1456.2	1128.0	799.7
55°	5564.0	5277.8	4991.6	4301.4	3606.9	2916.7	2222.2	1860.3	1498.3	1132.2	770.2
57.5°	5896.5	5593.5	5294.7	4549.7	3804.7	3059.8	2314.8	1927.6	1536.2	1149.0	757.6
60°	6128.0	5833.4	5543.0	4751.7	3956.3	3165.0	2369.5	1965.5	1561.5	1153.2	749.2
62.5°	6153.3	5774.5	5399.9	4629.7	3859.5	3085.0	2314.8	1923.4	1532.0	1136.4	745.0
65°	5993.3	5551.4	5109.5	4372.9	3636.4	2899.9	2163.3	1805.6	1447.8	1085.9	728.1
67.5°	5673.5	5155.8	4638.1	3964.7	3291.3	2617.9	1944.5	1637.2	1334.2	1026.9	719.7
70°	4928.5	4473.9	4023.6	3438.6	2857.8	2272.7	1687.7	1435.2	1186.9	934.4	681.8
72.5°	4137.2	3712.2	3291.3	2815.7	2344.3	1868.7	1393.1	1203.7	1014.3	820.7	631.3
75°	3169.2	2849.4	2533.7	2180.2	1826.6	1468.9	1115.3	976.4	837.5	698.7	559.8
77.5°	2226.5	2053.9	1885.5	1620.4	1355.2	1090.1	824.9	732.3	639.7	547.1	454.5
80°	1511.0	1414.2	1321.6	1132.2	942.8	749.2	559.8	500.8	437.7	378.8	315.7
82.5°	938.6	934.4	925.9	795.5	665.0	534.5	404.0	353.5	307.2	256.7	206.2
85°	429.3	500.8	568.2	496.6	425.1	353.5	282.0	248.3	214.6	176.8	143.1
87.5°	134.7	164.1	189.4	181.0	168.4	159.9	147.3	126.3	105.2	84.2	63.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	2946.2	2933.5	2916.7	2899.9	2878.8	2862.0	2840.9	2819.9	2815.7	2807.3	2803.1
5°	2537.9	2512.6	2483.2	2457.9	2432.7	2403.2	2378.0	2348.5	2327.5	2302.2	2281.2
7.5°	2180.2	2138.1	2091.8	2045.5	2003.4	1961.3	1915.0	1872.9	1851.9	1830.8	1809.8
10°	1894.0	1851.9	1814.0	1771.9	1742.4	1717.2	1687.7	1658.3	1633.0	1607.8	1582.5
12.5°	1750.9	1721.4	1691.9	1662.5	1628.8	1599.3	1565.7	1532.0	1502.5	1477.3	1447.8
15°	1662.5	1620.4	1574.1	1532.0	1485.7	1443.6	1397.3	1351.0	1317.4	1287.9	1254.2
17.5°	1557.3	1494.1	1435.2	1372.1	1321.6	1271.1	1216.3	1165.8	1128.0	1085.9	1048.0
20°	1439.4	1367.9	1292.1	1220.5	1161.6	1106.9	1048.0	989.1	947.0	900.7	858.6
22.5°	1338.4	1245.8	1149.0	1052.2	989.1	925.9	858.6	795.5	757.6	715.5	677.6
25°	1229.0	1128.0	1022.7	917.5	854.4	787.0	723.9	656.6	627.1	601.9	572.4
27.5°	1170.0	1069.0	963.8	862.8	803.9	740.7	681.8	618.7	597.6	572.4	551.4
30°	1052.2	955.4	854.4	753.4	711.3	673.4	631.3	589.2	580.8	576.6	568.2
32.5°	947.0	846.0	745.0	643.9	606.1	568.2	530.3	492.4	488.2	479.8	475.6
35°	892.3	795.5	694.5	597.6	564.0	526.1	492.4	454.5	446.1	433.5	425.1
37.5°	879.6	778.6	673.4	572.4	538.7	505.1	467.2	433.5	425.1	416.7	408.3
40°	846.0	749.2	656.6	559.8	526.1	492.4	454.5	420.9	412.5	404.0	395.6
42.5°	820.7	728.1	631.3	534.5	505.1	475.6	441.9	412.5	404.0	395.6	383.0
45°	799.7	702.9	601.9	505.1	484.0	463.0	437.7	416.7	408.3	395.6	387.2
47.5°	766.0	673.4	576.6	479.8	458.8	441.9	420.9	399.8	391.4	383.0	374.6
50°	740.7	643.9	547.1	450.3	433.5	416.7	399.8	383.0	383.0	387.2	387.2
52.5°	707.1	614.5	521.9	429.3	412.5	395.6	378.8	362.0	366.2	370.4	374.6
55°	677.6	589.2	496.6	404.0	387.2	370.4	349.3	332.5	336.7	340.9	345.1
57.5°	665.0	572.4	479.8	387.2	370.4	349.3	332.5	311.5	311.5	311.5	311.5
60°	656.6	559.8	467.2	370.4	349.3	332.5	311.5	290.4	286.2	286.2	282.0
62.5°	652.4	555.6	463.0	366.2	340.9	319.9	294.6	269.4	265.2	260.9	256.7
65°	635.5	547.1	454.5	362.0	332.5	307.2	277.8	248.3	244.1	244.1	239.9
67.5°	631.3	538.7	450.3	357.7	328.3	294.6	265.2	231.5	227.3	223.1	218.9
70°	597.6	517.7	433.5	349.3	315.7	286.2	252.5	218.9	214.6	206.2	202.0
72.5°	555.6	484.0	408.3	332.5	298.8	265.2	231.5	197.8	193.6	189.4	181.0
75°	492.4	425.1	357.7	290.4	260.9	235.7	206.2	176.8	172.6	168.4	159.9
77.5°	404.0	349.3	298.8	244.1	223.1	202.0	181.0	159.9	155.7	151.5	143.1
80°	286.2	252.5	223.1	189.4	176.8	159.9	147.3	130.5	130.5	126.3	126.3
82.5°	189.4	172.6	155.7	138.9	130.5	122.1	113.6	105.2	105.2	101.0	101.0
85°	134.7	126.3	113.6	105.2	101.0	92.6	88.4	80.0	80.0	80.0	80.0
87.5°	63.1	63.1	58.9	58.9	54.7	54.7	50.5	46.3	46.3	46.3	46.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	2794.6	2782.0	2769.4	2752.5	2739.9	2723.1	2702.0	2685.2	2664.2	2664.2	2660.0
5°	2255.9	2243.3	2230.7	2213.8	2201.2	2184.4	2171.7	2154.9	2138.1	2138.1	2133.9
7.5°	1788.7	1763.5	1738.2	1708.8	1683.5	1666.7	1649.8	1628.8	1612.0	1599.3	1586.7
10°	1557.3	1532.0	1502.5	1477.3	1447.8	1426.8	1405.7	1380.5	1359.4	1342.6	1325.8
12.5°	1418.4	1388.9	1359.4	1330.0	1300.5	1271.1	1245.8	1216.3	1186.9	1165.8	1144.8
15°	1220.5	1191.1	1161.6	1132.2	1102.7	1069.0	1035.4	997.5	963.8	947.0	934.4
17.5°	1005.9	976.4	942.8	913.3	879.6	854.4	829.1	803.9	778.6	761.8	749.2
20°	812.3	778.6	745.0	711.3	677.6	660.8	643.9	627.1	610.3	597.6	589.2
22.5°	635.5	614.5	597.6	576.6	555.6	542.9	534.5	521.9	509.3	509.3	509.3
25°	542.9	530.3	521.9	509.3	496.6	492.4	488.2	479.8	475.6	471.4	471.4
27.5°	526.1	513.5	500.8	488.2	475.6	471.4	467.2	458.8	454.5	454.5	454.5
30°	559.8	555.6	551.4	547.1	542.9	534.5	521.9	513.5	500.8	492.4	484.0
32.5°	467.2	463.0	463.0	458.8	454.5	463.0	467.2	475.6	479.8	484.0	488.2
35°	412.5	404.0	395.6	387.2	378.8	374.6	370.4	366.2	362.0	362.0	357.7
37.5°	399.8	391.4	383.0	374.6	366.2	362.0	357.7	353.5	349.3	349.3	345.1
40°	387.2	378.8	374.6	366.2	357.7	353.5	349.3	340.9	336.7	332.5	332.5
42.5°	374.6	370.4	362.0	357.7	349.3	345.1	340.9	332.5	328.3	324.1	319.9
45°	374.6	366.2	357.7	349.3	340.9	336.7	328.3	324.1	315.7	315.7	311.5
47.5°	366.2	357.7	349.3	340.9	332.5	328.3	319.9	315.7	307.2	303.0	298.8
50°	387.2	374.6	357.7	345.1	328.3	324.1	315.7	311.5	303.0	298.8	294.6
52.5°	378.8	366.2	349.3	336.7	319.9	311.5	307.2	298.8	290.4	286.2	282.0
55°	349.3	336.7	328.3	315.7	303.0	294.6	286.2	277.8	269.4	265.2	265.2
57.5°	311.5	307.2	303.0	298.8	294.6	286.2	277.8	265.2	256.7	252.5	248.3
60°	277.8	282.0	286.2	290.4	294.6	282.0	269.4	256.7	244.1	239.9	235.7
62.5°	252.5	260.9	269.4	273.6	282.0	269.4	256.7	244.1	231.5	227.3	223.1
65°	235.7	239.9	239.9	244.1	244.1	235.7	231.5	223.1	214.6	210.4	210.4
67.5°	214.6	214.6	214.6	210.4	210.4	206.2	206.2	202.0	197.8	193.6	193.6
70°	193.6	193.6	193.6	189.4	189.4	185.2	185.2	181.0	176.8	176.8	172.6
72.5°	176.8	176.8	172.6	172.6	168.4	168.4	168.4	164.1	164.1	159.9	159.9
75°	155.7	155.7	151.5	151.5	147.3	147.3	147.3	143.1	143.1	143.1	138.9
77.5°	138.9	138.9	134.7	134.7	130.5	130.5	130.5	126.3	126.3	122.1	122.1
80°	122.1	122.1	117.8	117.8	113.6	113.6	109.4	109.4	105.2	105.2	101.0
82.5°	96.8	96.8	96.8	96.8	96.8	92.6	92.6	88.4	84.2	84.2	80.0
85°	80.0	80.0	80.0	75.8	75.8	75.8	71.5	71.5	67.3	63.1	63.1
87.5°	46.3	46.3	46.3	42.1	42.1	42.1	42.1	42.1	42.1	42.1	37.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	2660.0	2655.7	2638.9	2622.1	2638.9	2655.7	2655.7	2655.7	2651.5	2651.5	2651.5
5°	2133.9	2129.6	2121.2	2112.8	2112.8	2108.6	2117.0	2125.4	2133.9	2142.3	2150.7
7.5°	1569.9	1557.3	1544.6	1532.0	1540.4	1544.6	1557.3	1565.7	1578.3	1586.7	1607.8
10°	1308.9	1292.1	1279.5	1266.8	1258.4	1250.0	1241.6	1237.4	1229.0	1220.5	1229.0
12.5°	1119.5	1098.5	1077.5	1052.2	1048.0	1043.8	1035.4	1026.9	1018.5	1010.1	1005.9
15°	917.5	900.7	892.3	879.6	862.8	846.0	837.5	833.3	824.9	816.5	812.3
17.5°	732.3	715.5	702.9	690.2	686.0	677.6	677.6	677.6	677.6	677.6	677.6
20°	576.6	564.0	564.0	559.8	559.8	555.6	559.8	564.0	564.0	568.2	572.4
22.5°	505.1	505.1	500.8	496.6	500.8	500.8	505.1	509.3	513.5	517.7	521.9
25°	467.2	463.0	467.2	471.4	471.4	471.4	475.6	475.6	479.8	479.8	479.8
27.5°	450.3	450.3	454.5	454.5	458.8	458.8	458.8	454.5	454.5	450.3	450.3
30°	475.6	467.2	467.2	467.2	463.0	458.8	454.5	454.5	450.3	446.1	441.9
32.5°	492.4	496.6	492.4	484.0	479.8	471.4	467.2	458.8	454.5	446.1	437.7
35°	357.7	353.5	362.0	366.2	370.4	374.6	378.8	383.0	383.0	387.2	387.2
37.5°	345.1	340.9	340.9	336.7	336.7	336.7	336.7	336.7	332.5	332.5	336.7
40°	328.3	324.1	324.1	319.9	319.9	315.7	315.7	315.7	315.7	315.7	315.7
42.5°	315.7	311.5	311.5	311.5	311.5	307.2	307.2	303.0	303.0	298.8	298.8
45°	311.5	307.2	303.0	298.8	298.8	294.6	294.6	294.6	290.4	290.4	290.4
47.5°	294.6	290.4	290.4	286.2	286.2	282.0	282.0	282.0	277.8	277.8	277.8
50°	286.2	282.0	282.0	277.8	277.8	273.6	273.6	273.6	269.4	269.4	269.4
52.5°	273.6	269.4	269.4	269.4	265.2	260.9	260.9	260.9	256.7	256.7	256.7
55°	260.9	256.7	256.7	256.7	252.5	248.3	248.3	248.3	244.1	244.1	244.1
57.5°	244.1	239.9	239.9	235.7	235.7	235.7	235.7	235.7	231.5	231.5	231.5
60°	231.5	227.3	227.3	223.1	223.1	218.9	218.9	218.9	218.9	218.9	218.9
62.5°	218.9	214.6	210.4	206.2	210.4	210.4	210.4	210.4	206.2	206.2	206.2
65°	206.2	202.0	197.8	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6
67.5°	189.4	185.2	181.0	176.8	181.0	181.0	181.0	181.0	181.0	181.0	181.0
70°	172.6	168.4	168.4	164.1	164.1	159.9	159.9	164.1	164.1	164.1	164.1
72.5°	155.7	151.5	151.5	147.3	147.3	147.3	147.3	147.3	147.3	147.3	147.3
75°	138.9	134.7	134.7	130.5	130.5	130.5	130.5	130.5	130.5	130.5	130.5
77.5°	117.8	113.6	113.6	113.6	113.6	113.6	113.6	117.8	117.8	117.8	117.8
80°	101.0	96.8	96.8	96.8	96.8	96.8	96.8	96.8	96.8	96.8	96.8
82.5°	80.0	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8
85°	58.9	54.7	54.7	54.7	58.9	58.9	58.9	58.9	58.9	58.9	58.9
87.5°	37.9	33.7	33.7	33.7	37.9	37.9	37.9	37.9	33.7	33.7	33.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	2651.5	2651.5	2651.5	2647.3	2643.1	2638.9	2634.7	2647.3	2655.7	2668.4	2676.8
5°	2154.9	2163.3	2167.5	2180.2	2192.8	2205.4	2218.0	2226.5	2234.9	2239.1	2247.5
7.5°	1624.6	1645.6	1662.5	1679.3	1696.1	1708.8	1725.6	1738.2	1750.9	1763.5	1776.1
10°	1233.2	1241.6	1245.8	1262.6	1275.3	1292.1	1304.7	1317.4	1330.0	1338.4	1351.0
12.5°	1001.7	993.3	989.1	989.1	989.1	989.1	989.1	997.5	1005.9	1014.3	1022.7
15°	808.1	803.9	799.7	795.5	791.3	782.8	778.6	787.0	795.5	803.9	812.3
17.5°	677.6	677.6	677.6	673.4	669.2	665.0	660.8	665.0	669.2	669.2	673.4
20°	580.8	585.0	589.2	593.4	593.4	597.6	597.6	601.9	606.1	606.1	610.3
22.5°	521.9	526.1	526.1	526.1	530.3	530.3	530.3	534.5	538.7	542.9	547.1
25°	475.6	475.6	471.4	471.4	475.6	475.6	475.6	475.6	479.8	479.8	479.8
27.5°	450.3	446.1	446.1	446.1	446.1	441.9	441.9	441.9	441.9	441.9	441.9
30°	437.7	433.5	429.3	425.1	425.1	420.9	416.7	416.7	416.7	416.7	416.7
32.5°	433.5	425.1	416.7	412.5	412.5	408.3	404.0	399.8	399.8	395.6	391.4
35°	387.2	383.0	383.0	378.8	374.6	370.4	366.2	366.2	366.2	362.0	362.0
37.5°	336.7	340.9	340.9	340.9	345.1	345.1	345.1	345.1	349.3	349.3	349.3
40°	315.7	315.7	315.7	319.9	324.1	324.1	328.3	328.3	332.5	332.5	332.5
42.5°	298.8	294.6	294.6	298.8	298.8	303.0	303.0	307.2	311.5	311.5	315.7
45°	290.4	286.2	286.2	286.2	286.2	282.0	282.0	286.2	290.4	294.6	298.8
47.5°	273.6	273.6	269.4	269.4	269.4	269.4	269.4	269.4	273.6	273.6	273.6
50°	265.2	265.2	260.9	260.9	260.9	260.9	260.9	260.9	260.9	260.9	260.9
52.5°	256.7	252.5	252.5	252.5	252.5	248.3	248.3	248.3	248.3	248.3	248.3
55°	244.1	239.9	239.9	239.9	239.9	239.9	239.9	239.9	244.1	244.1	244.1
57.5°	231.5	227.3	227.3	227.3	231.5	231.5	231.5	231.5	235.7	235.7	235.7
60°	218.9	218.9	218.9	218.9	218.9	218.9	218.9	223.1	223.1	227.3	227.3
62.5°	206.2	206.2	206.2	206.2	210.4	210.4	210.4	210.4	214.6	214.6	214.6
65°	193.6	193.6	193.6	193.6	197.8	197.8	197.8	197.8	197.8	197.8	197.8
67.5°	181.0	181.0	181.0	181.0	181.0	181.0	181.0	185.2	185.2	189.4	189.4
70°	164.1	159.9	159.9	164.1	164.1	168.4	168.4	172.6	172.6	176.8	176.8
72.5°	147.3	147.3	147.3	147.3	147.3	147.3	147.3	151.5	155.7	155.7	159.9
75°	130.5	130.5	130.5	130.5	134.7	134.7	134.7	138.9	138.9	143.1	143.1
77.5°	117.8	113.6	113.6	113.6	117.8	117.8	117.8	122.1	122.1	126.3	126.3
80°	96.8	96.8	96.8	96.8	101.0	101.0	101.0	101.0	105.2	105.2	105.2
82.5°	80.0	80.0	80.0	80.0	80.0	80.0	80.0	80.0	84.2	84.2	84.2
85°	58.9	58.9	58.9	58.9	63.1	63.1	63.1	63.1	63.1	63.1	63.1
87.5°	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.9	42.1	42.1	42.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	2676.8	2676.8	2676.8	2676.8	2685.2	2689.4	2697.8	2702.0	2697.8	2693.6	2685.2
5°	2251.7	2255.9	2255.9	2260.1	2260.1	2260.1	2260.1	2260.1	2268.5	2277.0	2285.4
7.5°	1780.3	1784.5	1788.7	1792.9	1792.9	1792.9	1788.7	1788.7	1792.9	1792.9	1797.2
10°	1363.6	1380.5	1393.1	1405.7	1397.3	1384.7	1376.3	1363.6	1363.6	1363.6	1359.4
12.5°	1031.2	1035.4	1043.8	1048.0	1043.8	1043.8	1039.6	1035.4	1039.6	1048.0	1052.2
15°	816.5	816.5	820.7	820.7	824.9	829.1	829.1	833.3	841.8	846.0	854.4
17.5°	677.6	681.8	681.8	686.0	686.0	690.2	690.2	690.2	698.7	707.1	719.7
20°	610.3	610.3	610.3	610.3	610.3	606.1	606.1	601.9	606.1	614.5	618.7
22.5°	547.1	551.4	551.4	551.4	547.1	542.9	534.5	530.3	530.3	534.5	534.5
25°	479.8	475.6	475.6	471.4	471.4	475.6	475.6	475.6	479.8	479.8	484.0
27.5°	441.9	437.7	437.7	433.5	433.5	437.7	437.7	437.7	437.7	437.7	437.7
30°	412.5	412.5	408.3	404.0	408.3	408.3	412.5	412.5	416.7	416.7	420.9
32.5°	391.4	387.2	387.2	383.0	387.2	387.2	391.4	391.4	395.6	399.8	399.8
35°	362.0	362.0	362.0	362.0	362.0	362.0	357.7	357.7	357.7	357.7	357.7
37.5°	345.1	345.1	340.9	336.7	336.7	336.7	336.7	336.7	332.5	328.3	324.1
40°	332.5	328.3	328.3	324.1	319.9	319.9	315.7	311.5	311.5	307.2	307.2
42.5°	315.7	311.5	311.5	307.2	303.0	303.0	298.8	294.6	294.6	294.6	290.4
45°	294.6	294.6	290.4	286.2	286.2	286.2	282.0	282.0	282.0	282.0	277.8
47.5°	273.6	273.6	269.4	269.4	269.4	269.4	265.2	265.2	265.2	265.2	265.2
50°	260.9	260.9	260.9	260.9	260.9	260.9	256.7	256.7	256.7	256.7	256.7
52.5°	248.3	248.3	248.3	248.3	248.3	248.3	248.3	248.3	248.3	248.3	248.3
55°	244.1	244.1	244.1	244.1	244.1	244.1	239.9	239.9	239.9	244.1	244.1
57.5°	235.7	235.7	231.5	231.5	231.5	231.5	231.5	231.5	231.5	231.5	231.5
60°	227.3	227.3	227.3	227.3	227.3	227.3	227.3	227.3	227.3	227.3	227.3
62.5°	214.6	214.6	214.6	214.6	214.6	218.9	218.9	218.9	218.9	218.9	214.6
65°	197.8	202.0	202.0	202.0	202.0	202.0	202.0	202.0	202.0	202.0	202.0
67.5°	189.4	189.4	189.4	189.4	189.4	189.4	189.4	189.4	189.4	189.4	189.4
70°	176.8	176.8	172.6	172.6	172.6	176.8	176.8	176.8	176.8	176.8	176.8
72.5°	159.9	159.9	159.9	159.9	159.9	159.9	159.9	159.9	159.9	164.1	164.1
75°	143.1	143.1	143.1	143.1	143.1	143.1	143.1	143.1	143.1	143.1	143.1
77.5°	126.3	126.3	122.1	122.1	122.1	126.3	126.3	126.3	126.3	130.5	130.5
80°	105.2	105.2	105.2	105.2	105.2	105.2	105.2	105.2	105.2	109.4	109.4
82.5°	84.2	84.2	84.2	84.2	84.2	84.2	84.2	84.2	84.2	88.4	88.4
85°	63.1	67.3	67.3	67.3	67.3	67.3	67.3	67.3	67.3	71.5	71.5
87.5°	42.1	42.1	42.1	42.1	42.1	42.1	37.9	37.9	37.9	37.9	33.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	2681.0	2685.2	2689.4	2689.4	2693.6	2697.8	2697.8	2714.7	2731.5	2739.9	2748.3
5°	2293.8	2289.6	2289.6	2285.4	2281.2	2293.8	2306.4	2331.7	2356.9	2361.1	2369.5
7.5°	1797.2	1801.4	1805.6	1805.6	1809.8	1797.2	1780.3	1784.5	1788.7	1809.8	1826.6
10°	1359.4	1363.6	1367.9	1367.9	1372.1	1367.9	1359.4	1372.1	1384.7	1401.5	1422.6
12.5°	1056.4	1069.0	1081.7	1090.1	1102.7	1111.1	1115.3	1132.2	1144.8	1165.8	1186.9
15°	862.8	871.2	879.6	888.1	896.5	904.9	913.3	930.1	947.0	972.2	997.5
17.5°	728.1	728.1	732.3	732.3	732.3	740.7	749.2	757.6	761.8	787.0	812.3
20°	622.9	618.7	614.5	610.3	606.1	614.5	618.7	622.9	627.1	643.9	656.6
22.5°	534.5	534.5	538.7	538.7	538.7	534.5	526.1	530.3	530.3	538.7	551.4
25°	484.0	484.0	484.0	479.8	479.8	484.0	488.2	488.2	484.0	488.2	492.4
27.5°	437.7	441.9	441.9	446.1	446.1	450.3	450.3	450.3	450.3	454.5	458.8
30°	420.9	420.9	425.1	425.1	425.1	429.3	433.5	433.5	433.5	437.7	446.1
32.5°	404.0	408.3	412.5	416.7	420.9	425.1	425.1	429.3	429.3	433.5	437.7
35°	357.7	353.5	353.5	349.3	345.1	345.1	345.1	345.1	340.9	345.1	345.1
37.5°	319.9	319.9	319.9	315.7	315.7	319.9	319.9	319.9	319.9	324.1	324.1
40°	303.0	303.0	303.0	303.0	303.0	303.0	303.0	307.2	307.2	311.5	315.7
42.5°	290.4	290.4	290.4	290.4	290.4	294.6	294.6	294.6	294.6	298.8	298.8
45°	277.8	277.8	277.8	277.8	277.8	277.8	277.8	282.0	282.0	286.2	290.4
47.5°	265.2	265.2	265.2	265.2	265.2	269.4	273.6	273.6	273.6	277.8	277.8
50°	256.7	256.7	256.7	256.7	256.7	260.9	260.9	265.2	265.2	269.4	273.6
52.5°	248.3	248.3	248.3	248.3	248.3	252.5	252.5	256.7	256.7	260.9	265.2
55°	244.1	244.1	244.1	239.9	239.9	244.1	244.1	248.3	248.3	252.5	252.5
57.5°	231.5	231.5	231.5	231.5	231.5	231.5	231.5	235.7	235.7	239.9	244.1
60°	227.3	227.3	223.1	223.1	218.9	223.1	223.1	227.3	227.3	231.5	231.5
62.5°	214.6	214.6	214.6	210.4	210.4	214.6	214.6	214.6	214.6	218.9	223.1
65°	202.0	202.0	202.0	197.8	197.8	202.0	202.0	202.0	202.0	206.2	210.4
67.5°	189.4	189.4	189.4	185.2	185.2	185.2	185.2	189.4	189.4	193.6	197.8
70°	176.8	176.8	176.8	172.6	172.6	172.6	168.4	172.6	176.8	181.0	181.0
72.5°	164.1	164.1	164.1	159.9	159.9	159.9	155.7	159.9	159.9	164.1	164.1
75°	143.1	143.1	143.1	143.1	143.1	143.1	138.9	138.9	138.9	143.1	143.1
77.5°	130.5	130.5	130.5	126.3	126.3	126.3	122.1	122.1	122.1	126.3	126.3
80°	109.4	109.4	109.4	105.2	105.2	105.2	101.0	101.0	101.0	105.2	105.2
82.5°	88.4	88.4	88.4	84.2	84.2	84.2	80.0	80.0	80.0	84.2	84.2
85°	71.5	71.5	71.5	71.5	71.5	71.5	67.3	67.3	67.3	71.5	75.8
87.5°	33.7	33.7	37.9	37.9	37.9	37.9	33.7	33.7	29.5	29.5	33.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	2756.8	2765.2	2786.2	2803.1	2824.1	2840.9	2853.6	2870.4	2883.0	2895.6	2904.1
5°	2373.8	2378.0	2399.0	2420.1	2436.9	2457.9	2487.4	2516.9	2546.3	2575.8	2596.8
7.5°	1847.7	1864.5	1889.7	1919.2	1944.5	1969.7	1999.2	2032.8	2062.3	2091.8	2121.2
10°	1439.4	1456.2	1481.5	1506.7	1527.8	1553.0	1586.7	1620.4	1654.1	1687.7	1721.4
12.5°	1207.9	1229.0	1258.4	1287.9	1313.1	1342.6	1384.7	1422.6	1464.7	1502.5	1544.6
15°	1018.5	1043.8	1081.7	1123.7	1161.6	1199.5	1241.6	1283.7	1321.6	1363.6	1405.7
17.5°	837.5	862.8	896.5	934.4	968.0	1001.7	1052.2	1098.5	1149.0	1195.3	1241.6
20°	673.4	686.0	719.7	753.4	787.0	820.7	858.6	896.5	934.4	972.2	1031.2
22.5°	559.8	568.2	585.0	597.6	614.5	627.1	665.0	702.9	736.5	774.4	829.1
25°	492.4	496.6	509.3	517.7	530.3	538.7	564.0	585.0	610.3	631.3	681.8
27.5°	458.8	463.0	467.2	471.4	475.6	479.8	496.6	513.5	526.1	542.9	589.2
30°	450.3	454.5	467.2	475.6	488.2	496.6	505.1	513.5	521.9	530.3	559.8
32.5°	441.9	446.1	446.1	441.9	441.9	437.7	446.1	450.3	458.8	463.0	488.2
35°	349.3	349.3	353.5	357.7	362.0	366.2	378.8	387.2	399.8	408.3	429.3
37.5°	328.3	328.3	332.5	340.9	345.1	349.3	357.7	366.2	374.6	383.0	404.0
40°	315.7	319.9	324.1	328.3	332.5	336.7	345.1	349.3	357.7	362.0	378.8
42.5°	303.0	303.0	307.2	315.7	319.9	324.1	332.5	336.7	345.1	349.3	366.2
45°	294.6	298.8	303.0	307.2	307.2	311.5	319.9	328.3	332.5	340.9	357.7
47.5°	282.0	282.0	290.4	294.6	303.0	307.2	315.7	319.9	328.3	332.5	349.3
50°	273.6	277.8	286.2	290.4	298.8	303.0	315.7	324.1	336.7	345.1	353.5
52.5°	265.2	269.4	277.8	282.0	290.4	294.6	311.5	328.3	340.9	357.7	357.7
55°	256.7	256.7	265.2	277.8	286.2	294.6	303.0	315.7	324.1	332.5	332.5
57.5°	244.1	248.3	256.7	269.4	277.8	286.2	294.6	303.0	307.2	315.7	311.5
60°	235.7	235.7	248.3	260.9	273.6	286.2	286.2	286.2	282.0	282.0	282.0
62.5°	223.1	227.3	244.1	265.2	282.0	298.8	286.2	273.6	260.9	248.3	252.5
65°	214.6	218.9	227.3	239.9	248.3	256.7	248.3	244.1	235.7	227.3	231.5
67.5°	197.8	202.0	206.2	206.2	210.4	210.4	210.4	210.4	210.4	210.4	214.6
70°	185.2	185.2	185.2	189.4	189.4	189.4	189.4	189.4	189.4	189.4	193.6
72.5°	168.4	168.4	168.4	168.4	168.4	168.4	168.4	168.4	168.4	168.4	172.6
75°	147.3	147.3	147.3	147.3	147.3	147.3	147.3	147.3	147.3	147.3	151.5
77.5°	130.5	130.5	130.5	130.5	130.5	130.5	130.5	130.5	126.3	126.3	130.5
80°	109.4	109.4	109.4	109.4	105.2	105.2	105.2	105.2	105.2	105.2	109.4
82.5°	88.4	88.4	88.4	88.4	84.2	84.2	84.2	84.2	80.0	80.0	84.2
85°	80.0	84.2	84.2	88.4	88.4	88.4	84.2	80.0	75.8	71.5	71.5
87.5°	33.7	33.7	33.7	33.7	29.5	29.5	29.5	29.5	29.5	29.5	29.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	2916.7	2925.1	2933.5	2946.2	2963.0	2975.6	2988.2	3013.5	3043.0	3068.2	3093.5
5°	2617.9	2638.9	2660.0	2685.2	2710.5	2731.5	2756.8	2807.3	2857.8	2904.1	2954.6
7.5°	2146.5	2175.9	2201.2	2243.3	2281.2	2323.3	2361.1	2424.3	2483.2	2546.3	2605.2
10°	1755.1	1788.7	1822.4	1877.1	1936.0	1990.8	2045.5	2096.0	2150.7	2201.2	2251.7
12.5°	1586.7	1624.6	1666.7	1700.4	1738.2	1771.9	1805.6	1864.5	1923.4	1982.3	2041.3
15°	1447.8	1489.9	1532.0	1574.1	1612.0	1654.1	1691.9	1742.4	1797.2	1847.7	1898.2
17.5°	1287.9	1330.0	1376.3	1422.6	1468.9	1515.2	1561.5	1633.0	1704.6	1771.9	1843.5
20°	1085.9	1144.8	1199.5	1262.6	1325.8	1388.9	1452.0	1527.8	1603.5	1675.1	1750.9
22.5°	883.8	938.6	993.3	1069.0	1144.8	1216.3	1292.1	1393.1	1489.9	1590.9	1687.7
25°	736.5	787.0	837.5	921.7	1001.7	1085.9	1165.8	1287.9	1405.7	1527.8	1645.6
27.5°	635.5	681.8	728.1	816.5	904.9	989.1	1077.5	1212.1	1342.6	1477.3	1607.8
30°	589.2	618.7	648.2	732.3	816.5	896.5	980.6	1111.1	1241.6	1372.1	1502.5
32.5°	513.5	538.7	564.0	639.7	715.5	787.0	862.8	997.5	1128.0	1262.6	1393.1
35°	454.5	475.6	496.6	568.2	635.5	707.1	774.4	909.1	1043.8	1178.5	1313.1
37.5°	420.9	441.9	458.8	521.9	589.2	652.4	715.5	850.2	980.6	1115.3	1245.8
40°	395.6	408.3	425.1	488.2	547.1	610.3	669.2	791.3	917.5	1039.6	1161.6
42.5°	378.8	395.6	408.3	463.0	521.9	576.6	631.3	749.2	867.0	980.6	1098.5
45°	374.6	391.4	408.3	454.5	500.8	542.9	589.2	702.9	816.5	930.1	1043.8
47.5°	366.2	378.8	395.6	433.5	467.2	505.1	538.7	652.4	766.0	875.4	989.1
50°	362.0	366.2	374.6	408.3	441.9	475.6	509.3	622.9	736.5	850.2	963.8
52.5°	357.7	357.7	357.7	387.2	416.7	441.9	471.4	585.0	702.9	816.5	930.1
55°	332.5	328.3	328.3	357.7	383.0	412.5	437.7	551.4	665.0	774.4	888.1
57.5°	307.2	303.0	298.8	324.1	349.3	374.6	399.8	513.5	631.3	745.0	858.6
60°	282.0	277.8	277.8	303.0	324.1	349.3	370.4	488.2	601.9	719.7	833.3
62.5°	252.5	256.7	256.7	277.8	303.0	324.1	345.1	463.0	585.0	702.9	820.7
65°	231.5	235.7	235.7	260.9	286.2	311.5	336.7	450.3	568.2	681.8	795.5
67.5°	214.6	218.9	218.9	248.3	273.6	303.0	328.3	429.3	534.5	635.5	736.5
70°	197.8	197.8	202.0	231.5	260.9	290.4	319.9	408.3	496.6	580.8	669.2
72.5°	176.8	181.0	185.2	214.6	239.9	269.4	294.6	374.6	454.5	534.5	614.5
75°	155.7	159.9	164.1	189.4	214.6	239.9	265.2	340.9	412.5	488.2	559.8
77.5°	138.9	143.1	147.3	168.4	189.4	210.4	231.5	286.2	345.1	399.8	454.5
80°	113.6	113.6	117.8	134.7	151.5	164.1	181.0	218.9	256.7	290.4	328.3
82.5°	84.2	88.4	88.4	101.0	109.4	122.1	130.5	151.5	168.4	189.4	206.2
85°	71.5	67.3	67.3	75.8	80.0	88.4	92.6	105.2	113.6	126.3	134.7
87.5°	29.5	25.3	25.3	29.5	37.9	42.1	46.3	46.3	50.5	50.5	50.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	3106.1	3114.5	3127.1	3135.5	3156.6	3173.4	3194.5	3211.3	3223.9	3245.0	3236.6
5°	2992.5	3030.3	3068.2	3106.1	3135.5	3165.0	3190.3	3219.7	3253.4	3316.5	3333.4
7.5°	2655.7	2706.3	2752.5	2803.1	2862.0	2920.9	2979.8	3038.7	3093.5	3173.4	3223.9
10°	2323.3	2394.8	2462.1	2533.7	2588.4	2643.1	2693.6	2748.3	2824.1	2904.1	2996.7
12.5°	2112.8	2184.4	2255.9	2327.5	2407.4	2483.2	2563.2	2638.9	2710.5	2773.6	2878.8
15°	1973.9	2053.9	2129.6	2205.4	2302.2	2394.8	2491.6	2584.2	2689.4	2773.6	2845.1
17.5°	1940.3	2037.1	2129.6	2226.5	2327.5	2428.5	2529.5	2630.5	2735.7	2862.0	2954.6
20°	1881.3	2011.8	2142.3	2272.7	2403.2	2529.5	2660.0	2786.2	2925.1	3076.6	3118.7
22.5°	1847.7	2003.4	2163.3	2319.0	2495.8	2676.8	2853.6	3030.3	3177.6	3291.3	3417.5
25°	1843.5	2037.1	2234.9	2428.5	2651.5	2870.4	3093.5	3312.3	3501.7	3615.4	3716.4
27.5°	1839.2	2074.9	2306.4	2537.9	2811.5	3080.8	3354.4	3623.8	3800.5	3964.7	4048.9
30°	1788.7	2070.7	2356.9	2638.9	2946.2	3253.4	3560.6	3867.9	4048.9	4162.5	4204.6
32.5°	1725.6	2058.1	2390.6	2723.1	3072.4	3421.7	3766.9	4116.2	4259.3	4356.1	4322.4
35°	1675.1	2041.3	2403.2	2765.2	3135.5	3510.1	3880.5	4250.9	4457.1	4591.8	4537.1
37.5°	1628.8	2011.8	2394.8	2777.8	3211.3	3644.8	4078.3	4511.8	4709.6	4852.7	4789.6
40°	1574.1	1982.3	2394.8	2803.1	3299.7	3792.1	4288.8	4781.2	5037.9	5160.0	5063.2
42.5°	1527.8	1952.9	2382.2	2807.3	3337.6	3867.9	4398.2	4928.5	5214.7	5387.3	5265.2
45°	1468.9	1894.0	2314.8	2739.9	3324.9	3910.0	4490.8	5075.8	5408.3	5543.0	5374.6
47.5°	1405.7	1826.6	2243.3	2660.0	3282.9	3905.8	4528.7	5151.6	5458.8	5618.7	5463.0
50°	1384.7	1805.6	2222.2	2643.1	3316.5	3994.1	4667.5	5341.0	5564.0	5694.5	5488.3
52.5°	1380.5	1826.6	2277.0	2723.1	3400.7	4074.1	4751.7	5425.1	5606.1	5745.0	5559.8
55°	1367.9	1851.9	2331.7	2811.5	3518.5	4229.8	4936.9	5644.0	5825.0	5926.0	5787.1
57.5°	1380.5	1902.4	2420.1	2941.9	3670.1	4398.2	5126.3	5854.4	6073.3	6144.8	6115.4
60°	1388.9	1944.5	2495.8	3051.4	3762.7	4473.9	5185.2	5896.5	6123.8	6300.6	6334.2
62.5°	1367.9	1915.0	2457.9	3005.1	3649.0	4293.0	4936.9	5580.9	5955.4	6216.4	6367.9
65°	1304.7	1809.8	2319.0	2824.1	3417.5	4015.2	4608.6	5202.1	5597.7	5984.9	6107.0
67.5°	1165.8	1595.1	2024.4	2453.7	2971.4	3489.1	4002.6	4520.2	5016.9	5391.5	5559.8
70°	1010.1	1346.8	1687.7	2024.4	2495.8	2967.2	3438.6	3910.0	4347.7	4760.1	4920.1
72.5°	879.6	1140.6	1405.7	1666.7	2003.4	2335.9	2672.6	3005.1	3522.8	3935.2	4090.9
75°	749.2	938.6	1123.7	1313.1	1544.6	1776.1	2003.4	2234.9	2601.0	2971.4	3127.1
77.5°	576.6	702.9	824.9	947.0	1106.9	1262.6	1422.6	1578.3	1835.0	2112.8	2192.8
80°	399.8	471.4	538.7	610.3	736.5	862.8	989.1	1115.3	1283.7	1439.4	1561.5
82.5°	248.3	294.6	336.7	378.8	479.8	580.8	677.6	778.6	846.0	854.4	976.4
85°	159.9	189.4	214.6	239.9	298.8	362.0	420.9	479.8	429.3	399.8	475.6
87.5°	63.1	80.0	92.6	105.2	101.0	96.8	92.6	88.4	75.8	67.3	84.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	3245.0	3257.6	3270.2	3278.6	3291.3	3295.5	3299.7	3299.7	3303.9	3308.1	3316.5
5°	3400.7	3426.0	3451.2	3472.3	3497.5	3518.5	3535.4	3556.4	3573.3	3573.3	3569.1
7.5°	3270.2	3333.4	3396.5	3459.6	3522.8	3569.1	3611.1	3657.4	3699.5	3707.9	3716.4
10°	3097.7	3165.0	3228.1	3295.5	3358.6	3430.2	3497.5	3564.8	3636.4	3649.0	3665.9
12.5°	2937.7	3017.7	3097.7	3173.4	3253.4	3303.9	3354.4	3400.7	3451.2	3484.9	3518.5
15°	2933.5	3000.9	3068.2	3131.3	3198.7	3228.1	3257.6	3282.9	3312.3	3312.3	3316.5
17.5°	3030.3	3072.4	3114.5	3152.4	3194.5	3198.7	3207.1	3211.3	3215.5	3202.9	3190.3
20°	3219.7	3236.6	3253.4	3270.2	3287.1	3257.6	3232.4	3202.9	3173.4	3139.8	3110.3
22.5°	3497.5	3459.6	3421.7	3383.9	3346.0	3295.5	3240.8	3190.3	3135.5	3093.5	3051.4
25°	3758.5	3712.2	3665.9	3619.6	3573.3	3463.8	3354.4	3240.8	3131.3	3085.0	3038.7
27.5°	4107.8	4036.2	3964.7	3893.1	3821.6	3674.3	3527.0	3379.7	3232.4	3152.4	3076.6
30°	4192.0	4112.0	4032.0	3947.8	3867.9	3724.8	3585.9	3442.8	3299.7	3207.1	3118.7
32.5°	4314.0	4221.4	4128.8	4036.2	3943.6	3804.7	3665.9	3522.8	3383.9	3299.7	3211.3
35°	4516.0	4410.8	4305.6	4196.2	4090.9	3947.8	3809.0	3665.9	3522.8	3426.0	3333.4
37.5°	4688.6	4566.5	4444.5	4322.4	4200.4	4074.1	3943.6	3817.4	3686.9	3590.1	3497.5
40°	4882.2	4747.5	4612.8	4482.4	4347.7	4229.8	4112.0	3989.9	3872.1	3796.3	3720.6
42.5°	5050.5	4886.4	4726.5	4566.5	4402.4	4322.4	4246.7	4166.7	4086.7	4048.9	4006.8
45°	5168.4	5016.9	4861.2	4709.6	4558.1	4499.2	4440.3	4381.4	4322.4	4360.3	4398.2
47.5°	5218.9	5096.8	4979.0	4861.2	4739.1	4760.1	4781.2	4798.0	4819.1	4869.6	4924.3
50°	5265.2	5197.9	5126.3	5059.0	4987.4	5067.4	5143.1	5223.1	5303.1	5408.3	5513.5
52.5°	5357.8	5319.9	5286.2	5248.4	5210.5	5349.4	5488.3	5627.2	5766.0	5883.9	6001.7
55°	5635.6	5606.1	5576.6	5543.0	5513.5	5711.3	5904.9	6102.7	6300.6	6422.6	6544.7
57.5°	6018.6	6001.7	5980.7	5963.9	5942.8	6136.4	6325.8	6515.2	6708.8	6826.7	6948.7
60°	6309.0	6313.2	6313.2	6317.4	6317.4	6464.7	6612.0	6763.5	6910.8	7011.8	7117.1
62.5°	6464.7	6456.3	6447.9	6439.5	6431.0	6553.1	6675.1	6797.2	6919.3	6995.0	7070.8
65°	6296.4	6342.6	6388.9	6435.2	6481.5	6498.4	6511.0	6527.8	6540.5	6586.8	6633.1
67.5°	5732.4	5825.0	5913.4	6005.9	6094.3	6031.2	5972.3	5909.1	5846.0	5858.6	5867.1
70°	5105.3	5210.5	5319.9	5425.1	5530.4	5383.0	5235.7	5084.2	4936.9	4886.4	4835.9
72.5°	4305.6	4398.2	4495.0	4587.6	4680.2	4499.2	4322.4	4141.5	3960.5	3872.1	3783.7
75°	3291.3	3400.7	3514.3	3623.8	3733.2	3531.2	3324.9	3122.9	2916.7	2857.8	2803.1
77.5°	2399.0	2529.5	2660.0	2790.4	2920.9	2739.9	2558.9	2373.8	2192.8	2159.1	2125.4
80°	1746.6	1847.7	1944.5	2045.5	2142.3	2037.1	1931.8	1826.6	1721.4	1717.2	1713.0
82.5°	1178.5	1266.8	1351.0	1439.4	1523.6	1481.5	1443.6	1401.5	1359.4	1401.5	1447.8
85°	606.1	728.1	854.4	976.4	1098.5	1085.9	1077.5	1064.8	1052.2	1106.9	1157.4
87.5°	122.1	227.3	332.5	433.5	538.7	513.5	488.2	458.8	433.5	450.3	463.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	3320.7	3324.9	3324.9	3324.9	3324.9	3324.9	3316.5	3312.3	3303.9	3295.5	3282.9
5°	3569.1	3564.8	3548.0	3531.2	3510.1	3493.3	3480.7	3463.8	3451.2	3434.4	3409.1
7.5°	3724.8	3733.2	3703.7	3678.5	3649.0	3619.6	3590.1	3560.6	3531.2	3501.7	3442.8
10°	3678.5	3691.1	3674.3	3657.4	3636.4	3619.6	3585.9	3548.0	3514.3	3476.5	3404.9
12.5°	3548.0	3581.7	3573.3	3564.8	3556.4	3548.0	3527.0	3501.7	3480.7	3455.4	3375.5
15°	3316.5	3316.5	3320.7	3324.9	3324.9	3329.2	3333.4	3337.6	3341.8	3346.0	3299.7
17.5°	3177.6	3165.0	3165.0	3165.0	3165.0	3165.0	3181.8	3202.9	3219.7	3236.6	3223.9
20°	3076.6	3047.2	3043.0	3043.0	3038.7	3034.5	3064.0	3097.7	3127.1	3156.6	3173.4
22.5°	3009.3	2967.2	2963.0	2958.8	2954.6	2950.4	2988.2	3026.1	3064.0	3101.9	3160.8
25°	2992.5	2946.2	2950.4	2954.6	2954.6	2958.8	2988.2	3017.7	3047.2	3076.6	3177.6
27.5°	2996.7	2920.9	2925.1	2929.3	2929.3	2933.5	2979.8	3021.9	3068.2	3110.3	3236.6
30°	3026.1	2937.7	2929.3	2920.9	2912.5	2904.1	2967.2	3030.3	3093.5	3156.6	3253.4
32.5°	3127.1	3043.0	3021.9	3000.9	2979.8	2958.8	3034.5	3106.1	3181.8	3253.4	3333.4
35°	3236.6	3144.0	3135.5	3127.1	3114.5	3106.1	3173.4	3245.0	3312.3	3379.7	3451.2
37.5°	3400.7	3308.1	3299.7	3287.1	3278.6	3266.0	3341.8	3413.3	3489.1	3560.6	3623.8
40°	3644.8	3569.1	3564.8	3564.8	3560.6	3556.4	3615.4	3678.5	3737.4	3796.3	3838.4
42.5°	3968.9	3931.0	3943.6	3960.5	3973.1	3985.7	4032.0	4082.5	4128.8	4175.1	4162.5
45°	4436.1	4473.9	4478.2	4482.4	4486.6	4490.8	4503.4	4520.2	4532.9	4545.5	4495.0
47.5°	4974.8	5025.3	5050.5	5075.8	5096.8	5122.1	5105.3	5084.2	5067.4	5046.3	4920.1
50°	5614.5	5719.7	5715.5	5711.3	5702.9	5698.7	5665.0	5631.4	5593.5	5559.8	5374.6
52.5°	6119.6	6237.4	6258.5	6279.5	6300.6	6321.6	6258.5	6195.3	6128.0	6064.9	5833.4
55°	6662.5	6784.6	6788.8	6793.0	6793.0	6797.2	6708.8	6620.4	6527.8	6439.5	6199.5
57.5°	7066.6	7184.4	7171.8	7163.4	7150.7	7138.1	7032.9	6927.7	6822.5	6717.2	6477.3
60°	7218.1	7319.1	7293.8	7268.6	7239.1	7213.9	7133.9	7053.9	6969.8	6889.8	6658.3
62.5°	7146.5	7222.3	7184.4	7150.7	7112.9	7075.0	6974.0	6868.7	6767.7	6662.5	6494.2
65°	6675.1	6721.4	6670.9	6624.6	6578.3	6527.8	6443.7	6359.5	6271.1	6186.9	6073.3
67.5°	5879.7	5888.1	5883.9	5879.7	5875.5	5871.3	5749.2	5627.2	5500.9	5378.8	5370.4
70°	4789.6	4739.1	4747.5	4760.1	4768.6	4777.0	4684.4	4596.0	4503.4	4410.8	4452.9
72.5°	3695.3	3606.9	3628.0	3653.2	3674.3	3695.3	3619.6	3548.0	3472.3	3396.5	3455.4
75°	2744.1	2689.4	2710.5	2735.7	2756.8	2777.8	2748.3	2718.9	2685.2	2655.7	2710.5
77.5°	2091.8	2058.1	2062.3	2062.3	2066.5	2066.5	2070.7	2079.1	2083.4	2087.6	2146.5
80°	1704.6	1700.4	1696.1	1691.9	1683.5	1679.3	1721.4	1763.5	1805.6	1847.7	1877.1
82.5°	1489.9	1532.0	1506.7	1485.7	1460.5	1435.2	1473.1	1511.0	1548.8	1586.7	1574.1
85°	1212.1	1262.6	1216.3	1170.0	1119.5	1073.2	1106.9	1136.4	1170.0	1199.5	1182.7
87.5°	479.8	492.4	416.7	345.1	269.4	193.6	307.2	416.7	530.3	639.7	656.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963

CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3	3030.3
2.5°	3270.2	3253.4	3240.8	3236.6	3228.1	3223.9	3215.5	3207.1	3194.5	3186.1	3173.4
5°	3379.7	3354.4	3324.9	3282.9	3245.0	3202.9	3160.8	3122.9	3085.0	3043.0	3005.1
7.5°	3383.9	3324.9	3266.0	3211.3	3152.4	3097.7	3038.7	2988.2	2933.5	2878.8	2828.3
10°	3337.6	3266.0	3194.5	3122.9	3055.6	2984.0	2912.5	2853.6	2790.4	2727.3	2668.4
12.5°	3299.7	3219.7	3139.8	3055.6	2975.6	2891.4	2807.3	2748.3	2689.4	2630.5	2571.6
15°	3253.4	3202.9	3156.6	3080.8	3005.1	2929.3	2853.6	2773.6	2697.8	2617.9	2537.9
17.5°	3215.5	3202.9	3190.3	3139.8	3089.3	3034.5	2984.0	2904.1	2824.1	2739.9	2660.0
20°	3194.5	3211.3	3228.1	3202.9	3177.6	3148.2	3122.9	3064.0	3005.1	2941.9	2883.0
22.5°	3219.7	3282.9	3341.8	3346.0	3354.4	3358.6	3362.8	3308.1	3253.4	3194.5	3139.8
25°	3278.6	3379.7	3480.7	3535.4	3590.1	3649.0	3703.7	3670.1	3636.4	3602.7	3569.1
27.5°	3358.6	3484.9	3611.1	3691.1	3766.9	3846.8	3926.8	3922.6	3918.4	3910.0	3905.8
30°	3346.0	3442.8	3539.6	3636.4	3733.2	3830.0	3926.8	3977.3	4023.6	4074.1	4124.6
32.5°	3417.5	3497.5	3581.7	3682.7	3783.7	3888.9	3989.9	4095.2	4196.2	4301.4	4406.6
35°	3527.0	3598.5	3674.3	3783.7	3897.3	4006.8	4120.4	4246.7	4377.1	4507.6	4633.9
37.5°	3691.1	3754.2	3821.6	3914.2	4011.0	4103.6	4200.4	4385.6	4570.7	4760.1	4945.3
40°	3880.5	3922.6	3964.7	4053.1	4141.5	4229.8	4318.2	4549.7	4781.2	5012.7	5244.2
42.5°	4154.1	4141.5	4128.8	4200.4	4276.1	4347.7	4423.4	4633.9	4844.3	5054.8	5265.2
45°	4444.5	4394.0	4343.5	4377.1	4415.0	4448.7	4486.6	4701.2	4915.9	5134.7	5349.4
47.5°	4793.8	4667.5	4541.3	4511.8	4482.4	4448.7	4419.2	4650.7	4882.2	5117.9	5349.4
50°	5189.4	5000.0	4814.9	4739.1	4659.1	4583.4	4503.4	4692.8	4886.4	5080.0	5269.4
52.5°	5601.9	5366.2	5134.7	5016.9	4899.0	4777.0	4659.1	4819.1	4983.2	5147.4	5307.3
55°	5955.4	5715.5	5471.4	5332.5	5193.6	5054.8	4915.9	5075.8	5235.7	5395.7	5555.6
57.5°	6237.4	5997.5	5757.6	5627.2	5492.5	5362.0	5227.3	5378.8	5534.6	5690.3	5841.8
60°	6431.0	6199.5	5968.1	5841.8	5715.5	5589.3	5463.0	5644.0	5825.0	6010.2	6191.1
62.5°	6330.0	6161.7	5993.3	5938.6	5883.9	5825.0	5770.3	5942.8	6111.2	6283.7	6456.3
65°	5959.6	5846.0	5732.4	5787.1	5846.0	5900.7	5959.6	6073.3	6186.9	6304.8	6418.4
67.5°	5357.8	5349.4	5336.7	5458.8	5580.9	5707.1	5829.2	5904.9	5976.5	6052.2	6128.0
70°	4495.0	4541.3	4583.4	4793.8	5004.3	5214.7	5425.1	5454.6	5484.1	5513.5	5543.0
72.5°	3518.5	3577.5	3640.6	3918.4	4192.0	4469.7	4747.5	4730.7	4713.8	4692.8	4676.0
75°	2769.4	2824.1	2883.0	3139.8	3396.5	3653.2	3910.0	3838.4	3771.1	3699.5	3628.0
77.5°	2209.6	2268.5	2331.7	2571.6	2811.5	3055.6	3295.5	3122.9	2950.4	2777.8	2605.2
80°	1902.4	1931.8	1957.1	2121.2	2281.2	2445.3	2609.5	2432.7	2251.7	2070.7	1894.0
82.5°	1561.5	1544.6	1532.0	1628.8	1725.6	1822.4	1919.2	1750.9	1582.5	1409.9	1241.6
85°	1165.8	1149.0	1132.2	1182.7	1233.2	1287.9	1338.4	1144.8	951.2	753.4	559.8
87.5°	677.6	694.5	711.3	766.0	820.7	879.6	934.4	736.5	538.7	336.7	138.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675963
 CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	3030.3	3030.3
2.5°	3148.2	3127.1
5°	2975.6	2946.2
7.5°	2786.2	2748.3
10°	2613.7	2563.2
12.5°	2504.2	2441.1
15°	2462.1	2386.4
17.5°	2588.4	2516.9
20°	2782.0	2685.2
22.5°	3017.7	2899.9
25°	3426.0	3282.9
27.5°	3758.5	3611.1
30°	3964.7	3804.7
32.5°	4192.0	3981.5
35°	4427.6	4225.6
37.5°	4713.8	4486.6
40°	5008.5	4772.8
42.5°	5109.5	4958.0
45°	5206.3	5063.2
47.5°	5227.3	5109.5
50°	5248.4	5231.5
52.5°	5307.3	5303.1
55°	5559.8	5564.0
57.5°	5871.3	5896.5
60°	6157.5	6128.0
62.5°	6304.8	6153.3
65°	6203.8	5993.3
67.5°	5900.7	5673.5
70°	5235.7	4928.5
72.5°	4406.6	4137.2
75°	3396.5	3169.2
77.5°	2415.8	2226.5
80°	1700.4	1511.0
82.5°	1090.1	938.6
85°	492.4	429.3
87.5°	138.9	134.7
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675963
CATALOG NUMBER: CCW-SA-2E-727-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)