

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P676449

Luminaire Tested: **CCW-SA-2D-760-U-T3-HSS**

Issue Date: 04/25/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P676449  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/25/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCW-SA-2D-760-U-T3-HSS  
Description: INVUE CLEAR CURVE Wall Pack MOUNT Light Square Luminaire @800mA w/  
T3 distribution lens and House Side Shield  
Light Source: (32) 5700K CCT, 70 CRI LEDs  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8218.6 lumens  
Efficiency: N/A  
Efficacy: 101.7 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B1 - U0 - G2

Input Watts (W): 80.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P676449  
 CATALOG NUMBER: CCW-SA-2D-760-U-T3-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 5.8 fc  
 Type III - Medium - N/A

REPORT NUMBER: P676449  
CATALOG NUMBER: CCW-SA-2D-760-U-T3-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 57-Deg Lateral      - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P676449

CATALOG NUMBER: CCW-SA-2D-760-U-T3-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	968.8	0.0	968.8
	% Fixture	11.8	0.0	11.8
<b>Street Side</b>	Lumens	7249.8	0.0	7249.8
	% Fixture	88.2	0.0	88.2
<b>Total</b>	Lumens	8218.6	0.0	8218.6
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.8	1.2
10°-20°	264.9	3.2
20°-30°	446.3	5.4
30°-40°	763.8	9.3
40°-50°	1282.5	15.6
50°-60°	1968.7	24.0
60°-70°	2272.9	27.7
70°-80°	1073.7	13.1
80°-90°	50.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8218.6	100.0
0°-180°	8218.6	100.0




REPORT NUMBER: P676449  
 CATALOG NUMBER: CCW-SA-2D-760-U-T3-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	497.2	6.0			
FM (30°-60°)	3551.9	43.2			
FH (60°-80°)	3150.7	38.3			G2/5000
FVH (80°-90°)	50.0	0.6			G1/100
BL (0°-30°)	308.8	3.8	B1/500		
BM (30°-60°)	463.1	5.6	B1/1000		
BH (60°-80°)	195.9	2.4	B1/500		G1/500
BVH (80°-90°)	0.9	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**  
 Type III Medium





REPORT NUMBER: P676449

CATALOG NUMBER: CCW-SA-2D-760-U-T3-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	57°	65°	75°	85°
0°	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1
2.5°	999.4	993.1	999.4	1007.8	999.4	1005.7	1003.6	1009.9	1001.5	1001.5	1007.8
5°	934.3	944.8	949.0	959.5	970.0	988.9	1001.5	1001.5	1014.1	1020.4	1028.8
7.5°	911.2	894.4	911.2	919.6	930.1	961.6	980.5	988.9	1005.7	1028.8	1041.4
10°	877.6	890.2	890.2	917.5	932.2	951.1	984.7	991.0	1028.8	1051.9	1064.5
12.5°	875.5	875.5	886.0	904.9	934.3	970.0	1012.0	999.4	1039.3	1081.3	1102.2
15°	881.8	896.5	896.5	921.7	944.8	995.2	1030.9	1033.0	1089.6	1131.6	1150.5
17.5°	909.1	902.8	911.2	925.9	961.6	1009.9	1068.7	1075.0	1140.0	1196.7	1224.0
20°	965.8	976.3	963.7	955.3	970.0	1033.0	1108.5	1121.1	1194.6	1249.2	1276.5
22.5°	1177.8	1169.4	1119.0	1060.3	1035.1	1064.5	1146.3	1175.7	1261.8	1326.9	1350.0
25°	1417.2	1402.5	1343.7	1255.5	1140.0	1127.4	1221.9	1221.9	1345.8	1417.2	1410.9
27.5°	1643.9	1639.7	1570.4	1478.1	1314.3	1224.0	1282.8	1305.9	1440.3	1499.1	1471.8
30°	1874.9	1879.1	1816.1	1704.8	1532.6	1379.4	1368.9	1387.8	1511.7	1604.0	1547.3
32.5°	2143.6	2105.8	2061.7	1908.5	1751.0	1578.8	1480.2	1471.8	1591.4	1675.4	1599.8
35°	2382.9	2359.9	2311.6	2173.0	1992.4	1786.7	1648.1	1627.1	1692.2	1803.5	1721.6
37.5°	2592.9	2569.8	2506.8	2414.4	2273.8	2044.9	1849.7	1818.2	1845.5	1963.0	1864.4
40°	2773.5	2779.8	2763.0	2672.7	2542.5	2334.7	2110.0	2059.6	2036.5	2141.5	2030.2
42.5°	2903.6	2964.5	2968.7	2857.4	2752.5	2639.1	2387.1	2347.3	2292.7	2380.9	2303.2
45°	3176.6	3143.0	3164.0	3124.1	3008.6	2991.8	2706.3	2683.2	2607.6	2637.0	2555.1
47.5°	3390.7	3384.4	3424.3	3359.2	3327.7	3329.8	3069.5	3029.6	2922.5	2977.1	2884.7
50°	3514.6	3481.0	3625.9	3676.3	3670.0	3695.1	3436.9	3403.3	3300.4	3380.2	3182.9
52.5°	3544.0	3604.9	3741.3	3924.0	4001.7	4054.2	3837.9	3825.3	3714.0	3764.4	3491.5
55°	3617.5	3676.3	3756.0	4056.3	4343.9	4356.5	4232.6	4245.2	4146.5	4133.9	3785.4
57.5°	3615.4	3602.8	3823.2	4171.7	4570.6	4751.2	4684.0	4623.1	4516.1	4392.2	3974.4
60°	3483.1	3476.8	3705.6	4186.4	4694.5	5108.1	5135.4	5064.0	4795.3	4612.6	4196.9
62.5°	3220.7	3245.9	3476.8	4060.5	4812.1	5236.2	5337.0	5288.7	4954.9	4759.6	4459.4
65°	2920.4	2867.9	3136.7	3745.5	4547.6	5198.4	5416.7	5400.0	5143.8	4919.2	4700.8
67.5°	2343.1	2366.2	2571.9	3222.8	4096.2	5059.8	5603.6	5628.8	5295.0	5059.8	4774.3
70°	1484.4	1526.3	1740.5	2328.4	3344.5	4623.1	5771.6	5845.1	5414.6	5047.2	4560.1
72.5°	432.5	449.3	741.1	1161.0	2131.0	3707.7	5502.8	5540.6	5181.6	4581.1	3527.2
75°	142.8	151.2	218.3	377.9	835.6	1916.9	4064.7	4243.1	4123.4	3321.4	2017.6
77.5°	94.5	98.7	119.7	180.6	317.0	600.5	2179.3	2370.4	2324.2	1555.7	650.8
80°	69.3	71.4	88.2	121.8	193.2	216.3	804.1	930.1	898.6	356.9	130.2
82.5°	44.1	44.1	65.1	86.1	121.8	107.1	233.0	258.2	251.9	136.5	50.4
85°	29.4	31.5	48.3	67.2	67.2	50.4	67.2	77.7	84.0	73.5	23.1
87.5°	8.4	10.5	27.3	46.2	27.3	25.2	23.1	25.2	29.4	39.9	12.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676449

CATALOG NUMBER: CCW-SA-2D-760-U-T3-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1	1014.1
2.5°	1014.1	1022.5	1020.4	1024.6	1018.3	1012.0	1018.3	1018.3	1018.3	1012.0	1007.8
5°	1022.5	1018.3	1022.5	1014.1	1022.5	1014.1	1009.9	997.3	995.2	995.2	1003.6
7.5°	1035.1	1039.3	1020.4	1020.4	1001.5	1005.7	995.2	997.3	993.1	986.8	982.6
10°	1054.0	1070.8	1051.9	1045.6	1024.6	1007.8	982.6	970.0	970.0	961.6	970.0
12.5°	1106.4	1100.1	1089.6	1068.7	1043.5	1009.9	949.0	888.1	837.7	799.9	818.8
15°	1148.4	1146.3	1131.6	1091.7	1058.2	955.3	802.0	644.6	560.6	522.8	516.5
17.5°	1213.5	1207.2	1182.0	1129.5	1018.3	791.5	550.1	417.8	335.9	317.0	310.7
20°	1274.4	1272.3	1217.7	1150.5	917.5	577.4	359.0	275.0	251.9	254.0	249.8
22.5°	1339.5	1329.0	1263.9	1125.3	730.6	384.2	256.1	245.6	237.2	235.1	239.3
25°	1413.0	1375.2	1310.1	1068.7	537.5	264.5	241.4	233.0	224.6	222.5	222.5
27.5°	1442.4	1417.2	1331.1	932.2	340.1	230.9	226.7	216.3	205.8	199.5	197.4
30°	1509.6	1467.6	1352.1	732.7	241.4	212.1	205.8	193.2	178.5	168.0	168.0
32.5°	1576.7	1526.3	1354.2	512.3	201.6	191.1	180.6	163.8	144.9	134.4	136.5
35°	1660.7	1591.4	1331.1	331.7	180.6	168.0	147.0	128.1	111.3	102.9	102.9
37.5°	1803.5	1738.4	1236.6	218.3	163.8	142.8	121.8	100.8	86.1	79.8	79.8
40°	1984.0	1900.1	1106.4	172.2	144.9	121.8	96.6	77.7	69.3	63.0	63.0
42.5°	2200.3	2095.3	913.3	153.3	128.1	100.8	75.6	60.9	52.5	52.5	50.4
45°	2416.5	2244.4	715.9	140.7	113.4	84.0	58.8	48.3	44.1	42.0	42.0
47.5°	2725.2	2424.9	512.3	128.1	98.7	65.1	48.3	39.9	35.7	33.6	35.7
50°	3021.2	2595.0	363.2	115.5	81.9	52.5	39.9	35.7	31.5	29.4	29.4
52.5°	3281.5	2712.6	254.0	100.8	69.3	44.1	35.7	31.5	29.4	27.3	27.3
55°	3424.3	2672.7	174.3	86.1	56.7	37.8	31.5	27.3	25.2	23.1	23.1
57.5°	3571.3	2561.4	132.3	71.4	46.2	35.7	29.4	25.2	23.1	21.0	21.0
60°	3695.1	2479.5	102.9	56.7	37.8	29.4	25.2	21.0	18.9	16.8	14.7
62.5°	3701.4	2315.8	75.6	42.0	29.4	25.2	21.0	16.8	10.5	8.4	6.3
65°	3726.6	2143.6	54.6	31.5	21.0	18.9	14.7	8.4	4.2	0.0	0.0
67.5°	3638.5	1940.0	44.1	23.1	14.7	10.5	6.3	2.1	0.0	0.0	0.0
70°	3279.4	1637.6	33.6	16.8	10.5	6.3	2.1	0.0	0.0	0.0	0.0
72.5°	2347.3	1064.5	23.1	12.6	4.2	2.1	0.0	0.0	0.0	0.0	0.0
75°	1251.3	453.5	16.8	8.4	2.1	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	392.6	115.5	10.5	4.2	2.1	0.0	0.0	0.0	0.0	0.0	0.0
80°	86.1	31.5	6.3	2.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	29.4	12.6	4.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	10.5	4.2	2.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.2	2.1	2.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)