

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675951

Luminaire Tested: **CCW-SA-2D-722-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P675951
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2D-722-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @800mA w/
SLR distribution lens
Light Source: (32) 2200K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6817.5 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 80.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 9.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P675951
CATALOG NUMBER: CCW-SA-2D-722-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1402.7	0.0	1402.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	5414.8	0.0	5414.8
	% Fixture	79.4	0.0	79.4
Total	Lumens	6817.5	0.0	6817.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.2	2.5
10°-20°	357.2	5.2
20°-30°	522.6	7.7
30°-40°	736.2	10.8
40°-50°	1011.6	14.8
50°-60°	1378.9	20.2
60°-70°	1509.2	22.1
70°-80°	871.5	12.8
80°-90°	261.3	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6817.5	100.0
0°-180°	6817.5	100.0




REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	700.2	10.3			
FM (30°-60°)	2487.9	36.5			
FH (60°-80°)	2004.8	29.4			G2/5000
FVH (80°-90°)	221.9	3.3			G2/225
BL (0°-30°)	348.7	5.1	B1/500		
BM (30°-60°)	638.8	9.4	B1/1000		
BH (60°-80°)	375.9	5.5	B1/500		G1/500
BVH (80°-90°)	39.3	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P675951

CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	2246.6	2234.5	2225.5	2216.4	2204.3	2195.2	2183.1	2171.0	2155.9	2143.8	2128.7
5°	2116.6	2080.3	2044.0	2022.9	1998.7	1977.5	1953.3	1926.1	1898.9	1868.7	1841.5
7.5°	1974.5	1929.1	1883.8	1847.5	1808.2	1771.9	1732.6	1699.3	1666.1	1632.8	1599.6
10°	1841.5	1799.1	1756.8	1711.4	1663.1	1617.7	1569.3	1524.0	1478.6	1433.3	1387.9
12.5°	1753.8	1702.4	1654.0	1602.6	1554.2	1502.8	1451.4	1409.1	1366.7	1321.4	1279.0
15°	1714.5	1666.1	1620.7	1569.3	1517.9	1466.5	1415.1	1366.7	1321.4	1273.0	1224.6
17.5°	1808.2	1738.7	1669.1	1602.6	1536.1	1469.5	1403.0	1342.5	1282.1	1221.6	1161.1
20°	1929.1	1841.5	1756.8	1675.2	1590.5	1508.8	1424.2	1339.5	1254.9	1170.2	1085.5
22.5°	2083.4	1983.6	1886.8	1781.0	1672.1	1566.3	1457.4	1351.6	1245.8	1136.9	1031.1
25°	2358.5	2240.6	2122.7	1971.5	1817.3	1666.1	1511.9	1372.8	1236.7	1097.6	958.5
27.5°	2594.4	2434.1	2276.9	2095.5	1914.0	1732.6	1551.2	1390.9	1233.7	1073.4	913.2
30°	2733.5	2576.2	2419.0	2198.3	1980.6	1759.8	1539.1	1360.7	1185.3	1006.9	828.5
32.5°	2860.5	2685.1	2509.7	2267.8	2022.9	1781.0	1536.1	1339.5	1146.0	949.5	752.9
35°	3035.8	2842.3	2651.8	2370.6	2089.4	1808.2	1527.0	1324.4	1118.8	916.2	710.6
37.5°	3223.3	2984.4	2748.6	2437.1	2125.7	1814.2	1502.8	1303.2	1103.7	904.1	704.5
40°	3428.9	3138.6	2851.4	2506.7	2165.0	1820.3	1475.6	1276.0	1076.5	873.9	674.3
42.5°	3562.0	3247.5	2933.0	2561.1	2192.2	1820.3	1448.4	1251.8	1055.3	855.7	659.2
45°	3637.6	3332.2	3029.8	2627.6	2225.5	1823.3	1421.2	1227.6	1034.1	837.6	644.1
47.5°	3670.8	3386.6	3102.4	2679.0	2258.7	1835.4	1412.1	1215.5	1016.0	819.4	619.9
50°	3758.5	3507.5	3256.6	2803.0	2352.5	1898.9	1445.3	1233.7	1025.0	813.4	601.7
52.5°	3809.9	3595.2	3380.5	2914.9	2449.2	1983.6	1517.9	1282.1	1046.2	810.4	574.5
55°	3997.4	3791.8	3586.2	3090.3	2591.3	2095.5	1596.5	1336.5	1076.5	813.4	553.3
57.5°	4236.3	4018.6	3803.9	3268.7	2733.5	2198.3	1663.1	1384.9	1103.7	825.5	544.3
60°	4402.6	4190.9	3982.3	3413.8	2842.3	2273.9	1702.4	1412.1	1121.8	828.5	538.2
62.5°	4420.7	4148.6	3879.5	3326.1	2772.8	2216.4	1663.1	1381.8	1100.6	816.4	535.2
65°	4305.8	3988.3	3670.8	3141.7	2612.5	2083.4	1554.2	1297.2	1040.2	780.1	523.1
67.5°	4076.0	3704.1	3332.2	2848.4	2364.6	1880.8	1397.0	1176.2	958.5	737.8	517.1
70°	3540.8	3214.2	2890.7	2470.4	2053.1	1632.8	1212.5	1031.1	852.7	671.3	489.8
72.5°	2972.3	2666.9	2364.6	2022.9	1684.2	1342.5	1000.9	864.8	728.7	589.6	453.6
75°	2276.9	2047.1	1820.3	1566.3	1312.3	1055.3	801.3	701.5	601.7	501.9	402.2
77.5°	1599.6	1475.6	1354.6	1164.1	973.6	783.1	592.7	526.1	459.6	393.1	326.6
80°	1085.5	1016.0	949.5	813.4	677.3	538.2	402.2	359.8	314.5	272.1	226.8
82.5°	674.3	671.3	665.2	571.5	477.8	384.0	290.3	254.0	220.7	184.4	148.2
85°	308.4	359.8	408.2	356.8	305.4	254.0	202.6	178.4	154.2	127.0	102.8
87.5°	96.8	117.9	136.1	130.0	120.9	114.9	105.8	90.7	75.6	60.5	45.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951

CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	2116.6	2107.5	2095.5	2083.4	2068.2	2056.1	2041.0	2025.9	2022.9	2016.8	2013.8
5°	1823.3	1805.2	1784.0	1765.9	1747.7	1726.6	1708.4	1687.2	1672.1	1654.0	1638.9
7.5°	1566.3	1536.1	1502.8	1469.5	1439.3	1409.1	1375.8	1345.6	1330.4	1315.3	1300.2
10°	1360.7	1330.4	1303.2	1273.0	1251.8	1233.7	1212.5	1191.4	1173.2	1155.1	1136.9
12.5°	1257.9	1236.7	1215.5	1194.4	1170.2	1149.0	1124.8	1100.6	1079.5	1061.3	1040.2
15°	1194.4	1164.1	1130.9	1100.6	1067.4	1037.1	1003.9	970.6	946.4	925.3	901.1
17.5°	1118.8	1073.4	1031.1	985.7	949.5	913.2	873.9	837.6	810.4	780.1	752.9
20°	1034.1	982.7	928.3	876.9	834.6	795.2	752.9	710.6	680.3	647.1	616.8
22.5°	961.5	895.0	825.5	755.9	710.6	665.2	616.8	571.5	544.3	514.0	486.8
25°	882.9	810.4	734.8	659.2	613.8	565.4	520.1	471.7	450.5	432.4	411.2
27.5°	840.6	768.0	692.4	619.9	577.5	532.2	489.8	444.5	429.4	411.2	396.1
30°	755.9	686.4	613.8	541.2	511.0	483.8	453.6	423.3	417.3	414.3	408.2
32.5°	680.3	607.8	535.2	462.6	435.4	408.2	381.0	353.8	350.8	344.7	341.7
35°	641.0	571.5	498.9	429.4	405.2	378.0	353.8	326.6	320.5	311.4	305.4
37.5°	632.0	559.4	483.8	411.2	387.0	362.8	335.6	311.4	305.4	299.4	293.3
40°	607.8	538.2	471.7	402.2	378.0	353.8	326.6	302.4	296.3	290.3	284.2
42.5°	589.6	523.1	453.6	384.0	362.8	341.7	317.5	296.3	290.3	284.2	275.2
45°	574.5	505.0	432.4	362.8	347.7	332.6	314.5	299.4	293.3	284.2	278.2
47.5°	550.3	483.8	414.3	344.7	329.6	317.5	302.4	287.3	281.2	275.2	269.1
50°	532.2	462.6	393.1	323.5	311.4	299.4	287.3	275.2	275.2	278.2	278.2
52.5°	508.0	441.5	374.9	308.4	296.3	284.2	272.1	260.0	263.1	266.1	269.1
55°	486.8	423.3	356.8	290.3	278.2	266.1	251.0	238.9	241.9	244.9	247.9
57.5°	477.8	411.2	344.7	278.2	266.1	251.0	238.9	223.8	223.8	223.8	223.8
60°	471.7	402.2	335.6	266.1	251.0	238.9	223.8	208.6	205.6	205.6	202.6
62.5°	468.7	399.1	332.6	263.1	244.9	229.8	211.7	193.5	190.5	187.5	184.4
65°	456.6	393.1	326.6	260.0	238.9	220.7	199.6	178.4	175.4	175.4	172.4
67.5°	453.6	387.0	323.5	257.0	235.9	211.7	190.5	166.3	163.3	160.3	157.2
70°	429.4	371.9	311.4	251.0	226.8	205.6	181.4	157.2	154.2	148.2	145.1
72.5°	399.1	347.7	293.3	238.9	214.7	190.5	166.3	142.1	139.1	136.1	130.0
75°	353.8	305.4	257.0	208.6	187.5	169.3	148.2	127.0	124.0	120.9	114.9
77.5°	290.3	251.0	214.7	175.4	160.3	145.1	130.0	114.9	111.9	108.9	102.8
80°	205.6	181.4	160.3	136.1	127.0	114.9	105.8	93.7	93.7	90.7	90.7
82.5°	136.1	124.0	111.9	99.8	93.7	87.7	81.6	75.6	75.6	72.6	72.6
85°	96.8	90.7	81.6	75.6	72.6	66.5	63.5	57.5	57.5	57.5	57.5
87.5°	45.4	45.4	42.3	42.3	39.3	39.3	36.3	33.3	33.3	33.3	33.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951

CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	2007.8	1998.7	1989.6	1977.5	1968.5	1956.4	1941.2	1929.1	1914.0	1914.0	1911.0
5°	1620.7	1611.7	1602.6	1590.5	1581.4	1569.3	1560.3	1548.2	1536.1	1536.1	1533.0
7.5°	1285.1	1266.9	1248.8	1227.6	1209.5	1197.4	1185.3	1170.2	1158.1	1149.0	1140.0
10°	1118.8	1100.6	1079.5	1061.3	1040.2	1025.0	1009.9	991.8	976.7	964.6	952.5
12.5°	1019.0	997.8	976.7	955.5	934.3	913.2	895.0	873.9	852.7	837.6	822.5
15°	876.9	855.7	834.6	813.4	792.2	768.0	743.8	716.6	692.4	680.3	671.3
17.5°	722.7	701.5	677.3	656.2	632.0	613.8	595.7	577.5	559.4	547.3	538.2
20°	583.6	559.4	535.2	511.0	486.8	474.7	462.6	450.5	438.4	429.4	423.3
22.5°	456.6	441.5	429.4	414.3	399.1	390.1	384.0	374.9	365.9	365.9	365.9
25°	390.1	381.0	374.9	365.9	356.8	353.8	350.8	344.7	341.7	338.7	338.7
27.5°	378.0	368.9	359.8	350.8	341.7	338.7	335.6	329.6	326.6	326.6	326.6
30°	402.2	399.1	396.1	393.1	390.1	384.0	374.9	368.9	359.8	353.8	347.7
32.5°	335.6	332.6	332.6	329.6	326.6	332.6	335.6	341.7	344.7	347.7	350.8
35°	296.3	290.3	284.2	278.2	272.1	269.1	266.1	263.1	260.0	260.0	257.0
37.5°	287.3	281.2	275.2	269.1	263.1	260.0	257.0	254.0	251.0	251.0	247.9
40°	278.2	272.1	269.1	263.1	257.0	254.0	251.0	244.9	241.9	238.9	238.9
42.5°	269.1	266.1	260.0	257.0	251.0	247.9	244.9	238.9	235.9	232.8	229.8
45°	269.1	263.1	257.0	251.0	244.9	241.9	235.9	232.8	226.8	226.8	223.8
47.5°	263.1	257.0	251.0	244.9	238.9	235.9	229.8	226.8	220.7	217.7	214.7
50°	278.2	269.1	257.0	247.9	235.9	232.8	226.8	223.8	217.7	214.7	211.7
52.5°	272.1	263.1	251.0	241.9	229.8	223.8	220.7	214.7	208.6	205.6	202.6
55°	251.0	241.9	235.9	226.8	217.7	211.7	205.6	199.6	193.5	190.5	190.5
57.5°	223.8	220.7	217.7	214.7	211.7	205.6	199.6	190.5	184.4	181.4	178.4
60°	199.6	202.6	205.6	208.6	211.7	202.6	193.5	184.4	175.4	172.4	169.3
62.5°	181.4	187.5	193.5	196.5	202.6	193.5	184.4	175.4	166.3	163.3	160.3
65°	169.3	172.4	172.4	175.4	175.4	169.3	166.3	160.3	154.2	151.2	151.2
67.5°	154.2	154.2	154.2	151.2	151.2	148.2	148.2	145.1	142.1	139.1	139.1
70°	139.1	139.1	139.1	136.1	136.1	133.0	133.0	130.0	127.0	127.0	124.0
72.5°	127.0	127.0	124.0	124.0	120.9	120.9	120.9	117.9	117.9	114.9	114.9
75°	111.9	111.9	108.9	108.9	105.8	105.8	105.8	102.8	102.8	102.8	99.8
77.5°	99.8	99.8	96.8	96.8	93.7	93.7	93.7	90.7	90.7	87.7	87.7
80°	87.7	87.7	84.7	84.7	81.6	81.6	78.6	78.6	75.6	75.6	72.6
82.5°	69.5	69.5	69.5	69.5	69.5	66.5	66.5	63.5	60.5	60.5	57.5
85°	57.5	57.5	57.5	54.4	54.4	54.4	51.4	51.4	48.4	45.4	45.4
87.5°	33.3	33.3	33.3	30.2	30.2	30.2	30.2	30.2	30.2	30.2	27.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	1911.0	1908.0	1895.9	1883.8	1895.9	1908.0	1908.0	1908.0	1905.0	1905.0	1905.0
5°	1533.0	1530.0	1524.0	1517.9	1517.9	1514.9	1520.9	1527.0	1533.0	1539.1	1545.1
7.5°	1127.9	1118.8	1109.7	1100.6	1106.7	1109.7	1118.8	1124.8	1133.9	1140.0	1155.1
10°	940.4	928.3	919.2	910.1	904.1	898.1	892.0	889.0	882.9	876.9	882.9
12.5°	804.3	789.2	774.1	755.9	752.9	749.9	743.8	737.8	731.7	725.7	722.7
15°	659.2	647.1	641.0	632.0	619.9	607.8	601.7	598.7	592.7	586.6	583.6
17.5°	526.1	514.0	505.0	495.9	492.9	486.8	486.8	486.8	486.8	486.8	486.8
20°	414.3	405.2	405.2	402.2	402.2	399.1	402.2	405.2	405.2	408.2	411.2
22.5°	362.8	362.8	359.8	356.8	359.8	359.8	362.8	365.9	368.9	371.9	374.9
25°	335.6	332.6	335.6	338.7	338.7	338.7	341.7	341.7	344.7	344.7	344.7
27.5°	323.5	323.5	326.6	326.6	329.6	329.6	329.6	326.6	326.6	323.5	323.5
30°	341.7	335.6	335.6	335.6	332.6	329.6	326.6	326.6	323.5	320.5	317.5
32.5°	353.8	356.8	353.8	347.7	344.7	338.7	335.6	329.6	326.6	320.5	314.5
35°	257.0	254.0	260.0	263.1	266.1	269.1	272.1	275.2	275.2	278.2	278.2
37.5°	247.9	244.9	244.9	241.9	241.9	241.9	241.9	241.9	238.9	238.9	241.9
40°	235.9	232.8	232.8	229.8	229.8	226.8	226.8	226.8	226.8	226.8	226.8
42.5°	226.8	223.8	223.8	223.8	223.8	220.7	220.7	217.7	217.7	214.7	214.7
45°	223.8	220.7	217.7	214.7	214.7	211.7	211.7	211.7	208.6	208.6	208.6
47.5°	211.7	208.6	208.6	205.6	205.6	202.6	202.6	202.6	199.6	199.6	199.6
50°	205.6	202.6	202.6	199.6	199.6	196.5	196.5	196.5	193.5	193.5	193.5
52.5°	196.5	193.5	193.5	193.5	190.5	187.5	187.5	187.5	184.4	184.4	184.4
55°	187.5	184.4	184.4	184.4	181.4	178.4	178.4	178.4	175.4	175.4	175.4
57.5°	175.4	172.4	172.4	169.3	169.3	169.3	169.3	169.3	166.3	166.3	166.3
60°	166.3	163.3	163.3	160.3	160.3	157.2	157.2	157.2	157.2	157.2	157.2
62.5°	157.2	154.2	151.2	148.2	151.2	151.2	151.2	151.2	148.2	148.2	148.2
65°	148.2	145.1	142.1	139.1	139.1	139.1	139.1	139.1	139.1	139.1	139.1
67.5°	136.1	133.0	130.0	127.0	130.0	130.0	130.0	130.0	130.0	130.0	130.0
70°	124.0	120.9	120.9	117.9	117.9	114.9	114.9	117.9	117.9	117.9	117.9
72.5°	111.9	108.9	108.9	105.8	105.8	105.8	105.8	105.8	105.8	105.8	105.8
75°	99.8	96.8	96.8	93.7	93.7	93.7	93.7	93.7	93.7	93.7	93.7
77.5°	84.7	81.6	81.6	81.6	81.6	81.6	81.6	84.7	84.7	84.7	84.7
80°	72.6	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5
82.5°	57.5	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.4
85°	42.3	39.3	39.3	39.3	42.3	42.3	42.3	42.3	42.3	42.3	42.3
87.5°	27.2	24.2	24.2	24.2	27.2	27.2	27.2	27.2	24.2	24.2	24.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	1905.0	1905.0	1905.0	1901.9	1898.9	1895.9	1892.9	1901.9	1908.0	1917.1	1923.1
5°	1548.2	1554.2	1557.2	1566.3	1575.4	1584.4	1593.5	1599.6	1605.6	1608.6	1614.7
7.5°	1167.2	1182.3	1194.4	1206.5	1218.6	1227.6	1239.7	1248.8	1257.9	1266.9	1276.0
10°	886.0	892.0	895.0	907.1	916.2	928.3	937.4	946.4	955.5	961.5	970.6
12.5°	719.7	713.6	710.6	710.6	710.6	710.6	710.6	716.6	722.7	728.7	734.8
15°	580.6	577.5	574.5	571.5	568.5	562.4	559.4	565.4	571.5	577.5	583.6
17.5°	486.8	486.8	486.8	483.8	480.8	477.8	474.7	477.8	480.8	480.8	483.8
20°	417.3	420.3	423.3	426.3	426.3	429.4	429.4	432.4	435.4	435.4	438.4
22.5°	374.9	378.0	378.0	378.0	381.0	381.0	381.0	384.0	387.0	390.1	393.1
25°	341.7	341.7	338.7	338.7	341.7	341.7	341.7	341.7	344.7	344.7	344.7
27.5°	323.5	320.5	320.5	320.5	320.5	317.5	317.5	317.5	317.5	317.5	317.5
30°	314.5	311.4	308.4	305.4	305.4	302.4	299.4	299.4	299.4	299.4	299.4
32.5°	311.4	305.4	299.4	296.3	296.3	293.3	290.3	287.3	287.3	284.2	281.2
35°	278.2	275.2	275.2	272.1	269.1	266.1	263.1	263.1	263.1	260.0	260.0
37.5°	241.9	244.9	244.9	244.9	247.9	247.9	247.9	247.9	251.0	251.0	251.0
40°	226.8	226.8	226.8	229.8	232.8	232.8	235.9	235.9	238.9	238.9	238.9
42.5°	214.7	211.7	211.7	214.7	214.7	217.7	217.7	220.7	223.8	223.8	226.8
45°	208.6	205.6	205.6	205.6	205.6	202.6	202.6	205.6	208.6	211.7	214.7
47.5°	196.5	196.5	193.5	193.5	193.5	193.5	193.5	193.5	196.5	196.5	196.5
50°	190.5	190.5	187.5	187.5	187.5	187.5	187.5	187.5	187.5	187.5	187.5
52.5°	184.4	181.4	181.4	181.4	181.4	178.4	178.4	178.4	178.4	178.4	178.4
55°	175.4	172.4	172.4	172.4	172.4	172.4	172.4	172.4	175.4	175.4	175.4
57.5°	166.3	163.3	163.3	163.3	166.3	166.3	166.3	166.3	169.3	169.3	169.3
60°	157.2	157.2	157.2	157.2	157.2	157.2	157.2	160.3	160.3	163.3	163.3
62.5°	148.2	148.2	148.2	148.2	151.2	151.2	151.2	151.2	154.2	154.2	154.2
65°	139.1	139.1	139.1	139.1	142.1	142.1	142.1	142.1	142.1	142.1	142.1
67.5°	130.0	130.0	130.0	130.0	130.0	130.0	130.0	133.0	133.0	136.1	136.1
70°	117.9	114.9	114.9	117.9	117.9	120.9	120.9	124.0	124.0	127.0	127.0
72.5°	105.8	105.8	105.8	105.8	105.8	105.8	105.8	108.9	111.9	111.9	114.9
75°	93.7	93.7	93.7	93.7	96.8	96.8	96.8	99.8	99.8	102.8	102.8
77.5°	84.7	81.6	81.6	81.6	84.7	84.7	84.7	87.7	87.7	90.7	90.7
80°	69.5	69.5	69.5	69.5	72.6	72.6	72.6	72.6	75.6	75.6	75.6
82.5°	57.5	57.5	57.5	57.5	57.5	57.5	57.5	57.5	60.5	60.5	60.5
85°	42.3	42.3	42.3	42.3	45.4	45.4	45.4	45.4	45.4	45.4	45.4
87.5°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	30.2	30.2	30.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951

CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	1923.1	1923.1	1923.1	1923.1	1929.1	1932.2	1938.2	1941.2	1938.2	1935.2	1929.1
5°	1617.7	1620.7	1620.7	1623.7	1623.7	1623.7	1623.7	1623.7	1629.8	1635.8	1641.9
7.5°	1279.0	1282.1	1285.1	1288.1	1288.1	1288.1	1285.1	1285.1	1288.1	1288.1	1291.1
10°	979.7	991.8	1000.9	1009.9	1003.9	994.8	988.8	979.7	979.7	979.7	976.7
12.5°	740.8	743.8	749.9	752.9	749.9	749.9	746.9	743.8	746.9	752.9	755.9
15°	586.6	586.6	589.6	589.6	592.7	595.7	595.7	598.7	604.7	607.8	613.8
17.5°	486.8	489.8	489.8	492.9	492.9	495.9	495.9	495.9	501.9	508.0	517.1
20°	438.4	438.4	438.4	438.4	438.4	435.4	435.4	432.4	435.4	441.5	444.5
22.5°	393.1	396.1	396.1	396.1	393.1	390.1	384.0	381.0	381.0	384.0	384.0
25°	344.7	341.7	341.7	338.7	338.7	341.7	341.7	341.7	344.7	344.7	347.7
27.5°	317.5	314.5	314.5	311.4	311.4	314.5	314.5	314.5	314.5	314.5	314.5
30°	296.3	296.3	293.3	290.3	293.3	293.3	296.3	296.3	299.4	299.4	302.4
32.5°	281.2	278.2	278.2	275.2	278.2	278.2	281.2	281.2	284.2	287.3	287.3
35°	260.0	260.0	260.0	260.0	260.0	260.0	257.0	257.0	257.0	257.0	257.0
37.5°	247.9	247.9	244.9	241.9	241.9	241.9	241.9	241.9	238.9	235.9	232.8
40°	238.9	235.9	235.9	232.8	229.8	229.8	226.8	223.8	223.8	220.7	220.7
42.5°	226.8	223.8	223.8	220.7	217.7	217.7	214.7	211.7	211.7	211.7	208.6
45°	211.7	211.7	208.6	205.6	205.6	205.6	202.6	202.6	202.6	202.6	199.6
47.5°	196.5	196.5	193.5	193.5	193.5	193.5	190.5	190.5	190.5	190.5	190.5
50°	187.5	187.5	187.5	187.5	187.5	187.5	184.4	184.4	184.4	184.4	184.4
52.5°	178.4	178.4	178.4	178.4	178.4	178.4	178.4	178.4	178.4	178.4	178.4
55°	175.4	175.4	175.4	175.4	175.4	175.4	172.4	172.4	172.4	175.4	175.4
57.5°	169.3	169.3	166.3	166.3	166.3	166.3	166.3	166.3	166.3	166.3	166.3
60°	163.3	163.3	163.3	163.3	163.3	163.3	163.3	163.3	163.3	163.3	163.3
62.5°	154.2	154.2	154.2	154.2	154.2	157.2	157.2	157.2	157.2	157.2	154.2
65°	142.1	145.1	145.1	145.1	145.1	145.1	145.1	145.1	145.1	145.1	145.1
67.5°	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1
70°	127.0	127.0	124.0	124.0	124.0	127.0	127.0	127.0	127.0	127.0	127.0
72.5°	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.9	117.9	117.9
75°	102.8	102.8	102.8	102.8	102.8	102.8	102.8	102.8	102.8	102.8	102.8
77.5°	90.7	90.7	87.7	87.7	87.7	90.7	90.7	90.7	90.7	93.7	93.7
80°	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6	78.6	78.6
82.5°	60.5	60.5	60.5	60.5	60.5	60.5	60.5	60.5	60.5	63.5	63.5
85°	45.4	48.4	48.4	48.4	48.4	48.4	48.4	48.4	48.4	51.4	51.4
87.5°	30.2	30.2	30.2	30.2	30.2	30.2	27.2	27.2	27.2	27.2	24.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951

CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	1926.1	1929.1	1932.2	1932.2	1935.2	1938.2	1938.2	1950.3	1962.4	1968.5	1974.5
5°	1647.9	1644.9	1644.9	1641.9	1638.9	1647.9	1657.0	1675.2	1693.3	1696.3	1702.4
7.5°	1291.1	1294.2	1297.2	1297.2	1300.2	1291.1	1279.0	1282.1	1285.1	1300.2	1312.3
10°	976.7	979.7	982.7	982.7	985.7	982.7	976.7	985.7	994.8	1006.9	1022.0
12.5°	759.0	768.0	777.1	783.1	792.2	798.3	801.3	813.4	822.5	837.6	852.7
15°	619.9	625.9	632.0	638.0	644.1	650.1	656.2	668.2	680.3	698.5	716.6
17.5°	523.1	523.1	526.1	526.1	526.1	532.2	538.2	544.3	547.3	565.4	583.6
20°	447.5	444.5	441.5	438.4	435.4	441.5	444.5	447.5	450.5	462.6	471.7
22.5°	384.0	384.0	387.0	387.0	387.0	384.0	378.0	381.0	381.0	387.0	396.1
25°	347.7	347.7	347.7	344.7	344.7	347.7	350.8	350.8	347.7	350.8	353.8
27.5°	314.5	317.5	317.5	320.5	320.5	323.5	323.5	323.5	323.5	326.6	329.6
30°	302.4	302.4	305.4	305.4	305.4	308.4	311.4	311.4	311.4	314.5	320.5
32.5°	290.3	293.3	296.3	299.4	302.4	305.4	305.4	308.4	308.4	311.4	314.5
35°	257.0	254.0	254.0	251.0	247.9	247.9	247.9	247.9	244.9	247.9	247.9
37.5°	229.8	229.8	229.8	226.8	226.8	229.8	229.8	229.8	229.8	232.8	232.8
40°	217.7	217.7	217.7	217.7	217.7	217.7	217.7	220.7	220.7	223.8	226.8
42.5°	208.6	208.6	208.6	208.6	208.6	211.7	211.7	211.7	211.7	214.7	214.7
45°	199.6	199.6	199.6	199.6	199.6	199.6	199.6	202.6	202.6	205.6	208.6
47.5°	190.5	190.5	190.5	190.5	190.5	193.5	196.5	196.5	196.5	199.6	199.6
50°	184.4	184.4	184.4	184.4	184.4	187.5	187.5	190.5	190.5	193.5	196.5
52.5°	178.4	178.4	178.4	178.4	178.4	181.4	181.4	184.4	184.4	187.5	190.5
55°	175.4	175.4	175.4	172.4	172.4	175.4	175.4	178.4	178.4	181.4	181.4
57.5°	166.3	166.3	166.3	166.3	166.3	166.3	166.3	169.3	169.3	172.4	175.4
60°	163.3	163.3	160.3	160.3	157.2	160.3	160.3	163.3	163.3	166.3	166.3
62.5°	154.2	154.2	154.2	151.2	151.2	154.2	154.2	154.2	154.2	157.2	160.3
65°	145.1	145.1	145.1	142.1	142.1	145.1	145.1	145.1	145.1	148.2	151.2
67.5°	136.1	136.1	136.1	133.0	133.0	133.0	133.0	136.1	136.1	139.1	142.1
70°	127.0	127.0	127.0	124.0	124.0	124.0	120.9	124.0	127.0	130.0	130.0
72.5°	117.9	117.9	117.9	114.9	114.9	114.9	111.9	114.9	114.9	117.9	117.9
75°	102.8	102.8	102.8	102.8	102.8	102.8	99.8	99.8	99.8	102.8	102.8
77.5°	93.7	93.7	93.7	90.7	90.7	90.7	87.7	87.7	87.7	90.7	90.7
80°	78.6	78.6	78.6	75.6	75.6	75.6	72.6	72.6	72.6	75.6	75.6
82.5°	63.5	63.5	63.5	60.5	60.5	60.5	57.5	57.5	57.5	60.5	60.5
85°	51.4	51.4	51.4	51.4	51.4	51.4	48.4	48.4	48.4	51.4	54.4
87.5°	24.2	24.2	27.2	27.2	27.2	27.2	24.2	24.2	21.2	21.2	24.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951

CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	1980.6	1986.6	2001.7	2013.8	2028.9	2041.0	2050.1	2062.2	2071.3	2080.3	2086.4
5°	1705.4	1708.4	1723.5	1738.7	1750.7	1765.9	1787.0	1808.2	1829.4	1850.5	1865.6
7.5°	1327.4	1339.5	1357.7	1378.8	1397.0	1415.1	1436.3	1460.5	1481.6	1502.8	1524.0
10°	1034.1	1046.2	1064.4	1082.5	1097.6	1115.8	1140.0	1164.1	1188.3	1212.5	1236.7
12.5°	867.8	882.9	904.1	925.3	943.4	964.6	994.8	1022.0	1052.3	1079.5	1109.7
15°	731.7	749.9	777.1	807.3	834.6	861.8	892.0	922.2	949.5	979.7	1009.9
17.5°	601.7	619.9	644.1	671.3	695.5	719.7	755.9	789.2	825.5	858.7	892.0
20°	483.8	492.9	517.1	541.2	565.4	589.6	616.8	644.1	671.3	698.5	740.8
22.5°	402.2	408.2	420.3	429.4	441.5	450.5	477.8	505.0	529.2	556.4	595.7
25°	353.8	356.8	365.9	371.9	381.0	387.0	405.2	420.3	438.4	453.6	489.8
27.5°	329.6	332.6	335.6	338.7	341.7	344.7	356.8	368.9	378.0	390.1	423.3
30°	323.5	326.6	335.6	341.7	350.8	356.8	362.8	368.9	374.9	381.0	402.2
32.5°	317.5	320.5	320.5	317.5	317.5	314.5	320.5	323.5	329.6	332.6	350.8
35°	251.0	251.0	254.0	257.0	260.0	263.1	272.1	278.2	287.3	293.3	308.4
37.5°	235.9	235.9	238.9	244.9	247.9	251.0	257.0	263.1	269.1	275.2	290.3
40°	226.8	229.8	232.8	235.9	238.9	241.9	247.9	251.0	257.0	260.0	272.1
42.5°	217.7	217.7	220.7	226.8	229.8	232.8	238.9	241.9	247.9	251.0	263.1
45°	211.7	214.7	217.7	220.7	220.7	223.8	229.8	235.9	238.9	244.9	257.0
47.5°	202.6	202.6	208.6	211.7	217.7	220.7	226.8	229.8	235.9	238.9	251.0
50°	196.5	199.6	205.6	208.6	214.7	217.7	226.8	232.8	241.9	247.9	254.0
52.5°	190.5	193.5	199.6	202.6	208.6	211.7	223.8	235.9	244.9	257.0	257.0
55°	184.4	184.4	190.5	199.6	205.6	211.7	217.7	226.8	232.8	238.9	238.9
57.5°	175.4	178.4	184.4	193.5	199.6	205.6	211.7	217.7	220.7	226.8	223.8
60°	169.3	169.3	178.4	187.5	196.5	205.6	205.6	205.6	202.6	202.6	202.6
62.5°	160.3	163.3	175.4	190.5	202.6	214.7	205.6	196.5	187.5	178.4	181.4
65°	154.2	157.2	163.3	172.4	178.4	184.4	178.4	175.4	169.3	163.3	166.3
67.5°	142.1	145.1	148.2	148.2	151.2	151.2	151.2	151.2	151.2	151.2	154.2
70°	133.0	133.0	133.0	136.1	136.1	136.1	136.1	136.1	136.1	136.1	139.1
72.5°	120.9	120.9	120.9	120.9	120.9	120.9	120.9	120.9	120.9	120.9	124.0
75°	105.8	105.8	105.8	105.8	105.8	105.8	105.8	105.8	105.8	105.8	108.9
77.5°	93.7	93.7	93.7	93.7	93.7	93.7	93.7	93.7	90.7	90.7	93.7
80°	78.6	78.6	78.6	78.6	75.6	75.6	75.6	75.6	75.6	75.6	78.6
82.5°	63.5	63.5	63.5	63.5	60.5	60.5	60.5	60.5	57.5	57.5	60.5
85°	57.5	60.5	60.5	63.5	63.5	63.5	60.5	57.5	54.4	51.4	51.4
87.5°	24.2	24.2	24.2	24.2	21.2	21.2	21.2	21.2	21.2	21.2	21.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	2095.5	2101.5	2107.5	2116.6	2128.7	2137.8	2146.9	2165.0	2186.2	2204.3	2222.4
5°	1880.8	1895.9	1911.0	1929.1	1947.3	1962.4	1980.6	2016.8	2053.1	2086.4	2122.7
7.5°	1542.1	1563.3	1581.4	1611.7	1638.9	1669.1	1696.3	1741.7	1784.0	1829.4	1871.7
10°	1260.9	1285.1	1309.3	1348.6	1390.9	1430.2	1469.5	1505.8	1545.1	1581.4	1617.7
12.5°	1140.0	1167.2	1197.4	1221.6	1248.8	1273.0	1297.2	1339.5	1381.8	1424.2	1466.5
15°	1040.2	1070.4	1100.6	1130.9	1158.1	1188.3	1215.5	1251.8	1291.1	1327.4	1363.7
17.5°	925.3	955.5	988.8	1022.0	1055.3	1088.5	1121.8	1173.2	1224.6	1273.0	1324.4
20°	780.1	822.5	861.8	907.1	952.5	997.8	1043.2	1097.6	1152.0	1203.4	1257.9
22.5°	635.0	674.3	713.6	768.0	822.5	873.9	928.3	1000.9	1070.4	1143.0	1212.5
25°	529.2	565.4	601.7	662.2	719.7	780.1	837.6	925.3	1009.9	1097.6	1182.3
27.5°	456.6	489.8	523.1	586.6	650.1	710.6	774.1	870.8	964.6	1061.3	1155.1
30°	423.3	444.5	465.7	526.1	586.6	644.1	704.5	798.3	892.0	985.7	1079.5
32.5°	368.9	387.0	405.2	459.6	514.0	565.4	619.9	716.6	810.4	907.1	1000.9
35°	326.6	341.7	356.8	408.2	456.6	508.0	556.4	653.1	749.9	846.6	943.4
37.5°	302.4	317.5	329.6	374.9	423.3	468.7	514.0	610.8	704.5	801.3	895.0
40°	284.2	293.3	305.4	350.8	393.1	438.4	480.8	568.5	659.2	746.9	834.6
42.5°	272.1	284.2	293.3	332.6	374.9	414.3	453.6	538.2	622.9	704.5	789.2
45°	269.1	281.2	293.3	326.6	359.8	390.1	423.3	505.0	586.6	668.2	749.9
47.5°	263.1	272.1	284.2	311.4	335.6	362.8	387.0	468.7	550.3	628.9	710.6
50°	260.0	263.1	269.1	293.3	317.5	341.7	365.9	447.5	529.2	610.8	692.4
52.5°	257.0	257.0	257.0	278.2	299.4	317.5	338.7	420.3	505.0	586.6	668.2
55°	238.9	235.9	235.9	257.0	275.2	296.3	314.5	396.1	477.8	556.4	638.0
57.5°	220.7	217.7	214.7	232.8	251.0	269.1	287.3	368.9	453.6	535.2	616.8
60°	202.6	199.6	199.6	217.7	232.8	251.0	266.1	350.8	432.4	517.1	598.7
62.5°	181.4	184.4	184.4	199.6	217.7	232.8	247.9	332.6	420.3	505.0	589.6
65°	166.3	169.3	169.3	187.5	205.6	223.8	241.9	323.5	408.2	489.8	571.5
67.5°	154.2	157.2	157.2	178.4	196.5	217.7	235.9	308.4	384.0	456.6	529.2
70°	142.1	142.1	145.1	166.3	187.5	208.6	229.8	293.3	356.8	417.3	480.8
72.5°	127.0	130.0	133.0	154.2	172.4	193.5	211.7	269.1	326.6	384.0	441.5
75°	111.9	114.9	117.9	136.1	154.2	172.4	190.5	244.9	296.3	350.8	402.2
77.5°	99.8	102.8	105.8	120.9	136.1	151.2	166.3	205.6	247.9	287.3	326.6
80°	81.6	81.6	84.7	96.8	108.9	117.9	130.0	157.2	184.4	208.6	235.9
82.5°	60.5	63.5	63.5	72.6	78.6	87.7	93.7	108.9	120.9	136.1	148.2
85°	51.4	48.4	48.4	54.4	57.5	63.5	66.5	75.6	81.6	90.7	96.8
87.5°	21.2	18.1	18.1	21.2	27.2	30.2	33.3	33.3	36.3	36.3	36.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951

CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	2231.5	2237.6	2246.6	2252.7	2267.8	2279.9	2295.0	2307.1	2316.2	2331.3	2325.3
5°	2149.9	2177.1	2204.3	2231.5	2252.7	2273.9	2292.0	2313.2	2337.4	2382.7	2394.8
7.5°	1908.0	1944.3	1977.5	2013.8	2056.1	2098.5	2140.8	2183.1	2222.4	2279.9	2316.2
10°	1669.1	1720.5	1768.9	1820.3	1859.6	1898.9	1935.2	1974.5	2028.9	2086.4	2152.9
12.5°	1517.9	1569.3	1620.7	1672.1	1729.6	1784.0	1841.5	1895.9	1947.3	1992.6	2068.2
15°	1418.1	1475.6	1530.0	1584.4	1654.0	1720.5	1790.1	1856.6	1932.2	1992.6	2044.0
17.5°	1393.9	1463.5	1530.0	1599.6	1672.1	1744.7	1817.3	1889.8	1965.4	2056.1	2122.7
20°	1351.6	1445.3	1539.1	1632.8	1726.6	1817.3	1911.0	2001.7	2101.5	2210.4	2240.6
22.5°	1327.4	1439.3	1554.2	1666.1	1793.1	1923.1	2050.1	2177.1	2282.9	2364.6	2455.3
25°	1324.4	1463.5	1605.6	1744.7	1905.0	2062.2	2222.4	2379.7	2515.8	2597.4	2670.0
27.5°	1321.4	1490.7	1657.0	1823.3	2019.9	2213.4	2409.9	2603.4	2730.4	2848.4	2908.8
30°	1285.1	1487.7	1693.3	1895.9	2116.6	2337.4	2558.1	2778.8	2908.8	2990.5	3020.7
32.5°	1239.7	1478.6	1717.5	1956.4	2207.3	2458.3	2706.2	2957.2	3060.0	3129.6	3105.4
35°	1203.4	1466.5	1726.6	1986.6	2252.7	2521.8	2787.9	3054.0	3202.1	3298.9	3259.6
37.5°	1170.2	1445.3	1720.5	1995.7	2307.1	2618.6	2930.0	3241.4	3383.6	3486.4	3441.0
40°	1130.9	1424.2	1720.5	2013.8	2370.6	2724.4	3081.2	3435.0	3619.4	3707.1	3637.6
42.5°	1097.6	1403.0	1711.4	2016.8	2397.8	2778.8	3159.8	3540.8	3746.4	3870.4	3782.7
45°	1055.3	1360.7	1663.1	1968.5	2388.8	2809.1	3226.3	3646.6	3885.5	3982.3	3861.3
47.5°	1009.9	1312.3	1611.7	1911.0	2358.5	2806.0	3253.5	3701.1	3921.8	4036.7	3924.8
50°	994.8	1297.2	1596.5	1898.9	2382.7	2869.5	3353.3	3837.1	3997.4	4091.1	3943.0
52.5°	991.8	1312.3	1635.8	1956.4	2443.2	2927.0	3413.8	3897.6	4027.6	4127.4	3994.4
55°	982.7	1330.4	1675.2	2019.9	2527.8	3038.9	3546.8	4054.8	4184.9	4257.4	4157.6
57.5°	991.8	1366.7	1738.7	2113.6	2636.7	3159.8	3682.9	4206.0	4363.3	4414.7	4393.5
60°	997.8	1397.0	1793.1	2192.2	2703.2	3214.2	3725.2	4236.3	4399.5	4526.5	4550.7
62.5°	982.7	1375.8	1765.9	2159.0	2621.6	3084.2	3546.8	4009.5	4278.6	4466.1	4574.9
65°	937.4	1300.2	1666.1	2028.9	2455.3	2884.6	3311.0	3737.3	4021.6	4299.8	4387.4
67.5°	837.6	1146.0	1454.4	1762.8	2134.8	2506.7	2875.6	3247.5	3604.3	3873.4	3994.4
70°	725.7	967.6	1212.5	1454.4	1793.1	2131.7	2470.4	2809.1	3123.5	3419.9	3534.8
72.5°	632.0	819.4	1009.9	1197.4	1439.3	1678.2	1920.1	2159.0	2530.9	2827.2	2939.1
75°	538.2	674.3	807.3	943.4	1109.7	1276.0	1439.3	1605.6	1868.7	2134.8	2246.6
77.5°	414.3	505.0	592.7	680.3	795.2	907.1	1022.0	1133.9	1318.4	1517.9	1575.4
80°	287.3	338.7	387.0	438.4	529.2	619.9	710.6	801.3	922.2	1034.1	1121.8
82.5°	178.4	211.7	241.9	272.1	344.7	417.3	486.8	559.4	607.8	613.8	701.5
85°	114.9	136.1	154.2	172.4	214.7	260.0	302.4	344.7	308.4	287.3	341.7
87.5°	45.4	57.5	66.5	75.6	72.6	69.5	66.5	63.5	54.4	48.4	60.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951

CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	2331.3	2340.4	2349.4	2355.5	2364.6	2367.6	2370.6	2370.6	2373.6	2376.7	2382.7
5°	2443.2	2461.3	2479.5	2494.6	2512.7	2527.8	2539.9	2555.1	2567.2	2567.2	2564.1
7.5°	2349.4	2394.8	2440.2	2485.5	2530.9	2564.1	2594.4	2627.6	2657.9	2663.9	2670.0
10°	2225.5	2273.9	2319.2	2367.6	2412.9	2464.3	2512.7	2561.1	2612.5	2621.6	2633.7
12.5°	2110.6	2168.0	2225.5	2279.9	2337.4	2373.6	2409.9	2443.2	2479.5	2503.7	2527.8
15°	2107.5	2155.9	2204.3	2249.7	2298.0	2319.2	2340.4	2358.5	2379.7	2379.7	2382.7
17.5°	2177.1	2207.3	2237.6	2264.8	2295.0	2298.0	2304.1	2307.1	2310.1	2301.1	2292.0
20°	2313.2	2325.3	2337.4	2349.4	2361.5	2340.4	2322.2	2301.1	2279.9	2255.7	2234.5
22.5°	2512.7	2485.5	2458.3	2431.1	2403.9	2367.6	2328.3	2292.0	2252.7	2222.4	2192.2
25°	2700.2	2666.9	2633.7	2600.4	2567.2	2488.5	2409.9	2328.3	2249.7	2216.4	2183.1
27.5°	2951.2	2899.8	2848.4	2797.0	2745.6	2639.7	2533.9	2428.1	2322.2	2264.8	2210.4
30°	3011.6	2954.2	2896.7	2836.3	2778.8	2676.0	2576.2	2473.4	2370.6	2304.1	2240.6
32.5°	3099.3	3032.8	2966.3	2899.8	2833.2	2733.5	2633.7	2530.9	2431.1	2370.6	2307.1
35°	3244.5	3168.9	3093.3	3014.7	2939.1	2836.3	2736.5	2633.7	2530.9	2461.3	2394.8
37.5°	3368.4	3280.8	3193.1	3105.4	3017.7	2927.0	2833.2	2742.5	2648.8	2579.3	2512.7
40°	3507.5	3410.8	3314.0	3220.3	3123.5	3038.9	2954.2	2866.5	2781.8	2727.4	2673.0
42.5°	3628.5	3510.6	3395.7	3280.8	3162.8	3105.4	3051.0	2993.5	2936.1	2908.8	2878.6
45°	3713.2	3604.3	3492.4	3383.6	3274.7	3232.4	3190.0	3147.7	3105.4	3132.6	3159.8
47.5°	3749.4	3661.7	3577.1	3492.4	3404.7	3419.9	3435.0	3447.1	3462.2	3498.5	3537.8
50°	3782.7	3734.3	3682.9	3634.5	3583.1	3640.6	3695.0	3752.5	3809.9	3885.5	3961.1
52.5°	3849.2	3822.0	3797.8	3770.6	3743.4	3843.2	3943.0	4042.7	4142.5	4227.2	4311.9
55°	4048.8	4027.6	4006.5	3982.3	3961.1	4103.2	4242.3	4384.4	4526.5	4614.2	4701.9
57.5°	4323.9	4311.9	4296.7	4284.6	4269.5	4408.6	4544.7	4680.8	4819.8	4904.5	4992.2
60°	4532.6	4535.6	4535.6	4538.6	4538.6	4644.5	4750.3	4859.2	4965.0	5037.6	5113.1
62.5°	4644.5	4638.4	4632.4	4626.3	4620.3	4708.0	4795.7	4883.3	4971.0	5025.5	5079.9
65°	4523.5	4556.8	4590.0	4623.3	4656.6	4668.7	4677.7	4689.8	4698.9	4732.2	4765.4
67.5°	4118.3	4184.9	4248.4	4314.9	4378.4	4333.0	4290.7	4245.3	4200.0	4209.0	4215.1
70°	3667.8	3743.4	3822.0	3897.6	3973.2	3867.4	3761.5	3652.7	3546.8	3510.6	3474.3
72.5°	3093.3	3159.8	3229.4	3295.9	3362.4	3232.4	3105.4	2975.4	2845.3	2781.8	2718.3
75°	2364.6	2443.2	2524.8	2603.4	2682.1	2536.9	2388.8	2243.6	2095.5	2053.1	2013.8
77.5°	1723.5	1817.3	1911.0	2004.7	2098.5	1968.5	1838.4	1705.4	1575.4	1551.2	1527.0
80°	1254.9	1327.4	1397.0	1469.5	1539.1	1463.5	1387.9	1312.3	1236.7	1233.7	1230.7
82.5°	846.6	910.1	970.6	1034.1	1094.6	1064.4	1037.1	1006.9	976.7	1006.9	1040.2
85°	435.4	523.1	613.8	701.5	789.2	780.1	774.1	765.0	755.9	795.2	831.5
87.5°	87.7	163.3	238.9	311.4	387.0	368.9	350.8	329.6	311.4	323.5	332.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951

CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	2385.7	2388.8	2388.8	2388.8	2388.8	2388.8	2382.7	2379.7	2373.6	2367.6	2358.5
5°	2564.1	2561.1	2549.0	2536.9	2521.8	2509.7	2500.6	2488.5	2479.5	2467.4	2449.2
7.5°	2676.0	2682.1	2660.9	2642.7	2621.6	2600.4	2579.3	2558.1	2536.9	2515.8	2473.4
10°	2642.7	2651.8	2639.7	2627.6	2612.5	2600.4	2576.2	2549.0	2524.8	2497.6	2446.2
12.5°	2549.0	2573.2	2567.2	2561.1	2555.1	2549.0	2533.9	2515.8	2500.6	2482.5	2425.0
15°	2382.7	2382.7	2385.7	2388.8	2388.8	2391.8	2394.8	2397.8	2400.8	2403.9	2370.6
17.5°	2282.9	2273.9	2273.9	2273.9	2273.9	2273.9	2285.9	2301.1	2313.2	2325.3	2316.2
20°	2210.4	2189.2	2186.2	2186.2	2183.1	2180.1	2201.3	2225.5	2246.6	2267.8	2279.9
22.5°	2162.0	2131.7	2128.7	2125.7	2122.7	2119.6	2146.9	2174.1	2201.3	2228.5	2270.8
25°	2149.9	2116.6	2119.6	2122.7	2122.7	2125.7	2146.9	2168.0	2189.2	2210.4	2282.9
27.5°	2152.9	2098.5	2101.5	2104.5	2104.5	2107.5	2140.8	2171.0	2204.3	2234.5	2325.3
30°	2174.1	2110.6	2104.5	2098.5	2092.4	2086.4	2131.7	2177.1	2222.4	2267.8	2337.4
32.5°	2246.6	2186.2	2171.0	2155.9	2140.8	2125.7	2180.1	2231.5	2285.9	2337.4	2394.8
35°	2325.3	2258.7	2252.7	2246.6	2237.6	2231.5	2279.9	2331.3	2379.7	2428.1	2479.5
37.5°	2443.2	2376.7	2370.6	2361.5	2355.5	2346.4	2400.8	2452.3	2506.7	2558.1	2603.4
40°	2618.6	2564.1	2561.1	2561.1	2558.1	2555.1	2597.4	2642.7	2685.1	2727.4	2757.7
42.5°	2851.4	2824.2	2833.2	2845.3	2854.4	2863.5	2896.7	2933.0	2966.3	2999.6	2990.5
45°	3187.0	3214.2	3217.3	3220.3	3223.3	3226.3	3235.4	3247.5	3256.6	3265.6	3229.4
47.5°	3574.1	3610.3	3628.5	3646.6	3661.7	3679.9	3667.8	3652.7	3640.6	3625.5	3534.8
50°	4033.7	4109.3	4106.2	4103.2	4097.2	4094.1	4070.0	4045.8	4018.6	3994.4	3861.3
52.5°	4396.5	4481.2	4496.3	4511.4	4526.5	4541.7	4496.3	4450.9	4402.6	4357.2	4190.9
55°	4786.6	4874.3	4877.3	4880.3	4880.3	4883.3	4819.8	4756.3	4689.8	4626.3	4454.0
57.5°	5076.9	5161.5	5152.5	5146.4	5137.3	5128.3	5052.7	4977.1	4901.5	4825.9	4653.5
60°	5185.7	5258.3	5240.1	5222.0	5200.8	5182.7	5125.2	5067.8	5007.3	4949.9	4783.6
62.5°	5134.3	5188.7	5161.5	5137.3	5110.1	5082.9	5010.3	4934.7	4862.2	4786.6	4665.6
65°	4795.7	4828.9	4792.6	4759.4	4726.1	4689.8	4629.3	4568.9	4505.4	4444.9	4363.3
67.5°	4224.2	4230.2	4227.2	4224.2	4221.1	4218.1	4130.4	4042.7	3952.0	3864.3	3858.3
70°	3441.0	3404.7	3410.8	3419.9	3425.9	3431.9	3365.4	3301.9	3235.4	3168.9	3199.1
72.5°	2654.8	2591.3	2606.5	2624.6	2639.7	2654.8	2600.4	2549.0	2494.6	2440.2	2482.5
75°	1971.5	1932.2	1947.3	1965.4	1980.6	1995.7	1974.5	1953.3	1929.1	1908.0	1947.3
77.5°	1502.8	1478.6	1481.6	1481.6	1484.7	1484.7	1487.7	1493.7	1496.8	1499.8	1542.1
80°	1224.6	1221.6	1218.6	1215.5	1209.5	1206.5	1236.7	1266.9	1297.2	1327.4	1348.6
82.5°	1070.4	1100.6	1082.5	1067.4	1049.2	1031.1	1058.3	1085.5	1112.7	1140.0	1130.9
85°	870.8	907.1	873.9	840.6	804.3	771.1	795.2	816.4	840.6	861.8	849.7
87.5°	344.7	353.8	299.4	247.9	193.5	139.1	220.7	299.4	381.0	459.6	471.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951

CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1	2177.1
2.5°	2349.4	2337.4	2328.3	2325.3	2319.2	2316.2	2310.1	2304.1	2295.0	2289.0	2279.9
5°	2428.1	2409.9	2388.8	2358.5	2331.3	2301.1	2270.8	2243.6	2216.4	2186.2	2159.0
7.5°	2431.1	2388.8	2346.4	2307.1	2264.8	2225.5	2183.1	2146.9	2107.5	2068.2	2032.0
10°	2397.8	2346.4	2295.0	2243.6	2195.2	2143.8	2092.4	2050.1	2004.7	1959.4	1917.1
12.5°	2370.6	2313.2	2255.7	2195.2	2137.8	2077.3	2016.8	1974.5	1932.2	1889.8	1847.5
15°	2337.4	2301.1	2267.8	2213.4	2159.0	2104.5	2050.1	1992.6	1938.2	1880.8	1823.3
17.5°	2310.1	2301.1	2292.0	2255.7	2219.4	2180.1	2143.8	2086.4	2028.9	1968.5	1911.0
20°	2295.0	2307.1	2319.2	2301.1	2282.9	2261.8	2243.6	2201.3	2159.0	2113.6	2071.3
22.5°	2313.2	2358.5	2400.8	2403.9	2409.9	2412.9	2416.0	2376.7	2337.4	2295.0	2255.7
25°	2355.5	2428.1	2500.6	2539.9	2579.3	2621.6	2660.9	2636.7	2612.5	2588.3	2564.1
27.5°	2412.9	2503.7	2594.4	2651.8	2706.2	2763.7	2821.1	2818.1	2815.1	2809.1	2806.0
30°	2403.9	2473.4	2543.0	2612.5	2682.1	2751.6	2821.1	2857.4	2890.7	2927.0	2963.3
32.5°	2455.3	2512.7	2573.2	2645.8	2718.3	2793.9	2866.5	2942.1	3014.7	3090.3	3165.9
35°	2533.9	2585.3	2639.7	2718.3	2800.0	2878.6	2960.2	3051.0	3144.7	3238.4	3329.1
37.5°	2651.8	2697.2	2745.6	2812.1	2881.6	2948.1	3017.7	3150.7	3283.8	3419.9	3552.9
40°	2787.9	2818.1	2848.4	2911.9	2975.4	3038.9	3102.4	3268.7	3435.0	3601.3	3767.6
42.5°	2984.4	2975.4	2966.3	3017.7	3072.1	3123.5	3178.0	3329.1	3480.3	3631.5	3782.7
45°	3193.1	3156.8	3120.5	3144.7	3171.9	3196.1	3223.3	3377.5	3531.7	3689.0	3843.2
47.5°	3444.0	3353.3	3262.6	3241.4	3220.3	3196.1	3174.9	3341.2	3507.5	3676.9	3843.2
50°	3728.3	3592.2	3459.2	3404.7	3347.3	3292.9	3235.4	3371.5	3510.6	3649.7	3785.7
52.5°	4024.6	3855.3	3689.0	3604.3	3519.6	3431.9	3347.3	3462.2	3580.1	3698.0	3812.9
55°	4278.6	4106.2	3930.9	3831.1	3731.3	3631.5	3531.7	3646.6	3761.5	3876.4	3991.3
57.5°	4481.2	4308.8	4136.5	4042.7	3946.0	3852.2	3755.5	3864.3	3976.2	4088.1	4197.0
60°	4620.3	4454.0	4287.7	4197.0	4106.2	4015.5	3924.8	4054.8	4184.9	4317.9	4447.9
62.5°	4547.7	4426.8	4305.8	4266.5	4227.2	4184.9	4145.5	4269.5	4390.5	4514.4	4638.4
65°	4281.6	4200.0	4118.3	4157.6	4200.0	4239.3	4281.6	4363.3	4444.9	4529.6	4611.2
67.5°	3849.2	3843.2	3834.1	3921.8	4009.5	4100.2	4187.9	4242.3	4293.7	4348.1	4402.6
70°	3229.4	3262.6	3292.9	3444.0	3595.2	3746.4	3897.6	3918.8	3939.9	3961.1	3982.3
72.5°	2527.8	2570.2	2615.5	2815.1	3011.6	3211.2	3410.8	3398.7	3386.6	3371.5	3359.4
75°	1989.6	2028.9	2071.3	2255.7	2440.2	2624.6	2809.1	2757.7	2709.3	2657.9	2606.5
77.5°	1587.5	1629.8	1675.2	1847.5	2019.9	2195.2	2367.6	2243.6	2119.6	1995.7	1871.7
80°	1366.7	1387.9	1406.0	1524.0	1638.9	1756.8	1874.7	1747.7	1617.7	1487.7	1360.7
82.5°	1121.8	1109.7	1100.6	1170.2	1239.7	1309.3	1378.8	1257.9	1136.9	1013.0	892.0
85°	837.6	825.5	813.4	849.7	886.0	925.3	961.5	822.5	683.4	541.2	402.2
87.5°	486.8	498.9	511.0	550.3	589.6	632.0	671.3	529.2	387.0	241.9	99.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675951
 CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2177.1	2177.1
2.5°	2261.8	2246.6
5°	2137.8	2116.6
7.5°	2001.7	1974.5
10°	1877.7	1841.5
12.5°	1799.1	1753.8
15°	1768.9	1714.5
17.5°	1859.6	1808.2
20°	1998.7	1929.1
22.5°	2168.0	2083.4
25°	2461.3	2358.5
27.5°	2700.2	2594.4
30°	2848.4	2733.5
32.5°	3011.6	2860.5
35°	3181.0	3035.8
37.5°	3386.6	3223.3
40°	3598.3	3428.9
42.5°	3670.8	3562.0
45°	3740.4	3637.6
47.5°	3755.5	3670.8
50°	3770.6	3758.5
52.5°	3812.9	3809.9
55°	3994.4	3997.4
57.5°	4218.1	4236.3
60°	4423.7	4402.6
62.5°	4529.6	4420.7
65°	4457.0	4305.8
67.5°	4239.3	4076.0
70°	3761.5	3540.8
72.5°	3165.9	2972.3
75°	2440.2	2276.9
77.5°	1735.6	1599.6
80°	1221.6	1085.5
82.5°	783.1	674.3
85°	353.8	308.4
87.5°	99.8	96.8
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675951
CATALOG NUMBER: CCW-SA-2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)