

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676014

Luminaire Tested: **CCW-SA-2A-760-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P676014
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2A-760-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @350mA w/
SLR distribution lens
Light Source: (32) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4644.7 lumens
Efficiency: N/A
Efficacy: 128.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 6.6 fc
 Type IV - Short - N/A

REPORT NUMBER: P676014
CATALOG NUMBER: CCW-SA-2A-760-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	955.7	0.0	955.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3689.0	0.0	3689.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	4644.7	0.0	4644.7
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	2.5
10°-20°	243.3	5.2
20°-30°	356.0	7.7
30°-40°	501.6	10.8
40°-50°	689.2	14.8
50°-60°	939.4	20.2
60°-70°	1028.2	22.1
70°-80°	593.8	12.8
80°-90°	178.0	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4644.7	100.0
0°-180°	4644.7	100.0



REPORT NUMBER: P676014


CATALOG NUMBER: CCW-SA-2A-760-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	477.0	10.3			
FM (30°-60°)	1695.0	36.5			
FH (60°-80°)	1365.8	29.4			G1/1800
FVH (80°-90°)	151.2	3.3			G2/225
BL (0°-30°)	237.6	5.1	B1/500		
BM (30°-60°)	435.2	9.4	B1/1000		
BH (60°-80°)	256.1	5.5	B1/500		G1/500
BVH (80°-90°)	26.8	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P676014

CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1530.6	1522.4	1516.2	1510.0	1501.8	1495.6	1487.4	1479.1	1468.8	1460.6	1450.3
5°	1442.0	1417.3	1392.6	1378.2	1361.7	1347.3	1330.8	1312.3	1293.7	1273.1	1254.6
7.5°	1345.2	1314.3	1283.4	1258.7	1231.9	1207.2	1180.4	1157.8	1135.1	1112.4	1089.8
10°	1254.6	1225.7	1196.9	1166.0	1133.0	1102.1	1069.2	1038.3	1007.4	976.5	945.6
12.5°	1194.8	1159.8	1126.9	1091.8	1058.9	1023.8	988.8	960.0	931.1	900.2	871.4
15°	1168.1	1135.1	1104.2	1069.2	1034.1	999.1	964.1	931.1	900.2	867.3	834.3
17.5°	1231.9	1184.5	1137.2	1091.8	1046.5	1001.2	955.9	914.7	873.5	832.3	791.1
20°	1314.3	1254.6	1196.9	1141.3	1083.6	1028.0	970.3	912.6	854.9	797.2	739.6
22.5°	1419.4	1351.4	1285.5	1213.4	1139.2	1067.1	992.9	920.8	848.7	774.6	702.5
25°	1606.8	1526.5	1446.2	1343.2	1238.1	1135.1	1030.0	935.3	842.6	747.8	653.0
27.5°	1767.5	1658.3	1551.2	1427.6	1304.0	1180.4	1056.8	947.6	840.5	731.3	622.1
30°	1862.3	1755.2	1648.0	1497.7	1349.3	1199.0	1048.6	927.0	807.5	686.0	564.5
32.5°	1948.8	1829.3	1709.8	1545.0	1378.2	1213.4	1046.5	912.6	780.8	646.9	513.0
35°	2068.3	1936.5	1806.7	1615.1	1423.5	1231.9	1040.3	902.3	762.2	624.2	484.1
37.5°	2196.0	2033.3	1872.6	1660.4	1448.2	1236.0	1023.8	887.9	751.9	616.0	480.0
40°	2336.1	2138.3	1942.6	1707.8	1475.0	1240.2	1005.3	869.3	733.4	595.4	459.4
42.5°	2426.7	2212.5	1998.3	1744.9	1493.5	1240.2	986.8	852.9	719.0	583.0	449.1
45°	2478.3	2270.2	2064.2	1790.2	1516.2	1242.2	968.2	836.4	704.5	570.6	438.8
47.5°	2500.9	2307.3	2113.6	1825.2	1538.9	1250.5	962.0	828.1	692.2	558.3	422.3
50°	2560.7	2389.7	2218.7	1909.7	1602.7	1293.7	984.7	840.5	698.4	554.2	410.0
52.5°	2595.7	2449.4	2303.1	1985.9	1668.6	1351.4	1034.1	873.5	712.8	552.1	391.4
55°	2723.4	2583.3	2443.2	2105.4	1765.5	1427.6	1087.7	910.5	733.4	554.2	377.0
57.5°	2886.1	2737.8	2591.6	2226.9	1862.3	1497.7	1133.0	943.5	751.9	562.4	370.8
60°	2999.4	2855.2	2713.1	2325.8	1936.5	1549.2	1159.8	962.0	764.3	564.5	366.7
62.5°	3011.8	2826.4	2643.1	2266.1	1889.1	1510.0	1133.0	941.4	749.9	556.2	364.6
65°	2933.5	2717.2	2500.9	2140.4	1779.9	1419.4	1058.9	883.8	708.7	531.5	356.4
67.5°	2777.0	2523.6	2270.2	1940.6	1611.0	1281.4	951.7	801.4	653.0	502.7	352.3
70°	2412.3	2189.8	1969.4	1683.1	1398.8	1112.4	826.1	702.5	580.9	457.3	333.7
72.5°	2025.0	1817.0	1611.0	1378.2	1147.5	914.7	681.9	589.2	496.5	401.7	309.0
75°	1551.2	1394.7	1240.2	1067.1	894.1	719.0	545.9	477.9	410.0	342.0	274.0
77.5°	1089.8	1005.3	922.9	793.1	663.3	533.6	403.8	358.5	313.1	267.8	222.5
80°	739.6	692.2	646.9	554.2	461.5	366.7	274.0	245.1	214.2	185.4	154.5
82.5°	459.4	457.3	453.2	389.4	325.5	261.6	197.8	173.0	150.4	125.7	100.9
85°	210.1	245.1	278.1	243.1	208.1	173.0	138.0	121.5	105.1	86.5	70.0
87.5°	65.9	80.3	92.7	88.6	82.4	78.3	72.1	61.8	51.5	41.2	30.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014

CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1442.0	1435.9	1427.6	1419.4	1409.1	1400.8	1390.5	1380.2	1378.2	1374.1	1372.0
5°	1242.2	1229.9	1215.4	1203.1	1190.7	1176.3	1163.9	1149.5	1139.2	1126.9	1116.6
7.5°	1067.1	1046.5	1023.8	1001.2	980.6	960.0	937.3	916.7	906.4	896.1	885.8
10°	927.0	906.4	887.9	867.3	852.9	840.5	826.1	811.7	799.3	786.9	774.6
12.5°	857.0	842.6	828.1	813.7	797.2	782.8	766.3	749.9	735.4	723.1	708.7
15°	813.7	793.1	770.5	749.9	727.2	706.6	683.9	661.3	644.8	630.4	613.9
17.5°	762.2	731.3	702.5	671.6	646.9	622.1	595.4	570.6	552.1	531.5	513.0
20°	704.5	669.5	632.4	597.4	568.6	541.8	513.0	484.1	463.5	440.9	420.3
22.5°	655.1	609.8	562.4	515.0	484.1	453.2	420.3	389.4	370.8	350.2	331.7
25°	601.5	552.1	500.6	449.1	418.2	385.2	354.3	321.4	306.9	294.6	280.2
27.5°	572.7	523.3	471.8	422.3	393.5	362.6	333.7	302.8	292.5	280.2	269.9
30°	515.0	467.6	418.2	368.8	348.1	329.6	309.0	288.4	284.3	282.2	278.1
32.5°	463.5	414.1	364.6	315.2	296.6	278.1	259.6	241.0	239.0	234.8	232.8
35°	436.7	389.4	339.9	292.5	276.0	257.5	241.0	222.5	218.4	212.2	208.1
37.5°	430.6	381.1	329.6	280.2	263.7	247.2	228.7	212.2	208.1	203.9	199.8
40°	414.1	366.7	321.4	274.0	257.5	241.0	222.5	206.0	201.9	197.8	193.6
42.5°	401.7	356.4	309.0	261.6	247.2	232.8	216.3	201.9	197.8	193.6	187.5
45°	391.4	344.0	294.6	247.2	236.9	226.6	214.2	203.9	199.8	193.6	189.5
47.5°	374.9	329.6	282.2	234.8	224.5	216.3	206.0	195.7	191.6	187.5	183.3
50°	362.6	315.2	267.8	220.4	212.2	203.9	195.7	187.5	187.5	189.5	189.5
52.5°	346.1	300.8	255.4	210.1	201.9	193.6	185.4	177.2	179.2	181.3	183.3
55°	331.7	288.4	243.1	197.8	189.5	181.3	171.0	162.7	164.8	166.9	168.9
57.5°	325.5	280.2	234.8	189.5	181.3	171.0	162.7	152.4	152.4	152.4	152.4
60°	321.4	274.0	228.7	181.3	171.0	162.7	152.4	142.1	140.1	140.1	138.0
62.5°	319.3	271.9	226.6	179.2	166.9	156.6	144.2	131.8	129.8	127.7	125.7
65°	311.1	267.8	222.5	177.2	162.7	150.4	136.0	121.5	119.5	119.5	117.4
67.5°	309.0	263.7	220.4	175.1	160.7	144.2	129.8	113.3	111.2	109.2	107.1
70°	292.5	253.4	212.2	171.0	154.5	140.1	123.6	107.1	105.1	100.9	98.9
72.5°	271.9	236.9	199.8	162.7	146.3	129.8	113.3	96.8	94.8	92.7	88.6
75°	241.0	208.1	175.1	142.1	127.7	115.4	100.9	86.5	84.5	82.4	78.3
77.5°	197.8	171.0	146.3	119.5	109.2	98.9	88.6	78.3	76.2	74.2	70.0
80°	140.1	123.6	109.2	92.7	86.5	78.3	72.1	63.9	63.9	61.8	61.8
82.5°	92.7	84.5	76.2	68.0	63.9	59.7	55.6	51.5	51.5	49.4	49.4
85°	65.9	61.8	55.6	51.5	49.4	45.3	43.3	39.1	39.1	39.1	39.1
87.5°	30.9	30.9	28.8	28.8	26.8	26.8	24.7	22.7	22.7	22.7	22.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1367.9	1361.7	1355.5	1347.3	1341.1	1332.9	1322.6	1314.3	1304.0	1304.0	1302.0
5°	1104.2	1098.0	1091.8	1083.6	1077.4	1069.2	1063.0	1054.7	1046.5	1046.5	1044.4
7.5°	875.5	863.2	850.8	836.4	824.0	815.8	807.5	797.2	789.0	782.8	776.6
10°	762.2	749.9	735.4	723.1	708.7	698.4	688.1	675.7	665.4	657.2	648.9
12.5°	694.2	679.8	665.4	651.0	636.6	622.1	609.8	595.4	580.9	570.6	560.3
15°	597.4	583.0	568.6	554.2	539.7	523.3	506.8	488.2	471.8	463.5	457.3
17.5°	492.4	477.9	461.5	447.0	430.6	418.2	405.8	393.5	381.1	372.9	366.7
20°	397.6	381.1	364.6	348.1	331.7	323.4	315.2	306.9	298.7	292.5	288.4
22.5°	311.1	300.8	292.5	282.2	271.9	265.7	261.6	255.4	249.3	249.3	249.3
25°	265.7	259.6	255.4	249.3	243.1	241.0	239.0	234.8	232.8	230.7	230.7
27.5°	257.5	251.3	245.1	239.0	232.8	230.7	228.7	224.5	222.5	222.5	222.5
30°	274.0	271.9	269.9	267.8	265.7	261.6	255.4	251.3	245.1	241.0	236.9
32.5°	228.7	226.6	226.6	224.5	222.5	226.6	228.7	232.8	234.8	236.9	239.0
35°	201.9	197.8	193.6	189.5	185.4	183.3	181.3	179.2	177.2	177.2	175.1
37.5°	195.7	191.6	187.5	183.3	179.2	177.2	175.1	173.0	171.0	171.0	168.9
40°	189.5	185.4	183.3	179.2	175.1	173.0	171.0	166.9	164.8	162.7	162.7
42.5°	183.3	181.3	177.2	175.1	171.0	168.9	166.9	162.7	160.7	158.6	156.6
45°	183.3	179.2	175.1	171.0	166.9	164.8	160.7	158.6	154.5	154.5	152.4
47.5°	179.2	175.1	171.0	166.9	162.7	160.7	156.6	154.5	150.4	148.3	146.3
50°	189.5	183.3	175.1	168.9	160.7	158.6	154.5	152.4	148.3	146.3	144.2
52.5°	185.4	179.2	171.0	164.8	156.6	152.4	150.4	146.3	142.1	140.1	138.0
55°	171.0	164.8	160.7	154.5	148.3	144.2	140.1	136.0	131.8	129.8	129.8
57.5°	152.4	150.4	148.3	146.3	144.2	140.1	136.0	129.8	125.7	123.6	121.5
60°	136.0	138.0	140.1	142.1	144.2	138.0	131.8	125.7	119.5	117.4	115.4
62.5°	123.6	127.7	131.8	133.9	138.0	131.8	125.7	119.5	113.3	111.2	109.2
65°	115.4	117.4	117.4	119.5	119.5	115.4	113.3	109.2	105.1	103.0	103.0
67.5°	105.1	105.1	105.1	103.0	103.0	100.9	100.9	98.9	96.8	94.8	94.8
70°	94.8	94.8	94.8	92.7	92.7	90.6	90.6	88.6	86.5	86.5	84.5
72.5°	86.5	86.5	84.5	84.5	82.4	82.4	82.4	80.3	80.3	78.3	78.3
75°	76.2	76.2	74.2	74.2	72.1	72.1	72.1	70.0	70.0	70.0	68.0
77.5°	68.0	68.0	65.9	65.9	63.9	63.9	63.9	61.8	61.8	59.7	59.7
80°	59.7	59.7	57.7	57.7	55.6	55.6	53.6	53.6	51.5	51.5	49.4
82.5°	47.4	47.4	47.4	47.4	47.4	45.3	45.3	43.3	41.2	41.2	39.1
85°	39.1	39.1	39.1	37.1	37.1	37.1	35.0	35.0	33.0	30.9	30.9
87.5°	22.7	22.7	22.7	20.6	20.6	20.6	20.6	20.6	20.6	20.6	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014

CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1302.0	1299.9	1291.7	1283.4	1291.7	1299.9	1299.9	1299.9	1297.8	1297.8	1297.8
5°	1044.4	1042.4	1038.3	1034.1	1034.1	1032.1	1036.2	1040.3	1044.4	1048.6	1052.7
7.5°	768.4	762.2	756.0	749.9	754.0	756.0	762.2	766.3	772.5	776.6	786.9
10°	640.7	632.4	626.3	620.1	616.0	611.8	607.7	605.7	601.5	597.4	601.5
12.5°	548.0	537.7	527.4	515.0	513.0	510.9	506.8	502.7	498.5	494.4	492.4
15°	449.1	440.9	436.7	430.6	422.3	414.1	410.0	407.9	403.8	399.7	397.6
17.5°	358.5	350.2	344.0	337.8	335.8	331.7	331.7	331.7	331.7	331.7	331.7
20°	282.2	276.0	276.0	274.0	274.0	271.9	274.0	276.0	276.0	278.1	280.2
22.5°	247.2	247.2	245.1	243.1	245.1	245.1	247.2	249.3	251.3	253.4	255.4
25°	228.7	226.6	228.7	230.7	230.7	230.7	232.8	232.8	234.8	234.8	234.8
27.5°	220.4	220.4	222.5	222.5	224.5	224.5	224.5	222.5	222.5	220.4	220.4
30°	232.8	228.7	228.7	228.7	226.6	224.5	222.5	222.5	220.4	218.4	216.3
32.5°	241.0	243.1	241.0	236.9	234.8	230.7	228.7	224.5	222.5	218.4	214.2
35°	175.1	173.0	177.2	179.2	181.3	183.3	185.4	187.5	187.5	189.5	189.5
37.5°	168.9	166.9	166.9	164.8	164.8	164.8	164.8	164.8	162.7	162.7	164.8
40°	160.7	158.6	158.6	156.6	156.6	154.5	154.5	154.5	154.5	154.5	154.5
42.5°	154.5	152.4	152.4	152.4	152.4	150.4	150.4	148.3	148.3	146.3	146.3
45°	152.4	150.4	148.3	146.3	146.3	144.2	144.2	144.2	142.1	142.1	142.1
47.5°	144.2	142.1	142.1	140.1	140.1	138.0	138.0	138.0	136.0	136.0	136.0
50°	140.1	138.0	138.0	136.0	136.0	133.9	133.9	133.9	131.8	131.8	131.8
52.5°	133.9	131.8	131.8	131.8	129.8	127.7	127.7	127.7	125.7	125.7	125.7
55°	127.7	125.7	125.7	125.7	123.6	121.5	121.5	121.5	119.5	119.5	119.5
57.5°	119.5	117.4	117.4	115.4	115.4	115.4	115.4	115.4	113.3	113.3	113.3
60°	113.3	111.2	111.2	109.2	109.2	107.1	107.1	107.1	107.1	107.1	107.1
62.5°	107.1	105.1	103.0	100.9	103.0	103.0	103.0	103.0	100.9	100.9	100.9
65°	100.9	98.9	96.8	94.8	94.8	94.8	94.8	94.8	94.8	94.8	94.8
67.5°	92.7	90.6	88.6	86.5	88.6	88.6	88.6	88.6	88.6	88.6	88.6
70°	84.5	82.4	82.4	80.3	80.3	78.3	78.3	80.3	80.3	80.3	80.3
72.5°	76.2	74.2	74.2	72.1	72.1	72.1	72.1	72.1	72.1	72.1	72.1
75°	68.0	65.9	65.9	63.9	63.9	63.9	63.9	63.9	63.9	63.9	63.9
77.5°	57.7	55.6	55.6	55.6	55.6	55.6	55.6	57.7	57.7	57.7	57.7
80°	49.4	47.4	47.4	47.4	47.4	47.4	47.4	47.4	47.4	47.4	47.4
82.5°	39.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1
85°	28.8	26.8	26.8	26.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8
87.5°	18.5	16.5	16.5	16.5	18.5	18.5	18.5	18.5	16.5	16.5	16.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1297.8	1297.8	1297.8	1295.8	1293.7	1291.7	1289.6	1295.8	1299.9	1306.1	1310.2
5°	1054.7	1058.9	1060.9	1067.1	1073.3	1079.5	1085.7	1089.8	1093.9	1096.0	1100.1
7.5°	795.2	805.5	813.7	822.0	830.2	836.4	844.6	850.8	857.0	863.2	869.3
10°	603.6	607.7	609.8	618.0	624.2	632.4	638.6	644.8	651.0	655.1	661.3
12.5°	490.3	486.2	484.1	484.1	484.1	484.1	484.1	488.2	492.4	496.5	500.6
15°	395.5	393.5	391.4	389.4	387.3	383.2	381.1	385.2	389.4	393.5	397.6
17.5°	331.7	331.7	331.7	329.6	327.5	325.5	323.4	325.5	327.5	327.5	329.6
20°	284.3	286.3	288.4	290.5	290.5	292.5	292.5	294.6	296.6	296.6	298.7
22.5°	255.4	257.5	257.5	257.5	259.6	259.6	259.6	261.6	263.7	265.7	267.8
25°	232.8	232.8	230.7	230.7	232.8	232.8	232.8	232.8	234.8	234.8	234.8
27.5°	220.4	218.4	218.4	218.4	218.4	216.3	216.3	216.3	216.3	216.3	216.3
30°	214.2	212.2	210.1	208.1	208.1	206.0	203.9	203.9	203.9	203.9	203.9
32.5°	212.2	208.1	203.9	201.9	201.9	199.8	197.8	195.7	195.7	193.6	191.6
35°	189.5	187.5	187.5	185.4	183.3	181.3	179.2	179.2	179.2	177.2	177.2
37.5°	164.8	166.9	166.9	166.9	168.9	168.9	168.9	168.9	171.0	171.0	171.0
40°	154.5	154.5	154.5	156.6	158.6	158.6	160.7	160.7	162.7	162.7	162.7
42.5°	146.3	144.2	144.2	146.3	146.3	148.3	148.3	150.4	152.4	152.4	154.5
45°	142.1	140.1	140.1	140.1	140.1	138.0	138.0	140.1	142.1	144.2	146.3
47.5°	133.9	133.9	131.8	131.8	131.8	131.8	131.8	131.8	133.9	133.9	133.9
50°	129.8	129.8	127.7	127.7	127.7	127.7	127.7	127.7	127.7	127.7	127.7
52.5°	125.7	123.6	123.6	123.6	123.6	121.5	121.5	121.5	121.5	121.5	121.5
55°	119.5	117.4	117.4	117.4	117.4	117.4	117.4	117.4	119.5	119.5	119.5
57.5°	113.3	111.2	111.2	111.2	113.3	113.3	113.3	113.3	115.4	115.4	115.4
60°	107.1	107.1	107.1	107.1	107.1	107.1	107.1	109.2	109.2	111.2	111.2
62.5°	100.9	100.9	100.9	100.9	103.0	103.0	103.0	103.0	105.1	105.1	105.1
65°	94.8	94.8	94.8	94.8	96.8	96.8	96.8	96.8	96.8	96.8	96.8
67.5°	88.6	88.6	88.6	88.6	88.6	88.6	88.6	90.6	90.6	92.7	92.7
70°	80.3	78.3	78.3	80.3	80.3	82.4	82.4	84.5	84.5	86.5	86.5
72.5°	72.1	72.1	72.1	72.1	72.1	72.1	72.1	74.2	76.2	76.2	78.3
75°	63.9	63.9	63.9	63.9	65.9	65.9	65.9	68.0	68.0	70.0	70.0
77.5°	57.7	55.6	55.6	55.6	57.7	57.7	57.7	59.7	59.7	61.8	61.8
80°	47.4	47.4	47.4	47.4	49.4	49.4	49.4	49.4	51.5	51.5	51.5
82.5°	39.1	39.1	39.1	39.1	39.1	39.1	39.1	39.1	41.2	41.2	41.2
85°	28.8	28.8	28.8	28.8	30.9	30.9	30.9	30.9	30.9	30.9	30.9
87.5°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	20.6	20.6	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1310.2	1310.2	1310.2	1310.2	1314.3	1316.4	1320.5	1322.6	1320.5	1318.4	1314.3
5°	1102.1	1104.2	1104.2	1106.3	1106.3	1106.3	1106.3	1106.3	1110.4	1114.5	1118.6
7.5°	871.4	873.5	875.5	877.6	877.6	877.6	875.5	875.5	877.6	877.6	879.6
10°	667.5	675.7	681.9	688.1	683.9	677.8	673.6	667.5	667.5	667.5	665.4
12.5°	504.7	506.8	510.9	513.0	510.9	510.9	508.8	506.8	508.8	513.0	515.0
15°	399.7	399.7	401.7	401.7	403.8	405.8	405.8	407.9	412.0	414.1	418.2
17.5°	331.7	333.7	333.7	335.8	335.8	337.8	337.8	337.8	342.0	346.1	352.3
20°	298.7	298.7	298.7	298.7	298.7	296.6	296.6	294.6	296.6	300.8	302.8
22.5°	267.8	269.9	269.9	269.9	267.8	265.7	261.6	259.6	259.6	261.6	261.6
25°	234.8	232.8	232.8	230.7	230.7	232.8	232.8	232.8	234.8	234.8	236.9
27.5°	216.3	214.2	214.2	212.2	212.2	214.2	214.2	214.2	214.2	214.2	214.2
30°	201.9	201.9	199.8	197.8	199.8	199.8	201.9	201.9	203.9	203.9	206.0
32.5°	191.6	189.5	189.5	187.5	189.5	189.5	191.6	191.6	193.6	195.7	195.7
35°	177.2	177.2	177.2	177.2	177.2	177.2	175.1	175.1	175.1	175.1	175.1
37.5°	168.9	168.9	166.9	164.8	164.8	164.8	164.8	164.8	162.7	160.7	158.6
40°	162.7	160.7	160.7	158.6	156.6	156.6	154.5	152.4	152.4	150.4	150.4
42.5°	154.5	152.4	152.4	150.4	148.3	148.3	146.3	144.2	144.2	144.2	142.1
45°	144.2	144.2	142.1	140.1	140.1	140.1	138.0	138.0	138.0	138.0	136.0
47.5°	133.9	133.9	131.8	131.8	131.8	131.8	129.8	129.8	129.8	129.8	129.8
50°	127.7	127.7	127.7	127.7	127.7	127.7	125.7	125.7	125.7	125.7	125.7
52.5°	121.5	121.5	121.5	121.5	121.5	121.5	121.5	121.5	121.5	121.5	121.5
55°	119.5	119.5	119.5	119.5	119.5	119.5	117.4	117.4	117.4	119.5	119.5
57.5°	115.4	115.4	113.3	113.3	113.3	113.3	113.3	113.3	113.3	113.3	113.3
60°	111.2	111.2	111.2	111.2	111.2	111.2	111.2	111.2	111.2	111.2	111.2
62.5°	105.1	105.1	105.1	105.1	105.1	107.1	107.1	107.1	107.1	107.1	105.1
65°	96.8	98.9	98.9	98.9	98.9	98.9	98.9	98.9	98.9	98.9	98.9
67.5°	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7
70°	86.5	86.5	84.5	84.5	84.5	86.5	86.5	86.5	86.5	86.5	86.5
72.5°	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3	80.3	80.3
75°	70.0	70.0	70.0	70.0	70.0	70.0	70.0	70.0	70.0	70.0	70.0
77.5°	61.8	61.8	59.7	59.7	59.7	61.8	61.8	61.8	61.8	63.9	63.9
80°	51.5	51.5	51.5	51.5	51.5	51.5	51.5	51.5	51.5	53.6	53.6
82.5°	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	43.3	43.3
85°	30.9	33.0	33.0	33.0	33.0	33.0	33.0	33.0	33.0	35.0	35.0
87.5°	20.6	20.6	20.6	20.6	20.6	20.6	18.5	18.5	18.5	18.5	16.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014

CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1312.3	1314.3	1316.4	1316.4	1318.4	1320.5	1320.5	1328.7	1337.0	1341.1	1345.2
5°	1122.7	1120.7	1120.7	1118.6	1116.6	1122.7	1128.9	1141.3	1153.6	1155.7	1159.8
7.5°	879.6	881.7	883.8	883.8	885.8	879.6	871.4	873.5	875.5	885.8	894.1
10°	665.4	667.5	669.5	669.5	671.6	669.5	665.4	671.6	677.8	686.0	696.3
12.5°	517.1	523.3	529.4	533.6	539.7	543.9	545.9	554.2	560.3	570.6	580.9
15°	422.3	426.4	430.6	434.7	438.8	442.9	447.0	455.3	463.5	475.9	488.2
17.5°	356.4	356.4	358.5	358.5	358.5	362.6	366.7	370.8	372.9	385.2	397.6
20°	304.9	302.8	300.8	298.7	296.6	300.8	302.8	304.9	306.9	315.2	321.4
22.5°	261.6	261.6	263.7	263.7	263.7	261.6	257.5	259.6	259.6	263.7	269.9
25°	236.9	236.9	236.9	234.8	234.8	236.9	239.0	239.0	236.9	239.0	241.0
27.5°	214.2	216.3	216.3	218.4	218.4	220.4	220.4	220.4	220.4	222.5	224.5
30°	206.0	206.0	208.1	208.1	208.1	210.1	212.2	212.2	212.2	214.2	218.4
32.5°	197.8	199.8	201.9	203.9	206.0	208.1	208.1	210.1	210.1	212.2	214.2
35°	175.1	173.0	173.0	171.0	168.9	168.9	168.9	168.9	166.9	168.9	168.9
37.5°	156.6	156.6	156.6	154.5	154.5	156.6	156.6	156.6	156.6	158.6	158.6
40°	148.3	148.3	148.3	148.3	148.3	148.3	148.3	150.4	150.4	152.4	154.5
42.5°	142.1	142.1	142.1	142.1	142.1	144.2	144.2	144.2	144.2	146.3	146.3
45°	136.0	136.0	136.0	136.0	136.0	136.0	136.0	138.0	138.0	140.1	142.1
47.5°	129.8	129.8	129.8	129.8	129.8	131.8	133.9	133.9	133.9	136.0	136.0
50°	125.7	125.7	125.7	125.7	125.7	127.7	127.7	129.8	129.8	131.8	133.9
52.5°	121.5	121.5	121.5	121.5	121.5	123.6	123.6	125.7	125.7	127.7	129.8
55°	119.5	119.5	119.5	117.4	117.4	119.5	119.5	121.5	121.5	123.6	123.6
57.5°	113.3	113.3	113.3	113.3	113.3	113.3	113.3	115.4	115.4	117.4	119.5
60°	111.2	111.2	109.2	109.2	107.1	109.2	109.2	111.2	111.2	113.3	113.3
62.5°	105.1	105.1	105.1	103.0	103.0	105.1	105.1	105.1	105.1	107.1	109.2
65°	98.9	98.9	98.9	96.8	96.8	98.9	98.9	98.9	98.9	100.9	103.0
67.5°	92.7	92.7	92.7	90.6	90.6	90.6	90.6	92.7	92.7	94.8	96.8
70°	86.5	86.5	86.5	84.5	84.5	84.5	82.4	84.5	86.5	88.6	88.6
72.5°	80.3	80.3	80.3	78.3	78.3	78.3	76.2	78.3	78.3	80.3	80.3
75°	70.0	70.0	70.0	70.0	70.0	70.0	68.0	68.0	68.0	70.0	70.0
77.5°	63.9	63.9	63.9	61.8	61.8	61.8	59.7	59.7	59.7	61.8	61.8
80°	53.6	53.6	53.6	51.5	51.5	51.5	49.4	49.4	49.4	51.5	51.5
82.5°	43.3	43.3	43.3	41.2	41.2	41.2	39.1	39.1	39.1	41.2	41.2
85°	35.0	35.0	35.0	35.0	35.0	35.0	33.0	33.0	33.0	35.0	37.1
87.5°	16.5	16.5	18.5	18.5	18.5	18.5	16.5	16.5	14.4	14.4	16.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014

CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1349.3	1353.5	1363.8	1372.0	1382.3	1390.5	1396.7	1405.0	1411.1	1417.3	1421.4
5°	1161.9	1163.9	1174.2	1184.5	1192.8	1203.1	1217.5	1231.9	1246.3	1260.8	1271.1
7.5°	904.4	912.6	925.0	939.4	951.7	964.1	978.5	995.0	1009.4	1023.8	1038.3
10°	704.5	712.8	725.1	737.5	747.8	760.2	776.6	793.1	809.6	826.1	842.6
12.5°	591.2	601.5	616.0	630.4	642.7	657.2	677.8	696.3	716.9	735.4	756.0
15°	498.5	510.9	529.4	550.0	568.6	587.1	607.7	628.3	646.9	667.5	688.1
17.5°	410.0	422.3	438.8	457.3	473.8	490.3	515.0	537.7	562.4	585.1	607.7
20°	329.6	335.8	352.3	368.8	385.2	401.7	420.3	438.8	457.3	475.9	504.7
22.5°	274.0	278.1	286.3	292.5	300.8	306.9	325.5	344.0	360.5	379.1	405.8
25°	241.0	243.1	249.3	253.4	259.6	263.7	276.0	286.3	298.7	309.0	333.7
27.5°	224.5	226.6	228.7	230.7	232.8	234.8	243.1	251.3	257.5	265.7	288.4
30°	220.4	222.5	228.7	232.8	239.0	243.1	247.2	251.3	255.4	259.6	274.0
32.5°	216.3	218.4	218.4	216.3	216.3	214.2	218.4	220.4	224.5	226.6	239.0
35°	171.0	171.0	173.0	175.1	177.2	179.2	185.4	189.5	195.7	199.8	210.1
37.5°	160.7	160.7	162.7	166.9	168.9	171.0	175.1	179.2	183.3	187.5	197.8
40°	154.5	156.6	158.6	160.7	162.7	164.8	168.9	171.0	175.1	177.2	185.4
42.5°	148.3	148.3	150.4	154.5	156.6	158.6	162.7	164.8	168.9	171.0	179.2
45°	144.2	146.3	148.3	150.4	150.4	152.4	156.6	160.7	162.7	166.9	175.1
47.5°	138.0	138.0	142.1	144.2	148.3	150.4	154.5	156.6	160.7	162.7	171.0
50°	133.9	136.0	140.1	142.1	146.3	148.3	154.5	158.6	164.8	168.9	173.0
52.5°	129.8	131.8	136.0	138.0	142.1	144.2	152.4	160.7	166.9	175.1	175.1
55°	125.7	125.7	129.8	136.0	140.1	144.2	148.3	154.5	158.6	162.7	162.7
57.5°	119.5	121.5	125.7	131.8	136.0	140.1	144.2	148.3	150.4	154.5	152.4
60°	115.4	115.4	121.5	127.7	133.9	140.1	140.1	140.1	138.0	138.0	138.0
62.5°	109.2	111.2	119.5	129.8	138.0	146.3	140.1	133.9	127.7	121.5	123.6
65°	105.1	107.1	111.2	117.4	121.5	125.7	121.5	119.5	115.4	111.2	113.3
67.5°	96.8	98.9	100.9	100.9	103.0	103.0	103.0	103.0	103.0	103.0	105.1
70°	90.6	90.6	90.6	92.7	92.7	92.7	92.7	92.7	92.7	92.7	94.8
72.5°	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4	84.5
75°	72.1	72.1	72.1	72.1	72.1	72.1	72.1	72.1	72.1	72.1	74.2
77.5°	63.9	63.9	63.9	63.9	63.9	63.9	63.9	63.9	61.8	61.8	63.9
80°	53.6	53.6	53.6	53.6	51.5	51.5	51.5	51.5	51.5	51.5	53.6
82.5°	43.3	43.3	43.3	43.3	41.2	41.2	41.2	41.2	39.1	39.1	41.2
85°	39.1	41.2	41.2	43.3	43.3	43.3	41.2	39.1	37.1	35.0	35.0
87.5°	16.5	16.5	16.5	16.5	14.4	14.4	14.4	14.4	14.4	14.4	14.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014

CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1427.6	1431.7	1435.9	1442.0	1450.3	1456.5	1462.6	1475.0	1489.4	1501.8	1514.1
5°	1281.4	1291.7	1302.0	1314.3	1326.7	1337.0	1349.3	1374.1	1398.8	1421.4	1446.2
7.5°	1050.6	1065.1	1077.4	1098.0	1116.6	1137.2	1155.7	1186.6	1215.4	1246.3	1275.2
10°	859.0	875.5	892.0	918.8	947.6	974.4	1001.2	1025.9	1052.7	1077.4	1102.1
12.5°	776.6	795.2	815.8	832.3	850.8	867.3	883.8	912.6	941.4	970.3	999.1
15°	708.7	729.3	749.9	770.5	789.0	809.6	828.1	852.9	879.6	904.4	929.1
17.5°	630.4	651.0	673.6	696.3	719.0	741.6	764.3	799.3	834.3	867.3	902.3
20°	531.5	560.3	587.1	618.0	648.9	679.8	710.7	747.8	784.9	819.9	857.0
22.5°	432.6	459.4	486.2	523.3	560.3	595.4	632.4	681.9	729.3	778.7	826.1
25°	360.5	385.2	410.0	451.2	490.3	531.5	570.6	630.4	688.1	747.8	805.5
27.5°	311.1	333.7	356.4	399.7	442.9	484.1	527.4	593.3	657.2	723.1	786.9
30°	288.4	302.8	317.2	358.5	399.7	438.8	480.0	543.9	607.7	671.6	735.4
32.5°	251.3	263.7	276.0	313.1	350.2	385.2	422.3	488.2	552.1	618.0	681.9
35°	222.5	232.8	243.1	278.1	311.1	346.1	379.1	445.0	510.9	576.8	642.7
37.5°	206.0	216.3	224.5	255.4	288.4	319.3	350.2	416.1	480.0	545.9	609.8
40°	193.6	199.8	208.1	239.0	267.8	298.7	327.5	387.3	449.1	508.8	568.6
42.5°	185.4	193.6	199.8	226.6	255.4	282.2	309.0	366.7	424.4	480.0	537.7
45°	183.3	191.6	199.8	222.5	245.1	265.7	288.4	344.0	399.7	455.3	510.9
47.5°	179.2	185.4	193.6	212.2	228.7	247.2	263.7	319.3	374.9	428.5	484.1
50°	177.2	179.2	183.3	199.8	216.3	232.8	249.3	304.9	360.5	416.1	471.8
52.5°	175.1	175.1	175.1	189.5	203.9	216.3	230.7	286.3	344.0	399.7	455.3
55°	162.7	160.7	160.7	175.1	187.5	201.9	214.2	269.9	325.5	379.1	434.7
57.5°	150.4	148.3	146.3	158.6	171.0	183.3	195.7	251.3	309.0	364.6	420.3
60°	138.0	136.0	136.0	148.3	158.6	171.0	181.3	239.0	294.6	352.3	407.9
62.5°	123.6	125.7	125.7	136.0	148.3	158.6	168.9	226.6	286.3	344.0	401.7
65°	113.3	115.4	115.4	127.7	140.1	152.4	164.8	220.4	278.1	333.7	389.4
67.5°	105.1	107.1	107.1	121.5	133.9	148.3	160.7	210.1	261.6	311.1	360.5
70°	96.8	96.8	98.9	113.3	127.7	142.1	156.6	199.8	243.1	284.3	327.5
72.5°	86.5	88.6	90.6	105.1	117.4	131.8	144.2	183.3	222.5	261.6	300.8
75°	76.2	78.3	80.3	92.7	105.1	117.4	129.8	166.9	201.9	239.0	274.0
77.5°	68.0	70.0	72.1	82.4	92.7	103.0	113.3	140.1	168.9	195.7	222.5
80°	55.6	55.6	57.7	65.9	74.2	80.3	88.6	107.1	125.7	142.1	160.7
82.5°	41.2	43.3	43.3	49.4	53.6	59.7	63.9	74.2	82.4	92.7	100.9
85°	35.0	33.0	33.0	37.1	39.1	43.3	45.3	51.5	55.6	61.8	65.9
87.5°	14.4	12.4	12.4	14.4	18.5	20.6	22.7	22.7	24.7	24.7	24.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014

CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1520.3	1524.4	1530.6	1534.7	1545.0	1553.3	1563.6	1571.8	1578.0	1588.3	1584.2
5°	1464.7	1483.2	1501.8	1520.3	1534.7	1549.2	1561.5	1575.9	1592.4	1623.3	1631.6
7.5°	1299.9	1324.6	1347.3	1372.0	1400.8	1429.7	1458.5	1487.4	1514.1	1553.3	1578.0
10°	1137.2	1172.2	1205.1	1240.2	1266.9	1293.7	1318.4	1345.2	1382.3	1421.4	1466.8
12.5°	1034.1	1069.2	1104.2	1139.2	1178.4	1215.4	1254.6	1291.7	1326.7	1357.6	1409.1
15°	966.2	1005.3	1042.4	1079.5	1126.9	1172.2	1219.6	1264.9	1316.4	1357.6	1392.6
17.5°	949.7	997.1	1042.4	1089.8	1139.2	1188.7	1238.1	1287.5	1339.0	1400.8	1446.2
20°	920.8	984.7	1048.6	1112.4	1176.3	1238.1	1302.0	1363.8	1431.7	1505.9	1526.5
22.5°	904.4	980.6	1058.9	1135.1	1221.6	1310.2	1396.7	1483.2	1555.3	1611.0	1672.8
25°	902.3	997.1	1093.9	1188.7	1297.8	1405.0	1514.1	1621.3	1714.0	1769.6	1819.0
27.5°	900.2	1015.6	1128.9	1242.2	1376.1	1508.0	1641.9	1773.7	1860.2	1940.6	1981.8
30°	875.5	1013.5	1153.6	1291.7	1442.0	1592.4	1742.8	1893.2	1981.8	2037.4	2058.0
32.5°	844.6	1007.4	1170.1	1332.9	1503.8	1674.8	1843.8	2014.7	2084.8	2132.2	2115.7
35°	819.9	999.1	1176.3	1353.5	1534.7	1718.1	1899.4	2080.7	2181.6	2247.5	2220.7
37.5°	797.2	984.7	1172.2	1359.6	1571.8	1784.0	1996.2	2208.4	2305.2	2375.2	2344.3
40°	770.5	970.3	1172.2	1372.0	1615.1	1856.1	2099.2	2340.2	2465.9	2525.6	2478.3
42.5°	747.8	955.9	1166.0	1374.1	1633.6	1893.2	2152.8	2412.3	2552.4	2636.9	2577.1
45°	719.0	927.0	1133.0	1341.1	1627.4	1913.8	2198.1	2484.4	2647.2	2713.1	2630.7
47.5°	688.1	894.1	1098.0	1302.0	1606.8	1911.7	2216.6	2521.5	2671.9	2750.2	2674.0
50°	677.8	883.8	1087.7	1293.7	1623.3	1955.0	2284.6	2614.2	2723.4	2787.3	2686.3
52.5°	675.7	894.1	1114.5	1332.9	1664.5	1994.1	2325.8	2655.4	2744.0	2812.0	2721.3
55°	669.5	906.4	1141.3	1376.1	1722.2	2070.4	2416.4	2762.5	2851.1	2900.6	2832.6
57.5°	675.7	931.1	1184.5	1440.0	1796.4	2152.8	2509.2	2865.5	2972.7	3007.7	2993.3
60°	679.8	951.7	1221.6	1493.5	1841.7	2189.8	2538.0	2886.1	2997.4	3083.9	3100.4
62.5°	669.5	937.3	1203.1	1470.9	1786.1	2101.3	2416.4	2731.6	2915.0	3042.7	3116.9
65°	638.6	885.8	1135.1	1382.3	1672.8	1965.3	2255.8	2546.2	2739.9	2929.4	2989.1
67.5°	570.6	780.8	990.9	1201.0	1454.4	1707.8	1959.1	2212.5	2455.6	2638.9	2721.3
70°	494.4	659.2	826.1	990.9	1221.6	1452.3	1683.1	1913.8	2128.0	2329.9	2408.2
72.5°	430.6	558.3	688.1	815.8	980.6	1143.3	1308.1	1470.9	1724.3	1926.2	2002.4
75°	366.7	459.4	550.0	642.7	756.0	869.3	980.6	1093.9	1273.1	1454.4	1530.6
77.5°	282.2	344.0	403.8	463.5	541.8	618.0	696.3	772.5	898.2	1034.1	1073.3
80°	195.7	230.7	263.7	298.7	360.5	422.3	484.1	545.9	628.3	704.5	764.3
82.5°	121.5	144.2	164.8	185.4	234.8	284.3	331.7	381.1	414.1	418.2	477.9
85°	78.3	92.7	105.1	117.4	146.3	177.2	206.0	234.8	210.1	195.7	232.8
87.5°	30.9	39.1	45.3	51.5	49.4	47.4	45.3	43.3	37.1	33.0	41.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014

CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1588.3	1594.5	1600.7	1604.8	1611.0	1613.0	1615.1	1615.1	1617.1	1619.2	1623.3
5°	1664.5	1676.9	1689.2	1699.5	1711.9	1722.2	1730.4	1740.7	1749.0	1749.0	1746.9
7.5°	1600.7	1631.6	1662.5	1693.4	1724.3	1746.9	1767.5	1790.2	1810.8	1814.9	1819.0
10°	1516.2	1549.2	1580.1	1613.0	1643.9	1678.9	1711.9	1744.9	1779.9	1786.1	1794.3
12.5°	1437.9	1477.1	1516.2	1553.3	1592.4	1617.1	1641.9	1664.5	1689.2	1705.7	1722.2
15°	1435.9	1468.8	1501.8	1532.7	1565.6	1580.1	1594.5	1606.8	1621.3	1621.3	1623.3
17.5°	1483.2	1503.8	1524.4	1543.0	1563.6	1565.6	1569.8	1571.8	1573.9	1567.7	1561.5
20°	1575.9	1584.2	1592.4	1600.7	1608.9	1594.5	1582.1	1567.7	1553.3	1536.8	1522.4
22.5°	1711.9	1693.4	1674.8	1656.3	1637.7	1613.0	1586.2	1561.5	1534.7	1514.1	1493.5
25°	1839.6	1817.0	1794.3	1771.7	1749.0	1695.4	1641.9	1586.2	1532.7	1510.0	1487.4
27.5°	2010.6	1975.6	1940.6	1905.6	1870.5	1798.4	1726.3	1654.2	1582.1	1543.0	1505.9
30°	2051.8	2012.7	1973.5	1932.3	1893.2	1823.2	1755.2	1685.1	1615.1	1569.8	1526.5
32.5°	2111.6	2066.2	2020.9	1975.6	1930.3	1862.3	1794.3	1724.3	1656.3	1615.1	1571.8
35°	2210.4	2158.9	2107.4	2053.9	2002.4	1932.3	1864.4	1794.3	1724.3	1676.9	1631.6
37.5°	2294.9	2235.2	2175.4	2115.7	2055.9	1994.1	1930.3	1868.5	1804.6	1757.2	1711.9
40°	2389.7	2323.7	2257.8	2194.0	2128.0	2070.4	2012.7	1952.9	1895.3	1858.2	1821.1
42.5°	2472.1	2391.7	2313.4	2235.2	2154.8	2115.7	2078.6	2039.5	2000.3	1981.8	1961.2
45°	2529.8	2455.6	2379.4	2305.2	2231.0	2202.2	2173.4	2144.5	2115.7	2134.2	2152.8
47.5°	2554.5	2494.7	2437.0	2379.4	2319.6	2329.9	2340.2	2348.5	2358.8	2383.5	2410.3
50°	2577.1	2544.2	2509.2	2476.2	2441.2	2480.3	2517.4	2556.5	2595.7	2647.2	2698.7
52.5°	2622.5	2603.9	2587.4	2568.9	2550.4	2618.3	2686.3	2754.3	2822.3	2880.0	2937.6
55°	2758.4	2744.0	2729.6	2713.1	2698.7	2795.5	2890.3	2987.1	3083.9	3143.6	3203.4
57.5°	2945.9	2937.6	2927.3	2919.1	2908.8	3003.6	3096.3	3189.0	3283.7	3341.4	3401.2
60°	3088.0	3090.1	3090.1	3092.1	3092.1	3164.2	3236.4	3310.5	3382.6	3432.1	3483.6
62.5°	3164.2	3160.1	3156.0	3151.9	3147.8	3207.5	3267.3	3327.0	3386.7	3423.8	3460.9
65°	3081.8	3104.5	3127.2	3149.8	3172.5	3180.7	3186.9	3195.2	3201.3	3224.0	3246.7
67.5°	2805.8	2851.1	2894.4	2939.7	2983.0	2952.1	2923.2	2892.3	2861.4	2867.6	2871.7
70°	2498.9	2550.4	2603.9	2655.4	2706.9	2634.8	2562.7	2488.6	2416.4	2391.7	2367.0
72.5°	2107.4	2152.8	2200.1	2245.5	2290.8	2202.2	2115.7	2027.1	1938.5	1895.3	1852.0
75°	1611.0	1664.5	1720.1	1773.7	1827.3	1728.4	1627.4	1528.6	1427.6	1398.8	1372.0
77.5°	1174.2	1238.1	1302.0	1365.8	1429.7	1341.1	1252.5	1161.9	1073.3	1056.8	1040.3
80°	854.9	904.4	951.7	1001.2	1048.6	997.1	945.6	894.1	842.6	840.5	838.4
82.5°	576.8	620.1	661.3	704.5	745.7	725.1	706.6	686.0	665.4	686.0	708.7
85°	296.6	356.4	418.2	477.9	537.7	531.5	527.4	521.2	515.0	541.8	566.5
87.5°	59.7	111.2	162.7	212.2	263.7	251.3	239.0	224.5	212.2	220.4	226.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014

CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1625.4	1627.4	1627.4	1627.4	1627.4	1627.4	1623.3	1621.3	1617.1	1613.0	1606.8
5°	1746.9	1744.9	1736.6	1728.4	1718.1	1709.8	1703.7	1695.4	1689.2	1681.0	1668.6
7.5°	1823.2	1827.3	1812.9	1800.5	1786.1	1771.7	1757.2	1742.8	1728.4	1714.0	1685.1
10°	1800.5	1806.7	1798.4	1790.2	1779.9	1771.7	1755.2	1736.6	1720.1	1701.6	1666.6
12.5°	1736.6	1753.1	1749.0	1744.9	1740.7	1736.6	1726.3	1714.0	1703.7	1691.3	1652.2
15°	1623.3	1623.3	1625.4	1627.4	1627.4	1629.5	1631.6	1633.6	1635.7	1637.7	1615.1
17.5°	1555.3	1549.2	1549.2	1549.2	1549.2	1549.2	1557.4	1567.7	1575.9	1584.2	1578.0
20°	1505.9	1491.5	1489.4	1489.4	1487.4	1485.3	1499.7	1516.2	1530.6	1545.0	1553.3
22.5°	1472.9	1452.3	1450.3	1448.2	1446.2	1444.1	1462.6	1481.2	1499.7	1518.3	1547.1
25°	1464.7	1442.0	1444.1	1446.2	1446.2	1448.2	1462.6	1477.1	1491.5	1505.9	1555.3
27.5°	1466.8	1429.7	1431.7	1433.8	1433.8	1435.9	1458.5	1479.1	1501.8	1522.4	1584.2
30°	1481.2	1437.9	1433.8	1429.7	1425.6	1421.4	1452.3	1483.2	1514.1	1545.0	1592.4
32.5°	1530.6	1489.4	1479.1	1468.8	1458.5	1448.2	1485.3	1520.3	1557.4	1592.4	1631.6
35°	1584.2	1538.9	1534.7	1530.6	1524.4	1520.3	1553.3	1588.3	1621.3	1654.2	1689.2
37.5°	1664.5	1619.2	1615.1	1608.9	1604.8	1598.6	1635.7	1670.7	1707.8	1742.8	1773.7
40°	1784.0	1746.9	1744.9	1744.9	1742.8	1740.7	1769.6	1800.5	1829.3	1858.2	1878.8
42.5°	1942.6	1924.1	1930.3	1938.5	1944.7	1950.9	1973.5	1998.3	2020.9	2043.6	2037.4
45°	2171.3	2189.8	2191.9	2194.0	2196.0	2198.1	2204.3	2212.5	2218.7	2224.9	2200.1
47.5°	2435.0	2459.7	2472.1	2484.4	2494.7	2507.1	2498.9	2488.6	2480.3	2470.0	2408.2
50°	2748.1	2799.6	2797.6	2795.5	2791.4	2789.3	2772.8	2756.4	2737.8	2721.3	2630.7
52.5°	2995.3	3053.0	3063.3	3073.6	3083.9	3094.2	3063.3	3032.4	2999.4	2968.5	2855.2
55°	3261.1	3320.8	3322.9	3324.9	3324.9	3327.0	3283.7	3240.5	3195.2	3151.9	3034.5
57.5°	3458.8	3516.5	3510.3	3506.2	3500.0	3493.9	3442.4	3390.9	3339.4	3287.9	3170.4
60°	3533.0	3582.4	3570.1	3557.7	3543.3	3530.9	3491.8	3452.7	3411.5	3372.3	3259.0
62.5°	3498.0	3535.1	3516.5	3500.0	3481.5	3463.0	3413.5	3362.0	3312.6	3261.1	3178.7
65°	3267.3	3289.9	3265.2	3242.5	3219.9	3195.2	3153.9	3112.7	3069.5	3028.3	2972.7
67.5°	2877.9	2882.0	2880.0	2877.9	2875.8	2873.8	2814.0	2754.3	2692.5	2632.8	2628.6
70°	2344.3	2319.6	2323.7	2329.9	2334.0	2338.2	2292.8	2249.6	2204.3	2158.9	2179.5
72.5°	1808.7	1765.5	1775.8	1788.1	1798.4	1808.7	1771.7	1736.6	1699.5	1662.5	1691.3
75°	1343.2	1316.4	1326.7	1339.0	1349.3	1359.6	1345.2	1330.8	1314.3	1299.9	1326.7
77.5°	1023.8	1007.4	1009.4	1009.4	1011.5	1011.5	1013.5	1017.7	1019.7	1021.8	1050.6
80°	834.3	832.3	830.2	828.1	824.0	822.0	842.6	863.2	883.8	904.4	918.8
82.5°	729.3	749.9	737.5	727.2	714.8	702.5	721.0	739.6	758.1	776.6	770.5
85°	593.3	618.0	595.4	572.7	548.0	525.3	541.8	556.2	572.7	587.1	578.9
87.5°	234.8	241.0	203.9	168.9	131.8	94.8	150.4	203.9	259.6	313.1	321.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014

CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2	1483.2
2.5°	1600.7	1592.4	1586.2	1584.2	1580.1	1578.0	1573.9	1569.8	1563.6	1559.5	1553.3
5°	1654.2	1641.9	1627.4	1606.8	1588.3	1567.7	1547.1	1528.6	1510.0	1489.4	1470.9
7.5°	1656.3	1627.4	1598.6	1571.8	1543.0	1516.2	1487.4	1462.6	1435.9	1409.1	1384.4
10°	1633.6	1598.6	1563.6	1528.6	1495.6	1460.6	1425.6	1396.7	1365.8	1334.9	1306.1
12.5°	1615.1	1575.9	1536.8	1495.6	1456.5	1415.3	1374.1	1345.2	1316.4	1287.5	1258.7
15°	1592.4	1567.7	1545.0	1508.0	1470.9	1433.8	1396.7	1357.6	1320.5	1281.4	1242.2
17.5°	1573.9	1567.7	1561.5	1536.8	1512.1	1485.3	1460.6	1421.4	1382.3	1341.1	1302.0
20°	1563.6	1571.8	1580.1	1567.7	1555.3	1540.9	1528.6	1499.7	1470.9	1440.0	1411.1
22.5°	1575.9	1606.8	1635.7	1637.7	1641.9	1643.9	1646.0	1619.2	1592.4	1563.6	1536.8
25°	1604.8	1654.2	1703.7	1730.4	1757.2	1786.1	1812.9	1796.4	1779.9	1763.4	1746.9
27.5°	1643.9	1705.7	1767.5	1806.7	1843.8	1882.9	1922.0	1920.0	1917.9	1913.8	1911.7
30°	1637.7	1685.1	1732.5	1779.9	1827.3	1874.7	1922.0	1946.8	1969.4	1994.1	2018.9
32.5°	1672.8	1711.9	1753.1	1802.6	1852.0	1903.5	1952.9	2004.4	2053.9	2105.4	2156.9
35°	1726.3	1761.3	1798.4	1852.0	1907.6	1961.2	2016.8	2078.6	2142.5	2206.3	2268.1
37.5°	1806.7	1837.6	1870.5	1915.9	1963.2	2008.6	2055.9	2146.6	2237.2	2329.9	2420.6
40°	1899.4	1920.0	1940.6	1983.8	2027.1	2070.4	2113.6	2226.9	2340.2	2453.5	2566.8
42.5°	2033.3	2027.1	2020.9	2055.9	2093.0	2128.0	2165.1	2268.1	2371.1	2474.1	2577.1
45°	2175.4	2150.7	2126.0	2142.5	2161.0	2177.5	2196.0	2301.1	2406.1	2513.3	2618.3
47.5°	2346.4	2284.6	2222.8	2208.4	2194.0	2177.5	2163.1	2276.4	2389.7	2505.0	2618.3
50°	2540.1	2447.3	2356.7	2319.6	2280.5	2243.4	2204.3	2297.0	2391.7	2486.5	2579.2
52.5°	2741.9	2626.6	2513.3	2455.6	2397.9	2338.2	2280.5	2358.8	2439.1	2519.5	2597.7
55°	2915.0	2797.6	2678.1	2610.1	2542.1	2474.1	2406.1	2484.4	2562.7	2641.0	2719.3
57.5°	3053.0	2935.6	2818.2	2754.3	2688.4	2624.5	2558.6	2632.8	2709.0	2785.2	2859.4
60°	3147.8	3034.5	2921.2	2859.4	2797.6	2735.8	2674.0	2762.5	2851.1	2941.8	3030.3
62.5°	3098.3	3015.9	2933.5	2906.7	2880.0	2851.1	2824.3	2908.8	2991.2	3075.7	3160.1
65°	2917.0	2861.4	2805.8	2832.6	2861.4	2888.2	2917.0	2972.7	3028.3	3086.0	3141.6
67.5°	2622.5	2618.3	2612.2	2671.9	2731.6	2793.4	2853.2	2890.3	2925.3	2962.4	2999.4
70°	2200.1	2222.8	2243.4	2346.4	2449.4	2552.4	2655.4	2669.8	2684.3	2698.7	2713.1
72.5°	1722.2	1751.0	1782.0	1917.9	2051.8	2187.8	2323.7	2315.5	2307.3	2297.0	2288.7
75°	1355.5	1382.3	1411.1	1536.8	1662.5	1788.1	1913.8	1878.8	1845.8	1810.8	1775.8
77.5°	1081.5	1110.4	1141.3	1258.7	1376.1	1495.6	1613.0	1528.6	1444.1	1359.6	1275.2
80°	931.1	945.6	957.9	1038.3	1116.6	1196.9	1277.2	1190.7	1102.1	1013.5	927.0
82.5°	764.3	756.0	749.9	797.2	844.6	892.0	939.4	857.0	774.6	690.1	607.7
85°	570.6	562.4	554.2	578.9	603.6	630.4	655.1	560.3	465.6	368.8	274.0
87.5°	331.7	339.9	348.1	374.9	401.7	430.6	457.3	360.5	263.7	164.8	68.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
 CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676014
CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1483.2	1483.2
2.5°	1540.9	1530.6
5°	1456.5	1442.0
7.5°	1363.8	1345.2
10°	1279.3	1254.6
12.5°	1225.7	1194.8
15°	1205.1	1168.1
17.5°	1266.9	1231.9
20°	1361.7	1314.3
22.5°	1477.1	1419.4
25°	1676.9	1606.8
27.5°	1839.6	1767.5
30°	1940.6	1862.3
32.5°	2051.8	1948.8
35°	2167.2	2068.3
37.5°	2307.3	2196.0
40°	2451.5	2336.1
42.5°	2500.9	2426.7
45°	2548.3	2478.3
47.5°	2558.6	2500.9
50°	2568.9	2560.7
52.5°	2597.7	2595.7
55°	2721.3	2723.4
57.5°	2873.8	2886.1
60°	3013.9	2999.4
62.5°	3086.0	3011.8
65°	3036.5	2933.5
67.5°	2888.2	2777.0
70°	2562.7	2412.3
72.5°	2156.9	2025.0
75°	1662.5	1551.2
77.5°	1182.5	1089.8
80°	832.3	739.6
82.5°	533.6	459.4
85°	241.0	210.1
87.5°	68.0	65.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676014
CATALOG NUMBER: CCW-SA-2A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)