

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676051

Luminaire Tested: **CCW-SA-2E-835-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P676051
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2E-835-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/
SLR distribution lens
Light Source: (32) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9349.8 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G3

Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 13.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P676051
CATALOG NUMBER: CCW-SA-2E-835-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1923.8	0.0	1923.8
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	7426.0	0.0	7426.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	9349.8	0.0	9349.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.0	2.5
10°-20°	489.8	5.2
20°-30°	716.7	7.7
30°-40°	1009.6	10.8
40°-50°	1387.4	14.8
50°-60°	1891.0	20.2
60°-70°	2069.7	22.1
70°-80°	1195.3	12.8
80°-90°	358.3	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9349.8	100.0
0°-180°	9349.8	100.0



REPORT NUMBER: P676051


CATALOG NUMBER: CCW-SA-2E-835-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	960.3	10.3			
FM (30°-60°)	3412.0	36.5			
FH (60°-80°)	2749.4	29.4			G2/5000
FVH (80°-90°)	304.3	3.3			G3/500
BL (0°-30°)	478.3	5.1	B1/500		
BM (30°-60°)	876.0	9.4	B1/1000		
BH (60°-80°)	515.6	5.5	B2/1000		G2/1000
BVH (80°-90°)	54.0	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short





REPORT NUMBER: P676051

CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	3081.1	3064.6	3052.1	3039.7	3023.1	3010.6	2994.1	2977.5	2956.7	2940.1	2919.4
5°	2902.8	2853.1	2803.3	2774.3	2741.1	2712.1	2678.9	2641.6	2604.2	2562.8	2525.5
7.5°	2707.9	2645.7	2583.5	2533.7	2479.8	2430.1	2376.2	2330.6	2284.9	2239.3	2193.7
10°	2525.5	2467.4	2409.3	2347.1	2280.8	2218.6	2152.2	2090.0	2027.8	1965.6	1903.4
12.5°	2405.2	2334.7	2268.3	2197.9	2131.5	2061.0	1990.5	1932.5	1874.4	1812.2	1754.1
15°	2351.3	2284.9	2222.7	2152.2	2081.7	2011.2	1940.7	1874.4	1812.2	1745.8	1679.5
17.5°	2479.8	2384.5	2289.1	2197.9	2106.6	2015.4	1924.2	1841.2	1758.3	1675.3	1592.4
20°	2645.7	2525.5	2409.3	2297.4	2181.3	2069.3	1953.2	1837.1	1721.0	1604.8	1488.7
22.5°	2857.2	2720.4	2587.7	2442.5	2293.2	2148.1	1998.8	1853.7	1708.5	1559.2	1414.1
25°	3234.6	3072.8	2911.1	2703.8	2492.3	2284.9	2073.4	1882.7	1696.1	1505.3	1314.6
27.5°	3558.0	3338.2	3122.6	2873.8	2625.0	2376.2	2127.4	1907.6	1691.9	1472.1	1252.4
30°	3748.8	3533.2	3317.5	3014.8	2716.2	2413.5	2110.8	1866.1	1625.6	1380.9	1136.2
32.5°	3923.0	3682.4	3441.9	3110.2	2774.3	2442.5	2106.6	1837.1	1571.7	1302.1	1032.6
35°	4163.5	3898.1	3636.8	3251.2	2865.5	2479.8	2094.2	1816.3	1534.3	1256.5	974.5
37.5°	4420.6	4093.0	3769.5	3342.4	2915.3	2488.1	2061.0	1787.3	1513.6	1239.9	966.2
40°	4702.6	4304.5	3910.5	3437.8	2969.2	2496.4	2023.7	1750.0	1476.3	1198.5	924.8
42.5°	4885.0	4453.8	4022.5	3512.4	3006.5	2496.4	1986.4	1716.8	1447.3	1173.6	904.0
45°	4988.7	4569.9	4155.2	3603.6	3052.1	2500.6	1949.0	1683.6	1418.2	1148.7	883.3
47.5°	5034.3	4644.5	4254.7	3674.1	3097.7	2517.2	1936.6	1667.0	1393.4	1123.8	850.1
50°	5154.6	4810.4	4466.2	3844.2	3226.3	2604.2	1982.2	1691.9	1405.8	1115.5	825.2
52.5°	5225.1	4930.7	4636.2	3997.6	3359.0	2720.4	2081.7	1758.3	1434.8	1111.4	787.9
55°	5482.2	5200.2	4918.2	4238.1	3553.9	2873.8	2189.6	1832.9	1476.3	1115.5	758.9
57.5°	5809.8	5511.2	5216.8	4482.8	3748.8	3014.8	2280.8	1899.3	1513.6	1132.1	746.4
60°	6037.9	5747.6	5461.5	4681.8	3898.1	3118.5	2334.7	1936.6	1538.5	1136.2	738.1
62.5°	6062.8	5689.5	5320.5	4561.6	3802.7	3039.7	2280.8	1895.1	1509.5	1119.7	734.0
65°	5905.2	5469.7	5034.3	4308.6	3582.9	2857.2	2131.5	1779.0	1426.5	1069.9	717.4
67.5°	5590.0	5079.9	4569.9	3906.4	3242.9	2579.4	1915.9	1613.1	1314.6	1011.8	709.1
70°	4856.0	4408.1	3964.4	3388.0	2815.7	2239.3	1662.9	1414.1	1169.4	920.6	671.8
72.5°	4076.4	3657.6	3242.9	2774.3	2309.8	1841.2	1372.6	1186.0	999.4	808.6	622.0
75°	3122.6	2807.4	2496.4	2148.1	1799.8	1447.3	1098.9	962.1	825.2	688.4	551.5
77.5°	2193.7	2023.7	1857.8	1596.6	1335.3	1074.0	812.8	721.6	630.3	539.1	447.9
80°	1488.7	1393.4	1302.1	1115.5	928.9	738.1	551.5	493.5	431.3	373.2	311.0
82.5°	924.8	920.6	912.3	783.8	655.2	526.7	398.1	348.3	302.7	253.0	203.2
85°	423.0	493.5	559.8	489.3	418.8	348.3	277.8	244.7	211.5	174.2	141.0
87.5°	132.7	161.7	186.6	178.3	165.9	157.6	145.1	124.4	103.7	82.9	62.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051

CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	2902.8	2890.4	2873.8	2857.2	2836.5	2819.9	2799.2	2778.4	2774.3	2766.0	2761.8
5°	2500.6	2475.7	2446.7	2421.8	2396.9	2367.9	2343.0	2314.0	2293.2	2268.3	2247.6
7.5°	2148.1	2106.6	2061.0	2015.4	1973.9	1932.5	1886.8	1845.4	1824.6	1803.9	1783.2
10°	1866.1	1824.6	1787.3	1745.8	1716.8	1691.9	1662.9	1633.9	1609.0	1584.1	1559.2
12.5°	1725.1	1696.1	1667.0	1638.0	1604.8	1575.8	1542.6	1509.5	1480.4	1455.6	1426.5
15°	1638.0	1596.6	1550.9	1509.5	1463.9	1422.4	1376.8	1331.2	1298.0	1268.9	1235.8
17.5°	1534.3	1472.1	1414.1	1351.9	1302.1	1252.4	1198.5	1148.7	1111.4	1069.9	1032.6
20°	1418.2	1347.7	1273.1	1202.6	1144.5	1090.6	1032.6	974.5	933.1	887.4	846.0
22.5°	1318.7	1227.5	1132.1	1036.7	974.5	912.3	846.0	783.8	746.4	705.0	667.6
25°	1210.9	1111.4	1007.7	904.0	841.8	775.5	713.3	646.9	617.9	593.0	564.0
27.5°	1152.8	1053.3	949.6	850.1	792.1	729.9	671.8	609.6	588.9	564.0	543.2
30°	1036.7	941.3	841.8	742.3	700.8	663.5	622.0	580.6	572.3	568.1	559.8
32.5°	933.1	833.5	734.0	634.5	597.2	559.8	522.5	485.2	481.0	472.7	468.6
35°	879.1	783.8	684.2	588.9	555.7	518.4	485.2	447.9	439.6	427.1	418.8
37.5°	866.7	767.2	663.5	564.0	530.8	497.6	460.3	427.1	418.8	410.5	402.2
40°	833.5	738.1	646.9	551.5	518.4	485.2	447.9	414.7	406.4	398.1	389.8
42.5°	808.6	717.4	622.0	526.7	497.6	468.6	435.4	406.4	398.1	389.8	377.4
45°	787.9	692.5	593.0	497.6	476.9	456.2	431.3	410.5	402.2	389.8	381.5
47.5°	754.7	663.5	568.1	472.7	452.0	435.4	414.7	394.0	385.7	377.4	369.1
50°	729.9	634.5	539.1	443.7	427.1	410.5	394.0	377.4	377.4	381.5	381.5
52.5°	696.7	605.4	514.2	423.0	406.4	389.8	373.2	356.6	360.8	364.9	369.1
55°	667.6	580.6	489.3	398.1	381.5	364.9	344.2	327.6	331.8	335.9	340.0
57.5°	655.2	564.0	472.7	381.5	364.9	344.2	327.6	306.9	306.9	306.9	306.9
60°	646.9	551.5	460.3	364.9	344.2	327.6	306.9	286.1	282.0	282.0	277.8
62.5°	642.8	547.4	456.2	360.8	335.9	315.2	290.3	265.4	261.3	257.1	253.0
65°	626.2	539.1	447.9	356.6	327.6	302.7	273.7	244.7	240.5	240.5	236.4
67.5°	622.0	530.8	443.7	352.5	323.5	290.3	261.3	228.1	223.9	219.8	215.6
70°	588.9	510.1	427.1	344.2	311.0	282.0	248.8	215.6	211.5	203.2	199.1
72.5°	547.4	476.9	402.2	327.6	294.4	261.3	228.1	194.9	190.8	186.6	178.3
75°	485.2	418.8	352.5	286.1	257.1	232.2	203.2	174.2	170.0	165.9	157.6
77.5°	398.1	344.2	294.4	240.5	219.8	199.1	178.3	157.6	153.4	149.3	141.0
80°	282.0	248.8	219.8	186.6	174.2	157.6	145.1	128.6	128.6	124.4	124.4
82.5°	186.6	170.0	153.4	136.8	128.6	120.3	112.0	103.7	103.7	99.5	99.5
85°	132.7	124.4	112.0	103.7	99.5	91.2	87.1	78.8	78.8	78.8	78.8
87.5°	62.2	62.2	58.1	58.1	53.9	53.9	49.8	45.6	45.6	45.6	45.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	2753.5	2741.1	2728.7	2712.1	2699.6	2683.0	2662.3	2645.7	2625.0	2625.0	2620.8
5°	2222.7	2210.3	2197.9	2181.3	2168.8	2152.2	2139.8	2123.2	2106.6	2106.6	2102.5
7.5°	1762.4	1737.5	1712.7	1683.6	1658.8	1642.2	1625.6	1604.8	1588.3	1575.8	1563.4
10°	1534.3	1509.5	1480.4	1455.6	1426.5	1405.8	1385.1	1360.2	1339.4	1322.9	1306.3
12.5°	1397.5	1368.5	1339.4	1310.4	1281.4	1252.4	1227.5	1198.5	1169.4	1148.7	1128.0
15°	1202.6	1173.6	1144.5	1115.5	1086.5	1053.3	1020.1	982.8	949.6	933.1	920.6
17.5°	991.1	962.1	928.9	899.9	866.7	841.8	816.9	792.1	767.2	750.6	738.1
20°	800.3	767.2	734.0	700.8	667.6	651.1	634.5	617.9	601.3	588.9	580.6
22.5°	626.2	605.4	588.9	568.1	547.4	534.9	526.7	514.2	501.8	501.8	501.8
25°	534.9	522.5	514.2	501.8	489.3	485.2	481.0	472.7	468.6	464.5	464.5
27.5°	518.4	505.9	493.5	481.0	468.6	464.5	460.3	452.0	447.9	447.9	447.9
30°	551.5	547.4	543.2	539.1	534.9	526.7	514.2	505.9	493.5	485.2	476.9
32.5°	460.3	456.2	456.2	452.0	447.9	456.2	460.3	468.6	472.7	476.9	481.0
35°	406.4	398.1	389.8	381.5	373.2	369.1	364.9	360.8	356.6	356.6	352.5
37.5°	394.0	385.7	377.4	369.1	360.8	356.6	352.5	348.3	344.2	344.2	340.0
40°	381.5	373.2	369.1	360.8	352.5	348.3	344.2	335.9	331.8	327.6	327.6
42.5°	369.1	364.9	356.6	352.5	344.2	340.0	335.9	327.6	323.5	319.3	315.2
45°	369.1	360.8	352.5	344.2	335.9	331.8	323.5	319.3	311.0	311.0	306.9
47.5°	360.8	352.5	344.2	335.9	327.6	323.5	315.2	311.0	302.7	298.6	294.4
50°	381.5	369.1	352.5	340.0	323.5	319.3	311.0	306.9	298.6	294.4	290.3
52.5°	373.2	360.8	344.2	331.8	315.2	306.9	302.7	294.4	286.1	282.0	277.8
55°	344.2	331.8	323.5	311.0	298.6	290.3	282.0	273.7	265.4	261.3	261.3
57.5°	306.9	302.7	298.6	294.4	290.3	282.0	273.7	261.3	253.0	248.8	244.7
60°	273.7	277.8	282.0	286.1	290.3	277.8	265.4	253.0	240.5	236.4	232.2
62.5°	248.8	257.1	265.4	269.5	277.8	265.4	253.0	240.5	228.1	223.9	219.8
65°	232.2	236.4	236.4	240.5	240.5	232.2	228.1	219.8	211.5	207.3	207.3
67.5°	211.5	211.5	211.5	207.3	207.3	203.2	203.2	199.1	194.9	190.8	190.8
70°	190.8	190.8	190.8	186.6	186.6	182.5	182.5	178.3	174.2	174.2	170.0
72.5°	174.2	174.2	170.0	170.0	165.9	165.9	165.9	161.7	161.7	157.6	157.6
75°	153.4	153.4	149.3	149.3	145.1	145.1	145.1	141.0	141.0	141.0	136.8
77.5°	136.8	136.8	132.7	132.7	128.6	128.6	128.6	124.4	124.4	120.3	120.3
80°	120.3	120.3	116.1	116.1	112.0	112.0	107.8	107.8	103.7	103.7	99.5
82.5°	95.4	95.4	95.4	95.4	95.4	91.2	91.2	87.1	82.9	82.9	78.8
85°	78.8	78.8	78.8	74.6	74.6	74.6	70.5	70.5	66.4	62.2	62.2
87.5°	45.6	45.6	45.6	41.5	41.5	41.5	41.5	41.5	41.5	41.5	37.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051

CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	2620.8	2616.7	2600.1	2583.5	2600.1	2616.7	2616.7	2616.7	2612.5	2612.5	2612.5
5°	2102.5	2098.3	2090.0	2081.7	2081.7	2077.6	2085.9	2094.2	2102.5	2110.8	2119.1
7.5°	1546.8	1534.3	1521.9	1509.5	1517.8	1521.9	1534.3	1542.6	1555.1	1563.4	1584.1
10°	1289.7	1273.1	1260.7	1248.2	1239.9	1231.6	1223.3	1219.2	1210.9	1202.6	1210.9
12.5°	1103.1	1082.3	1061.6	1036.7	1032.6	1028.4	1020.1	1011.8	1003.5	995.3	991.1
15°	904.0	887.4	879.1	866.7	850.1	833.5	825.2	821.1	812.8	804.5	800.3
17.5°	721.6	705.0	692.5	680.1	675.9	667.6	667.6	667.6	667.6	667.6	667.6
20°	568.1	555.7	555.7	551.5	551.5	547.4	551.5	555.7	555.7	559.8	564.0
22.5°	497.6	497.6	493.5	489.3	493.5	493.5	497.6	501.8	505.9	510.1	514.2
25°	460.3	456.2	460.3	464.5	464.5	464.5	468.6	468.6	472.7	472.7	472.7
27.5°	443.7	443.7	447.9	447.9	452.0	452.0	452.0	447.9	447.9	443.7	443.7
30°	468.6	460.3	460.3	460.3	456.2	452.0	447.9	447.9	443.7	439.6	435.4
32.5°	485.2	489.3	485.2	476.9	472.7	464.5	460.3	452.0	447.9	439.6	431.3
35°	352.5	348.3	356.6	360.8	364.9	369.1	373.2	377.4	377.4	381.5	381.5
37.5°	340.0	335.9	335.9	331.8	331.8	331.8	331.8	331.8	327.6	327.6	331.8
40°	323.5	319.3	319.3	315.2	315.2	311.0	311.0	311.0	311.0	311.0	311.0
42.5°	311.0	306.9	306.9	306.9	306.9	302.7	302.7	298.6	298.6	294.4	294.4
45°	306.9	302.7	298.6	294.4	294.4	290.3	290.3	290.3	286.1	286.1	286.1
47.5°	290.3	286.1	286.1	282.0	282.0	277.8	277.8	277.8	273.7	273.7	273.7
50°	282.0	277.8	277.8	273.7	273.7	269.5	269.5	269.5	265.4	265.4	265.4
52.5°	269.5	265.4	265.4	265.4	261.3	257.1	257.1	257.1	253.0	253.0	253.0
55°	257.1	253.0	253.0	253.0	248.8	244.7	244.7	244.7	240.5	240.5	240.5
57.5°	240.5	236.4	236.4	232.2	232.2	232.2	232.2	232.2	228.1	228.1	228.1
60°	228.1	223.9	223.9	219.8	219.8	215.6	215.6	215.6	215.6	215.6	215.6
62.5°	215.6	211.5	207.3	203.2	207.3	207.3	207.3	207.3	203.2	203.2	203.2
65°	203.2	199.1	194.9	190.8	190.8	190.8	190.8	190.8	190.8	190.8	190.8
67.5°	186.6	182.5	178.3	174.2	178.3	178.3	178.3	178.3	178.3	178.3	178.3
70°	170.0	165.9	165.9	161.7	161.7	157.6	157.6	161.7	161.7	161.7	161.7
72.5°	153.4	149.3	149.3	145.1	145.1	145.1	145.1	145.1	145.1	145.1	145.1
75°	136.8	132.7	132.7	128.6	128.6	128.6	128.6	128.6	128.6	128.6	128.6
77.5°	116.1	112.0	112.0	112.0	112.0	112.0	112.0	116.1	116.1	116.1	116.1
80°	99.5	95.4	95.4	95.4	95.4	95.4	95.4	95.4	95.4	95.4	95.4
82.5°	78.8	74.6	74.6	74.6	74.6	74.6	74.6	74.6	74.6	74.6	74.6
85°	58.1	53.9	53.9	53.9	58.1	58.1	58.1	58.1	58.1	58.1	58.1
87.5°	37.3	33.2	33.2	33.2	37.3	37.3	37.3	37.3	33.2	33.2	33.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051

CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	2612.5	2612.5	2612.5	2608.4	2604.2	2600.1	2596.0	2608.4	2616.7	2629.1	2637.4
5°	2123.2	2131.5	2135.6	2148.1	2160.5	2173.0	2185.4	2193.7	2202.0	2206.1	2214.4
7.5°	1600.7	1621.4	1638.0	1654.6	1671.2	1683.6	1700.2	1712.7	1725.1	1737.5	1750.0
10°	1215.0	1223.3	1227.5	1244.1	1256.5	1273.1	1285.5	1298.0	1310.4	1318.7	1331.2
12.5°	987.0	978.7	974.5	974.5	974.5	974.5	974.5	982.8	991.1	999.4	1007.7
15°	796.2	792.1	787.9	783.8	779.6	771.3	767.2	775.5	783.8	792.1	800.3
17.5°	667.6	667.6	667.6	663.5	659.4	655.2	651.1	655.2	659.4	659.4	663.5
20°	572.3	576.4	580.6	584.7	584.7	588.9	588.9	593.0	597.2	597.2	601.3
22.5°	514.2	518.4	518.4	518.4	522.5	522.5	522.5	526.7	530.8	534.9	539.1
25°	468.6	468.6	464.5	464.5	468.6	468.6	468.6	468.6	472.7	472.7	472.7
27.5°	443.7	439.6	439.6	439.6	439.6	435.4	435.4	435.4	435.4	435.4	435.4
30°	431.3	427.1	423.0	418.8	418.8	414.7	410.5	410.5	410.5	410.5	410.5
32.5°	427.1	418.8	410.5	406.4	406.4	402.2	398.1	394.0	394.0	389.8	385.7
35°	381.5	377.4	377.4	373.2	369.1	364.9	360.8	360.8	360.8	356.6	356.6
37.5°	331.8	335.9	335.9	335.9	340.0	340.0	340.0	340.0	344.2	344.2	344.2
40°	311.0	311.0	311.0	315.2	319.3	319.3	323.5	323.5	327.6	327.6	327.6
42.5°	294.4	290.3	290.3	294.4	294.4	298.6	298.6	302.7	306.9	306.9	311.0
45°	286.1	282.0	282.0	282.0	282.0	277.8	277.8	282.0	286.1	290.3	294.4
47.5°	269.5	269.5	265.4	265.4	265.4	265.4	265.4	265.4	269.5	269.5	269.5
50°	261.3	261.3	257.1	257.1	257.1	257.1	257.1	257.1	257.1	257.1	257.1
52.5°	253.0	248.8	248.8	248.8	248.8	244.7	244.7	244.7	244.7	244.7	244.7
55°	240.5	236.4	236.4	236.4	236.4	236.4	236.4	236.4	240.5	240.5	240.5
57.5°	228.1	223.9	223.9	223.9	228.1	228.1	228.1	228.1	232.2	232.2	232.2
60°	215.6	215.6	215.6	215.6	215.6	215.6	215.6	219.8	219.8	223.9	223.9
62.5°	203.2	203.2	203.2	203.2	207.3	207.3	207.3	207.3	211.5	211.5	211.5
65°	190.8	190.8	190.8	190.8	194.9	194.9	194.9	194.9	194.9	194.9	194.9
67.5°	178.3	178.3	178.3	178.3	178.3	178.3	178.3	182.5	182.5	186.6	186.6
70°	161.7	157.6	157.6	161.7	161.7	165.9	165.9	170.0	170.0	174.2	174.2
72.5°	145.1	145.1	145.1	145.1	145.1	145.1	145.1	149.3	153.4	153.4	157.6
75°	128.6	128.6	128.6	128.6	132.7	132.7	132.7	136.8	136.8	141.0	141.0
77.5°	116.1	112.0	112.0	112.0	116.1	116.1	116.1	120.3	120.3	124.4	124.4
80°	95.4	95.4	95.4	95.4	99.5	99.5	99.5	99.5	103.7	103.7	103.7
82.5°	78.8	78.8	78.8	78.8	78.8	78.8	78.8	78.8	82.9	82.9	82.9
85°	58.1	58.1	58.1	58.1	62.2	62.2	62.2	62.2	62.2	62.2	62.2
87.5°	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	41.5	41.5	41.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051

CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	2637.4	2637.4	2637.4	2637.4	2645.7	2649.9	2658.2	2662.3	2658.2	2654.0	2645.7
5°	2218.6	2222.7	2222.7	2226.9	2226.9	2226.9	2226.9	2226.9	2235.2	2243.5	2251.8
7.5°	1754.1	1758.3	1762.4	1766.6	1766.6	1766.6	1762.4	1762.4	1766.6	1766.6	1770.7
10°	1343.6	1360.2	1372.6	1385.1	1376.8	1364.3	1356.0	1343.6	1343.6	1343.6	1339.4
12.5°	1016.0	1020.1	1028.4	1032.6	1028.4	1028.4	1024.3	1020.1	1024.3	1032.6	1036.7
15°	804.5	804.5	808.6	808.6	812.8	816.9	816.9	821.1	829.4	833.5	841.8
17.5°	667.6	671.8	671.8	675.9	675.9	680.1	680.1	680.1	688.4	696.7	709.1
20°	601.3	601.3	601.3	601.3	601.3	597.2	597.2	593.0	597.2	605.4	609.6
22.5°	539.1	543.2	543.2	543.2	539.1	534.9	526.7	522.5	522.5	526.7	526.7
25°	472.7	468.6	468.6	464.5	464.5	468.6	468.6	468.6	472.7	472.7	476.9
27.5°	435.4	431.3	431.3	427.1	427.1	431.3	431.3	431.3	431.3	431.3	431.3
30°	406.4	406.4	402.2	398.1	402.2	402.2	406.4	406.4	410.5	410.5	414.7
32.5°	385.7	381.5	381.5	377.4	381.5	381.5	385.7	385.7	389.8	394.0	394.0
35°	356.6	356.6	356.6	356.6	356.6	356.6	352.5	352.5	352.5	352.5	352.5
37.5°	340.0	340.0	335.9	331.8	331.8	331.8	331.8	331.8	327.6	323.5	319.3
40°	327.6	323.5	323.5	319.3	315.2	315.2	311.0	306.9	306.9	302.7	302.7
42.5°	311.0	306.9	306.9	302.7	298.6	298.6	294.4	290.3	290.3	290.3	286.1
45°	290.3	290.3	286.1	282.0	282.0	282.0	277.8	277.8	277.8	277.8	273.7
47.5°	269.5	269.5	265.4	265.4	265.4	265.4	261.3	261.3	261.3	261.3	261.3
50°	257.1	257.1	257.1	257.1	257.1	257.1	253.0	253.0	253.0	253.0	253.0
52.5°	244.7	244.7	244.7	244.7	244.7	244.7	244.7	244.7	244.7	244.7	244.7
55°	240.5	240.5	240.5	240.5	240.5	240.5	236.4	236.4	236.4	240.5	240.5
57.5°	232.2	232.2	228.1	228.1	228.1	228.1	228.1	228.1	228.1	228.1	228.1
60°	223.9	223.9	223.9	223.9	223.9	223.9	223.9	223.9	223.9	223.9	223.9
62.5°	211.5	211.5	211.5	211.5	211.5	215.6	215.6	215.6	215.6	215.6	211.5
65°	194.9	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1
67.5°	186.6	186.6	186.6	186.6	186.6	186.6	186.6	186.6	186.6	186.6	186.6
70°	174.2	174.2	170.0	170.0	170.0	174.2	174.2	174.2	174.2	174.2	174.2
72.5°	157.6	157.6	157.6	157.6	157.6	157.6	157.6	157.6	157.6	161.7	161.7
75°	141.0	141.0	141.0	141.0	141.0	141.0	141.0	141.0	141.0	141.0	141.0
77.5°	124.4	124.4	120.3	120.3	120.3	124.4	124.4	124.4	124.4	128.6	128.6
80°	103.7	103.7	103.7	103.7	103.7	103.7	103.7	103.7	103.7	107.8	107.8
82.5°	82.9	82.9	82.9	82.9	82.9	82.9	82.9	82.9	82.9	87.1	87.1
85°	62.2	66.4	66.4	66.4	66.4	66.4	66.4	66.4	66.4	70.5	70.5
87.5°	41.5	41.5	41.5	41.5	41.5	41.5	37.3	37.3	37.3	37.3	33.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051

CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	2641.6	2645.7	2649.9	2649.9	2654.0	2658.2	2658.2	2674.7	2691.3	2699.6	2707.9
5°	2260.1	2255.9	2255.9	2251.8	2247.6	2260.1	2272.5	2297.4	2322.3	2326.4	2334.7
7.5°	1770.7	1774.9	1779.0	1779.0	1783.2	1770.7	1754.1	1758.3	1762.4	1783.2	1799.8
10°	1339.4	1343.6	1347.7	1347.7	1351.9	1347.7	1339.4	1351.9	1364.3	1380.9	1401.6
12.5°	1040.9	1053.3	1065.8	1074.0	1086.5	1094.8	1098.9	1115.5	1128.0	1148.7	1169.4
15°	850.1	858.4	866.7	875.0	883.3	891.6	899.9	916.5	933.1	957.9	982.8
17.5°	717.4	717.4	721.6	721.6	721.6	729.9	738.1	746.4	750.6	775.5	800.3
20°	613.7	609.6	605.4	601.3	597.2	605.4	609.6	613.7	617.9	634.5	646.9
22.5°	526.7	526.7	530.8	530.8	530.8	526.7	518.4	522.5	522.5	530.8	543.2
25°	476.9	476.9	476.9	472.7	472.7	476.9	481.0	481.0	476.9	481.0	485.2
27.5°	431.3	435.4	435.4	439.6	439.6	443.7	443.7	443.7	443.7	447.9	452.0
30°	414.7	414.7	418.8	418.8	418.8	423.0	427.1	427.1	427.1	431.3	439.6
32.5°	398.1	402.2	406.4	410.5	414.7	418.8	418.8	423.0	423.0	427.1	431.3
35°	352.5	348.3	348.3	344.2	340.0	340.0	340.0	340.0	335.9	340.0	340.0
37.5°	315.2	315.2	315.2	311.0	311.0	315.2	315.2	315.2	315.2	319.3	319.3
40°	298.6	298.6	298.6	298.6	298.6	298.6	298.6	302.7	302.7	306.9	311.0
42.5°	286.1	286.1	286.1	286.1	286.1	290.3	290.3	290.3	290.3	294.4	294.4
45°	273.7	273.7	273.7	273.7	273.7	273.7	273.7	277.8	277.8	282.0	286.1
47.5°	261.3	261.3	261.3	261.3	261.3	265.4	269.5	269.5	269.5	273.7	273.7
50°	253.0	253.0	253.0	253.0	253.0	257.1	257.1	261.3	261.3	265.4	269.5
52.5°	244.7	244.7	244.7	244.7	244.7	248.8	248.8	253.0	253.0	257.1	261.3
55°	240.5	240.5	240.5	236.4	236.4	240.5	240.5	244.7	244.7	248.8	248.8
57.5°	228.1	228.1	228.1	228.1	228.1	228.1	228.1	232.2	232.2	236.4	240.5
60°	223.9	223.9	219.8	219.8	215.6	219.8	219.8	223.9	223.9	228.1	228.1
62.5°	211.5	211.5	211.5	207.3	207.3	211.5	211.5	211.5	211.5	215.6	219.8
65°	199.1	199.1	199.1	194.9	194.9	199.1	199.1	199.1	199.1	203.2	207.3
67.5°	186.6	186.6	186.6	182.5	182.5	182.5	182.5	186.6	186.6	190.8	194.9
70°	174.2	174.2	174.2	170.0	170.0	170.0	165.9	170.0	174.2	178.3	178.3
72.5°	161.7	161.7	161.7	157.6	157.6	157.6	153.4	157.6	157.6	161.7	161.7
75°	141.0	141.0	141.0	141.0	141.0	141.0	136.8	136.8	136.8	141.0	141.0
77.5°	128.6	128.6	128.6	124.4	124.4	124.4	120.3	120.3	120.3	124.4	124.4
80°	107.8	107.8	107.8	103.7	103.7	103.7	99.5	99.5	99.5	103.7	103.7
82.5°	87.1	87.1	87.1	82.9	82.9	82.9	78.8	78.8	78.8	82.9	82.9
85°	70.5	70.5	70.5	70.5	70.5	70.5	66.4	66.4	66.4	70.5	74.6
87.5°	33.2	33.2	37.3	37.3	37.3	37.3	33.2	33.2	29.0	29.0	33.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	2716.2	2724.5	2745.2	2761.8	2782.6	2799.2	2811.6	2828.2	2840.6	2853.1	2861.4
5°	2338.8	2343.0	2363.7	2384.5	2401.0	2421.8	2450.8	2479.8	2508.9	2537.9	2558.6
7.5°	1820.5	1837.1	1862.0	1891.0	1915.9	1940.7	1969.8	2002.9	2032.0	2061.0	2090.0
10°	1418.2	1434.8	1459.7	1484.6	1505.3	1530.2	1563.4	1596.6	1629.7	1662.9	1696.1
12.5°	1190.2	1210.9	1239.9	1268.9	1293.8	1322.9	1364.3	1401.6	1443.1	1480.4	1521.9
15°	1003.5	1028.4	1065.8	1107.2	1144.5	1181.9	1223.3	1264.8	1302.1	1343.6	1385.1
17.5°	825.2	850.1	883.3	920.6	953.8	987.0	1036.7	1082.3	1132.1	1177.7	1223.3
20°	663.5	675.9	709.1	742.3	775.5	808.6	846.0	883.3	920.6	957.9	1016.0
22.5°	551.5	559.8	576.4	588.9	605.4	617.9	655.2	692.5	725.7	763.0	816.9
25°	485.2	489.3	501.8	510.1	522.5	530.8	555.7	576.4	601.3	622.0	671.8
27.5°	452.0	456.2	460.3	464.5	468.6	472.7	489.3	505.9	518.4	534.9	580.6
30°	443.7	447.9	460.3	468.6	481.0	489.3	497.6	505.9	514.2	522.5	551.5
32.5°	435.4	439.6	439.6	435.4	435.4	431.3	439.6	443.7	452.0	456.2	481.0
35°	344.2	344.2	348.3	352.5	356.6	360.8	373.2	381.5	394.0	402.2	423.0
37.5°	323.5	323.5	327.6	335.9	340.0	344.2	352.5	360.8	369.1	377.4	398.1
40°	311.0	315.2	319.3	323.5	327.6	331.8	340.0	344.2	352.5	356.6	373.2
42.5°	298.6	298.6	302.7	311.0	315.2	319.3	327.6	331.8	340.0	344.2	360.8
45°	290.3	294.4	298.6	302.7	302.7	306.9	315.2	323.5	327.6	335.9	352.5
47.5°	277.8	277.8	286.1	290.3	298.6	302.7	311.0	315.2	323.5	327.6	344.2
50°	269.5	273.7	282.0	286.1	294.4	298.6	311.0	319.3	331.8	340.0	348.3
52.5°	261.3	265.4	273.7	277.8	286.1	290.3	306.9	323.5	335.9	352.5	352.5
55°	253.0	253.0	261.3	273.7	282.0	290.3	298.6	311.0	319.3	327.6	327.6
57.5°	240.5	244.7	253.0	265.4	273.7	282.0	290.3	298.6	302.7	311.0	306.9
60°	232.2	232.2	244.7	257.1	269.5	282.0	282.0	282.0	277.8	277.8	277.8
62.5°	219.8	223.9	240.5	261.3	277.8	294.4	282.0	269.5	257.1	244.7	248.8
65°	211.5	215.6	223.9	236.4	244.7	253.0	244.7	240.5	232.2	223.9	228.1
67.5°	194.9	199.1	203.2	203.2	207.3	207.3	207.3	207.3	207.3	207.3	211.5
70°	182.5	182.5	182.5	186.6	186.6	186.6	186.6	186.6	186.6	186.6	190.8
72.5°	165.9	165.9	165.9	165.9	165.9	165.9	165.9	165.9	165.9	165.9	170.0
75°	145.1	145.1	145.1	145.1	145.1	145.1	145.1	145.1	145.1	145.1	149.3
77.5°	128.6	128.6	128.6	128.6	128.6	128.6	128.6	128.6	124.4	124.4	128.6
80°	107.8	107.8	107.8	107.8	103.7	103.7	103.7	103.7	103.7	103.7	107.8
82.5°	87.1	87.1	87.1	87.1	82.9	82.9	82.9	82.9	78.8	78.8	82.9
85°	78.8	82.9	82.9	87.1	87.1	87.1	82.9	78.8	74.6	70.5	70.5
87.5°	33.2	33.2	33.2	33.2	29.0	29.0	29.0	29.0	29.0	29.0	29.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051

CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	2873.8	2882.1	2890.4	2902.8	2919.4	2931.9	2944.3	2969.2	2998.2	3023.1	3048.0
5°	2579.4	2600.1	2620.8	2645.7	2670.6	2691.3	2716.2	2766.0	2815.7	2861.4	2911.1
7.5°	2114.9	2143.9	2168.8	2210.3	2247.6	2289.1	2326.4	2388.6	2446.7	2508.9	2566.9
10°	1729.3	1762.4	1795.6	1849.5	1907.6	1961.5	2015.4	2065.2	2119.1	2168.8	2218.6
12.5°	1563.4	1600.7	1642.2	1675.3	1712.7	1745.8	1779.0	1837.1	1895.1	1953.2	2011.2
15°	1426.5	1468.0	1509.5	1550.9	1588.3	1629.7	1667.0	1716.8	1770.7	1820.5	1870.2
17.5°	1268.9	1310.4	1356.0	1401.6	1447.3	1492.9	1538.5	1609.0	1679.5	1745.8	1816.3
20°	1069.9	1128.0	1181.9	1244.1	1306.3	1368.5	1430.7	1505.3	1580.0	1650.5	1725.1
22.5°	870.8	924.8	978.7	1053.3	1128.0	1198.5	1273.1	1372.6	1468.0	1567.5	1662.9
25°	725.7	775.5	825.2	908.2	987.0	1069.9	1148.7	1268.9	1385.1	1505.3	1621.4
27.5°	626.2	671.8	717.4	804.5	891.6	974.5	1061.6	1194.3	1322.9	1455.6	1584.1
30°	580.6	609.6	638.6	721.6	804.5	883.3	966.2	1094.8	1223.3	1351.9	1480.4
32.5°	505.9	530.8	555.7	630.3	705.0	775.5	850.1	982.8	1111.4	1244.1	1372.6
35°	447.9	468.6	489.3	559.8	626.2	696.7	763.0	895.7	1028.4	1161.1	1293.8
37.5°	414.7	435.4	452.0	514.2	580.6	642.8	705.0	837.7	966.2	1098.9	1227.5
40°	389.8	402.2	418.8	481.0	539.1	601.3	659.4	779.6	904.0	1024.3	1144.5
42.5°	373.2	389.8	402.2	456.2	514.2	568.1	622.0	738.1	854.3	966.2	1082.3
45°	369.1	385.7	402.2	447.9	493.5	534.9	580.6	692.5	804.5	916.5	1028.4
47.5°	360.8	373.2	389.8	427.1	460.3	497.6	530.8	642.8	754.7	862.6	974.5
50°	356.6	360.8	369.1	402.2	435.4	468.6	501.8	613.7	725.7	837.7	949.6
52.5°	352.5	352.5	352.5	381.5	410.5	435.4	464.5	576.4	692.5	804.5	916.5
55°	327.6	323.5	323.5	352.5	377.4	406.4	431.3	543.2	655.2	763.0	875.0
57.5°	302.7	298.6	294.4	319.3	344.2	369.1	394.0	505.9	622.0	734.0	846.0
60°	277.8	273.7	273.7	298.6	319.3	344.2	364.9	481.0	593.0	709.1	821.1
62.5°	248.8	253.0	253.0	273.7	298.6	319.3	340.0	456.2	576.4	692.5	808.6
65°	228.1	232.2	232.2	257.1	282.0	306.9	331.8	443.7	559.8	671.8	783.8
67.5°	211.5	215.6	215.6	244.7	269.5	298.6	323.5	423.0	526.7	626.2	725.7
70°	194.9	194.9	199.1	228.1	257.1	286.1	315.2	402.2	489.3	572.3	659.4
72.5°	174.2	178.3	182.5	211.5	236.4	265.4	290.3	369.1	447.9	526.7	605.4
75°	153.4	157.6	161.7	186.6	211.5	236.4	261.3	335.9	406.4	481.0	551.5
77.5°	136.8	141.0	145.1	165.9	186.6	207.3	228.1	282.0	340.0	394.0	447.9
80°	112.0	112.0	116.1	132.7	149.3	161.7	178.3	215.6	253.0	286.1	323.5
82.5°	82.9	87.1	87.1	99.5	107.8	120.3	128.6	149.3	165.9	186.6	203.2
85°	70.5	66.4	66.4	74.6	78.8	87.1	91.2	103.7	112.0	124.4	132.7
87.5°	29.0	24.9	24.9	29.0	37.3	41.5	45.6	45.6	49.8	49.8	49.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051

CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	3060.4	3068.7	3081.1	3089.4	3110.2	3126.8	3147.5	3164.1	3176.5	3197.3	3189.0
5°	2948.4	2985.8	3023.1	3060.4	3089.4	3118.5	3143.3	3172.4	3205.5	3267.7	3284.3
7.5°	2616.7	2666.5	2712.1	2761.8	2819.9	2877.9	2936.0	2994.1	3048.0	3126.8	3176.5
10°	2289.1	2359.6	2425.9	2496.4	2550.3	2604.2	2654.0	2707.9	2782.6	2861.4	2952.6
12.5°	2081.7	2152.2	2222.7	2293.2	2372.0	2446.7	2525.5	2600.1	2670.6	2732.8	2836.5
15°	1944.9	2023.7	2098.3	2173.0	2268.3	2359.6	2455.0	2546.2	2649.9	2732.8	2803.3
17.5°	1911.7	2007.1	2098.3	2193.7	2293.2	2392.8	2492.3	2591.8	2695.5	2819.9	2911.1
20°	1853.7	1982.2	2110.8	2239.3	2367.9	2492.3	2620.8	2745.2	2882.1	3031.4	3072.8
22.5°	1820.5	1973.9	2131.5	2284.9	2459.1	2637.4	2811.6	2985.8	3130.9	3242.9	3367.3
25°	1816.3	2007.1	2202.0	2392.8	2612.5	2828.2	3048.0	3263.6	3450.2	3562.2	3661.7
27.5°	1812.2	2044.4	2272.5	2500.6	2770.1	3035.5	3305.1	3570.5	3744.6	3906.4	3989.3
30°	1762.4	2040.3	2322.3	2600.1	2902.8	3205.5	3508.3	3811.0	3989.3	4101.3	4142.7
32.5°	1700.2	2027.8	2355.4	2683.0	3027.2	3371.4	3711.5	4055.7	4196.7	4292.0	4258.9
35°	1650.5	2011.2	2367.9	2724.5	3089.4	3458.5	3823.4	4188.4	4391.6	4524.3	4470.3
37.5°	1604.8	1982.2	2359.6	2736.9	3164.1	3591.2	4018.3	4445.5	4640.4	4781.4	4719.2
40°	1550.9	1953.2	2359.6	2761.8	3251.2	3736.3	4225.7	4710.9	4963.8	5084.1	4988.7
42.5°	1505.3	1924.2	2347.1	2766.0	3288.5	3811.0	4333.5	4856.0	5138.0	5308.0	5187.8
45°	1447.3	1866.1	2280.8	2699.6	3276.0	3852.5	4424.7	5001.1	5328.8	5461.5	5295.6
47.5°	1385.1	1799.8	2210.3	2620.8	3234.6	3848.3	4462.1	5075.8	5378.5	5536.1	5382.7
50°	1364.3	1779.0	2189.6	2604.2	3267.7	3935.4	4598.9	5262.4	5482.2	5610.7	5407.5
52.5°	1360.2	1799.8	2243.5	2683.0	3350.7	4014.2	4681.8	5345.3	5523.7	5660.5	5478.0
55°	1347.7	1824.6	2297.4	2770.1	3466.8	4167.6	4864.3	5561.0	5739.3	5838.8	5702.0
57.5°	1360.2	1874.4	2384.5	2898.7	3616.1	4333.5	5050.9	5768.3	5984.0	6054.5	6025.4
60°	1368.5	1915.9	2459.1	3006.5	3707.3	4408.1	5109.0	5809.8	6033.7	6207.9	6241.1
62.5°	1347.7	1886.8	2421.8	2960.9	3595.4	4229.8	4864.3	5498.8	5867.8	6125.0	6274.2
65°	1285.5	1783.2	2284.9	2782.6	3367.3	3956.1	4540.8	5125.6	5515.4	5896.9	6017.1
67.5°	1148.7	1571.7	1994.7	2417.6	2927.7	3437.8	3943.7	4453.8	4943.1	5312.2	5478.0
70°	995.3	1327.0	1662.9	1994.7	2459.1	2923.6	3388.0	3852.5	4283.7	4690.1	4847.7
72.5°	866.7	1123.8	1385.1	1642.2	1973.9	2301.5	2633.3	2960.9	3470.9	3877.3	4030.8
75°	738.1	924.8	1107.2	1293.8	1521.9	1750.0	1973.9	2202.0	2562.8	2927.7	3081.1
77.5°	568.1	692.5	812.8	933.1	1090.6	1244.1	1401.6	1555.1	1808.0	2081.7	2160.5
80°	394.0	464.5	530.8	601.3	725.7	850.1	974.5	1098.9	1264.8	1418.2	1538.5
82.5°	244.7	290.3	331.8	373.2	472.7	572.3	667.6	767.2	833.5	841.8	962.1
85°	157.6	186.6	211.5	236.4	294.4	356.6	414.7	472.7	423.0	394.0	468.6
87.5°	62.2	78.8	91.2	103.7	99.5	95.4	91.2	87.1	74.6	66.4	82.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051

CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	3197.3	3209.7	3222.1	3230.4	3242.9	3247.0	3251.2	3251.2	3255.3	3259.5	3267.7
5°	3350.7	3375.6	3400.4	3421.2	3446.1	3466.8	3483.4	3504.1	3520.7	3520.7	3516.6
7.5°	3222.1	3284.3	3346.5	3408.7	3470.9	3516.6	3558.0	3603.6	3645.1	3653.4	3661.7
10°	3052.1	3118.5	3180.7	3247.0	3309.2	3379.7	3446.1	3512.4	3582.9	3595.4	3611.9
12.5°	2894.5	2973.3	3052.1	3126.8	3205.5	3255.3	3305.1	3350.7	3400.4	3433.6	3466.8
15°	2890.4	2956.7	3023.1	3085.3	3151.6	3180.7	3209.7	3234.6	3263.6	3263.6	3267.7
17.5°	2985.8	3027.2	3068.7	3106.0	3147.5	3151.6	3159.9	3164.1	3168.2	3155.8	3143.3
20°	3172.4	3189.0	3205.5	3222.1	3238.7	3209.7	3184.8	3155.8	3126.8	3093.6	3064.6
22.5°	3446.1	3408.7	3371.4	3334.1	3296.8	3247.0	3193.1	3143.3	3089.4	3048.0	3006.5
25°	3703.2	3657.6	3611.9	3566.3	3520.7	3412.9	3305.1	3193.1	3085.3	3039.7	2994.1
27.5°	4047.4	3976.9	3906.4	3835.9	3765.4	3620.2	3475.1	3330.0	3184.8	3106.0	3031.4
30°	4130.3	4051.5	3972.7	3889.8	3811.0	3670.0	3533.2	3392.2	3251.2	3159.9	3072.8
32.5°	4250.6	4159.3	4068.1	3976.9	3885.6	3748.8	3611.9	3470.9	3334.1	3251.2	3164.1
35°	4449.6	4345.9	4242.3	4134.4	4030.8	3889.8	3752.9	3611.9	3470.9	3375.6	3284.3
37.5°	4619.6	4499.4	4379.1	4258.9	4138.6	4014.2	3885.6	3761.2	3632.7	3537.3	3446.1
40°	4810.4	4677.7	4545.0	4416.4	4283.7	4167.6	4051.5	3931.3	3815.1	3740.5	3665.9
42.5°	4976.3	4814.5	4657.0	4499.4	4337.6	4258.9	4184.2	4105.4	4026.6	3989.3	3947.8
45°	5092.4	4943.1	4789.7	4640.4	4491.1	4433.0	4375.0	4316.9	4258.9	4296.2	4333.5
47.5°	5142.1	5021.9	4905.8	4789.7	4669.4	4690.1	4710.9	4727.5	4748.2	4798.0	4851.9
50°	5187.8	5121.4	5050.9	4984.6	4914.1	4992.9	5067.5	5146.3	5225.1	5328.8	5432.4
52.5°	5279.0	5241.7	5208.5	5171.2	5133.9	5270.7	5407.5	5544.4	5681.2	5797.4	5913.5
55°	5552.7	5523.7	5494.6	5461.5	5432.4	5627.3	5818.1	6013.0	6207.9	6328.2	6448.4
57.5°	5930.1	5913.5	5892.7	5876.1	5855.4	6046.2	6232.8	6419.4	6610.1	6726.3	6846.5
60°	6216.2	6220.3	6220.3	6224.5	6224.5	6369.6	6514.8	6664.1	6809.2	6908.7	7012.4
62.5°	6369.6	6361.3	6353.0	6344.7	6336.4	6456.7	6577.0	6697.2	6817.5	6892.1	6966.8
65°	6203.7	6249.4	6295.0	6340.6	6386.2	6402.8	6415.2	6431.8	6444.3	6489.9	6535.5
67.5°	5648.1	5739.3	5826.4	5917.6	6004.7	5942.5	5884.4	5822.2	5760.0	5772.5	5780.8
70°	5030.2	5133.9	5241.7	5345.3	5449.0	5303.9	5158.7	5009.4	4864.3	4814.5	4764.8
72.5°	4242.3	4333.5	4428.9	4520.1	4611.3	4433.0	4258.9	4080.5	3902.2	3815.1	3728.1
75°	3242.9	3350.7	3462.7	3570.5	3678.3	3479.2	3276.0	3077.0	2873.8	2815.7	2761.8
77.5°	2363.7	2492.3	2620.8	2749.4	2877.9	2699.6	2521.3	2338.8	2160.5	2127.4	2094.2
80°	1721.0	1820.5	1915.9	2015.4	2110.8	2007.1	1903.4	1799.8	1696.1	1691.9	1687.8
82.5°	1161.1	1248.2	1331.2	1418.2	1501.2	1459.7	1422.4	1380.9	1339.4	1380.9	1426.5
85°	597.2	717.4	841.8	962.1	1082.3	1069.9	1061.6	1049.2	1036.7	1090.6	1140.4
87.5°	120.3	223.9	327.6	427.1	530.8	505.9	481.0	452.0	427.1	443.7	456.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051

CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	3271.9	3276.0	3276.0	3276.0	3276.0	3276.0	3267.7	3263.6	3255.3	3247.0	3234.6
5°	3516.6	3512.4	3495.8	3479.2	3458.5	3441.9	3429.5	3412.9	3400.4	3383.9	3359.0
7.5°	3670.0	3678.3	3649.3	3624.4	3595.4	3566.3	3537.3	3508.3	3479.2	3450.2	3392.2
10°	3624.4	3636.8	3620.2	3603.6	3582.9	3566.3	3533.2	3495.8	3462.7	3425.3	3354.8
12.5°	3495.8	3529.0	3520.7	3512.4	3504.1	3495.8	3475.1	3450.2	3429.5	3404.6	3325.8
15°	3267.7	3267.7	3271.9	3276.0	3276.0	3280.2	3284.3	3288.5	3292.6	3296.8	3251.2
17.5°	3130.9	3118.5	3118.5	3118.5	3118.5	3118.5	3135.0	3155.8	3172.4	3189.0	3176.5
20°	3031.4	3002.3	2998.2	2998.2	2994.1	2989.9	3018.9	3052.1	3081.1	3110.2	3126.8
22.5°	2965.0	2923.6	2919.4	2915.3	2911.1	2907.0	2944.3	2981.6	3018.9	3056.3	3114.3
25°	2948.4	2902.8	2907.0	2911.1	2911.1	2915.3	2944.3	2973.3	3002.3	3031.4	3130.9
27.5°	2952.6	2877.9	2882.1	2886.2	2886.2	2890.4	2936.0	2977.5	3023.1	3064.6	3189.0
30°	2981.6	2894.5	2886.2	2877.9	2869.6	2861.4	2923.6	2985.8	3048.0	3110.2	3205.5
32.5°	3081.1	2998.2	2977.5	2956.7	2936.0	2915.3	2989.9	3060.4	3135.0	3205.5	3284.3
35°	3189.0	3097.7	3089.4	3081.1	3068.7	3060.4	3126.8	3197.3	3263.6	3330.0	3400.4
37.5°	3350.7	3259.5	3251.2	3238.7	3230.4	3218.0	3292.6	3363.1	3437.8	3508.3	3570.5
40°	3591.2	3516.6	3512.4	3512.4	3508.3	3504.1	3562.2	3624.4	3682.4	3740.5	3782.0
42.5°	3910.5	3873.2	3885.6	3902.2	3914.7	3927.1	3972.7	4022.5	4068.1	4113.7	4101.3
45°	4370.8	4408.1	4412.3	4416.4	4420.6	4424.7	4437.2	4453.8	4466.2	4478.6	4428.9
47.5°	4901.6	4951.4	4976.3	5001.1	5021.9	5046.8	5030.2	5009.4	4992.9	4972.1	4847.7
50°	5532.0	5635.6	5631.5	5627.3	5619.0	5614.9	5581.7	5548.5	5511.2	5478.0	5295.6
52.5°	6029.6	6145.7	6166.4	6187.2	6207.9	6228.6	6166.4	6104.2	6037.9	5975.7	5747.6
55°	6564.5	6684.8	6688.9	6693.1	6693.1	6697.2	6610.1	6523.1	6431.8	6344.7	6108.4
57.5°	6962.6	7078.7	7066.3	7058.0	7045.6	7033.1	6929.5	6825.8	6722.1	6618.4	6382.1
60°	7111.9	7211.4	7186.6	7161.7	7132.7	7107.8	7029.0	6950.2	6867.3	6788.5	6560.4
62.5°	7041.4	7116.1	7078.7	7045.6	7008.2	6970.9	6871.4	6767.7	6668.2	6564.5	6398.7
65°	6577.0	6622.6	6572.8	6527.2	6481.6	6431.8	6348.9	6266.0	6178.9	6095.9	5984.0
67.5°	5793.2	5801.5	5797.4	5793.2	5789.1	5784.9	5664.7	5544.4	5420.0	5299.7	5291.4
70°	4719.2	4669.4	4677.7	4690.1	4698.4	4706.7	4615.5	4528.4	4437.2	4345.9	4387.4
72.5°	3641.0	3553.9	3574.6	3599.5	3620.2	3641.0	3566.3	3495.8	3421.2	3346.5	3404.6
75°	2703.8	2649.9	2670.6	2695.5	2716.2	2736.9	2707.9	2678.9	2645.7	2616.7	2670.6
77.5°	2061.0	2027.8	2032.0	2032.0	2036.1	2036.1	2040.3	2048.6	2052.7	2056.9	2114.9
80°	1679.5	1675.3	1671.2	1667.0	1658.8	1654.6	1696.1	1737.5	1779.0	1820.5	1849.5
82.5°	1468.0	1509.5	1484.6	1463.9	1439.0	1414.1	1451.4	1488.7	1526.1	1563.4	1550.9
85°	1194.3	1244.1	1198.5	1152.8	1103.1	1057.5	1090.6	1119.7	1152.8	1181.9	1165.3
87.5°	472.7	485.2	410.5	340.0	265.4	190.8	302.7	410.5	522.5	630.3	646.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051

CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8	2985.8
2.5°	3222.1	3205.5	3193.1	3189.0	3180.7	3176.5	3168.2	3159.9	3147.5	3139.2	3126.8
5°	3330.0	3305.1	3276.0	3234.6	3197.3	3155.8	3114.3	3077.0	3039.7	2998.2	2960.9
7.5°	3334.1	3276.0	3218.0	3164.1	3106.0	3052.1	2994.1	2944.3	2890.4	2836.5	2786.7
10°	3288.5	3218.0	3147.5	3077.0	3010.6	2940.1	2869.6	2811.6	2749.4	2687.2	2629.1
12.5°	3251.2	3172.4	3093.6	3010.6	2931.9	2848.9	2766.0	2707.9	2649.9	2591.8	2533.7
15°	3205.5	3155.8	3110.2	3035.5	2960.9	2886.2	2811.6	2732.8	2658.2	2579.4	2500.6
17.5°	3168.2	3155.8	3143.3	3093.6	3043.8	2989.9	2940.1	2861.4	2782.6	2699.6	2620.8
20°	3147.5	3164.1	3180.7	3155.8	3130.9	3101.9	3077.0	3018.9	2960.9	2898.7	2840.6
22.5°	3172.4	3234.6	3292.6	3296.8	3305.1	3309.2	3313.4	3259.5	3205.5	3147.5	3093.6
25°	3230.4	3330.0	3429.5	3483.4	3537.3	3595.4	3649.3	3616.1	3582.9	3549.7	3516.6
27.5°	3309.2	3433.6	3558.0	3636.8	3711.5	3790.3	3869.0	3864.9	3860.8	3852.5	3848.3
30°	3296.8	3392.2	3487.5	3582.9	3678.3	3773.7	3869.0	3918.8	3964.4	4014.2	4064.0
32.5°	3367.3	3446.1	3529.0	3628.5	3728.1	3831.7	3931.3	4034.9	4134.4	4238.1	4341.8
35°	3475.1	3545.6	3620.2	3728.1	3840.0	3947.8	4059.8	4184.2	4312.8	4441.3	4565.7
37.5°	3636.8	3699.0	3765.4	3856.6	3952.0	4043.2	4138.6	4321.1	4503.5	4690.1	4872.6
40°	3823.4	3864.9	3906.4	3993.5	4080.5	4167.6	4254.7	4482.8	4710.9	4938.9	5167.0
42.5°	4093.0	4080.5	4068.1	4138.6	4213.2	4283.7	4358.4	4565.7	4773.1	4980.4	5187.8
45°	4379.1	4329.4	4279.6	4312.8	4350.1	4383.3	4420.6	4632.1	4843.6	5059.2	5270.7
47.5°	4723.3	4598.9	4474.5	4445.5	4416.4	4383.3	4354.2	4582.3	4810.4	5042.6	5270.7
50°	5113.1	4926.5	4744.0	4669.4	4590.6	4516.0	4437.2	4623.8	4814.5	5005.3	5191.9
52.5°	5519.5	5287.3	5059.2	4943.1	4827.0	4706.7	4590.6	4748.2	4909.9	5071.6	5229.2
55°	5867.8	5631.5	5391.0	5254.1	5117.3	4980.4	4843.6	5001.1	5158.7	5316.3	5473.9
57.5°	6145.7	5909.3	5672.9	5544.4	5411.7	5283.1	5150.4	5299.7	5453.2	5606.6	5755.9
60°	6336.4	6108.4	5880.3	5755.9	5631.5	5507.1	5382.7	5561.0	5739.3	5921.8	6100.1
62.5°	6236.9	6071.0	5905.2	5851.3	5797.4	5739.3	5685.4	5855.4	6021.3	6191.3	6361.3
65°	5872.0	5760.0	5648.1	5702.0	5760.0	5813.9	5872.0	5984.0	6095.9	6212.0	6324.0
67.5°	5279.0	5270.7	5258.3	5378.5	5498.8	5623.2	5743.4	5818.1	5888.6	5963.2	6037.9
70°	4428.9	4474.5	4516.0	4723.3	4930.7	5138.0	5345.3	5374.4	5403.4	5432.4	5461.5
72.5°	3466.8	3524.9	3587.1	3860.8	4130.3	4404.0	4677.7	4661.1	4644.5	4623.8	4607.2
75°	2728.7	2782.6	2840.6	3093.6	3346.5	3599.5	3852.5	3782.0	3715.6	3645.1	3574.6
77.5°	2177.1	2235.2	2297.4	2533.7	2770.1	3010.6	3247.0	3077.0	2907.0	2736.9	2566.9
80°	1874.4	1903.4	1928.3	2090.0	2247.6	2409.3	2571.1	2396.9	2218.6	2040.3	1866.1
82.5°	1538.5	1521.9	1509.5	1604.8	1700.2	1795.6	1891.0	1725.1	1559.2	1389.2	1223.3
85°	1148.7	1132.1	1115.5	1165.3	1215.0	1268.9	1318.7	1128.0	937.2	742.3	551.5
87.5°	667.6	684.2	700.8	754.7	808.6	866.7	920.6	725.7	530.8	331.8	136.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676051
 CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2985.8	2985.8
2.5°	3101.9	3081.1
5°	2931.9	2902.8
7.5°	2745.2	2707.9
10°	2575.2	2525.5
12.5°	2467.4	2405.2
15°	2425.9	2351.3
17.5°	2550.3	2479.8
20°	2741.1	2645.7
22.5°	2973.3	2857.2
25°	3375.6	3234.6
27.5°	3703.2	3558.0
30°	3906.4	3748.8
32.5°	4130.3	3923.0
35°	4362.5	4163.5
37.5°	4644.5	4420.6
40°	4934.8	4702.6
42.5°	5034.3	4885.0
45°	5129.7	4988.7
47.5°	5150.4	5034.3
50°	5171.2	5154.6
52.5°	5229.2	5225.1
55°	5478.0	5482.2
57.5°	5784.9	5809.8
60°	6066.9	6037.9
62.5°	6212.0	6062.8
65°	6112.5	5905.2
67.5°	5813.9	5590.0
70°	5158.7	4856.0
72.5°	4341.8	4076.4
75°	3346.5	3122.6
77.5°	2380.3	2193.7
80°	1675.3	1488.7
82.5°	1074.0	924.8
85°	485.2	423.0
87.5°	136.8	132.7
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676051
CATALOG NUMBER: CCW-SA-2E-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)