

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P676062

Luminaire Tested: **CCW-SA-2E-840-U-SLR**

Issue Date: 04/25/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P676062  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/25/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCW-SA-2E-840-U-SLR  
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/  
SLR distribution lens  
Light Source: (32) 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9674.4 lumens  
Efficiency: N/A  
Efficacy: 90.8 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G3

Input Watts (W): 106.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 13.7 fc  
 Type IV - Short - N/A

REPORT NUMBER: P676062  
CATALOG NUMBER: CCW-SA-2E-840-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1990.6	0.0	1990.6
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	7683.8	0.0	7683.8
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	9674.4	0.0	9674.4
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	240.1	2.5
10°-20°	506.8	5.2
20°-30°	741.5	7.7
30°-40°	1044.7	10.8
40°-50°	1435.5	14.8
50°-60°	1956.7	20.2
60°-70°	2141.6	22.1
70°-80°	1236.7	12.8
80°-90°	370.7	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9674.4	100.0
0°-180°	9674.4	100.0




REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	993.6	10.3			
FM (30°-60°)	3530.5	36.5			
FH (60°-80°)	2844.8	29.4			G2/5000
FVH (80°-90°)	314.9	3.3			G3/500
BL (0°-30°)	494.9	5.1	B1/500		
BM (30°-60°)	906.4	9.4	B1/1000		
BH (60°-80°)	533.5	5.5	B2/1000		G2/1000
BVH (80°-90°)	55.8	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G3**

Type IV Short





REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	3188.1	3170.9	3158.0	3145.2	3128.0	3115.1	3098.0	3080.8	3059.4	3042.2	3020.7
5°	3003.6	2952.1	2900.6	2870.6	2836.2	2806.2	2771.9	2733.3	2694.6	2651.7	2613.1
7.5°	2801.9	2737.5	2673.2	2621.7	2565.9	2514.4	2458.6	2411.4	2364.2	2317.0	2269.8
10°	2613.1	2553.0	2493.0	2428.6	2360.0	2295.6	2226.9	2162.6	2098.2	2033.9	1969.5
12.5°	2488.7	2415.7	2347.1	2274.1	2205.5	2132.5	2059.6	1999.5	1939.5	1875.1	1815.0
15°	2432.9	2364.2	2299.9	2226.9	2154.0	2081.0	2008.1	1939.5	1875.1	1806.4	1737.8
17.5°	2565.9	2467.2	2368.5	2274.1	2179.7	2085.3	1990.9	1905.1	1819.3	1733.5	1647.7
20°	2737.5	2613.1	2493.0	2377.1	2257.0	2141.1	2021.0	1900.8	1780.7	1660.5	1540.4
22.5°	2956.4	2814.8	2677.5	2527.3	2372.8	2222.6	2068.2	1918.0	1767.8	1613.3	1463.2
25°	3346.8	3179.5	3012.2	2797.6	2578.8	2364.2	2145.4	1948.0	1754.9	1557.6	1360.2
27.5°	3681.5	3454.1	3231.0	2973.5	2716.1	2458.6	2201.2	1973.8	1750.7	1523.2	1295.8
30°	3878.9	3655.8	3432.7	3119.4	2810.5	2497.3	2184.0	1930.9	1682.0	1428.8	1175.7
32.5°	4059.1	3810.3	3561.4	3218.1	2870.6	2527.3	2179.7	1900.8	1626.2	1347.3	1068.4
35°	4308.0	4033.4	3763.1	3364.0	2965.0	2565.9	2166.9	1879.4	1587.6	1300.1	1008.3
37.5°	4574.0	4235.0	3900.4	3458.4	3016.4	2574.5	2132.5	1849.3	1566.2	1283.0	999.8
40°	4865.8	4453.9	4046.2	3557.1	3072.2	2583.1	2093.9	1810.7	1527.5	1240.0	956.9
42.5°	5054.6	4608.3	4162.1	3634.3	3110.8	2583.1	2055.3	1776.4	1497.5	1214.3	935.4
45°	5161.9	4728.5	4299.4	3728.7	3158.0	2587.4	2016.7	1742.1	1467.5	1188.6	913.9
47.5°	5209.1	4805.7	4402.4	3801.7	3205.2	2604.5	2003.8	1724.9	1441.7	1162.8	879.6
50°	5333.5	4977.4	4621.2	3977.6	3338.3	2694.6	2051.0	1750.7	1454.6	1154.2	853.9
52.5°	5406.4	5101.8	4797.1	4136.4	3475.6	2814.8	2154.0	1819.3	1484.6	1149.9	815.3
55°	5672.5	5380.7	5088.9	4385.2	3677.2	2973.5	2265.6	1896.5	1527.5	1154.2	785.2
57.5°	6011.4	5702.5	5397.9	4638.4	3878.9	3119.4	2360.0	1965.2	1566.2	1171.4	772.3
60°	6247.4	5947.1	5651.0	4844.3	4033.4	3226.7	2415.7	2003.8	1591.9	1175.7	763.8
62.5°	6273.2	5887.0	5505.1	4719.9	3934.7	3145.2	2360.0	1960.9	1561.9	1158.5	759.5
65°	6110.1	5659.6	5209.1	4458.2	3707.3	2956.4	2205.5	1840.8	1476.0	1107.0	742.3
67.5°	5784.0	5256.3	4728.5	4042.0	3355.4	2668.9	1982.4	1669.1	1360.2	1047.0	733.7
70°	5024.6	4561.1	4102.0	3505.6	2913.5	2317.0	1720.6	1463.2	1210.0	952.6	695.1
72.5°	4217.9	3784.5	3355.4	2870.6	2390.0	1905.1	1420.3	1227.2	1034.1	836.7	643.6
75°	3231.0	2904.9	2583.1	2222.6	1862.2	1497.5	1137.1	995.5	853.9	712.3	570.7
77.5°	2269.8	2093.9	1922.3	1652.0	1381.6	1111.3	841.0	746.6	652.2	557.8	463.4
80°	1540.4	1441.7	1347.3	1154.2	961.1	763.8	570.7	510.6	446.2	386.2	321.8
82.5°	956.9	952.6	944.0	811.0	678.0	544.9	411.9	360.4	313.2	261.7	210.3
85°	437.7	510.6	579.3	506.3	433.4	360.4	287.5	253.2	218.8	180.2	145.9
87.5°	137.3	167.3	193.1	184.5	171.6	163.1	150.2	128.7	107.3	85.8	64.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	3003.6	2990.7	2973.5	2956.4	2934.9	2917.8	2896.3	2874.9	2870.6	2862.0	2857.7
5°	2587.4	2561.6	2531.6	2505.8	2480.1	2450.1	2424.3	2394.3	2372.8	2347.1	2325.6
7.5°	2222.6	2179.7	2132.5	2085.3	2042.4	1999.5	1952.3	1909.4	1888.0	1866.5	1845.1
10°	1930.9	1888.0	1849.3	1806.4	1776.4	1750.7	1720.6	1690.6	1664.8	1639.1	1613.3
12.5°	1785.0	1754.9	1724.9	1694.9	1660.5	1630.5	1596.2	1561.9	1531.8	1506.1	1476.0
15°	1694.9	1652.0	1604.8	1561.9	1514.7	1471.8	1424.6	1377.4	1343.0	1313.0	1278.7
17.5°	1587.6	1523.2	1463.2	1398.8	1347.3	1295.8	1240.0	1188.6	1149.9	1107.0	1068.4
20°	1467.5	1394.5	1317.3	1244.3	1184.3	1128.5	1068.4	1008.3	965.4	918.2	875.3
22.5°	1364.5	1270.1	1171.4	1072.7	1008.3	944.0	875.3	811.0	772.3	729.4	690.8
25°	1252.9	1149.9	1042.7	935.4	871.0	802.4	738.0	669.4	639.3	613.6	583.6
27.5°	1192.8	1089.9	982.6	879.6	819.5	755.2	695.1	630.8	609.3	583.6	562.1
30°	1072.7	974.0	871.0	768.1	725.1	686.5	643.6	600.7	592.1	587.8	579.3
32.5°	965.4	862.5	759.5	656.5	617.9	579.3	540.6	502.0	497.7	489.2	484.9
35°	909.7	811.0	708.0	609.3	575.0	536.4	502.0	463.4	454.8	442.0	433.4
37.5°	896.8	793.8	686.5	583.6	549.2	514.9	476.3	442.0	433.4	424.8	416.2
40°	862.5	763.8	669.4	570.7	536.4	502.0	463.4	429.1	420.5	411.9	403.3
42.5°	836.7	742.3	643.6	544.9	514.9	484.9	450.5	420.5	411.9	403.3	390.5
45°	815.3	716.6	613.6	514.9	493.4	472.0	446.2	424.8	416.2	403.3	394.8
47.5°	780.9	686.5	587.8	489.2	467.7	450.5	429.1	407.6	399.0	390.5	381.9
50°	755.2	656.5	557.8	459.1	442.0	424.8	407.6	390.5	390.5	394.8	394.8
52.5°	720.9	626.5	532.1	437.7	420.5	403.3	386.2	369.0	373.3	377.6	381.9
55°	690.8	600.7	506.3	411.9	394.8	377.6	356.1	339.0	343.3	347.6	351.8
57.5°	678.0	583.6	489.2	394.8	377.6	356.1	339.0	317.5	317.5	317.5	317.5
60°	669.4	570.7	476.3	377.6	356.1	339.0	317.5	296.1	291.8	291.8	287.5
62.5°	665.1	566.4	472.0	373.3	347.6	326.1	300.4	274.6	270.3	266.0	261.7
65°	647.9	557.8	463.4	369.0	339.0	313.2	283.2	253.2	248.9	248.9	244.6
67.5°	643.6	549.2	459.1	364.7	334.7	300.4	270.3	236.0	231.7	227.4	223.1
70°	609.3	527.8	442.0	356.1	321.8	291.8	257.4	223.1	218.8	210.3	206.0
72.5°	566.4	493.4	416.2	339.0	304.6	270.3	236.0	201.7	197.4	193.1	184.5
75°	502.0	433.4	364.7	296.1	266.0	240.3	210.3	180.2	175.9	171.6	163.1
77.5°	411.9	356.1	304.6	248.9	227.4	206.0	184.5	163.1	158.8	154.5	145.9
80°	291.8	257.4	227.4	193.1	180.2	163.1	150.2	133.0	133.0	128.7	128.7
82.5°	193.1	175.9	158.8	141.6	133.0	124.4	115.9	107.3	107.3	103.0	103.0
85°	137.3	128.7	115.9	107.3	103.0	94.4	90.1	81.5	81.5	81.5	81.5
87.5°	64.4	64.4	60.1	60.1	55.8	55.8	51.5	47.2	47.2	47.2	47.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	2849.1	2836.2	2823.4	2806.2	2793.3	2776.2	2754.7	2737.5	2716.1	2716.1	2711.8
5°	2299.9	2287.0	2274.1	2257.0	2244.1	2226.9	2214.1	2196.9	2179.7	2179.7	2175.4
7.5°	1823.6	1797.9	1772.1	1742.1	1716.3	1699.2	1682.0	1660.5	1643.4	1630.5	1617.6
10°	1587.6	1561.9	1531.8	1506.1	1476.0	1454.6	1433.1	1407.4	1385.9	1368.8	1351.6
12.5°	1446.0	1416.0	1385.9	1355.9	1325.9	1295.8	1270.1	1240.0	1210.0	1188.6	1167.1
15°	1244.3	1214.3	1184.3	1154.2	1124.2	1089.9	1055.5	1016.9	982.6	965.4	952.6
17.5°	1025.5	995.5	961.1	931.1	896.8	871.0	845.3	819.5	793.8	776.6	763.8
20°	828.1	793.8	759.5	725.1	690.8	673.7	656.5	639.3	622.2	609.3	600.7
22.5°	647.9	626.5	609.3	587.8	566.4	553.5	544.9	532.1	519.2	519.2	519.2
25°	553.5	540.6	532.1	519.2	506.3	502.0	497.7	489.2	484.9	480.6	480.6
27.5°	536.4	523.5	510.6	497.7	484.9	480.6	476.3	467.7	463.4	463.4	463.4
30°	570.7	566.4	562.1	557.8	553.5	544.9	532.1	523.5	510.6	502.0	493.4
32.5°	476.3	472.0	472.0	467.7	463.4	472.0	476.3	484.9	489.2	493.4	497.7
35°	420.5	411.9	403.3	394.8	386.2	381.9	377.6	373.3	369.0	369.0	364.7
37.5°	407.6	399.0	390.5	381.9	373.3	369.0	364.7	360.4	356.1	356.1	351.8
40°	394.8	386.2	381.9	373.3	364.7	360.4	356.1	347.6	343.3	339.0	339.0
42.5°	381.9	377.6	369.0	364.7	356.1	351.8	347.6	339.0	334.7	330.4	326.1
45°	381.9	373.3	364.7	356.1	347.6	343.3	334.7	330.4	321.8	321.8	317.5
47.5°	373.3	364.7	356.1	347.6	339.0	334.7	326.1	321.8	313.2	308.9	304.6
50°	394.8	381.9	364.7	351.8	334.7	330.4	321.8	317.5	308.9	304.6	300.4
52.5°	386.2	373.3	356.1	343.3	326.1	317.5	313.2	304.6	296.1	291.8	287.5
55°	356.1	343.3	334.7	321.8	308.9	300.4	291.8	283.2	274.6	270.3	270.3
57.5°	317.5	313.2	308.9	304.6	300.4	291.8	283.2	270.3	261.7	257.4	253.2
60°	283.2	287.5	291.8	296.1	300.4	287.5	274.6	261.7	248.9	244.6	240.3
62.5°	257.4	266.0	274.6	278.9	287.5	274.6	261.7	248.9	236.0	231.7	227.4
65°	240.3	244.6	244.6	248.9	248.9	240.3	236.0	227.4	218.8	214.5	214.5
67.5°	218.8	218.8	218.8	214.5	214.5	210.3	210.3	206.0	201.7	197.4	197.4
70°	197.4	197.4	197.4	193.1	193.1	188.8	188.8	184.5	180.2	180.2	175.9
72.5°	180.2	180.2	175.9	175.9	171.6	171.6	171.6	167.3	167.3	163.1	163.1
75°	158.8	158.8	154.5	154.5	150.2	150.2	150.2	145.9	145.9	145.9	141.6
77.5°	141.6	141.6	137.3	137.3	133.0	133.0	133.0	128.7	128.7	124.4	124.4
80°	124.4	124.4	120.1	120.1	115.9	115.9	111.6	111.6	107.3	107.3	103.0
82.5°	98.7	98.7	98.7	98.7	98.7	94.4	94.4	90.1	85.8	85.8	81.5
85°	81.5	81.5	81.5	77.2	77.2	77.2	72.9	72.9	68.7	64.4	64.4
87.5°	47.2	47.2	47.2	42.9	42.9	42.9	42.9	42.9	42.9	42.9	38.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	2711.8	2707.5	2690.3	2673.2	2690.3	2707.5	2707.5	2707.5	2703.2	2703.2	2703.2
5°	2175.4	2171.2	2162.6	2154.0	2154.0	2149.7	2158.3	2166.9	2175.4	2184.0	2192.6
7.5°	1600.5	1587.6	1574.7	1561.9	1570.4	1574.7	1587.6	1596.2	1609.1	1617.6	1639.1
10°	1334.4	1317.3	1304.4	1291.5	1283.0	1274.4	1265.8	1261.5	1252.9	1244.3	1252.9
12.5°	1141.4	1119.9	1098.5	1072.7	1068.4	1064.1	1055.5	1047.0	1038.4	1029.8	1025.5
15°	935.4	918.2	909.7	896.8	879.6	862.5	853.9	849.6	841.0	832.4	828.1
17.5°	746.6	729.4	716.6	703.7	699.4	690.8	690.8	690.8	690.8	690.8	690.8
20°	587.8	575.0	575.0	570.7	570.7	566.4	570.7	575.0	575.0	579.3	583.6
22.5°	514.9	514.9	510.6	506.3	510.6	510.6	514.9	519.2	523.5	527.8	532.1
25°	476.3	472.0	476.3	480.6	480.6	480.6	484.9	484.9	489.2	489.2	489.2
27.5°	459.1	459.1	463.4	463.4	467.7	467.7	467.7	463.4	463.4	459.1	459.1
30°	484.9	476.3	476.3	476.3	472.0	467.7	463.4	463.4	459.1	454.8	450.5
32.5°	502.0	506.3	502.0	493.4	489.2	480.6	476.3	467.7	463.4	454.8	446.2
35°	364.7	360.4	369.0	373.3	377.6	381.9	386.2	390.5	390.5	394.8	394.8
37.5°	351.8	347.6	347.6	343.3	343.3	343.3	343.3	343.3	339.0	339.0	343.3
40°	334.7	330.4	330.4	326.1	326.1	321.8	321.8	321.8	321.8	321.8	321.8
42.5°	321.8	317.5	317.5	317.5	317.5	313.2	313.2	308.9	308.9	304.6	304.6
45°	317.5	313.2	308.9	304.6	304.6	300.4	300.4	300.4	296.1	296.1	296.1
47.5°	300.4	296.1	296.1	291.8	291.8	287.5	287.5	287.5	283.2	283.2	283.2
50°	291.8	287.5	287.5	283.2	283.2	278.9	278.9	278.9	274.6	274.6	274.6
52.5°	278.9	274.6	274.6	274.6	270.3	266.0	266.0	266.0	261.7	261.7	261.7
55°	266.0	261.7	261.7	261.7	257.4	253.2	253.2	253.2	248.9	248.9	248.9
57.5°	248.9	244.6	244.6	240.3	240.3	240.3	240.3	240.3	236.0	236.0	236.0
60°	236.0	231.7	231.7	227.4	227.4	223.1	223.1	223.1	223.1	223.1	223.1
62.5°	223.1	218.8	214.5	210.3	214.5	214.5	214.5	214.5	210.3	210.3	210.3
65°	210.3	206.0	201.7	197.4	197.4	197.4	197.4	197.4	197.4	197.4	197.4
67.5°	193.1	188.8	184.5	180.2	184.5	184.5	184.5	184.5	184.5	184.5	184.5
70°	175.9	171.6	171.6	167.3	167.3	163.1	163.1	167.3	167.3	167.3	167.3
72.5°	158.8	154.5	154.5	150.2	150.2	150.2	150.2	150.2	150.2	150.2	150.2
75°	141.6	137.3	137.3	133.0	133.0	133.0	133.0	133.0	133.0	133.0	133.0
77.5°	120.1	115.9	115.9	115.9	115.9	115.9	115.9	120.1	120.1	120.1	120.1
80°	103.0	98.7	98.7	98.7	98.7	98.7	98.7	98.7	98.7	98.7	98.7
82.5°	81.5	77.2	77.2	77.2	77.2	77.2	77.2	77.2	77.2	77.2	77.2
85°	60.1	55.8	55.8	55.8	60.1	60.1	60.1	60.1	60.1	60.1	60.1
87.5°	38.6	34.3	34.3	34.3	38.6	38.6	38.6	38.6	34.3	34.3	34.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	2703.2	2703.2	2703.2	2698.9	2694.6	2690.3	2686.1	2698.9	2707.5	2720.4	2729.0
5°	2196.9	2205.5	2209.8	2222.6	2235.5	2248.4	2261.3	2269.8	2278.4	2282.7	2291.3
7.5°	1656.3	1677.7	1694.9	1712.0	1729.2	1742.1	1759.2	1772.1	1785.0	1797.9	1810.7
10°	1257.2	1265.8	1270.1	1287.2	1300.1	1317.3	1330.2	1343.0	1355.9	1364.5	1377.4
12.5°	1021.2	1012.6	1008.3	1008.3	1008.3	1008.3	1008.3	1016.9	1025.5	1034.1	1042.7
15°	823.8	819.5	815.3	811.0	806.7	798.1	793.8	802.4	811.0	819.5	828.1
17.5°	690.8	690.8	690.8	686.5	682.2	678.0	673.7	678.0	682.2	682.2	686.5
20°	592.1	596.4	600.7	605.0	605.0	609.3	609.3	613.6	617.9	617.9	622.2
22.5°	532.1	536.4	536.4	536.4	540.6	540.6	540.6	544.9	549.2	553.5	557.8
25°	484.9	484.9	480.6	480.6	484.9	484.9	484.9	484.9	489.2	489.2	489.2
27.5°	459.1	454.8	454.8	454.8	454.8	450.5	450.5	450.5	450.5	450.5	450.5
30°	446.2	442.0	437.7	433.4	433.4	429.1	424.8	424.8	424.8	424.8	424.8
32.5°	442.0	433.4	424.8	420.5	420.5	416.2	411.9	407.6	407.6	403.3	399.0
35°	394.8	390.5	390.5	386.2	381.9	377.6	373.3	373.3	373.3	369.0	369.0
37.5°	343.3	347.6	347.6	347.6	351.8	351.8	351.8	351.8	356.1	356.1	356.1
40°	321.8	321.8	321.8	326.1	330.4	330.4	334.7	334.7	339.0	339.0	339.0
42.5°	304.6	300.4	300.4	304.6	304.6	308.9	308.9	313.2	317.5	317.5	321.8
45°	296.1	291.8	291.8	291.8	291.8	287.5	287.5	291.8	296.1	300.4	304.6
47.5°	278.9	278.9	274.6	274.6	274.6	274.6	274.6	274.6	278.9	278.9	278.9
50°	270.3	270.3	266.0	266.0	266.0	266.0	266.0	266.0	266.0	266.0	266.0
52.5°	261.7	257.4	257.4	257.4	257.4	253.2	253.2	253.2	253.2	253.2	253.2
55°	248.9	244.6	244.6	244.6	244.6	244.6	244.6	244.6	248.9	248.9	248.9
57.5°	236.0	231.7	231.7	231.7	236.0	236.0	236.0	236.0	240.3	240.3	240.3
60°	223.1	223.1	223.1	223.1	223.1	223.1	223.1	227.4	227.4	231.7	231.7
62.5°	210.3	210.3	210.3	210.3	214.5	214.5	214.5	214.5	218.8	218.8	218.8
65°	197.4	197.4	197.4	197.4	201.7	201.7	201.7	201.7	201.7	201.7	201.7
67.5°	184.5	184.5	184.5	184.5	184.5	184.5	184.5	188.8	188.8	193.1	193.1
70°	167.3	163.1	163.1	167.3	167.3	171.6	171.6	175.9	175.9	180.2	180.2
72.5°	150.2	150.2	150.2	150.2	150.2	150.2	150.2	154.5	158.8	158.8	163.1
75°	133.0	133.0	133.0	133.0	137.3	137.3	137.3	141.6	141.6	145.9	145.9
77.5°	120.1	115.9	115.9	115.9	120.1	120.1	120.1	124.4	124.4	128.7	128.7
80°	98.7	98.7	98.7	98.7	103.0	103.0	103.0	103.0	107.3	107.3	107.3
82.5°	81.5	81.5	81.5	81.5	81.5	81.5	81.5	81.5	85.8	85.8	85.8
85°	60.1	60.1	60.1	60.1	64.4	64.4	64.4	64.4	64.4	64.4	64.4
87.5°	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6	42.9	42.9	42.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	2729.0	2729.0	2729.0	2729.0	2737.5	2741.8	2750.4	2754.7	2750.4	2746.1	2737.5
5°	2295.6	2299.9	2299.9	2304.2	2304.2	2304.2	2304.2	2304.2	2312.8	2321.3	2329.9
7.5°	1815.0	1819.3	1823.6	1827.9	1827.9	1827.9	1823.6	1823.6	1827.9	1827.9	1832.2
10°	1390.2	1407.4	1420.3	1433.1	1424.6	1411.7	1403.1	1390.2	1390.2	1390.2	1385.9
12.5°	1051.3	1055.5	1064.1	1068.4	1064.1	1064.1	1059.8	1055.5	1059.8	1068.4	1072.7
15°	832.4	832.4	836.7	836.7	841.0	845.3	845.3	849.6	858.2	862.5	871.0
17.5°	690.8	695.1	695.1	699.4	699.4	703.7	703.7	703.7	712.3	720.9	733.7
20°	622.2	622.2	622.2	622.2	622.2	617.9	617.9	613.6	617.9	626.5	630.8
22.5°	557.8	562.1	562.1	562.1	557.8	553.5	544.9	540.6	540.6	544.9	544.9
25°	489.2	484.9	484.9	480.6	480.6	484.9	484.9	484.9	489.2	489.2	493.4
27.5°	450.5	446.2	446.2	442.0	442.0	446.2	446.2	446.2	446.2	446.2	446.2
30°	420.5	420.5	416.2	411.9	416.2	416.2	420.5	420.5	424.8	424.8	429.1
32.5°	399.0	394.8	394.8	390.5	394.8	394.8	399.0	399.0	403.3	407.6	407.6
35°	369.0	369.0	369.0	369.0	369.0	369.0	364.7	364.7	364.7	364.7	364.7
37.5°	351.8	351.8	347.6	343.3	343.3	343.3	343.3	343.3	339.0	334.7	330.4
40°	339.0	334.7	334.7	330.4	326.1	326.1	321.8	317.5	317.5	313.2	313.2
42.5°	321.8	317.5	317.5	313.2	308.9	308.9	304.6	300.4	300.4	300.4	296.1
45°	300.4	300.4	296.1	291.8	291.8	291.8	287.5	287.5	287.5	287.5	283.2
47.5°	278.9	278.9	274.6	274.6	274.6	274.6	270.3	270.3	270.3	270.3	270.3
50°	266.0	266.0	266.0	266.0	266.0	266.0	261.7	261.7	261.7	261.7	261.7
52.5°	253.2	253.2	253.2	253.2	253.2	253.2	253.2	253.2	253.2	253.2	253.2
55°	248.9	248.9	248.9	248.9	248.9	248.9	244.6	244.6	244.6	248.9	248.9
57.5°	240.3	240.3	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0
60°	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7
62.5°	218.8	218.8	218.8	218.8	218.8	223.1	223.1	223.1	223.1	223.1	218.8
65°	201.7	206.0	206.0	206.0	206.0	206.0	206.0	206.0	206.0	206.0	206.0
67.5°	193.1	193.1	193.1	193.1	193.1	193.1	193.1	193.1	193.1	193.1	193.1
70°	180.2	180.2	175.9	175.9	175.9	180.2	180.2	180.2	180.2	180.2	180.2
72.5°	163.1	163.1	163.1	163.1	163.1	163.1	163.1	163.1	163.1	167.3	167.3
75°	145.9	145.9	145.9	145.9	145.9	145.9	145.9	145.9	145.9	145.9	145.9
77.5°	128.7	128.7	124.4	124.4	124.4	128.7	128.7	128.7	128.7	133.0	133.0
80°	107.3	107.3	107.3	107.3	107.3	107.3	107.3	107.3	107.3	111.6	111.6
82.5°	85.8	85.8	85.8	85.8	85.8	85.8	85.8	85.8	85.8	90.1	90.1
85°	64.4	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.7	72.9	72.9
87.5°	42.9	42.9	42.9	42.9	42.9	42.9	38.6	38.6	38.6	38.6	34.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	2733.3	2737.5	2741.8	2741.8	2746.1	2750.4	2750.4	2767.6	2784.7	2793.3	2801.9
5°	2338.5	2334.2	2334.2	2329.9	2325.6	2338.5	2351.4	2377.1	2402.9	2407.2	2415.7
7.5°	1832.2	1836.5	1840.8	1840.8	1845.1	1832.2	1815.0	1819.3	1823.6	1845.1	1862.2
10°	1385.9	1390.2	1394.5	1394.5	1398.8	1394.5	1385.9	1398.8	1411.7	1428.8	1450.3
12.5°	1077.0	1089.9	1102.7	1111.3	1124.2	1132.8	1137.1	1154.2	1167.1	1188.6	1210.0
15°	879.6	888.2	896.8	905.4	913.9	922.5	931.1	948.3	965.4	991.2	1016.9
17.5°	742.3	742.3	746.6	746.6	746.6	755.2	763.8	772.3	776.6	802.4	828.1
20°	635.0	630.8	626.5	622.2	617.9	626.5	630.8	635.0	639.3	656.5	669.4
22.5°	544.9	544.9	549.2	549.2	549.2	544.9	536.4	540.6	540.6	549.2	562.1
25°	493.4	493.4	493.4	489.2	489.2	493.4	497.7	497.7	493.4	497.7	502.0
27.5°	446.2	450.5	450.5	454.8	454.8	459.1	459.1	459.1	459.1	463.4	467.7
30°	429.1	429.1	433.4	433.4	433.4	437.7	442.0	442.0	442.0	446.2	454.8
32.5°	411.9	416.2	420.5	424.8	429.1	433.4	433.4	437.7	437.7	442.0	446.2
35°	364.7	360.4	360.4	356.1	351.8	351.8	351.8	351.8	347.6	351.8	351.8
37.5°	326.1	326.1	326.1	321.8	321.8	326.1	326.1	326.1	326.1	330.4	330.4
40°	308.9	308.9	308.9	308.9	308.9	308.9	308.9	313.2	313.2	317.5	321.8
42.5°	296.1	296.1	296.1	296.1	296.1	300.4	300.4	300.4	300.4	304.6	304.6
45°	283.2	283.2	283.2	283.2	283.2	283.2	283.2	287.5	287.5	291.8	296.1
47.5°	270.3	270.3	270.3	270.3	270.3	274.6	278.9	278.9	278.9	283.2	283.2
50°	261.7	261.7	261.7	261.7	261.7	266.0	266.0	270.3	270.3	274.6	278.9
52.5°	253.2	253.2	253.2	253.2	253.2	257.4	257.4	261.7	261.7	266.0	270.3
55°	248.9	248.9	248.9	244.6	244.6	248.9	248.9	253.2	253.2	257.4	257.4
57.5°	236.0	236.0	236.0	236.0	236.0	236.0	236.0	240.3	240.3	244.6	248.9
60°	231.7	231.7	227.4	227.4	223.1	227.4	227.4	231.7	231.7	236.0	236.0
62.5°	218.8	218.8	218.8	214.5	214.5	218.8	218.8	218.8	218.8	223.1	227.4
65°	206.0	206.0	206.0	201.7	201.7	206.0	206.0	206.0	206.0	210.3	214.5
67.5°	193.1	193.1	193.1	188.8	188.8	188.8	188.8	193.1	193.1	197.4	201.7
70°	180.2	180.2	180.2	175.9	175.9	175.9	171.6	175.9	180.2	184.5	184.5
72.5°	167.3	167.3	167.3	163.1	163.1	163.1	158.8	163.1	163.1	167.3	167.3
75°	145.9	145.9	145.9	145.9	145.9	145.9	141.6	141.6	141.6	145.9	145.9
77.5°	133.0	133.0	133.0	128.7	128.7	128.7	124.4	124.4	124.4	128.7	128.7
80°	111.6	111.6	111.6	107.3	107.3	107.3	103.0	103.0	103.0	107.3	107.3
82.5°	90.1	90.1	90.1	85.8	85.8	85.8	81.5	81.5	81.5	85.8	85.8
85°	72.9	72.9	72.9	72.9	72.9	72.9	68.7	68.7	68.7	72.9	77.2
87.5°	34.3	34.3	38.6	38.6	38.6	38.6	34.3	34.3	30.0	30.0	34.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	2810.5	2819.1	2840.5	2857.7	2879.1	2896.3	2909.2	2926.3	2939.2	2952.1	2960.7
5°	2420.0	2424.3	2445.8	2467.2	2484.4	2505.8	2535.9	2565.9	2595.9	2626.0	2647.4
7.5°	1883.7	1900.8	1926.6	1956.6	1982.4	2008.1	2038.1	2072.5	2102.5	2132.5	2162.6
10°	1467.5	1484.6	1510.4	1536.1	1557.6	1583.3	1617.6	1652.0	1686.3	1720.6	1754.9
12.5°	1231.5	1252.9	1283.0	1313.0	1338.7	1368.8	1411.7	1450.3	1493.2	1531.8	1574.7
15°	1038.4	1064.1	1102.7	1145.6	1184.3	1222.9	1265.8	1308.7	1347.3	1390.2	1433.1
17.5°	853.9	879.6	913.9	952.6	986.9	1021.2	1072.7	1119.9	1171.4	1218.6	1265.8
20°	686.5	699.4	733.7	768.1	802.4	836.7	875.3	913.9	952.6	991.2	1051.3
22.5°	570.7	579.3	596.4	609.3	626.5	639.3	678.0	716.6	750.9	789.5	845.3
25°	502.0	506.3	519.2	527.8	540.6	549.2	575.0	596.4	622.2	643.6	695.1
27.5°	467.7	472.0	476.3	480.6	484.9	489.2	506.3	523.5	536.4	553.5	600.7
30°	459.1	463.4	476.3	484.9	497.7	506.3	514.9	523.5	532.1	540.6	570.7
32.5°	450.5	454.8	454.8	450.5	450.5	446.2	454.8	459.1	467.7	472.0	497.7
35°	356.1	356.1	360.4	364.7	369.0	373.3	386.2	394.8	407.6	416.2	437.7
37.5°	334.7	334.7	339.0	347.6	351.8	356.1	364.7	373.3	381.9	390.5	411.9
40°	321.8	326.1	330.4	334.7	339.0	343.3	351.8	356.1	364.7	369.0	386.2
42.5°	308.9	308.9	313.2	321.8	326.1	330.4	339.0	343.3	351.8	356.1	373.3
45°	300.4	304.6	308.9	313.2	313.2	317.5	326.1	334.7	339.0	347.6	364.7
47.5°	287.5	287.5	296.1	300.4	308.9	313.2	321.8	326.1	334.7	339.0	356.1
50°	278.9	283.2	291.8	296.1	304.6	308.9	321.8	330.4	343.3	351.8	360.4
52.5°	270.3	274.6	283.2	287.5	296.1	300.4	317.5	334.7	347.6	364.7	364.7
55°	261.7	261.7	270.3	283.2	291.8	300.4	308.9	321.8	330.4	339.0	339.0
57.5°	248.9	253.2	261.7	274.6	283.2	291.8	300.4	308.9	313.2	321.8	317.5
60°	240.3	240.3	253.2	266.0	278.9	291.8	291.8	291.8	287.5	287.5	287.5
62.5°	227.4	231.7	248.9	270.3	287.5	304.6	291.8	278.9	266.0	253.2	257.4
65°	218.8	223.1	231.7	244.6	253.2	261.7	253.2	248.9	240.3	231.7	236.0
67.5°	201.7	206.0	210.3	210.3	214.5	214.5	214.5	214.5	214.5	214.5	218.8
70°	188.8	188.8	188.8	193.1	193.1	193.1	193.1	193.1	193.1	193.1	197.4
72.5°	171.6	171.6	171.6	171.6	171.6	171.6	171.6	171.6	171.6	171.6	175.9
75°	150.2	150.2	150.2	150.2	150.2	150.2	150.2	150.2	150.2	150.2	154.5
77.5°	133.0	133.0	133.0	133.0	133.0	133.0	133.0	133.0	128.7	128.7	133.0
80°	111.6	111.6	111.6	111.6	107.3	107.3	107.3	107.3	107.3	107.3	111.6
82.5°	90.1	90.1	90.1	90.1	85.8	85.8	85.8	85.8	81.5	81.5	85.8
85°	81.5	85.8	85.8	90.1	90.1	90.1	85.8	81.5	77.2	72.9	72.9
87.5°	34.3	34.3	34.3	34.3	30.0	30.0	30.0	30.0	30.0	30.0	30.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	2973.5	2982.1	2990.7	3003.6	3020.7	3033.6	3046.5	3072.2	3102.3	3128.0	3153.8
5°	2668.9	2690.3	2711.8	2737.5	2763.3	2784.7	2810.5	2862.0	2913.5	2960.7	3012.2
7.5°	2188.3	2218.4	2244.1	2287.0	2325.6	2368.5	2407.2	2471.5	2531.6	2595.9	2656.0
10°	1789.3	1823.6	1857.9	1913.7	1973.8	2029.6	2085.3	2136.8	2192.6	2244.1	2295.6
12.5°	1617.6	1656.3	1699.2	1733.5	1772.1	1806.4	1840.8	1900.8	1960.9	2021.0	2081.0
15°	1476.0	1519.0	1561.9	1604.8	1643.4	1686.3	1724.9	1776.4	1832.2	1883.7	1935.2
17.5°	1313.0	1355.9	1403.1	1450.3	1497.5	1544.7	1591.9	1664.8	1737.8	1806.4	1879.4
20°	1107.0	1167.1	1222.9	1287.2	1351.6	1416.0	1480.3	1557.6	1634.8	1707.7	1785.0
22.5°	901.1	956.9	1012.6	1089.9	1167.1	1240.0	1317.3	1420.3	1519.0	1621.9	1720.6
25°	750.9	802.4	853.9	939.7	1021.2	1107.0	1188.6	1313.0	1433.1	1557.6	1677.7
27.5°	647.9	695.1	742.3	832.4	922.5	1008.3	1098.5	1235.8	1368.8	1506.1	1639.1
30°	600.7	630.8	660.8	746.6	832.4	913.9	999.8	1132.8	1265.8	1398.8	1531.8
32.5°	523.5	549.2	575.0	652.2	729.4	802.4	879.6	1016.9	1149.9	1287.2	1420.3
35°	463.4	484.9	506.3	579.3	647.9	720.9	789.5	926.8	1064.1	1201.4	1338.7
37.5°	429.1	450.5	467.7	532.1	600.7	665.1	729.4	866.7	999.8	1137.1	1270.1
40°	403.3	416.2	433.4	497.7	557.8	622.2	682.2	806.7	935.4	1059.8	1184.3
42.5°	386.2	403.3	416.2	472.0	532.1	587.8	643.6	763.8	883.9	999.8	1119.9
45°	381.9	399.0	416.2	463.4	510.6	553.5	600.7	716.6	832.4	948.3	1064.1
47.5°	373.3	386.2	403.3	442.0	476.3	514.9	549.2	665.1	780.9	892.5	1008.3
50°	369.0	373.3	381.9	416.2	450.5	484.9	519.2	635.0	750.9	866.7	982.6
52.5°	364.7	364.7	364.7	394.8	424.8	450.5	480.6	596.4	716.6	832.4	948.3
55°	339.0	334.7	334.7	364.7	390.5	420.5	446.2	562.1	678.0	789.5	905.4
57.5°	313.2	308.9	304.6	330.4	356.1	381.9	407.6	523.5	643.6	759.5	875.3
60°	287.5	283.2	283.2	308.9	330.4	356.1	377.6	497.7	613.6	733.7	849.6
62.5°	257.4	261.7	261.7	283.2	308.9	330.4	351.8	472.0	596.4	716.6	836.7
65°	236.0	240.3	240.3	266.0	291.8	317.5	343.3	459.1	579.3	695.1	811.0
67.5°	218.8	223.1	223.1	253.2	278.9	308.9	334.7	437.7	544.9	647.9	750.9
70°	201.7	201.7	206.0	236.0	266.0	296.1	326.1	416.2	506.3	592.1	682.2
72.5°	180.2	184.5	188.8	218.8	244.6	274.6	300.4	381.9	463.4	544.9	626.5
75°	158.8	163.1	167.3	193.1	218.8	244.6	270.3	347.6	420.5	497.7	570.7
77.5°	141.6	145.9	150.2	171.6	193.1	214.5	236.0	291.8	351.8	407.6	463.4
80°	115.9	115.9	120.1	137.3	154.5	167.3	184.5	223.1	261.7	296.1	334.7
82.5°	85.8	90.1	90.1	103.0	111.6	124.4	133.0	154.5	171.6	193.1	210.3
85°	72.9	68.7	68.7	77.2	81.5	90.1	94.4	107.3	115.9	128.7	137.3
87.5°	30.0	25.7	25.7	30.0	38.6	42.9	47.2	47.2	51.5	51.5	51.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	3166.6	3175.2	3188.1	3196.7	3218.1	3235.3	3256.7	3273.9	3286.8	3308.2	3299.6
5°	3050.8	3089.4	3128.0	3166.6	3196.7	3226.7	3252.4	3282.5	3316.8	3381.2	3398.3
7.5°	2707.5	2759.0	2806.2	2857.7	2917.8	2977.8	3037.9	3098.0	3153.8	3235.3	3286.8
10°	2368.5	2441.5	2510.1	2583.1	2638.9	2694.6	2746.1	2801.9	2879.1	2960.7	3055.1
12.5°	2154.0	2226.9	2299.9	2372.8	2454.4	2531.6	2613.1	2690.3	2763.3	2827.7	2934.9
15°	2012.4	2093.9	2171.2	2248.4	2347.1	2441.5	2540.2	2634.6	2741.8	2827.7	2900.6
17.5°	1978.1	2076.8	2171.2	2269.8	2372.8	2475.8	2578.8	2681.8	2789.0	2917.8	3012.2
20°	1918.0	2051.0	2184.0	2317.0	2450.1	2578.8	2711.8	2840.5	2982.1	3136.6	3179.5
22.5°	1883.7	2042.4	2205.5	2364.2	2544.5	2729.0	2909.2	3089.4	3239.6	3355.4	3484.1
25°	1879.4	2076.8	2278.4	2475.8	2703.2	2926.3	3153.8	3376.9	3570.0	3685.8	3788.8
27.5°	1875.1	2115.4	2351.4	2587.4	2866.3	3140.9	3419.8	3694.4	3874.6	4042.0	4127.8
30°	1823.6	2111.1	2402.9	2690.3	3003.6	3316.8	3630.0	3943.3	4127.8	4243.6	4286.5
32.5°	1759.2	2098.2	2437.2	2776.2	3132.3	3488.4	3840.3	4196.4	4342.3	4441.0	4406.7
35°	1707.7	2081.0	2450.1	2819.1	3196.7	3578.5	3956.1	4333.7	4544.0	4681.3	4625.5
37.5°	1660.5	2051.0	2441.5	2831.9	3273.9	3715.9	4157.8	4599.8	4801.4	4947.3	4883.0
40°	1604.8	2021.0	2441.5	2857.7	3364.0	3866.0	4372.3	4874.4	5136.1	5260.5	5161.9
42.5°	1557.6	1990.9	2428.6	2862.0	3402.6	3943.3	4483.9	5024.6	5316.3	5492.3	5367.8
45°	1497.5	1930.9	2360.0	2793.3	3389.8	3986.2	4578.3	5174.7	5513.7	5651.0	5479.4
47.5°	1433.1	1862.2	2287.0	2711.8	3346.8	3981.9	4616.9	5252.0	5565.2	5728.2	5569.5
50°	1411.7	1840.8	2265.6	2694.6	3381.2	4072.0	4758.5	5445.1	5672.5	5805.5	5595.2
52.5°	1407.4	1862.2	2321.3	2776.2	3467.0	4153.5	4844.3	5530.9	5715.4	5857.0	5668.2
55°	1394.5	1888.0	2377.1	2866.3	3587.1	4312.3	5033.1	5754.0	5938.5	6041.5	5899.9
57.5°	1407.4	1939.5	2467.2	2999.3	3741.6	4483.9	5226.2	5968.5	6191.7	6264.6	6234.6
60°	1416.0	1982.4	2544.5	3110.8	3836.0	4561.1	5286.3	6011.4	6243.1	6423.4	6457.7
62.5°	1394.5	1952.3	2505.8	3063.6	3720.1	4376.6	5033.1	5689.6	6071.5	6337.5	6492.0
65°	1330.2	1845.1	2364.2	2879.1	3484.1	4093.4	4698.5	5303.5	5706.8	6101.6	6226.0
67.5°	1188.6	1626.2	2063.9	2501.6	3029.3	3557.1	4080.6	4608.3	5114.7	5496.5	5668.2
70°	1029.8	1373.1	1720.6	2063.9	2544.5	3025.0	3505.6	3986.2	4432.4	4852.9	5016.0
72.5°	896.8	1162.8	1433.1	1699.2	2042.4	2381.4	2724.7	3063.6	3591.4	4011.9	4170.7
75°	763.8	956.9	1145.6	1338.7	1574.7	1810.7	2042.4	2278.4	2651.7	3029.3	3188.1
77.5°	587.8	716.6	841.0	965.4	1128.5	1287.2	1450.3	1609.1	1870.8	2154.0	2235.5
80°	407.6	480.6	549.2	622.2	750.9	879.6	1008.3	1137.1	1308.7	1467.5	1591.9
82.5°	253.2	300.4	343.3	386.2	489.2	592.1	690.8	793.8	862.5	871.0	995.5
85°	163.1	193.1	218.8	244.6	304.6	369.0	429.1	489.2	437.7	407.6	484.9
87.5°	64.4	81.5	94.4	107.3	103.0	98.7	94.4	90.1	77.2	68.7	85.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	3308.2	3321.1	3334.0	3342.6	3355.4	3359.7	3364.0	3364.0	3368.3	3372.6	3381.2
5°	3467.0	3492.7	3518.5	3539.9	3565.7	3587.1	3604.3	3625.7	3642.9	3642.9	3638.6
7.5°	3334.0	3398.3	3462.7	3527.1	3591.4	3638.6	3681.5	3728.7	3771.6	3780.2	3788.8
10°	3158.0	3226.7	3291.1	3359.7	3424.1	3497.0	3565.7	3634.3	3707.3	3720.1	3737.3
12.5°	2995.0	3076.5	3158.0	3235.3	3316.8	3368.3	3419.8	3467.0	3518.5	3552.8	3587.1
15°	2990.7	3059.4	3128.0	3192.4	3261.0	3291.1	3321.1	3346.8	3376.9	3376.9	3381.2
17.5°	3089.4	3132.3	3175.2	3213.8	3256.7	3261.0	3269.6	3273.9	3278.2	3265.3	3252.4
20°	3282.5	3299.6	3316.8	3334.0	3351.1	3321.1	3295.4	3265.3	3235.3	3201.0	3170.9
22.5°	3565.7	3527.1	3488.4	3449.8	3411.2	3359.7	3303.9	3252.4	3196.7	3153.8	3110.8
25°	3831.7	3784.5	3737.3	3690.1	3642.9	3531.3	3419.8	3303.9	3192.4	3145.2	3098.0
27.5°	4187.8	4114.9	4042.0	3969.0	3896.1	3745.9	3595.7	3445.5	3295.4	3213.8	3136.6
30°	4273.7	4192.1	4110.6	4024.8	3943.3	3797.4	3655.8	3509.9	3364.0	3269.6	3179.5
32.5°	4398.1	4303.7	4209.3	4114.9	4020.5	3878.9	3737.3	3591.4	3449.8	3364.0	3273.9
35°	4604.1	4496.8	4389.5	4278.0	4170.7	4024.8	3883.2	3737.3	3591.4	3492.7	3398.3
37.5°	4780.0	4655.5	4531.1	4406.7	4282.2	4153.5	4020.5	3891.8	3758.8	3660.1	3565.7
40°	4977.4	4840.0	4702.7	4569.7	4432.4	4312.3	4192.1	4067.7	3947.6	3870.3	3793.1
42.5°	5149.0	4981.6	4818.6	4655.5	4488.2	4406.7	4329.4	4247.9	4166.4	4127.8	4084.9
45°	5269.1	5114.7	4955.9	4801.4	4647.0	4586.9	4526.8	4466.7	4406.7	4445.3	4483.9
47.5°	5320.6	5196.2	5076.0	4955.9	4831.5	4852.9	4874.4	4891.5	4913.0	4964.5	5020.3
50°	5367.8	5299.2	5226.2	5157.6	5084.6	5166.2	5243.4	5324.9	5406.4	5513.7	5621.0
52.5°	5462.2	5423.6	5389.3	5350.7	5312.0	5453.6	5595.2	5736.8	5878.4	5998.6	6118.7
55°	5745.4	5715.4	5685.3	5651.0	5621.0	5822.6	6020.0	6221.7	6423.4	6547.8	6672.2
57.5°	6135.9	6118.7	6097.3	6080.1	6058.6	6256.0	6449.1	6642.2	6839.6	6959.7	7084.1
60°	6431.9	6436.2	6436.2	6440.5	6440.5	6590.7	6740.9	6895.4	7045.5	7148.5	7255.8
62.5°	6590.7	6582.1	6573.5	6565.0	6556.4	6680.8	6805.2	6929.7	7054.1	7131.3	7208.6
65°	6419.1	6466.3	6513.5	6560.7	6607.9	6625.0	6637.9	6655.1	6667.9	6715.1	6762.3
67.5°	5844.1	5938.5	6028.6	6123.0	6213.1	6148.8	6088.7	6024.3	5960.0	5972.8	5981.4
70°	5204.8	5312.0	5423.6	5530.9	5638.1	5488.0	5337.8	5183.3	5033.1	4981.6	4930.2
72.5°	4389.5	4483.9	4582.6	4677.0	4771.4	4586.9	4406.7	4222.2	4037.7	3947.6	3857.5
75°	3355.4	3467.0	3582.8	3694.4	3806.0	3600.0	3389.8	3183.8	2973.5	2913.5	2857.7
77.5°	2445.8	2578.8	2711.8	2844.8	2977.8	2793.3	2608.8	2420.0	2235.5	2201.2	2166.9
80°	1780.7	1883.7	1982.4	2085.3	2184.0	2076.8	1969.5	1862.2	1754.9	1750.7	1746.4
82.5°	1201.4	1291.5	1377.4	1467.5	1553.3	1510.4	1471.8	1428.8	1385.9	1428.8	1476.0
85°	617.9	742.3	871.0	995.5	1119.9	1107.0	1098.5	1085.6	1072.7	1128.5	1180.0
87.5°	124.4	231.7	339.0	442.0	549.2	523.5	497.7	467.7	442.0	459.1	472.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	3385.5	3389.8	3389.8	3389.8	3389.8	3389.8	3381.2	3376.9	3368.3	3359.7	3346.8
5°	3638.6	3634.3	3617.2	3600.0	3578.5	3561.4	3548.5	3531.3	3518.5	3501.3	3475.6
7.5°	3797.4	3806.0	3775.9	3750.2	3720.1	3690.1	3660.1	3630.0	3600.0	3570.0	3509.9
10°	3750.2	3763.1	3745.9	3728.7	3707.3	3690.1	3655.8	3617.2	3582.8	3544.2	3471.3
12.5°	3617.2	3651.5	3642.9	3634.3	3625.7	3617.2	3595.7	3570.0	3548.5	3522.8	3441.2
15°	3381.2	3381.2	3385.5	3389.8	3389.8	3394.0	3398.3	3402.6	3406.9	3411.2	3364.0
17.5°	3239.6	3226.7	3226.7	3226.7	3226.7	3226.7	3243.9	3265.3	3282.5	3299.6	3286.8
20°	3136.6	3106.6	3102.3	3102.3	3098.0	3093.7	3123.7	3158.0	3188.1	3218.1	3235.3
22.5°	3067.9	3025.0	3020.7	3016.4	3012.2	3007.9	3046.5	3085.1	3123.7	3162.3	3222.4
25°	3050.8	3003.6	3007.9	3012.2	3012.2	3016.4	3046.5	3076.5	3106.6	3136.6	3239.6
27.5°	3055.1	2977.8	2982.1	2986.4	2986.4	2990.7	3037.9	3080.8	3128.0	3170.9	3299.6
30°	3085.1	2995.0	2986.4	2977.8	2969.2	2960.7	3025.0	3089.4	3153.8	3218.1	3316.8
32.5°	3188.1	3102.3	3080.8	3059.4	3037.9	3016.4	3093.7	3166.6	3243.9	3316.8	3398.3
35°	3299.6	3205.2	3196.7	3188.1	3175.2	3166.6	3235.3	3308.2	3376.9	3445.5	3518.5
37.5°	3467.0	3372.6	3364.0	3351.1	3342.6	3329.7	3406.9	3479.9	3557.1	3630.0	3694.4
40°	3715.9	3638.6	3634.3	3634.3	3630.0	3625.7	3685.8	3750.2	3810.3	3870.3	3913.2
42.5°	4046.2	4007.6	4020.5	4037.7	4050.5	4063.4	4110.6	4162.1	4209.3	4256.5	4243.6
45°	4522.5	4561.1	4565.4	4569.7	4574.0	4578.3	4591.2	4608.3	4621.2	4634.1	4582.6
47.5°	5071.8	5123.2	5149.0	5174.7	5196.2	5221.9	5204.8	5183.3	5166.2	5144.7	5016.0
50°	5724.0	5831.2	5826.9	5822.6	5814.1	5809.8	5775.4	5741.1	5702.5	5668.2	5479.4
52.5°	6238.9	6359.0	6380.5	6401.9	6423.4	6444.8	6380.5	6316.1	6247.4	6183.1	5947.1
55°	6792.4	6916.8	6921.1	6925.4	6925.4	6929.7	6839.6	6749.5	6655.1	6565.0	6320.4
57.5°	7204.3	7324.4	7311.6	7303.0	7290.1	7277.2	7170.0	7062.7	6955.4	6848.2	6603.6
60°	7358.8	7461.7	7436.0	7410.3	7380.2	7354.5	7272.9	7191.4	7105.6	7024.1	6788.1
62.5°	7285.8	7363.1	7324.4	7290.1	7251.5	7212.9	7109.9	7002.6	6899.6	6792.4	6620.7
65°	6805.2	6852.4	6801.0	6753.8	6706.6	6655.1	6569.3	6483.4	6393.3	6307.5	6191.7
67.5°	5994.3	6002.9	5998.6	5994.3	5990.0	5985.7	5861.3	5736.8	5608.1	5483.7	5475.1
70°	4883.0	4831.5	4840.0	4852.9	4861.5	4870.1	4775.7	4685.6	4591.2	4496.8	4539.7
72.5°	3767.3	3677.2	3698.7	3724.4	3745.9	3767.3	3690.1	3617.2	3539.9	3462.7	3522.8
75°	2797.6	2741.8	2763.3	2789.0	2810.5	2831.9	2801.9	2771.9	2737.5	2707.5	2763.3
77.5°	2132.5	2098.2	2102.5	2102.5	2106.8	2106.8	2111.1	2119.7	2124.0	2128.2	2188.3
80°	1737.8	1733.5	1729.2	1724.9	1716.3	1712.0	1754.9	1797.9	1840.8	1883.7	1913.7
82.5°	1519.0	1561.9	1536.1	1514.7	1488.9	1463.2	1501.8	1540.4	1579.0	1617.6	1604.8
85°	1235.8	1287.2	1240.0	1192.8	1141.4	1094.2	1128.5	1158.5	1192.8	1222.9	1205.7
87.5°	489.2	502.0	424.8	351.8	274.6	197.4	313.2	424.8	540.6	652.2	669.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062

CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4	3089.4
2.5°	3334.0	3316.8	3303.9	3299.6	3291.1	3286.8	3278.2	3269.6	3256.7	3248.2	3235.3
5°	3445.5	3419.8	3389.8	3346.8	3308.2	3265.3	3222.4	3183.8	3145.2	3102.3	3063.6
7.5°	3449.8	3389.8	3329.7	3273.9	3213.8	3158.0	3098.0	3046.5	2990.7	2934.9	2883.4
10°	3402.6	3329.7	3256.7	3183.8	3115.1	3042.2	2969.2	2909.2	2844.8	2780.5	2720.4
12.5°	3364.0	3282.5	3201.0	3115.1	3033.6	2947.8	2862.0	2801.9	2741.8	2681.8	2621.7
15°	3316.8	3265.3	3218.1	3140.9	3063.6	2986.4	2909.2	2827.7	2750.4	2668.9	2587.4
17.5°	3278.2	3265.3	3252.4	3201.0	3149.5	3093.7	3042.2	2960.7	2879.1	2793.3	2711.8
20°	3256.7	3273.9	3291.1	3265.3	3239.6	3209.5	3183.8	3123.7	3063.6	2999.3	2939.2
22.5°	3282.5	3346.8	3406.9	3411.2	3419.8	3424.1	3428.4	3372.6	3316.8	3256.7	3201.0
25°	3342.6	3445.5	3548.5	3604.3	3660.1	3720.1	3775.9	3741.6	3707.3	3672.9	3638.6
27.5°	3424.1	3552.8	3681.5	3763.1	3840.3	3921.8	4003.3	3999.0	3994.8	3986.2	3981.9
30°	3411.2	3509.9	3608.6	3707.3	3806.0	3904.6	4003.3	4054.8	4102.0	4153.5	4205.0
32.5°	3484.1	3565.7	3651.5	3754.5	3857.5	3964.7	4067.7	4175.0	4278.0	4385.2	4492.5
35°	3595.7	3668.7	3745.9	3857.5	3973.3	4084.9	4200.7	4329.4	4462.5	4595.5	4724.2
37.5°	3763.1	3827.4	3896.1	3990.5	4089.2	4183.6	4282.2	4471.0	4659.8	4852.9	5041.7
40°	3956.1	3999.0	4042.0	4132.1	4222.2	4312.3	4402.4	4638.4	4874.4	5110.4	5346.4
42.5°	4235.0	4222.2	4209.3	4282.2	4359.5	4432.4	4509.7	4724.2	4938.7	5153.3	5367.8
45°	4531.1	4479.6	4428.1	4462.5	4501.1	4535.4	4574.0	4792.8	5011.7	5234.8	5453.6
47.5°	4887.2	4758.5	4629.8	4599.8	4569.7	4535.4	4505.4	4741.4	4977.4	5217.6	5453.6
50°	5290.6	5097.5	4908.7	4831.5	4749.9	4672.7	4591.2	4784.3	4981.6	5179.0	5372.1
52.5°	5711.1	5470.8	5234.8	5114.7	4994.5	4870.1	4749.9	4913.0	5080.3	5247.7	5410.7
55°	6071.5	5826.9	5578.1	5436.5	5294.9	5153.3	5011.7	5174.7	5337.8	5500.8	5663.9
57.5°	6359.0	6114.4	5869.8	5736.8	5599.5	5466.5	5329.2	5483.7	5642.4	5801.2	5955.7
60°	6556.4	6320.4	6084.4	5955.7	5826.9	5698.2	5569.5	5754.0	5938.5	6127.3	6311.8
62.5°	6453.4	6281.8	6110.1	6054.4	5998.6	5938.5	5882.7	6058.6	6230.3	6406.2	6582.1
65°	6075.8	5960.0	5844.1	5899.9	5960.0	6015.7	6075.8	6191.7	6307.5	6427.7	6543.5
67.5°	5462.2	5453.6	5440.8	5565.2	5689.6	5818.4	5942.8	6020.0	6093.0	6170.2	6247.4
70°	4582.6	4629.8	4672.7	4887.2	5101.8	5316.3	5530.9	5560.9	5590.9	5621.0	5651.0
72.5°	3587.1	3647.2	3711.6	3994.8	4273.7	4556.9	4840.0	4822.9	4805.7	4784.3	4767.1
75°	2823.4	2879.1	2939.2	3201.0	3462.7	3724.4	3986.2	3913.2	3844.6	3771.6	3698.7
77.5°	2252.7	2312.8	2377.1	2621.7	2866.3	3115.1	3359.7	3183.8	3007.9	2831.9	2656.0
80°	1939.5	1969.5	1995.2	2162.6	2325.6	2493.0	2660.3	2480.1	2295.6	2111.1	1930.9
82.5°	1591.9	1574.7	1561.9	1660.5	1759.2	1857.9	1956.6	1785.0	1613.3	1437.4	1265.8
85°	1188.6	1171.4	1154.2	1205.7	1257.2	1313.0	1364.5	1167.1	969.7	768.1	570.7
87.5°	690.8	708.0	725.1	780.9	836.7	896.8	952.6	750.9	549.2	343.3	141.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676062  
 CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676062  
CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	3089.4	3089.4
2.5°	3209.5	3188.1
5°	3033.6	3003.6
7.5°	2840.5	2801.9
10°	2664.6	2613.1
12.5°	2553.0	2488.7
15°	2510.1	2432.9
17.5°	2638.9	2565.9
20°	2836.2	2737.5
22.5°	3076.5	2956.4
25°	3492.7	3346.8
27.5°	3831.7	3681.5
30°	4042.0	3878.9
32.5°	4273.7	4059.1
35°	4513.9	4308.0
37.5°	4805.7	4574.0
40°	5106.1	4865.8
42.5°	5209.1	5054.6
45°	5307.7	5161.9
47.5°	5329.2	5209.1
50°	5350.7	5333.5
52.5°	5410.7	5406.4
55°	5668.2	5672.5
57.5°	5985.7	6011.4
60°	6277.5	6247.4
62.5°	6427.7	6273.2
65°	6324.7	6110.1
67.5°	6015.7	5784.0
70°	5337.8	5024.6
72.5°	4492.5	4217.9
75°	3462.7	3231.0
77.5°	2462.9	2269.8
80°	1733.5	1540.4
82.5°	1111.3	956.9
85°	502.0	437.7
87.5°	141.6	137.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676062  
CATALOG NUMBER: CCW-SA-2E-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)