

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P676070

Luminaire Tested: **CCW-SA-2B-850-U-SLR**

Issue Date: 04/25/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P676070  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/25/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCW-SA-2B-850-U-SLR  
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @450mA w/  
SLR distribution lens  
Light Source: (32) 5000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5001.1 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2

Input Watts (W): 46  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 7.1 fc  
 Type IV - Short - N/A

REPORT NUMBER: P676070  
CATALOG NUMBER: CCW-SA-2B-850-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P676070

CATALOG NUMBER: CCW-SA-2B-850-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1029.0	0.0	1029.0
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	3972.1	0.0	3972.1
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	5001.1	0.0	5001.1
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.1	2.5
10°-20°	262.0	5.2
20°-30°	383.3	7.7
30°-40°	540.0	10.8
40°-50°	742.1	14.8
50°-60°	1011.5	20.2
60°-70°	1107.1	22.1
70°-80°	639.3	12.8
80°-90°	191.6	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5001.1	100.0
0°-180°	5001.1	100.0



REPORT NUMBER: P676070


CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	513.6	10.3			
FM (30°-60°)	1825.1	36.5			
FH (60°-80°)	1470.6	29.4			G1/1800
FVH (80°-90°)	162.8	3.3			G2/225
BL (0°-30°)	255.8	5.1	B1/500		
BM (30°-60°)	468.6	9.4	B1/1000		
BH (60°-80°)	275.8	5.5	B1/500		G1/500
BVH (80°-90°)	28.9	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**

Type IV Short





REPORT NUMBER: P676070

CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1648.1	1639.2	1632.5	1625.9	1617.0	1610.4	1601.5	1592.6	1581.5	1572.6	1561.6
5°	1552.7	1526.1	1499.4	1483.9	1466.2	1450.6	1432.9	1412.9	1393.0	1370.8	1350.8
7.5°	1448.4	1415.2	1381.9	1355.3	1326.4	1299.8	1271.0	1246.6	1222.2	1197.8	1173.4
10°	1350.8	1319.8	1288.7	1255.5	1220.0	1186.7	1151.2	1117.9	1084.7	1051.4	1018.1
12.5°	1286.5	1248.8	1213.3	1175.6	1140.1	1102.4	1064.7	1033.6	1002.6	969.3	938.3
15°	1257.7	1222.2	1188.9	1151.2	1113.5	1075.8	1038.1	1002.6	969.3	933.8	898.3
17.5°	1326.4	1275.4	1224.4	1175.6	1126.8	1078.0	1029.2	984.8	940.5	896.1	851.8
20°	1415.2	1350.8	1288.7	1228.8	1166.7	1106.8	1044.7	982.6	920.5	858.4	796.3
22.5°	1528.3	1455.1	1384.1	1306.5	1226.6	1149.0	1069.1	991.5	913.9	834.0	756.4
25°	1730.1	1643.6	1557.1	1446.2	1333.1	1222.2	1109.1	1007.0	907.2	805.2	703.1
27.5°	1903.1	1785.6	1670.2	1537.2	1404.1	1271.0	1137.9	1020.3	905.0	787.4	669.9
30°	2005.2	1889.8	1774.5	1612.6	1452.9	1290.9	1129.0	998.2	869.5	738.6	607.8
32.5°	2098.3	1969.7	1841.0	1663.6	1483.9	1306.5	1126.8	982.6	840.7	696.5	552.3
35°	2227.0	2085.0	1945.3	1739.0	1532.7	1326.4	1120.1	971.5	820.7	672.1	521.3
37.5°	2364.5	2189.3	2016.3	1787.8	1559.3	1330.9	1102.4	956.0	809.6	663.2	516.8
40°	2515.3	2302.4	2091.7	1838.8	1588.2	1335.3	1082.4	936.0	789.6	641.0	494.6
42.5°	2612.9	2382.3	2151.6	1878.7	1608.1	1335.3	1062.5	918.3	774.1	627.7	483.5
45°	2668.4	2444.4	2222.6	1927.5	1632.5	1337.5	1042.5	900.6	758.6	614.4	472.5
47.5°	2692.8	2484.3	2275.8	1965.3	1656.9	1346.4	1035.9	891.7	745.3	601.1	454.7
50°	2757.1	2573.0	2388.9	2056.2	1725.7	1393.0	1060.3	905.0	751.9	596.7	441.4
52.5°	2794.8	2637.3	2479.9	2138.3	1796.7	1455.1	1113.5	940.5	767.5	594.5	421.4
55°	2932.3	2781.5	2630.7	2266.9	1900.9	1537.2	1171.2	980.4	789.6	596.7	405.9
57.5°	3107.6	2947.9	2790.4	2397.8	2005.2	1612.6	1220.0	1015.9	809.6	605.5	399.3
60°	3229.6	3074.3	2921.3	2504.3	2085.0	1668.0	1248.8	1035.9	822.9	607.8	394.8
62.5°	3242.9	3043.3	2845.8	2439.9	2034.0	1625.9	1220.0	1013.7	807.4	598.9	392.6
65°	3158.6	2925.7	2692.8	2304.6	1916.5	1528.3	1140.1	951.6	763.0	572.3	383.7
67.5°	2990.0	2717.2	2444.4	2089.5	1734.6	1379.7	1024.8	862.8	703.1	541.2	379.3
70°	2597.4	2357.9	2120.5	1812.2	1506.1	1197.8	889.5	756.4	625.5	492.4	359.3
72.5°	2180.4	1956.4	1734.6	1483.9	1235.5	984.8	734.2	634.4	534.6	432.5	332.7
75°	1670.2	1501.7	1335.3	1149.0	962.7	774.1	587.8	514.6	441.4	368.2	295.0
77.5°	1173.4	1082.4	993.7	854.0	714.2	574.5	434.8	386.0	337.2	288.4	239.6
80°	796.3	745.3	696.5	596.7	496.9	394.8	295.0	264.0	230.7	199.6	166.4
82.5°	494.6	492.4	488.0	419.2	350.5	281.7	212.9	186.3	161.9	135.3	108.7
85°	226.2	264.0	299.4	261.7	224.0	186.3	148.6	130.9	113.1	93.2	75.4
87.5°	71.0	86.5	99.8	95.4	88.7	84.3	77.6	66.5	55.5	44.4	33.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1552.7	1546.0	1537.2	1528.3	1517.2	1508.3	1497.2	1486.1	1483.9	1479.5	1477.3
5°	1337.5	1324.2	1308.7	1295.4	1282.1	1266.5	1253.2	1237.7	1226.6	1213.3	1202.2
7.5°	1149.0	1126.8	1102.4	1078.0	1055.8	1033.6	1009.2	987.1	976.0	964.9	953.8
10°	998.2	976.0	956.0	933.8	918.3	905.0	889.5	873.9	860.6	847.3	834.0
12.5°	922.7	907.2	891.7	876.2	858.4	842.9	825.1	807.4	791.9	778.6	763.0
15°	876.2	854.0	829.6	807.4	783.0	760.8	736.4	712.0	694.3	678.7	661.0
17.5°	820.7	787.4	756.4	723.1	696.5	669.9	641.0	614.4	594.5	572.3	552.3
20°	758.6	720.9	681.0	643.3	612.2	583.4	552.3	521.3	499.1	474.7	452.5
22.5°	705.4	656.6	605.5	554.5	521.3	488.0	452.5	419.2	399.3	377.1	357.1
25°	647.7	594.5	539.0	483.5	450.3	414.8	381.5	346.0	330.5	317.2	301.7
27.5°	616.6	563.4	507.9	454.7	423.7	390.4	359.3	326.1	315.0	301.7	290.6
30°	554.5	503.5	450.3	397.0	374.9	354.9	332.7	310.5	306.1	303.9	299.4
32.5°	499.1	445.8	392.6	339.4	319.4	299.4	279.5	259.5	257.3	252.9	250.6
35°	470.2	419.2	366.0	315.0	297.2	277.3	259.5	239.6	235.1	228.5	224.0
37.5°	463.6	410.4	354.9	301.7	283.9	266.2	246.2	228.5	224.0	219.6	215.2
40°	445.8	394.8	346.0	295.0	277.3	259.5	239.6	221.8	217.4	212.9	208.5
42.5°	432.5	383.7	332.7	281.7	266.2	250.6	232.9	217.4	212.9	208.5	201.8
45°	421.4	370.4	317.2	266.2	255.1	244.0	230.7	219.6	215.2	208.5	204.1
47.5°	403.7	354.9	303.9	252.9	241.8	232.9	221.8	210.7	206.3	201.8	197.4
50°	390.4	339.4	288.4	237.3	228.5	219.6	210.7	201.8	201.8	204.1	204.1
52.5°	372.6	323.8	275.0	226.2	217.4	208.5	199.6	190.8	193.0	195.2	197.4
55°	357.1	310.5	261.7	212.9	204.1	195.2	184.1	175.2	177.4	179.7	181.9
57.5°	350.5	301.7	252.9	204.1	195.2	184.1	175.2	164.1	164.1	164.1	164.1
60°	346.0	295.0	246.2	195.2	184.1	175.2	164.1	153.0	150.8	150.8	148.6
62.5°	343.8	292.8	244.0	193.0	179.7	168.6	155.3	142.0	139.7	137.5	135.3
65°	334.9	288.4	239.6	190.8	175.2	161.9	146.4	130.9	128.7	128.7	126.4
67.5°	332.7	283.9	237.3	188.5	173.0	155.3	139.7	122.0	119.8	117.6	115.3
70°	315.0	272.8	228.5	184.1	166.4	150.8	133.1	115.3	113.1	108.7	106.5
72.5°	292.8	255.1	215.2	175.2	157.5	139.7	122.0	104.3	102.0	99.8	95.4
75°	259.5	224.0	188.5	153.0	137.5	124.2	108.7	93.2	90.9	88.7	84.3
77.5°	212.9	184.1	157.5	128.7	117.6	106.5	95.4	84.3	82.1	79.9	75.4
80°	150.8	133.1	117.6	99.8	93.2	84.3	77.6	68.8	68.8	66.5	66.5
82.5°	99.8	90.9	82.1	73.2	68.8	64.3	59.9	55.5	55.5	53.2	53.2
85°	71.0	66.5	59.9	55.5	53.2	48.8	46.6	42.1	42.1	42.1	42.1
87.5°	33.3	33.3	31.1	31.1	28.8	28.8	26.6	24.4	24.4	24.4	24.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1472.8	1466.2	1459.5	1450.6	1444.0	1435.1	1424.0	1415.2	1404.1	1404.1	1401.8
5°	1188.9	1182.3	1175.6	1166.7	1160.1	1151.2	1144.5	1135.7	1126.8	1126.8	1124.6
7.5°	942.7	929.4	916.1	900.6	887.2	878.4	869.5	858.4	849.5	842.9	836.2
10°	820.7	807.4	791.9	778.6	763.0	751.9	740.9	727.5	716.5	707.6	698.7
12.5°	747.5	732.0	716.5	700.9	685.4	669.9	656.6	641.0	625.5	614.4	603.3
15°	643.3	627.7	612.2	596.7	581.1	563.4	545.7	525.7	507.9	499.1	492.4
17.5°	530.1	514.6	496.9	481.3	463.6	450.3	437.0	423.7	410.4	401.5	394.8
20°	428.1	410.4	392.6	374.9	357.1	348.2	339.4	330.5	321.6	315.0	310.5
22.5°	334.9	323.8	315.0	303.9	292.8	286.1	281.7	275.0	268.4	268.4	268.4
25°	286.1	279.5	275.0	268.4	261.7	259.5	257.3	252.9	250.6	248.4	248.4
27.5°	277.3	270.6	264.0	257.3	250.6	248.4	246.2	241.8	239.6	239.6	239.6
30°	295.0	292.8	290.6	288.4	286.1	281.7	275.0	270.6	264.0	259.5	255.1
32.5°	246.2	244.0	244.0	241.8	239.6	244.0	246.2	250.6	252.9	255.1	257.3
35°	217.4	212.9	208.5	204.1	199.6	197.4	195.2	193.0	190.8	190.8	188.5
37.5°	210.7	206.3	201.8	197.4	193.0	190.8	188.5	186.3	184.1	184.1	181.9
40°	204.1	199.6	197.4	193.0	188.5	186.3	184.1	179.7	177.4	175.2	175.2
42.5°	197.4	195.2	190.8	188.5	184.1	181.9	179.7	175.2	173.0	170.8	168.6
45°	197.4	193.0	188.5	184.1	179.7	177.4	173.0	170.8	166.4	166.4	164.1
47.5°	193.0	188.5	184.1	179.7	175.2	173.0	168.6	166.4	161.9	159.7	157.5
50°	204.1	197.4	188.5	181.9	173.0	170.8	166.4	164.1	159.7	157.5	155.3
52.5°	199.6	193.0	184.1	177.4	168.6	164.1	161.9	157.5	153.0	150.8	148.6
55°	184.1	177.4	173.0	166.4	159.7	155.3	150.8	146.4	142.0	139.7	139.7
57.5°	164.1	161.9	159.7	157.5	155.3	150.8	146.4	139.7	135.3	133.1	130.9
60°	146.4	148.6	150.8	153.0	155.3	148.6	142.0	135.3	128.7	126.4	124.2
62.5°	133.1	137.5	142.0	144.2	148.6	142.0	135.3	128.7	122.0	119.8	117.6
65°	124.2	126.4	126.4	128.7	128.7	124.2	122.0	117.6	113.1	110.9	110.9
67.5°	113.1	113.1	113.1	110.9	110.9	108.7	108.7	106.5	104.3	102.0	102.0
70°	102.0	102.0	102.0	99.8	99.8	97.6	97.6	95.4	93.2	93.2	90.9
72.5°	93.2	93.2	90.9	90.9	88.7	88.7	88.7	86.5	86.5	84.3	84.3
75°	82.1	82.1	79.9	79.9	77.6	77.6	77.6	75.4	75.4	75.4	73.2
77.5°	73.2	73.2	71.0	71.0	68.8	68.8	68.8	66.5	66.5	64.3	64.3
80°	64.3	64.3	62.1	62.1	59.9	59.9	57.7	57.7	55.5	55.5	53.2
82.5°	51.0	51.0	51.0	51.0	51.0	48.8	48.8	46.6	44.4	44.4	42.1
85°	42.1	42.1	42.1	39.9	39.9	39.9	37.7	37.7	35.5	33.3	33.3
87.5°	24.4	24.4	24.4	22.2	22.2	22.2	22.2	22.2	22.2	22.2	20.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1401.8	1399.6	1390.8	1381.9	1390.8	1399.6	1399.6	1399.6	1397.4	1397.4	1397.4
5°	1124.6	1122.4	1117.9	1113.5	1113.5	1111.3	1115.7	1120.1	1124.6	1129.0	1133.5
7.5°	827.4	820.7	814.0	807.4	811.8	814.0	820.7	825.1	831.8	836.2	847.3
10°	689.8	681.0	674.3	667.7	663.2	658.8	654.3	652.1	647.7	643.3	647.7
12.5°	590.0	578.9	567.8	554.5	552.3	550.1	545.7	541.2	536.8	532.3	530.1
15°	483.5	474.7	470.2	463.6	454.7	445.8	441.4	439.2	434.8	430.3	428.1
17.5°	386.0	377.1	370.4	363.8	361.6	357.1	357.1	357.1	357.1	357.1	357.1
20°	303.9	297.2	297.2	295.0	295.0	292.8	295.0	297.2	297.2	299.4	301.7
22.5°	266.2	266.2	264.0	261.7	264.0	264.0	266.2	268.4	270.6	272.8	275.0
25°	246.2	244.0	246.2	248.4	248.4	248.4	250.6	250.6	252.9	252.9	252.9
27.5°	237.3	237.3	239.6	239.6	241.8	241.8	241.8	239.6	239.6	237.3	237.3
30°	250.6	246.2	246.2	246.2	244.0	241.8	239.6	239.6	237.3	235.1	232.9
32.5°	259.5	261.7	259.5	255.1	252.9	248.4	246.2	241.8	239.6	235.1	230.7
35°	188.5	186.3	190.8	193.0	195.2	197.4	199.6	201.8	201.8	204.1	204.1
37.5°	181.9	179.7	179.7	177.4	177.4	177.4	177.4	177.4	175.2	175.2	177.4
40°	173.0	170.8	170.8	168.6	168.6	166.4	166.4	166.4	166.4	166.4	166.4
42.5°	166.4	164.1	164.1	164.1	164.1	161.9	161.9	159.7	159.7	157.5	157.5
45°	164.1	161.9	159.7	157.5	157.5	155.3	155.3	155.3	153.0	153.0	153.0
47.5°	155.3	153.0	153.0	150.8	150.8	148.6	148.6	148.6	146.4	146.4	146.4
50°	150.8	148.6	148.6	146.4	146.4	144.2	144.2	144.2	142.0	142.0	142.0
52.5°	144.2	142.0	142.0	142.0	139.7	137.5	137.5	137.5	135.3	135.3	135.3
55°	137.5	135.3	135.3	135.3	133.1	130.9	130.9	130.9	128.7	128.7	128.7
57.5°	128.7	126.4	126.4	124.2	124.2	124.2	124.2	124.2	122.0	122.0	122.0
60°	122.0	119.8	119.8	117.6	117.6	115.3	115.3	115.3	115.3	115.3	115.3
62.5°	115.3	113.1	110.9	108.7	110.9	110.9	110.9	110.9	108.7	108.7	108.7
65°	108.7	106.5	104.3	102.0	102.0	102.0	102.0	102.0	102.0	102.0	102.0
67.5°	99.8	97.6	95.4	93.2	95.4	95.4	95.4	95.4	95.4	95.4	95.4
70°	90.9	88.7	88.7	86.5	86.5	84.3	84.3	86.5	86.5	86.5	86.5
72.5°	82.1	79.9	79.9	77.6	77.6	77.6	77.6	77.6	77.6	77.6	77.6
75°	73.2	71.0	71.0	68.8	68.8	68.8	68.8	68.8	68.8	68.8	68.8
77.5°	62.1	59.9	59.9	59.9	59.9	59.9	59.9	62.1	62.1	62.1	62.1
80°	53.2	51.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0
82.5°	42.1	39.9	39.9	39.9	39.9	39.9	39.9	39.9	39.9	39.9	39.9
85°	31.1	28.8	28.8	28.8	31.1	31.1	31.1	31.1	31.1	31.1	31.1
87.5°	20.0	17.7	17.7	17.7	20.0	20.0	20.0	20.0	17.7	17.7	17.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1397.4	1397.4	1397.4	1395.2	1393.0	1390.8	1388.5	1395.2	1399.6	1406.3	1410.7
5°	1135.7	1140.1	1142.3	1149.0	1155.6	1162.3	1168.9	1173.4	1177.8	1180.0	1184.5
7.5°	856.2	867.3	876.2	885.0	893.9	900.6	909.4	916.1	922.7	929.4	936.0
10°	649.9	654.3	656.6	665.4	672.1	681.0	687.6	694.3	700.9	705.4	712.0
12.5°	527.9	523.5	521.3	521.3	521.3	521.3	521.3	525.7	530.1	534.6	539.0
15°	425.9	423.7	421.4	419.2	417.0	412.6	410.4	414.8	419.2	423.7	428.1
17.5°	357.1	357.1	357.1	354.9	352.7	350.5	348.2	350.5	352.7	352.7	354.9
20°	306.1	308.3	310.5	312.8	312.8	315.0	315.0	317.2	319.4	319.4	321.6
22.5°	275.0	277.3	277.3	277.3	279.5	279.5	279.5	281.7	283.9	286.1	288.4
25°	250.6	250.6	248.4	248.4	250.6	250.6	250.6	250.6	252.9	252.9	252.9
27.5°	237.3	235.1	235.1	235.1	235.1	232.9	232.9	232.9	232.9	232.9	232.9
30°	230.7	228.5	226.2	224.0	224.0	221.8	219.6	219.6	219.6	219.6	219.6
32.5°	228.5	224.0	219.6	217.4	217.4	215.2	212.9	210.7	210.7	208.5	206.3
35°	204.1	201.8	201.8	199.6	197.4	195.2	193.0	193.0	193.0	190.8	190.8
37.5°	177.4	179.7	179.7	179.7	181.9	181.9	181.9	181.9	184.1	184.1	184.1
40°	166.4	166.4	166.4	168.6	170.8	170.8	173.0	173.0	175.2	175.2	175.2
42.5°	157.5	155.3	155.3	157.5	157.5	159.7	159.7	161.9	164.1	164.1	166.4
45°	153.0	150.8	150.8	150.8	150.8	148.6	148.6	150.8	153.0	155.3	157.5
47.5°	144.2	144.2	142.0	142.0	142.0	142.0	142.0	142.0	144.2	144.2	144.2
50°	139.7	139.7	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5
52.5°	135.3	133.1	133.1	133.1	133.1	130.9	130.9	130.9	130.9	130.9	130.9
55°	128.7	126.4	126.4	126.4	126.4	126.4	126.4	126.4	128.7	128.7	128.7
57.5°	122.0	119.8	119.8	119.8	122.0	122.0	122.0	122.0	124.2	124.2	124.2
60°	115.3	115.3	115.3	115.3	115.3	115.3	115.3	117.6	117.6	119.8	119.8
62.5°	108.7	108.7	108.7	108.7	110.9	110.9	110.9	110.9	113.1	113.1	113.1
65°	102.0	102.0	102.0	102.0	104.3	104.3	104.3	104.3	104.3	104.3	104.3
67.5°	95.4	95.4	95.4	95.4	95.4	95.4	95.4	97.6	97.6	99.8	99.8
70°	86.5	84.3	84.3	86.5	86.5	88.7	88.7	90.9	90.9	93.2	93.2
72.5°	77.6	77.6	77.6	77.6	77.6	77.6	77.6	79.9	82.1	82.1	84.3
75°	68.8	68.8	68.8	68.8	71.0	71.0	71.0	73.2	73.2	75.4	75.4
77.5°	62.1	59.9	59.9	59.9	62.1	62.1	62.1	64.3	64.3	66.5	66.5
80°	51.0	51.0	51.0	51.0	53.2	53.2	53.2	53.2	55.5	55.5	55.5
82.5°	42.1	42.1	42.1	42.1	42.1	42.1	42.1	42.1	44.4	44.4	44.4
85°	31.1	31.1	31.1	31.1	33.3	33.3	33.3	33.3	33.3	33.3	33.3
87.5°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	22.2	22.2	22.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1410.7	1410.7	1410.7	1410.7	1415.2	1417.4	1421.8	1424.0	1421.8	1419.6	1415.2
5°	1186.7	1188.9	1188.9	1191.1	1191.1	1191.1	1191.1	1191.1	1195.6	1200.0	1204.4
7.5°	938.3	940.5	942.7	944.9	944.9	944.9	942.7	942.7	944.9	944.9	947.1
10°	718.7	727.5	734.2	740.9	736.4	729.8	725.3	718.7	718.7	718.7	716.5
12.5°	543.4	545.7	550.1	552.3	550.1	550.1	547.9	545.7	547.9	552.3	554.5
15°	430.3	430.3	432.5	432.5	434.8	437.0	437.0	439.2	443.6	445.8	450.3
17.5°	357.1	359.3	359.3	361.6	361.6	363.8	363.8	363.8	368.2	372.6	379.3
20°	321.6	321.6	321.6	321.6	321.6	319.4	319.4	317.2	319.4	323.8	326.1
22.5°	288.4	290.6	290.6	290.6	288.4	286.1	281.7	279.5	279.5	281.7	281.7
25°	252.9	250.6	250.6	248.4	248.4	250.6	250.6	250.6	252.9	252.9	255.1
27.5°	232.9	230.7	230.7	228.5	228.5	230.7	230.7	230.7	230.7	230.7	230.7
30°	217.4	217.4	215.2	212.9	215.2	215.2	217.4	217.4	219.6	219.6	221.8
32.5°	206.3	204.1	204.1	201.8	204.1	204.1	206.3	206.3	208.5	210.7	210.7
35°	190.8	190.8	190.8	190.8	190.8	190.8	188.5	188.5	188.5	188.5	188.5
37.5°	181.9	181.9	179.7	177.4	177.4	177.4	177.4	177.4	175.2	173.0	170.8
40°	175.2	173.0	173.0	170.8	168.6	168.6	166.4	164.1	164.1	161.9	161.9
42.5°	166.4	164.1	164.1	161.9	159.7	159.7	157.5	155.3	155.3	155.3	153.0
45°	155.3	155.3	153.0	150.8	150.8	150.8	148.6	148.6	148.6	148.6	146.4
47.5°	144.2	144.2	142.0	142.0	142.0	142.0	139.7	139.7	139.7	139.7	139.7
50°	137.5	137.5	137.5	137.5	137.5	137.5	135.3	135.3	135.3	135.3	135.3
52.5°	130.9	130.9	130.9	130.9	130.9	130.9	130.9	130.9	130.9	130.9	130.9
55°	128.7	128.7	128.7	128.7	128.7	128.7	126.4	126.4	126.4	128.7	128.7
57.5°	124.2	124.2	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0
60°	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8
62.5°	113.1	113.1	113.1	113.1	113.1	115.3	115.3	115.3	115.3	115.3	113.1
65°	104.3	106.5	106.5	106.5	106.5	106.5	106.5	106.5	106.5	106.5	106.5
67.5°	99.8	99.8	99.8	99.8	99.8	99.8	99.8	99.8	99.8	99.8	99.8
70°	93.2	93.2	90.9	90.9	90.9	93.2	93.2	93.2	93.2	93.2	93.2
72.5°	84.3	84.3	84.3	84.3	84.3	84.3	84.3	84.3	84.3	86.5	86.5
75°	75.4	75.4	75.4	75.4	75.4	75.4	75.4	75.4	75.4	75.4	75.4
77.5°	66.5	66.5	64.3	64.3	64.3	66.5	66.5	66.5	66.5	68.8	68.8
80°	55.5	55.5	55.5	55.5	55.5	55.5	55.5	55.5	55.5	57.7	57.7
82.5°	44.4	44.4	44.4	44.4	44.4	44.4	44.4	44.4	44.4	46.6	46.6
85°	33.3	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5	37.7	37.7
87.5°	22.2	22.2	22.2	22.2	22.2	22.2	20.0	20.0	20.0	20.0	17.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1412.9	1415.2	1417.4	1417.4	1419.6	1421.8	1421.8	1430.7	1439.6	1444.0	1448.4
5°	1208.9	1206.7	1206.7	1204.4	1202.2	1208.9	1215.5	1228.8	1242.1	1244.4	1248.8
7.5°	947.1	949.4	951.6	951.6	953.8	947.1	938.3	940.5	942.7	953.8	962.7
10°	716.5	718.7	720.9	720.9	723.1	720.9	716.5	723.1	729.8	738.6	749.7
12.5°	556.7	563.4	570.1	574.5	581.1	585.6	587.8	596.7	603.3	614.4	625.5
15°	454.7	459.1	463.6	468.0	472.5	476.9	481.3	490.2	499.1	512.4	525.7
17.5°	383.7	383.7	386.0	386.0	386.0	390.4	394.8	399.3	401.5	414.8	428.1
20°	328.3	326.1	323.8	321.6	319.4	323.8	326.1	328.3	330.5	339.4	346.0
22.5°	281.7	281.7	283.9	283.9	283.9	281.7	277.3	279.5	279.5	283.9	290.6
25°	255.1	255.1	255.1	252.9	252.9	255.1	257.3	257.3	255.1	257.3	259.5
27.5°	230.7	232.9	232.9	235.1	235.1	237.3	237.3	237.3	237.3	239.6	241.8
30°	221.8	221.8	224.0	224.0	224.0	226.2	228.5	228.5	228.5	230.7	235.1
32.5°	212.9	215.2	217.4	219.6	221.8	224.0	224.0	226.2	226.2	228.5	230.7
35°	188.5	186.3	186.3	184.1	181.9	181.9	181.9	181.9	179.7	181.9	181.9
37.5°	168.6	168.6	168.6	166.4	166.4	168.6	168.6	168.6	168.6	170.8	170.8
40°	159.7	159.7	159.7	159.7	159.7	159.7	159.7	161.9	161.9	164.1	166.4
42.5°	153.0	153.0	153.0	153.0	153.0	155.3	155.3	155.3	155.3	157.5	157.5
45°	146.4	146.4	146.4	146.4	146.4	146.4	146.4	148.6	148.6	150.8	153.0
47.5°	139.7	139.7	139.7	139.7	139.7	142.0	144.2	144.2	144.2	146.4	146.4
50°	135.3	135.3	135.3	135.3	135.3	137.5	137.5	139.7	139.7	142.0	144.2
52.5°	130.9	130.9	130.9	130.9	130.9	133.1	133.1	135.3	135.3	137.5	139.7
55°	128.7	128.7	128.7	126.4	126.4	128.7	128.7	130.9	130.9	133.1	133.1
57.5°	122.0	122.0	122.0	122.0	122.0	122.0	122.0	124.2	124.2	126.4	128.7
60°	119.8	119.8	117.6	117.6	115.3	117.6	117.6	119.8	119.8	122.0	122.0
62.5°	113.1	113.1	113.1	110.9	110.9	113.1	113.1	113.1	113.1	115.3	117.6
65°	106.5	106.5	106.5	104.3	104.3	106.5	106.5	106.5	106.5	108.7	110.9
67.5°	99.8	99.8	99.8	97.6	97.6	97.6	97.6	99.8	99.8	102.0	104.3
70°	93.2	93.2	93.2	90.9	90.9	90.9	88.7	90.9	93.2	95.4	95.4
72.5°	86.5	86.5	86.5	84.3	84.3	84.3	82.1	84.3	84.3	86.5	86.5
75°	75.4	75.4	75.4	75.4	75.4	75.4	73.2	73.2	73.2	75.4	75.4
77.5°	68.8	68.8	68.8	66.5	66.5	66.5	64.3	64.3	64.3	66.5	66.5
80°	57.7	57.7	57.7	55.5	55.5	55.5	53.2	53.2	53.2	55.5	55.5
82.5°	46.6	46.6	46.6	44.4	44.4	44.4	42.1	42.1	42.1	44.4	44.4
85°	37.7	37.7	37.7	37.7	37.7	37.7	35.5	35.5	35.5	37.7	39.9
87.5°	17.7	17.7	20.0	20.0	20.0	20.0	17.7	17.7	15.5	15.5	17.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1452.9	1457.3	1468.4	1477.3	1488.4	1497.2	1503.9	1512.8	1519.4	1526.1	1530.5
5°	1251.0	1253.2	1264.3	1275.4	1284.3	1295.4	1310.9	1326.4	1342.0	1357.5	1368.6
7.5°	973.8	982.6	995.9	1011.5	1024.8	1038.1	1053.6	1071.3	1086.9	1102.4	1117.9
10°	758.6	767.5	780.8	794.1	805.2	818.5	836.2	854.0	871.7	889.5	907.2
12.5°	636.6	647.7	663.2	678.7	692.1	707.6	729.8	749.7	771.9	791.9	814.0
15°	536.8	550.1	570.1	592.2	612.2	632.2	654.3	676.5	696.5	718.7	740.9
17.5°	441.4	454.7	472.5	492.4	510.2	527.9	554.5	578.9	605.5	629.9	654.3
20°	354.9	361.6	379.3	397.0	414.8	432.5	452.5	472.5	492.4	512.4	543.4
22.5°	295.0	299.4	308.3	315.0	323.8	330.5	350.5	370.4	388.2	408.1	437.0
25°	259.5	261.7	268.4	272.8	279.5	283.9	297.2	308.3	321.6	332.7	359.3
27.5°	241.8	244.0	246.2	248.4	250.6	252.9	261.7	270.6	277.3	286.1	310.5
30°	237.3	239.6	246.2	250.6	257.3	261.7	266.2	270.6	275.0	279.5	295.0
32.5°	232.9	235.1	235.1	232.9	232.9	230.7	235.1	237.3	241.8	244.0	257.3
35°	184.1	184.1	186.3	188.5	190.8	193.0	199.6	204.1	210.7	215.2	226.2
37.5°	173.0	173.0	175.2	179.7	181.9	184.1	188.5	193.0	197.4	201.8	212.9
40°	166.4	168.6	170.8	173.0	175.2	177.4	181.9	184.1	188.5	190.8	199.6
42.5°	159.7	159.7	161.9	166.4	168.6	170.8	175.2	177.4	181.9	184.1	193.0
45°	155.3	157.5	159.7	161.9	161.9	164.1	168.6	173.0	175.2	179.7	188.5
47.5°	148.6	148.6	153.0	155.3	159.7	161.9	166.4	168.6	173.0	175.2	184.1
50°	144.2	146.4	150.8	153.0	157.5	159.7	166.4	170.8	177.4	181.9	186.3
52.5°	139.7	142.0	146.4	148.6	153.0	155.3	164.1	173.0	179.7	188.5	188.5
55°	135.3	135.3	139.7	146.4	150.8	155.3	159.7	166.4	170.8	175.2	175.2
57.5°	128.7	130.9	135.3	142.0	146.4	150.8	155.3	159.7	161.9	166.4	164.1
60°	124.2	124.2	130.9	137.5	144.2	150.8	150.8	150.8	148.6	148.6	148.6
62.5°	117.6	119.8	128.7	139.7	148.6	157.5	150.8	144.2	137.5	130.9	133.1
65°	113.1	115.3	119.8	126.4	130.9	135.3	130.9	128.7	124.2	119.8	122.0
67.5°	104.3	106.5	108.7	108.7	110.9	110.9	110.9	110.9	110.9	110.9	113.1
70°	97.6	97.6	97.6	99.8	99.8	99.8	99.8	99.8	99.8	99.8	102.0
72.5°	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	90.9
75°	77.6	77.6	77.6	77.6	77.6	77.6	77.6	77.6	77.6	77.6	79.9
77.5°	68.8	68.8	68.8	68.8	68.8	68.8	68.8	68.8	66.5	66.5	68.8
80°	57.7	57.7	57.7	57.7	55.5	55.5	55.5	55.5	55.5	55.5	57.7
82.5°	46.6	46.6	46.6	46.6	44.4	44.4	44.4	44.4	42.1	42.1	44.4
85°	42.1	44.4	44.4	46.6	46.6	46.6	44.4	42.1	39.9	37.7	37.7
87.5°	17.7	17.7	17.7	17.7	15.5	15.5	15.5	15.5	15.5	15.5	15.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1537.2	1541.6	1546.0	1552.7	1561.6	1568.2	1574.9	1588.2	1603.7	1617.0	1630.3
5°	1379.7	1390.8	1401.8	1415.2	1428.5	1439.6	1452.9	1479.5	1506.1	1530.5	1557.1
7.5°	1131.2	1146.8	1160.1	1182.3	1202.2	1224.4	1244.4	1277.6	1308.7	1342.0	1373.0
10°	925.0	942.7	960.4	989.3	1020.3	1049.2	1078.0	1104.6	1133.5	1160.1	1186.7
12.5°	836.2	856.2	878.4	896.1	916.1	933.8	951.6	982.6	1013.7	1044.7	1075.8
15°	763.0	785.2	807.4	829.6	849.5	871.7	891.7	918.3	947.1	973.8	1000.4
17.5°	678.7	700.9	725.3	749.7	774.1	798.5	822.9	860.6	898.3	933.8	971.5
20°	572.3	603.3	632.2	665.4	698.7	732.0	765.2	805.2	845.1	882.8	922.7
22.5°	465.8	494.6	523.5	563.4	603.3	641.0	681.0	734.2	785.2	838.4	889.5
25°	388.2	414.8	441.4	485.8	527.9	572.3	614.4	678.7	740.9	805.2	867.3
27.5°	334.9	359.3	383.7	430.3	476.9	521.3	567.8	638.8	707.6	778.6	847.3
30°	310.5	326.1	341.6	386.0	430.3	472.5	516.8	585.6	654.3	723.1	791.9
32.5°	270.6	283.9	297.2	337.2	377.1	414.8	454.7	525.7	594.5	665.4	734.2
35°	239.6	250.6	261.7	299.4	334.9	372.6	408.1	479.1	550.1	621.1	692.1
37.5°	221.8	232.9	241.8	275.0	310.5	343.8	377.1	448.1	516.8	587.8	656.6
40°	208.5	215.2	224.0	257.3	288.4	321.6	352.7	417.0	483.5	547.9	612.2
42.5°	199.6	208.5	215.2	244.0	275.0	303.9	332.7	394.8	456.9	516.8	578.9
45°	197.4	206.3	215.2	239.6	264.0	286.1	310.5	370.4	430.3	490.2	550.1
47.5°	193.0	199.6	208.5	228.5	246.2	266.2	283.9	343.8	403.7	461.4	521.3
50°	190.8	193.0	197.4	215.2	232.9	250.6	268.4	328.3	388.2	448.1	507.9
52.5°	188.5	188.5	188.5	204.1	219.6	232.9	248.4	308.3	370.4	430.3	490.2
55°	175.2	173.0	173.0	188.5	201.8	217.4	230.7	290.6	350.5	408.1	468.0
57.5°	161.9	159.7	157.5	170.8	184.1	197.4	210.7	270.6	332.7	392.6	452.5
60°	148.6	146.4	146.4	159.7	170.8	184.1	195.2	257.3	317.2	379.3	439.2
62.5°	133.1	135.3	135.3	146.4	159.7	170.8	181.9	244.0	308.3	370.4	432.5
65°	122.0	124.2	124.2	137.5	150.8	164.1	177.4	237.3	299.4	359.3	419.2
67.5°	113.1	115.3	115.3	130.9	144.2	159.7	173.0	226.2	281.7	334.9	388.2
70°	104.3	104.3	106.5	122.0	137.5	153.0	168.6	215.2	261.7	306.1	352.7
72.5°	93.2	95.4	97.6	113.1	126.4	142.0	155.3	197.4	239.6	281.7	323.8
75°	82.1	84.3	86.5	99.8	113.1	126.4	139.7	179.7	217.4	257.3	295.0
77.5°	73.2	75.4	77.6	88.7	99.8	110.9	122.0	150.8	181.9	210.7	239.6
80°	59.9	59.9	62.1	71.0	79.9	86.5	95.4	115.3	135.3	153.0	173.0
82.5°	44.4	46.6	46.6	53.2	57.7	64.3	68.8	79.9	88.7	99.8	108.7
85°	37.7	35.5	35.5	39.9	42.1	46.6	48.8	55.5	59.9	66.5	71.0
87.5°	15.5	13.3	13.3	15.5	20.0	22.2	24.4	24.4	26.6	26.6	26.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676070

CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1637.0	1641.4	1648.1	1652.5	1663.6	1672.5	1683.5	1692.4	1699.1	1710.2	1705.7
5°	1577.1	1597.0	1617.0	1637.0	1652.5	1668.0	1681.3	1696.9	1714.6	1747.9	1756.7
7.5°	1399.6	1426.2	1450.6	1477.3	1508.3	1539.4	1570.4	1601.5	1630.3	1672.5	1699.1
10°	1224.4	1262.1	1297.6	1335.3	1364.1	1393.0	1419.6	1448.4	1488.4	1530.5	1579.3
12.5°	1113.5	1151.2	1188.9	1226.6	1268.8	1308.7	1350.8	1390.8	1428.5	1461.7	1517.2
15°	1040.3	1082.4	1122.4	1162.3	1213.3	1262.1	1313.1	1361.9	1417.4	1461.7	1499.4
17.5°	1022.6	1073.6	1122.4	1173.4	1226.6	1279.9	1333.1	1386.3	1441.8	1508.3	1557.1
20°	991.5	1060.3	1129.0	1197.8	1266.5	1333.1	1401.8	1468.4	1541.6	1621.4	1643.6
22.5°	973.8	1055.8	1140.1	1222.2	1315.3	1410.7	1503.9	1597.0	1674.7	1734.6	1801.1
25°	971.5	1073.6	1177.8	1279.9	1397.4	1512.8	1630.3	1745.7	1845.5	1905.4	1958.6
27.5°	969.3	1093.5	1215.5	1337.5	1481.7	1623.7	1767.8	1909.8	2003.0	2089.5	2133.8
30°	942.7	1091.3	1242.1	1390.8	1552.7	1714.6	1876.5	2038.4	2133.8	2193.7	2215.9
32.5°	909.4	1084.7	1259.9	1435.1	1619.2	1803.3	1985.2	2169.3	2244.7	2295.7	2278.0
35°	882.8	1075.8	1266.5	1457.3	1652.5	1849.9	2045.1	2240.3	2349.0	2420.0	2391.1
37.5°	858.4	1060.3	1262.1	1464.0	1692.4	1920.9	2149.4	2377.8	2482.1	2557.5	2524.2
40°	829.6	1044.7	1262.1	1477.3	1739.0	1998.5	2260.3	2519.8	2655.1	2719.4	2668.4
42.5°	805.2	1029.2	1255.5	1479.5	1759.0	2038.4	2317.9	2597.4	2748.2	2839.2	2774.9
45°	774.1	998.2	1220.0	1444.0	1752.3	2060.6	2366.7	2675.0	2850.3	2921.3	2832.5
47.5°	740.9	962.7	1182.3	1401.8	1730.1	2058.4	2386.7	2715.0	2876.9	2961.2	2879.1
50°	729.8	951.6	1171.2	1393.0	1747.9	2105.0	2459.9	2814.8	2932.3	3001.1	2892.4
52.5°	727.5	962.7	1200.0	1435.1	1792.2	2147.1	2504.3	2859.2	2954.5	3027.7	2930.1
55°	720.9	976.0	1228.8	1481.7	1854.3	2229.2	2601.8	2974.5	3069.9	3123.1	3049.9
57.5°	727.5	1002.6	1275.4	1550.5	1934.2	2317.9	2701.7	3085.4	3200.7	3238.4	3222.9
60°	732.0	1024.8	1315.3	1608.1	1983.0	2357.9	2732.7	3107.6	3227.4	3320.5	3338.3
62.5°	720.9	1009.2	1295.4	1583.7	1923.1	2262.5	2601.8	2941.2	3138.6	3276.2	3356.0
65°	687.6	953.8	1222.2	1488.4	1801.1	2116.1	2428.8	2741.6	2950.1	3154.2	3218.5
67.5°	614.4	840.7	1066.9	1293.2	1566.0	1838.8	2109.4	2382.3	2644.0	2841.4	2930.1
70°	532.3	709.8	889.5	1066.9	1315.3	1563.8	1812.2	2060.6	2291.3	2508.7	2593.0
72.5°	463.6	601.1	740.9	878.4	1055.8	1231.1	1408.5	1583.7	1856.6	2073.9	2156.0
75°	394.8	494.6	592.2	692.1	814.0	936.0	1055.8	1177.8	1370.8	1566.0	1648.1
77.5°	303.9	370.4	434.8	499.1	583.4	665.4	749.7	831.8	967.1	1113.5	1155.6
80°	210.7	248.4	283.9	321.6	388.2	454.7	521.3	587.8	676.5	758.6	822.9
82.5°	130.9	155.3	177.4	199.6	252.9	306.1	357.1	410.4	445.8	450.3	514.6
85°	84.3	99.8	113.1	126.4	157.5	190.8	221.8	252.9	226.2	210.7	250.6
87.5°	33.3	42.1	48.8	55.5	53.2	51.0	48.8	46.6	39.9	35.5	44.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070

CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1710.2	1716.8	1723.5	1727.9	1734.6	1736.8	1739.0	1739.0	1741.2	1743.4	1747.9
5°	1792.2	1805.5	1818.9	1829.9	1843.3	1854.3	1863.2	1874.3	1883.2	1883.2	1881.0
7.5°	1723.5	1756.7	1790.0	1823.3	1856.6	1881.0	1903.1	1927.5	1949.7	1954.2	1958.6
10°	1632.5	1668.0	1701.3	1736.8	1770.1	1807.8	1843.3	1878.7	1916.5	1923.1	1932.0
12.5°	1548.2	1590.4	1632.5	1672.5	1714.6	1741.2	1767.8	1792.2	1818.9	1836.6	1854.3
15°	1546.0	1581.5	1617.0	1650.3	1685.8	1701.3	1716.8	1730.1	1745.7	1745.7	1747.9
17.5°	1597.0	1619.2	1641.4	1661.4	1683.5	1685.8	1690.2	1692.4	1694.6	1688.0	1681.3
20°	1696.9	1705.7	1714.6	1723.5	1732.3	1716.8	1703.5	1688.0	1672.5	1654.7	1639.2
22.5°	1843.3	1823.3	1803.3	1783.4	1763.4	1736.8	1707.9	1681.3	1652.5	1630.3	1608.1
25°	1980.8	1956.4	1932.0	1907.6	1883.2	1825.5	1767.8	1707.9	1650.3	1625.9	1601.5
27.5°	2164.9	2127.2	2089.5	2051.8	2014.0	1936.4	1858.8	1781.1	1703.5	1661.4	1621.4
30°	2209.2	2167.1	2125.0	2080.6	2038.4	1963.0	1889.8	1814.4	1739.0	1690.2	1643.6
32.5°	2273.6	2224.8	2176.0	2127.2	2078.4	2005.2	1932.0	1856.6	1783.4	1739.0	1692.4
35°	2380.0	2324.6	2269.1	2211.5	2156.0	2080.6	2007.4	1932.0	1856.6	1805.5	1756.7
37.5°	2471.0	2406.7	2342.3	2278.0	2213.7	2147.1	2078.4	2011.8	1943.1	1892.1	1843.3
40°	2573.0	2502.0	2431.1	2362.3	2291.3	2229.2	2167.1	2102.8	2040.7	2000.7	1960.8
42.5°	2661.7	2575.2	2490.9	2406.7	2320.1	2278.0	2238.1	2195.9	2153.8	2133.8	2111.6
45°	2723.8	2644.0	2561.9	2482.1	2402.2	2371.2	2340.1	2309.1	2278.0	2298.0	2317.9
47.5°	2750.5	2686.1	2624.0	2561.9	2497.6	2508.7	2519.8	2528.7	2539.7	2566.4	2595.2
50°	2774.9	2739.4	2701.7	2666.2	2628.5	2670.6	2710.5	2752.7	2794.8	2850.3	2905.7
52.5°	2823.7	2803.7	2786.0	2766.0	2746.0	2819.2	2892.4	2965.6	3038.8	3100.9	3163.0
55°	2970.1	2954.5	2939.0	2921.3	2905.7	3010.0	3112.0	3216.3	3320.5	3384.8	3449.2
57.5°	3171.9	3163.0	3151.9	3143.1	3132.0	3234.0	3333.8	3433.6	3535.7	3597.8	3662.1
60°	3325.0	3327.2	3327.2	3329.4	3329.4	3407.0	3484.7	3564.5	3642.1	3695.4	3750.8
62.5°	3407.0	3402.6	3398.2	3393.7	3389.3	3453.6	3517.9	3582.3	3646.6	3686.5	3726.4
65°	3318.3	3342.7	3367.1	3391.5	3415.9	3424.8	3431.4	3440.3	3447.0	3471.4	3495.8
67.5°	3021.1	3069.9	3116.5	3165.3	3211.8	3178.6	3147.5	3114.2	3081.0	3087.6	3092.1
70°	2690.6	2746.0	2803.7	2859.2	2914.6	2837.0	2759.3	2679.5	2601.8	2575.2	2548.6
72.5°	2269.1	2317.9	2368.9	2417.7	2466.5	2371.2	2278.0	2182.6	2087.2	2040.7	1994.1
75°	1734.6	1792.2	1852.1	1909.8	1967.5	1861.0	1752.3	1645.8	1537.2	1506.1	1477.3
77.5°	1264.3	1333.1	1401.8	1470.6	1539.4	1444.0	1348.6	1251.0	1155.6	1137.9	1120.1
80°	920.5	973.8	1024.8	1078.0	1129.0	1073.6	1018.1	962.7	907.2	905.0	902.8
82.5°	621.1	667.7	712.0	758.6	803.0	780.8	760.8	738.6	716.5	738.6	763.0
85°	319.4	383.7	450.3	514.6	578.9	572.3	567.8	561.2	554.5	583.4	610.0
87.5°	64.3	119.8	175.2	228.5	283.9	270.6	257.3	241.8	228.5	237.3	244.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070

CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1750.1	1752.3	1752.3	1752.3	1752.3	1752.3	1747.9	1745.7	1741.2	1736.8	1730.1
5°	1881.0	1878.7	1869.9	1861.0	1849.9	1841.0	1834.4	1825.5	1818.9	1810.0	1796.7
7.5°	1963.0	1967.5	1951.9	1938.6	1923.1	1907.6	1892.1	1876.5	1861.0	1845.5	1814.4
10°	1938.6	1945.3	1936.4	1927.5	1916.5	1907.6	1889.8	1869.9	1852.1	1832.2	1794.5
12.5°	1869.9	1887.6	1883.2	1878.7	1874.3	1869.9	1858.8	1845.5	1834.4	1821.1	1778.9
15°	1747.9	1747.9	1750.1	1752.3	1752.3	1754.5	1756.7	1759.0	1761.2	1763.4	1739.0
17.5°	1674.7	1668.0	1668.0	1668.0	1668.0	1668.0	1676.9	1688.0	1696.9	1705.7	1699.1
20°	1621.4	1605.9	1603.7	1603.7	1601.5	1599.3	1614.8	1632.5	1648.1	1663.6	1672.5
22.5°	1586.0	1563.8	1561.6	1559.3	1557.1	1554.9	1574.9	1594.8	1614.8	1634.8	1665.8
25°	1577.1	1552.7	1554.9	1557.1	1557.1	1559.3	1574.9	1590.4	1605.9	1621.4	1674.7
27.5°	1579.3	1539.4	1541.6	1543.8	1543.8	1546.0	1570.4	1592.6	1617.0	1639.2	1705.7
30°	1594.8	1548.2	1543.8	1539.4	1534.9	1530.5	1563.8	1597.0	1630.3	1663.6	1714.6
32.5°	1648.1	1603.7	1592.6	1581.5	1570.4	1559.3	1599.3	1637.0	1676.9	1714.6	1756.7
35°	1705.7	1656.9	1652.5	1648.1	1641.4	1637.0	1672.5	1710.2	1745.7	1781.1	1818.9
37.5°	1792.2	1743.4	1739.0	1732.3	1727.9	1721.3	1761.2	1798.9	1838.8	1876.5	1909.8
40°	1920.9	1881.0	1878.7	1878.7	1876.5	1874.3	1905.4	1938.6	1969.7	2000.7	2022.9
42.5°	2091.7	2071.7	2078.4	2087.2	2093.9	2100.6	2125.0	2151.6	2176.0	2200.4	2193.7
45°	2337.9	2357.9	2360.1	2362.3	2364.5	2366.7	2373.4	2382.3	2388.9	2395.6	2368.9
47.5°	2621.8	2648.4	2661.7	2675.0	2686.1	2699.4	2690.6	2679.5	2670.6	2659.5	2593.0
50°	2959.0	3014.4	3012.2	3010.0	3005.5	3003.3	2985.6	2967.8	2947.9	2930.1	2832.5
52.5°	3225.1	3287.2	3298.3	3309.4	3320.5	3331.6	3298.3	3265.1	3229.6	3196.3	3074.3
55°	3511.3	3575.6	3577.8	3580.0	3580.0	3582.3	3535.7	3489.1	3440.3	3393.7	3267.3
57.5°	3724.2	3786.3	3779.7	3775.2	3768.6	3761.9	3706.5	3651.0	3595.6	3540.1	3413.7
60°	3804.1	3857.3	3844.0	3830.7	3815.2	3801.9	3759.7	3717.6	3673.2	3631.1	3509.1
62.5°	3766.4	3806.3	3786.3	3768.6	3748.6	3728.7	3675.4	3620.0	3566.7	3511.3	3422.6
65°	3517.9	3542.3	3515.7	3491.3	3466.9	3440.3	3395.9	3351.6	3305.0	3260.6	3200.7
67.5°	3098.7	3103.1	3100.9	3098.7	3096.5	3094.3	3029.9	2965.6	2899.1	2834.8	2830.3
70°	2524.2	2497.6	2502.0	2508.7	2513.1	2517.6	2468.8	2422.2	2373.4	2324.6	2346.8
72.5°	1947.5	1900.9	1912.0	1925.3	1936.4	1947.5	1907.6	1869.9	1829.9	1790.0	1821.1
75°	1446.2	1417.4	1428.5	1441.8	1452.9	1464.0	1448.4	1432.9	1415.2	1399.6	1428.5
77.5°	1102.4	1084.7	1086.9	1086.9	1089.1	1089.1	1091.3	1095.7	1098.0	1100.2	1131.2
80°	898.3	896.1	893.9	891.7	887.2	885.0	907.2	929.4	951.6	973.8	989.3
82.5°	785.2	807.4	794.1	783.0	769.7	756.4	776.3	796.3	816.3	836.2	829.6
85°	638.8	665.4	641.0	616.6	590.0	565.6	583.4	598.9	616.6	632.2	623.3
87.5°	252.9	259.5	219.6	181.9	142.0	102.0	161.9	219.6	279.5	337.2	346.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070

CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1723.5	1714.6	1707.9	1705.7	1701.3	1699.1	1694.6	1690.2	1683.5	1679.1	1672.5
5°	1781.1	1767.8	1752.3	1730.1	1710.2	1688.0	1665.8	1645.8	1625.9	1603.7	1583.7
7.5°	1783.4	1752.3	1721.3	1692.4	1661.4	1632.5	1601.5	1574.9	1546.0	1517.2	1490.6
10°	1759.0	1721.3	1683.5	1645.8	1610.4	1572.6	1534.9	1503.9	1470.6	1437.3	1406.3
12.5°	1739.0	1696.9	1654.7	1610.4	1568.2	1523.8	1479.5	1448.4	1417.4	1386.3	1355.3
15°	1714.6	1688.0	1663.6	1623.7	1583.7	1543.8	1503.9	1461.7	1421.8	1379.7	1337.5
17.5°	1694.6	1688.0	1681.3	1654.7	1628.1	1599.3	1572.6	1530.5	1488.4	1444.0	1401.8
20°	1683.5	1692.4	1701.3	1688.0	1674.7	1659.2	1645.8	1614.8	1583.7	1550.5	1519.4
22.5°	1696.9	1730.1	1761.2	1763.4	1767.8	1770.1	1772.3	1743.4	1714.6	1683.5	1654.7
25°	1727.9	1781.1	1834.4	1863.2	1892.1	1923.1	1951.9	1934.2	1916.5	1898.7	1881.0
27.5°	1770.1	1836.6	1903.1	1945.3	1985.2	2027.4	2069.5	2067.3	2065.1	2060.6	2058.4
30°	1763.4	1814.4	1865.4	1916.5	1967.5	2018.5	2069.5	2096.1	2120.5	2147.1	2173.8
32.5°	1801.1	1843.3	1887.6	1940.9	1994.1	2049.5	2102.8	2158.2	2211.5	2266.9	2322.4
35°	1858.8	1896.5	1936.4	1994.1	2054.0	2111.6	2171.5	2238.1	2306.8	2375.6	2442.1
37.5°	1945.3	1978.6	2014.0	2062.8	2113.9	2162.7	2213.7	2311.3	2408.9	2508.7	2606.3
40°	2045.1	2067.3	2089.5	2136.0	2182.6	2229.2	2275.8	2397.8	2519.8	2641.8	2763.8
42.5°	2189.3	2182.6	2176.0	2213.7	2253.6	2291.3	2331.2	2442.1	2553.1	2664.0	2774.9
45°	2342.3	2315.7	2289.1	2306.8	2326.8	2344.5	2364.5	2477.6	2590.8	2706.1	2819.2
47.5°	2526.4	2459.9	2393.3	2377.8	2362.3	2344.5	2329.0	2451.0	2573.0	2697.2	2819.2
50°	2734.9	2635.1	2537.5	2497.6	2455.5	2415.5	2373.4	2473.2	2575.2	2677.3	2777.1
52.5°	2952.3	2828.1	2706.1	2644.0	2581.9	2517.6	2455.5	2539.7	2626.2	2712.8	2797.0
55°	3138.6	3012.2	2883.6	2810.4	2737.2	2664.0	2590.8	2675.0	2759.3	2843.6	2927.9
57.5°	3287.2	3160.8	3034.4	2965.6	2894.6	2825.9	2754.9	2834.8	2916.8	2998.9	3078.7
60°	3389.3	3267.3	3145.3	3078.7	3012.2	2945.7	2879.1	2974.5	3069.9	3167.5	3262.8
62.5°	3336.0	3247.3	3158.6	3129.8	3100.9	3069.9	3041.0	3132.0	3220.7	3311.6	3402.6
65°	3140.9	3081.0	3021.1	3049.9	3081.0	3109.8	3140.9	3200.7	3260.6	3322.7	3382.6
67.5°	2823.7	2819.2	2812.6	2876.9	2941.2	3007.8	3072.1	3112.0	3149.7	3189.7	3229.6
70°	2368.9	2393.3	2415.5	2526.4	2637.3	2748.2	2859.2	2874.7	2890.2	2905.7	2921.3
72.5°	1854.3	1885.4	1918.7	2065.1	2209.2	2355.6	2502.0	2493.2	2484.3	2473.2	2464.3
75°	1459.5	1488.4	1519.4	1654.7	1790.0	1925.3	2060.6	2022.9	1987.4	1949.7	1912.0
77.5°	1164.5	1195.6	1228.8	1355.3	1481.7	1610.4	1736.8	1645.8	1554.9	1464.0	1373.0
80°	1002.6	1018.1	1031.4	1117.9	1202.2	1288.7	1375.2	1282.1	1186.7	1091.3	998.2
82.5°	822.9	814.0	807.4	858.4	909.4	960.4	1011.5	922.7	834.0	743.1	654.3
85°	614.4	605.5	596.7	623.3	649.9	678.7	705.4	603.3	501.3	397.0	295.0
87.5°	357.1	366.0	374.9	403.7	432.5	463.6	492.4	388.2	283.9	177.4	73.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676070  
 CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676070  
CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	1597.0	1597.0
2.5°	1659.2	1648.1
5°	1568.2	1552.7
7.5°	1468.4	1448.4
10°	1377.4	1350.8
12.5°	1319.8	1286.5
15°	1297.6	1257.7
17.5°	1364.1	1326.4
20°	1466.2	1415.2
22.5°	1590.4	1528.3
25°	1805.5	1730.1
27.5°	1980.8	1903.1
30°	2089.5	2005.2
32.5°	2209.2	2098.3
35°	2333.5	2227.0
37.5°	2484.3	2364.5
40°	2639.6	2515.3
42.5°	2692.8	2612.9
45°	2743.8	2668.4
47.5°	2754.9	2692.8
50°	2766.0	2757.1
52.5°	2797.0	2794.8
55°	2930.1	2932.3
57.5°	3094.3	3107.6
60°	3245.1	3229.6
62.5°	3322.7	3242.9
65°	3269.5	3158.6
67.5°	3109.8	2990.0
70°	2759.3	2597.4
72.5°	2322.4	2180.4
75°	1790.0	1670.2
77.5°	1273.2	1173.4
80°	896.1	796.3
82.5°	574.5	494.6
85°	259.5	226.2
87.5°	73.2	71.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676070  
CATALOG NUMBER: CCW-SA-2B-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)