

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676073

Luminaire Tested: **CCW-SA-2E-850-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P676073
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2E-850-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/
SLR distribution lens
Light Source: (32) 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9901.3 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G3

Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 14.1 fc
 Type IV - Short - N/A

REPORT NUMBER: P676073
CATALOG NUMBER: CCW-SA-2E-850-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2037.3	0.0	2037.3
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	7864.0	0.0	7864.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	9901.3	0.0	9901.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.7	2.5
10°-20°	518.7	5.2
20°-30°	758.9	7.7
30°-40°	1069.2	10.8
40°-50°	1469.2	14.8
50°-60°	2002.6	20.2
60°-70°	2191.8	22.1
70°-80°	1265.8	12.8
80°-90°	379.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9901.3	100.0
0°-180°	9901.3	100.0



REPORT NUMBER: P676073


CATALOG NUMBER: CCW-SA-2E-850-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1016.9	10.3			
FM	(30°-60°)	3613.3	36.5			
FH	(60°-80°)	2911.6	29.4			G2/5000
FVH	(80°-90°)	322.3	3.3			G3/500
BL	(0°-30°)	506.5	5.1	B2/1000		
BM	(30°-60°)	927.7	9.4	B1/1000		
BH	(60°-80°)	546.0	5.5	B2/1000		G2/1000
BVH	(80°-90°)	57.1	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short





REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	3262.9	3245.3	3232.1	3219.0	3201.4	3188.2	3170.6	3153.1	3131.1	3113.6	3091.6
5°	3074.0	3021.3	2968.6	2937.9	2902.8	2872.0	2836.9	2797.4	2757.8	2713.9	2674.4
7.5°	2867.6	2801.8	2735.9	2683.2	2626.1	2573.4	2516.3	2468.0	2419.7	2371.4	2323.1
10°	2674.4	2612.9	2551.4	2485.6	2415.3	2349.4	2279.2	2213.3	2147.4	2081.6	2015.7
12.5°	2547.1	2472.4	2402.1	2327.5	2257.2	2182.6	2107.9	2046.4	1984.9	1919.1	1857.6
15°	2490.0	2419.7	2353.8	2279.2	2204.5	2129.9	2055.2	1984.9	1919.1	1848.8	1778.5
17.5°	2626.1	2525.1	2424.1	2327.5	2230.9	2134.3	2037.6	1949.8	1862.0	1774.2	1686.3
20°	2801.8	2674.4	2551.4	2432.9	2309.9	2191.3	2068.4	1945.4	1822.5	1699.5	1576.5
22.5°	3025.7	2880.8	2740.3	2586.6	2428.5	2274.8	2116.7	1963.0	1809.3	1651.2	1497.5
25°	3425.4	3254.1	3082.8	2863.2	2639.3	2419.7	2195.7	1993.7	1796.1	1594.1	1392.1
27.5°	3767.9	3535.1	3306.8	3043.3	2779.8	2516.3	2252.8	2020.1	1791.7	1559.0	1326.2
30°	3969.9	3741.5	3513.2	3192.6	2876.4	2555.8	2235.3	1976.2	1721.5	1462.4	1203.3
32.5°	4154.3	3899.6	3644.9	3293.6	2937.9	2586.6	2230.9	1945.4	1664.4	1378.9	1093.5
35°	4409.0	4128.0	3851.3	3442.9	3034.5	2626.1	2217.7	1923.5	1624.8	1330.6	1032.0
37.5°	4681.3	4334.4	3991.9	3539.5	3087.2	2634.9	2182.6	1892.7	1602.9	1313.1	1023.2
40°	4979.9	4558.4	4141.2	3640.5	3144.3	2643.7	2143.0	1853.2	1563.4	1269.1	979.3
42.5°	5173.2	4716.4	4259.7	3719.6	3183.8	2643.7	2103.5	1818.1	1532.6	1242.8	957.3
45°	5282.9	4839.4	4400.3	3816.2	3232.1	2648.1	2064.0	1782.9	1501.9	1216.4	935.4
47.5°	5331.3	4918.5	4505.7	3890.8	3280.4	2665.6	2050.8	1765.4	1475.5	1190.1	900.3
50°	5458.6	5094.1	4729.6	4070.9	3416.6	2757.8	2099.1	1791.7	1488.7	1181.3	873.9
52.5°	5533.3	5221.5	4909.7	4233.4	3557.1	2880.8	2204.5	1862.0	1519.5	1176.9	834.4
55°	5805.5	5506.9	5208.3	4488.1	3763.5	3043.3	2318.7	1941.0	1563.4	1181.3	803.6
57.5°	6152.5	5836.3	5524.5	4747.2	3969.9	3192.6	2415.3	2011.3	1602.9	1198.9	790.5
60°	6394.0	6086.6	5783.6	4958.0	4128.0	3302.4	2472.4	2050.8	1629.2	1203.3	781.7
62.5°	6420.3	6025.1	5634.3	4830.6	4027.0	3219.0	2415.3	2006.9	1598.5	1185.7	777.3
65°	6253.5	5792.4	5331.3	4562.7	3794.2	3025.7	2257.2	1883.9	1510.7	1133.0	759.7
67.5°	5919.7	5379.6	4839.4	4136.8	3434.1	2731.5	2028.9	1708.3	1392.1	1071.5	750.9
70°	5142.4	4668.1	4198.3	3587.8	2981.8	2371.4	1761.0	1497.5	1238.4	974.9	711.4
72.5°	4316.8	3873.3	3434.1	2937.9	2446.1	1949.8	1453.6	1256.0	1058.3	856.3	658.7
75°	3306.8	2973.0	2643.7	2274.8	1905.9	1532.6	1163.7	1018.8	873.9	729.0	584.1
77.5°	2323.1	2143.0	1967.4	1690.7	1414.1	1137.4	860.7	764.1	667.5	570.9	474.3
80°	1576.5	1475.5	1378.9	1181.3	983.7	781.7	584.1	522.6	456.7	395.2	329.4
82.5°	979.3	974.9	966.1	830.0	693.9	557.7	421.6	368.9	320.6	267.9	215.2
85°	447.9	522.6	592.8	518.2	443.5	368.9	294.2	259.1	224.0	184.4	149.3
87.5°	140.5	171.3	197.6	188.8	175.7	166.9	153.7	131.7	109.8	87.8	65.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	3074.0	3060.9	3043.3	3025.7	3003.8	2986.2	2964.2	2942.3	2937.9	2929.1	2924.7
5°	2648.1	2621.7	2591.0	2564.6	2538.3	2507.5	2481.2	2450.4	2428.5	2402.1	2380.2
7.5°	2274.8	2230.9	2182.6	2134.3	2090.3	2046.4	1998.1	1954.2	1932.2	1910.3	1888.3
10°	1976.2	1932.2	1892.7	1848.8	1818.1	1791.7	1761.0	1730.2	1703.9	1677.5	1651.2
12.5°	1826.9	1796.1	1765.4	1734.6	1699.5	1668.8	1633.6	1598.5	1567.8	1541.4	1510.7
15°	1734.6	1690.7	1642.4	1598.5	1550.2	1506.3	1458.0	1409.7	1374.5	1343.8	1308.7
17.5°	1624.8	1559.0	1497.5	1431.6	1378.9	1326.2	1269.1	1216.4	1176.9	1133.0	1093.5
20°	1501.9	1427.2	1348.2	1273.5	1212.0	1155.0	1093.5	1032.0	988.1	939.8	895.9
22.5°	1396.5	1299.9	1198.9	1097.9	1032.0	966.1	895.9	830.0	790.5	746.6	707.0
25°	1282.3	1176.9	1067.1	957.3	891.5	821.2	755.3	685.1	654.3	628.0	597.2
27.5°	1220.8	1115.4	1005.6	900.3	838.8	772.9	711.4	645.5	623.6	597.2	575.3
30°	1097.9	996.9	891.5	786.1	742.2	702.6	658.7	614.8	606.0	601.6	592.8
32.5°	988.1	882.7	777.3	671.9	632.4	592.8	553.3	513.8	509.4	500.6	496.2
35°	931.0	830.0	724.6	623.6	588.5	548.9	513.8	474.3	465.5	452.3	443.5
37.5°	917.8	812.4	702.6	597.2	562.1	527.0	487.5	452.3	443.5	434.8	426.0
40°	882.7	781.7	685.1	584.1	548.9	513.8	474.3	439.1	430.4	421.6	412.8
42.5°	856.3	759.7	658.7	557.7	527.0	496.2	461.1	430.4	421.6	412.8	399.6
45°	834.4	733.4	628.0	527.0	505.0	483.1	456.7	434.8	426.0	412.8	404.0
47.5°	799.2	702.6	601.6	500.6	478.7	461.1	439.1	417.2	408.4	399.6	390.8
50°	772.9	671.9	570.9	469.9	452.3	434.8	417.2	399.6	399.6	404.0	404.0
52.5°	737.8	641.2	544.5	447.9	430.4	412.8	395.2	377.7	382.1	386.4	390.8
55°	707.0	614.8	518.2	421.6	404.0	386.4	364.5	346.9	351.3	355.7	360.1
57.5°	693.9	597.2	500.6	404.0	386.4	364.5	346.9	325.0	325.0	325.0	325.0
60°	685.1	584.1	487.5	386.4	364.5	346.9	325.0	303.0	298.6	298.6	294.2
62.5°	680.7	579.7	483.1	382.1	355.7	333.8	307.4	281.1	276.7	272.3	267.9
65°	663.1	570.9	474.3	377.7	346.9	320.6	289.8	259.1	254.7	254.7	250.3
67.5°	658.7	562.1	469.9	373.3	342.5	307.4	276.7	241.5	237.1	232.7	228.4
70°	623.6	540.2	452.3	364.5	329.4	298.6	263.5	228.4	224.0	215.2	210.8
72.5°	579.7	505.0	426.0	346.9	311.8	276.7	241.5	206.4	202.0	197.6	188.8
75°	513.8	443.5	373.3	303.0	272.3	245.9	215.2	184.4	180.1	175.7	166.9
77.5°	421.6	364.5	311.8	254.7	232.7	210.8	188.8	166.9	162.5	158.1	149.3
80°	298.6	263.5	232.7	197.6	184.4	166.9	153.7	136.1	136.1	131.7	131.7
82.5°	197.6	180.1	162.5	144.9	136.1	127.4	118.6	109.8	109.8	105.4	105.4
85°	140.5	131.7	118.6	109.8	105.4	96.6	92.2	83.4	83.4	83.4	83.4
87.5°	65.9	65.9	61.5	61.5	57.1	57.1	52.7	48.3	48.3	48.3	48.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	2915.9	2902.8	2889.6	2872.0	2858.9	2841.3	2819.3	2801.8	2779.8	2779.8	2775.4
5°	2353.8	2340.7	2327.5	2309.9	2296.7	2279.2	2266.0	2248.4	2230.9	2230.9	2226.5
7.5°	1866.4	1840.0	1813.7	1782.9	1756.6	1739.0	1721.5	1699.5	1681.9	1668.8	1655.6
10°	1624.8	1598.5	1567.8	1541.4	1510.7	1488.7	1466.8	1440.4	1418.4	1400.9	1383.3
12.5°	1479.9	1449.2	1418.4	1387.7	1357.0	1326.2	1299.9	1269.1	1238.4	1216.4	1194.5
15°	1273.5	1242.8	1212.0	1181.3	1150.6	1115.4	1080.3	1040.8	1005.6	988.1	974.9
17.5°	1049.6	1018.8	983.7	953.0	917.8	891.5	865.1	838.8	812.4	794.9	781.7
20°	847.6	812.4	777.3	742.2	707.0	689.5	671.9	654.3	636.8	623.6	614.8
22.5°	663.1	641.2	623.6	601.6	579.7	566.5	557.7	544.5	531.4	531.4	531.4
25°	566.5	553.3	544.5	531.4	518.2	513.8	509.4	500.6	496.2	491.8	491.8
27.5°	548.9	535.8	522.6	509.4	496.2	491.8	487.5	478.7	474.3	474.3	474.3
30°	584.1	579.7	575.3	570.9	566.5	557.7	544.5	535.8	522.6	513.8	505.0
32.5°	487.5	483.1	483.1	478.7	474.3	483.1	487.5	496.2	500.6	505.0	509.4
35°	430.4	421.6	412.8	404.0	395.2	390.8	386.4	382.1	377.7	377.7	373.3
37.5°	417.2	408.4	399.6	390.8	382.1	377.7	373.3	368.9	364.5	364.5	360.1
40°	404.0	395.2	390.8	382.1	373.3	368.9	364.5	355.7	351.3	346.9	346.9
42.5°	390.8	386.4	377.7	373.3	364.5	360.1	355.7	346.9	342.5	338.1	333.8
45°	390.8	382.1	373.3	364.5	355.7	351.3	342.5	338.1	329.4	329.4	325.0
47.5°	382.1	373.3	364.5	355.7	346.9	342.5	333.8	329.4	320.6	316.2	311.8
50°	404.0	390.8	373.3	360.1	342.5	338.1	329.4	325.0	316.2	311.8	307.4
52.5°	395.2	382.1	364.5	351.3	333.8	325.0	320.6	311.8	303.0	298.6	294.2
55°	364.5	351.3	342.5	329.4	316.2	307.4	298.6	289.8	281.1	276.7	276.7
57.5°	325.0	320.6	316.2	311.8	307.4	298.6	289.8	276.7	267.9	263.5	259.1
60°	289.8	294.2	298.6	303.0	307.4	294.2	281.1	267.9	254.7	250.3	245.9
62.5°	263.5	272.3	281.1	285.4	294.2	281.1	267.9	254.7	241.5	237.1	232.7
65°	245.9	250.3	250.3	254.7	254.7	245.9	241.5	232.7	224.0	219.6	219.6
67.5°	224.0	224.0	224.0	219.6	219.6	215.2	215.2	210.8	206.4	202.0	202.0
70°	202.0	202.0	202.0	197.6	197.6	193.2	193.2	188.8	184.4	184.4	180.1
72.5°	184.4	184.4	180.1	180.1	175.7	175.7	175.7	171.3	171.3	166.9	166.9
75°	162.5	162.5	158.1	158.1	153.7	153.7	153.7	149.3	149.3	149.3	144.9
77.5°	144.9	144.9	140.5	140.5	136.1	136.1	136.1	131.7	131.7	127.4	127.4
80°	127.4	127.4	123.0	123.0	118.6	118.6	114.2	114.2	109.8	109.8	105.4
82.5°	101.0	101.0	101.0	101.0	101.0	96.6	96.6	92.2	87.8	87.8	83.4
85°	83.4	83.4	83.4	79.0	79.0	79.0	74.7	74.7	70.3	65.9	65.9
87.5°	48.3	48.3	48.3	43.9	43.9	43.9	43.9	43.9	43.9	43.9	39.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	2775.4	2771.0	2753.5	2735.9	2753.5	2771.0	2771.0	2771.0	2766.6	2766.6	2766.6
5°	2226.5	2222.1	2213.3	2204.5	2204.5	2200.1	2208.9	2217.7	2226.5	2235.3	2244.0
7.5°	1638.0	1624.8	1611.7	1598.5	1607.3	1611.7	1624.8	1633.6	1646.8	1655.6	1677.5
10°	1365.7	1348.2	1335.0	1321.8	1313.1	1304.3	1295.5	1291.1	1282.3	1273.5	1282.3
12.5°	1168.1	1146.2	1124.2	1097.9	1093.5	1089.1	1080.3	1071.5	1062.7	1054.0	1049.6
15°	957.3	939.8	931.0	917.8	900.3	882.7	873.9	869.5	860.7	851.9	847.6
17.5°	764.1	746.6	733.4	720.2	715.8	707.0	707.0	707.0	707.0	707.0	707.0
20°	601.6	588.5	588.5	584.1	584.1	579.7	584.1	588.5	588.5	592.8	597.2
22.5°	527.0	527.0	522.6	518.2	522.6	522.6	527.0	531.4	535.8	540.2	544.5
25°	487.5	483.1	487.5	491.8	491.8	491.8	496.2	496.2	500.6	500.6	500.6
27.5°	469.9	469.9	474.3	474.3	478.7	478.7	478.7	474.3	474.3	469.9	469.9
30°	496.2	487.5	487.5	487.5	483.1	478.7	474.3	474.3	469.9	465.5	461.1
32.5°	513.8	518.2	513.8	505.0	500.6	491.8	487.5	478.7	474.3	465.5	456.7
35°	373.3	368.9	377.7	382.1	386.4	390.8	395.2	399.6	399.6	404.0	404.0
37.5°	360.1	355.7	355.7	351.3	351.3	351.3	351.3	351.3	346.9	346.9	351.3
40°	342.5	338.1	338.1	333.8	333.8	329.4	329.4	329.4	329.4	329.4	329.4
42.5°	329.4	325.0	325.0	325.0	325.0	320.6	320.6	316.2	316.2	311.8	311.8
45°	325.0	320.6	316.2	311.8	311.8	307.4	307.4	307.4	303.0	303.0	303.0
47.5°	307.4	303.0	303.0	298.6	298.6	294.2	294.2	294.2	289.8	289.8	289.8
50°	298.6	294.2	294.2	289.8	289.8	285.4	285.4	285.4	281.1	281.1	281.1
52.5°	285.4	281.1	281.1	281.1	276.7	272.3	272.3	272.3	267.9	267.9	267.9
55°	272.3	267.9	267.9	267.9	263.5	259.1	259.1	259.1	254.7	254.7	254.7
57.5°	254.7	250.3	250.3	245.9	245.9	245.9	245.9	245.9	241.5	241.5	241.5
60°	241.5	237.1	237.1	232.7	232.7	228.4	228.4	228.4	228.4	228.4	228.4
62.5°	228.4	224.0	219.6	215.2	219.6	219.6	219.6	219.6	215.2	215.2	215.2
65°	215.2	210.8	206.4	202.0	202.0	202.0	202.0	202.0	202.0	202.0	202.0
67.5°	197.6	193.2	188.8	184.4	188.8	188.8	188.8	188.8	188.8	188.8	188.8
70°	180.1	175.7	175.7	171.3	171.3	166.9	166.9	171.3	171.3	171.3	171.3
72.5°	162.5	158.1	158.1	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7
75°	144.9	140.5	140.5	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1
77.5°	123.0	118.6	118.6	118.6	118.6	118.6	118.6	123.0	123.0	123.0	123.0
80°	105.4	101.0	101.0	101.0	101.0	101.0	101.0	101.0	101.0	101.0	101.0
82.5°	83.4	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0
85°	61.5	57.1	57.1	57.1	61.5	61.5	61.5	61.5	61.5	61.5	61.5
87.5°	39.5	35.1	35.1	35.1	39.5	39.5	39.5	39.5	35.1	35.1	35.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	2766.6	2766.6	2766.6	2762.2	2757.8	2753.5	2749.1	2762.2	2771.0	2784.2	2793.0
5°	2248.4	2257.2	2261.6	2274.8	2288.0	2301.1	2314.3	2323.1	2331.9	2336.3	2345.0
7.5°	1695.1	1717.1	1734.6	1752.2	1769.8	1782.9	1800.5	1813.7	1826.9	1840.0	1853.2
10°	1286.7	1295.5	1299.9	1317.4	1330.6	1348.2	1361.4	1374.5	1387.7	1396.5	1409.7
12.5°	1045.2	1036.4	1032.0	1032.0	1032.0	1032.0	1032.0	1040.8	1049.6	1058.3	1067.1
15°	843.2	838.8	834.4	830.0	825.6	816.8	812.4	821.2	830.0	838.8	847.6
17.5°	707.0	707.0	707.0	702.6	698.2	693.9	689.5	693.9	698.2	698.2	702.6
20°	606.0	610.4	614.8	619.2	619.2	623.6	623.6	628.0	632.4	632.4	636.8
22.5°	544.5	548.9	548.9	548.9	553.3	553.3	553.3	557.7	562.1	566.5	570.9
25°	496.2	496.2	491.8	491.8	496.2	496.2	496.2	496.2	500.6	500.6	500.6
27.5°	469.9	465.5	465.5	465.5	465.5	461.1	461.1	461.1	461.1	461.1	461.1
30°	456.7	452.3	447.9	443.5	443.5	439.1	434.8	434.8	434.8	434.8	434.8
32.5°	452.3	443.5	434.8	430.4	430.4	426.0	421.6	417.2	417.2	412.8	408.4
35°	404.0	399.6	399.6	395.2	390.8	386.4	382.1	382.1	382.1	377.7	377.7
37.5°	351.3	355.7	355.7	355.7	360.1	360.1	360.1	360.1	364.5	364.5	364.5
40°	329.4	329.4	329.4	333.8	338.1	338.1	342.5	342.5	346.9	346.9	346.9
42.5°	311.8	307.4	307.4	311.8	311.8	316.2	316.2	320.6	325.0	325.0	329.4
45°	303.0	298.6	298.6	298.6	298.6	294.2	294.2	298.6	303.0	307.4	311.8
47.5°	285.4	285.4	281.1	281.1	281.1	281.1	281.1	281.1	285.4	285.4	285.4
50°	276.7	276.7	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3
52.5°	267.9	263.5	263.5	263.5	263.5	259.1	259.1	259.1	259.1	259.1	259.1
55°	254.7	250.3	250.3	250.3	250.3	250.3	250.3	250.3	254.7	254.7	254.7
57.5°	241.5	237.1	237.1	237.1	241.5	241.5	241.5	241.5	245.9	245.9	245.9
60°	228.4	228.4	228.4	228.4	228.4	228.4	228.4	232.7	232.7	237.1	237.1
62.5°	215.2	215.2	215.2	215.2	219.6	219.6	219.6	219.6	224.0	224.0	224.0
65°	202.0	202.0	202.0	202.0	206.4	206.4	206.4	206.4	206.4	206.4	206.4
67.5°	188.8	188.8	188.8	188.8	188.8	188.8	188.8	193.2	193.2	197.6	197.6
70°	171.3	166.9	166.9	171.3	171.3	175.7	175.7	180.1	180.1	184.4	184.4
72.5°	153.7	153.7	153.7	153.7	153.7	153.7	153.7	158.1	162.5	162.5	166.9
75°	136.1	136.1	136.1	136.1	140.5	140.5	140.5	144.9	144.9	149.3	149.3
77.5°	123.0	118.6	118.6	118.6	123.0	123.0	123.0	127.4	127.4	131.7	131.7
80°	101.0	101.0	101.0	101.0	105.4	105.4	105.4	105.4	109.8	109.8	109.8
82.5°	83.4	83.4	83.4	83.4	83.4	83.4	83.4	83.4	87.8	87.8	87.8
85°	61.5	61.5	61.5	61.5	65.9	65.9	65.9	65.9	65.9	65.9	65.9
87.5°	39.5	39.5	39.5	39.5	39.5	39.5	39.5	39.5	43.9	43.9	43.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	2793.0	2793.0	2793.0	2793.0	2801.8	2806.2	2814.9	2819.3	2814.9	2810.5	2801.8
5°	2349.4	2353.8	2353.8	2358.2	2358.2	2358.2	2358.2	2358.2	2367.0	2375.8	2384.6
7.5°	1857.6	1862.0	1866.4	1870.8	1870.8	1870.8	1866.4	1866.4	1870.8	1870.8	1875.2
10°	1422.8	1440.4	1453.6	1466.8	1458.0	1444.8	1436.0	1422.8	1422.8	1422.8	1418.4
12.5°	1075.9	1080.3	1089.1	1093.5	1089.1	1089.1	1084.7	1080.3	1084.7	1093.5	1097.9
15°	851.9	851.9	856.3	856.3	860.7	865.1	865.1	869.5	878.3	882.7	891.5
17.5°	707.0	711.4	711.4	715.8	715.8	720.2	720.2	720.2	729.0	737.8	750.9
20°	636.8	636.8	636.8	636.8	636.8	632.4	632.4	628.0	632.4	641.2	645.5
22.5°	570.9	575.3	575.3	575.3	570.9	566.5	557.7	553.3	553.3	557.7	557.7
25°	500.6	496.2	496.2	491.8	491.8	496.2	496.2	496.2	500.6	500.6	505.0
27.5°	461.1	456.7	456.7	452.3	452.3	456.7	456.7	456.7	456.7	456.7	456.7
30°	430.4	430.4	426.0	421.6	426.0	426.0	430.4	430.4	434.8	434.8	439.1
32.5°	408.4	404.0	404.0	399.6	404.0	404.0	408.4	408.4	412.8	417.2	417.2
35°	377.7	377.7	377.7	377.7	377.7	377.7	373.3	373.3	373.3	373.3	373.3
37.5°	360.1	360.1	355.7	351.3	351.3	351.3	351.3	351.3	346.9	342.5	338.1
40°	346.9	342.5	342.5	338.1	333.8	333.8	329.4	325.0	325.0	320.6	320.6
42.5°	329.4	325.0	325.0	320.6	316.2	316.2	311.8	307.4	307.4	307.4	303.0
45°	307.4	307.4	303.0	298.6	298.6	298.6	294.2	294.2	294.2	294.2	289.8
47.5°	285.4	285.4	281.1	281.1	281.1	281.1	276.7	276.7	276.7	276.7	276.7
50°	272.3	272.3	272.3	272.3	272.3	272.3	267.9	267.9	267.9	267.9	267.9
52.5°	259.1	259.1	259.1	259.1	259.1	259.1	259.1	259.1	259.1	259.1	259.1
55°	254.7	254.7	254.7	254.7	254.7	254.7	250.3	250.3	250.3	254.7	254.7
57.5°	245.9	245.9	241.5	241.5	241.5	241.5	241.5	241.5	241.5	241.5	241.5
60°	237.1	237.1	237.1	237.1	237.1	237.1	237.1	237.1	237.1	237.1	237.1
62.5°	224.0	224.0	224.0	224.0	224.0	228.4	228.4	228.4	228.4	228.4	224.0
65°	206.4	210.8	210.8	210.8	210.8	210.8	210.8	210.8	210.8	210.8	210.8
67.5°	197.6	197.6	197.6	197.6	197.6	197.6	197.6	197.6	197.6	197.6	197.6
70°	184.4	184.4	180.1	180.1	180.1	184.4	184.4	184.4	184.4	184.4	184.4
72.5°	166.9	166.9	166.9	166.9	166.9	166.9	166.9	166.9	166.9	171.3	171.3
75°	149.3	149.3	149.3	149.3	149.3	149.3	149.3	149.3	149.3	149.3	149.3
77.5°	131.7	131.7	127.4	127.4	127.4	131.7	131.7	131.7	131.7	136.1	136.1
80°	109.8	109.8	109.8	109.8	109.8	109.8	109.8	109.8	109.8	114.2	114.2
82.5°	87.8	87.8	87.8	87.8	87.8	87.8	87.8	87.8	87.8	92.2	92.2
85°	65.9	70.3	70.3	70.3	70.3	70.3	70.3	70.3	70.3	74.7	74.7
87.5°	43.9	43.9	43.9	43.9	43.9	43.9	39.5	39.5	39.5	39.5	35.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	2797.4	2801.8	2806.2	2806.2	2810.5	2814.9	2814.9	2832.5	2850.1	2858.9	2867.6
5°	2393.4	2389.0	2389.0	2384.6	2380.2	2393.4	2406.5	2432.9	2459.2	2463.6	2472.4
7.5°	1875.2	1879.6	1883.9	1883.9	1888.3	1875.2	1857.6	1862.0	1866.4	1888.3	1905.9
10°	1418.4	1422.8	1427.2	1427.2	1431.6	1427.2	1418.4	1431.6	1444.8	1462.4	1484.3
12.5°	1102.3	1115.4	1128.6	1137.4	1150.6	1159.3	1163.7	1181.3	1194.5	1216.4	1238.4
15°	900.3	909.0	917.8	926.6	935.4	944.2	953.0	970.5	988.1	1014.4	1040.8
17.5°	759.7	759.7	764.1	764.1	764.1	772.9	781.7	790.5	794.9	821.2	847.6
20°	649.9	645.5	641.2	636.8	632.4	641.2	645.5	649.9	654.3	671.9	685.1
22.5°	557.7	557.7	562.1	562.1	562.1	557.7	548.9	553.3	553.3	562.1	575.3
25°	505.0	505.0	505.0	500.6	500.6	505.0	509.4	509.4	505.0	509.4	513.8
27.5°	456.7	461.1	461.1	465.5	465.5	469.9	469.9	469.9	469.9	474.3	478.7
30°	439.1	439.1	443.5	443.5	443.5	447.9	452.3	452.3	452.3	456.7	465.5
32.5°	421.6	426.0	430.4	434.8	439.1	443.5	443.5	447.9	447.9	452.3	456.7
35°	373.3	368.9	368.9	364.5	360.1	360.1	360.1	360.1	355.7	360.1	360.1
37.5°	333.8	333.8	333.8	329.4	329.4	333.8	333.8	333.8	333.8	338.1	338.1
40°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	320.6	320.6	325.0	329.4
42.5°	303.0	303.0	303.0	303.0	303.0	307.4	307.4	307.4	307.4	311.8	311.8
45°	289.8	289.8	289.8	289.8	289.8	289.8	289.8	294.2	294.2	298.6	303.0
47.5°	276.7	276.7	276.7	276.7	276.7	281.1	285.4	285.4	285.4	289.8	289.8
50°	267.9	267.9	267.9	267.9	267.9	272.3	272.3	276.7	276.7	281.1	285.4
52.5°	259.1	259.1	259.1	259.1	259.1	263.5	263.5	267.9	267.9	272.3	276.7
55°	254.7	254.7	254.7	250.3	250.3	254.7	254.7	259.1	259.1	263.5	263.5
57.5°	241.5	241.5	241.5	241.5	241.5	241.5	241.5	245.9	245.9	250.3	254.7
60°	237.1	237.1	232.7	232.7	228.4	232.7	232.7	237.1	237.1	241.5	241.5
62.5°	224.0	224.0	224.0	219.6	219.6	224.0	224.0	224.0	224.0	228.4	232.7
65°	210.8	210.8	210.8	206.4	206.4	210.8	210.8	210.8	210.8	215.2	219.6
67.5°	197.6	197.6	197.6	193.2	193.2	193.2	193.2	197.6	197.6	202.0	206.4
70°	184.4	184.4	184.4	180.1	180.1	180.1	175.7	180.1	184.4	188.8	188.8
72.5°	171.3	171.3	171.3	166.9	166.9	166.9	162.5	166.9	166.9	171.3	171.3
75°	149.3	149.3	149.3	149.3	149.3	149.3	144.9	144.9	144.9	149.3	149.3
77.5°	136.1	136.1	136.1	131.7	131.7	131.7	127.4	127.4	127.4	131.7	131.7
80°	114.2	114.2	114.2	109.8	109.8	109.8	105.4	105.4	105.4	109.8	109.8
82.5°	92.2	92.2	92.2	87.8	87.8	87.8	83.4	83.4	83.4	87.8	87.8
85°	74.7	74.7	74.7	74.7	74.7	74.7	70.3	70.3	70.3	74.7	79.0
87.5°	35.1	35.1	39.5	39.5	39.5	39.5	35.1	35.1	30.7	30.7	35.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	2876.4	2885.2	2907.2	2924.7	2946.7	2964.2	2977.4	2995.0	3008.2	3021.3	3030.1
5°	2476.8	2481.2	2503.1	2525.1	2542.7	2564.6	2595.4	2626.1	2656.8	2687.6	2709.5
7.5°	1927.9	1945.4	1971.8	2002.5	2028.9	2055.2	2086.0	2121.1	2151.8	2182.6	2213.3
10°	1501.9	1519.5	1545.8	1572.1	1594.1	1620.5	1655.6	1690.7	1725.9	1761.0	1796.1
12.5°	1260.4	1282.3	1313.1	1343.8	1370.1	1400.9	1444.8	1484.3	1528.2	1567.8	1611.7
15°	1062.7	1089.1	1128.6	1172.5	1212.0	1251.6	1295.5	1339.4	1378.9	1422.8	1466.8
17.5°	873.9	900.3	935.4	974.9	1010.0	1045.2	1097.9	1146.2	1198.9	1247.2	1295.5
20°	702.6	715.8	750.9	786.1	821.2	856.3	895.9	935.4	974.9	1014.4	1075.9
22.5°	584.1	592.8	610.4	623.6	641.2	654.3	693.9	733.4	768.5	808.0	865.1
25°	513.8	518.2	531.4	540.2	553.3	562.1	588.5	610.4	636.8	658.7	711.4
27.5°	478.7	483.1	487.5	491.8	496.2	500.6	518.2	535.8	548.9	566.5	614.8
30°	469.9	474.3	487.5	496.2	509.4	518.2	527.0	535.8	544.5	553.3	584.1
32.5°	461.1	465.5	465.5	461.1	461.1	456.7	465.5	469.9	478.7	483.1	509.4
35°	364.5	364.5	368.9	373.3	377.7	382.1	395.2	404.0	417.2	426.0	447.9
37.5°	342.5	342.5	346.9	355.7	360.1	364.5	373.3	382.1	390.8	399.6	421.6
40°	329.4	333.8	338.1	342.5	346.9	351.3	360.1	364.5	373.3	377.7	395.2
42.5°	316.2	316.2	320.6	329.4	333.8	338.1	346.9	351.3	360.1	364.5	382.1
45°	307.4	311.8	316.2	320.6	320.6	325.0	333.8	342.5	346.9	355.7	373.3
47.5°	294.2	294.2	303.0	307.4	316.2	320.6	329.4	333.8	342.5	346.9	364.5
50°	285.4	289.8	298.6	303.0	311.8	316.2	329.4	338.1	351.3	360.1	368.9
52.5°	276.7	281.1	289.8	294.2	303.0	307.4	325.0	342.5	355.7	373.3	373.3
55°	267.9	267.9	276.7	289.8	298.6	307.4	316.2	329.4	338.1	346.9	346.9
57.5°	254.7	259.1	267.9	281.1	289.8	298.6	307.4	316.2	320.6	329.4	325.0
60°	245.9	245.9	259.1	272.3	285.4	298.6	298.6	298.6	294.2	294.2	294.2
62.5°	232.7	237.1	254.7	276.7	294.2	311.8	298.6	285.4	272.3	259.1	263.5
65°	224.0	228.4	237.1	250.3	259.1	267.9	259.1	254.7	245.9	237.1	241.5
67.5°	206.4	210.8	215.2	215.2	219.6	219.6	219.6	219.6	219.6	219.6	224.0
70°	193.2	193.2	193.2	197.6	197.6	197.6	197.6	197.6	197.6	197.6	202.0
72.5°	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	180.1
75°	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	158.1
77.5°	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1	131.7	131.7	136.1
80°	114.2	114.2	114.2	114.2	109.8	109.8	109.8	109.8	109.8	109.8	114.2
82.5°	92.2	92.2	92.2	92.2	87.8	87.8	87.8	87.8	83.4	83.4	87.8
85°	83.4	87.8	87.8	92.2	92.2	92.2	87.8	83.4	79.0	74.7	74.7
87.5°	35.1	35.1	35.1	35.1	30.7	30.7	30.7	30.7	30.7	30.7	30.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	3043.3	3052.1	3060.9	3074.0	3091.6	3104.8	3117.9	3144.3	3175.0	3201.4	3227.7
5°	2731.5	2753.5	2775.4	2801.8	2828.1	2850.1	2876.4	2929.1	2981.8	3030.1	3082.8
7.5°	2239.7	2270.4	2296.7	2340.7	2380.2	2424.1	2463.6	2529.5	2591.0	2656.8	2718.3
10°	1831.2	1866.4	1901.5	1958.6	2020.1	2077.2	2134.3	2187.0	2244.0	2296.7	2349.4
12.5°	1655.6	1695.1	1739.0	1774.2	1813.7	1848.8	1883.9	1945.4	2006.9	2068.4	2129.9
15°	1510.7	1554.6	1598.5	1642.4	1681.9	1725.9	1765.4	1818.1	1875.2	1927.9	1980.6
17.5°	1343.8	1387.7	1436.0	1484.3	1532.6	1580.9	1629.2	1703.9	1778.5	1848.8	1923.5
20°	1133.0	1194.5	1251.6	1317.4	1383.3	1449.2	1515.1	1594.1	1673.2	1747.8	1826.9
22.5°	922.2	979.3	1036.4	1115.4	1194.5	1269.1	1348.2	1453.6	1554.6	1660.0	1761.0
25°	768.5	821.2	873.9	961.7	1045.2	1133.0	1216.4	1343.8	1466.8	1594.1	1717.1
27.5°	663.1	711.4	759.7	851.9	944.2	1032.0	1124.2	1264.7	1400.9	1541.4	1677.5
30°	614.8	645.5	676.3	764.1	851.9	935.4	1023.2	1159.3	1295.5	1431.6	1567.8
32.5°	535.8	562.1	588.5	667.5	746.6	821.2	900.3	1040.8	1176.9	1317.4	1453.6
35°	474.3	496.2	518.2	592.8	663.1	737.8	808.0	948.6	1089.1	1229.6	1370.1
37.5°	439.1	461.1	478.7	544.5	614.8	680.7	746.6	887.1	1023.2	1163.7	1299.9
40°	412.8	426.0	443.5	509.4	570.9	636.8	698.2	825.6	957.3	1084.7	1212.0
42.5°	395.2	412.8	426.0	483.1	544.5	601.6	658.7	781.7	904.6	1023.2	1146.2
45°	390.8	408.4	426.0	474.3	522.6	566.5	614.8	733.4	851.9	970.5	1089.1
47.5°	382.1	395.2	412.8	452.3	487.5	527.0	562.1	680.7	799.2	913.4	1032.0
50°	377.7	382.1	390.8	426.0	461.1	496.2	531.4	649.9	768.5	887.1	1005.6
52.5°	373.3	373.3	373.3	404.0	434.8	461.1	491.8	610.4	733.4	851.9	970.5
55°	346.9	342.5	342.5	373.3	399.6	430.4	456.7	575.3	693.9	808.0	926.6
57.5°	320.6	316.2	311.8	338.1	364.5	390.8	417.2	535.8	658.7	777.3	895.9
60°	294.2	289.8	289.8	316.2	338.1	364.5	386.4	509.4	628.0	750.9	869.5
62.5°	263.5	267.9	267.9	289.8	316.2	338.1	360.1	483.1	610.4	733.4	856.3
65°	241.5	245.9	245.9	272.3	298.6	325.0	351.3	469.9	592.8	711.4	830.0
67.5°	224.0	228.4	228.4	259.1	285.4	316.2	342.5	447.9	557.7	663.1	768.5
70°	206.4	206.4	210.8	241.5	272.3	303.0	333.8	426.0	518.2	606.0	698.2
72.5°	184.4	188.8	193.2	224.0	250.3	281.1	307.4	390.8	474.3	557.7	641.2
75°	162.5	166.9	171.3	197.6	224.0	250.3	276.7	355.7	430.4	509.4	584.1
77.5°	144.9	149.3	153.7	175.7	197.6	219.6	241.5	298.6	360.1	417.2	474.3
80°	118.6	118.6	123.0	140.5	158.1	171.3	188.8	228.4	267.9	303.0	342.5
82.5°	87.8	92.2	92.2	105.4	114.2	127.4	136.1	158.1	175.7	197.6	215.2
85°	74.7	70.3	70.3	79.0	83.4	92.2	96.6	109.8	118.6	131.7	140.5
87.5°	30.7	26.3	26.3	30.7	39.5	43.9	48.3	48.3	52.7	52.7	52.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	3240.9	3249.7	3262.9	3271.6	3293.6	3311.2	3333.1	3350.7	3363.9	3385.8	3377.0
5°	3122.3	3161.9	3201.4	3240.9	3271.6	3302.4	3328.7	3359.5	3394.6	3460.5	3478.0
7.5°	2771.0	2823.7	2872.0	2924.7	2986.2	3047.7	3109.2	3170.6	3227.7	3311.2	3363.9
10°	2424.1	2498.7	2569.0	2643.7	2700.8	2757.8	2810.5	2867.6	2946.7	3030.1	3126.7
12.5°	2204.5	2279.2	2353.8	2428.5	2511.9	2591.0	2674.4	2753.5	2828.1	2894.0	3003.8
15°	2059.6	2143.0	2222.1	2301.1	2402.1	2498.7	2599.8	2696.4	2806.2	2894.0	2968.6
17.5°	2024.5	2125.5	2222.1	2323.1	2428.5	2533.9	2639.3	2744.7	2854.5	2986.2	3082.8
20°	1963.0	2099.1	2235.3	2371.4	2507.5	2639.3	2775.4	2907.2	3052.1	3210.2	3254.1
22.5°	1927.9	2090.3	2257.2	2419.7	2604.1	2793.0	2977.4	3161.9	3315.6	3434.1	3565.9
25°	1923.5	2125.5	2331.9	2533.9	2766.6	2995.0	3227.7	3456.1	3653.7	3772.3	3877.7
27.5°	1919.1	2165.0	2406.5	2648.1	2933.5	3214.6	3500.0	3781.1	3965.5	4136.8	4224.6
30°	1866.4	2160.6	2459.2	2753.5	3074.0	3394.6	3715.2	4035.8	4224.6	4343.2	4387.1
32.5°	1800.5	2147.4	2494.4	2841.3	3205.8	3570.3	3930.4	4294.9	4444.2	4545.2	4510.0
35°	1747.8	2129.9	2507.5	2885.2	3271.6	3662.5	4048.9	4435.4	4650.6	4791.1	4734.0
37.5°	1699.5	2099.1	2498.7	2898.4	3350.7	3803.0	4255.3	4707.7	4914.1	5063.4	4997.5
40°	1642.4	2068.4	2498.7	2924.7	3442.9	3956.7	4474.9	4988.7	5256.6	5383.9	5282.9
42.5°	1594.1	2037.6	2485.6	2929.1	3482.4	4035.8	4589.1	5142.4	5441.0	5621.1	5493.7
45°	1532.6	1976.2	2415.3	2858.9	3469.3	4079.7	4685.7	5296.1	5643.0	5783.6	5607.9
47.5°	1466.8	1905.9	2340.7	2775.4	3425.4	4075.3	4725.2	5375.2	5695.7	5862.6	5700.1
50°	1444.8	1883.9	2318.7	2757.8	3460.5	4167.5	4870.1	5572.8	5805.5	5941.7	5726.5
52.5°	1440.4	1905.9	2375.8	2841.3	3548.3	4250.9	4958.0	5660.6	5849.4	5994.4	5801.1
55°	1427.2	1932.2	2432.9	2933.5	3671.3	4413.4	5151.2	5889.0	6077.8	6183.2	6038.3
57.5°	1440.4	1984.9	2525.1	3069.6	3829.4	4589.1	5348.8	6108.5	6336.9	6411.6	6380.8
60°	1449.2	2028.9	2604.1	3183.8	3926.0	4668.1	5410.3	6152.5	6389.6	6574.0	6609.2
62.5°	1427.2	1998.1	2564.6	3135.5	3807.4	4479.3	5151.2	5823.1	6213.9	6486.2	6644.3
65°	1361.4	1888.3	2419.7	2946.7	3565.9	4189.5	4808.7	5427.9	5840.7	6244.7	6372.0
67.5°	1216.4	1664.4	2112.3	2560.2	3100.4	3640.5	4176.3	4716.4	5234.6	5625.5	5801.1
70°	1054.0	1405.3	1761.0	2112.3	2604.1	3096.0	3587.8	4079.7	4536.4	4966.8	5133.6
72.5°	917.8	1190.1	1466.8	1739.0	2090.3	2437.3	2788.6	3135.5	3675.7	4106.0	4268.5
75°	781.7	979.3	1172.5	1370.1	1611.7	1853.2	2090.3	2331.9	2713.9	3100.4	3262.9
77.5°	601.6	733.4	860.7	988.1	1155.0	1317.4	1484.3	1646.8	1914.7	2204.5	2288.0
80°	417.2	491.8	562.1	636.8	768.5	900.3	1032.0	1163.7	1339.4	1501.9	1629.2
82.5°	259.1	307.4	351.3	395.2	500.6	606.0	707.0	812.4	882.7	891.5	1018.8
85°	166.9	197.6	224.0	250.3	311.8	377.7	439.1	500.6	447.9	417.2	496.2
87.5°	65.9	83.4	96.6	109.8	105.4	101.0	96.6	92.2	79.0	70.3	87.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	3385.8	3399.0	3412.2	3421.0	3434.1	3438.5	3442.9	3442.9	3447.3	3451.7	3460.5
5°	3548.3	3574.7	3601.0	3623.0	3649.3	3671.3	3688.8	3710.8	3728.4	3728.4	3724.0
7.5°	3412.2	3478.0	3543.9	3609.8	3675.7	3724.0	3767.9	3816.2	3860.1	3868.9	3877.7
10°	3232.1	3302.4	3368.3	3438.5	3504.4	3579.1	3649.3	3719.6	3794.2	3807.4	3825.0
12.5°	3065.3	3148.7	3232.1	3311.2	3394.6	3447.3	3500.0	3548.3	3601.0	3636.1	3671.3
15°	3060.9	3131.1	3201.4	3267.3	3337.5	3368.3	3399.0	3425.4	3456.1	3456.1	3460.5
17.5°	3161.9	3205.8	3249.7	3289.2	3333.1	3337.5	3346.3	3350.7	3355.1	3341.9	3328.7
20°	3359.5	3377.0	3394.6	3412.2	3429.7	3399.0	3372.7	3341.9	3311.2	3276.0	3245.3
22.5°	3649.3	3609.8	3570.3	3530.7	3491.2	3438.5	3381.4	3328.7	3271.6	3227.7	3183.8
25°	3921.6	3873.3	3825.0	3776.7	3728.4	3614.2	3500.0	3381.4	3267.3	3219.0	3170.6
27.5°	4286.1	4211.4	4136.8	4062.1	3987.5	3833.8	3680.1	3526.4	3372.7	3289.2	3210.2
30°	4373.9	4290.5	4207.0	4119.2	4035.8	3886.5	3741.5	3592.2	3442.9	3346.3	3254.1
32.5°	4501.3	4404.7	4308.0	4211.4	4114.8	3969.9	3825.0	3675.7	3530.7	3442.9	3350.7
35°	4712.1	4602.3	4492.5	4378.3	4268.5	4119.2	3974.3	3825.0	3675.7	3574.7	3478.0
37.5°	4892.1	4764.8	4637.4	4510.0	4382.7	4250.9	4114.8	3983.1	3846.9	3745.9	3649.3
40°	5094.1	4953.6	4813.1	4676.9	4536.4	4413.4	4290.5	4163.1	4040.2	3961.1	3882.1
42.5°	5269.8	5098.5	4931.6	4764.8	4593.5	4510.0	4431.0	4347.6	4264.1	4224.6	4180.7
45°	5392.7	5234.6	5072.2	4914.1	4756.0	4694.5	4633.0	4571.5	4510.0	4549.6	4589.1
47.5°	5445.4	5318.1	5195.1	5072.2	4944.8	4966.8	4988.7	5006.3	5028.2	5080.9	5138.0
50°	5493.7	5423.5	5348.8	5278.6	5203.9	5287.3	5366.4	5449.8	5533.3	5643.0	5752.8
52.5°	5590.3	5550.8	5515.7	5476.2	5436.6	5581.6	5726.5	5871.4	6016.3	6139.3	6262.2
55°	5880.2	5849.4	5818.7	5783.6	5752.8	5959.2	6161.2	6367.6	6574.0	6701.4	6828.7
57.5°	6279.8	6262.2	6240.3	6222.7	6200.8	6402.8	6600.4	6798.0	7000.0	7123.0	7250.3
60°	6582.8	6587.2	6587.2	6591.6	6591.6	6745.3	6899.0	7057.1	7210.8	7316.2	7426.0
62.5°	6745.3	6736.5	6727.7	6719.0	6710.2	6837.5	6964.9	7092.2	7219.6	7298.6	7377.7
65°	6569.6	6618.0	6666.3	6714.6	6762.9	6780.4	6793.6	6811.2	6824.4	6872.7	6921.0
67.5°	5981.2	6077.8	6170.0	6266.6	6358.9	6293.0	6231.5	6165.6	6099.8	6112.9	6121.7
70°	5326.9	5436.6	5550.8	5660.6	5770.4	5616.7	5463.0	5304.9	5151.2	5098.5	5045.8
72.5°	4492.5	4589.1	4690.1	4786.7	4883.3	4694.5	4510.0	4321.2	4132.4	4040.2	3947.9
75°	3434.1	3548.3	3666.9	3781.1	3895.2	3684.4	3469.3	3258.5	3043.3	2981.8	2924.7
77.5°	2503.1	2639.3	2775.4	2911.5	3047.7	2858.9	2670.0	2476.8	2288.0	2252.8	2217.7
80°	1822.5	1927.9	2028.9	2134.3	2235.3	2125.5	2015.7	1905.9	1796.1	1791.7	1787.3
82.5°	1229.6	1321.8	1409.7	1501.9	1589.7	1545.8	1506.3	1462.4	1418.4	1462.4	1510.7
85°	632.4	759.7	891.5	1018.8	1146.2	1133.0	1124.2	1111.0	1097.9	1155.0	1207.7
87.5°	127.4	237.1	346.9	452.3	562.1	535.8	509.4	478.7	452.3	469.9	483.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	3464.9	3469.3	3469.3	3469.3	3469.3	3469.3	3460.5	3456.1	3447.3	3438.5	3425.4
5°	3724.0	3719.6	3702.0	3684.4	3662.5	3644.9	3631.8	3614.2	3601.0	3583.4	3557.1
7.5°	3886.5	3895.2	3864.5	3838.2	3807.4	3776.7	3745.9	3715.2	3684.4	3653.7	3592.2
10°	3838.2	3851.3	3833.8	3816.2	3794.2	3776.7	3741.5	3702.0	3666.9	3627.4	3552.7
12.5°	3702.0	3737.1	3728.4	3719.6	3710.8	3702.0	3680.1	3653.7	3631.8	3605.4	3522.0
15°	3460.5	3460.5	3464.9	3469.3	3469.3	3473.7	3478.0	3482.4	3486.8	3491.2	3442.9
17.5°	3315.6	3302.4	3302.4	3302.4	3302.4	3302.4	3320.0	3341.9	3359.5	3377.0	3363.9
20°	3210.2	3179.4	3175.0	3175.0	3170.6	3166.3	3197.0	3232.1	3262.9	3293.6	3311.2
22.5°	3139.9	3096.0	3091.6	3087.2	3082.8	3078.4	3117.9	3157.5	3197.0	3236.5	3298.0
25°	3122.3	3074.0	3078.4	3082.8	3082.8	3087.2	3117.9	3148.7	3179.4	3210.2	3315.6
27.5°	3126.7	3047.7	3052.1	3056.5	3056.5	3060.9	3109.2	3153.1	3201.4	3245.3	3377.0
30°	3157.5	3065.3	3056.5	3047.7	3038.9	3030.1	3096.0	3161.9	3227.7	3293.6	3394.6
32.5°	3262.9	3175.0	3153.1	3131.1	3109.2	3087.2	3166.3	3240.9	3320.0	3394.6	3478.0
35°	3377.0	3280.4	3271.6	3262.9	3249.7	3240.9	3311.2	3385.8	3456.1	3526.4	3601.0
37.5°	3548.3	3451.7	3442.9	3429.7	3421.0	3407.8	3486.8	3561.5	3640.5	3715.2	3781.1
40°	3803.0	3724.0	3719.6	3719.6	3715.2	3710.8	3772.3	3838.2	3899.6	3961.1	4005.0
42.5°	4141.2	4101.6	4114.8	4132.4	4145.6	4158.7	4207.0	4259.7	4308.0	4356.3	4343.2
45°	4628.6	4668.1	4672.5	4676.9	4681.3	4685.7	4698.9	4716.4	4729.6	4742.8	4690.1
47.5°	5190.7	5243.4	5269.8	5296.1	5318.1	5344.4	5326.9	5304.9	5287.3	5265.4	5133.6
50°	5858.2	5968.0	5963.6	5959.2	5950.5	5946.1	5910.9	5875.8	5836.3	5801.1	5607.9
52.5°	6385.2	6508.2	6530.1	6552.1	6574.0	6596.0	6530.1	6464.3	6394.0	6328.1	6086.6
55°	6951.7	7079.1	7083.5	7087.8	7087.8	7092.2	7000.0	6907.8	6811.2	6719.0	6468.6
57.5°	7373.3	7496.2	7483.1	7474.3	7461.1	7447.9	7338.2	7228.4	7118.6	7008.8	6758.5
60°	7531.4	7636.8	7610.4	7584.1	7553.3	7527.0	7443.6	7360.1	7272.3	7188.8	6947.3
62.5°	7456.7	7535.8	7496.2	7461.1	7421.6	7382.1	7276.7	7166.9	7061.5	6951.7	6776.0
65°	6964.9	7013.2	6960.5	6912.2	6863.9	6811.2	6723.3	6635.5	6543.3	6455.5	6336.9
67.5°	6134.9	6143.7	6139.3	6134.9	6130.5	6126.1	5998.8	5871.4	5739.7	5612.3	5603.5
70°	4997.5	4944.8	4953.6	4966.8	4975.5	4984.3	4887.7	4795.5	4698.9	4602.3	4646.2
72.5°	3855.7	3763.5	3785.5	3811.8	3833.8	3855.7	3776.7	3702.0	3623.0	3543.9	3605.4
75°	2863.2	2806.2	2828.1	2854.5	2876.4	2898.4	2867.6	2836.9	2801.8	2771.0	2828.1
77.5°	2182.6	2147.4	2151.8	2151.8	2156.2	2156.2	2160.6	2169.4	2173.8	2178.2	2239.7
80°	1778.5	1774.2	1769.8	1765.4	1756.6	1752.2	1796.1	1840.0	1883.9	1927.9	1958.6
82.5°	1554.6	1598.5	1572.1	1550.2	1523.8	1497.5	1537.0	1576.5	1616.1	1655.6	1642.4
85°	1264.7	1317.4	1269.1	1220.8	1168.1	1119.8	1155.0	1185.7	1220.8	1251.6	1234.0
87.5°	500.6	513.8	434.8	360.1	281.1	202.0	320.6	434.8	553.3	667.5	685.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073

CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9	3161.9
2.5°	3412.2	3394.6	3381.4	3377.0	3368.3	3363.9	3355.1	3346.3	3333.1	3324.3	3311.2
5°	3526.4	3500.0	3469.3	3425.4	3385.8	3341.9	3298.0	3258.5	3219.0	3175.0	3135.5
7.5°	3530.7	3469.3	3407.8	3350.7	3289.2	3232.1	3170.6	3117.9	3060.9	3003.8	2951.1
10°	3482.4	3407.8	3333.1	3258.5	3188.2	3113.6	3038.9	2977.4	2911.5	2845.7	2784.2
12.5°	3442.9	3359.5	3276.0	3188.2	3104.8	3016.9	2929.1	2867.6	2806.2	2744.7	2683.2
15°	3394.6	3341.9	3293.6	3214.6	3135.5	3056.5	2977.4	2894.0	2814.9	2731.5	2648.1
17.5°	3355.1	3341.9	3328.7	3276.0	3223.3	3166.3	3113.6	3030.1	2946.7	2858.9	2775.4
20°	3333.1	3350.7	3368.3	3341.9	3315.6	3284.8	3258.5	3197.0	3135.5	3069.6	3008.2
22.5°	3359.5	3425.4	3486.8	3491.2	3500.0	3504.4	3508.8	3451.7	3394.6	3333.1	3276.0
25°	3421.0	3526.4	3631.8	3688.8	3745.9	3807.4	3864.5	3829.4	3794.2	3759.1	3724.0
27.5°	3504.4	3636.1	3767.9	3851.3	3930.4	4013.8	4097.2	4092.9	4088.5	4079.7	4075.3
30°	3491.2	3592.2	3693.2	3794.2	3895.2	3996.2	4097.2	4149.9	4198.3	4250.9	4303.6
32.5°	3565.9	3649.3	3737.1	3842.5	3947.9	4057.7	4163.1	4272.9	4378.3	4488.1	4597.9
35°	3680.1	3754.7	3833.8	3947.9	4066.5	4180.7	4299.3	4431.0	4567.1	4703.3	4835.0
37.5°	3851.3	3917.2	3987.5	4084.1	4185.1	4281.7	4382.7	4575.9	4769.1	4966.8	5160.0
40°	4048.9	4092.9	4136.8	4229.0	4321.2	4413.4	4505.7	4747.2	4988.7	5230.2	5471.8
42.5°	4334.4	4321.2	4308.0	4382.7	4461.7	4536.4	4615.4	4835.0	5054.6	5274.2	5493.7
45°	4637.4	4584.7	4532.0	4567.1	4606.7	4641.8	4681.3	4905.3	5129.2	5357.6	5581.6
47.5°	5001.9	4870.1	4738.4	4707.7	4676.9	4641.8	4611.0	4852.6	5094.1	5340.0	5581.6
50°	5414.7	5217.1	5023.8	4944.8	4861.4	4782.3	4698.9	4896.5	5098.5	5300.5	5498.1
52.5°	5845.1	5599.1	5357.6	5234.6	5111.7	4984.3	4861.4	5028.2	5199.5	5370.8	5537.7
55°	6213.9	5963.6	5708.9	5564.0	5419.1	5274.2	5129.2	5296.1	5463.0	5629.9	5796.7
57.5°	6508.2	6257.9	6007.5	5871.4	5730.9	5594.7	5454.2	5612.3	5774.8	5937.3	6095.4
60°	6710.2	6468.6	6227.1	6095.4	5963.6	5831.9	5700.1	5889.0	6077.8	6271.0	6459.9
62.5°	6604.8	6429.1	6253.5	6196.4	6139.3	6077.8	6020.7	6200.8	6376.4	6556.5	6736.5
65°	6218.3	6099.8	5981.2	6038.3	6099.8	6156.8	6218.3	6336.9	6455.5	6578.4	6697.0
67.5°	5590.3	5581.6	5568.4	5695.7	5823.1	5954.8	6082.2	6161.2	6235.9	6314.9	6394.0
70°	4690.1	4738.4	4782.3	5001.9	5221.5	5441.0	5660.6	5691.4	5722.1	5752.8	5783.6
72.5°	3671.3	3732.8	3798.6	4088.5	4373.9	4663.7	4953.6	4936.0	4918.5	4896.5	4878.9
75°	2889.6	2946.7	3008.2	3276.0	3543.9	3811.8	4079.7	4005.0	3934.8	3860.1	3785.5
77.5°	2305.5	2367.0	2432.9	2683.2	2933.5	3188.2	3438.5	3258.5	3078.4	2898.4	2718.3
80°	1984.9	2015.7	2042.0	2213.3	2380.2	2551.4	2722.7	2538.3	2349.4	2160.6	1976.2
82.5°	1629.2	1611.7	1598.5	1699.5	1800.5	1901.5	2002.5	1826.9	1651.2	1471.1	1295.5
85°	1216.4	1198.9	1181.3	1234.0	1286.7	1343.8	1396.5	1194.5	992.5	786.1	584.1
87.5°	707.0	724.6	742.2	799.2	856.3	917.8	974.9	768.5	562.1	351.3	144.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
 CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676073
CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	3161.9	3161.9
2.5°	3284.8	3262.9
5°	3104.8	3074.0
7.5°	2907.2	2867.6
10°	2727.1	2674.4
12.5°	2612.9	2547.1
15°	2569.0	2490.0
17.5°	2700.8	2626.1
20°	2902.8	2801.8
22.5°	3148.7	3025.7
25°	3574.7	3425.4
27.5°	3921.6	3767.9
30°	4136.8	3969.9
32.5°	4373.9	4154.3
35°	4619.8	4409.0
37.5°	4918.5	4681.3
40°	5225.9	4979.9
42.5°	5331.3	5173.2
45°	5432.3	5282.9
47.5°	5454.2	5331.3
50°	5476.2	5458.6
52.5°	5537.7	5533.3
55°	5801.1	5805.5
57.5°	6126.1	6152.5
60°	6424.7	6394.0
62.5°	6578.4	6420.3
65°	6473.0	6253.5
67.5°	6156.8	5919.7
70°	5463.0	5142.4
72.5°	4597.9	4316.8
75°	3543.9	3306.8
77.5°	2520.7	2323.1
80°	1774.2	1576.5
82.5°	1137.4	979.3
85°	513.8	447.9
87.5°	144.9	140.5
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676073
CATALOG NUMBER: CCW-SA-2E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)