

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P401156

Luminaire Tested: **ENC-SA1B-740-U-T4FT**

Issue Date: 5/20/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P401156  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2004-754-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/20/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: ENC-SA1B-740-U-T4FT  
Description: ENTRI LED LUMINAIRE  
(1) 70 CRI, 4000K, 450mA LIGHTSQUARE WITH 16 LEDS AND TYPE IV FORWARD  
THROW OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3282 lumens  
Efficiency: N/A  
Efficacy: 129.2 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short - Non-Cutoff  
BUG Rating: B1 - U0 - G1


Input Watts (W): 25.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P401156  
 CATALOG NUMBER: ENC-SA1B-740-U-T4FT

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 5.4 fc  
 Type IV - Short - Non-Cutoff

REPORT NUMBER: P401156  
CATALOG NUMBER: ENC-SA1B-740-U-T4FT

### Luminous Intensity Polar Plot



— Vertical Plane Through 33-Deg Lateral      - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P401156

CATALOG NUMBER: ENC-SA1B-740-U-T4FT

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	797.3	0.0	797.3
	% Fixture	24.3	0.0	24.3
<b>Street Side</b>	Lumens	2484.7	0.0	2484.7
	% Fixture	75.7	0.0	75.7
<b>Total</b>	Lumens	3282.0	0.0	3282.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.0	1.4
10°-20°	132.1	4.0
20°-30°	219.7	6.7
30°-40°	327.8	10.0
40°-50°	457.9	14.0
50°-60°	611.2	18.6
60°-70°	757.8	23.1
70°-80°	655.2	20.0
80°-90°	73.2	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3282.0	100.0
0°-180°	3282.0	100.0



REPORT NUMBER: P401156


CATALOG NUMBER: ENC-SA1B-740-U-T4FT

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	190.0	5.8			
FM	(30°-60°)	1014.8	30.9			
FH	(60°-80°)	1238.5	37.7			G1/1800
FVH	(80°-90°)	41.4	1.3			G1/100
BL	(0°-30°)	208.8	6.4	B1/500		
BM	(30°-60°)	382.0	11.6	B1/1000		
BH	(60°-80°)	174.6	5.3	B1/500		G1/500
BVH	(80°-90°)	31.9	1.0			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G1**

Type IV Short





REPORT NUMBER: P401156

CATALOG NUMBER: ENC-SA1B-740-U-T4FT

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
0°	502.9	502.9	502.9	502.9	502.9	502.9	502.9	502.9	502.9	502.9	502.9
2.5°	456.1	457.1	460.0	463.4	465.4	465.4	470.7	477.1	484.9	491.7	499.0
5°	418.1	419.6	422.0	426.4	431.8	432.7	443.4	454.7	468.8	483.9	498.5
7.5°	380.6	383.5	388.4	394.2	402.5	404.5	419.6	434.7	454.2	477.1	501.0
10°	351.8	353.8	356.2	364.5	374.7	378.2	398.1	417.1	443.9	472.2	503.9
12.5°	344.0	344.0	344.0	347.9	356.2	359.1	380.1	404.5	434.7	468.8	508.3
15°	355.2	354.8	349.4	346.5	351.3	353.8	371.8	395.7	429.8	469.8	516.5
17.5°	380.6	379.1	366.5	356.7	360.1	361.6	373.3	393.7	428.3	473.7	528.7
20°	413.7	410.3	390.8	376.2	375.7	376.7	385.5	399.6	430.8	480.5	541.9
22.5°	457.6	455.6	426.9	404.5	400.6	400.6	404.5	413.2	437.1	488.3	559.9
25°	514.1	508.7	474.1	443.9	435.2	432.7	432.2	432.2	448.3	500.0	582.3
27.5°	572.1	565.8	530.7	489.7	478.0	473.7	465.9	460.0	462.9	512.6	609.1
30°	624.2	615.5	585.7	543.3	525.8	519.0	504.8	492.7	484.9	530.2	644.7
32.5°	653.0	649.6	629.1	590.6	570.6	567.7	544.3	528.2	514.6	553.1	692.5
35°	691.5	687.1	673.9	642.3	618.4	611.1	593.5	574.5	552.6	583.8	752.9
37.5°	727.1	724.6	719.8	697.8	672.5	665.2	649.1	629.1	599.4	629.1	820.6
40°	763.1	760.2	758.2	750.5	732.4	727.5	719.8	696.4	656.4	678.8	887.4
42.5°	815.8	809.4	788.9	788.5	789.9	793.8	794.3	768.5	718.8	740.7	945.9
45°	884.5	866.9	821.1	819.7	836.7	846.9	871.8	849.9	783.6	804.1	1011.2
47.5°	919.5	901.5	854.2	851.3	873.7	888.8	950.2	928.8	850.8	875.2	1078.9
50°	936.6	924.9	883.5	892.7	915.6	930.3	1024.8	1007.8	920.5	952.2	1164.2
52.5°	960.5	941.0	911.8	931.2	965.4	980.5	1091.6	1088.6	979.5	1036.0	1257.7
55°	952.2	942.0	947.3	973.6	1016.5	1038.9	1158.8	1158.8	1039.4	1125.7	1350.3
57.5°	959.0	952.2	996.5	1019.9	1074.0	1106.2	1239.7	1218.3	1090.1	1200.7	1412.7
60°	1017.0	997.5	1032.1	1078.4	1148.1	1179.3	1332.3	1280.6	1131.5	1265.5	1423.9
62.5°	1119.3	1103.8	1107.2	1160.3	1250.4	1286.5	1423.9	1335.7	1159.3	1292.8	1382.0
65°	1288.9	1281.6	1239.7	1271.9	1396.1	1428.8	1538.4	1383.5	1151.5	1272.4	1271.4
67.5°	1517.0	1487.7	1431.2	1460.0	1603.2	1636.4	1676.3	1401.5	1100.8	1150.0	1021.9
70°	1706.1	1681.7	1655.9	1731.4	1896.1	1914.1	1820.1	1384.4	977.5	900.1	685.2
72.5°	1826.4	1808.9	1832.8	2055.0	2318.6	2284.5	1961.9	1265.0	762.6	551.1	342.6
75°	1576.4	1568.2	1704.6	2155.4	2511.1	2498.4	1912.7	946.8	442.5	242.7	155.9
77.5°	792.8	883.0	1026.8	1529.2	1998.0	2000.4	1393.7	455.1	186.2	136.0	107.2
80°	223.2	226.1	342.6	630.6	997.5	1062.8	527.3	154.5	106.2	101.4	79.9
82.5°	53.1	49.2	87.7	186.6	334.8	348.4	158.4	55.6	59.5	63.3	49.2
85°	0.5	0.5	0.5	0.5	0.5	1.0	5.8	5.8	14.1	18.0	14.1
87.5°	0.0	0.0	0.0	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P401156

CATALOG NUMBER: ENC-SA1B-740-U-T4FT

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	502.9	502.9	502.9	502.9	502.9	502.9	502.9	502.9	502.9	502.9	502.9
2.5°	502.4	507.3	515.1	521.9	527.8	532.1	539.0	539.9	541.9	542.9	543.8
5°	506.8	516.1	530.7	543.3	552.1	554.6	560.4	559.9	560.4	560.4	559.9
7.5°	512.6	525.3	545.8	559.9	564.8	563.3	561.9	556.5	552.1	550.2	547.7
10°	520.0	534.6	558.5	568.7	566.3	558.5	549.2	539.4	531.7	527.8	526.8
12.5°	527.3	546.3	568.7	571.6	561.9	547.7	532.1	521.4	511.2	505.8	505.8
15°	539.4	560.4	577.0	571.1	553.6	535.6	514.1	499.5	487.8	480.5	480.0
17.5°	554.1	576.5	585.7	568.7	543.3	518.0	492.2	473.2	458.1	450.8	446.4
20°	572.1	593.1	590.1	560.9	528.2	497.1	464.9	442.0	426.4	418.6	417.1
22.5°	592.6	610.1	591.6	548.2	507.8	467.8	432.7	409.8	399.6	393.7	394.2
25°	617.4	631.1	592.1	533.1	478.5	429.3	398.6	387.9	386.4	384.0	385.0
27.5°	648.6	653.0	590.1	512.6	441.0	388.9	370.8	375.2	379.1	377.7	378.6
30°	685.6	679.3	585.7	482.9	394.7	351.8	352.8	362.6	367.9	366.5	366.9
32.5°	729.0	705.6	577.5	446.9	350.9	329.4	337.2	347.0	352.3	352.3	352.8
35°	777.7	737.3	561.4	400.1	320.2	315.8	322.6	330.4	333.8	331.9	333.3
37.5°	828.9	764.6	535.6	347.9	297.3	305.1	309.0	310.9	310.4	307.5	306.0
40°	876.7	786.0	489.3	296.3	278.3	293.8	295.8	290.4	284.1	278.7	275.3
42.5°	913.2	797.2	424.9	258.8	260.2	281.2	282.6	271.9	259.7	251.5	249.5
45°	950.7	801.1	361.1	228.5	240.7	268.5	272.4	257.8	241.2	231.5	230.0
47.5°	993.6	810.9	298.2	207.6	224.2	259.7	266.1	248.0	229.5	214.9	212.5
50°	1051.1	829.4	251.0	191.5	212.5	255.3	264.1	240.2	216.9	200.8	198.8
52.5°	1124.2	856.7	207.1	178.8	203.2	248.5	261.2	232.4	207.6	188.1	185.2
55°	1187.1	866.9	178.8	168.1	193.5	240.2	258.8	229.5	197.4	175.4	172.0
57.5°	1215.8	837.7	158.9	157.4	183.2	230.0	253.9	219.8	186.2	169.1	166.2
60°	1202.7	765.1	143.8	147.7	171.5	216.9	241.2	210.0	178.4	164.2	161.3
62.5°	1144.2	681.3	132.5	138.4	158.4	200.3	226.6	201.3	171.5	158.9	155.0
65°	1041.4	589.2	124.3	130.1	146.7	184.2	214.9	191.0	163.7	151.1	147.7
67.5°	849.9	468.8	115.5	121.8	136.9	171.0	204.2	182.7	155.0	146.7	143.8
70°	562.4	315.3	107.2	113.5	127.2	158.4	193.0	174.0	146.7	141.3	137.4
72.5°	258.3	169.6	98.4	104.8	116.0	144.2	178.8	160.8	135.5	132.1	126.2
75°	127.7	104.3	87.7	93.6	102.3	127.2	162.3	149.6	125.2	119.4	112.6
77.5°	93.1	78.0	75.5	81.4	88.7	112.6	144.7	137.9	115.0	106.7	102.8
80°	69.2	60.4	63.3	69.2	76.0	101.8	135.5	129.1	106.2	97.9	95.0
82.5°	42.4	40.4	48.7	55.6	63.8	93.6	129.1	117.9	95.5	87.7	84.3
85°	12.2	14.6	24.9	36.1	45.3	75.5	120.4	103.3	80.4	67.2	64.8
87.5°	0.0	1.5	7.8	16.6	26.8	50.2	92.6	80.9	61.4	49.7	47.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)