

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P400995

Luminaire Tested: **ENC-SA1A-750-U-T4FT-HSS**

Issue Date: 5/20/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P400995  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2004-754-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/20/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: ENC-SA1A-750-U-T4FT-HSS  
Description: ENTRI LED LUMINAIRE  
(1) 70 CRI, 5000K, 350mA LIGHTSQUARE WITH 16 LEDS AND TYPE IV FORWARD  
THROW OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1936 lumens  
Efficiency: N/A  
Efficacy: 96.3 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short - Semi-Cutoff  
BUG Rating: B0 - U0 - G1


Input Watts (W): 20.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P400995  
 CATALOG NUMBER: ENC-SA1A-750-U-T4FT-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 3 fc  
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P400995  
CATALOG NUMBER: ENC-SA1A-750-U-T4FT-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 34-Deg Lateral    - - - Horizontal Cone Through 71-Deg Vertical

REPORT NUMBER: P400995

CATALOG NUMBER: ENC-SA1A-750-U-T4FT-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	214.1	0.0	214.1
	% Fixture	11.1	0.0	11.1
<b>Street Side</b>	Lumens	1721.9	0.0	1721.9
	% Fixture	88.9	0.0	88.9
<b>Total</b>	Lumens	1936.0	0.0	1936.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.4	1.4
10°-20°	60.6	3.1
20°-30°	90.4	4.7
30°-40°	151.1	7.8
40°-50°	272.8	14.1
50°-60°	432.9	22.4
60°-70°	581.7	30.0
70°-80°	308.7	15.9
80°-90°	11.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	1936.0	100.0
0°-180°	1936.0	100.0



REPORT NUMBER: P400995


CATALOG NUMBER: ENC-SA1A-750-U-T4FT-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	103.0	5.3			
FM	(30°-60°)	743.2	38.4			
FH	(60°-80°)	865.4	44.7			G1/1800
FVH	(80°-90°)	10.4	0.5			G1/100
BL	(0°-30°)	74.5	3.8	B0/110		
BM	(30°-60°)	113.6	5.9	B0/220		
BH	(60°-80°)	25.0	1.3	B0/110		G0/110
BVH	(80°-90°)	1.0	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B0-U0-G1**

Type IV Short





REPORT NUMBER: P400995

CATALOG NUMBER: ENC-SA1A-750-U-T4FT-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	34°	35°	45°	55°	65°	75°	85°
0°	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0
2.5°	273.2	269.7	272.8	274.3	275.5	277.0	279.4	283.7	288.3	293.8	296.9
5°	238.2	240.1	241.3	245.6	249.8	250.6	258.0	266.6	277.4	288.3	297.6
7.5°	209.8	209.8	213.3	219.9	226.9	227.7	240.5	251.8	267.3	284.0	299.2
10°	187.3	188.1	190.8	197.4	206.3	208.3	222.6	238.2	257.6	279.4	300.7
12.5°	179.9	179.5	179.1	183.8	191.2	193.1	209.0	227.7	250.6	277.0	304.6
15°	184.6	183.4	180.7	181.5	186.1	188.1	202.1	220.7	246.4	276.7	311.2
17.5°	192.0	190.4	185.3	183.8	188.8	190.8	202.4	218.8	244.8	278.6	319.0
20°	200.9	199.3	191.6	189.6	194.7	196.2	208.3	222.3	245.6	282.5	329.5
22.5°	213.7	211.8	200.5	198.2	203.2	204.8	217.6	230.4	250.2	289.5	343.9
25°	229.3	226.9	212.5	209.4	215.7	217.2	230.0	242.1	258.0	298.8	362.1
27.5°	246.4	243.6	228.5	222.3	229.3	231.6	243.6	256.8	269.3	310.5	386.2
30°	261.9	258.8	244.0	237.0	244.0	245.2	259.6	274.3	287.5	330.3	421.6
32.5°	305.0	297.3	274.3	254.1	258.8	261.1	278.6	301.9	321.7	354.0	467.1
35°	369.5	363.3	335.3	300.4	284.0	284.8	307.4	336.9	345.8	381.6	523.4
37.5°	431.7	426.3	401.8	369.5	338.4	339.6	343.5	371.9	382.3	429.4	592.2
40°	499.7	491.1	471.7	441.0	419.7	414.6	395.6	415.4	438.3	489.6	667.2
42.5°	531.2	523.0	502.8	504.7	502.4	493.5	455.8	483.4	509.0	577.0	749.9
45°	583.2	567.3	525.7	528.8	525.7	526.5	535.8	575.9	598.0	669.5	843.6
47.5°	631.4	613.2	569.6	566.5	580.1	587.1	637.2	685.8	687.8	749.9	917.0
50°	675.3	662.1	622.1	622.5	647.4	655.1	755.4	799.7	760.4	811.7	974.5
52.5°	733.6	715.0	679.2	692.0	730.9	737.9	873.1	899.5	812.9	867.7	1019.6
55°	787.6	777.5	751.1	770.1	829.6	847.9	992.8	976.5	849.8	917.4	1041.4
57.5°	876.2	866.5	859.5	869.2	948.9	971.8	1114.0	1030.9	878.5	950.4	1031.3
60°	1023.9	1014.2	993.2	1002.1	1105.9	1117.5	1209.2	1086.0	889.8	959.8	991.6
62.5°	1206.1	1194.1	1160.3	1201.4	1305.6	1305.2	1307.9	1115.2	875.4	932.2	887.1
65°	1370.5	1353.8	1336.3	1420.2	1546.9	1529.4	1412.8	1118.7	830.0	798.9	686.2
67.5°	1490.2	1483.5	1493.3	1624.2	1760.6	1743.1	1514.6	1070.5	690.9	576.6	423.9
70°	1485.5	1471.9	1533.7	1742.7	1866.7	1852.3	1510.4	879.7	460.8	305.4	177.6
71°	1405.1	1389.5	1483.5	1731.1	1872.9	1859.3	1456.0	752.7	364.5	215.7	117.0
72.5°	1085.7	1132.7	1282.3	1606.3	1813.0	1795.6	1307.9	576.2	230.8	124.7	58.7
75°	459.3	484.9	761.2	1146.7	1360.0	1351.0	881.7	266.2	106.1	56.3	22.5
77.5°	118.1	116.6	233.1	491.9	791.9	805.9	406.4	91.3	55.2	40.0	12.8
80°	22.9	24.9	66.4	171.0	302.3	310.5	132.5	40.0	36.9	31.5	6.6
82.5°	2.3	2.7	11.7	52.8	101.4	97.9	29.1	15.2	22.5	21.4	3.1
85°	0.0	0.0	0.4	0.4	0.4	0.4	0.4	1.6	5.4	5.8	0.8
87.5°	0.0	0.0	0.4	0.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P400995

CATALOG NUMBER: ENC-SA1A-750-U-T4FT-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0
2.5°	299.2	302.7	306.6	309.3	312.0	312.4	316.3	315.5	316.7	317.1	316.7
5°	302.7	307.4	314.7	318.6	320.2	317.5	316.7	312.4	310.9	308.9	307.0
7.5°	306.6	312.4	321.0	322.9	317.5	307.4	299.2	288.7	279.0	272.8	273.6
10°	310.9	318.2	325.2	320.2	306.2	286.4	263.4	240.1	219.5	211.8	214.5
12.5°	316.3	325.2	328.3	314.3	287.2	247.1	205.6	170.2	148.8	136.0	134.4
15°	324.5	333.4	329.9	305.0	256.8	194.3	142.6	106.9	86.3	79.7	76.2
17.5°	334.6	343.1	329.9	288.3	213.7	139.1	86.7	64.9	58.3	56.7	57.1
20°	347.0	355.1	328.3	263.1	164.8	85.5	57.9	53.6	53.6	53.6	53.2
22.5°	363.7	368.0	326.0	229.6	113.5	57.9	51.3	50.9	51.3	51.3	51.3
25°	383.9	383.1	321.7	189.6	71.5	49.3	49.0	49.0	49.3	49.7	49.7
27.5°	410.7	402.6	314.3	141.8	50.5	45.9	46.6	47.4	48.2	49.0	49.0
30°	448.0	428.2	302.3	96.0	42.7	42.4	43.9	46.2	47.4	48.2	48.2
32.5°	488.0	454.6	281.7	61.4	39.2	38.9	40.4	43.9	47.0	47.8	47.8
35°	538.6	483.0	251.0	44.3	36.9	36.1	37.7	40.8	45.5	47.8	47.8
37.5°	591.8	513.3	206.3	37.3	34.6	33.8	35.0	37.3	42.7	47.0	47.4
40°	648.5	540.1	155.0	34.6	32.3	31.9	32.3	34.6	38.9	44.7	45.9
42.5°	705.6	562.6	108.4	31.9	30.3	29.5	30.3	31.9	35.7	40.8	41.6
45°	768.6	587.5	72.3	29.5	28.8	28.0	28.8	29.9	32.6	35.4	35.7
47.5°	814.4	596.4	49.7	26.8	26.4	26.8	27.2	28.0	29.5	29.9	29.5
50°	844.7	591.8	35.7	24.1	24.5	25.6	25.6	26.0	26.0	24.9	24.5
52.5°	866.9	574.7	27.6	20.6	22.9	24.1	24.1	23.3	22.5	21.0	20.6
55°	869.2	536.2	21.8	17.9	20.6	22.5	22.1	20.6	19.0	17.5	17.5
57.5°	839.7	477.9	17.9	15.2	17.9	19.8	19.0	17.5	15.5	14.4	14.4
60°	791.9	418.1	15.2	12.8	14.8	16.7	15.5	14.4	12.4	11.3	11.3
62.5°	703.7	359.0	12.4	10.5	12.0	13.2	12.8	11.7	9.7	8.9	8.5
65°	539.3	273.2	9.3	8.2	9.3	10.9	10.1	8.9	7.8	6.6	6.2
67.5°	324.1	164.4	7.4	6.2	7.4	8.5	7.8	6.6	5.4	4.7	4.7
70°	137.2	70.3	5.8	4.7	5.4	6.6	6.2	5.4	4.3	3.9	3.9
71°	93.3	50.1	5.1	4.3	5.1	6.2	5.8	5.1	4.3	3.9	3.9
72.5°	47.8	25.6	4.3	3.5	4.7	5.4	5.4	4.7	3.9	3.9	3.9
75°	17.1	10.9	3.5	3.1	3.9	3.9	4.3	4.3	4.3	4.3	3.9
77.5°	9.7	6.6	3.1	3.1	3.1	3.5	4.3	4.7	5.1	5.1	4.7
80°	5.4	3.5	1.9	2.3	3.1	3.5	4.3	4.7	5.4	5.4	5.1
82.5°	2.7	1.2	0.4	1.2	1.9	3.1	3.5	3.9	4.7	4.3	4.3
85°	0.4	0.0	0.0	0.4	1.2	1.6	2.3	3.1	3.9	3.9	3.5
87.5°	0.0	0.0	0.0	0.0	0.4	0.8	1.2	1.9	2.7	3.1	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)