

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P401181

Luminaire Tested: **ENT-SA1B-760-U-SL3-HSS**

Issue Date: 5/20/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P401181  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2004-754-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/20/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: ENT-SA1B-760-U-SL3-HSS  
Description: ENTRI LED LUMINAIRE  
(1) 70 CRI, 5700K, 450mA LIGHTSQUARE WITH 16 LEDS AND TYPE III SPILL  
LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2872 lumens  
Efficiency: N/A  
Efficacy: 113.1 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Short - Semi-Cutoff  
BUG Rating: B1 - U0 - G1


Input Watts (W): 25.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P401181  
 CATALOG NUMBER: ENT-SA1B-760-U-SL3-HSS

### Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 8.8 fc  
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P401181

CATALOG NUMBER: ENT-SA1B-760-U-SL3-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 60-Deg Lateral    - - - Horizontal Cone Through 68-Deg Vertical

REPORT NUMBER: P401181

CATALOG NUMBER: ENT-SA1B-760-U-SL3-HSS

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	321.1	0.0	321.1
	% Fixture	11.2	0.0	11.2
<b>Street Side</b>	Lumens	2550.9	0.0	2550.9
	% Fixture	88.8	0.0	88.8
<b>Total</b>	Lumens	2872.0	0.0	2872.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.3	2.5
10°-20°	145.5	5.1
20°-30°	191.6	6.7
30°-40°	264.4	9.2
40°-50°	400.7	14.0
50°-60°	646.6	22.5
60°-70°	768.2	26.7
70°-80°	362.1	12.6
80°-90°	21.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2872.0	100.0
0°-180°	2872.0	100.0



REPORT NUMBER: P401181


CATALOG NUMBER: ENT-SA1B-760-U-SL3-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	288.2	10.0			
FM	(30°-60°)	1188.3	41.4			
FH	(60°-80°)	1053.6	36.7			G1/1800
FVH	(80°-90°)	20.7	0.7			G1/100
BL	(0°-30°)	120.2	4.2	B1/500		
BM	(30°-60°)	123.4	4.3	B0/220		
BH	(60°-80°)	76.6	2.7	B0/110		G0/110
BVH	(80°-90°)	0.9	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G1**

Type III Short





REPORT NUMBER: P401181

CATALOG NUMBER: ENT-SA1B-760-U-SL3-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	60°	65°	75°	85°
0°	879.1	879.1	879.1	879.1	879.1	879.1	879.1	879.1	879.1	879.1	879.1
2.5°	871.3	869.3	874.7	876.2	877.6	880.5	880.1	880.5	881.0	880.1	874.2
5°	811.8	815.3	820.1	826.5	832.8	847.4	853.3	859.1	863.0	865.9	860.6
7.5°	753.4	760.2	764.1	775.8	785.5	800.6	813.3	823.5	833.3	844.0	838.6
10°	706.6	709.0	712.4	723.2	737.8	760.7	777.2	789.9	801.6	819.6	815.3
12.5°	660.8	662.2	669.1	680.8	695.9	724.1	746.1	760.7	773.8	796.2	796.7
15°	627.2	627.6	632.0	642.7	660.3	690.5	718.8	734.8	753.4	780.7	782.1
17.5°	605.2	604.7	605.7	612.5	629.1	657.9	692.0	711.0	732.9	768.0	769.4
20°	598.4	597.4	595.5	594.0	604.3	629.1	667.6	688.6	714.4	758.7	759.2
22.5°	604.3	602.3	597.9	589.6	592.6	608.6	640.8	666.1	697.8	753.9	750.4
25°	618.4	618.4	612.5	599.4	592.6	596.0	621.8	646.2	681.2	751.4	744.1
27.5°	641.8	640.8	633.0	619.4	606.7	597.4	610.1	633.0	669.1	754.3	741.2
30°	670.0	667.1	658.8	649.1	633.5	613.5	612.5	629.6	663.2	763.6	743.1
32.5°	696.8	696.8	693.4	684.2	669.1	642.7	627.6	641.3	670.5	778.7	749.5
35°	730.0	729.5	730.5	727.0	713.9	686.1	661.8	668.6	692.9	804.0	764.6
37.5°	756.3	756.8	765.1	770.9	765.1	735.8	710.5	710.5	730.9	842.1	790.4
40°	782.1	783.1	798.7	815.7	817.2	793.8	769.4	769.0	780.7	888.8	830.4
42.5°	805.5	809.4	831.8	861.1	878.1	862.5	844.5	838.6	844.5	959.5	895.2
45°	830.4	838.2	869.3	911.7	939.5	940.0	933.2	926.4	929.3	1038.9	981.9
47.5°	862.5	871.3	910.3	962.4	1015.0	1028.7	1035.0	1032.6	1024.8	1139.3	1094.0
50°	914.7	922.9	959.5	1018.0	1090.1	1139.3	1156.4	1159.3	1149.1	1250.4	1221.2
52.5°	1003.3	1008.2	1042.3	1088.6	1169.5	1261.6	1306.4	1306.9	1284.0	1380.5	1358.6
55°	1098.4	1111.0	1151.0	1204.6	1287.9	1391.2	1503.3	1515.5	1444.8	1494.5	1459.0
57.5°	1099.8	1112.0	1178.3	1281.1	1455.6	1592.5	1692.4	1701.2	1622.7	1586.2	1553.5
60°	983.9	990.2	1082.3	1232.9	1515.5	1863.9	1907.8	1894.6	1747.5	1680.7	1671.9
62.5°	694.4	697.3	806.5	1004.8	1383.0	1993.5	2235.7	2165.1	1924.8	1820.1	1849.3
65°	437.1	435.6	481.0	639.3	1028.7	1865.9	2641.2	2589.5	2250.8	1994.5	1987.7
67.5°	322.6	314.8	327.0	376.2	587.7	1464.8	2715.7	2948.6	2561.2	2067.1	1867.8
68°	309.4	302.6	315.3	353.3	508.3	1325.9	2679.7	2974.5	2610.5	2055.4	1826.9
70°	262.7	256.3	267.0	295.8	353.8	860.6	2364.4	2860.0	2655.3	1956.0	1610.0
72.5°	186.6	190.0	218.3	253.9	299.7	441.5	1741.1	2348.8	2284.0	1739.7	1225.1
75°	110.6	117.0	154.0	204.7	275.3	291.4	1123.2	1707.5	1675.8	1204.6	663.7
77.5°	39.0	41.4	76.5	136.4	227.1	231.0	625.7	1073.5	998.5	492.2	195.9
80°	14.1	14.1	28.3	76.0	146.7	176.4	332.3	573.1	394.2	127.7	54.1
82.5°	2.4	2.4	6.3	25.8	64.8	94.0	154.5	203.7	117.0	28.3	26.8
85°	0.0	0.0	0.0	0.0	1.0	1.0	45.3	45.8	21.4	3.9	11.7
87.5°	0.0	0.0	0.0	0.0	0.0	0.5	1.0	1.0	1.0	1.0	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P401181

CATALOG NUMBER: ENT-SA1B-760-U-SL3-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	879.1	879.1	879.1	879.1	879.1	879.1	879.1	879.1	879.1	879.1	879.1
2.5°	871.8	870.8	865.4	855.7	847.4	833.8	831.3	818.2	813.3	809.4	813.3
5°	856.7	851.3	833.3	811.4	781.6	746.5	726.1	697.8	692.0	676.4	685.6
7.5°	831.8	819.6	786.0	738.7	684.2	630.6	589.6	550.2	516.5	504.8	501.4
10°	805.5	788.4	731.9	658.8	579.9	497.5	436.6	379.6	347.9	318.2	317.2
12.5°	780.7	754.8	673.0	571.1	461.0	363.0	284.1	224.2	186.6	166.2	171.5
15°	760.7	726.1	613.5	483.4	344.0	233.9	160.8	122.3	109.2	102.8	103.8
17.5°	741.2	695.4	556.0	391.8	245.1	144.2	104.3	91.1	87.2	85.8	84.8
20°	723.6	665.7	495.6	308.9	161.8	99.9	85.8	81.4	79.9	78.9	78.9
22.5°	706.1	634.5	435.2	229.0	110.6	81.9	77.0	75.0	74.1	72.6	72.6
25°	690.0	604.3	374.7	160.3	84.8	73.1	69.7	67.7	65.8	64.3	64.3
27.5°	677.8	581.3	318.7	113.5	71.1	65.8	62.4	59.0	56.5	54.6	54.6
30°	670.0	558.9	264.6	85.8	63.3	58.5	54.1	49.7	45.8	43.4	42.9
32.5°	665.7	540.4	214.4	70.2	56.5	51.2	45.8	40.9	36.5	33.6	33.6
35°	667.6	525.8	164.2	59.5	51.2	44.8	39.0	33.1	29.2	26.8	26.3
37.5°	680.3	517.5	122.3	52.6	45.8	39.0	33.1	27.3	23.4	21.4	21.0
40°	704.1	519.5	93.1	47.8	41.9	34.1	27.3	22.4	19.0	17.1	17.1
42.5°	752.4	533.6	73.6	43.9	37.5	29.2	22.9	18.5	15.6	14.1	13.6
45°	816.2	560.4	60.4	40.4	33.1	24.9	19.5	15.6	12.7	11.2	11.2
47.5°	912.7	603.3	52.1	37.0	28.8	21.0	16.1	12.7	9.7	8.8	8.3
50°	1024.3	663.2	45.8	33.1	25.3	17.5	13.6	9.7	7.8	6.3	6.3
52.5°	1138.3	730.0	41.4	29.7	21.9	15.1	10.7	7.3	5.4	4.4	4.4
55°	1243.1	786.0	37.0	26.8	18.5	12.7	8.8	5.8	3.9	2.9	2.9
57.5°	1344.5	837.2	32.2	23.4	15.1	10.2	6.8	4.4	2.9	1.9	1.9
60°	1471.6	903.5	27.8	20.0	12.2	8.3	5.4	3.4	1.9	1.5	1.0
62.5°	1625.1	951.7	23.4	16.1	9.7	6.3	3.9	2.4	1.5	0.5	0.5
65°	1681.7	887.9	19.5	13.2	7.8	4.9	2.9	1.9	1.0	0.5	0.5
67.5°	1523.8	715.4	15.6	10.2	5.8	3.4	2.4	1.5	1.0	0.5	0.5
68°	1479.9	680.3	15.1	9.7	5.4	3.4	1.9	1.5	0.5	0.5	0.0
70°	1249.4	546.3	12.2	7.3	4.4	2.9	1.9	1.0	0.5	0.5	0.0
72.5°	926.4	376.7	8.8	4.9	2.9	1.9	1.5	1.0	0.5	0.5	0.0
75°	488.8	146.7	6.8	3.9	2.4	1.9	1.5	1.5	1.0	0.5	0.5
77.5°	140.3	46.3	5.4	2.9	2.4	2.4	2.4	1.9	1.9	1.5	1.0
80°	40.9	15.1	3.4	1.9	2.4	2.4	2.9	2.4	2.4	1.9	1.9
82.5°	21.9	5.8	1.9	1.5	1.5	1.9	2.4	1.9	1.5	1.0	0.5
85°	9.3	1.9	1.5	1.0	1.0	1.0	1.0	1.0	1.0	0.5	0.5
87.5°	0.5	1.0	1.0	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)