

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P401539

Luminaire Tested: **ENT-SA1D-760-U-SL2-HSS**

Issue Date: 5/20/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P401539  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2004-754-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/20/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: ENT-SA1D-760-U-SL2-HSS  
Description: ENTRI LED LUMINAIRE  
(1) 70 CRI, 5700K, 800mA LIGHTSQUARE WITH 16 LEDS AND TYPE II SPILL LIGHT  
ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4564 lumens  
Efficiency: N/A  
Efficacy: 105.9 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Medium - Non-Cutoff  
BUG Rating: B1 - U0 - G1

Input Watts (W): 43.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P401539

CATALOG NUMBER: ENT-SA1D-760-U-SL2-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 11.8 fc  
 Type III - Medium - Non-Cutoff

REPORT NUMBER: P401539  
CATALOG NUMBER: ENT-SA1D-760-U-SL2-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 64-Deg Lateral    - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P401539

CATALOG NUMBER: ENT-SA1D-760-U-SL2-HSS

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	586.3	0.0	586.3
	% Fixture	12.8	0.0	12.8
<b>Street Side</b>	Lumens	3977.7	0.0	3977.7
	% Fixture	87.2	0.0	87.2
<b>Total</b>	Lumens	4564.0	0.0	4564.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.6	2.2
10°-20°	220.9	4.8
20°-30°	304.3	6.7
30°-40°	419.0	9.2
40°-50°	624.5	13.7
50°-60°	986.5	21.6
60°-70°	1117.8	24.5
70°-80°	733.9	16.1
80°-90°	57.5	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4564.0	100.0
0°-180°	4564.0	100.0



REPORT NUMBER: P401539


CATALOG NUMBER: ENT-SA1D-760-U-SL2-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	420.7	9.2			
FM	(30°-60°)	1816.4	39.8			
FH	(60°-80°)	1686.2	36.9			G1/1800
FVH	(80°-90°)	54.4	1.2			G1/100
BL	(0°-30°)	204.1	4.5	B1/500		
BM	(30°-60°)	213.5	4.7	B0/220		
BH	(60°-80°)	165.5	3.6	B1/500		G1/500
BVH	(80°-90°)	3.2	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G1**

Type III Medium





REPORT NUMBER: P401539

CATALOG NUMBER: ENT-SA1D-760-U-SL2-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	64°	65°	75°	85°
0°	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4
2.5°	1148.5	1148.5	1154.2	1159.8	1163.0	1171.8	1178.2	1183.1	1183.1	1186.3	1180.6
5°	1072.3	1072.3	1077.1	1090.8	1105.2	1123.7	1144.5	1165.4	1169.4	1184.7	1183.9
7.5°	1001.7	1008.1	1016.1	1029.8	1045.0	1072.3	1101.2	1137.3	1141.3	1178.2	1186.3
10°	952.7	956.7	961.5	976.8	999.3	1030.6	1061.9	1104.4	1111.6	1167.0	1186.3
12.5°	913.4	914.2	921.4	938.3	959.9	990.4	1025.7	1072.3	1081.1	1146.9	1183.1
15°	885.3	884.5	892.5	908.6	929.4	960.7	995.2	1044.2	1053.8	1130.1	1182.2
17.5°	868.4	869.2	875.7	887.7	907.8	937.5	972.8	1020.9	1030.6	1116.4	1186.3
20°	868.4	868.4	872.4	878.1	893.3	919.8	954.3	1004.1	1013.7	1107.6	1191.9
22.5°	885.3	883.7	886.9	882.1	889.3	907.8	943.1	992.8	1003.3	1103.6	1200.7
25°	915.8	912.6	915.0	904.5	896.5	904.5	935.8	988.0	999.3	1104.4	1208.7
27.5°	958.3	958.3	953.5	939.1	919.0	910.2	935.0	984.8	996.0	1104.4	1214.4
30°	1017.7	1015.3	1008.1	993.6	962.3	932.6	943.1	984.8	996.0	1105.2	1216.0
32.5°	1077.1	1078.7	1082.7	1068.3	1025.7	971.2	962.3	992.0	1001.7	1104.4	1213.6
35°	1137.3	1138.1	1155.8	1157.4	1102.8	1033.0	995.2	1011.3	1017.7	1112.4	1215.2
37.5°	1190.3	1194.3	1228.8	1245.7	1200.7	1112.4	1047.4	1047.4	1050.6	1134.1	1224.8
40°	1249.7	1260.1	1301.8	1339.6	1321.9	1214.4	1123.7	1100.4	1102.0	1173.4	1246.5
42.5°	1318.7	1331.5	1386.1	1440.7	1439.9	1339.6	1220.0	1184.7	1186.3	1241.6	1290.6
45°	1406.2	1415.0	1484.0	1552.3	1566.7	1477.6	1341.2	1294.6	1296.2	1345.2	1376.5
47.5°	1512.9	1523.4	1590.0	1671.8	1708.8	1643.8	1498.5	1447.9	1443.1	1477.6	1500.1
50°	1652.6	1672.6	1712.0	1790.6	1879.7	1836.4	1683.1	1632.5	1626.1	1653.4	1660.6
52.5°	1785.8	1804.3	1820.3	1892.6	2065.1	2075.6	1909.4	1854.0	1847.6	1854.0	1862.9
55°	1805.9	1816.3	1828.4	1926.3	2215.2	2379.7	2167.1	2101.2	2082.8	2070.7	2100.4
57.5°	1646.2	1639.7	1679.9	1813.1	2240.1	2716.0	2515.4	2387.8	2370.1	2303.5	2273.8
60°	1303.4	1294.6	1332.3	1514.5	2100.4	2883.0	2998.6	2704.8	2661.5	2438.3	2409.4
62.5°	915.8	905.3	954.3	1061.9	1629.3	2850.1	3543.5	3005.0	2919.1	2557.9	2518.6
65°	705.5	700.7	727.2	751.2	994.4	2468.8	3843.7	3590.9	3413.5	2688.0	2637.4
67.5°	553.0	559.4	592.3	662.2	642.1	1538.6	3815.6	4485.0	4307.6	2927.1	2895.0
70°	444.6	446.3	487.2	598.7	606.0	783.4	3230.5	4947.3	4944.9	3313.2	3099.7
72.5°	268.9	276.1	342.7	517.7	611.6	599.6	2171.9	4533.2	4595.8	3403.1	2795.5
75°	129.2	136.4	177.4	347.5	607.6	583.5	1175.0	3432.0	3512.2	3051.5	2266.6
77.5°	48.2	54.6	81.9	170.2	450.3	534.5	618.0	2313.9	2377.3	2233.7	1535.4
80°	15.2	17.7	32.1	77.9	228.7	441.4	398.1	1305.0	1347.6	977.6	516.1
82.5°	1.6	2.4	8.8	26.5	88.3	224.7	233.6	491.2	512.9	191.0	104.3
85°	0.0	0.0	0.0	0.0	1.6	1.6	57.8	93.9	77.1	18.5	30.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.8	1.6	2.4	2.4	2.4	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P401539

CATALOG NUMBER: ENT-SA1D-760-U-SL2-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4	1181.4
2.5°	1179.8	1179.8	1174.2	1165.4	1154.2	1138.1	1134.1	1121.3	1121.3	1110.8	1109.2
5°	1181.4	1176.6	1158.2	1130.9	1093.2	1052.2	1026.5	998.5	974.4	959.1	960.7
7.5°	1181.4	1171.0	1134.1	1073.9	1003.3	932.6	878.9	816.3	787.4	768.1	776.9
10°	1178.2	1160.6	1096.4	1004.9	893.3	795.4	707.1	634.9	585.1	564.2	546.6
12.5°	1171.0	1145.3	1049.0	919.0	776.1	647.7	525.7	431.0	365.2	332.3	328.3
15°	1164.6	1129.3	993.6	825.1	643.7	475.9	339.5	248.8	192.6	179.8	181.4
17.5°	1163.0	1114.0	940.7	725.6	514.5	317.0	195.8	158.1	150.1	146.9	146.1
20°	1163.8	1100.4	882.9	626.8	364.4	197.4	148.5	139.7	136.4	134.8	134.0
22.5°	1167.0	1085.1	825.9	523.3	248.8	144.5	132.4	126.8	122.8	120.4	119.6
25°	1167.0	1068.3	762.5	413.3	162.9	126.8	118.8	111.6	105.9	102.7	102.7
27.5°	1164.6	1049.0	696.7	313.8	129.2	113.2	104.3	94.7	87.5	83.5	83.5
30°	1157.4	1025.7	633.3	219.1	113.2	101.1	89.9	77.9	69.0	65.0	63.4
32.5°	1146.9	1000.9	560.2	154.1	101.9	88.3	75.4	62.6	54.6	49.8	49.8
35°	1135.7	976.0	481.6	118.0	92.3	77.9	63.4	50.6	43.3	40.1	39.3
37.5°	1130.1	949.5	404.5	101.9	82.7	66.6	51.4	40.9	35.3	32.9	32.1
40°	1134.1	929.4	329.1	91.5	73.8	56.2	42.5	34.5	29.7	26.5	26.5
42.5°	1158.2	918.2	257.6	83.5	65.8	47.4	35.3	28.1	23.3	20.9	20.9
45°	1207.1	926.2	195.8	76.2	56.2	39.3	29.7	22.5	17.7	15.2	15.2
47.5°	1289.0	958.3	148.5	69.8	48.2	32.1	24.1	17.7	13.6	12.0	11.2
50°	1408.6	1021.7	116.4	63.4	40.1	27.3	20.1	13.6	10.4	8.8	8.8
52.5°	1581.1	1131.7	99.5	56.2	32.9	22.5	16.1	10.4	8.0	6.4	6.4
55°	1793.0	1271.3	89.9	49.8	26.5	18.5	12.8	8.0	5.6	4.8	4.0
57.5°	1964.8	1382.1	84.3	43.3	22.5	16.1	9.6	6.4	4.8	3.2	3.2
60°	2116.5	1453.5	74.6	36.1	19.3	12.8	8.0	4.8	3.2	2.4	2.4
62.5°	2239.3	1500.1	61.8	28.9	16.1	10.4	6.4	4.0	3.2	2.4	2.4
65°	2378.9	1537.8	50.6	22.5	13.6	8.8	5.6	3.2	2.4	2.4	2.4
67.5°	2652.6	1622.1	37.7	17.7	10.4	7.2	4.8	3.2	2.4	1.6	1.6
70°	2759.4	1523.4	29.7	14.4	8.0	6.4	4.8	3.2	1.6	1.6	1.6
72.5°	2348.4	1140.5	23.3	12.0	7.2	5.6	4.8	3.2	2.4	2.4	1.6
75°	1862.9	770.5	18.5	9.6	7.2	6.4	4.8	4.8	4.0	3.2	3.2
77.5°	1189.5	341.1	14.4	8.0	7.2	8.0	7.2	4.8	4.8	4.0	4.0
80°	354.8	81.9	10.4	6.4	5.6	6.4	7.2	4.8	3.2	2.4	2.4
82.5°	77.1	19.3	6.4	3.2	4.0	3.2	4.8	4.8	3.2	2.4	2.4
85°	25.7	7.2	4.0	3.2	2.4	2.4	2.4	2.4	2.4	2.4	1.6
87.5°	1.6	2.4	2.4	1.6	1.6	1.6	1.6	0.8	0.8	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)