

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P139714

Luminaire Tested: **ENV-F02-LED-E1-BL4-7030**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P139714  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33646)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: ENV-F02-LED-E1-BL4-7030  
Description: ENTRI LED LUMINAIRE  
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL  
Light Source: (14) 3000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3939.7 lumens  
Efficiency: N/A  
Efficacy: 79.9 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.33' x H: 0')  
IES Classification: Type III - Short - Full Cutoff  
BUG Rating: B1 - U0 - G1

Input Watts (W): 49.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P139714

CATALOG NUMBER: ENV-F02-LED-E1-BL4-7030

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 8.5 fc  
 Type III - Short - Full Cutoff

REPORT NUMBER: P139714  
CATALOG NUMBER: ENV-F02-LED-E1-BL4-7030

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P139714

CATALOG NUMBER: ENV-F02-LED-E1-BL4-7030


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	923.2	0.0	923.2
	% Fixture	23.4	0.0	23.4
<b>Street Side</b>	Lumens	3016.5	0.0	3016.5
	% Fixture	76.6	0.0	76.6
<b>Total</b>	Lumens	3939.7	0.0	3939.7
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.1	2.0
10°-20°	212.9	5.4
20°-30°	306.8	7.8
30°-40°	391.5	9.9
40°-50°	462.1	11.7
50°-60°	741.0	18.8
60°-70°	1247.2	31.7
70°-80°	463.9	11.8
80°-90°	35.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3939.7	100.0
0°-180°	3939.7	100.0



REPORT NUMBER: P139714


CATALOG NUMBER: ENV-F02-LED-E1-BL4-7030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	322.0	8.2			
FM (30°-60°)	1193.8	30.3			
FH (60°-80°)	1479.7	37.6			G1/1800
FVH (80°-90°)	20.9	0.5			G1/100
BL (0°-30°)	276.7	7.0	B1/500		
BM (30°-60°)	400.8	10.2	B1/1000		
BH (60°-80°)	231.4	5.9	B1/500		G1/500
BVH (80°-90°)	14.3	0.4			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G1**

Type III Short





REPORT NUMBER: P139714

CATALOG NUMBER: ENV-F02-LED-E1-BL4-7030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	60°	61°	62°	64°
0°	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3
2.5°	839.2	839.2	840.7	840.7	843.0	844.5	843.0	846.0	846.0	845.2	846.7
5°	827.1	827.1	827.9	827.9	829.4	831.7	830.1	833.2	832.4	833.2	833.2
7.5°	812.8	812.8	814.3	813.6	814.3	815.8	812.1	814.3	814.3	815.1	814.3
10°	794.7	796.2	797.7	797.0	797.0	797.7	791.7	794.0	793.2	793.2	792.4
12.5°	778.1	776.6	778.1	779.6	778.9	778.9	772.8	771.3	771.3	771.3	772.1
15°	760.8	762.3	764.5	762.3	760.8	757.8	751.7	750.2	750.2	750.2	751.0
17.5°	757.0	757.0	758.5	756.3	750.2	744.2	732.1	729.9	729.9	729.1	729.1
20°	767.6	766.8	769.1	764.5	751.0	735.1	716.3	712.5	712.5	712.5	711.8
22.5°	789.4	789.4	793.2	787.9	766.1	735.9	708.0	702.0	701.2	700.5	699.0
25°	831.7	830.9	833.2	819.6	787.9	745.7	705.7	696.7	695.9	694.4	692.9
27.5°	880.7	882.2	886.7	866.3	819.6	763.0	715.5	700.5	699.0	696.7	693.7
30°	928.9	933.4	941.7	919.9	855.8	784.9	730.6	713.3	710.3	707.2	702.0
32.5°	990.0	988.5	1002.1	968.9	887.5	808.3	746.5	725.3	721.6	717.0	710.3
35°	1054.8	1057.9	1060.9	1007.3	913.8	827.1	756.3	732.1	727.6	723.1	713.3
37.5°	1119.7	1120.4	1113.6	1038.2	929.7	838.4	761.5	733.6	727.6	720.8	709.5
40°	1179.2	1177.0	1156.6	1061.6	938.7	844.5	763.8	730.6	723.1	716.3	703.5
42.5°	1213.2	1210.9	1185.3	1072.2	939.5	843.7	763.8	727.6	719.3	711.0	696.7
45°	1227.5	1226.0	1196.6	1073.7	934.2	839.2	759.3	724.6	716.3	708.8	693.7
47.5°	1229.0	1229.0	1198.8	1071.4	929.7	836.2	759.3	728.4	721.6	715.5	704.2
50°	1222.2	1223.0	1199.6	1077.5	933.4	843.0	766.8	737.4	730.6	724.6	711.8
52.5°	1302.1	1294.6	1242.6	1104.6	958.3	864.8	792.4	766.1	763.8	760.0	750.2
55°	1912.9	1918.9	1634.7	1274.2	1063.1	977.2	947.0	941.7	958.3	964.4	964.4
57.5°	2428.6	2409.0	2301.9	1859.3	1390.4	1287.1	1299.1	1311.9	1336.1	1346.6	1354.2
60°	2554.5	2556.0	2553.0	2427.1	2052.4	1817.1	1758.3	1702.5	1700.3	1680.7	1665.6
62.5°	2539.5	2551.5	2608.1	2636.7	2673.7	2501.0	2142.1	1987.5	1957.4	1920.4	1867.6
65°	2430.1	2448.2	2538.7	2678.2	2996.4	3138.1	2400.7	2124.0	2077.3	2032.8	1943.8
67.5°	2070.5	2109.7	2283.1	2546.2	3034.8	3393.7	2442.9	2057.6	1995.8	1937.8	1832.2
70°	1278.0	1298.4	1566.0	2054.6	2749.8	3094.4	2218.2	1746.2	1667.8	1593.9	1449.9
72.5°	824.9	818.1	863.3	1157.4	2020.7	2404.5	1525.3	1161.1	1097.1	1038.2	945.5
75°	577.6	578.3	558.0	551.9	937.2	1489.1	690.7	496.1	467.5	455.4	435.8
77.5°	376.2	380.8	375.5	389.8	375.5	619.0	317.4	233.0	221.7	214.1	202.1
80°	227.0	242.0	246.6	249.6	253.3	233.7	188.5	137.2	123.7	110.8	91.2
82.5°	40.0	39.2	54.3	73.1	95.8	109.3	79.2	49.8	46.7	45.2	41.5
85°	0.0	0.0	0.8	0.8	1.5	5.3	8.3	9.8	9.0	9.8	10.6
87.5°	0.0	0.0	0.0	0.8	0.8	1.5	1.5	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P139714

CATALOG NUMBER: ENV-F02-LED-E1-BL4-7030

**CANDELA DISTRIBUTION (continued):**

	65°	66°	67°	68°	69°	70°	71°	72°	73°	74°	75°
0°	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3
2.5°	846.7	846.0	845.2	845.2	846.7	846.7	846.0	846.0	846.7	846.0	847.5
5°	833.9	833.2	833.2	832.4	833.2	833.9	833.2	833.2	833.9	833.2	834.7
7.5°	813.6	814.3	813.6	813.6	814.3	815.1	814.3	814.3	814.3	814.3	813.6
10°	792.4	792.4	791.7	791.7	793.2	792.4	791.7	791.7	792.4	793.2	791.7
12.5°	771.3	772.8	772.8	769.8	770.6	771.3	771.3	770.6	770.6	772.8	770.6
15°	750.2	751.0	750.2	751.0	749.5	748.7	749.5	749.5	748.0	747.2	747.2
17.5°	729.1	728.4	728.4	726.8	726.1	726.1	725.3	726.1	724.6	725.3	723.1
20°	710.3	709.5	708.8	708.8	706.5	706.5	706.5	705.7	704.2	704.2	703.5
22.5°	699.0	698.2	697.4	695.9	695.2	694.4	694.4	693.7	692.2	691.4	690.7
25°	692.9	692.2	690.7	689.2	688.4	687.6	687.6	686.9	685.4	683.9	683.1
27.5°	693.7	692.2	690.7	689.2	688.4	686.9	686.1	685.4	683.9	682.4	680.9
30°	700.5	697.4	694.4	692.2	689.9	687.6	686.1	685.4	683.1	680.9	678.6
32.5°	707.2	703.5	699.0	694.4	690.7	686.9	684.6	682.4	679.3	675.6	673.3
35°	709.5	705.0	698.2	694.4	689.2	684.6	680.9	677.8	672.6	668.0	664.3
37.5°	704.2	699.0	692.2	686.9	681.6	675.6	671.1	666.5	662.8	657.5	653.7
40°	695.9	689.9	683.1	675.6	670.3	664.3	659.7	656.0	650.7	646.2	643.2
42.5°	689.2	682.4	674.8	668.8	662.8	656.7	651.5	647.7	642.4	637.1	633.4
45°	686.9	680.1	674.1	666.5	660.5	656.0	651.5	646.2	641.6	637.1	632.6
47.5°	699.0	692.9	686.9	680.9	675.6	670.3	665.8	660.5	655.2	649.2	644.7
50°	705.7	699.0	693.7	686.9	680.9	675.6	671.1	665.8	662.0	656.0	651.5
52.5°	754.7	745.7	747.2	741.2	741.2	735.1	739.7	732.9	736.7	732.1	738.9
55°	962.1	965.1	984.0	987.0	994.5	993.8	998.3	1017.9	1010.4	1000.5	1003.6
57.5°	1333.8	1340.6	1350.4	1341.4	1348.1	1349.6	1362.5	1357.2	1352.7	1349.6	1339.8
60°	1656.5	1647.5	1633.1	1615.8	1609.0	1601.5	1588.7	1588.7	1572.1	1566.8	1554.0
62.5°	1845.8	1819.4	1801.3	1773.4	1753.8	1740.2	1717.6	1700.3	1677.6	1660.3	1639.9
65°	1907.6	1863.1	1831.5	1796.8	1765.9	1736.4	1704.0	1679.1	1651.2	1632.4	1600.0
67.5°	1787.7	1742.5	1688.9	1652.0	1619.6	1582.6	1532.1	1501.2	1477.1	1440.9	1425.0
70°	1391.9	1344.4	1277.3	1259.2	1209.4	1152.1	1100.8	1069.9	1034.5	1009.6	983.2
72.5°	882.9	829.4	800.0	778.1	745.7	698.2	653.7	635.6	604.7	597.9	580.6
75°	414.7	378.5	371.0	365.7	330.2	323.5	309.9	303.9	289.5	282.0	279.0
77.5°	185.5	177.2	163.6	159.8	148.5	137.2	123.7	117.6	110.1	105.6	99.5
80°	84.4	76.2	70.9	67.1	65.6	61.8	58.8	56.5	54.3	54.3	50.5
82.5°	40.7	39.2	37.7	37.7	35.4	35.4	33.2	32.4	31.7	30.9	30.9
85°	11.3	11.3	11.3	12.1	12.1	12.1	12.1	12.1	12.1	12.8	12.8
87.5°	1.5	1.5	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P139714

CATALOG NUMBER: ENV-F02-LED-E1-BL4-7030

**CANDELA DISTRIBUTION (continued):**

	76°	77°	78°	79°	80°	81°	82°	83°	84°	85°	86°
0°	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3
2.5°	846.7	846.7	846.7	848.2	847.5	849.8	849.8	849.8	851.3	852.0	851.3
5°	834.7	834.7	834.7	835.4	835.4	836.9	836.9	838.4	838.4	839.2	839.2
7.5°	815.1	815.8	815.8	817.3	816.6	817.3	817.3	819.6	819.6	820.3	820.3
10°	792.4	793.2	793.2	793.2	794.0	794.7	794.7	796.2	797.0	797.0	798.5
12.5°	771.3	770.6	771.3	770.6	772.8	772.8	773.6	772.8	773.6	774.4	775.1
15°	748.0	748.0	747.2	748.0	748.0	747.2	746.5	747.2	748.7	748.7	748.7
17.5°	724.6	722.3	722.3	722.3	721.6	720.1	721.6	720.8	720.8	721.6	720.8
20°	702.7	702.0	701.2	700.5	699.7	697.4	697.4	697.4	696.7	696.7	696.7
22.5°	689.2	688.4	687.6	686.9	683.9	682.4	681.6	680.9	679.3	678.6	677.8
25°	681.6	680.1	678.6	677.1	674.8	672.6	670.3	669.5	668.0	666.5	664.3
27.5°	679.3	677.8	674.8	673.3	670.3	668.0	665.8	663.5	661.3	659.0	656.7
30°	675.6	673.3	670.3	668.0	665.8	662.0	659.0	656.7	653.0	650.7	647.7
32.5°	670.3	667.3	664.3	661.3	658.2	654.5	650.7	647.7	644.7	641.6	637.9
35°	661.3	657.5	653.0	649.9	646.2	642.4	639.4	634.1	631.8	628.1	624.3
37.5°	649.2	645.4	641.6	637.9	633.4	630.3	625.8	621.3	619.0	616.8	611.5
40°	638.6	634.1	630.3	627.3	622.0	619.8	615.3	610.7	607.7	605.5	600.9
42.5°	628.8	624.3	620.5	616.0	612.2	609.2	605.5	600.9	597.9	596.4	592.6
45°	628.8	623.6	619.0	615.3	611.5	607.7	604.7	600.2	597.9	594.9	592.6
47.5°	639.4	633.4	628.1	622.8	617.5	613.8	609.2	604.7	600.9	598.7	595.7
50°	646.9	640.9	637.9	631.8	628.8	623.6	618.3	616.0	612.2	610.0	609.2
52.5°	738.9	735.1	735.9	720.8	717.8	725.3	713.3	723.8	720.8	711.8	711.8
55°	1020.9	1019.4	1026.2	1007.3	999.0	1014.1	1020.2	998.3	1003.6	1003.6	1002.1
57.5°	1349.6	1339.8	1330.0	1332.3	1320.2	1329.3	1318.0	1304.4	1309.7	1305.2	1289.3
60°	1545.7	1539.7	1525.3	1511.8	1498.9	1486.9	1476.3	1464.3	1458.2	1447.7	1436.4
62.5°	1624.9	1609.0	1591.7	1573.6	1553.2	1533.6	1521.6	1505.7	1489.1	1478.6	1466.5
65°	1582.6	1559.3	1540.4	1514.0	1492.2	1468.0	1452.2	1434.1	1419.0	1400.9	1385.8
67.5°	1394.1	1367.0	1317.2	1293.1	1260.7	1223.0	1212.4	1190.6	1182.3	1155.1	1110.6
70°	949.3	922.1	892.0	843.0	811.3	778.9	743.4	717.8	714.0	692.2	659.7
72.5°	558.0	539.1	519.5	491.6	468.2	455.4	430.5	404.9	404.1	379.3	366.4
75°	263.9	254.1	234.5	227.7	206.6	205.1	189.3	186.2	189.3	181.7	180.2
77.5°	89.7	87.5	82.9	76.9	72.4	70.9	67.1	64.8	63.3	61.8	60.3
80°	49.0	47.5	46.7	44.5	43.0	42.2	40.0	39.2	38.5	37.7	36.9
82.5°	29.4	30.2	28.7	27.1	27.1	25.6	24.9	24.1	23.4	23.4	23.4
85°	12.1	12.8	12.1	11.3	10.6	11.3	11.3	10.6	9.8	10.6	10.6
87.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P139714

CATALOG NUMBER: ENV-F02-LED-E1-BL4-7030

**CANDELA DISTRIBUTION (continued):**

	87°	88°	89°	90°	95°	105°	115°	125°	135°	145°	155°
0°	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3	851.3
2.5°	849.8	849.0	849.0	848.2	847.5	849.0	850.5	852.8	851.3	852.8	853.5
5°	837.7	837.7	837.7	838.4	837.7	839.9	843.0	847.5	848.2	851.3	853.5
7.5°	818.1	818.1	818.8	819.6	818.8	821.9	827.1	832.4	836.2	841.5	846.0
10°	795.5	795.5	795.5	795.5	796.2	800.0	803.8	809.8	815.8	824.1	830.9
12.5°	775.1	772.8	773.6	775.1	773.6	773.6	777.4	781.9	785.7	796.2	808.3
15°	748.0	748.0	746.5	747.2	743.4	742.7	744.2	747.2	750.2	759.3	772.1
17.5°	719.3	719.3	719.3	717.0	714.0	706.5	705.7	705.7	705.7	712.5	727.6
20°	693.7	693.7	692.2	690.7	683.9	671.1	660.5	656.0	654.5	665.8	672.6
22.5°	675.6	674.8	671.8	670.3	659.7	639.4	622.8	610.0	606.2	610.0	612.2
25°	661.3	659.7	656.7	653.7	639.4	611.5	585.1	563.2	552.7	549.7	542.1
27.5°	653.0	650.7	646.2	643.2	624.3	588.9	554.2	525.5	505.9	491.6	478.0
30°	643.9	640.1	635.6	631.1	610.0	570.8	530.8	495.4	460.7	435.8	416.2
32.5°	633.4	629.6	625.1	620.5	597.2	554.2	512.0	468.2	420.0	386.0	356.6
35°	620.5	616.8	612.2	607.0	583.6	540.6	499.1	441.8	383.8	340.1	301.6
37.5°	607.7	603.9	599.4	594.1	570.8	533.8	491.6	417.0	350.6	297.1	246.6
40°	597.9	594.1	589.6	585.1	564.0	530.8	487.8	395.8	321.2	254.8	196.8
42.5°	589.6	585.9	582.1	577.6	559.5	532.3	479.5	377.8	292.5	212.6	154.6
45°	588.9	586.6	582.1	578.3	561.0	539.1	472.8	361.9	263.1	171.9	130.4
47.5°	594.1	591.1	588.1	585.1	571.5	556.4	468.2	345.3	230.0	138.7	124.4
50°	607.0	603.9	602.4	600.9	592.6	579.8	468.2	328.0	191.5	122.1	123.7
52.5°	710.3	702.0	699.7	705.7	683.1	619.0	471.2	306.9	150.0	116.9	124.4
55°	999.0	1007.3	986.2	975.7	936.5	716.3	473.5	275.2	122.1	116.1	122.9
57.5°	1290.8	1290.8	1283.3	1266.7	1218.5	882.2	484.1	224.7	111.6	114.6	121.4
60°	1433.3	1424.3	1416.8	1407.0	1333.8	997.5	499.9	165.9	107.1	113.9	119.9
62.5°	1459.0	1444.7	1434.8	1422.0	1324.8	1003.6	506.7	124.4	102.5	113.9	116.1
65°	1374.5	1359.5	1346.6	1325.5	1207.1	908.6	472.8	101.8	99.5	110.8	112.3
67.5°	1113.6	1095.6	1085.8	1075.2	996.8	797.7	382.3	91.2	95.8	105.6	108.6
70°	637.1	617.5	606.2	608.5	561.0	631.1	305.4	83.7	90.5	99.5	104.1
72.5°	343.1	322.0	315.2	293.3	250.3	318.2	235.2	76.9	83.7	90.5	95.0
75°	169.6	162.1	164.4	153.8	130.4	98.0	151.6	68.6	74.6	81.4	84.4
77.5°	58.8	57.3	56.5	55.8	54.3	52.0	69.4	58.8	64.1	69.4	72.4
80°	36.2	35.4	36.2	35.4	34.7	40.0	44.5	46.7	51.3	58.1	58.8
82.5°	21.9	21.9	21.9	21.9	21.9	27.9	31.7	36.2	40.0	44.5	48.3
85°	10.6	10.6	10.6	10.6	11.3	18.8	21.1	26.4	27.9	31.7	34.7
87.5°	2.3	2.3	2.3	2.3	3.0	9.8	12.8	15.8	16.6	16.6	18.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P139714

CATALOG NUMBER: ENV-F02-LED-E1-BL4-7030

**CANDELA DISTRIBUTION (continued):**

	165°	175°	180°
0°	851.3	851.3	851.3
2.5°	852.8	851.3	850.5
5°	855.0	853.5	852.8
7.5°	849.0	849.8	849.0
10°	836.2	838.4	839.2
12.5°	815.8	820.3	823.4
15°	781.9	788.7	787.2
17.5°	736.7	744.9	744.9
20°	680.1	683.9	681.6
22.5°	610.7	612.2	610.0
25°	537.6	537.6	534.6
27.5°	469.7	466.0	463.7
30°	404.9	395.1	392.1
32.5°	336.3	319.7	319.7
35°	266.9	253.3	249.6
37.5°	207.3	192.3	187.7
40°	159.1	147.8	147.0
42.5°	134.2	131.9	132.7
45°	128.2	131.2	131.2
47.5°	128.9	132.7	133.5
50°	129.7	133.5	134.2
52.5°	129.7	131.9	131.9
55°	128.2	128.2	128.2
57.5°	125.2	124.4	125.9
60°	122.9	122.9	122.9
62.5°	119.1	119.1	119.1
65°	113.1	113.9	113.9
67.5°	107.1	107.1	107.1
70°	99.5	99.5	101.0
72.5°	92.0	95.0	96.5
75°	86.7	92.0	94.2
77.5°	76.2	81.4	84.4
80°	62.6	63.3	63.3
82.5°	49.8	48.3	46.0
85°	35.4	33.2	33.2
87.5°	18.8	18.1	18.8
90°	0.0	0.0	0.0

(END OF REPORT)