

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P401736

Luminaire Tested: **ENV-SA1E-760-U-T4W**

Issue Date: 5/20/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P401736  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2004-754-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/20/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: ENV-SA1E-760-U-T4W  
Description: ENTRI LED LUMINAIRE  
(1) 70 CRI, 5700K, 1050mA LIGHTSQUARE WITH 16 LEDS AND TYPE IV WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7034.1 lumens  
Efficiency: N/A  
Efficacy: 123.0 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short - Semi-Cutoff  
BUG Rating: B1 - U0 - G2

Input Watts (W): 57.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P401736

CATALOG NUMBER: ENV-SA1E-760-U-T4W

### Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 8.8 fc  
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P401736

CATALOG NUMBER: ENV-SA1E-760-U-T4W

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P401736

CATALOG NUMBER: ENV-SA1E-760-U-T4W

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1656.1	0.0	1656.1
	% Fixture	23.5	0.0	23.5
<b>Street Side</b>	Lumens	5378.0	0.0	5378.0
	% Fixture	76.5	0.0	76.5
<b>Total</b>	Lumens	7034.1	0.0	7034.1
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.7	1.0
10°-20°	241.1	3.4
20°-30°	407.4	5.8
30°-40°	589.4	8.4
40°-50°	889.9	12.7
50°-60°	1500.6	21.3
60°-70°	2064.4	29.3
70°-80°	1144.0	16.3
80°-90°	124.5	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7034.1	100.0
0°-180°	7034.1	100.0



REPORT NUMBER: P401736


CATALOG NUMBER: ENV-SA1E-760-U-T4W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	383.9	5.5			
FM	(30°-60°)	2212.3	31.5			
FH	(60°-80°)	2728.4	38.8			G2/5000
FVH	(80°-90°)	53.3	0.8			G1/100
BL	(0°-30°)	337.2	4.8	B1/500		
BM	(30°-60°)	767.7	10.9	B1/1000		
BH	(60°-80°)	480.0	6.8	B1/500		G1/500
BVH	(80°-90°)	71.2	1.0			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**

Type IV Short





REPORT NUMBER: P401736

CATALOG NUMBER: ENV-SA1E-760-U-T4W

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	46°	55°	65°	75°	85°
0°	714.0	714.0	714.0	714.0	714.0	714.0	714.0	714.0	714.0	714.0	714.0
2.5°	759.0	758.0	759.0	755.0	751.0	745.0	743.0	736.0	731.0	724.0	718.0
5°	815.0	818.0	817.0	812.0	796.0	784.0	784.0	769.0	753.0	738.0	724.0
7.5°	876.0	876.0	870.0	860.0	844.0	826.0	824.0	804.0	781.0	760.0	738.0
10°	920.0	922.0	913.0	899.0	879.0	860.0	858.0	835.0	813.0	786.0	759.0
12.5°	951.0	951.0	943.0	930.0	906.0	888.0	886.0	865.0	842.0	814.0	783.0
15°	967.0	965.0	958.0	944.0	923.0	908.0	905.0	887.0	868.0	840.0	807.0
17.5°	964.0	964.0	958.0	944.0	929.0	917.0	915.0	902.0	888.0	861.0	828.0
20°	951.0	950.0	948.0	937.0	927.0	922.0	920.0	914.0	905.0	882.0	851.0
22.5°	939.0	938.0	935.0	928.0	924.0	927.0	927.0	926.0	925.0	907.0	877.0
25°	946.0	945.0	939.0	929.0	928.0	942.0	943.0	946.0	948.0	933.0	902.0
27.5°	995.0	992.0	975.0	949.0	940.0	958.0	960.0	969.0	967.0	951.0	924.0
30°	1091.0	1092.0	1054.0	998.0	968.0	976.0	977.0	987.0	984.0	971.0	949.0
32.5°	1235.9	1235.9	1173.9	1089.0	1013.0	997.0	994.0	1003.0	1015.0	998.0	976.0
35°	1419.9	1414.9	1339.9	1208.9	1090.0	1033.0	1031.0	1027.0	1048.0	1032.0	1000.0
37.5°	1604.9	1586.9	1513.9	1369.9	1197.9	1102.9	1095.0	1083.0	1095.0	1061.0	1033.0
40°	1753.9	1750.9	1690.9	1544.9	1325.9	1187.9	1181.9	1128.9	1136.9	1109.9	1098.9
42.5°	1917.9	1919.9	1879.9	1732.9	1478.9	1302.9	1286.9	1204.9	1227.9	1217.9	1212.9
45°	2097.9	2095.9	2065.9	1911.9	1665.9	1462.9	1442.9	1341.9	1388.9	1382.9	1410.9
47.5°	2235.9	2246.9	2229.9	2120.9	1887.9	1656.9	1641.9	1518.9	1589.9	1637.9	1690.9
50°	2423.9	2422.9	2376.9	2331.9	2145.9	1904.9	1889.9	1752.9	1854.9	1924.9	2021.9
52.5°	2656.9	2648.9	2553.9	2537.9	2459.9	2175.9	2162.9	2019.9	2165.9	2226.9	2423.9
55°	2802.9	2801.9	2752.9	2780.9	2782.9	2477.9	2461.9	2334.9	2499.9	2569.9	2867.9
57.5°	2924.9	2925.9	2966.9	3064.9	3130.9	2844.9	2838.9	2683.9	2850.9	2948.9	3300.8
60°	3018.9	3038.9	3153.9	3377.8	3487.8	3312.8	3286.9	3122.9	3234.9	3273.9	3631.8
62.5°	2980.9	3006.9	3232.9	3562.8	3845.8	3808.8	3799.8	3562.8	3561.8	3541.8	3878.8
65°	2680.9	2736.9	3092.9	3555.8	4081.8	4312.8	4299.8	3977.8	3865.8	3765.8	3952.8
67.5°	2193.9	2205.9	2634.9	3283.9	4079.8	4629.8	4615.8	4279.8	4054.8	3809.8	3735.8
69°	1785.9	1829.9	2226.9	2939.9	3935.8	4693.8	4693.8	4363.8	4047.8	3704.8	3417.8
70°	1544.9	1546.9	1929.9	2665.9	3739.8	4655.8	4664.8	4363.8	3990.8	3567.8	3135.9
72.5°	724.0	769.0	1011.0	1739.9	3020.9	4279.8	4301.8	4075.8	3659.8	3073.9	2352.9
75°	217.0	225.0	337.0	825.0	1730.9	3296.8	3345.8	3390.8	2980.9	2262.9	1448.9
77.5°	129.0	128.0	163.0	280.0	801.0	1954.9	1976.9	2168.9	1933.9	1257.9	658.0
80°	63.0	65.0	87.0	136.0	300.0	710.0	781.0	1014.0	857.0	492.0	241.0
82.5°	21.0	23.0	36.0	55.0	127.0	229.0	253.0	318.0	274.0	179.0	103.0
85°	0.0	0.0	1.0	2.0	7.0	17.0	17.0	38.0	57.0	63.0	34.0
87.5°	0.0	0.0	1.0	1.0	2.0	2.0	2.0	2.0	2.0	2.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P401736

CATALOG NUMBER: ENV-SA1E-760-U-T4W

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	714.0	714.0	714.0	714.0	714.0	714.0	714.0	714.0	714.0	714.0	714.0
2.5°	715.0	713.0	709.0	705.0	703.0	698.0	699.0	697.0	696.0	696.0	697.0
5°	717.0	714.0	708.0	704.0	700.0	698.0	703.0	705.0	707.0	707.0	708.0
7.5°	729.0	723.0	716.0	711.0	712.0	715.0	723.0	729.0	732.0	734.0	736.0
10°	749.0	742.0	732.0	731.0	733.0	741.0	752.0	761.0	769.0	774.0	774.0
12.5°	770.0	761.0	753.0	755.0	764.0	776.0	787.0	797.0	804.0	809.0	810.0
15°	793.0	784.0	776.0	781.0	796.0	810.0	820.0	824.0	827.0	832.0	833.0
17.5°	814.0	806.0	799.0	812.0	825.0	836.0	839.0	837.0	833.0	836.0	838.0
20°	836.0	829.0	825.0	839.0	848.0	849.0	841.0	832.0	822.0	822.0	823.0
22.5°	863.0	854.0	852.0	859.0	856.0	844.0	824.0	810.0	796.0	794.0	797.0
25°	889.0	880.0	879.0	874.0	848.0	817.0	790.0	774.0	763.0	764.0	770.0
27.5°	915.0	909.0	910.0	883.0	825.0	778.0	742.0	729.0	732.0	734.0	740.0
30°	941.0	941.0	945.0	883.0	793.0	723.0	689.0	688.0	696.0	702.0	709.0
32.5°	971.0	980.0	973.0	872.0	750.0	667.0	640.0	642.0	651.0	661.0	667.0
35°	1000.0	1021.0	1001.0	847.0	691.0	616.0	594.0	591.0	598.0	607.0	610.0
37.5°	1046.0	1080.0	1025.0	808.0	630.0	571.0	549.0	541.0	534.0	541.0	540.0
40°	1125.9	1166.9	1043.0	743.0	571.0	529.0	506.0	491.0	474.0	459.0	459.0
42.5°	1253.9	1280.9	1053.0	664.0	512.0	487.0	464.0	442.0	416.0	389.0	389.0
45°	1462.9	1468.9	1057.0	580.0	458.0	445.0	421.0	400.0	366.0	339.0	333.0
47.5°	1741.9	1715.9	1067.0	499.0	411.0	408.0	388.0	364.0	327.0	302.0	299.0
50°	2116.9	2004.9	1110.9	434.0	373.0	376.0	361.0	333.0	298.0	280.0	276.0
52.5°	2538.9	2369.9	1144.9	382.0	340.0	349.0	338.0	311.0	281.0	266.0	263.0
55°	2999.9	2720.9	1136.9	347.0	315.0	325.0	321.0	298.0	271.0	258.0	255.0
57.5°	3375.8	2967.9	1067.0	316.0	290.0	304.0	308.0	290.0	265.0	253.0	250.0
60°	3657.8	3102.9	923.0	290.0	270.0	287.0	298.0	285.0	264.0	257.0	254.0
62.5°	3785.8	3090.9	736.0	270.0	255.0	275.0	299.0	293.0	279.0	284.0	285.0
65°	3713.8	2939.9	552.0	255.0	246.0	277.0	316.0	316.0	295.0	304.0	305.0
67.5°	3344.8	2544.9	402.0	244.0	237.0	287.0	348.0	328.0	288.0	295.0	292.0
69°	2993.9	2276.9	345.0	238.0	230.0	292.0	362.0	330.0	280.0	288.0	280.0
70°	2735.9	2034.9	310.0	233.0	227.0	292.0	366.0	328.0	276.0	282.0	273.0
72.5°	1946.9	1412.9	255.0	223.0	216.0	270.0	359.0	317.0	265.0	258.0	241.0
75°	1131.9	781.0	217.0	212.0	191.0	237.0	341.0	305.0	254.0	241.0	229.0
77.5°	475.0	349.0	185.0	193.0	169.0	211.0	319.0	293.0	241.0	223.0	217.0
80°	193.0	174.0	154.0	167.0	147.0	186.0	294.0	273.0	222.0	204.0	195.0
82.5°	101.0	96.0	118.0	135.0	122.0	171.0	277.0	259.0	206.0	188.0	177.0
85°	30.0	40.0	67.0	92.0	93.0	154.0	269.0	240.0	179.0	155.0	153.0
87.5°	2.0	8.0	23.0	48.0	61.0	118.0	218.0	197.0	145.0	122.0	123.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)