

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: io LED

Report Number: P895865

Luminaire Tested: **GRZ-15L-927-50x60-X-UNV-STD-1F**

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-08
Report Number: P895865
Test Lab: INNOVATION CENTER(G3)
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: GRZ-15L-927-50x60-X-UNV-STD-1F
Description: iO LED 90CRI 2700K GRAZER 1500 lumens per ft WITH 50 deg x 60 deg OPTIC
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1087.3 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.95 / 0.87
Luminous Opening: Rectangular (W 1' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P895865
CATALOG NUMBER: GRZ-15L-927-50x60-X-UNV-STD-1F

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P895865

CATALOG NUMBER: GRZ-15L-927-50x60-X-UNV-STD-1F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68	68	68	68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63	63	63	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	67	63	60	59	59	59	59
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55	55	55	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48	48	48	48

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	76109	76109	76109
5°	75097	75305	73794
10°	71881	70701	69455
15°	69683	65725	65224
20°	63850	61816	61740
25°	48654	54154	57538
30°	31844	40352	48874
35°	19919	25831	34415
40°	11312	15324	18536
45°	6273	8785	9168
50°	4038	5093	4993
55°	2972	3445	3096
60°	2182	2454	2182
65°	1772	1940	1620
70°	1189	1397	1397
75°	798	1048	1048
80°	781	781	781
85°	815	815	815



TEST NUMBER: P895865
 CATALOG NUMBER: GRZ-15L-927-50x60-X-UNV-STD-1F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.3	9.9
10°-20°	277.9	25.6
20°-30°	335.1	30.8
30°-40°	228.8	21.0
40°-50°	91.2	8.4
50°-60°	29.6	2.7
60°-70°	11.9	1.1
70°-80°	4.6	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	720.3	66.2
0°-40°	949.1	87.3
0°-60°	1069.8	98.4
0°-90°	1087.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1087.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1179	1179	1179	1179	1179	
5°	1159	1158	1162	1142	1138	109
15°	1042	1006	983	968	976	291
25°	683	679	760	784	808	307
35°	253	318	328	467	437	162
45°	69	132	96	130	100	58
55°	26	36	31	30	28	24
65°	12	12	13	12	11	11
75°	3	4	4	4	4	4
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P895865

CATALOG NUMBER: GRZ-15L-927-50x60-X-UNV-STD-1F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1178.7	1178.7	1178.7	1178.7	1178.7
2.5°	1189.3	1177.6	1173.4	1168.1	1140.6
5°	1158.6	1157.6	1161.8	1141.7	1138.5
7.5°	1126.9	1121.6	1118.5	1104.7	1095.2
10°	1096.3	1084.6	1078.3	1059.3	1059.3
12.5°	1070.9	1051.9	1030.7	1011.7	1004.3
15°	1042.4	1006.4	983.2	968.3	975.7
17.5°	1008.5	952.4	942.9	922.8	930.2
20°	929.2	891.1	899.6	880.6	898.5
22.5°	815.0	793.9	841.5	837.2	864.7
25°	682.9	678.7	760.1	784.4	807.6
27.5°	540.1	562.3	656.5	723.1	736.8
30°	427.1	461.9	541.2	649.1	655.5
32.5°	335.1	384.8	427.1	562.3	552.8
35°	252.7	318.2	327.7	467.2	436.6
37.5°	186.0	267.5	249.5	367.9	314.0
40°	134.2	218.9	181.8	271.7	219.9
42.5°	95.1	174.4	132.1	196.7	149.0
45°	68.7	132.1	96.2	130.0	100.4
47.5°	51.8	97.2	69.7	85.6	70.8
50°	40.2	68.7	50.7	58.1	49.7
52.5°	32.8	49.7	39.1	41.2	37.0
55°	26.4	35.9	30.6	29.6	27.5
57.5°	21.1	27.5	24.3	23.2	22.2
60°	16.9	20.1	19.0	18.0	16.9
62.5°	13.7	15.9	15.9	13.7	13.7
65°	11.6	11.6	12.7	11.6	10.6
67.5°	8.5	9.5	9.5	8.5	8.5
70°	6.3	7.4	7.4	7.4	7.4
72.5°	5.3	5.3	6.3	5.3	5.3
75°	3.2	4.2	4.2	4.2	4.2
77.5°	2.1	3.2	3.2	3.2	3.2
80°	2.1	2.1	2.1	2.1	2.1
82.5°	1.1	1.1	2.1	1.1	1.1
85°	1.1	1.1	1.1	1.1	1.1
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

iO LED

Report Number: SP1-2101-124-1

Luminaire Tested: GRZ-05L-927-10X10-X-UNV-STD-2F

Test Date: 02/10/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-124-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 02/10/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: iO LED
 Catalog Number: **GRZ-05L-927-10X10-X-UNV-STD-2F**
 Description: IO LED Wall Grazer GRZ

Spectral Parameters


CCT (K): 2729
 CIE u': 0.2613
 CIE v': 0.5257
 Duv: -0.0007
 CIE x: 0.4561
 CIE y: 0.4078
 CIE z: 0.1361
 Peak Wavelength (nm): 624
 Dominant Wavelength (nm): 584
 Purity: 59.5

 Rf: 93.5
 Rg: 99.9

CRI (Ra):	94.7		
R1:	95.4	R9:	67.0
R2:	98.0	R10:	94.1
R3:	98.7	R11:	96.2
R4:	95.1	R12:	88.6
R5:	95.2	R13:	96.3
R6:	97.5	R14:	98.5
R7:	92.8		
R8:	84.7		

Test Conditions

Stabilization Time: 176M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.1/39%
 Sphere Temperature (°C): 24.5




REPORT NUMBER: SP1-2101-124-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	1/31/2021	7/31/2021
Power Meter	IN0071	12/1/2020	12/1/2021
AC Power Source	IN0063	12/1/2020	12/1/2021
DC Power Source	IN0208	12/1/2020	12/1/2021
Sphere Thermometer	IN0085	12/1/2020	12/1/2021
Room Thermometer	IN0046	12/1/2020	12/1/2021

REPORT NUMBER: SP1-2101-124-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2101-124-1

Photopic Flux vs. Wavelength




#####

λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)
360	309	0.0	490	4342	0.6	620	16630	4.3	750	1836	0.0	880	324	0.0
365	277	0.0	495	4830	0.9	625	16799	3.7	755	1629	0.0	885	500	0.0
370	260	0.0	500	5328	1.2	630	16562	3.0	760	1434	0.0	890	571	0.0
375	295	0.0	505	5798	1.6	635	16219	2.4	765	1231	0.0	895	494	0.0
380	288	0.0	510	6250	2.1	640	15881	1.9	770	1141	0.0	900	267	0.0
385	260	0.0	515	6656	2.8	645	15637	1.5	775	986	0.0	905	379	0.0
390	252	0.0	520	7162	3.5	650	15133	1.1	780	904	0.0	910	465	0.0
395	226	0.0	525	7622	4.1	655	14463	0.8	785	827	0.0	915	557	0.0
400	191	0.0	530	8063	4.7	660	13640	0.6	790	768	0.0	920	412	0.0
405	196	0.0	535	8439	5.2	665	12787	0.4	795	711	0.0	925	332	0.0
410	195	0.0	540	8846	5.8	670	11721	0.3	800	693	0.0	930	466	0.0
415	235	0.0	545	9169	6.1	675	10776	0.2	805	609	0.0	935	480	0.0
420	323	0.0	550	9555	6.5	680	9728	0.1	810	615	0.0	940	404	0.0
425	510	0.0	555	9909	6.8	685	8803	0.1	815	547	0.0	945	502	0.0
430	889	0.0	560	10257	7.0	690	7856	0.0	820	491	0.0	950	495	0.0
435	1599	0.0	565	10655	7.1	695	6947	0.0	825	570	0.0	955	285	0.0
440	2967	0.0	570	11020	7.2	700	6181	0.0	830	477	0.0	960	433	0.0
445	4944	0.1	575	11481	7.1	705	5516	0.0	835	401	0.0	965	277	0.0
450	5950	0.2	580	12032	7.1	710	4865	0.0	840	440	0.0	970	517	0.0
455	5013	0.2	585	12647	7.0	715	4321	0.0	845	330	0.0	975	498	0.0
460	4393	0.2	590	13350	6.9	720	3839	0.0	850	336	0.0	980	465	0.0
465	3971	0.2	595	14054	6.7	725	3403	0.0	855	350	0.0	985	724	0.0
470	3442	0.2	600	14775	6.4	730	2978	0.0	860	266	0.0	990	861	0.0
475	3372	0.3	605	15552	6.0	735	2581	0.0	865	338	0.0	995	562	0.0
480	3623	0.3	610	16054	5.5	740	2292	0.0	870	363	0.0	1000	816	0.0
485	3960	0.5	615	16452	5.0	745	2037	0.0	875	335	0.0			

REPORT NUMBER: SP1-2101-124-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: 1011.1

S/P: 1.32

λ (nm)	Power ($\mu\text{W}/\text{nm}$)	Lumens (ϕ/nm)	λ (nm)	Power ($\mu\text{W}/\text{nm}$)	Lumens (ϕ/nm)	λ (nm)	Power ($\mu\text{W}/\text{nm}$)	Lumens (ϕ/nm)	λ (nm)	Power ($\mu\text{W}/\text{nm}$)	Lumens (ϕ/nm)	λ (nm)	Power ($\mu\text{W}/\text{nm}$)	Lumens (ϕ/nm)
360	309	0.0	490	4342	6.7	620	16630	0.2	750	1836	0.0	880	324	0.0
365	277	0.0	495	4830	7.8	625	16799	0.1	755	1629	0.0	885	500	0.0
370	260	0.0	500	5328	8.9	630	16562	0.1	760	1434	0.0	890	571	0.0
375	295	0.0	505	5798	9.9	635	16219	0.1	765	1231	0.0	895	494	0.0
380	288	0.0	510	6250	10.6	640	15881	0.0	770	1141	0.0	900	267	0.0
385	260	0.0	515	6656	11.0	645	15637	0.0	775	986	0.0	905	379	0.0
390	252	0.0	520	7162	11.4	650	15133	0.0	780	904	0.0	910	465	0.0
395	226	0.0	525	7622	11.4	655	14463	0.0	785	827	0.0	915	557	0.0
400	191	0.0	530	8063	11.1	660	13640	0.0	790	768	0.0	920	412	0.0
405	196	0.0	535	8439	10.5	665	12787	0.0	795	711	0.0	925	332	0.0
410	195	0.0	540	8846	9.8	670	11721	0.0	800	693	0.0	930	466	0.0
415	235	0.0	545	9169	8.8	675	10776	0.0	805	609	0.0	935	480	0.0
420	323	0.1	550	9555	7.8	680	9728	0.0	810	615	0.0	940	404	0.0
425	510	0.1	555	9909	6.8	685	8803	0.0	815	547	0.0	945	502	0.0
430	889	0.3	560	10257	5.7	690	7856	0.0	820	491	0.0	950	495	0.0
435	1599	0.7	565	10655	4.8	695	6947	0.0	825	570	0.0	955	285	0.0
440	2967	1.7	570	11020	3.9	700	6181	0.0	830	477	0.0	960	433	0.0
445	4944	3.3	575	11481	3.1	705	5516	0.0	835	401	0.0	965	277	0.0
450	5950	4.6	580	12032	2.5	710	4865	0.0	840	440	0.0	970	517	0.0
455	5013	4.4	585	12647	1.9	715	4321	0.0	845	330	0.0	975	498	0.0
460	4393	4.2	590	13350	1.5	720	3839	0.0	850	336	0.0	980	465	0.0
465	3971	4.2	595	14054	1.1	725	3403	0.0	855	350	0.0	985	724	0.0
470	3442	4.0	600	14775	0.8	730	2978	0.0	860	266	0.0	990	861	0.0
475	3372	4.2	605	15552	0.6	735	2581	0.0	865	338	0.0	995	562	0.0
480	3623	4.9	610	16054	0.4	740	2292	0.0	870	363	0.0	1000	816	0.0
485	3960	5.7	615	16452	0.3	745	2037	0.0	875	335	0.0			

REPORT NUMBER: SP1-2101-124-1

Melanopic Flux vs. Wavelength




Melanopic Lumens: 382.4

M/P: 0.5





λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)
360	309	0.0	490	4342	3.6	620	16630	0.0	750	1836	0.0	880	324	0.0
365	277	0.0	495	4830	4.0	625	16799	0.0	755	1629	0.0	885	500	0.0
370	260	0.0	500	5328	4.3	630	16562	0.0	760	1434	0.0	890	571	0.0
375	295	0.0	505	5798	4.5	635	16219	0.0	765	1231	0.0	895	494	0.0
380	288	0.0	510	6250	4.5	640	15881	0.0	770	1141	0.0	900	267	0.0
385	260	0.0	515	6656	4.3	645	15637	0.0	775	986	0.0	905	379	0.0
390	252	0.0	520	7162	4.2	650	15133	0.0	780	904	0.0	910	465	0.0
395	226	0.0	525	7622	3.9	655	14463	0.0	785	827	0.0	915	557	0.0
400	191	0.0	530	8063	3.5	660	13640	0.0	790	768	0.0	920	412	0.0
405	196	0.0	535	8439	3.0	665	12787	0.0	795	711	0.0	925	332	0.0
410	195	0.0	540	8846	2.6	670	11721	0.0	800	693	0.0	930	466	0.0
415	235	0.0	545	9169	2.1	675	10776	0.0	805	609	0.0	935	480	0.0
420	323	0.0	550	9555	1.7	680	9728	0.0	810	615	0.0	940	404	0.0
425	510	0.1	555	9909	1.3	685	8803	0.0	815	547	0.0	945	502	0.0
430	889	0.2	560	10257	1.0	690	7856	0.0	820	491	0.0	950	495	0.0
435	1599	0.4	565	10655	0.7	695	6947	0.0	825	570	0.0	955	285	0.0
440	2967	1.0	570	11020	0.5	700	6181	0.0	830	477	0.0	960	433	0.0
445	4944	2.0	575	11481	0.4	705	5516	0.0	835	401	0.0	965	277	0.0
450	5950	2.7	580	12032	0.3	710	4865	0.0	840	440	0.0	970	517	0.0
455	5013	2.6	585	12647	0.2	715	4321	0.0	845	330	0.0	975	498	0.0
460	4393	2.6	590	13350	0.1	720	3839	0.0	850	336	0.0	980	465	0.0
465	3971	2.6	595	14054	0.1	725	3403	0.0	855	350	0.0	985	724	0.0
470	3442	2.5	600	14775	0.1	730	2978	0.0	860	266	0.0	990	861	0.0
475	3372	2.6	605	15552	0.0	735	2581	0.0	865	338	0.0	995	562	0.0
480	3623	2.9	610	16054	0.0	740	2292	0.0	870	363	0.0	1000	816	0.0
485	3960	3.3	615	16452	0.0	745	2037	0.0	875	335	0.0			

Summary

$R_f = 93.5$
 $R_g = 99.9$
 CIE $R_a = 94.7$
 $R_9 = 67.0$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 95	CES51 = 99	CES76 = 92
CES02 = 64	CES27 = 95	CES52 = 98	CES77 = 90
CES03 = 32	CES28 = 98	CES53 = 97	CES78 = 90
CES04 = 71	CES29 = 96	CES54 = 96	CES79 = 93
CES05 = 51	CES30 = 97	CES55 = 95	CES80 = 93
CES06 = 52	CES31 = 96	CES56 = 97	CES81 = 84
CES07 = 44	CES32 = 91	CES57 = 96	CES82 = 97
CES08 = 43	CES33 = 98	CES58 = 97	CES83 = 96
CES09 = 29	CES34 = 96	CES59 = 98	CES84 = 96
CES10 = 77	CES35 = 97	CES60 = 95	CES85 = 85
CES11 = 59	CES36 = 88	CES61 = 95	CES86 = 85
CES12 = 66	CES37 = 96	CES62 = 93	CES87 = 93
CES13 = 44	CES38 = 94	CES63 = 95	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 94	CES89 = 87
CES15 = 72	CES40 = 98	CES65 = 92	CES90 = 97
CES16 = 48	CES41 = 98	CES66 = 93	CES91 = 83
CES17 = 50	CES42 = 96	CES67 = 92	CES92 = 83
CES18 = 57	CES43 = 94	CES68 = 92	CES93 = 90
CES19 = 72	CES44 = 99	CES69 = 93	CES94 = 82
CES20 = 68	CES45 = 97	CES70 = 91	CES95 = 88
CES21 = 87	CES46 = 96	CES71 = 90	CES96 = 94
CES22 = 79	CES47 = 94	CES72 = 96	CES97 = 96
CES23 = 92	CES48 = 95	CES73 = 87	CES98 = 95
CES24 = 91	CES49 = 96	CES74 = 91	CES99 = 93
CES25 = 72	CES50 = 99	CES75 = 91	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)