

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: io LED

Report Number: P895854

Luminaire Tested: **GRZ-05L-930-30x60-X-UNV-STD-1F**

Issue Date: 11/20/2024



Test Information

Test Method: LM-79-08
Report Number: P895854
Test Lab: INNOVATION CENTER(G3)
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: GRZ-05L-930-30x60-X-UNV-STD-1F
Description: io LED 90CRI 3000K GRAZER 500 lumens per ft WITH 30 deg x 60 deg OPTIC
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 429.5 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 1.01 / 0.76
Luminous Opening: Rectangular (W 1' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 5.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P895854
CATALOG NUMBER: GRZ-05L-930-30x60-X-UNV-STD-1F

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P895854

CATALOG NUMBER: GRZ-05L-930-30x60-X-UNV-STD-1F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1 | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99 | 99 | 98 | 96 | 96 | 95 | 94 | 96 | 95 | 94 | 92 |
| 2 | 106 | 100 | 96 | 92 | 104 | 99 | 94 | 91 | 95 | 92 | 89 | 92 | 89 | 87 | 89 | 87 | 85 | 89 | 87 | 85 | 83 |
| 3 | 100 | 92 | 87 | 82 | 98 | 91 | 86 | 81 | 88 | 84 | 80 | 86 | 82 | 79 | 83 | 80 | 78 | 83 | 80 | 78 | 76 |
| 4 | 94 | 85 | 79 | 74 | 92 | 84 | 78 | 74 | 82 | 77 | 73 | 80 | 75 | 72 | 78 | 74 | 71 | 78 | 74 | 71 | 69 |
| 5 | 88 | 79 | 72 | 67 | 87 | 78 | 72 | 67 | 76 | 71 | 67 | 74 | 70 | 66 | 73 | 69 | 65 | 73 | 69 | 65 | 64 |
| 6 | 83 | 73 | 67 | 62 | 82 | 73 | 66 | 62 | 71 | 65 | 61 | 69 | 65 | 61 | 68 | 64 | 60 | 68 | 64 | 60 | 59 |
| 7 | 79 | 68 | 62 | 57 | 77 | 68 | 61 | 57 | 66 | 61 | 57 | 65 | 60 | 56 | 64 | 59 | 56 | 64 | 59 | 56 | 54 |
| 8 | 75 | 64 | 57 | 53 | 73 | 63 | 57 | 53 | 62 | 57 | 53 | 61 | 56 | 52 | 60 | 56 | 52 | 60 | 56 | 52 | 51 |
| 9 | 71 | 60 | 54 | 49 | 70 | 60 | 53 | 49 | 59 | 53 | 49 | 58 | 53 | 49 | 57 | 52 | 49 | 57 | 52 | 49 | 47 |
| 10 | 67 | 57 | 50 | 46 | 66 | 56 | 50 | 46 | 55 | 50 | 46 | 55 | 49 | 46 | 54 | 49 | 46 | 54 | 49 | 46 | 44 |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 45° | 90° |
|-----|-------|-------|-------|
| 0° | 30219 | 30219 | 30219 |
| 5° | 31397 | 31015 | 30309 |
| 10° | 26705 | 29446 | 30351 |
| 15° | 17287 | 24246 | 30891 |
| 20° | 11984 | 17715 | 30193 |
| 25° | 9426 | 13565 | 25513 |
| 30° | 8075 | 11176 | 20071 |
| 35° | 6645 | 9499 | 15142 |
| 40° | 5150 | 8058 | 11287 |
| 45° | 3808 | 6502 | 8730 |
| 50° | 2793 | 4993 | 6941 |
| 55° | 2083 | 3557 | 5077 |
| 60° | 1472 | 2389 | 3422 |
| 65° | 1024 | 1543 | 2322 |
| 70° | 717 | 1038 | 1510 |
| 75° | 524 | 624 | 1048 |
| 80° | 297 | 483 | 781 |
| 85° | 296 | 296 | 296 |



TEST NUMBER: P895854
 CATALOG NUMBER: GRZ-05L-930-30x60-X-UNV-STD-1F

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 44.3 | 10.3 |
| 10°-20° | 100.8 | 23.5 |
| 20°-30° | 103.1 | 24.0 |
| 30°-40° | 82.5 | 19.2 |
| 40°-50° | 55.1 | 12.8 |
| 50°-60° | 29.0 | 6.8 |
| 60°-70° | 11.0 | 2.6 |
| 70°-80° | 3.2 | 0.8 |
| 80°-90° | 0.5 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 248.1 | 57.8 |
| 0°-40° | 330.6 | 77.0 |
| 0°-60° | 414.8 | 96.6 |
| 0°-90° | 429.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 429.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0° | 468 | 468 | 468 | 468 | 468 | |
| 5° | 484 | 477 | 478 | 471 | 468 | 43 |
| 15° | 259 | 285 | 363 | 440 | 462 | 74 |
| 25° | 132 | 143 | 190 | 313 | 358 | 62 |
| 35° | 84 | 92 | 120 | 174 | 192 | 53 |
| 45° | 42 | 48 | 71 | 94 | 96 | 33 |
| 55° | 18 | 21 | 32 | 43 | 45 | 17 |
| 65° | 7 | 8 | 10 | 14 | 15 | 7 |
| 75° | 2 | 2 | 2 | 4 | 4 | 2 |
| 85° | 0 | 0 | 0 | 0 | 0 | 0 |
| 90° | 0 | 0 | 0 | 0 | 0 | |

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P895854

CATALOG NUMBER: GRZ-05L-930-30x60-X-UNV-STD-1F

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 468.0 | 468.0 | 468.0 | 468.0 | 468.0 | 468.0 | 468.0 | 468.0 | 468.0 | 468.0 | 468.0 |
| 2.5° | 473.1 | 472.6 | 477.3 | 473.9 | 475.2 | 473.9 | 470.1 | 468.0 | 467.6 | 463.4 | 465.5 |
| 5° | 484.4 | 477.7 | 478.9 | 476.8 | 478.9 | 478.5 | 474.3 | 471.8 | 469.7 | 467.2 | 467.6 |
| 7.5° | 457.1 | 457.9 | 461.7 | 463.4 | 469.3 | 471.4 | 469.3 | 467.6 | 465.9 | 464.6 | 465.1 |
| 10° | 407.3 | 410.3 | 415.7 | 426.7 | 438.9 | 449.1 | 453.3 | 457.9 | 461.7 | 462.1 | 462.9 |
| 12.5° | 335.3 | 339.5 | 348.4 | 360.2 | 387.1 | 411.5 | 432.2 | 448.2 | 457.5 | 462.5 | 461.7 |
| 15° | 258.6 | 259.9 | 270.8 | 290.2 | 319.7 | 362.7 | 403.5 | 436.0 | 452.8 | 464.6 | 462.1 |
| 17.5° | 206.0 | 207.7 | 216.5 | 231.3 | 259.5 | 307.1 | 368.2 | 416.6 | 447.4 | 455.8 | 453.7 |
| 20° | 174.4 | 173.1 | 179.8 | 192.1 | 215.7 | 257.8 | 321.4 | 386.3 | 425.0 | 436.8 | 439.4 |
| 22.5° | 149.1 | 150.4 | 154.6 | 164.3 | 184.9 | 219.9 | 278.0 | 346.7 | 389.6 | 402.7 | 404.8 |
| 25° | 132.3 | 133.5 | 137.7 | 144.5 | 161.3 | 190.4 | 240.5 | 302.4 | 344.6 | 357.2 | 358.1 |
| 27.5° | 121.3 | 120.5 | 123.4 | 128.5 | 143.2 | 168.1 | 209.4 | 260.7 | 299.9 | 312.6 | 313.4 |
| 30° | 108.3 | 107.8 | 110.8 | 116.3 | 128.1 | 149.9 | 184.9 | 226.6 | 254.4 | 266.6 | 269.2 |
| 32.5° | 96.5 | 96.1 | 99.4 | 104.1 | 115.8 | 134.8 | 165.1 | 197.6 | 216.5 | 226.6 | 229.2 |
| 35° | 84.3 | 84.7 | 87.2 | 93.1 | 103.6 | 120.5 | 148.3 | 171.0 | 184.5 | 189.6 | 192.1 |
| 37.5° | 72.5 | 72.9 | 76.3 | 82.2 | 92.7 | 107.8 | 130.2 | 147.8 | 155.8 | 159.6 | 159.2 |
| 40° | 61.1 | 61.9 | 64.0 | 70.8 | 81.3 | 95.6 | 113.7 | 126.8 | 132.3 | 132.7 | 133.9 |
| 42.5° | 50.9 | 50.9 | 54.3 | 59.8 | 69.9 | 83.4 | 99.4 | 108.7 | 112.9 | 112.5 | 111.6 |
| 45° | 41.7 | 42.1 | 44.2 | 49.7 | 59.0 | 71.2 | 85.1 | 93.5 | 96.1 | 94.4 | 95.6 |
| 47.5° | 34.1 | 34.5 | 36.2 | 41.3 | 49.3 | 61.1 | 72.1 | 80.1 | 82.2 | 80.9 | 80.9 |
| 50° | 27.8 | 28.2 | 29.5 | 33.3 | 40.0 | 49.7 | 59.8 | 66.6 | 68.7 | 68.3 | 69.1 |
| 52.5° | 22.7 | 22.7 | 24.0 | 26.9 | 32.4 | 40.4 | 48.4 | 54.3 | 56.0 | 55.6 | 55.2 |
| 55° | 18.5 | 18.5 | 19.4 | 21.5 | 25.7 | 31.6 | 38.3 | 42.9 | 44.2 | 44.6 | 45.1 |
| 57.5° | 14.7 | 14.7 | 15.2 | 16.8 | 19.8 | 24.4 | 29.5 | 32.8 | 34.1 | 34.5 | 34.9 |
| 60° | 11.4 | 11.4 | 12.2 | 13.1 | 15.6 | 18.5 | 21.9 | 24.4 | 26.1 | 26.1 | 26.5 |
| 62.5° | 8.8 | 8.8 | 9.3 | 10.1 | 11.8 | 13.9 | 16.0 | 18.1 | 18.9 | 19.8 | 20.2 |
| 65° | 6.7 | 6.7 | 7.2 | 7.6 | 8.8 | 10.1 | 11.8 | 13.5 | 14.3 | 14.7 | 15.2 |
| 67.5° | 5.1 | 5.1 | 5.1 | 5.9 | 6.7 | 7.6 | 8.4 | 9.7 | 10.1 | 10.9 | 11.4 |
| 70° | 3.8 | 3.8 | 3.8 | 4.2 | 4.6 | 5.5 | 5.9 | 6.7 | 7.6 | 8.0 | 8.0 |
| 72.5° | 2.9 | 2.9 | 2.9 | 2.9 | 3.4 | 3.8 | 4.2 | 4.6 | 5.5 | 5.9 | 5.9 |
| 75° | 2.1 | 2.1 | 2.1 | 2.1 | 2.5 | 2.5 | 2.9 | 3.4 | 3.8 | 4.2 | 4.2 |
| 77.5° | 1.7 | 1.7 | 1.3 | 1.7 | 1.7 | 1.7 | 2.1 | 2.1 | 2.5 | 2.9 | 2.9 |
| 80° | 0.8 | 0.8 | 0.8 | 0.8 | 1.3 | 1.3 | 1.3 | 1.7 | 1.7 | 1.7 | 2.1 |
| 82.5° | 0.4 | 0.4 | 0.4 | 0.4 | 0.8 | 0.8 | 0.8 | 0.8 | 0.8 | 1.3 | 1.3 |
| 85° | 0.4 | 0.4 | 0.4 | 0.4 | 0.4 | 0.4 | 0.4 | 0.4 | 0.4 | 0.4 | 0.4 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

iO LED

Report Number: SP1-2101-124-2

Luminaire Tested: GRZ-05L-930-10X10-X-UNV-STD-2F

Test Date: 02/10/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-124-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 02/10/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: iO LED
 Catalog Number: **GRZ-05L-930-10X10-X-UNV-STD-2F**
 Description: IO LED Wall Grazer GRZ

Spectral Parameters


CCT (K): 2957
 CIE u': 0.2518
 CIE v': 0.5232
 Duv: 0.0007
 CIE x: 0.4409
 CIE y: 0.4072
 CIE z: 0.1519
 Peak Wavelength (nm): 624
 Dominant Wavelength (nm): 582
 Purity: 54.9

 Rf: 93.7
 Rg: 100.3

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 94.1 | | |
| R1: | 94.6 | R9: | 66.4 |
| R2: | 96.3 | R10: | 90.2 |
| R3: | 96.6 | R11: | 96.1 |
| R4: | 95.3 | R12: | 86.8 |
| R5: | 94.2 | R13: | 95.0 |
| R6: | 95.7 | R14: | 97.3 |
| R7: | 94.2 | | |
| R8: | 85.7 | | |

Test Conditions

Stabilization Time: 48M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.4/38%
 Sphere Temperature (°C): 24.4




REPORT NUMBER: SP1-2101-124-2


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-124-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2101-124-2

Photopic Flux vs. Wavelength




#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 368 | 0.0 | 490 | 5466 | 0.8 | 620 | 17862 | 4.6 | 750 | 1898 | 0.0 | 880 | 436 | 0.0 |
| 365 | 310 | 0.0 | 495 | 6091 | 1.1 | 625 | 17922 | 4.0 | 755 | 1681 | 0.0 | 885 | 632 | 0.0 |
| 370 | 293 | 0.0 | 500 | 6757 | 1.5 | 630 | 17723 | 3.2 | 760 | 1509 | 0.0 | 890 | 653 | 0.0 |
| 375 | 346 | 0.0 | 505 | 7358 | 2.1 | 635 | 17256 | 2.6 | 765 | 1279 | 0.0 | 895 | 546 | 0.0 |
| 380 | 338 | 0.0 | 510 | 7854 | 2.7 | 640 | 16836 | 2.0 | 770 | 1201 | 0.0 | 900 | 354 | 0.0 |
| 385 | 299 | 0.0 | 515 | 8389 | 3.5 | 645 | 16513 | 1.6 | 775 | 1028 | 0.0 | 905 | 454 | 0.0 |
| 390 | 270 | 0.0 | 520 | 8991 | 4.4 | 650 | 15949 | 1.2 | 780 | 937 | 0.0 | 910 | 426 | 0.0 |
| 395 | 252 | 0.0 | 525 | 9495 | 5.1 | 655 | 15172 | 0.9 | 785 | 877 | 0.0 | 915 | 565 | 0.0 |
| 400 | 234 | 0.0 | 530 | 9972 | 5.9 | 660 | 14269 | 0.6 | 790 | 784 | 0.0 | 920 | 483 | 0.0 |
| 405 | 236 | 0.0 | 535 | 10431 | 6.5 | 665 | 13357 | 0.4 | 795 | 723 | 0.0 | 925 | 418 | 0.0 |
| 410 | 267 | 0.0 | 540 | 10792 | 7.0 | 670 | 12286 | 0.3 | 800 | 735 | 0.0 | 930 | 416 | 0.0 |
| 415 | 349 | 0.0 | 545 | 11118 | 7.4 | 675 | 11211 | 0.2 | 805 | 729 | 0.0 | 935 | 626 | 0.0 |
| 420 | 560 | 0.0 | 550 | 11517 | 7.8 | 680 | 10179 | 0.1 | 810 | 667 | 0.0 | 940 | 584 | 0.0 |
| 425 | 974 | 0.0 | 555 | 11837 | 8.1 | 685 | 9184 | 0.1 | 815 | 584 | 0.0 | 945 | 579 | 0.0 |
| 430 | 1769 | 0.0 | 560 | 12154 | 8.3 | 690 | 8166 | 0.0 | 820 | 546 | 0.0 | 950 | 504 | 0.0 |
| 435 | 3208 | 0.0 | 565 | 12489 | 8.3 | 695 | 7279 | 0.0 | 825 | 620 | 0.0 | 955 | 485 | 0.0 |
| 440 | 5576 | 0.1 | 570 | 12803 | 8.3 | 700 | 6419 | 0.0 | 830 | 532 | 0.0 | 960 | 719 | 0.0 |
| 445 | 7682 | 0.2 | 575 | 13201 | 8.2 | 705 | 5709 | 0.0 | 835 | 420 | 0.0 | 965 | 552 | 0.0 |
| 450 | 6958 | 0.2 | 580 | 13645 | 8.1 | 710 | 5055 | 0.0 | 840 | 444 | 0.0 | 970 | 586 | 0.0 |
| 455 | 5347 | 0.2 | 585 | 14250 | 7.9 | 715 | 4482 | 0.0 | 845 | 562 | 0.0 | 975 | 439 | 0.0 |
| 460 | 4823 | 0.2 | 590 | 14919 | 7.7 | 720 | 3984 | 0.0 | 850 | 454 | 0.0 | 980 | 736 | 0.0 |
| 465 | 4070 | 0.2 | 595 | 15606 | 7.4 | 725 | 3526 | 0.0 | 855 | 433 | 0.0 | 985 | 863 | 0.0 |
| 470 | 3650 | 0.2 | 600 | 16305 | 7.0 | 730 | 3109 | 0.0 | 860 | 383 | 0.0 | 990 | 722 | 0.0 |
| 475 | 3914 | 0.3 | 605 | 17030 | 6.6 | 735 | 2684 | 0.0 | 865 | 322 | 0.0 | 995 | 579 | 0.0 |
| 480 | 4339 | 0.4 | 610 | 17428 | 6.0 | 740 | 2396 | 0.0 | 870 | 523 | 0.0 | 1000 | 672 | 0.0 |
| 485 | 4881 | 0.6 | 615 | 17762 | 5.4 | 745 | 2098 | 0.0 | 875 | 541 | 0.0 | | | |

REPORT NUMBER: SP1-2101-124-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: 1239

S/P: 1.4

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 368 | 0.0 | 490 | 5466 | 8.4 | 620 | 17862 | 0.2 | 750 | 1898 | 0.0 | 880 | 436 | 0.0 |
| 365 | 310 | 0.0 | 495 | 6091 | 9.8 | 625 | 17922 | 0.2 | 755 | 1681 | 0.0 | 885 | 632 | 0.0 |
| 370 | 293 | 0.0 | 500 | 6757 | 11.3 | 630 | 17723 | 0.1 | 760 | 1509 | 0.0 | 890 | 653 | 0.0 |
| 375 | 346 | 0.0 | 505 | 7358 | 12.5 | 635 | 17256 | 0.1 | 765 | 1279 | 0.0 | 895 | 546 | 0.0 |
| 380 | 338 | 0.0 | 510 | 7854 | 13.3 | 640 | 16836 | 0.0 | 770 | 1201 | 0.0 | 900 | 354 | 0.0 |
| 385 | 299 | 0.0 | 515 | 8389 | 13.9 | 645 | 16513 | 0.0 | 775 | 1028 | 0.0 | 905 | 454 | 0.0 |
| 390 | 270 | 0.0 | 520 | 8991 | 14.3 | 650 | 15949 | 0.0 | 780 | 937 | 0.0 | 910 | 426 | 0.0 |
| 395 | 252 | 0.0 | 525 | 9495 | 14.2 | 655 | 15172 | 0.0 | 785 | 877 | 0.0 | 915 | 565 | 0.0 |
| 400 | 234 | 0.0 | 530 | 9972 | 13.7 | 660 | 14269 | 0.0 | 790 | 784 | 0.0 | 920 | 483 | 0.0 |
| 405 | 236 | 0.0 | 535 | 10431 | 13.0 | 665 | 13357 | 0.0 | 795 | 723 | 0.0 | 925 | 418 | 0.0 |
| 410 | 267 | 0.0 | 540 | 10792 | 11.9 | 670 | 12286 | 0.0 | 800 | 735 | 0.0 | 930 | 416 | 0.0 |
| 415 | 349 | 0.0 | 545 | 11118 | 10.7 | 675 | 11211 | 0.0 | 805 | 729 | 0.0 | 935 | 626 | 0.0 |
| 420 | 560 | 0.1 | 550 | 11517 | 9.4 | 680 | 10179 | 0.0 | 810 | 667 | 0.0 | 940 | 584 | 0.0 |
| 425 | 974 | 0.2 | 555 | 11837 | 8.1 | 685 | 9184 | 0.0 | 815 | 584 | 0.0 | 945 | 579 | 0.0 |
| 430 | 1769 | 0.6 | 560 | 12154 | 6.8 | 690 | 8166 | 0.0 | 820 | 546 | 0.0 | 950 | 504 | 0.0 |
| 435 | 3208 | 1.4 | 565 | 12489 | 5.6 | 695 | 7279 | 0.0 | 825 | 620 | 0.0 | 955 | 485 | 0.0 |
| 440 | 5576 | 3.1 | 570 | 12803 | 4.5 | 700 | 6419 | 0.0 | 830 | 532 | 0.0 | 960 | 719 | 0.0 |
| 445 | 7682 | 5.1 | 575 | 13201 | 3.6 | 705 | 5709 | 0.0 | 835 | 420 | 0.0 | 965 | 552 | 0.0 |
| 450 | 6958 | 5.4 | 580 | 13645 | 2.8 | 710 | 5055 | 0.0 | 840 | 444 | 0.0 | 970 | 586 | 0.0 |
| 455 | 5347 | 4.7 | 585 | 14250 | 2.2 | 715 | 4482 | 0.0 | 845 | 562 | 0.0 | 975 | 439 | 0.0 |
| 460 | 4823 | 4.7 | 590 | 14919 | 1.7 | 720 | 3984 | 0.0 | 850 | 454 | 0.0 | 980 | 736 | 0.0 |
| 465 | 4070 | 4.3 | 595 | 15606 | 1.2 | 725 | 3526 | 0.0 | 855 | 433 | 0.0 | 985 | 863 | 0.0 |
| 470 | 3650 | 4.2 | 600 | 16305 | 0.9 | 730 | 3109 | 0.0 | 860 | 383 | 0.0 | 990 | 722 | 0.0 |
| 475 | 3914 | 4.9 | 605 | 17030 | 0.7 | 735 | 2684 | 0.0 | 865 | 322 | 0.0 | 995 | 579 | 0.0 |
| 480 | 4339 | 5.9 | 610 | 17428 | 0.5 | 740 | 2396 | 0.0 | 870 | 523 | 0.0 | 1000 | 672 | 0.0 |
| 485 | 4881 | 7.1 | 615 | 17762 | 0.3 | 745 | 2098 | 0.0 | 875 | 541 | 0.0 | | | |

REPORT NUMBER: SP1-2101-124-2

Melanopic Flux vs. Wavelength




Melanopic Lumens: 471.9

M/P: 0.53





| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 368 | 0.0 | 490 | 5466 | 4.5 | 620 | 17862 | 0.0 | 750 | 1898 | 0.0 | 880 | 436 | 0.0 |
| 365 | 310 | 0.0 | 495 | 6091 | 5.0 | 625 | 17922 | 0.0 | 755 | 1681 | 0.0 | 885 | 632 | 0.0 |
| 370 | 293 | 0.0 | 500 | 6757 | 5.4 | 630 | 17723 | 0.0 | 760 | 1509 | 0.0 | 890 | 653 | 0.0 |
| 375 | 346 | 0.0 | 505 | 7358 | 5.6 | 635 | 17256 | 0.0 | 765 | 1279 | 0.0 | 895 | 546 | 0.0 |
| 380 | 338 | 0.0 | 510 | 7854 | 5.6 | 640 | 16836 | 0.0 | 770 | 1201 | 0.0 | 900 | 354 | 0.0 |
| 385 | 299 | 0.0 | 515 | 8389 | 5.5 | 645 | 16513 | 0.0 | 775 | 1028 | 0.0 | 905 | 454 | 0.0 |
| 390 | 270 | 0.0 | 520 | 8991 | 5.2 | 650 | 15949 | 0.0 | 780 | 937 | 0.0 | 910 | 426 | 0.0 |
| 395 | 252 | 0.0 | 525 | 9495 | 4.8 | 655 | 15172 | 0.0 | 785 | 877 | 0.0 | 915 | 565 | 0.0 |
| 400 | 234 | 0.0 | 530 | 9972 | 4.3 | 660 | 14269 | 0.0 | 790 | 784 | 0.0 | 920 | 483 | 0.0 |
| 405 | 236 | 0.0 | 535 | 10431 | 3.8 | 665 | 13357 | 0.0 | 795 | 723 | 0.0 | 925 | 418 | 0.0 |
| 410 | 267 | 0.0 | 540 | 10792 | 3.2 | 670 | 12286 | 0.0 | 800 | 735 | 0.0 | 930 | 416 | 0.0 |
| 415 | 349 | 0.0 | 545 | 11118 | 2.6 | 675 | 11211 | 0.0 | 805 | 729 | 0.0 | 935 | 626 | 0.0 |
| 420 | 560 | 0.1 | 550 | 11517 | 2.1 | 680 | 10179 | 0.0 | 810 | 667 | 0.0 | 940 | 584 | 0.0 |
| 425 | 974 | 0.2 | 555 | 11837 | 1.6 | 685 | 9184 | 0.0 | 815 | 584 | 0.0 | 945 | 579 | 0.0 |
| 430 | 1769 | 0.4 | 560 | 12154 | 1.2 | 690 | 8166 | 0.0 | 820 | 546 | 0.0 | 950 | 504 | 0.0 |
| 435 | 3208 | 0.9 | 565 | 12489 | 0.9 | 695 | 7279 | 0.0 | 825 | 620 | 0.0 | 955 | 485 | 0.0 |
| 440 | 5576 | 1.9 | 570 | 12803 | 0.6 | 700 | 6419 | 0.0 | 830 | 532 | 0.0 | 960 | 719 | 0.0 |
| 445 | 7682 | 3.0 | 575 | 13201 | 0.4 | 705 | 5709 | 0.0 | 835 | 420 | 0.0 | 965 | 552 | 0.0 |
| 450 | 6958 | 3.2 | 580 | 13645 | 0.3 | 710 | 5055 | 0.0 | 840 | 444 | 0.0 | 970 | 586 | 0.0 |
| 455 | 5347 | 2.8 | 585 | 14250 | 0.2 | 715 | 4482 | 0.0 | 845 | 562 | 0.0 | 975 | 439 | 0.0 |
| 460 | 4823 | 2.8 | 590 | 14919 | 0.1 | 720 | 3984 | 0.0 | 850 | 454 | 0.0 | 980 | 736 | 0.0 |
| 465 | 4070 | 2.7 | 595 | 15606 | 0.1 | 725 | 3526 | 0.0 | 855 | 433 | 0.0 | 985 | 863 | 0.0 |
| 470 | 3650 | 2.6 | 600 | 16305 | 0.1 | 730 | 3109 | 0.0 | 860 | 383 | 0.0 | 990 | 722 | 0.0 |
| 475 | 3914 | 3.0 | 605 | 17030 | 0.0 | 735 | 2684 | 0.0 | 865 | 322 | 0.0 | 995 | 579 | 0.0 |
| 480 | 4339 | 3.5 | 610 | 17428 | 0.0 | 740 | 2396 | 0.0 | 870 | 523 | 0.0 | 1000 | 672 | 0.0 |
| 485 | 4881 | 4.0 | 615 | 17762 | 0.0 | 745 | 2098 | 0.0 | 875 | 541 | 0.0 | | | |

Summary

$R_f = 93.7$
 $R_g = 100.3$
 CIE $R_a = 94.1$
 $R_9 = 66.4$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 93 | CES51 = 99 | CES76 = 90 |
| CES02 = 63 | CES27 = 96 | CES52 = 98 | CES77 = 92 |
| CES03 = 32 | CES28 = 97 | CES53 = 96 | CES78 = 88 |
| CES04 = 70 | CES29 = 93 | CES54 = 98 | CES79 = 95 |
| CES05 = 51 | CES30 = 96 | CES55 = 98 | CES80 = 95 |
| CES06 = 51 | CES31 = 94 | CES56 = 96 | CES81 = 87 |
| CES07 = 44 | CES32 = 90 | CES57 = 95 | CES82 = 97 |
| CES08 = 42 | CES33 = 94 | CES58 = 96 | CES83 = 96 |
| CES09 = 29 | CES34 = 94 | CES59 = 98 | CES84 = 96 |
| CES10 = 76 | CES35 = 97 | CES60 = 97 | CES85 = 87 |
| CES11 = 59 | CES36 = 92 | CES61 = 96 | CES86 = 87 |
| CES12 = 65 | CES37 = 95 | CES62 = 97 | CES87 = 93 |
| CES13 = 44 | CES38 = 99 | CES63 = 94 | CES88 = 96 |
| CES14 = 74 | CES39 = 99 | CES64 = 95 | CES89 = 87 |
| CES15 = 72 | CES40 = 97 | CES65 = 92 | CES90 = 97 |
| CES16 = 48 | CES41 = 97 | CES66 = 94 | CES91 = 86 |
| CES17 = 50 | CES42 = 95 | CES67 = 93 | CES92 = 85 |
| CES18 = 57 | CES43 = 94 | CES68 = 93 | CES93 = 91 |
| CES19 = 72 | CES44 = 99 | CES69 = 94 | CES94 = 83 |
| CES20 = 67 | CES45 = 96 | CES70 = 91 | CES95 = 88 |
| CES21 = 86 | CES46 = 95 | CES71 = 90 | CES96 = 93 |
| CES22 = 79 | CES47 = 93 | CES72 = 96 | CES97 = 95 |
| CES23 = 92 | CES48 = 95 | CES73 = 87 | CES98 = 94 |
| CES24 = 91 | CES49 = 95 | CES74 = 94 | CES99 = 93 |
| CES25 = 72 | CES50 = 99 | CES75 = 90 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)