

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: io LED

Report Number: P895884

Luminaire Tested: **GRZ-05L-940-ASYMx40-X-UNV-STD-1F**

Issue Date: 11/20/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P895884  
Test Lab: EVERFINE  
Issue Date: 11/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: GRZ-05L-940-ASYMx40-X-UNV-STD-1F  
Description: iO LED 90CRI 4000K GRAZER 500 lumens per ft WITH Asymmetric x 40 deg OPTIC  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 457.4 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.7 / 0.73  
Luminous Opening: Rectangular (W 1' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P895884  
CATALOG NUMBER: GRZ-05L-940-ASYMx40-X-UNV-STD-1F

### Luminous Intensity Polar Plot





TEST NUMBER: P895884

CATALOG NUMBER: GRZ-05L-940-ASYMx40-X-UNV-STD-1F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 103 | 100 | 98  | 99  | 97  | 95  | 95  | 94  | 93  | 95  | 94  | 93  | 91  |
| 2   | 105 | 100 | 95  | 91  | 103 | 98  | 93  | 90  | 94  | 91  | 88  | 91  | 88  | 86  | 89  | 86  | 84  | 89  | 86  | 84  | 82  |
| 3   | 99  | 91  | 86  | 81  | 97  | 90  | 85  | 80  | 87  | 83  | 79  | 85  | 81  | 78  | 82  | 79  | 76  | 82  | 79  | 76  | 75  |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 73  | 81  | 76  | 72  | 79  | 74  | 71  | 77  | 73  | 70  | 77  | 73  | 70  | 68  |
| 5   | 88  | 78  | 71  | 67  | 86  | 77  | 71  | 66  | 75  | 70  | 66  | 74  | 69  | 65  | 72  | 68  | 64  | 72  | 68  | 64  | 63  |
| 6   | 83  | 73  | 66  | 61  | 81  | 72  | 66  | 61  | 70  | 65  | 60  | 69  | 64  | 60  | 68  | 63  | 60  | 68  | 63  | 60  | 58  |
| 7   | 78  | 68  | 61  | 57  | 77  | 67  | 61  | 56  | 66  | 60  | 56  | 65  | 60  | 56  | 64  | 59  | 55  | 64  | 59  | 55  | 54  |
| 8   | 74  | 64  | 57  | 53  | 73  | 63  | 57  | 53  | 62  | 56  | 52  | 61  | 56  | 52  | 60  | 55  | 52  | 60  | 55  | 52  | 50  |
| 9   | 71  | 60  | 54  | 49  | 70  | 60  | 53  | 49  | 59  | 53  | 49  | 58  | 52  | 49  | 57  | 52  | 49  | 57  | 52  | 49  | 47  |
| 10  | 67  | 57  | 50  | 46  | 66  | 56  | 50  | 46  | 55  | 50  | 46  | 55  | 50  | 46  | 54  | 49  | 46  | 54  | 49  | 46  | 44  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 90°   | 180°  |
|-----|-------|-------|-------|
| 0°  | 36076 | 36076 | 36076 |
| 5°  | 47731 | 34625 | 24417 |
| 10° | 51903 | 30908 | 15972 |
| 15° | 43973 | 26472 | 10221 |
| 20° | 32983 | 21947 | 6384  |
| 25° | 24765 | 17227 | 4118  |
| 30° | 19497 | 12862 | 2796  |
| 35° | 16057 | 9286  | 2010  |
| 40° | 13529 | 6676  | 1526  |
| 45° | 11442 | 4767  | 1288  |
| 50° | 9533  | 3476  | 1045  |
| 55° | 7824  | 2634  | 912   |
| 60° | 6509  | 2118  | 852   |
| 65° | 5454  | 1818  | 825   |
| 70° | 4493  | 1661  | 812   |
| 75° | 3568  | 1597  | 873   |
| 80° | 2938  | 1673  | 967   |
| 85° | 2963  | 1778  | 1185  |



TEST NUMBER: P895884  
 CATALOG NUMBER: GRZ-05L-940-ASYMx40-X-UNV-STD-1F

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 50.6   | 11.1      |
| 10°-20°   | 111.7  | 24.4      |
| 20°-30°   | 104.3  | 22.8      |
| 30°-40°   | 77.3   | 16.9      |
| 40°-50°   | 52.5   | 11.5      |
| 50°-60°   | 32.1   | 7.0       |
| 60°-70°   | 17.5   | 3.8       |
| 70°-80°   | 8.6    | 1.9       |
| 80°-90°   | 2.9    | 0.6       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 266.6  | 58.3      |
| 0°-40°    | 343.9  | 75.2      |
| 0°-60°    | 428.5  | 93.7      |
| 0°-90°    | 457.4  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 457.4  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 45° | 90° | 135° | 180° | Flux |
|-----|-----|-----|-----|------|------|------|
| 0°  | 559 | 559 | 559 | 559  | 559  |      |
| 5°  | 736 | 663 | 534 | 429  | 377  | 72   |
| 15° | 658 | 602 | 396 | 215  | 153  | 179  |
| 25° | 348 | 363 | 242 | 94   | 58   | 161  |
| 35° | 204 | 212 | 118 | 40   | 26   | 128  |
| 45° | 125 | 122 | 52  | 20   | 14   | 97   |
| 55° | 70  | 64  | 23  | 11   | 8    | 63   |
| 65° | 36  | 29  | 12  | 7    | 5    | 36   |
| 75° | 14  | 12  | 6   | 4    | 4    | 16   |
| 85° | 4   | 4   | 2   | 2    | 2    | 4    |
| 90° | 0   | 0   | 0   | 0    | 0    |      |



TEST NUMBER: P895884

CATALOG NUMBER: GRZ-05L-940-ASYMx40-X-UNV-STD-1F

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 30°   | 60°   | 90°   | 120°  | 150°  | 180°  |
|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 558.7 | 558.7 | 558.7 | 558.7 | 558.7 | 558.7 | 558.7 |
| 0.5°  | 572.6 | 565.7 | 566.0 | 559.5 | 552.9 | 552.6 | 533.4 |
| 1°    | 592.1 | 582.0 | 575.0 | 558.4 | 542.0 | 535.7 | 514.2 |
| 1.5°  | 611.6 | 598.4 | 583.0 | 557.0 | 531.4 | 518.8 | 494.8 |
| 2°    | 631.1 | 614.6 | 590.9 | 554.9 | 520.4 | 501.7 | 476.3 |
| 2.5°  | 650.2 | 630.1 | 598.4 | 552.7 | 509.3 | 485.3 | 458.6 |
| 3°    | 668.7 | 645.6 | 605.3 | 549.8 | 498.0 | 468.7 | 441.0 |
| 3.5°  | 687.1 | 660.1 | 611.4 | 546.7 | 486.8 | 452.3 | 423.8 |
| 4°    | 704.4 | 674.0 | 617.3 | 543.1 | 475.2 | 436.6 | 407.6 |
| 4.5°  | 721.2 | 687.0 | 622.2 | 538.8 | 463.7 | 421.2 | 392.0 |
| 5°    | 736.4 | 699.0 | 626.3 | 534.2 | 452.3 | 406.4 | 376.7 |
| 5.5°  | 750.5 | 710.1 | 629.7 | 529.4 | 440.7 | 392.2 | 361.8 |
| 6°    | 763.1 | 719.9 | 632.2 | 524.1 | 429.2 | 377.8 | 347.0 |
| 6.5°  | 774.0 | 728.3 | 634.2 | 518.4 | 417.9 | 364.0 | 332.3 |
| 7°    | 783.0 | 735.3 | 635.3 | 512.3 | 406.8 | 350.7 | 318.3 |
| 7.5°  | 790.1 | 740.5 | 635.6 | 506.3 | 395.7 | 337.6 | 304.4 |
| 8°    | 794.9 | 744.4 | 635.1 | 499.7 | 384.7 | 324.5 | 291.3 |
| 8.5°  | 797.5 | 746.9 | 633.6 | 493.0 | 374.0 | 311.9 | 278.7 |
| 9°    | 797.7 | 747.6 | 631.6 | 485.9 | 363.6 | 299.2 | 266.4 |
| 9.5°  | 795.7 | 746.6 | 628.8 | 478.6 | 353.1 | 287.1 | 254.8 |
| 10°   | 791.6 | 743.8 | 625.2 | 471.4 | 342.7 | 275.3 | 243.6 |
| 10.5° | 785.1 | 739.8 | 621.0 | 463.9 | 332.7 | 264.1 | 232.7 |
| 11°   | 776.8 | 734.4 | 616.1 | 456.3 | 322.9 | 253.3 | 222.7 |
| 11.5° | 766.1 | 727.1 | 610.7 | 449.0 | 313.4 | 243.0 | 212.4 |
| 12°   | 754.4 | 718.4 | 604.9 | 441.5 | 304.0 | 232.8 | 202.8 |
| 12.5° | 740.7 | 708.6 | 598.3 | 433.9 | 294.8 | 223.0 | 193.9 |
| 13°   | 725.9 | 697.5 | 591.5 | 426.4 | 285.4 | 213.6 | 185.2 |
| 13.5° | 709.9 | 685.6 | 584.0 | 418.8 | 276.7 | 204.6 | 177.1 |
| 14°   | 693.1 | 672.7 | 576.5 | 411.2 | 267.9 | 195.9 | 169.1 |
| 14.5° | 675.5 | 658.9 | 568.2 | 403.6 | 259.3 | 187.6 | 161.0 |
| 15°   | 657.8 | 644.3 | 559.6 | 396.0 | 250.7 | 179.8 | 152.9 |
| 15.5° | 639.5 | 629.3 | 551.0 | 388.3 | 242.6 | 172.1 | 144.8 |
| 16°   | 621.2 | 613.9 | 541.9 | 380.5 | 234.4 | 164.3 | 137.8 |
| 16.5° | 602.5 | 598.0 | 532.6 | 373.1 | 226.2 | 156.6 | 131.3 |
| 17°   | 583.9 | 582.3 | 523.0 | 365.5 | 218.5 | 148.9 | 125.1 |
| 17.5° | 565.8 | 566.5 | 513.5 | 358.0 | 210.8 | 142.1 | 118.9 |
| 18°   | 548.1 | 550.5 | 503.7 | 350.4 | 203.3 | 135.8 | 113.3 |
| 18.5° | 530.4 | 535.0 | 493.7 | 342.7 | 196.0 | 129.7 | 107.7 |
| 19°   | 513.1 | 519.4 | 483.6 | 335.0 | 188.9 | 123.6 | 102.5 |
| 19.5° | 496.4 | 503.7 | 473.5 | 327.3 | 181.9 | 118.0 | 97.5  |
| 20°   | 480.0 | 488.8 | 463.4 | 319.4 | 175.1 | 112.5 | 92.9  |
| 20.5° | 464.7 | 474.0 | 453.3 | 311.6 | 168.7 | 107.4 | 88.4  |
| 21°   | 449.5 | 459.8 | 442.9 | 303.7 | 162.1 | 102.5 | 84.2  |
| 21.5° | 434.8 | 446.0 | 433.1 | 296.1 | 155.9 | 97.7  | 80.2  |
| 22°   | 421.0 | 432.4 | 422.9 | 288.4 | 149.7 | 93.3  | 76.5  |



TEST NUMBER: P895884

CATALOG NUMBER: GRZ-05L-940-ASYMx40-X-UNV-STD-1F

**CANDELA DISTRIBUTION (continued):**

|       | 0°    | 30°   | 60°   | 90°   | 120°  | 150° | 180° |
|-------|-------|-------|-------|-------|-------|------|------|
| 22.5° | 407.0 | 419.3 | 412.8 | 280.4 | 143.8 | 89.0 | 72.9 |
| 23°   | 394.0 | 406.7 | 402.8 | 272.6 | 138.1 | 85.0 | 69.5 |
| 23.5° | 381.8 | 394.7 | 392.6 | 265.0 | 132.6 | 81.1 | 66.3 |
| 24°   | 369.8 | 383.0 | 383.1 | 257.1 | 127.2 | 77.4 | 63.3 |
| 24.5° | 358.6 | 371.6 | 373.5 | 249.6 | 121.9 | 73.9 | 60.5 |
| 25°   | 347.6 | 360.9 | 364.2 | 241.8 | 117.1 | 70.7 | 57.8 |
| 25.5° | 337.4 | 350.5 | 354.8 | 234.2 | 112.2 | 67.5 | 55.2 |
| 26°   | 327.3 | 340.7 | 345.7 | 226.7 | 107.6 | 64.6 | 52.8 |
| 26.5° | 317.8 | 331.0 | 336.7 | 219.5 | 103.1 | 61.7 | 50.5 |
| 27°   | 308.8 | 321.6 | 328.0 | 212.2 | 98.7  | 59.1 | 48.3 |
| 27.5° | 299.9 | 313.0 | 319.3 | 205.1 | 94.6  | 56.5 | 46.3 |
| 28°   | 291.7 | 304.4 | 311.0 | 198.2 | 90.6  | 54.1 | 44.3 |
| 28.5° | 283.5 | 296.2 | 302.6 | 191.4 | 86.8  | 51.7 | 42.4 |
| 29°   | 276.0 | 288.4 | 294.5 | 185.0 | 83.1  | 49.6 | 40.7 |
| 29.5° | 268.7 | 280.6 | 286.6 | 178.8 | 79.7  | 47.5 | 39.0 |
| 30°   | 261.5 | 273.4 | 278.9 | 172.5 | 76.4  | 45.6 | 37.5 |
| 30.5° | 254.9 | 266.3 | 271.5 | 166.3 | 73.2  | 43.8 | 36.0 |
| 31°   | 248.3 | 259.5 | 264.1 | 160.1 | 70.0  | 42.0 | 34.5 |
| 31.5° | 242.1 | 252.8 | 256.9 | 153.9 | 66.8  | 40.3 | 33.2 |
| 32°   | 236.0 | 246.3 | 249.9 | 147.7 | 64.1  | 38.7 | 31.9 |
| 32.5° | 230.1 | 240.3 | 243.0 | 142.3 | 61.3  | 37.2 | 30.7 |
| 33°   | 224.4 | 234.3 | 236.4 | 137.1 | 58.8  | 35.8 | 29.5 |
| 33.5° | 219.0 | 228.4 | 229.6 | 132.1 | 56.4  | 34.4 | 28.4 |
| 34°   | 213.7 | 222.8 | 223.3 | 127.1 | 54.0  | 33.1 | 27.4 |
| 34.5° | 208.6 | 217.5 | 216.9 | 122.4 | 51.9  | 31.9 | 26.4 |
| 35°   | 203.7 | 212.2 | 210.9 | 117.8 | 49.8  | 30.7 | 25.5 |
| 35.5° | 198.8 | 207.1 | 204.7 | 113.3 | 47.7  | 29.6 | 24.6 |
| 36°   | 194.1 | 202.0 | 199.0 | 109.0 | 45.8  | 28.5 | 23.7 |
| 36.5° | 189.6 | 197.1 | 193.3 | 104.8 | 44.0  | 27.5 | 22.9 |
| 37°   | 185.1 | 192.5 | 187.7 | 100.8 | 42.3  | 26.5 | 22.1 |
| 37.5° | 180.9 | 187.9 | 182.3 | 96.9  | 40.6  | 25.6 | 21.3 |
| 38°   | 176.8 | 183.4 | 177.0 | 93.2  | 39.1  | 24.7 | 20.6 |
| 38.5° | 172.5 | 179.0 | 171.9 | 89.4  | 37.5  | 23.9 | 19.9 |
| 39°   | 168.4 | 174.8 | 166.8 | 85.8  | 36.1  | 23.1 | 19.3 |
| 39.5° | 164.5 | 170.5 | 161.7 | 82.4  | 34.7  | 22.4 | 18.7 |
| 40°   | 160.5 | 166.3 | 157.1 | 79.2  | 33.4  | 21.6 | 18.1 |
| 40.5° | 156.7 | 162.0 | 152.5 | 76.0  | 32.1  | 20.9 | 17.5 |
| 41°   | 153.0 | 157.8 | 148.0 | 72.9  | 31.0  | 20.3 | 17.0 |
| 41.5° | 149.4 | 153.5 | 143.7 | 70.0  | 29.9  | 19.6 | 16.5 |
| 42°   | 145.7 | 149.6 | 139.4 | 67.1  | 28.8  | 19.0 | 16.0 |
| 42.5° | 142.2 | 145.8 | 135.2 | 64.4  | 27.8  | 18.5 | 15.6 |
| 43°   | 138.7 | 142.1 | 131.1 | 61.7  | 26.8  | 17.9 | 15.1 |
| 43.5° | 135.3 | 138.4 | 127.2 | 59.2  | 25.8  | 17.4 | 14.7 |
| 44°   | 131.9 | 135.0 | 123.5 | 56.8  | 24.9  | 17.0 | 14.3 |
| 44.5° | 128.6 | 132.4 | 119.8 | 54.5  | 24.2  | 16.6 | 14.2 |



TEST NUMBER: P895884

CATALOG NUMBER: GRZ-05L-940-ASYMx40-X-UNV-STD-1F

**CANDELA DISTRIBUTION (continued):**

|       | 0°    | 30°   | 60°   | 90°  | 120° | 150° | 180° |
|-------|-------|-------|-------|------|------|------|------|
| 45°   | 125.3 | 127.9 | 116.2 | 52.2 | 23.3 | 15.9 | 14.1 |
| 45.5° | 122.1 | 124.5 | 112.5 | 50.1 | 22.5 | 15.5 | 13.6 |
| 46°   | 118.9 | 121.1 | 109.0 | 48.0 | 21.7 | 15.1 | 13.5 |
| 46.5° | 115.7 | 117.8 | 105.6 | 46.1 | 21.0 | 14.7 | 13.2 |
| 47°   | 112.7 | 114.5 | 102.3 | 44.2 | 20.3 | 14.3 | 12.6 |
| 47.5° | 109.6 | 111.4 | 99.1  | 42.5 | 19.7 | 13.9 | 12.2 |
| 48°   | 106.5 | 108.1 | 96.0  | 40.7 | 19.1 | 13.5 | 12.0 |
| 48.5° | 103.6 | 105.1 | 92.9  | 39.1 | 18.5 | 13.2 | 11.7 |
| 49°   | 100.6 | 102.0 | 89.9  | 37.5 | 17.9 | 12.8 | 11.0 |
| 49.5° | 97.8  | 99.0  | 87.0  | 36.0 | 17.4 | 12.5 | 10.6 |
| 50°   | 94.9  | 96.1  | 84.1  | 34.6 | 16.8 | 12.2 | 10.4 |
| 50.5° | 92.2  | 93.2  | 81.3  | 33.2 | 16.3 | 11.9 | 10.1 |
| 51°   | 89.4  | 90.3  | 78.6  | 31.9 | 15.9 | 11.6 | 9.8  |
| 51.5° | 86.8  | 87.5  | 75.8  | 30.7 | 15.4 | 11.3 | 9.6  |
| 52°   | 84.2  | 84.8  | 73.1  | 29.5 | 15.0 | 11.1 | 9.4  |
| 52.5° | 81.7  | 82.1  | 70.4  | 28.3 | 14.6 | 10.8 | 9.2  |
| 53°   | 79.1  | 79.5  | 67.9  | 27.3 | 14.1 | 10.6 | 9.0  |
| 53.5° | 76.7  | 76.8  | 65.5  | 26.2 | 13.8 | 10.3 | 8.7  |
| 54°   | 74.3  | 74.3  | 63.2  | 25.3 | 13.4 | 10.1 | 8.5  |
| 54.5° | 71.9  | 71.7  | 60.8  | 24.3 | 13.0 | 9.8  | 8.3  |
| 55°   | 69.5  | 69.3  | 58.6  | 23.4 | 12.7 | 9.6  | 8.1  |
| 55.5° | 67.3  | 66.9  | 56.4  | 22.6 | 12.4 | 9.4  | 8.0  |
| 56°   | 65.2  | 64.6  | 54.2  | 21.7 | 12.0 | 9.2  | 7.8  |
| 56.5° | 63.2  | 62.3  | 52.1  | 21.0 | 11.7 | 9.0  | 7.6  |
| 57°   | 61.2  | 60.1  | 50.1  | 20.2 | 11.4 | 8.8  | 7.5  |
| 57.5° | 59.3  | 57.9  | 48.2  | 19.5 | 11.1 | 8.6  | 7.3  |
| 58°   | 57.4  | 55.8  | 46.2  | 18.8 | 10.9 | 8.4  | 7.1  |
| 58.5° | 55.5  | 53.8  | 44.4  | 18.2 | 10.6 | 8.2  | 7.0  |
| 59°   | 53.8  | 51.8  | 42.5  | 17.6 | 10.4 | 8.1  | 6.9  |
| 59.5° | 52.1  | 49.8  | 40.8  | 17.0 | 10.1 | 7.9  | 6.7  |
| 60°   | 50.4  | 47.9  | 39.1  | 16.4 | 9.9  | 7.7  | 6.6  |
| 60.5° | 48.7  | 46.1  | 37.5  | 15.9 | 9.6  | 7.6  | 6.4  |
| 61°   | 47.0  | 44.4  | 35.9  | 15.4 | 9.4  | 7.4  | 6.3  |
| 61.5° | 45.4  | 42.6  | 34.4  | 14.9 | 9.2  | 7.2  | 6.2  |
| 62°   | 43.9  | 41.0  | 32.9  | 14.4 | 9.0  | 7.1  | 6.1  |
| 62.5° | 42.3  | 39.4  | 31.5  | 13.9 | 8.8  | 6.9  | 5.9  |
| 63°   | 40.9  | 37.9  | 30.2  | 13.5 | 8.6  | 6.8  | 5.8  |
| 63.5° | 39.4  | 36.4  | 28.9  | 13.1 | 8.4  | 6.6  | 5.7  |
| 64°   | 38.1  | 35.0  | 27.6  | 12.7 | 8.2  | 6.5  | 5.6  |
| 64.5° | 36.9  | 33.6  | 26.4  | 12.3 | 8.0  | 6.4  | 5.5  |
| 65°   | 35.7  | 32.2  | 25.2  | 11.9 | 7.8  | 6.2  | 5.4  |
| 65.5° | 34.6  | 31.0  | 24.1  | 11.6 | 7.6  | 6.1  | 5.3  |
| 66°   | 33.4  | 29.7  | 23.1  | 11.2 | 7.5  | 6.0  | 5.1  |
| 66.5° | 32.2  | 28.6  | 22.0  | 10.9 | 7.3  | 5.8  | 5.0  |
| 67°   | 31.0  | 27.4  | 21.1  | 10.5 | 7.1  | 5.7  | 4.9  |





TEST NUMBER: P895884

CATALOG NUMBER: GRZ-05L-940-ASYMx40-X-UNV-STD-1F

**CANDELA DISTRIBUTION (continued):**

|       | 0°   | 30°  | 60°  | 90°  | 120° | 150° | 180° |
|-------|------|------|------|------|------|------|------|
| 67.5° | 29.8 | 26.3 | 20.2 | 10.2 | 7.0  | 5.6  | 4.8  |
| 68°   | 28.6 | 25.2 | 19.2 | 9.9  | 6.8  | 5.5  | 4.7  |
| 68.5° | 27.4 | 24.2 | 18.4 | 9.6  | 6.7  | 5.3  | 4.6  |
| 69°   | 26.2 | 23.2 | 17.5 | 9.3  | 6.5  | 5.2  | 4.5  |
| 69.5° | 25.0 | 22.3 | 16.7 | 9.0  | 6.4  | 5.1  | 4.4  |
| 70°   | 23.8 | 21.3 | 16.0 | 8.8  | 6.2  | 5.0  | 4.3  |
| 70.5° | 22.7 | 20.5 | 15.3 | 8.5  | 6.1  | 4.9  | 4.3  |
| 71°   | 21.7 | 19.6 | 14.6 | 8.2  | 5.9  | 4.8  | 4.2  |
| 71.5° | 20.6 | 18.8 | 13.9 | 8.0  | 5.8  | 4.7  | 4.1  |
| 72°   | 19.6 | 17.9 | 13.3 | 7.8  | 5.7  | 4.6  | 4.0  |
| 72.5° | 18.6 | 17.2 | 12.6 | 7.5  | 5.5  | 4.4  | 3.9  |
| 73°   | 17.7 | 16.4 | 12.0 | 7.3  | 5.4  | 4.3  | 3.8  |
| 73.5° | 16.8 | 15.7 | 11.5 | 7.1  | 5.3  | 4.2  | 3.7  |
| 74°   | 15.9 | 15.0 | 11.0 | 6.8  | 5.1  | 4.1  | 3.6  |
| 74.5° | 15.0 | 14.3 | 10.4 | 6.6  | 5.0  | 4.0  | 3.5  |
| 75°   | 14.3 | 13.6 | 9.9  | 6.4  | 4.9  | 3.9  | 3.5  |
| 75.5° | 13.5 | 13.0 | 9.5  | 6.2  | 4.7  | 3.8  | 3.4  |
| 76°   | 12.7 | 12.4 | 9.0  | 6.0  | 4.6  | 3.7  | 3.3  |
| 76.5° | 12.0 | 11.8 | 8.6  | 5.8  | 4.5  | 3.6  | 3.2  |
| 77°   | 11.3 | 11.2 | 8.2  | 5.6  | 4.3  | 3.5  | 3.1  |
| 77.5° | 10.7 | 10.7 | 7.8  | 5.4  | 4.2  | 3.4  | 3.0  |
| 78°   | 10.1 | 10.1 | 7.4  | 5.2  | 4.1  | 3.3  | 2.9  |
| 78.5° | 9.5  | 9.6  | 7.0  | 5.0  | 3.9  | 3.2  | 2.9  |
| 79°   | 9.0  | 9.1  | 6.7  | 4.8  | 3.8  | 3.1  | 2.8  |
| 79.5° | 8.5  | 8.6  | 6.3  | 4.6  | 3.7  | 3.0  | 2.7  |
| 80°   | 7.9  | 8.2  | 6.0  | 4.5  | 3.6  | 2.9  | 2.6  |
| 80.5° | 7.5  | 7.7  | 5.7  | 4.3  | 3.4  | 2.8  | 2.5  |
| 81°   | 7.0  | 7.3  | 5.4  | 4.1  | 3.3  | 2.7  | 2.4  |
| 81.5° | 6.6  | 6.8  | 5.1  | 3.9  | 3.1  | 2.6  | 2.3  |
| 82°   | 6.2  | 6.4  | 4.8  | 3.7  | 3.0  | 2.5  | 2.2  |
| 82.5° | 5.8  | 6.0  | 4.5  | 3.5  | 2.9  | 2.4  | 2.1  |
| 83°   | 5.4  | 5.6  | 4.2  | 3.3  | 2.7  | 2.3  | 2.0  |
| 83.5° | 5.1  | 5.2  | 3.9  | 3.1  | 2.5  | 2.1  | 1.9  |
| 84°   | 4.7  | 4.9  | 3.6  | 2.9  | 2.4  | 2.0  | 1.8  |
| 84.5° | 4.3  | 4.5  | 3.3  | 2.7  | 2.2  | 1.9  | 1.7  |
| 85°   | 4.0  | 4.1  | 3.0  | 2.4  | 2.1  | 1.8  | 1.6  |
| 85.5° | 3.6  | 3.7  | 2.7  | 2.2  | 1.9  | 1.6  | 1.5  |
| 86°   | 3.3  | 3.3  | 2.4  | 2.0  | 1.7  | 1.5  | 1.3  |
| 86.5° | 2.9  | 2.9  | 2.1  | 1.7  | 1.5  | 1.3  | 1.2  |
| 87°   | 2.6  | 2.5  | 1.8  | 1.5  | 1.3  | 1.2  | 1.0  |
| 87.5° | 2.2  | 2.1  | 1.5  | 1.2  | 1.1  | 1.0  | 0.9  |
| 88°   | 1.8  | 1.6  | 1.1  | 0.9  | 0.8  | 0.8  | 0.7  |
| 88.5° | 1.4  | 1.2  | 0.8  | 0.6  | 0.6  | 0.6  | 0.5  |
| 89°   | 1.0  | 0.7  | 0.5  | 0.4  | 0.4  | 0.4  | 0.3  |
| 89.5° | 0.6  | 0.4  | 0.2  | 0.2  | 0.2  | 0.2  | 0.2  |



TEST NUMBER: P895884  
CATALOG NUMBER: GRZ-05L-940-ASYMx40-X-UNV-STD-1F

**CANDELA DISTRIBUTION (continued):**

|     | 0°  | 30° | 60° | 90° | 120° | 150° | 180° |
|-----|-----|-----|-----|-----|------|------|------|
| 90° | 0.3 | 0.2 | 0.2 | 0.1 | 0.1  | 0.1  | 0.1  |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

iO LED

Report Number: SP1-2101-124-4

Luminaire Tested: GRZ-05L-940-10X10-X-UNV-STD-2F

Test Date: 02/11/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-124-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 02/11/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: iO LED  
 Catalog Number: **GRZ-05L-940-10X10-X-UNV-STD-2F**  
 Description: IO LED Wall Grazer GRZ


**Spectral Parameters**

CCT (K): 3816  
 CIE u': 0.2273  
 CIE v': 0.5079  
 Duv: 0.0023  
 CIE x: 0.3907  
 CIE y: 0.3879  
 CIE z: 0.2214  
 Peak Wavelength (nm): 614  
 Dominant Wavelength (nm): 578  
 Purity: 33.8  
  
 Rf: 93.1  
 Rg: 100.2

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 93.3 |      |      |
| R1:       | 93.7 | R9:  | 69.2 |
| R2:       | 94.3 | R10: | 85.8 |
| R3:       | 93.9 | R11: | 94.6 |
| R4:       | 94.7 | R12: | 78.9 |
| R5:       | 92.9 | R13: | 93.7 |
| R6:       | 92.1 | R14: | 96.1 |
| R7:       | 95.7 |      |      |
| R8:       | 88.8 |      |      |

**Test Conditions**

Stabilization Time: 162M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.1/41%  
 Sphere Temperature (°C): 24.1




REPORT NUMBER: SP1-2101-124-4


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-124-4

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 7-step quadrangle

REPORT NUMBER: SP1-2101-124-4

**Photopic Flux vs. Wavelength**




#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 405           | 0.0           | 490    | 7814          | 1.1           | 620    | 16090         | 4.2           | 750    | 1625          | 0.0           | 880    | 367           | 0.0           |
| 365    | 335           | 0.0           | 495    | 8606          | 1.6           | 625    | 16048         | 3.5           | 755    | 1453          | 0.0           | 885    | 533           | 0.0           |
| 370    | 363           | 0.0           | 500    | 9360          | 2.1           | 630    | 15632         | 2.8           | 760    | 1318          | 0.0           | 890    | 535           | 0.0           |
| 375    | 388           | 0.0           | 505    | 10093         | 2.8           | 635    | 15196         | 2.3           | 765    | 1153          | 0.0           | 895    | 583           | 0.0           |
| 380    | 378           | 0.0           | 510    | 10690         | 3.7           | 640    | 14791         | 1.8           | 770    | 1033          | 0.0           | 900    | 438           | 0.0           |
| 385    | 344           | 0.0           | 515    | 11247         | 4.7           | 645    | 14481         | 1.4           | 775    | 948           | 0.0           | 905    | 410           | 0.0           |
| 390    | 323           | 0.0           | 520    | 11881         | 5.8           | 650    | 13840         | 1.0           | 780    | 831           | 0.0           | 910    | 413           | 0.0           |
| 395    | 292           | 0.0           | 525    | 12359         | 6.6           | 655    | 13125         | 0.8           | 785    | 778           | 0.0           | 915    | 489           | 0.0           |
| 400    | 261           | 0.0           | 530    | 12780         | 7.5           | 660    | 12353         | 0.5           | 790    | 708           | 0.0           | 920    | 518           | 0.0           |
| 405    | 272           | 0.0           | 535    | 13137         | 8.1           | 665    | 11536         | 0.4           | 795    | 643           | 0.0           | 925    | 563           | 0.0           |
| 410    | 331           | 0.0           | 540    | 13369         | 8.7           | 670    | 10559         | 0.2           | 800    | 645           | 0.0           | 930    | 452           | 0.0           |
| 415    | 497           | 0.0           | 545    | 13551         | 9.0           | 675    | 9658          | 0.2           | 805    | 648           | 0.0           | 935    | 454           | 0.0           |
| 420    | 847           | 0.0           | 550    | 13731         | 9.3           | 680    | 8746          | 0.1           | 810    | 610           | 0.0           | 940    | 446           | 0.0           |
| 425    | 1620          | 0.0           | 555    | 13860         | 9.5           | 685    | 7852          | 0.1           | 815    | 505           | 0.0           | 945    | 516           | 0.0           |
| 430    | 3114          | 0.0           | 560    | 13921         | 9.5           | 690    | 7031          | 0.0           | 820    | 544           | 0.0           | 950    | 514           | 0.0           |
| 435    | 5958          | 0.1           | 565    | 13987         | 9.3           | 695    | 6210          | 0.0           | 825    | 591           | 0.0           | 955    | 487           | 0.0           |
| 440    | 10649         | 0.2           | 570    | 14001         | 9.1           | 700    | 5517          | 0.0           | 830    | 484           | 0.0           | 960    | 723           | 0.0           |
| 445    | 14435         | 0.3           | 575    | 14097         | 8.8           | 705    | 4890          | 0.0           | 835    | 440           | 0.0           | 965    | 281           | 0.0           |
| 450    | 12623         | 0.3           | 580    | 14256         | 8.5           | 710    | 4342          | 0.0           | 840    | 452           | 0.0           | 970    | 627           | 0.0           |
| 455    | 9257          | 0.3           | 585    | 14467         | 8.0           | 715    | 3886          | 0.0           | 845    | 527           | 0.0           | 975    | 532           | 0.0           |
| 460    | 8011          | 0.3           | 590    | 14814         | 7.7           | 720    | 3470          | 0.0           | 850    | 515           | 0.0           | 980    | 902           | 0.0           |
| 465    | 6473          | 0.3           | 595    | 15120         | 7.2           | 725    | 3080          | 0.0           | 855    | 517           | 0.0           | 985    | 1126          | 0.0           |
| 470    | 5561          | 0.3           | 600    | 15449         | 6.7           | 730    | 2713          | 0.0           | 860    | 406           | 0.0           | 990    | 578           | 0.0           |
| 475    | 5845          | 0.5           | 605    | 15859         | 6.1           | 735    | 2357          | 0.0           | 865    | 434           | 0.0           | 995    | 699           | 0.0           |
| 480    | 6344          | 0.6           | 610    | 16059         | 5.5           | 740    | 2032          | 0.0           | 870    | 578           | 0.0           | 1000   | 687           | 0.0           |
| 485    | 7040          | 0.8           | 615    | 16120         | 4.9           | 745    | 1812          | 0.0           | 875    | 517           | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-124-4

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 1669.3**


**S/P: 1.71**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 405           | 0.0           | 490    | 7814          | 12.0          | 620    | 16090         | 0.2           | 750    | 1625          | 0.0           | 880    | 367           | 0.0           |
| 365    | 335           | 0.0           | 495    | 8606          | 13.9          | 625    | 16048         | 0.1           | 755    | 1453          | 0.0           | 885    | 533           | 0.0           |
| 370    | 363           | 0.0           | 500    | 9360          | 15.7          | 630    | 15632         | 0.1           | 760    | 1318          | 0.0           | 890    | 535           | 0.0           |
| 375    | 388           | 0.0           | 505    | 10093         | 17.2          | 635    | 15196         | 0.1           | 765    | 1153          | 0.0           | 895    | 583           | 0.0           |
| 380    | 378           | 0.0           | 510    | 10690         | 18.1          | 640    | 14791         | 0.0           | 770    | 1033          | 0.0           | 900    | 438           | 0.0           |
| 385    | 344           | 0.0           | 515    | 11247         | 18.6          | 645    | 14481         | 0.0           | 775    | 948           | 0.0           | 905    | 410           | 0.0           |
| 390    | 323           | 0.0           | 520    | 11881         | 18.9          | 650    | 13840         | 0.0           | 780    | 831           | 0.0           | 910    | 413           | 0.0           |
| 395    | 292           | 0.0           | 525    | 12359         | 18.5          | 655    | 13125         | 0.0           | 785    | 778           | 0.0           | 915    | 489           | 0.0           |
| 400    | 261           | 0.0           | 530    | 12780         | 17.6          | 660    | 12353         | 0.0           | 790    | 708           | 0.0           | 920    | 518           | 0.0           |
| 405    | 272           | 0.0           | 535    | 13137         | 16.4          | 665    | 11536         | 0.0           | 795    | 643           | 0.0           | 925    | 563           | 0.0           |
| 410    | 331           | 0.0           | 540    | 13369         | 14.8          | 670    | 10559         | 0.0           | 800    | 645           | 0.0           | 930    | 452           | 0.0           |
| 415    | 497           | 0.1           | 545    | 13551         | 13.0          | 675    | 9658          | 0.0           | 805    | 648           | 0.0           | 935    | 454           | 0.0           |
| 420    | 847           | 0.1           | 550    | 13731         | 11.2          | 680    | 8746          | 0.0           | 810    | 610           | 0.0           | 940    | 446           | 0.0           |
| 425    | 1620          | 0.4           | 555    | 13860         | 9.5           | 685    | 7852          | 0.0           | 815    | 505           | 0.0           | 945    | 516           | 0.0           |
| 430    | 3114          | 1.1           | 560    | 13921         | 7.8           | 690    | 7031          | 0.0           | 820    | 544           | 0.0           | 950    | 514           | 0.0           |
| 435    | 5958          | 2.7           | 565    | 13987         | 6.3           | 695    | 6210          | 0.0           | 825    | 591           | 0.0           | 955    | 487           | 0.0           |
| 440    | 10649         | 6.0           | 570    | 14001         | 4.9           | 700    | 5517          | 0.0           | 830    | 484           | 0.0           | 960    | 723           | 0.0           |
| 445    | 14435         | 9.7           | 575    | 14097         | 3.8           | 705    | 4890          | 0.0           | 835    | 440           | 0.0           | 965    | 281           | 0.0           |
| 450    | 12623         | 9.8           | 580    | 14256         | 2.9           | 710    | 4342          | 0.0           | 840    | 452           | 0.0           | 970    | 627           | 0.0           |
| 455    | 9257          | 8.1           | 585    | 14467         | 2.2           | 715    | 3886          | 0.0           | 845    | 527           | 0.0           | 975    | 532           | 0.0           |
| 460    | 8011          | 7.7           | 590    | 14814         | 1.6           | 720    | 3470          | 0.0           | 850    | 515           | 0.0           | 980    | 902           | 0.0           |
| 465    | 6473          | 6.8           | 595    | 15120         | 1.2           | 725    | 3080          | 0.0           | 855    | 517           | 0.0           | 985    | 1126          | 0.0           |
| 470    | 5561          | 6.4           | 600    | 15449         | 0.9           | 730    | 2713          | 0.0           | 860    | 406           | 0.0           | 990    | 578           | 0.0           |
| 475    | 5845          | 7.3           | 605    | 15859         | 0.6           | 735    | 2357          | 0.0           | 865    | 434           | 0.0           | 995    | 699           | 0.0           |
| 480    | 6344          | 8.6           | 610    | 16059         | 0.4           | 740    | 2032          | 0.0           | 870    | 578           | 0.0           | 1000   | 687           | 0.0           |
| 485    | 7040          | 10.2          | 615    | 16120         | 0.3           | 745    | 1812          | 0.0           | 875    | 517           | 0.0           |        |               |               |



REPORT NUMBER: SP1-2101-124-4

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: 670.2 M/P: 0.69**





| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 405           | 0.0           | 490    | 7814          | 6.5           | 620    | 16090         | 0.0           | 750    | 1625          | 0.0           | 880    | 367           | 0.0           |
| 365    | 335           | 0.0           | 495    | 8606          | 7.1           | 625    | 16048         | 0.0           | 755    | 1453          | 0.0           | 885    | 533           | 0.0           |
| 370    | 363           | 0.0           | 500    | 9360          | 7.5           | 630    | 15632         | 0.0           | 760    | 1318          | 0.0           | 890    | 535           | 0.0           |
| 375    | 388           | 0.0           | 505    | 10093         | 7.7           | 635    | 15196         | 0.0           | 765    | 1153          | 0.0           | 895    | 583           | 0.0           |
| 380    | 378           | 0.0           | 510    | 10690         | 7.7           | 640    | 14791         | 0.0           | 770    | 1033          | 0.0           | 900    | 438           | 0.0           |
| 385    | 344           | 0.0           | 515    | 11247         | 7.3           | 645    | 14481         | 0.0           | 775    | 948           | 0.0           | 905    | 410           | 0.0           |
| 390    | 323           | 0.0           | 520    | 11881         | 6.9           | 650    | 13840         | 0.0           | 780    | 831           | 0.0           | 910    | 413           | 0.0           |
| 395    | 292           | 0.0           | 525    | 12359         | 6.3           | 655    | 13125         | 0.0           | 785    | 778           | 0.0           | 915    | 489           | 0.0           |
| 400    | 261           | 0.0           | 530    | 12780         | 5.5           | 660    | 12353         | 0.0           | 790    | 708           | 0.0           | 920    | 518           | 0.0           |
| 405    | 272           | 0.0           | 535    | 13137         | 4.7           | 665    | 11536         | 0.0           | 795    | 643           | 0.0           | 925    | 563           | 0.0           |
| 410    | 331           | 0.0           | 540    | 13369         | 3.9           | 670    | 10559         | 0.0           | 800    | 645           | 0.0           | 930    | 452           | 0.0           |
| 415    | 497           | 0.0           | 545    | 13551         | 3.1           | 675    | 9658          | 0.0           | 805    | 648           | 0.0           | 935    | 454           | 0.0           |
| 420    | 847           | 0.1           | 550    | 13731         | 2.5           | 680    | 8746          | 0.0           | 810    | 610           | 0.0           | 940    | 446           | 0.0           |
| 425    | 1620          | 0.3           | 555    | 13860         | 1.9           | 685    | 7852          | 0.0           | 815    | 505           | 0.0           | 945    | 516           | 0.0           |
| 430    | 3114          | 0.7           | 560    | 13921         | 1.4           | 690    | 7031          | 0.0           | 820    | 544           | 0.0           | 950    | 514           | 0.0           |
| 435    | 5958          | 1.6           | 565    | 13987         | 1.0           | 695    | 6210          | 0.0           | 825    | 591           | 0.0           | 955    | 487           | 0.0           |
| 440    | 10649         | 3.6           | 570    | 14001         | 0.7           | 700    | 5517          | 0.0           | 830    | 484           | 0.0           | 960    | 723           | 0.0           |
| 445    | 14435         | 5.7           | 575    | 14097         | 0.5           | 705    | 4890          | 0.0           | 835    | 440           | 0.0           | 965    | 281           | 0.0           |
| 450    | 12623         | 5.8           | 580    | 14256         | 0.3           | 710    | 4342          | 0.0           | 840    | 452           | 0.0           | 970    | 627           | 0.0           |
| 455    | 9257          | 4.9           | 585    | 14467         | 0.2           | 715    | 3886          | 0.0           | 845    | 527           | 0.0           | 975    | 532           | 0.0           |
| 460    | 8011          | 4.7           | 590    | 14814         | 0.1           | 720    | 3470          | 0.0           | 850    | 515           | 0.0           | 980    | 902           | 0.0           |
| 465    | 6473          | 4.2           | 595    | 15120         | 0.1           | 725    | 3080          | 0.0           | 855    | 517           | 0.0           | 985    | 1126          | 0.0           |
| 470    | 5561          | 4.0           | 600    | 15449         | 0.1           | 730    | 2713          | 0.0           | 860    | 406           | 0.0           | 990    | 578           | 0.0           |
| 475    | 5845          | 4.5           | 605    | 15859         | 0.0           | 735    | 2357          | 0.0           | 865    | 434           | 0.0           | 995    | 699           | 0.0           |
| 480    | 6344          | 5.1           | 610    | 16059         | 0.0           | 740    | 2032          | 0.0           | 870    | 578           | 0.0           | 1000   | 687           | 0.0           |
| 485    | 7040          | 5.8           | 615    | 16120         | 0.0           | 745    | 1812          | 0.0           | 875    | 517           | 0.0           |        |               |               |

**Summary**

$R_f = 93.1$   
 $R_g = 100.2$   
 CIE  $R_a = 93.3$   
 $R_9 = 69.2$




**Color Vector Graphics**






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |             |            |            |
|------------|-------------|------------|------------|
| CES01 = 86 | CES26 = 93  | CES51 = 99 | CES76 = 86 |
| CES02 = 62 | CES27 = 94  | CES52 = 98 | CES77 = 90 |
| CES03 = 31 | CES28 = 96  | CES53 = 95 | CES78 = 84 |
| CES04 = 69 | CES29 = 94  | CES54 = 97 | CES79 = 97 |
| CES05 = 49 | CES30 = 99  | CES55 = 96 | CES80 = 94 |
| CES06 = 51 | CES31 = 95  | CES56 = 95 | CES81 = 92 |
| CES07 = 42 | CES32 = 90  | CES57 = 94 | CES82 = 97 |
| CES08 = 41 | CES33 = 96  | CES58 = 95 | CES83 = 97 |
| CES09 = 29 | CES34 = 93  | CES59 = 97 | CES84 = 95 |
| CES10 = 74 | CES35 = 96  | CES60 = 95 | CES85 = 87 |
| CES11 = 57 | CES36 = 87  | CES61 = 94 | CES86 = 91 |
| CES12 = 63 | CES37 = 94  | CES62 = 93 | CES87 = 92 |
| CES13 = 43 | CES38 = 95  | CES63 = 94 | CES88 = 97 |
| CES14 = 74 | CES39 = 99  | CES64 = 93 | CES89 = 89 |
| CES15 = 71 | CES40 = 97  | CES65 = 90 | CES90 = 97 |
| CES16 = 47 | CES41 = 99  | CES66 = 91 | CES91 = 79 |
| CES17 = 49 | CES42 = 93  | CES67 = 90 | CES92 = 84 |
| CES18 = 56 | CES43 = 94  | CES68 = 90 | CES93 = 91 |
| CES19 = 71 | CES44 = 100 | CES69 = 91 | CES94 = 85 |
| CES20 = 66 | CES45 = 96  | CES70 = 88 | CES95 = 86 |
| CES21 = 85 | CES46 = 96  | CES71 = 85 | CES96 = 93 |
| CES22 = 78 | CES47 = 97  | CES72 = 95 | CES97 = 94 |
| CES23 = 91 | CES48 = 96  | CES73 = 82 | CES98 = 94 |
| CES24 = 90 | CES49 = 95  | CES74 = 95 | CES99 = 93 |
| CES25 = 71 | CES50 = 99  | CES75 = 85 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)