

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P895845

Luminaire Tested: **GRZ-05L-935-17x30-X-UNV-STD-1F**

Issue Date: 11/20/2024

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-79-08
Report Number: P895845
Test Lab: INNOVATION CENTER(G3)
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: GRZ-05L-935-17x30-X-UNV-STD-1F
Description: iO LED 90CRI 3500K GRAZER 500 lumens per ft WITH 17 deg x 30 deg OPTIC
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 546.8 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.52 / 0.34
Luminous Opening: Rectangular (W 1' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 5.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P895845
CATALOG NUMBER: GRZ-05L-935-17x30-X-UNV-STD-1F

Luminous Intensity Polar Plot



TEST NUMBER: P895845

CATALOG NUMBER: GRZ-05L-935-17x30-X-UNV-STD-1F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	95
2	110	105	102	99	107	104	100	98	100	98	96	98	95	94	95	93	92	92	92	90
3	105	100	95	92	103	98	94	91	96	93	90	93	91	88	91	89	87	87	87	86
4	101	95	90	86	99	94	89	86	92	88	85	90	86	84	88	85	83	83	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	79	79	78
6	94	86	81	78	92	86	81	77	84	80	77	83	79	76	82	78	76	76	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	73	73	72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	70	70	69
9	84	77	72	68	83	76	72	68	75	71	68	74	71	68	74	70	68	68	68	67
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	65	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	145549	145549	145549
5°	130166	137017	131378
10°	45352	75375	110932
15°	20161	31318	80365
20°	11750	16794	60771
25°	5044	10708	47329
30°	1700	6643	20899
35°	1041	3429	19029
40°	893	1964	16715
45°	968	1525	11689
50°	763	713	5133
55°	687	687	2049
60°	659	723	1898
65°	703	703	1772
70°	661	566	1340
75°	499	499	624
80°	372	372	372
85°	370	370	370



TEST NUMBER: P895845
CATALOG NUMBER: GRZ-05L-935-17x30-X-UNV-STD-1F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.5	30.3
10°-20°	175.1	32.0
20°-30°	108.4	19.8
30°-40°	54.8	10.0
40°-50°	27.1	5.0
50°-60°	8.1	1.5
60°-70°	5.0	0.9
70°-80°	2.3	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	449.0	82.1
0°-40°	503.8	92.1
0°-60°	539.1	98.6
0°-90°	546.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	546.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2254	2254	2254	2254	2254	
5°	2008	2052	2114	2055	2027	140
15°	302	335	468	820	1202	90
25°	71	88	150	360	664	36
35°	13	14	44	161	241	9
45°	11	9	17	44	128	8
55°	6	6	6	9	18	6
65°	5	5	5	3	12	4
75°	2	3	2	1	2	2
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P895845

CATALOG NUMBER: GRZ-05L-935-17x30-X-UNV-STD-1F

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2254.1	2254.1	2254.1	2254.1	2254.1	2254.1	2254.1	2254.1	2254.1	2254.1	2254.1
1°	2276.8	2269.7	2271.3	2280.4	2285.9	2275.3	2260.1	2248.5	2253.6	2237.9	2230.3
2°	2300.1	2294.5	2291.0	2294.0	2281.9	2268.2	2252.5	2243.9	2240.9	2232.8	2240.4
3°	2274.8	2267.7	2269.7	2276.8	2270.8	2271.8	2232.8	2206.5	2204.0	2193.4	2184.8
4°	2174.7	2179.7	2189.8	2190.8	2197.9	2199.9	2186.3	2136.2	2137.2	2117.4	2107.8
5°	2008.2	2011.7	2042.1	2054.7	2100.3	2113.9	2117.4	2056.8	2050.7	2020.8	2026.9
6°	1785.0	1719.8	1801.2	1833.6	1925.2	1987.4	2009.2	1999.5	1969.2	1934.8	1935.3
7°	1392.9	1398.5	1445.1	1534.6	1705.1	1825.5	1915.1	1934.8	1894.3	1870.1	1847.3
8°	1074.2	1097.4	1163.7	1258.3	1427.9	1622.6	1785.0	1829.6	1819.4	1795.2	1791.6
9°	889.5	871.8	924.9	1000.3	1162.7	1413.2	1613.5	1708.1	1737.5	1745.1	1746.6
10°	691.7	712.4	737.7	816.1	953.7	1149.6	1412.7	1559.4	1636.3	1679.3	1691.9
11°	560.1	567.7	600.1	674.0	777.7	957.8	1223.9	1389.4	1507.8	1594.8	1605.9
12°	460.9	467.5	489.3	543.9	638.0	781.2	1009.9	1216.8	1394.9	1496.6	1519.4
13°	391.6	399.2	416.9	459.4	532.3	657.2	815.6	1039.8	1244.7	1388.9	1409.1
14°	336.5	345.0	356.7	394.2	453.3	541.9	677.0	891.0	1110.6	1272.5	1299.3
15°	301.6	302.6	315.2	341.0	393.2	468.5	584.9	764.0	987.7	1169.8	1202.2
17.5°	226.7	225.2	226.7	246.9	277.3	332.4	412.4	567.7	806.0	964.3	999.8
20°	171.0	171.5	168.0	179.6	204.9	244.4	310.7	461.9	705.8	864.2	884.4
22.5°	118.9	117.9	119.4	130.5	154.8	191.2	243.4	377.0	643.1	797.4	814.1
25°	70.8	72.3	78.5	91.6	115.4	150.3	198.8	304.6	526.7	629.4	664.3
27.5°	41.0	41.5	46.5	60.7	83.5	116.9	163.4	237.3	364.8	419.5	428.6
30°	22.8	22.8	26.3	35.4	56.6	89.1	133.6	196.8	264.6	279.8	280.3
32.5°	15.2	15.2	16.2	20.7	34.9	64.7	108.8	169.5	229.7	251.5	255.0
35°	13.2	12.6	13.2	14.7	21.7	43.5	83.5	144.2	211.5	237.3	241.4
37.5°	11.6	11.6	12.1	13.7	16.7	28.3	59.2	114.4	187.2	219.6	224.2
40°	10.6	10.6	11.1	13.7	16.7	23.3	37.4	83.0	154.3	193.3	198.3
42.5°	10.1	10.1	10.1	12.1	15.7	21.2	21.7	53.1	118.9	158.9	166.5
45°	10.6	10.1	9.1	9.6	12.1	16.7	12.6	31.4	82.5	122.5	128.0
47.5°	10.1	10.1	9.6	9.1	9.1	11.1	8.1	17.2	51.6	85.0	88.1
50°	7.6	7.6	6.6	8.1	8.6	7.1	6.1	11.1	31.9	48.0	51.1
52.5°	6.6	6.6	6.1	6.1	7.1	6.6	4.6	9.1	20.2	26.8	27.8
55°	6.1	5.6	5.6	6.1	6.6	6.1	4.0	7.1	14.2	17.7	18.2
57.5°	5.6	5.6	5.6	5.6	6.6	6.1	4.0	5.1	11.1	14.2	15.7
60°	5.1	5.1	5.6	5.6	6.1	5.6	3.5	3.5	9.1	12.6	14.7
62.5°	4.6	5.1	5.1	5.6	6.1	5.1	3.0	2.5	7.1	11.6	13.7
65°	4.6	4.6	5.1	5.6	5.6	4.6	2.5	2.0	5.6	9.6	11.6
67.5°	4.0	4.0	4.6	5.1	5.6	4.0	1.5	1.5	4.6	8.1	9.6
70°	3.5	3.5	4.0	4.6	4.6	3.0	1.5	1.5	3.0	6.6	7.1
72.5°	3.0	3.0	3.5	4.0	4.0	2.5	1.0	1.0	2.0	5.1	4.6
75°	2.0	2.5	2.5	3.0	3.0	2.0	1.0	1.0	1.5	3.0	2.5
77.5°	1.5	1.5	2.0	2.5	2.5	1.5	0.5	0.5	1.0	2.0	1.5
80°	1.0	1.0	1.5	1.5	1.5	1.0	0.5	0.5	0.5	1.0	1.0
82.5°	0.5	0.5	1.0	1.0	1.0	0.5	0.5	0.5	0.5	0.5	0.5
85°	0.5	0.5	0.5	0.5	0.5	0.5	0.0	0.0	0.0	0.5	0.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P895845
CATALOG NUMBER: GRZ-05L-935-17x30-X-UNV-STD-1F

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

iO LED

Report Number: SP1-2101-124-3

Luminaire Tested: GRZ-05L-935-10X10-X-UNV-STD-2F


Test Date: 02/10/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-124-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 02/10/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: iO LED
 Catalog Number: **GRZ-05L-935-10X10-X-UNV-STD-2F**
 Description: IO LED Wall Grazer GRZ

Spectral Parameters

CCT (K):	3431	CRI (Ra):	94.0		
CIE u':	0.2369	R1:	94.7	R9:	69.9
CIE v':	0.5141	R2:	95.5	R10:	88.4
Duv:	0.0011	R3:	95.0	R11:	95.7
CIE x:	0.4104	R4:	95.4	R12:	83.2
CIE y:	0.3958	R5:	94.1	R13:	94.8
CIE z:	0.1938	R6:	94.0	R14:	96.6
Peak Wavelength (nm):	624	R7:	95.4		
Dominant Wavelength (nm):	580	R8:	88.3		
Purity:	42.2				
Rf:	93.6				
Rg:	100.6				



Test Conditions


Stabilization Time: 57M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.5/38%
 Sphere Temperature (°C): 24.4

REPORT NUMBER: SP1-2101-124-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	1/31/2021	7/31/2021
Power Meter	IN0071	12/1/2020	12/1/2021
AC Power Source	IN0063	12/1/2020	12/1/2021
DC Power Source	IN0208	12/1/2020	12/1/2021
Sphere Thermometer	IN0085	12/1/2020	12/1/2021
Room Thermometer	IN0046	12/1/2020	12/1/2021

REPORT NUMBER: SP1-2101-124-3

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-124-3

Photopic Flux vs. Wavelength




#####

λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)
360	436	0.0	490	7373	1.0	620	18112	4.7	750	1864	0.0	880	485	0.0
365	370	0.0	495	8181	1.5	625	18107	4.0	755	1693	0.0	885	593	0.0
370	381	0.0	500	8943	2.0	630	17758	3.2	760	1498	0.0	890	677	0.0
375	432	0.0	505	9613	2.7	635	17291	2.6	765	1302	0.0	895	646	0.0
380	398	0.0	510	10245	3.5	640	16854	2.0	770	1180	0.0	900	526	0.0
385	359	0.0	515	10835	4.5	645	16410	1.6	775	1079	0.0	905	557	0.0
390	355	0.0	520	11465	5.6	650	15843	1.2	780	946	0.0	910	613	0.0
395	320	0.0	525	12004	6.4	655	15029	0.9	785	883	0.0	915	556	0.0
400	290	0.0	530	12512	7.4	660	14175	0.6	790	832	0.0	920	623	0.0
405	278	0.0	535	12925	8.0	665	13195	0.4	795	731	0.0	925	528	0.0
410	327	0.0	540	13254	8.6	670	12132	0.3	800	744	0.0	930	586	0.0
415	471	0.0	545	13437	8.9	675	11067	0.2	805	688	0.0	935	744	0.0
420	803	0.0	550	13744	9.3	680	10056	0.1	810	699	0.0	940	610	0.0
425	1501	0.0	555	13925	9.5	685	9011	0.1	815	651	0.0	945	486	0.0
430	2800	0.0	560	14164	9.6	690	8032	0.0	820	620	0.0	950	719	0.0
435	5221	0.1	565	14379	9.6	695	7112	0.0	825	686	0.0	955	527	0.0
440	9255	0.1	570	14511	9.4	700	6301	0.0	830	578	0.0	960	561	0.0
445	12350	0.3	575	14729	9.2	705	5570	0.0	835	502	0.0	965	364	0.0
450	10708	0.3	580	15069	9.0	710	4970	0.0	840	624	0.0	970	739	0.0
455	8053	0.3	585	15482	8.6	715	4396	0.0	845	523	0.0	975	457	0.0
460	7058	0.3	590	15975	8.3	720	3921	0.0	850	555	0.0	980	848	0.0
465	5809	0.3	595	16476	7.8	725	3489	0.0	855	553	0.0	985	1084	0.0
470	5111	0.3	600	17051	7.3	730	3068	0.0	860	424	0.0	990	980	0.0
475	5409	0.4	605	17607	6.8	735	2631	0.0	865	489	0.0	995	1093	0.0
480	5958	0.6	610	17893	6.1	740	2336	0.0	870	652	0.0	1000	1033	0.0
485	6631	0.8	615	18072	5.5	745	2108	0.0	875	622	0.0			

REPORT NUMBER: SP1-2101-124-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: 1600.8

S/P: 1.59

λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)
360	436	0.0	490	7373	11.4	620	18112	0.2	750	1864	0.0	880	485	0.0
365	370	0.0	495	8181	13.2	625	18107	0.2	755	1693	0.0	885	593	0.0
370	381	0.0	500	8943	15.0	630	17758	0.1	760	1498	0.0	890	677	0.0
375	432	0.0	505	9613	16.3	635	17291	0.1	765	1302	0.0	895	646	0.0
380	398	0.0	510	10245	17.4	640	16854	0.0	770	1180	0.0	900	526	0.0
385	359	0.0	515	10835	18.0	645	16410	0.0	775	1079	0.0	905	557	0.0
390	355	0.0	520	11465	18.2	650	15843	0.0	780	946	0.0	910	613	0.0
395	320	0.0	525	12004	18.0	655	15029	0.0	785	883	0.0	915	556	0.0
400	290	0.0	530	12512	17.3	660	14175	0.0	790	832	0.0	920	623	0.0
405	278	0.0	535	12925	16.1	665	13195	0.0	795	731	0.0	925	528	0.0
410	327	0.0	540	13254	14.6	670	12132	0.0	800	744	0.0	930	586	0.0
415	471	0.0	545	13437	12.9	675	11067	0.0	805	688	0.0	935	744	0.0
420	803	0.1	550	13744	11.2	680	10056	0.0	810	699	0.0	940	610	0.0
425	1501	0.4	555	13925	9.5	685	9011	0.0	815	651	0.0	945	486	0.0
430	2800	1.0	560	14164	7.9	690	8032	0.0	820	620	0.0	950	719	0.0
435	5221	2.3	565	14379	6.5	695	7112	0.0	825	686	0.0	955	527	0.0
440	9255	5.2	570	14511	5.1	700	6301	0.0	830	578	0.0	960	561	0.0
445	12350	8.3	575	14729	4.0	705	5570	0.0	835	502	0.0	965	364	0.0
450	10708	8.3	580	15069	3.1	710	4970	0.0	840	624	0.0	970	739	0.0
455	8053	7.0	585	15482	2.4	715	4396	0.0	845	523	0.0	975	457	0.0
460	7058	6.8	590	15975	1.8	720	3921	0.0	850	555	0.0	980	848	0.0
465	5809	6.1	595	16476	1.3	725	3489	0.0	855	553	0.0	985	1084	0.0
470	5111	5.9	600	17051	1.0	730	3068	0.0	860	424	0.0	990	980	0.0
475	5409	6.8	605	17607	0.7	735	2631	0.0	865	489	0.0	995	1093	0.0
480	5958	8.0	610	17893	0.5	740	2336	0.0	870	652	0.0	1000	1033	0.0
485	6631	9.6	615	18072	0.3	745	2108	0.0	875	622	0.0			

REPORT NUMBER: SP1-2101-124-3

Melanopic Flux vs. Wavelength


Melanopic Lumens: 631
M/P: 0.63

λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)
360	436	0.0	490	7373	6.1	620	18112	0.0	750	1864	0.0	880	485	0.0
365	370	0.0	495	8181	6.8	625	18107	0.0	755	1693	0.0	885	593	0.0
370	381	0.0	500	8943	7.2	630	17758	0.0	760	1498	0.0	890	677	0.0
375	432	0.0	505	9613	7.4	635	17291	0.0	765	1302	0.0	895	646	0.0
380	398	0.0	510	10245	7.4	640	16854	0.0	770	1180	0.0	900	526	0.0
385	359	0.0	515	10835	7.1	645	16410	0.0	775	1079	0.0	905	557	0.0
390	355	0.0	520	11465	6.7	650	15843	0.0	780	946	0.0	910	613	0.0
395	320	0.0	525	12004	6.1	655	15029	0.0	785	883	0.0	915	556	0.0
400	290	0.0	530	12512	5.4	660	14175	0.0	790	832	0.0	920	623	0.0
405	278	0.0	535	12925	4.7	665	13195	0.0	795	731	0.0	925	528	0.0
410	327	0.0	540	13254	3.9	670	12132	0.0	800	744	0.0	930	586	0.0
415	471	0.0	545	13437	3.1	675	11067	0.0	805	688	0.0	935	744	0.0
420	803	0.1	550	13744	2.5	680	10056	0.0	810	699	0.0	940	610	0.0
425	1501	0.2	555	13925	1.9	685	9011	0.0	815	651	0.0	945	486	0.0
430	2800	0.6	560	14164	1.4	690	8032	0.0	820	620	0.0	950	719	0.0
435	5221	1.4	565	14379	1.0	695	7112	0.0	825	686	0.0	955	527	0.0
440	9255	3.1	570	14511	0.7	700	6301	0.0	830	578	0.0	960	561	0.0
445	12350	4.9	575	14729	0.5	705	5570	0.0	835	502	0.0	965	364	0.0
450	10708	4.9	580	15069	0.3	710	4970	0.0	840	624	0.0	970	739	0.0
455	8053	4.2	585	15482	0.2	715	4396	0.0	845	523	0.0	975	457	0.0
460	7058	4.2	590	15975	0.2	720	3921	0.0	850	555	0.0	980	848	0.0
465	5809	3.8	595	16476	0.1	725	3489	0.0	855	553	0.0	985	1084	0.0
470	5111	3.7	600	17051	0.1	730	3068	0.0	860	424	0.0	990	980	0.0
475	5409	4.1	605	17607	0.0	735	2631	0.0	865	489	0.0	995	1093	0.0
480	5958	4.8	610	17893	0.0	740	2336	0.0	870	652	0.0	1000	1033	0.0
485	6631	5.5	615	18072	0.0	745	2108	0.0	875	622	0.0			


REPORT NUMBER: SP1-2101-124-3

TM-30-18





Summary

$R_f = 93.6$
 $R_g = 100.6$
 CIE $R_a = 94.0$
 $R_9 = 69.9$

Spectral Power Distribution Comparison




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 93	CES51 = 99	CES76 = 88
CES02 = 62	CES27 = 95	CES52 = 98	CES77 = 92
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 86
CES04 = 70	CES29 = 93	CES54 = 98	CES79 = 97
CES05 = 50	CES30 = 97	CES55 = 97	CES80 = 94
CES06 = 51	CES31 = 94	CES56 = 95	CES81 = 90
CES07 = 43	CES32 = 90	CES57 = 95	CES82 = 97
CES08 = 42	CES33 = 94	CES58 = 96	CES83 = 97
CES09 = 29	CES34 = 93	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 96	CES60 = 96	CES85 = 88
CES11 = 58	CES36 = 90	CES61 = 95	CES86 = 90
CES12 = 64	CES37 = 94	CES62 = 95	CES87 = 93
CES13 = 43	CES38 = 98	CES63 = 94	CES88 = 97
CES14 = 74	CES39 = 99	CES64 = 94	CES89 = 89
CES15 = 71	CES40 = 97	CES65 = 92	CES90 = 97
CES16 = 48	CES41 = 98	CES66 = 92	CES91 = 82
CES17 = 49	CES42 = 94	CES67 = 92	CES92 = 85
CES18 = 56	CES43 = 94	CES68 = 92	CES93 = 91
CES19 = 71	CES44 = 99	CES69 = 93	CES94 = 84
CES20 = 66	CES45 = 96	CES70 = 89	CES95 = 87
CES21 = 86	CES46 = 96	CES71 = 88	CES96 = 93
CES22 = 78	CES47 = 95	CES72 = 95	CES97 = 94
CES23 = 91	CES48 = 96	CES73 = 85	CES98 = 94
CES24 = 90	CES49 = 95	CES74 = 95	CES99 = 94
CES25 = 71	CES50 = 99	CES75 = 88	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)