

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: io LED

Report Number: P895871

Luminaire Tested: **GRZ-15L-935-50x60-X-UNV-STD-1F**

Issue Date: 11/20/2024

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-79-08
Report Number: P895871
Test Lab: INNOVATION CENTER(G3)
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: GRZ-15L-935-50x60-X-UNV-STD-1F
Description: iO LED 90CRI 3500K GRAZER 1500 lumens per ft WITH 50 deg x 60 deg OPTIC
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1167.9 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.95 / 0.87
Luminous Opening: Rectangular (W 1' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P895871
CATALOG NUMBER: GRZ-15L-935-50x60-X-UNV-STD-1F

Luminous Intensity Polar Plot



TEST NUMBER: P895871

CATALOG NUMBER: GRZ-15L-935-50x60-X-UNV-STD-1F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68	68	68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63	63	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59	59	59
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55	55	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51	51	51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48	48	48

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	81753	81753	81753
5°	80665	80885	79265
10°	77205	75939	74602
15°	74843	70599	70057
20°	68577	66399	66316
25°	52259	58165	61806
30°	34201	43342	52490
35°	21393	27747	36962
40°	12155	16454	19910
45°	6739	9433	9844
50°	4330	5475	5364
55°	3197	3704	3321
60°	2350	2634	2350
65°	1910	2078	1742
70°	1284	1491	1491
75°	848	1123	1123
80°	855	855	855
85°	815	815	815

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P895871

CATALOG NUMBER: GRZ-15L-935-50x60-X-UNV-STD-1F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	9.9
10°-20°	298.5	25.6
20°-30°	360.0	30.8
30°-40°	245.7	21.0
40°-50°	97.9	8.4
50°-60°	31.8	2.7
60°-70°	12.8	1.1
70°-80°	4.9	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	773.7	66.3
0°-40°	1019.5	87.3
0°-60°	1149.2	98.4
0°-90°	1167.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1167.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1266	1266	1266	1266	1266	
5°	1244	1243	1248	1226	1223	117
15°	1120	1081	1056	1040	1048	312
25°	734	729	816	842	868	330
35°	271	342	352	502	469	174
45°	74	142	103	140	108	62
55°	28	39	33	32	30	26
65°	12	12	14	12	11	12
75°	3	4	4	4	4	4
85°	1	1	1	1	1	1
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P895871

CATALOG NUMBER: GRZ-15L-935-50x60-X-UNV-STD-1F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1266.1	1266.1	1266.1	1266.1	1266.1
2.5°	1277.4	1264.9	1260.4	1254.7	1225.2
5°	1244.5	1243.4	1247.9	1226.3	1222.9
7.5°	1210.4	1204.8	1201.4	1186.6	1176.4
10°	1177.5	1165.0	1158.2	1137.8	1137.8
12.5°	1150.3	1129.8	1107.1	1086.7	1078.8
15°	1119.6	1081.0	1056.1	1040.0	1048.0
17.5°	1083.3	1023.0	1012.8	991.2	999.2
20°	998.0	957.2	966.3	945.8	965.1
22.5°	875.4	852.7	903.8	899.3	928.8
25°	733.5	729.0	816.4	842.5	867.5
27.5°	580.2	604.0	705.2	776.7	791.4
30°	458.7	496.2	581.3	697.2	704.0
32.5°	360.0	413.3	458.7	604.0	593.8
35°	271.4	341.8	352.0	501.9	468.9
37.5°	199.8	287.3	268.0	395.2	337.3
40°	144.2	235.1	195.2	291.9	236.2
42.5°	102.2	187.3	141.9	211.3	160.1
45°	73.8	141.9	103.3	139.6	107.8
47.5°	55.6	104.4	74.9	91.9	76.1
50°	43.1	73.8	54.5	62.4	53.4
52.5°	35.2	53.4	42.0	44.3	39.7
55°	28.4	38.6	32.9	31.8	29.5
57.5°	22.7	29.5	26.1	25.0	23.8
60°	18.2	21.6	20.4	19.3	18.2
62.5°	14.8	17.0	17.0	14.8	14.8
65°	12.5	12.5	13.6	12.5	11.4
67.5°	9.1	10.2	10.2	9.1	9.1
70°	6.8	7.9	7.9	7.9	7.9
72.5°	5.7	5.7	6.8	5.7	5.7
75°	3.4	4.5	4.5	4.5	4.5
77.5°	2.3	3.4	3.4	3.4	3.4
80°	2.3	2.3	2.3	2.3	2.3
82.5°	1.1	1.1	2.3	1.1	1.1
85°	1.1	1.1	1.1	1.1	1.1
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

iO LED

Report Number: SP1-2101-124-3

Luminaire Tested: GRZ-05L-935-10X10-X-UNV-STD-2F


Test Date: 02/10/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-124-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 02/10/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: iO LED
 Catalog Number: **GRZ-05L-935-10X10-X-UNV-STD-2F**
 Description: IO LED Wall Grazer GRZ

Spectral Parameters

CCT (K):	3431	CRI (Ra):	94.0		
CIE u':	0.2369	R1:	94.7	R9:	69.9
CIE v':	0.5141	R2:	95.5	R10:	88.4
Duv:	0.0011	R3:	95.0	R11:	95.7
CIE x:	0.4104	R4:	95.4	R12:	83.2
CIE y:	0.3958	R5:	94.1	R13:	94.8
CIE z:	0.1938	R6:	94.0	R14:	96.6
Peak Wavelength (nm):	624	R7:	95.4		
Dominant Wavelength (nm):	580	R8:	88.3		
Purity:	42.2				
Rf:	93.6				
Rg:	100.6				



Test Conditions


Stabilization Time: 57M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.5/38%
 Sphere Temperature (°C): 24.4

REPORT NUMBER: SP1-2101-124-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	1/31/2021	7/31/2021
Power Meter	IN0071	12/1/2020	12/1/2021
AC Power Source	IN0063	12/1/2020	12/1/2021
DC Power Source	IN0208	12/1/2020	12/1/2021
Sphere Thermometer	IN0085	12/1/2020	12/1/2021
Room Thermometer	IN0046	12/1/2020	12/1/2021

REPORT NUMBER: SP1-2101-124-3

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-124-3

Photopic Flux vs. Wavelength




#####

λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)
360	436	0.0	490	7373	1.0	620	18112	4.7	750	1864	0.0	880	485	0.0
365	370	0.0	495	8181	1.5	625	18107	4.0	755	1693	0.0	885	593	0.0
370	381	0.0	500	8943	2.0	630	17758	3.2	760	1498	0.0	890	677	0.0
375	432	0.0	505	9613	2.7	635	17291	2.6	765	1302	0.0	895	646	0.0
380	398	0.0	510	10245	3.5	640	16854	2.0	770	1180	0.0	900	526	0.0
385	359	0.0	515	10835	4.5	645	16410	1.6	775	1079	0.0	905	557	0.0
390	355	0.0	520	11465	5.6	650	15843	1.2	780	946	0.0	910	613	0.0
395	320	0.0	525	12004	6.4	655	15029	0.9	785	883	0.0	915	556	0.0
400	290	0.0	530	12512	7.4	660	14175	0.6	790	832	0.0	920	623	0.0
405	278	0.0	535	12925	8.0	665	13195	0.4	795	731	0.0	925	528	0.0
410	327	0.0	540	13254	8.6	670	12132	0.3	800	744	0.0	930	586	0.0
415	471	0.0	545	13437	8.9	675	11067	0.2	805	688	0.0	935	744	0.0
420	803	0.0	550	13744	9.3	680	10056	0.1	810	699	0.0	940	610	0.0
425	1501	0.0	555	13925	9.5	685	9011	0.1	815	651	0.0	945	486	0.0
430	2800	0.0	560	14164	9.6	690	8032	0.0	820	620	0.0	950	719	0.0
435	5221	0.1	565	14379	9.6	695	7112	0.0	825	686	0.0	955	527	0.0
440	9255	0.1	570	14511	9.4	700	6301	0.0	830	578	0.0	960	561	0.0
445	12350	0.3	575	14729	9.2	705	5570	0.0	835	502	0.0	965	364	0.0
450	10708	0.3	580	15069	9.0	710	4970	0.0	840	624	0.0	970	739	0.0
455	8053	0.3	585	15482	8.6	715	4396	0.0	845	523	0.0	975	457	0.0
460	7058	0.3	590	15975	8.3	720	3921	0.0	850	555	0.0	980	848	0.0
465	5809	0.3	595	16476	7.8	725	3489	0.0	855	553	0.0	985	1084	0.0
470	5111	0.3	600	17051	7.3	730	3068	0.0	860	424	0.0	990	980	0.0
475	5409	0.4	605	17607	6.8	735	2631	0.0	865	489	0.0	995	1093	0.0
480	5958	0.6	610	17893	6.1	740	2336	0.0	870	652	0.0	1000	1033	0.0
485	6631	0.8	615	18072	5.5	745	2108	0.0	875	622	0.0			

REPORT NUMBER: SP1-2101-124-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: 1600.8

S/P: 1.59

λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)
360	436	0.0	490	7373	11.4	620	18112	0.2	750	1864	0.0	880	485	0.0
365	370	0.0	495	8181	13.2	625	18107	0.2	755	1693	0.0	885	593	0.0
370	381	0.0	500	8943	15.0	630	17758	0.1	760	1498	0.0	890	677	0.0
375	432	0.0	505	9613	16.3	635	17291	0.1	765	1302	0.0	895	646	0.0
380	398	0.0	510	10245	17.4	640	16854	0.0	770	1180	0.0	900	526	0.0
385	359	0.0	515	10835	18.0	645	16410	0.0	775	1079	0.0	905	557	0.0
390	355	0.0	520	11465	18.2	650	15843	0.0	780	946	0.0	910	613	0.0
395	320	0.0	525	12004	18.0	655	15029	0.0	785	883	0.0	915	556	0.0
400	290	0.0	530	12512	17.3	660	14175	0.0	790	832	0.0	920	623	0.0
405	278	0.0	535	12925	16.1	665	13195	0.0	795	731	0.0	925	528	0.0
410	327	0.0	540	13254	14.6	670	12132	0.0	800	744	0.0	930	586	0.0
415	471	0.0	545	13437	12.9	675	11067	0.0	805	688	0.0	935	744	0.0
420	803	0.1	550	13744	11.2	680	10056	0.0	810	699	0.0	940	610	0.0
425	1501	0.4	555	13925	9.5	685	9011	0.0	815	651	0.0	945	486	0.0
430	2800	1.0	560	14164	7.9	690	8032	0.0	820	620	0.0	950	719	0.0
435	5221	2.3	565	14379	6.5	695	7112	0.0	825	686	0.0	955	527	0.0
440	9255	5.2	570	14511	5.1	700	6301	0.0	830	578	0.0	960	561	0.0
445	12350	8.3	575	14729	4.0	705	5570	0.0	835	502	0.0	965	364	0.0
450	10708	8.3	580	15069	3.1	710	4970	0.0	840	624	0.0	970	739	0.0
455	8053	7.0	585	15482	2.4	715	4396	0.0	845	523	0.0	975	457	0.0
460	7058	6.8	590	15975	1.8	720	3921	0.0	850	555	0.0	980	848	0.0
465	5809	6.1	595	16476	1.3	725	3489	0.0	855	553	0.0	985	1084	0.0
470	5111	5.9	600	17051	1.0	730	3068	0.0	860	424	0.0	990	980	0.0
475	5409	6.8	605	17607	0.7	735	2631	0.0	865	489	0.0	995	1093	0.0
480	5958	8.0	610	17893	0.5	740	2336	0.0	870	652	0.0	1000	1033	0.0
485	6631	9.6	615	18072	0.3	745	2108	0.0	875	622	0.0			

REPORT NUMBER: SP1-2101-124-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: 631

M/P: 0.63

λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)
360	436	0.0	490	7373	6.1	620	18112	0.0	750	1864	0.0	880	485	0.0
365	370	0.0	495	8181	6.8	625	18107	0.0	755	1693	0.0	885	593	0.0
370	381	0.0	500	8943	7.2	630	17758	0.0	760	1498	0.0	890	677	0.0
375	432	0.0	505	9613	7.4	635	17291	0.0	765	1302	0.0	895	646	0.0
380	398	0.0	510	10245	7.4	640	16854	0.0	770	1180	0.0	900	526	0.0
385	359	0.0	515	10835	7.1	645	16410	0.0	775	1079	0.0	905	557	0.0
390	355	0.0	520	11465	6.7	650	15843	0.0	780	946	0.0	910	613	0.0
395	320	0.0	525	12004	6.1	655	15029	0.0	785	883	0.0	915	556	0.0
400	290	0.0	530	12512	5.4	660	14175	0.0	790	832	0.0	920	623	0.0
405	278	0.0	535	12925	4.7	665	13195	0.0	795	731	0.0	925	528	0.0
410	327	0.0	540	13254	3.9	670	12132	0.0	800	744	0.0	930	586	0.0
415	471	0.0	545	13437	3.1	675	11067	0.0	805	688	0.0	935	744	0.0
420	803	0.1	550	13744	2.5	680	10056	0.0	810	699	0.0	940	610	0.0
425	1501	0.2	555	13925	1.9	685	9011	0.0	815	651	0.0	945	486	0.0
430	2800	0.6	560	14164	1.4	690	8032	0.0	820	620	0.0	950	719	0.0
435	5221	1.4	565	14379	1.0	695	7112	0.0	825	686	0.0	955	527	0.0
440	9255	3.1	570	14511	0.7	700	6301	0.0	830	578	0.0	960	561	0.0
445	12350	4.9	575	14729	0.5	705	5570	0.0	835	502	0.0	965	364	0.0
450	10708	4.9	580	15069	0.3	710	4970	0.0	840	624	0.0	970	739	0.0
455	8053	4.2	585	15482	0.2	715	4396	0.0	845	523	0.0	975	457	0.0
460	7058	4.2	590	15975	0.2	720	3921	0.0	850	555	0.0	980	848	0.0
465	5809	3.8	595	16476	0.1	725	3489	0.0	855	553	0.0	985	1084	0.0
470	5111	3.7	600	17051	0.1	730	3068	0.0	860	424	0.0	990	980	0.0
475	5409	4.1	605	17607	0.0	735	2631	0.0	865	489	0.0	995	1093	0.0
480	5958	4.8	610	17893	0.0	740	2336	0.0	870	652	0.0	1000	1033	0.0
485	6631	5.5	615	18072	0.0	745	2108	0.0	875	622	0.0			


REPORT NUMBER: SP1-2101-124-3

TM-30-18





Summary

$R_f = 93.6$
 $R_g = 100.6$
 CIE $R_a = 94.0$
 $R_g = 69.9$

Spectral Power Distribution Comparison




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 93	CES51 = 99	CES76 = 88
CES02 = 62	CES27 = 95	CES52 = 98	CES77 = 92
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 86
CES04 = 70	CES29 = 93	CES54 = 98	CES79 = 97
CES05 = 50	CES30 = 97	CES55 = 97	CES80 = 94
CES06 = 51	CES31 = 94	CES56 = 95	CES81 = 90
CES07 = 43	CES32 = 90	CES57 = 95	CES82 = 97
CES08 = 42	CES33 = 94	CES58 = 96	CES83 = 97
CES09 = 29	CES34 = 93	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 96	CES60 = 96	CES85 = 88
CES11 = 58	CES36 = 90	CES61 = 95	CES86 = 90
CES12 = 64	CES37 = 94	CES62 = 95	CES87 = 93
CES13 = 43	CES38 = 98	CES63 = 94	CES88 = 97
CES14 = 74	CES39 = 99	CES64 = 94	CES89 = 89
CES15 = 71	CES40 = 97	CES65 = 92	CES90 = 97
CES16 = 48	CES41 = 98	CES66 = 92	CES91 = 82
CES17 = 49	CES42 = 94	CES67 = 92	CES92 = 85
CES18 = 56	CES43 = 94	CES68 = 92	CES93 = 91
CES19 = 71	CES44 = 99	CES69 = 93	CES94 = 84
CES20 = 66	CES45 = 96	CES70 = 89	CES95 = 87
CES21 = 86	CES46 = 96	CES71 = 88	CES96 = 93
CES22 = 78	CES47 = 95	CES72 = 95	CES97 = 94
CES23 = 91	CES48 = 96	CES73 = 85	CES98 = 94
CES24 = 90	CES49 = 95	CES74 = 95	CES99 = 94
CES25 = 71	CES50 = 99	CES75 = 88	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)