

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P400768

Luminaire Tested: **ENV-SA1-740-U-SL2-XXB**

Issue Date: 5/20/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P400768  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2004-754-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/20/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: ENV-SA1-740-U-SL2-XXB  
Description: ENTRI LED LUMINAIRE  
(1) 70 CRI, 4000K LIGHTSQUARE IN BATTERY OPERATION WITH 16 LEDS AND TYPE II SPILL LIGHT ELIMINATOR OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 762 lumens  
Efficiency: N/A  
Efficacy: 58.6 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Medium - Non-Cutoff  
BUG Rating: B0 - U0 - G1

Input Watts (W): 13  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P400768

CATALOG NUMBER: ENV-SA1-740-U-SL2-XXB

### Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 1.7 fc  
 Type III - Medium - Non-Cutoff

REPORT NUMBER: P400768

CATALOG NUMBER: ENV-SA1-740-U-SL2-XXB

### Luminous Intensity Polar Plot



— Vertical Plane Through 67-Deg Lateral      - - - Horizontal Cone Through 71-Deg Vertical

REPORT NUMBER: P400768

CATALOG NUMBER: ENV-SA1-740-U-SL2-XXB

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	156.1	0.0	156.1
	% Fixture	20.5	0.0	20.5
<b>Street Side</b>	Lumens	605.9	0.0	605.9
	% Fixture	79.5	0.0	79.5
<b>Total</b>	Lumens	762.0	0.0	762.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	15.4	2.0
10°-20°	37.8	5.0
20°-30°	51.1	6.7
30°-40°	67.3	8.8
40°-50°	95.8	12.6
50°-60°	146.4	19.2
60°-70°	182.8	24.0
70°-80°	147.6	19.4
80°-90°	17.8	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	762.0	100.0
0°-180°	762.0	100.0



REPORT NUMBER: P400768


CATALOG NUMBER: ENV-SA1-740-U-SL2-XXB

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	60.8	8.0			
FM	(30°-60°)	256.0	33.6			
FH	(60°-80°)	274.9	36.1			G0/660
FVH	(80°-90°)	14.2	1.9			G1/100
BL	(0°-30°)	43.6	5.7	B0/110		
BM	(30°-60°)	53.5	7.0	B0/220		
BH	(60°-80°)	55.5	7.3	B0/110		G0/110
BVH	(80°-90°)	3.6	0.5			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B0-U0-G1**

Type III Medium





REPORT NUMBER: P400768

CATALOG NUMBER: ENV-SA1-740-U-SL2-XXB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	67°	75°	85°
0°	173.8	173.8	173.8	173.8	173.8	173.8	173.8	173.8	173.8	173.8	173.8
2.5°	163.9	164.7	164.8	166.3	166.8	168.6	169.6	171.2	171.5	172.4	173.1
5°	153.2	153.4	154.0	155.3	157.4	160.6	163.0	167.1	167.8	170.7	173.2
7.5°	143.7	144.2	145.3	147.3	149.7	153.5	157.2	162.8	163.9	168.5	173.3
10°	137.2	137.8	138.7	140.8	143.3	147.4	151.9	158.4	159.6	166.0	173.0
12.5°	132.1	132.6	133.3	135.7	138.3	142.5	147.1	154.3	155.5	162.9	172.2
15°	128.7	128.8	129.7	131.6	134.6	138.7	143.3	150.7	152.1	160.5	172.0
17.5°	126.6	126.8	127.6	129.1	131.7	135.7	140.2	147.8	149.4	158.5	172.1
20°	126.7	126.9	127.4	127.9	129.8	133.2	137.9	145.6	147.2	157.3	172.9
22.5°	129.0	129.1	129.2	128.5	129.1	131.5	136.1	144.0	145.8	156.8	173.8
25°	133.4	133.4	133.2	131.4	130.0	131.0	135.1	143.5	145.2	156.3	174.6
27.5°	139.4	139.9	138.8	136.7	133.4	131.7	134.9	143.0	144.8	156.3	175.1
30°	147.6	147.9	147.4	144.7	139.3	134.8	135.6	142.7	144.5	156.1	175.2
32.5°	156.0	156.6	157.2	154.8	148.3	140.3	138.2	143.2	144.7	156.0	174.9
35°	164.4	164.9	167.5	167.1	160.0	148.5	142.5	144.9	146.2	156.5	175.1
37.5°	171.7	172.7	176.5	179.5	174.0	159.7	149.8	148.7	149.5	159.3	176.3
40°	179.5	180.9	186.6	192.2	189.8	173.8	160.3	155.7	155.4	164.3	179.2
42.5°	188.2	189.9	197.2	205.3	206.1	191.6	174.2	165.4	165.2	173.0	185.7
45°	198.5	200.1	210.1	219.7	224.4	211.6	191.3	179.2	179.4	185.1	196.0
47.5°	211.3	213.7	223.3	235.6	244.1	234.1	212.0	198.5	197.7	203.3	212.9
50°	229.2	231.1	239.1	251.1	265.9	261.3	238.1	221.8	221.1	223.8	235.5
52.5°	247.9	248.6	252.4	264.8	289.7	294.3	270.3	250.7	248.1	249.6	263.6
55°	249.0	250.4	253.0	268.6	311.1	333.9	305.7	284.7	281.4	280.4	295.5
57.5°	226.2	228.5	231.8	252.1	312.0	379.7	356.1	324.4	318.4	313.5	329.6
60°	177.8	180.8	186.8	211.7	289.7	405.8	440.1	368.9	363.6	346.9	363.0
62.5°	128.6	129.8	135.6	146.8	229.9	407.3	527.6	427.0	414.0	379.3	391.7
65°	103.6	105.5	107.3	107.2	136.1	361.2	585.8	530.5	491.1	415.6	423.3
67.5°	85.3	86.0	90.3	97.7	92.6	223.1	591.6	681.6	641.7	464.6	460.8
70°	71.3	71.5	75.8	89.2	88.6	115.2	496.0	768.6	759.0	544.9	519.5
71°	62.4	64.3	69.0	86.3	88.2	98.4	421.4	773.2	778.1	576.3	528.6
72.5°	49.1	49.1	55.8	79.2	89.0	90.8	310.5	748.1	762.0	612.1	512.8
75°	28.8	28.6	32.3	55.2	90.9	90.5	169.6	621.7	649.9	618.6	474.6
77.5°	16.2	16.6	18.5	30.7	72.2	86.9	97.4	452.7	485.9	517.4	401.4
80°	7.5	7.9	9.3	14.9	42.6	75.0	69.5	294.0	306.6	311.0	189.7
82.5°	2.0	2.2	2.9	5.7	16.5	51.1	51.4	123.1	127.1	73.5	40.7
85°	0.0	0.0	0.0	0.0	0.2	6.3	14.6	22.2	18.4	9.8	8.3
87.5°	0.0	0.0	0.0	0.0	0.0	0.2	0.3	0.4	0.4	0.4	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P400768

CATALOG NUMBER: ENV-SA1-740-U-SL2-XXB

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	173.8	173.8	173.8	173.8	173.8	173.8	173.8	173.8	173.8	173.8	173.8
2.5°	173.6	174.1	174.9	174.7	174.5	173.2	174.0	173.2	173.1	172.8	172.9
5°	174.1	174.7	175.2	174.2	172.5	169.7	168.7	166.2	164.5	163.7	163.2
7.5°	174.7	175.2	175.0	172.2	167.9	162.6	158.0	154.3	150.5	149.8	149.6
10°	174.7	175.2	173.4	168.2	160.8	152.4	145.3	139.4	133.5	131.3	131.6
12.5°	174.3	174.5	170.5	162.0	151.4	139.9	130.0	120.2	112.7	108.0	107.2
15°	174.0	173.6	166.5	154.3	140.2	125.9	111.0	97.8	88.9	82.8	82.1
17.5°	174.0	172.8	161.8	145.6	128.0	108.4	88.6	74.4	64.4	60.9	60.8
20°	174.2	171.6	156.8	136.5	112.9	87.5	66.1	54.0	50.2	49.7	49.8
22.5°	174.4	169.9	151.3	126.1	96.0	65.3	47.3	42.9	43.2	44.5	44.4
25°	174.2	167.7	144.8	114.6	77.6	47.1	38.2	37.1	39.1	40.6	41.0
27.5°	173.6	164.9	137.9	100.9	59.1	37.1	33.3	33.2	35.2	36.6	36.5
30°	172.0	161.5	129.9	86.4	42.7	31.6	30.1	30.4	31.7	33.0	33.0
32.5°	170.2	157.6	121.4	70.6	32.8	28.6	28.1	28.2	29.1	30.1	29.9
35°	168.4	153.9	112.8	54.2	28.7	26.9	26.7	26.5	26.9	27.1	27.1
37.5°	167.3	150.6	103.2	40.8	26.5	25.8	25.3	24.9	24.8	24.6	24.4
40°	167.7	148.4	94.0	31.6	25.2	24.6	23.9	23.3	22.8	22.6	22.5
42.5°	170.8	147.8	83.8	27.2	24.0	23.5	22.6	21.5	21.1	21.1	21.0
45°	177.9	149.7	74.3	25.0	22.9	22.3	20.8	20.1	19.7	19.9	19.9
47.5°	189.1	155.3	65.7	23.9	22.2	21.2	19.5	18.8	18.5	18.6	18.6
50°	205.9	165.9	56.9	22.9	21.3	20.0	18.5	17.7	17.3	17.3	17.3
52.5°	230.5	183.2	50.6	22.3	20.5	19.0	17.6	16.6	16.1	16.1	16.0
55°	260.4	205.8	48.2	21.8	19.5	18.1	16.6	15.6	14.9	14.7	14.8
57.5°	293.2	235.1	51.7	21.7	18.4	17.1	15.6	14.4	13.7	13.6	13.5
60°	327.0	264.1	61.8	21.2	17.6	15.9	14.5	13.4	12.7	12.5	12.4
62.5°	356.2	293.1	78.4	20.7	16.9	14.8	13.3	12.3	11.7	11.4	11.4
65°	391.4	326.3	103.9	21.3	16.6	13.7	12.2	11.3	10.9	10.5	10.5
67.5°	439.4	375.6	123.2	23.9	17.3	12.8	11.0	10.3	10.0	9.8	9.8
70°	486.7	403.2	85.7	28.1	19.3	12.1	9.9	9.4	9.2	9.0	9.0
71°	486.1	388.4	64.4	29.1	20.0	11.8	9.4	9.1	8.9	8.8	8.7
72.5°	461.7	353.1	46.2	28.2	19.6	11.2	8.9	8.6	8.3	8.3	8.2
75°	414.1	311.2	36.1	23.6	16.5	10.0	7.9	7.7	7.5	7.3	7.5
77.5°	339.3	249.0	28.4	18.6	12.5	8.2	7.0	6.7	6.6	6.5	6.6
80°	155.9	108.5	20.7	14.5	9.3	6.6	5.9	5.8	5.7	5.6	5.6
82.5°	37.5	30.4	11.1	9.7	6.4	5.0	4.7	4.7	4.7	4.6	4.6
85°	8.2	8.2	4.5	4.5	3.8	3.5	3.7	3.7	3.7	3.5	3.5
87.5°	0.4	1.3	1.4	2.1	2.2	2.1	2.5	2.6	2.5	2.4	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)