

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: IRiS

Report Number: P106318

Luminaire Tested: **P3LED09NSP10930-E3MRC**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P106318  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13665)  
Test Lab: PEACHTREE CITY  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: IRiS  
Catalog Number: P3LED09NSP10930-E3MRC  
Description: IRIS 3 INCH LED FIXTURE WITH  
SPECULAR CLEAR DOWNLIGHT REFLECTOR  
AND 10 DEGREE PRIMARY OPTIC, 0 DEGREE AIMING ANGLE  
Light Source: (1) 3000K 90CRI LED  
Ballast/Driver: (1) 340mA ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 844.1 lumens  
Efficiency: N/A  
Efficacy: 59.0 lumens/watt  
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.26  
Luminous Opening: Circular (Dia: 0.31' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P106318  
CATALOG NUMBER: P3LED09NSP10930-E3MRC

### Luminous Intensity Polar Plot





TEST NUMBER: P106318

CATALOG NUMBER: P3LED09NSP10930-E3MRC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		107	107	107		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	112	108	105	103	110	106	104	102	103	101	99		100	99	97		98	96	95	94
3	108	104	100	97	107	102	99	97	100	97	95		98	96	94		96	94	92	91
4	105	100	96	93	104	99	96	93	97	94	92		95	93	91		94	91	90	89
5	102	97	93	90	101	96	92	90	94	91	89		93	90	88		91	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86		91	88	86		89	87	85	84
7	97	91	87	84	96	90	87	84	89	86	84		88	85	83		87	85	83	82
8	95	89	85	82	94	88	84	82	87	84	82		86	83	81		86	83	81	80
9	93	86	82	80	92	86	82	80	85	82	79		84	81	79		84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	78		83	80	77		82	79	77	76

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	896083
5°	744937
10°	250124
15°	167142
20°	106424
25°	49845
30°	3824
35°	1148
40°	128
45°	0
50°	0
55°	0
60°	2077
65°	232
70°	287
75°	2169
80°	0
85°	10788



TEST NUMBER: P106318

CATALOG NUMBER: P3LED09NSP10930-E3MRC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	360.5	42.7
10°-20°	314.1	37.2
20°-30°	155.4	18.4
30°-40°	4.1	0.5
40°-50°	1.1	0.1
50°-60°	3.3	0.4
60°-70°	1.3	0.2
70°-80°	2.0	0.2
80°-90°	3.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	830.1	98.3
0°-40°	834.2	98.8
0°-60°	838.6	99.3
0°-90°	845.2	100.1
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	844.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6385	
5°	5288	361
15°	1150	314
25°	322	155
35°	7	4
45°	0	1
55°	0	3
65°	1	1
75°	4	2
85°	7	3
90°	0	



TEST NUMBER: P106318

CATALOG NUMBER: P3LED09NSP10930-E3MRC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6385.1
1°	6431.6
2°	6393.2
3°	6227.5
4°	5885.3
5°	5287.9
6°	4444.0
7°	3469.4
8°	2647.7
9°	2088.6
10°	1755.2
11°	1556.5
12.5°	1360.5
15°	1150.4
17.5°	907.9
20°	712.6
22.5°	552.3
25°	321.9
27.5°	183.9
30°	23.6
32.5°	3.4
35°	6.7
37.5°	4.7
40°	0.7
42.5°	2.7
45°	0.0
47.5°	2.7
50°	0.0
52.5°	0.0
55°	0.0
57.5°	5.4
60°	7.4
62.5°	0.0
65°	0.7
67.5°	0.7
70°	0.7
72.5°	2.7
75°	4.0
77.5°	0.7
80°	0.0
82.5°	3.4
85°	6.7
87.5°	2.0
90°	0.0

(END OF REPORT)