

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: IRiS

Report Number: P108702

Luminaire Tested: **PN3LED12NFL25830-E3MRC**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P108702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13663)
Test Lab: PEACHTREE CITY
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: IRiS
Catalog Number: PN3LED12NFL25830-E3MRC
Description: IRIS 3 INCH LED FIXTURE WITH
SPECULAR CLEAR DOWNLIGHT REFLECTOR
AND 25 DEGREE PRIMARY OPTIC, 0 DEGREE AIMING ANGLE
Light Source: (1) 3000K 80CRI LED
Ballast/Driver: (1) 450mA ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1152.4 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.47
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct

Input Watts (W): 18.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P108702
CATALOG NUMBER: PN3LED12NFL25830-E3MRC

Luminous Intensity Polar Plot





TEST NUMBER: P108702

CATALOG NUMBER: PN3LED12NFL25830-E3MRC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93	91	89	88
5	102	96	92	89	100	95	91	89	93	90	88		92	89	87		91	88	86	85
6	99	93	89	86	98	92	88	85	91	87	85		89	87	84		88	86	84	83
7	96	90	86	83	95	89	85	83	88	85	82		87	84	82		86	83	81	80
8	93	87	83	80	92	86	83	80	86	82	80		85	82	79		84	81	79	78
9	91	84	80	78	90	84	80	78	83	80	77		82	79	77		82	79	77	76
10	89	82	78	75	88	82	78	75	81	78	75		80	77	75		80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	705425
5°	688455
10°	561863
15°	321915
20°	184250
25°	82942
30°	2604
35°	1573
40°	841
45°	228
50°	0
55°	0
60°	0
65°	381
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P108702

CATALOG NUMBER: PN3LED12NFL25830-E3MRC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	381.7	33.1
10°-20°	549.8	47.7
20°-30°	214.7	18.6
30°-40°	4.6	0.4
40°-50°	0.9	0.1
50°-60°	0.4	0.0
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1146.2	99.5
0°-40°	1150.8	99.9
0°-60°	1152.2	100.0
0°-90°	1152.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1152.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4379	
5°	4257	382
15°	1930	550
25°	467	215
35°	8	5
45°	1	1
55°	0	0
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P108702

CATALOG NUMBER: PN3LED12NFL25830-E3MRC

CANDELA DISTRIBUTION (FULL):

0°	
0°	4378.7
2.5°	4381.7
5°	4257.1
7.5°	3995.9
10°	3434.6
12.5°	2671.9
15°	1930.1
17.5°	1397.8
20°	1074.7
22.5°	817.5
25°	466.6
27.5°	162.5
30°	14.0
32.5°	8.0
35°	8.0
37.5°	5.0
40°	4.0
42.5°	2.0
45°	1.0
47.5°	0.0
50°	0.0
52.5°	1.0
55°	0.0
57.5°	1.0
60°	0.0
62.5°	0.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)