

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMARK

Report Number: P295385

Luminaire Tested: **TCRL20S(7040-7050)**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P295385  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-222-4)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMARK  
Catalog Number: TCRL20S(7040-7050)  
Description: TRACER LARGE, STANDARD TRIM NEMA 3x3  
Light Source: (16) 4000K&5000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2038.7 lumens  
Efficiency: N/A  
Efficacy: 115.8 lumens/watt  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
IES Classification: Type V - Short - Full Cutoff  
BUG Rating: B2 - U0 - G0


Input Watts (W): 17.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P295385  
 CATALOG NUMBER: TCRL20S(7040-7050)

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 94 fc  
 Type V - Short - Full Cutoff

REPORT NUMBER: P295385  
CATALOG NUMBER: TCRL20S(7040-7050)

### Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral      - - - Horizontal Cone Through 0-Deg Vertical

REPORT NUMBER: P295385

CATALOG NUMBER: TCRL20S(7040-7050)


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1019.4	0.0	1019.4
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1019.4	0.0	1019.4
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	2038.7	0.0	2038.7
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	660.3	32.4
10°-20°	727.5	35.7
20°-30°	340.1	16.7
30°-40°	151.0	7.4
40°-50°	85.5	4.2
50°-60°	51.9	2.5
60°-70°	20.1	1.0
70°-80°	2.1	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2038.7	100.0
0°-180°	2038.7	100.0



REPORT NUMBER: P295385


CATALOG NUMBER: TCRL20S(7040-7050)

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	864.0	42.4			
FM (30°-60°)	144.2	7.1			
FH (60°-80°)	11.1	0.5			G0/660
FVH (80°-90°)	0.1	0.0			G0/10
BL (0°-30°)	864.0	42.4	B2/1000		
BM (30°-60°)	144.2	7.1	B0/220		
BH (60°-80°)	11.1	0.5	B0/110		G0/660
BVH (80°-90°)	0.1	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G0**

Type V Short



REPORT NUMBER: P295385  
CATALOG NUMBER: TCRL20S(7040-7050)

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9399.6
2.5°	9014.1
5°	7975.9
7.5°	6483.3
10°	4893.2
12.5°	3544.9
15°	2519.1
17.5°	1819.6
20°	1309.9
22.5°	962.8
25°	707.9
27.5°	524.6
30°	388.8
32.5°	295.1
35°	228.8
37.5°	184.6
40°	152.8
42.5°	128.1
45°	108.6
47.5°	93.0
50°	79.3
52.5°	68.3
55°	57.9
57.5°	48.1
60°	37.7
62.5°	28.0
65°	19.5
67.5°	12.4
70°	5.9
72.5°	2.6
75°	1.3
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)