

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: io LED

Report Number: P895803

Luminaire Tested: **GRZ-05L-927-10x10FR-X-UNV-STD-1F**

Issue Date: 11/20/2024

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-79-08
Report Number: P895803
Test Lab: INNOVATION CENTER(G3)
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: GRZ-05L-927-10x10FR-X-UNV-STD-1F
Description: io LED 90CRI 2700K GRAZER 500 lumens per ft WITH 10 deg x 10 deg,
1/3 Frosted OPTIC
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 468.6 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 0.19 / 0.25 / 0.25
Luminous Opening: Rectangular (W 1' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 5.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P895803
CATALOG NUMBER: GRZ-05L-927-10x10FR-X-UNV-STD-1F

Luminous Intensity Polar Plot



0% Up
100% Dn

— 0°-180° - - 45°-225° - - - 90°-270°

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P895803

CATALOG NUMBER: GRZ-05L-927-10x10FR-X-UNV-STD-1F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	98	98	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	95	95	95	93
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	93	93	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89	88
5	102	96	93	90	101	96	92	89	94	91	89	93	90	88	91	89	87	91	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	89	87	85	84
7	97	91	87	85	96	91	87	84	90	86	84	89	86	84	88	85	83	88	85	83	82
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	86	84	82	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	85	82	80	79
10	91	85	82	79	91	85	82	79	84	81	79	84	81	79	83	81	79	83	81	79	78

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	327696	327696	327696
5°	158199	223937	205056
10°	63908	99589	87689
15°	25336	36633	27140
20°	9895	12114	7978
25°	4560	4802	3669
30°	2692	2617	2155
35°	1821	1821	1443
40°	1382	1458	1138
45°	1187	1278	968
50°	1015	1165	824
55°	923	1081	754
60°	814	1059	749
65°	733	1024	733
70°	642	1001	642
75°	474	848	599
80°	372	707	521
85°	370	370	370



TEST NUMBER: P895803

CATALOG NUMBER: GRZ-05L-927-10x10FR-X-UNV-STD-1F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.6	52.2
10°-20°	147.8	31.6
20°-30°	33.0	7.0
30°-40°	14.3	3.0
40°-50°	10.3	2.2
50°-60°	8.2	1.7
60°-70°	6.1	1.3
70°-80°	3.5	0.7
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.4	90.8
0°-40°	439.7	93.8
0°-60°	458.1	97.8
0°-90°	468.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	468.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	5075	5075	5075	5075	5075	
5°	2441	3012	3455	3471	3164	190
15°	379	488	548	451	406	116
25°	64	73	67	53	52	33
35°	23	23	23	20	18	15
45°	13	14	14	12	11	10
55°	8	10	10	9	7	7
65°	5	7	7	6	5	5
75°	2	4	3	3	2	2
85°	0	1	0	1	0	1
90°	0	0	0	0	0	



TEST NUMBER: P895803

CATALOG NUMBER: GRZ-05L-927-10x10FR-X-UNV-STD-1F

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	5075.0	5075.0	5075.0	5075.0	5075.0	5075.0	5075.0	5075.0	5075.0	5075.0	5075.0
1°	4709.0	4856.8	4820.2	4854.9	4861.1	4884.7	4900.2	4910.8	4936.3	4927.2	4895.8
2°	4331.9	4413.7	4408.9	4430.2	4551.0	4534.1	4577.5	4669.0	4654.6	4675.7	4720.0
3°	3687.0	3866.7	3825.3	3821.4	3937.5	3987.6	4159.5	4199.9	4300.6	4368.5	4369.9
4°	2978.7	3095.2	3122.6	3344.6	3332.1	3551.7	3654.3	3738.6	3817.1	4062.7	3955.8
5°	2440.7	2526.9	2612.6	2721.9	2748.9	3011.9	3070.1	3191.5	3403.9	3495.9	3454.9
6°	1998.1	2082.9	2082.4	2192.2	2292.8	2480.6	2545.7	2720.0	2892.9	3014.3	3019.6
7°	1661.9	1710.6	1741.4	1812.2	1924.4	2024.1	2176.3	2290.9	2402.2	2528.8	2605.9
8°	1382.2	1428.9	1446.2	1510.7	1577.2	1718.8	1871.0	1960.1	2076.6	2186.9	2164.7
9°	1161.6	1234.3	1224.2	1262.3	1337.8	1433.7	1524.7	1656.6	1731.8	1840.6	1815.6
10°	974.7	1020.9	1050.9	1098.5	1126.4	1231.4	1286.8	1372.6	1466.9	1481.8	1518.9
12.5°	639.6	650.1	656.4	680.0	731.1	782.1	837.5	882.7	910.7	916.5	943.9
15°	379.0	397.3	401.1	433.4	461.4	488.3	523.5	530.2	545.1	539.4	548.0
17.5°	233.1	235.0	249.5	250.0	280.3	294.3	318.8	324.6	316.4	312.1	312.1
20°	144.0	145.0	148.8	158.9	164.7	180.1	192.6	194.1	189.7	180.6	176.3
22.5°	93.5	96.3	93.5	97.3	103.1	111.7	117.5	118.5	112.7	109.3	108.9
25°	64.0	64.5	66.9	64.5	67.4	72.7	74.6	76.1	71.3	69.8	67.4
27.5°	47.2	47.2	47.2	47.2	48.1	48.1	49.1	49.6	48.1	47.2	47.7
30°	36.1	35.6	36.1	36.1	35.1	36.1	36.6	36.6	35.6	35.6	35.1
32.5°	27.9	28.4	28.9	28.4	27.9	28.4	28.9	28.4	28.4	28.9	27.9
35°	23.1	23.1	23.6	23.1	23.1	23.1	23.6	23.6	23.6	23.6	23.1
37.5°	18.8	19.3	19.7	19.7	19.7	19.7	20.2	20.2	20.7	19.7	19.3
40°	16.4	16.4	16.8	16.8	17.3	16.8	17.3	17.8	17.8	17.3	17.3
42.5°	14.4	14.4	14.9	14.9	14.9	15.4	15.9	15.9	15.9	15.9	15.4
45°	13.0	12.5	13.0	13.5	14.0	14.0	14.4	14.9	14.4	14.4	14.0
47.5°	11.6	11.6	11.6	12.0	12.5	13.0	13.0	13.5	13.5	13.0	12.5
50°	10.1	10.1	10.6	11.1	11.6	12.0	12.0	12.5	12.5	12.0	11.6
52.5°	8.7	8.7	9.1	10.1	10.6	11.1	11.1	11.6	11.6	11.1	10.6
55°	8.2	7.7	8.2	8.7	9.6	10.1	10.6	10.6	10.6	10.1	9.6
57.5°	6.7	6.7	7.2	7.7	8.7	9.6	9.6	10.1	9.6	9.1	9.1
60°	6.3	6.3	6.7	7.2	8.2	9.1	9.1	9.1	8.7	8.2	8.2
62.5°	5.3	5.3	5.8	6.3	7.2	8.2	8.7	8.7	8.2	7.7	7.2
65°	4.8	4.8	4.8	5.8	6.7	7.2	7.7	7.7	7.2	6.7	6.7
67.5°	3.9	3.9	4.3	4.8	5.8	6.3	6.7	7.2	6.7	6.3	5.8
70°	3.4	3.4	3.4	4.3	5.3	5.8	6.3	6.3	5.8	5.3	5.3
72.5°	2.4	2.4	2.9	3.4	4.3	4.8	5.3	5.3	4.8	4.3	4.3
75°	1.9	1.9	2.4	2.9	3.4	3.9	4.3	4.3	4.3	3.9	3.4
77.5°	1.4	1.4	1.9	2.4	2.9	3.4	3.4	3.4	3.4	2.9	2.9
80°	1.0	1.0	1.4	1.4	1.9	2.4	2.4	2.4	2.4	1.9	1.9
82.5°	1.0	0.5	1.0	1.0	1.4	1.4	1.9	1.9	1.4	1.4	1.4
85°	0.5	0.5	0.5	0.5	1.0	1.0	1.0	1.0	1.0	1.0	0.5
87.5°	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P895803

CATALOG NUMBER: GRZ-05L-927-10x10FR-X-UNV-STD-1F

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5075.0	5075.0	5075.0	5075.0	5075.0	5075.0	5075.0	5075.0	5075.0	5075.0
1°	4972.9	5045.6	4997.4	5051.4	5076.9	5076.9	5085.6	5049.0	5024.9	5042.7
2°	4739.3	4802.9	4821.7	4811.1	4778.8	4783.6	4722.4	4716.2	4635.8	4728.7
3°	4403.1	4473.5	4444.6	4407.5	4413.7	4344.9	4246.6	4200.4	4172.0	4159.0
4°	3999.6	4044.9	4037.2	4011.2	3929.7	3849.3	3760.2	3790.1	3608.5	3632.6
5°	3560.9	3611.4	3585.4	3499.7	3470.8	3384.1	3339.3	3246.9	3149.1	3163.6
6°	3063.4	3046.5	3096.1	3035.9	3022.0	2869.3	2845.2	2860.6	2792.2	2786.0
7°	2557.2	2674.8	2642.0	2599.1	2582.8	2491.8	2477.3	2383.9	2389.6	2354.0
8°	2225.4	2237.0	2267.3	2209.1	2156.0	2145.0	2089.1	2034.2	2046.3	2021.2
9°	1850.3	1886.4	1861.8	1867.6	1798.7	1727.5	1701.0	1715.4	1674.5	1680.2
10°	1499.2	1557.5	1542.1	1529.1	1515.5	1441.9	1429.4	1396.6	1375.0	1337.4
12.5°	943.9	922.3	932.8	891.0	874.5	817.3	806.2	792.2	745.5	745.5
15°	574.6	528.8	545.1	492.2	451.3	439.2	408.9	409.4	407.9	406.0
17.5°	302.4	302.4	295.7	253.8	241.3	219.6	216.7	219.6	212.4	213.8
20°	177.7	171.4	161.3	141.6	132.9	123.8	121.9	120.4	120.4	116.1
22.5°	109.3	104.0	98.3	86.2	79.4	76.5	73.7	75.1	75.1	75.6
25°	69.8	65.5	63.1	55.8	53.0	52.5	51.0	49.1	49.6	51.5
27.5°	46.7	44.8	42.8	40.0	38.0	37.1	37.1	37.6	36.6	35.6
30°	35.1	32.7	31.8	30.8	29.4	29.4	29.4	28.9	28.4	28.9
32.5°	27.9	26.5	25.5	24.6	24.1	23.6	24.1	23.6	23.1	22.6
35°	23.1	21.7	21.2	20.7	20.2	19.7	19.7	19.7	18.8	18.3
37.5°	19.3	18.8	18.8	17.8	17.3	16.8	16.8	16.8	15.9	15.9
40°	17.3	16.8	16.4	15.9	15.4	14.9	14.4	14.4	13.5	13.5
42.5°	15.4	14.9	14.9	14.4	14.0	13.0	13.0	12.5	12.0	12.0
45°	14.0	13.5	13.5	13.0	12.5	12.0	11.6	11.1	10.6	10.6
47.5°	13.0	12.5	12.5	12.0	11.1	10.6	10.1	9.6	9.6	9.6
50°	11.6	11.6	11.6	11.1	10.6	10.1	9.1	8.7	8.2	8.2
52.5°	10.6	10.6	10.1	10.1	9.6	9.1	8.2	7.7	7.7	7.7
55°	10.1	9.6	9.6	9.1	8.7	8.7	7.7	7.2	6.7	6.7
57.5°	9.1	8.7	8.7	8.2	8.2	7.7	6.7	6.7	6.3	6.3
60°	8.2	7.7	7.7	7.2	7.2	6.7	6.3	5.8	5.8	5.8
62.5°	7.2	6.7	7.2	6.7	6.7	6.3	5.8	5.3	5.3	5.3
65°	6.7	6.3	6.3	6.3	5.8	5.8	5.3	4.8	4.8	4.8
67.5°	5.8	5.3	5.8	5.3	5.3	4.8	4.8	4.3	4.3	3.9
70°	4.8	4.8	4.8	4.8	4.8	4.3	3.9	3.9	3.4	3.4
72.5°	4.3	4.3	4.3	4.3	3.9	3.9	3.4	3.4	2.9	2.9
75°	3.4	3.4	3.4	3.4	3.4	3.4	2.9	2.9	2.4	2.4
77.5°	2.9	2.9	2.9	2.9	2.9	2.4	2.4	1.9	1.9	1.9
80°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.4	1.4	1.4
82.5°	1.4	1.4	1.4	1.4	1.4	1.0	1.0	1.0	1.0	1.0
85°	1.0	1.0	1.0	1.0	1.0	0.5	0.5	0.5	0.5	0.5
87.5°	0.5	0.5	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

iO LED

Report Number: SP1-2101-124-1

Luminaire Tested: GRZ-05L-927-10X10-X-UNV-STD-2F

Test Date: 02/10/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-124-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 02/10/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: iO LED
 Catalog Number: **GRZ-05L-927-10X10-X-UNV-STD-2F**
 Description: IO LED Wall Grazer GRZ

Spectral Parameters


CCT (K): 2729
 CIE u': 0.2613
 CIE v': 0.5257
 Duv: -0.0007
 CIE x: 0.4561
 CIE y: 0.4078
 CIE z: 0.1361
 Peak Wavelength (nm): 624
 Dominant Wavelength (nm): 584
 Purity: 59.5

 Rf: 93.5
 Rg: 99.9

CRI (Ra):	94.7		
R1:	95.4	R9:	67.0
R2:	98.0	R10:	94.1
R3:	98.7	R11:	96.2
R4:	95.1	R12:	88.6
R5:	95.2	R13:	96.3
R6:	97.5	R14:	98.5
R7:	92.8		
R8:	84.7		

Test Conditions

Stabilization Time: 176M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.1/39%
 Sphere Temperature (°C): 24.5




REPORT NUMBER: SP1-2101-124-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	1/31/2021	7/31/2021
Power Meter	IN0071	12/1/2020	12/1/2021
AC Power Source	IN0063	12/1/2020	12/1/2021
DC Power Source	IN0208	12/1/2020	12/1/2021
Sphere Thermometer	IN0085	12/1/2020	12/1/2021
Room Thermometer	IN0046	12/1/2020	12/1/2021

REPORT NUMBER: SP1-2101-124-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2101-124-1

Photopic Flux vs. Wavelength




#####

λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)
360	309	0.0	490	4342	0.6	620	16630	4.3	750	1836	0.0	880	324	0.0
365	277	0.0	495	4830	0.9	625	16799	3.7	755	1629	0.0	885	500	0.0
370	260	0.0	500	5328	1.2	630	16562	3.0	760	1434	0.0	890	571	0.0
375	295	0.0	505	5798	1.6	635	16219	2.4	765	1231	0.0	895	494	0.0
380	288	0.0	510	6250	2.1	640	15881	1.9	770	1141	0.0	900	267	0.0
385	260	0.0	515	6656	2.8	645	15637	1.5	775	986	0.0	905	379	0.0
390	252	0.0	520	7162	3.5	650	15133	1.1	780	904	0.0	910	465	0.0
395	226	0.0	525	7622	4.1	655	14463	0.8	785	827	0.0	915	557	0.0
400	191	0.0	530	8063	4.7	660	13640	0.6	790	768	0.0	920	412	0.0
405	196	0.0	535	8439	5.2	665	12787	0.4	795	711	0.0	925	332	0.0
410	195	0.0	540	8846	5.8	670	11721	0.3	800	693	0.0	930	466	0.0
415	235	0.0	545	9169	6.1	675	10776	0.2	805	609	0.0	935	480	0.0
420	323	0.0	550	9555	6.5	680	9728	0.1	810	615	0.0	940	404	0.0
425	510	0.0	555	9909	6.8	685	8803	0.1	815	547	0.0	945	502	0.0
430	889	0.0	560	10257	7.0	690	7856	0.0	820	491	0.0	950	495	0.0
435	1599	0.0	565	10655	7.1	695	6947	0.0	825	570	0.0	955	285	0.0
440	2967	0.0	570	11020	7.2	700	6181	0.0	830	477	0.0	960	433	0.0
445	4944	0.1	575	11481	7.1	705	5516	0.0	835	401	0.0	965	277	0.0
450	5950	0.2	580	12032	7.1	710	4865	0.0	840	440	0.0	970	517	0.0
455	5013	0.2	585	12647	7.0	715	4321	0.0	845	330	0.0	975	498	0.0
460	4393	0.2	590	13350	6.9	720	3839	0.0	850	336	0.0	980	465	0.0
465	3971	0.2	595	14054	6.7	725	3403	0.0	855	350	0.0	985	724	0.0
470	3442	0.2	600	14775	6.4	730	2978	0.0	860	266	0.0	990	861	0.0
475	3372	0.3	605	15552	6.0	735	2581	0.0	865	338	0.0	995	562	0.0
480	3623	0.3	610	16054	5.5	740	2292	0.0	870	363	0.0	1000	816	0.0
485	3960	0.5	615	16452	5.0	745	2037	0.0	875	335	0.0			

REPORT NUMBER: SP1-2101-124-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: 1011.1

S/P: 1.32

λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)
360	309	0.0	490	4342	6.7	620	16630	0.2	750	1836	0.0	880	324	0.0
365	277	0.0	495	4830	7.8	625	16799	0.1	755	1629	0.0	885	500	0.0
370	260	0.0	500	5328	8.9	630	16562	0.1	760	1434	0.0	890	571	0.0
375	295	0.0	505	5798	9.9	635	16219	0.1	765	1231	0.0	895	494	0.0
380	288	0.0	510	6250	10.6	640	15881	0.0	770	1141	0.0	900	267	0.0
385	260	0.0	515	6656	11.0	645	15637	0.0	775	986	0.0	905	379	0.0
390	252	0.0	520	7162	11.4	650	15133	0.0	780	904	0.0	910	465	0.0
395	226	0.0	525	7622	11.4	655	14463	0.0	785	827	0.0	915	557	0.0
400	191	0.0	530	8063	11.1	660	13640	0.0	790	768	0.0	920	412	0.0
405	196	0.0	535	8439	10.5	665	12787	0.0	795	711	0.0	925	332	0.0
410	195	0.0	540	8846	9.8	670	11721	0.0	800	693	0.0	930	466	0.0
415	235	0.0	545	9169	8.8	675	10776	0.0	805	609	0.0	935	480	0.0
420	323	0.1	550	9555	7.8	680	9728	0.0	810	615	0.0	940	404	0.0
425	510	0.1	555	9909	6.8	685	8803	0.0	815	547	0.0	945	502	0.0
430	889	0.3	560	10257	5.7	690	7856	0.0	820	491	0.0	950	495	0.0
435	1599	0.7	565	10655	4.8	695	6947	0.0	825	570	0.0	955	285	0.0
440	2967	1.7	570	11020	3.9	700	6181	0.0	830	477	0.0	960	433	0.0
445	4944	3.3	575	11481	3.1	705	5516	0.0	835	401	0.0	965	277	0.0
450	5950	4.6	580	12032	2.5	710	4865	0.0	840	440	0.0	970	517	0.0
455	5013	4.4	585	12647	1.9	715	4321	0.0	845	330	0.0	975	498	0.0
460	4393	4.2	590	13350	1.5	720	3839	0.0	850	336	0.0	980	465	0.0
465	3971	4.2	595	14054	1.1	725	3403	0.0	855	350	0.0	985	724	0.0
470	3442	4.0	600	14775	0.8	730	2978	0.0	860	266	0.0	990	861	0.0
475	3372	4.2	605	15552	0.6	735	2581	0.0	865	338	0.0	995	562	0.0
480	3623	4.9	610	16054	0.4	740	2292	0.0	870	363	0.0	1000	816	0.0
485	3960	5.7	615	16452	0.3	745	2037	0.0	875	335	0.0			

REPORT NUMBER: SP1-2101-124-1

Melanopic Flux vs. Wavelength




Melanopic Lumens: 382.4

M/P: 0.5





λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)
360	309	0.0	490	4342	3.6	620	16630	0.0	750	1836	0.0	880	324	0.0
365	277	0.0	495	4830	4.0	625	16799	0.0	755	1629	0.0	885	500	0.0
370	260	0.0	500	5328	4.3	630	16562	0.0	760	1434	0.0	890	571	0.0
375	295	0.0	505	5798	4.5	635	16219	0.0	765	1231	0.0	895	494	0.0
380	288	0.0	510	6250	4.5	640	15881	0.0	770	1141	0.0	900	267	0.0
385	260	0.0	515	6656	4.3	645	15637	0.0	775	986	0.0	905	379	0.0
390	252	0.0	520	7162	4.2	650	15133	0.0	780	904	0.0	910	465	0.0
395	226	0.0	525	7622	3.9	655	14463	0.0	785	827	0.0	915	557	0.0
400	191	0.0	530	8063	3.5	660	13640	0.0	790	768	0.0	920	412	0.0
405	196	0.0	535	8439	3.0	665	12787	0.0	795	711	0.0	925	332	0.0
410	195	0.0	540	8846	2.6	670	11721	0.0	800	693	0.0	930	466	0.0
415	235	0.0	545	9169	2.1	675	10776	0.0	805	609	0.0	935	480	0.0
420	323	0.0	550	9555	1.7	680	9728	0.0	810	615	0.0	940	404	0.0
425	510	0.1	555	9909	1.3	685	8803	0.0	815	547	0.0	945	502	0.0
430	889	0.2	560	10257	1.0	690	7856	0.0	820	491	0.0	950	495	0.0
435	1599	0.4	565	10655	0.7	695	6947	0.0	825	570	0.0	955	285	0.0
440	2967	1.0	570	11020	0.5	700	6181	0.0	830	477	0.0	960	433	0.0
445	4944	2.0	575	11481	0.4	705	5516	0.0	835	401	0.0	965	277	0.0
450	5950	2.7	580	12032	0.3	710	4865	0.0	840	440	0.0	970	517	0.0
455	5013	2.6	585	12647	0.2	715	4321	0.0	845	330	0.0	975	498	0.0
460	4393	2.6	590	13350	0.1	720	3839	0.0	850	336	0.0	980	465	0.0
465	3971	2.6	595	14054	0.1	725	3403	0.0	855	350	0.0	985	724	0.0
470	3442	2.5	600	14775	0.1	730	2978	0.0	860	266	0.0	990	861	0.0
475	3372	2.6	605	15552	0.0	735	2581	0.0	865	338	0.0	995	562	0.0
480	3623	2.9	610	16054	0.0	740	2292	0.0	870	363	0.0	1000	816	0.0
485	3960	3.3	615	16452	0.0	745	2037	0.0	875	335	0.0			

Summary

$R_f = 93.5$
 $R_g = 99.9$
 CIE $R_a = 94.7$
 $R_9 = 67.0$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 95	CES51 = 99	CES76 = 92
CES02 = 64	CES27 = 95	CES52 = 98	CES77 = 90
CES03 = 32	CES28 = 98	CES53 = 97	CES78 = 90
CES04 = 71	CES29 = 96	CES54 = 96	CES79 = 93
CES05 = 51	CES30 = 97	CES55 = 95	CES80 = 93
CES06 = 52	CES31 = 96	CES56 = 97	CES81 = 84
CES07 = 44	CES32 = 91	CES57 = 96	CES82 = 97
CES08 = 43	CES33 = 98	CES58 = 97	CES83 = 96
CES09 = 29	CES34 = 96	CES59 = 98	CES84 = 96
CES10 = 77	CES35 = 97	CES60 = 95	CES85 = 85
CES11 = 59	CES36 = 88	CES61 = 95	CES86 = 85
CES12 = 66	CES37 = 96	CES62 = 93	CES87 = 93
CES13 = 44	CES38 = 94	CES63 = 95	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 94	CES89 = 87
CES15 = 72	CES40 = 98	CES65 = 92	CES90 = 97
CES16 = 48	CES41 = 98	CES66 = 93	CES91 = 83
CES17 = 50	CES42 = 96	CES67 = 92	CES92 = 83
CES18 = 57	CES43 = 94	CES68 = 92	CES93 = 90
CES19 = 72	CES44 = 99	CES69 = 93	CES94 = 82
CES20 = 68	CES45 = 97	CES70 = 91	CES95 = 88
CES21 = 87	CES46 = 96	CES71 = 90	CES96 = 94
CES22 = 79	CES47 = 94	CES72 = 96	CES97 = 96
CES23 = 92	CES48 = 95	CES73 = 87	CES98 = 95
CES24 = 91	CES49 = 96	CES74 = 91	CES99 = 93
CES25 = 72	CES50 = 99	CES75 = 91	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)