

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: io LED

Report Number: P895832

Luminaire Tested: **GRZ-15L-930-10x60-X-UNV-STD-1F**

Issue Date: 11/20/2024



Test Information

Test Method: LM-79-08
Report Number: P895832
Test Lab: INNOVATION CENTER(G3)
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: GRZ-15L-930-10x60-X-UNV-STD-1F
Description: io LED 90CRI 3000K GRAZER 1500 lumens per ft WITH 10 deg x 60 deg OPTIC
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1347.1 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 0.18 / 0.97 / 0.31
Luminous Opening: Rectangular (W 1' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P895832
CATALOG NUMBER: GRZ-15L-930-10x60-X-UNV-STD-1F

Luminous Intensity Polar Plot





TEST NUMBER: P895832

CATALOG NUMBER: GRZ-15L-930-10x60-X-UNV-STD-1F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 96 | 96 | 96 | 94 |
| 2 | 108 | 104 | 100 | 97 | 106 | 102 | 98 | 95 | 99 | 96 | 93 | 96 | 93 | 91 | 93 | 91 | 89 | 93 | 91 | 89 | 88 |
| 3 | 103 | 97 | 92 | 89 | 101 | 96 | 91 | 88 | 93 | 90 | 86 | 91 | 88 | 85 | 89 | 86 | 84 | 89 | 86 | 84 | 82 |
| 4 | 98 | 91 | 86 | 82 | 97 | 90 | 85 | 82 | 88 | 84 | 81 | 86 | 83 | 80 | 84 | 81 | 79 | 84 | 81 | 79 | 77 |
| 5 | 94 | 86 | 81 | 77 | 92 | 85 | 80 | 76 | 83 | 79 | 76 | 82 | 78 | 75 | 80 | 77 | 74 | 80 | 77 | 74 | 73 |
| 6 | 90 | 82 | 76 | 72 | 88 | 81 | 75 | 72 | 79 | 75 | 71 | 78 | 74 | 71 | 77 | 73 | 70 | 77 | 73 | 70 | 69 |
| 7 | 86 | 77 | 72 | 68 | 85 | 77 | 71 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 73 | 69 | 67 | 73 | 69 | 67 | 65 |
| 8 | 82 | 74 | 68 | 64 | 81 | 73 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 64 | 70 | 66 | 63 | 70 | 66 | 63 | 62 |
| 9 | 79 | 70 | 65 | 61 | 78 | 70 | 64 | 61 | 69 | 64 | 61 | 68 | 64 | 60 | 67 | 63 | 60 | 67 | 63 | 60 | 59 |
| 10 | 76 | 67 | 62 | 58 | 75 | 67 | 61 | 58 | 66 | 61 | 58 | 65 | 61 | 58 | 64 | 60 | 58 | 64 | 60 | 58 | 56 |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 45° | 90° |
|-----|--------|--------|--------|
| 0° | 280333 | 280333 | 280333 |
| 5° | 145197 | 199605 | 263015 |
| 10° | 58741 | 94265 | 254858 |
| 15° | 32869 | 57583 | 290563 |
| 20° | 16052 | 39690 | 288965 |
| 25° | 5764 | 21488 | 231848 |
| 30° | 3064 | 9961 | 145391 |
| 35° | 2128 | 4659 | 92897 |
| 40° | 1838 | 2815 | 65789 |
| 45° | 1644 | 2466 | 52507 |
| 50° | 1547 | 2582 | 33401 |
| 55° | 1306 | 2454 | 16188 |
| 60° | 1330 | 1821 | 8291 |
| 65° | 1375 | 1176 | 4125 |
| 70° | 1454 | 963 | 2417 |
| 75° | 1272 | 973 | 1597 |
| 80° | 967 | 967 | 967 |
| 85° | 963 | 963 | 0 |



TEST NUMBER: P895832
 CATALOG NUMBER: GRZ-15L-930-10x60-X-UNV-STD-1F

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 259.7 | 19.3 |
| 10°-20° | 413.9 | 30.7 |
| 20°-30° | 348.3 | 25.9 |
| 30°-40° | 176.0 | 13.1 |
| 40°-50° | 89.3 | 6.6 |
| 50°-60° | 40.4 | 3.0 |
| 60°-70° | 13.4 | 1.0 |
| 70°-80° | 5.1 | 0.4 |
| 80°-90° | 0.9 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1021.9 | 75.9 |
| 0°-40° | 1197.9 | 88.9 |
| 0°-60° | 1327.6 | 98.6 |
| 0°-90° | 1347.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1347.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|------|-------|------|-------|------|------|
| 0° | 4342 | 4342 | 4342 | 4342 | 4342 | |
| 5° | 2240 | 2431 | 3080 | 3760 | 4058 | 168 |
| 15° | 492 | 581 | 861 | 2061 | 4347 | 139 |
| 25° | 81 | 110 | 302 | 1065 | 3254 | 45 |
| 35° | 27 | 31 | 59 | 446 | 1178 | 18 |
| 45° | 18 | 20 | 27 | 139 | 575 | 14 |
| 55° | 12 | 15 | 22 | 53 | 144 | 11 |
| 65° | 9 | 8 | 8 | 15 | 27 | 9 |
| 75° | 5 | 5 | 4 | 5 | 6 | 5 |
| 85° | 1 | 1 | 1 | 0 | 0 | 1 |
| 90° | 0 | 0 | 0 | 0 | 0 | |

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P895832

CATALOG NUMBER: GRZ-15L-930-10x60-X-UNV-STD-1F

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4341.5 | 4341.5 | 4341.5 | 4341.5 | 4341.5 | 4341.5 | 4341.5 | 4341.5 | 4341.5 | 4341.5 | 4341.5 |
| 1° | 4097.6 | 4258.0 | 4371.0 | 4205.3 | 4333.7 | 4255.4 | 4309.3 | 4222.0 | 4282.4 | 4331.2 | 4296.5 |
| 2° | 3718.9 | 3922.9 | 3916.5 | 3897.3 | 3930.7 | 4096.3 | 4246.4 | 4232.3 | 4299.1 | 4270.8 | 4291.4 |
| 3° | 3264.4 | 3373.6 | 3409.4 | 3464.6 | 3608.5 | 3771.4 | 3956.3 | 4119.3 | 4284.9 | 4318.3 | 4277.2 |
| 4° | 2703.4 | 2743.2 | 2865.2 | 2880.6 | 3154.0 | 3386.4 | 3698.4 | 3883.1 | 4210.5 | 4264.4 | 4250.3 |
| 5° | 2240.1 | 2228.5 | 2344.0 | 2459.5 | 2801.0 | 3079.5 | 3462.1 | 3654.7 | 4075.8 | 4222.0 | 4057.8 |
| 6° | 1741.9 | 1835.7 | 1947.4 | 2055.1 | 2350.4 | 2702.1 | 3112.9 | 3552.0 | 4032.1 | 4162.9 | 4083.5 |
| 7° | 1449.3 | 1468.6 | 1550.7 | 1635.4 | 1955.1 | 2372.2 | 2725.2 | 3281.1 | 3807.4 | 4075.8 | 4112.9 |
| 8° | 1175.9 | 1175.9 | 1282.3 | 1359.4 | 1663.6 | 1962.7 | 2522.5 | 3028.3 | 3681.7 | 4073.2 | 3897.3 |
| 9° | 1001.2 | 1024.4 | 1074.4 | 1196.4 | 1374.8 | 1698.3 | 2179.7 | 2797.1 | 3585.3 | 3998.7 | 4044.9 |
| 10° | 895.9 | 926.8 | 953.7 | 1000.0 | 1191.3 | 1437.7 | 1934.6 | 2572.5 | 3503.2 | 4002.6 | 3887.0 |
| 12.5° | 664.9 | 681.6 | 713.7 | 767.7 | 912.6 | 1062.9 | 1455.7 | 2129.6 | 3105.2 | 4071.9 | 4183.5 |
| 15° | 491.7 | 496.8 | 541.6 | 594.3 | 716.3 | 861.4 | 1124.5 | 1767.6 | 2939.7 | 4193.8 | 4346.6 |
| 17.5° | 363.3 | 369.7 | 399.2 | 448.0 | 531.5 | 715.0 | 967.9 | 1459.6 | 2747.0 | 4184.8 | 4404.4 |
| 20° | 233.6 | 241.3 | 270.8 | 309.3 | 409.5 | 577.6 | 813.9 | 1204.2 | 2464.7 | 3884.4 | 4205.3 |
| 22.5° | 138.7 | 146.4 | 156.7 | 193.8 | 287.5 | 432.6 | 670.1 | 1035.9 | 1962.7 | 3483.9 | 3827.9 |
| 25° | 80.9 | 79.6 | 91.2 | 116.9 | 175.9 | 301.6 | 546.8 | 885.8 | 1603.4 | 3005.2 | 3254.2 |
| 27.5° | 52.7 | 53.9 | 59.1 | 71.9 | 109.2 | 202.8 | 431.3 | 761.2 | 1259.2 | 2288.9 | 2541.7 |
| 30° | 41.1 | 41.1 | 43.7 | 50.1 | 70.6 | 133.6 | 324.8 | 634.1 | 1038.5 | 1747.1 | 1950.0 |
| 32.5° | 32.1 | 33.4 | 34.7 | 38.5 | 50.1 | 87.3 | 233.6 | 507.1 | 846.0 | 1318.3 | 1484.0 |
| 35° | 27.0 | 28.3 | 29.5 | 32.1 | 39.8 | 59.1 | 159.2 | 372.3 | 668.8 | 1000.0 | 1178.5 |
| 37.5° | 24.4 | 24.4 | 25.7 | 27.0 | 33.4 | 42.4 | 104.0 | 254.1 | 511.0 | 822.9 | 928.0 |
| 40° | 21.8 | 21.8 | 23.1 | 24.4 | 29.5 | 33.4 | 64.2 | 166.9 | 398.0 | 679.1 | 780.5 |
| 42.5° | 19.3 | 20.5 | 21.8 | 21.8 | 25.7 | 29.5 | 44.9 | 124.6 | 323.5 | 607.1 | 677.8 |
| 45° | 18.0 | 18.0 | 19.3 | 20.5 | 24.4 | 27.0 | 34.7 | 96.3 | 267.0 | 511.0 | 575.0 |
| 47.5° | 16.7 | 16.7 | 18.0 | 19.3 | 23.1 | 25.7 | 28.3 | 74.5 | 223.3 | 413.4 | 458.3 |
| 50° | 15.4 | 15.4 | 16.7 | 19.3 | 21.8 | 25.7 | 23.1 | 56.5 | 178.4 | 309.3 | 332.5 |
| 52.5° | 12.8 | 14.1 | 15.4 | 16.7 | 19.3 | 24.4 | 19.3 | 43.7 | 147.7 | 216.9 | 218.2 |
| 55° | 11.6 | 11.6 | 12.8 | 15.4 | 16.7 | 21.8 | 15.4 | 32.1 | 115.6 | 149.0 | 143.8 |
| 57.5° | 11.6 | 10.3 | 11.6 | 12.8 | 14.1 | 19.3 | 11.6 | 24.4 | 86.0 | 100.2 | 92.5 |
| 60° | 10.3 | 10.3 | 10.3 | 10.3 | 11.6 | 14.1 | 9.0 | 19.3 | 62.9 | 66.8 | 64.2 |
| 62.5° | 9.0 | 9.0 | 9.0 | 9.0 | 9.0 | 11.6 | 7.7 | 14.1 | 42.4 | 42.4 | 39.8 |
| 65° | 9.0 | 9.0 | 7.7 | 7.7 | 7.7 | 7.7 | 6.4 | 11.6 | 27.0 | 27.0 | 27.0 |
| 67.5° | 9.0 | 7.7 | 7.7 | 6.4 | 6.4 | 6.4 | 5.1 | 9.0 | 16.7 | 19.3 | 18.0 |
| 70° | 7.7 | 7.7 | 6.4 | 6.4 | 5.1 | 5.1 | 5.1 | 7.7 | 11.6 | 12.8 | 12.8 |
| 72.5° | 6.4 | 6.4 | 6.4 | 5.1 | 5.1 | 3.9 | 3.9 | 6.4 | 9.0 | 9.0 | 9.0 |
| 75° | 5.1 | 5.1 | 5.1 | 5.1 | 3.9 | 3.9 | 2.6 | 5.1 | 5.1 | 6.4 | 6.4 |
| 77.5° | 3.9 | 3.9 | 3.9 | 3.9 | 3.9 | 2.6 | 2.6 | 3.9 | 3.9 | 3.9 | 3.9 |
| 80° | 2.6 | 2.6 | 2.6 | 2.6 | 2.6 | 2.6 | 1.3 | 2.6 | 2.6 | 2.6 | 2.6 |
| 82.5° | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 |
| 85° | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

iO LED

Report Number: SP1-2101-124-2

Luminaire Tested: GRZ-05L-930-10X10-X-UNV-STD-2F

Test Date: 02/10/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-124-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 02/10/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: iO LED
 Catalog Number: **GRZ-05L-930-10X10-X-UNV-STD-2F**
 Description: IO LED Wall Grazer GRZ

Spectral Parameters


CCT (K): 2957
 CIE u': 0.2518
 CIE v': 0.5232
 Duv: 0.0007
 CIE x: 0.4409
 CIE y: 0.4072
 CIE z: 0.1519
 Peak Wavelength (nm): 624
 Dominant Wavelength (nm): 582
 Purity: 54.9

 Rf: 93.7
 Rg: 100.3

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 94.1 | | |
| R1: | 94.6 | R9: | 66.4 |
| R2: | 96.3 | R10: | 90.2 |
| R3: | 96.6 | R11: | 96.1 |
| R4: | 95.3 | R12: | 86.8 |
| R5: | 94.2 | R13: | 95.0 |
| R6: | 95.7 | R14: | 97.3 |
| R7: | 94.2 | | |
| R8: | 85.7 | | |

Test Conditions

Stabilization Time: 48M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.4/38%
 Sphere Temperature (°C): 24.4




REPORT NUMBER: SP1-2101-124-2


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-124-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2101-124-2

Photopic Flux vs. Wavelength




#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 368 | 0.0 | 490 | 5466 | 0.8 | 620 | 17862 | 4.6 | 750 | 1898 | 0.0 | 880 | 436 | 0.0 |
| 365 | 310 | 0.0 | 495 | 6091 | 1.1 | 625 | 17922 | 4.0 | 755 | 1681 | 0.0 | 885 | 632 | 0.0 |
| 370 | 293 | 0.0 | 500 | 6757 | 1.5 | 630 | 17723 | 3.2 | 760 | 1509 | 0.0 | 890 | 653 | 0.0 |
| 375 | 346 | 0.0 | 505 | 7358 | 2.1 | 635 | 17256 | 2.6 | 765 | 1279 | 0.0 | 895 | 546 | 0.0 |
| 380 | 338 | 0.0 | 510 | 7854 | 2.7 | 640 | 16836 | 2.0 | 770 | 1201 | 0.0 | 900 | 354 | 0.0 |
| 385 | 299 | 0.0 | 515 | 8389 | 3.5 | 645 | 16513 | 1.6 | 775 | 1028 | 0.0 | 905 | 454 | 0.0 |
| 390 | 270 | 0.0 | 520 | 8991 | 4.4 | 650 | 15949 | 1.2 | 780 | 937 | 0.0 | 910 | 426 | 0.0 |
| 395 | 252 | 0.0 | 525 | 9495 | 5.1 | 655 | 15172 | 0.9 | 785 | 877 | 0.0 | 915 | 565 | 0.0 |
| 400 | 234 | 0.0 | 530 | 9972 | 5.9 | 660 | 14269 | 0.6 | 790 | 784 | 0.0 | 920 | 483 | 0.0 |
| 405 | 236 | 0.0 | 535 | 10431 | 6.5 | 665 | 13357 | 0.4 | 795 | 723 | 0.0 | 925 | 418 | 0.0 |
| 410 | 267 | 0.0 | 540 | 10792 | 7.0 | 670 | 12286 | 0.3 | 800 | 735 | 0.0 | 930 | 416 | 0.0 |
| 415 | 349 | 0.0 | 545 | 11118 | 7.4 | 675 | 11211 | 0.2 | 805 | 729 | 0.0 | 935 | 626 | 0.0 |
| 420 | 560 | 0.0 | 550 | 11517 | 7.8 | 680 | 10179 | 0.1 | 810 | 667 | 0.0 | 940 | 584 | 0.0 |
| 425 | 974 | 0.0 | 555 | 11837 | 8.1 | 685 | 9184 | 0.1 | 815 | 584 | 0.0 | 945 | 579 | 0.0 |
| 430 | 1769 | 0.0 | 560 | 12154 | 8.3 | 690 | 8166 | 0.0 | 820 | 546 | 0.0 | 950 | 504 | 0.0 |
| 435 | 3208 | 0.0 | 565 | 12489 | 8.3 | 695 | 7279 | 0.0 | 825 | 620 | 0.0 | 955 | 485 | 0.0 |
| 440 | 5576 | 0.1 | 570 | 12803 | 8.3 | 700 | 6419 | 0.0 | 830 | 532 | 0.0 | 960 | 719 | 0.0 |
| 445 | 7682 | 0.2 | 575 | 13201 | 8.2 | 705 | 5709 | 0.0 | 835 | 420 | 0.0 | 965 | 552 | 0.0 |
| 450 | 6958 | 0.2 | 580 | 13645 | 8.1 | 710 | 5055 | 0.0 | 840 | 444 | 0.0 | 970 | 586 | 0.0 |
| 455 | 5347 | 0.2 | 585 | 14250 | 7.9 | 715 | 4482 | 0.0 | 845 | 562 | 0.0 | 975 | 439 | 0.0 |
| 460 | 4823 | 0.2 | 590 | 14919 | 7.7 | 720 | 3984 | 0.0 | 850 | 454 | 0.0 | 980 | 736 | 0.0 |
| 465 | 4070 | 0.2 | 595 | 15606 | 7.4 | 725 | 3526 | 0.0 | 855 | 433 | 0.0 | 985 | 863 | 0.0 |
| 470 | 3650 | 0.2 | 600 | 16305 | 7.0 | 730 | 3109 | 0.0 | 860 | 383 | 0.0 | 990 | 722 | 0.0 |
| 475 | 3914 | 0.3 | 605 | 17030 | 6.6 | 735 | 2684 | 0.0 | 865 | 322 | 0.0 | 995 | 579 | 0.0 |
| 480 | 4339 | 0.4 | 610 | 17428 | 6.0 | 740 | 2396 | 0.0 | 870 | 523 | 0.0 | 1000 | 672 | 0.0 |
| 485 | 4881 | 0.6 | 615 | 17762 | 5.4 | 745 | 2098 | 0.0 | 875 | 541 | 0.0 | | | |

REPORT NUMBER: SP1-2101-124-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: 1239

S/P: 1.4

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 368 | 0.0 | 490 | 5466 | 8.4 | 620 | 17862 | 0.2 | 750 | 1898 | 0.0 | 880 | 436 | 0.0 |
| 365 | 310 | 0.0 | 495 | 6091 | 9.8 | 625 | 17922 | 0.2 | 755 | 1681 | 0.0 | 885 | 632 | 0.0 |
| 370 | 293 | 0.0 | 500 | 6757 | 11.3 | 630 | 17723 | 0.1 | 760 | 1509 | 0.0 | 890 | 653 | 0.0 |
| 375 | 346 | 0.0 | 505 | 7358 | 12.5 | 635 | 17256 | 0.1 | 765 | 1279 | 0.0 | 895 | 546 | 0.0 |
| 380 | 338 | 0.0 | 510 | 7854 | 13.3 | 640 | 16836 | 0.0 | 770 | 1201 | 0.0 | 900 | 354 | 0.0 |
| 385 | 299 | 0.0 | 515 | 8389 | 13.9 | 645 | 16513 | 0.0 | 775 | 1028 | 0.0 | 905 | 454 | 0.0 |
| 390 | 270 | 0.0 | 520 | 8991 | 14.3 | 650 | 15949 | 0.0 | 780 | 937 | 0.0 | 910 | 426 | 0.0 |
| 395 | 252 | 0.0 | 525 | 9495 | 14.2 | 655 | 15172 | 0.0 | 785 | 877 | 0.0 | 915 | 565 | 0.0 |
| 400 | 234 | 0.0 | 530 | 9972 | 13.7 | 660 | 14269 | 0.0 | 790 | 784 | 0.0 | 920 | 483 | 0.0 |
| 405 | 236 | 0.0 | 535 | 10431 | 13.0 | 665 | 13357 | 0.0 | 795 | 723 | 0.0 | 925 | 418 | 0.0 |
| 410 | 267 | 0.0 | 540 | 10792 | 11.9 | 670 | 12286 | 0.0 | 800 | 735 | 0.0 | 930 | 416 | 0.0 |
| 415 | 349 | 0.0 | 545 | 11118 | 10.7 | 675 | 11211 | 0.0 | 805 | 729 | 0.0 | 935 | 626 | 0.0 |
| 420 | 560 | 0.1 | 550 | 11517 | 9.4 | 680 | 10179 | 0.0 | 810 | 667 | 0.0 | 940 | 584 | 0.0 |
| 425 | 974 | 0.2 | 555 | 11837 | 8.1 | 685 | 9184 | 0.0 | 815 | 584 | 0.0 | 945 | 579 | 0.0 |
| 430 | 1769 | 0.6 | 560 | 12154 | 6.8 | 690 | 8166 | 0.0 | 820 | 546 | 0.0 | 950 | 504 | 0.0 |
| 435 | 3208 | 1.4 | 565 | 12489 | 5.6 | 695 | 7279 | 0.0 | 825 | 620 | 0.0 | 955 | 485 | 0.0 |
| 440 | 5576 | 3.1 | 570 | 12803 | 4.5 | 700 | 6419 | 0.0 | 830 | 532 | 0.0 | 960 | 719 | 0.0 |
| 445 | 7682 | 5.1 | 575 | 13201 | 3.6 | 705 | 5709 | 0.0 | 835 | 420 | 0.0 | 965 | 552 | 0.0 |
| 450 | 6958 | 5.4 | 580 | 13645 | 2.8 | 710 | 5055 | 0.0 | 840 | 444 | 0.0 | 970 | 586 | 0.0 |
| 455 | 5347 | 4.7 | 585 | 14250 | 2.2 | 715 | 4482 | 0.0 | 845 | 562 | 0.0 | 975 | 439 | 0.0 |
| 460 | 4823 | 4.7 | 590 | 14919 | 1.7 | 720 | 3984 | 0.0 | 850 | 454 | 0.0 | 980 | 736 | 0.0 |
| 465 | 4070 | 4.3 | 595 | 15606 | 1.2 | 725 | 3526 | 0.0 | 855 | 433 | 0.0 | 985 | 863 | 0.0 |
| 470 | 3650 | 4.2 | 600 | 16305 | 0.9 | 730 | 3109 | 0.0 | 860 | 383 | 0.0 | 990 | 722 | 0.0 |
| 475 | 3914 | 4.9 | 605 | 17030 | 0.7 | 735 | 2684 | 0.0 | 865 | 322 | 0.0 | 995 | 579 | 0.0 |
| 480 | 4339 | 5.9 | 610 | 17428 | 0.5 | 740 | 2396 | 0.0 | 870 | 523 | 0.0 | 1000 | 672 | 0.0 |
| 485 | 4881 | 7.1 | 615 | 17762 | 0.3 | 745 | 2098 | 0.0 | 875 | 541 | 0.0 | | | |

REPORT NUMBER: SP1-2101-124-2

Melanopic Flux vs. Wavelength




Melanopic Lumens: 471.9

M/P: 0.53





| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 368 | 0.0 | 490 | 5466 | 4.5 | 620 | 17862 | 0.0 | 750 | 1898 | 0.0 | 880 | 436 | 0.0 |
| 365 | 310 | 0.0 | 495 | 6091 | 5.0 | 625 | 17922 | 0.0 | 755 | 1681 | 0.0 | 885 | 632 | 0.0 |
| 370 | 293 | 0.0 | 500 | 6757 | 5.4 | 630 | 17723 | 0.0 | 760 | 1509 | 0.0 | 890 | 653 | 0.0 |
| 375 | 346 | 0.0 | 505 | 7358 | 5.6 | 635 | 17256 | 0.0 | 765 | 1279 | 0.0 | 895 | 546 | 0.0 |
| 380 | 338 | 0.0 | 510 | 7854 | 5.6 | 640 | 16836 | 0.0 | 770 | 1201 | 0.0 | 900 | 354 | 0.0 |
| 385 | 299 | 0.0 | 515 | 8389 | 5.5 | 645 | 16513 | 0.0 | 775 | 1028 | 0.0 | 905 | 454 | 0.0 |
| 390 | 270 | 0.0 | 520 | 8991 | 5.2 | 650 | 15949 | 0.0 | 780 | 937 | 0.0 | 910 | 426 | 0.0 |
| 395 | 252 | 0.0 | 525 | 9495 | 4.8 | 655 | 15172 | 0.0 | 785 | 877 | 0.0 | 915 | 565 | 0.0 |
| 400 | 234 | 0.0 | 530 | 9972 | 4.3 | 660 | 14269 | 0.0 | 790 | 784 | 0.0 | 920 | 483 | 0.0 |
| 405 | 236 | 0.0 | 535 | 10431 | 3.8 | 665 | 13357 | 0.0 | 795 | 723 | 0.0 | 925 | 418 | 0.0 |
| 410 | 267 | 0.0 | 540 | 10792 | 3.2 | 670 | 12286 | 0.0 | 800 | 735 | 0.0 | 930 | 416 | 0.0 |
| 415 | 349 | 0.0 | 545 | 11118 | 2.6 | 675 | 11211 | 0.0 | 805 | 729 | 0.0 | 935 | 626 | 0.0 |
| 420 | 560 | 0.1 | 550 | 11517 | 2.1 | 680 | 10179 | 0.0 | 810 | 667 | 0.0 | 940 | 584 | 0.0 |
| 425 | 974 | 0.2 | 555 | 11837 | 1.6 | 685 | 9184 | 0.0 | 815 | 584 | 0.0 | 945 | 579 | 0.0 |
| 430 | 1769 | 0.4 | 560 | 12154 | 1.2 | 690 | 8166 | 0.0 | 820 | 546 | 0.0 | 950 | 504 | 0.0 |
| 435 | 3208 | 0.9 | 565 | 12489 | 0.9 | 695 | 7279 | 0.0 | 825 | 620 | 0.0 | 955 | 485 | 0.0 |
| 440 | 5576 | 1.9 | 570 | 12803 | 0.6 | 700 | 6419 | 0.0 | 830 | 532 | 0.0 | 960 | 719 | 0.0 |
| 445 | 7682 | 3.0 | 575 | 13201 | 0.4 | 705 | 5709 | 0.0 | 835 | 420 | 0.0 | 965 | 552 | 0.0 |
| 450 | 6958 | 3.2 | 580 | 13645 | 0.3 | 710 | 5055 | 0.0 | 840 | 444 | 0.0 | 970 | 586 | 0.0 |
| 455 | 5347 | 2.8 | 585 | 14250 | 0.2 | 715 | 4482 | 0.0 | 845 | 562 | 0.0 | 975 | 439 | 0.0 |
| 460 | 4823 | 2.8 | 590 | 14919 | 0.1 | 720 | 3984 | 0.0 | 850 | 454 | 0.0 | 980 | 736 | 0.0 |
| 465 | 4070 | 2.7 | 595 | 15606 | 0.1 | 725 | 3526 | 0.0 | 855 | 433 | 0.0 | 985 | 863 | 0.0 |
| 470 | 3650 | 2.6 | 600 | 16305 | 0.1 | 730 | 3109 | 0.0 | 860 | 383 | 0.0 | 990 | 722 | 0.0 |
| 475 | 3914 | 3.0 | 605 | 17030 | 0.0 | 735 | 2684 | 0.0 | 865 | 322 | 0.0 | 995 | 579 | 0.0 |
| 480 | 4339 | 3.5 | 610 | 17428 | 0.0 | 740 | 2396 | 0.0 | 870 | 523 | 0.0 | 1000 | 672 | 0.0 |
| 485 | 4881 | 4.0 | 615 | 17762 | 0.0 | 745 | 2098 | 0.0 | 875 | 541 | 0.0 | | | |

Summary

$R_f = 93.7$
 $R_g = 100.3$
 CIE $R_a = 94.1$
 $R_9 = 66.4$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 93 | CES51 = 99 | CES76 = 90 |
| CES02 = 63 | CES27 = 96 | CES52 = 98 | CES77 = 92 |
| CES03 = 32 | CES28 = 97 | CES53 = 96 | CES78 = 88 |
| CES04 = 70 | CES29 = 93 | CES54 = 98 | CES79 = 95 |
| CES05 = 51 | CES30 = 96 | CES55 = 98 | CES80 = 95 |
| CES06 = 51 | CES31 = 94 | CES56 = 96 | CES81 = 87 |
| CES07 = 44 | CES32 = 90 | CES57 = 95 | CES82 = 97 |
| CES08 = 42 | CES33 = 94 | CES58 = 96 | CES83 = 96 |
| CES09 = 29 | CES34 = 94 | CES59 = 98 | CES84 = 96 |
| CES10 = 76 | CES35 = 97 | CES60 = 97 | CES85 = 87 |
| CES11 = 59 | CES36 = 92 | CES61 = 96 | CES86 = 87 |
| CES12 = 65 | CES37 = 95 | CES62 = 97 | CES87 = 93 |
| CES13 = 44 | CES38 = 99 | CES63 = 94 | CES88 = 96 |
| CES14 = 74 | CES39 = 99 | CES64 = 95 | CES89 = 87 |
| CES15 = 72 | CES40 = 97 | CES65 = 92 | CES90 = 97 |
| CES16 = 48 | CES41 = 97 | CES66 = 94 | CES91 = 86 |
| CES17 = 50 | CES42 = 95 | CES67 = 93 | CES92 = 85 |
| CES18 = 57 | CES43 = 94 | CES68 = 93 | CES93 = 91 |
| CES19 = 72 | CES44 = 99 | CES69 = 94 | CES94 = 83 |
| CES20 = 67 | CES45 = 96 | CES70 = 91 | CES95 = 88 |
| CES21 = 86 | CES46 = 95 | CES71 = 90 | CES96 = 93 |
| CES22 = 79 | CES47 = 93 | CES72 = 96 | CES97 = 95 |
| CES23 = 92 | CES48 = 95 | CES73 = 87 | CES98 = 94 |
| CES24 = 91 | CES49 = 95 | CES74 = 94 | CES99 = 93 |
| CES25 = 72 | CES50 = 99 | CES75 = 90 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)