

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: io LED

Report Number: P895860

Luminaire Tested: **GRZ-05L-940-30x60-X-UNV-STD-1F**

Issue Date: 11/20/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P895860  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 11/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: GRZ-05L-940-30x60-X-UNV-STD-1F  
Description: io LED 90CRI 4000K GRAZER 500 lumens per ft WITH 30 deg x 60 deg OPTIC  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 460.2 lumens  
Efficiency: N/A  
Efficacy: 86.8 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 1.01 / 0.76  
Luminous Opening: Rectangular (W 1' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P895860  
CATALOG NUMBER: GRZ-05L-940-30x60-X-UNV-STD-1F

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P895860

CATALOG NUMBER: GRZ-05L-940-30x60-X-UNV-STD-1F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 95  | 93  | 96  | 95  | 93  | 92  |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  | 92  | 89  | 87  | 89  | 87  | 85  | 89  | 87  | 85  | 83  |
| 3   | 100 | 92  | 87  | 82  | 98  | 91  | 86  | 81  | 88  | 84  | 80  | 86  | 82  | 79  | 83  | 80  | 78  | 83  | 80  | 78  | 76  |
| 4   | 94  | 85  | 79  | 74  | 92  | 84  | 78  | 74  | 82  | 77  | 73  | 80  | 75  | 72  | 78  | 74  | 71  | 78  | 74  | 71  | 69  |
| 5   | 88  | 79  | 72  | 67  | 87  | 78  | 72  | 67  | 76  | 71  | 66  | 74  | 70  | 66  | 73  | 69  | 65  | 73  | 69  | 65  | 64  |
| 6   | 83  | 73  | 67  | 62  | 82  | 73  | 66  | 62  | 71  | 65  | 61  | 69  | 65  | 61  | 68  | 64  | 60  | 68  | 64  | 60  | 59  |
| 7   | 79  | 68  | 62  | 57  | 77  | 68  | 61  | 57  | 66  | 61  | 57  | 65  | 60  | 56  | 64  | 59  | 56  | 64  | 59  | 56  | 54  |
| 8   | 75  | 64  | 57  | 53  | 73  | 63  | 57  | 53  | 62  | 57  | 53  | 61  | 56  | 52  | 60  | 56  | 52  | 60  | 56  | 52  | 51  |
| 9   | 71  | 60  | 54  | 49  | 70  | 60  | 53  | 49  | 59  | 53  | 49  | 58  | 53  | 49  | 57  | 52  | 49  | 57  | 52  | 49  | 47  |
| 10  | 67  | 57  | 50  | 46  | 66  | 56  | 50  | 46  | 55  | 50  | 46  | 55  | 49  | 46  | 54  | 49  | 46  | 54  | 49  | 46  | 44  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 45°   | 90°   |
|-----|-------|-------|-------|
| 0°  | 32376 | 32376 | 32376 |
| 5°  | 33640 | 33232 | 32473 |
| 10° | 28613 | 31544 | 32521 |
| 15° | 18524 | 25977 | 33097 |
| 20° | 12836 | 18979 | 32344 |
| 25° | 10096 | 14534 | 27330 |
| 30° | 8649  | 11982 | 21503 |
| 35° | 7118  | 10176 | 16222 |
| 40° | 5521  | 8640  | 12096 |
| 45° | 4082  | 6967  | 9360  |
| 50° | 2994  | 5344  | 7434  |
| 55° | 2240  | 3805  | 5437  |
| 60° | 1576  | 2570  | 3668  |
| 65° | 1100  | 1650  | 2475  |
| 70° | 774   | 1114  | 1624  |
| 75° | 574   | 674   | 1123  |
| 80° | 335   | 521   | 855   |
| 85° | 370   | 370   | 370   |



TEST NUMBER: P895860  
 CATALOG NUMBER: GRZ-05L-940-30x60-X-UNV-STD-1F

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 47.4   | 10.3      |
| 10°-20°   | 108.0  | 23.5      |
| 20°-30°   | 110.4  | 24.0      |
| 30°-40°   | 88.4   | 19.2      |
| 40°-50°   | 59.1   | 12.8      |
| 50°-60°   | 31.1   | 6.8       |
| 60°-70°   | 11.8   | 2.6       |
| 70°-80°   | 3.5    | 0.8       |
| 80°-90°   | 0.5    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 265.9  | 57.8      |
| 0°-40°    | 354.2  | 77.0      |
| 0°-60°    | 444.4  | 96.6      |
| 0°-90°    | 460.2  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 460.2  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0°  | 501 | 501   | 501 | 501   | 501 |      |
| 5°  | 519 | 511   | 513 | 505   | 501 | 47   |
| 15° | 277 | 306   | 389 | 472   | 495 | 79   |
| 25° | 142 | 153   | 204 | 335   | 384 | 67   |
| 35° | 90  | 98    | 129 | 187   | 206 | 56   |
| 45° | 45  | 52    | 76  | 101   | 102 | 35   |
| 55° | 20  | 22    | 34  | 46    | 48  | 18   |
| 65° | 7   | 8     | 11  | 15    | 16  | 7    |
| 75° | 2   | 2     | 3   | 4     | 4   | 3    |
| 85° | 0   | 0     | 0   | 0     | 0   | 0    |
| 90° | 0   | 0     | 0   | 0     | 0   |      |

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P895860

CATALOG NUMBER: GRZ-05L-940-30x60-X-UNV-STD-1F

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 5°    | 15°   | 25°   | 35°   | 45°   | 55°   | 65°   | 75°   | 85°   | 90°   |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 501.4 | 501.4 | 501.4 | 501.4 | 501.4 | 501.4 | 501.4 | 501.4 | 501.4 | 501.4 | 501.4 |
| 2.5°  | 506.8 | 506.4 | 511.4 | 507.7 | 509.1 | 507.7 | 503.7 | 501.4 | 501.0 | 496.5 | 498.7 |
| 5°    | 519.0 | 511.8 | 513.2 | 510.9 | 513.2 | 512.7 | 508.2 | 505.5 | 503.2 | 500.5 | 501.0 |
| 7.5°  | 489.7 | 490.6 | 494.7 | 496.5 | 502.8 | 505.0 | 502.8 | 501.0 | 499.2 | 497.8 | 498.3 |
| 10°   | 436.4 | 439.6 | 445.4 | 457.2 | 470.3 | 481.1 | 485.6 | 490.6 | 494.7 | 495.1 | 496.0 |
| 12.5° | 359.3 | 363.8 | 373.3 | 385.9 | 414.8 | 440.9 | 463.1 | 480.2 | 490.1 | 495.6 | 494.7 |
| 15°   | 277.1 | 278.5 | 290.2 | 310.9 | 342.6 | 388.6 | 432.4 | 467.1 | 485.2 | 497.8 | 495.1 |
| 17.5° | 220.7 | 222.5 | 232.0 | 247.8 | 278.0 | 329.0 | 394.5 | 446.3 | 479.3 | 488.3 | 486.1 |
| 20°   | 186.8 | 185.5 | 192.7 | 205.8 | 231.1 | 276.2 | 344.4 | 413.9 | 455.4 | 468.0 | 470.7 |
| 22.5° | 159.8 | 161.1 | 165.6 | 176.0 | 198.2 | 235.6 | 297.9 | 371.4 | 417.5 | 431.4 | 433.7 |
| 25°   | 141.7 | 143.1 | 147.6 | 154.8 | 172.8 | 204.0 | 257.7 | 324.0 | 369.2 | 382.7 | 383.6 |
| 27.5° | 130.0 | 129.1 | 132.2 | 137.7 | 153.4 | 180.1 | 224.3 | 279.4 | 321.3 | 334.9 | 335.8 |
| 30°   | 116.0 | 115.5 | 118.7 | 124.6 | 137.2 | 160.7 | 198.2 | 242.8 | 272.6 | 285.7 | 288.4 |
| 32.5° | 103.4 | 102.9 | 106.5 | 111.5 | 124.1 | 144.4 | 176.9 | 211.7 | 232.0 | 242.8 | 245.5 |
| 35°   | 90.3  | 90.7  | 93.4  | 99.8  | 111.0 | 129.1 | 158.9 | 183.2 | 197.7 | 203.1 | 205.8 |
| 37.5° | 77.6  | 78.1  | 81.7  | 88.0  | 99.3  | 115.5 | 139.5 | 158.4 | 167.0 | 171.0 | 170.6 |
| 40°   | 65.5  | 66.4  | 68.6  | 75.8  | 87.1  | 102.5 | 121.9 | 135.8 | 141.7 | 142.2 | 143.5 |
| 42.5° | 54.6  | 54.6  | 58.2  | 64.1  | 74.9  | 89.4  | 106.5 | 116.4 | 121.0 | 120.5 | 119.6 |
| 45°   | 44.7  | 45.1  | 47.4  | 53.2  | 63.2  | 76.3  | 91.2  | 100.2 | 102.9 | 101.1 | 102.5 |
| 47.5° | 36.5  | 37.0  | 38.8  | 44.2  | 52.8  | 65.5  | 77.2  | 85.8  | 88.0  | 86.7  | 86.7  |
| 50°   | 29.8  | 30.2  | 31.6  | 35.6  | 42.9  | 53.2  | 64.1  | 71.3  | 73.6  | 73.1  | 74.0  |
| 52.5° | 24.4  | 24.4  | 25.7  | 28.9  | 34.7  | 43.3  | 51.9  | 58.2  | 60.0  | 59.6  | 59.1  |
| 55°   | 19.9  | 19.9  | 20.8  | 23.0  | 27.5  | 33.8  | 41.1  | 46.0  | 47.4  | 47.8  | 48.3  |
| 57.5° | 15.8  | 15.8  | 16.2  | 18.0  | 21.2  | 26.2  | 31.6  | 35.2  | 36.5  | 37.0  | 37.4  |
| 60°   | 12.2  | 12.2  | 13.1  | 14.0  | 16.7  | 19.9  | 23.5  | 26.2  | 28.0  | 28.0  | 28.4  |
| 62.5° | 9.5   | 9.5   | 9.9   | 10.8  | 12.6  | 14.9  | 17.1  | 19.4  | 20.3  | 21.2  | 21.7  |
| 65°   | 7.2   | 7.2   | 7.7   | 8.1   | 9.5   | 10.8  | 12.6  | 14.4  | 15.3  | 15.8  | 16.2  |
| 67.5° | 5.4   | 5.4   | 5.4   | 6.3   | 7.2   | 8.1   | 9.0   | 10.4  | 10.8  | 11.7  | 12.2  |
| 70°   | 4.1   | 4.1   | 4.1   | 4.5   | 5.0   | 5.9   | 6.3   | 7.2   | 8.1   | 8.6   | 8.6   |
| 72.5° | 3.2   | 3.2   | 3.2   | 3.2   | 3.6   | 4.1   | 4.5   | 5.0   | 5.9   | 6.3   | 6.3   |
| 75°   | 2.3   | 2.3   | 2.3   | 2.3   | 2.7   | 2.7   | 3.2   | 3.6   | 4.1   | 4.5   | 4.5   |
| 77.5° | 1.8   | 1.8   | 1.4   | 1.8   | 1.8   | 1.8   | 2.3   | 2.3   | 2.7   | 3.2   | 3.2   |
| 80°   | 0.9   | 0.9   | 0.9   | 0.9   | 1.4   | 1.4   | 1.4   | 1.8   | 1.8   | 1.8   | 2.3   |
| 82.5° | 0.5   | 0.5   | 0.5   | 0.5   | 0.9   | 0.9   | 0.9   | 0.9   | 0.9   | 1.4   | 1.4   |
| 85°   | 0.5   | 0.5   | 0.5   | 0.5   | 0.5   | 0.5   | 0.5   | 0.5   | 0.5   | 0.5   | 0.5   |
| 87.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

iO LED

Report Number: SP1-2101-124-4

Luminaire Tested: GRZ-05L-940-10X10-X-UNV-STD-2F

Test Date: 02/11/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-124-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 02/11/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: iO LED  
 Catalog Number: **GRZ-05L-940-10X10-X-UNV-STD-2F**  
 Description: IO LED Wall Grazer GRZ


**Spectral Parameters**

CCT (K): 3816  
 CIE u': 0.2273  
 CIE v': 0.5079  
 Duv: 0.0023  
 CIE x: 0.3907  
 CIE y: 0.3879  
 CIE z: 0.2214  
 Peak Wavelength (nm): 614  
 Dominant Wavelength (nm): 578  
 Purity: 33.8  
  
 Rf: 93.1  
 Rg: 100.2

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 93.3 |      |      |
| R1:       | 93.7 | R9:  | 69.2 |
| R2:       | 94.3 | R10: | 85.8 |
| R3:       | 93.9 | R11: | 94.6 |
| R4:       | 94.7 | R12: | 78.9 |
| R5:       | 92.9 | R13: | 93.7 |
| R6:       | 92.1 | R14: | 96.1 |
| R7:       | 95.7 |      |      |
| R8:       | 88.8 |      |      |

**Test Conditions**

Stabilization Time: 162M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.1/41%  
 Sphere Temperature (°C): 24.1






REPORT NUMBER: SP1-2101-124-4


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-124-4

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 7-step quadrangle

REPORT NUMBER: SP1-2101-124-4

**Photopic Flux vs. Wavelength**




#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 405           | 0.0           | 490    | 7814          | 1.1           | 620    | 16090         | 4.2           | 750    | 1625          | 0.0           | 880    | 367           | 0.0           |
| 365    | 335           | 0.0           | 495    | 8606          | 1.6           | 625    | 16048         | 3.5           | 755    | 1453          | 0.0           | 885    | 533           | 0.0           |
| 370    | 363           | 0.0           | 500    | 9360          | 2.1           | 630    | 15632         | 2.8           | 760    | 1318          | 0.0           | 890    | 535           | 0.0           |
| 375    | 388           | 0.0           | 505    | 10093         | 2.8           | 635    | 15196         | 2.3           | 765    | 1153          | 0.0           | 895    | 583           | 0.0           |
| 380    | 378           | 0.0           | 510    | 10690         | 3.7           | 640    | 14791         | 1.8           | 770    | 1033          | 0.0           | 900    | 438           | 0.0           |
| 385    | 344           | 0.0           | 515    | 11247         | 4.7           | 645    | 14481         | 1.4           | 775    | 948           | 0.0           | 905    | 410           | 0.0           |
| 390    | 323           | 0.0           | 520    | 11881         | 5.8           | 650    | 13840         | 1.0           | 780    | 831           | 0.0           | 910    | 413           | 0.0           |
| 395    | 292           | 0.0           | 525    | 12359         | 6.6           | 655    | 13125         | 0.8           | 785    | 778           | 0.0           | 915    | 489           | 0.0           |
| 400    | 261           | 0.0           | 530    | 12780         | 7.5           | 660    | 12353         | 0.5           | 790    | 708           | 0.0           | 920    | 518           | 0.0           |
| 405    | 272           | 0.0           | 535    | 13137         | 8.1           | 665    | 11536         | 0.4           | 795    | 643           | 0.0           | 925    | 563           | 0.0           |
| 410    | 331           | 0.0           | 540    | 13369         | 8.7           | 670    | 10559         | 0.2           | 800    | 645           | 0.0           | 930    | 452           | 0.0           |
| 415    | 497           | 0.0           | 545    | 13551         | 9.0           | 675    | 9658          | 0.2           | 805    | 648           | 0.0           | 935    | 454           | 0.0           |
| 420    | 847           | 0.0           | 550    | 13731         | 9.3           | 680    | 8746          | 0.1           | 810    | 610           | 0.0           | 940    | 446           | 0.0           |
| 425    | 1620          | 0.0           | 555    | 13860         | 9.5           | 685    | 7852          | 0.1           | 815    | 505           | 0.0           | 945    | 516           | 0.0           |
| 430    | 3114          | 0.0           | 560    | 13921         | 9.5           | 690    | 7031          | 0.0           | 820    | 544           | 0.0           | 950    | 514           | 0.0           |
| 435    | 5958          | 0.1           | 565    | 13987         | 9.3           | 695    | 6210          | 0.0           | 825    | 591           | 0.0           | 955    | 487           | 0.0           |
| 440    | 10649         | 0.2           | 570    | 14001         | 9.1           | 700    | 5517          | 0.0           | 830    | 484           | 0.0           | 960    | 723           | 0.0           |
| 445    | 14435         | 0.3           | 575    | 14097         | 8.8           | 705    | 4890          | 0.0           | 835    | 440           | 0.0           | 965    | 281           | 0.0           |
| 450    | 12623         | 0.3           | 580    | 14256         | 8.5           | 710    | 4342          | 0.0           | 840    | 452           | 0.0           | 970    | 627           | 0.0           |
| 455    | 9257          | 0.3           | 585    | 14467         | 8.0           | 715    | 3886          | 0.0           | 845    | 527           | 0.0           | 975    | 532           | 0.0           |
| 460    | 8011          | 0.3           | 590    | 14814         | 7.7           | 720    | 3470          | 0.0           | 850    | 515           | 0.0           | 980    | 902           | 0.0           |
| 465    | 6473          | 0.3           | 595    | 15120         | 7.2           | 725    | 3080          | 0.0           | 855    | 517           | 0.0           | 985    | 1126          | 0.0           |
| 470    | 5561          | 0.3           | 600    | 15449         | 6.7           | 730    | 2713          | 0.0           | 860    | 406           | 0.0           | 990    | 578           | 0.0           |
| 475    | 5845          | 0.5           | 605    | 15859         | 6.1           | 735    | 2357          | 0.0           | 865    | 434           | 0.0           | 995    | 699           | 0.0           |
| 480    | 6344          | 0.6           | 610    | 16059         | 5.5           | 740    | 2032          | 0.0           | 870    | 578           | 0.0           | 1000   | 687           | 0.0           |
| 485    | 7040          | 0.8           | 615    | 16120         | 4.9           | 745    | 1812          | 0.0           | 875    | 517           | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-124-4

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: 1669.3**

**S/P: 1.71**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 405           | 0.0           | 490    | 7814          | 12.0          | 620    | 16090         | 0.2           | 750    | 1625          | 0.0           | 880    | 367           | 0.0           |
| 365    | 335           | 0.0           | 495    | 8606          | 13.9          | 625    | 16048         | 0.1           | 755    | 1453          | 0.0           | 885    | 533           | 0.0           |
| 370    | 363           | 0.0           | 500    | 9360          | 15.7          | 630    | 15632         | 0.1           | 760    | 1318          | 0.0           | 890    | 535           | 0.0           |
| 375    | 388           | 0.0           | 505    | 10093         | 17.2          | 635    | 15196         | 0.1           | 765    | 1153          | 0.0           | 895    | 583           | 0.0           |
| 380    | 378           | 0.0           | 510    | 10690         | 18.1          | 640    | 14791         | 0.0           | 770    | 1033          | 0.0           | 900    | 438           | 0.0           |
| 385    | 344           | 0.0           | 515    | 11247         | 18.6          | 645    | 14481         | 0.0           | 775    | 948           | 0.0           | 905    | 410           | 0.0           |
| 390    | 323           | 0.0           | 520    | 11881         | 18.9          | 650    | 13840         | 0.0           | 780    | 831           | 0.0           | 910    | 413           | 0.0           |
| 395    | 292           | 0.0           | 525    | 12359         | 18.5          | 655    | 13125         | 0.0           | 785    | 778           | 0.0           | 915    | 489           | 0.0           |
| 400    | 261           | 0.0           | 530    | 12780         | 17.6          | 660    | 12353         | 0.0           | 790    | 708           | 0.0           | 920    | 518           | 0.0           |
| 405    | 272           | 0.0           | 535    | 13137         | 16.4          | 665    | 11536         | 0.0           | 795    | 643           | 0.0           | 925    | 563           | 0.0           |
| 410    | 331           | 0.0           | 540    | 13369         | 14.8          | 670    | 10559         | 0.0           | 800    | 645           | 0.0           | 930    | 452           | 0.0           |
| 415    | 497           | 0.1           | 545    | 13551         | 13.0          | 675    | 9658          | 0.0           | 805    | 648           | 0.0           | 935    | 454           | 0.0           |
| 420    | 847           | 0.1           | 550    | 13731         | 11.2          | 680    | 8746          | 0.0           | 810    | 610           | 0.0           | 940    | 446           | 0.0           |
| 425    | 1620          | 0.4           | 555    | 13860         | 9.5           | 685    | 7852          | 0.0           | 815    | 505           | 0.0           | 945    | 516           | 0.0           |
| 430    | 3114          | 1.1           | 560    | 13921         | 7.8           | 690    | 7031          | 0.0           | 820    | 544           | 0.0           | 950    | 514           | 0.0           |
| 435    | 5958          | 2.7           | 565    | 13987         | 6.3           | 695    | 6210          | 0.0           | 825    | 591           | 0.0           | 955    | 487           | 0.0           |
| 440    | 10649         | 6.0           | 570    | 14001         | 4.9           | 700    | 5517          | 0.0           | 830    | 484           | 0.0           | 960    | 723           | 0.0           |
| 445    | 14435         | 9.7           | 575    | 14097         | 3.8           | 705    | 4890          | 0.0           | 835    | 440           | 0.0           | 965    | 281           | 0.0           |
| 450    | 12623         | 9.8           | 580    | 14256         | 2.9           | 710    | 4342          | 0.0           | 840    | 452           | 0.0           | 970    | 627           | 0.0           |
| 455    | 9257          | 8.1           | 585    | 14467         | 2.2           | 715    | 3886          | 0.0           | 845    | 527           | 0.0           | 975    | 532           | 0.0           |
| 460    | 8011          | 7.7           | 590    | 14814         | 1.6           | 720    | 3470          | 0.0           | 850    | 515           | 0.0           | 980    | 902           | 0.0           |
| 465    | 6473          | 6.8           | 595    | 15120         | 1.2           | 725    | 3080          | 0.0           | 855    | 517           | 0.0           | 985    | 1126          | 0.0           |
| 470    | 5561          | 6.4           | 600    | 15449         | 0.9           | 730    | 2713          | 0.0           | 860    | 406           | 0.0           | 990    | 578           | 0.0           |
| 475    | 5845          | 7.3           | 605    | 15859         | 0.6           | 735    | 2357          | 0.0           | 865    | 434           | 0.0           | 995    | 699           | 0.0           |
| 480    | 6344          | 8.6           | 610    | 16059         | 0.4           | 740    | 2032          | 0.0           | 870    | 578           | 0.0           | 1000   | 687           | 0.0           |
| 485    | 7040          | 10.2          | 615    | 16120         | 0.3           | 745    | 1812          | 0.0           | 875    | 517           | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-124-4

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: 670.2 M/P: 0.69**





| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 405           | 0.0           | 490    | 7814          | 6.5           | 620    | 16090         | 0.0           | 750    | 1625          | 0.0           | 880    | 367           | 0.0           |
| 365    | 335           | 0.0           | 495    | 8606          | 7.1           | 625    | 16048         | 0.0           | 755    | 1453          | 0.0           | 885    | 533           | 0.0           |
| 370    | 363           | 0.0           | 500    | 9360          | 7.5           | 630    | 15632         | 0.0           | 760    | 1318          | 0.0           | 890    | 535           | 0.0           |
| 375    | 388           | 0.0           | 505    | 10093         | 7.7           | 635    | 15196         | 0.0           | 765    | 1153          | 0.0           | 895    | 583           | 0.0           |
| 380    | 378           | 0.0           | 510    | 10690         | 7.7           | 640    | 14791         | 0.0           | 770    | 1033          | 0.0           | 900    | 438           | 0.0           |
| 385    | 344           | 0.0           | 515    | 11247         | 7.3           | 645    | 14481         | 0.0           | 775    | 948           | 0.0           | 905    | 410           | 0.0           |
| 390    | 323           | 0.0           | 520    | 11881         | 6.9           | 650    | 13840         | 0.0           | 780    | 831           | 0.0           | 910    | 413           | 0.0           |
| 395    | 292           | 0.0           | 525    | 12359         | 6.3           | 655    | 13125         | 0.0           | 785    | 778           | 0.0           | 915    | 489           | 0.0           |
| 400    | 261           | 0.0           | 530    | 12780         | 5.5           | 660    | 12353         | 0.0           | 790    | 708           | 0.0           | 920    | 518           | 0.0           |
| 405    | 272           | 0.0           | 535    | 13137         | 4.7           | 665    | 11536         | 0.0           | 795    | 643           | 0.0           | 925    | 563           | 0.0           |
| 410    | 331           | 0.0           | 540    | 13369         | 3.9           | 670    | 10559         | 0.0           | 800    | 645           | 0.0           | 930    | 452           | 0.0           |
| 415    | 497           | 0.0           | 545    | 13551         | 3.1           | 675    | 9658          | 0.0           | 805    | 648           | 0.0           | 935    | 454           | 0.0           |
| 420    | 847           | 0.1           | 550    | 13731         | 2.5           | 680    | 8746          | 0.0           | 810    | 610           | 0.0           | 940    | 446           | 0.0           |
| 425    | 1620          | 0.3           | 555    | 13860         | 1.9           | 685    | 7852          | 0.0           | 815    | 505           | 0.0           | 945    | 516           | 0.0           |
| 430    | 3114          | 0.7           | 560    | 13921         | 1.4           | 690    | 7031          | 0.0           | 820    | 544           | 0.0           | 950    | 514           | 0.0           |
| 435    | 5958          | 1.6           | 565    | 13987         | 1.0           | 695    | 6210          | 0.0           | 825    | 591           | 0.0           | 955    | 487           | 0.0           |
| 440    | 10649         | 3.6           | 570    | 14001         | 0.7           | 700    | 5517          | 0.0           | 830    | 484           | 0.0           | 960    | 723           | 0.0           |
| 445    | 14435         | 5.7           | 575    | 14097         | 0.5           | 705    | 4890          | 0.0           | 835    | 440           | 0.0           | 965    | 281           | 0.0           |
| 450    | 12623         | 5.8           | 580    | 14256         | 0.3           | 710    | 4342          | 0.0           | 840    | 452           | 0.0           | 970    | 627           | 0.0           |
| 455    | 9257          | 4.9           | 585    | 14467         | 0.2           | 715    | 3886          | 0.0           | 845    | 527           | 0.0           | 975    | 532           | 0.0           |
| 460    | 8011          | 4.7           | 590    | 14814         | 0.1           | 720    | 3470          | 0.0           | 850    | 515           | 0.0           | 980    | 902           | 0.0           |
| 465    | 6473          | 4.2           | 595    | 15120         | 0.1           | 725    | 3080          | 0.0           | 855    | 517           | 0.0           | 985    | 1126          | 0.0           |
| 470    | 5561          | 4.0           | 600    | 15449         | 0.1           | 730    | 2713          | 0.0           | 860    | 406           | 0.0           | 990    | 578           | 0.0           |
| 475    | 5845          | 4.5           | 605    | 15859         | 0.0           | 735    | 2357          | 0.0           | 865    | 434           | 0.0           | 995    | 699           | 0.0           |
| 480    | 6344          | 5.1           | 610    | 16059         | 0.0           | 740    | 2032          | 0.0           | 870    | 578           | 0.0           | 1000   | 687           | 0.0           |
| 485    | 7040          | 5.8           | 615    | 16120         | 0.0           | 745    | 1812          | 0.0           | 875    | 517           | 0.0           |        |               |               |

**Summary**

$R_f = 93.1$   
 $R_g = 100.2$   
 CIE  $R_a = 93.3$   
 $R_9 = 69.2$




**Color Vector Graphics**






**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |             |            |            |
|------------|-------------|------------|------------|
| CES01 = 86 | CES26 = 93  | CES51 = 99 | CES76 = 86 |
| CES02 = 62 | CES27 = 94  | CES52 = 98 | CES77 = 90 |
| CES03 = 31 | CES28 = 96  | CES53 = 95 | CES78 = 84 |
| CES04 = 69 | CES29 = 94  | CES54 = 97 | CES79 = 97 |
| CES05 = 49 | CES30 = 99  | CES55 = 96 | CES80 = 94 |
| CES06 = 51 | CES31 = 95  | CES56 = 95 | CES81 = 92 |
| CES07 = 42 | CES32 = 90  | CES57 = 94 | CES82 = 97 |
| CES08 = 41 | CES33 = 96  | CES58 = 95 | CES83 = 97 |
| CES09 = 29 | CES34 = 93  | CES59 = 97 | CES84 = 95 |
| CES10 = 74 | CES35 = 96  | CES60 = 95 | CES85 = 87 |
| CES11 = 57 | CES36 = 87  | CES61 = 94 | CES86 = 91 |
| CES12 = 63 | CES37 = 94  | CES62 = 93 | CES87 = 92 |
| CES13 = 43 | CES38 = 95  | CES63 = 94 | CES88 = 97 |
| CES14 = 74 | CES39 = 99  | CES64 = 93 | CES89 = 89 |
| CES15 = 71 | CES40 = 97  | CES65 = 90 | CES90 = 97 |
| CES16 = 47 | CES41 = 99  | CES66 = 91 | CES91 = 79 |
| CES17 = 49 | CES42 = 93  | CES67 = 90 | CES92 = 84 |
| CES18 = 56 | CES43 = 94  | CES68 = 90 | CES93 = 91 |
| CES19 = 71 | CES44 = 100 | CES69 = 91 | CES94 = 85 |
| CES20 = 66 | CES45 = 96  | CES70 = 88 | CES95 = 86 |
| CES21 = 85 | CES46 = 96  | CES71 = 85 | CES96 = 93 |
| CES22 = 78 | CES47 = 97  | CES72 = 95 | CES97 = 94 |
| CES23 = 91 | CES48 = 96  | CES73 = 82 | CES98 = 94 |
| CES24 = 90 | CES49 = 95  | CES74 = 95 | CES99 = 93 |
| CES25 = 71 | CES50 = 99  | CES75 = 85 |            |





Color Rendition by Hue-Angle Bin





Measure Comparisons



(END OF REPORT)