

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: IRiS

Report Number: P106255

Luminaire Tested: **P3LED09FL40835-E3MRC**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P106255
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13660)
Test Lab: PEACHTREE CITY
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: IRiS
Catalog Number: P3LED09FL40835-E3MRC
Description: IRIS 3 INCH LED FIXTURE WITH
SPECULAR CLEAR DOWNLIGHT REFLECTOR
AND 40 DEGREE PRIMARY OPTIC, 0 DEGREE AIMING ANGLE
Light Source: (1) 3500K 80CRI LED
Ballast/Driver: (1) 340mA ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1018.4 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.62
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct

Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P106255
CATALOG NUMBER: P3LED09FL40835-E3MRC

Luminous Intensity Polar Plot





TEST NUMBER: P106255

CATALOG NUMBER: P3LED09FL40835-E3MRC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96
2	110	106	103	100	108	105	102	99	101	99	97	98	97	95	96	94	93	91
3	106	101	97	94	104	100	96	93	97	94	91	95	92	90	93	91	89	87
4	102	96	92	88	101	95	91	88	93	90	87	91	88	86	89	87	85	84
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80
6	95	88	83	80	94	87	83	79	86	82	79	84	81	78	83	80	78	77
7	92	84	79	76	90	84	79	76	82	78	75	81	78	75	80	77	75	74
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71
9	85	78	73	70	84	77	73	70	76	72	69	76	72	69	75	71	69	68
10	82	75	70	67	82	74	70	67	74	70	67	73	69	67	72	69	66	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	354525
5°	356607
10°	347414
15°	284889
20°	203349
25°	87866
30°	52385
35°	19864
40°	189
45°	0
50°	226
55°	0
60°	0
65°	343
70°	424
75°	560
80°	835
85°	0



TEST NUMBER: P106255

CATALOG NUMBER: P3LED09FL40835-E3MRC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.4	20.5
10°-20°	464.7	45.6
20°-30°	273.0	26.8
30°-40°	70.2	6.9
40°-50°	0.5	0.1
50°-60°	0.3	0.0
60°-70°	0.3	0.0
70°-80°	0.5	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	946.1	92.9
0°-40°	1016.3	99.8
0°-60°	1017.2	99.9
0°-90°	1018.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1018.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2201	
5°	2205	208
15°	1708	465
25°	494	273
35°	101	70
45°	0	1
55°	0	0
65°	1	0
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P106255

CATALOG NUMBER: P3LED09FL40835-E3MRC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2200.6
2.5°	2202.4
5°	2205.1
7.5°	2196.1
10°	2123.7
12.5°	1936.9
15°	1708.1
17.5°	1450.7
20°	1186.1
22.5°	905.5
25°	494.3
27.5°	342.3
30°	281.6
32.5°	200.2
35°	101.0
37.5°	28.6
40°	0.9
42.5°	0.9
45°	0.0
47.5°	0.9
50°	0.9
52.5°	0.0
55°	0.0
57.5°	0.9
60°	0.0
62.5°	0.0
65°	0.9
67.5°	0.0
70°	0.9
72.5°	0.0
75°	0.9
77.5°	0.0
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)