

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P246994

Luminaire Tested: **203-FL-8LED2710-12-BK-DIFF**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246994
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-12)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-FL-8LED2710-12-BK-DIFF
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 10 DEGREE SPOT OPTIC, FLUSH HOOD BLACK, DIFFUSED LENS
Light Source: (1) SORAA 2700K 90 CRI LED
SM16-07-10D-927-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 261.9 lumens
Efficiency: N/A
Efficacy: 32.7 lumens/watt
Spacing Criteria (0/90/45): 0.38 / 0.38 / 0.41
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246994
CATALOG NUMBER: 203-FL-8LED2710-12-BK-DIFF

Luminous Intensity Polar Plot





TEST NUMBER: P246994

CATALOG NUMBER: 203-FL-8LED2710-12-BK-DIFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	86
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	69	68
7	86	77	71	67	84	76	71	67	75	70	67		74	70	67		73	69	66	65
8	82	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		67	64	61	60
10	77	68	62	59	76	67	62	59	67	62	59		66	62	59		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	443647
5°	382047
10°	254303
15°	147821
20°	82904
25°	50192
30°	33271
35°	24755
40°	19966
45°	16537
50°	14737
55°	13333
60°	11742
65°	10624
70°	7934
75°	7053
80°	5114
85°	0



TEST NUMBER: P246994

CATALOG NUMBER: 203-FL-8LED2710-12-BK-DIFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.9	24.8
10°-20°	81.0	30.9
20°-30°	44.1	16.8
30°-40°	26.3	10.1
40°-50°	18.7	7.1
50°-60°	13.9	5.3
60°-70°	8.7	3.3
70°-80°	3.9	1.5
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	189.9	72.5
0°-40°	216.3	82.6
0°-60°	248.8	95.0
0°-90°	261.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	261.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	899	
5°	771	65
15°	289	81
25°	92	44
35°	41	26
45°	24	19
55°	16	14
65°	9	9
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P246994

CATALOG NUMBER: 203-FL-8LED2710-12-BK-DIFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	899.2
1°	891.0
2°	872.7
3°	846.2
4°	812.5
5°	771.4
6°	723.9
7°	672.8
8°	617.1
9°	562.3
10°	507.6
11°	455.5
12°	408.1
13°	365.2
14°	325.0
15°	289.4
17.5°	211.8
20°	157.9
22.5°	118.7
25°	92.2
27.5°	73.0
30°	58.4
32.5°	48.4
35°	41.1
37.5°	35.6
40°	31.0
42.5°	27.4
45°	23.7
47.5°	21.0
50°	19.2
52.5°	17.3
55°	15.5
57.5°	13.7
60°	11.9
62.5°	10.0
65°	9.1
67.5°	7.3
70°	5.5
72.5°	4.6
75°	3.7
77.5°	2.7
80°	1.8
82.5°	0.9
85°	0.0
87.5°	0.0



TEST NUMBER: P246994

CATALOG NUMBER: 203-FL-8LED2710-12-BK-DIFF

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

(END OF REPORT)