

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-8LED4025-12-BK**

Test Date: 04/06/18

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-8LED4025-12-BK
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD BLACK
Light Source: (1) SORAA 4000K 95 CRI 25°NFL LED
SM16-07-25D-940-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004


Summary

Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	372.3 lumens	Max Intensity:	2559 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	47.1 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	18.2°H x 18.2°V	Field Angle (10%):	39.8°H x 39.8°V
Beam Lumens:	146.6 lumens	Field Lumens:	316.7 lumens
Beam Efficiency:	39.4%	Field Efficiency:	85.1%
Input Watts (W):	7.9		
Input Voltage (V):	12.0		
Input Current (Ain):	0.693		
Voltage Rise (V):	NR		
Power Factor:	0.9491		
Total Harmonic Distortion (THDi):	26.9%		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	9 HR		
Ambient Temperature (°C):	25.1		
Test Distance:	25 FT		



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED4025-12-BK

Iso-Candela Plot




REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40		0.0	0.0	0.0	0.0	0.1	0.2	0.3	0.3	0.2	0.1	0.0	0.0	0.0	0.0	0.0	
30	0.0	0.0	0.0	0.0	0.1	0.3	1.3	3.0	3.0	1.3	0.3	0.1	0.0	0.0	0.0	0.0	0.0
20		0.0	0.0	0.0	0.2	1.3	6.6	15.1	15.1	6.6	1.3	0.2	0.0	0.0	0.0	0.0	
10	0.0	0.0	0.0	0.0	0.2	2.8	14.7	46.4	46.4	14.7	2.8	0.2	0.0	0.0	0.0	0.0	0.0
0		0.0	0.0	0.0	0.2	2.8	14.7	46.4	46.4	14.7	2.8	0.2	0.0	0.0	0.0	0.0	
-10	0.0	0.0	0.0	0.0	0.2	1.3	6.6	15.1	15.1	6.6	1.3	0.2	0.0	0.0	0.0	0.0	0.0
-20		0.0	0.0	0.0	0.1	0.3	1.3	3.0	3.0	1.3	0.3	0.1	0.0	0.0	0.0	0.0	
-30	0.0	0.0	0.0	0.0	0.0	0.1	0.2	0.3	0.3	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0
-40		0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED4025-12-BK


Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED4025-12-BK

Luminous Intensity Plot



Beam:
H Angle: 18.2°
V Angle: 18.2°
Lumens: 146.6
Efficiency: 39.4%

Field:
H Angle: 39.8°
V Angle: 39.8°
Lumens: 316.7
Efficiency: 85.1%

Spill:
Lumens: 55.7
Efficiency: 14.9%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	1
50°	0	0	0	0	0	0	0	0	0	1	1
47.5°	0	0	0	0	0	0	0	0	1	1	1
45°	0	0	0	0	0	0	0	1	1	1	1
42.5°	0	0	0	0	0	0	1	1	1	1	1
40°	0	0	0	0	0	1	1	1	1	1	1
37.5°	0	0	0	0	1	1	1	1	1	1	1
35°	0	0	0	0	1	1	1	1	1	1	1
32.5°	0	0	0	1	1	1	1	1	1	1	1
30°	0	0	0	1	1	1	1	1	1	1	1
27.5°	0	0	0	1	1	1	1	1	1	1	2
25°	0	0	1	1	1	1	1	1	1	2	2
22.5°	0	0	1	1	1	1	1	1	1	2	3
20°	0	0	1	1	1	1	1	1	2	2	3
17.5°	0	0	1	1	1	1	1	1	2	3	4
15°	0	1	1	1	1	1	1	1	2	3	4
12.5°	0	1	1	1	1	1	1	1	2	3	4
10°	0	1	1	1	1	1	1	2	3	4	5
7.5°	0	1	1	1	1	1	1	2	3	4	5
5°	0	1	1	1	1	1	1	2	3	4	5
2.5°	0	1	1	1	1	1	1	2	3	4	5
0°	0	1	1	1	1	1	1	2	3	4	5
-2.5°	0	1	1	1	1	1	1	2	3	4	5
-5°	0	1	1	1	1	1	1	2	3	4	5
-7.5°	0	1	1	1	1	1	1	2	3	4	5
-10°	0	1	1	1	1	1	1	2	3	4	5
-12.5°	0	1	1	1	1	1	1	1	2	3	4
-15°	0	1	1	1	1	1	1	1	2	3	4
-17.5°	0	0	1	1	1	1	1	1	2	3	4
-20°	0	0	1	1	1	1	1	1	2	2	3



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	0	0	1	1	1	1	1	1	1	2	3
-25°	0	0	1	1	1	1	1	1	1	2	2
-27.5°	0	0	0	1	1	1	1	1	1	1	2
-30°	0	0	0	1	1	1	1	1	1	1	1
-32.5°	0	0	0	1	1	1	1	1	1	1	1
-35°	0	0	0	0	1	1	1	1	1	1	1
-37.5°	0	0	0	0	1	1	1	1	1	1	1
-40°	0	0	0	0	0	1	1	1	1	1	1
-42.5°	0	0	0	0	0	0	1	1	1	1	1
-45°	0	0	0	0	0	0	0	1	1	1	1
-47.5°	0	0	0	0	0	0	0	0	1	1	1
-50°	0	0	0	0	0	0	0	0	0	1	1
-52.5°	0	0	0	0	0	0	0	0	0	0	1
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	1	1	1
57.5°	0	0	0	0	1	1	1	1	1	1	1
55°	0	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	2
42.5°	1	1	1	1	1	1	2	2	2	2	3
40°	1	1	1	1	2	2	2	3	3	3	4
37.5°	1	1	1	2	2	3	3	4	4	4	5
35°	1	1	2	3	3	4	4	5	5	6	7
32.5°	1	2	3	3	4	4	5	6	7	9	10
30°	2	3	3	4	5	6	7	9	12	14	17
27.5°	3	3	4	5	6	8	11	14	18	22	32
25°	3	4	5	6	8	12	16	21	35	48	65
22.5°	4	4	6	8	12	17	25	43	65	90	114
20°	4	5	7	11	16	25	45	75	106	139	170
17.5°	5	6	9	14	21	43	75	113	153	201	248
15°	5	7	12	18	35	65	106	153	212	279	350
12.5°	6	9	14	22	48	90	139	201	279	368	467
10°	7	10	17	32	65	114	170	248	350	467	605
7.5°	7	11	19	40	81	134	205	300	420	566	749
5°	8	12	21	46	93	150	230	340	477	663	940
2.5°	8	13	22	50	100	159	246	365	514	725	1066
0°	8	13	22	51	102	162	251	373	526	746	1110
-2.5°	8	13	22	50	100	159	246	365	514	725	1066
-5°	8	12	21	46	93	150	230	340	477	663	940
-7.5°	7	11	19	40	81	134	205	300	420	566	749
-10°	7	10	17	32	65	114	170	248	350	467	605
-12.5°	6	9	14	22	48	90	139	201	279	368	467
-15°	5	7	12	18	35	65	106	153	212	279	350
-17.5°	5	6	9	14	21	43	75	113	153	201	248
-20°	4	5	7	11	16	25	45	75	106	139	170



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	4	4	6	8	12	17	25	43	65	90	114
-25°	3	4	5	6	8	12	16	21	35	48	65
-27.5°	3	3	4	5	6	8	11	14	18	22	32
-30°	2	3	3	4	5	6	7	9	12	14	17
-32.5°	1	2	3	3	4	4	5	6	7	9	10
-35°	1	1	2	3	3	4	4	5	5	6	7
-37.5°	1	1	1	2	2	3	3	4	4	4	5
-40°	1	1	1	1	2	2	2	3	3	3	4
-42.5°	1	1	1	1	1	1	2	2	2	2	3
-45°	1	1	1	1	1	1	1	1	1	1	2
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-55°	0	1	1	1	1	1	1	1	1	1	1
-57.5°	0	0	0	0	1	1	1	1	1	1	1
-60°	0	0	0	0	0	0	0	0	1	1	1
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	1	1	1	1	1	1	1	1	1	1	0
57.5°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
45°	2	2	2	2	2	2	2	2	1	1	1
42.5°	3	3	3	3	3	3	3	3	2	2	2
40°	4	4	4	4	4	4	4	4	3	3	3
37.5°	5	5	5	5	5	5	5	5	4	4	4
35°	7	8	8	8	8	8	7	7	6	5	5
32.5°	11	12	13	13	13	12	11	10	9	7	6
30°	19	21	22	22	22	21	19	17	14	12	9
27.5°	40	46	50	51	50	46	40	32	22	18	14
25°	81	93	100	102	100	93	81	65	48	35	21
22.5°	134	150	159	162	159	150	134	114	90	65	43
20°	205	230	246	251	246	230	205	170	139	106	75
17.5°	300	340	365	373	365	340	300	248	201	153	113
15°	420	477	514	526	514	477	420	350	279	212	153
12.5°	566	663	725	746	725	663	566	467	368	279	201
10°	749	940	1066	1110	1066	940	749	605	467	350	248
7.5°	1024	1289	1496	1574	1496	1289	1024	749	566	420	300
5°	1289	1656	1929	2035	1929	1656	1289	940	663	477	340
2.5°	1496	1929	2267	2397	2267	1929	1496	1066	725	514	365
0°	1574	2035	2397	2559	2397	2035	1574	1110	746	526	373
-2.5°	1496	1929	2267	2397	2267	1929	1496	1066	725	514	365
-5°	1289	1656	1929	2035	1929	1656	1289	940	663	477	340
-7.5°	1024	1289	1496	1574	1496	1289	1024	749	566	420	300
-10°	749	940	1066	1110	1066	940	749	605	467	350	248
-12.5°	566	663	725	746	725	663	566	467	368	279	201
-15°	420	477	514	526	514	477	420	350	279	212	153
-17.5°	300	340	365	373	365	340	300	248	201	153	113
-20°	205	230	246	251	246	230	205	170	139	106	75



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	134	150	159	162	159	150	134	114	90	65	43
-25°	81	93	100	102	100	93	81	65	48	35	21
-27.5°	40	46	50	51	50	46	40	32	22	18	14
-30°	19	21	22	22	22	21	19	17	14	12	9
-32.5°	11	12	13	13	13	12	11	10	9	7	6
-35°	7	8	8	8	8	8	7	7	6	5	5
-37.5°	5	5	5	5	5	5	5	5	4	4	4
-40°	4	4	4	4	4	4	4	4	3	3	3
-42.5°	3	3	3	3	3	3	3	3	2	2	2
-45°	2	2	2	2	2	2	2	2	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	1	1	0	0	0	0	0
52.5°	1	1	1	1	1	1	1	1	0	0	0
50°	1	1	1	1	1	1	1	1	1	0	0
47.5°	1	1	1	1	1	1	1	1	1	1	0
45°	1	1	1	1	1	1	1	1	1	1	1
42.5°	2	1	1	1	1	1	1	1	1	1	1
40°	2	2	2	1	1	1	1	1	1	1	1
37.5°	3	3	2	2	1	1	1	1	1	1	1
35°	4	4	3	3	2	1	1	1	1	1	1
32.5°	5	4	4	3	3	2	1	1	1	1	1
30°	7	6	5	4	3	3	2	1	1	1	1
27.5°	11	8	6	5	4	3	3	2	1	1	1
25°	16	12	8	6	5	4	3	2	2	1	1
22.5°	25	17	12	8	6	4	4	3	2	1	1
20°	45	25	16	11	7	5	4	3	2	2	1
17.5°	75	43	21	14	9	6	5	4	3	2	1
15°	106	65	35	18	12	7	5	4	3	2	1
12.5°	139	90	48	22	14	9	6	4	3	2	1
10°	170	114	65	32	17	10	7	5	4	3	2
7.5°	205	134	81	40	19	11	7	5	4	3	2
5°	230	150	93	46	21	12	8	5	4	3	2
2.5°	246	159	100	50	22	13	8	5	4	3	2
0°	251	162	102	51	22	13	8	5	4	3	2
-2.5°	246	159	100	50	22	13	8	5	4	3	2
-5°	230	150	93	46	21	12	8	5	4	3	2
-7.5°	205	134	81	40	19	11	7	5	4	3	2
-10°	170	114	65	32	17	10	7	5	4	3	2
-12.5°	139	90	48	22	14	9	6	4	3	2	1
-15°	106	65	35	18	12	7	5	4	3	2	1
-17.5°	75	43	21	14	9	6	5	4	3	2	1
-20°	45	25	16	11	7	5	4	3	2	2	1



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	25	17	12	8	6	4	4	3	2	1	1
-25°	16	12	8	6	5	4	3	2	2	1	1
-27.5°	11	8	6	5	4	3	3	2	1	1	1
-30°	7	6	5	4	3	3	2	1	1	1	1
-32.5°	5	4	4	3	3	2	1	1	1	1	1
-35°	4	4	3	3	2	1	1	1	1	1	1
-37.5°	3	3	2	2	1	1	1	1	1	1	1
-40°	2	2	2	1	1	1	1	1	1	1	1
-42.5°	2	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	0
-50°	1	1	1	1	1	1	1	1	1	0	0
-52.5°	1	1	1	1	1	1	1	1	0	0	0
-55°	1	1	1	1	1	1	0	0	0	0	0
-57.5°	1	1	1	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	1	0	0	0	0	0	0	0	0	0	0
40°	1	1	0	0	0	0	0	0	0	0	0
37.5°	1	1	1	0	0	0	0	0	0	0	0
35°	1	1	1	0	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
27.5°	1	1	1	1	0	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
22.5°	1	1	1	1	1	0	0	0	0	0	0
20°	1	1	1	1	1	0	0	0	0	0	0
17.5°	1	1	1	1	1	0	0	0	0	0	0
15°	1	1	1	1	1	1	0	0	0	0	0
12.5°	1	1	1	1	1	1	0	0	0	0	0
10°	1	1	1	1	1	1	0	0	0	0	0
7.5°	1	1	1	1	1	1	0	0	0	0	0
5°	1	1	1	1	1	1	0	0	0	0	0
2.5°	1	1	1	1	1	1	0	0	0	0	0
0°	1	1	1	1	1	1	0	0	0	0	0
-2.5°	1	1	1	1	1	1	0	0	0	0	0
-5°	1	1	1	1	1	1	0	0	0	0	0
-7.5°	1	1	1	1	1	1	0	0	0	0	0
-10°	1	1	1	1	1	1	0	0	0	0	0
-12.5°	1	1	1	1	1	1	0	0	0	0	0
-15°	1	1	1	1	1	1	0	0	0	0	0
-17.5°	1	1	1	1	1	0	0	0	0	0	0
-20°	1	1	1	1	1	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	1	1	1	1	1	0	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	0	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-35°	1	1	1	0	0	0	0	0	0	0	0
-37.5°	1	1	1	0	0	0	0	0	0	0	0
-40°	1	1	0	0	0	0	0	0	0	0	0
-42.5°	1	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-5 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED4025-12-BK

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0

(END OF REPORT)